

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331621-940

Luminaire Tested: **S122RDIP-S290D530U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331621-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S290D530U940-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2893.8 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 25.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	95	91	87	84	86	82	79	77	66	64	62	52	50	49	38	37	37	30
2	87	80	74	70	78	73	68	64	59	55	53	46	44	42	34	33	32	26
3	80	71	64	59	72	64	59	54	52	48	45	41	38	36	31	29	28	23
4	73	63	56	50	66	57	51	46	47	42	39	37	34	31	28	26	24	20
5	67	56	49	43	61	51	45	40	42	37	34	34	30	28	26	23	22	18
6	62	51	43	38	56	46	40	35	38	33	30	31	27	24	23	21	19	16
7	58	46	38	33	52	42	36	31	35	30	26	28	24	22	22	19	17	15
8	53	42	35	29	48	38	32	27	32	27	24	26	22	20	20	18	16	13
9	50	38	31	26	45	35	29	25	29	25	21	24	20	18	19	16	14	12
10	47	35	28	24	42	32	26	22	27	22	19	22	19	16	17	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9411	9411	9411	9411
5°	10511	9470	8399	9470
10°	11663	9404	7279	9404
15°	12236	9267	5735	9267
20°	10608	9062	4962	9062
25°	6957	8783	4431	8783
30°	4683	8444	4010	8444
35°	3792	8016	3617	8016
40°	3372	7552	3347	7552
45°	3053	7005	2987	7005
50°	2778	6465	2768	6465
55°	2609	5866	2578	5866
60°	2186	5318	2160	5318
65°	1841	4829	2090	4829
70°	1699	4310	1969	4310
75°	1591	3755	1822	3755
80°	1469	3096	1618	3096
85°	1352	2445	1426	2445



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.3	1.9
10°-20°	154.0	5.3
20°-30°	198.4	6.9
30°-40°	188.6	6.5
40°-50°	161.5	5.6
50°-60°	123.0	4.3
60°-70°	77.8	2.7
70°-80°	38.8	1.3
80°-90°	11.7	0.4
90°-100°	21.5	0.7
100°-110°	78.7	2.7
110°-120°	210.3	7.3
120°-130°	347.1	12.0
130°-140°	369.2	12.8
140°-150°	343.1	11.9
150°-160°	275.9	9.5
160°-170°	177.8	6.1
170°-180°	61.2	2.1
0°-30°	407.7	14.1
0°-40°	596.2	20.6
0°-60°	880.8	30.4
0°-90°	1009.1	34.9
90°-120°	310.4	10.7
90°-150°	1369.9	47.3
90°-180°	1885.0	65.1
0°-180°	2893.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	583	583	583	583	583	
5°	648	584	518	584	648	64
15°	732	554	343	554	732	197
25°	390	493	249	493	390	185
35°	192	407	184	407	192	123
45°	134	307	131	307	134	103
55°	93	208	92	208	93	81
65°	48	126	55	126	48	49
75°	26	60	29	60	26	27
85°	7	13	8	13	7	8
90°	13	0	13	0	13	6
95°	20	30	20	30	20	19
105°	35	141	35	141	35	37
115°	38	268	38	268	38	96
125°	398	378	398	378	398	344
135°	484	468	484	468	484	373
145°	551	543	551	543	551	345
155°	598	598	598	598	598	276
165°	629	630	629	630	629	177
175°	641	644	641	644	641	61
180°	643	643	643	643	643	



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	606.6	607.1	607.6	606.5	606.5	605.5	603.3	601.7	597.2	596.6	596.6
5°	648.5	648.2	649.0	646.3	642.7	641.9	638.0	632.9	627.7	621.9	620.6
7.5°	690.3	689.6	688.0	687.6	684.8	678.7	672.5	665.9	657.2	648.6	644.4
10°	711.4	718.1	714.0	706.9	708.3	698.8	693.8	685.0	677.7	664.9	662.2
12.5°	732.1	734.8	733.4	729.4	727.6	721.0	714.2	706.6	693.1	681.7	671.7
15°	732.0	735.8	736.9	735.7	736.6	736.3	732.6	726.4	714.6	702.0	691.1
17.5°	678.0	680.6	687.3	691.8	697.5	709.4	715.4	717.6	716.0	708.7	701.1
20°	617.4	613.0	631.6	641.1	649.2	669.4	686.9	693.6	704.3	704.1	702.0
22.5°	531.5	532.5	550.2	561.5	585.1	605.5	625.3	650.4	671.2	684.9	692.9
25°	390.5	398.2	415.8	431.2	457.5	495.3	529.5	569.2	606.6	636.2	664.4
27.5°	293.3	293.9	307.8	322.1	337.7	368.5	411.7	459.1	512.5	556.6	607.3
30°	251.2	249.9	255.8	264.6	277.9	301.8	334.2	380.8	434.1	500.5	559.6
32.5°	221.3	221.4	225.9	232.3	243.3	259.5	281.7	319.6	369.9	435.2	504.5
35°	192.4	192.3	195.5	200.1	204.7	215.1	230.3	250.1	284.8	345.7	416.6
37.5°	171.7	172.5	174.2	177.1	182.2	188.0	197.1	210.4	235.1	271.2	330.7
40°	160.0	160.4	162.6	165.1	168.1	172.5	180.0	190.8	208.8	237.6	281.2
42.5°	149.4	149.7	151.3	153.6	156.0	160.4	166.7	175.9	190.6	212.9	248.9
45°	133.7	133.7	135.1	136.1	138.8	142.8	147.8	155.6	165.7	182.3	206.2
47.5°	119.0	119.0	120.0	121.7	123.4	126.5	131.5	137.9	145.2	158.0	178.4
50°	110.6	110.8	111.4	112.8	113.9	116.6	120.6	126.0	133.7	143.7	160.6
52.5°	103.8	103.7	104.4	105.0	105.8	107.7	110.7	115.5	122.3	131.0	145.1
55°	92.7	91.9	93.2	94.2	94.8	95.6	97.2	100.2	106.1	113.4	123.9
57.5°	79.0	78.6	79.5	80.4	82.4	84.5	86.0	87.8	90.9	96.1	106.6
60°	67.7	67.7	69.5	70.1	72.3	75.2	78.0	79.6	82.7	86.1	93.8
62.5°	57.6	57.8	58.6	59.2	60.5	63.9	67.9	71.5	74.4	77.7	82.8
65°	48.2	48.6	48.6	49.0	49.8	50.6	52.3	55.1	60.2	64.8	68.7
67.5°	40.9	41.0	41.2	41.6	41.7	42.6	43.3	44.6	45.7	50.1	54.9
70°	36.0	36.6	36.5	36.8	37.1	37.5	38.3	38.9	40.8	41.7	44.6
72.5°	31.5	31.9	31.9	32.2	32.7	32.8	33.4	34.1	35.2	36.0	37.6
75°	25.5	25.3	25.5	25.9	26.1	26.3	26.3	27.1	27.7	28.5	29.6
77.5°	19.7	19.9	19.9	19.9	20.0	20.3	20.2	20.6	21.2	21.7	22.1
80°	15.8	16.0	15.8	16.0	16.2	16.4	16.2	16.4	17.0	17.4	17.4
82.5°	12.2	12.3	12.4	12.4	12.5	12.5	12.8	12.8	13.3	13.2	13.4
85°	7.3	7.1	7.1	7.1	7.3	7.5	7.3	7.3	7.5	7.5	7.5
87.5°	5.1	5.3	5.2	5.2	5.1	5.0	4.9	5.0	4.7	4.8	4.5
90°	12.6	12.4	12.1	11.9	11.8	11.4	10.9	10.3	9.8	9.3	8.5
92.5°	12.6	12.5	12.3	12.2	12.0	11.9	11.6	11.3	11.1	10.8	10.3
95°	20.0	20.2	20.2	20.3	20.4	20.2	19.7	19.2	18.6	18.2	17.4
97.5°	26.8	26.6	26.5	26.3	26.2	25.9	25.5	25.1	24.7	24.3	22.6
100°	31.2	30.9	30.8	30.6	30.3	29.9	29.0	28.2	27.4	26.5	24.8
102.5°	33.4	33.1	32.8	32.5	32.3	31.6	30.5	29.4	28.4	27.3	42.0
105°	35.4	35.0	34.5	34.2	33.7	32.9	31.8	30.7	29.5	28.4	56.6
107.5°	36.4	35.9	35.6	35.1	34.8	35.1	36.3	37.5	38.6	39.8	73.6
110°	36.7	36.4	35.9	35.5	35.1	40.0	50.4	60.7	71.1	81.4	111.3



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	37.1	36.8	36.5	36.1	35.8	54.5	92.2	129.9	167.6	205.5	212.8
115°	38.2	45.6	53.1	60.5	67.9	95.6	143.5	191.4	239.2	287.1	284.5
117.5°	155.8	180.3	204.7	229.2	253.7	271.7	283.3	294.9	306.5	318.0	316.3
120°	283.8	297.8	311.8	325.7	339.7	346.1	344.8	343.6	342.3	341.1	339.2
122.5°	354.2	357.0	359.6	362.4	365.1	366.0	365.3	364.5	363.8	363.1	361.1
125°	397.9	397.6	397.3	397.0	396.6	396.1	395.4	394.7	394.0	393.2	391.3
127.5°	425.4	425.3	425.3	425.3	425.2	424.6	423.6	422.5	421.4	420.4	418.9
130°	442.6	442.6	442.7	442.8	443.0	442.5	441.3	440.1	439.1	437.9	436.8
132.5°	459.3	459.4	459.5	459.6	459.7	459.3	458.3	457.4	456.4	455.4	454.2
135°	483.5	483.8	483.9	484.1	484.4	483.9	482.9	481.9	480.8	479.7	478.8
137.5°	505.6	506.0	506.2	506.6	506.9	506.7	505.6	504.6	503.6	502.6	501.5
140°	519.3	519.9	520.4	520.8	521.4	521.2	520.2	519.3	518.4	517.5	516.3
142.5°	532.7	533.2	533.8	534.3	534.8	534.7	533.8	533.0	532.1	531.3	529.9
145°	551.4	552.0	552.5	553.0	553.5	553.4	552.7	552.0	551.3	550.5	548.8
147.5°	567.9	568.4	568.8	569.3	569.6	569.6	569.1	568.6	568.0	567.5	565.7
150°	578.0	578.5	579.0	579.5	580.1	580.0	579.3	578.7	578.1	577.5	575.9
152.5°	586.6	587.2	587.9	588.6	589.2	589.3	588.7	588.1	587.5	586.8	585.2
155°	598.4	599.3	600.1	600.9	601.7	601.9	601.3	600.7	600.0	599.4	598.2
157.5°	609.3	610.1	610.9	611.7	612.6	612.6	611.9	611.2	610.5	609.8	608.9
160°	615.6	616.4	617.2	617.9	618.6	618.6	618.0	617.3	616.8	616.2	615.5
162.5°	620.9	621.8	622.7	623.6	624.5	624.6	623.8	623.1	622.4	621.7	621.2
165°	628.7	629.5	630.2	630.9	631.6	631.6	630.9	630.2	629.5	628.7	628.4
167.5°	633.6	634.5	635.5	636.4	637.4	637.5	636.8	636.0	635.3	634.5	634.3
170°	636.6	637.6	638.5	639.4	640.3	640.4	639.7	639.0	638.3	637.6	637.3
172.5°	638.8	639.8	640.7	641.7	642.6	642.7	641.9	641.2	640.5	639.8	639.5
175°	640.8	641.9	642.8	643.9	645.0	645.1	644.4	643.6	642.9	642.2	641.9
177.5°	642.0	642.7	643.5	644.3	645.0	645.1	644.5	643.9	643.4	642.7	642.7
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	596.9	595.6	594.4	591.6	590.0	586.8	586.4	586.2	582.0	577.9	576.8
5°	617.4	614.1	609.3	603.6	597.7	591.7	587.6	584.3	576.2	568.6	564.1
7.5°	638.0	631.1	622.7	612.0	603.0	593.0	585.5	578.8	567.3	556.2	548.8
10°	653.4	642.1	631.0	616.2	604.6	593.3	582.7	573.6	560.7	546.1	535.7
12.5°	663.0	650.5	635.2	620.7	605.7	591.3	577.2	565.5	550.3	535.2	523.0
15°	675.9	662.5	643.9	623.2	604.0	585.1	569.0	554.4	534.6	516.5	501.5
17.5°	686.5	668.1	648.1	624.2	601.9	578.0	557.1	538.5	516.4	494.6	477.0
20°	689.9	671.6	648.5	624.6	598.3	570.2	547.7	527.4	503.7	480.0	459.8
22.5°	687.8	673.6	647.9	619.3	592.4	562.9	537.5	514.0	487.7	463.5	440.1
25°	673.5	668.6	644.4	613.1	582.4	548.1	518.7	493.0	463.1	437.1	411.6
27.5°	640.2	650.7	635.6	602.4	568.1	531.5	498.4	469.1	438.0	408.8	383.4
30°	608.1	632.1	625.7	594.9	556.6	520.6	483.5	452.9	419.7	389.7	364.6
32.5°	564.2	604.0	610.3	584.5	544.9	505.3	466.5	436.0	401.4	369.8	345.3
35°	494.2	553.8	581.1	564.7	525.0	482.2	442.2	406.7	371.8	340.7	316.4
37.5°	410.8	492.0	537.5	538.7	502.2	457.8	414.1	378.9	343.2	312.6	286.3
40°	356.7	444.6	504.0	517.1	486.3	438.4	394.1	358.3	323.5	293.5	263.3
42.5°	308.1	395.7	468.6	491.5	467.1	419.4	375.1	337.6	303.7	275.4	244.5
45°	249.1	325.7	406.1	447.0	433.5	389.3	342.5	306.8	275.1	250.6	221.0
47.5°	210.2	264.1	342.0	397.3	397.1	356.8	310.7	276.6	247.1	224.1	200.2
50°	188.0	235.0	300.8	363.6	368.8	335.0	291.2	257.4	229.9	205.8	186.5
52.5°	168.0	206.8	265.9	326.2	341.2	311.8	269.4	238.2	211.4	189.2	172.8
55°	142.0	172.0	217.0	273.2	296.0	275.3	237.6	208.4	186.7	168.1	153.9
57.5°	120.1	142.6	178.7	224.0	250.4	237.5	206.3	182.6	164.1	147.2	136.1
60°	106.4	124.8	155.3	193.2	222.4	213.3	186.7	164.7	148.9	134.3	123.8
62.5°	93.4	109.2	135.5	166.2	192.9	189.1	167.5	148.9	135.1	121.8	112.9
65°	75.2	86.7	107.2	131.3	152.8	154.5	138.9	126.4	114.0	103.5	95.6
67.5°	59.8	67.4	81.8	102.1	118.2	123.9	114.4	104.8	95.0	86.9	80.0
70°	50.5	56.5	67.1	83.5	98.3	104.3	98.8	91.3	82.8	76.2	70.3
72.5°	40.8	46.8	54.6	66.6	79.3	85.9	83.9	78.6	71.7	66.1	60.5
75°	30.8	32.6	37.9	46.0	55.9	61.6	63.0	60.2	54.7	50.5	47.2
77.5°	22.7	23.9	26.4	30.6	37.1	42.2	44.2	43.9	40.1	37.7	34.6
80°	18.2	18.8	20.1	21.8	26.8	31.8	33.3	33.3	30.6	29.6	26.6
82.5°	13.8	14.3	15.1	16.1	18.3	22.7	24.3	24.6	23.0	21.7	19.3
85°	7.9	7.7	8.1	8.7	9.1	10.3	12.8	13.2	12.8	11.1	10.5
87.5°	4.3	4.3	4.1	3.7	3.7	3.7	4.2	4.8	4.4	4.1	4.0
90°	7.7	6.9	6.0	5.0	3.8	2.8	1.6	0.4	1.6	2.8	3.8
92.5°	10.0	9.5	9.2	9.0	9.1	9.2	9.3	9.4	9.3	9.2	9.1
95°	16.7	16.0	15.2	16.6	20.0	23.5	26.8	30.2	26.8	23.5	20.0
97.5°	21.0	19.3	17.6	21.6	31.2	40.8	50.4	60.0	50.4	40.8	31.2
100°	23.0	21.2	19.5	25.7	39.9	54.0	68.2	82.4	68.2	54.0	39.9
102.5°	56.7	71.4	86.1	95.0	97.9	100.9	104.0	106.9	104.0	100.9	97.9
105°	84.9	113.1	141.3	153.9	150.8	147.7	144.5	141.4	144.5	147.7	150.8
107.5°	107.5	141.3	175.1	190.8	188.3	185.8	183.3	180.8	183.3	185.8	188.3
110°	141.2	171.1	201.0	214.8	212.7	210.5	208.3	206.2	208.3	210.5	212.7





TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	220.2	227.6	235.0	237.6	235.8	233.8	231.9	230.0	231.9	233.8	235.8
115°	282.0	279.4	276.8	274.6	272.9	271.1	269.3	267.6	269.3	271.1	272.9
117.5°	314.5	312.7	310.9	309.1	307.1	305.1	303.2	301.2	303.2	305.1	307.1
120°	337.4	335.6	333.7	332.0	330.4	328.9	327.3	325.7	327.3	328.9	330.4
122.5°	359.0	357.0	355.0	353.1	351.5	349.9	348.2	346.6	348.2	349.9	351.5
125°	389.3	387.4	385.4	383.7	382.4	381.0	379.7	378.4	379.7	381.0	382.4
127.5°	417.5	416.0	414.6	413.0	411.5	410.1	408.6	407.1	408.6	410.1	411.5
130°	435.6	434.5	433.4	431.9	430.3	428.6	427.0	425.3	427.0	428.6	430.3
132.5°	453.2	452.0	450.8	449.6	448.2	446.7	445.3	444.0	445.3	446.7	448.2
135°	478.0	477.0	476.1	474.7	473.1	471.4	469.8	468.1	469.8	471.4	473.1
137.5°	500.5	499.4	498.4	497.2	496.1	494.9	493.7	492.7	493.7	494.9	496.1
140°	515.2	514.1	512.9	511.9	511.1	510.3	509.4	508.6	509.4	510.3	511.1
142.5°	528.6	527.4	526.0	525.0	524.2	523.5	522.8	522.0	522.8	523.5	524.2
145°	547.0	545.3	543.5	542.7	542.8	542.9	543.0	543.1	543.0	542.9	542.8
147.5°	564.0	562.2	560.5	559.8	560.3	560.6	561.0	561.4	561.0	560.6	560.3
150°	574.2	572.6	570.9	570.4	571.1	571.9	572.6	573.3	572.6	571.9	571.1
152.5°	583.7	582.1	580.5	580.1	580.9	581.8	582.6	583.4	582.6	581.8	580.9
155°	596.9	595.7	594.4	594.2	595.2	596.1	597.1	598.0	597.1	596.1	595.2
157.5°	608.1	607.2	606.4	606.3	607.1	607.9	608.7	609.4	608.7	607.9	607.1
160°	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2	615.5	614.9	614.3
162.5°	620.6	620.1	619.6	619.6	620.2	620.8	621.4	622.1	621.4	620.8	620.2
165°	628.0	627.8	627.5	627.6	628.2	628.8	629.5	630.1	629.5	628.8	628.2
167.5°	634.0	633.6	633.4	633.6	634.2	634.8	635.4	636.1	635.4	634.8	634.2
170°	637.1	636.9	636.7	636.9	637.6	638.2	638.8	639.4	638.8	638.2	637.6
172.5°	639.4	639.2	638.9	639.2	639.8	640.4	641.1	641.7	641.1	640.4	639.8
175°	641.8	641.6	641.4	641.6	642.4	643.1	643.8	644.5	643.8	643.1	642.4
177.5°	642.6	642.5	642.4	642.7	643.3	643.8	644.4	645.0	644.4	643.8	643.3
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	574.7	573.5	571.4	568.2	566.2	562.8	560.6	561.9	562.2	561.9	561.6
5°	559.3	555.0	549.1	543.4	538.1	532.5	529.2	527.9	525.0	523.4	522.5
7.5°	540.6	533.2	525.0	515.1	506.7	497.8	493.4	491.2	485.4	482.2	479.5
10°	526.6	515.1	506.8	493.8	485.9	474.4	466.5	466.7	458.8	454.3	451.1
12.5°	511.2	498.6	484.7	473.1	462.1	452.8	443.3	439.4	431.1	426.8	418.0
15°	485.7	470.9	456.4	440.6	429.4	415.0	401.3	384.4	370.9	359.1	355.9
17.5°	457.9	439.5	424.9	406.4	387.3	363.1	347.1	337.3	329.2	323.0	318.3
20°	438.7	420.1	404.5	376.6	350.8	334.4	322.7	315.1	306.7	300.0	296.3
22.5°	418.7	399.2	377.9	346.7	326.6	313.5	303.1	294.4	288.6	283.5	280.1
25°	390.1	368.8	333.8	312.4	296.1	282.3	275.1	269.8	263.8	256.6	253.4
27.5°	360.0	326.2	301.0	285.0	269.6	260.6	254.0	246.2	240.8	237.6	234.2
30°	337.4	303.6	284.0	266.5	255.7	245.7	238.0	233.5	228.3	222.8	220.6
32.5°	312.4	285.3	266.4	252.0	240.9	232.4	226.3	219.1	215.3	212.0	207.3
35°	281.2	260.6	243.4	231.8	221.1	214.3	207.2	203.0	196.1	193.2	191.5
37.5°	254.8	237.0	224.2	211.8	203.4	195.8	191.5	184.7	181.7	177.7	173.9
40°	239.8	222.4	210.1	199.9	190.6	184.9	179.5	174.0	169.5	167.7	163.1
42.5°	224.6	210.4	198.0	187.0	180.7	174.7	167.8	163.8	159.2	156.2	153.4
45°	203.6	191.0	180.5	171.4	164.4	158.2	153.7	147.0	144.5	138.6	136.1
47.5°	185.1	173.4	163.4	154.7	148.0	143.9	137.4	132.2	128.0	124.3	121.2
50°	172.0	162.2	152.5	144.8	138.8	132.9	126.2	123.6	117.1	115.2	113.4
52.5°	160.0	150.7	141.9	134.3	128.2	122.5	116.6	113.2	108.8	107.0	105.7
55°	143.2	134.3	125.8	119.1	113.1	107.2	103.5	99.2	97.2	95.8	94.2
57.5°	126.4	118.3	111.8	105.0	98.9	94.3	90.1	87.5	85.4	83.6	81.6
60°	115.7	108.0	102.1	95.8	89.5	85.7	82.5	79.4	77.0	74.1	73.3
62.5°	104.3	97.6	92.2	86.1	80.6	77.1	74.0	71.2	68.2	64.1	63.0
65°	88.7	83.5	77.8	72.7	67.9	64.4	59.9	56.7	55.5	55.1	54.9
67.5°	74.6	69.6	64.7	59.6	55.2	52.0	49.7	49.2	48.3	48.2	47.5
70°	65.2	60.5	55.7	50.8	46.5	46.0	45.2	44.3	43.3	43.0	42.5
72.5°	56.8	52.0	47.1	43.2	41.4	40.7	39.9	39.0	38.3	37.9	37.7
75°	43.5	39.1	35.8	34.4	33.4	32.8	31.6	31.0	30.6	30.0	29.8
77.5°	31.4	28.8	27.4	26.5	25.4	24.8	24.1	23.5	23.0	22.9	22.6
80°	23.9	22.6	21.7	20.4	20.1	19.3	19.1	18.5	18.6	18.0	18.0
82.5°	18.5	17.0	16.1	15.6	15.2	14.5	14.4	14.1	14.1	13.6	13.6
85°	9.5	9.1	8.7	8.3	8.3	7.7	7.9	7.7	7.7	7.3	7.1
87.5°	4.1	4.1	3.9	4.1	4.3	4.3	4.4	4.4	4.5	4.5	4.5
90°	5.0	6.0	6.9	7.7	8.5	9.3	9.8	10.3	10.9	11.4	11.8
92.5°	9.0	9.2	9.5	10.0	10.3	10.8	11.1	11.3	11.6	11.9	12.0
95°	16.6	15.2	16.0	16.7	17.4	18.2	18.6	19.2	19.7	20.2	20.4
97.5°	21.6	17.6	19.3	21.0	22.6	24.3	24.7	25.1	25.5	25.9	26.2
100°	25.7	19.5	21.2	23.0	24.8	26.5	27.4	28.2	29.0	29.9	30.3
102.5°	95.0	86.1	71.4	56.7	42.0	27.3	28.4	29.4	30.5	31.6	32.3
105°	153.9	141.3	113.1	84.9	56.6	28.4	29.5	30.7	31.8	32.9	33.7
107.5°	190.8	175.1	141.3	107.5	73.6	39.8	38.6	37.5	36.3	35.1	34.8
110°	214.8	201.0	171.1	141.2	111.3	81.4	71.1	60.7	50.4	40.0	35.1



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	237.6	235.0	227.6	220.2	212.8	205.5	167.6	129.9	92.2	54.5	35.8
115°	274.6	276.8	279.4	282.0	284.5	287.1	239.2	191.4	143.5	95.6	67.9
117.5°	309.1	310.9	312.7	314.5	316.3	318.0	306.5	294.9	283.3	271.7	253.7
120°	332.0	333.7	335.6	337.4	339.2	341.1	342.3	343.6	344.8	346.1	339.7
122.5°	353.1	355.0	357.0	359.0	361.1	363.1	363.8	364.5	365.3	366.0	365.1
125°	383.7	385.4	387.4	389.3	391.3	393.2	394.0	394.7	395.4	396.1	396.6
127.5°	413.0	414.6	416.0	417.5	418.9	420.4	421.4	422.5	423.6	424.6	425.2
130°	431.9	433.4	434.5	435.6	436.8	437.9	439.1	440.1	441.3	442.5	443.0
132.5°	449.6	450.8	452.0	453.2	454.2	455.4	456.4	457.4	458.3	459.3	459.7
135°	474.7	476.1	477.0	478.0	478.8	479.7	480.8	481.9	482.9	483.9	484.4
137.5°	497.2	498.4	499.4	500.5	501.5	502.6	503.6	504.6	505.6	506.7	506.9
140°	511.9	512.9	514.1	515.2	516.3	517.5	518.4	519.3	520.2	521.2	521.4
142.5°	525.0	526.0	527.4	528.6	529.9	531.3	532.1	533.0	533.8	534.7	534.8
145°	542.7	543.5	545.3	547.0	548.8	550.5	551.3	552.0	552.7	553.4	553.5
147.5°	559.8	560.5	562.2	564.0	565.7	567.5	568.0	568.6	569.1	569.6	569.6
150°	570.4	570.9	572.6	574.2	575.9	577.5	578.1	578.7	579.3	580.0	580.1
152.5°	580.1	580.5	582.1	583.7	585.2	586.8	587.5	588.1	588.7	589.3	589.2
155°	594.2	594.4	595.7	596.9	598.2	599.4	600.0	600.7	601.3	601.9	601.7
157.5°	606.3	606.4	607.2	608.1	608.9	609.8	610.5	611.2	611.9	612.6	612.6
160°	613.7	613.7	614.3	614.9	615.5	616.2	616.8	617.3	618.0	618.6	618.6
162.5°	619.6	619.6	620.1	620.6	621.2	621.7	622.4	623.1	623.8	624.6	624.5
165°	627.6	627.5	627.8	628.0	628.4	628.7	629.5	630.2	630.9	631.6	631.6
167.5°	633.6	633.4	633.6	634.0	634.3	634.5	635.3	636.0	636.8	637.5	637.4
170°	636.9	636.7	636.9	637.1	637.3	637.6	638.3	639.0	639.7	640.4	640.3
172.5°	639.2	638.9	639.2	639.4	639.5	639.8	640.5	641.2	641.9	642.7	642.6
175°	641.6	641.4	641.6	641.8	641.9	642.2	642.9	643.6	644.4	645.1	645.0
177.5°	642.7	642.4	642.5	642.6	642.7	642.7	643.4	643.9	644.5	645.1	645.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	559.8	560.1	559.6	559.9	559.6	560.1	559.8	561.6	561.9	562.2	561.9
5°	521.6	519.2	518.7	518.2	518.7	519.2	521.6	522.5	523.4	525.0	527.9
7.5°	476.0	475.6	474.6	473.1	474.6	475.6	476.0	479.5	482.2	485.4	491.2
10°	446.7	445.6	445.4	444.0	445.4	445.6	446.7	451.1	454.3	458.8	466.7
12.5°	412.2	405.7	405.1	401.5	405.1	405.7	412.2	418.0	426.8	431.1	439.4
15°	351.1	349.8	345.7	343.1	345.7	349.8	351.1	355.9	359.1	370.9	384.4
17.5°	316.0	312.0	310.8	310.2	310.8	312.0	316.0	318.3	323.0	329.2	337.3
20°	293.5	289.9	289.3	288.8	289.3	289.9	293.5	296.3	300.0	306.7	315.1
22.5°	277.9	274.1	272.6	271.3	272.6	274.1	277.9	280.1	283.5	288.6	294.4
25°	251.4	249.9	249.1	248.7	249.1	249.9	251.4	253.4	256.6	263.8	269.8
27.5°	230.6	227.5	226.9	225.8	226.9	227.5	230.6	234.2	237.6	240.8	246.2
30°	218.7	217.8	216.3	215.1	216.3	217.8	218.7	220.6	222.8	228.3	233.5
32.5°	204.8	203.9	202.7	202.2	202.7	203.9	204.8	207.3	212.0	215.3	219.1
35°	189.4	186.5	185.3	183.5	185.3	186.5	189.4	191.5	193.2	196.1	203.0
37.5°	173.1	171.6	169.9	170.5	169.9	171.6	173.1	173.9	177.7	181.7	184.7
40°	160.4	159.4	159.0	158.8	159.0	159.4	160.4	163.1	167.7	169.5	174.0
42.5°	150.3	147.6	146.5	146.5	146.5	147.6	150.3	153.4	156.2	159.2	163.8
45°	135.1	132.5	130.6	130.8	130.6	132.5	135.1	136.1	138.6	144.5	147.0
47.5°	119.5	119.4	118.2	118.6	118.2	119.4	119.5	121.2	124.3	128.0	132.2
50°	112.0	110.8	109.9	110.2	109.9	110.8	112.0	113.4	115.2	117.1	123.6
52.5°	104.9	103.8	103.2	104.1	103.2	103.8	104.9	105.7	107.0	108.8	113.2
55°	93.2	91.9	91.8	91.6	91.8	91.9	93.2	94.2	95.8	97.2	99.2
57.5°	80.1	79.3	78.0	77.6	78.0	79.3	80.1	81.6	83.6	85.4	87.5
60°	70.7	69.1	67.1	66.9	67.1	69.1	70.7	73.3	74.1	77.0	79.4
62.5°	62.1	61.8	61.3	61.3	61.3	61.8	62.1	63.0	64.1	68.2	71.2
65°	54.5	54.3	54.5	54.7	54.5	54.3	54.5	54.9	55.1	55.5	56.7
67.5°	47.4	47.1	46.7	46.9	46.7	47.1	47.4	47.5	48.2	48.3	49.2
70°	42.1	41.9	41.7	41.7	41.7	41.9	42.1	42.5	43.0	43.3	44.3
72.5°	36.9	36.9	36.7	36.6	36.7	36.9	36.9	37.7	37.9	38.3	39.0
75°	29.6	29.2	29.2	29.2	29.2	29.2	29.6	29.8	30.0	30.6	31.0
77.5°	22.6	22.3	22.1	21.9	22.1	22.3	22.6	22.6	22.9	23.0	23.5
80°	17.8	17.7	17.4	17.4	17.4	17.7	17.8	18.0	18.0	18.6	18.5
82.5°	13.6	13.4	13.4	13.2	13.4	13.4	13.6	13.6	13.6	14.1	14.1
85°	7.3	7.5	7.3	7.7	7.3	7.5	7.3	7.1	7.3	7.7	7.7
87.5°	4.5	4.4	4.5	4.5	4.5	4.4	4.5	4.5	4.5	4.5	4.4
90°	11.9	12.1	12.4	12.6	12.4	12.1	11.9	11.8	11.4	10.9	10.3
92.5°	12.2	12.3	12.5	12.6	12.5	12.3	12.2	12.0	11.9	11.6	11.3
95°	20.3	20.2	20.2	20.0	20.2	20.2	20.3	20.4	20.2	19.7	19.2
97.5°	26.3	26.5	26.6	26.8	26.6	26.5	26.3	26.2	25.9	25.5	25.1
100°	30.6	30.8	30.9	31.2	30.9	30.8	30.6	30.3	29.9	29.0	28.2
102.5°	32.5	32.8	33.1	33.4	33.1	32.8	32.5	32.3	31.6	30.5	29.4
105°	34.2	34.5	35.0	35.4	35.0	34.5	34.2	33.7	32.9	31.8	30.7
107.5°	35.1	35.6	35.9	36.4	35.9	35.6	35.1	34.8	35.1	36.3	37.5
110°	35.5	35.9	36.4	36.7	36.4	35.9	35.5	35.1	40.0	50.4	60.7



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	36.1	36.5	36.8	37.1	36.8	36.5	36.1	35.8	54.5	92.2	129.9
115°	60.5	53.1	45.6	38.2	45.6	53.1	60.5	67.9	95.6	143.5	191.4
117.5°	229.2	204.7	180.3	155.8	180.3	204.7	229.2	253.7	271.7	283.3	294.9
120°	325.7	311.8	297.8	283.8	297.8	311.8	325.7	339.7	346.1	344.8	343.6
122.5°	362.4	359.6	357.0	354.2	357.0	359.6	362.4	365.1	366.0	365.3	364.5
125°	397.0	397.3	397.6	397.9	397.6	397.3	397.0	396.6	396.1	395.4	394.7
127.5°	425.3	425.3	425.3	425.4	425.3	425.3	425.3	425.2	424.6	423.6	422.5
130°	442.8	442.7	442.6	442.6	442.6	442.7	442.8	443.0	442.5	441.3	440.1
132.5°	459.6	459.5	459.4	459.3	459.4	459.5	459.6	459.7	459.3	458.3	457.4
135°	484.1	483.9	483.8	483.5	483.8	483.9	484.1	484.4	483.9	482.9	481.9
137.5°	506.6	506.2	506.0	505.6	506.0	506.2	506.6	506.9	506.7	505.6	504.6
140°	520.8	520.4	519.9	519.3	519.9	520.4	520.8	521.4	521.2	520.2	519.3
142.5°	534.3	533.8	533.2	532.7	533.2	533.8	534.3	534.8	534.7	533.8	533.0
145°	553.0	552.5	552.0	551.4	552.0	552.5	553.0	553.5	553.4	552.7	552.0
147.5°	569.3	568.8	568.4	567.9	568.4	568.8	569.3	569.6	569.6	569.1	568.6
150°	579.5	579.0	578.5	578.0	578.5	579.0	579.5	580.1	580.0	579.3	578.7
152.5°	588.6	587.9	587.2	586.6	587.2	587.9	588.6	589.2	589.3	588.7	588.1
155°	600.9	600.1	599.3	598.4	599.3	600.1	600.9	601.7	601.9	601.3	600.7
157.5°	611.7	610.9	610.1	609.3	610.1	610.9	611.7	612.6	612.6	611.9	611.2
160°	617.9	617.2	616.4	615.6	616.4	617.2	617.9	618.6	618.6	618.0	617.3
162.5°	623.6	622.7	621.8	620.9	621.8	622.7	623.6	624.5	624.6	623.8	623.1
165°	630.9	630.2	629.5	628.7	629.5	630.2	630.9	631.6	631.6	630.9	630.2
167.5°	636.4	635.5	634.5	633.6	634.5	635.5	636.4	637.4	637.5	636.8	636.0
170°	639.4	638.5	637.6	636.6	637.6	638.5	639.4	640.3	640.4	639.7	639.0
172.5°	641.7	640.7	639.8	638.8	639.8	640.7	641.7	642.6	642.7	641.9	641.2
175°	643.9	642.8	641.9	640.8	641.9	642.8	643.9	645.0	645.1	644.4	643.6
177.5°	644.3	643.5	642.7	642.0	642.7	643.5	644.3	645.0	645.1	644.5	643.9
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	560.6	562.8	566.2	568.2	571.4	573.5	574.7	576.8	577.9	582.0	586.2
5°	529.2	532.5	538.1	543.4	549.1	555.0	559.3	564.1	568.6	576.2	584.3
7.5°	493.4	497.8	506.7	515.1	525.0	533.2	540.6	548.8	556.2	567.3	578.8
10°	466.5	474.4	485.9	493.8	506.8	515.1	526.6	535.7	546.1	560.7	573.6
12.5°	443.3	452.8	462.1	473.1	484.7	498.6	511.2	523.0	535.2	550.3	565.5
15°	401.3	415.0	429.4	440.6	456.4	470.9	485.7	501.5	516.5	534.6	554.4
17.5°	347.1	363.1	387.3	406.4	424.9	439.5	457.9	477.0	494.6	516.4	538.5
20°	322.7	334.4	350.8	376.6	404.5	420.1	438.7	459.8	480.0	503.7	527.4
22.5°	303.1	313.5	326.6	346.7	377.9	399.2	418.7	440.1	463.5	487.7	514.0
25°	275.1	282.3	296.1	312.4	333.8	368.8	390.1	411.6	437.1	463.1	493.0
27.5°	254.0	260.6	269.6	285.0	301.0	326.2	360.0	383.4	408.8	438.0	469.1
30°	238.0	245.7	255.7	266.5	284.0	303.6	337.4	364.6	389.7	419.7	452.9
32.5°	226.3	232.4	240.9	252.0	266.4	285.3	312.4	345.3	369.8	401.4	436.0
35°	207.2	214.3	221.1	231.8	243.4	260.6	281.2	316.4	340.7	371.8	406.7
37.5°	191.5	195.8	203.4	211.8	224.2	237.0	254.8	286.3	312.6	343.2	378.9
40°	179.5	184.9	190.6	199.9	210.1	222.4	239.8	263.3	293.5	323.5	358.3
42.5°	167.8	174.7	180.7	187.0	198.0	210.4	224.6	244.5	275.4	303.7	337.6
45°	153.7	158.2	164.4	171.4	180.5	191.0	203.6	221.0	250.6	275.1	306.8
47.5°	137.4	143.9	148.0	154.7	163.4	173.4	185.1	200.2	224.1	247.1	276.6
50°	126.2	132.9	138.8	144.8	152.5	162.2	172.0	186.5	205.8	229.9	257.4
52.5°	116.6	122.5	128.2	134.3	141.9	150.7	160.0	172.8	189.2	211.4	238.2
55°	103.5	107.2	113.1	119.1	125.8	134.3	143.2	153.9	168.1	186.7	208.4
57.5°	90.1	94.3	98.9	105.0	111.8	118.3	126.4	136.1	147.2	164.1	182.6
60°	82.5	85.7	89.5	95.8	102.1	108.0	115.7	123.8	134.3	148.9	164.7
62.5°	74.0	77.1	80.6	86.1	92.2	97.6	104.3	112.9	121.8	135.1	148.9
65°	59.9	64.4	67.9	72.7	77.8	83.5	88.7	95.6	103.5	114.0	126.4
67.5°	49.7	52.0	55.2	59.6	64.7	69.6	74.6	80.0	86.9	95.0	104.8
70°	45.2	46.0	46.5	50.8	55.7	60.5	65.2	70.3	76.2	82.8	91.3
72.5°	39.9	40.7	41.4	43.2	47.1	52.0	56.8	60.5	66.1	71.7	78.6
75°	31.6	32.8	33.4	34.4	35.8	39.1	43.5	47.2	50.5	54.7	60.2
77.5°	24.1	24.8	25.4	26.5	27.4	28.8	31.4	34.6	37.7	40.1	43.9
80°	19.1	19.3	20.1	20.4	21.7	22.6	23.9	26.6	29.6	30.6	33.3
82.5°	14.4	14.5	15.2	15.6	16.1	17.0	18.5	19.3	21.7	23.0	24.6
85°	7.9	7.7	8.3	8.3	8.7	9.1	9.5	10.5	11.1	12.8	13.2
87.5°	4.4	4.3	4.3	4.1	3.9	4.1	4.1	4.0	4.1	4.4	4.8
90°	9.8	9.3	8.5	7.7	6.9	6.0	5.0	3.8	2.8	1.6	0.4
92.5°	11.1	10.8	10.3	10.0	9.5	9.2	9.0	9.1	9.2	9.3	9.4
95°	18.6	18.2	17.4	16.7	16.0	15.2	16.6	20.0	23.5	26.8	30.2
97.5°	24.7	24.3	22.6	21.0	19.3	17.6	21.6	31.2	40.8	50.4	60.0
100°	27.4	26.5	24.8	23.0	21.2	19.5	25.7	39.9	54.0	68.2	82.4
102.5°	28.4	27.3	42.0	56.7	71.4	86.1	95.0	97.9	100.9	104.0	106.9
105°	29.5	28.4	56.6	84.9	113.1	141.3	153.9	150.8	147.7	144.5	141.4
107.5°	38.6	39.8	73.6	107.5	141.3	175.1	190.8	188.3	185.8	183.3	180.8
110°	71.1	81.4	111.3	141.2	171.1	201.0	214.8	212.7	210.5	208.3	206.2



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	167.6	205.5	212.8	220.2	227.6	235.0	237.6	235.8	233.8	231.9	230.0
115°	239.2	287.1	284.5	282.0	279.4	276.8	274.6	272.9	271.1	269.3	267.6
117.5°	306.5	318.0	316.3	314.5	312.7	310.9	309.1	307.1	305.1	303.2	301.2
120°	342.3	341.1	339.2	337.4	335.6	333.7	332.0	330.4	328.9	327.3	325.7
122.5°	363.8	363.1	361.1	359.0	357.0	355.0	353.1	351.5	349.9	348.2	346.6
125°	394.0	393.2	391.3	389.3	387.4	385.4	383.7	382.4	381.0	379.7	378.4
127.5°	421.4	420.4	418.9	417.5	416.0	414.6	413.0	411.5	410.1	408.6	407.1
130°	439.1	437.9	436.8	435.6	434.5	433.4	431.9	430.3	428.6	427.0	425.3
132.5°	456.4	455.4	454.2	453.2	452.0	450.8	449.6	448.2	446.7	445.3	444.0
135°	480.8	479.7	478.8	478.0	477.0	476.1	474.7	473.1	471.4	469.8	468.1
137.5°	503.6	502.6	501.5	500.5	499.4	498.4	497.2	496.1	494.9	493.7	492.7
140°	518.4	517.5	516.3	515.2	514.1	512.9	511.9	511.1	510.3	509.4	508.6
142.5°	532.1	531.3	529.9	528.6	527.4	526.0	525.0	524.2	523.5	522.8	522.0
145°	551.3	550.5	548.8	547.0	545.3	543.5	542.7	542.8	542.9	543.0	543.1
147.5°	568.0	567.5	565.7	564.0	562.2	560.5	559.8	560.3	560.6	561.0	561.4
150°	578.1	577.5	575.9	574.2	572.6	570.9	570.4	571.1	571.9	572.6	573.3
152.5°	587.5	586.8	585.2	583.7	582.1	580.5	580.1	580.9	581.8	582.6	583.4
155°	600.0	599.4	598.2	596.9	595.7	594.4	594.2	595.2	596.1	597.1	598.0
157.5°	610.5	609.8	608.9	608.1	607.2	606.4	606.3	607.1	607.9	608.7	609.4
160°	616.8	616.2	615.5	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2
162.5°	622.4	621.7	621.2	620.6	620.1	619.6	619.6	620.2	620.8	621.4	622.1
165°	629.5	628.7	628.4	628.0	627.8	627.5	627.6	628.2	628.8	629.5	630.1
167.5°	635.3	634.5	634.3	634.0	633.6	633.4	633.6	634.2	634.8	635.4	636.1
170°	638.3	637.6	637.3	637.1	636.9	636.7	636.9	637.6	638.2	638.8	639.4
172.5°	640.5	639.8	639.5	639.4	639.2	638.9	639.2	639.8	640.4	641.1	641.7
175°	642.9	642.2	641.9	641.8	641.6	641.4	641.6	642.4	643.1	643.8	644.5
177.5°	643.4	642.7	642.7	642.6	642.5	642.4	642.7	643.3	643.8	644.4	645.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	586.4	586.8	590.0	591.6	594.4	595.6	596.9	596.6	596.6	597.2	601.7
5°	587.6	591.7	597.7	603.6	609.3	614.1	617.4	620.6	621.9	627.7	632.9
7.5°	585.5	593.0	603.0	612.0	622.7	631.1	638.0	644.4	648.6	657.2	665.9
10°	582.7	593.3	604.6	616.2	631.0	642.1	653.4	662.2	664.9	677.7	685.0
12.5°	577.2	591.3	605.7	620.7	635.2	650.5	663.0	671.7	681.7	693.1	706.6
15°	569.0	585.1	604.0	623.2	643.9	662.5	675.9	691.1	702.0	714.6	726.4
17.5°	557.1	578.0	601.9	624.2	648.1	668.1	686.5	701.1	708.7	716.0	717.6
20°	547.7	570.2	598.3	624.6	648.5	671.6	689.9	702.0	704.1	704.3	693.6
22.5°	537.5	562.9	592.4	619.3	647.9	673.6	687.8	692.9	684.9	671.2	650.4
25°	518.7	548.1	582.4	613.1	644.4	668.6	673.5	664.4	636.2	606.6	569.2
27.5°	498.4	531.5	568.1	602.4	635.6	650.7	640.2	607.3	556.6	512.5	459.1
30°	483.5	520.6	556.6	594.9	625.7	632.1	608.1	559.6	500.5	434.1	380.8
32.5°	466.5	505.3	544.9	584.5	610.3	604.0	564.2	504.5	435.2	369.9	319.6
35°	442.2	482.2	525.0	564.7	581.1	553.8	494.2	416.6	345.7	284.8	250.1
37.5°	414.1	457.8	502.2	538.7	537.5	492.0	410.8	330.7	271.2	235.1	210.4
40°	394.1	438.4	486.3	517.1	504.0	444.6	356.7	281.2	237.6	208.8	190.8
42.5°	375.1	419.4	467.1	491.5	468.6	395.7	308.1	248.9	212.9	190.6	175.9
45°	342.5	389.3	433.5	447.0	406.1	325.7	249.1	206.2	182.3	165.7	155.6
47.5°	310.7	356.8	397.1	397.3	342.0	264.1	210.2	178.4	158.0	145.2	137.9
50°	291.2	335.0	368.8	363.6	300.8	235.0	188.0	160.6	143.7	133.7	126.0
52.5°	269.4	311.8	341.2	326.2	265.9	206.8	168.0	145.1	131.0	122.3	115.5
55°	237.6	275.3	296.0	273.2	217.0	172.0	142.0	123.9	113.4	106.1	100.2
57.5°	206.3	237.5	250.4	224.0	178.7	142.6	120.1	106.6	96.1	90.9	87.8
60°	186.7	213.3	222.4	193.2	155.3	124.8	106.4	93.8	86.1	82.7	79.6
62.5°	167.5	189.1	192.9	166.2	135.5	109.2	93.4	82.8	77.7	74.4	71.5
65°	138.9	154.5	152.8	131.3	107.2	86.7	75.2	68.7	64.8	60.2	55.1
67.5°	114.4	123.9	118.2	102.1	81.8	67.4	59.8	54.9	50.1	45.7	44.6
70°	98.8	104.3	98.3	83.5	67.1	56.5	50.5	44.6	41.7	40.8	38.9
72.5°	83.9	85.9	79.3	66.6	54.6	46.8	40.8	37.6	36.0	35.2	34.1
75°	63.0	61.6	55.9	46.0	37.9	32.6	30.8	29.6	28.5	27.7	27.1
77.5°	44.2	42.2	37.1	30.6	26.4	23.9	22.7	22.1	21.7	21.2	20.6
80°	33.3	31.8	26.8	21.8	20.1	18.8	18.2	17.4	17.4	17.0	16.4
82.5°	24.3	22.7	18.3	16.1	15.1	14.3	13.8	13.4	13.2	13.3	12.8
85°	12.8	10.3	9.1	8.7	8.1	7.7	7.9	7.5	7.5	7.5	7.3
87.5°	4.2	3.7	3.7	3.7	4.1	4.3	4.3	4.5	4.8	4.7	5.0
90°	1.6	2.8	3.8	5.0	6.0	6.9	7.7	8.5	9.3	9.8	10.3
92.5°	9.3	9.2	9.1	9.0	9.2	9.5	10.0	10.3	10.8	11.1	11.3
95°	26.8	23.5	20.0	16.6	15.2	16.0	16.7	17.4	18.2	18.6	19.2
97.5°	50.4	40.8	31.2	21.6	17.6	19.3	21.0	22.6	24.3	24.7	25.1
100°	68.2	54.0	39.9	25.7	19.5	21.2	23.0	24.8	26.5	27.4	28.2
102.5°	104.0	100.9	97.9	95.0	86.1	71.4	56.7	42.0	27.3	28.4	29.4
105°	144.5	147.7	150.8	153.9	141.3	113.1	84.9	56.6	28.4	29.5	30.7
107.5°	183.3	185.8	188.3	190.8	175.1	141.3	107.5	73.6	39.8	38.6	37.5
110°	208.3	210.5	212.7	214.8	201.0	171.1	141.2	111.3	81.4	71.1	60.7





TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	231.9	233.8	235.8	237.6	235.0	227.6	220.2	212.8	205.5	167.6	129.9
115°	269.3	271.1	272.9	274.6	276.8	279.4	282.0	284.5	287.1	239.2	191.4
117.5°	303.2	305.1	307.1	309.1	310.9	312.7	314.5	316.3	318.0	306.5	294.9
120°	327.3	328.9	330.4	332.0	333.7	335.6	337.4	339.2	341.1	342.3	343.6
122.5°	348.2	349.9	351.5	353.1	355.0	357.0	359.0	361.1	363.1	363.8	364.5
125°	379.7	381.0	382.4	383.7	385.4	387.4	389.3	391.3	393.2	394.0	394.7
127.5°	408.6	410.1	411.5	413.0	414.6	416.0	417.5	418.9	420.4	421.4	422.5
130°	427.0	428.6	430.3	431.9	433.4	434.5	435.6	436.8	437.9	439.1	440.1
132.5°	445.3	446.7	448.2	449.6	450.8	452.0	453.2	454.2	455.4	456.4	457.4
135°	469.8	471.4	473.1	474.7	476.1	477.0	478.0	478.8	479.7	480.8	481.9
137.5°	493.7	494.9	496.1	497.2	498.4	499.4	500.5	501.5	502.6	503.6	504.6
140°	509.4	510.3	511.1	511.9	512.9	514.1	515.2	516.3	517.5	518.4	519.3
142.5°	522.8	523.5	524.2	525.0	526.0	527.4	528.6	529.9	531.3	532.1	533.0
145°	543.0	542.9	542.8	542.7	543.5	545.3	547.0	548.8	550.5	551.3	552.0
147.5°	561.0	560.6	560.3	559.8	560.5	562.2	564.0	565.7	567.5	568.0	568.6
150°	572.6	571.9	571.1	570.4	570.9	572.6	574.2	575.9	577.5	578.1	578.7
152.5°	582.6	581.8	580.9	580.1	580.5	582.1	583.7	585.2	586.8	587.5	588.1
155°	597.1	596.1	595.2	594.2	594.4	595.7	596.9	598.2	599.4	600.0	600.7
157.5°	608.7	607.9	607.1	606.3	606.4	607.2	608.1	608.9	609.8	610.5	611.2
160°	615.5	614.9	614.3	613.7	613.7	614.3	614.9	615.5	616.2	616.8	617.3
162.5°	621.4	620.8	620.2	619.6	619.6	620.1	620.6	621.2	621.7	622.4	623.1
165°	629.5	628.8	628.2	627.6	627.5	627.8	628.0	628.4	628.7	629.5	630.2
167.5°	635.4	634.8	634.2	633.6	633.4	633.6	634.0	634.3	634.5	635.3	636.0
170°	638.8	638.2	637.6	636.9	636.7	636.9	637.1	637.3	637.6	638.3	639.0
172.5°	641.1	640.4	639.8	639.2	638.9	639.2	639.4	639.5	639.8	640.5	641.2
175°	643.8	643.1	642.4	641.6	641.4	641.6	641.8	641.9	642.2	642.9	643.6
177.5°	644.4	643.8	643.3	642.7	642.4	642.5	642.6	642.7	642.7	643.4	643.9
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1	643.1



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	603.3	605.5	606.5	606.5	607.6	607.1	606.6
5°	638.0	641.9	642.7	646.3	649.0	648.2	648.5
7.5°	672.5	678.7	684.8	687.6	688.0	689.6	690.3
10°	693.8	698.8	708.3	706.9	714.0	718.1	711.4
12.5°	714.2	721.0	727.6	729.4	733.4	734.8	732.1
15°	732.6	736.3	736.6	735.7	736.9	735.8	732.0
17.5°	715.4	709.4	697.5	691.8	687.3	680.6	678.0
20°	686.9	669.4	649.2	641.1	631.6	613.0	617.4
22.5°	625.3	605.5	585.1	561.5	550.2	532.5	531.5
25°	529.5	495.3	457.5	431.2	415.8	398.2	390.5
27.5°	411.7	368.5	337.7	322.1	307.8	293.9	293.3
30°	334.2	301.8	277.9	264.6	255.8	249.9	251.2
32.5°	281.7	259.5	243.3	232.3	225.9	221.4	221.3
35°	230.3	215.1	204.7	200.1	195.5	192.3	192.4
37.5°	197.1	188.0	182.2	177.1	174.2	172.5	171.7
40°	180.0	172.5	168.1	165.1	162.6	160.4	160.0
42.5°	166.7	160.4	156.0	153.6	151.3	149.7	149.4
45°	147.8	142.8	138.8	136.1	135.1	133.7	133.7
47.5°	131.5	126.5	123.4	121.7	120.0	119.0	119.0
50°	120.6	116.6	113.9	112.8	111.4	110.8	110.6
52.5°	110.7	107.7	105.8	105.0	104.4	103.7	103.8
55°	97.2	95.6	94.8	94.2	93.2	91.9	92.7
57.5°	86.0	84.5	82.4	80.4	79.5	78.6	79.0
60°	78.0	75.2	72.3	70.1	69.5	67.7	67.7
62.5°	67.9	63.9	60.5	59.2	58.6	57.8	57.6
65°	52.3	50.6	49.8	49.0	48.6	48.6	48.2
67.5°	43.3	42.6	41.7	41.6	41.2	41.0	40.9
70°	38.3	37.5	37.1	36.8	36.5	36.6	36.0
72.5°	33.4	32.8	32.7	32.2	31.9	31.9	31.5
75°	26.3	26.3	26.1	25.9	25.5	25.3	25.5
77.5°	20.2	20.3	20.0	19.9	19.9	19.9	19.7
80°	16.2	16.4	16.2	16.0	15.8	16.0	15.8
82.5°	12.8	12.5	12.5	12.4	12.4	12.3	12.2
85°	7.3	7.5	7.3	7.1	7.1	7.1	7.3
87.5°	4.9	5.0	5.1	5.2	5.2	5.3	5.1
90°	10.9	11.4	11.8	11.9	12.1	12.4	12.6
92.5°	11.6	11.9	12.0	12.2	12.3	12.5	12.6
95°	19.7	20.2	20.4	20.3	20.2	20.2	20.0
97.5°	25.5	25.9	26.2	26.3	26.5	26.6	26.8
100°	29.0	29.9	30.3	30.6	30.8	30.9	31.2
102.5°	30.5	31.6	32.3	32.5	32.8	33.1	33.4
105°	31.8	32.9	33.7	34.2	34.5	35.0	35.4
107.5°	36.3	35.1	34.8	35.1	35.6	35.9	36.4
110°	50.4	40.0	35.1	35.5	35.9	36.4	36.7



TEST NUMBER: P331621-940

CATALOG NUMBER: S122RDIP-S290D530U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	92.2	54.5	35.8	36.1	36.5	36.8	37.1
115°	143.5	95.6	67.9	60.5	53.1	45.6	38.2
117.5°	283.3	271.7	253.7	229.2	204.7	180.3	155.8
120°	344.8	346.1	339.7	325.7	311.8	297.8	283.8
122.5°	365.3	366.0	365.1	362.4	359.6	357.0	354.2
125°	395.4	396.1	396.6	397.0	397.3	397.6	397.9
127.5°	423.6	424.6	425.2	425.3	425.3	425.3	425.4
130°	441.3	442.5	443.0	442.8	442.7	442.6	442.6
132.5°	458.3	459.3	459.7	459.6	459.5	459.4	459.3
135°	482.9	483.9	484.4	484.1	483.9	483.8	483.5
137.5°	505.6	506.7	506.9	506.6	506.2	506.0	505.6
140°	520.2	521.2	521.4	520.8	520.4	519.9	519.3
142.5°	533.8	534.7	534.8	534.3	533.8	533.2	532.7
145°	552.7	553.4	553.5	553.0	552.5	552.0	551.4
147.5°	569.1	569.6	569.6	569.3	568.8	568.4	567.9
150°	579.3	580.0	580.1	579.5	579.0	578.5	578.0
152.5°	588.7	589.3	589.2	588.6	587.9	587.2	586.6
155°	601.3	601.9	601.7	600.9	600.1	599.3	598.4
157.5°	611.9	612.6	612.6	611.7	610.9	610.1	609.3
160°	618.0	618.6	618.6	617.9	617.2	616.4	615.6
162.5°	623.8	624.6	624.5	623.6	622.7	621.8	620.9
165°	630.9	631.6	631.6	630.9	630.2	629.5	628.7
167.5°	636.8	637.5	637.4	636.4	635.5	634.5	633.6
170°	639.7	640.4	640.3	639.4	638.5	637.6	636.6
172.5°	641.9	642.7	642.6	641.7	640.7	639.8	638.8
175°	644.4	645.1	645.0	643.9	642.8	641.9	640.8
177.5°	644.5	645.1	645.0	644.3	643.5	642.7	642.0
180°	643.1	643.1	643.1	643.1	643.1	643.1	643.1

(END OF REPORT)