

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331628-940

Luminaire Tested: **S122RDIP-S290D725U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331628-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S290D725U940-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3320.3 lumens  
Efficiency: N/A  
Efficacy: 106.4 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38	30
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	27
2	86	79	73	68	77	71	66	62	57	53	51	43	41	39	31	30	29	23
3	79	70	63	58	70	63	57	53	50	46	43	39	36	34	28	26	25	20
4	72	62	55	49	65	56	50	45	45	41	37	35	32	29	25	23	22	18
5	66	55	48	42	59	50	44	39	41	36	32	31	28	26	23	21	19	16
6	61	50	42	37	55	45	39	34	37	32	28	29	25	23	21	19	17	14
7	57	45	38	32	51	41	35	30	33	29	25	26	23	20	19	17	16	13
8	53	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14	12
9	49	37	30	26	44	34	28	24	28	23	20	22	19	17	17	15	13	11
10	46	34	28	23	41	31	25	21	26	21	18	20	17	15	15	13	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9411	9411	9411	9411
5°	10511	9470	8399	9470
10°	11663	9404	7279	9404
15°	12236	9267	5735	9267
20°	10608	9062	4962	9062
25°	6957	8783	4431	8783
30°	4683	8444	4010	8444
35°	3792	8016	3617	8016
40°	3372	7552	3347	7552
45°	3053	7005	2987	7005
50°	2778	6465	2768	6465
55°	2609	5866	2578	5866
60°	2186	5318	2160	5318
65°	1841	4829	2090	4829
70°	1699	4310	1969	4310
75°	1591	3755	1822	3755
80°	1469	3096	1618	3096
85°	1352	2445	1426	2445



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.3	1.7
10°-20°	154.0	4.6
20°-30°	198.4	6.0
30°-40°	188.6	5.7
40°-50°	161.5	4.9
50°-60°	123.0	3.7
60°-70°	77.8	2.3
70°-80°	38.8	1.2
80°-90°	13.4	0.4
90°-100°	52.3	1.6
100°-110°	162.5	4.9
110°-120°	277.9	8.4
120°-130°	365.4	11.0
130°-140°	410.1	12.4
140°-150°	402.1	12.1
150°-160°	337.3	10.2
160°-170°	223.7	6.7
170°-180°	78.2	2.4
0°-30°	407.7	12.3
0°-40°	596.2	18.0
0°-60°	880.8	26.5
0°-90°	1010.8	30.4
90°-120°	492.7	14.8
90°-150°	1670.3	50.3
90°-180°	2309.0	69.5
0°-180°	3320.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	583	583	583	583	583	
5°	648	584	518	584	648	64
15°	732	554	343	554	732	197
25°	390	493	249	493	390	185
35°	192	407	184	407	192	123
45°	134	307	131	307	134	103
55°	93	208	92	208	93	81
65°	48	126	55	126	48	49
75°	26	60	29	60	26	27
85°	7	13	8	13	7	8
90°	24	1	24	1	24	11
95°	43	36	43	36	43	48
105°	155	150	155	150	155	163
115°	279	279	279	279	279	275
125°	407	406	407	406	407	363
135°	531	525	531	525	531	409
145°	644	637	644	637	644	402
155°	734	728	734	728	734	338
165°	793	792	793	792	793	224
175°	822	825	822	825	822	78
180°	826	826	826	826	826	



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	606.6	607.1	607.6	606.5	606.5	605.5	603.3	601.7	597.2	596.6	596.6
5°	648.5	648.2	649.0	646.3	642.7	641.9	638.0	632.9	627.7	621.9	620.6
7.5°	690.3	689.6	688.0	687.6	684.8	678.7	672.5	665.9	657.2	648.6	644.4
10°	711.4	718.1	714.0	706.9	708.3	698.8	693.8	685.0	677.7	664.9	662.2
12.5°	732.1	734.8	733.4	729.4	727.6	721.0	714.2	706.6	693.1	681.7	671.7
15°	732.0	735.8	736.9	735.7	736.6	736.3	732.6	726.4	714.6	702.0	691.1
17.5°	678.0	680.6	687.3	691.8	697.5	709.4	715.4	717.6	716.0	708.7	701.1
20°	617.4	613.0	631.6	641.1	649.2	669.4	686.9	693.6	704.3	704.1	702.0
22.5°	531.5	532.5	550.2	561.5	585.1	605.5	625.3	650.4	671.2	684.9	692.9
25°	390.5	398.2	415.8	431.2	457.5	495.3	529.5	569.2	606.6	636.2	664.4
27.5°	293.3	293.9	307.8	322.1	337.7	368.5	411.7	459.1	512.5	556.6	607.3
30°	251.2	249.9	255.8	264.6	277.9	301.8	334.2	380.8	434.1	500.5	559.6
32.5°	221.3	221.4	225.9	232.3	243.3	259.5	281.7	319.6	369.9	435.2	504.5
35°	192.4	192.3	195.5	200.1	204.7	215.1	230.3	250.1	284.8	345.7	416.6
37.5°	171.7	172.5	174.2	177.1	182.2	188.0	197.1	210.4	235.1	271.2	330.7
40°	160.0	160.4	162.6	165.1	168.1	172.5	180.0	190.8	208.8	237.6	281.2
42.5°	149.4	149.7	151.3	153.6	156.0	160.4	166.7	175.9	190.6	212.9	248.9
45°	133.7	133.7	135.1	136.1	138.8	142.8	147.8	155.6	165.7	182.3	206.2
47.5°	119.0	119.0	120.0	121.7	123.4	126.5	131.5	137.9	145.2	158.0	178.4
50°	110.6	110.8	111.4	112.8	113.9	116.6	120.6	126.0	133.7	143.7	160.6
52.5°	103.8	103.7	104.4	105.0	105.8	107.7	110.7	115.5	122.3	131.0	145.1
55°	92.7	91.9	93.2	94.2	94.8	95.6	97.2	100.2	106.1	113.4	123.9
57.5°	79.0	78.6	79.5	80.4	82.4	84.5	86.0	87.8	90.9	96.1	106.6
60°	67.7	67.7	69.5	70.1	72.3	75.2	78.0	79.6	82.7	86.1	93.8
62.5°	57.6	57.8	58.6	59.2	60.5	63.9	67.9	71.5	74.4	77.7	82.8
65°	48.2	48.6	48.6	49.0	49.8	50.6	52.3	55.1	60.2	64.8	68.7
67.5°	40.9	41.0	41.2	41.6	41.7	42.6	43.3	44.6	45.7	50.1	54.9
70°	36.0	36.6	36.5	36.8	37.1	37.5	38.3	38.9	40.8	41.7	44.6
72.5°	31.5	31.9	31.9	32.2	32.7	32.8	33.4	34.1	35.2	36.0	37.6
75°	25.5	25.3	25.5	25.9	26.1	26.3	26.3	27.1	27.7	28.5	29.6
77.5°	19.7	19.9	19.9	19.9	20.0	20.3	20.2	20.6	21.2	21.7	22.1
80°	15.8	16.0	15.8	16.0	16.2	16.4	16.2	16.4	17.0	17.4	17.4
82.5°	12.2	12.3	12.4	12.4	12.5	12.5	12.8	12.8	13.3	13.2	13.4
85°	7.3	7.1	7.1	7.1	7.3	7.5	7.3	7.3	7.5	7.5	7.5
87.5°	7.3	7.5	7.4	7.4	7.4	7.4	7.5	7.7	7.6	7.8	7.0
90°	23.7	23.5	23.4	23.3	23.1	23.2	23.5	23.8	24.1	24.4	21.0
92.5°	22.6	22.6	22.6	22.5	22.5	22.4	22.4	22.3	22.2	22.2	21.4
95°	43.2	43.5	43.9	44.1	44.5	44.6	44.6	44.6	44.6	44.6	44.3
97.5°	74.8	74.9	74.9	75.0	75.0	75.0	75.0	75.0	75.0	75.0	74.4
100°	95.5	95.7	95.8	95.9	96.1	96.2	96.2	96.2	96.2	96.2	95.7
102.5°	118.9	119.0	119.2	119.4	119.5	119.6	119.4	119.3	119.1	119.0	118.4
105°	154.7	154.7	154.7	154.7	154.7	154.6	154.3	154.0	153.6	153.4	153.0
107.5°	188.5	189.2	189.9	190.6	191.4	191.6	191.5	191.4	191.3	191.1	191.1
110°	214.6	215.2	215.6	216.1	216.5	216.8	216.8	216.8	216.8	216.8	216.8



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	239.8	240.1	240.4	240.8	241.1	241.5	241.8	242.2	242.6	243.0	243.1
115°	278.8	279.3	279.7	280.2	280.6	281.0	281.2	281.2	281.4	281.6	281.9
117.5°	316.0	316.5	316.9	317.4	317.9	318.3	318.7	319.1	319.4	319.8	320.7
120°	342.2	342.7	343.1	343.6	344.1	344.3	344.3	344.3	344.3	344.3	345.5
122.5°	367.9	368.2	368.5	368.9	369.3	369.6	370.0	370.3	370.7	371.0	371.9
125°	407.1	407.2	407.3	407.5	407.7	408.0	408.4	408.9	409.4	409.8	410.3
127.5°	442.7	443.3	443.7	444.3	444.7	445.2	445.8	446.4	446.9	447.5	448.0
130°	468.4	469.0	469.7	470.2	470.8	471.4	471.6	472.0	472.3	472.6	472.9
132.5°	492.9	493.4	493.9	494.4	494.9	495.5	496.1	496.9	497.6	498.2	498.1
135°	531.1	531.5	532.1	532.5	533.0	533.2	533.4	533.6	533.8	533.9	533.6
137.5°	565.7	566.3	566.9	567.6	568.2	568.6	568.6	568.8	568.9	569.0	568.6
140°	589.7	590.3	590.9	591.6	592.1	592.5	592.5	592.5	592.5	592.5	591.7
142.5°	611.4	612.1	612.6	613.2	613.9	614.1	614.0	613.9	613.8	613.7	613.1
145°	644.0	644.6	645.2	645.9	646.5	646.8	646.6	646.4	646.3	646.1	645.2
147.5°	673.2	673.8	674.3	674.9	675.6	675.6	675.3	674.9	674.6	674.3	673.7
150°	692.1	692.6	693.0	693.5	694.0	694.0	693.5	693.0	692.6	692.1	691.5
152.5°	710.0	710.5	711.1	711.8	712.3	712.3	711.8	711.1	710.5	710.0	709.2
155°	734.0	734.4	734.9	735.3	735.8	735.7	734.9	734.1	733.3	732.5	732.1
157.5°	754.6	755.3	756.1	756.8	757.5	757.4	756.3	755.3	754.2	753.1	752.9
160°	767.4	768.0	768.7	769.3	769.9	769.7	768.8	767.9	767.0	766.0	765.9
162.5°	778.6	779.3	780.1	780.8	781.5	781.4	780.3	779.3	778.2	777.1	777.0
165°	793.2	794.0	794.7	795.5	796.3	796.1	795.0	794.0	792.9	791.8	791.8
167.5°	805.2	806.0	806.8	807.6	808.4	808.2	807.2	806.1	805.0	803.9	804.0
170°	811.3	812.3	813.2	814.1	815.0	814.9	813.9	812.8	811.7	810.6	810.7
172.5°	816.4	817.3	818.1	819.1	820.0	819.9	818.9	817.8	816.7	815.6	815.8
175°	821.8	822.7	823.6	824.6	825.5	825.4	824.3	823.2	822.2	821.1	821.4
177.5°	824.3	825.0	825.7	826.5	827.2	827.2	826.5	825.7	825.0	824.3	824.5
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	596.9	595.6	594.4	591.6	590.0	586.8	586.4	586.2	582.0	577.9	576.8
5°	617.4	614.1	609.3	603.6	597.7	591.7	587.6	584.3	576.2	568.6	564.1
7.5°	638.0	631.1	622.7	612.0	603.0	593.0	585.5	578.8	567.3	556.2	548.8
10°	653.4	642.1	631.0	616.2	604.6	593.3	582.7	573.6	560.7	546.1	535.7
12.5°	663.0	650.5	635.2	620.7	605.7	591.3	577.2	565.5	550.3	535.2	523.0
15°	675.9	662.5	643.9	623.2	604.0	585.1	569.0	554.4	534.6	516.5	501.5
17.5°	686.5	668.1	648.1	624.2	601.9	578.0	557.1	538.5	516.4	494.6	477.0
20°	689.9	671.6	648.5	624.6	598.3	570.2	547.7	527.4	503.7	480.0	459.8
22.5°	687.8	673.6	647.9	619.3	592.4	562.9	537.5	514.0	487.7	463.5	440.1
25°	673.5	668.6	644.4	613.1	582.4	548.1	518.7	493.0	463.1	437.1	411.6
27.5°	640.2	650.7	635.6	602.4	568.1	531.5	498.4	469.1	438.0	408.8	383.4
30°	608.1	632.1	625.7	594.9	556.6	520.6	483.5	452.9	419.7	389.7	364.6
32.5°	564.2	604.0	610.3	584.5	544.9	505.3	466.5	436.0	401.4	369.8	345.3
35°	494.2	553.8	581.1	564.7	525.0	482.2	442.2	406.7	371.8	340.7	316.4
37.5°	410.8	492.0	537.5	538.7	502.2	457.8	414.1	378.9	343.2	312.6	286.3
40°	356.7	444.6	504.0	517.1	486.3	438.4	394.1	358.3	323.5	293.5	263.3
42.5°	308.1	395.7	468.6	491.5	467.1	419.4	375.1	337.6	303.7	275.4	244.5
45°	249.1	325.7	406.1	447.0	433.5	389.3	342.5	306.8	275.1	250.6	221.0
47.5°	210.2	264.1	342.0	397.3	397.1	356.8	310.7	276.6	247.1	224.1	200.2
50°	188.0	235.0	300.8	363.6	368.8	335.0	291.2	257.4	229.9	205.8	186.5
52.5°	168.0	206.8	265.9	326.2	341.2	311.8	269.4	238.2	211.4	189.2	172.8
55°	142.0	172.0	217.0	273.2	296.0	275.3	237.6	208.4	186.7	168.1	153.9
57.5°	120.1	142.6	178.7	224.0	250.4	237.5	206.3	182.6	164.1	147.2	136.1
60°	106.4	124.8	155.3	193.2	222.4	213.3	186.7	164.7	148.9	134.3	123.8
62.5°	93.4	109.2	135.5	166.2	192.9	189.1	167.5	148.9	135.1	121.8	112.9
65°	75.2	86.7	107.2	131.3	152.8	154.5	138.9	126.4	114.0	103.5	95.6
67.5°	59.8	67.4	81.8	102.1	118.2	123.9	114.4	104.8	95.0	86.9	80.0
70°	50.5	56.5	67.1	83.5	98.3	104.3	98.8	91.3	82.8	76.2	70.3
72.5°	40.8	46.8	54.6	66.6	79.3	85.9	83.9	78.6	71.7	66.1	60.5
75°	30.8	32.6	37.9	46.0	55.9	61.6	63.0	60.2	54.7	50.5	47.2
77.5°	22.7	23.9	26.4	30.6	37.1	42.2	44.2	43.9	40.1	37.7	34.6
80°	18.2	18.8	20.1	21.8	26.8	31.8	33.3	33.3	30.6	29.6	26.6
82.5°	13.8	14.3	15.1	16.1	18.3	22.7	24.3	24.6	23.0	21.7	19.3
85°	7.9	7.7	8.1	8.7	9.1	10.3	12.8	13.2	12.8	11.1	10.5
87.5°	6.2	5.7	5.1	4.4	4.2	3.9	4.4	4.8	4.5	4.5	4.5
90°	17.6	14.2	10.8	8.1	6.2	4.5	2.6	0.7	2.6	4.5	6.2
92.5°	20.5	19.7	18.9	17.8	16.5	15.2	13.7	12.4	13.7	15.2	16.5
95°	44.0	43.7	43.3	42.4	40.9	39.3	37.8	36.2	37.8	39.3	40.9
97.5°	73.8	73.2	72.7	71.7	70.3	68.9	67.6	66.3	67.6	68.9	70.3
100°	95.2	94.8	94.3	93.5	92.2	91.0	89.8	88.5	89.8	91.0	92.2
102.5°	117.9	117.3	116.7	115.9	114.9	114.0	112.9	111.9	112.9	114.0	114.9
105°	152.8	152.4	152.1	151.7	151.2	150.8	150.3	149.9	150.3	150.8	151.2
107.5°	191.1	191.1	191.1	190.7	190.1	189.4	188.8	188.1	188.8	189.4	190.1
110°	216.8	216.8	216.8	216.3	215.3	214.5	213.5	212.6	213.5	214.5	215.3





TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	243.3	243.3	243.4	243.1	242.1	241.2	240.3	239.3	240.3	241.2	242.1
115°	282.2	282.5	282.9	282.5	281.6	280.6	279.7	278.8	279.7	280.6	281.6
117.5°	321.6	322.4	323.2	323.1	321.8	320.6	319.3	318.1	319.3	320.6	321.8
120°	346.8	348.0	349.3	349.3	348.0	346.8	345.5	344.3	345.5	346.8	348.0
122.5°	372.8	373.7	374.5	374.3	372.7	371.3	369.8	368.3	369.8	371.3	372.7
125°	410.7	411.3	411.7	411.3	409.8	408.4	407.1	405.6	407.1	408.4	409.8
127.5°	448.6	449.2	449.7	449.1	447.4	445.6	443.8	442.0	443.8	445.6	447.4
130°	473.1	473.5	473.8	473.0	470.9	469.0	466.9	464.9	466.9	469.0	470.9
132.5°	498.1	498.0	497.9	497.1	495.4	493.8	492.2	490.5	492.2	493.8	495.4
135°	533.2	533.0	532.6	531.6	529.9	528.2	526.6	524.9	526.6	528.2	529.9
137.5°	568.2	567.8	567.4	566.5	565.2	563.7	562.3	561.0	562.3	563.7	565.2
140°	590.9	590.1	589.3	588.3	586.8	585.5	584.1	582.7	584.1	585.5	586.8
142.5°	612.6	612.1	611.5	610.6	609.2	607.8	606.4	605.0	606.4	607.8	609.2
145°	644.3	643.4	642.4	641.4	640.3	639.3	638.1	637.0	638.1	639.3	640.3
147.5°	673.1	672.4	671.8	670.8	669.5	668.2	666.9	665.7	666.9	668.2	669.5
150°	690.9	690.3	689.6	688.8	688.0	687.0	686.1	685.2	686.1	687.0	688.0
152.5°	708.5	707.8	706.9	706.1	705.3	704.3	703.4	702.4	703.4	704.3	705.3
155°	731.6	731.1	730.7	730.2	729.8	729.3	728.8	728.3	728.8	729.3	729.8
157.5°	752.6	752.3	752.1	751.8	751.4	751.2	750.8	750.6	750.8	751.2	751.4
160°	765.7	765.5	765.4	765.2	764.8	764.6	764.2	763.9	764.2	764.6	764.8
162.5°	776.9	776.7	776.5	776.4	776.3	776.3	776.2	776.1	776.2	776.3	776.3
165°	791.8	791.8	791.8	791.8	792.0	792.2	792.4	792.5	792.4	792.2	792.0
167.5°	804.0	804.1	804.1	804.3	804.8	805.2	805.7	806.1	805.7	805.2	804.8
170°	810.9	811.1	811.2	811.5	812.0	812.4	813.0	813.4	813.0	812.4	812.0
172.5°	815.9	816.1	816.3	816.5	817.0	817.5	818.0	818.4	818.0	817.5	817.0
175°	821.7	822.0	822.3	822.7	823.1	823.6	824.1	824.6	824.1	823.6	823.1
177.5°	824.7	825.0	825.3	825.5	825.9	826.3	826.7	827.1	826.7	826.3	825.9
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	574.7	573.5	571.4	568.2	566.2	562.8	560.6	561.9	562.2	561.9	561.6
5°	559.3	555.0	549.1	543.4	538.1	532.5	529.2	527.9	525.0	523.4	522.5
7.5°	540.6	533.2	525.0	515.1	506.7	497.8	493.4	491.2	485.4	482.2	479.5
10°	526.6	515.1	506.8	493.8	485.9	474.4	466.5	466.7	458.8	454.3	451.1
12.5°	511.2	498.6	484.7	473.1	462.1	452.8	443.3	439.4	431.1	426.8	418.0
15°	485.7	470.9	456.4	440.6	429.4	415.0	401.3	384.4	370.9	359.1	355.9
17.5°	457.9	439.5	424.9	406.4	387.3	363.1	347.1	337.3	329.2	323.0	318.3
20°	438.7	420.1	404.5	376.6	350.8	334.4	322.7	315.1	306.7	300.0	296.3
22.5°	418.7	399.2	377.9	346.7	326.6	313.5	303.1	294.4	288.6	283.5	280.1
25°	390.1	368.8	333.8	312.4	296.1	282.3	275.1	269.8	263.8	256.6	253.4
27.5°	360.0	326.2	301.0	285.0	269.6	260.6	254.0	246.2	240.8	237.6	234.2
30°	337.4	303.6	284.0	266.5	255.7	245.7	238.0	233.5	228.3	222.8	220.6
32.5°	312.4	285.3	266.4	252.0	240.9	232.4	226.3	219.1	215.3	212.0	207.3
35°	281.2	260.6	243.4	231.8	221.1	214.3	207.2	203.0	196.1	193.2	191.5
37.5°	254.8	237.0	224.2	211.8	203.4	195.8	191.5	184.7	181.7	177.7	173.9
40°	239.8	222.4	210.1	199.9	190.6	184.9	179.5	174.0	169.5	167.7	163.1
42.5°	224.6	210.4	198.0	187.0	180.7	174.7	167.8	163.8	159.2	156.2	153.4
45°	203.6	191.0	180.5	171.4	164.4	158.2	153.7	147.0	144.5	138.6	136.1
47.5°	185.1	173.4	163.4	154.7	148.0	143.9	137.4	132.2	128.0	124.3	121.2
50°	172.0	162.2	152.5	144.8	138.8	132.9	126.2	123.6	117.1	115.2	113.4
52.5°	160.0	150.7	141.9	134.3	128.2	122.5	116.6	113.2	108.8	107.0	105.7
55°	143.2	134.3	125.8	119.1	113.1	107.2	103.5	99.2	97.2	95.8	94.2
57.5°	126.4	118.3	111.8	105.0	98.9	94.3	90.1	87.5	85.4	83.6	81.6
60°	115.7	108.0	102.1	95.8	89.5	85.7	82.5	79.4	77.0	74.1	73.3
62.5°	104.3	97.6	92.2	86.1	80.6	77.1	74.0	71.2	68.2	64.1	63.0
65°	88.7	83.5	77.8	72.7	67.9	64.4	59.9	56.7	55.5	55.1	54.9
67.5°	74.6	69.6	64.7	59.6	55.2	52.0	49.7	49.2	48.3	48.2	47.5
70°	65.2	60.5	55.7	50.8	46.5	46.0	45.2	44.3	43.3	43.0	42.5
72.5°	56.8	52.0	47.1	43.2	41.4	40.7	39.9	39.0	38.3	37.9	37.7
75°	43.5	39.1	35.8	34.4	33.4	32.8	31.6	31.0	30.6	30.0	29.8
77.5°	31.4	28.8	27.4	26.5	25.4	24.8	24.1	23.5	23.0	22.9	22.6
80°	23.9	22.6	21.7	20.4	20.1	19.3	19.1	18.5	18.6	18.0	18.0
82.5°	18.5	17.0	16.1	15.6	15.2	14.5	14.4	14.1	14.1	13.6	13.6
85°	9.5	9.1	8.7	8.3	8.3	7.7	7.9	7.7	7.7	7.3	7.1
87.5°	4.7	5.1	5.4	6.2	6.8	7.3	7.2	7.0	7.0	6.9	6.7
90°	8.1	10.8	14.2	17.6	21.0	24.4	24.1	23.8	23.5	23.2	23.1
92.5°	17.8	18.9	19.7	20.5	21.4	22.2	22.2	22.3	22.4	22.4	22.5
95°	42.4	43.3	43.7	44.0	44.3	44.6	44.6	44.6	44.6	44.6	44.5
97.5°	71.7	72.7	73.2	73.8	74.4	75.0	75.0	75.0	75.0	75.0	75.0
100°	93.5	94.3	94.8	95.2	95.7	96.2	96.2	96.2	96.2	96.2	96.1
102.5°	115.9	116.7	117.3	117.9	118.4	119.0	119.1	119.3	119.4	119.6	119.5
105°	151.7	152.1	152.4	152.8	153.0	153.4	153.6	154.0	154.3	154.6	154.7
107.5°	190.7	191.1	191.1	191.1	191.1	191.1	191.3	191.4	191.5	191.6	191.4
110°	216.3	216.8	216.8	216.8	216.8	216.8	216.8	216.8	216.8	216.8	216.5



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	243.1	243.4	243.3	243.3	243.1	243.0	242.6	242.2	241.8	241.5	241.1
115°	282.5	282.9	282.5	282.2	281.9	281.6	281.4	281.2	281.2	281.0	280.6
117.5°	323.1	323.2	322.4	321.6	320.7	319.8	319.4	319.1	318.7	318.3	317.9
120°	349.3	349.3	348.0	346.8	345.5	344.3	344.3	344.3	344.3	344.3	344.1
122.5°	374.3	374.5	373.7	372.8	371.9	371.0	370.7	370.3	370.0	369.6	369.3
125°	411.3	411.7	411.3	410.7	410.3	409.8	409.4	408.9	408.4	408.0	407.7
127.5°	449.1	449.7	449.2	448.6	448.0	447.5	446.9	446.4	445.8	445.2	444.7
130°	473.0	473.8	473.5	473.1	472.9	472.6	472.3	472.0	471.6	471.4	470.8
132.5°	497.1	497.9	498.0	498.1	498.1	498.2	497.6	496.9	496.1	495.5	494.9
135°	531.6	532.6	533.0	533.2	533.6	533.9	533.8	533.6	533.4	533.2	533.0
137.5°	566.5	567.4	567.8	568.2	568.6	569.0	568.9	568.8	568.6	568.6	568.2
140°	588.3	589.3	590.1	590.9	591.7	592.5	592.5	592.5	592.5	592.5	592.1
142.5°	610.6	611.5	612.1	612.6	613.1	613.7	613.8	613.9	614.0	614.1	613.9
145°	641.4	642.4	643.4	644.3	645.2	646.1	646.3	646.4	646.6	646.8	646.5
147.5°	670.8	671.8	672.4	673.1	673.7	674.3	674.6	674.9	675.3	675.6	675.6
150°	688.8	689.6	690.3	690.9	691.5	692.1	692.6	693.0	693.5	694.0	694.0
152.5°	706.1	706.9	707.8	708.5	709.2	710.0	710.5	711.1	711.8	712.3	712.3
155°	730.2	730.7	731.1	731.6	732.1	732.5	733.3	734.1	734.9	735.7	735.8
157.5°	751.8	752.1	752.3	752.6	752.9	753.1	754.2	755.3	756.3	757.4	757.5
160°	765.2	765.4	765.5	765.7	765.9	766.0	767.0	767.9	768.8	769.7	769.9
162.5°	776.4	776.5	776.7	776.9	777.0	777.1	778.2	779.3	780.3	781.4	781.5
165°	791.8	791.8	791.8	791.8	791.8	791.8	792.9	794.0	795.0	796.1	796.3
167.5°	804.3	804.1	804.1	804.0	804.0	803.9	805.0	806.1	807.2	808.2	808.4
170°	811.5	811.2	811.1	810.9	810.7	810.6	811.7	812.8	813.9	814.9	815.0
172.5°	816.5	816.3	816.1	815.9	815.8	815.6	816.7	817.8	818.9	819.9	820.0
175°	822.7	822.3	822.0	821.7	821.4	821.1	822.2	823.2	824.3	825.4	825.5
177.5°	825.5	825.3	825.0	824.7	824.5	824.3	825.0	825.7	826.5	827.2	827.2
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	559.8	560.1	559.6	559.9	559.6	560.1	559.8	561.6	561.9	562.2	561.9
5°	521.6	519.2	518.7	518.2	518.7	519.2	521.6	522.5	523.4	525.0	527.9
7.5°	476.0	475.6	474.6	473.1	474.6	475.6	476.0	479.5	482.2	485.4	491.2
10°	446.7	445.6	445.4	444.0	445.4	445.6	446.7	451.1	454.3	458.8	466.7
12.5°	412.2	405.7	405.1	401.5	405.1	405.7	412.2	418.0	426.8	431.1	439.4
15°	351.1	349.8	345.7	343.1	345.7	349.8	351.1	355.9	359.1	370.9	384.4
17.5°	316.0	312.0	310.8	310.2	310.8	312.0	316.0	318.3	323.0	329.2	337.3
20°	293.5	289.9	289.3	288.8	289.3	289.9	293.5	296.3	300.0	306.7	315.1
22.5°	277.9	274.1	272.6	271.3	272.6	274.1	277.9	280.1	283.5	288.6	294.4
25°	251.4	249.9	249.1	248.7	249.1	249.9	251.4	253.4	256.6	263.8	269.8
27.5°	230.6	227.5	226.9	225.8	226.9	227.5	230.6	234.2	237.6	240.8	246.2
30°	218.7	217.8	216.3	215.1	216.3	217.8	218.7	220.6	222.8	228.3	233.5
32.5°	204.8	203.9	202.7	202.2	202.7	203.9	204.8	207.3	212.0	215.3	219.1
35°	189.4	186.5	185.3	183.5	185.3	186.5	189.4	191.5	193.2	196.1	203.0
37.5°	173.1	171.6	169.9	170.5	169.9	171.6	173.1	173.9	177.7	181.7	184.7
40°	160.4	159.4	159.0	158.8	159.0	159.4	160.4	163.1	167.7	169.5	174.0
42.5°	150.3	147.6	146.5	146.5	146.5	147.6	150.3	153.4	156.2	159.2	163.8
45°	135.1	132.5	130.6	130.8	130.6	132.5	135.1	136.1	138.6	144.5	147.0
47.5°	119.5	119.4	118.2	118.6	118.2	119.4	119.5	121.2	124.3	128.0	132.2
50°	112.0	110.8	109.9	110.2	109.9	110.8	112.0	113.4	115.2	117.1	123.6
52.5°	104.9	103.8	103.2	104.1	103.2	103.8	104.9	105.7	107.0	108.8	113.2
55°	93.2	91.9	91.8	91.6	91.8	91.9	93.2	94.2	95.8	97.2	99.2
57.5°	80.1	79.3	78.0	77.6	78.0	79.3	80.1	81.6	83.6	85.4	87.5
60°	70.7	69.1	67.1	66.9	67.1	69.1	70.7	73.3	74.1	77.0	79.4
62.5°	62.1	61.8	61.3	61.3	61.3	61.8	62.1	63.0	64.1	68.2	71.2
65°	54.5	54.3	54.5	54.7	54.5	54.3	54.5	54.9	55.1	55.5	56.7
67.5°	47.4	47.1	46.7	46.9	46.7	47.1	47.4	47.5	48.2	48.3	49.2
70°	42.1	41.9	41.7	41.7	41.7	41.9	42.1	42.5	43.0	43.3	44.3
72.5°	36.9	36.9	36.7	36.6	36.7	36.9	36.9	37.7	37.9	38.3	39.0
75°	29.6	29.2	29.2	29.2	29.2	29.2	29.6	29.8	30.0	30.6	31.0
77.5°	22.6	22.3	22.1	21.9	22.1	22.3	22.6	22.6	22.9	23.0	23.5
80°	17.8	17.7	17.4	17.4	17.4	17.7	17.8	18.0	18.0	18.6	18.5
82.5°	13.6	13.4	13.4	13.2	13.4	13.4	13.6	13.6	13.6	14.1	14.1
85°	7.3	7.5	7.3	7.7	7.3	7.5	7.3	7.1	7.3	7.7	7.7
87.5°	6.8	6.6	6.8	6.7	6.8	6.6	6.8	6.7	6.9	7.0	7.0
90°	23.3	23.4	23.5	23.7	23.5	23.4	23.3	23.1	23.2	23.5	23.8
92.5°	22.5	22.6	22.6	22.6	22.6	22.6	22.5	22.5	22.4	22.4	22.3
95°	44.1	43.9	43.5	43.2	43.5	43.9	44.1	44.5	44.6	44.6	44.6
97.5°	75.0	74.9	74.9	74.8	74.9	74.9	75.0	75.0	75.0	75.0	75.0
100°	95.9	95.8	95.7	95.5	95.7	95.8	95.9	96.1	96.2	96.2	96.2
102.5°	119.4	119.2	119.0	118.9	119.0	119.2	119.4	119.5	119.6	119.4	119.3
105°	154.7	154.7	154.7	154.7	154.7	154.7	154.7	154.7	154.6	154.3	154.0
107.5°	190.6	189.9	189.2	188.5	189.2	189.9	190.6	191.4	191.6	191.5	191.4
110°	216.1	215.6	215.2	214.6	215.2	215.6	216.1	216.5	216.8	216.8	216.8



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	240.8	240.4	240.1	239.8	240.1	240.4	240.8	241.1	241.5	241.8	242.2
115°	280.2	279.7	279.3	278.8	279.3	279.7	280.2	280.6	281.0	281.2	281.2
117.5°	317.4	316.9	316.5	316.0	316.5	316.9	317.4	317.9	318.3	318.7	319.1
120°	343.6	343.1	342.7	342.2	342.7	343.1	343.6	344.1	344.3	344.3	344.3
122.5°	368.9	368.5	368.2	367.9	368.2	368.5	368.9	369.3	369.6	370.0	370.3
125°	407.5	407.3	407.2	407.1	407.2	407.3	407.5	407.7	408.0	408.4	408.9
127.5°	444.3	443.7	443.3	442.7	443.3	443.7	444.3	444.7	445.2	445.8	446.4
130°	470.2	469.7	469.0	468.4	469.0	469.7	470.2	470.8	471.4	471.6	472.0
132.5°	494.4	493.9	493.4	492.9	493.4	493.9	494.4	494.9	495.5	496.1	496.9
135°	532.5	532.1	531.5	531.1	531.5	532.1	532.5	533.0	533.2	533.4	533.6
137.5°	567.6	566.9	566.3	565.7	566.3	566.9	567.6	568.2	568.6	568.6	568.8
140°	591.6	590.9	590.3	589.7	590.3	590.9	591.6	592.1	592.5	592.5	592.5
142.5°	613.2	612.6	612.1	611.4	612.1	612.6	613.2	613.9	614.1	614.0	613.9
145°	645.9	645.2	644.6	644.0	644.6	645.2	645.9	646.5	646.8	646.6	646.4
147.5°	674.9	674.3	673.8	673.2	673.8	674.3	674.9	675.6	675.6	675.3	674.9
150°	693.5	693.0	692.6	692.1	692.6	693.0	693.5	694.0	694.0	693.5	693.0
152.5°	711.8	711.1	710.5	710.0	710.5	711.1	711.8	712.3	712.3	711.8	711.1
155°	735.3	734.9	734.4	734.0	734.4	734.9	735.3	735.8	735.7	734.9	734.1
157.5°	756.8	756.1	755.3	754.6	755.3	756.1	756.8	757.5	757.4	756.3	755.3
160°	769.3	768.7	768.0	767.4	768.0	768.7	769.3	769.9	769.7	768.8	767.9
162.5°	780.8	780.1	779.3	778.6	779.3	780.1	780.8	781.5	781.4	780.3	779.3
165°	795.5	794.7	794.0	793.2	794.0	794.7	795.5	796.3	796.1	795.0	794.0
167.5°	807.6	806.8	806.0	805.2	806.0	806.8	807.6	808.4	808.2	807.2	806.1
170°	814.1	813.2	812.3	811.3	812.3	813.2	814.1	815.0	814.9	813.9	812.8
172.5°	819.1	818.1	817.3	816.4	817.3	818.1	819.1	820.0	819.9	818.9	817.8
175°	824.6	823.6	822.7	821.8	822.7	823.6	824.6	825.5	825.4	824.3	823.2
177.5°	826.5	825.7	825.0	824.3	825.0	825.7	826.5	827.2	827.2	826.5	825.7
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	560.6	562.8	566.2	568.2	571.4	573.5	574.7	576.8	577.9	582.0	586.2
5°	529.2	532.5	538.1	543.4	549.1	555.0	559.3	564.1	568.6	576.2	584.3
7.5°	493.4	497.8	506.7	515.1	525.0	533.2	540.6	548.8	556.2	567.3	578.8
10°	466.5	474.4	485.9	493.8	506.8	515.1	526.6	535.7	546.1	560.7	573.6
12.5°	443.3	452.8	462.1	473.1	484.7	498.6	511.2	523.0	535.2	550.3	565.5
15°	401.3	415.0	429.4	440.6	456.4	470.9	485.7	501.5	516.5	534.6	554.4
17.5°	347.1	363.1	387.3	406.4	424.9	439.5	457.9	477.0	494.6	516.4	538.5
20°	322.7	334.4	350.8	376.6	404.5	420.1	438.7	459.8	480.0	503.7	527.4
22.5°	303.1	313.5	326.6	346.7	377.9	399.2	418.7	440.1	463.5	487.7	514.0
25°	275.1	282.3	296.1	312.4	333.8	368.8	390.1	411.6	437.1	463.1	493.0
27.5°	254.0	260.6	269.6	285.0	301.0	326.2	360.0	383.4	408.8	438.0	469.1
30°	238.0	245.7	255.7	266.5	284.0	303.6	337.4	364.6	389.7	419.7	452.9
32.5°	226.3	232.4	240.9	252.0	266.4	285.3	312.4	345.3	369.8	401.4	436.0
35°	207.2	214.3	221.1	231.8	243.4	260.6	281.2	316.4	340.7	371.8	406.7
37.5°	191.5	195.8	203.4	211.8	224.2	237.0	254.8	286.3	312.6	343.2	378.9
40°	179.5	184.9	190.6	199.9	210.1	222.4	239.8	263.3	293.5	323.5	358.3
42.5°	167.8	174.7	180.7	187.0	198.0	210.4	224.6	244.5	275.4	303.7	337.6
45°	153.7	158.2	164.4	171.4	180.5	191.0	203.6	221.0	250.6	275.1	306.8
47.5°	137.4	143.9	148.0	154.7	163.4	173.4	185.1	200.2	224.1	247.1	276.6
50°	126.2	132.9	138.8	144.8	152.5	162.2	172.0	186.5	205.8	229.9	257.4
52.5°	116.6	122.5	128.2	134.3	141.9	150.7	160.0	172.8	189.2	211.4	238.2
55°	103.5	107.2	113.1	119.1	125.8	134.3	143.2	153.9	168.1	186.7	208.4
57.5°	90.1	94.3	98.9	105.0	111.8	118.3	126.4	136.1	147.2	164.1	182.6
60°	82.5	85.7	89.5	95.8	102.1	108.0	115.7	123.8	134.3	148.9	164.7
62.5°	74.0	77.1	80.6	86.1	92.2	97.6	104.3	112.9	121.8	135.1	148.9
65°	59.9	64.4	67.9	72.7	77.8	83.5	88.7	95.6	103.5	114.0	126.4
67.5°	49.7	52.0	55.2	59.6	64.7	69.6	74.6	80.0	86.9	95.0	104.8
70°	45.2	46.0	46.5	50.8	55.7	60.5	65.2	70.3	76.2	82.8	91.3
72.5°	39.9	40.7	41.4	43.2	47.1	52.0	56.8	60.5	66.1	71.7	78.6
75°	31.6	32.8	33.4	34.4	35.8	39.1	43.5	47.2	50.5	54.7	60.2
77.5°	24.1	24.8	25.4	26.5	27.4	28.8	31.4	34.6	37.7	40.1	43.9
80°	19.1	19.3	20.1	20.4	21.7	22.6	23.9	26.6	29.6	30.6	33.3
82.5°	14.4	14.5	15.2	15.6	16.1	17.0	18.5	19.3	21.7	23.0	24.6
85°	7.9	7.7	8.3	8.3	8.7	9.1	9.5	10.5	11.1	12.8	13.2
87.5°	7.2	7.3	6.8	6.2	5.4	5.1	4.7	4.5	4.5	4.5	4.8
90°	24.1	24.4	21.0	17.6	14.2	10.8	8.1	6.2	4.5	2.6	0.7
92.5°	22.2	22.2	21.4	20.5	19.7	18.9	17.8	16.5	15.2	13.7	12.4
95°	44.6	44.6	44.3	44.0	43.7	43.3	42.4	40.9	39.3	37.8	36.2
97.5°	75.0	75.0	74.4	73.8	73.2	72.7	71.7	70.3	68.9	67.6	66.3
100°	96.2	96.2	95.7	95.2	94.8	94.3	93.5	92.2	91.0	89.8	88.5
102.5°	119.1	119.0	118.4	117.9	117.3	116.7	115.9	114.9	114.0	112.9	111.9
105°	153.6	153.4	153.0	152.8	152.4	152.1	151.7	151.2	150.8	150.3	149.9
107.5°	191.3	191.1	191.1	191.1	191.1	191.1	190.7	190.1	189.4	188.8	188.1
110°	216.8	216.8	216.8	216.8	216.8	216.8	216.3	215.3	214.5	213.5	212.6



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	242.6	243.0	243.1	243.3	243.3	243.4	243.1	242.1	241.2	240.3	239.3
115°	281.4	281.6	281.9	282.2	282.5	282.9	282.5	281.6	280.6	279.7	278.8
117.5°	319.4	319.8	320.7	321.6	322.4	323.2	323.1	321.8	320.6	319.3	318.1
120°	344.3	344.3	345.5	346.8	348.0	349.3	349.3	348.0	346.8	345.5	344.3
122.5°	370.7	371.0	371.9	372.8	373.7	374.5	374.3	372.7	371.3	369.8	368.3
125°	409.4	409.8	410.3	410.7	411.3	411.7	411.3	409.8	408.4	407.1	405.6
127.5°	446.9	447.5	448.0	448.6	449.2	449.7	449.1	447.4	445.6	443.8	442.0
130°	472.3	472.6	472.9	473.1	473.5	473.8	473.0	470.9	469.0	466.9	464.9
132.5°	497.6	498.2	498.1	498.1	498.0	497.9	497.1	495.4	493.8	492.2	490.5
135°	533.8	533.9	533.6	533.2	533.0	532.6	531.6	529.9	528.2	526.6	524.9
137.5°	568.9	569.0	568.6	568.2	567.8	567.4	566.5	565.2	563.7	562.3	561.0
140°	592.5	592.5	591.7	590.9	590.1	589.3	588.3	586.8	585.5	584.1	582.7
142.5°	613.8	613.7	613.1	612.6	612.1	611.5	610.6	609.2	607.8	606.4	605.0
145°	646.3	646.1	645.2	644.3	643.4	642.4	641.4	640.3	639.3	638.1	637.0
147.5°	674.6	674.3	673.7	673.1	672.4	671.8	670.8	669.5	668.2	666.9	665.7
150°	692.6	692.1	691.5	690.9	690.3	689.6	688.8	688.0	687.0	686.1	685.2
152.5°	710.5	710.0	709.2	708.5	707.8	706.9	706.1	705.3	704.3	703.4	702.4
155°	733.3	732.5	732.1	731.6	731.1	730.7	730.2	729.8	729.3	728.8	728.3
157.5°	754.2	753.1	752.9	752.6	752.3	752.1	751.8	751.4	751.2	750.8	750.6
160°	767.0	766.0	765.9	765.7	765.5	765.4	765.2	764.8	764.6	764.2	763.9
162.5°	778.2	777.1	777.0	776.9	776.7	776.5	776.4	776.3	776.3	776.2	776.1
165°	792.9	791.8	791.8	791.8	791.8	791.8	791.8	792.0	792.2	792.4	792.5
167.5°	805.0	803.9	804.0	804.0	804.1	804.1	804.3	804.8	805.2	805.7	806.1
170°	811.7	810.6	810.7	810.9	811.1	811.2	811.5	812.0	812.4	813.0	813.4
172.5°	816.7	815.6	815.8	815.9	816.1	816.3	816.5	817.0	817.5	818.0	818.4
175°	822.2	821.1	821.4	821.7	822.0	822.3	822.7	823.1	823.6	824.1	824.6
177.5°	825.0	824.3	824.5	824.7	825.0	825.3	825.5	825.9	826.3	826.7	827.1
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	586.4	586.8	590.0	591.6	594.4	595.6	596.9	596.6	596.6	597.2	601.7
5°	587.6	591.7	597.7	603.6	609.3	614.1	617.4	620.6	621.9	627.7	632.9
7.5°	585.5	593.0	603.0	612.0	622.7	631.1	638.0	644.4	648.6	657.2	665.9
10°	582.7	593.3	604.6	616.2	631.0	642.1	653.4	662.2	664.9	677.7	685.0
12.5°	577.2	591.3	605.7	620.7	635.2	650.5	663.0	671.7	681.7	693.1	706.6
15°	569.0	585.1	604.0	623.2	643.9	662.5	675.9	691.1	702.0	714.6	726.4
17.5°	557.1	578.0	601.9	624.2	648.1	668.1	686.5	701.1	708.7	716.0	717.6
20°	547.7	570.2	598.3	624.6	648.5	671.6	689.9	702.0	704.1	704.3	693.6
22.5°	537.5	562.9	592.4	619.3	647.9	673.6	687.8	692.9	684.9	671.2	650.4
25°	518.7	548.1	582.4	613.1	644.4	668.6	673.5	664.4	636.2	606.6	569.2
27.5°	498.4	531.5	568.1	602.4	635.6	650.7	640.2	607.3	556.6	512.5	459.1
30°	483.5	520.6	556.6	594.9	625.7	632.1	608.1	559.6	500.5	434.1	380.8
32.5°	466.5	505.3	544.9	584.5	610.3	604.0	564.2	504.5	435.2	369.9	319.6
35°	442.2	482.2	525.0	564.7	581.1	553.8	494.2	416.6	345.7	284.8	250.1
37.5°	414.1	457.8	502.2	538.7	537.5	492.0	410.8	330.7	271.2	235.1	210.4
40°	394.1	438.4	486.3	517.1	504.0	444.6	356.7	281.2	237.6	208.8	190.8
42.5°	375.1	419.4	467.1	491.5	468.6	395.7	308.1	248.9	212.9	190.6	175.9
45°	342.5	389.3	433.5	447.0	406.1	325.7	249.1	206.2	182.3	165.7	155.6
47.5°	310.7	356.8	397.1	397.3	342.0	264.1	210.2	178.4	158.0	145.2	137.9
50°	291.2	335.0	368.8	363.6	300.8	235.0	188.0	160.6	143.7	133.7	126.0
52.5°	269.4	311.8	341.2	326.2	265.9	206.8	168.0	145.1	131.0	122.3	115.5
55°	237.6	275.3	296.0	273.2	217.0	172.0	142.0	123.9	113.4	106.1	100.2
57.5°	206.3	237.5	250.4	224.0	178.7	142.6	120.1	106.6	96.1	90.9	87.8
60°	186.7	213.3	222.4	193.2	155.3	124.8	106.4	93.8	86.1	82.7	79.6
62.5°	167.5	189.1	192.9	166.2	135.5	109.2	93.4	82.8	77.7	74.4	71.5
65°	138.9	154.5	152.8	131.3	107.2	86.7	75.2	68.7	64.8	60.2	55.1
67.5°	114.4	123.9	118.2	102.1	81.8	67.4	59.8	54.9	50.1	45.7	44.6
70°	98.8	104.3	98.3	83.5	67.1	56.5	50.5	44.6	41.7	40.8	38.9
72.5°	83.9	85.9	79.3	66.6	54.6	46.8	40.8	37.6	36.0	35.2	34.1
75°	63.0	61.6	55.9	46.0	37.9	32.6	30.8	29.6	28.5	27.7	27.1
77.5°	44.2	42.2	37.1	30.6	26.4	23.9	22.7	22.1	21.7	21.2	20.6
80°	33.3	31.8	26.8	21.8	20.1	18.8	18.2	17.4	17.4	17.0	16.4
82.5°	24.3	22.7	18.3	16.1	15.1	14.3	13.8	13.4	13.2	13.3	12.8
85°	12.8	10.3	9.1	8.7	8.1	7.7	7.9	7.5	7.5	7.5	7.3
87.5°	4.4	3.9	4.2	4.4	5.1	5.7	6.2	7.0	7.8	7.6	7.7
90°	2.6	4.5	6.2	8.1	10.8	14.2	17.6	21.0	24.4	24.1	23.8
92.5°	13.7	15.2	16.5	17.8	18.9	19.7	20.5	21.4	22.2	22.2	22.3
95°	37.8	39.3	40.9	42.4	43.3	43.7	44.0	44.3	44.6	44.6	44.6
97.5°	67.6	68.9	70.3	71.7	72.7	73.2	73.8	74.4	75.0	75.0	75.0
100°	89.8	91.0	92.2	93.5	94.3	94.8	95.2	95.7	96.2	96.2	96.2
102.5°	112.9	114.0	114.9	115.9	116.7	117.3	117.9	118.4	119.0	119.1	119.3
105°	150.3	150.8	151.2	151.7	152.1	152.4	152.8	153.0	153.4	153.6	154.0
107.5°	188.8	189.4	190.1	190.7	191.1	191.1	191.1	191.1	191.1	191.3	191.4
110°	213.5	214.5	215.3	216.3	216.8	216.8	216.8	216.8	216.8	216.8	216.8





TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	240.3	241.2	242.1	243.1	243.4	243.3	243.3	243.1	243.0	242.6	242.2
115°	279.7	280.6	281.6	282.5	282.9	282.5	282.2	281.9	281.6	281.4	281.2
117.5°	319.3	320.6	321.8	323.1	323.2	322.4	321.6	320.7	319.8	319.4	319.1
120°	345.5	346.8	348.0	349.3	349.3	348.0	346.8	345.5	344.3	344.3	344.3
122.5°	369.8	371.3	372.7	374.3	374.5	373.7	372.8	371.9	371.0	370.7	370.3
125°	407.1	408.4	409.8	411.3	411.7	411.3	410.7	410.3	409.8	409.4	408.9
127.5°	443.8	445.6	447.4	449.1	449.7	449.2	448.6	448.0	447.5	446.9	446.4
130°	466.9	469.0	470.9	473.0	473.8	473.5	473.1	472.9	472.6	472.3	472.0
132.5°	492.2	493.8	495.4	497.1	497.9	498.0	498.1	498.1	498.2	497.6	496.9
135°	526.6	528.2	529.9	531.6	532.6	533.0	533.2	533.6	533.9	533.8	533.6
137.5°	562.3	563.7	565.2	566.5	567.4	567.8	568.2	568.6	569.0	568.9	568.8
140°	584.1	585.5	586.8	588.3	589.3	590.1	590.9	591.7	592.5	592.5	592.5
142.5°	606.4	607.8	609.2	610.6	611.5	612.1	612.6	613.1	613.7	613.8	613.9
145°	638.1	639.3	640.3	641.4	642.4	643.4	644.3	645.2	646.1	646.3	646.4
147.5°	666.9	668.2	669.5	670.8	671.8	672.4	673.1	673.7	674.3	674.6	674.9
150°	686.1	687.0	688.0	688.8	689.6	690.3	690.9	691.5	692.1	692.6	693.0
152.5°	703.4	704.3	705.3	706.1	706.9	707.8	708.5	709.2	710.0	710.5	711.1
155°	728.8	729.3	729.8	730.2	730.7	731.1	731.6	732.1	732.5	733.3	734.1
157.5°	750.8	751.2	751.4	751.8	752.1	752.3	752.6	752.9	753.1	754.2	755.3
160°	764.2	764.6	764.8	765.2	765.4	765.5	765.7	765.9	766.0	767.0	767.9
162.5°	776.2	776.3	776.3	776.4	776.5	776.7	776.9	777.0	777.1	778.2	779.3
165°	792.4	792.2	792.0	791.8	791.8	791.8	791.8	791.8	791.8	792.9	794.0
167.5°	805.7	805.2	804.8	804.3	804.1	804.1	804.0	804.0	803.9	805.0	806.1
170°	813.0	812.4	812.0	811.5	811.2	811.1	810.9	810.7	810.6	811.7	812.8
172.5°	818.0	817.5	817.0	816.5	816.3	816.1	815.9	815.8	815.6	816.7	817.8
175°	824.1	823.6	823.1	822.7	822.3	822.0	821.7	821.4	821.1	822.2	823.2
177.5°	826.7	826.3	825.9	825.5	825.3	825.0	824.7	824.5	824.3	825.0	825.7
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9	825.9



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	603.3	605.5	606.5	606.5	607.6	607.1	606.6
5°	638.0	641.9	642.7	646.3	649.0	648.2	648.5
7.5°	672.5	678.7	684.8	687.6	688.0	689.6	690.3
10°	693.8	698.8	708.3	706.9	714.0	718.1	711.4
12.5°	714.2	721.0	727.6	729.4	733.4	734.8	732.1
15°	732.6	736.3	736.6	735.7	736.9	735.8	732.0
17.5°	715.4	709.4	697.5	691.8	687.3	680.6	678.0
20°	686.9	669.4	649.2	641.1	631.6	613.0	617.4
22.5°	625.3	605.5	585.1	561.5	550.2	532.5	531.5
25°	529.5	495.3	457.5	431.2	415.8	398.2	390.5
27.5°	411.7	368.5	337.7	322.1	307.8	293.9	293.3
30°	334.2	301.8	277.9	264.6	255.8	249.9	251.2
32.5°	281.7	259.5	243.3	232.3	225.9	221.4	221.3
35°	230.3	215.1	204.7	200.1	195.5	192.3	192.4
37.5°	197.1	188.0	182.2	177.1	174.2	172.5	171.7
40°	180.0	172.5	168.1	165.1	162.6	160.4	160.0
42.5°	166.7	160.4	156.0	153.6	151.3	149.7	149.4
45°	147.8	142.8	138.8	136.1	135.1	133.7	133.7
47.5°	131.5	126.5	123.4	121.7	120.0	119.0	119.0
50°	120.6	116.6	113.9	112.8	111.4	110.8	110.6
52.5°	110.7	107.7	105.8	105.0	104.4	103.7	103.8
55°	97.2	95.6	94.8	94.2	93.2	91.9	92.7
57.5°	86.0	84.5	82.4	80.4	79.5	78.6	79.0
60°	78.0	75.2	72.3	70.1	69.5	67.7	67.7
62.5°	67.9	63.9	60.5	59.2	58.6	57.8	57.6
65°	52.3	50.6	49.8	49.0	48.6	48.6	48.2
67.5°	43.3	42.6	41.7	41.6	41.2	41.0	40.9
70°	38.3	37.5	37.1	36.8	36.5	36.6	36.0
72.5°	33.4	32.8	32.7	32.2	31.9	31.9	31.5
75°	26.3	26.3	26.1	25.9	25.5	25.3	25.5
77.5°	20.2	20.3	20.0	19.9	19.9	19.9	19.7
80°	16.2	16.4	16.2	16.0	15.8	16.0	15.8
82.5°	12.8	12.5	12.5	12.4	12.4	12.3	12.2
85°	7.3	7.5	7.3	7.1	7.1	7.1	7.3
87.5°	7.5	7.4	7.4	7.4	7.4	7.5	7.3
90°	23.5	23.2	23.1	23.3	23.4	23.5	23.7
92.5°	22.4	22.4	22.5	22.5	22.6	22.6	22.6
95°	44.6	44.6	44.5	44.1	43.9	43.5	43.2
97.5°	75.0	75.0	75.0	75.0	74.9	74.9	74.8
100°	96.2	96.2	96.1	95.9	95.8	95.7	95.5
102.5°	119.4	119.6	119.5	119.4	119.2	119.0	118.9
105°	154.3	154.6	154.7	154.7	154.7	154.7	154.7
107.5°	191.5	191.6	191.4	190.6	189.9	189.2	188.5
110°	216.8	216.8	216.5	216.1	215.6	215.2	214.6



TEST NUMBER: P331628-940

CATALOG NUMBER: S122RDIP-S290D725U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	241.8	241.5	241.1	240.8	240.4	240.1	239.8
115°	281.2	281.0	280.6	280.2	279.7	279.3	278.8
117.5°	318.7	318.3	317.9	317.4	316.9	316.5	316.0
120°	344.3	344.3	344.1	343.6	343.1	342.7	342.2
122.5°	370.0	369.6	369.3	368.9	368.5	368.2	367.9
125°	408.4	408.0	407.7	407.5	407.3	407.2	407.1
127.5°	445.8	445.2	444.7	444.3	443.7	443.3	442.7
130°	471.6	471.4	470.8	470.2	469.7	469.0	468.4
132.5°	496.1	495.5	494.9	494.4	493.9	493.4	492.9
135°	533.4	533.2	533.0	532.5	532.1	531.5	531.1
137.5°	568.6	568.6	568.2	567.6	566.9	566.3	565.7
140°	592.5	592.5	592.1	591.6	590.9	590.3	589.7
142.5°	614.0	614.1	613.9	613.2	612.6	612.1	611.4
145°	646.6	646.8	646.5	645.9	645.2	644.6	644.0
147.5°	675.3	675.6	675.6	674.9	674.3	673.8	673.2
150°	693.5	694.0	694.0	693.5	693.0	692.6	692.1
152.5°	711.8	712.3	712.3	711.8	711.1	710.5	710.0
155°	734.9	735.7	735.8	735.3	734.9	734.4	734.0
157.5°	756.3	757.4	757.5	756.8	756.1	755.3	754.6
160°	768.8	769.7	769.9	769.3	768.7	768.0	767.4
162.5°	780.3	781.4	781.5	780.8	780.1	779.3	778.6
165°	795.0	796.1	796.3	795.5	794.7	794.0	793.2
167.5°	807.2	808.2	808.4	807.6	806.8	806.0	805.2
170°	813.9	814.9	815.0	814.1	813.2	812.3	811.3
172.5°	818.9	819.9	820.0	819.1	818.1	817.3	816.4
175°	824.3	825.4	825.5	824.6	823.6	822.7	821.8
177.5°	826.5	827.2	827.2	826.5	825.7	825.0	824.3
180°	825.9	825.9	825.9	825.9	825.9	825.9	825.9

(END OF REPORT)