

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331634-940

Luminaire Tested: **S122RDIP-S290D925U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331634-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S290D925U940-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3960.3 lumens  
Efficiency: N/A  
Efficacy: 106.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26				
1	93	89	85	82	82	79	76	74	61	60	58	45	44	43	30	30	29	22				
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25	19				
3	77	69	62	57	69	62	56	51	48	44	41	36	33	31	24	23	22	17				
4	71	61	54	48	63	55	49	44	43	39	35	32	29	27	22	21	19	15				
5	65	54	47	41	58	49	43	38	39	34	31	29	26	24	20	18	17	13				
6	60	49	41	36	54	44	38	33	35	30	27	26	23	21	18	17	15	12				
7	56	44	37	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11				
8	52	40	33	28	46	36	30	26	29	24	21	22	19	17	16	14	12	10				
9	48	37	30	25	43	33	27	23	27	22	19	20	17	15	15	13	11	9				
10	45	33	27	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9411	9411	9411	9411
5°	10511	9470	8399	9470
10°	11663	9404	7279	9404
15°	12236	9267	5735	9267
20°	10608	9062	4962	9062
25°	6957	8783	4431	8783
30°	4683	8444	4010	8444
35°	3792	8016	3617	8016
40°	3372	7552	3347	7552
45°	3053	7005	2987	7005
50°	2778	6465	2768	6465
55°	2609	5866	2578	5866
60°	2186	5318	2160	5318
65°	1841	4829	2090	4829
70°	1699	4310	1969	4310
75°	1591	3755	1822	3755
80°	1469	3096	1618	3096
85°	1352	2445	1426	2445



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.3	1.4
10°-20°	154.0	3.9
20°-30°	198.4	5.0
30°-40°	188.6	4.8
40°-50°	161.5	4.1
50°-60°	123.0	3.1
60°-70°	77.8	2.0
70°-80°	38.8	1.0
80°-90°	14.3	0.4
90°-100°	66.8	1.7
100°-110°	207.5	5.2
110°-120°	354.7	9.0
120°-130°	466.5	11.8
130°-140°	523.6	13.2
140°-150°	513.4	13.0
150°-160°	430.6	10.9
160°-170°	285.6	7.2
170°-180°	99.8	2.5
0°-30°	407.7	10.3
0°-40°	596.2	15.1
0°-60°	880.8	22.2
0°-90°	1011.7	25.5
90°-120°	629.1	15.9
90°-150°	2132.6	53.8
90°-180°	2949.0	74.5
0°-180°	3960.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	583	583	583	583	583	
5°	648	584	518	584	648	64
15°	732	554	343	554	732	197
25°	390	493	249	493	390	185
35°	192	407	184	407	192	123
45°	134	307	131	307	134	103
55°	93	208	92	208	93	81
65°	48	126	55	126	48	49
75°	26	60	29	60	26	27
85°	7	13	8	13	7	9
90°	30	1	30	1	30	13
95°	55	46	55	46	55	62
105°	198	191	198	191	198	208
115°	356	356	356	356	356	352
125°	520	518	520	518	520	463
135°	678	670	678	670	678	522
145°	822	813	822	813	822	513
155°	937	930	937	930	937	431
165°	1013	1012	1013	1012	1013	286
175°	1049	1053	1049	1053	1049	100
180°	1054	1054	1054	1054	1054	



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	606.6	607.1	607.6	606.5	606.5	605.5	603.3	601.7	597.2	596.6	596.6
5°	648.5	648.2	649.0	646.3	642.7	641.9	638.0	632.9	627.7	621.9	620.6
7.5°	690.3	689.6	688.0	687.6	684.8	678.7	672.5	665.9	657.2	648.6	644.4
10°	711.4	718.1	714.0	706.9	708.3	698.8	693.8	685.0	677.7	664.9	662.2
12.5°	732.1	734.8	733.4	729.4	727.6	721.0	714.2	706.6	693.1	681.7	671.7
15°	732.0	735.8	736.9	735.7	736.6	736.3	732.6	726.4	714.6	702.0	691.1
17.5°	678.0	680.6	687.3	691.8	697.5	709.4	715.4	717.6	716.0	708.7	701.1
20°	617.4	613.0	631.6	641.1	649.2	669.4	686.9	693.6	704.3	704.1	702.0
22.5°	531.5	532.5	550.2	561.5	585.1	605.5	625.3	650.4	671.2	684.9	692.9
25°	390.5	398.2	415.8	431.2	457.5	495.3	529.5	569.2	606.6	636.2	664.4
27.5°	293.3	293.9	307.8	322.1	337.7	368.5	411.7	459.1	512.5	556.6	607.3
30°	251.2	249.9	255.8	264.6	277.9	301.8	334.2	380.8	434.1	500.5	559.6
32.5°	221.3	221.4	225.9	232.3	243.3	259.5	281.7	319.6	369.9	435.2	504.5
35°	192.4	192.3	195.5	200.1	204.7	215.1	230.3	250.1	284.8	345.7	416.6
37.5°	171.7	172.5	174.2	177.1	182.2	188.0	197.1	210.4	235.1	271.2	330.7
40°	160.0	160.4	162.6	165.1	168.1	172.5	180.0	190.8	208.8	237.6	281.2
42.5°	149.4	149.7	151.3	153.6	156.0	160.4	166.7	175.9	190.6	212.9	248.9
45°	133.7	133.7	135.1	136.1	138.8	142.8	147.8	155.6	165.7	182.3	206.2
47.5°	119.0	119.0	120.0	121.7	123.4	126.5	131.5	137.9	145.2	158.0	178.4
50°	110.6	110.8	111.4	112.8	113.9	116.6	120.6	126.0	133.7	143.7	160.6
52.5°	103.8	103.7	104.4	105.0	105.8	107.7	110.7	115.5	122.3	131.0	145.1
55°	92.7	91.9	93.2	94.2	94.8	95.6	97.2	100.2	106.1	113.4	123.9
57.5°	79.0	78.6	79.5	80.4	82.4	84.5	86.0	87.8	90.9	96.1	106.6
60°	67.7	67.7	69.5	70.1	72.3	75.2	78.0	79.6	82.7	86.1	93.8
62.5°	57.6	57.8	58.6	59.2	60.5	63.9	67.9	71.5	74.4	77.7	82.8
65°	48.2	48.6	48.6	49.0	49.8	50.6	52.3	55.1	60.2	64.8	68.7
67.5°	40.9	41.0	41.2	41.6	41.7	42.6	43.3	44.6	45.7	50.1	54.9
70°	36.0	36.6	36.5	36.8	37.1	37.5	38.3	38.9	40.8	41.7	44.6
72.5°	31.5	31.9	31.9	32.2	32.7	32.8	33.4	34.1	35.2	36.0	37.6
75°	25.5	25.3	25.5	25.9	26.1	26.3	26.3	27.1	27.7	28.5	29.6
77.5°	19.7	19.9	19.9	19.9	20.0	20.3	20.2	20.6	21.2	21.7	22.1
80°	15.8	16.0	15.8	16.0	16.2	16.4	16.2	16.4	17.0	17.4	17.4
82.5°	12.2	12.3	12.4	12.4	12.5	12.5	12.8	12.8	13.3	13.2	13.4
85°	7.3	7.1	7.1	7.1	7.3	7.5	7.3	7.3	7.5	7.5	7.5
87.5°	8.6	8.7	8.7	8.6	8.6	8.6	8.7	9.0	8.9	9.2	8.1
90°	30.2	30.1	29.9	29.7	29.4	29.6	30.0	30.3	30.8	31.1	26.8
92.5°	28.8	28.8	28.7	28.7	28.7	28.6	28.5	28.4	28.4	28.3	27.3
95°	55.2	55.6	56.0	56.4	56.7	57.0	57.0	57.0	57.0	57.0	56.5
97.5°	95.6	95.6	95.7	95.7	95.8	95.8	95.8	95.8	95.8	95.8	95.0
100°	121.9	122.1	122.3	122.5	122.7	122.8	122.8	122.8	122.8	122.8	122.3
102.5°	151.9	152.0	152.2	152.4	152.6	152.7	152.5	152.3	152.1	152.0	151.2
105°	197.5	197.5	197.5	197.5	197.5	197.3	197.0	196.5	196.2	195.7	195.4
107.5°	240.6	241.6	242.5	243.3	244.2	244.6	244.5	244.3	244.2	244.0	244.0
110°	274.1	274.6	275.3	275.9	276.4	276.8	276.8	276.8	276.8	276.8	276.8



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	306.1	306.6	307.0	307.5	307.8	308.4	308.8	309.2	309.8	310.2	310.4
115°	356.0	356.5	357.1	357.8	358.3	358.7	358.9	359.1	359.4	359.5	359.9
117.5°	403.5	404.0	404.7	405.3	405.8	406.4	406.9	407.3	407.8	408.3	409.4
120°	436.9	437.6	438.1	438.7	439.3	439.6	439.6	439.6	439.6	439.6	441.2
122.5°	469.7	470.1	470.6	471.0	471.4	471.9	472.3	472.8	473.3	473.8	474.9
125°	519.7	519.9	520.0	520.3	520.5	520.8	521.5	522.1	522.6	523.3	523.9
127.5°	565.3	565.9	566.5	567.1	567.8	568.5	569.2	569.9	570.6	571.3	572.0
130°	598.0	598.8	599.6	600.4	601.2	601.7	602.2	602.5	603.0	603.3	603.8
132.5°	629.4	630.0	630.6	631.2	631.9	632.6	633.5	634.4	635.3	636.1	636.0
135°	678.1	678.7	679.3	679.8	680.5	680.8	681.1	681.3	681.4	681.6	681.3
137.5°	722.2	723.0	723.8	724.6	725.4	725.9	726.0	726.2	726.4	726.5	726.0
140°	752.9	753.7	754.4	755.2	756.0	756.4	756.4	756.4	756.4	756.4	755.5
142.5°	780.6	781.4	782.2	783.0	783.8	784.1	783.9	783.8	783.6	783.5	782.7
145°	822.2	823.0	823.9	824.7	825.5	825.7	825.5	825.3	825.1	824.9	823.8
147.5°	859.4	860.2	860.9	861.7	862.5	862.6	862.2	861.7	861.3	860.9	860.1
150°	883.7	884.2	884.8	885.5	886.0	886.0	885.5	884.8	884.2	883.7	882.9
152.5°	906.4	907.2	907.9	908.7	909.5	909.5	908.7	907.9	907.2	906.4	905.4
155°	937.0	937.6	938.3	938.8	939.4	939.2	938.3	937.3	936.3	935.2	934.7
157.5°	963.4	964.3	965.3	966.3	967.1	967.0	965.6	964.3	963.0	961.6	961.3
160°	979.7	980.5	981.3	982.1	982.9	982.8	981.5	980.3	979.2	977.9	977.8
162.5°	994.0	995.0	995.9	996.8	997.8	997.6	996.2	994.9	993.5	992.2	992.0
165°	1012.7	1013.7	1014.7	1015.7	1016.6	1016.5	1015.0	1013.7	1012.3	1010.9	1010.9
167.5°	1028.0	1029.0	1030.0	1031.1	1032.1	1031.9	1030.6	1029.1	1027.8	1026.4	1026.4
170°	1035.8	1037.0	1038.2	1039.4	1040.5	1040.4	1039.1	1037.7	1036.3	1034.9	1035.1
172.5°	1042.2	1043.4	1044.6	1045.8	1047.0	1046.9	1045.5	1044.1	1042.8	1041.3	1041.5
175°	1049.2	1050.3	1051.5	1052.8	1053.9	1053.8	1052.4	1051.1	1049.6	1048.3	1048.7
177.5°	1052.4	1053.3	1054.3	1055.3	1056.1	1056.1	1055.3	1054.3	1053.3	1052.4	1052.7
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	596.9	595.6	594.4	591.6	590.0	586.8	586.4	586.2	582.0	577.9	576.8
5°	617.4	614.1	609.3	603.6	597.7	591.7	587.6	584.3	576.2	568.6	564.1
7.5°	638.0	631.1	622.7	612.0	603.0	593.0	585.5	578.8	567.3	556.2	548.8
10°	653.4	642.1	631.0	616.2	604.6	593.3	582.7	573.6	560.7	546.1	535.7
12.5°	663.0	650.5	635.2	620.7	605.7	591.3	577.2	565.5	550.3	535.2	523.0
15°	675.9	662.5	643.9	623.2	604.0	585.1	569.0	554.4	534.6	516.5	501.5
17.5°	686.5	668.1	648.1	624.2	601.9	578.0	557.1	538.5	516.4	494.6	477.0
20°	689.9	671.6	648.5	624.6	598.3	570.2	547.7	527.4	503.7	480.0	459.8
22.5°	687.8	673.6	647.9	619.3	592.4	562.9	537.5	514.0	487.7	463.5	440.1
25°	673.5	668.6	644.4	613.1	582.4	548.1	518.7	493.0	463.1	437.1	411.6
27.5°	640.2	650.7	635.6	602.4	568.1	531.5	498.4	469.1	438.0	408.8	383.4
30°	608.1	632.1	625.7	594.9	556.6	520.6	483.5	452.9	419.7	389.7	364.6
32.5°	564.2	604.0	610.3	584.5	544.9	505.3	466.5	436.0	401.4	369.8	345.3
35°	494.2	553.8	581.1	564.7	525.0	482.2	442.2	406.7	371.8	340.7	316.4
37.5°	410.8	492.0	537.5	538.7	502.2	457.8	414.1	378.9	343.2	312.6	286.3
40°	356.7	444.6	504.0	517.1	486.3	438.4	394.1	358.3	323.5	293.5	263.3
42.5°	308.1	395.7	468.6	491.5	467.1	419.4	375.1	337.6	303.7	275.4	244.5
45°	249.1	325.7	406.1	447.0	433.5	389.3	342.5	306.8	275.1	250.6	221.0
47.5°	210.2	264.1	342.0	397.3	397.1	356.8	310.7	276.6	247.1	224.1	200.2
50°	188.0	235.0	300.8	363.6	368.8	335.0	291.2	257.4	229.9	205.8	186.5
52.5°	168.0	206.8	265.9	326.2	341.2	311.8	269.4	238.2	211.4	189.2	172.8
55°	142.0	172.0	217.0	273.2	296.0	275.3	237.6	208.4	186.7	168.1	153.9
57.5°	120.1	142.6	178.7	224.0	250.4	237.5	206.3	182.6	164.1	147.2	136.1
60°	106.4	124.8	155.3	193.2	222.4	213.3	186.7	164.7	148.9	134.3	123.8
62.5°	93.4	109.2	135.5	166.2	192.9	189.1	167.5	148.9	135.1	121.8	112.9
65°	75.2	86.7	107.2	131.3	152.8	154.5	138.9	126.4	114.0	103.5	95.6
67.5°	59.8	67.4	81.8	102.1	118.2	123.9	114.4	104.8	95.0	86.9	80.0
70°	50.5	56.5	67.1	83.5	98.3	104.3	98.8	91.3	82.8	76.2	70.3
72.5°	40.8	46.8	54.6	66.6	79.3	85.9	83.9	78.6	71.7	66.1	60.5
75°	30.8	32.6	37.9	46.0	55.9	61.6	63.0	60.2	54.7	50.5	47.2
77.5°	22.7	23.9	26.4	30.6	37.1	42.2	44.2	43.9	40.1	37.7	34.6
80°	18.2	18.8	20.1	21.8	26.8	31.8	33.3	33.3	30.6	29.6	26.6
82.5°	13.8	14.3	15.1	16.1	18.3	22.7	24.3	24.6	23.0	21.7	19.3
85°	7.9	7.7	8.1	8.7	9.1	10.3	12.8	13.2	12.8	11.1	10.5
87.5°	7.2	6.5	5.7	4.8	4.5	4.2	4.5	4.9	4.7	4.7	4.8
90°	22.5	18.1	13.7	10.3	8.0	5.6	3.3	0.9	3.3	5.6	8.0
92.5°	26.2	25.2	24.2	22.8	21.0	19.4	17.6	15.9	17.6	19.4	21.0
95°	56.2	55.7	55.4	54.2	52.2	50.2	48.2	46.3	48.2	50.2	52.2
97.5°	94.3	93.5	92.7	91.5	89.8	88.0	86.3	84.5	86.3	88.0	89.8
100°	121.6	121.0	120.5	119.3	117.8	116.2	114.6	113.0	114.6	116.2	117.8
102.5°	150.5	149.7	149.0	147.9	146.7	145.4	144.2	142.9	144.2	145.4	146.7
105°	195.0	194.6	194.2	193.7	193.1	192.5	191.9	191.4	191.9	192.5	193.1
107.5°	244.0	244.0	244.0	243.6	242.7	241.8	240.9	240.0	240.9	241.8	242.7
110°	276.8	276.8	276.8	276.2	275.0	273.8	272.6	271.4	272.6	273.8	275.0





TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	310.5	310.7	310.9	310.3	309.2	308.0	306.7	305.6	306.7	308.0	309.2
115°	360.3	360.7	361.1	360.7	359.5	358.3	357.1	356.0	357.1	358.3	359.5
117.5°	410.5	411.6	412.7	412.5	410.9	409.3	407.7	406.2	407.7	409.3	410.9
120°	442.7	444.3	445.9	445.9	444.3	442.7	441.2	439.6	441.2	442.7	444.3
122.5°	476.0	477.1	478.2	477.8	475.9	474.0	472.1	470.2	472.1	474.0	475.9
125°	524.4	525.0	525.7	525.0	523.3	521.5	519.7	517.9	519.7	521.5	523.3
127.5°	572.7	573.5	574.2	573.4	571.1	568.9	566.6	564.4	566.6	568.9	571.1
130°	604.1	604.5	604.9	603.9	601.3	598.7	596.1	593.5	596.1	598.7	601.3
132.5°	636.0	635.9	635.8	634.7	632.6	630.5	628.4	626.3	628.4	630.5	632.6
135°	680.8	680.5	680.1	678.8	676.6	674.4	672.3	670.1	672.3	674.4	676.6
137.5°	725.5	725.0	724.4	723.3	721.5	719.7	717.9	716.2	717.9	719.7	721.5
140°	754.4	753.4	752.4	751.1	749.3	747.5	745.7	744.0	745.7	747.5	749.3
142.5°	782.1	781.4	780.8	779.5	777.8	776.0	774.2	772.4	774.2	776.0	777.8
145°	822.5	821.4	820.2	818.9	817.5	816.1	814.8	813.3	814.8	816.1	817.5
147.5°	859.3	858.5	857.7	856.5	854.8	853.2	851.5	849.8	851.5	853.2	854.8
150°	882.1	881.3	880.5	879.5	878.3	877.1	875.9	874.8	875.9	877.1	878.3
152.5°	904.6	903.6	902.7	901.6	900.4	899.2	898.0	896.8	898.0	899.2	900.4
155°	934.1	933.5	932.9	932.3	931.7	931.1	930.5	930.0	930.5	931.1	931.7
157.5°	960.9	960.6	960.2	959.8	959.4	959.0	958.6	958.2	958.6	959.0	959.4
160°	977.6	977.4	977.2	976.9	976.5	976.1	975.7	975.4	975.7	976.1	976.5
162.5°	991.8	991.7	991.4	991.3	991.2	991.1	991.0	991.0	991.0	991.1	991.2
165°	1010.9	1010.9	1010.9	1011.0	1011.2	1011.4	1011.6	1011.8	1011.6	1011.4	1011.2
167.5°	1026.4	1026.5	1026.5	1026.9	1027.4	1028.1	1028.7	1029.2	1028.7	1028.1	1027.4
170°	1035.4	1035.5	1035.7	1036.1	1036.7	1037.3	1037.9	1038.5	1037.9	1037.3	1036.7
172.5°	1041.7	1042.0	1042.1	1042.5	1043.1	1043.7	1044.3	1044.9	1044.3	1043.7	1043.1
175°	1049.1	1049.5	1049.9	1050.3	1051.0	1051.5	1052.1	1052.8	1052.1	1051.5	1051.0
177.5°	1053.0	1053.3	1053.6	1054.0	1054.5	1055.0	1055.4	1056.0	1055.4	1055.0	1054.5
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	574.7	573.5	571.4	568.2	566.2	562.8	560.6	561.9	562.2	561.9	561.6
5°	559.3	555.0	549.1	543.4	538.1	532.5	529.2	527.9	525.0	523.4	522.5
7.5°	540.6	533.2	525.0	515.1	506.7	497.8	493.4	491.2	485.4	482.2	479.5
10°	526.6	515.1	506.8	493.8	485.9	474.4	466.5	466.7	458.8	454.3	451.1
12.5°	511.2	498.6	484.7	473.1	462.1	452.8	443.3	439.4	431.1	426.8	418.0
15°	485.7	470.9	456.4	440.6	429.4	415.0	401.3	384.4	370.9	359.1	355.9
17.5°	457.9	439.5	424.9	406.4	387.3	363.1	347.1	337.3	329.2	323.0	318.3
20°	438.7	420.1	404.5	376.6	350.8	334.4	322.7	315.1	306.7	300.0	296.3
22.5°	418.7	399.2	377.9	346.7	326.6	313.5	303.1	294.4	288.6	283.5	280.1
25°	390.1	368.8	333.8	312.4	296.1	282.3	275.1	269.8	263.8	256.6	253.4
27.5°	360.0	326.2	301.0	285.0	269.6	260.6	254.0	246.2	240.8	237.6	234.2
30°	337.4	303.6	284.0	266.5	255.7	245.7	238.0	233.5	228.3	222.8	220.6
32.5°	312.4	285.3	266.4	252.0	240.9	232.4	226.3	219.1	215.3	212.0	207.3
35°	281.2	260.6	243.4	231.8	221.1	214.3	207.2	203.0	196.1	193.2	191.5
37.5°	254.8	237.0	224.2	211.8	203.4	195.8	191.5	184.7	181.7	177.7	173.9
40°	239.8	222.4	210.1	199.9	190.6	184.9	179.5	174.0	169.5	167.7	163.1
42.5°	224.6	210.4	198.0	187.0	180.7	174.7	167.8	163.8	159.2	156.2	153.4
45°	203.6	191.0	180.5	171.4	164.4	158.2	153.7	147.0	144.5	138.6	136.1
47.5°	185.1	173.4	163.4	154.7	148.0	143.9	137.4	132.2	128.0	124.3	121.2
50°	172.0	162.2	152.5	144.8	138.8	132.9	126.2	123.6	117.1	115.2	113.4
52.5°	160.0	150.7	141.9	134.3	128.2	122.5	116.6	113.2	108.8	107.0	105.7
55°	143.2	134.3	125.8	119.1	113.1	107.2	103.5	99.2	97.2	95.8	94.2
57.5°	126.4	118.3	111.8	105.0	98.9	94.3	90.1	87.5	85.4	83.6	81.6
60°	115.7	108.0	102.1	95.8	89.5	85.7	82.5	79.4	77.0	74.1	73.3
62.5°	104.3	97.6	92.2	86.1	80.6	77.1	74.0	71.2	68.2	64.1	63.0
65°	88.7	83.5	77.8	72.7	67.9	64.4	59.9	56.7	55.5	55.1	54.9
67.5°	74.6	69.6	64.7	59.6	55.2	52.0	49.7	49.2	48.3	48.2	47.5
70°	65.2	60.5	55.7	50.8	46.5	46.0	45.2	44.3	43.3	43.0	42.5
72.5°	56.8	52.0	47.1	43.2	41.4	40.7	39.9	39.0	38.3	37.9	37.7
75°	43.5	39.1	35.8	34.4	33.4	32.8	31.6	31.0	30.6	30.0	29.8
77.5°	31.4	28.8	27.4	26.5	25.4	24.8	24.1	23.5	23.0	22.9	22.6
80°	23.9	22.6	21.7	20.4	20.1	19.3	19.1	18.5	18.6	18.0	18.0
82.5°	18.5	17.0	16.1	15.6	15.2	14.5	14.4	14.1	14.1	13.6	13.6
85°	9.5	9.1	8.7	8.3	8.3	7.7	7.9	7.7	7.7	7.3	7.1
87.5°	5.2	5.7	6.2	7.0	7.9	8.6	8.6	8.4	8.3	8.2	8.0
90°	10.3	13.7	18.1	22.5	26.8	31.1	30.8	30.3	30.0	29.6	29.4
92.5°	22.8	24.2	25.2	26.2	27.3	28.3	28.4	28.4	28.5	28.6	28.7
95°	54.2	55.4	55.7	56.2	56.5	57.0	57.0	57.0	57.0	57.0	56.7
97.5°	91.5	92.7	93.5	94.3	95.0	95.8	95.8	95.8	95.8	95.8	95.8
100°	119.3	120.5	121.0	121.6	122.3	122.8	122.8	122.8	122.8	122.8	122.7
102.5°	147.9	149.0	149.7	150.5	151.2	152.0	152.1	152.3	152.5	152.7	152.6
105°	193.7	194.2	194.6	195.0	195.4	195.7	196.2	196.5	197.0	197.3	197.5
107.5°	243.6	244.0	244.0	244.0	244.0	244.0	244.2	244.3	244.5	244.6	244.2
110°	276.2	276.8	276.8	276.8	276.8	276.8	276.8	276.8	276.8	276.8	276.4



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	310.3	310.9	310.7	310.5	310.4	310.2	309.8	309.2	308.8	308.4	307.8
115°	360.7	361.1	360.7	360.3	359.9	359.5	359.4	359.1	358.9	358.7	358.3
117.5°	412.5	412.7	411.6	410.5	409.4	408.3	407.8	407.3	406.9	406.4	405.8
120°	445.9	445.9	444.3	442.7	441.2	439.6	439.6	439.6	439.6	439.6	439.3
122.5°	477.8	478.2	477.1	476.0	474.9	473.8	473.3	472.8	472.3	471.9	471.4
125°	525.0	525.7	525.0	524.4	523.9	523.3	522.6	522.1	521.5	520.8	520.5
127.5°	573.4	574.2	573.5	572.7	572.0	571.3	570.6	569.9	569.2	568.5	567.8
130°	603.9	604.9	604.5	604.1	603.8	603.3	603.0	602.5	602.2	601.7	601.2
132.5°	634.7	635.8	635.9	636.0	636.0	636.1	635.3	634.4	633.5	632.6	631.9
135°	678.8	680.1	680.5	680.8	681.3	681.6	681.4	681.3	681.1	680.8	680.5
137.5°	723.3	724.4	725.0	725.5	726.0	726.5	726.4	726.2	726.0	725.9	725.4
140°	751.1	752.4	753.4	754.4	755.5	756.4	756.4	756.4	756.4	756.4	756.0
142.5°	779.5	780.8	781.4	782.1	782.7	783.5	783.6	783.8	783.9	784.1	783.8
145°	818.9	820.2	821.4	822.5	823.8	824.9	825.1	825.3	825.5	825.7	825.5
147.5°	856.5	857.7	858.5	859.3	860.1	860.9	861.3	861.7	862.2	862.6	862.5
150°	879.5	880.5	881.3	882.1	882.9	883.7	884.2	884.8	885.5	886.0	886.0
152.5°	901.6	902.7	903.6	904.6	905.4	906.4	907.2	907.9	908.7	909.5	909.5
155°	932.3	932.9	933.5	934.1	934.7	935.2	936.3	937.3	938.3	939.2	939.4
157.5°	959.8	960.2	960.6	960.9	961.3	961.6	963.0	964.3	965.6	967.0	967.1
160°	976.9	977.2	977.4	977.6	977.8	977.9	979.2	980.3	981.5	982.8	982.9
162.5°	991.3	991.4	991.7	991.8	992.0	992.2	993.5	994.9	996.2	997.6	997.8
165°	1011.0	1010.9	1010.9	1010.9	1010.9	1010.9	1012.3	1013.7	1015.0	1016.5	1016.6
167.5°	1026.9	1026.5	1026.5	1026.4	1026.4	1026.4	1027.8	1029.1	1030.6	1031.9	1032.1
170°	1036.1	1035.7	1035.5	1035.4	1035.1	1034.9	1036.3	1037.7	1039.1	1040.4	1040.5
172.5°	1042.5	1042.1	1042.0	1041.7	1041.5	1041.3	1042.8	1044.1	1045.5	1046.9	1047.0
175°	1050.3	1049.9	1049.5	1049.1	1048.7	1048.3	1049.6	1051.1	1052.4	1053.8	1053.9
177.5°	1054.0	1053.6	1053.3	1053.0	1052.7	1052.4	1053.3	1054.3	1055.3	1056.1	1056.1
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	559.8	560.1	559.6	559.9	559.6	560.1	559.8	561.6	561.9	562.2	561.9
5°	521.6	519.2	518.7	518.2	518.7	519.2	521.6	522.5	523.4	525.0	527.9
7.5°	476.0	475.6	474.6	473.1	474.6	475.6	476.0	479.5	482.2	485.4	491.2
10°	446.7	445.6	445.4	444.0	445.4	445.6	446.7	451.1	454.3	458.8	466.7
12.5°	412.2	405.7	405.1	401.5	405.1	405.7	412.2	418.0	426.8	431.1	439.4
15°	351.1	349.8	345.7	343.1	345.7	349.8	351.1	355.9	359.1	370.9	384.4
17.5°	316.0	312.0	310.8	310.2	310.8	312.0	316.0	318.3	323.0	329.2	337.3
20°	293.5	289.9	289.3	288.8	289.3	289.9	293.5	296.3	300.0	306.7	315.1
22.5°	277.9	274.1	272.6	271.3	272.6	274.1	277.9	280.1	283.5	288.6	294.4
25°	251.4	249.9	249.1	248.7	249.1	249.9	251.4	253.4	256.6	263.8	269.8
27.5°	230.6	227.5	226.9	225.8	226.9	227.5	230.6	234.2	237.6	240.8	246.2
30°	218.7	217.8	216.3	215.1	216.3	217.8	218.7	220.6	222.8	228.3	233.5
32.5°	204.8	203.9	202.7	202.2	202.7	203.9	204.8	207.3	212.0	215.3	219.1
35°	189.4	186.5	185.3	183.5	185.3	186.5	189.4	191.5	193.2	196.1	203.0
37.5°	173.1	171.6	169.9	170.5	169.9	171.6	173.1	173.9	177.7	181.7	184.7
40°	160.4	159.4	159.0	158.8	159.0	159.4	160.4	163.1	167.7	169.5	174.0
42.5°	150.3	147.6	146.5	146.5	146.5	147.6	150.3	153.4	156.2	159.2	163.8
45°	135.1	132.5	130.6	130.8	130.6	132.5	135.1	136.1	138.6	144.5	147.0
47.5°	119.5	119.4	118.2	118.6	118.2	119.4	119.5	121.2	124.3	128.0	132.2
50°	112.0	110.8	109.9	110.2	109.9	110.8	112.0	113.4	115.2	117.1	123.6
52.5°	104.9	103.8	103.2	104.1	103.2	103.8	104.9	105.7	107.0	108.8	113.2
55°	93.2	91.9	91.8	91.6	91.8	91.9	93.2	94.2	95.8	97.2	99.2
57.5°	80.1	79.3	78.0	77.6	78.0	79.3	80.1	81.6	83.6	85.4	87.5
60°	70.7	69.1	67.1	66.9	67.1	69.1	70.7	73.3	74.1	77.0	79.4
62.5°	62.1	61.8	61.3	61.3	61.3	61.8	62.1	63.0	64.1	68.2	71.2
65°	54.5	54.3	54.5	54.7	54.5	54.3	54.5	54.9	55.1	55.5	56.7
67.5°	47.4	47.1	46.7	46.9	46.7	47.1	47.4	47.5	48.2	48.3	49.2
70°	42.1	41.9	41.7	41.7	41.7	41.9	42.1	42.5	43.0	43.3	44.3
72.5°	36.9	36.9	36.7	36.6	36.7	36.9	36.9	37.7	37.9	38.3	39.0
75°	29.6	29.2	29.2	29.2	29.2	29.2	29.6	29.8	30.0	30.6	31.0
77.5°	22.6	22.3	22.1	21.9	22.1	22.3	22.6	22.6	22.9	23.0	23.5
80°	17.8	17.7	17.4	17.4	17.4	17.7	17.8	18.0	18.0	18.6	18.5
82.5°	13.6	13.4	13.4	13.2	13.4	13.4	13.6	13.6	13.6	14.1	14.1
85°	7.3	7.5	7.3	7.7	7.3	7.5	7.3	7.1	7.3	7.7	7.7
87.5°	8.0	7.9	8.1	8.0	8.1	7.9	8.0	8.0	8.2	8.3	8.4
90°	29.7	29.9	30.1	30.2	30.1	29.9	29.7	29.4	29.6	30.0	30.3
92.5°	28.7	28.7	28.8	28.8	28.8	28.7	28.7	28.7	28.6	28.5	28.4
95°	56.4	56.0	55.6	55.2	55.6	56.0	56.4	56.7	57.0	57.0	57.0
97.5°	95.7	95.7	95.6	95.6	95.6	95.7	95.7	95.8	95.8	95.8	95.8
100°	122.5	122.3	122.1	121.9	122.1	122.3	122.5	122.7	122.8	122.8	122.8
102.5°	152.4	152.2	152.0	151.9	152.0	152.2	152.4	152.6	152.7	152.5	152.3
105°	197.5	197.5	197.5	197.5	197.5	197.5	197.5	197.5	197.3	197.0	196.5
107.5°	243.3	242.5	241.6	240.6	241.6	242.5	243.3	244.2	244.6	244.5	244.3
110°	275.9	275.3	274.6	274.1	274.6	275.3	275.9	276.4	276.8	276.8	276.8



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	307.5	307.0	306.6	306.1	306.6	307.0	307.5	307.8	308.4	308.8	309.2
115°	357.8	357.1	356.5	356.0	356.5	357.1	357.8	358.3	358.7	358.9	359.1
117.5°	405.3	404.7	404.0	403.5	404.0	404.7	405.3	405.8	406.4	406.9	407.3
120°	438.7	438.1	437.6	436.9	437.6	438.1	438.7	439.3	439.6	439.6	439.6
122.5°	471.0	470.6	470.1	469.7	470.1	470.6	471.0	471.4	471.9	472.3	472.8
125°	520.3	520.0	519.9	519.7	519.9	520.0	520.3	520.5	520.8	521.5	522.1
127.5°	567.1	566.5	565.9	565.3	565.9	566.5	567.1	567.8	568.5	569.2	569.9
130°	600.4	599.6	598.8	598.0	598.8	599.6	600.4	601.2	601.7	602.2	602.5
132.5°	631.2	630.6	630.0	629.4	630.0	630.6	631.2	631.9	632.6	633.5	634.4
135°	679.8	679.3	678.7	678.1	678.7	679.3	679.8	680.5	680.8	681.1	681.3
137.5°	724.6	723.8	723.0	722.2	723.0	723.8	724.6	725.4	725.9	726.0	726.2
140°	755.2	754.4	753.7	752.9	753.7	754.4	755.2	756.0	756.4	756.4	756.4
142.5°	783.0	782.2	781.4	780.6	781.4	782.2	783.0	783.8	784.1	783.9	783.8
145°	824.7	823.9	823.0	822.2	823.0	823.9	824.7	825.5	825.7	825.5	825.3
147.5°	861.7	860.9	860.2	859.4	860.2	860.9	861.7	862.5	862.6	862.2	861.7
150°	885.5	884.8	884.2	883.7	884.2	884.8	885.5	886.0	886.0	885.5	884.8
152.5°	908.7	907.9	907.2	906.4	907.2	907.9	908.7	909.5	909.5	908.7	907.9
155°	938.8	938.3	937.6	937.0	937.6	938.3	938.8	939.4	939.2	938.3	937.3
157.5°	966.3	965.3	964.3	963.4	964.3	965.3	966.3	967.1	967.0	965.6	964.3
160°	982.1	981.3	980.5	979.7	980.5	981.3	982.1	982.9	982.8	981.5	980.3
162.5°	996.8	995.9	995.0	994.0	995.0	995.9	996.8	997.8	997.6	996.2	994.9
165°	1015.7	1014.7	1013.7	1012.7	1013.7	1014.7	1015.7	1016.6	1016.5	1015.0	1013.7
167.5°	1031.1	1030.0	1029.0	1028.0	1029.0	1030.0	1031.1	1032.1	1031.9	1030.6	1029.1
170°	1039.4	1038.2	1037.0	1035.8	1037.0	1038.2	1039.4	1040.5	1040.4	1039.1	1037.7
172.5°	1045.8	1044.6	1043.4	1042.2	1043.4	1044.6	1045.8	1047.0	1046.9	1045.5	1044.1
175°	1052.8	1051.5	1050.3	1049.2	1050.3	1051.5	1052.8	1053.9	1053.8	1052.4	1051.1
177.5°	1055.3	1054.3	1053.3	1052.4	1053.3	1054.3	1055.3	1056.1	1056.1	1055.3	1054.3
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	560.6	562.8	566.2	568.2	571.4	573.5	574.7	576.8	577.9	582.0	586.2
5°	529.2	532.5	538.1	543.4	549.1	555.0	559.3	564.1	568.6	576.2	584.3
7.5°	493.4	497.8	506.7	515.1	525.0	533.2	540.6	548.8	556.2	567.3	578.8
10°	466.5	474.4	485.9	493.8	506.8	515.1	526.6	535.7	546.1	560.7	573.6
12.5°	443.3	452.8	462.1	473.1	484.7	498.6	511.2	523.0	535.2	550.3	565.5
15°	401.3	415.0	429.4	440.6	456.4	470.9	485.7	501.5	516.5	534.6	554.4
17.5°	347.1	363.1	387.3	406.4	424.9	439.5	457.9	477.0	494.6	516.4	538.5
20°	322.7	334.4	350.8	376.6	404.5	420.1	438.7	459.8	480.0	503.7	527.4
22.5°	303.1	313.5	326.6	346.7	377.9	399.2	418.7	440.1	463.5	487.7	514.0
25°	275.1	282.3	296.1	312.4	333.8	368.8	390.1	411.6	437.1	463.1	493.0
27.5°	254.0	260.6	269.6	285.0	301.0	326.2	360.0	383.4	408.8	438.0	469.1
30°	238.0	245.7	255.7	266.5	284.0	303.6	337.4	364.6	389.7	419.7	452.9
32.5°	226.3	232.4	240.9	252.0	266.4	285.3	312.4	345.3	369.8	401.4	436.0
35°	207.2	214.3	221.1	231.8	243.4	260.6	281.2	316.4	340.7	371.8	406.7
37.5°	191.5	195.8	203.4	211.8	224.2	237.0	254.8	286.3	312.6	343.2	378.9
40°	179.5	184.9	190.6	199.9	210.1	222.4	239.8	263.3	293.5	323.5	358.3
42.5°	167.8	174.7	180.7	187.0	198.0	210.4	224.6	244.5	275.4	303.7	337.6
45°	153.7	158.2	164.4	171.4	180.5	191.0	203.6	221.0	250.6	275.1	306.8
47.5°	137.4	143.9	148.0	154.7	163.4	173.4	185.1	200.2	224.1	247.1	276.6
50°	126.2	132.9	138.8	144.8	152.5	162.2	172.0	186.5	205.8	229.9	257.4
52.5°	116.6	122.5	128.2	134.3	141.9	150.7	160.0	172.8	189.2	211.4	238.2
55°	103.5	107.2	113.1	119.1	125.8	134.3	143.2	153.9	168.1	186.7	208.4
57.5°	90.1	94.3	98.9	105.0	111.8	118.3	126.4	136.1	147.2	164.1	182.6
60°	82.5	85.7	89.5	95.8	102.1	108.0	115.7	123.8	134.3	148.9	164.7
62.5°	74.0	77.1	80.6	86.1	92.2	97.6	104.3	112.9	121.8	135.1	148.9
65°	59.9	64.4	67.9	72.7	77.8	83.5	88.7	95.6	103.5	114.0	126.4
67.5°	49.7	52.0	55.2	59.6	64.7	69.6	74.6	80.0	86.9	95.0	104.8
70°	45.2	46.0	46.5	50.8	55.7	60.5	65.2	70.3	76.2	82.8	91.3
72.5°	39.9	40.7	41.4	43.2	47.1	52.0	56.8	60.5	66.1	71.7	78.6
75°	31.6	32.8	33.4	34.4	35.8	39.1	43.5	47.2	50.5	54.7	60.2
77.5°	24.1	24.8	25.4	26.5	27.4	28.8	31.4	34.6	37.7	40.1	43.9
80°	19.1	19.3	20.1	20.4	21.7	22.6	23.9	26.6	29.6	30.6	33.3
82.5°	14.4	14.5	15.2	15.6	16.1	17.0	18.5	19.3	21.7	23.0	24.6
85°	7.9	7.7	8.3	8.3	8.7	9.1	9.5	10.5	11.1	12.8	13.2
87.5°	8.6	8.6	7.9	7.0	6.2	5.7	5.2	4.8	4.7	4.7	4.9
90°	30.8	31.1	26.8	22.5	18.1	13.7	10.3	8.0	5.6	3.3	0.9
92.5°	28.4	28.3	27.3	26.2	25.2	24.2	22.8	21.0	19.4	17.6	15.9
95°	57.0	57.0	56.5	56.2	55.7	55.4	54.2	52.2	50.2	48.2	46.3
97.5°	95.8	95.8	95.0	94.3	93.5	92.7	91.5	89.8	88.0	86.3	84.5
100°	122.8	122.8	122.3	121.6	121.0	120.5	119.3	117.8	116.2	114.6	113.0
102.5°	152.1	152.0	151.2	150.5	149.7	149.0	147.9	146.7	145.4	144.2	142.9
105°	196.2	195.7	195.4	195.0	194.6	194.2	193.7	193.1	192.5	191.9	191.4
107.5°	244.2	244.0	244.0	244.0	244.0	244.0	243.6	242.7	241.8	240.9	240.0
110°	276.8	276.8	276.8	276.8	276.8	276.8	276.2	275.0	273.8	272.6	271.4



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	309.8	310.2	310.4	310.5	310.7	310.9	310.3	309.2	308.0	306.7	305.6
115°	359.4	359.5	359.9	360.3	360.7	361.1	360.7	359.5	358.3	357.1	356.0
117.5°	407.8	408.3	409.4	410.5	411.6	412.7	412.5	410.9	409.3	407.7	406.2
120°	439.6	439.6	441.2	442.7	444.3	445.9	445.9	444.3	442.7	441.2	439.6
122.5°	473.3	473.8	474.9	476.0	477.1	478.2	477.8	475.9	474.0	472.1	470.2
125°	522.6	523.3	523.9	524.4	525.0	525.7	525.0	523.3	521.5	519.7	517.9
127.5°	570.6	571.3	572.0	572.7	573.5	574.2	573.4	571.1	568.9	566.6	564.4
130°	603.0	603.3	603.8	604.1	604.5	604.9	603.9	601.3	598.7	596.1	593.5
132.5°	635.3	636.1	636.0	636.0	635.9	635.8	634.7	632.6	630.5	628.4	626.3
135°	681.4	681.6	681.3	680.8	680.5	680.1	678.8	676.6	674.4	672.3	670.1
137.5°	726.4	726.5	726.0	725.5	725.0	724.4	723.3	721.5	719.7	717.9	716.2
140°	756.4	756.4	755.5	754.4	753.4	752.4	751.1	749.3	747.5	745.7	744.0
142.5°	783.6	783.5	782.7	782.1	781.4	780.8	779.5	777.8	776.0	774.2	772.4
145°	825.1	824.9	823.8	822.5	821.4	820.2	818.9	817.5	816.1	814.8	813.3
147.5°	861.3	860.9	860.1	859.3	858.5	857.7	856.5	854.8	853.2	851.5	849.8
150°	884.2	883.7	882.9	882.1	881.3	880.5	879.5	878.3	877.1	875.9	874.8
152.5°	907.2	906.4	905.4	904.6	903.6	902.7	901.6	900.4	899.2	898.0	896.8
155°	936.3	935.2	934.7	934.1	933.5	932.9	932.3	931.7	931.1	930.5	930.0
157.5°	963.0	961.6	961.3	960.9	960.6	960.2	959.8	959.4	959.0	958.6	958.2
160°	979.2	977.9	977.8	977.6	977.4	977.2	976.9	976.5	976.1	975.7	975.4
162.5°	993.5	992.2	992.0	991.8	991.7	991.4	991.3	991.2	991.1	991.0	991.0
165°	1012.3	1010.9	1010.9	1010.9	1010.9	1010.9	1011.0	1011.2	1011.4	1011.6	1011.8
167.5°	1027.8	1026.4	1026.4	1026.4	1026.5	1026.5	1026.9	1027.4	1028.1	1028.7	1029.2
170°	1036.3	1034.9	1035.1	1035.4	1035.5	1035.7	1036.1	1036.7	1037.3	1037.9	1038.5
172.5°	1042.8	1041.3	1041.5	1041.7	1042.0	1042.1	1042.5	1043.1	1043.7	1044.3	1044.9
175°	1049.6	1048.3	1048.7	1049.1	1049.5	1049.9	1050.3	1051.0	1051.5	1052.1	1052.8
177.5°	1053.3	1052.4	1052.7	1053.0	1053.3	1053.6	1054.0	1054.5	1055.0	1055.4	1056.0
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	586.4	586.8	590.0	591.6	594.4	595.6	596.9	596.6	596.6	597.2	601.7
5°	587.6	591.7	597.7	603.6	609.3	614.1	617.4	620.6	621.9	627.7	632.9
7.5°	585.5	593.0	603.0	612.0	622.7	631.1	638.0	644.4	648.6	657.2	665.9
10°	582.7	593.3	604.6	616.2	631.0	642.1	653.4	662.2	664.9	677.7	685.0
12.5°	577.2	591.3	605.7	620.7	635.2	650.5	663.0	671.7	681.7	693.1	706.6
15°	569.0	585.1	604.0	623.2	643.9	662.5	675.9	691.1	702.0	714.6	726.4
17.5°	557.1	578.0	601.9	624.2	648.1	668.1	686.5	701.1	708.7	716.0	717.6
20°	547.7	570.2	598.3	624.6	648.5	671.6	689.9	702.0	704.1	704.3	693.6
22.5°	537.5	562.9	592.4	619.3	647.9	673.6	687.8	692.9	684.9	671.2	650.4
25°	518.7	548.1	582.4	613.1	644.4	668.6	673.5	664.4	636.2	606.6	569.2
27.5°	498.4	531.5	568.1	602.4	635.6	650.7	640.2	607.3	556.6	512.5	459.1
30°	483.5	520.6	556.6	594.9	625.7	632.1	608.1	559.6	500.5	434.1	380.8
32.5°	466.5	505.3	544.9	584.5	610.3	604.0	564.2	504.5	435.2	369.9	319.6
35°	442.2	482.2	525.0	564.7	581.1	553.8	494.2	416.6	345.7	284.8	250.1
37.5°	414.1	457.8	502.2	538.7	537.5	492.0	410.8	330.7	271.2	235.1	210.4
40°	394.1	438.4	486.3	517.1	504.0	444.6	356.7	281.2	237.6	208.8	190.8
42.5°	375.1	419.4	467.1	491.5	468.6	395.7	308.1	248.9	212.9	190.6	175.9
45°	342.5	389.3	433.5	447.0	406.1	325.7	249.1	206.2	182.3	165.7	155.6
47.5°	310.7	356.8	397.1	397.3	342.0	264.1	210.2	178.4	158.0	145.2	137.9
50°	291.2	335.0	368.8	363.6	300.8	235.0	188.0	160.6	143.7	133.7	126.0
52.5°	269.4	311.8	341.2	326.2	265.9	206.8	168.0	145.1	131.0	122.3	115.5
55°	237.6	275.3	296.0	273.2	217.0	172.0	142.0	123.9	113.4	106.1	100.2
57.5°	206.3	237.5	250.4	224.0	178.7	142.6	120.1	106.6	96.1	90.9	87.8
60°	186.7	213.3	222.4	193.2	155.3	124.8	106.4	93.8	86.1	82.7	79.6
62.5°	167.5	189.1	192.9	166.2	135.5	109.2	93.4	82.8	77.7	74.4	71.5
65°	138.9	154.5	152.8	131.3	107.2	86.7	75.2	68.7	64.8	60.2	55.1
67.5°	114.4	123.9	118.2	102.1	81.8	67.4	59.8	54.9	50.1	45.7	44.6
70°	98.8	104.3	98.3	83.5	67.1	56.5	50.5	44.6	41.7	40.8	38.9
72.5°	83.9	85.9	79.3	66.6	54.6	46.8	40.8	37.6	36.0	35.2	34.1
75°	63.0	61.6	55.9	46.0	37.9	32.6	30.8	29.6	28.5	27.7	27.1
77.5°	44.2	42.2	37.1	30.6	26.4	23.9	22.7	22.1	21.7	21.2	20.6
80°	33.3	31.8	26.8	21.8	20.1	18.8	18.2	17.4	17.4	17.0	16.4
82.5°	24.3	22.7	18.3	16.1	15.1	14.3	13.8	13.4	13.2	13.3	12.8
85°	12.8	10.3	9.1	8.7	8.1	7.7	7.9	7.5	7.5	7.5	7.3
87.5°	4.5	4.2	4.5	4.8	5.7	6.5	7.2	8.1	9.2	8.9	9.0
90°	3.3	5.6	8.0	10.3	13.7	18.1	22.5	26.8	31.1	30.8	30.3
92.5°	17.6	19.4	21.0	22.8	24.2	25.2	26.2	27.3	28.3	28.4	28.4
95°	48.2	50.2	52.2	54.2	55.4	55.7	56.2	56.5	57.0	57.0	57.0
97.5°	86.3	88.0	89.8	91.5	92.7	93.5	94.3	95.0	95.8	95.8	95.8
100°	114.6	116.2	117.8	119.3	120.5	121.0	121.6	122.3	122.8	122.8	122.8
102.5°	144.2	145.4	146.7	147.9	149.0	149.7	150.5	151.2	152.0	152.1	152.3
105°	191.9	192.5	193.1	193.7	194.2	194.6	195.0	195.4	195.7	196.2	196.5
107.5°	240.9	241.8	242.7	243.6	244.0	244.0	244.0	244.0	244.0	244.2	244.3
110°	272.6	273.8	275.0	276.2	276.8	276.8	276.8	276.8	276.8	276.8	276.8





TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	306.7	308.0	309.2	310.3	310.9	310.7	310.5	310.4	310.2	309.8	309.2
115°	357.1	358.3	359.5	360.7	361.1	360.7	360.3	359.9	359.5	359.4	359.1
117.5°	407.7	409.3	410.9	412.5	412.7	411.6	410.5	409.4	408.3	407.8	407.3
120°	441.2	442.7	444.3	445.9	445.9	444.3	442.7	441.2	439.6	439.6	439.6
122.5°	472.1	474.0	475.9	477.8	478.2	477.1	476.0	474.9	473.8	473.3	472.8
125°	519.7	521.5	523.3	525.0	525.7	525.0	524.4	523.9	523.3	522.6	522.1
127.5°	566.6	568.9	571.1	573.4	574.2	573.5	572.7	572.0	571.3	570.6	569.9
130°	596.1	598.7	601.3	603.9	604.9	604.5	604.1	603.8	603.3	603.0	602.5
132.5°	628.4	630.5	632.6	634.7	635.8	635.9	636.0	636.0	636.1	635.3	634.4
135°	672.3	674.4	676.6	678.8	680.1	680.5	680.8	681.3	681.6	681.4	681.3
137.5°	717.9	719.7	721.5	723.3	724.4	725.0	725.5	726.0	726.5	726.4	726.2
140°	745.7	747.5	749.3	751.1	752.4	753.4	754.4	755.5	756.4	756.4	756.4
142.5°	774.2	776.0	777.8	779.5	780.8	781.4	782.1	782.7	783.5	783.6	783.8
145°	814.8	816.1	817.5	818.9	820.2	821.4	822.5	823.8	824.9	825.1	825.3
147.5°	851.5	853.2	854.8	856.5	857.7	858.5	859.3	860.1	860.9	861.3	861.7
150°	875.9	877.1	878.3	879.5	880.5	881.3	882.1	882.9	883.7	884.2	884.8
152.5°	898.0	899.2	900.4	901.6	902.7	903.6	904.6	905.4	906.4	907.2	907.9
155°	930.5	931.1	931.7	932.3	932.9	933.5	934.1	934.7	935.2	936.3	937.3
157.5°	958.6	959.0	959.4	959.8	960.2	960.6	960.9	961.3	961.6	963.0	964.3
160°	975.7	976.1	976.5	976.9	977.2	977.4	977.6	977.8	977.9	979.2	980.3
162.5°	991.0	991.1	991.2	991.3	991.4	991.7	991.8	992.0	992.2	993.5	994.9
165°	1011.6	1011.4	1011.2	1011.0	1010.9	1010.9	1010.9	1010.9	1010.9	1012.3	1013.7
167.5°	1028.7	1028.1	1027.4	1026.9	1026.5	1026.5	1026.4	1026.4	1026.4	1027.8	1029.1
170°	1037.9	1037.3	1036.7	1036.1	1035.7	1035.5	1035.4	1035.1	1034.9	1036.3	1037.7
172.5°	1044.3	1043.7	1043.1	1042.5	1042.1	1042.0	1041.7	1041.5	1041.3	1042.8	1044.1
175°	1052.1	1051.5	1051.0	1050.3	1049.9	1049.5	1049.1	1048.7	1048.3	1049.6	1051.1
177.5°	1055.4	1055.0	1054.5	1054.0	1053.6	1053.3	1053.0	1052.7	1052.4	1053.3	1054.3
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	582.9	582.9	582.9	582.9	582.9	582.9	582.9
2.5°	603.3	605.5	606.5	606.5	607.6	607.1	606.6
5°	638.0	641.9	642.7	646.3	649.0	648.2	648.5
7.5°	672.5	678.7	684.8	687.6	688.0	689.6	690.3
10°	693.8	698.8	708.3	706.9	714.0	718.1	711.4
12.5°	714.2	721.0	727.6	729.4	733.4	734.8	732.1
15°	732.6	736.3	736.6	735.7	736.9	735.8	732.0
17.5°	715.4	709.4	697.5	691.8	687.3	680.6	678.0
20°	686.9	669.4	649.2	641.1	631.6	613.0	617.4
22.5°	625.3	605.5	585.1	561.5	550.2	532.5	531.5
25°	529.5	495.3	457.5	431.2	415.8	398.2	390.5
27.5°	411.7	368.5	337.7	322.1	307.8	293.9	293.3
30°	334.2	301.8	277.9	264.6	255.8	249.9	251.2
32.5°	281.7	259.5	243.3	232.3	225.9	221.4	221.3
35°	230.3	215.1	204.7	200.1	195.5	192.3	192.4
37.5°	197.1	188.0	182.2	177.1	174.2	172.5	171.7
40°	180.0	172.5	168.1	165.1	162.6	160.4	160.0
42.5°	166.7	160.4	156.0	153.6	151.3	149.7	149.4
45°	147.8	142.8	138.8	136.1	135.1	133.7	133.7
47.5°	131.5	126.5	123.4	121.7	120.0	119.0	119.0
50°	120.6	116.6	113.9	112.8	111.4	110.8	110.6
52.5°	110.7	107.7	105.8	105.0	104.4	103.7	103.8
55°	97.2	95.6	94.8	94.2	93.2	91.9	92.7
57.5°	86.0	84.5	82.4	80.4	79.5	78.6	79.0
60°	78.0	75.2	72.3	70.1	69.5	67.7	67.7
62.5°	67.9	63.9	60.5	59.2	58.6	57.8	57.6
65°	52.3	50.6	49.8	49.0	48.6	48.6	48.2
67.5°	43.3	42.6	41.7	41.6	41.2	41.0	40.9
70°	38.3	37.5	37.1	36.8	36.5	36.6	36.0
72.5°	33.4	32.8	32.7	32.2	31.9	31.9	31.5
75°	26.3	26.3	26.1	25.9	25.5	25.3	25.5
77.5°	20.2	20.3	20.0	19.9	19.9	19.9	19.7
80°	16.2	16.4	16.2	16.0	15.8	16.0	15.8
82.5°	12.8	12.5	12.5	12.4	12.4	12.3	12.2
85°	7.3	7.5	7.3	7.1	7.1	7.1	7.3
87.5°	8.7	8.6	8.6	8.6	8.7	8.7	8.6
90°	30.0	29.6	29.4	29.7	29.9	30.1	30.2
92.5°	28.5	28.6	28.7	28.7	28.7	28.8	28.8
95°	57.0	57.0	56.7	56.4	56.0	55.6	55.2
97.5°	95.8	95.8	95.8	95.7	95.7	95.6	95.6
100°	122.8	122.8	122.7	122.5	122.3	122.1	121.9
102.5°	152.5	152.7	152.6	152.4	152.2	152.0	151.9
105°	197.0	197.3	197.5	197.5	197.5	197.5	197.5
107.5°	244.5	244.6	244.2	243.3	242.5	241.6	240.6
110°	276.8	276.8	276.4	275.9	275.3	274.6	274.1



TEST NUMBER: P331634-940

CATALOG NUMBER: S122RDIP-S290D925U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	308.8	308.4	307.8	307.5	307.0	306.6	306.1
115°	358.9	358.7	358.3	357.8	357.1	356.5	356.0
117.5°	406.9	406.4	405.8	405.3	404.7	404.0	403.5
120°	439.6	439.6	439.3	438.7	438.1	437.6	436.9
122.5°	472.3	471.9	471.4	471.0	470.6	470.1	469.7
125°	521.5	520.8	520.5	520.3	520.0	519.9	519.7
127.5°	569.2	568.5	567.8	567.1	566.5	565.9	565.3
130°	602.2	601.7	601.2	600.4	599.6	598.8	598.0
132.5°	633.5	632.6	631.9	631.2	630.6	630.0	629.4
135°	681.1	680.8	680.5	679.8	679.3	678.7	678.1
137.5°	726.0	725.9	725.4	724.6	723.8	723.0	722.2
140°	756.4	756.4	756.0	755.2	754.4	753.7	752.9
142.5°	783.9	784.1	783.8	783.0	782.2	781.4	780.6
145°	825.5	825.7	825.5	824.7	823.9	823.0	822.2
147.5°	862.2	862.6	862.5	861.7	860.9	860.2	859.4
150°	885.5	886.0	886.0	885.5	884.8	884.2	883.7
152.5°	908.7	909.5	909.5	908.7	907.9	907.2	906.4
155°	938.3	939.2	939.4	938.8	938.3	937.6	937.0
157.5°	965.6	967.0	967.1	966.3	965.3	964.3	963.4
160°	981.5	982.8	982.9	982.1	981.3	980.5	979.7
162.5°	996.2	997.6	997.8	996.8	995.9	995.0	994.0
165°	1015.0	1016.5	1016.6	1015.7	1014.7	1013.7	1012.7
167.5°	1030.6	1031.9	1032.1	1031.1	1030.0	1029.0	1028.0
170°	1039.1	1040.4	1040.5	1039.4	1038.2	1037.0	1035.8
172.5°	1045.5	1046.9	1047.0	1045.8	1044.6	1043.4	1042.2
175°	1052.4	1053.8	1053.9	1052.8	1051.5	1050.3	1049.2
177.5°	1055.3	1056.1	1056.1	1055.3	1054.3	1053.3	1052.4
180°	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5	1054.5

(END OF REPORT)