

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331671-940

Luminaire Tested: **S122RDIP-S485D1080U940-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331671-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D1080U940-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5409.4 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	94	90	86	83	84	81	78	75	64	62	60	49	48	46	35	34	33	27
2	86	79	73	69	77	71	67	62	57	54	51	43	41	39	31	30	29	23
3	79	70	63	58	70	63	57	53	51	47	43	39	36	34	28	26	25	20
4	72	62	55	49	65	56	50	45	45	41	37	35	32	30	25	24	22	18
5	66	56	48	42	60	50	44	39	41	36	32	32	28	26	23	21	20	16
6	61	50	42	37	55	45	39	34	37	32	28	29	25	23	21	19	17	14
7	57	45	38	32	51	41	35	30	33	29	25	26	23	20	19	17	16	13
8	53	41	34	29	47	37	31	27	31	26	22	24	21	18	18	16	14	12
9	49	37	30	26	44	34	28	24	28	23	20	22	19	17	17	15	13	11
10	46	34	28	23	41	31	25	21	26	21	18	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15474	15474	15474	15474
5°	17280	15571	13807	15571
10°	19174	15462	11968	15462
15°	20117	15234	9429	15234
20°	17438	14899	8158	14899
25°	11437	14439	7285	14439
30°	7700	13882	6594	13882
35°	6236	13180	5947	13180
40°	5545	12416	5503	12416
45°	5019	11520	4912	11520
50°	4567	10630	4549	10630
55°	4293	9647	4236	9647
60°	3591	8741	3549	8741
65°	3030	7939	3435	7939
70°	2799	7091	3238	7091
75°	2620	6170	2994	6170
80°	2408	5077	2659	5077
85°	2205	4020	2353	4020



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.8	1.7
10°-20°	253.1	4.7
20°-30°	326.2	6.0
30°-40°	310.0	5.7
40°-50°	265.6	4.9
50°-60°	202.2	3.7
60°-70°	127.8	2.4
70°-80°	63.8	1.2
80°-90°	21.5	0.4
90°-100°	215.4	4.0
100°-110°	730.9	13.5
110°-120°	776.4	14.4
120°-130°	639.2	11.8
130°-140°	513.3	9.5
140°-150°	387.9	7.2
150°-160°	272.6	5.0
160°-170°	160.5	3.0
170°-180°	52.2	1.0
0°-30°	670.2	12.4
0°-40°	980.2	18.1
0°-60°	1448.0	26.8
0°-90°	1661.1	30.7
90°-120°	1722.7	31.8
90°-150°	3263.0	60.3
90°-180°	3748.0	69.3
0°-180°	5409.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	958	958	958	958	958	
5°	1066	961	852	961	1066	105
15°	1204	911	564	911	1204	325
25°	642	810	409	810	642	305
35°	316	669	302	669	316	202
45°	220	504	215	504	220	170
55°	152	343	150	343	152	134
65°	79	208	90	208	79	81
75°	42	99	48	99	42	45
85°	12	22	13	22	12	14
90°	34	1	34	1	34	19
95°	118	36	118	36	118	154
105°	1167	126	1167	126	1167	1130
115°	1536	223	1536	223	1536	1504
125°	1246	311	1246	311	1246	1126
135°	1033	365	1033	365	1033	802
145°	825	416	825	416	825	524
155°	693	473	693	473	693	323
165°	608	516	608	516	608	174
175°	548	538	548	538	548	53
180°	539	539	539	539	539	



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	997.3	998.1	998.9	997.0	997.0	995.4	991.9	989.3	981.8	980.7	980.7
5°	1066.2	1065.6	1066.9	1062.6	1056.6	1055.3	1048.9	1040.6	1032.0	1022.3	1020.3
7.5°	1134.9	1133.9	1131.2	1130.4	1125.9	1115.8	1105.6	1094.8	1080.4	1066.3	1059.3
10°	1169.5	1180.4	1173.8	1162.2	1164.5	1148.9	1140.5	1126.2	1114.2	1093.2	1088.6
12.5°	1203.5	1207.9	1205.8	1199.2	1196.2	1185.4	1174.1	1161.6	1139.5	1120.7	1104.3
15°	1203.5	1209.8	1211.5	1209.4	1211.1	1210.4	1204.4	1194.1	1174.8	1154.1	1136.2
17.5°	1114.6	1119.0	1129.9	1137.3	1146.7	1166.4	1176.1	1179.9	1177.0	1165.2	1152.5
20°	1014.9	1007.6	1038.3	1053.9	1067.3	1100.5	1129.2	1140.1	1157.8	1157.5	1154.1
22.5°	873.8	875.5	904.6	923.1	962.1	995.3	1028.0	1069.3	1103.5	1126.1	1139.2
25°	642.0	654.7	683.7	708.9	752.2	814.2	870.5	935.8	997.3	1046.0	1092.3
27.5°	482.1	483.1	506.0	529.5	555.2	605.9	676.8	754.7	842.6	915.0	998.4
30°	413.0	410.9	420.6	434.9	456.9	496.1	549.5	626.1	713.6	822.9	920.1
32.5°	363.9	364.0	371.3	381.9	400.1	426.6	463.2	525.3	608.1	715.5	829.5
35°	316.4	316.0	321.4	329.0	336.6	353.7	378.6	411.3	468.2	568.5	685.0
37.5°	282.2	283.7	286.3	291.1	299.5	309.0	324.0	345.9	386.5	445.8	543.7
40°	263.1	263.8	267.4	271.4	276.4	283.7	296.0	313.7	343.3	390.6	462.2
42.5°	245.5	246.1	248.8	252.4	256.4	263.8	273.9	289.2	313.3	350.1	409.2
45°	219.8	219.8	222.1	223.7	228.1	234.8	243.1	255.7	272.4	299.7	339.0
47.5°	195.6	195.7	197.2	200.1	202.9	208.0	216.2	226.6	238.7	259.8	293.4
50°	181.8	182.2	183.2	185.5	187.2	191.8	198.1	207.1	219.8	236.1	264.0
52.5°	170.6	170.4	171.7	172.7	173.8	177.2	181.9	189.8	201.2	215.3	238.5
55°	152.5	151.1	153.2	154.8	155.9	157.2	159.8	164.9	174.5	186.5	203.8
57.5°	129.8	129.3	130.7	132.2	135.4	139.0	141.2	144.5	149.5	158.0	175.2
60°	111.2	111.2	114.2	115.2	118.9	123.5	128.2	130.9	135.9	141.5	154.2
62.5°	94.7	95.0	96.4	97.4	99.4	105.1	111.7	117.5	122.3	127.7	136.1
65°	79.3	79.9	79.9	80.6	81.9	83.3	85.9	90.6	98.9	106.6	112.9
67.5°	67.2	67.5	67.7	68.3	68.7	70.1	71.2	73.3	75.2	82.5	90.3
70°	59.3	60.3	59.9	60.6	60.9	61.6	63.0	63.9	67.0	68.6	73.3
72.5°	51.8	52.5	52.5	52.9	53.8	53.9	54.9	55.9	57.9	59.3	61.8
75°	42.0	41.6	42.0	42.6	43.0	43.2	43.2	44.6	45.7	47.0	48.6
77.5°	32.4	32.7	32.6	32.7	32.7	33.3	33.3	33.9	34.9	35.6	36.4
80°	25.9	26.3	25.9	26.3	26.7	26.9	26.7	26.9	28.0	28.6	28.6
82.5°	20.2	20.2	20.4	20.4	20.5	20.6	21.0	21.1	21.8	21.7	21.9
85°	11.9	11.7	11.7	11.7	11.9	12.3	11.9	11.9	12.3	12.3	12.3
87.5°	11.1	11.3	11.3	11.3	11.3	11.1	10.7	11.4	11.3	11.9	11.3
90°	34.2	34.2	34.2	34.2	34.2	33.2	31.1	33.2	34.2	35.2	34.2
92.5°	57.4	59.0	58.2	61.5	62.3	68.8	77.5	90.3	113.8	134.6	132.8
95°	118.1	117.1	120.2	128.4	141.9	164.7	208.2	271.4	355.3	406.1	359.4
97.5°	232.5	241.1	256.3	281.8	331.3	406.1	518.2	633.3	727.2	693.2	522.1
100°	370.9	389.5	419.5	464.0	550.0	675.4	817.3	945.7	967.5	818.3	563.5
102.5°	652.6	677.9	715.4	791.4	884.8	1017.6	1121.4	1150.5	1057.0	822.5	547.8
105°	1167.4	1182.0	1226.5	1290.7	1355.0	1389.1	1375.6	1258.6	1043.1	767.6	516.9
107.5°	1491.2	1510.5	1519.4	1523.0	1514.8	1464.7	1357.0	1180.7	952.2	708.7	501.6
110°	1589.0	1590.1	1580.7	1561.0	1516.5	1431.6	1299.0	1113.6	895.0	680.6	498.3



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1587.3	1581.8	1564.1	1531.2	1469.3	1371.9	1230.2	1052.2	855.2	662.4	499.1
115°	1536.2	1526.9	1499.9	1452.3	1378.8	1272.0	1136.4	976.9	805.9	642.2	503.5
117.5°	1444.8	1437.0	1408.5	1358.3	1283.3	1183.2	1060.2	920.1	774.8	632.5	510.9
120°	1386.0	1375.6	1345.6	1296.9	1224.4	1130.2	1020.3	891.9	758.2	626.7	515.9
122.5°	1324.6	1316.0	1289.2	1241.4	1176.3	1091.2	987.2	869.5	744.1	623.4	521.7
125°	1246.2	1237.9	1212.0	1172.6	1112.5	1034.8	943.7	837.0	724.1	617.4	530.4
127.5°	1177.4	1170.7	1148.3	1111.5	1059.1	987.4	901.4	804.9	705.4	613.9	539.3
130°	1138.4	1130.2	1109.5	1074.2	1023.4	955.1	873.3	784.2	693.0	612.2	545.9
132.5°	1097.8	1090.4	1071.3	1036.1	986.1	921.9	846.8	764.3	683.1	611.4	552.5
135°	1032.8	1028.6	1010.0	975.8	931.2	873.3	804.9	736.5	669.1	610.1	560.4
137.5°	968.9	962.8	946.4	916.9	876.4	825.8	771.5	714.3	659.4	609.9	567.5
140°	925.1	918.8	903.3	876.4	843.2	797.6	750.0	700.3	653.6	609.1	570.8
142.5°	881.1	879.9	866.0	841.5	810.0	772.0	730.9	688.7	647.8	609.1	573.3
145°	824.6	821.4	811.1	793.4	768.7	738.6	706.5	672.3	640.2	607.0	576.0
147.5°	777.1	775.3	768.2	754.1	733.6	711.7	686.6	659.7	632.3	603.3	576.8
150°	748.9	747.9	741.7	729.2	713.7	695.1	673.3	650.5	625.6	600.8	576.0
152.5°	724.9	724.7	720.1	709.4	697.1	681.0	662.5	641.4	619.8	596.6	574.3
155°	693.0	695.1	690.9	683.7	672.3	660.8	645.3	628.7	609.1	589.4	571.8
157.5°	665.8	665.8	664.0	658.0	649.9	641.0	627.9	614.0	599.0	581.9	567.0
160°	648.5	648.5	647.4	642.2	635.0	627.8	616.4	604.9	591.5	577.0	564.5
162.5°	631.9	632.7	631.7	628.1	620.9	615.3	605.6	595.8	584.9	572.8	562.0
165°	608.1	609.1	609.1	604.9	600.8	596.6	589.4	582.2	573.9	564.5	557.3
167.5°	586.1	587.4	587.5	585.2	583.4	579.7	574.7	569.1	563.1	557.3	552.5
170°	572.8	574.9	576.0	572.8	571.8	569.7	565.6	562.5	557.3	553.1	550.0
172.5°	562.0	563.3	564.4	562.9	561.9	560.6	557.3	555.0	551.5	548.2	546.7
175°	548.0	550.0	551.1	550.0	550.0	549.0	548.0	547.0	543.9	542.8	541.8
177.5°	539.5	541.2	542.0	542.0	542.0	542.0	541.2	541.2	539.5	538.7	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	981.2	979.2	977.3	972.5	970.1	964.7	963.9	963.7	956.8	950.1	948.2
5°	1014.9	1009.7	1001.7	992.3	982.7	972.7	966.0	960.7	947.4	934.7	927.4
7.5°	1048.9	1037.5	1023.7	1006.0	991.3	974.8	962.6	951.5	932.6	914.5	902.3
10°	1074.2	1055.6	1037.3	1013.0	994.0	975.4	958.1	943.1	921.8	897.8	880.7
12.5°	1089.9	1069.4	1044.2	1020.5	995.9	972.1	949.0	929.7	904.7	879.9	859.7
15°	1111.3	1089.2	1058.6	1024.7	993.0	962.1	935.4	911.4	878.8	849.2	824.5
17.5°	1128.6	1098.3	1065.4	1026.2	989.5	950.2	915.9	885.2	848.9	813.2	784.2
20°	1134.2	1104.2	1066.2	1027.0	983.6	937.4	900.4	867.1	828.1	789.2	755.9
22.5°	1130.7	1107.4	1065.1	1018.2	973.8	925.4	883.7	845.0	801.8	762.1	723.4
25°	1107.2	1099.2	1059.3	1008.0	957.3	901.1	852.8	810.5	761.3	718.6	676.6
27.5°	1052.4	1069.7	1044.9	990.2	934.0	873.6	819.4	771.2	720.1	672.1	630.3
30°	999.7	1039.3	1028.6	978.0	915.1	855.8	794.9	744.6	690.0	640.7	599.4
32.5°	927.5	992.9	1003.4	961.0	895.9	830.7	766.9	716.8	659.9	607.9	567.7
35°	812.5	910.4	955.4	928.4	863.1	792.9	726.9	668.7	611.4	560.1	520.1
37.5°	675.4	808.7	883.7	885.6	825.6	752.6	680.8	622.9	564.3	514.0	470.7
40°	586.4	730.9	828.5	850.2	799.5	720.6	648.0	589.1	531.8	482.5	432.9
42.5°	506.5	650.5	770.4	808.1	767.9	689.5	616.6	555.0	499.3	452.6	402.0
45°	409.6	535.5	667.6	734.9	712.7	640.0	563.1	504.5	452.2	411.9	363.3
47.5°	345.5	434.3	562.1	653.2	652.7	586.5	510.9	454.7	406.2	368.5	329.0
50°	309.0	386.3	494.5	597.7	606.4	550.8	478.8	423.2	378.0	338.3	306.7
52.5°	276.3	339.9	437.2	536.2	560.8	512.6	442.9	391.6	347.6	311.1	284.0
55°	233.4	282.7	356.7	449.2	486.5	452.5	390.6	342.7	307.0	276.4	253.1
57.5°	197.4	234.4	293.7	368.3	411.7	390.3	339.3	300.3	269.8	242.1	223.7
60°	174.9	205.1	255.4	317.7	365.6	350.6	307.0	270.7	244.8	220.8	203.5
62.5°	153.6	179.6	222.7	273.2	317.2	310.9	275.4	244.9	222.1	200.3	185.7
65°	123.5	142.5	176.1	215.8	251.1	254.0	228.5	207.8	187.4	170.1	157.2
67.5°	98.4	110.8	134.5	167.8	194.3	203.8	188.1	172.3	156.1	142.8	131.5
70°	82.9	92.9	110.2	137.2	161.5	171.5	162.5	150.2	136.2	125.2	115.6
72.5°	67.2	77.0	89.7	109.5	130.4	141.2	138.0	129.1	117.8	108.7	99.6
75°	50.6	53.6	62.2	75.6	91.9	101.2	103.5	98.9	89.9	82.9	77.6
77.5°	37.5	39.2	43.3	50.4	61.0	69.3	72.8	72.2	66.0	62.0	57.0
80°	30.0	30.9	33.0	35.9	44.0	52.3	54.6	54.6	50.3	48.6	43.6
82.5°	22.7	23.5	24.7	26.4	30.1	37.4	39.9	40.5	37.7	35.6	31.7
85°	13.0	12.7	13.3	14.4	15.0	16.9	21.0	21.7	21.0	18.3	17.3
87.5°	10.2	8.9	7.9	7.0	6.9	6.7	7.2	7.9	7.5	7.5	7.4
90°	28.0	20.7	15.5	12.4	10.3	8.3	4.1	1.1	4.1	8.3	10.3
92.5°	103.3	70.4	47.0	37.3	30.2	25.7	18.2	12.7	18.2	25.7	30.2
95°	239.2	149.2	101.5	76.7	60.1	50.7	40.4	36.3	40.4	50.7	60.1
97.5°	322.4	196.8	137.0	108.8	89.7	75.6	64.6	59.0	64.6	75.6	89.7
100°	339.7	213.4	158.5	129.5	108.8	92.2	82.8	79.7	82.8	92.2	108.8
102.5°	340.6	228.3	177.5	148.6	127.0	110.4	101.1	98.8	101.1	110.4	127.0
105°	346.0	253.8	205.1	176.1	153.3	137.8	130.5	126.4	130.5	137.8	153.3
107.5°	360.3	279.9	232.6	203.5	180.8	166.6	159.5	156.2	159.5	166.6	180.8
110°	371.8	297.3	251.7	221.7	199.9	186.5	180.2	176.1	180.2	186.5	199.9



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	384.3	313.9	269.9	239.1	218.1	205.5	198.5	194.3	198.5	205.5	218.1
115°	403.0	339.7	295.2	267.2	246.6	234.1	227.9	222.7	227.9	234.1	246.6
117.5°	422.8	363.6	322.4	293.4	273.5	262.5	256.3	252.2	256.3	262.5	273.5
120°	436.1	380.1	339.7	310.8	290.1	280.7	274.5	270.4	274.5	280.7	290.1
122.5°	447.7	395.9	358.0	328.1	307.5	297.3	291.1	287.8	291.1	297.3	307.5
125°	466.2	419.5	382.3	353.2	332.5	320.1	313.9	310.8	313.9	320.1	332.5
127.5°	483.3	441.5	405.2	375.4	355.5	341.9	333.1	329.0	333.1	341.9	355.5
130°	494.1	454.8	418.5	389.5	368.8	354.3	343.9	339.7	343.9	354.3	368.8
132.5°	504.9	466.4	431.8	402.8	381.2	365.9	354.7	349.7	354.7	365.9	381.2
135°	519.0	482.7	449.6	420.5	396.7	381.2	368.8	364.6	368.8	381.2	396.7
137.5°	529.8	496.0	463.2	436.3	412.7	396.1	383.7	378.7	383.7	396.1	412.7
140°	535.6	503.5	472.3	445.4	422.7	406.1	393.6	389.5	393.6	406.1	422.7
142.5°	540.6	509.3	479.0	453.7	431.8	415.2	403.6	400.3	403.6	415.2	431.8
145°	547.0	517.9	490.0	467.2	446.5	431.0	420.5	416.4	420.5	431.0	446.5
147.5°	550.5	525.0	498.6	478.4	461.2	446.8	436.9	433.8	436.9	446.8	461.2
150°	552.1	528.3	504.4	485.8	470.3	456.8	448.5	445.4	448.5	456.8	470.3
152.5°	552.9	531.6	510.2	493.3	478.6	466.7	458.5	457.0	458.5	466.7	478.6
155°	554.2	536.5	519.0	503.5	492.0	480.6	474.4	473.4	474.4	480.6	492.0
157.5°	554.2	540.1	525.2	512.1	503.0	493.1	488.1	487.1	488.1	493.1	503.0
160°	554.2	541.8	529.3	517.9	509.6	501.3	497.2	496.1	497.2	501.3	509.6
162.5°	553.4	542.6	531.8	522.9	515.4	508.8	504.7	505.3	504.7	508.8	515.4
165°	551.1	543.9	534.5	528.3	523.1	516.9	514.9	515.9	514.9	516.9	523.1
167.5°	549.7	543.6	536.8	532.9	529.1	525.2	523.3	524.6	523.3	525.2	529.1
170°	548.0	542.8	537.6	534.5	532.4	529.3	528.3	530.4	528.3	529.3	532.4
172.5°	545.5	542.0	538.4	536.2	534.9	531.8	532.4	533.7	532.4	531.8	534.9
175°	542.8	540.7	538.7	537.6	537.6	535.6	536.5	537.6	536.5	535.6	537.6
177.5°	541.2	539.5	538.7	538.7	538.7	537.0	537.8	539.5	537.8	537.0	538.7
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	944.8	942.9	939.4	934.2	930.9	925.3	921.6	923.7	924.3	923.7	923.2
5°	919.4	912.4	902.8	893.4	884.8	875.5	870.1	867.8	863.1	860.5	859.2
7.5°	888.7	876.6	863.0	846.8	832.9	818.5	811.1	807.4	797.9	792.7	788.2
10°	865.8	846.8	833.1	811.8	798.9	779.9	766.9	767.2	754.2	746.9	741.5
12.5°	840.5	819.7	796.9	777.8	759.7	744.5	728.8	722.5	708.6	701.6	687.2
15°	798.5	774.2	750.3	724.2	706.0	682.3	659.7	632.0	609.8	590.4	585.1
17.5°	752.7	722.6	698.6	668.1	636.7	596.9	570.7	554.6	541.2	531.0	523.4
20°	721.3	690.6	665.0	619.0	576.8	549.7	530.5	518.2	504.2	493.2	487.1
22.5°	688.2	656.3	621.3	570.0	537.1	515.4	498.2	484.0	474.6	466.0	460.6
25°	641.3	606.4	548.8	513.4	486.9	464.2	452.2	443.5	433.5	421.9	416.6
27.5°	591.8	536.2	494.8	468.6	443.2	428.5	417.7	404.7	395.8	390.6	385.0
30°	554.7	499.2	466.9	438.2	420.3	403.9	391.3	384.0	375.3	366.3	362.7
32.5°	513.4	469.0	438.1	414.3	396.0	382.1	372.1	360.3	354.0	348.5	340.8
35°	462.2	428.6	400.3	380.9	363.6	352.3	340.6	333.7	322.4	317.7	314.7
37.5°	418.7	389.6	368.5	348.1	334.4	321.9	314.8	303.6	298.7	292.2	285.9
40°	394.2	365.6	345.4	328.7	313.3	304.0	295.1	286.1	278.7	275.7	268.0
42.5°	369.3	345.9	325.6	307.4	297.1	287.2	275.9	269.3	261.6	256.8	252.1
45°	334.7	314.1	296.7	281.7	270.4	260.1	252.7	241.7	237.5	227.7	223.7
47.5°	304.3	285.1	268.6	254.3	243.3	236.6	225.9	217.2	210.4	204.4	199.3
50°	282.7	266.7	250.7	238.1	228.1	218.5	207.5	203.1	192.4	189.5	186.5
52.5°	263.0	247.8	233.2	220.8	210.8	201.4	191.7	186.1	178.9	175.8	173.7
55°	235.4	220.8	206.8	195.8	185.8	176.1	170.1	163.2	159.8	157.5	154.8
57.5°	207.7	194.6	183.8	172.7	162.6	155.0	148.0	143.8	140.4	137.3	134.1
60°	190.1	177.5	167.8	157.5	147.2	140.9	135.5	130.5	126.5	121.9	120.6
62.5°	171.5	160.4	151.6	141.5	132.5	126.7	121.7	117.0	112.2	105.4	103.5
65°	145.9	137.2	127.9	119.6	111.6	105.9	98.5	93.3	91.2	90.6	90.2
67.5°	122.7	114.5	106.5	98.0	90.7	85.4	81.7	80.9	79.5	79.1	78.2
70°	107.2	99.6	91.6	83.6	76.6	75.6	74.3	72.9	71.2	70.6	69.9
72.5°	93.4	85.4	77.5	71.1	68.0	66.8	65.5	64.1	63.0	62.3	62.0
75°	71.6	64.3	58.9	56.6	54.9	53.9	52.0	50.9	50.3	49.3	49.0
77.5°	51.5	47.4	44.9	43.5	41.7	40.7	39.6	38.5	37.8	37.6	37.1
80°	39.3	37.3	35.7	33.6	33.0	31.7	31.3	30.3	30.7	29.6	29.6
82.5°	30.5	28.0	26.6	25.7	25.0	23.9	23.5	23.1	23.2	22.5	22.5
85°	15.7	15.0	14.4	13.6	13.6	12.7	13.0	12.7	12.7	11.9	11.7
87.5°	7.6	7.9	8.4	9.9	11.1	11.1	10.8	10.3	10.0	10.3	10.3
90°	12.4	15.5	20.7	28.0	34.2	35.2	34.2	33.2	31.1	33.2	34.2
92.5°	37.3	47.0	70.4	103.3	132.8	134.6	113.8	90.3	77.5	68.8	62.3
95°	76.7	101.5	149.2	239.2	359.4	406.1	355.3	271.4	208.2	164.7	141.9
97.5°	108.8	137.0	196.8	322.4	522.1	693.2	727.2	633.3	518.2	406.1	331.3
100°	129.5	158.5	213.4	339.7	563.5	818.3	967.5	945.7	817.3	675.4	550.0
102.5°	148.6	177.5	228.3	340.6	547.8	822.5	1057.0	1150.5	1121.4	1017.6	884.8
105°	176.1	205.1	253.8	346.0	516.9	767.6	1043.1	1258.6	1375.6	1389.1	1355.0
107.5°	203.5	232.6	279.9	360.3	501.6	708.7	952.2	1180.7	1357.0	1464.7	1514.8
110°	221.7	251.7	297.3	371.8	498.3	680.6	895.0	1113.6	1299.0	1431.6	1516.5



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	239.1	269.9	313.9	384.3	499.1	662.4	855.2	1052.2	1230.2	1371.9	1469.3
115°	267.2	295.2	339.7	403.0	503.5	642.2	805.9	976.9	1136.4	1272.0	1378.8
117.5°	293.4	322.4	363.6	422.8	510.9	632.5	774.8	920.1	1060.2	1183.2	1283.3
120°	310.8	339.7	380.1	436.1	515.9	626.7	758.2	891.9	1020.3	1130.2	1224.4
122.5°	328.1	358.0	395.9	447.7	521.7	623.4	744.1	869.5	987.2	1091.2	1176.3
125°	353.2	382.3	419.5	466.2	530.4	617.4	724.1	837.0	943.7	1034.8	1112.5
127.5°	375.4	405.2	441.5	483.3	539.3	613.9	705.4	804.9	901.4	987.4	1059.1
130°	389.5	418.5	454.8	494.1	545.9	612.2	693.0	784.2	873.3	955.1	1023.4
132.5°	402.8	431.8	466.4	504.9	552.5	611.4	683.1	764.3	846.8	921.9	986.1
135°	420.5	449.6	482.7	519.0	560.4	610.1	669.1	736.5	804.9	873.3	931.2
137.5°	436.3	463.2	496.0	529.8	567.5	609.9	659.4	714.3	771.5	825.8	876.4
140°	445.4	472.3	503.5	535.6	570.8	609.1	653.6	700.3	750.0	797.6	843.2
142.5°	453.7	479.0	509.3	540.6	573.3	609.1	647.8	688.7	730.9	772.0	810.0
145°	467.2	490.0	517.9	547.0	576.0	607.0	640.2	672.3	706.5	738.6	768.7
147.5°	478.4	498.6	525.0	550.5	576.8	603.3	632.3	659.7	686.6	711.7	733.6
150°	485.8	504.4	528.3	552.1	576.0	600.8	625.6	650.5	673.3	695.1	713.7
152.5°	493.3	510.2	531.6	552.9	574.3	596.6	619.8	641.4	662.5	681.0	697.1
155°	503.5	519.0	536.5	554.2	571.8	589.4	609.1	628.7	645.3	660.8	672.3
157.5°	512.1	525.2	540.1	554.2	567.0	581.9	599.0	614.0	627.9	641.0	649.9
160°	517.9	529.3	541.8	554.2	564.5	577.0	591.5	604.9	616.4	627.8	635.0
162.5°	522.9	531.8	542.6	553.4	562.0	572.8	584.9	595.8	605.6	615.3	620.9
165°	528.3	534.5	543.9	551.1	557.3	564.5	573.9	582.2	589.4	596.6	600.8
167.5°	532.9	536.8	543.6	549.7	552.5	557.3	563.1	569.1	574.7	579.7	583.4
170°	534.5	537.6	542.8	548.0	550.0	553.1	557.3	562.5	565.6	569.7	571.8
172.5°	536.2	538.4	542.0	545.5	546.7	548.2	551.5	555.0	557.3	560.6	561.9
175°	537.6	538.7	540.7	542.8	541.8	542.8	543.9	547.0	548.0	549.0	550.0
177.5°	538.7	538.7	539.5	541.2	539.5	538.7	539.5	541.2	541.2	542.0	542.0
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	920.2	920.8	920.0	920.5	920.0	920.8	920.2	923.2	923.7	924.3	923.7
5°	857.5	853.5	852.8	851.9	852.8	853.5	857.5	859.2	860.5	863.1	867.8
7.5°	782.5	781.9	780.2	777.8	780.2	781.9	782.5	788.2	792.7	797.9	807.4
10°	734.2	732.6	732.3	730.0	732.3	732.6	734.2	741.5	746.9	754.2	767.2
12.5°	677.8	667.1	665.9	660.1	665.9	667.1	677.8	687.2	701.6	708.6	722.5
15°	577.1	575.1	568.5	564.1	568.5	575.1	577.1	585.1	590.4	609.8	632.0
17.5°	519.5	513.0	511.0	510.1	511.0	513.0	519.5	523.4	531.0	541.2	554.6
20°	482.5	476.5	475.5	474.8	475.5	476.5	482.5	487.1	493.2	504.2	518.2
22.5°	456.9	450.7	448.1	446.1	448.1	450.7	456.9	460.6	466.0	474.6	484.0
25°	413.2	410.9	409.6	408.9	409.6	410.9	413.2	416.6	421.9	433.5	443.5
27.5°	379.1	374.0	372.9	371.2	372.9	374.0	379.1	385.0	390.6	395.8	404.7
30°	359.6	357.9	355.6	353.7	355.6	357.9	359.6	362.7	366.3	375.3	384.0
32.5°	336.7	335.4	333.2	332.3	333.2	335.4	336.7	340.8	348.5	354.0	360.3
35°	311.4	306.7	304.7	301.7	304.7	306.7	311.4	314.7	317.7	322.4	333.7
37.5°	284.5	282.0	279.3	280.3	279.3	282.0	284.5	285.9	292.2	298.7	303.6
40°	263.8	262.1	261.4	261.1	261.4	262.1	263.8	268.0	275.7	278.7	286.1
42.5°	247.2	242.6	240.9	240.9	240.9	242.6	247.2	252.1	256.8	261.6	269.3
45°	222.1	217.8	214.8	215.1	214.8	217.8	222.1	223.7	227.7	237.5	241.7
47.5°	196.4	196.3	194.4	195.0	194.4	196.3	196.4	199.3	204.4	210.4	217.2
50°	184.1	182.2	180.8	181.1	180.8	182.2	184.1	186.5	189.5	192.4	203.1
52.5°	172.5	170.7	169.6	171.0	169.6	170.7	172.5	173.7	175.8	178.9	186.1
55°	153.2	151.1	150.9	150.5	150.9	151.1	153.2	154.8	157.5	159.8	163.2
57.5°	131.7	130.4	128.3	127.5	128.3	130.4	131.7	134.1	137.3	140.4	143.8
60°	116.2	113.5	110.2	109.9	110.2	113.5	116.2	120.6	121.9	126.5	130.5
62.5°	102.1	101.6	100.9	100.9	100.9	101.6	102.1	103.5	105.4	112.2	117.0
65°	89.6	89.3	89.6	89.9	89.6	89.3	89.6	90.2	90.6	91.2	93.3
67.5°	78.0	77.5	76.9	77.1	76.9	77.5	78.0	78.2	79.1	79.5	80.9
70°	69.3	68.9	68.6	68.6	68.6	68.9	69.3	69.9	70.6	71.2	72.9
72.5°	60.7	60.6	60.4	60.1	60.4	60.6	60.7	62.0	62.3	63.0	64.1
75°	48.6	48.0	48.0	48.0	48.0	48.0	48.6	49.0	49.3	50.3	50.9
77.5°	37.0	36.7	36.4	36.1	36.4	36.7	37.0	37.1	37.6	37.8	38.5
80°	29.3	29.0	28.6	28.6	28.6	29.0	29.3	29.6	29.6	30.7	30.3
82.5°	22.4	22.0	21.9	21.7	21.9	22.0	22.4	22.5	22.5	23.2	23.1
85°	11.9	12.3	11.9	12.7	11.9	12.3	11.9	11.7	11.9	12.7	12.7
87.5°	10.3	10.1	10.3	10.1	10.3	10.1	10.3	10.3	10.3	10.0	10.3
90°	34.2	34.2	34.2	34.2	34.2	34.2	34.2	34.2	33.2	31.1	33.2
92.5°	61.5	58.2	59.0	57.4	59.0	58.2	61.5	62.3	68.8	77.5	90.3
95°	128.4	120.2	117.1	118.1	117.1	120.2	128.4	141.9	164.7	208.2	271.4
97.5°	281.8	256.3	241.1	232.5	241.1	256.3	281.8	331.3	406.1	518.2	633.3
100°	464.0	419.5	389.5	370.9	389.5	419.5	464.0	550.0	675.4	817.3	945.7
102.5°	791.4	715.4	677.9	652.6	677.9	715.4	791.4	884.8	1017.6	1121.4	1150.5
105°	1290.7	1226.5	1182.0	1167.4	1182.0	1226.5	1290.7	1355.0	1389.1	1375.6	1258.6
107.5°	1523.0	1519.4	1510.5	1491.2	1510.5	1519.4	1523.0	1514.8	1464.7	1357.0	1180.7
110°	1561.0	1580.7	1590.1	1589.0	1590.1	1580.7	1561.0	1516.5	1431.6	1299.0	1113.6



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1531.2	1564.1	1581.8	1587.3	1581.8	1564.1	1531.2	1469.3	1371.9	1230.2	1052.2
115°	1452.3	1499.9	1526.9	1536.2	1526.9	1499.9	1452.3	1378.8	1272.0	1136.4	976.9
117.5°	1358.3	1408.5	1437.0	1444.8	1437.0	1408.5	1358.3	1283.3	1183.2	1060.2	920.1
120°	1296.9	1345.6	1375.6	1386.0	1375.6	1345.6	1296.9	1224.4	1130.2	1020.3	891.9
122.5°	1241.4	1289.2	1316.0	1324.6	1316.0	1289.2	1241.4	1176.3	1091.2	987.2	869.5
125°	1172.6	1212.0	1237.9	1246.2	1237.9	1212.0	1172.6	1112.5	1034.8	943.7	837.0
127.5°	1111.5	1148.3	1170.7	1177.4	1170.7	1148.3	1111.5	1059.1	987.4	901.4	804.9
130°	1074.2	1109.5	1130.2	1138.4	1130.2	1109.5	1074.2	1023.4	955.1	873.3	784.2
132.5°	1036.1	1071.3	1090.4	1097.8	1090.4	1071.3	1036.1	986.1	921.9	846.8	764.3
135°	975.8	1010.0	1028.6	1032.8	1028.6	1010.0	975.8	931.2	873.3	804.9	736.5
137.5°	916.9	946.4	962.8	968.9	962.8	946.4	916.9	876.4	825.8	771.5	714.3
140°	876.4	903.3	918.8	925.1	918.8	903.3	876.4	843.2	797.6	750.0	700.3
142.5°	841.5	866.0	879.9	881.1	879.9	866.0	841.5	810.0	772.0	730.9	688.7
145°	793.4	811.1	821.4	824.6	821.4	811.1	793.4	768.7	738.6	706.5	672.3
147.5°	754.1	768.2	775.3	777.1	775.3	768.2	754.1	733.6	711.7	686.6	659.7
150°	729.2	741.7	747.9	748.9	747.9	741.7	729.2	713.7	695.1	673.3	650.5
152.5°	709.4	720.1	724.7	724.9	724.7	720.1	709.4	697.1	681.0	662.5	641.4
155°	683.7	690.9	695.1	693.0	695.1	690.9	683.7	672.3	660.8	645.3	628.7
157.5°	658.0	664.0	665.8	665.8	665.8	664.0	658.0	649.9	641.0	627.9	614.0
160°	642.2	647.4	648.5	648.5	648.5	647.4	642.2	635.0	627.8	616.4	604.9
162.5°	628.1	631.7	632.7	631.9	632.7	631.7	628.1	620.9	615.3	605.6	595.8
165°	604.9	609.1	609.1	608.1	609.1	609.1	604.9	600.8	596.6	589.4	582.2
167.5°	585.2	587.5	587.4	586.1	587.4	587.5	585.2	583.4	579.7	574.7	569.1
170°	572.8	576.0	574.9	572.8	574.9	576.0	572.8	571.8	569.7	565.6	562.5
172.5°	562.9	564.4	563.3	562.0	563.3	564.4	562.9	561.9	560.6	557.3	555.0
175°	550.0	551.1	550.0	548.0	550.0	551.1	550.0	550.0	549.0	548.0	547.0
177.5°	542.0	542.0	541.2	539.5	541.2	542.0	542.0	542.0	542.0	541.2	541.2
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	921.6	925.3	930.9	934.2	939.4	942.9	944.8	948.2	950.1	956.8	963.7
5°	870.1	875.5	884.8	893.4	902.8	912.4	919.4	927.4	934.7	947.4	960.7
7.5°	811.1	818.5	832.9	846.8	863.0	876.6	888.7	902.3	914.5	932.6	951.5
10°	766.9	779.9	798.9	811.8	833.1	846.8	865.8	880.7	897.8	921.8	943.1
12.5°	728.8	744.5	759.7	777.8	796.9	819.7	840.5	859.7	879.9	904.7	929.7
15°	659.7	682.3	706.0	724.2	750.3	774.2	798.5	824.5	849.2	878.8	911.4
17.5°	570.7	596.9	636.7	668.1	698.6	722.6	752.7	784.2	813.2	848.9	885.2
20°	530.5	549.7	576.8	619.0	665.0	690.6	721.3	755.9	789.2	828.1	867.1
22.5°	498.2	515.4	537.1	570.0	621.3	656.3	688.2	723.4	762.1	801.8	845.0
25°	452.2	464.2	486.9	513.4	548.8	606.4	641.3	676.6	718.6	761.3	810.5
27.5°	417.7	428.5	443.2	468.6	494.8	536.2	591.8	630.3	672.1	720.1	771.2
30°	391.3	403.9	420.3	438.2	466.9	499.2	554.7	599.4	640.7	690.0	744.6
32.5°	372.1	382.1	396.0	414.3	438.1	469.0	513.4	567.7	607.9	659.9	716.8
35°	340.6	352.3	363.6	380.9	400.3	428.6	462.2	520.1	560.1	611.4	668.7
37.5°	314.8	321.9	334.4	348.1	368.5	389.6	418.7	470.7	514.0	564.3	622.9
40°	295.1	304.0	313.3	328.7	345.4	365.6	394.2	432.9	482.5	531.8	589.1
42.5°	275.9	287.2	297.1	307.4	325.6	345.9	369.3	402.0	452.6	499.3	555.0
45°	252.7	260.1	270.4	281.7	296.7	314.1	334.7	363.3	411.9	452.2	504.5
47.5°	225.9	236.6	243.3	254.3	268.6	285.1	304.3	329.0	368.5	406.2	454.7
50°	207.5	218.5	228.1	238.1	250.7	266.7	282.7	306.7	338.3	378.0	423.2
52.5°	191.7	201.4	210.8	220.8	233.2	247.8	263.0	284.0	311.1	347.6	391.6
55°	170.1	176.1	185.8	195.8	206.8	220.8	235.4	253.1	276.4	307.0	342.7
57.5°	148.0	155.0	162.6	172.7	183.8	194.6	207.7	223.7	242.1	269.8	300.3
60°	135.5	140.9	147.2	157.5	167.8	177.5	190.1	203.5	220.8	244.8	270.7
62.5°	121.7	126.7	132.5	141.5	151.6	160.4	171.5	185.7	200.3	222.1	244.9
65°	98.5	105.9	111.6	119.6	127.9	137.2	145.9	157.2	170.1	187.4	207.8
67.5°	81.7	85.4	90.7	98.0	106.5	114.5	122.7	131.5	142.8	156.1	172.3
70°	74.3	75.6	76.6	83.6	91.6	99.6	107.2	115.6	125.2	136.2	150.2
72.5°	65.5	66.8	68.0	71.1	77.5	85.4	93.4	99.6	108.7	117.8	129.1
75°	52.0	53.9	54.9	56.6	58.9	64.3	71.6	77.6	82.9	89.9	98.9
77.5°	39.6	40.7	41.7	43.5	44.9	47.4	51.5	57.0	62.0	66.0	72.2
80°	31.3	31.7	33.0	33.6	35.7	37.3	39.3	43.6	48.6	50.3	54.6
82.5°	23.5	23.9	25.0	25.7	26.6	28.0	30.5	31.7	35.6	37.7	40.5
85°	13.0	12.7	13.6	13.6	14.4	15.0	15.7	17.3	18.3	21.0	21.7
87.5°	10.8	11.1	11.1	9.9	8.4	7.9	7.6	7.4	7.5	7.5	7.9
90°	34.2	35.2	34.2	28.0	20.7	15.5	12.4	10.3	8.3	4.1	1.1
92.5°	113.8	134.6	132.8	103.3	70.4	47.0	37.3	30.2	25.7	18.2	12.7
95°	355.3	406.1	359.4	239.2	149.2	101.5	76.7	60.1	50.7	40.4	36.3
97.5°	727.2	693.2	522.1	322.4	196.8	137.0	108.8	89.7	75.6	64.6	59.0
100°	967.5	818.3	563.5	339.7	213.4	158.5	129.5	108.8	92.2	82.8	79.7
102.5°	1057.0	822.5	547.8	340.6	228.3	177.5	148.6	127.0	110.4	101.1	98.8
105°	1043.1	767.6	516.9	346.0	253.8	205.1	176.1	153.3	137.8	130.5	126.4
107.5°	952.2	708.7	501.6	360.3	279.9	232.6	203.5	180.8	166.6	159.5	156.2
110°	895.0	680.6	498.3	371.8	297.3	251.7	221.7	199.9	186.5	180.2	176.1



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	855.2	662.4	499.1	384.3	313.9	269.9	239.1	218.1	205.5	198.5	194.3
115°	805.9	642.2	503.5	403.0	339.7	295.2	267.2	246.6	234.1	227.9	222.7
117.5°	774.8	632.5	510.9	422.8	363.6	322.4	293.4	273.5	262.5	256.3	252.2
120°	758.2	626.7	515.9	436.1	380.1	339.7	310.8	290.1	280.7	274.5	270.4
122.5°	744.1	623.4	521.7	447.7	395.9	358.0	328.1	307.5	297.3	291.1	287.8
125°	724.1	617.4	530.4	466.2	419.5	382.3	353.2	332.5	320.1	313.9	310.8
127.5°	705.4	613.9	539.3	483.3	441.5	405.2	375.4	355.5	341.9	333.1	329.0
130°	693.0	612.2	545.9	494.1	454.8	418.5	389.5	368.8	354.3	343.9	339.7
132.5°	683.1	611.4	552.5	504.9	466.4	431.8	402.8	381.2	365.9	354.7	349.7
135°	669.1	610.1	560.4	519.0	482.7	449.6	420.5	396.7	381.2	368.8	364.6
137.5°	659.4	609.9	567.5	529.8	496.0	463.2	436.3	412.7	396.1	383.7	378.7
140°	653.6	609.1	570.8	535.6	503.5	472.3	445.4	422.7	406.1	393.6	389.5
142.5°	647.8	609.1	573.3	540.6	509.3	479.0	453.7	431.8	415.2	403.6	400.3
145°	640.2	607.0	576.0	547.0	517.9	490.0	467.2	446.5	431.0	420.5	416.4
147.5°	632.3	603.3	576.8	550.5	525.0	498.6	478.4	461.2	446.8	436.9	433.8
150°	625.6	600.8	576.0	552.1	528.3	504.4	485.8	470.3	456.8	448.5	445.4
152.5°	619.8	596.6	574.3	552.9	531.6	510.2	493.3	478.6	466.7	458.5	457.0
155°	609.1	589.4	571.8	554.2	536.5	519.0	503.5	492.0	480.6	474.4	473.4
157.5°	599.0	581.9	567.0	554.2	540.1	525.2	512.1	503.0	493.1	488.1	487.1
160°	591.5	577.0	564.5	554.2	541.8	529.3	517.9	509.6	501.3	497.2	496.1
162.5°	584.9	572.8	562.0	553.4	542.6	531.8	522.9	515.4	508.8	504.7	505.3
165°	573.9	564.5	557.3	551.1	543.9	534.5	528.3	523.1	516.9	514.9	515.9
167.5°	563.1	557.3	552.5	549.7	543.6	536.8	532.9	529.1	525.2	523.3	524.6
170°	557.3	553.1	550.0	548.0	542.8	537.6	534.5	532.4	529.3	528.3	530.4
172.5°	551.5	548.2	546.7	545.5	542.0	538.4	536.2	534.9	531.8	532.4	533.7
175°	543.9	542.8	541.8	542.8	540.7	538.7	537.6	537.6	535.6	536.5	537.6
177.5°	539.5	538.7	539.5	541.2	539.5	538.7	538.7	538.7	537.0	537.8	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	963.9	964.7	970.1	972.5	977.3	979.2	981.2	980.7	980.7	981.8	989.3
5°	966.0	972.7	982.7	992.3	1001.7	1009.7	1014.9	1020.3	1022.3	1032.0	1040.6
7.5°	962.6	974.8	991.3	1006.0	1023.7	1037.5	1048.9	1059.3	1066.3	1080.4	1094.8
10°	958.1	975.4	994.0	1013.0	1037.3	1055.6	1074.2	1088.6	1093.2	1114.2	1126.2
12.5°	949.0	972.1	995.9	1020.5	1044.2	1069.4	1089.9	1104.3	1120.7	1139.5	1161.6
15°	935.4	962.1	993.0	1024.7	1058.6	1089.2	1111.3	1136.2	1154.1	1174.8	1194.1
17.5°	915.9	950.2	989.5	1026.2	1065.4	1098.3	1128.6	1152.5	1165.2	1177.0	1179.9
20°	900.4	937.4	983.6	1027.0	1066.2	1104.2	1134.2	1154.1	1157.5	1157.8	1140.1
22.5°	883.7	925.4	973.8	1018.2	1065.1	1107.4	1130.7	1139.2	1126.1	1103.5	1069.3
25°	852.8	901.1	957.3	1008.0	1059.3	1099.2	1107.2	1092.3	1046.0	997.3	935.8
27.5°	819.4	873.6	934.0	990.2	1044.9	1069.7	1052.4	998.4	915.0	842.6	754.7
30°	794.9	855.8	915.1	978.0	1028.6	1039.3	999.7	920.1	822.9	713.6	626.1
32.5°	766.9	830.7	895.9	961.0	1003.4	992.9	927.5	829.5	715.5	608.1	525.3
35°	726.9	792.9	863.1	928.4	955.4	910.4	812.5	685.0	568.5	468.2	411.3
37.5°	680.8	752.6	825.6	885.6	883.7	808.7	675.4	543.7	445.8	386.5	345.9
40°	648.0	720.6	799.5	850.2	828.5	730.9	586.4	462.2	390.6	343.3	313.7
42.5°	616.6	689.5	767.9	808.1	770.4	650.5	506.5	409.2	350.1	313.3	289.2
45°	563.1	640.0	712.7	734.9	667.6	535.5	409.6	339.0	299.7	272.4	255.7
47.5°	510.9	586.5	652.7	653.2	562.1	434.3	345.5	293.4	259.8	238.7	226.6
50°	478.8	550.8	606.4	597.7	494.5	386.3	309.0	264.0	236.1	219.8	207.1
52.5°	442.9	512.6	560.8	536.2	437.2	339.9	276.3	238.5	215.3	201.2	189.8
55°	390.6	452.5	486.5	449.2	356.7	282.7	233.4	203.8	186.5	174.5	164.9
57.5°	339.3	390.3	411.7	368.3	293.7	234.4	197.4	175.2	158.0	149.5	144.5
60°	307.0	350.6	365.6	317.7	255.4	205.1	174.9	154.2	141.5	135.9	130.9
62.5°	275.4	310.9	317.2	273.2	222.7	179.6	153.6	136.1	127.7	122.3	117.5
65°	228.5	254.0	251.1	215.8	176.1	142.5	123.5	112.9	106.6	98.9	90.6
67.5°	188.1	203.8	194.3	167.8	134.5	110.8	98.4	90.3	82.5	75.2	73.3
70°	162.5	171.5	161.5	137.2	110.2	92.9	82.9	73.3	68.6	67.0	63.9
72.5°	138.0	141.2	130.4	109.5	89.7	77.0	67.2	61.8	59.3	57.9	55.9
75°	103.5	101.2	91.9	75.6	62.2	53.6	50.6	48.6	47.0	45.7	44.6
77.5°	72.8	69.3	61.0	50.4	43.3	39.2	37.5	36.4	35.6	34.9	33.9
80°	54.6	52.3	44.0	35.9	33.0	30.9	30.0	28.6	28.6	28.0	26.9
82.5°	39.9	37.4	30.1	26.4	24.7	23.5	22.7	21.9	21.7	21.8	21.1
85°	21.0	16.9	15.0	14.4	13.3	12.7	13.0	12.3	12.3	12.3	11.9
87.5°	7.2	6.7	6.9	7.0	7.9	8.9	10.2	11.3	11.9	11.3	11.4
90°	4.1	8.3	10.3	12.4	15.5	20.7	28.0	34.2	35.2	34.2	33.2
92.5°	18.2	25.7	30.2	37.3	47.0	70.4	103.3	132.8	134.6	113.8	90.3
95°	40.4	50.7	60.1	76.7	101.5	149.2	239.2	359.4	406.1	355.3	271.4
97.5°	64.6	75.6	89.7	108.8	137.0	196.8	322.4	522.1	693.2	727.2	633.3
100°	82.8	92.2	108.8	129.5	158.5	213.4	339.7	563.5	818.3	967.5	945.7
102.5°	101.1	110.4	127.0	148.6	177.5	228.3	340.6	547.8	822.5	1057.0	1150.5
105°	130.5	137.8	153.3	176.1	205.1	253.8	346.0	516.9	767.6	1043.1	1258.6
107.5°	159.5	166.6	180.8	203.5	232.6	279.9	360.3	501.6	708.7	952.2	1180.7
110°	180.2	186.5	199.9	221.7	251.7	297.3	371.8	498.3	680.6	895.0	1113.6



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	198.5	205.5	218.1	239.1	269.9	313.9	384.3	499.1	662.4	855.2	1052.2
115°	227.9	234.1	246.6	267.2	295.2	339.7	403.0	503.5	642.2	805.9	976.9
117.5°	256.3	262.5	273.5	293.4	322.4	363.6	422.8	510.9	632.5	774.8	920.1
120°	274.5	280.7	290.1	310.8	339.7	380.1	436.1	515.9	626.7	758.2	891.9
122.5°	291.1	297.3	307.5	328.1	358.0	395.9	447.7	521.7	623.4	744.1	869.5
125°	313.9	320.1	332.5	353.2	382.3	419.5	466.2	530.4	617.4	724.1	837.0
127.5°	333.1	341.9	355.5	375.4	405.2	441.5	483.3	539.3	613.9	705.4	804.9
130°	343.9	354.3	368.8	389.5	418.5	454.8	494.1	545.9	612.2	693.0	784.2
132.5°	354.7	365.9	381.2	402.8	431.8	466.4	504.9	552.5	611.4	683.1	764.3
135°	368.8	381.2	396.7	420.5	449.6	482.7	519.0	560.4	610.1	669.1	736.5
137.5°	383.7	396.1	412.7	436.3	463.2	496.0	529.8	567.5	609.9	659.4	714.3
140°	393.6	406.1	422.7	445.4	472.3	503.5	535.6	570.8	609.1	653.6	700.3
142.5°	403.6	415.2	431.8	453.7	479.0	509.3	540.6	573.3	609.1	647.8	688.7
145°	420.5	431.0	446.5	467.2	490.0	517.9	547.0	576.0	607.0	640.2	672.3
147.5°	436.9	446.8	461.2	478.4	498.6	525.0	550.5	576.8	603.3	632.3	659.7
150°	448.5	456.8	470.3	485.8	504.4	528.3	552.1	576.0	600.8	625.6	650.5
152.5°	458.5	466.7	478.6	493.3	510.2	531.6	552.9	574.3	596.6	619.8	641.4
155°	474.4	480.6	492.0	503.5	519.0	536.5	554.2	571.8	589.4	609.1	628.7
157.5°	488.1	493.1	503.0	512.1	525.2	540.1	554.2	567.0	581.9	599.0	614.0
160°	497.2	501.3	509.6	517.9	529.3	541.8	554.2	564.5	577.0	591.5	604.9
162.5°	504.7	508.8	515.4	522.9	531.8	542.6	553.4	562.0	572.8	584.9	595.8
165°	514.9	516.9	523.1	528.3	534.5	543.9	551.1	557.3	564.5	573.9	582.2
167.5°	523.3	525.2	529.1	532.9	536.8	543.6	549.7	552.5	557.3	563.1	569.1
170°	528.3	529.3	532.4	534.5	537.6	542.8	548.0	550.0	553.1	557.3	562.5
172.5°	532.4	531.8	534.9	536.2	538.4	542.0	545.5	546.7	548.2	551.5	555.0
175°	536.5	535.6	537.6	537.6	538.7	540.7	542.8	541.8	542.8	543.9	547.0
177.5°	537.8	537.0	538.7	538.7	538.7	539.5	541.2	539.5	538.7	539.5	541.2
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7	538.7



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	958.4	958.4	958.4	958.4	958.4	958.4	958.4
2.5°	991.9	995.4	997.0	997.0	998.9	998.1	997.3
5°	1048.9	1055.3	1056.6	1062.6	1066.9	1065.6	1066.2
7.5°	1105.6	1115.8	1125.9	1130.4	1131.2	1133.9	1134.9
10°	1140.5	1148.9	1164.5	1162.2	1173.8	1180.4	1169.5
12.5°	1174.1	1185.4	1196.2	1199.2	1205.8	1207.9	1203.5
15°	1204.4	1210.4	1211.1	1209.4	1211.5	1209.8	1203.5
17.5°	1176.1	1166.4	1146.7	1137.3	1129.9	1119.0	1114.6
20°	1129.2	1100.5	1067.3	1053.9	1038.3	1007.6	1014.9
22.5°	1028.0	995.3	962.1	923.1	904.6	875.5	873.8
25°	870.5	814.2	752.2	708.9	683.7	654.7	642.0
27.5°	676.8	605.9	555.2	529.5	506.0	483.1	482.1
30°	549.5	496.1	456.9	434.9	420.6	410.9	413.0
32.5°	463.2	426.6	400.1	381.9	371.3	364.0	363.9
35°	378.6	353.7	336.6	329.0	321.4	316.0	316.4
37.5°	324.0	309.0	299.5	291.1	286.3	283.7	282.2
40°	296.0	283.7	276.4	271.4	267.4	263.8	263.1
42.5°	273.9	263.8	256.4	252.4	248.8	246.1	245.5
45°	243.1	234.8	228.1	223.7	222.1	219.8	219.8
47.5°	216.2	208.0	202.9	200.1	197.2	195.7	195.6
50°	198.1	191.8	187.2	185.5	183.2	182.2	181.8
52.5°	181.9	177.2	173.8	172.7	171.7	170.4	170.6
55°	159.8	157.2	155.9	154.8	153.2	151.1	152.5
57.5°	141.2	139.0	135.4	132.2	130.7	129.3	129.8
60°	128.2	123.5	118.9	115.2	114.2	111.2	111.2
62.5°	111.7	105.1	99.4	97.4	96.4	95.0	94.7
65°	85.9	83.3	81.9	80.6	79.9	79.9	79.3
67.5°	71.2	70.1	68.7	68.3	67.7	67.5	67.2
70°	63.0	61.6	60.9	60.6	59.9	60.3	59.3
72.5°	54.9	53.9	53.8	52.9	52.5	52.5	51.8
75°	43.2	43.2	43.0	42.6	42.0	41.6	42.0
77.5°	33.3	33.3	32.7	32.7	32.6	32.7	32.4
80°	26.7	26.9	26.7	26.3	25.9	26.3	25.9
82.5°	21.0	20.6	20.5	20.4	20.4	20.2	20.2
85°	11.9	12.3	11.9	11.7	11.7	11.7	11.9
87.5°	10.7	11.1	11.3	11.3	11.3	11.3	11.1
90°	31.1	33.2	34.2	34.2	34.2	34.2	34.2
92.5°	77.5	68.8	62.3	61.5	58.2	59.0	57.4
95°	208.2	164.7	141.9	128.4	120.2	117.1	118.1
97.5°	518.2	406.1	331.3	281.8	256.3	241.1	232.5
100°	817.3	675.4	550.0	464.0	419.5	389.5	370.9
102.5°	1121.4	1017.6	884.8	791.4	715.4	677.9	652.6
105°	1375.6	1389.1	1355.0	1290.7	1226.5	1182.0	1167.4
107.5°	1357.0	1464.7	1514.8	1523.0	1519.4	1510.5	1491.2
110°	1299.0	1431.6	1516.5	1561.0	1580.7	1590.1	1589.0



TEST NUMBER: P331671-940

CATALOG NUMBER: S122RDIP-S485D1080U940-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1230.2	1371.9	1469.3	1531.2	1564.1	1581.8	1587.3
115°	1136.4	1272.0	1378.8	1452.3	1499.9	1526.9	1536.2
117.5°	1060.2	1183.2	1283.3	1358.3	1408.5	1437.0	1444.8
120°	1020.3	1130.2	1224.4	1296.9	1345.6	1375.6	1386.0
122.5°	987.2	1091.2	1176.3	1241.4	1289.2	1316.0	1324.6
125°	943.7	1034.8	1112.5	1172.6	1212.0	1237.9	1246.2
127.5°	901.4	987.4	1059.1	1111.5	1148.3	1170.7	1177.4
130°	873.3	955.1	1023.4	1074.2	1109.5	1130.2	1138.4
132.5°	846.8	921.9	986.1	1036.1	1071.3	1090.4	1097.8
135°	804.9	873.3	931.2	975.8	1010.0	1028.6	1032.8
137.5°	771.5	825.8	876.4	916.9	946.4	962.8	968.9
140°	750.0	797.6	843.2	876.4	903.3	918.8	925.1
142.5°	730.9	772.0	810.0	841.5	866.0	879.9	881.1
145°	706.5	738.6	768.7	793.4	811.1	821.4	824.6
147.5°	686.6	711.7	733.6	754.1	768.2	775.3	777.1
150°	673.3	695.1	713.7	729.2	741.7	747.9	748.9
152.5°	662.5	681.0	697.1	709.4	720.1	724.7	724.9
155°	645.3	660.8	672.3	683.7	690.9	695.1	693.0
157.5°	627.9	641.0	649.9	658.0	664.0	665.8	665.8
160°	616.4	627.8	635.0	642.2	647.4	648.5	648.5
162.5°	605.6	615.3	620.9	628.1	631.7	632.7	631.9
165°	589.4	596.6	600.8	604.9	609.1	609.1	608.1
167.5°	574.7	579.7	583.4	585.2	587.5	587.4	586.1
170°	565.6	569.7	571.8	572.8	576.0	574.9	572.8
172.5°	557.3	560.6	561.9	562.9	564.4	563.3	562.0
175°	548.0	549.0	550.0	550.0	551.1	550.0	548.0
177.5°	541.2	542.0	542.0	542.0	542.0	541.2	539.5
180°	538.7	538.7	538.7	538.7	538.7	538.7	538.7

(END OF REPORT)