

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331867-927

Luminaire Tested: **S123DIP-S340D365U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331867-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S340D365U927-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2191.2 lumens  
Efficiency: N/A  
Efficacy: 107.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	42	38
3	82	73	66	60	76	68	62	56	58	53	50	49	46	43	41	39	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	23	28	23	20	23	20	18	15
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4100	4100	4100	4100
5°	4889	4118	3649	4118
10°	6120	4098	3296	4098
15°	7506	4063	3069	4063
20°	8942	4013	2922	4013
25°	9495	3950	2888	3950
30°	8139	3904	2903	3904
35°	5660	3840	2934	3840
40°	4263	3763	2925	3763
45°	3539	3649	2888	3649
50°	3170	3418	2862	3418
55°	2965	3170	2826	3170
60°	2781	2908	2796	2908
65°	2613	2651	2707	2651
70°	2452	2357	2578	2357
75°	2196	2067	2366	2067
80°	1922	1692	2039	1692
85°	1507	1235	1371	1235



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.5	1.7
10°-20°	120.3	5.5
20°-30°	201.9	9.2
30°-40°	228.6	10.4
40°-50°	205.0	9.4
50°-60°	165.5	7.6
60°-70°	115.3	5.3
70°-80°	60.6	2.8
80°-90°	15.9	0.7
90°-100°	77.0	3.5
100°-110°	217.9	9.9
110°-120°	214.4	9.8
120°-130°	171.0	7.8
130°-140°	134.8	6.2
140°-150°	100.6	4.6
150°-160°	70.1	3.2
160°-170°	41.2	1.9
170°-180°	13.4	0.6
0°-30°	359.8	16.4
0°-40°	588.4	26.9
0°-60°	958.9	43.8
0°-90°	1150.7	52.5
90°-120°	509.3	23.2
90°-150°	915.7	41.8
90°-180°	1040.0	47.5
0°-180°	2191.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	381	381	381	381	381	
5°	452	381	338	381	452	47
15°	674	365	275	365	674	194
25°	800	333	243	333	800	351
35°	431	292	223	292	431	280
45°	232	240	190	240	232	184
55°	158	169	151	169	158	142
65°	103	104	106	104	103	102
75°	53	50	57	50	53	56
85°	12	10	11	10	12	15
90°	8	1	8	1	8	5
95°	32	10	32	10	32	59
105°	356	32	356	32	356	351
115°	433	57	433	57	433	421
125°	342	80	342	80	342	309
135°	277	94	277	94	277	215
145°	216	107	216	107	216	138
155°	179	121	179	121	179	84
165°	156	132	156	132	156	45
175°	141	138	141	138	141	14
180°	138	138	138	138	138	



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	404.3	403.9	403.2	403.8	402.6	401.0	400.8	399.3	395.1	394.8	393.6
5°	452.5	451.1	450.8	450.7	448.1	444.6	437.9	437.4	428.5	424.1	418.7
7.5°	515.1	515.8	513.1	510.8	502.9	497.6	490.5	481.4	470.6	459.5	452.2
10°	559.9	566.0	558.5	553.3	548.5	539.5	528.9	515.8	502.7	487.4	475.8
12.5°	608.1	611.0	609.5	604.7	597.2	583.4	564.8	550.3	538.3	512.8	502.5
15°	673.6	684.8	677.6	661.1	661.4	648.3	624.0	597.2	583.0	560.6	530.2
17.5°	743.5	744.8	741.8	727.9	718.7	700.7	678.2	652.6	623.8	596.8	564.4
20°	780.6	779.5	773.1	765.9	750.0	736.0	711.5	682.9	645.9	619.3	584.1
22.5°	801.3	799.5	796.4	790.4	777.2	762.2	740.1	708.8	673.7	637.1	596.4
25°	799.5	801.8	802.2	800.6	796.0	787.0	769.6	744.7	709.6	662.5	620.1
27.5°	727.1	730.6	740.4	749.2	758.9	768.9	767.5	755.2	729.2	688.6	636.7
30°	654.8	647.4	665.7	688.7	704.4	732.1	747.6	748.5	734.0	699.1	648.5
32.5°	554.4	562.5	570.6	599.0	633.3	664.3	695.2	720.0	722.9	699.7	655.5
35°	430.7	440.9	455.7	470.4	507.3	539.1	593.3	640.6	678.2	683.2	656.1
37.5°	347.1	352.1	361.5	376.3	400.4	438.1	480.0	539.7	594.3	634.9	636.6
40°	303.4	304.9	315.4	326.6	346.2	377.2	415.0	467.9	533.1	589.9	613.5
42.5°	270.6	273.9	278.4	289.1	304.8	328.0	363.2	406.9	466.8	532.0	578.1
45°	232.5	236.2	239.0	246.2	257.3	273.0	297.5	337.4	382.9	450.3	512.5
47.5°	207.4	207.6	209.7	215.2	222.7	234.5	251.8	277.4	319.2	373.9	437.8
50°	189.3	192.3	193.1	197.3	203.2	211.8	226.2	248.0	282.3	330.3	389.0
52.5°	176.7	177.5	179.6	182.7	187.8	194.6	207.1	224.1	251.0	292.0	345.9
55°	158.0	158.0	160.0	162.4	165.3	171.4	179.7	192.3	212.8	244.5	289.2
57.5°	140.7	141.6	143.1	143.8	146.3	150.4	157.2	166.8	182.0	206.5	242.0
60°	129.2	130.9	130.6	132.1	134.4	137.5	143.4	151.1	164.8	184.3	214.3
62.5°	119.1	119.1	119.0	120.8	122.9	126.0	129.8	136.5	148.1	165.5	190.9
65°	102.6	102.3	103.5	104.6	105.4	107.6	110.5	116.5	124.2	137.1	156.9
67.5°	87.9	86.8	87.5	87.9	89.2	90.9	93.7	97.4	103.5	113.8	128.7
70°	77.9	76.9	76.8	77.2	78.3	79.5	81.6	85.1	90.8	99.1	110.0
72.5°	67.6	66.9	66.9	67.7	68.2	69.1	70.5	73.7	78.3	84.5	94.7
75°	52.8	52.8	52.8	53.0	53.6	54.3	55.4	57.0	60.5	65.0	71.8
77.5°	39.5	39.5	39.3	39.3	40.1	40.4	40.6	42.2	44.2	47.1	52.1
80°	31.0	30.1	30.4	31.0	31.4	31.5	32.1	32.5	34.1	35.8	39.3
82.5°	23.1	22.3	22.3	23.2	23.3	23.4	24.0	24.5	25.1	26.6	28.5
85°	12.2	12.2	12.4	12.4	12.5	12.4	12.9	13.1	13.1	14.0	15.1
87.5°	6.0	5.8	5.9	6.0	5.9	5.9	6.0	6.1	6.2	6.4	6.4
90°	8.1	8.4	8.1	7.8	8.1	7.5	7.3	7.0	6.7	7.0	6.2
92.5°	13.5	14.0	13.7	14.6	15.1	16.5	18.7	23.6	32.5	43.0	47.4
95°	32.5	33.6	35.6	38.1	43.4	53.5	68.3	100.8	134.7	166.0	147.8
97.5°	88.4	90.8	98.4	111.0	131.7	165.1	201.2	251.2	275.2	257.3	188.4
100°	175.5	175.2	186.2	206.6	234.9	274.6	307.4	330.0	320.3	265.1	179.2
102.5°	257.5	264.0	273.1	289.2	311.2	336.4	355.5	356.2	322.5	250.6	165.7
105°	356.1	357.5	366.5	377.1	390.0	397.2	391.9	363.9	305.4	225.1	149.2
107.5°	412.9	415.4	418.4	422.1	421.8	411.9	387.3	341.8	275.5	202.6	138.7
110°	436.2	436.7	437.3	435.1	427.2	407.6	372.3	320.8	256.7	189.8	134.7



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	440.8	440.8	438.6	431.7	417.3	392.1	352.6	300.0	240.3	181.3	132.4
115°	433.1	431.7	426.0	413.8	392.8	362.3	321.1	272.4	220.6	172.1	131.6
117.5°	408.3	406.4	398.4	384.3	362.3	331.4	294.5	252.4	208.7	166.8	132.1
120°	387.7	386.0	379.3	363.6	341.5	313.2	279.6	241.9	202.4	164.3	133.0
122.5°	368.4	366.3	358.9	344.8	325.2	298.9	267.8	233.6	197.3	162.8	134.5
125°	341.5	339.6	332.6	320.3	302.4	280.0	253.1	222.5	190.7	160.7	136.9
127.5°	319.3	317.6	311.2	300.7	284.8	264.4	240.1	212.9	184.8	159.7	139.6
130°	306.8	304.6	298.7	288.6	273.8	254.8	232.1	206.8	181.6	159.0	141.4
132.5°	294.5	292.9	287.7	277.7	263.7	245.6	224.4	201.3	178.8	158.8	142.8
135°	276.9	274.9	269.9	261.5	247.7	231.8	213.6	193.7	175.0	158.4	144.7
137.5°	258.3	256.9	252.7	244.2	232.7	218.8	203.1	186.8	171.7	157.8	146.1
140°	245.3	245.5	241.1	233.2	222.5	210.5	197.1	182.8	169.6	157.6	146.9
142.5°	233.1	233.4	229.4	222.4	213.3	202.9	191.2	179.0	167.9	157.2	147.7
145°	216.4	215.9	213.6	207.7	200.7	192.6	183.6	174.4	165.4	156.5	148.1
147.5°	202.6	202.4	200.3	196.3	191.0	185.2	178.0	170.6	163.1	155.4	148.1
150°	194.6	194.6	192.9	189.8	185.6	180.3	174.4	167.9	161.5	154.6	148.1
152.5°	187.8	187.8	186.8	183.9	180.7	176.3	171.0	165.5	159.7	153.4	147.4
155°	179.4	179.2	178.6	176.3	173.8	170.5	166.3	161.8	157.0	151.5	146.7
157.5°	171.7	171.8	171.3	169.7	167.5	164.9	161.6	157.9	154.0	149.7	145.8
160°	166.8	167.2	167.2	165.4	163.5	161.5	158.8	155.7	152.0	148.4	145.3
162.5°	162.4	162.6	162.6	161.2	159.9	158.2	155.6	153.0	150.0	147.0	144.4
165°	156.5	156.5	156.8	155.7	154.6	153.1	151.1	149.5	147.3	145.0	143.1
167.5°	150.9	150.9	151.1	150.4	149.9	148.9	147.7	146.5	144.7	143.0	141.7
170°	147.5	147.5	147.8	147.3	146.9	146.4	145.3	144.4	143.1	141.6	140.9
172.5°	144.4	144.7	145.1	144.6	144.5	144.2	143.3	142.7	141.5	140.5	140.1
175°	140.9	141.1	141.4	141.1	141.1	141.1	140.5	140.2	139.7	139.1	139.1
177.5°	138.7	138.7	139.2	138.9	139.2	139.2	138.9	138.7	138.6	138.3	138.6
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	392.7	391.6	390.4	388.3	386.5	384.0	383.3	382.4	379.7	377.4	375.6
5°	416.7	412.3	405.8	399.9	395.1	388.6	385.0	381.1	375.6	370.6	366.5
7.5°	441.8	433.1	423.0	412.3	402.1	392.4	384.5	377.5	369.7	362.4	356.6
10°	461.8	449.2	435.1	420.0	407.1	394.6	384.0	374.9	364.9	356.2	349.0
12.5°	484.5	465.9	446.6	428.2	412.9	395.5	382.7	371.0	359.7	349.3	341.2
15°	511.4	487.7	464.9	439.6	416.4	394.6	379.5	364.6	351.6	340.9	330.5
17.5°	535.9	509.1	479.0	448.2	420.2	394.3	373.2	356.5	340.1	327.0	316.7
20°	549.8	519.4	485.2	453.3	422.2	393.5	370.2	350.3	332.6	318.7	307.1
22.5°	561.7	526.1	490.8	456.6	422.1	391.1	364.7	344.2	325.0	311.5	299.1
25°	574.2	531.5	496.1	456.1	417.5	385.3	355.8	332.6	313.4	297.5	284.8
27.5°	584.8	531.2	489.1	446.0	410.1	378.0	346.4	321.5	301.1	283.8	270.9
30°	591.8	531.9	481.9	439.3	403.1	369.9	339.2	314.1	292.7	275.2	263.0
32.5°	596.3	531.4	475.2	429.8	391.8	362.4	331.4	305.4	283.4	266.2	254.4
35°	598.9	528.1	463.7	410.3	373.8	345.1	319.1	292.2	269.1	253.0	239.7
37.5°	593.7	521.3	450.5	391.4	351.4	323.3	301.3	278.5	256.4	238.7	227.2
40°	585.6	516.9	440.1	378.1	336.0	309.0	290.3	267.8	246.0	229.2	218.5
42.5°	570.1	507.9	428.8	363.4	320.1	293.0	275.8	257.0	236.4	220.6	209.9
45°	532.3	488.3	411.7	341.3	296.6	268.5	253.4	239.7	221.1	205.8	196.5
47.5°	479.7	458.8	387.1	317.9	272.0	245.0	229.3	218.3	204.7	192.3	183.5
50°	443.3	434.6	370.4	301.9	255.6	229.2	214.0	204.1	194.3	182.0	173.9
52.5°	401.2	406.5	350.9	285.4	238.9	212.9	198.8	190.8	182.0	171.7	164.7
55°	342.0	361.3	317.3	257.6	214.0	189.3	175.9	168.9	163.7	156.1	150.0
57.5°	286.5	311.2	280.8	229.0	189.6	168.3	155.4	147.8	144.5	140.5	135.7
60°	253.6	277.9	254.8	209.8	173.3	153.0	141.6	135.1	131.7	129.0	124.9
62.5°	224.2	248.8	229.5	190.4	157.2	138.4	128.4	122.1	119.5	118.1	114.6
65°	183.8	205.0	192.1	160.0	134.2	117.6	108.5	104.1	101.7	101.2	98.9
67.5°	149.6	165.7	156.4	132.7	112.4	98.1	90.4	86.6	84.8	84.5	82.9
70°	127.1	142.3	135.1	113.7	96.2	84.9	78.3	74.9	73.8	73.7	72.7
72.5°	109.7	120.3	114.5	96.7	83.2	73.0	68.0	64.6	63.4	63.6	63.0
75°	81.2	89.1	85.8	73.4	62.6	55.9	51.9	49.7	48.6	49.1	48.3
77.5°	58.5	63.5	60.4	51.9	45.2	40.4	37.4	36.0	35.0	35.0	34.7
80°	44.1	47.1	45.4	40.2	34.7	30.7	28.2	27.3	26.8	26.5	26.4
82.5°	31.4	33.9	31.9	28.4	24.6	22.2	20.8	19.6	19.3	19.3	19.2
85°	15.8	16.8	16.1	13.9	12.4	11.2	10.5	10.0	9.6	9.7	9.4
87.5°	6.5	6.5	5.9	5.2	4.8	4.2	4.0	3.6	3.5	3.6	3.6
90°	5.3	4.5	3.6	3.1	2.5	1.7	1.1	0.6	1.1	1.7	2.5
92.5°	35.6	23.5	16.2	12.0	9.7	7.5	5.1	3.5	5.1	7.5	9.7
95°	101.9	60.2	36.4	25.5	18.2	13.5	10.4	9.5	10.4	13.5	18.2
97.5°	111.8	64.8	42.1	30.3	23.1	18.9	16.5	16.2	16.5	18.9	23.1
100°	105.5	64.1	44.5	33.6	26.9	23.0	21.0	20.8	21.0	23.0	26.9
102.5°	100.1	65.0	47.5	37.4	31.4	27.6	25.9	25.4	25.9	27.6	31.4
105°	96.3	67.5	52.4	43.6	38.3	35.0	33.4	32.5	33.4	35.0	38.3
107.5°	96.0	72.1	58.8	50.7	45.7	42.5	40.8	40.0	40.8	42.5	45.7
110°	97.1	75.9	63.3	55.5	50.7	47.6	46.2	45.3	46.2	47.6	50.7





TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	99.4	79.7	68.0	60.4	55.6	52.5	51.1	50.3	51.1	52.5	55.6
115°	103.0	86.0	75.3	67.7	63.0	60.2	58.5	57.4	58.5	60.2	63.0
117.5°	107.8	92.6	82.1	75.1	69.8	67.2	65.8	64.5	65.8	67.2	69.8
120°	111.4	96.9	86.7	79.8	74.5	71.7	70.3	69.4	70.3	71.7	74.5
122.5°	114.8	101.3	91.5	84.1	79.0	75.9	74.5	73.7	74.5	75.9	79.0
125°	120.1	107.8	98.0	90.4	85.1	82.0	80.3	79.8	80.3	82.0	85.1
127.5°	124.5	113.4	103.9	96.3	90.5	87.4	85.2	84.4	85.2	87.4	90.5
130°	127.4	116.8	107.5	100.0	94.0	90.7	88.2	87.4	88.2	90.7	94.0
132.5°	130.1	119.6	110.7	103.3	97.4	93.4	90.6	89.6	90.6	93.4	97.4
135°	133.6	124.0	115.3	107.8	101.9	97.7	94.6	93.5	94.6	97.7	101.9
137.5°	136.1	127.1	118.7	111.7	105.8	101.4	98.4	97.2	98.4	101.4	105.8
140°	137.4	129.0	121.0	113.9	108.4	103.9	101.1	99.7	101.1	103.9	108.4
142.5°	138.8	130.6	122.7	116.2	110.6	106.5	103.5	102.3	103.5	106.5	110.6
145°	140.2	132.7	125.4	119.0	114.2	110.0	107.5	106.6	107.5	110.0	114.2
147.5°	141.2	134.4	127.7	122.2	117.6	114.0	111.5	111.1	111.5	114.0	117.6
150°	141.4	135.5	129.0	124.0	120.1	116.5	114.2	113.9	114.2	116.5	120.1
152.5°	141.8	136.2	130.6	125.8	122.3	119.1	116.9	116.8	116.9	119.1	122.3
155°	142.0	137.4	132.7	128.8	125.7	122.9	121.2	121.2	121.2	122.9	125.7
157.5°	142.2	138.2	134.4	131.3	128.7	126.3	124.9	124.7	124.9	126.3	128.7
160°	142.2	138.9	135.5	132.7	130.7	128.5	127.4	127.4	127.4	128.5	130.7
162.5°	142.0	139.1	136.2	133.8	132.1	130.3	129.4	129.4	129.4	130.3	132.1
165°	141.4	139.4	137.2	135.2	134.1	132.7	132.1	132.4	132.1	132.7	134.1
167.5°	140.9	139.3	137.8	136.5	135.7	134.7	134.4	134.7	134.4	134.7	135.7
170°	140.2	139.1	137.8	137.2	136.6	135.8	135.5	136.0	135.5	135.8	136.6
172.5°	140.1	139.1	137.9	137.6	137.3	136.7	136.6	137.0	136.6	136.7	137.3
175°	139.4	138.9	138.3	138.0	138.0	137.4	137.8	138.0	137.8	137.4	138.0
177.5°	138.9	138.6	138.3	138.3	138.3	138.1	138.3	138.6	138.3	138.1	138.3
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	374.5	373.5	372.1	369.9	368.0	365.3	365.3	365.7	365.7	365.6	365.3
5°	363.2	360.4	357.1	353.2	349.2	345.1	344.4	342.9	341.8	341.0	340.2
7.5°	351.2	346.3	341.4	336.0	331.1	327.0	324.2	321.8	320.3	318.6	317.4
10°	343.1	337.0	331.3	325.6	319.2	314.3	311.2	309.0	307.3	305.8	305.1
12.5°	333.5	326.5	320.2	314.7	307.9	302.8	299.8	298.7	296.8	293.7	292.1
15°	319.5	313.0	305.5	297.1	293.8	287.6	284.0	282.3	281.2	278.8	278.1
17.5°	307.4	299.0	290.5	284.3	278.1	273.1	271.1	269.0	267.6	265.6	265.0
20°	297.9	290.3	282.6	275.9	269.4	263.9	262.2	260.8	259.3	258.4	257.6
22.5°	288.1	280.6	274.1	267.9	261.0	257.4	255.6	254.0	252.9	252.3	251.6
25°	274.4	267.8	260.5	255.1	249.5	247.1	246.0	245.1	244.3	243.4	243.2
27.5°	262.2	254.9	249.1	243.9	240.0	238.0	236.9	236.5	236.6	236.9	237.2
30°	253.0	246.4	241.6	237.2	233.5	231.6	231.4	231.4	232.2	232.3	232.7
32.5°	244.6	239.2	234.3	230.0	227.3	226.0	226.7	226.7	227.3	227.8	228.5
35°	232.3	227.5	223.9	220.1	217.8	218.3	218.7	219.0	220.0	221.1	221.8
37.5°	220.6	216.5	212.6	209.8	208.7	209.6	210.6	211.3	212.4	213.3	214.0
40°	212.2	209.1	205.4	202.8	203.2	203.7	204.5	205.4	206.4	206.9	207.6
42.5°	204.4	201.1	198.3	196.1	196.7	197.4	197.8	198.3	199.4	200.4	200.8
45°	192.5	189.9	187.4	186.0	186.4	186.8	187.1	187.7	188.6	189.3	189.6
47.5°	179.1	177.3	175.5	174.3	174.9	174.8	175.2	176.4	176.7	177.1	178.2
50°	170.6	168.9	166.8	166.4	166.4	166.4	166.7	168.1	168.1	168.9	169.6
52.5°	161.1	160.0	158.8	158.0	157.7	157.7	158.5	159.2	159.5	160.6	161.4
55°	147.1	146.0	144.9	144.3	143.9	144.3	145.8	146.2	147.1	147.7	148.2
57.5°	132.5	131.7	130.8	130.5	130.4	130.9	131.7	132.8	133.0	134.8	135.5
60°	122.9	121.6	120.9	120.9	120.5	122.2	121.8	123.7	124.1	125.2	126.4
62.5°	113.0	111.3	111.0	111.0	111.5	112.0	112.5	113.3	114.3	115.7	116.7
65°	97.0	96.2	97.4	97.3	96.9	98.0	98.0	98.9	100.1	101.3	103.4
67.5°	82.0	81.5	81.6	81.6	82.1	82.8	83.3	84.1	85.5	86.8	88.2
70°	71.8	72.3	71.5	72.2	72.7	72.9	73.3	74.4	75.8	76.8	78.3
72.5°	61.9	61.9	61.9	62.3	62.8	63.1	63.5	64.8	66.4	67.2	68.4
75°	47.6	47.5	48.0	48.0	48.9	49.3	49.7	50.2	51.7	52.8	53.7
77.5°	34.8	35.0	34.9	35.5	35.3	35.3	36.4	37.0	37.2	39.4	39.8
80°	26.2	26.5	26.8	26.9	27.1	26.8	28.0	28.6	28.6	29.9	30.8
82.5°	18.9	19.0	19.5	19.7	19.7	20.1	20.2	20.6	21.1	21.6	22.8
85°	9.4	10.0	10.1	10.0	10.1	9.7	10.3	10.5	10.7	10.7	10.7
87.5°	3.6	3.8	3.9	4.2	4.2	4.5	4.4	4.2	4.3	4.8	4.3
90°	3.1	3.6	4.5	5.3	6.2	7.0	6.7	7.0	7.3	7.5	8.1
92.5°	12.0	16.2	23.5	35.6	47.4	43.0	32.5	23.6	18.7	16.5	15.1
95°	25.5	36.4	60.2	101.9	147.8	166.0	134.7	100.8	68.3	53.5	43.4
97.5°	30.3	42.1	64.8	111.8	188.4	257.3	275.2	251.2	201.2	165.1	131.7
100°	33.6	44.5	64.1	105.5	179.2	265.1	320.3	330.0	307.4	274.6	234.9
102.5°	37.4	47.5	65.0	100.1	165.7	250.6	322.5	356.2	355.5	336.4	311.2
105°	43.6	52.4	67.5	96.3	149.2	225.1	305.4	363.9	391.9	397.2	390.0
107.5°	50.7	58.8	72.1	96.0	138.7	202.6	275.5	341.8	387.3	411.9	421.8
110°	55.5	63.3	75.9	97.1	134.7	189.8	256.7	320.8	372.3	407.6	427.2



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	60.4	68.0	79.7	99.4	132.4	181.3	240.3	300.0	352.6	392.1	417.3
115°	67.7	75.3	86.0	103.0	131.6	172.1	220.6	272.4	321.1	362.3	392.8
117.5°	75.1	82.1	92.6	107.8	132.1	166.8	208.7	252.4	294.5	331.4	362.3
120°	79.8	86.7	96.9	111.4	133.0	164.3	202.4	241.9	279.6	313.2	341.5
122.5°	84.1	91.5	101.3	114.8	134.5	162.8	197.3	233.6	267.8	298.9	325.2
125°	90.4	98.0	107.8	120.1	136.9	160.7	190.7	222.5	253.1	280.0	302.4
127.5°	96.3	103.9	113.4	124.5	139.6	159.7	184.8	212.9	240.1	264.4	284.8
130°	100.0	107.5	116.8	127.4	141.4	159.0	181.6	206.8	232.1	254.8	273.8
132.5°	103.3	110.7	119.6	130.1	142.8	158.8	178.8	201.3	224.4	245.6	263.7
135°	107.8	115.3	124.0	133.6	144.7	158.4	175.0	193.7	213.6	231.8	247.7
137.5°	111.7	118.7	127.1	136.1	146.1	157.8	171.7	186.8	203.1	218.8	232.7
140°	113.9	121.0	129.0	137.4	146.9	157.6	169.6	182.8	197.1	210.5	222.5
142.5°	116.2	122.7	130.6	138.8	147.7	157.2	167.9	179.0	191.2	202.9	213.3
145°	119.0	125.4	132.7	140.2	148.1	156.5	165.4	174.4	183.6	192.6	200.7
147.5°	122.2	127.7	134.4	141.2	148.1	155.4	163.1	170.6	178.0	185.2	191.0
150°	124.0	129.0	135.5	141.4	148.1	154.6	161.5	167.9	174.4	180.3	185.6
152.5°	125.8	130.6	136.2	141.8	147.4	153.4	159.7	165.5	171.0	176.3	180.7
155°	128.8	132.7	137.4	142.0	146.7	151.5	157.0	161.8	166.3	170.5	173.8
157.5°	131.3	134.4	138.2	142.2	145.8	149.7	154.0	157.9	161.6	164.9	167.5
160°	132.7	135.5	138.9	142.2	145.3	148.4	152.0	155.7	158.8	161.5	163.5
162.5°	133.8	136.2	139.1	142.0	144.4	147.0	150.0	153.0	155.6	158.2	159.9
165°	135.2	137.2	139.4	141.4	143.1	145.0	147.3	149.5	151.1	153.1	154.6
167.5°	136.5	137.8	139.3	140.9	141.7	143.0	144.7	146.5	147.7	148.9	149.9
170°	137.2	137.8	139.1	140.2	140.9	141.6	143.1	144.4	145.3	146.4	146.9
172.5°	137.6	137.9	139.1	140.1	140.1	140.5	141.5	142.7	143.3	144.2	144.5
175°	138.0	138.3	138.9	139.4	139.1	139.1	139.7	140.2	140.5	141.1	141.1
177.5°	138.3	138.3	138.6	138.9	138.6	138.3	138.6	138.7	138.9	139.2	139.2
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	364.2	364.1	365.1	364.4	365.1	364.1	364.2	365.3	365.6	365.7	365.7
5°	339.1	339.6	337.7	337.7	337.7	339.6	339.1	340.2	341.0	341.8	342.9
7.5°	316.6	315.8	315.8	314.8	315.8	315.8	316.6	317.4	318.6	320.3	321.8
10°	302.9	301.7	301.3	301.6	301.3	301.7	302.9	305.1	305.8	307.3	309.0
12.5°	291.4	291.3	288.8	288.8	288.8	291.3	291.4	292.1	293.7	296.8	298.7
15°	278.1	274.6	274.3	275.4	274.3	274.6	278.1	278.1	278.8	281.2	282.3
17.5°	264.7	262.8	263.0	262.4	263.0	262.8	264.7	265.0	265.6	267.6	269.0
20°	257.6	256.5	256.4	255.1	256.4	256.5	257.6	257.6	258.4	259.3	260.8
22.5°	251.1	250.8	250.9	249.5	250.9	250.8	251.1	251.6	252.3	252.9	254.0
25°	243.0	244.0	243.2	243.2	243.2	244.0	243.0	243.2	243.4	244.3	245.1
27.5°	237.6	237.6	237.2	237.2	237.2	237.6	237.6	237.2	236.9	236.6	236.5
30°	233.5	233.3	233.6	233.6	233.6	233.3	233.5	232.7	232.3	232.2	231.4
32.5°	229.3	229.6	229.7	229.8	229.7	229.6	229.3	228.5	227.8	227.3	226.7
35°	222.9	223.2	223.7	223.3	223.7	223.2	222.9	221.8	221.1	220.0	219.0
37.5°	214.3	215.2	215.0	215.2	215.0	215.2	214.3	214.0	213.3	212.4	211.3
40°	207.8	208.3	208.2	208.2	208.2	208.3	207.8	207.6	206.9	206.4	205.4
42.5°	201.1	201.5	201.1	200.8	201.1	201.5	201.1	200.8	200.4	199.4	198.3
45°	190.3	189.9	190.4	189.7	190.4	189.9	190.3	189.6	189.3	188.6	187.7
47.5°	178.1	178.5	178.6	179.2	178.6	178.5	178.1	178.2	177.1	176.7	176.4
50°	170.0	171.1	171.1	170.9	171.1	171.1	170.0	169.6	168.9	168.1	168.1
52.5°	162.0	162.5	163.3	163.2	163.3	162.5	162.0	161.4	160.6	159.5	159.2
55°	149.6	150.0	150.4	150.6	150.4	150.0	149.6	148.2	147.7	147.1	146.2
57.5°	136.9	136.7	137.6	137.9	137.6	136.7	136.9	135.5	134.8	133.0	132.8
60°	127.9	127.9	129.4	129.9	129.4	127.9	127.9	126.4	125.2	124.1	123.7
62.5°	118.3	118.9	120.3	119.6	120.3	118.9	118.3	116.7	115.7	114.3	113.3
65°	104.3	105.8	105.6	106.3	105.6	105.8	104.3	103.4	101.3	100.1	98.9
67.5°	89.6	90.5	91.9	92.0	91.9	90.5	89.6	88.2	86.8	85.5	84.1
70°	79.7	80.6	81.4	81.9	81.4	80.6	79.7	78.3	76.8	75.8	74.4
72.5°	70.1	70.6	72.4	71.6	72.4	70.6	70.1	68.4	67.2	66.4	64.8
75°	55.0	56.3	57.4	56.9	57.4	56.3	55.0	53.7	52.8	51.7	50.2
77.5°	40.6	42.0	42.5	42.0	42.5	42.0	40.6	39.8	39.4	37.2	37.0
80°	32.1	31.9	33.0	32.9	33.0	31.9	32.1	30.8	29.9	28.6	28.6
82.5°	23.5	23.4	23.8	24.0	23.8	23.4	23.5	22.8	21.6	21.1	20.6
85°	11.4	12.0	11.2	11.1	11.2	12.0	11.4	10.7	10.7	10.7	10.5
87.5°	4.2	4.3	4.2	4.0	4.2	4.3	4.2	4.3	4.8	4.3	4.2
90°	7.8	8.1	8.4	8.1	8.4	8.1	7.8	8.1	7.5	7.3	7.0
92.5°	14.6	13.7	14.0	13.5	14.0	13.7	14.6	15.1	16.5	18.7	23.6
95°	38.1	35.6	33.6	32.5	33.6	35.6	38.1	43.4	53.5	68.3	100.8
97.5°	111.0	98.4	90.8	88.4	90.8	98.4	111.0	131.7	165.1	201.2	251.2
100°	206.6	186.2	175.2	175.5	175.2	186.2	206.6	234.9	274.6	307.4	330.0
102.5°	289.2	273.1	264.0	257.5	264.0	273.1	289.2	311.2	336.4	355.5	356.2
105°	377.1	366.5	357.5	356.1	357.5	366.5	377.1	390.0	397.2	391.9	363.9
107.5°	422.1	418.4	415.4	412.9	415.4	418.4	422.1	421.8	411.9	387.3	341.8
110°	435.1	437.3	436.7	436.2	436.7	437.3	435.1	427.2	407.6	372.3	320.8



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	431.7	438.6	440.8	440.8	440.8	438.6	431.7	417.3	392.1	352.6	300.0
115°	413.8	426.0	431.7	433.1	431.7	426.0	413.8	392.8	362.3	321.1	272.4
117.5°	384.3	398.4	406.4	408.3	406.4	398.4	384.3	362.3	331.4	294.5	252.4
120°	363.6	379.3	386.0	387.7	386.0	379.3	363.6	341.5	313.2	279.6	241.9
122.5°	344.8	358.9	366.3	368.4	366.3	358.9	344.8	325.2	298.9	267.8	233.6
125°	320.3	332.6	339.6	341.5	339.6	332.6	320.3	302.4	280.0	253.1	222.5
127.5°	300.7	311.2	317.6	319.3	317.6	311.2	300.7	284.8	264.4	240.1	212.9
130°	288.6	298.7	304.6	306.8	304.6	298.7	288.6	273.8	254.8	232.1	206.8
132.5°	277.7	287.7	292.9	294.5	292.9	287.7	277.7	263.7	245.6	224.4	201.3
135°	261.5	269.9	274.9	276.9	274.9	269.9	261.5	247.7	231.8	213.6	193.7
137.5°	244.2	252.7	256.9	258.3	256.9	252.7	244.2	232.7	218.8	203.1	186.8
140°	233.2	241.1	245.5	245.3	245.5	241.1	233.2	222.5	210.5	197.1	182.8
142.5°	222.4	229.4	233.4	233.1	233.4	229.4	222.4	213.3	202.9	191.2	179.0
145°	207.7	213.6	215.9	216.4	215.9	213.6	207.7	200.7	192.6	183.6	174.4
147.5°	196.3	200.3	202.4	202.6	202.4	200.3	196.3	191.0	185.2	178.0	170.6
150°	189.8	192.9	194.6	194.6	194.6	192.9	189.8	185.6	180.3	174.4	167.9
152.5°	183.9	186.8	187.8	187.8	187.8	186.8	183.9	180.7	176.3	171.0	165.5
155°	176.3	178.6	179.2	179.4	179.2	178.6	176.3	173.8	170.5	166.3	161.8
157.5°	169.7	171.3	171.8	171.7	171.8	171.3	169.7	167.5	164.9	161.6	157.9
160°	165.4	167.2	167.2	166.8	167.2	167.2	165.4	163.5	161.5	158.8	155.7
162.5°	161.2	162.6	162.6	162.4	162.6	162.6	161.2	159.9	158.2	155.6	153.0
165°	155.7	156.8	156.5	156.5	156.5	156.8	155.7	154.6	153.1	151.1	149.5
167.5°	150.4	151.1	150.9	150.9	150.9	151.1	150.4	149.9	148.9	147.7	146.5
170°	147.3	147.8	147.5	147.5	147.5	147.8	147.3	146.9	146.4	145.3	144.4
172.5°	144.6	145.1	144.7	144.4	144.7	145.1	144.6	144.5	144.2	143.3	142.7
175°	141.1	141.4	141.1	140.9	141.1	141.4	141.1	141.1	141.1	140.5	140.2
177.5°	138.9	139.2	138.7	138.7	138.7	139.2	138.9	139.2	139.2	138.9	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	365.3	365.3	368.0	369.9	372.1	373.5	374.5	375.6	377.4	379.7	382.4
5°	344.4	345.1	349.2	353.2	357.1	360.4	363.2	366.5	370.6	375.6	381.1
7.5°	324.2	327.0	331.1	336.0	341.4	346.3	351.2	356.6	362.4	369.7	377.5
10°	311.2	314.3	319.2	325.6	331.3	337.0	343.1	349.0	356.2	364.9	374.9
12.5°	299.8	302.8	307.9	314.7	320.2	326.5	333.5	341.2	349.3	359.7	371.0
15°	284.0	287.6	293.8	297.1	305.5	313.0	319.5	330.5	340.9	351.6	364.6
17.5°	271.1	273.1	278.1	284.3	290.5	299.0	307.4	316.7	327.0	340.1	356.5
20°	262.2	263.9	269.4	275.9	282.6	290.3	297.9	307.1	318.7	332.6	350.3
22.5°	255.6	257.4	261.0	267.9	274.1	280.6	288.1	299.1	311.5	325.0	344.2
25°	246.0	247.1	249.5	255.1	260.5	267.8	274.4	284.8	297.5	313.4	332.6
27.5°	236.9	238.0	240.0	243.9	249.1	254.9	262.2	270.9	283.8	301.1	321.5
30°	231.4	231.6	233.5	237.2	241.6	246.4	253.0	263.0	275.2	292.7	314.1
32.5°	226.7	226.0	227.3	230.0	234.3	239.2	244.6	254.4	266.2	283.4	305.4
35°	218.7	218.3	217.8	220.1	223.9	227.5	232.3	239.7	253.0	269.1	292.2
37.5°	210.6	209.6	208.7	209.8	212.6	216.5	220.6	227.2	238.7	256.4	278.5
40°	204.5	203.7	203.2	202.8	205.4	209.1	212.2	218.5	229.2	246.0	267.8
42.5°	197.8	197.4	196.7	196.1	198.3	201.1	204.4	209.9	220.6	236.4	257.0
45°	187.1	186.8	186.4	186.0	187.4	189.9	192.5	196.5	205.8	221.1	239.7
47.5°	175.2	174.8	174.9	174.3	175.5	177.3	179.1	183.5	192.3	204.7	218.3
50°	166.7	166.4	166.4	166.4	166.8	168.9	170.6	173.9	182.0	194.3	204.1
52.5°	158.5	157.7	157.7	158.0	158.8	160.0	161.1	164.7	171.7	182.0	190.8
55°	145.8	144.3	143.9	144.3	144.9	146.0	147.1	150.0	156.1	163.7	168.9
57.5°	131.7	130.9	130.4	130.5	130.8	131.7	132.5	135.7	140.5	144.5	147.8
60°	121.8	122.2	120.5	120.9	120.9	121.6	122.9	124.9	129.0	131.7	135.1
62.5°	112.5	112.0	111.5	111.0	111.0	111.3	113.0	114.6	118.1	119.5	122.1
65°	98.0	98.0	96.9	97.3	97.4	96.2	97.0	98.9	101.2	101.7	104.1
67.5°	83.3	82.8	82.1	81.6	81.6	81.5	82.0	82.9	84.5	84.8	86.6
70°	73.3	72.9	72.7	72.2	71.5	72.3	71.8	72.7	73.7	73.8	74.9
72.5°	63.5	63.1	62.8	62.3	61.9	61.9	61.9	63.0	63.6	63.4	64.6
75°	49.7	49.3	48.9	48.0	48.0	47.5	47.6	48.3	49.1	48.6	49.7
77.5°	36.4	35.3	35.3	35.5	34.9	35.0	34.8	34.7	35.0	35.0	36.0
80°	28.0	26.8	27.1	26.9	26.8	26.5	26.2	26.4	26.5	26.8	27.3
82.5°	20.2	20.1	19.7	19.7	19.5	19.0	18.9	19.2	19.3	19.3	19.6
85°	10.3	9.7	10.1	10.0	10.1	10.0	9.4	9.4	9.7	9.6	10.0
87.5°	4.4	4.5	4.2	4.2	3.9	3.8	3.6	3.6	3.6	3.5	3.6
90°	6.7	7.0	6.2	5.3	4.5	3.6	3.1	2.5	1.7	1.1	0.6
92.5°	32.5	43.0	47.4	35.6	23.5	16.2	12.0	9.7	7.5	5.1	3.5
95°	134.7	166.0	147.8	101.9	60.2	36.4	25.5	18.2	13.5	10.4	9.5
97.5°	275.2	257.3	188.4	111.8	64.8	42.1	30.3	23.1	18.9	16.5	16.2
100°	320.3	265.1	179.2	105.5	64.1	44.5	33.6	26.9	23.0	21.0	20.8
102.5°	322.5	250.6	165.7	100.1	65.0	47.5	37.4	31.4	27.6	25.9	25.4
105°	305.4	225.1	149.2	96.3	67.5	52.4	43.6	38.3	35.0	33.4	32.5
107.5°	275.5	202.6	138.7	96.0	72.1	58.8	50.7	45.7	42.5	40.8	40.0
110°	256.7	189.8	134.7	97.1	75.9	63.3	55.5	50.7	47.6	46.2	45.3



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	240.3	181.3	132.4	99.4	79.7	68.0	60.4	55.6	52.5	51.1	50.3
115°	220.6	172.1	131.6	103.0	86.0	75.3	67.7	63.0	60.2	58.5	57.4
117.5°	208.7	166.8	132.1	107.8	92.6	82.1	75.1	69.8	67.2	65.8	64.5
120°	202.4	164.3	133.0	111.4	96.9	86.7	79.8	74.5	71.7	70.3	69.4
122.5°	197.3	162.8	134.5	114.8	101.3	91.5	84.1	79.0	75.9	74.5	73.7
125°	190.7	160.7	136.9	120.1	107.8	98.0	90.4	85.1	82.0	80.3	79.8
127.5°	184.8	159.7	139.6	124.5	113.4	103.9	96.3	90.5	87.4	85.2	84.4
130°	181.6	159.0	141.4	127.4	116.8	107.5	100.0	94.0	90.7	88.2	87.4
132.5°	178.8	158.8	142.8	130.1	119.6	110.7	103.3	97.4	93.4	90.6	89.6
135°	175.0	158.4	144.7	133.6	124.0	115.3	107.8	101.9	97.7	94.6	93.5
137.5°	171.7	157.8	146.1	136.1	127.1	118.7	111.7	105.8	101.4	98.4	97.2
140°	169.6	157.6	146.9	137.4	129.0	121.0	113.9	108.4	103.9	101.1	99.7
142.5°	167.9	157.2	147.7	138.8	130.6	122.7	116.2	110.6	106.5	103.5	102.3
145°	165.4	156.5	148.1	140.2	132.7	125.4	119.0	114.2	110.0	107.5	106.6
147.5°	163.1	155.4	148.1	141.2	134.4	127.7	122.2	117.6	114.0	111.5	111.1
150°	161.5	154.6	148.1	141.4	135.5	129.0	124.0	120.1	116.5	114.2	113.9
152.5°	159.7	153.4	147.4	141.8	136.2	130.6	125.8	122.3	119.1	116.9	116.8
155°	157.0	151.5	146.7	142.0	137.4	132.7	128.8	125.7	122.9	121.2	121.2
157.5°	154.0	149.7	145.8	142.2	138.2	134.4	131.3	128.7	126.3	124.9	124.7
160°	152.0	148.4	145.3	142.2	138.9	135.5	132.7	130.7	128.5	127.4	127.4
162.5°	150.0	147.0	144.4	142.0	139.1	136.2	133.8	132.1	130.3	129.4	129.4
165°	147.3	145.0	143.1	141.4	139.4	137.2	135.2	134.1	132.7	132.1	132.4
167.5°	144.7	143.0	141.7	140.9	139.3	137.8	136.5	135.7	134.7	134.4	134.7
170°	143.1	141.6	140.9	140.2	139.1	137.8	137.2	136.6	135.8	135.5	136.0
172.5°	141.5	140.5	140.1	140.1	139.1	137.9	137.6	137.3	136.7	136.6	137.0
175°	139.7	139.1	139.1	139.4	138.9	138.3	138.0	138.0	137.4	137.8	138.0
177.5°	138.6	138.3	138.6	138.9	138.6	138.3	138.3	138.3	138.1	138.3	138.6
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	383.3	384.0	386.5	388.3	390.4	391.6	392.7	393.6	394.8	395.1	399.3
5°	385.0	388.6	395.1	399.9	405.8	412.3	416.7	418.7	424.1	428.5	437.4
7.5°	384.5	392.4	402.1	412.3	423.0	433.1	441.8	452.2	459.5	470.6	481.4
10°	384.0	394.6	407.1	420.0	435.1	449.2	461.8	475.8	487.4	502.7	515.8
12.5°	382.7	395.5	412.9	428.2	446.6	465.9	484.5	502.5	512.8	538.3	550.3
15°	379.5	394.6	416.4	439.6	464.9	487.7	511.4	530.2	560.6	583.0	597.2
17.5°	373.2	394.3	420.2	448.2	479.0	509.1	535.9	564.4	596.8	623.8	652.6
20°	370.2	393.5	422.2	453.3	485.2	519.4	549.8	584.1	619.3	645.9	682.9
22.5°	364.7	391.1	422.1	456.6	490.8	526.1	561.7	596.4	637.1	673.7	708.8
25°	355.8	385.3	417.5	456.1	496.1	531.5	574.2	620.1	662.5	709.6	744.7
27.5°	346.4	378.0	410.1	446.0	489.1	531.2	584.8	636.7	688.6	729.2	755.2
30°	339.2	369.9	403.1	439.3	481.9	531.9	591.8	648.5	699.1	734.0	748.5
32.5°	331.4	362.4	391.8	429.8	475.2	531.4	596.3	655.5	699.7	722.9	720.0
35°	319.1	345.1	373.8	410.3	463.7	528.1	598.9	656.1	683.2	678.2	640.6
37.5°	301.3	323.3	351.4	391.4	450.5	521.3	593.7	636.6	634.9	594.3	539.7
40°	290.3	309.0	336.0	378.1	440.1	516.9	585.6	613.5	589.9	533.1	467.9
42.5°	275.8	293.0	320.1	363.4	428.8	507.9	570.1	578.1	532.0	466.8	406.9
45°	253.4	268.5	296.6	341.3	411.7	488.3	532.3	512.5	450.3	382.9	337.4
47.5°	229.3	245.0	272.0	317.9	387.1	458.8	479.7	437.8	373.9	319.2	277.4
50°	214.0	229.2	255.6	301.9	370.4	434.6	443.3	389.0	330.3	282.3	248.0
52.5°	198.8	212.9	238.9	285.4	350.9	406.5	401.2	345.9	292.0	251.0	224.1
55°	175.9	189.3	214.0	257.6	317.3	361.3	342.0	289.2	244.5	212.8	192.3
57.5°	155.4	168.3	189.6	229.0	280.8	311.2	286.5	242.0	206.5	182.0	166.8
60°	141.6	153.0	173.3	209.8	254.8	277.9	253.6	214.3	184.3	164.8	151.1
62.5°	128.4	138.4	157.2	190.4	229.5	248.8	224.2	190.9	165.5	148.1	136.5
65°	108.5	117.6	134.2	160.0	192.1	205.0	183.8	156.9	137.1	124.2	116.5
67.5°	90.4	98.1	112.4	132.7	156.4	165.7	149.6	128.7	113.8	103.5	97.4
70°	78.3	84.9	96.2	113.7	135.1	142.3	127.1	110.0	99.1	90.8	85.1
72.5°	68.0	73.0	83.2	96.7	114.5	120.3	109.7	94.7	84.5	78.3	73.7
75°	51.9	55.9	62.6	73.4	85.8	89.1	81.2	71.8	65.0	60.5	57.0
77.5°	37.4	40.4	45.2	51.9	60.4	63.5	58.5	52.1	47.1	44.2	42.2
80°	28.2	30.7	34.7	40.2	45.4	47.1	44.1	39.3	35.8	34.1	32.5
82.5°	20.8	22.2	24.6	28.4	31.9	33.9	31.4	28.5	26.6	25.1	24.5
85°	10.5	11.2	12.4	13.9	16.1	16.8	15.8	15.1	14.0	13.1	13.1
87.5°	4.0	4.2	4.8	5.2	5.9	6.5	6.5	6.4	6.4	6.2	6.1
90°	1.1	1.7	2.5	3.1	3.6	4.5	5.3	6.2	7.0	6.7	7.0
92.5°	5.1	7.5	9.7	12.0	16.2	23.5	35.6	47.4	43.0	32.5	23.6
95°	10.4	13.5	18.2	25.5	36.4	60.2	101.9	147.8	166.0	134.7	100.8
97.5°	16.5	18.9	23.1	30.3	42.1	64.8	111.8	188.4	257.3	275.2	251.2
100°	21.0	23.0	26.9	33.6	44.5	64.1	105.5	179.2	265.1	320.3	330.0
102.5°	25.9	27.6	31.4	37.4	47.5	65.0	100.1	165.7	250.6	322.5	356.2
105°	33.4	35.0	38.3	43.6	52.4	67.5	96.3	149.2	225.1	305.4	363.9
107.5°	40.8	42.5	45.7	50.7	58.8	72.1	96.0	138.7	202.6	275.5	341.8
110°	46.2	47.6	50.7	55.5	63.3	75.9	97.1	134.7	189.8	256.7	320.8





TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	51.1	52.5	55.6	60.4	68.0	79.7	99.4	132.4	181.3	240.3	300.0
115°	58.5	60.2	63.0	67.7	75.3	86.0	103.0	131.6	172.1	220.6	272.4
117.5°	65.8	67.2	69.8	75.1	82.1	92.6	107.8	132.1	166.8	208.7	252.4
120°	70.3	71.7	74.5	79.8	86.7	96.9	111.4	133.0	164.3	202.4	241.9
122.5°	74.5	75.9	79.0	84.1	91.5	101.3	114.8	134.5	162.8	197.3	233.6
125°	80.3	82.0	85.1	90.4	98.0	107.8	120.1	136.9	160.7	190.7	222.5
127.5°	85.2	87.4	90.5	96.3	103.9	113.4	124.5	139.6	159.7	184.8	212.9
130°	88.2	90.7	94.0	100.0	107.5	116.8	127.4	141.4	159.0	181.6	206.8
132.5°	90.6	93.4	97.4	103.3	110.7	119.6	130.1	142.8	158.8	178.8	201.3
135°	94.6	97.7	101.9	107.8	115.3	124.0	133.6	144.7	158.4	175.0	193.7
137.5°	98.4	101.4	105.8	111.7	118.7	127.1	136.1	146.1	157.8	171.7	186.8
140°	101.1	103.9	108.4	113.9	121.0	129.0	137.4	146.9	157.6	169.6	182.8
142.5°	103.5	106.5	110.6	116.2	122.7	130.6	138.8	147.7	157.2	167.9	179.0
145°	107.5	110.0	114.2	119.0	125.4	132.7	140.2	148.1	156.5	165.4	174.4
147.5°	111.5	114.0	117.6	122.2	127.7	134.4	141.2	148.1	155.4	163.1	170.6
150°	114.2	116.5	120.1	124.0	129.0	135.5	141.4	148.1	154.6	161.5	167.9
152.5°	116.9	119.1	122.3	125.8	130.6	136.2	141.8	147.4	153.4	159.7	165.5
155°	121.2	122.9	125.7	128.8	132.7	137.4	142.0	146.7	151.5	157.0	161.8
157.5°	124.9	126.3	128.7	131.3	134.4	138.2	142.2	145.8	149.7	154.0	157.9
160°	127.4	128.5	130.7	132.7	135.5	138.9	142.2	145.3	148.4	152.0	155.7
162.5°	129.4	130.3	132.1	133.8	136.2	139.1	142.0	144.4	147.0	150.0	153.0
165°	132.1	132.7	134.1	135.2	137.2	139.4	141.4	143.1	145.0	147.3	149.5
167.5°	134.4	134.7	135.7	136.5	137.8	139.3	140.9	141.7	143.0	144.7	146.5
170°	135.5	135.8	136.6	137.2	137.8	139.1	140.2	140.9	141.6	143.1	144.4
172.5°	136.6	136.7	137.3	137.6	137.9	139.1	140.1	140.1	140.5	141.5	142.7
175°	137.8	137.4	138.0	138.0	138.3	138.9	139.4	139.1	139.1	139.7	140.2
177.5°	138.3	138.1	138.3	138.3	138.3	138.6	138.9	138.6	138.3	138.6	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	400.8	401.0	402.6	403.8	403.2	403.9	404.3
5°	437.9	444.6	448.1	450.7	450.8	451.1	452.5
7.5°	490.5	497.6	502.9	510.8	513.1	515.8	515.1
10°	528.9	539.5	548.5	553.3	558.5	566.0	559.9
12.5°	564.8	583.4	597.2	604.7	609.5	611.0	608.1
15°	624.0	648.3	661.4	661.1	677.6	684.8	673.6
17.5°	678.2	700.7	718.7	727.9	741.8	744.8	743.5
20°	711.5	736.0	750.0	765.9	773.1	779.5	780.6
22.5°	740.1	762.2	777.2	790.4	796.4	799.5	801.3
25°	769.6	787.0	796.0	800.6	802.2	801.8	799.5
27.5°	767.5	768.9	758.9	749.2	740.4	730.6	727.1
30°	747.6	732.1	704.4	688.7	665.7	647.4	654.8
32.5°	695.2	664.3	633.3	599.0	570.6	562.5	554.4
35°	593.3	539.1	507.3	470.4	455.7	440.9	430.7
37.5°	480.0	438.1	400.4	376.3	361.5	352.1	347.1
40°	415.0	377.2	346.2	326.6	315.4	304.9	303.4
42.5°	363.2	328.0	304.8	289.1	278.4	273.9	270.6
45°	297.5	273.0	257.3	246.2	239.0	236.2	232.5
47.5°	251.8	234.5	222.7	215.2	209.7	207.6	207.4
50°	226.2	211.8	203.2	197.3	193.1	192.3	189.3
52.5°	207.1	194.6	187.8	182.7	179.6	177.5	176.7
55°	179.7	171.4	165.3	162.4	160.0	158.0	158.0
57.5°	157.2	150.4	146.3	143.8	143.1	141.6	140.7
60°	143.4	137.5	134.4	132.1	130.6	130.9	129.2
62.5°	129.8	126.0	122.9	120.8	119.0	119.1	119.1
65°	110.5	107.6	105.4	104.6	103.5	102.3	102.6
67.5°	93.7	90.9	89.2	87.9	87.5	86.8	87.9
70°	81.6	79.5	78.3	77.2	76.8	76.9	77.9
72.5°	70.5	69.1	68.2	67.7	66.9	66.9	67.6
75°	55.4	54.3	53.6	53.0	52.8	52.8	52.8
77.5°	40.6	40.4	40.1	39.3	39.3	39.5	39.5
80°	32.1	31.5	31.4	31.0	30.4	30.1	31.0
82.5°	24.0	23.4	23.3	23.2	22.3	22.3	23.1
85°	12.9	12.4	12.5	12.4	12.4	12.2	12.2
87.5°	6.0	5.9	5.9	6.0	5.9	5.8	6.0
90°	7.3	7.5	8.1	7.8	8.1	8.4	8.1
92.5°	18.7	16.5	15.1	14.6	13.7	14.0	13.5
95°	68.3	53.5	43.4	38.1	35.6	33.6	32.5
97.5°	201.2	165.1	131.7	111.0	98.4	90.8	88.4
100°	307.4	274.6	234.9	206.6	186.2	175.2	175.5
102.5°	355.5	336.4	311.2	289.2	273.1	264.0	257.5
105°	391.9	397.2	390.0	377.1	366.5	357.5	356.1
107.5°	387.3	411.9	421.8	422.1	418.4	415.4	412.9
110°	372.3	407.6	427.2	435.1	437.3	436.7	436.2



TEST NUMBER: P331867-927

CATALOG NUMBER: S123DIP-S340D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	352.6	392.1	417.3	431.7	438.6	440.8	440.8
115°	321.1	362.3	392.8	413.8	426.0	431.7	433.1
117.5°	294.5	331.4	362.3	384.3	398.4	406.4	408.3
120°	279.6	313.2	341.5	363.6	379.3	386.0	387.7
122.5°	267.8	298.9	325.2	344.8	358.9	366.3	368.4
125°	253.1	280.0	302.4	320.3	332.6	339.6	341.5
127.5°	240.1	264.4	284.8	300.7	311.2	317.6	319.3
130°	232.1	254.8	273.8	288.6	298.7	304.6	306.8
132.5°	224.4	245.6	263.7	277.7	287.7	292.9	294.5
135°	213.6	231.8	247.7	261.5	269.9	274.9	276.9
137.5°	203.1	218.8	232.7	244.2	252.7	256.9	258.3
140°	197.1	210.5	222.5	233.2	241.1	245.5	245.3
142.5°	191.2	202.9	213.3	222.4	229.4	233.4	233.1
145°	183.6	192.6	200.7	207.7	213.6	215.9	216.4
147.5°	178.0	185.2	191.0	196.3	200.3	202.4	202.6
150°	174.4	180.3	185.6	189.8	192.9	194.6	194.6
152.5°	171.0	176.3	180.7	183.9	186.8	187.8	187.8
155°	166.3	170.5	173.8	176.3	178.6	179.2	179.4
157.5°	161.6	164.9	167.5	169.7	171.3	171.8	171.7
160°	158.8	161.5	163.5	165.4	167.2	167.2	166.8
162.5°	155.6	158.2	159.9	161.2	162.6	162.6	162.4
165°	151.1	153.1	154.6	155.7	156.8	156.5	156.5
167.5°	147.7	148.9	149.9	150.4	151.1	150.9	150.9
170°	145.3	146.4	146.9	147.3	147.8	147.5	147.5
172.5°	143.3	144.2	144.5	144.6	145.1	144.7	144.4
175°	140.5	141.1	141.1	141.1	141.4	141.1	140.9
177.5°	138.9	139.2	139.2	138.9	139.2	138.7	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3

(END OF REPORT)