

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331876-927

Luminaire Tested: **S123DIP-S340D585U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331876-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D585U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2830.7 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41																												
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35																												
2	87	80	74	69	79	73	68	64	60	57	54	49	46	44	38	36	34	29																												
3	80	71	64	58	73	65	59	54	53	49	45	43	40	37	33	31	30	25																												
4	73	63	55	49	66	57	51	46	48	43	39	38	35	32	30	28	26	22																												
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	24	22	19																												
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17																												
7	57	45	37	32	52	42	35	30	35	29	26	28	24	22	22	20	18	15																												
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13																												
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																												
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4100	4100	4100	4100
5°	4889	4118	3649	4118
10°	6120	4098	3296	4098
15°	7506	4063	3069	4063
20°	8942	4013	2922	4013
25°	9495	3950	2888	3950
30°	8139	3904	2903	3904
35°	5660	3840	2934	3840
40°	4263	3763	2925	3763
45°	3539	3649	2888	3649
50°	3170	3418	2862	3418
55°	2965	3170	2826	3170
60°	2781	2908	2796	2908
65°	2613	2651	2707	2651
70°	2452	2357	2578	2357
75°	2196	2067	2366	2067
80°	1922	1692	2039	1692
85°	1507	1235	1371	1235



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.5	1.3
10°-20°	120.3	4.3
20°-30°	201.9	7.1
30°-40°	228.6	8.1
40°-50°	205.0	7.2
50°-60°	165.5	5.8
60°-70°	115.3	4.1
70°-80°	60.6	2.1
80°-90°	16.5	0.6
90°-100°	124.2	4.4
100°-110°	351.7	12.4
110°-120°	346.0	12.2
120°-130°	276.0	9.7
130°-140°	217.6	7.7
140°-150°	162.4	5.7
150°-160°	113.2	4.0
160°-170°	66.5	2.3
170°-180°	21.6	0.8
0°-30°	359.8	12.7
0°-40°	588.4	20.8
0°-60°	958.9	33.9
0°-90°	1151.4	40.7
90°-120°	822.0	29.0
90°-150°	1478.0	52.2
90°-180°	1679.0	59.3
0°-180°	2830.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	381	381	381	381	381	
5°	452	381	338	381	452	47
15°	674	365	275	365	674	194
25°	800	333	243	333	800	351
35°	431	292	223	292	431	280
45°	232	240	190	240	232	184
55°	158	169	151	169	158	142
65°	103	104	106	104	103	102
75°	53	50	57	50	53	56
85°	12	10	11	10	12	15
90°	13	1	13	1	13	8
95°	52	15	52	15	52	94
105°	575	52	575	52	575	567
115°	699	93	699	93	699	679
125°	551	129	551	129	551	500
135°	447	151	447	151	447	347
145°	349	172	349	172	349	222
155°	290	196	290	196	290	135
165°	252	214	252	214	252	72
175°	227	223	227	223	227	22
180°	223	223	223	223	223	



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	404.3	403.9	403.2	403.8	402.6	401.0	400.8	399.3	395.1	394.8	393.6
5°	452.5	451.1	450.8	450.7	448.1	444.6	437.9	437.4	428.5	424.1	418.7
7.5°	515.1	515.8	513.1	510.8	502.9	497.6	490.5	481.4	470.6	459.5	452.2
10°	559.9	566.0	558.5	553.3	548.5	539.5	528.9	515.8	502.7	487.4	475.8
12.5°	608.1	611.0	609.5	604.7	597.2	583.4	564.8	550.3	538.3	512.8	502.5
15°	673.6	684.8	677.6	661.1	661.4	648.3	624.0	597.2	583.0	560.6	530.2
17.5°	743.5	744.8	741.8	727.9	718.7	700.7	678.2	652.6	623.8	596.8	564.4
20°	780.6	779.5	773.1	765.9	750.0	736.0	711.5	682.9	645.9	619.3	584.1
22.5°	801.3	799.5	796.4	790.4	777.2	762.2	740.1	708.8	673.7	637.1	596.4
25°	799.5	801.8	802.2	800.6	796.0	787.0	769.6	744.7	709.6	662.5	620.1
27.5°	727.1	730.6	740.4	749.2	758.9	768.9	767.5	755.2	729.2	688.6	636.7
30°	654.8	647.4	665.7	688.7	704.4	732.1	747.6	748.5	734.0	699.1	648.5
32.5°	554.4	562.5	570.6	599.0	633.3	664.3	695.2	720.0	722.9	699.7	655.5
35°	430.7	440.9	455.7	470.4	507.3	539.1	593.3	640.6	678.2	683.2	656.1
37.5°	347.1	352.1	361.5	376.3	400.4	438.1	480.0	539.7	594.3	634.9	636.6
40°	303.4	304.9	315.4	326.6	346.2	377.2	415.0	467.9	533.1	589.9	613.5
42.5°	270.6	273.9	278.4	289.1	304.8	328.0	363.2	406.9	466.8	532.0	578.1
45°	232.5	236.2	239.0	246.2	257.3	273.0	297.5	337.4	382.9	450.3	512.5
47.5°	207.4	207.6	209.7	215.2	222.7	234.5	251.8	277.4	319.2	373.9	437.8
50°	189.3	192.3	193.1	197.3	203.2	211.8	226.2	248.0	282.3	330.3	389.0
52.5°	176.7	177.5	179.6	182.7	187.8	194.6	207.1	224.1	251.0	292.0	345.9
55°	158.0	158.0	160.0	162.4	165.3	171.4	179.7	192.3	212.8	244.5	289.2
57.5°	140.7	141.6	143.1	143.8	146.3	150.4	157.2	166.8	182.0	206.5	242.0
60°	129.2	130.9	130.6	132.1	134.4	137.5	143.4	151.1	164.8	184.3	214.3
62.5°	119.1	119.1	119.0	120.8	122.9	126.0	129.8	136.5	148.1	165.5	190.9
65°	102.6	102.3	103.5	104.6	105.4	107.6	110.5	116.5	124.2	137.1	156.9
67.5°	87.9	86.8	87.5	87.9	89.2	90.9	93.7	97.4	103.5	113.8	128.7
70°	77.9	76.9	76.8	77.2	78.3	79.5	81.6	85.1	90.8	99.1	110.0
72.5°	67.6	66.9	66.9	67.7	68.2	69.1	70.5	73.7	78.3	84.5	94.7
75°	52.8	52.8	52.8	53.0	53.6	54.3	55.4	57.0	60.5	65.0	71.8
77.5°	39.5	39.5	39.3	39.3	40.1	40.4	40.6	42.2	44.2	47.1	52.1
80°	31.0	30.1	30.4	31.0	31.4	31.5	32.1	32.5	34.1	35.8	39.3
82.5°	23.1	22.3	22.3	23.2	23.3	23.4	24.0	24.5	25.1	26.6	28.5
85°	12.2	12.2	12.4	12.4	12.5	12.4	12.9	13.1	13.1	14.0	15.1
87.5°	7.1	6.8	6.9	7.0	6.9	6.9	6.9	7.0	7.1	7.3	7.1
90°	13.1	13.5	13.1	12.7	13.1	12.2	11.7	11.3	10.9	11.3	9.9
92.5°	21.8	22.6	22.1	23.5	24.3	26.7	30.2	38.0	52.4	69.5	76.4
95°	52.4	54.2	57.4	61.5	70.0	86.3	110.3	162.6	217.3	267.9	238.6
97.5°	142.7	146.6	158.8	179.1	212.5	266.5	324.8	405.5	444.3	415.3	304.0
100°	283.3	282.9	300.5	333.4	379.1	443.2	496.1	532.7	516.9	427.9	289.1
102.5°	415.6	426.0	440.7	466.8	502.3	543.0	573.9	575.0	520.5	404.4	267.5
105°	574.7	577.0	591.4	608.6	629.4	641.2	632.6	587.4	493.0	363.3	240.8
107.5°	666.4	670.5	675.4	681.2	680.8	664.7	625.2	551.8	444.7	326.9	223.9
110°	703.9	704.9	705.8	702.2	689.5	657.9	600.9	517.8	414.3	306.3	217.3



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	711.5	711.4	708.0	696.7	673.6	633.0	569.1	484.2	387.9	292.6	213.7
115°	699.0	696.7	687.7	667.8	633.9	584.7	518.2	439.7	356.1	277.9	212.4
117.5°	659.0	656.0	642.9	620.2	584.9	534.9	475.2	407.3	336.8	269.2	213.2
120°	625.8	623.1	612.3	586.9	551.3	505.6	451.4	390.4	326.7	265.2	214.6
122.5°	594.7	591.3	579.3	556.6	524.8	482.4	432.2	377.0	318.4	262.7	217.1
125°	551.3	548.1	536.8	516.9	488.0	451.9	408.4	359.2	307.7	259.4	220.9
127.5°	515.5	512.5	502.3	485.4	459.6	426.7	387.6	343.6	298.3	257.7	225.3
130°	495.2	491.6	482.1	465.9	441.9	411.1	374.5	333.9	293.3	256.7	228.1
132.5°	475.3	472.8	464.4	448.1	425.6	396.3	362.3	324.9	288.5	256.3	230.4
135°	446.9	443.7	435.5	422.0	399.9	374.1	344.8	312.7	282.4	255.7	233.6
137.5°	416.8	414.7	407.8	394.1	375.5	353.2	327.9	301.6	277.1	254.8	235.8
140°	395.8	396.2	389.0	376.4	359.2	339.8	318.1	295.1	273.8	254.4	237.2
142.5°	376.3	376.8	370.3	359.0	344.4	327.5	308.7	288.9	270.9	253.7	238.3
145°	349.3	348.4	344.8	335.3	324.0	310.9	296.4	281.5	267.0	252.5	239.0
147.5°	327.0	326.7	323.2	316.8	308.2	299.0	287.2	275.4	263.2	250.9	239.0
150°	314.0	314.0	311.3	306.3	299.6	291.0	281.5	271.1	260.7	249.4	239.0
152.5°	303.2	303.2	301.6	296.9	291.6	284.5	276.1	267.1	257.9	247.6	238.0
155°	289.6	289.1	288.3	284.6	280.6	275.2	268.4	261.2	253.5	244.5	236.8
157.5°	277.3	277.3	276.6	273.9	270.4	266.2	260.9	254.8	248.6	241.6	235.2
160°	269.3	269.7	269.7	267.0	263.9	260.7	256.2	251.2	245.3	239.5	234.5
162.5°	262.1	262.5	262.5	260.2	258.1	255.3	251.1	246.9	242.1	237.3	233.1
165°	252.5	252.5	253.0	251.2	249.4	247.2	244.0	241.3	237.7	234.1	230.9
167.5°	243.5	243.5	244.0	242.7	241.9	240.3	238.4	236.4	233.5	230.8	228.7
170°	238.1	238.1	238.6	237.7	237.2	236.3	234.5	233.1	230.9	228.6	227.3
172.5°	233.1	233.5	234.2	233.3	233.2	232.7	231.2	230.3	228.4	226.8	226.2
175°	227.3	227.8	228.1	227.8	227.8	227.8	226.8	226.4	225.5	224.6	224.6
177.5°	223.9	223.9	224.7	224.3	224.7	224.7	224.3	223.9	223.6	223.2	223.6
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	392.7	391.6	390.4	388.3	386.5	384.0	383.3	382.4	379.7	377.4	375.6
5°	416.7	412.3	405.8	399.9	395.1	388.6	385.0	381.1	375.6	370.6	366.5
7.5°	441.8	433.1	423.0	412.3	402.1	392.4	384.5	377.5	369.7	362.4	356.6
10°	461.8	449.2	435.1	420.0	407.1	394.6	384.0	374.9	364.9	356.2	349.0
12.5°	484.5	465.9	446.6	428.2	412.9	395.5	382.7	371.0	359.7	349.3	341.2
15°	511.4	487.7	464.9	439.6	416.4	394.6	379.5	364.6	351.6	340.9	330.5
17.5°	535.9	509.1	479.0	448.2	420.2	394.3	373.2	356.5	340.1	327.0	316.7
20°	549.8	519.4	485.2	453.3	422.2	393.5	370.2	350.3	332.6	318.7	307.1
22.5°	561.7	526.1	490.8	456.6	422.1	391.1	364.7	344.2	325.0	311.5	299.1
25°	574.2	531.5	496.1	456.1	417.5	385.3	355.8	332.6	313.4	297.5	284.8
27.5°	584.8	531.2	489.1	446.0	410.1	378.0	346.4	321.5	301.1	283.8	270.9
30°	591.8	531.9	481.9	439.3	403.1	369.9	339.2	314.1	292.7	275.2	263.0
32.5°	596.3	531.4	475.2	429.8	391.8	362.4	331.4	305.4	283.4	266.2	254.4
35°	598.9	528.1	463.7	410.3	373.8	345.1	319.1	292.2	269.1	253.0	239.7
37.5°	593.7	521.3	450.5	391.4	351.4	323.3	301.3	278.5	256.4	238.7	227.2
40°	585.6	516.9	440.1	378.1	336.0	309.0	290.3	267.8	246.0	229.2	218.5
42.5°	570.1	507.9	428.8	363.4	320.1	293.0	275.8	257.0	236.4	220.6	209.9
45°	532.3	488.3	411.7	341.3	296.6	268.5	253.4	239.7	221.1	205.8	196.5
47.5°	479.7	458.8	387.1	317.9	272.0	245.0	229.3	218.3	204.7	192.3	183.5
50°	443.3	434.6	370.4	301.9	255.6	229.2	214.0	204.1	194.3	182.0	173.9
52.5°	401.2	406.5	350.9	285.4	238.9	212.9	198.8	190.8	182.0	171.7	164.7
55°	342.0	361.3	317.3	257.6	214.0	189.3	175.9	168.9	163.7	156.1	150.0
57.5°	286.5	311.2	280.8	229.0	189.6	168.3	155.4	147.8	144.5	140.5	135.7
60°	253.6	277.9	254.8	209.8	173.3	153.0	141.6	135.1	131.7	129.0	124.9
62.5°	224.2	248.8	229.5	190.4	157.2	138.4	128.4	122.1	119.5	118.1	114.6
65°	183.8	205.0	192.1	160.0	134.2	117.6	108.5	104.1	101.7	101.2	98.9
67.5°	149.6	165.7	156.4	132.7	112.4	98.1	90.4	86.6	84.8	84.5	82.9
70°	127.1	142.3	135.1	113.7	96.2	84.9	78.3	74.9	73.8	73.7	72.7
72.5°	109.7	120.3	114.5	96.7	83.2	73.0	68.0	64.6	63.4	63.6	63.0
75°	81.2	89.1	85.8	73.4	62.6	55.9	51.9	49.7	48.6	49.1	48.3
77.5°	58.5	63.5	60.4	51.9	45.2	40.4	37.4	36.0	35.0	35.0	34.7
80°	44.1	47.1	45.4	40.2	34.7	30.7	28.2	27.3	26.8	26.5	26.4
82.5°	31.4	33.9	31.9	28.4	24.6	22.2	20.8	19.6	19.3	19.3	19.2
85°	15.8	16.8	16.1	13.9	12.4	11.2	10.5	10.0	9.6	9.7	9.4
87.5°	7.2	7.1	6.3	5.5	5.1	4.4	4.2	3.7	3.6	3.8	3.9
90°	8.6	7.2	5.9	5.0	4.0	2.7	1.8	0.9	1.8	2.7	4.0
92.5°	57.4	37.9	26.1	19.4	15.6	12.1	8.3	5.6	8.3	12.1	15.6
95°	164.5	97.1	58.7	41.1	29.4	21.7	16.7	15.4	16.7	21.7	29.4
97.5°	180.5	104.6	67.9	48.8	37.2	30.6	26.7	26.2	26.7	30.6	37.2
100°	170.3	103.5	71.9	54.2	43.4	37.1	33.9	33.4	33.9	37.1	43.4
102.5°	161.7	104.9	76.5	60.4	50.6	44.7	41.8	41.0	41.8	44.7	50.6
105°	155.4	108.9	84.5	70.5	61.9	56.5	53.8	52.4	53.8	56.5	61.9
107.5°	155.0	116.3	94.9	81.9	73.8	68.5	65.9	64.5	65.9	68.5	73.8
110°	156.8	122.5	102.1	89.4	81.8	76.8	74.5	73.2	74.5	76.8	81.8



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	160.4	128.6	109.7	97.4	89.8	84.8	82.5	81.1	82.5	84.8	89.8
115°	166.3	138.7	121.5	109.3	101.6	97.1	94.4	92.6	94.4	97.1	101.6
117.5°	174.0	149.5	132.5	121.2	112.6	108.4	106.2	104.1	106.2	108.4	112.6
120°	179.8	156.3	140.1	128.8	120.2	115.7	113.4	112.1	113.4	115.7	120.2
122.5°	185.3	163.6	147.7	135.6	127.4	122.6	120.3	118.9	120.3	122.6	127.4
125°	193.8	174.0	158.1	145.9	137.4	132.4	129.7	128.8	129.7	132.4	137.4
127.5°	200.9	183.0	167.7	155.5	146.0	141.0	137.6	136.3	137.6	141.0	146.0
130°	205.6	188.4	173.5	161.3	151.8	146.4	142.4	141.0	142.4	146.4	151.8
132.5°	209.9	193.1	178.6	166.8	157.2	150.8	146.3	144.6	146.3	150.8	157.2
135°	215.6	200.2	186.2	174.0	164.5	157.7	152.7	150.9	152.7	157.7	164.5
137.5°	219.7	205.0	191.5	180.3	170.9	163.7	158.8	156.9	158.8	163.7	170.9
140°	221.9	208.3	195.2	183.9	174.8	167.6	163.1	160.9	163.1	167.6	174.8
142.5°	224.0	210.8	198.1	187.5	178.5	172.0	167.1	165.2	167.1	172.0	178.5
145°	226.4	214.2	202.4	192.0	184.3	177.6	173.5	172.1	173.5	177.6	184.3
147.5°	227.8	216.9	206.1	197.3	189.9	184.0	180.0	179.2	180.0	184.0	189.9
150°	228.1	218.7	208.3	200.2	193.8	188.0	184.3	183.9	184.3	188.0	193.8
152.5°	228.9	219.8	210.8	203.0	197.5	192.3	188.7	188.6	188.7	192.3	197.5
155°	229.1	221.9	214.2	207.9	202.9	198.4	195.7	195.7	195.7	198.4	202.9
157.5°	229.6	223.0	216.9	212.0	207.8	203.7	201.6	201.2	201.6	203.7	207.8
160°	229.6	224.1	218.7	214.2	211.0	207.4	205.6	205.6	205.6	207.4	211.0
162.5°	229.2	224.5	219.8	215.9	213.2	210.3	208.8	208.8	208.8	210.3	213.2
165°	228.1	225.0	221.4	218.2	216.4	214.2	213.3	213.7	213.3	214.2	216.4
167.5°	227.4	224.9	222.3	220.3	219.0	217.3	216.9	217.5	216.9	217.3	219.0
170°	226.4	224.6	222.3	221.4	220.5	219.1	218.7	219.6	218.7	219.1	220.5
172.5°	226.0	224.6	222.7	222.1	221.6	220.6	220.5	221.0	220.5	220.6	221.6
175°	225.0	224.1	223.2	222.8	222.8	221.9	222.3	222.8	222.3	221.9	222.8
177.5°	224.3	223.6	223.2	223.2	223.2	222.8	223.2	223.6	223.2	222.8	223.2
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	374.5	373.5	372.1	369.9	368.0	365.3	365.3	365.7	365.7	365.6	365.3
5°	363.2	360.4	357.1	353.2	349.2	345.1	344.4	342.9	341.8	341.0	340.2
7.5°	351.2	346.3	341.4	336.0	331.1	327.0	324.2	321.8	320.3	318.6	317.4
10°	343.1	337.0	331.3	325.6	319.2	314.3	311.2	309.0	307.3	305.8	305.1
12.5°	333.5	326.5	320.2	314.7	307.9	302.8	299.8	298.7	296.8	293.7	292.1
15°	319.5	313.0	305.5	297.1	293.8	287.6	284.0	282.3	281.2	278.8	278.1
17.5°	307.4	299.0	290.5	284.3	278.1	273.1	271.1	269.0	267.6	265.6	265.0
20°	297.9	290.3	282.6	275.9	269.4	263.9	262.2	260.8	259.3	258.4	257.6
22.5°	288.1	280.6	274.1	267.9	261.0	257.4	255.6	254.0	252.9	252.3	251.6
25°	274.4	267.8	260.5	255.1	249.5	247.1	246.0	245.1	244.3	243.4	243.2
27.5°	262.2	254.9	249.1	243.9	240.0	238.0	236.9	236.5	236.6	236.9	237.2
30°	253.0	246.4	241.6	237.2	233.5	231.6	231.4	231.4	232.2	232.3	232.7
32.5°	244.6	239.2	234.3	230.0	227.3	226.0	226.7	226.7	227.3	227.8	228.5
35°	232.3	227.5	223.9	220.1	217.8	218.3	218.7	219.0	220.0	221.1	221.8
37.5°	220.6	216.5	212.6	209.8	208.7	209.6	210.6	211.3	212.4	213.3	214.0
40°	212.2	209.1	205.4	202.8	203.2	203.7	204.5	205.4	206.4	206.9	207.6
42.5°	204.4	201.1	198.3	196.1	196.7	197.4	197.8	198.3	199.4	200.4	200.8
45°	192.5	189.9	187.4	186.0	186.4	186.8	187.1	187.7	188.6	189.3	189.6
47.5°	179.1	177.3	175.5	174.3	174.9	174.8	175.2	176.4	176.7	177.1	178.2
50°	170.6	168.9	166.8	166.4	166.4	166.4	166.7	168.1	168.1	168.9	169.6
52.5°	161.1	160.0	158.8	158.0	157.7	157.7	158.5	159.2	159.5	160.6	161.4
55°	147.1	146.0	144.9	144.3	143.9	144.3	145.8	146.2	147.1	147.7	148.2
57.5°	132.5	131.7	130.8	130.5	130.4	130.9	131.7	132.8	133.0	134.8	135.5
60°	122.9	121.6	120.9	120.9	120.5	122.2	121.8	123.7	124.1	125.2	126.4
62.5°	113.0	111.3	111.0	111.0	111.5	112.0	112.5	113.3	114.3	115.7	116.7
65°	97.0	96.2	97.4	97.3	96.9	98.0	98.0	98.9	100.1	101.3	103.4
67.5°	82.0	81.5	81.6	81.6	82.1	82.8	83.3	84.1	85.5	86.8	88.2
70°	71.8	72.3	71.5	72.2	72.7	72.9	73.3	74.4	75.8	76.8	78.3
72.5°	61.9	61.9	61.9	62.3	62.8	63.1	63.5	64.8	66.4	67.2	68.4
75°	47.6	47.5	48.0	48.0	48.9	49.3	49.7	50.2	51.7	52.8	53.7
77.5°	34.8	35.0	34.9	35.5	35.3	35.3	36.4	37.0	37.2	39.4	39.8
80°	26.2	26.5	26.8	26.9	27.1	26.8	28.0	28.6	28.6	29.9	30.8
82.5°	18.9	19.0	19.5	19.7	19.7	20.1	20.2	20.6	21.1	21.6	22.8
85°	9.4	10.0	10.1	10.0	10.1	9.7	10.3	10.5	10.7	10.7	10.7
87.5°	4.0	4.3	4.4	4.8	4.9	5.4	5.3	5.1	5.1	5.7	5.3
90°	5.0	5.9	7.2	8.6	9.9	11.3	10.9	11.3	11.7	12.2	13.1
92.5°	19.4	26.1	37.9	57.4	76.4	69.5	52.4	38.0	30.2	26.7	24.3
95°	41.1	58.7	97.1	164.5	238.6	267.9	217.3	162.6	110.3	86.3	70.0
97.5°	48.8	67.9	104.6	180.5	304.0	415.3	444.3	405.5	324.8	266.5	212.5
100°	54.2	71.9	103.5	170.3	289.1	427.9	516.9	532.7	496.1	443.2	379.1
102.5°	60.4	76.5	104.9	161.7	267.5	404.4	520.5	575.0	573.9	543.0	502.3
105°	70.5	84.5	108.9	155.4	240.8	363.3	493.0	587.4	632.6	641.2	629.4
107.5°	81.9	94.9	116.3	155.0	223.9	326.9	444.7	551.8	625.2	664.7	680.8
110°	89.4	102.1	122.5	156.8	217.3	306.3	414.3	517.8	600.9	657.9	689.5



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	97.4	109.7	128.6	160.4	213.7	292.6	387.9	484.2	569.1	633.0	673.6
115°	109.3	121.5	138.7	166.3	212.4	277.9	356.1	439.7	518.2	584.7	633.9
117.5°	121.2	132.5	149.5	174.0	213.2	269.2	336.8	407.3	475.2	534.9	584.9
120°	128.8	140.1	156.3	179.8	214.6	265.2	326.7	390.4	451.4	505.6	551.3
122.5°	135.6	147.7	163.6	185.3	217.1	262.7	318.4	377.0	432.2	482.4	524.8
125°	145.9	158.1	174.0	193.8	220.9	259.4	307.7	359.2	408.4	451.9	488.0
127.5°	155.5	167.7	183.0	200.9	225.3	257.7	298.3	343.6	387.6	426.7	459.6
130°	161.3	173.5	188.4	205.6	228.1	256.7	293.3	333.9	374.5	411.1	441.9
132.5°	166.8	178.6	193.1	209.9	230.4	256.3	288.5	324.9	362.3	396.3	425.6
135°	174.0	186.2	200.2	215.6	233.6	255.7	282.4	312.7	344.8	374.1	399.9
137.5°	180.3	191.5	205.0	219.7	235.8	254.8	277.1	301.6	327.9	353.2	375.5
140°	183.9	195.2	208.3	221.9	237.2	254.4	273.8	295.1	318.1	339.8	359.2
142.5°	187.5	198.1	210.8	224.0	238.3	253.7	270.9	288.9	308.7	327.5	344.4
145°	192.0	202.4	214.2	226.4	239.0	252.5	267.0	281.5	296.4	310.9	324.0
147.5°	197.3	206.1	216.9	227.8	239.0	250.9	263.2	275.4	287.2	299.0	308.2
150°	200.2	208.3	218.7	228.1	239.0	249.4	260.7	271.1	281.5	291.0	299.6
152.5°	203.0	210.8	219.8	228.9	238.0	247.6	257.9	267.1	276.1	284.5	291.6
155°	207.9	214.2	221.9	229.1	236.8	244.5	253.5	261.2	268.4	275.2	280.6
157.5°	212.0	216.9	223.0	229.6	235.2	241.6	248.6	254.8	260.9	266.2	270.4
160°	214.2	218.7	224.1	229.6	234.5	239.5	245.3	251.2	256.2	260.7	263.9
162.5°	215.9	219.8	224.5	229.2	233.1	237.3	242.1	246.9	251.1	255.3	258.1
165°	218.2	221.4	225.0	228.1	230.9	234.1	237.7	241.3	244.0	247.2	249.4
167.5°	220.3	222.3	224.9	227.4	228.7	230.8	233.5	236.4	238.4	240.3	241.9
170°	221.4	222.3	224.6	226.4	227.3	228.6	230.9	233.1	234.5	236.3	237.2
172.5°	222.1	222.7	224.6	226.0	226.2	226.8	228.4	230.3	231.2	232.7	233.2
175°	222.8	223.2	224.1	225.0	224.6	224.6	225.5	226.4	226.8	227.8	227.8
177.5°	223.2	223.2	223.6	224.3	223.6	223.2	223.6	223.9	224.3	224.7	224.7
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	364.2	364.1	365.1	364.4	365.1	364.1	364.2	365.3	365.6	365.7	365.7
5°	339.1	339.6	337.7	337.7	337.7	339.6	339.1	340.2	341.0	341.8	342.9
7.5°	316.6	315.8	315.8	314.8	315.8	315.8	316.6	317.4	318.6	320.3	321.8
10°	302.9	301.7	301.3	301.6	301.3	301.7	302.9	305.1	305.8	307.3	309.0
12.5°	291.4	291.3	288.8	288.8	288.8	291.3	291.4	292.1	293.7	296.8	298.7
15°	278.1	274.6	274.3	275.4	274.3	274.6	278.1	278.1	278.8	281.2	282.3
17.5°	264.7	262.8	263.0	262.4	263.0	262.8	264.7	265.0	265.6	267.6	269.0
20°	257.6	256.5	256.4	255.1	256.4	256.5	257.6	257.6	258.4	259.3	260.8
22.5°	251.1	250.8	250.9	249.5	250.9	250.8	251.1	251.6	252.3	252.9	254.0
25°	243.0	244.0	243.2	243.2	243.2	244.0	243.0	243.2	243.4	244.3	245.1
27.5°	237.6	237.6	237.2	237.2	237.2	237.6	237.6	237.2	236.9	236.6	236.5
30°	233.5	233.3	233.6	233.6	233.6	233.3	233.5	232.7	232.3	232.2	231.4
32.5°	229.3	229.6	229.7	229.8	229.7	229.6	229.3	228.5	227.8	227.3	226.7
35°	222.9	223.2	223.7	223.3	223.7	223.2	222.9	221.8	221.1	220.0	219.0
37.5°	214.3	215.2	215.0	215.2	215.0	215.2	214.3	214.0	213.3	212.4	211.3
40°	207.8	208.3	208.2	208.2	208.2	208.3	207.8	207.6	206.9	206.4	205.4
42.5°	201.1	201.5	201.1	200.8	201.1	201.5	201.1	200.8	200.4	199.4	198.3
45°	190.3	189.9	190.4	189.7	190.4	189.9	190.3	189.6	189.3	188.6	187.7
47.5°	178.1	178.5	178.6	179.2	178.6	178.5	178.1	178.2	177.1	176.7	176.4
50°	170.0	171.1	171.1	170.9	171.1	171.1	170.0	169.6	168.9	168.1	168.1
52.5°	162.0	162.5	163.3	163.2	163.3	162.5	162.0	161.4	160.6	159.5	159.2
55°	149.6	150.0	150.4	150.6	150.4	150.0	149.6	148.2	147.7	147.1	146.2
57.5°	136.9	136.7	137.6	137.9	137.6	136.7	136.9	135.5	134.8	133.0	132.8
60°	127.9	127.9	129.4	129.9	129.4	127.9	127.9	126.4	125.2	124.1	123.7
62.5°	118.3	118.9	120.3	119.6	120.3	118.9	118.3	116.7	115.7	114.3	113.3
65°	104.3	105.8	105.6	106.3	105.6	105.8	104.3	103.4	101.3	100.1	98.9
67.5°	89.6	90.5	91.9	92.0	91.9	90.5	89.6	88.2	86.8	85.5	84.1
70°	79.7	80.6	81.4	81.9	81.4	80.6	79.7	78.3	76.8	75.8	74.4
72.5°	70.1	70.6	72.4	71.6	72.4	70.6	70.1	68.4	67.2	66.4	64.8
75°	55.0	56.3	57.4	56.9	57.4	56.3	55.0	53.7	52.8	51.7	50.2
77.5°	40.6	42.0	42.5	42.0	42.5	42.0	40.6	39.8	39.4	37.2	37.0
80°	32.1	31.9	33.0	32.9	33.0	31.9	32.1	30.8	29.9	28.6	28.6
82.5°	23.5	23.4	23.8	24.0	23.8	23.4	23.5	22.8	21.6	21.1	20.6
85°	11.4	12.0	11.2	11.1	11.2	12.0	11.4	10.7	10.7	10.7	10.5
87.5°	5.1	5.3	5.2	5.0	5.2	5.3	5.1	5.3	5.7	5.1	5.1
90°	12.7	13.1	13.5	13.1	13.5	13.1	12.7	13.1	12.2	11.7	11.3
92.5°	23.5	22.1	22.6	21.8	22.6	22.1	23.5	24.3	26.7	30.2	38.0
95°	61.5	57.4	54.2	52.4	54.2	57.4	61.5	70.0	86.3	110.3	162.6
97.5°	179.1	158.8	146.6	142.7	146.6	158.8	179.1	212.5	266.5	324.8	405.5
100°	333.4	300.5	282.9	283.3	282.9	300.5	333.4	379.1	443.2	496.1	532.7
102.5°	466.8	440.7	426.0	415.6	426.0	440.7	466.8	502.3	543.0	573.9	575.0
105°	608.6	591.4	577.0	574.7	577.0	591.4	608.6	629.4	641.2	632.6	587.4
107.5°	681.2	675.4	670.5	666.4	670.5	675.4	681.2	680.8	664.7	625.2	551.8
110°	702.2	705.8	704.9	703.9	704.9	705.8	702.2	689.5	657.9	600.9	517.8



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	696.7	708.0	711.4	711.5	711.4	708.0	696.7	673.6	633.0	569.1	484.2
115°	667.8	687.7	696.7	699.0	696.7	687.7	667.8	633.9	584.7	518.2	439.7
117.5°	620.2	642.9	656.0	659.0	656.0	642.9	620.2	584.9	534.9	475.2	407.3
120°	586.9	612.3	623.1	625.8	623.1	612.3	586.9	551.3	505.6	451.4	390.4
122.5°	556.6	579.3	591.3	594.7	591.3	579.3	556.6	524.8	482.4	432.2	377.0
125°	516.9	536.8	548.1	551.3	548.1	536.8	516.9	488.0	451.9	408.4	359.2
127.5°	485.4	502.3	512.5	515.5	512.5	502.3	485.4	459.6	426.7	387.6	343.6
130°	465.9	482.1	491.6	495.2	491.6	482.1	465.9	441.9	411.1	374.5	333.9
132.5°	448.1	464.4	472.8	475.3	472.8	464.4	448.1	425.6	396.3	362.3	324.9
135°	422.0	435.5	443.7	446.9	443.7	435.5	422.0	399.9	374.1	344.8	312.7
137.5°	394.1	407.8	414.7	416.8	414.7	407.8	394.1	375.5	353.2	327.9	301.6
140°	376.4	389.0	396.2	395.8	396.2	389.0	376.4	359.2	339.8	318.1	295.1
142.5°	359.0	370.3	376.8	376.3	376.8	370.3	359.0	344.4	327.5	308.7	288.9
145°	335.3	344.8	348.4	349.3	348.4	344.8	335.3	324.0	310.9	296.4	281.5
147.5°	316.8	323.2	326.7	327.0	326.7	323.2	316.8	308.2	299.0	287.2	275.4
150°	306.3	311.3	314.0	314.0	314.0	311.3	306.3	299.6	291.0	281.5	271.1
152.5°	296.9	301.6	303.2	303.2	303.2	301.6	296.9	291.6	284.5	276.1	267.1
155°	284.6	288.3	289.1	289.6	289.1	288.3	284.6	280.6	275.2	268.4	261.2
157.5°	273.9	276.6	277.3	277.3	277.3	276.6	273.9	270.4	266.2	260.9	254.8
160°	267.0	269.7	269.7	269.3	269.7	269.7	267.0	263.9	260.7	256.2	251.2
162.5°	260.2	262.5	262.5	262.1	262.5	262.5	260.2	258.1	255.3	251.1	246.9
165°	251.2	253.0	252.5	252.5	252.5	253.0	251.2	249.4	247.2	244.0	241.3
167.5°	242.7	244.0	243.5	243.5	243.5	244.0	242.7	241.9	240.3	238.4	236.4
170°	237.7	238.6	238.1	238.1	238.1	238.6	237.7	237.2	236.3	234.5	233.1
172.5°	233.3	234.2	233.5	233.1	233.5	234.2	233.3	233.2	232.7	231.2	230.3
175°	227.8	228.1	227.8	227.3	227.8	228.1	227.8	227.8	227.8	226.8	226.4
177.5°	224.3	224.7	223.9	223.9	223.9	224.7	224.3	224.7	224.7	224.3	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	365.3	365.3	368.0	369.9	372.1	373.5	374.5	375.6	377.4	379.7	382.4
5°	344.4	345.1	349.2	353.2	357.1	360.4	363.2	366.5	370.6	375.6	381.1
7.5°	324.2	327.0	331.1	336.0	341.4	346.3	351.2	356.6	362.4	369.7	377.5
10°	311.2	314.3	319.2	325.6	331.3	337.0	343.1	349.0	356.2	364.9	374.9
12.5°	299.8	302.8	307.9	314.7	320.2	326.5	333.5	341.2	349.3	359.7	371.0
15°	284.0	287.6	293.8	297.1	305.5	313.0	319.5	330.5	340.9	351.6	364.6
17.5°	271.1	273.1	278.1	284.3	290.5	299.0	307.4	316.7	327.0	340.1	356.5
20°	262.2	263.9	269.4	275.9	282.6	290.3	297.9	307.1	318.7	332.6	350.3
22.5°	255.6	257.4	261.0	267.9	274.1	280.6	288.1	299.1	311.5	325.0	344.2
25°	246.0	247.1	249.5	255.1	260.5	267.8	274.4	284.8	297.5	313.4	332.6
27.5°	236.9	238.0	240.0	243.9	249.1	254.9	262.2	270.9	283.8	301.1	321.5
30°	231.4	231.6	233.5	237.2	241.6	246.4	253.0	263.0	275.2	292.7	314.1
32.5°	226.7	226.0	227.3	230.0	234.3	239.2	244.6	254.4	266.2	283.4	305.4
35°	218.7	218.3	217.8	220.1	223.9	227.5	232.3	239.7	253.0	269.1	292.2
37.5°	210.6	209.6	208.7	209.8	212.6	216.5	220.6	227.2	238.7	256.4	278.5
40°	204.5	203.7	203.2	202.8	205.4	209.1	212.2	218.5	229.2	246.0	267.8
42.5°	197.8	197.4	196.7	196.1	198.3	201.1	204.4	209.9	220.6	236.4	257.0
45°	187.1	186.8	186.4	186.0	187.4	189.9	192.5	196.5	205.8	221.1	239.7
47.5°	175.2	174.8	174.9	174.3	175.5	177.3	179.1	183.5	192.3	204.7	218.3
50°	166.7	166.4	166.4	166.4	166.8	168.9	170.6	173.9	182.0	194.3	204.1
52.5°	158.5	157.7	157.7	158.0	158.8	160.0	161.1	164.7	171.7	182.0	190.8
55°	145.8	144.3	143.9	144.3	144.9	146.0	147.1	150.0	156.1	163.7	168.9
57.5°	131.7	130.9	130.4	130.5	130.8	131.7	132.5	135.7	140.5	144.5	147.8
60°	121.8	122.2	120.5	120.9	120.9	121.6	122.9	124.9	129.0	131.7	135.1
62.5°	112.5	112.0	111.5	111.0	111.0	111.3	113.0	114.6	118.1	119.5	122.1
65°	98.0	98.0	96.9	97.3	97.4	96.2	97.0	98.9	101.2	101.7	104.1
67.5°	83.3	82.8	82.1	81.6	81.6	81.5	82.0	82.9	84.5	84.8	86.6
70°	73.3	72.9	72.7	72.2	71.5	72.3	71.8	72.7	73.7	73.8	74.9
72.5°	63.5	63.1	62.8	62.3	61.9	61.9	61.9	63.0	63.6	63.4	64.6
75°	49.7	49.3	48.9	48.0	48.0	47.5	47.6	48.3	49.1	48.6	49.7
77.5°	36.4	35.3	35.3	35.5	34.9	35.0	34.8	34.7	35.0	35.0	36.0
80°	28.0	26.8	27.1	26.9	26.8	26.5	26.2	26.4	26.5	26.8	27.3
82.5°	20.2	20.1	19.7	19.7	19.5	19.0	18.9	19.2	19.3	19.3	19.6
85°	10.3	9.7	10.1	10.0	10.1	10.0	9.4	9.4	9.7	9.6	10.0
87.5°	5.3	5.4	4.9	4.8	4.4	4.3	4.0	3.9	3.8	3.6	3.7
90°	10.9	11.3	9.9	8.6	7.2	5.9	5.0	4.0	2.7	1.8	0.9
92.5°	52.4	69.5	76.4	57.4	37.9	26.1	19.4	15.6	12.1	8.3	5.6
95°	217.3	267.9	238.6	164.5	97.1	58.7	41.1	29.4	21.7	16.7	15.4
97.5°	444.3	415.3	304.0	180.5	104.6	67.9	48.8	37.2	30.6	26.7	26.2
100°	516.9	427.9	289.1	170.3	103.5	71.9	54.2	43.4	37.1	33.9	33.4
102.5°	520.5	404.4	267.5	161.7	104.9	76.5	60.4	50.6	44.7	41.8	41.0
105°	493.0	363.3	240.8	155.4	108.9	84.5	70.5	61.9	56.5	53.8	52.4
107.5°	444.7	326.9	223.9	155.0	116.3	94.9	81.9	73.8	68.5	65.9	64.5
110°	414.3	306.3	217.3	156.8	122.5	102.1	89.4	81.8	76.8	74.5	73.2



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	387.9	292.6	213.7	160.4	128.6	109.7	97.4	89.8	84.8	82.5	81.1
115°	356.1	277.9	212.4	166.3	138.7	121.5	109.3	101.6	97.1	94.4	92.6
117.5°	336.8	269.2	213.2	174.0	149.5	132.5	121.2	112.6	108.4	106.2	104.1
120°	326.7	265.2	214.6	179.8	156.3	140.1	128.8	120.2	115.7	113.4	112.1
122.5°	318.4	262.7	217.1	185.3	163.6	147.7	135.6	127.4	122.6	120.3	118.9
125°	307.7	259.4	220.9	193.8	174.0	158.1	145.9	137.4	132.4	129.7	128.8
127.5°	298.3	257.7	225.3	200.9	183.0	167.7	155.5	146.0	141.0	137.6	136.3
130°	293.3	256.7	228.1	205.6	188.4	173.5	161.3	151.8	146.4	142.4	141.0
132.5°	288.5	256.3	230.4	209.9	193.1	178.6	166.8	157.2	150.8	146.3	144.6
135°	282.4	255.7	233.6	215.6	200.2	186.2	174.0	164.5	157.7	152.7	150.9
137.5°	277.1	254.8	235.8	219.7	205.0	191.5	180.3	170.9	163.7	158.8	156.9
140°	273.8	254.4	237.2	221.9	208.3	195.2	183.9	174.8	167.6	163.1	160.9
142.5°	270.9	253.7	238.3	224.0	210.8	198.1	187.5	178.5	172.0	167.1	165.2
145°	267.0	252.5	239.0	226.4	214.2	202.4	192.0	184.3	177.6	173.5	172.1
147.5°	263.2	250.9	239.0	227.8	216.9	206.1	197.3	189.9	184.0	180.0	179.2
150°	260.7	249.4	239.0	228.1	218.7	208.3	200.2	193.8	188.0	184.3	183.9
152.5°	257.9	247.6	238.0	228.9	219.8	210.8	203.0	197.5	192.3	188.7	188.6
155°	253.5	244.5	236.8	229.1	221.9	214.2	207.9	202.9	198.4	195.7	195.7
157.5°	248.6	241.6	235.2	229.6	223.0	216.9	212.0	207.8	203.7	201.6	201.2
160°	245.3	239.5	234.5	229.6	224.1	218.7	214.2	211.0	207.4	205.6	205.6
162.5°	242.1	237.3	233.1	229.2	224.5	219.8	215.9	213.2	210.3	208.8	208.8
165°	237.7	234.1	230.9	228.1	225.0	221.4	218.2	216.4	214.2	213.3	213.7
167.5°	233.5	230.8	228.7	227.4	224.9	222.3	220.3	219.0	217.3	216.9	217.5
170°	230.9	228.6	227.3	226.4	224.6	222.3	221.4	220.5	219.1	218.7	219.6
172.5°	228.4	226.8	226.2	226.0	224.6	222.7	222.1	221.6	220.6	220.5	221.0
175°	225.5	224.6	224.6	225.0	224.1	223.2	222.8	222.8	221.9	222.3	222.8
177.5°	223.6	223.2	223.6	224.3	223.6	223.2	223.2	223.2	222.8	223.2	223.6
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	383.3	384.0	386.5	388.3	390.4	391.6	392.7	393.6	394.8	395.1	399.3
5°	385.0	388.6	395.1	399.9	405.8	412.3	416.7	418.7	424.1	428.5	437.4
7.5°	384.5	392.4	402.1	412.3	423.0	433.1	441.8	452.2	459.5	470.6	481.4
10°	384.0	394.6	407.1	420.0	435.1	449.2	461.8	475.8	487.4	502.7	515.8
12.5°	382.7	395.5	412.9	428.2	446.6	465.9	484.5	502.5	512.8	538.3	550.3
15°	379.5	394.6	416.4	439.6	464.9	487.7	511.4	530.2	560.6	583.0	597.2
17.5°	373.2	394.3	420.2	448.2	479.0	509.1	535.9	564.4	596.8	623.8	652.6
20°	370.2	393.5	422.2	453.3	485.2	519.4	549.8	584.1	619.3	645.9	682.9
22.5°	364.7	391.1	422.1	456.6	490.8	526.1	561.7	596.4	637.1	673.7	708.8
25°	355.8	385.3	417.5	456.1	496.1	531.5	574.2	620.1	662.5	709.6	744.7
27.5°	346.4	378.0	410.1	446.0	489.1	531.2	584.8	636.7	688.6	729.2	755.2
30°	339.2	369.9	403.1	439.3	481.9	531.9	591.8	648.5	699.1	734.0	748.5
32.5°	331.4	362.4	391.8	429.8	475.2	531.4	596.3	655.5	699.7	722.9	720.0
35°	319.1	345.1	373.8	410.3	463.7	528.1	598.9	656.1	683.2	678.2	640.6
37.5°	301.3	323.3	351.4	391.4	450.5	521.3	593.7	636.6	634.9	594.3	539.7
40°	290.3	309.0	336.0	378.1	440.1	516.9	585.6	613.5	589.9	533.1	467.9
42.5°	275.8	293.0	320.1	363.4	428.8	507.9	570.1	578.1	532.0	466.8	406.9
45°	253.4	268.5	296.6	341.3	411.7	488.3	532.3	512.5	450.3	382.9	337.4
47.5°	229.3	245.0	272.0	317.9	387.1	458.8	479.7	437.8	373.9	319.2	277.4
50°	214.0	229.2	255.6	301.9	370.4	434.6	443.3	389.0	330.3	282.3	248.0
52.5°	198.8	212.9	238.9	285.4	350.9	406.5	401.2	345.9	292.0	251.0	224.1
55°	175.9	189.3	214.0	257.6	317.3	361.3	342.0	289.2	244.5	212.8	192.3
57.5°	155.4	168.3	189.6	229.0	280.8	311.2	286.5	242.0	206.5	182.0	166.8
60°	141.6	153.0	173.3	209.8	254.8	277.9	253.6	214.3	184.3	164.8	151.1
62.5°	128.4	138.4	157.2	190.4	229.5	248.8	224.2	190.9	165.5	148.1	136.5
65°	108.5	117.6	134.2	160.0	192.1	205.0	183.8	156.9	137.1	124.2	116.5
67.5°	90.4	98.1	112.4	132.7	156.4	165.7	149.6	128.7	113.8	103.5	97.4
70°	78.3	84.9	96.2	113.7	135.1	142.3	127.1	110.0	99.1	90.8	85.1
72.5°	68.0	73.0	83.2	96.7	114.5	120.3	109.7	94.7	84.5	78.3	73.7
75°	51.9	55.9	62.6	73.4	85.8	89.1	81.2	71.8	65.0	60.5	57.0
77.5°	37.4	40.4	45.2	51.9	60.4	63.5	58.5	52.1	47.1	44.2	42.2
80°	28.2	30.7	34.7	40.2	45.4	47.1	44.1	39.3	35.8	34.1	32.5
82.5°	20.8	22.2	24.6	28.4	31.9	33.9	31.4	28.5	26.6	25.1	24.5
85°	10.5	11.2	12.4	13.9	16.1	16.8	15.8	15.1	14.0	13.1	13.1
87.5°	4.2	4.4	5.1	5.5	6.3	7.1	7.2	7.1	7.3	7.1	7.0
90°	1.8	2.7	4.0	5.0	5.9	7.2	8.6	9.9	11.3	10.9	11.3
92.5°	8.3	12.1	15.6	19.4	26.1	37.9	57.4	76.4	69.5	52.4	38.0
95°	16.7	21.7	29.4	41.1	58.7	97.1	164.5	238.6	267.9	217.3	162.6
97.5°	26.7	30.6	37.2	48.8	67.9	104.6	180.5	304.0	415.3	444.3	405.5
100°	33.9	37.1	43.4	54.2	71.9	103.5	170.3	289.1	427.9	516.9	532.7
102.5°	41.8	44.7	50.6	60.4	76.5	104.9	161.7	267.5	404.4	520.5	575.0
105°	53.8	56.5	61.9	70.5	84.5	108.9	155.4	240.8	363.3	493.0	587.4
107.5°	65.9	68.5	73.8	81.9	94.9	116.3	155.0	223.9	326.9	444.7	551.8
110°	74.5	76.8	81.8	89.4	102.1	122.5	156.8	217.3	306.3	414.3	517.8



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	82.5	84.8	89.8	97.4	109.7	128.6	160.4	213.7	292.6	387.9	484.2
115°	94.4	97.1	101.6	109.3	121.5	138.7	166.3	212.4	277.9	356.1	439.7
117.5°	106.2	108.4	112.6	121.2	132.5	149.5	174.0	213.2	269.2	336.8	407.3
120°	113.4	115.7	120.2	128.8	140.1	156.3	179.8	214.6	265.2	326.7	390.4
122.5°	120.3	122.6	127.4	135.6	147.7	163.6	185.3	217.1	262.7	318.4	377.0
125°	129.7	132.4	137.4	145.9	158.1	174.0	193.8	220.9	259.4	307.7	359.2
127.5°	137.6	141.0	146.0	155.5	167.7	183.0	200.9	225.3	257.7	298.3	343.6
130°	142.4	146.4	151.8	161.3	173.5	188.4	205.6	228.1	256.7	293.3	333.9
132.5°	146.3	150.8	157.2	166.8	178.6	193.1	209.9	230.4	256.3	288.5	324.9
135°	152.7	157.7	164.5	174.0	186.2	200.2	215.6	233.6	255.7	282.4	312.7
137.5°	158.8	163.7	170.9	180.3	191.5	205.0	219.7	235.8	254.8	277.1	301.6
140°	163.1	167.6	174.8	183.9	195.2	208.3	221.9	237.2	254.4	273.8	295.1
142.5°	167.1	172.0	178.5	187.5	198.1	210.8	224.0	238.3	253.7	270.9	288.9
145°	173.5	177.6	184.3	192.0	202.4	214.2	226.4	239.0	252.5	267.0	281.5
147.5°	180.0	184.0	189.9	197.3	206.1	216.9	227.8	239.0	250.9	263.2	275.4
150°	184.3	188.0	193.8	200.2	208.3	218.7	228.1	239.0	249.4	260.7	271.1
152.5°	188.7	192.3	197.5	203.0	210.8	219.8	228.9	238.0	247.6	257.9	267.1
155°	195.7	198.4	202.9	207.9	214.2	221.9	229.1	236.8	244.5	253.5	261.2
157.5°	201.6	203.7	207.8	212.0	216.9	223.0	229.6	235.2	241.6	248.6	254.8
160°	205.6	207.4	211.0	214.2	218.7	224.1	229.6	234.5	239.5	245.3	251.2
162.5°	208.8	210.3	213.2	215.9	219.8	224.5	229.2	233.1	237.3	242.1	246.9
165°	213.3	214.2	216.4	218.2	221.4	225.0	228.1	230.9	234.1	237.7	241.3
167.5°	216.9	217.3	219.0	220.3	222.3	224.9	227.4	228.7	230.8	233.5	236.4
170°	218.7	219.1	220.5	221.4	222.3	224.6	226.4	227.3	228.6	230.9	233.1
172.5°	220.5	220.6	221.6	222.1	222.7	224.6	226.0	226.2	226.8	228.4	230.3
175°	222.3	221.9	222.8	222.8	223.2	224.1	225.0	224.6	224.6	225.5	226.4
177.5°	223.2	222.8	223.2	223.2	223.2	223.6	224.3	223.6	223.2	223.6	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	380.9	380.9	380.9	380.9	380.9	380.9	380.9
2.5°	400.8	401.0	402.6	403.8	403.2	403.9	404.3
5°	437.9	444.6	448.1	450.7	450.8	451.1	452.5
7.5°	490.5	497.6	502.9	510.8	513.1	515.8	515.1
10°	528.9	539.5	548.5	553.3	558.5	566.0	559.9
12.5°	564.8	583.4	597.2	604.7	609.5	611.0	608.1
15°	624.0	648.3	661.4	661.1	677.6	684.8	673.6
17.5°	678.2	700.7	718.7	727.9	741.8	744.8	743.5
20°	711.5	736.0	750.0	765.9	773.1	779.5	780.6
22.5°	740.1	762.2	777.2	790.4	796.4	799.5	801.3
25°	769.6	787.0	796.0	800.6	802.2	801.8	799.5
27.5°	767.5	768.9	758.9	749.2	740.4	730.6	727.1
30°	747.6	732.1	704.4	688.7	665.7	647.4	654.8
32.5°	695.2	664.3	633.3	599.0	570.6	562.5	554.4
35°	593.3	539.1	507.3	470.4	455.7	440.9	430.7
37.5°	480.0	438.1	400.4	376.3	361.5	352.1	347.1
40°	415.0	377.2	346.2	326.6	315.4	304.9	303.4
42.5°	363.2	328.0	304.8	289.1	278.4	273.9	270.6
45°	297.5	273.0	257.3	246.2	239.0	236.2	232.5
47.5°	251.8	234.5	222.7	215.2	209.7	207.6	207.4
50°	226.2	211.8	203.2	197.3	193.1	192.3	189.3
52.5°	207.1	194.6	187.8	182.7	179.6	177.5	176.7
55°	179.7	171.4	165.3	162.4	160.0	158.0	158.0
57.5°	157.2	150.4	146.3	143.8	143.1	141.6	140.7
60°	143.4	137.5	134.4	132.1	130.6	130.9	129.2
62.5°	129.8	126.0	122.9	120.8	119.0	119.1	119.1
65°	110.5	107.6	105.4	104.6	103.5	102.3	102.6
67.5°	93.7	90.9	89.2	87.9	87.5	86.8	87.9
70°	81.6	79.5	78.3	77.2	76.8	76.9	77.9
72.5°	70.5	69.1	68.2	67.7	66.9	66.9	67.6
75°	55.4	54.3	53.6	53.0	52.8	52.8	52.8
77.5°	40.6	40.4	40.1	39.3	39.3	39.5	39.5
80°	32.1	31.5	31.4	31.0	30.4	30.1	31.0
82.5°	24.0	23.4	23.3	23.2	22.3	22.3	23.1
85°	12.9	12.4	12.5	12.4	12.4	12.2	12.2
87.5°	6.9	6.9	6.9	7.0	6.9	6.8	7.1
90°	11.7	12.2	13.1	12.7	13.1	13.5	13.1
92.5°	30.2	26.7	24.3	23.5	22.1	22.6	21.8
95°	110.3	86.3	70.0	61.5	57.4	54.2	52.4
97.5°	324.8	266.5	212.5	179.1	158.8	146.6	142.7
100°	496.1	443.2	379.1	333.4	300.5	282.9	283.3
102.5°	573.9	543.0	502.3	466.8	440.7	426.0	415.6
105°	632.6	641.2	629.4	608.6	591.4	577.0	574.7
107.5°	625.2	664.7	680.8	681.2	675.4	670.5	666.4
110°	600.9	657.9	689.5	702.2	705.8	704.9	703.9



TEST NUMBER: P331876-927

CATALOG NUMBER: S123DIP-S340D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	569.1	633.0	673.6	696.7	708.0	711.4	711.5
115°	518.2	584.7	633.9	667.8	687.7	696.7	699.0
117.5°	475.2	534.9	584.9	620.2	642.9	656.0	659.0
120°	451.4	505.6	551.3	586.9	612.3	623.1	625.8
122.5°	432.2	482.4	524.8	556.6	579.3	591.3	594.7
125°	408.4	451.9	488.0	516.9	536.8	548.1	551.3
127.5°	387.6	426.7	459.6	485.4	502.3	512.5	515.5
130°	374.5	411.1	441.9	465.9	482.1	491.6	495.2
132.5°	362.3	396.3	425.6	448.1	464.4	472.8	475.3
135°	344.8	374.1	399.9	422.0	435.5	443.7	446.9
137.5°	327.9	353.2	375.5	394.1	407.8	414.7	416.8
140°	318.1	339.8	359.2	376.4	389.0	396.2	395.8
142.5°	308.7	327.5	344.4	359.0	370.3	376.8	376.3
145°	296.4	310.9	324.0	335.3	344.8	348.4	349.3
147.5°	287.2	299.0	308.2	316.8	323.2	326.7	327.0
150°	281.5	291.0	299.6	306.3	311.3	314.0	314.0
152.5°	276.1	284.5	291.6	296.9	301.6	303.2	303.2
155°	268.4	275.2	280.6	284.6	288.3	289.1	289.6
157.5°	260.9	266.2	270.4	273.9	276.6	277.3	277.3
160°	256.2	260.7	263.9	267.0	269.7	269.7	269.3
162.5°	251.1	255.3	258.1	260.2	262.5	262.5	262.1
165°	244.0	247.2	249.4	251.2	253.0	252.5	252.5
167.5°	238.4	240.3	241.9	242.7	244.0	243.5	243.5
170°	234.5	236.3	237.2	237.7	238.6	238.1	238.1
172.5°	231.2	232.7	233.2	233.3	234.2	233.5	233.1
175°	226.8	227.8	227.8	227.8	228.1	227.8	227.3
177.5°	224.3	224.7	224.7	224.3	224.7	223.9	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2

(END OF REPORT)