

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331939-927

Luminaire Tested: **S123DIP-S560D1025U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331939-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1025U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4832.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	39	33
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33	28
3	80	70	63	58	72	64	58	53	53	48	45	42	39	37	32	30	29	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	41	34	30	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6740	6740	6740	6740
5°	8038	6769	5999	6769
10°	10061	6735	5418	6735
15°	12340	6681	5045	6681
20°	14701	6596	4803	6596
25°	15610	6494	4749	6494
30°	13380	6418	4774	6418
35°	9305	6311	4824	6311
40°	7009	6185	4808	6185
45°	5820	5999	4748	5999
50°	5213	5620	4706	5620
55°	4874	5210	4647	5210
60°	4573	4781	4598	4781
65°	4297	4358	4452	4358
70°	4028	3877	4239	3877
75°	3606	3394	3889	3394
80°	3155	2783	3347	2783
85°	2470	2025	2248	2025



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.7	1.3
10°-20°	197.8	4.1
20°-30°	332.0	6.9
30°-40°	375.9	7.8
40°-50°	337.1	7.0
50°-60°	272.0	5.6
60°-70°	189.6	3.9
70°-80°	99.6	2.1
80°-90°	27.4	0.6
90°-100°	217.4	4.5
100°-110°	615.6	12.7
110°-120°	605.5	12.5
120°-130°	483.0	10.0
130°-140°	380.8	7.9
140°-150°	284.2	5.9
150°-160°	198.1	4.1
160°-170°	116.4	2.4
170°-180°	37.9	0.8
0°-30°	591.5	12.2
0°-40°	967.4	20.0
0°-60°	1576.5	32.6
0°-90°	1893.1	39.2
90°-120°	1438.5	29.8
90°-150°	2586.5	53.5
90°-180°	2939.0	60.8
0°-180°	4832.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	626	626	626	626	626	
5°	744	626	555	626	744	77
15°	1107	600	453	600	1107	320
25°	1314	547	400	547	1314	576
35°	708	480	367	480	708	460
45°	382	394	312	394	382	303
55°	260	278	248	278	260	233
65°	169	171	175	171	169	168
75°	87	82	94	82	87	93
85°	20	16	18	16	20	24
90°	23	2	23	2	23	13
95°	92	27	92	27	92	165
105°	1006	92	1006	92	1006	992
115°	1223	162	1223	162	1223	1189
125°	965	225	965	225	965	874
135°	782	264	782	264	782	607
145°	611	301	611	301	611	389
155°	507	342	507	342	507	236
165°	442	374	442	374	442	126
175°	398	390	398	390	398	39
180°	391	391	391	391	391	



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	664.6	664.1	662.9	663.8	661.9	659.3	659.0	656.6	649.5	649.0	647.1
5°	743.9	741.5	741.2	740.9	736.7	730.9	719.9	719.1	704.5	697.2	688.4
7.5°	846.8	848.0	843.6	839.7	826.7	818.2	806.4	791.5	773.6	755.4	743.3
10°	920.5	930.5	918.1	909.6	901.7	886.8	869.6	848.0	826.5	801.3	782.2
12.5°	999.7	1004.6	1002.1	994.0	981.8	959.2	928.5	904.8	884.9	843.0	826.1
15°	1107.4	1125.9	1114.1	1086.8	1087.4	1065.9	1025.8	981.8	958.5	921.7	871.6
17.5°	1222.3	1224.6	1219.5	1196.7	1181.5	1152.0	1115.0	1072.9	1025.5	981.1	928.0
20°	1283.4	1281.6	1271.0	1259.1	1233.0	1210.0	1169.6	1122.6	1061.9	1018.2	960.3
22.5°	1317.4	1314.3	1309.3	1299.4	1277.7	1252.9	1216.7	1165.3	1107.6	1047.3	980.4
25°	1314.3	1318.3	1318.9	1316.1	1308.6	1293.7	1265.2	1224.2	1166.6	1089.3	1019.5
27.5°	1195.4	1200.9	1217.2	1231.6	1247.7	1264.0	1261.9	1241.5	1198.9	1132.0	1046.7
30°	1076.5	1064.3	1094.4	1132.3	1158.1	1203.6	1229.1	1230.6	1206.7	1149.3	1066.1
32.5°	911.4	924.8	938.0	984.7	1041.1	1092.2	1142.9	1183.8	1188.4	1150.2	1077.5
35°	708.1	724.8	749.1	773.4	834.1	886.2	975.4	1053.1	1115.0	1123.2	1078.6
37.5°	570.6	578.9	594.2	618.5	658.2	720.2	789.2	887.3	977.0	1043.7	1046.6
40°	498.8	501.2	518.5	537.0	569.2	620.1	682.4	769.1	876.5	969.7	1008.5
42.5°	444.9	450.3	457.6	475.4	501.0	539.3	597.1	668.9	767.3	874.5	950.5
45°	382.3	388.3	392.9	404.7	422.9	448.7	489.1	554.6	629.5	740.3	842.6
47.5°	340.9	341.4	344.8	353.7	366.1	385.5	414.0	456.1	524.9	614.7	719.7
50°	311.3	316.2	317.3	324.3	334.1	348.3	372.0	407.7	464.2	543.1	639.6
52.5°	290.4	291.8	295.2	300.3	308.8	319.9	340.4	368.4	412.7	480.0	568.7
55°	259.7	259.7	263.1	267.0	271.9	281.9	295.5	316.2	349.8	402.0	475.5
57.5°	231.3	232.8	235.2	236.4	240.5	247.2	258.6	274.3	299.4	339.5	397.9
60°	212.4	215.1	214.8	217.2	220.9	226.0	235.8	248.5	270.9	303.1	352.3
62.5°	195.9	195.7	195.7	198.5	202.2	207.1	213.4	224.4	243.5	272.0	313.9
65°	168.7	168.1	170.2	172.1	173.3	176.9	181.7	191.5	204.2	225.5	257.9
67.5°	144.6	142.8	143.9	144.6	146.6	149.5	154.0	160.0	170.2	187.2	211.7
70°	128.0	126.5	126.2	126.8	128.7	130.8	134.1	139.9	149.2	163.0	180.9
72.5°	111.1	110.0	110.0	111.3	112.2	113.5	115.9	121.2	128.7	138.9	155.6
75°	86.7	86.7	86.7	87.1	88.0	89.2	91.0	93.7	99.5	106.8	118.0
77.5°	65.0	65.0	64.6	64.6	65.9	66.5	66.9	69.4	72.6	77.6	85.7
80°	50.9	49.4	50.1	50.9	51.6	51.9	52.8	53.4	56.2	58.9	64.6
82.5°	37.9	36.6	36.7	38.1	38.3	38.5	39.5	40.3	41.4	43.8	46.9
85°	20.0	20.0	20.4	20.4	20.6	20.4	21.2	21.5	21.5	23.1	24.9
87.5°	11.9	11.6	11.6	11.7	11.6	11.6	11.6	11.7	11.8	12.2	12.0
90°	22.9	23.7	22.9	22.1	22.9	21.4	20.6	19.8	19.0	19.8	17.4
92.5°	38.1	39.5	38.7	41.1	42.5	46.7	52.8	66.5	91.7	121.6	133.8
95°	91.7	94.9	100.4	107.6	122.6	151.1	193.0	284.6	380.3	468.9	417.5
97.5°	249.7	256.5	277.9	313.5	371.8	466.4	568.4	709.6	777.4	726.7	532.0
100°	495.8	495.0	525.9	583.6	663.5	775.7	868.2	932.3	904.6	748.8	506.0
102.5°	727.3	745.5	771.3	817.0	879.2	950.3	1004.2	1006.3	910.9	707.7	468.1
105°	1005.8	1009.8	1035.1	1065.1	1101.5	1122.0	1107.1	1027.9	862.7	635.7	421.4
107.5°	1166.2	1173.5	1182.0	1192.2	1191.5	1163.3	1094.1	965.7	778.2	572.2	391.7
110°	1232.0	1233.6	1235.2	1228.8	1206.7	1151.3	1051.7	906.2	725.1	536.1	380.3



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1245.2	1244.9	1238.9	1219.3	1178.8	1107.6	996.0	847.3	678.9	512.1	374.0
115°	1223.3	1219.3	1203.5	1168.7	1109.4	1023.2	907.0	769.4	623.1	486.3	371.6
117.5°	1153.3	1148.0	1125.2	1085.4	1023.5	936.0	831.7	713.0	589.4	471.1	373.0
120°	1095.2	1090.4	1071.4	1027.1	964.7	884.9	790.0	683.2	571.7	464.1	375.6
122.5°	1040.8	1034.7	1013.9	974.1	918.5	844.4	756.5	659.8	557.1	459.7	380.0
125°	964.7	959.2	939.4	904.6	854.0	790.8	714.9	628.7	538.5	453.9	386.7
127.5°	902.1	897.0	879.2	849.4	804.3	746.8	678.3	601.4	522.0	451.1	394.3
130°	866.6	860.3	843.8	815.2	773.3	719.5	655.5	584.4	513.2	449.2	399.3
132.5°	831.9	827.4	812.7	784.3	744.9	693.6	634.0	568.5	504.9	448.5	403.1
135°	782.0	776.5	762.2	738.6	699.8	654.7	603.3	547.2	494.2	447.6	408.8
137.5°	729.4	725.7	713.8	689.7	657.1	618.1	573.8	527.8	484.9	445.8	412.6
140°	692.7	693.5	680.8	658.7	628.7	594.6	556.7	516.3	479.2	445.2	415.1
142.5°	658.5	659.3	647.9	628.4	602.7	573.1	540.3	505.6	474.1	443.9	417.0
145°	611.2	609.7	603.3	586.7	567.0	544.0	518.7	492.7	467.3	442.0	418.3
147.5°	572.4	571.7	565.7	554.4	539.5	523.2	502.7	482.0	460.7	439.0	418.3
150°	549.5	549.5	544.8	536.1	524.3	509.2	492.7	474.4	456.2	436.5	418.3
152.5°	530.6	530.6	527.8	519.7	510.3	497.9	483.2	467.5	451.2	433.3	416.4
155°	506.8	506.0	504.5	498.2	491.1	481.6	469.7	457.0	443.6	427.8	414.3
157.5°	485.2	485.4	484.1	479.3	473.2	465.7	456.5	446.0	435.1	422.9	411.7
160°	471.3	472.1	472.1	467.3	461.8	456.2	448.4	439.7	429.4	419.1	410.4
162.5°	458.6	459.4	459.4	455.3	451.7	446.8	439.5	432.1	423.7	415.3	407.9
165°	442.0	442.0	442.8	439.7	436.5	432.5	427.0	422.2	415.9	409.6	404.1
167.5°	426.2	426.2	427.0	424.8	423.3	420.5	417.3	413.7	408.5	403.9	400.3
170°	416.7	416.7	417.5	415.9	415.1	413.5	410.4	408.1	404.1	400.1	397.8
172.5°	407.9	408.5	410.0	408.4	408.2	407.3	404.7	403.0	399.7	397.0	395.9
175°	397.8	398.5	399.3	398.5	398.5	398.5	397.0	396.2	394.6	393.0	393.0
177.5°	391.9	391.9	393.2	392.5	393.2	393.2	392.5	391.9	391.3	390.6	391.3
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	645.6	643.7	641.7	638.3	635.4	631.3	630.1	628.7	624.3	620.4	617.5
5°	685.1	677.8	667.2	657.4	649.6	639.0	632.9	626.5	617.4	609.3	602.5
7.5°	726.4	712.0	695.5	677.7	661.1	645.0	632.1	620.6	607.8	595.7	586.4
10°	759.1	738.5	715.4	690.5	669.3	648.6	631.4	616.2	599.8	585.6	573.7
12.5°	796.5	765.9	734.1	703.9	678.7	650.1	629.2	609.9	591.4	574.2	560.9
15°	840.7	801.9	764.3	722.7	684.4	648.6	623.8	599.5	578.0	560.4	543.4
17.5°	881.0	837.0	787.4	736.9	690.8	648.3	613.5	586.1	559.1	537.6	520.6
20°	903.8	853.7	797.6	745.1	694.2	646.8	608.6	575.8	546.8	523.9	504.9
22.5°	923.5	864.9	806.8	750.8	694.0	642.9	599.7	565.9	534.3	512.1	491.8
25°	943.9	873.8	815.6	749.7	686.3	633.5	584.9	546.8	515.2	489.1	468.2
27.5°	961.4	873.2	804.1	733.2	674.3	621.4	569.6	528.5	495.0	466.7	445.4
30°	973.0	874.4	792.2	722.1	662.7	608.0	557.6	516.4	481.2	452.3	432.4
32.5°	980.3	873.7	781.3	706.5	644.2	595.9	544.8	502.1	465.9	437.6	418.3
35°	984.5	868.3	762.5	674.5	614.4	567.4	524.6	480.3	442.4	416.0	394.1
37.5°	976.0	857.1	740.6	643.5	577.7	531.5	495.4	457.7	421.4	392.4	373.5
40°	962.7	849.9	723.6	621.7	552.5	507.9	477.3	440.2	404.4	376.8	359.3
42.5°	937.2	835.0	705.0	597.4	526.2	481.6	453.4	422.6	388.6	362.7	345.2
45°	875.0	802.8	676.9	561.0	487.6	441.5	416.6	394.1	363.5	338.3	323.1
47.5°	788.7	754.3	636.4	522.6	447.2	402.8	376.9	358.9	336.4	316.2	301.6
50°	728.8	714.5	609.0	496.4	420.2	376.8	352.0	335.6	319.5	299.1	285.8
52.5°	659.6	668.4	576.9	469.2	392.8	350.1	326.7	313.7	299.1	282.4	270.8
55°	562.2	594.1	521.6	423.6	352.0	311.3	289.1	277.6	269.1	256.7	246.7
57.5°	471.0	511.5	461.7	376.5	311.8	276.8	255.6	243.0	237.5	231.0	223.2
60°	416.8	456.9	419.0	345.0	284.9	251.5	232.7	222.1	216.7	212.1	205.4
62.5°	368.6	409.1	377.2	312.9	258.4	227.5	211.1	200.7	196.5	194.1	188.4
65°	302.2	337.1	315.8	263.1	220.5	193.3	178.4	171.1	167.2	166.3	162.6
67.5°	246.0	272.5	257.1	218.2	184.7	161.1	148.5	142.4	139.3	139.0	136.3
70°	209.1	233.9	222.1	186.9	158.0	139.6	128.7	123.2	121.4	121.0	119.5
72.5°	180.4	197.7	188.4	159.0	136.7	119.9	111.9	106.2	104.1	104.6	103.5
75°	133.5	146.6	141.1	120.7	102.8	91.9	85.2	81.6	79.8	80.7	79.5
77.5°	96.1	104.3	99.4	85.3	74.3	66.4	61.5	59.3	57.6	57.5	57.0
80°	72.5	77.4	74.6	66.1	57.0	50.4	46.4	44.9	44.0	43.7	43.4
82.5°	51.7	55.8	52.5	46.7	40.6	36.5	34.3	32.3	31.6	31.8	31.5
85°	26.1	27.6	26.4	22.7	20.4	18.5	17.3	16.4	15.8	16.1	15.4
87.5°	12.0	11.7	10.5	9.3	8.5	7.3	7.0	6.2	5.9	6.3	6.5
90°	15.1	12.7	10.3	8.7	7.1	4.8	3.2	1.6	3.2	4.8	7.1
92.5°	100.4	66.4	45.7	34.0	27.3	21.2	14.6	9.8	14.6	21.2	27.3
95°	287.8	170.0	102.8	71.9	51.4	37.9	29.2	26.9	29.2	37.9	51.4
97.5°	315.8	183.0	118.7	85.4	65.1	53.5	46.7	45.9	46.7	53.5	65.1
100°	298.1	181.1	125.7	94.9	75.9	64.9	59.3	58.5	59.3	64.9	75.9
102.5°	282.9	183.6	134.0	105.7	88.6	78.1	73.2	71.8	73.2	78.1	88.6
105°	272.0	190.6	147.9	123.3	108.4	98.9	94.1	91.7	94.1	98.9	108.4
107.5°	271.2	203.5	166.0	143.3	129.2	119.9	115.3	112.9	115.3	119.9	129.2
110°	274.4	214.3	178.7	156.5	143.1	134.4	130.5	128.1	130.5	134.4	143.1



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.7	225.1	192.0	170.5	157.0	148.4	144.4	142.0	144.4	148.4	157.0
115°	291.0	242.7	212.7	191.4	177.9	170.0	165.2	162.1	165.2	170.0	177.9
117.5°	304.6	261.6	231.9	212.1	197.0	189.8	185.8	182.2	185.8	189.8	197.0
120°	314.7	273.6	245.1	225.4	210.3	202.4	198.4	196.1	198.4	202.4	210.3
122.5°	324.2	286.2	258.4	237.4	223.0	214.4	210.5	208.1	210.5	214.4	223.0
125°	339.2	304.4	276.8	255.4	240.3	231.7	227.0	225.4	227.0	231.7	240.3
127.5°	351.6	320.3	293.5	272.2	255.6	246.7	240.8	238.5	240.8	246.7	255.6
130°	359.8	329.7	303.6	282.3	265.7	256.2	249.1	246.7	249.1	256.2	265.7
132.5°	367.4	337.9	312.5	291.8	275.2	263.8	256.0	253.0	256.0	263.8	275.2
135°	377.2	350.3	325.7	304.4	287.8	276.0	267.3	264.1	267.3	276.0	287.8
137.5°	384.4	358.9	335.3	315.5	299.0	286.4	277.9	274.6	277.9	286.4	299.0
140°	388.2	364.6	341.6	321.9	306.0	293.3	285.4	281.5	285.4	293.3	306.0
142.5°	392.1	369.0	346.7	328.1	312.4	301.0	292.4	289.1	292.4	301.0	312.4
145°	396.2	374.8	354.3	336.0	322.7	310.8	303.6	301.3	303.6	310.8	322.7
147.5°	398.7	379.5	360.8	345.2	332.2	322.0	315.1	313.6	315.1	322.0	332.2
150°	399.3	382.7	364.6	350.3	339.2	328.9	322.7	321.9	322.7	328.9	339.2
152.5°	400.6	384.6	369.0	355.4	345.5	336.5	330.2	330.0	330.2	336.5	345.5
155°	400.9	388.2	374.8	363.8	355.1	347.1	342.4	342.4	342.4	347.1	355.1
157.5°	401.7	390.3	379.5	371.0	363.6	356.6	352.8	352.2	352.8	356.6	363.6
160°	401.7	392.2	382.7	374.8	369.2	363.0	359.8	359.8	359.8	363.0	369.2
162.5°	401.1	392.8	384.6	378.0	373.0	368.0	365.5	365.5	365.5	368.0	373.0
165°	399.3	393.8	387.5	381.9	378.7	374.8	373.2	374.0	373.2	374.8	378.7
167.5°	398.1	393.6	389.0	385.6	383.3	380.3	379.5	380.5	379.5	380.3	383.3
170°	396.2	393.0	389.0	387.5	385.9	383.5	382.7	384.3	382.7	383.5	385.9
172.5°	395.5	393.0	389.7	388.7	387.8	386.0	385.9	386.8	385.9	386.0	387.8
175°	393.8	392.2	390.6	389.8	389.8	388.2	389.0	389.8	389.0	388.2	389.8
177.5°	392.5	391.3	390.6	390.6	390.6	390.0	390.6	391.3	390.6	390.0	390.6
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	615.8	614.1	611.6	608.0	605.1	600.5	600.5	601.2	601.2	600.9	600.5
5°	597.1	592.6	587.1	580.7	574.0	567.4	566.2	563.7	561.9	560.7	559.2
7.5°	577.3	569.3	561.3	552.5	544.3	537.6	532.9	529.0	526.5	523.9	521.9
10°	564.0	554.0	544.6	535.2	524.9	516.7	511.5	507.9	505.2	502.7	501.5
12.5°	548.3	536.8	526.4	517.5	506.2	497.7	492.8	491.2	487.9	482.8	480.1
15°	525.2	514.6	502.2	488.5	483.0	472.7	466.9	464.2	462.4	458.4	457.2
17.5°	505.5	491.5	477.6	467.4	457.2	448.9	445.7	442.3	439.9	436.7	435.7
20°	489.7	477.3	464.5	453.6	443.0	433.9	431.1	428.7	426.3	424.8	423.6
22.5°	473.6	461.2	450.7	440.5	429.1	423.2	420.2	417.6	415.8	414.8	413.6
25°	451.1	440.2	428.4	419.3	410.2	406.2	404.4	402.9	401.7	400.2	399.9
27.5°	431.0	419.1	409.6	401.0	394.5	391.2	389.4	388.7	389.0	389.5	389.8
30°	416.0	405.0	397.1	389.8	383.8	380.8	380.5	380.5	381.7	382.0	382.6
32.5°	402.1	393.2	385.2	378.2	373.6	371.5	372.7	372.7	373.7	374.5	375.6
35°	382.0	374.1	368.0	361.9	358.0	358.9	359.5	360.1	361.6	363.5	364.7
37.5°	362.7	355.9	349.6	344.8	343.0	344.7	346.1	347.4	349.2	350.5	351.7
40°	348.9	343.7	337.7	333.4	334.1	334.9	336.2	337.7	339.2	340.1	341.4
42.5°	336.0	330.7	326.1	322.5	323.4	324.6	325.3	326.1	327.8	329.5	330.2
45°	316.5	312.2	307.9	305.9	306.4	307.0	307.7	308.6	310.1	311.3	311.6
47.5°	294.5	291.4	288.6	286.5	287.5	287.2	288.0	290.0	290.5	291.2	292.9
50°	280.4	277.6	274.3	273.7	273.7	273.7	273.9	276.4	276.4	277.6	278.8
52.5°	264.8	263.1	260.9	259.8	259.4	259.4	260.6	261.8	262.3	264.0	265.2
55°	241.8	240.0	238.2	237.3	236.6	237.3	239.7	240.3	241.8	242.7	243.6
57.5°	217.9	216.4	215.0	214.5	214.4	215.2	216.5	218.3	218.7	221.5	222.8
60°	202.1	199.9	198.8	198.8	198.1	200.8	200.3	203.3	203.9	205.7	207.9
62.5°	185.8	182.9	182.4	182.4	183.3	184.1	185.0	186.3	187.9	190.2	191.8
65°	159.6	158.0	160.2	159.9	159.3	161.1	161.1	162.6	164.5	166.6	169.9
67.5°	134.8	134.0	134.2	134.2	135.1	136.1	137.0	138.3	140.5	142.8	144.9
70°	118.0	118.9	117.4	118.7	119.5	119.9	120.4	122.2	124.7	126.2	128.7
72.5°	101.8	101.7	101.9	102.3	103.3	103.9	104.4	106.5	109.2	110.4	112.4
75°	78.3	78.0	78.9	78.9	80.4	81.0	81.6	82.5	84.9	86.7	88.3
77.5°	57.2	57.5	57.4	58.4	58.0	58.1	60.0	60.8	61.1	64.7	65.5
80°	43.1	43.7	44.0	44.3	44.6	44.0	46.1	47.1	47.1	49.1	50.7
82.5°	31.0	31.3	32.1	32.4	32.5	33.0	33.3	33.9	34.6	35.6	37.5
85°	15.4	16.4	16.7	16.4	16.7	16.1	17.0	17.3	17.6	17.6	17.6
87.5°	6.6	7.1	7.4	8.1	8.3	9.0	8.9	8.6	8.7	9.6	9.0
90°	8.7	10.3	12.7	15.1	17.4	19.8	19.0	19.8	20.6	21.4	22.9
92.5°	34.0	45.7	66.4	100.4	133.8	121.6	91.7	66.5	52.8	46.7	42.5
95°	71.9	102.8	170.0	287.8	417.5	468.9	380.3	284.6	193.0	151.1	122.6
97.5°	85.4	118.7	183.0	315.8	532.0	726.7	777.4	709.6	568.4	466.4	371.8
100°	94.9	125.7	181.1	298.1	506.0	748.8	904.6	932.3	868.2	775.7	663.5
102.5°	105.7	134.0	183.6	282.9	468.1	707.7	910.9	1006.3	1004.2	950.3	879.2
105°	123.3	147.9	190.6	272.0	421.4	635.7	862.7	1027.9	1107.1	1122.0	1101.5
107.5°	143.3	166.0	203.5	271.2	391.7	572.2	778.2	965.7	1094.1	1163.3	1191.5
110°	156.5	178.7	214.3	274.4	380.3	536.1	725.1	906.2	1051.7	1151.3	1206.7



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.5	192.0	225.1	280.7	374.0	512.1	678.9	847.3	996.0	1107.6	1178.8
115°	191.4	212.7	242.7	291.0	371.6	486.3	623.1	769.4	907.0	1023.2	1109.4
117.5°	212.1	231.9	261.6	304.6	373.0	471.1	589.4	713.0	831.7	936.0	1023.5
120°	225.4	245.1	273.6	314.7	375.6	464.1	571.7	683.2	790.0	884.9	964.7
122.5°	237.4	258.4	286.2	324.2	380.0	459.7	557.1	659.8	756.5	844.4	918.5
125°	255.4	276.8	304.4	339.2	386.7	453.9	538.5	628.7	714.9	790.8	854.0
127.5°	272.2	293.5	320.3	351.6	394.3	451.1	522.0	601.4	678.3	746.8	804.3
130°	282.3	303.6	329.7	359.8	399.3	449.2	513.2	584.4	655.5	719.5	773.3
132.5°	291.8	312.5	337.9	367.4	403.1	448.5	504.9	568.5	634.0	693.6	744.9
135°	304.4	325.7	350.3	377.2	408.8	447.6	494.2	547.2	603.3	654.7	699.8
137.5°	315.5	335.3	358.9	384.4	412.6	445.8	484.9	527.8	573.8	618.1	657.1
140°	321.9	341.6	364.6	388.2	415.1	445.2	479.2	516.3	556.7	594.6	628.7
142.5°	328.1	346.7	369.0	392.1	417.0	443.9	474.1	505.6	540.3	573.1	602.7
145°	336.0	354.3	374.8	396.2	418.3	442.0	467.3	492.7	518.7	544.0	567.0
147.5°	345.2	360.8	379.5	398.7	418.3	439.0	460.7	482.0	502.7	523.2	539.5
150°	350.3	364.6	382.7	399.3	418.3	436.5	456.2	474.4	492.7	509.2	524.3
152.5°	355.4	369.0	384.6	400.6	416.4	433.3	451.2	467.5	483.2	497.9	510.3
155°	363.8	374.8	388.2	400.9	414.3	427.8	443.6	457.0	469.7	481.6	491.1
157.5°	371.0	379.5	390.3	401.7	411.7	422.9	435.1	446.0	456.5	465.7	473.2
160°	374.8	382.7	392.2	401.7	410.4	419.1	429.4	439.7	448.4	456.2	461.8
162.5°	378.0	384.6	392.8	401.1	407.9	415.3	423.7	432.1	439.5	446.8	451.7
165°	381.9	387.5	393.8	399.3	404.1	409.6	415.9	422.2	427.0	432.5	436.5
167.5°	385.6	389.0	393.6	398.1	400.3	403.9	408.5	413.7	417.3	420.5	423.3
170°	387.5	389.0	393.0	396.2	397.8	400.1	404.1	408.1	410.4	413.5	415.1
172.5°	388.7	389.7	393.0	395.5	395.9	397.0	399.7	403.0	404.7	407.3	408.2
175°	389.8	390.6	392.2	393.8	393.0	393.0	394.6	396.2	397.0	398.5	398.5
177.5°	390.6	390.6	391.3	392.5	391.3	390.6	391.3	391.9	392.5	393.2	393.2
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	598.8	598.6	600.2	599.0	600.2	598.6	598.8	600.5	600.9	601.2	601.2
5°	557.4	558.3	555.2	555.2	555.2	558.3	557.4	559.2	560.7	561.9	563.7
7.5°	520.5	519.1	519.3	517.6	519.3	519.1	520.5	521.9	523.9	526.5	529.0
10°	497.9	496.1	495.4	495.7	495.4	496.1	497.9	501.5	502.7	505.2	507.9
12.5°	479.2	478.8	474.8	474.9	474.8	478.8	479.2	480.1	482.8	487.9	491.2
15°	457.2	451.5	450.8	452.7	450.8	451.5	457.2	457.2	458.4	462.4	464.2
17.5°	435.2	432.1	432.4	431.4	432.4	432.1	435.2	435.7	436.7	439.9	442.3
20°	423.6	421.8	421.4	419.3	421.4	421.8	423.6	423.6	424.8	426.3	428.7
22.5°	412.9	412.3	412.4	410.1	412.4	412.3	412.9	413.6	414.8	415.8	417.6
25°	399.6	401.1	399.9	399.9	399.9	401.1	399.6	399.9	400.2	401.7	402.9
27.5°	390.6	390.5	389.9	389.9	389.9	390.5	390.6	389.8	389.5	389.0	388.7
30°	383.8	383.5	384.1	384.1	384.1	383.5	383.8	382.6	382.0	381.7	380.5
32.5°	377.0	377.4	377.6	377.8	377.6	377.4	377.0	375.6	374.5	373.7	372.7
35°	366.5	366.8	367.7	367.1	367.7	366.8	366.5	364.7	363.5	361.6	360.1
37.5°	352.3	353.7	353.4	353.9	353.4	353.7	352.3	351.7	350.5	349.2	347.4
40°	341.7	342.5	342.2	342.2	342.2	342.5	341.7	341.4	340.1	339.2	337.7
42.5°	330.7	331.4	330.6	330.1	330.6	331.4	330.7	330.2	329.5	327.8	326.1
45°	312.8	312.2	313.1	311.9	313.1	312.2	312.8	311.6	311.3	310.1	308.6
47.5°	292.8	293.4	293.7	294.5	293.7	293.4	292.8	292.9	291.2	290.5	290.0
50°	279.4	281.2	281.2	281.0	281.2	281.2	279.4	278.8	277.6	276.4	276.4
52.5°	266.3	267.2	268.4	268.3	268.4	267.2	266.3	265.2	264.0	262.3	261.8
55°	246.1	246.7	247.2	247.6	247.2	246.7	246.1	243.6	242.7	241.8	240.3
57.5°	225.1	224.8	226.2	226.7	226.2	224.8	225.1	222.8	221.5	218.7	218.3
60°	210.2	210.2	212.7	213.6	212.7	210.2	210.2	207.9	205.7	203.9	203.3
62.5°	194.5	195.4	197.9	196.6	197.9	195.4	194.5	191.8	190.2	187.9	186.3
65°	171.4	173.9	173.6	174.8	173.6	173.9	171.4	169.9	166.6	164.5	162.6
67.5°	147.3	148.9	151.1	151.2	151.1	148.9	147.3	144.9	142.8	140.5	138.3
70°	131.1	132.6	133.8	134.7	133.8	132.6	131.1	128.7	126.2	124.7	122.2
72.5°	115.3	116.1	119.0	117.7	119.0	116.1	115.3	112.4	110.4	109.2	106.5
75°	90.4	92.5	94.3	93.5	94.3	92.5	90.4	88.3	86.7	84.9	82.5
77.5°	66.9	69.0	69.9	69.1	69.9	69.0	66.9	65.5	64.7	61.1	60.8
80°	52.8	52.5	54.3	54.0	54.3	52.5	52.8	50.7	49.1	47.1	47.1
82.5°	38.7	38.4	39.3	39.5	39.3	38.4	38.7	37.5	35.6	34.6	33.9
85°	18.8	19.7	18.5	18.2	18.5	19.7	18.8	17.6	17.6	17.6	17.3
87.5°	8.8	9.0	8.9	8.5	8.9	9.0	8.8	9.0	9.6	8.7	8.6
90°	22.1	22.9	23.7	22.9	23.7	22.9	22.1	22.9	21.4	20.6	19.8
92.5°	41.1	38.7	39.5	38.1	39.5	38.7	41.1	42.5	46.7	52.8	66.5
95°	107.6	100.4	94.9	91.7	94.9	100.4	107.6	122.6	151.1	193.0	284.6
97.5°	313.5	277.9	256.5	249.7	256.5	277.9	313.5	371.8	466.4	568.4	709.6
100°	583.6	525.9	495.0	495.8	495.0	525.9	583.6	663.5	775.7	868.2	932.3
102.5°	817.0	771.3	745.5	727.3	745.5	771.3	817.0	879.2	950.3	1004.2	1006.3
105°	1065.1	1035.1	1009.8	1005.8	1009.8	1035.1	1065.1	1101.5	1122.0	1107.1	1027.9
107.5°	1192.2	1182.0	1173.5	1166.2	1173.5	1182.0	1192.2	1191.5	1163.3	1094.1	965.7
110°	1228.8	1235.2	1233.6	1232.0	1233.6	1235.2	1228.8	1206.7	1151.3	1051.7	906.2



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1219.3	1238.9	1244.9	1245.2	1244.9	1238.9	1219.3	1178.8	1107.6	996.0	847.3
115°	1168.7	1203.5	1219.3	1223.3	1219.3	1203.5	1168.7	1109.4	1023.2	907.0	769.4
117.5°	1085.4	1125.2	1148.0	1153.3	1148.0	1125.2	1085.4	1023.5	936.0	831.7	713.0
120°	1027.1	1071.4	1090.4	1095.2	1090.4	1071.4	1027.1	964.7	884.9	790.0	683.2
122.5°	974.1	1013.9	1034.7	1040.8	1034.7	1013.9	974.1	918.5	844.4	756.5	659.8
125°	904.6	939.4	959.2	964.7	959.2	939.4	904.6	854.0	790.8	714.9	628.7
127.5°	849.4	879.2	897.0	902.1	897.0	879.2	849.4	804.3	746.8	678.3	601.4
130°	815.2	843.8	860.3	866.6	860.3	843.8	815.2	773.3	719.5	655.5	584.4
132.5°	784.3	812.7	827.4	831.9	827.4	812.7	784.3	744.9	693.6	634.0	568.5
135°	738.6	762.2	776.5	782.0	776.5	762.2	738.6	699.8	654.7	603.3	547.2
137.5°	689.7	713.8	725.7	729.4	725.7	713.8	689.7	657.1	618.1	573.8	527.8
140°	658.7	680.8	693.5	692.7	693.5	680.8	658.7	628.7	594.6	556.7	516.3
142.5°	628.4	647.9	659.3	658.5	659.3	647.9	628.4	602.7	573.1	540.3	505.6
145°	586.7	603.3	609.7	611.2	609.7	603.3	586.7	567.0	544.0	518.7	492.7
147.5°	554.4	565.7	571.7	572.4	571.7	565.7	554.4	539.5	523.2	502.7	482.0
150°	536.1	544.8	549.5	549.5	549.5	544.8	536.1	524.3	509.2	492.7	474.4
152.5°	519.7	527.8	530.6	530.6	530.6	527.8	519.7	510.3	497.9	483.2	467.5
155°	498.2	504.5	506.0	506.8	506.0	504.5	498.2	491.1	481.6	469.7	457.0
157.5°	479.3	484.1	485.4	485.2	485.4	484.1	479.3	473.2	465.7	456.5	446.0
160°	467.3	472.1	472.1	471.3	472.1	472.1	467.3	461.8	456.2	448.4	439.7
162.5°	455.3	459.4	459.4	458.6	459.4	459.4	455.3	451.7	446.8	439.5	432.1
165°	439.7	442.8	442.0	442.0	442.0	442.8	439.7	436.5	432.5	427.0	422.2
167.5°	424.8	427.0	426.2	426.2	426.2	427.0	424.8	423.3	420.5	417.3	413.7
170°	415.9	417.5	416.7	416.7	416.7	417.5	415.9	415.1	413.5	410.4	408.1
172.5°	408.4	410.0	408.5	407.9	408.5	410.0	408.4	408.2	407.3	404.7	403.0
175°	398.5	399.3	398.5	397.8	398.5	399.3	398.5	398.5	398.5	397.0	396.2
177.5°	392.5	393.2	391.9	391.9	391.9	393.2	392.5	393.2	393.2	392.5	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	600.5	600.5	605.1	608.0	611.6	614.1	615.8	617.5	620.4	624.3	628.7
5°	566.2	567.4	574.0	580.7	587.1	592.6	597.1	602.5	609.3	617.4	626.5
7.5°	532.9	537.6	544.3	552.5	561.3	569.3	577.3	586.4	595.7	607.8	620.6
10°	511.5	516.7	524.9	535.2	544.6	554.0	564.0	573.7	585.6	599.8	616.2
12.5°	492.8	497.7	506.2	517.5	526.4	536.8	548.3	560.9	574.2	591.4	609.9
15°	466.9	472.7	483.0	488.5	502.2	514.6	525.2	543.4	560.4	578.0	599.5
17.5°	445.7	448.9	457.2	467.4	477.6	491.5	505.5	520.6	537.6	559.1	586.1
20°	431.1	433.9	443.0	453.6	464.5	477.3	489.7	504.9	523.9	546.8	575.8
22.5°	420.2	423.2	429.1	440.5	450.7	461.2	473.6	491.8	512.1	534.3	565.9
25°	404.4	406.2	410.2	419.3	428.4	440.2	451.1	468.2	489.1	515.2	546.8
27.5°	389.4	391.2	394.5	401.0	409.6	419.1	431.0	445.4	466.7	495.0	528.5
30°	380.5	380.8	383.8	389.8	397.1	405.0	416.0	432.4	452.3	481.2	516.4
32.5°	372.7	371.5	373.6	378.2	385.2	393.2	402.1	418.3	437.6	465.9	502.1
35°	359.5	358.9	358.0	361.9	368.0	374.1	382.0	394.1	416.0	442.4	480.3
37.5°	346.1	344.7	343.0	344.8	349.6	355.9	362.7	373.5	392.4	421.4	457.7
40°	336.2	334.9	334.1	333.4	337.7	343.7	348.9	359.3	376.8	404.4	440.2
42.5°	325.3	324.6	323.4	322.5	326.1	330.7	336.0	345.2	362.7	388.6	422.6
45°	307.7	307.0	306.4	305.9	307.9	312.2	316.5	323.1	338.3	363.5	394.1
47.5°	288.0	287.2	287.5	286.5	288.6	291.4	294.5	301.6	316.2	336.4	358.9
50°	273.9	273.7	273.7	273.7	274.3	277.6	280.4	285.8	299.1	319.5	335.6
52.5°	260.6	259.4	259.4	259.8	260.9	263.1	264.8	270.8	282.4	299.1	313.7
55°	239.7	237.3	236.6	237.3	238.2	240.0	241.8	246.7	256.7	269.1	277.6
57.5°	216.5	215.2	214.4	214.5	215.0	216.4	217.9	223.2	231.0	237.5	243.0
60°	200.3	200.8	198.1	198.8	198.8	199.9	202.1	205.4	212.1	216.7	222.1
62.5°	185.0	184.1	183.3	182.4	182.4	182.9	185.8	188.4	194.1	196.5	200.7
65°	161.1	161.1	159.3	159.9	160.2	158.0	159.6	162.6	166.3	167.2	171.1
67.5°	137.0	136.1	135.1	134.2	134.2	134.0	134.8	136.3	139.0	139.3	142.4
70°	120.4	119.9	119.5	118.7	117.4	118.9	118.0	119.5	121.0	121.4	123.2
72.5°	104.4	103.9	103.3	102.3	101.9	101.7	101.8	103.5	104.6	104.1	106.2
75°	81.6	81.0	80.4	78.9	78.9	78.0	78.3	79.5	80.7	79.8	81.6
77.5°	60.0	58.1	58.0	58.4	57.4	57.5	57.2	57.0	57.5	57.6	59.3
80°	46.1	44.0	44.6	44.3	44.0	43.7	43.1	43.4	43.7	44.0	44.9
82.5°	33.3	33.0	32.5	32.4	32.1	31.3	31.0	31.5	31.8	31.6	32.3
85°	17.0	16.1	16.7	16.4	16.7	16.4	15.4	15.4	16.1	15.8	16.4
87.5°	8.9	9.0	8.3	8.1	7.4	7.1	6.6	6.5	6.3	5.9	6.2
90°	19.0	19.8	17.4	15.1	12.7	10.3	8.7	7.1	4.8	3.2	1.6
92.5°	91.7	121.6	133.8	100.4	66.4	45.7	34.0	27.3	21.2	14.6	9.8
95°	380.3	468.9	417.5	287.8	170.0	102.8	71.9	51.4	37.9	29.2	26.9
97.5°	777.4	726.7	532.0	315.8	183.0	118.7	85.4	65.1	53.5	46.7	45.9
100°	904.6	748.8	506.0	298.1	181.1	125.7	94.9	75.9	64.9	59.3	58.5
102.5°	910.9	707.7	468.1	282.9	183.6	134.0	105.7	88.6	78.1	73.2	71.8
105°	862.7	635.7	421.4	272.0	190.6	147.9	123.3	108.4	98.9	94.1	91.7
107.5°	778.2	572.2	391.7	271.2	203.5	166.0	143.3	129.2	119.9	115.3	112.9
110°	725.1	536.1	380.3	274.4	214.3	178.7	156.5	143.1	134.4	130.5	128.1



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	678.9	512.1	374.0	280.7	225.1	192.0	170.5	157.0	148.4	144.4	142.0
115°	623.1	486.3	371.6	291.0	242.7	212.7	191.4	177.9	170.0	165.2	162.1
117.5°	589.4	471.1	373.0	304.6	261.6	231.9	212.1	197.0	189.8	185.8	182.2
120°	571.7	464.1	375.6	314.7	273.6	245.1	225.4	210.3	202.4	198.4	196.1
122.5°	557.1	459.7	380.0	324.2	286.2	258.4	237.4	223.0	214.4	210.5	208.1
125°	538.5	453.9	386.7	339.2	304.4	276.8	255.4	240.3	231.7	227.0	225.4
127.5°	522.0	451.1	394.3	351.6	320.3	293.5	272.2	255.6	246.7	240.8	238.5
130°	513.2	449.2	399.3	359.8	329.7	303.6	282.3	265.7	256.2	249.1	246.7
132.5°	504.9	448.5	403.1	367.4	337.9	312.5	291.8	275.2	263.8	256.0	253.0
135°	494.2	447.6	408.8	377.2	350.3	325.7	304.4	287.8	276.0	267.3	264.1
137.5°	484.9	445.8	412.6	384.4	358.9	335.3	315.5	299.0	286.4	277.9	274.6
140°	479.2	445.2	415.1	388.2	364.6	341.6	321.9	306.0	293.3	285.4	281.5
142.5°	474.1	443.9	417.0	392.1	369.0	346.7	328.1	312.4	301.0	292.4	289.1
145°	467.3	442.0	418.3	396.2	374.8	354.3	336.0	322.7	310.8	303.6	301.3
147.5°	460.7	439.0	418.3	398.7	379.5	360.8	345.2	332.2	322.0	315.1	313.6
150°	456.2	436.5	418.3	399.3	382.7	364.6	350.3	339.2	328.9	322.7	321.9
152.5°	451.2	433.3	416.4	400.6	384.6	369.0	355.4	345.5	336.5	330.2	330.0
155°	443.6	427.8	414.3	400.9	388.2	374.8	363.8	355.1	347.1	342.4	342.4
157.5°	435.1	422.9	411.7	401.7	390.3	379.5	371.0	363.6	356.6	352.8	352.2
160°	429.4	419.1	410.4	401.7	392.2	382.7	374.8	369.2	363.0	359.8	359.8
162.5°	423.7	415.3	407.9	401.1	392.8	384.6	378.0	373.0	368.0	365.5	365.5
165°	415.9	409.6	404.1	399.3	393.8	387.5	381.9	378.7	374.8	373.2	374.0
167.5°	408.5	403.9	400.3	398.1	393.6	389.0	385.6	383.3	380.3	379.5	380.5
170°	404.1	400.1	397.8	396.2	393.0	389.0	387.5	385.9	383.5	382.7	384.3
172.5°	399.7	397.0	395.9	395.5	393.0	389.7	388.7	387.8	386.0	385.9	386.8
175°	394.6	393.0	393.0	393.8	392.2	390.6	389.8	389.8	388.2	389.0	389.8
177.5°	391.3	390.6	391.3	392.5	391.3	390.6	390.6	390.6	390.0	390.6	391.3
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	630.1	631.3	635.4	638.3	641.7	643.7	645.6	647.1	649.0	649.5	656.6
5°	632.9	639.0	649.6	657.4	667.2	677.8	685.1	688.4	697.2	704.5	719.1
7.5°	632.1	645.0	661.1	677.7	695.5	712.0	726.4	743.3	755.4	773.6	791.5
10°	631.4	648.6	669.3	690.5	715.4	738.5	759.1	782.2	801.3	826.5	848.0
12.5°	629.2	650.1	678.7	703.9	734.1	765.9	796.5	826.1	843.0	884.9	904.8
15°	623.8	648.6	684.4	722.7	764.3	801.9	840.7	871.6	921.7	958.5	981.8
17.5°	613.5	648.3	690.8	736.9	787.4	837.0	881.0	928.0	981.1	1025.5	1072.9
20°	608.6	646.8	694.2	745.1	797.6	853.7	903.8	960.3	1018.2	1061.9	1122.6
22.5°	599.7	642.9	694.0	750.8	806.8	864.9	923.5	980.4	1047.3	1107.6	1165.3
25°	584.9	633.5	686.3	749.7	815.6	873.8	943.9	1019.5	1089.3	1166.6	1224.2
27.5°	569.6	621.4	674.3	733.2	804.1	873.2	961.4	1046.7	1132.0	1198.9	1241.5
30°	557.6	608.0	662.7	722.1	792.2	874.4	973.0	1066.1	1149.3	1206.7	1230.6
32.5°	544.8	595.9	644.2	706.5	781.3	873.7	980.3	1077.5	1150.2	1188.4	1183.8
35°	524.6	567.4	614.4	674.5	762.5	868.3	984.5	1078.6	1123.2	1115.0	1053.1
37.5°	495.4	531.5	577.7	643.5	740.6	857.1	976.0	1046.6	1043.7	977.0	887.3
40°	477.3	507.9	552.5	621.7	723.6	849.9	962.7	1008.5	969.7	876.5	769.1
42.5°	453.4	481.6	526.2	597.4	705.0	835.0	937.2	950.5	874.5	767.3	668.9
45°	416.6	441.5	487.6	561.0	676.9	802.8	875.0	842.6	740.3	629.5	554.6
47.5°	376.9	402.8	447.2	522.6	636.4	754.3	788.7	719.7	614.7	524.9	456.1
50°	352.0	376.8	420.2	496.4	609.0	714.5	728.8	639.6	543.1	464.2	407.7
52.5°	326.7	350.1	392.8	469.2	576.9	668.4	659.6	568.7	480.0	412.7	368.4
55°	289.1	311.3	352.0	423.6	521.6	594.1	562.2	475.5	402.0	349.8	316.2
57.5°	255.6	276.8	311.8	376.5	461.7	511.5	471.0	397.9	339.5	299.4	274.3
60°	232.7	251.5	284.9	345.0	419.0	456.9	416.8	352.3	303.1	270.9	248.5
62.5°	211.1	227.5	258.4	312.9	377.2	409.1	368.6	313.9	272.0	243.5	224.4
65°	178.4	193.3	220.5	263.1	315.8	337.1	302.2	257.9	225.5	204.2	191.5
67.5°	148.5	161.1	184.7	218.2	257.1	272.5	246.0	211.7	187.2	170.2	160.0
70°	128.7	139.6	158.0	186.9	222.1	233.9	209.1	180.9	163.0	149.2	139.9
72.5°	111.9	119.9	136.7	159.0	188.4	197.7	180.4	155.6	138.9	128.7	121.2
75°	85.2	91.9	102.8	120.7	141.1	146.6	133.5	118.0	106.8	99.5	93.7
77.5°	61.5	66.4	74.3	85.3	99.4	104.3	96.1	85.7	77.6	72.6	69.4
80°	46.4	50.4	57.0	66.1	74.6	77.4	72.5	64.6	58.9	56.2	53.4
82.5°	34.3	36.5	40.6	46.7	52.5	55.8	51.7	46.9	43.8	41.4	40.3
85°	17.3	18.5	20.4	22.7	26.4	27.6	26.1	24.9	23.1	21.5	21.5
87.5°	7.0	7.3	8.5	9.3	10.5	11.7	12.0	12.0	12.2	11.8	11.7
90°	3.2	4.8	7.1	8.7	10.3	12.7	15.1	17.4	19.8	19.0	19.8
92.5°	14.6	21.2	27.3	34.0	45.7	66.4	100.4	133.8	121.6	91.7	66.5
95°	29.2	37.9	51.4	71.9	102.8	170.0	287.8	417.5	468.9	380.3	284.6
97.5°	46.7	53.5	65.1	85.4	118.7	183.0	315.8	532.0	726.7	777.4	709.6
100°	59.3	64.9	75.9	94.9	125.7	181.1	298.1	506.0	748.8	904.6	932.3
102.5°	73.2	78.1	88.6	105.7	134.0	183.6	282.9	468.1	707.7	910.9	1006.3
105°	94.1	98.9	108.4	123.3	147.9	190.6	272.0	421.4	635.7	862.7	1027.9
107.5°	115.3	119.9	129.2	143.3	166.0	203.5	271.2	391.7	572.2	778.2	965.7
110°	130.5	134.4	143.1	156.5	178.7	214.3	274.4	380.3	536.1	725.1	906.2



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.4	148.4	157.0	170.5	192.0	225.1	280.7	374.0	512.1	678.9	847.3
115°	165.2	170.0	177.9	191.4	212.7	242.7	291.0	371.6	486.3	623.1	769.4
117.5°	185.8	189.8	197.0	212.1	231.9	261.6	304.6	373.0	471.1	589.4	713.0
120°	198.4	202.4	210.3	225.4	245.1	273.6	314.7	375.6	464.1	571.7	683.2
122.5°	210.5	214.4	223.0	237.4	258.4	286.2	324.2	380.0	459.7	557.1	659.8
125°	227.0	231.7	240.3	255.4	276.8	304.4	339.2	386.7	453.9	538.5	628.7
127.5°	240.8	246.7	255.6	272.2	293.5	320.3	351.6	394.3	451.1	522.0	601.4
130°	249.1	256.2	265.7	282.3	303.6	329.7	359.8	399.3	449.2	513.2	584.4
132.5°	256.0	263.8	275.2	291.8	312.5	337.9	367.4	403.1	448.5	504.9	568.5
135°	267.3	276.0	287.8	304.4	325.7	350.3	377.2	408.8	447.6	494.2	547.2
137.5°	277.9	286.4	299.0	315.5	335.3	358.9	384.4	412.6	445.8	484.9	527.8
140°	285.4	293.3	306.0	321.9	341.6	364.6	388.2	415.1	445.2	479.2	516.3
142.5°	292.4	301.0	312.4	328.1	346.7	369.0	392.1	417.0	443.9	474.1	505.6
145°	303.6	310.8	322.7	336.0	354.3	374.8	396.2	418.3	442.0	467.3	492.7
147.5°	315.1	322.0	332.2	345.2	360.8	379.5	398.7	418.3	439.0	460.7	482.0
150°	322.7	328.9	339.2	350.3	364.6	382.7	399.3	418.3	436.5	456.2	474.4
152.5°	330.2	336.5	345.5	355.4	369.0	384.6	400.6	416.4	433.3	451.2	467.5
155°	342.4	347.1	355.1	363.8	374.8	388.2	400.9	414.3	427.8	443.6	457.0
157.5°	352.8	356.6	363.6	371.0	379.5	390.3	401.7	411.7	422.9	435.1	446.0
160°	359.8	363.0	369.2	374.8	382.7	392.2	401.7	410.4	419.1	429.4	439.7
162.5°	365.5	368.0	373.0	378.0	384.6	392.8	401.1	407.9	415.3	423.7	432.1
165°	373.2	374.8	378.7	381.9	387.5	393.8	399.3	404.1	409.6	415.9	422.2
167.5°	379.5	380.3	383.3	385.6	389.0	393.6	398.1	400.3	403.9	408.5	413.7
170°	382.7	383.5	385.9	387.5	389.0	393.0	396.2	397.8	400.1	404.1	408.1
172.5°	385.9	386.0	387.8	388.7	389.7	393.0	395.5	395.9	397.0	399.7	403.0
175°	389.0	388.2	389.8	389.8	390.6	392.2	393.8	393.0	393.0	394.6	396.2
177.5°	390.6	390.0	390.6	390.6	390.6	391.3	392.5	391.3	390.6	391.3	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	626.2	626.2	626.2	626.2	626.2	626.2	626.2
2.5°	659.0	659.3	661.9	663.8	662.9	664.1	664.6
5°	719.9	730.9	736.7	740.9	741.2	741.5	743.9
7.5°	806.4	818.2	826.7	839.7	843.6	848.0	846.8
10°	869.6	886.8	901.7	909.6	918.1	930.5	920.5
12.5°	928.5	959.2	981.8	994.0	1002.1	1004.6	999.7
15°	1025.8	1065.9	1087.4	1086.8	1114.1	1125.9	1107.4
17.5°	1115.0	1152.0	1181.5	1196.7	1219.5	1224.6	1222.3
20°	1169.6	1210.0	1233.0	1259.1	1271.0	1281.6	1283.4
22.5°	1216.7	1252.9	1277.7	1299.4	1309.3	1314.3	1317.4
25°	1265.2	1293.7	1308.6	1316.1	1318.9	1318.3	1314.3
27.5°	1261.9	1264.0	1247.7	1231.6	1217.2	1200.9	1195.4
30°	1229.1	1203.6	1158.1	1132.3	1094.4	1064.3	1076.5
32.5°	1142.9	1092.2	1041.1	984.7	938.0	924.8	911.4
35°	975.4	886.2	834.1	773.4	749.1	724.8	708.1
37.5°	789.2	720.2	658.2	618.5	594.2	578.9	570.6
40°	682.4	620.1	569.2	537.0	518.5	501.2	498.8
42.5°	597.1	539.3	501.0	475.4	457.6	450.3	444.9
45°	489.1	448.7	422.9	404.7	392.9	388.3	382.3
47.5°	414.0	385.5	366.1	353.7	344.8	341.4	340.9
50°	372.0	348.3	334.1	324.3	317.3	316.2	311.3
52.5°	340.4	319.9	308.8	300.3	295.2	291.8	290.4
55°	295.5	281.9	271.9	267.0	263.1	259.7	259.7
57.5°	258.6	247.2	240.5	236.4	235.2	232.8	231.3
60°	235.8	226.0	220.9	217.2	214.8	215.1	212.4
62.5°	213.4	207.1	202.2	198.5	195.7	195.7	195.9
65°	181.7	176.9	173.3	172.1	170.2	168.1	168.7
67.5°	154.0	149.5	146.6	144.6	143.9	142.8	144.6
70°	134.1	130.8	128.7	126.8	126.2	126.5	128.0
72.5°	115.9	113.5	112.2	111.3	110.0	110.0	111.1
75°	91.0	89.2	88.0	87.1	86.7	86.7	86.7
77.5°	66.9	66.5	65.9	64.6	64.6	65.0	65.0
80°	52.8	51.9	51.6	50.9	50.1	49.4	50.9
82.5°	39.5	38.5	38.3	38.1	36.7	36.6	37.9
85°	21.2	20.4	20.6	20.4	20.4	20.0	20.0
87.5°	11.6	11.6	11.6	11.7	11.6	11.6	11.9
90°	20.6	21.4	22.9	22.1	22.9	23.7	22.9
92.5°	52.8	46.7	42.5	41.1	38.7	39.5	38.1
95°	193.0	151.1	122.6	107.6	100.4	94.9	91.7
97.5°	568.4	466.4	371.8	313.5	277.9	256.5	249.7
100°	868.2	775.7	663.5	583.6	525.9	495.0	495.8
102.5°	1004.2	950.3	879.2	817.0	771.3	745.5	727.3
105°	1107.1	1122.0	1101.5	1065.1	1035.1	1009.8	1005.8
107.5°	1094.1	1163.3	1191.5	1192.2	1182.0	1173.5	1166.2
110°	1051.7	1151.3	1206.7	1228.8	1235.2	1233.6	1232.0



TEST NUMBER: P331939-927

CATALOG NUMBER: S123DIP-S560D1025U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	996.0	1107.6	1178.8	1219.3	1238.9	1244.9	1245.2
115°	907.0	1023.2	1109.4	1168.7	1203.5	1219.3	1223.3
117.5°	831.7	936.0	1023.5	1085.4	1125.2	1148.0	1153.3
120°	790.0	884.9	964.7	1027.1	1071.4	1090.4	1095.2
122.5°	756.5	844.4	918.5	974.1	1013.9	1034.7	1040.8
125°	714.9	790.8	854.0	904.6	939.4	959.2	964.7
127.5°	678.3	746.8	804.3	849.4	879.2	897.0	902.1
130°	655.5	719.5	773.3	815.2	843.8	860.3	866.6
132.5°	634.0	693.6	744.9	784.3	812.7	827.4	831.9
135°	603.3	654.7	699.8	738.6	762.2	776.5	782.0
137.5°	573.8	618.1	657.1	689.7	713.8	725.7	729.4
140°	556.7	594.6	628.7	658.7	680.8	693.5	692.7
142.5°	540.3	573.1	602.7	628.4	647.9	659.3	658.5
145°	518.7	544.0	567.0	586.7	603.3	609.7	611.2
147.5°	502.7	523.2	539.5	554.4	565.7	571.7	572.4
150°	492.7	509.2	524.3	536.1	544.8	549.5	549.5
152.5°	483.2	497.9	510.3	519.7	527.8	530.6	530.6
155°	469.7	481.6	491.1	498.2	504.5	506.0	506.8
157.5°	456.5	465.7	473.2	479.3	484.1	485.4	485.2
160°	448.4	456.2	461.8	467.3	472.1	472.1	471.3
162.5°	439.5	446.8	451.7	455.3	459.4	459.4	458.6
165°	427.0	432.5	436.5	439.7	442.8	442.0	442.0
167.5°	417.3	420.5	423.3	424.8	427.0	426.2	426.2
170°	410.4	413.5	415.1	415.9	417.5	416.7	416.7
172.5°	404.7	407.3	408.2	408.4	410.0	408.5	407.9
175°	397.0	398.5	398.5	398.5	399.3	398.5	397.8
177.5°	392.5	393.2	393.2	392.5	393.2	391.9	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6

(END OF REPORT)