

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332369-927

Luminaire Tested: **S123RDIP-S1165D585U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332369-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D585U927-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5324.9 lumens  
Efficiency: N/A  
Efficacy: 96.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332369-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332369-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92		80	80	80		70	70	70	65
1	102	97	94	90	95	92	88	85	81	79	76		72	70	68		63	61	60	56
2	93	86	79	74	87	81	75	71	72	68	64		63	60	57		56	53	51	47
3	85	76	68	62	80	71	65	60	64	58	54		56	52	49		50	47	44	41
4	78	67	59	53	73	64	57	51	57	51	47		50	46	42		45	41	38	35
5	72	60	52	46	67	57	50	44	51	45	41		46	41	37		40	37	34	31
6	66	54	46	40	62	51	44	39	46	40	36		41	36	33		37	33	30	27
7	62	49	41	36	58	47	39	34	42	36	32		38	33	29		34	30	27	24
8	57	45	37	32	54	43	35	31	39	33	28		35	30	26		31	27	24	22
9	53	41	33	28	50	39	32	27	35	30	26		32	27	24		29	25	22	20
10	50	38	31	26	47	36	29	25	33	27	23		30	25	22		27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16527	16527	16527
5°	16590	16361	16455
10°	16497	16156	16101
15°	16319	15778	15611
20°	16076	15306	14948
25°	15824	14775	14301
30°	15493	14162	13387
35°	15152	13548	12550
40°	14838	12826	11514
45°	14425	12113	10577
50°	13971	11302	9530
55°	13508	10376	8552
60°	13082	9384	7481
65°	12528	8308	6406
70°	11833	6977	5174
75°	10821	5490	4870
80°	9651	4860	4475
85°	8151	4310	4001



TEST NUMBER: P332369-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.2	2.7
10°-20°	401.2	7.5
20°-30°	577.6	10.8
30°-40°	650.7	12.2
40°-50°	622.5	11.7
50°-60°	509.7	9.6
60°-70°	343.9	6.5
70°-80°	173.0	3.2
80°-90°	47.5	0.9
90°-100°	22.1	0.4
100°-110°	105.4	2.0
110°-120°	253.1	4.8
120°-130°	322.3	6.1
130°-140°	344.4	6.5
140°-150°	322.0	6.0
150°-160°	259.8	4.9
160°-170°	167.7	3.1
170°-180°	57.8	1.1
0°-30°	1123.0	21.1
0°-40°	1773.6	33.3
0°-60°	2905.8	54.6
0°-90°	3470.3	65.2
90°-120°	380.6	7.1
90°-150°	1369.4	25.7
90°-180°	1855.0	34.8
0°-180°	5324.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1535	1535	1535	1535	1535	
5°	1535	1529	1514	1525	1523	146
15°	1464	1450	1416	1410	1401	412
25°	1332	1300	1244	1219	1204	613
35°	1153	1106	1031	979	955	721
45°	948	889	796	727	695	731
55°	720	656	553	483	456	645
65°	492	422	326	268	252	487
75°	260	200	132	120	117	278
85°	66	40	35	32	32	74
90°	0	5	11	13	14	5
95°	28	10	14	17	17	34
105°	135	137	99	24	20	143
115°	252	255	259	264	266	249
125°	356	360	362	362	363	318
135°	443	446	448	449	448	341
145°	511	515	516	516	516	320
155°	563	563	563	565	562	259
165°	594	593	592	596	593	168
175°	608	606	606	609	606	58
180°	608	608	608	608	608	



TEST NUMBER: P332369-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1540.4	1539.4	1538.6	1537.7	1536.8	1535.0	1532.4	1529.7	1527.1	1524.4	1526.9
5°	1535.4	1534.0	1532.6	1531.2	1529.9	1527.5	1524.2	1520.8	1517.5	1514.2	1516.7
7.5°	1521.1	1519.7	1518.2	1516.7	1515.2	1512.3	1508.0	1503.6	1499.4	1495.0	1496.4
10°	1509.3	1507.3	1505.4	1503.4	1501.5	1498.0	1493.0	1488.0	1483.0	1478.1	1478.4
12.5°	1492.3	1490.2	1488.0	1485.8	1483.7	1479.6	1473.5	1467.4	1461.3	1455.2	1455.0
15°	1464.4	1461.3	1458.3	1455.2	1452.2	1446.8	1439.1	1431.3	1423.6	1415.9	1414.4
17.5°	1429.3	1425.8	1422.2	1418.6	1415.2	1408.4	1398.6	1388.7	1378.9	1369.0	1366.1
20°	1403.4	1399.0	1394.6	1390.1	1385.7	1378.2	1367.7	1357.2	1346.6	1336.2	1332.5
22.5°	1374.5	1369.4	1364.3	1359.2	1354.2	1346.0	1334.8	1323.7	1312.5	1301.2	1296.8
25°	1332.4	1325.5	1318.6	1311.6	1304.7	1294.9	1282.1	1269.5	1256.7	1244.0	1238.2
27.5°	1281.4	1273.7	1266.1	1258.5	1250.8	1239.9	1225.7	1211.6	1197.4	1183.2	1175.1
30°	1246.5	1238.2	1229.9	1221.5	1213.3	1201.3	1185.9	1170.4	1154.9	1139.4	1130.0
32.5°	1211.6	1202.2	1192.8	1183.4	1174.0	1161.1	1144.7	1128.3	1111.9	1095.6	1085.3
35°	1153.1	1143.1	1133.1	1123.2	1113.3	1099.7	1082.5	1065.4	1048.2	1031.0	1019.1
37.5°	1093.8	1082.8	1071.7	1060.6	1049.6	1034.8	1016.5	998.2	979.9	961.6	948.1
40°	1056.0	1043.8	1031.6	1019.5	1007.3	991.3	971.7	952.0	932.4	912.8	898.3
42.5°	1013.1	1000.9	988.8	976.6	964.4	948.2	927.9	907.5	887.2	867.0	851.2
45°	947.6	935.2	922.7	910.3	897.8	880.9	859.6	838.3	817.0	795.7	779.9
47.5°	882.1	868.5	854.8	841.1	827.4	809.9	788.6	767.3	746.0	724.8	707.6
50°	834.3	821.3	808.3	795.3	782.3	764.6	742.2	719.8	697.4	674.9	657.7
52.5°	791.5	777.4	763.3	749.2	735.0	716.8	694.7	672.5	650.3	628.1	610.3
55°	719.8	706.2	692.6	679.1	665.5	647.0	623.4	599.9	576.4	552.9	536.9
57.5°	653.5	638.7	623.9	609.2	594.4	575.2	551.6	527.9	504.3	480.7	465.5
60°	607.7	592.5	577.3	562.1	546.8	527.7	504.7	481.8	458.8	435.9	420.9
62.5°	561.8	546.6	531.4	516.2	501.0	481.9	458.9	435.9	413.0	390.0	376.0
65°	491.9	476.7	461.4	446.2	431.0	412.6	391.0	369.4	347.8	326.2	312.7
67.5°	421.9	406.5	391.1	375.7	360.4	342.3	321.6	300.9	280.2	259.5	249.4
70°	376.0	361.2	346.2	331.2	316.3	299.1	279.8	260.4	241.1	221.7	212.0
72.5°	330.3	315.5	300.8	286.1	271.3	255.2	237.6	220.0	202.4	184.8	176.9
75°	260.2	247.0	233.7	220.4	207.2	192.9	177.7	162.4	147.2	132.0	129.2
77.5°	196.5	184.5	172.5	160.5	148.5	137.5	127.8	118.0	108.1	98.4	96.9
80°	155.7	144.3	132.9	121.6	110.3	101.7	95.9	90.1	84.3	78.4	77.6
82.5°	116.8	107.0	97.2	87.4	77.6	71.4	68.7	65.9	63.2	60.5	59.7
85°	66.0	59.9	53.8	47.8	41.7	38.2	37.4	36.5	35.7	34.9	34.3
87.5°	24.0	21.8	19.6	17.3	15.1	14.1	14.3	14.6	14.9	15.1	15.0
90°	0.5	1.4	2.5	3.5	4.4	5.6	6.9	8.2	9.5	10.9	11.2
92.5°	8.4	8.2	7.8	7.5	7.3	7.6	8.6	9.6	10.6	11.6	12.2
95°	27.6	23.4	19.3	15.2	11.1	9.6	10.7	11.8	12.9	14.0	14.7
97.5°	55.4	53.6	51.7	49.8	48.0	43.5	36.2	29.0	21.8	14.6	15.4
100°	76.4	78.3	80.4	82.4	84.4	77.6	61.9	46.3	30.6	14.9	15.7
102.5°	100.2	101.6	103.1	104.6	106.0	98.2	81.0	63.9	46.8	29.7	27.3
105°	134.7	135.8	136.9	137.9	139.0	135.1	126.0	117.0	108.0	98.9	81.2
107.5°	171.0	171.8	172.8	173.6	174.5	175.6	177.1	178.5	179.9	181.3	168.3
110°	195.2	196.0	196.8	197.6	198.4	199.4	200.4	201.5	202.6	203.7	200.4



TEST NUMBER: P332369-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.3	219.0	219.8	220.5	221.2	222.1	223.2	224.3	225.5	226.6	226.6
115°	252.5	253.2	253.7	254.4	255.0	255.7	256.7	257.5	258.4	259.4	260.4
117.5°	285.7	286.5	287.2	288.0	288.7	289.3	289.8	290.3	290.7	291.1	292.0
120°	306.3	307.2	308.2	309.0	310.0	310.5	310.9	311.2	311.5	311.7	312.6
122.5°	327.3	328.0	328.8	329.5	330.3	330.8	331.2	331.6	332.0	332.4	333.0
125°	356.0	356.9	357.7	358.5	359.3	359.9	360.3	360.7	361.1	361.5	361.6
127.5°	383.9	384.7	385.5	386.3	387.1	387.7	388.2	388.7	389.2	389.7	390.0
130°	401.2	402.0	402.8	403.6	404.4	405.0	405.4	405.8	406.2	406.6	407.0
132.5°	417.9	418.7	419.5	420.3	421.0	421.6	421.9	422.2	422.6	422.9	423.3
135°	443.2	443.9	444.4	445.0	445.7	446.2	446.6	446.9	447.3	447.7	448.1
137.5°	464.9	465.7	466.4	467.2	467.9	468.5	468.7	468.9	469.1	469.4	469.8
140°	479.3	480.0	480.6	481.2	481.8	482.3	482.5	482.8	483.2	483.5	483.9
142.5°	492.7	493.4	494.0	494.6	495.2	495.6	495.9	496.2	496.5	496.9	497.2
145°	511.4	512.1	512.9	513.6	514.3	514.8	514.9	515.2	515.3	515.6	515.7
147.5°	529.1	529.6	530.0	530.4	530.9	531.2	531.5	531.6	531.9	532.1	532.3
150°	540.0	540.3	540.5	540.8	541.1	541.4	541.6	541.8	542.0	542.2	542.4
152.5°	549.7	549.9	549.9	550.1	550.2	550.4	550.5	550.6	550.7	550.9	551.2
155°	563.4	563.2	563.0	562.8	562.6	562.6	562.7	562.8	562.8	563.0	563.5
157.5°	574.1	574.1	574.0	574.0	574.0	573.9	573.9	573.8	573.6	573.5	574.2
160°	580.6	580.5	580.4	580.3	580.2	580.1	580.0	579.9	579.8	579.7	580.3
162.5°	586.8	586.5	586.2	586.0	585.7	585.5	585.4	585.3	585.2	585.1	585.8
165°	594.1	593.8	593.6	593.3	592.9	592.7	592.6	592.6	592.5	592.3	593.2
167.5°	599.9	599.5	599.1	598.7	598.3	598.1	598.1	598.1	598.1	598.1	599.0
170°	603.2	602.8	602.4	602.0	601.6	601.3	601.3	601.3	601.3	601.3	602.2
172.5°	605.4	604.9	604.4	603.9	603.4	603.2	603.3	603.4	603.5	603.6	604.4
175°	608.2	607.7	607.1	606.7	606.2	605.9	606.0	606.2	606.3	606.3	607.0
177.5°	608.9	608.5	608.1	607.7	607.3	607.1	607.2	607.3	607.4	607.4	608.1
180°	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2



TEST NUMBER: P332369-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1529.3	1531.8	1534.1	1535.2	1534.7	1534.3	1533.8	1533.3
5°	1519.2	1521.7	1524.2	1525.1	1524.6	1524.0	1523.4	1522.9
7.5°	1497.8	1499.2	1500.6	1500.8	1499.8	1498.9	1497.9	1497.0
10°	1478.7	1478.9	1479.2	1478.7	1477.3	1475.9	1474.5	1473.1
12.5°	1454.8	1454.7	1454.5	1453.7	1452.1	1450.4	1448.8	1447.2
15°	1413.1	1411.7	1410.3	1408.7	1406.7	1404.8	1402.8	1400.9
17.5°	1363.2	1360.2	1357.2	1354.4	1351.5	1348.6	1345.8	1342.8
20°	1329.0	1325.3	1321.8	1318.3	1314.9	1311.6	1308.4	1305.0
22.5°	1292.3	1287.9	1283.3	1279.5	1276.4	1273.4	1270.3	1267.2
25°	1232.4	1226.5	1220.8	1216.3	1213.3	1210.2	1207.2	1204.1
27.5°	1167.0	1159.0	1150.9	1144.5	1139.9	1135.3	1130.6	1125.9
30°	1120.5	1111.2	1101.8	1094.9	1090.4	1086.0	1081.6	1077.1
32.5°	1075.0	1064.7	1054.4	1046.9	1042.3	1037.6	1033.0	1028.3
35°	1007.3	995.4	983.5	975.0	970.0	965.0	960.0	955.1
37.5°	934.5	921.1	907.5	897.7	891.6	885.4	879.3	873.1
40°	884.0	869.6	855.2	844.9	838.4	832.1	825.8	819.4
42.5°	835.5	819.8	804.1	793.4	787.7	782.0	776.3	770.6
45°	764.1	748.4	732.6	721.4	714.8	708.1	701.5	694.8
47.5°	690.4	673.3	656.1	644.6	638.7	632.7	626.8	620.9
50°	640.6	623.4	606.3	594.5	588.2	581.8	575.4	569.1
52.5°	592.5	574.6	556.8	545.0	539.3	533.7	528.0	522.3
55°	520.8	504.7	488.7	477.9	472.4	466.8	461.3	455.7
57.5°	450.4	435.1	420.0	410.0	405.4	400.7	395.9	391.3
60°	405.9	391.0	376.0	366.2	361.6	356.8	352.1	347.5
62.5°	361.9	347.8	333.7	324.3	319.3	314.4	309.5	304.6
65°	299.1	285.6	272.0	263.7	260.7	257.6	254.6	251.5
67.5°	239.2	229.1	219.0	212.3	209.1	205.7	202.5	199.2
70°	202.2	192.6	182.9	176.6	173.5	170.5	167.4	164.4
72.5°	169.0	161.1	153.1	148.5	147.3	146.0	144.7	143.5
75°	126.4	123.7	120.9	119.3	118.7	118.2	117.6	117.1
77.5°	95.4	93.9	92.4	91.3	90.8	90.2	89.7	89.1
80°	76.8	76.0	75.1	74.5	73.9	73.4	72.8	72.2
82.5°	58.9	58.1	57.2	56.7	56.6	56.5	56.4	56.3
85°	33.7	33.2	32.6	32.4	32.4	32.4	32.4	32.4
87.5°	14.8	14.7	14.6	14.4	14.2	14.0	13.9	13.7
90°	11.6	12.0	12.4	12.8	13.0	13.2	13.4	13.5
92.5°	12.8	13.5	14.1	14.5	14.7	14.7	14.9	15.0
95°	15.4	16.1	16.8	17.2	17.2	17.2	17.2	17.2
97.5°	16.2	17.0	17.7	18.2	18.3	18.4	18.5	18.6
100°	16.5	17.3	18.1	18.5	18.7	18.8	18.9	19.0
102.5°	24.7	22.3	19.8	18.6	18.8	19.0	19.2	19.3
105°	63.4	45.6	27.9	19.1	19.3	19.5	19.6	19.9
107.5°	155.3	142.3	129.2	116.1	102.6	89.2	75.8	62.4
110°	197.2	193.8	190.5	181.6	167.3	153.0	138.6	124.2





TEST NUMBER: P332369-927

CATALOG NUMBER: S123RDIP-S1165D585U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	226.6	226.7	226.8	225.3	222.3	219.2	216.2	213.2
115°	261.3	262.4	263.4	264.0	264.4	264.9	265.3	265.7
117.5°	292.8	293.6	294.4	294.9	294.9	295.0	295.1	295.2
120°	313.4	314.2	315.0	315.4	315.4	315.4	315.4	315.4
122.5°	333.5	334.1	334.6	334.9	335.0	335.1	335.2	335.3
125°	361.9	362.0	362.3	362.5	362.7	362.9	363.1	363.3
127.5°	390.3	390.6	390.9	391.0	390.8	390.6	390.4	390.2
130°	407.4	407.8	408.2	408.4	408.1	408.0	407.7	407.6
132.5°	423.7	424.1	424.5	424.6	424.3	424.0	423.7	423.4
135°	448.4	448.7	448.9	448.9	448.7	448.4	448.1	447.7
137.5°	470.3	470.8	471.3	471.4	471.2	471.0	470.8	470.6
140°	484.3	484.7	485.1	485.1	485.0	484.7	484.6	484.3
142.5°	497.5	497.8	498.1	498.1	497.9	497.6	497.3	497.0
145°	515.9	516.1	516.3	516.4	516.4	516.4	516.4	516.4
147.5°	532.5	532.7	532.9	532.7	532.3	531.8	531.4	530.9
150°	542.6	542.8	543.0	543.0	542.6	542.3	542.0	541.8
152.5°	551.6	551.9	552.3	552.2	551.8	551.4	550.9	550.4
155°	564.0	564.5	565.0	564.9	564.4	563.7	563.2	562.5
157.5°	574.7	575.4	576.0	575.8	575.0	574.3	573.5	572.7
160°	580.9	581.5	582.1	582.0	581.4	580.7	580.0	579.2
162.5°	586.5	587.2	587.9	587.9	587.2	586.6	586.0	585.4
165°	594.0	594.8	595.6	595.6	594.9	594.2	593.5	592.8
167.5°	599.8	600.6	601.3	601.3	600.6	599.8	599.0	598.1
170°	603.0	603.8	604.6	604.6	603.8	603.0	602.2	601.3
172.5°	605.1	605.9	606.7	606.7	605.9	605.0	604.0	603.2
175°	607.8	608.5	609.2	609.1	608.3	607.5	606.7	605.9
177.5°	608.7	609.3	610.0	609.9	609.1	608.3	607.5	606.7
180°	608.2	608.2	608.2	608.2	608.2	608.2	608.2	608.2

(END OF REPORT)