

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332260-927

Luminaire Tested: **S123RDIP-S340D1025U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332260-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S340D1025U927-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4015.3 lumens  
Efficiency: N/A  
Efficacy: 107.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot



73% Up  
27% Dn



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30	23
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26	20
3	77	69	62	56	69	62	56	51	48	44	41	36	34	32	25	23	22	17
4	71	61	53	48	63	55	48	44	43	39	35	32	30	27	22	21	19	15
5	65	54	47	41	58	49	42	37	39	34	30	29	26	24	20	18	17	13
6	60	49	41	35	53	44	37	32	35	30	27	26	23	21	18	17	15	12
7	55	44	36	31	49	40	33	28	32	27	23	24	21	18	17	15	13	11
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10
9	48	36	29	24	43	33	27	22	26	22	18	20	17	15	14	12	11	9
10	44	33	26	22	40	30	24	20	24	20	17	19	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4640	4640	4640	4640
5°	5532	4660	4105	4660
10°	6907	4634	3707	4634
15°	8107	4586	3381	4586
20°	9049	4515	3103	4515
25°	8904	4441	2932	4441
30°	6400	4373	2757	4373
35°	4273	4282	2643	4282
40°	3147	4175	2525	4175
45°	2641	3987	2411	3987
50°	2331	3739	2251	3739
55°	2044	3457	2029	3457
60°	1819	3186	1858	3186
65°	1597	2896	1729	2896
70°	1253	2637	1580	2637
75°	1102	2304	1443	2304
80°	961	1953	1420	1953
85°	778	1581	1507	1581



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.4	1.1
10°-20°	132.5	3.3
20°-30°	208.1	5.2
30°-40°	217.1	5.4
40°-50°	185.8	4.6
50°-60°	141.6	3.5
60°-70°	90.8	2.3
70°-80°	43.7	1.1
80°-90°	14.6	0.4
90°-100°	217.4	5.4
100°-110°	615.6	15.3
110°-120°	605.5	15.1
120°-130°	483.0	12.0
130°-140°	380.8	9.5
140°-150°	284.2	7.1
150°-160°	198.1	4.9
160°-170°	116.4	2.9
170°-180°	37.9	0.9
0°-30°	382.9	9.5
0°-40°	600.1	14.9
0°-60°	927.5	23.1
0°-90°	1076.5	26.8
90°-120°	1438.5	35.8
90°-150°	2586.5	64.4
90°-180°	2939.0	73.2
0°-180°	4015.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	431	431	431	431	431	
5°	512	431	380	431	512	53
15°	728	412	303	412	728	206
25°	750	374	247	374	750	322
35°	325	326	201	326	325	213
45°	174	262	158	262	174	136
55°	109	184	108	184	109	98
65°	63	114	68	114	63	62
75°	26	55	35	55	26	28
85°	6	13	12	13	6	8
90°	23	2	23	2	23	12
95°	92	27	92	27	92	165
105°	1006	92	1006	92	1006	992
115°	1223	162	1223	162	1223	1189
125°	965	225	965	225	965	874
135°	782	264	782	264	782	607
145°	611	301	611	301	611	389
155°	507	342	507	342	507	236
165°	442	374	442	374	442	126
175°	398	390	398	390	398	39
180°	391	391	391	391	391	



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	459.2	459.8	457.9	457.6	455.3	454.8	454.8	451.6	449.7	447.3	445.8
5°	512.0	514.9	513.4	510.2	504.6	503.3	499.8	494.2	488.0	480.2	476.6
7.5°	577.9	581.9	580.4	575.3	569.4	564.7	554.8	545.7	532.8	521.5	511.8
10°	631.9	627.7	624.4	619.4	614.0	605.4	595.0	580.8	564.4	551.4	537.1
12.5°	672.4	671.7	667.5	662.3	654.8	646.6	633.8	616.6	597.5	578.8	562.3
15°	727.5	728.6	725.9	720.6	709.8	695.2	676.0	668.8	641.5	621.2	600.9
17.5°	765.7	765.5	765.1	757.7	746.8	736.4	718.6	699.7	674.9	646.3	619.0
20°	790.0	788.1	788.5	780.1	772.1	760.0	742.7	715.2	694.9	661.9	633.6
22.5°	789.3	788.9	790.4	787.5	781.6	772.5	758.8	735.5	709.6	676.3	644.5
25°	749.7	748.2	756.9	759.3	768.7	770.4	766.3	753.6	729.0	694.7	655.4
27.5°	627.4	626.6	642.7	662.9	688.4	708.3	727.5	736.7	729.0	704.4	665.0
30°	514.9	532.3	540.4	569.6	602.1	640.8	674.8	707.0	715.0	704.3	672.0
32.5°	427.5	442.7	449.5	474.4	504.8	550.2	601.1	646.8	679.1	687.3	667.9
35°	325.2	325.3	340.9	352.0	380.0	426.7	476.2	537.4	598.3	644.5	649.3
37.5°	259.5	260.4	269.8	280.8	301.9	326.5	370.1	421.0	491.4	562.2	603.8
40°	224.0	225.7	232.7	243.6	258.7	277.4	311.3	359.3	418.0	496.9	561.3
42.5°	201.3	204.0	207.6	216.0	225.4	242.9	270.3	307.4	360.8	435.3	509.6
45°	173.5	175.0	177.8	181.6	190.1	202.2	220.7	245.7	289.9	349.9	424.3
47.5°	153.0	152.3	155.2	158.3	164.0	172.3	184.7	204.9	236.5	284.7	347.8
50°	139.2	138.9	141.0	143.4	148.8	154.9	165.0	180.3	205.4	245.3	303.1
52.5°	126.2	126.8	128.3	131.3	135.1	140.1	149.2	160.3	181.8	216.2	264.4
55°	108.9	109.5	111.5	113.1	115.9	120.9	126.6	135.9	150.6	174.6	214.3
57.5°	94.3	94.0	95.9	96.4	99.5	103.5	108.0	115.2	125.9	143.7	170.4
60°	84.5	84.0	85.6	86.9	88.6	91.9	95.6	102.6	111.1	124.2	147.1
62.5°	75.7	75.4	76.6	78.0	79.3	82.3	85.4	90.8	97.5	108.5	126.7
65°	62.7	63.3	63.8	64.4	65.1	67.0	69.9	73.7	78.3	86.0	99.1
67.5°	49.4	49.9	50.1	51.2	52.8	53.9	55.8	59.0	62.3	68.8	76.2
70°	39.8	39.7	39.8	40.4	42.5	44.4	46.9	49.3	51.3	55.9	62.2
72.5°	34.2	33.9	34.4	34.5	35.5	36.0	37.5	39.8	42.5	45.6	50.1
75°	26.5	26.5	26.5	26.5	27.3	27.6	28.2	28.8	29.7	31.2	34.5
77.5°	19.6	19.6	20.0	20.1	20.3	20.5	20.8	21.4	21.7	22.5	23.9
80°	15.5	15.7	15.5	15.7	15.7	16.1	16.2	16.8	17.0	17.9	18.5
82.5°	11.6	11.6	11.6	11.9	11.9	12.2	12.3	12.7	12.7	13.2	13.7
85°	6.3	5.9	6.3	6.1	6.5	6.1	6.3	6.7	6.7	6.8	7.6
87.5°	6.1	6.5	6.1	6.0	6.2	6.0	5.9	5.7	5.9	5.9	5.5
90°	22.9	23.7	22.9	22.1	22.9	21.4	20.6	19.8	19.0	19.8	17.4
92.5°	38.1	39.5	38.7	41.1	42.5	46.7	52.8	66.5	91.7	121.6	133.8
95°	91.7	94.9	100.4	107.6	122.6	151.1	193.0	284.6	380.3	468.9	417.5
97.5°	249.7	256.5	277.9	313.5	371.8	466.4	568.4	709.6	777.4	726.7	532.0
100°	495.8	495.0	525.9	583.6	663.5	775.7	868.2	932.3	904.6	748.8	506.0
102.5°	727.3	745.5	771.3	817.0	879.2	950.3	1004.2	1006.3	910.9	707.7	468.1
105°	1005.8	1009.8	1035.1	1065.1	1101.5	1122.0	1107.1	1027.9	862.7	635.7	421.4
107.5°	1166.2	1173.5	1182.0	1192.2	1191.5	1163.3	1094.1	965.7	778.2	572.2	391.7
110°	1232.0	1233.6	1235.2	1228.8	1206.7	1151.3	1051.7	906.2	725.1	536.1	380.3



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1245.2	1244.9	1238.9	1219.3	1178.8	1107.6	996.0	847.3	678.9	512.1	374.0
115°	1223.3	1219.3	1203.5	1168.7	1109.4	1023.2	907.0	769.4	623.1	486.3	371.6
117.5°	1153.3	1148.0	1125.2	1085.4	1023.5	936.0	831.7	713.0	589.4	471.1	373.0
120°	1095.2	1090.4	1071.4	1027.1	964.7	884.9	790.0	683.2	571.7	464.1	375.6
122.5°	1040.8	1034.7	1013.9	974.1	918.5	844.4	756.5	659.8	557.1	459.7	380.0
125°	964.7	959.2	939.4	904.6	854.0	790.8	714.9	628.7	538.5	453.9	386.7
127.5°	902.1	897.0	879.2	849.4	804.3	746.8	678.3	601.4	522.0	451.1	394.3
130°	866.6	860.3	843.8	815.2	773.3	719.5	655.5	584.4	513.2	449.2	399.3
132.5°	831.9	827.4	812.7	784.3	744.9	693.6	634.0	568.5	504.9	448.5	403.1
135°	782.0	776.5	762.2	738.6	699.8	654.7	603.3	547.2	494.2	447.6	408.8
137.5°	729.4	725.7	713.8	689.7	657.1	618.1	573.8	527.8	484.9	445.8	412.6
140°	692.7	693.5	680.8	658.7	628.7	594.6	556.7	516.3	479.2	445.2	415.1
142.5°	658.5	659.3	647.9	628.4	602.7	573.1	540.3	505.6	474.1	443.9	417.0
145°	611.2	609.7	603.3	586.7	567.0	544.0	518.7	492.7	467.3	442.0	418.3
147.5°	572.4	571.7	565.7	554.4	539.5	523.2	502.7	482.0	460.7	439.0	418.3
150°	549.5	549.5	544.8	536.1	524.3	509.2	492.7	474.4	456.2	436.5	418.3
152.5°	530.6	530.6	527.8	519.7	510.3	497.9	483.2	467.5	451.2	433.3	416.4
155°	506.8	506.0	504.5	498.2	491.1	481.6	469.7	457.0	443.6	427.8	414.3
157.5°	485.2	485.4	484.1	479.3	473.2	465.7	456.5	446.0	435.1	422.9	411.7
160°	471.3	472.1	472.1	467.3	461.8	456.2	448.4	439.7	429.4	419.1	410.4
162.5°	458.6	459.4	459.4	455.3	451.7	446.8	439.5	432.1	423.7	415.3	407.9
165°	442.0	442.0	442.8	439.7	436.5	432.5	427.0	422.2	415.9	409.6	404.1
167.5°	426.2	426.2	427.0	424.8	423.3	420.5	417.3	413.7	408.5	403.9	400.3
170°	416.7	416.7	417.5	415.9	415.1	413.5	410.4	408.1	404.1	400.1	397.8
172.5°	407.9	408.5	410.0	408.4	408.2	407.3	404.7	403.0	399.7	397.0	395.9
175°	397.8	398.5	399.3	398.5	398.5	398.5	397.0	396.2	394.6	393.0	393.0
177.5°	391.9	391.9	393.2	392.5	393.2	393.2	392.5	391.9	391.3	390.6	391.3
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	445.1	444.7	442.7	440.3	437.2	435.1	433.5	432.6	429.9	426.7	424.5
5°	472.7	467.1	461.2	454.0	447.3	440.5	436.3	431.3	425.2	418.4	413.6
7.5°	502.1	491.2	479.6	467.5	455.6	444.9	435.4	427.3	417.6	407.8	401.0
10°	524.7	508.8	492.4	475.6	460.3	445.9	434.8	424.0	412.3	401.1	392.5
12.5°	545.3	524.3	505.4	484.7	465.2	448.0	432.1	419.2	405.2	393.2	383.6
15°	571.2	549.8	527.0	495.5	469.5	447.7	428.3	411.5	394.6	379.9	370.4
17.5°	595.5	563.3	532.5	506.4	472.5	445.4	421.7	401.6	382.9	367.3	355.7
20°	605.5	574.3	541.0	507.6	474.4	443.9	416.4	394.2	374.9	357.1	346.4
22.5°	611.6	576.3	541.1	505.2	469.9	438.2	411.1	386.7	365.7	348.9	335.6
25°	618.6	576.6	537.8	502.4	466.4	432.1	399.7	373.9	351.3	333.4	319.3
27.5°	623.3	573.8	528.0	488.6	452.1	418.0	388.3	360.9	337.9	318.9	303.9
30°	624.2	571.6	520.5	477.8	440.8	409.3	378.0	351.8	327.4	307.3	293.3
32.5°	625.3	566.1	510.2	465.0	427.0	395.9	367.5	342.5	317.5	297.7	283.4
35°	620.5	563.1	494.8	442.8	404.7	374.6	349.0	325.9	301.4	282.2	267.6
37.5°	599.5	551.1	478.8	417.7	378.0	350.1	329.2	309.1	286.6	265.9	252.2
40°	578.5	539.3	466.4	402.5	361.0	332.4	313.5	297.1	275.4	256.0	241.2
42.5°	547.0	523.2	454.6	386.6	341.8	314.3	298.3	283.0	263.9	244.2	230.3
45°	489.3	492.4	430.4	361.2	315.2	287.6	272.6	261.9	244.9	228.7	214.4
47.5°	416.9	446.2	402.0	334.1	287.2	261.3	248.2	238.8	227.4	211.4	198.4
50°	369.7	411.5	379.3	316.0	269.7	243.8	230.9	223.3	213.3	200.8	188.5
52.5°	326.1	371.1	351.8	295.7	250.6	227.0	214.4	208.1	200.2	188.4	177.2
55°	265.9	311.6	307.1	265.2	222.0	200.8	191.2	184.2	178.9	170.0	161.1
57.5°	215.2	258.3	260.6	231.2	196.9	175.9	167.6	162.3	158.8	152.2	143.9
60°	183.1	222.8	230.5	208.3	178.9	160.4	152.3	148.0	145.3	139.9	133.6
62.5°	156.5	190.3	199.1	183.2	161.6	144.3	137.9	133.9	132.0	127.4	121.8
65°	119.8	147.8	156.3	147.5	136.2	122.4	117.2	113.7	112.0	109.5	105.4
67.5°	90.1	110.5	119.9	113.6	109.5	100.8	97.5	95.6	94.1	92.4	89.0
70°	72.3	87.5	97.0	95.5	92.1	87.5	85.1	83.8	82.3	80.8	77.9
72.5°	58.1	68.6	77.6	78.4	75.7	74.8	72.6	72.1	71.2	69.5	67.8
75°	38.6	45.8	52.0	54.4	55.5	56.5	55.5	55.4	55.2	53.7	52.8
77.5°	25.3	29.2	33.1	37.2	39.0	40.2	40.5	41.2	40.6	39.9	39.5
80°	19.4	20.3	23.1	26.5	29.3	30.4	31.2	31.5	31.4	31.2	30.4
82.5°	14.1	14.8	16.2	18.6	20.9	22.7	23.2	23.1	23.5	23.7	23.1
85°	7.6	7.8	8.2	8.5	9.7	11.8	12.4	12.8	13.1	13.1	12.0
87.5°	5.4	4.8	4.6	4.3	4.4	4.0	4.6	5.1	5.5	5.2	5.7
90°	15.1	12.7	10.3	8.7	7.1	4.8	3.2	1.6	3.2	4.8	7.1
92.5°	100.4	66.4	45.7	34.0	27.3	21.2	14.6	9.8	14.6	21.2	27.3
95°	287.8	170.0	102.8	71.9	51.4	37.9	29.2	26.9	29.2	37.9	51.4
97.5°	315.8	183.0	118.7	85.4	65.1	53.5	46.7	45.9	46.7	53.5	65.1
100°	298.1	181.1	125.7	94.9	75.9	64.9	59.3	58.5	59.3	64.9	75.9
102.5°	282.9	183.6	134.0	105.7	88.6	78.1	73.2	71.8	73.2	78.1	88.6
105°	272.0	190.6	147.9	123.3	108.4	98.9	94.1	91.7	94.1	98.9	108.4
107.5°	271.2	203.5	166.0	143.3	129.2	119.9	115.3	112.9	115.3	119.9	129.2
110°	274.4	214.3	178.7	156.5	143.1	134.4	130.5	128.1	130.5	134.4	143.1





TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	280.7	225.1	192.0	170.5	157.0	148.4	144.4	142.0	144.4	148.4	157.0
115°	291.0	242.7	212.7	191.4	177.9	170.0	165.2	162.1	165.2	170.0	177.9
117.5°	304.6	261.6	231.9	212.1	197.0	189.8	185.8	182.2	185.8	189.8	197.0
120°	314.7	273.6	245.1	225.4	210.3	202.4	198.4	196.1	198.4	202.4	210.3
122.5°	324.2	286.2	258.4	237.4	223.0	214.4	210.5	208.1	210.5	214.4	223.0
125°	339.2	304.4	276.8	255.4	240.3	231.7	227.0	225.4	227.0	231.7	240.3
127.5°	351.6	320.3	293.5	272.2	255.6	246.7	240.8	238.5	240.8	246.7	255.6
130°	359.8	329.7	303.6	282.3	265.7	256.2	249.1	246.7	249.1	256.2	265.7
132.5°	367.4	337.9	312.5	291.8	275.2	263.8	256.0	253.0	256.0	263.8	275.2
135°	377.2	350.3	325.7	304.4	287.8	276.0	267.3	264.1	267.3	276.0	287.8
137.5°	384.4	358.9	335.3	315.5	299.0	286.4	277.9	274.6	277.9	286.4	299.0
140°	388.2	364.6	341.6	321.9	306.0	293.3	285.4	281.5	285.4	293.3	306.0
142.5°	392.1	369.0	346.7	328.1	312.4	301.0	292.4	289.1	292.4	301.0	312.4
145°	396.2	374.8	354.3	336.0	322.7	310.8	303.6	301.3	303.6	310.8	322.7
147.5°	398.7	379.5	360.8	345.2	332.2	322.0	315.1	313.6	315.1	322.0	332.2
150°	399.3	382.7	364.6	350.3	339.2	328.9	322.7	321.9	322.7	328.9	339.2
152.5°	400.6	384.6	369.0	355.4	345.5	336.5	330.2	330.0	330.2	336.5	345.5
155°	400.9	388.2	374.8	363.8	355.1	347.1	342.4	342.4	342.4	347.1	355.1
157.5°	401.7	390.3	379.5	371.0	363.6	356.6	352.8	352.2	352.8	356.6	363.6
160°	401.7	392.2	382.7	374.8	369.2	363.0	359.8	359.8	359.8	363.0	369.2
162.5°	401.1	392.8	384.6	378.0	373.0	368.0	365.5	365.5	365.5	368.0	373.0
165°	399.3	393.8	387.5	381.9	378.7	374.8	373.2	374.0	373.2	374.8	378.7
167.5°	398.1	393.6	389.0	385.6	383.3	380.3	379.5	380.5	379.5	380.3	383.3
170°	396.2	393.0	389.0	387.5	385.9	383.5	382.7	384.3	382.7	383.5	385.9
172.5°	395.5	393.0	389.7	388.7	387.8	386.0	385.9	386.8	385.9	386.0	387.8
175°	393.8	392.2	390.6	389.8	389.8	388.2	389.0	389.8	389.0	388.2	389.8
177.5°	392.5	391.3	390.6	390.6	390.6	390.0	390.6	391.3	390.6	390.0	390.6
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	423.7	421.8	420.5	417.6	415.7	413.6	411.5	412.8	412.6	412.6	412.6
5°	409.6	405.3	401.4	396.4	393.3	389.4	386.5	386.1	386.8	384.3	382.8
7.5°	395.5	389.7	384.1	378.7	372.8	368.1	365.3	363.8	362.0	360.4	358.8
10°	385.6	378.7	373.4	366.5	360.3	354.7	351.3	348.8	347.5	346.3	343.8
12.5°	375.3	368.7	361.9	354.1	348.2	341.7	339.1	336.4	334.0	332.5	329.2
15°	360.4	351.8	344.6	336.4	329.8	323.5	319.9	314.5	313.8	311.9	308.6
17.5°	345.5	336.1	326.1	320.1	312.7	306.1	300.5	298.7	293.4	291.4	288.5
20°	333.7	325.0	317.4	309.5	298.7	292.6	288.1	285.7	281.5	278.8	277.0
22.5°	323.5	314.7	305.9	296.7	287.7	280.8	277.6	273.9	271.6	267.9	265.9
25°	309.0	299.4	288.8	278.8	272.4	267.3	262.1	258.7	255.4	253.7	250.1
27.5°	292.1	282.0	272.2	264.6	256.7	251.6	246.9	244.0	240.0	237.2	235.1
30°	282.7	270.9	262.4	255.6	245.5	240.7	237.2	233.5	230.5	227.6	225.5
32.5°	272.0	261.2	253.2	244.7	236.9	231.6	227.1	223.9	221.3	218.6	216.5
35°	255.1	246.1	237.7	229.3	223.5	218.2	212.8	210.0	207.6	205.0	203.2
37.5°	239.8	231.3	223.4	215.4	208.3	203.9	199.6	197.5	194.2	192.5	190.7
40°	230.4	222.0	213.6	205.8	198.4	195.1	191.2	188.1	185.1	183.8	181.8
42.5°	220.0	211.7	204.5	196.2	190.1	185.6	182.0	178.6	176.4	174.5	173.4
45°	204.7	197.3	190.3	182.0	176.3	172.4	168.3	165.2	163.2	161.8	159.9
47.5°	189.8	182.4	175.3	168.1	162.6	158.1	154.0	151.9	149.2	147.6	146.2
50°	179.0	172.4	164.9	158.2	152.7	148.2	144.9	142.1	139.7	137.7	136.7
52.5°	169.1	162.1	155.5	149.3	143.5	138.5	135.5	132.5	130.7	128.4	127.3
55°	152.8	146.0	140.5	134.4	128.7	124.4	120.7	118.1	116.3	113.7	112.3
57.5°	137.5	131.3	124.8	119.5	113.6	110.0	106.9	103.5	101.2	99.2	97.7
60°	127.1	120.2	114.4	109.5	104.3	99.7	96.9	94.1	91.7	89.7	88.4
62.5°	116.4	110.3	104.8	99.4	94.7	90.6	87.5	85.2	83.0	81.8	80.4
65°	99.8	95.1	89.5	85.1	80.6	77.7	75.1	73.1	71.6	70.7	69.6
67.5°	84.6	80.0	75.2	70.8	67.8	65.6	63.9	62.2	61.4	60.2	59.5
70°	74.8	69.9	65.7	62.3	59.4	57.8	56.6	55.4	54.7	53.2	52.4
72.5°	64.0	60.5	57.4	54.7	52.4	50.9	49.4	47.8	46.7	45.0	44.3
75°	50.4	47.2	44.8	43.0	41.5	39.5	37.5	35.8	35.3	34.7	34.5
77.5°	37.3	35.3	33.6	32.0	30.2	28.8	28.3	27.9	27.8	27.5	27.5
80°	29.3	27.5	26.2	24.4	23.3	23.3	23.3	22.9	23.1	23.1	23.1
82.5°	21.8	20.1	19.4	18.8	18.5	18.7	18.7	18.8	18.6	18.9	18.8
85°	11.2	11.4	11.8	11.6	11.8	11.8	12.2	12.0	12.2	11.8	12.2
87.5°	5.9	6.7	7.3	7.8	8.5	8.8	8.8	9.0	9.3	9.4	9.7
90°	8.7	10.3	12.7	15.1	17.4	19.8	19.0	19.8	20.6	21.4	22.9
92.5°	34.0	45.7	66.4	100.4	133.8	121.6	91.7	66.5	52.8	46.7	42.5
95°	71.9	102.8	170.0	287.8	417.5	468.9	380.3	284.6	193.0	151.1	122.6
97.5°	85.4	118.7	183.0	315.8	532.0	726.7	777.4	709.6	568.4	466.4	371.8
100°	94.9	125.7	181.1	298.1	506.0	748.8	904.6	932.3	868.2	775.7	663.5
102.5°	105.7	134.0	183.6	282.9	468.1	707.7	910.9	1006.3	1004.2	950.3	879.2
105°	123.3	147.9	190.6	272.0	421.4	635.7	862.7	1027.9	1107.1	1122.0	1101.5
107.5°	143.3	166.0	203.5	271.2	391.7	572.2	778.2	965.7	1094.1	1163.3	1191.5
110°	156.5	178.7	214.3	274.4	380.3	536.1	725.1	906.2	1051.7	1151.3	1206.7



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	170.5	192.0	225.1	280.7	374.0	512.1	678.9	847.3	996.0	1107.6	1178.8
115°	191.4	212.7	242.7	291.0	371.6	486.3	623.1	769.4	907.0	1023.2	1109.4
117.5°	212.1	231.9	261.6	304.6	373.0	471.1	589.4	713.0	831.7	936.0	1023.5
120°	225.4	245.1	273.6	314.7	375.6	464.1	571.7	683.2	790.0	884.9	964.7
122.5°	237.4	258.4	286.2	324.2	380.0	459.7	557.1	659.8	756.5	844.4	918.5
125°	255.4	276.8	304.4	339.2	386.7	453.9	538.5	628.7	714.9	790.8	854.0
127.5°	272.2	293.5	320.3	351.6	394.3	451.1	522.0	601.4	678.3	746.8	804.3
130°	282.3	303.6	329.7	359.8	399.3	449.2	513.2	584.4	655.5	719.5	773.3
132.5°	291.8	312.5	337.9	367.4	403.1	448.5	504.9	568.5	634.0	693.6	744.9
135°	304.4	325.7	350.3	377.2	408.8	447.6	494.2	547.2	603.3	654.7	699.8
137.5°	315.5	335.3	358.9	384.4	412.6	445.8	484.9	527.8	573.8	618.1	657.1
140°	321.9	341.6	364.6	388.2	415.1	445.2	479.2	516.3	556.7	594.6	628.7
142.5°	328.1	346.7	369.0	392.1	417.0	443.9	474.1	505.6	540.3	573.1	602.7
145°	336.0	354.3	374.8	396.2	418.3	442.0	467.3	492.7	518.7	544.0	567.0
147.5°	345.2	360.8	379.5	398.7	418.3	439.0	460.7	482.0	502.7	523.2	539.5
150°	350.3	364.6	382.7	399.3	418.3	436.5	456.2	474.4	492.7	509.2	524.3
152.5°	355.4	369.0	384.6	400.6	416.4	433.3	451.2	467.5	483.2	497.9	510.3
155°	363.8	374.8	388.2	400.9	414.3	427.8	443.6	457.0	469.7	481.6	491.1
157.5°	371.0	379.5	390.3	401.7	411.7	422.9	435.1	446.0	456.5	465.7	473.2
160°	374.8	382.7	392.2	401.7	410.4	419.1	429.4	439.7	448.4	456.2	461.8
162.5°	378.0	384.6	392.8	401.1	407.9	415.3	423.7	432.1	439.5	446.8	451.7
165°	381.9	387.5	393.8	399.3	404.1	409.6	415.9	422.2	427.0	432.5	436.5
167.5°	385.6	389.0	393.6	398.1	400.3	403.9	408.5	413.7	417.3	420.5	423.3
170°	387.5	389.0	393.0	396.2	397.8	400.1	404.1	408.1	410.4	413.5	415.1
172.5°	388.7	389.7	393.0	395.5	395.9	397.0	399.7	403.0	404.7	407.3	408.2
175°	389.8	390.6	392.2	393.8	393.0	393.0	394.6	396.2	397.0	398.5	398.5
177.5°	390.6	390.6	391.3	392.5	391.3	390.6	391.3	391.9	392.5	393.2	393.2
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	410.7	410.6	410.7	410.2	410.7	410.6	410.7	412.6	412.6	412.6	412.8
5°	382.2	382.1	381.5	379.9	381.5	382.1	382.2	382.8	384.3	386.8	386.1
7.5°	357.3	357.0	355.5	355.5	355.5	357.0	357.3	358.8	360.4	362.0	363.8
10°	342.5	342.7	340.5	339.2	340.5	342.7	342.5	343.8	346.3	347.5	348.8
12.5°	328.2	327.4	325.6	324.2	325.6	327.4	328.2	329.2	332.5	334.0	336.4
15°	309.3	307.4	303.1	303.4	303.1	307.4	309.3	308.6	311.9	313.8	314.5
17.5°	287.1	285.7	285.7	283.0	285.7	285.7	287.1	288.5	291.4	293.4	298.7
20°	274.1	273.1	273.5	270.9	273.5	273.1	274.1	277.0	278.8	281.5	285.7
22.5°	263.9	262.9	261.4	260.6	261.4	262.9	263.9	265.9	267.9	271.6	273.9
25°	249.0	247.5	246.1	246.9	246.1	247.5	249.0	250.1	253.7	255.4	258.7
27.5°	234.1	233.0	231.5	231.3	231.5	233.0	234.1	235.1	237.2	240.0	244.0
30°	224.6	223.5	222.8	221.8	222.8	223.5	224.6	225.5	227.6	230.5	233.5
32.5°	215.0	214.8	213.5	213.3	213.5	214.8	215.0	216.5	218.6	221.3	223.9
35°	202.5	201.4	201.0	201.1	201.0	201.4	202.5	203.2	205.0	207.6	210.0
37.5°	190.5	189.1	188.4	187.7	188.4	189.1	190.5	190.7	192.5	194.2	197.5
40°	182.0	180.5	180.1	179.7	180.1	180.5	182.0	181.8	183.8	185.1	188.1
42.5°	172.4	171.8	171.6	170.9	171.6	171.8	172.4	173.4	174.5	176.4	178.6
45°	159.3	159.1	158.0	158.4	158.0	159.1	159.3	159.9	161.8	163.2	165.2
47.5°	145.4	144.7	143.9	144.4	143.9	144.7	145.4	146.2	147.6	149.2	151.9
50°	136.0	135.6	134.0	134.4	134.0	135.6	136.0	136.7	137.7	139.7	142.1
52.5°	126.6	125.2	124.5	124.3	124.5	125.2	126.6	127.3	128.4	130.7	132.5
55°	110.9	109.2	108.5	108.1	108.5	109.2	110.9	112.3	113.7	116.3	118.1
57.5°	95.5	95.1	94.5	94.9	94.5	95.1	95.5	97.7	99.2	101.2	103.5
60°	86.6	86.6	86.6	86.3	86.6	86.6	86.6	88.4	89.7	91.7	94.1
62.5°	79.6	79.1	79.1	79.3	79.1	79.1	79.6	80.4	81.8	83.0	85.2
65°	69.0	68.8	68.1	67.9	68.1	68.8	69.0	69.6	70.7	71.6	73.1
67.5°	59.0	58.4	58.1	57.9	58.1	58.4	59.0	59.5	60.2	61.4	62.2
70°	51.5	51.1	50.0	50.2	50.0	51.1	51.5	52.4	53.2	54.7	55.4
72.5°	43.4	43.0	42.8	42.5	42.8	43.0	43.4	44.3	45.0	46.7	47.8
75°	34.3	34.1	34.0	34.7	34.0	34.1	34.3	34.5	34.7	35.3	35.8
77.5°	27.5	27.5	27.6	27.3	27.6	27.5	27.5	27.5	27.5	27.8	27.9
80°	23.1	23.1	22.9	22.9	22.9	23.1	23.1	23.1	23.1	23.1	22.9
82.5°	18.5	18.6	18.8	18.5	18.8	18.6	18.5	18.8	18.9	18.6	18.8
85°	12.2	12.0	12.4	12.2	12.4	12.0	12.2	12.2	11.8	12.2	12.0
87.5°	9.9	9.7	9.9	9.9	9.9	9.7	9.9	9.7	9.4	9.3	9.0
90°	22.1	22.9	23.7	22.9	23.7	22.9	22.1	22.9	21.4	20.6	19.8
92.5°	41.1	38.7	39.5	38.1	39.5	38.7	41.1	42.5	46.7	52.8	66.5
95°	107.6	100.4	94.9	91.7	94.9	100.4	107.6	122.6	151.1	193.0	284.6
97.5°	313.5	277.9	256.5	249.7	256.5	277.9	313.5	371.8	466.4	568.4	709.6
100°	583.6	525.9	495.0	495.8	495.0	525.9	583.6	663.5	775.7	868.2	932.3
102.5°	817.0	771.3	745.5	727.3	745.5	771.3	817.0	879.2	950.3	1004.2	1006.3
105°	1065.1	1035.1	1009.8	1005.8	1009.8	1035.1	1065.1	1101.5	1122.0	1107.1	1027.9
107.5°	1192.2	1182.0	1173.5	1166.2	1173.5	1182.0	1192.2	1191.5	1163.3	1094.1	965.7
110°	1228.8	1235.2	1233.6	1232.0	1233.6	1235.2	1228.8	1206.7	1151.3	1051.7	906.2



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1219.3	1238.9	1244.9	1245.2	1244.9	1238.9	1219.3	1178.8	1107.6	996.0	847.3
115°	1168.7	1203.5	1219.3	1223.3	1219.3	1203.5	1168.7	1109.4	1023.2	907.0	769.4
117.5°	1085.4	1125.2	1148.0	1153.3	1148.0	1125.2	1085.4	1023.5	936.0	831.7	713.0
120°	1027.1	1071.4	1090.4	1095.2	1090.4	1071.4	1027.1	964.7	884.9	790.0	683.2
122.5°	974.1	1013.9	1034.7	1040.8	1034.7	1013.9	974.1	918.5	844.4	756.5	659.8
125°	904.6	939.4	959.2	964.7	959.2	939.4	904.6	854.0	790.8	714.9	628.7
127.5°	849.4	879.2	897.0	902.1	897.0	879.2	849.4	804.3	746.8	678.3	601.4
130°	815.2	843.8	860.3	866.6	860.3	843.8	815.2	773.3	719.5	655.5	584.4
132.5°	784.3	812.7	827.4	831.9	827.4	812.7	784.3	744.9	693.6	634.0	568.5
135°	738.6	762.2	776.5	782.0	776.5	762.2	738.6	699.8	654.7	603.3	547.2
137.5°	689.7	713.8	725.7	729.4	725.7	713.8	689.7	657.1	618.1	573.8	527.8
140°	658.7	680.8	693.5	692.7	693.5	680.8	658.7	628.7	594.6	556.7	516.3
142.5°	628.4	647.9	659.3	658.5	659.3	647.9	628.4	602.7	573.1	540.3	505.6
145°	586.7	603.3	609.7	611.2	609.7	603.3	586.7	567.0	544.0	518.7	492.7
147.5°	554.4	565.7	571.7	572.4	571.7	565.7	554.4	539.5	523.2	502.7	482.0
150°	536.1	544.8	549.5	549.5	549.5	544.8	536.1	524.3	509.2	492.7	474.4
152.5°	519.7	527.8	530.6	530.6	530.6	527.8	519.7	510.3	497.9	483.2	467.5
155°	498.2	504.5	506.0	506.8	506.0	504.5	498.2	491.1	481.6	469.7	457.0
157.5°	479.3	484.1	485.4	485.2	485.4	484.1	479.3	473.2	465.7	456.5	446.0
160°	467.3	472.1	472.1	471.3	472.1	472.1	467.3	461.8	456.2	448.4	439.7
162.5°	455.3	459.4	459.4	458.6	459.4	459.4	455.3	451.7	446.8	439.5	432.1
165°	439.7	442.8	442.0	442.0	442.0	442.8	439.7	436.5	432.5	427.0	422.2
167.5°	424.8	427.0	426.2	426.2	426.2	427.0	424.8	423.3	420.5	417.3	413.7
170°	415.9	417.5	416.7	416.7	416.7	417.5	415.9	415.1	413.5	410.4	408.1
172.5°	408.4	410.0	408.5	407.9	408.5	410.0	408.4	408.2	407.3	404.7	403.0
175°	398.5	399.3	398.5	397.8	398.5	399.3	398.5	398.5	398.5	397.0	396.2
177.5°	392.5	393.2	391.9	391.9	391.9	393.2	392.5	393.2	393.2	392.5	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	411.5	413.6	415.7	417.6	420.5	421.8	423.7	424.5	426.7	429.9	432.6
5°	386.5	389.4	393.3	396.4	401.4	405.3	409.6	413.6	418.4	425.2	431.3
7.5°	365.3	368.1	372.8	378.7	384.1	389.7	395.5	401.0	407.8	417.6	427.3
10°	351.3	354.7	360.3	366.5	373.4	378.7	385.6	392.5	401.1	412.3	424.0
12.5°	339.1	341.7	348.2	354.1	361.9	368.7	375.3	383.6	393.2	405.2	419.2
15°	319.9	323.5	329.8	336.4	344.6	351.8	360.4	370.4	379.9	394.6	411.5
17.5°	300.5	306.1	312.7	320.1	326.1	336.1	345.5	355.7	367.3	382.9	401.6
20°	288.1	292.6	298.7	309.5	317.4	325.0	333.7	346.4	357.1	374.9	394.2
22.5°	277.6	280.8	287.7	296.7	305.9	314.7	323.5	335.6	348.9	365.7	386.7
25°	262.1	267.3	272.4	278.8	288.8	299.4	309.0	319.3	333.4	351.3	373.9
27.5°	246.9	251.6	256.7	264.6	272.2	282.0	292.1	303.9	318.9	337.9	360.9
30°	237.2	240.7	245.5	255.6	262.4	270.9	282.7	293.3	307.3	327.4	351.8
32.5°	227.1	231.6	236.9	244.7	253.2	261.2	272.0	283.4	297.7	317.5	342.5
35°	212.8	218.2	223.5	229.3	237.7	246.1	255.1	267.6	282.2	301.4	325.9
37.5°	199.6	203.9	208.3	215.4	223.4	231.3	239.8	252.2	265.9	286.6	309.1
40°	191.2	195.1	198.4	205.8	213.6	222.0	230.4	241.2	256.0	275.4	297.1
42.5°	182.0	185.6	190.1	196.2	204.5	211.7	220.0	230.3	244.2	263.9	283.0
45°	168.3	172.4	176.3	182.0	190.3	197.3	204.7	214.4	228.7	244.9	261.9
47.5°	154.0	158.1	162.6	168.1	175.3	182.4	189.8	198.4	211.4	227.4	238.8
50°	144.9	148.2	152.7	158.2	164.9	172.4	179.0	188.5	200.8	213.3	223.3
52.5°	135.5	138.5	143.5	149.3	155.5	162.1	169.1	177.2	188.4	200.2	208.1
55°	120.7	124.4	128.7	134.4	140.5	146.0	152.8	161.1	170.0	178.9	184.2
57.5°	106.9	110.0	113.6	119.5	124.8	131.3	137.5	143.9	152.2	158.8	162.3
60°	96.9	99.7	104.3	109.5	114.4	120.2	127.1	133.6	139.9	145.3	148.0
62.5°	87.5	90.6	94.7	99.4	104.8	110.3	116.4	121.8	127.4	132.0	133.9
65°	75.1	77.7	80.6	85.1	89.5	95.1	99.8	105.4	109.5	112.0	113.7
67.5°	63.9	65.6	67.8	70.8	75.2	80.0	84.6	89.0	92.4	94.1	95.6
70°	56.6	57.8	59.4	62.3	65.7	69.9	74.8	77.9	80.8	82.3	83.8
72.5°	49.4	50.9	52.4	54.7	57.4	60.5	64.0	67.8	69.5	71.2	72.1
75°	37.5	39.5	41.5	43.0	44.8	47.2	50.4	52.8	53.7	55.2	55.4
77.5°	28.3	28.8	30.2	32.0	33.6	35.3	37.3	39.5	39.9	40.6	41.2
80°	23.3	23.3	23.3	24.4	26.2	27.5	29.3	30.4	31.2	31.4	31.5
82.5°	18.7	18.7	18.5	18.8	19.4	20.1	21.8	23.1	23.7	23.5	23.1
85°	12.2	11.8	11.8	11.6	11.8	11.4	11.2	12.0	13.1	13.1	12.8
87.5°	8.8	8.8	8.5	7.8	7.3	6.7	5.9	5.7	5.2	5.5	5.1
90°	19.0	19.8	17.4	15.1	12.7	10.3	8.7	7.1	4.8	3.2	1.6
92.5°	91.7	121.6	133.8	100.4	66.4	45.7	34.0	27.3	21.2	14.6	9.8
95°	380.3	468.9	417.5	287.8	170.0	102.8	71.9	51.4	37.9	29.2	26.9
97.5°	777.4	726.7	532.0	315.8	183.0	118.7	85.4	65.1	53.5	46.7	45.9
100°	904.6	748.8	506.0	298.1	181.1	125.7	94.9	75.9	64.9	59.3	58.5
102.5°	910.9	707.7	468.1	282.9	183.6	134.0	105.7	88.6	78.1	73.2	71.8
105°	862.7	635.7	421.4	272.0	190.6	147.9	123.3	108.4	98.9	94.1	91.7
107.5°	778.2	572.2	391.7	271.2	203.5	166.0	143.3	129.2	119.9	115.3	112.9
110°	725.1	536.1	380.3	274.4	214.3	178.7	156.5	143.1	134.4	130.5	128.1



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	678.9	512.1	374.0	280.7	225.1	192.0	170.5	157.0	148.4	144.4	142.0
115°	623.1	486.3	371.6	291.0	242.7	212.7	191.4	177.9	170.0	165.2	162.1
117.5°	589.4	471.1	373.0	304.6	261.6	231.9	212.1	197.0	189.8	185.8	182.2
120°	571.7	464.1	375.6	314.7	273.6	245.1	225.4	210.3	202.4	198.4	196.1
122.5°	557.1	459.7	380.0	324.2	286.2	258.4	237.4	223.0	214.4	210.5	208.1
125°	538.5	453.9	386.7	339.2	304.4	276.8	255.4	240.3	231.7	227.0	225.4
127.5°	522.0	451.1	394.3	351.6	320.3	293.5	272.2	255.6	246.7	240.8	238.5
130°	513.2	449.2	399.3	359.8	329.7	303.6	282.3	265.7	256.2	249.1	246.7
132.5°	504.9	448.5	403.1	367.4	337.9	312.5	291.8	275.2	263.8	256.0	253.0
135°	494.2	447.6	408.8	377.2	350.3	325.7	304.4	287.8	276.0	267.3	264.1
137.5°	484.9	445.8	412.6	384.4	358.9	335.3	315.5	299.0	286.4	277.9	274.6
140°	479.2	445.2	415.1	388.2	364.6	341.6	321.9	306.0	293.3	285.4	281.5
142.5°	474.1	443.9	417.0	392.1	369.0	346.7	328.1	312.4	301.0	292.4	289.1
145°	467.3	442.0	418.3	396.2	374.8	354.3	336.0	322.7	310.8	303.6	301.3
147.5°	460.7	439.0	418.3	398.7	379.5	360.8	345.2	332.2	322.0	315.1	313.6
150°	456.2	436.5	418.3	399.3	382.7	364.6	350.3	339.2	328.9	322.7	321.9
152.5°	451.2	433.3	416.4	400.6	384.6	369.0	355.4	345.5	336.5	330.2	330.0
155°	443.6	427.8	414.3	400.9	388.2	374.8	363.8	355.1	347.1	342.4	342.4
157.5°	435.1	422.9	411.7	401.7	390.3	379.5	371.0	363.6	356.6	352.8	352.2
160°	429.4	419.1	410.4	401.7	392.2	382.7	374.8	369.2	363.0	359.8	359.8
162.5°	423.7	415.3	407.9	401.1	392.8	384.6	378.0	373.0	368.0	365.5	365.5
165°	415.9	409.6	404.1	399.3	393.8	387.5	381.9	378.7	374.8	373.2	374.0
167.5°	408.5	403.9	400.3	398.1	393.6	389.0	385.6	383.3	380.3	379.5	380.5
170°	404.1	400.1	397.8	396.2	393.0	389.0	387.5	385.9	383.5	382.7	384.3
172.5°	399.7	397.0	395.9	395.5	393.0	389.7	388.7	387.8	386.0	385.9	386.8
175°	394.6	393.0	393.0	393.8	392.2	390.6	389.8	389.8	388.2	389.0	389.8
177.5°	391.3	390.6	391.3	392.5	391.3	390.6	390.6	390.6	390.0	390.6	391.3
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	433.5	435.1	437.2	440.3	442.7	444.7	445.1	445.8	447.3	449.7	451.6
5°	436.3	440.5	447.3	454.0	461.2	467.1	472.7	476.6	480.2	488.0	494.2
7.5°	435.4	444.9	455.6	467.5	479.6	491.2	502.1	511.8	521.5	532.8	545.7
10°	434.8	445.9	460.3	475.6	492.4	508.8	524.7	537.1	551.4	564.4	580.8
12.5°	432.1	448.0	465.2	484.7	505.4	524.3	545.3	562.3	578.8	597.5	616.6
15°	428.3	447.7	469.5	495.5	527.0	549.8	571.2	600.9	621.2	641.5	668.8
17.5°	421.7	445.4	472.5	506.4	532.5	563.3	595.5	619.0	646.3	674.9	699.7
20°	416.4	443.9	474.4	507.6	541.0	574.3	605.5	633.6	661.9	694.9	715.2
22.5°	411.1	438.2	469.9	505.2	541.1	576.3	611.6	644.5	676.3	709.6	735.5
25°	399.7	432.1	466.4	502.4	537.8	576.6	618.6	655.4	694.7	729.0	753.6
27.5°	388.3	418.0	452.1	488.6	528.0	573.8	623.3	665.0	704.4	729.0	736.7
30°	378.0	409.3	440.8	477.8	520.5	571.6	624.2	672.0	704.3	715.0	707.0
32.5°	367.5	395.9	427.0	465.0	510.2	566.1	625.3	667.9	687.3	679.1	646.8
35°	349.0	374.6	404.7	442.8	494.8	563.1	620.5	649.3	644.5	598.3	537.4
37.5°	329.2	350.1	378.0	417.7	478.8	551.1	599.5	603.8	562.2	491.4	421.0
40°	313.5	332.4	361.0	402.5	466.4	539.3	578.5	561.3	496.9	418.0	359.3
42.5°	298.3	314.3	341.8	386.6	454.6	523.2	547.0	509.6	435.3	360.8	307.4
45°	272.6	287.6	315.2	361.2	430.4	492.4	489.3	424.3	349.9	289.9	245.7
47.5°	248.2	261.3	287.2	334.1	402.0	446.2	416.9	347.8	284.7	236.5	204.9
50°	230.9	243.8	269.7	316.0	379.3	411.5	369.7	303.1	245.3	205.4	180.3
52.5°	214.4	227.0	250.6	295.7	351.8	371.1	326.1	264.4	216.2	181.8	160.3
55°	191.2	200.8	222.0	265.2	307.1	311.6	265.9	214.3	174.6	150.6	135.9
57.5°	167.6	175.9	196.9	231.2	260.6	258.3	215.2	170.4	143.7	125.9	115.2
60°	152.3	160.4	178.9	208.3	230.5	222.8	183.1	147.1	124.2	111.1	102.6
62.5°	137.9	144.3	161.6	183.2	199.1	190.3	156.5	126.7	108.5	97.5	90.8
65°	117.2	122.4	136.2	147.5	156.3	147.8	119.8	99.1	86.0	78.3	73.7
67.5°	97.5	100.8	109.5	113.6	119.9	110.5	90.1	76.2	68.8	62.3	59.0
70°	85.1	87.5	92.1	95.5	97.0	87.5	72.3	62.2	55.9	51.3	49.3
72.5°	72.6	74.8	75.7	78.4	77.6	68.6	58.1	50.1	45.6	42.5	39.8
75°	55.5	56.5	55.5	54.4	52.0	45.8	38.6	34.5	31.2	29.7	28.8
77.5°	40.5	40.2	39.0	37.2	33.1	29.2	25.3	23.9	22.5	21.7	21.4
80°	31.2	30.4	29.3	26.5	23.1	20.3	19.4	18.5	17.9	17.0	16.8
82.5°	23.2	22.7	20.9	18.6	16.2	14.8	14.1	13.7	13.2	12.7	12.7
85°	12.4	11.8	9.7	8.5	8.2	7.8	7.6	7.6	6.8	6.7	6.7
87.5°	4.6	4.0	4.4	4.3	4.6	4.8	5.4	5.5	5.9	5.9	5.7
90°	3.2	4.8	7.1	8.7	10.3	12.7	15.1	17.4	19.8	19.0	19.8
92.5°	14.6	21.2	27.3	34.0	45.7	66.4	100.4	133.8	121.6	91.7	66.5
95°	29.2	37.9	51.4	71.9	102.8	170.0	287.8	417.5	468.9	380.3	284.6
97.5°	46.7	53.5	65.1	85.4	118.7	183.0	315.8	532.0	726.7	777.4	709.6
100°	59.3	64.9	75.9	94.9	125.7	181.1	298.1	506.0	748.8	904.6	932.3
102.5°	73.2	78.1	88.6	105.7	134.0	183.6	282.9	468.1	707.7	910.9	1006.3
105°	94.1	98.9	108.4	123.3	147.9	190.6	272.0	421.4	635.7	862.7	1027.9
107.5°	115.3	119.9	129.2	143.3	166.0	203.5	271.2	391.7	572.2	778.2	965.7
110°	130.5	134.4	143.1	156.5	178.7	214.3	274.4	380.3	536.1	725.1	906.2





TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.4	148.4	157.0	170.5	192.0	225.1	280.7	374.0	512.1	678.9	847.3
115°	165.2	170.0	177.9	191.4	212.7	242.7	291.0	371.6	486.3	623.1	769.4
117.5°	185.8	189.8	197.0	212.1	231.9	261.6	304.6	373.0	471.1	589.4	713.0
120°	198.4	202.4	210.3	225.4	245.1	273.6	314.7	375.6	464.1	571.7	683.2
122.5°	210.5	214.4	223.0	237.4	258.4	286.2	324.2	380.0	459.7	557.1	659.8
125°	227.0	231.7	240.3	255.4	276.8	304.4	339.2	386.7	453.9	538.5	628.7
127.5°	240.8	246.7	255.6	272.2	293.5	320.3	351.6	394.3	451.1	522.0	601.4
130°	249.1	256.2	265.7	282.3	303.6	329.7	359.8	399.3	449.2	513.2	584.4
132.5°	256.0	263.8	275.2	291.8	312.5	337.9	367.4	403.1	448.5	504.9	568.5
135°	267.3	276.0	287.8	304.4	325.7	350.3	377.2	408.8	447.6	494.2	547.2
137.5°	277.9	286.4	299.0	315.5	335.3	358.9	384.4	412.6	445.8	484.9	527.8
140°	285.4	293.3	306.0	321.9	341.6	364.6	388.2	415.1	445.2	479.2	516.3
142.5°	292.4	301.0	312.4	328.1	346.7	369.0	392.1	417.0	443.9	474.1	505.6
145°	303.6	310.8	322.7	336.0	354.3	374.8	396.2	418.3	442.0	467.3	492.7
147.5°	315.1	322.0	332.2	345.2	360.8	379.5	398.7	418.3	439.0	460.7	482.0
150°	322.7	328.9	339.2	350.3	364.6	382.7	399.3	418.3	436.5	456.2	474.4
152.5°	330.2	336.5	345.5	355.4	369.0	384.6	400.6	416.4	433.3	451.2	467.5
155°	342.4	347.1	355.1	363.8	374.8	388.2	400.9	414.3	427.8	443.6	457.0
157.5°	352.8	356.6	363.6	371.0	379.5	390.3	401.7	411.7	422.9	435.1	446.0
160°	359.8	363.0	369.2	374.8	382.7	392.2	401.7	410.4	419.1	429.4	439.7
162.5°	365.5	368.0	373.0	378.0	384.6	392.8	401.1	407.9	415.3	423.7	432.1
165°	373.2	374.8	378.7	381.9	387.5	393.8	399.3	404.1	409.6	415.9	422.2
167.5°	379.5	380.3	383.3	385.6	389.0	393.6	398.1	400.3	403.9	408.5	413.7
170°	382.7	383.5	385.9	387.5	389.0	393.0	396.2	397.8	400.1	404.1	408.1
172.5°	385.9	386.0	387.8	388.7	389.7	393.0	395.5	395.9	397.0	399.7	403.0
175°	389.0	388.2	389.8	389.8	390.6	392.2	393.8	393.0	393.0	394.6	396.2
177.5°	390.6	390.0	390.6	390.6	390.6	391.3	392.5	391.3	390.6	391.3	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6	390.6



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	454.8	454.8	455.3	457.6	457.9	459.8	459.2
5°	499.8	503.3	504.6	510.2	513.4	514.9	512.0
7.5°	554.8	564.7	569.4	575.3	580.4	581.9	577.9
10°	595.0	605.4	614.0	619.4	624.4	627.7	631.9
12.5°	633.8	646.6	654.8	662.3	667.5	671.7	672.4
15°	676.0	695.2	709.8	720.6	725.9	728.6	727.5
17.5°	718.6	736.4	746.8	757.7	765.1	765.5	765.7
20°	742.7	760.0	772.1	780.1	788.5	788.1	790.0
22.5°	758.8	772.5	781.6	787.5	790.4	788.9	789.3
25°	766.3	770.4	768.7	759.3	756.9	748.2	749.7
27.5°	727.5	708.3	688.4	662.9	642.7	626.6	627.4
30°	674.8	640.8	602.1	569.6	540.4	532.3	514.9
32.5°	601.1	550.2	504.8	474.4	449.5	442.7	427.5
35°	476.2	426.7	380.0	352.0	340.9	325.3	325.2
37.5°	370.1	326.5	301.9	280.8	269.8	260.4	259.5
40°	311.3	277.4	258.7	243.6	232.7	225.7	224.0
42.5°	270.3	242.9	225.4	216.0	207.6	204.0	201.3
45°	220.7	202.2	190.1	181.6	177.8	175.0	173.5
47.5°	184.7	172.3	164.0	158.3	155.2	152.3	153.0
50°	165.0	154.9	148.8	143.4	141.0	138.9	139.2
52.5°	149.2	140.1	135.1	131.3	128.3	126.8	126.2
55°	126.6	120.9	115.9	113.1	111.5	109.5	108.9
57.5°	108.0	103.5	99.5	96.4	95.9	94.0	94.3
60°	95.6	91.9	88.6	86.9	85.6	84.0	84.5
62.5°	85.4	82.3	79.3	78.0	76.6	75.4	75.7
65°	69.9	67.0	65.1	64.4	63.8	63.3	62.7
67.5°	55.8	53.9	52.8	51.2	50.1	49.9	49.4
70°	46.9	44.4	42.5	40.4	39.8	39.7	39.8
72.5°	37.5	36.0	35.5	34.5	34.4	33.9	34.2
75°	28.2	27.6	27.3	26.5	26.5	26.5	26.5
77.5°	20.8	20.5	20.3	20.1	20.0	19.6	19.6
80°	16.2	16.1	15.7	15.7	15.5	15.7	15.5
82.5°	12.3	12.2	11.9	11.9	11.6	11.6	11.6
85°	6.3	6.1	6.5	6.1	6.3	5.9	6.3
87.5°	5.9	6.0	6.2	6.0	6.1	6.5	6.1
90°	20.6	21.4	22.9	22.1	22.9	23.7	22.9
92.5°	52.8	46.7	42.5	41.1	38.7	39.5	38.1
95°	193.0	151.1	122.6	107.6	100.4	94.9	91.7
97.5°	568.4	466.4	371.8	313.5	277.9	256.5	249.7
100°	868.2	775.7	663.5	583.6	525.9	495.0	495.8
102.5°	1004.2	950.3	879.2	817.0	771.3	745.5	727.3
105°	1107.1	1122.0	1101.5	1065.1	1035.1	1009.8	1005.8
107.5°	1094.1	1163.3	1191.5	1192.2	1182.0	1173.5	1166.2
110°	1051.7	1151.3	1206.7	1228.8	1235.2	1233.6	1232.0



TEST NUMBER: P332260-927

CATALOG NUMBER: S123RDIP-S340D1025U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	996.0	1107.6	1178.8	1219.3	1238.9	1244.9	1245.2
115°	907.0	1023.2	1109.4	1168.7	1203.5	1219.3	1223.3
117.5°	831.7	936.0	1023.5	1085.4	1125.2	1148.0	1153.3
120°	790.0	884.9	964.7	1027.1	1071.4	1090.4	1095.2
122.5°	756.5	844.4	918.5	974.1	1013.9	1034.7	1040.8
125°	714.9	790.8	854.0	904.6	939.4	959.2	964.7
127.5°	678.3	746.8	804.3	849.4	879.2	897.0	902.1
130°	655.5	719.5	773.3	815.2	843.8	860.3	866.6
132.5°	634.0	693.6	744.9	784.3	812.7	827.4	831.9
135°	603.3	654.7	699.8	738.6	762.2	776.5	782.0
137.5°	573.8	618.1	657.1	689.7	713.8	725.7	729.4
140°	556.7	594.6	628.7	658.7	680.8	693.5	692.7
142.5°	540.3	573.1	602.7	628.4	647.9	659.3	658.5
145°	518.7	544.0	567.0	586.7	603.3	609.7	611.2
147.5°	502.7	523.2	539.5	554.4	565.7	571.7	572.4
150°	492.7	509.2	524.3	536.1	544.8	549.5	549.5
152.5°	483.2	497.9	510.3	519.7	527.8	530.6	530.6
155°	469.7	481.6	491.1	498.2	504.5	506.0	506.8
157.5°	456.5	465.7	473.2	479.3	484.1	485.4	485.2
160°	448.4	456.2	461.8	467.3	472.1	472.1	471.3
162.5°	439.5	446.8	451.7	455.3	459.4	459.4	458.6
165°	427.0	432.5	436.5	439.7	442.8	442.0	442.0
167.5°	417.3	420.5	423.3	424.8	427.0	426.2	426.2
170°	410.4	413.5	415.1	415.9	417.5	416.7	416.7
172.5°	404.7	407.3	408.2	408.4	410.0	408.5	407.9
175°	397.0	398.5	398.5	398.5	399.3	398.5	397.8
177.5°	392.5	393.2	393.2	392.5	393.2	391.9	391.9
180°	390.6	390.6	390.6	390.6	390.6	390.6	390.6

(END OF REPORT)