

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332272-927

Luminaire Tested: **S123RDIP-S560D365U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332272-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D365U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2806.3 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	97	94	90	95	91	88	85	81	78	76	71	69	67	61	60	59	54
2	93	86	80	75	87	81	76	71	71	68	64	63	60	57	55	53	51	47
3	85	76	69	63	80	72	66	60	64	59	55	56	52	49	49	46	44	41
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	44	41	39	35
5	72	61	53	47	68	58	51	45	51	46	41	46	41	38	40	37	34	31
6	67	55	47	41	63	52	45	40	47	41	37	42	37	33	37	33	30	28
7	62	50	42	37	58	47	40	35	43	37	32	38	33	30	34	30	27	25
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	31	27	25	22
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20
10	50	38	31	27	47	37	30	26	33	28	24	30	25	22	27	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7629	7629	7629	7629
5°	9095	7662	6748	7662
10°	11355	7618	6096	7618
15°	13329	7540	5558	7540
20°	14875	7424	5102	7424
25°	14638	7301	4822	7301
30°	10521	7188	4533	7188
35°	7025	7041	4346	7041
40°	5176	6864	4154	6864
45°	4341	6555	3962	6555
50°	3831	6149	3699	6149
55°	3359	5684	3337	5684
60°	2990	5240	3057	5240
65°	2626	4760	2845	4760
70°	2061	4337	2596	4337
75°	1817	3785	2371	3785
80°	1581	3217	2331	3217
85°	1272	2581	2470	2581



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.7	2.5
10°-20°	217.8	7.8
20°-30°	342.1	12.2
30°-40°	356.9	12.7
40°-50°	305.5	10.9
50°-60°	232.8	8.3
60°-70°	149.2	5.3
70°-80°	71.8	2.6
80°-90°	20.1	0.7
90°-100°	77.0	2.7
100°-110°	217.9	7.8
110°-120°	214.4	7.6
120°-130°	171.0	6.1
130°-140°	134.8	4.8
140°-150°	100.6	3.6
150°-160°	70.1	2.5
160°-170°	41.2	1.5
170°-180°	13.4	0.5
0°-30°	629.6	22.4
0°-40°	986.5	35.2
0°-60°	1524.8	54.3
0°-90°	1765.8	62.9
90°-120°	509.3	18.1
90°-150°	915.7	32.6
90°-180°	1040.0	37.1
0°-180°	2806.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	709	709	709	709	709	
5°	842	709	624	709	842	87
15°	1196	677	499	677	1196	339
25°	1232	615	406	615	1232	530
35°	535	536	331	536	535	351
45°	285	431	260	431	285	224
55°	179	303	178	303	179	162
65°	103	187	112	187	103	101
75°	44	91	57	91	44	47
85°	10	21	20	21	10	12
90°	8	1	8	1	8	5
95°	32	10	32	10	32	59
105°	356	32	356	32	356	351
115°	433	57	433	57	433	421
125°	342	80	342	80	342	309
135°	277	94	277	94	277	215
145°	216	107	216	107	216	138
155°	179	121	179	121	179	84
165°	156	132	156	132	156	45
175°	141	138	141	138	141	14
180°	138	138	138	138	138	



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	754.9	755.9	752.7	752.3	748.6	747.7	747.7	742.5	739.3	735.2	732.8
5°	841.7	846.5	844.1	838.7	829.6	827.4	821.7	812.5	802.2	789.5	783.5
7.5°	950.1	956.7	954.1	945.7	936.2	928.4	912.2	897.1	875.9	857.4	841.5
10°	1038.9	1031.9	1026.5	1018.3	1009.5	995.2	978.3	954.9	927.9	906.7	883.0
12.5°	1105.4	1104.3	1097.3	1088.9	1076.5	1063.0	1042.0	1013.6	982.2	951.5	924.5
15°	1196.1	1197.9	1193.3	1184.6	1167.0	1143.0	1111.4	1099.6	1054.7	1021.3	987.9
17.5°	1258.9	1258.5	1257.8	1245.6	1227.7	1210.6	1181.4	1150.2	1109.6	1062.6	1017.6
20°	1298.6	1295.6	1296.2	1282.5	1269.2	1249.5	1221.0	1175.8	1142.4	1088.1	1041.6
22.5°	1297.7	1297.0	1299.3	1294.7	1285.0	1269.9	1247.4	1209.3	1166.6	1111.8	1059.6
25°	1232.5	1230.1	1244.4	1248.2	1263.8	1266.5	1259.8	1238.9	1198.5	1142.1	1077.4
27.5°	1031.5	1030.2	1056.6	1089.7	1131.8	1164.4	1196.0	1211.2	1198.5	1158.1	1093.4
30°	846.5	875.0	888.4	936.4	989.8	1053.4	1109.3	1162.4	1175.4	1157.9	1104.8
32.5°	702.8	727.7	738.9	780.1	829.8	904.4	988.2	1063.3	1116.5	1130.0	1098.0
35°	534.6	535.0	560.4	578.6	624.7	701.5	782.8	883.5	983.7	1059.5	1067.5
37.5°	426.6	428.1	443.5	461.7	496.3	536.9	608.5	692.2	807.9	924.3	992.6
40°	368.4	371.1	382.6	400.5	425.4	456.1	511.9	590.7	687.2	816.8	922.7
42.5°	331.0	335.4	341.4	355.1	370.5	399.3	444.4	505.3	593.0	715.6	837.7
45°	285.2	287.6	292.2	298.6	312.5	332.6	362.9	403.9	476.7	575.3	697.6
47.5°	251.6	250.3	255.1	260.3	269.6	283.2	303.6	337.0	389.0	468.0	571.8
50°	228.8	228.5	231.8	235.8	244.5	254.6	271.2	296.4	337.7	403.2	498.2
52.5°	207.4	208.6	211.0	215.9	222.2	230.3	245.3	263.4	298.9	355.5	434.6
55°	179.0	179.9	183.2	186.0	190.5	198.8	208.2	223.3	247.6	287.0	352.3
57.5°	155.0	154.6	157.8	158.4	163.6	170.2	177.5	189.3	206.9	236.2	280.2
60°	138.9	138.1	140.8	142.9	145.6	151.1	157.2	168.7	182.7	204.2	241.9
62.5°	124.4	124.0	126.0	128.1	130.3	135.3	140.5	149.2	160.3	178.5	208.3
65°	103.1	104.1	105.0	105.9	107.1	110.1	115.0	121.0	128.7	141.4	163.0
67.5°	81.0	82.0	82.3	84.1	86.7	88.6	91.7	97.0	102.3	113.0	125.3
70°	65.5	65.2	65.5	66.5	69.8	73.1	77.1	81.0	84.4	92.0	102.3
72.5°	56.3	55.8	56.6	56.7	58.4	59.3	61.8	65.5	69.8	74.9	82.4
75°	43.7	43.7	43.7	43.7	44.9	45.6	46.4	47.4	48.9	51.3	56.7
77.5°	32.3	32.3	32.8	33.0	33.4	33.7	34.2	35.2	35.6	37.0	39.3
80°	25.5	25.8	25.5	25.8	25.8	26.4	26.7	27.6	27.9	29.5	30.3
82.5°	19.2	19.0	19.2	19.5	19.5	20.1	20.1	20.8	20.9	21.6	22.6
85°	10.3	9.7	10.3	10.0	10.6	10.0	10.3	10.9	10.9	11.2	12.4
87.5°	4.0	4.6	4.0	4.2	4.3	4.4	4.4	4.3	4.8	4.6	4.6
90°	8.1	8.4	8.1	7.8	8.1	7.5	7.3	7.0	6.7	7.0	6.2
92.5°	13.5	14.0	13.7	14.6	15.1	16.5	18.7	23.6	32.5	43.0	47.4
95°	32.5	33.6	35.6	38.1	43.4	53.5	68.3	100.8	134.7	166.0	147.8
97.5°	88.4	90.8	98.4	111.0	131.7	165.1	201.2	251.2	275.2	257.3	188.4
100°	175.5	175.2	186.2	206.6	234.9	274.6	307.4	330.0	320.3	265.1	179.2
102.5°	257.5	264.0	273.1	289.2	311.2	336.4	355.5	356.2	322.5	250.6	165.7
105°	356.1	357.5	366.5	377.1	390.0	397.2	391.9	363.9	305.4	225.1	149.2
107.5°	412.9	415.4	418.4	422.1	421.8	411.9	387.3	341.8	275.5	202.6	138.7
110°	436.2	436.7	437.3	435.1	427.2	407.6	372.3	320.8	256.7	189.8	134.7



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	440.8	440.8	438.6	431.7	417.3	392.1	352.6	300.0	240.3	181.3	132.4
115°	433.1	431.7	426.0	413.8	392.8	362.3	321.1	272.4	220.6	172.1	131.6
117.5°	408.3	406.4	398.4	384.3	362.3	331.4	294.5	252.4	208.7	166.8	132.1
120°	387.7	386.0	379.3	363.6	341.5	313.2	279.6	241.9	202.4	164.3	133.0
122.5°	368.4	366.3	358.9	344.8	325.2	298.9	267.8	233.6	197.3	162.8	134.5
125°	341.5	339.6	332.6	320.3	302.4	280.0	253.1	222.5	190.7	160.7	136.9
127.5°	319.3	317.6	311.2	300.7	284.8	264.4	240.1	212.9	184.8	159.7	139.6
130°	306.8	304.6	298.7	288.6	273.8	254.8	232.1	206.8	181.6	159.0	141.4
132.5°	294.5	292.9	287.7	277.7	263.7	245.6	224.4	201.3	178.8	158.8	142.8
135°	276.9	274.9	269.9	261.5	247.7	231.8	213.6	193.7	175.0	158.4	144.7
137.5°	258.3	256.9	252.7	244.2	232.7	218.8	203.1	186.8	171.7	157.8	146.1
140°	245.3	245.5	241.1	233.2	222.5	210.5	197.1	182.8	169.6	157.6	146.9
142.5°	233.1	233.4	229.4	222.4	213.3	202.9	191.2	179.0	167.9	157.2	147.7
145°	216.4	215.9	213.6	207.7	200.7	192.6	183.6	174.4	165.4	156.5	148.1
147.5°	202.6	202.4	200.3	196.3	191.0	185.2	178.0	170.6	163.1	155.4	148.1
150°	194.6	194.6	192.9	189.8	185.6	180.3	174.4	167.9	161.5	154.6	148.1
152.5°	187.8	187.8	186.8	183.9	180.7	176.3	171.0	165.5	159.7	153.4	147.4
155°	179.4	179.2	178.6	176.3	173.8	170.5	166.3	161.8	157.0	151.5	146.7
157.5°	171.7	171.8	171.3	169.7	167.5	164.9	161.6	157.9	154.0	149.7	145.8
160°	166.8	167.2	167.2	165.4	163.5	161.5	158.8	155.7	152.0	148.4	145.3
162.5°	162.4	162.6	162.6	161.2	159.9	158.2	155.6	153.0	150.0	147.0	144.4
165°	156.5	156.5	156.8	155.7	154.6	153.1	151.1	149.5	147.3	145.0	143.1
167.5°	150.9	150.9	151.1	150.4	149.9	148.9	147.7	146.5	144.7	143.0	141.7
170°	147.5	147.5	147.8	147.3	146.9	146.4	145.3	144.4	143.1	141.6	140.9
172.5°	144.4	144.7	145.1	144.6	144.5	144.2	143.3	142.7	141.5	140.5	140.1
175°	140.9	141.1	141.4	141.1	141.1	141.1	140.5	140.2	139.7	139.1	139.1
177.5°	138.7	138.7	139.2	138.9	139.2	139.2	138.9	138.7	138.6	138.3	138.6
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	731.8	731.1	727.7	723.8	718.7	715.3	712.6	711.2	706.9	701.5	697.8
5°	777.1	767.9	758.3	746.4	735.5	724.3	717.3	709.1	699.1	687.9	679.9
7.5°	825.5	807.6	788.4	768.6	748.9	731.3	715.8	702.5	686.6	670.5	659.2
10°	862.6	836.5	809.5	781.9	756.7	733.1	714.9	697.0	677.9	659.3	645.4
12.5°	896.4	862.1	830.9	796.9	764.8	736.5	710.3	689.2	666.2	646.5	630.6
15°	939.1	903.9	866.3	814.7	771.9	736.1	704.3	676.6	648.7	624.5	609.0
17.5°	979.0	926.1	875.5	832.4	776.9	732.1	693.2	660.2	629.6	603.9	584.8
20°	995.5	944.3	889.3	834.4	779.8	729.8	684.5	648.1	616.2	587.1	569.5
22.5°	1005.4	947.4	889.5	830.5	772.5	720.5	675.8	635.7	601.2	573.5	551.8
25°	1017.1	947.8	884.2	825.9	766.8	710.3	657.2	614.7	577.4	548.0	524.9
27.5°	1024.7	943.3	868.0	803.3	743.2	687.1	638.4	593.3	555.5	524.3	499.6
30°	1026.2	939.7	855.6	785.5	724.5	673.0	621.4	578.3	538.3	505.2	482.1
32.5°	1028.1	930.7	838.9	764.5	702.0	650.9	604.2	563.0	522.0	489.4	465.9
35°	1020.1	925.7	813.5	727.9	665.4	615.9	573.8	535.8	495.5	463.9	440.0
37.5°	985.6	906.0	787.1	686.7	621.4	575.6	541.2	508.2	471.2	437.1	414.5
40°	950.9	886.6	766.8	661.8	593.5	546.4	515.5	488.5	452.7	420.8	396.6
42.5°	899.2	860.2	747.3	635.6	561.9	516.6	490.5	465.2	433.8	401.4	378.6
45°	804.4	809.5	707.6	593.8	518.2	472.7	448.1	430.6	402.7	376.0	352.6
47.5°	685.4	733.6	660.9	549.3	472.2	429.4	408.0	392.6	373.8	347.6	326.3
50°	607.8	676.6	623.5	519.4	443.3	400.8	379.6	367.2	350.8	330.1	309.8
52.5°	536.1	610.1	578.4	486.2	412.0	373.1	352.4	342.1	329.2	309.7	291.4
55°	437.2	512.1	504.9	436.0	365.0	330.1	314.3	302.9	294.0	279.5	264.9
57.5°	353.6	424.7	428.5	380.2	323.6	289.1	275.6	266.9	261.1	250.2	236.7
60°	301.0	366.2	379.0	342.5	294.0	263.6	250.3	243.4	238.8	230.0	219.7
62.5°	257.3	312.8	327.3	301.0	265.6	237.2	226.8	220.1	217.0	209.4	200.3
65°	196.9	243.0	257.0	242.4	223.9	201.1	192.7	186.9	184.2	179.9	173.3
67.5°	148.1	181.7	197.0	186.7	180.1	165.6	160.3	157.2	154.7	151.9	146.2
70°	118.9	143.9	159.6	156.9	151.4	143.9	139.9	137.8	135.3	132.9	128.0
72.5°	95.6	112.7	127.5	129.0	124.5	122.9	119.5	118.6	117.1	114.2	111.5
75°	63.5	75.3	85.6	89.5	91.3	92.8	91.3	91.0	90.7	88.3	86.7
77.5°	41.6	47.9	54.4	61.2	64.0	66.1	66.5	67.7	66.9	65.6	64.9
80°	31.8	33.4	37.9	43.7	48.2	50.1	51.3	51.9	51.6	51.3	50.1
82.5°	23.1	24.4	26.5	30.6	34.4	37.5	38.2	38.0	38.7	38.9	37.9
85°	12.4	12.8	13.4	13.9	16.1	19.4	20.4	20.9	21.5	21.5	19.7
87.5°	4.9	4.5	4.8	4.8	5.4	5.5	6.8	7.8	8.2	7.4	7.5
90°	5.3	4.5	3.6	3.1	2.5	1.7	1.1	0.6	1.1	1.7	2.5
92.5°	35.6	23.5	16.2	12.0	9.7	7.5	5.1	3.5	5.1	7.5	9.7
95°	101.9	60.2	36.4	25.5	18.2	13.5	10.4	9.5	10.4	13.5	18.2
97.5°	111.8	64.8	42.1	30.3	23.1	18.9	16.5	16.2	16.5	18.9	23.1
100°	105.5	64.1	44.5	33.6	26.9	23.0	21.0	20.8	21.0	23.0	26.9
102.5°	100.1	65.0	47.5	37.4	31.4	27.6	25.9	25.4	25.9	27.6	31.4
105°	96.3	67.5	52.4	43.6	38.3	35.0	33.4	32.5	33.4	35.0	38.3
107.5°	96.0	72.1	58.8	50.7	45.7	42.5	40.8	40.0	40.8	42.5	45.7
110°	97.1	75.9	63.3	55.5	50.7	47.6	46.2	45.3	46.2	47.6	50.7



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	99.4	79.7	68.0	60.4	55.6	52.5	51.1	50.3	51.1	52.5	55.6
115°	103.0	86.0	75.3	67.7	63.0	60.2	58.5	57.4	58.5	60.2	63.0
117.5°	107.8	92.6	82.1	75.1	69.8	67.2	65.8	64.5	65.8	67.2	69.8
120°	111.4	96.9	86.7	79.8	74.5	71.7	70.3	69.4	70.3	71.7	74.5
122.5°	114.8	101.3	91.5	84.1	79.0	75.9	74.5	73.7	74.5	75.9	79.0
125°	120.1	107.8	98.0	90.4	85.1	82.0	80.3	79.8	80.3	82.0	85.1
127.5°	124.5	113.4	103.9	96.3	90.5	87.4	85.2	84.4	85.2	87.4	90.5
130°	127.4	116.8	107.5	100.0	94.0	90.7	88.2	87.4	88.2	90.7	94.0
132.5°	130.1	119.6	110.7	103.3	97.4	93.4	90.6	89.6	90.6	93.4	97.4
135°	133.6	124.0	115.3	107.8	101.9	97.7	94.6	93.5	94.6	97.7	101.9
137.5°	136.1	127.1	118.7	111.7	105.8	101.4	98.4	97.2	98.4	101.4	105.8
140°	137.4	129.0	121.0	113.9	108.4	103.9	101.1	99.7	101.1	103.9	108.4
142.5°	138.8	130.6	122.7	116.2	110.6	106.5	103.5	102.3	103.5	106.5	110.6
145°	140.2	132.7	125.4	119.0	114.2	110.0	107.5	106.6	107.5	110.0	114.2
147.5°	141.2	134.4	127.7	122.2	117.6	114.0	111.5	111.1	111.5	114.0	117.6
150°	141.4	135.5	129.0	124.0	120.1	116.5	114.2	113.9	114.2	116.5	120.1
152.5°	141.8	136.2	130.6	125.8	122.3	119.1	116.9	116.8	116.9	119.1	122.3
155°	142.0	137.4	132.7	128.8	125.7	122.9	121.2	121.2	121.2	122.9	125.7
157.5°	142.2	138.2	134.4	131.3	128.7	126.3	124.9	124.7	124.9	126.3	128.7
160°	142.2	138.9	135.5	132.7	130.7	128.5	127.4	127.4	127.4	128.5	130.7
162.5°	142.0	139.1	136.2	133.8	132.1	130.3	129.4	129.4	129.4	130.3	132.1
165°	141.4	139.4	137.2	135.2	134.1	132.7	132.1	132.4	132.1	132.7	134.1
167.5°	140.9	139.3	137.8	136.5	135.7	134.7	134.4	134.7	134.4	134.7	135.7
170°	140.2	139.1	137.8	137.2	136.6	135.8	135.5	136.0	135.5	135.8	136.6
172.5°	140.1	139.1	137.9	137.6	137.3	136.7	136.6	137.0	136.6	136.7	137.3
175°	139.4	138.9	138.3	138.0	138.0	137.4	137.8	138.0	137.8	137.4	138.0
177.5°	138.9	138.6	138.3	138.3	138.3	138.1	138.3	138.6	138.3	138.1	138.3
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	696.6	693.5	691.3	686.4	683.3	679.9	676.5	678.7	678.4	678.2	678.2
5°	673.3	666.3	660.0	651.7	646.6	640.2	635.3	634.8	636.0	631.7	629.3
7.5°	650.1	640.6	631.5	622.5	612.9	605.2	600.5	598.3	595.2	592.6	589.8
10°	633.8	622.7	613.8	602.6	592.3	583.2	577.4	573.5	571.3	569.2	565.3
12.5°	617.1	606.1	594.8	582.2	572.4	561.8	557.5	553.1	549.0	546.6	541.2
15°	592.6	578.3	566.5	553.1	542.2	531.9	525.9	517.1	515.8	512.8	507.3
17.5°	568.0	552.5	536.2	526.3	514.0	503.3	494.0	491.1	482.4	479.1	474.4
20°	548.6	534.3	521.9	508.8	490.9	480.9	473.6	469.7	462.7	458.4	455.4
22.5°	531.9	517.3	503.0	487.7	472.9	461.8	456.4	450.3	446.5	440.5	437.2
25°	507.9	492.2	474.8	458.4	447.8	439.3	430.9	425.4	419.9	417.2	411.1
27.5°	480.1	463.7	447.5	435.1	422.0	413.6	405.9	401.1	394.5	389.9	386.6
30°	464.9	445.4	431.5	420.3	403.5	395.7	389.9	383.8	379.0	374.1	370.7
32.5°	447.1	429.4	416.1	402.3	389.4	380.9	373.4	368.0	363.9	359.3	356.0
35°	419.3	404.5	390.8	376.8	367.4	358.6	349.8	345.3	341.4	337.1	334.1
37.5°	394.2	380.3	367.3	354.1	342.5	335.3	328.2	324.7	319.4	316.6	313.5
40°	378.7	365.0	351.1	338.3	326.1	320.8	314.3	309.2	304.4	302.2	298.9
42.5°	361.7	348.0	336.3	322.5	312.6	305.1	299.3	293.7	290.0	286.9	285.0
45°	336.5	324.3	312.8	299.2	289.8	283.4	276.7	271.6	268.2	266.1	262.8
47.5°	312.0	299.9	288.2	276.3	267.2	259.9	253.3	249.6	245.3	242.6	240.3
50°	294.3	283.4	270.9	260.0	251.0	243.7	238.2	233.6	229.7	226.3	224.8
52.5°	278.1	266.4	255.6	245.5	235.9	227.6	222.7	217.9	214.9	211.0	209.3
55°	251.2	240.0	230.9	220.9	211.5	204.5	198.4	194.2	191.2	186.9	184.5
57.5°	226.0	215.9	205.1	196.5	186.7	180.9	175.8	170.0	166.4	163.0	160.7
60°	209.1	197.5	188.1	179.9	171.4	163.8	159.3	154.7	150.8	147.4	145.4
62.5°	191.3	181.3	172.4	163.4	155.7	149.0	143.8	139.9	136.5	134.4	132.2
65°	164.1	156.3	147.2	139.9	132.6	127.8	123.5	120.2	117.7	116.2	114.4
67.5°	139.2	131.5	123.6	116.4	111.5	107.8	105.0	102.2	101.0	99.0	97.8
70°	122.9	115.0	108.1	102.6	97.7	95.0	93.2	91.0	89.8	87.4	86.2
72.5°	105.2	99.5	94.4	89.9	86.0	83.6	81.3	78.7	76.7	74.1	72.8
75°	82.9	77.7	73.8	70.7	68.3	65.0	61.6	58.9	58.0	57.0	56.7
77.5°	61.3	58.1	55.2	52.7	49.7	47.2	46.5	45.9	45.7	45.2	45.2
80°	48.2	45.2	43.1	40.1	38.3	38.3	38.3	37.6	37.9	37.9	37.9
82.5°	35.9	33.0	31.9	30.8	30.5	30.7	30.7	30.8	30.7	31.1	30.9
85°	18.5	18.8	19.4	19.1	19.4	19.4	20.0	19.7	20.0	19.4	20.0
87.5°	7.4	8.2	8.6	9.1	9.5	9.4	9.6	9.7	10.0	10.0	10.1
90°	3.1	3.6	4.5	5.3	6.2	7.0	6.7	7.0	7.3	7.5	8.1
92.5°	12.0	16.2	23.5	35.6	47.4	43.0	32.5	23.6	18.7	16.5	15.1
95°	25.5	36.4	60.2	101.9	147.8	166.0	134.7	100.8	68.3	53.5	43.4
97.5°	30.3	42.1	64.8	111.8	188.4	257.3	275.2	251.2	201.2	165.1	131.7
100°	33.6	44.5	64.1	105.5	179.2	265.1	320.3	330.0	307.4	274.6	234.9
102.5°	37.4	47.5	65.0	100.1	165.7	250.6	322.5	356.2	355.5	336.4	311.2
105°	43.6	52.4	67.5	96.3	149.2	225.1	305.4	363.9	391.9	397.2	390.0
107.5°	50.7	58.8	72.1	96.0	138.7	202.6	275.5	341.8	387.3	411.9	421.8
110°	55.5	63.3	75.9	97.1	134.7	189.8	256.7	320.8	372.3	407.6	427.2



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	60.4	68.0	79.7	99.4	132.4	181.3	240.3	300.0	352.6	392.1	417.3
115°	67.7	75.3	86.0	103.0	131.6	172.1	220.6	272.4	321.1	362.3	392.8
117.5°	75.1	82.1	92.6	107.8	132.1	166.8	208.7	252.4	294.5	331.4	362.3
120°	79.8	86.7	96.9	111.4	133.0	164.3	202.4	241.9	279.6	313.2	341.5
122.5°	84.1	91.5	101.3	114.8	134.5	162.8	197.3	233.6	267.8	298.9	325.2
125°	90.4	98.0	107.8	120.1	136.9	160.7	190.7	222.5	253.1	280.0	302.4
127.5°	96.3	103.9	113.4	124.5	139.6	159.7	184.8	212.9	240.1	264.4	284.8
130°	100.0	107.5	116.8	127.4	141.4	159.0	181.6	206.8	232.1	254.8	273.8
132.5°	103.3	110.7	119.6	130.1	142.8	158.8	178.8	201.3	224.4	245.6	263.7
135°	107.8	115.3	124.0	133.6	144.7	158.4	175.0	193.7	213.6	231.8	247.7
137.5°	111.7	118.7	127.1	136.1	146.1	157.8	171.7	186.8	203.1	218.8	232.7
140°	113.9	121.0	129.0	137.4	146.9	157.6	169.6	182.8	197.1	210.5	222.5
142.5°	116.2	122.7	130.6	138.8	147.7	157.2	167.9	179.0	191.2	202.9	213.3
145°	119.0	125.4	132.7	140.2	148.1	156.5	165.4	174.4	183.6	192.6	200.7
147.5°	122.2	127.7	134.4	141.2	148.1	155.4	163.1	170.6	178.0	185.2	191.0
150°	124.0	129.0	135.5	141.4	148.1	154.6	161.5	167.9	174.4	180.3	185.6
152.5°	125.8	130.6	136.2	141.8	147.4	153.4	159.7	165.5	171.0	176.3	180.7
155°	128.8	132.7	137.4	142.0	146.7	151.5	157.0	161.8	166.3	170.5	173.8
157.5°	131.3	134.4	138.2	142.2	145.8	149.7	154.0	157.9	161.6	164.9	167.5
160°	132.7	135.5	138.9	142.2	145.3	148.4	152.0	155.7	158.8	161.5	163.5
162.5°	133.8	136.2	139.1	142.0	144.4	147.0	150.0	153.0	155.6	158.2	159.9
165°	135.2	137.2	139.4	141.4	143.1	145.0	147.3	149.5	151.1	153.1	154.6
167.5°	136.5	137.8	139.3	140.9	141.7	143.0	144.7	146.5	147.7	148.9	149.9
170°	137.2	137.8	139.1	140.2	140.9	141.6	143.1	144.4	145.3	146.4	146.9
172.5°	137.6	137.9	139.1	140.1	140.1	140.5	141.5	142.7	143.3	144.2	144.5
175°	138.0	138.3	138.9	139.4	139.1	139.1	139.7	140.2	140.5	141.1	141.1
177.5°	138.3	138.3	138.6	138.9	138.6	138.3	138.6	138.7	138.9	139.2	139.2
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	675.3	675.0	675.3	674.3	675.3	675.0	675.3	678.2	678.2	678.4	678.7
5°	628.4	628.0	627.2	624.5	627.2	628.0	628.4	629.3	631.7	636.0	634.8
7.5°	587.4	587.0	584.3	584.4	584.3	587.0	587.4	589.8	592.6	595.2	598.3
10°	563.2	563.5	559.8	557.7	559.8	563.5	563.2	565.3	569.2	571.3	573.5
12.5°	539.6	538.2	535.3	532.9	535.3	538.2	539.6	541.2	546.6	549.0	553.1
15°	508.5	505.5	498.2	498.8	498.2	505.5	508.5	507.3	512.8	515.8	517.1
17.5°	471.9	469.7	469.6	465.3	469.6	469.7	471.9	474.4	479.1	482.4	491.1
20°	450.6	449.1	449.6	445.4	449.6	449.1	450.6	455.4	458.4	462.7	469.7
22.5°	433.8	432.3	429.8	428.4	429.8	432.3	433.8	437.2	440.5	446.5	450.3
25°	409.3	406.9	404.5	406.0	404.5	406.9	409.3	411.1	417.2	419.9	425.4
27.5°	384.8	382.9	380.6	380.2	380.6	382.9	384.8	386.6	389.9	394.5	401.1
30°	369.2	367.4	366.2	364.7	366.2	367.4	369.2	370.7	374.1	379.0	383.8
32.5°	353.5	353.2	350.9	350.6	350.9	353.2	353.5	356.0	359.3	363.9	368.0
35°	332.9	331.1	330.4	330.7	330.4	331.1	332.9	334.1	337.1	341.4	345.3
37.5°	313.2	310.9	309.7	308.6	309.7	310.9	313.2	313.5	316.6	319.4	324.7
40°	299.2	296.8	296.1	295.6	296.1	296.8	299.2	298.9	302.2	304.4	309.2
42.5°	283.4	282.4	282.1	281.0	282.1	282.4	283.4	285.0	286.9	290.0	293.7
45°	261.8	261.6	259.8	260.3	259.8	261.6	261.8	262.8	266.1	268.2	271.6
47.5°	239.2	237.8	236.5	237.4	236.5	237.8	239.2	240.3	242.6	245.3	249.6
50°	223.6	223.0	220.3	220.9	220.3	223.0	223.6	224.8	226.3	229.7	233.6
52.5°	208.1	205.8	204.8	204.4	204.8	205.8	208.1	209.3	211.0	214.9	217.9
55°	182.4	179.6	178.4	177.8	178.4	179.6	182.4	184.5	186.9	191.2	194.2
57.5°	157.1	156.4	155.4	156.1	155.4	156.4	157.1	160.7	163.0	166.4	170.0
60°	142.3	142.3	142.3	142.0	142.3	142.3	142.3	145.4	147.4	150.8	154.7
62.5°	130.9	130.2	129.9	130.3	129.9	130.2	130.9	132.2	134.4	136.5	139.9
65°	113.4	113.2	111.9	111.7	111.9	113.2	113.4	114.4	116.2	117.7	120.2
67.5°	97.0	95.9	95.6	95.1	95.6	95.9	97.0	97.8	99.0	101.0	102.2
70°	84.7	84.1	82.2	82.5	82.2	84.1	84.7	86.2	87.4	89.8	91.0
72.5°	71.3	70.7	70.3	69.9	70.3	70.7	71.3	72.8	74.1	76.7	78.7
75°	56.4	56.2	55.8	57.0	55.8	56.2	56.4	56.7	57.0	58.0	58.9
77.5°	45.2	45.2	45.4	44.9	45.4	45.2	45.2	45.2	45.2	45.7	45.9
80°	37.9	37.9	37.6	37.6	37.6	37.9	37.9	37.9	37.9	37.9	37.6
82.5°	30.4	30.7	30.8	30.3	30.8	30.7	30.4	30.9	31.1	30.7	30.8
85°	20.0	19.7	20.4	20.0	20.4	19.7	20.0	20.0	19.4	20.0	19.7
87.5°	10.5	10.1	10.1	10.4	10.1	10.1	10.5	10.1	10.0	10.0	9.7
90°	7.8	8.1	8.4	8.1	8.4	8.1	7.8	8.1	7.5	7.3	7.0
92.5°	14.6	13.7	14.0	13.5	14.0	13.7	14.6	15.1	16.5	18.7	23.6
95°	38.1	35.6	33.6	32.5	33.6	35.6	38.1	43.4	53.5	68.3	100.8
97.5°	111.0	98.4	90.8	88.4	90.8	98.4	111.0	131.7	165.1	201.2	251.2
100°	206.6	186.2	175.2	175.5	175.2	186.2	206.6	234.9	274.6	307.4	330.0
102.5°	289.2	273.1	264.0	257.5	264.0	273.1	289.2	311.2	336.4	355.5	356.2
105°	377.1	366.5	357.5	356.1	357.5	366.5	377.1	390.0	397.2	391.9	363.9
107.5°	422.1	418.4	415.4	412.9	415.4	418.4	422.1	421.8	411.9	387.3	341.8
110°	435.1	437.3	436.7	436.2	436.7	437.3	435.1	427.2	407.6	372.3	320.8



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	431.7	438.6	440.8	440.8	440.8	438.6	431.7	417.3	392.1	352.6	300.0
115°	413.8	426.0	431.7	433.1	431.7	426.0	413.8	392.8	362.3	321.1	272.4
117.5°	384.3	398.4	406.4	408.3	406.4	398.4	384.3	362.3	331.4	294.5	252.4
120°	363.6	379.3	386.0	387.7	386.0	379.3	363.6	341.5	313.2	279.6	241.9
122.5°	344.8	358.9	366.3	368.4	366.3	358.9	344.8	325.2	298.9	267.8	233.6
125°	320.3	332.6	339.6	341.5	339.6	332.6	320.3	302.4	280.0	253.1	222.5
127.5°	300.7	311.2	317.6	319.3	317.6	311.2	300.7	284.8	264.4	240.1	212.9
130°	288.6	298.7	304.6	306.8	304.6	298.7	288.6	273.8	254.8	232.1	206.8
132.5°	277.7	287.7	292.9	294.5	292.9	287.7	277.7	263.7	245.6	224.4	201.3
135°	261.5	269.9	274.9	276.9	274.9	269.9	261.5	247.7	231.8	213.6	193.7
137.5°	244.2	252.7	256.9	258.3	256.9	252.7	244.2	232.7	218.8	203.1	186.8
140°	233.2	241.1	245.5	245.3	245.5	241.1	233.2	222.5	210.5	197.1	182.8
142.5°	222.4	229.4	233.4	233.1	233.4	229.4	222.4	213.3	202.9	191.2	179.0
145°	207.7	213.6	215.9	216.4	215.9	213.6	207.7	200.7	192.6	183.6	174.4
147.5°	196.3	200.3	202.4	202.6	202.4	200.3	196.3	191.0	185.2	178.0	170.6
150°	189.8	192.9	194.6	194.6	194.6	192.9	189.8	185.6	180.3	174.4	167.9
152.5°	183.9	186.8	187.8	187.8	187.8	186.8	183.9	180.7	176.3	171.0	165.5
155°	176.3	178.6	179.2	179.4	179.2	178.6	176.3	173.8	170.5	166.3	161.8
157.5°	169.7	171.3	171.8	171.7	171.8	171.3	169.7	167.5	164.9	161.6	157.9
160°	165.4	167.2	167.2	166.8	167.2	167.2	165.4	163.5	161.5	158.8	155.7
162.5°	161.2	162.6	162.6	162.4	162.6	162.6	161.2	159.9	158.2	155.6	153.0
165°	155.7	156.8	156.5	156.5	156.5	156.8	155.7	154.6	153.1	151.1	149.5
167.5°	150.4	151.1	150.9	150.9	150.9	151.1	150.4	149.9	148.9	147.7	146.5
170°	147.3	147.8	147.5	147.5	147.5	147.8	147.3	146.9	146.4	145.3	144.4
172.5°	144.6	145.1	144.7	144.4	144.7	145.1	144.6	144.5	144.2	143.3	142.7
175°	141.1	141.4	141.1	140.9	141.1	141.4	141.1	141.1	141.1	140.5	140.2
177.5°	138.9	139.2	138.7	138.7	138.7	139.2	138.9	139.2	139.2	138.9	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	676.5	679.9	683.3	686.4	691.3	693.5	696.6	697.8	701.5	706.9	711.2
5°	635.3	640.2	646.6	651.7	660.0	666.3	673.3	679.9	687.9	699.1	709.1
7.5°	600.5	605.2	612.9	622.5	631.5	640.6	650.1	659.2	670.5	686.6	702.5
10°	577.4	583.2	592.3	602.6	613.8	622.7	633.8	645.4	659.3	677.9	697.0
12.5°	557.5	561.8	572.4	582.2	594.8	606.1	617.1	630.6	646.5	666.2	689.2
15°	525.9	531.9	542.2	553.1	566.5	578.3	592.6	609.0	624.5	648.7	676.6
17.5°	494.0	503.3	514.0	526.3	536.2	552.5	568.0	584.8	603.9	629.6	660.2
20°	473.6	480.9	490.9	508.8	521.9	534.3	548.6	569.5	587.1	616.2	648.1
22.5°	456.4	461.8	472.9	487.7	503.0	517.3	531.9	551.8	573.5	601.2	635.7
25°	430.9	439.3	447.8	458.4	474.8	492.2	507.9	524.9	548.0	577.4	614.7
27.5°	405.9	413.6	422.0	435.1	447.5	463.7	480.1	499.6	524.3	555.5	593.3
30°	389.9	395.7	403.5	420.3	431.5	445.4	464.9	482.1	505.2	538.3	578.3
32.5°	373.4	380.9	389.4	402.3	416.1	429.4	447.1	465.9	489.4	522.0	563.0
35°	349.8	358.6	367.4	376.8	390.8	404.5	419.3	440.0	463.9	495.5	535.8
37.5°	328.2	335.3	342.5	354.1	367.3	380.3	394.2	414.5	437.1	471.2	508.2
40°	314.3	320.8	326.1	338.3	351.1	365.0	378.7	396.6	420.8	452.7	488.5
42.5°	299.3	305.1	312.6	322.5	336.3	348.0	361.7	378.6	401.4	433.8	465.2
45°	276.7	283.4	289.8	299.2	312.8	324.3	336.5	352.6	376.0	402.7	430.6
47.5°	253.3	259.9	267.2	276.3	288.2	299.9	312.0	326.3	347.6	373.8	392.6
50°	238.2	243.7	251.0	260.0	270.9	283.4	294.3	309.8	330.1	350.8	367.2
52.5°	222.7	227.6	235.9	245.5	255.6	266.4	278.1	291.4	309.7	329.2	342.1
55°	198.4	204.5	211.5	220.9	230.9	240.0	251.2	264.9	279.5	294.0	302.9
57.5°	175.8	180.9	186.7	196.5	205.1	215.9	226.0	236.7	250.2	261.1	266.9
60°	159.3	163.8	171.4	179.9	188.1	197.5	209.1	219.7	230.0	238.8	243.4
62.5°	143.8	149.0	155.7	163.4	172.4	181.3	191.3	200.3	209.4	217.0	220.1
65°	123.5	127.8	132.6	139.9	147.2	156.3	164.1	173.3	179.9	184.2	186.9
67.5°	105.0	107.8	111.5	116.4	123.6	131.5	139.2	146.2	151.9	154.7	157.2
70°	93.2	95.0	97.7	102.6	108.1	115.0	122.9	128.0	132.9	135.3	137.8
72.5°	81.3	83.6	86.0	89.9	94.4	99.5	105.2	111.5	114.2	117.1	118.6
75°	61.6	65.0	68.3	70.7	73.8	77.7	82.9	86.7	88.3	90.7	91.0
77.5°	46.5	47.2	49.7	52.7	55.2	58.1	61.3	64.9	65.6	66.9	67.7
80°	38.3	38.3	38.3	40.1	43.1	45.2	48.2	50.1	51.3	51.6	51.9
82.5°	30.7	30.7	30.5	30.8	31.9	33.0	35.9	37.9	38.9	38.7	38.0
85°	20.0	19.4	19.4	19.1	19.4	18.8	18.5	19.7	21.5	21.5	20.9
87.5°	9.6	9.4	9.5	9.1	8.6	8.2	7.4	7.5	7.4	8.2	7.8
90°	6.7	7.0	6.2	5.3	4.5	3.6	3.1	2.5	1.7	1.1	0.6
92.5°	32.5	43.0	47.4	35.6	23.5	16.2	12.0	9.7	7.5	5.1	3.5
95°	134.7	166.0	147.8	101.9	60.2	36.4	25.5	18.2	13.5	10.4	9.5
97.5°	275.2	257.3	188.4	111.8	64.8	42.1	30.3	23.1	18.9	16.5	16.2
100°	320.3	265.1	179.2	105.5	64.1	44.5	33.6	26.9	23.0	21.0	20.8
102.5°	322.5	250.6	165.7	100.1	65.0	47.5	37.4	31.4	27.6	25.9	25.4
105°	305.4	225.1	149.2	96.3	67.5	52.4	43.6	38.3	35.0	33.4	32.5
107.5°	275.5	202.6	138.7	96.0	72.1	58.8	50.7	45.7	42.5	40.8	40.0
110°	256.7	189.8	134.7	97.1	75.9	63.3	55.5	50.7	47.6	46.2	45.3



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	240.3	181.3	132.4	99.4	79.7	68.0	60.4	55.6	52.5	51.1	50.3
115°	220.6	172.1	131.6	103.0	86.0	75.3	67.7	63.0	60.2	58.5	57.4
117.5°	208.7	166.8	132.1	107.8	92.6	82.1	75.1	69.8	67.2	65.8	64.5
120°	202.4	164.3	133.0	111.4	96.9	86.7	79.8	74.5	71.7	70.3	69.4
122.5°	197.3	162.8	134.5	114.8	101.3	91.5	84.1	79.0	75.9	74.5	73.7
125°	190.7	160.7	136.9	120.1	107.8	98.0	90.4	85.1	82.0	80.3	79.8
127.5°	184.8	159.7	139.6	124.5	113.4	103.9	96.3	90.5	87.4	85.2	84.4
130°	181.6	159.0	141.4	127.4	116.8	107.5	100.0	94.0	90.7	88.2	87.4
132.5°	178.8	158.8	142.8	130.1	119.6	110.7	103.3	97.4	93.4	90.6	89.6
135°	175.0	158.4	144.7	133.6	124.0	115.3	107.8	101.9	97.7	94.6	93.5
137.5°	171.7	157.8	146.1	136.1	127.1	118.7	111.7	105.8	101.4	98.4	97.2
140°	169.6	157.6	146.9	137.4	129.0	121.0	113.9	108.4	103.9	101.1	99.7
142.5°	167.9	157.2	147.7	138.8	130.6	122.7	116.2	110.6	106.5	103.5	102.3
145°	165.4	156.5	148.1	140.2	132.7	125.4	119.0	114.2	110.0	107.5	106.6
147.5°	163.1	155.4	148.1	141.2	134.4	127.7	122.2	117.6	114.0	111.5	111.1
150°	161.5	154.6	148.1	141.4	135.5	129.0	124.0	120.1	116.5	114.2	113.9
152.5°	159.7	153.4	147.4	141.8	136.2	130.6	125.8	122.3	119.1	116.9	116.8
155°	157.0	151.5	146.7	142.0	137.4	132.7	128.8	125.7	122.9	121.2	121.2
157.5°	154.0	149.7	145.8	142.2	138.2	134.4	131.3	128.7	126.3	124.9	124.7
160°	152.0	148.4	145.3	142.2	138.9	135.5	132.7	130.7	128.5	127.4	127.4
162.5°	150.0	147.0	144.4	142.0	139.1	136.2	133.8	132.1	130.3	129.4	129.4
165°	147.3	145.0	143.1	141.4	139.4	137.2	135.2	134.1	132.7	132.1	132.4
167.5°	144.7	143.0	141.7	140.9	139.3	137.8	136.5	135.7	134.7	134.4	134.7
170°	143.1	141.6	140.9	140.2	139.1	137.8	137.2	136.6	135.8	135.5	136.0
172.5°	141.5	140.5	140.1	140.1	139.1	137.9	137.6	137.3	136.7	136.6	137.0
175°	139.7	139.1	139.1	139.4	138.9	138.3	138.0	138.0	137.4	137.8	138.0
177.5°	138.6	138.3	138.6	138.9	138.6	138.3	138.3	138.3	138.1	138.3	138.6
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	712.6	715.3	718.7	723.8	727.7	731.1	731.8	732.8	735.2	739.3	742.5
5°	717.3	724.3	735.5	746.4	758.3	767.9	777.1	783.5	789.5	802.2	812.5
7.5°	715.8	731.3	748.9	768.6	788.4	807.6	825.5	841.5	857.4	875.9	897.1
10°	714.9	733.1	756.7	781.9	809.5	836.5	862.6	883.0	906.7	927.9	954.9
12.5°	710.3	736.5	764.8	796.9	830.9	862.1	896.4	924.5	951.5	982.2	1013.6
15°	704.3	736.1	771.9	814.7	866.3	903.9	939.1	987.9	1021.3	1054.7	1099.6
17.5°	693.2	732.1	776.9	832.4	875.5	926.1	979.0	1017.6	1062.6	1109.6	1150.2
20°	684.5	729.8	779.8	834.4	889.3	944.3	995.5	1041.6	1088.1	1142.4	1175.8
22.5°	675.8	720.5	772.5	830.5	889.5	947.4	1005.4	1059.6	1111.8	1166.6	1209.3
25°	657.2	710.3	766.8	825.9	884.2	947.8	1017.1	1077.4	1142.1	1198.5	1238.9
27.5°	638.4	687.1	743.2	803.3	868.0	943.3	1024.7	1093.4	1158.1	1198.5	1211.2
30°	621.4	673.0	724.5	785.5	855.6	939.7	1026.2	1104.8	1157.9	1175.4	1162.4
32.5°	604.2	650.9	702.0	764.5	838.9	930.7	1028.1	1098.0	1130.0	1116.5	1063.3
35°	573.8	615.9	665.4	727.9	813.5	925.7	1020.1	1067.5	1059.5	983.7	883.5
37.5°	541.2	575.6	621.4	686.7	787.1	906.0	985.6	992.6	924.3	807.9	692.2
40°	515.5	546.4	593.5	661.8	766.8	886.6	950.9	922.7	816.8	687.2	590.7
42.5°	490.5	516.6	561.9	635.6	747.3	860.2	899.2	837.7	715.6	593.0	505.3
45°	448.1	472.7	518.2	593.8	707.6	809.5	804.4	697.6	575.3	476.7	403.9
47.5°	408.0	429.4	472.2	549.3	660.9	733.6	685.4	571.8	468.0	389.0	337.0
50°	379.6	400.8	443.3	519.4	623.5	676.6	607.8	498.2	403.2	337.7	296.4
52.5°	352.4	373.1	412.0	486.2	578.4	610.1	536.1	434.6	355.5	298.9	263.4
55°	314.3	330.1	365.0	436.0	504.9	512.1	437.2	352.3	287.0	247.6	223.3
57.5°	275.6	289.1	323.6	380.2	428.5	424.7	353.6	280.2	236.2	206.9	189.3
60°	250.3	263.6	294.0	342.5	379.0	366.2	301.0	241.9	204.2	182.7	168.7
62.5°	226.8	237.2	265.6	301.0	327.3	312.8	257.3	208.3	178.5	160.3	149.2
65°	192.7	201.1	223.9	242.4	257.0	243.0	196.9	163.0	141.4	128.7	121.0
67.5°	160.3	165.6	180.1	186.7	197.0	181.7	148.1	125.3	113.0	102.3	97.0
70°	139.9	143.9	151.4	156.9	159.6	143.9	118.9	102.3	92.0	84.4	81.0
72.5°	119.5	122.9	124.5	129.0	127.5	112.7	95.6	82.4	74.9	69.8	65.5
75°	91.3	92.8	91.3	89.5	85.6	75.3	63.5	56.7	51.3	48.9	47.4
77.5°	66.5	66.1	64.0	61.2	54.4	47.9	41.6	39.3	37.0	35.6	35.2
80°	51.3	50.1	48.2	43.7	37.9	33.4	31.8	30.3	29.5	27.9	27.6
82.5°	38.2	37.5	34.4	30.6	26.5	24.4	23.1	22.6	21.6	20.9	20.8
85°	20.4	19.4	16.1	13.9	13.4	12.8	12.4	12.4	11.2	10.9	10.9
87.5°	6.8	5.5	5.4	4.8	4.8	4.5	4.9	4.6	4.6	4.8	4.3
90°	1.1	1.7	2.5	3.1	3.6	4.5	5.3	6.2	7.0	6.7	7.0
92.5°	5.1	7.5	9.7	12.0	16.2	23.5	35.6	47.4	43.0	32.5	23.6
95°	10.4	13.5	18.2	25.5	36.4	60.2	101.9	147.8	166.0	134.7	100.8
97.5°	16.5	18.9	23.1	30.3	42.1	64.8	111.8	188.4	257.3	275.2	251.2
100°	21.0	23.0	26.9	33.6	44.5	64.1	105.5	179.2	265.1	320.3	330.0
102.5°	25.9	27.6	31.4	37.4	47.5	65.0	100.1	165.7	250.6	322.5	356.2
105°	33.4	35.0	38.3	43.6	52.4	67.5	96.3	149.2	225.1	305.4	363.9
107.5°	40.8	42.5	45.7	50.7	58.8	72.1	96.0	138.7	202.6	275.5	341.8
110°	46.2	47.6	50.7	55.5	63.3	75.9	97.1	134.7	189.8	256.7	320.8



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	51.1	52.5	55.6	60.4	68.0	79.7	99.4	132.4	181.3	240.3	300.0
115°	58.5	60.2	63.0	67.7	75.3	86.0	103.0	131.6	172.1	220.6	272.4
117.5°	65.8	67.2	69.8	75.1	82.1	92.6	107.8	132.1	166.8	208.7	252.4
120°	70.3	71.7	74.5	79.8	86.7	96.9	111.4	133.0	164.3	202.4	241.9
122.5°	74.5	75.9	79.0	84.1	91.5	101.3	114.8	134.5	162.8	197.3	233.6
125°	80.3	82.0	85.1	90.4	98.0	107.8	120.1	136.9	160.7	190.7	222.5
127.5°	85.2	87.4	90.5	96.3	103.9	113.4	124.5	139.6	159.7	184.8	212.9
130°	88.2	90.7	94.0	100.0	107.5	116.8	127.4	141.4	159.0	181.6	206.8
132.5°	90.6	93.4	97.4	103.3	110.7	119.6	130.1	142.8	158.8	178.8	201.3
135°	94.6	97.7	101.9	107.8	115.3	124.0	133.6	144.7	158.4	175.0	193.7
137.5°	98.4	101.4	105.8	111.7	118.7	127.1	136.1	146.1	157.8	171.7	186.8
140°	101.1	103.9	108.4	113.9	121.0	129.0	137.4	146.9	157.6	169.6	182.8
142.5°	103.5	106.5	110.6	116.2	122.7	130.6	138.8	147.7	157.2	167.9	179.0
145°	107.5	110.0	114.2	119.0	125.4	132.7	140.2	148.1	156.5	165.4	174.4
147.5°	111.5	114.0	117.6	122.2	127.7	134.4	141.2	148.1	155.4	163.1	170.6
150°	114.2	116.5	120.1	124.0	129.0	135.5	141.4	148.1	154.6	161.5	167.9
152.5°	116.9	119.1	122.3	125.8	130.6	136.2	141.8	147.4	153.4	159.7	165.5
155°	121.2	122.9	125.7	128.8	132.7	137.4	142.0	146.7	151.5	157.0	161.8
157.5°	124.9	126.3	128.7	131.3	134.4	138.2	142.2	145.8	149.7	154.0	157.9
160°	127.4	128.5	130.7	132.7	135.5	138.9	142.2	145.3	148.4	152.0	155.7
162.5°	129.4	130.3	132.1	133.8	136.2	139.1	142.0	144.4	147.0	150.0	153.0
165°	132.1	132.7	134.1	135.2	137.2	139.4	141.4	143.1	145.0	147.3	149.5
167.5°	134.4	134.7	135.7	136.5	137.8	139.3	140.9	141.7	143.0	144.7	146.5
170°	135.5	135.8	136.6	137.2	137.8	139.1	140.2	140.9	141.6	143.1	144.4
172.5°	136.6	136.7	137.3	137.6	137.9	139.1	140.1	140.1	140.5	141.5	142.7
175°	137.8	137.4	138.0	138.0	138.3	138.9	139.4	139.1	139.1	139.7	140.2
177.5°	138.3	138.1	138.3	138.3	138.3	138.6	138.9	138.6	138.3	138.6	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	747.7	747.7	748.6	752.3	752.7	755.9	754.9
5°	821.7	827.4	829.6	838.7	844.1	846.5	841.7
7.5°	912.2	928.4	936.2	945.7	954.1	956.7	950.1
10°	978.3	995.2	1009.5	1018.3	1026.5	1031.9	1038.9
12.5°	1042.0	1063.0	1076.5	1088.9	1097.3	1104.3	1105.4
15°	1111.4	1143.0	1167.0	1184.6	1193.3	1197.9	1196.1
17.5°	1181.4	1210.6	1227.7	1245.6	1257.8	1258.5	1258.9
20°	1221.0	1249.5	1269.2	1282.5	1296.2	1295.6	1298.6
22.5°	1247.4	1269.9	1285.0	1294.7	1299.3	1297.0	1297.7
25°	1259.8	1266.5	1263.8	1248.2	1244.4	1230.1	1232.5
27.5°	1196.0	1164.4	1131.8	1089.7	1056.6	1030.2	1031.5
30°	1109.3	1053.4	989.8	936.4	888.4	875.0	846.5
32.5°	988.2	904.4	829.8	780.1	738.9	727.7	702.8
35°	782.8	701.5	624.7	578.6	560.4	535.0	534.6
37.5°	608.5	536.9	496.3	461.7	443.5	428.1	426.6
40°	511.9	456.1	425.4	400.5	382.6	371.1	368.4
42.5°	444.4	399.3	370.5	355.1	341.4	335.4	331.0
45°	362.9	332.6	312.5	298.6	292.2	287.6	285.2
47.5°	303.6	283.2	269.6	260.3	255.1	250.3	251.6
50°	271.2	254.6	244.5	235.8	231.8	228.5	228.8
52.5°	245.3	230.3	222.2	215.9	211.0	208.6	207.4
55°	208.2	198.8	190.5	186.0	183.2	179.9	179.0
57.5°	177.5	170.2	163.6	158.4	157.8	154.6	155.0
60°	157.2	151.1	145.6	142.9	140.8	138.1	138.9
62.5°	140.5	135.3	130.3	128.1	126.0	124.0	124.4
65°	115.0	110.1	107.1	105.9	105.0	104.1	103.1
67.5°	91.7	88.6	86.7	84.1	82.3	82.0	81.0
70°	77.1	73.1	69.8	66.5	65.5	65.2	65.5
72.5°	61.8	59.3	58.4	56.7	56.6	55.8	56.3
75°	46.4	45.6	44.9	43.7	43.7	43.7	43.7
77.5°	34.2	33.7	33.4	33.0	32.8	32.3	32.3
80°	26.7	26.4	25.8	25.8	25.5	25.8	25.5
82.5°	20.1	20.1	19.5	19.5	19.2	19.0	19.2
85°	10.3	10.0	10.6	10.0	10.3	9.7	10.3
87.5°	4.4	4.4	4.3	4.2	4.0	4.6	4.0
90°	7.3	7.5	8.1	7.8	8.1	8.4	8.1
92.5°	18.7	16.5	15.1	14.6	13.7	14.0	13.5
95°	68.3	53.5	43.4	38.1	35.6	33.6	32.5
97.5°	201.2	165.1	131.7	111.0	98.4	90.8	88.4
100°	307.4	274.6	234.9	206.6	186.2	175.2	175.5
102.5°	355.5	336.4	311.2	289.2	273.1	264.0	257.5
105°	391.9	397.2	390.0	377.1	366.5	357.5	356.1
107.5°	387.3	411.9	421.8	422.1	418.4	415.4	412.9
110°	372.3	407.6	427.2	435.1	437.3	436.7	436.2



TEST NUMBER: P332272-927

CATALOG NUMBER: S123RDIP-S560D365U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	352.6	392.1	417.3	431.7	438.6	440.8	440.8
115°	321.1	362.3	392.8	413.8	426.0	431.7	433.1
117.5°	294.5	331.4	362.3	384.3	398.4	406.4	408.3
120°	279.6	313.2	341.5	363.6	379.3	386.0	387.7
122.5°	267.8	298.9	325.2	344.8	358.9	366.3	368.4
125°	253.1	280.0	302.4	320.3	332.6	339.6	341.5
127.5°	240.1	264.4	284.8	300.7	311.2	317.6	319.3
130°	232.1	254.8	273.8	288.6	298.7	304.6	306.8
132.5°	224.4	245.6	263.7	277.7	287.7	292.9	294.5
135°	213.6	231.8	247.7	261.5	269.9	274.9	276.9
137.5°	203.1	218.8	232.7	244.2	252.7	256.9	258.3
140°	197.1	210.5	222.5	233.2	241.1	245.5	245.3
142.5°	191.2	202.9	213.3	222.4	229.4	233.4	233.1
145°	183.6	192.6	200.7	207.7	213.6	215.9	216.4
147.5°	178.0	185.2	191.0	196.3	200.3	202.4	202.6
150°	174.4	180.3	185.6	189.8	192.9	194.6	194.6
152.5°	171.0	176.3	180.7	183.9	186.8	187.8	187.8
155°	166.3	170.5	173.8	176.3	178.6	179.2	179.4
157.5°	161.6	164.9	167.5	169.7	171.3	171.8	171.7
160°	158.8	161.5	163.5	165.4	167.2	167.2	166.8
162.5°	155.6	158.2	159.9	161.2	162.6	162.6	162.4
165°	151.1	153.1	154.6	155.7	156.8	156.5	156.5
167.5°	147.7	148.9	149.9	150.4	151.1	150.9	150.9
170°	145.3	146.4	146.9	147.3	147.8	147.5	147.5
172.5°	143.3	144.2	144.5	144.6	145.1	144.7	144.4
175°	140.5	141.1	141.1	141.1	141.4	141.1	140.9
177.5°	138.9	139.2	139.2	138.9	139.2	138.7	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3

(END OF REPORT)