

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332278-927

Luminaire Tested: **S123RDIP-S560D585U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332278-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D585U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3445.8 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	95	91	88	91	88	84	82	75	72	70	63	61	60	52	51	50	44
2	90	83	77	73	83	77	72	68	66	62	59	56	53	51	46	44	43	38
3	83	74	67	61	76	69	62	57	59	54	50	50	46	44	41	39	37	33
4	76	66	58	52	70	61	54	49	53	47	43	45	41	38	37	35	32	29
5	70	59	51	45	65	55	48	43	47	42	38	40	36	33	34	31	29	25
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	25	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	28	25	23	20
8	56	44	36	31	51	41	34	29	36	30	26	31	27	23	26	23	21	18
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	19	17
10	49	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7629	7629	7629	7629
5°	9095	7662	6748	7662
10°	11355	7618	6096	7618
15°	13329	7540	5558	7540
20°	14875	7424	5102	7424
25°	14638	7301	4822	7301
30°	10521	7188	4533	7188
35°	7025	7041	4346	7041
40°	5176	6864	4154	6864
45°	4341	6555	3962	6555
50°	3831	6149	3699	6149
55°	3359	5684	3337	5684
60°	2990	5240	3057	5240
65°	2626	4760	2845	4760
70°	2061	4337	2596	4337
75°	1817	3785	2371	3785
80°	1581	3217	2331	3217
85°	1272	2581	2470	2581



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.7	2.0
10°-20°	217.8	6.3
20°-30°	342.1	9.9
30°-40°	356.9	10.4
40°-50°	305.5	8.9
50°-60°	232.8	6.8
60°-70°	149.2	4.3
70°-80°	71.8	2.1
80°-90°	20.7	0.6
90°-100°	124.2	3.6
100°-110°	351.7	10.2
110°-120°	346.0	10.0
120°-130°	276.0	8.0
130°-140°	217.6	6.3
140°-150°	162.4	4.7
150°-160°	113.2	3.3
160°-170°	66.5	1.9
170°-180°	21.6	0.6
0°-30°	629.6	18.3
0°-40°	986.5	28.6
0°-60°	1524.8	44.2
0°-90°	1766.5	51.3
90°-120°	822.0	23.9
90°-150°	1478.0	42.9
90°-180°	1679.0	48.7
0°-180°	3445.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	709	709	709	709	709	
5°	842	709	624	709	842	87
15°	1196	677	499	677	1196	339
25°	1232	615	406	615	1232	530
35°	535	536	331	536	535	351
45°	285	431	260	431	285	224
55°	179	303	178	303	179	162
65°	103	187	112	187	103	101
75°	44	91	57	91	44	47
85°	10	21	20	21	10	12
90°	13	1	13	1	13	7
95°	52	15	52	15	52	94
105°	575	52	575	52	575	567
115°	699	93	699	93	699	679
125°	551	129	551	129	551	500
135°	447	151	447	151	447	347
145°	349	172	349	172	349	222
155°	290	196	290	196	290	135
165°	252	214	252	214	252	72
175°	227	223	227	223	227	22
180°	223	223	223	223	223	



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	754.9	755.9	752.7	752.3	748.6	747.7	747.7	742.5	739.3	735.2	732.8
5°	841.7	846.5	844.1	838.7	829.6	827.4	821.7	812.5	802.2	789.5	783.5
7.5°	950.1	956.7	954.1	945.7	936.2	928.4	912.2	897.1	875.9	857.4	841.5
10°	1038.9	1031.9	1026.5	1018.3	1009.5	995.2	978.3	954.9	927.9	906.7	883.0
12.5°	1105.4	1104.3	1097.3	1088.9	1076.5	1063.0	1042.0	1013.6	982.2	951.5	924.5
15°	1196.1	1197.9	1193.3	1184.6	1167.0	1143.0	1111.4	1099.6	1054.7	1021.3	987.9
17.5°	1258.9	1258.5	1257.8	1245.6	1227.7	1210.6	1181.4	1150.2	1109.6	1062.6	1017.6
20°	1298.6	1295.6	1296.2	1282.5	1269.2	1249.5	1221.0	1175.8	1142.4	1088.1	1041.6
22.5°	1297.7	1297.0	1299.3	1294.7	1285.0	1269.9	1247.4	1209.3	1166.6	1111.8	1059.6
25°	1232.5	1230.1	1244.4	1248.2	1263.8	1266.5	1259.8	1238.9	1198.5	1142.1	1077.4
27.5°	1031.5	1030.2	1056.6	1089.7	1131.8	1164.4	1196.0	1211.2	1198.5	1158.1	1093.4
30°	846.5	875.0	888.4	936.4	989.8	1053.4	1109.3	1162.4	1175.4	1157.9	1104.8
32.5°	702.8	727.7	738.9	780.1	829.8	904.4	988.2	1063.3	1116.5	1130.0	1098.0
35°	534.6	535.0	560.4	578.6	624.7	701.5	782.8	883.5	983.7	1059.5	1067.5
37.5°	426.6	428.1	443.5	461.7	496.3	536.9	608.5	692.2	807.9	924.3	992.6
40°	368.4	371.1	382.6	400.5	425.4	456.1	511.9	590.7	687.2	816.8	922.7
42.5°	331.0	335.4	341.4	355.1	370.5	399.3	444.4	505.3	593.0	715.6	837.7
45°	285.2	287.6	292.2	298.6	312.5	332.6	362.9	403.9	476.7	575.3	697.6
47.5°	251.6	250.3	255.1	260.3	269.6	283.2	303.6	337.0	389.0	468.0	571.8
50°	228.8	228.5	231.8	235.8	244.5	254.6	271.2	296.4	337.7	403.2	498.2
52.5°	207.4	208.6	211.0	215.9	222.2	230.3	245.3	263.4	298.9	355.5	434.6
55°	179.0	179.9	183.2	186.0	190.5	198.8	208.2	223.3	247.6	287.0	352.3
57.5°	155.0	154.6	157.8	158.4	163.6	170.2	177.5	189.3	206.9	236.2	280.2
60°	138.9	138.1	140.8	142.9	145.6	151.1	157.2	168.7	182.7	204.2	241.9
62.5°	124.4	124.0	126.0	128.1	130.3	135.3	140.5	149.2	160.3	178.5	208.3
65°	103.1	104.1	105.0	105.9	107.1	110.1	115.0	121.0	128.7	141.4	163.0
67.5°	81.0	82.0	82.3	84.1	86.7	88.6	91.7	97.0	102.3	113.0	125.3
70°	65.5	65.2	65.5	66.5	69.8	73.1	77.1	81.0	84.4	92.0	102.3
72.5°	56.3	55.8	56.6	56.7	58.4	59.3	61.8	65.5	69.8	74.9	82.4
75°	43.7	43.7	43.7	43.7	44.9	45.6	46.4	47.4	48.9	51.3	56.7
77.5°	32.3	32.3	32.8	33.0	33.4	33.7	34.2	35.2	35.6	37.0	39.3
80°	25.5	25.8	25.5	25.8	25.8	26.4	26.7	27.6	27.9	29.5	30.3
82.5°	19.2	19.0	19.2	19.5	19.5	20.1	20.1	20.8	20.9	21.6	22.6
85°	10.3	9.7	10.3	10.0	10.6	10.0	10.3	10.9	10.9	11.2	12.4
87.5°	5.1	5.6	5.1	5.2	5.3	5.4	5.2	5.1	5.5	5.4	5.4
90°	13.1	13.5	13.1	12.7	13.1	12.2	11.7	11.3	10.9	11.3	9.9
92.5°	21.8	22.6	22.1	23.5	24.3	26.7	30.2	38.0	52.4	69.5	76.4
95°	52.4	54.2	57.4	61.5	70.0	86.3	110.3	162.6	217.3	267.9	238.6
97.5°	142.7	146.6	158.8	179.1	212.5	266.5	324.8	405.5	444.3	415.3	304.0
100°	283.3	282.9	300.5	333.4	379.1	443.2	496.1	532.7	516.9	427.9	289.1
102.5°	415.6	426.0	440.7	466.8	502.3	543.0	573.9	575.0	520.5	404.4	267.5
105°	574.7	577.0	591.4	608.6	629.4	641.2	632.6	587.4	493.0	363.3	240.8
107.5°	666.4	670.5	675.4	681.2	680.8	664.7	625.2	551.8	444.7	326.9	223.9
110°	703.9	704.9	705.8	702.2	689.5	657.9	600.9	517.8	414.3	306.3	217.3



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	711.5	711.4	708.0	696.7	673.6	633.0	569.1	484.2	387.9	292.6	213.7
115°	699.0	696.7	687.7	667.8	633.9	584.7	518.2	439.7	356.1	277.9	212.4
117.5°	659.0	656.0	642.9	620.2	584.9	534.9	475.2	407.3	336.8	269.2	213.2
120°	625.8	623.1	612.3	586.9	551.3	505.6	451.4	390.4	326.7	265.2	214.6
122.5°	594.7	591.3	579.3	556.6	524.8	482.4	432.2	377.0	318.4	262.7	217.1
125°	551.3	548.1	536.8	516.9	488.0	451.9	408.4	359.2	307.7	259.4	220.9
127.5°	515.5	512.5	502.3	485.4	459.6	426.7	387.6	343.6	298.3	257.7	225.3
130°	495.2	491.6	482.1	465.9	441.9	411.1	374.5	333.9	293.3	256.7	228.1
132.5°	475.3	472.8	464.4	448.1	425.6	396.3	362.3	324.9	288.5	256.3	230.4
135°	446.9	443.7	435.5	422.0	399.9	374.1	344.8	312.7	282.4	255.7	233.6
137.5°	416.8	414.7	407.8	394.1	375.5	353.2	327.9	301.6	277.1	254.8	235.8
140°	395.8	396.2	389.0	376.4	359.2	339.8	318.1	295.1	273.8	254.4	237.2
142.5°	376.3	376.8	370.3	359.0	344.4	327.5	308.7	288.9	270.9	253.7	238.3
145°	349.3	348.4	344.8	335.3	324.0	310.9	296.4	281.5	267.0	252.5	239.0
147.5°	327.0	326.7	323.2	316.8	308.2	299.0	287.2	275.4	263.2	250.9	239.0
150°	314.0	314.0	311.3	306.3	299.6	291.0	281.5	271.1	260.7	249.4	239.0
152.5°	303.2	303.2	301.6	296.9	291.6	284.5	276.1	267.1	257.9	247.6	238.0
155°	289.6	289.1	288.3	284.6	280.6	275.2	268.4	261.2	253.5	244.5	236.8
157.5°	277.3	277.3	276.6	273.9	270.4	266.2	260.9	254.8	248.6	241.6	235.2
160°	269.3	269.7	269.7	267.0	263.9	260.7	256.2	251.2	245.3	239.5	234.5
162.5°	262.1	262.5	262.5	260.2	258.1	255.3	251.1	246.9	242.1	237.3	233.1
165°	252.5	252.5	253.0	251.2	249.4	247.2	244.0	241.3	237.7	234.1	230.9
167.5°	243.5	243.5	244.0	242.7	241.9	240.3	238.4	236.4	233.5	230.8	228.7
170°	238.1	238.1	238.6	237.7	237.2	236.3	234.5	233.1	230.9	228.6	227.3
172.5°	233.1	233.5	234.2	233.3	233.2	232.7	231.2	230.3	228.4	226.8	226.2
175°	227.3	227.8	228.1	227.8	227.8	227.8	226.8	226.4	225.5	224.6	224.6
177.5°	223.9	223.9	224.7	224.3	224.7	224.7	224.3	223.9	223.6	223.2	223.6
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	731.8	731.1	727.7	723.8	718.7	715.3	712.6	711.2	706.9	701.5	697.8
5°	777.1	767.9	758.3	746.4	735.5	724.3	717.3	709.1	699.1	687.9	679.9
7.5°	825.5	807.6	788.4	768.6	748.9	731.3	715.8	702.5	686.6	670.5	659.2
10°	862.6	836.5	809.5	781.9	756.7	733.1	714.9	697.0	677.9	659.3	645.4
12.5°	896.4	862.1	830.9	796.9	764.8	736.5	710.3	689.2	666.2	646.5	630.6
15°	939.1	903.9	866.3	814.7	771.9	736.1	704.3	676.6	648.7	624.5	609.0
17.5°	979.0	926.1	875.5	832.4	776.9	732.1	693.2	660.2	629.6	603.9	584.8
20°	995.5	944.3	889.3	834.4	779.8	729.8	684.5	648.1	616.2	587.1	569.5
22.5°	1005.4	947.4	889.5	830.5	772.5	720.5	675.8	635.7	601.2	573.5	551.8
25°	1017.1	947.8	884.2	825.9	766.8	710.3	657.2	614.7	577.4	548.0	524.9
27.5°	1024.7	943.3	868.0	803.3	743.2	687.1	638.4	593.3	555.5	524.3	499.6
30°	1026.2	939.7	855.6	785.5	724.5	673.0	621.4	578.3	538.3	505.2	482.1
32.5°	1028.1	930.7	838.9	764.5	702.0	650.9	604.2	563.0	522.0	489.4	465.9
35°	1020.1	925.7	813.5	727.9	665.4	615.9	573.8	535.8	495.5	463.9	440.0
37.5°	985.6	906.0	787.1	686.7	621.4	575.6	541.2	508.2	471.2	437.1	414.5
40°	950.9	886.6	766.8	661.8	593.5	546.4	515.5	488.5	452.7	420.8	396.6
42.5°	899.2	860.2	747.3	635.6	561.9	516.6	490.5	465.2	433.8	401.4	378.6
45°	804.4	809.5	707.6	593.8	518.2	472.7	448.1	430.6	402.7	376.0	352.6
47.5°	685.4	733.6	660.9	549.3	472.2	429.4	408.0	392.6	373.8	347.6	326.3
50°	607.8	676.6	623.5	519.4	443.3	400.8	379.6	367.2	350.8	330.1	309.8
52.5°	536.1	610.1	578.4	486.2	412.0	373.1	352.4	342.1	329.2	309.7	291.4
55°	437.2	512.1	504.9	436.0	365.0	330.1	314.3	302.9	294.0	279.5	264.9
57.5°	353.6	424.7	428.5	380.2	323.6	289.1	275.6	266.9	261.1	250.2	236.7
60°	301.0	366.2	379.0	342.5	294.0	263.6	250.3	243.4	238.8	230.0	219.7
62.5°	257.3	312.8	327.3	301.0	265.6	237.2	226.8	220.1	217.0	209.4	200.3
65°	196.9	243.0	257.0	242.4	223.9	201.1	192.7	186.9	184.2	179.9	173.3
67.5°	148.1	181.7	197.0	186.7	180.1	165.6	160.3	157.2	154.7	151.9	146.2
70°	118.9	143.9	159.6	156.9	151.4	143.9	139.9	137.8	135.3	132.9	128.0
72.5°	95.6	112.7	127.5	129.0	124.5	122.9	119.5	118.6	117.1	114.2	111.5
75°	63.5	75.3	85.6	89.5	91.3	92.8	91.3	91.0	90.7	88.3	86.7
77.5°	41.6	47.9	54.4	61.2	64.0	66.1	66.5	67.7	66.9	65.6	64.9
80°	31.8	33.4	37.9	43.7	48.2	50.1	51.3	51.9	51.6	51.3	50.1
82.5°	23.1	24.4	26.5	30.6	34.4	37.5	38.2	38.0	38.7	38.9	37.9
85°	12.4	12.8	13.4	13.9	16.1	19.4	20.4	20.9	21.5	21.5	19.7
87.5°	5.6	5.1	5.3	5.1	5.7	5.6	6.9	7.9	8.4	7.6	7.8
90°	8.6	7.2	5.9	5.0	4.0	2.7	1.8	0.9	1.8	2.7	4.0
92.5°	57.4	37.9	26.1	19.4	15.6	12.1	8.3	5.6	8.3	12.1	15.6
95°	164.5	97.1	58.7	41.1	29.4	21.7	16.7	15.4	16.7	21.7	29.4
97.5°	180.5	104.6	67.9	48.8	37.2	30.6	26.7	26.2	26.7	30.6	37.2
100°	170.3	103.5	71.9	54.2	43.4	37.1	33.9	33.4	33.9	37.1	43.4
102.5°	161.7	104.9	76.5	60.4	50.6	44.7	41.8	41.0	41.8	44.7	50.6
105°	155.4	108.9	84.5	70.5	61.9	56.5	53.8	52.4	53.8	56.5	61.9
107.5°	155.0	116.3	94.9	81.9	73.8	68.5	65.9	64.5	65.9	68.5	73.8
110°	156.8	122.5	102.1	89.4	81.8	76.8	74.5	73.2	74.5	76.8	81.8



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	160.4	128.6	109.7	97.4	89.8	84.8	82.5	81.1	82.5	84.8	89.8
115°	166.3	138.7	121.5	109.3	101.6	97.1	94.4	92.6	94.4	97.1	101.6
117.5°	174.0	149.5	132.5	121.2	112.6	108.4	106.2	104.1	106.2	108.4	112.6
120°	179.8	156.3	140.1	128.8	120.2	115.7	113.4	112.1	113.4	115.7	120.2
122.5°	185.3	163.6	147.7	135.6	127.4	122.6	120.3	118.9	120.3	122.6	127.4
125°	193.8	174.0	158.1	145.9	137.4	132.4	129.7	128.8	129.7	132.4	137.4
127.5°	200.9	183.0	167.7	155.5	146.0	141.0	137.6	136.3	137.6	141.0	146.0
130°	205.6	188.4	173.5	161.3	151.8	146.4	142.4	141.0	142.4	146.4	151.8
132.5°	209.9	193.1	178.6	166.8	157.2	150.8	146.3	144.6	146.3	150.8	157.2
135°	215.6	200.2	186.2	174.0	164.5	157.7	152.7	150.9	152.7	157.7	164.5
137.5°	219.7	205.0	191.5	180.3	170.9	163.7	158.8	156.9	158.8	163.7	170.9
140°	221.9	208.3	195.2	183.9	174.8	167.6	163.1	160.9	163.1	167.6	174.8
142.5°	224.0	210.8	198.1	187.5	178.5	172.0	167.1	165.2	167.1	172.0	178.5
145°	226.4	214.2	202.4	192.0	184.3	177.6	173.5	172.1	173.5	177.6	184.3
147.5°	227.8	216.9	206.1	197.3	189.9	184.0	180.0	179.2	180.0	184.0	189.9
150°	228.1	218.7	208.3	200.2	193.8	188.0	184.3	183.9	184.3	188.0	193.8
152.5°	228.9	219.8	210.8	203.0	197.5	192.3	188.7	188.6	188.7	192.3	197.5
155°	229.1	221.9	214.2	207.9	202.9	198.4	195.7	195.7	195.7	198.4	202.9
157.5°	229.6	223.0	216.9	212.0	207.8	203.7	201.6	201.2	201.6	203.7	207.8
160°	229.6	224.1	218.7	214.2	211.0	207.4	205.6	205.6	205.6	207.4	211.0
162.5°	229.2	224.5	219.8	215.9	213.2	210.3	208.8	208.8	208.8	210.3	213.2
165°	228.1	225.0	221.4	218.2	216.4	214.2	213.3	213.7	213.3	214.2	216.4
167.5°	227.4	224.9	222.3	220.3	219.0	217.3	216.9	217.5	216.9	217.3	219.0
170°	226.4	224.6	222.3	221.4	220.5	219.1	218.7	219.6	218.7	219.1	220.5
172.5°	226.0	224.6	222.7	222.1	221.6	220.6	220.5	221.0	220.5	220.6	221.6
175°	225.0	224.1	223.2	222.8	222.8	221.9	222.3	222.8	222.3	221.9	222.8
177.5°	224.3	223.6	223.2	223.2	223.2	222.8	223.2	223.6	223.2	222.8	223.2
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	696.6	693.5	691.3	686.4	683.3	679.9	676.5	678.7	678.4	678.2	678.2
5°	673.3	666.3	660.0	651.7	646.6	640.2	635.3	634.8	636.0	631.7	629.3
7.5°	650.1	640.6	631.5	622.5	612.9	605.2	600.5	598.3	595.2	592.6	589.8
10°	633.8	622.7	613.8	602.6	592.3	583.2	577.4	573.5	571.3	569.2	565.3
12.5°	617.1	606.1	594.8	582.2	572.4	561.8	557.5	553.1	549.0	546.6	541.2
15°	592.6	578.3	566.5	553.1	542.2	531.9	525.9	517.1	515.8	512.8	507.3
17.5°	568.0	552.5	536.2	526.3	514.0	503.3	494.0	491.1	482.4	479.1	474.4
20°	548.6	534.3	521.9	508.8	490.9	480.9	473.6	469.7	462.7	458.4	455.4
22.5°	531.9	517.3	503.0	487.7	472.9	461.8	456.4	450.3	446.5	440.5	437.2
25°	507.9	492.2	474.8	458.4	447.8	439.3	430.9	425.4	419.9	417.2	411.1
27.5°	480.1	463.7	447.5	435.1	422.0	413.6	405.9	401.1	394.5	389.9	386.6
30°	464.9	445.4	431.5	420.3	403.5	395.7	389.9	383.8	379.0	374.1	370.7
32.5°	447.1	429.4	416.1	402.3	389.4	380.9	373.4	368.0	363.9	359.3	356.0
35°	419.3	404.5	390.8	376.8	367.4	358.6	349.8	345.3	341.4	337.1	334.1
37.5°	394.2	380.3	367.3	354.1	342.5	335.3	328.2	324.7	319.4	316.6	313.5
40°	378.7	365.0	351.1	338.3	326.1	320.8	314.3	309.2	304.4	302.2	298.9
42.5°	361.7	348.0	336.3	322.5	312.6	305.1	299.3	293.7	290.0	286.9	285.0
45°	336.5	324.3	312.8	299.2	289.8	283.4	276.7	271.6	268.2	266.1	262.8
47.5°	312.0	299.9	288.2	276.3	267.2	259.9	253.3	249.6	245.3	242.6	240.3
50°	294.3	283.4	270.9	260.0	251.0	243.7	238.2	233.6	229.7	226.3	224.8
52.5°	278.1	266.4	255.6	245.5	235.9	227.6	222.7	217.9	214.9	211.0	209.3
55°	251.2	240.0	230.9	220.9	211.5	204.5	198.4	194.2	191.2	186.9	184.5
57.5°	226.0	215.9	205.1	196.5	186.7	180.9	175.8	170.0	166.4	163.0	160.7
60°	209.1	197.5	188.1	179.9	171.4	163.8	159.3	154.7	150.8	147.4	145.4
62.5°	191.3	181.3	172.4	163.4	155.7	149.0	143.8	139.9	136.5	134.4	132.2
65°	164.1	156.3	147.2	139.9	132.6	127.8	123.5	120.2	117.7	116.2	114.4
67.5°	139.2	131.5	123.6	116.4	111.5	107.8	105.0	102.2	101.0	99.0	97.8
70°	122.9	115.0	108.1	102.6	97.7	95.0	93.2	91.0	89.8	87.4	86.2
72.5°	105.2	99.5	94.4	89.9	86.0	83.6	81.3	78.7	76.7	74.1	72.8
75°	82.9	77.7	73.8	70.7	68.3	65.0	61.6	58.9	58.0	57.0	56.7
77.5°	61.3	58.1	55.2	52.7	49.7	47.2	46.5	45.9	45.7	45.2	45.2
80°	48.2	45.2	43.1	40.1	38.3	38.3	38.3	37.6	37.9	37.9	37.9
82.5°	35.9	33.0	31.9	30.8	30.5	30.7	30.7	30.8	30.7	31.1	30.9
85°	18.5	18.8	19.4	19.1	19.4	19.4	20.0	19.7	20.0	19.4	20.0
87.5°	7.8	8.7	9.2	9.7	10.2	10.3	10.5	10.5	10.9	10.9	11.1
90°	5.0	5.9	7.2	8.6	9.9	11.3	10.9	11.3	11.7	12.2	13.1
92.5°	19.4	26.1	37.9	57.4	76.4	69.5	52.4	38.0	30.2	26.7	24.3
95°	41.1	58.7	97.1	164.5	238.6	267.9	217.3	162.6	110.3	86.3	70.0
97.5°	48.8	67.9	104.6	180.5	304.0	415.3	444.3	405.5	324.8	266.5	212.5
100°	54.2	71.9	103.5	170.3	289.1	427.9	516.9	532.7	496.1	443.2	379.1
102.5°	60.4	76.5	104.9	161.7	267.5	404.4	520.5	575.0	573.9	543.0	502.3
105°	70.5	84.5	108.9	155.4	240.8	363.3	493.0	587.4	632.6	641.2	629.4
107.5°	81.9	94.9	116.3	155.0	223.9	326.9	444.7	551.8	625.2	664.7	680.8
110°	89.4	102.1	122.5	156.8	217.3	306.3	414.3	517.8	600.9	657.9	689.5



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	97.4	109.7	128.6	160.4	213.7	292.6	387.9	484.2	569.1	633.0	673.6
115°	109.3	121.5	138.7	166.3	212.4	277.9	356.1	439.7	518.2	584.7	633.9
117.5°	121.2	132.5	149.5	174.0	213.2	269.2	336.8	407.3	475.2	534.9	584.9
120°	128.8	140.1	156.3	179.8	214.6	265.2	326.7	390.4	451.4	505.6	551.3
122.5°	135.6	147.7	163.6	185.3	217.1	262.7	318.4	377.0	432.2	482.4	524.8
125°	145.9	158.1	174.0	193.8	220.9	259.4	307.7	359.2	408.4	451.9	488.0
127.5°	155.5	167.7	183.0	200.9	225.3	257.7	298.3	343.6	387.6	426.7	459.6
130°	161.3	173.5	188.4	205.6	228.1	256.7	293.3	333.9	374.5	411.1	441.9
132.5°	166.8	178.6	193.1	209.9	230.4	256.3	288.5	324.9	362.3	396.3	425.6
135°	174.0	186.2	200.2	215.6	233.6	255.7	282.4	312.7	344.8	374.1	399.9
137.5°	180.3	191.5	205.0	219.7	235.8	254.8	277.1	301.6	327.9	353.2	375.5
140°	183.9	195.2	208.3	221.9	237.2	254.4	273.8	295.1	318.1	339.8	359.2
142.5°	187.5	198.1	210.8	224.0	238.3	253.7	270.9	288.9	308.7	327.5	344.4
145°	192.0	202.4	214.2	226.4	239.0	252.5	267.0	281.5	296.4	310.9	324.0
147.5°	197.3	206.1	216.9	227.8	239.0	250.9	263.2	275.4	287.2	299.0	308.2
150°	200.2	208.3	218.7	228.1	239.0	249.4	260.7	271.1	281.5	291.0	299.6
152.5°	203.0	210.8	219.8	228.9	238.0	247.6	257.9	267.1	276.1	284.5	291.6
155°	207.9	214.2	221.9	229.1	236.8	244.5	253.5	261.2	268.4	275.2	280.6
157.5°	212.0	216.9	223.0	229.6	235.2	241.6	248.6	254.8	260.9	266.2	270.4
160°	214.2	218.7	224.1	229.6	234.5	239.5	245.3	251.2	256.2	260.7	263.9
162.5°	215.9	219.8	224.5	229.2	233.1	237.3	242.1	246.9	251.1	255.3	258.1
165°	218.2	221.4	225.0	228.1	230.9	234.1	237.7	241.3	244.0	247.2	249.4
167.5°	220.3	222.3	224.9	227.4	228.7	230.8	233.5	236.4	238.4	240.3	241.9
170°	221.4	222.3	224.6	226.4	227.3	228.6	230.9	233.1	234.5	236.3	237.2
172.5°	222.1	222.7	224.6	226.0	226.2	226.8	228.4	230.3	231.2	232.7	233.2
175°	222.8	223.2	224.1	225.0	224.6	224.6	225.5	226.4	226.8	227.8	227.8
177.5°	223.2	223.2	223.6	224.3	223.6	223.2	223.6	223.9	224.3	224.7	224.7
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	675.3	675.0	675.3	674.3	675.3	675.0	675.3	678.2	678.2	678.4	678.7
5°	628.4	628.0	627.2	624.5	627.2	628.0	628.4	629.3	631.7	636.0	634.8
7.5°	587.4	587.0	584.3	584.4	584.3	587.0	587.4	589.8	592.6	595.2	598.3
10°	563.2	563.5	559.8	557.7	559.8	563.5	563.2	565.3	569.2	571.3	573.5
12.5°	539.6	538.2	535.3	532.9	535.3	538.2	539.6	541.2	546.6	549.0	553.1
15°	508.5	505.5	498.2	498.8	498.2	505.5	508.5	507.3	512.8	515.8	517.1
17.5°	471.9	469.7	469.6	465.3	469.6	469.7	471.9	474.4	479.1	482.4	491.1
20°	450.6	449.1	449.6	445.4	449.6	449.1	450.6	455.4	458.4	462.7	469.7
22.5°	433.8	432.3	429.8	428.4	429.8	432.3	433.8	437.2	440.5	446.5	450.3
25°	409.3	406.9	404.5	406.0	404.5	406.9	409.3	411.1	417.2	419.9	425.4
27.5°	384.8	382.9	380.6	380.2	380.6	382.9	384.8	386.6	389.9	394.5	401.1
30°	369.2	367.4	366.2	364.7	366.2	367.4	369.2	370.7	374.1	379.0	383.8
32.5°	353.5	353.2	350.9	350.6	350.9	353.2	353.5	356.0	359.3	363.9	368.0
35°	332.9	331.1	330.4	330.7	330.4	331.1	332.9	334.1	337.1	341.4	345.3
37.5°	313.2	310.9	309.7	308.6	309.7	310.9	313.2	313.5	316.6	319.4	324.7
40°	299.2	296.8	296.1	295.6	296.1	296.8	299.2	298.9	302.2	304.4	309.2
42.5°	283.4	282.4	282.1	281.0	282.1	282.4	283.4	285.0	286.9	290.0	293.7
45°	261.8	261.6	259.8	260.3	259.8	261.6	261.8	262.8	266.1	268.2	271.6
47.5°	239.2	237.8	236.5	237.4	236.5	237.8	239.2	240.3	242.6	245.3	249.6
50°	223.6	223.0	220.3	220.9	220.3	223.0	223.6	224.8	226.3	229.7	233.6
52.5°	208.1	205.8	204.8	204.4	204.8	205.8	208.1	209.3	211.0	214.9	217.9
55°	182.4	179.6	178.4	177.8	178.4	179.6	182.4	184.5	186.9	191.2	194.2
57.5°	157.1	156.4	155.4	156.1	155.4	156.4	157.1	160.7	163.0	166.4	170.0
60°	142.3	142.3	142.3	142.0	142.3	142.3	142.3	145.4	147.4	150.8	154.7
62.5°	130.9	130.2	129.9	130.3	129.9	130.2	130.9	132.2	134.4	136.5	139.9
65°	113.4	113.2	111.9	111.7	111.9	113.2	113.4	114.4	116.2	117.7	120.2
67.5°	97.0	95.9	95.6	95.1	95.6	95.9	97.0	97.8	99.0	101.0	102.2
70°	84.7	84.1	82.2	82.5	82.2	84.1	84.7	86.2	87.4	89.8	91.0
72.5°	71.3	70.7	70.3	69.9	70.3	70.7	71.3	72.8	74.1	76.7	78.7
75°	56.4	56.2	55.8	57.0	55.8	56.2	56.4	56.7	57.0	58.0	58.9
77.5°	45.2	45.2	45.4	44.9	45.4	45.2	45.2	45.2	45.2	45.7	45.9
80°	37.9	37.9	37.6	37.6	37.6	37.9	37.9	37.9	37.9	37.9	37.6
82.5°	30.4	30.7	30.8	30.3	30.8	30.7	30.4	30.9	31.1	30.7	30.8
85°	20.0	19.7	20.4	20.0	20.4	19.7	20.0	20.0	19.4	20.0	19.7
87.5°	11.5	11.1	11.2	11.3	11.2	11.1	11.5	11.1	10.9	10.9	10.5
90°	12.7	13.1	13.5	13.1	13.5	13.1	12.7	13.1	12.2	11.7	11.3
92.5°	23.5	22.1	22.6	21.8	22.6	22.1	23.5	24.3	26.7	30.2	38.0
95°	61.5	57.4	54.2	52.4	54.2	57.4	61.5	70.0	86.3	110.3	162.6
97.5°	179.1	158.8	146.6	142.7	146.6	158.8	179.1	212.5	266.5	324.8	405.5
100°	333.4	300.5	282.9	283.3	282.9	300.5	333.4	379.1	443.2	496.1	532.7
102.5°	466.8	440.7	426.0	415.6	426.0	440.7	466.8	502.3	543.0	573.9	575.0
105°	608.6	591.4	577.0	574.7	577.0	591.4	608.6	629.4	641.2	632.6	587.4
107.5°	681.2	675.4	670.5	666.4	670.5	675.4	681.2	680.8	664.7	625.2	551.8
110°	702.2	705.8	704.9	703.9	704.9	705.8	702.2	689.5	657.9	600.9	517.8



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	696.7	708.0	711.4	711.5	711.4	708.0	696.7	673.6	633.0	569.1	484.2
115°	667.8	687.7	696.7	699.0	696.7	687.7	667.8	633.9	584.7	518.2	439.7
117.5°	620.2	642.9	656.0	659.0	656.0	642.9	620.2	584.9	534.9	475.2	407.3
120°	586.9	612.3	623.1	625.8	623.1	612.3	586.9	551.3	505.6	451.4	390.4
122.5°	556.6	579.3	591.3	594.7	591.3	579.3	556.6	524.8	482.4	432.2	377.0
125°	516.9	536.8	548.1	551.3	548.1	536.8	516.9	488.0	451.9	408.4	359.2
127.5°	485.4	502.3	512.5	515.5	512.5	502.3	485.4	459.6	426.7	387.6	343.6
130°	465.9	482.1	491.6	495.2	491.6	482.1	465.9	441.9	411.1	374.5	333.9
132.5°	448.1	464.4	472.8	475.3	472.8	464.4	448.1	425.6	396.3	362.3	324.9
135°	422.0	435.5	443.7	446.9	443.7	435.5	422.0	399.9	374.1	344.8	312.7
137.5°	394.1	407.8	414.7	416.8	414.7	407.8	394.1	375.5	353.2	327.9	301.6
140°	376.4	389.0	396.2	395.8	396.2	389.0	376.4	359.2	339.8	318.1	295.1
142.5°	359.0	370.3	376.8	376.3	376.8	370.3	359.0	344.4	327.5	308.7	288.9
145°	335.3	344.8	348.4	349.3	348.4	344.8	335.3	324.0	310.9	296.4	281.5
147.5°	316.8	323.2	326.7	327.0	326.7	323.2	316.8	308.2	299.0	287.2	275.4
150°	306.3	311.3	314.0	314.0	314.0	311.3	306.3	299.6	291.0	281.5	271.1
152.5°	296.9	301.6	303.2	303.2	303.2	301.6	296.9	291.6	284.5	276.1	267.1
155°	284.6	288.3	289.1	289.6	289.1	288.3	284.6	280.6	275.2	268.4	261.2
157.5°	273.9	276.6	277.3	277.3	277.3	276.6	273.9	270.4	266.2	260.9	254.8
160°	267.0	269.7	269.7	269.3	269.7	269.7	267.0	263.9	260.7	256.2	251.2
162.5°	260.2	262.5	262.5	262.1	262.5	262.5	260.2	258.1	255.3	251.1	246.9
165°	251.2	253.0	252.5	252.5	252.5	253.0	251.2	249.4	247.2	244.0	241.3
167.5°	242.7	244.0	243.5	243.5	243.5	244.0	242.7	241.9	240.3	238.4	236.4
170°	237.7	238.6	238.1	238.1	238.1	238.6	237.7	237.2	236.3	234.5	233.1
172.5°	233.3	234.2	233.5	233.1	233.5	234.2	233.3	233.2	232.7	231.2	230.3
175°	227.8	228.1	227.8	227.3	227.8	228.1	227.8	227.8	227.8	226.8	226.4
177.5°	224.3	224.7	223.9	223.9	223.9	224.7	224.3	224.7	224.7	224.3	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	676.5	679.9	683.3	686.4	691.3	693.5	696.6	697.8	701.5	706.9	711.2
5°	635.3	640.2	646.6	651.7	660.0	666.3	673.3	679.9	687.9	699.1	709.1
7.5°	600.5	605.2	612.9	622.5	631.5	640.6	650.1	659.2	670.5	686.6	702.5
10°	577.4	583.2	592.3	602.6	613.8	622.7	633.8	645.4	659.3	677.9	697.0
12.5°	557.5	561.8	572.4	582.2	594.8	606.1	617.1	630.6	646.5	666.2	689.2
15°	525.9	531.9	542.2	553.1	566.5	578.3	592.6	609.0	624.5	648.7	676.6
17.5°	494.0	503.3	514.0	526.3	536.2	552.5	568.0	584.8	603.9	629.6	660.2
20°	473.6	480.9	490.9	508.8	521.9	534.3	548.6	569.5	587.1	616.2	648.1
22.5°	456.4	461.8	472.9	487.7	503.0	517.3	531.9	551.8	573.5	601.2	635.7
25°	430.9	439.3	447.8	458.4	474.8	492.2	507.9	524.9	548.0	577.4	614.7
27.5°	405.9	413.6	422.0	435.1	447.5	463.7	480.1	499.6	524.3	555.5	593.3
30°	389.9	395.7	403.5	420.3	431.5	445.4	464.9	482.1	505.2	538.3	578.3
32.5°	373.4	380.9	389.4	402.3	416.1	429.4	447.1	465.9	489.4	522.0	563.0
35°	349.8	358.6	367.4	376.8	390.8	404.5	419.3	440.0	463.9	495.5	535.8
37.5°	328.2	335.3	342.5	354.1	367.3	380.3	394.2	414.5	437.1	471.2	508.2
40°	314.3	320.8	326.1	338.3	351.1	365.0	378.7	396.6	420.8	452.7	488.5
42.5°	299.3	305.1	312.6	322.5	336.3	348.0	361.7	378.6	401.4	433.8	465.2
45°	276.7	283.4	289.8	299.2	312.8	324.3	336.5	352.6	376.0	402.7	430.6
47.5°	253.3	259.9	267.2	276.3	288.2	299.9	312.0	326.3	347.6	373.8	392.6
50°	238.2	243.7	251.0	260.0	270.9	283.4	294.3	309.8	330.1	350.8	367.2
52.5°	222.7	227.6	235.9	245.5	255.6	266.4	278.1	291.4	309.7	329.2	342.1
55°	198.4	204.5	211.5	220.9	230.9	240.0	251.2	264.9	279.5	294.0	302.9
57.5°	175.8	180.9	186.7	196.5	205.1	215.9	226.0	236.7	250.2	261.1	266.9
60°	159.3	163.8	171.4	179.9	188.1	197.5	209.1	219.7	230.0	238.8	243.4
62.5°	143.8	149.0	155.7	163.4	172.4	181.3	191.3	200.3	209.4	217.0	220.1
65°	123.5	127.8	132.6	139.9	147.2	156.3	164.1	173.3	179.9	184.2	186.9
67.5°	105.0	107.8	111.5	116.4	123.6	131.5	139.2	146.2	151.9	154.7	157.2
70°	93.2	95.0	97.7	102.6	108.1	115.0	122.9	128.0	132.9	135.3	137.8
72.5°	81.3	83.6	86.0	89.9	94.4	99.5	105.2	111.5	114.2	117.1	118.6
75°	61.6	65.0	68.3	70.7	73.8	77.7	82.9	86.7	88.3	90.7	91.0
77.5°	46.5	47.2	49.7	52.7	55.2	58.1	61.3	64.9	65.6	66.9	67.7
80°	38.3	38.3	38.3	40.1	43.1	45.2	48.2	50.1	51.3	51.6	51.9
82.5°	30.7	30.7	30.5	30.8	31.9	33.0	35.9	37.9	38.9	38.7	38.0
85°	20.0	19.4	19.4	19.1	19.4	18.8	18.5	19.7	21.5	21.5	20.9
87.5°	10.5	10.3	10.2	9.7	9.2	8.7	7.8	7.8	7.6	8.4	7.9
90°	10.9	11.3	9.9	8.6	7.2	5.9	5.0	4.0	2.7	1.8	0.9
92.5°	52.4	69.5	76.4	57.4	37.9	26.1	19.4	15.6	12.1	8.3	5.6
95°	217.3	267.9	238.6	164.5	97.1	58.7	41.1	29.4	21.7	16.7	15.4
97.5°	444.3	415.3	304.0	180.5	104.6	67.9	48.8	37.2	30.6	26.7	26.2
100°	516.9	427.9	289.1	170.3	103.5	71.9	54.2	43.4	37.1	33.9	33.4
102.5°	520.5	404.4	267.5	161.7	104.9	76.5	60.4	50.6	44.7	41.8	41.0
105°	493.0	363.3	240.8	155.4	108.9	84.5	70.5	61.9	56.5	53.8	52.4
107.5°	444.7	326.9	223.9	155.0	116.3	94.9	81.9	73.8	68.5	65.9	64.5
110°	414.3	306.3	217.3	156.8	122.5	102.1	89.4	81.8	76.8	74.5	73.2



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	387.9	292.6	213.7	160.4	128.6	109.7	97.4	89.8	84.8	82.5	81.1
115°	356.1	277.9	212.4	166.3	138.7	121.5	109.3	101.6	97.1	94.4	92.6
117.5°	336.8	269.2	213.2	174.0	149.5	132.5	121.2	112.6	108.4	106.2	104.1
120°	326.7	265.2	214.6	179.8	156.3	140.1	128.8	120.2	115.7	113.4	112.1
122.5°	318.4	262.7	217.1	185.3	163.6	147.7	135.6	127.4	122.6	120.3	118.9
125°	307.7	259.4	220.9	193.8	174.0	158.1	145.9	137.4	132.4	129.7	128.8
127.5°	298.3	257.7	225.3	200.9	183.0	167.7	155.5	146.0	141.0	137.6	136.3
130°	293.3	256.7	228.1	205.6	188.4	173.5	161.3	151.8	146.4	142.4	141.0
132.5°	288.5	256.3	230.4	209.9	193.1	178.6	166.8	157.2	150.8	146.3	144.6
135°	282.4	255.7	233.6	215.6	200.2	186.2	174.0	164.5	157.7	152.7	150.9
137.5°	277.1	254.8	235.8	219.7	205.0	191.5	180.3	170.9	163.7	158.8	156.9
140°	273.8	254.4	237.2	221.9	208.3	195.2	183.9	174.8	167.6	163.1	160.9
142.5°	270.9	253.7	238.3	224.0	210.8	198.1	187.5	178.5	172.0	167.1	165.2
145°	267.0	252.5	239.0	226.4	214.2	202.4	192.0	184.3	177.6	173.5	172.1
147.5°	263.2	250.9	239.0	227.8	216.9	206.1	197.3	189.9	184.0	180.0	179.2
150°	260.7	249.4	239.0	228.1	218.7	208.3	200.2	193.8	188.0	184.3	183.9
152.5°	257.9	247.6	238.0	228.9	219.8	210.8	203.0	197.5	192.3	188.7	188.6
155°	253.5	244.5	236.8	229.1	221.9	214.2	207.9	202.9	198.4	195.7	195.7
157.5°	248.6	241.6	235.2	229.6	223.0	216.9	212.0	207.8	203.7	201.6	201.2
160°	245.3	239.5	234.5	229.6	224.1	218.7	214.2	211.0	207.4	205.6	205.6
162.5°	242.1	237.3	233.1	229.2	224.5	219.8	215.9	213.2	210.3	208.8	208.8
165°	237.7	234.1	230.9	228.1	225.0	221.4	218.2	216.4	214.2	213.3	213.7
167.5°	233.5	230.8	228.7	227.4	224.9	222.3	220.3	219.0	217.3	216.9	217.5
170°	230.9	228.6	227.3	226.4	224.6	222.3	221.4	220.5	219.1	218.7	219.6
172.5°	228.4	226.8	226.2	226.0	224.6	222.7	222.1	221.6	220.6	220.5	221.0
175°	225.5	224.6	224.6	225.0	224.1	223.2	222.8	222.8	221.9	222.3	222.8
177.5°	223.6	223.2	223.6	224.3	223.6	223.2	223.2	223.2	222.8	223.2	223.6
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	712.6	715.3	718.7	723.8	727.7	731.1	731.8	732.8	735.2	739.3	742.5
5°	717.3	724.3	735.5	746.4	758.3	767.9	777.1	783.5	789.5	802.2	812.5
7.5°	715.8	731.3	748.9	768.6	788.4	807.6	825.5	841.5	857.4	875.9	897.1
10°	714.9	733.1	756.7	781.9	809.5	836.5	862.6	883.0	906.7	927.9	954.9
12.5°	710.3	736.5	764.8	796.9	830.9	862.1	896.4	924.5	951.5	982.2	1013.6
15°	704.3	736.1	771.9	814.7	866.3	903.9	939.1	987.9	1021.3	1054.7	1099.6
17.5°	693.2	732.1	776.9	832.4	875.5	926.1	979.0	1017.6	1062.6	1109.6	1150.2
20°	684.5	729.8	779.8	834.4	889.3	944.3	995.5	1041.6	1088.1	1142.4	1175.8
22.5°	675.8	720.5	772.5	830.5	889.5	947.4	1005.4	1059.6	1111.8	1166.6	1209.3
25°	657.2	710.3	766.8	825.9	884.2	947.8	1017.1	1077.4	1142.1	1198.5	1238.9
27.5°	638.4	687.1	743.2	803.3	868.0	943.3	1024.7	1093.4	1158.1	1198.5	1211.2
30°	621.4	673.0	724.5	785.5	855.6	939.7	1026.2	1104.8	1157.9	1175.4	1162.4
32.5°	604.2	650.9	702.0	764.5	838.9	930.7	1028.1	1098.0	1130.0	1116.5	1063.3
35°	573.8	615.9	665.4	727.9	813.5	925.7	1020.1	1067.5	1059.5	983.7	883.5
37.5°	541.2	575.6	621.4	686.7	787.1	906.0	985.6	992.6	924.3	807.9	692.2
40°	515.5	546.4	593.5	661.8	766.8	886.6	950.9	922.7	816.8	687.2	590.7
42.5°	490.5	516.6	561.9	635.6	747.3	860.2	899.2	837.7	715.6	593.0	505.3
45°	448.1	472.7	518.2	593.8	707.6	809.5	804.4	697.6	575.3	476.7	403.9
47.5°	408.0	429.4	472.2	549.3	660.9	733.6	685.4	571.8	468.0	389.0	337.0
50°	379.6	400.8	443.3	519.4	623.5	676.6	607.8	498.2	403.2	337.7	296.4
52.5°	352.4	373.1	412.0	486.2	578.4	610.1	536.1	434.6	355.5	298.9	263.4
55°	314.3	330.1	365.0	436.0	504.9	512.1	437.2	352.3	287.0	247.6	223.3
57.5°	275.6	289.1	323.6	380.2	428.5	424.7	353.6	280.2	236.2	206.9	189.3
60°	250.3	263.6	294.0	342.5	379.0	366.2	301.0	241.9	204.2	182.7	168.7
62.5°	226.8	237.2	265.6	301.0	327.3	312.8	257.3	208.3	178.5	160.3	149.2
65°	192.7	201.1	223.9	242.4	257.0	243.0	196.9	163.0	141.4	128.7	121.0
67.5°	160.3	165.6	180.1	186.7	197.0	181.7	148.1	125.3	113.0	102.3	97.0
70°	139.9	143.9	151.4	156.9	159.6	143.9	118.9	102.3	92.0	84.4	81.0
72.5°	119.5	122.9	124.5	129.0	127.5	112.7	95.6	82.4	74.9	69.8	65.5
75°	91.3	92.8	91.3	89.5	85.6	75.3	63.5	56.7	51.3	48.9	47.4
77.5°	66.5	66.1	64.0	61.2	54.4	47.9	41.6	39.3	37.0	35.6	35.2
80°	51.3	50.1	48.2	43.7	37.9	33.4	31.8	30.3	29.5	27.9	27.6
82.5°	38.2	37.5	34.4	30.6	26.5	24.4	23.1	22.6	21.6	20.9	20.8
85°	20.4	19.4	16.1	13.9	13.4	12.8	12.4	12.4	11.2	10.9	10.9
87.5°	6.9	5.6	5.7	5.1	5.3	5.1	5.6	5.4	5.4	5.5	5.1
90°	1.8	2.7	4.0	5.0	5.9	7.2	8.6	9.9	11.3	10.9	11.3
92.5°	8.3	12.1	15.6	19.4	26.1	37.9	57.4	76.4	69.5	52.4	38.0
95°	16.7	21.7	29.4	41.1	58.7	97.1	164.5	238.6	267.9	217.3	162.6
97.5°	26.7	30.6	37.2	48.8	67.9	104.6	180.5	304.0	415.3	444.3	405.5
100°	33.9	37.1	43.4	54.2	71.9	103.5	170.3	289.1	427.9	516.9	532.7
102.5°	41.8	44.7	50.6	60.4	76.5	104.9	161.7	267.5	404.4	520.5	575.0
105°	53.8	56.5	61.9	70.5	84.5	108.9	155.4	240.8	363.3	493.0	587.4
107.5°	65.9	68.5	73.8	81.9	94.9	116.3	155.0	223.9	326.9	444.7	551.8
110°	74.5	76.8	81.8	89.4	102.1	122.5	156.8	217.3	306.3	414.3	517.8



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	82.5	84.8	89.8	97.4	109.7	128.6	160.4	213.7	292.6	387.9	484.2
115°	94.4	97.1	101.6	109.3	121.5	138.7	166.3	212.4	277.9	356.1	439.7
117.5°	106.2	108.4	112.6	121.2	132.5	149.5	174.0	213.2	269.2	336.8	407.3
120°	113.4	115.7	120.2	128.8	140.1	156.3	179.8	214.6	265.2	326.7	390.4
122.5°	120.3	122.6	127.4	135.6	147.7	163.6	185.3	217.1	262.7	318.4	377.0
125°	129.7	132.4	137.4	145.9	158.1	174.0	193.8	220.9	259.4	307.7	359.2
127.5°	137.6	141.0	146.0	155.5	167.7	183.0	200.9	225.3	257.7	298.3	343.6
130°	142.4	146.4	151.8	161.3	173.5	188.4	205.6	228.1	256.7	293.3	333.9
132.5°	146.3	150.8	157.2	166.8	178.6	193.1	209.9	230.4	256.3	288.5	324.9
135°	152.7	157.7	164.5	174.0	186.2	200.2	215.6	233.6	255.7	282.4	312.7
137.5°	158.8	163.7	170.9	180.3	191.5	205.0	219.7	235.8	254.8	277.1	301.6
140°	163.1	167.6	174.8	183.9	195.2	208.3	221.9	237.2	254.4	273.8	295.1
142.5°	167.1	172.0	178.5	187.5	198.1	210.8	224.0	238.3	253.7	270.9	288.9
145°	173.5	177.6	184.3	192.0	202.4	214.2	226.4	239.0	252.5	267.0	281.5
147.5°	180.0	184.0	189.9	197.3	206.1	216.9	227.8	239.0	250.9	263.2	275.4
150°	184.3	188.0	193.8	200.2	208.3	218.7	228.1	239.0	249.4	260.7	271.1
152.5°	188.7	192.3	197.5	203.0	210.8	219.8	228.9	238.0	247.6	257.9	267.1
155°	195.7	198.4	202.9	207.9	214.2	221.9	229.1	236.8	244.5	253.5	261.2
157.5°	201.6	203.7	207.8	212.0	216.9	223.0	229.6	235.2	241.6	248.6	254.8
160°	205.6	207.4	211.0	214.2	218.7	224.1	229.6	234.5	239.5	245.3	251.2
162.5°	208.8	210.3	213.2	215.9	219.8	224.5	229.2	233.1	237.3	242.1	246.9
165°	213.3	214.2	216.4	218.2	221.4	225.0	228.1	230.9	234.1	237.7	241.3
167.5°	216.9	217.3	219.0	220.3	222.3	224.9	227.4	228.7	230.8	233.5	236.4
170°	218.7	219.1	220.5	221.4	222.3	224.6	226.4	227.3	228.6	230.9	233.1
172.5°	220.5	220.6	221.6	222.1	222.7	224.6	226.0	226.2	226.8	228.4	230.3
175°	222.3	221.9	222.8	222.8	223.2	224.1	225.0	224.6	224.6	225.5	226.4
177.5°	223.2	222.8	223.2	223.2	223.2	223.6	224.3	223.6	223.2	223.6	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2	223.2



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	747.7	747.7	748.6	752.3	752.7	755.9	754.9
5°	821.7	827.4	829.6	838.7	844.1	846.5	841.7
7.5°	912.2	928.4	936.2	945.7	954.1	956.7	950.1
10°	978.3	995.2	1009.5	1018.3	1026.5	1031.9	1038.9
12.5°	1042.0	1063.0	1076.5	1088.9	1097.3	1104.3	1105.4
15°	1111.4	1143.0	1167.0	1184.6	1193.3	1197.9	1196.1
17.5°	1181.4	1210.6	1227.7	1245.6	1257.8	1258.5	1258.9
20°	1221.0	1249.5	1269.2	1282.5	1296.2	1295.6	1298.6
22.5°	1247.4	1269.9	1285.0	1294.7	1299.3	1297.0	1297.7
25°	1259.8	1266.5	1263.8	1248.2	1244.4	1230.1	1232.5
27.5°	1196.0	1164.4	1131.8	1089.7	1056.6	1030.2	1031.5
30°	1109.3	1053.4	989.8	936.4	888.4	875.0	846.5
32.5°	988.2	904.4	829.8	780.1	738.9	727.7	702.8
35°	782.8	701.5	624.7	578.6	560.4	535.0	534.6
37.5°	608.5	536.9	496.3	461.7	443.5	428.1	426.6
40°	511.9	456.1	425.4	400.5	382.6	371.1	368.4
42.5°	444.4	399.3	370.5	355.1	341.4	335.4	331.0
45°	362.9	332.6	312.5	298.6	292.2	287.6	285.2
47.5°	303.6	283.2	269.6	260.3	255.1	250.3	251.6
50°	271.2	254.6	244.5	235.8	231.8	228.5	228.8
52.5°	245.3	230.3	222.2	215.9	211.0	208.6	207.4
55°	208.2	198.8	190.5	186.0	183.2	179.9	179.0
57.5°	177.5	170.2	163.6	158.4	157.8	154.6	155.0
60°	157.2	151.1	145.6	142.9	140.8	138.1	138.9
62.5°	140.5	135.3	130.3	128.1	126.0	124.0	124.4
65°	115.0	110.1	107.1	105.9	105.0	104.1	103.1
67.5°	91.7	88.6	86.7	84.1	82.3	82.0	81.0
70°	77.1	73.1	69.8	66.5	65.5	65.2	65.5
72.5°	61.8	59.3	58.4	56.7	56.6	55.8	56.3
75°	46.4	45.6	44.9	43.7	43.7	43.7	43.7
77.5°	34.2	33.7	33.4	33.0	32.8	32.3	32.3
80°	26.7	26.4	25.8	25.8	25.5	25.8	25.5
82.5°	20.1	20.1	19.5	19.5	19.2	19.0	19.2
85°	10.3	10.0	10.6	10.0	10.3	9.7	10.3
87.5°	5.2	5.4	5.3	5.2	5.1	5.6	5.1
90°	11.7	12.2	13.1	12.7	13.1	13.5	13.1
92.5°	30.2	26.7	24.3	23.5	22.1	22.6	21.8
95°	110.3	86.3	70.0	61.5	57.4	54.2	52.4
97.5°	324.8	266.5	212.5	179.1	158.8	146.6	142.7
100°	496.1	443.2	379.1	333.4	300.5	282.9	283.3
102.5°	573.9	543.0	502.3	466.8	440.7	426.0	415.6
105°	632.6	641.2	629.4	608.6	591.4	577.0	574.7
107.5°	625.2	664.7	680.8	681.2	675.4	670.5	666.4
110°	600.9	657.9	689.5	702.2	705.8	704.9	703.9



TEST NUMBER: P332278-927

CATALOG NUMBER: S123RDIP-S560D585U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	569.1	633.0	673.6	696.7	708.0	711.4	711.5
115°	518.2	584.7	633.9	667.8	687.7	696.7	699.0
117.5°	475.2	534.9	584.9	620.2	642.9	656.0	659.0
120°	451.4	505.6	551.3	586.9	612.3	623.1	625.8
122.5°	432.2	482.4	524.8	556.6	579.3	591.3	594.7
125°	408.4	451.9	488.0	516.9	536.8	548.1	551.3
127.5°	387.6	426.7	459.6	485.4	502.3	512.5	515.5
130°	374.5	411.1	441.9	465.9	482.1	491.6	495.2
132.5°	362.3	396.3	425.6	448.1	464.4	472.8	475.3
135°	344.8	374.1	399.9	422.0	435.5	443.7	446.9
137.5°	327.9	353.2	375.5	394.1	407.8	414.7	416.8
140°	318.1	339.8	359.2	376.4	389.0	396.2	395.8
142.5°	308.7	327.5	344.4	359.0	370.3	376.8	376.3
145°	296.4	310.9	324.0	335.3	344.8	348.4	349.3
147.5°	287.2	299.0	308.2	316.8	323.2	326.7	327.0
150°	281.5	291.0	299.6	306.3	311.3	314.0	314.0
152.5°	276.1	284.5	291.6	296.9	301.6	303.2	303.2
155°	268.4	275.2	280.6	284.6	288.3	289.1	289.6
157.5°	260.9	266.2	270.4	273.9	276.6	277.3	277.3
160°	256.2	260.7	263.9	267.0	269.7	269.7	269.3
162.5°	251.1	255.3	258.1	260.2	262.5	262.5	262.1
165°	244.0	247.2	249.4	251.2	253.0	252.5	252.5
167.5°	238.4	240.3	241.9	242.7	244.0	243.5	243.5
170°	234.5	236.3	237.2	237.7	238.6	238.1	238.1
172.5°	231.2	232.7	233.2	233.3	234.2	233.5	233.1
175°	226.8	227.8	227.8	227.8	228.1	227.8	227.3
177.5°	224.3	224.7	224.7	224.3	224.7	223.9	223.9
180°	223.2	223.2	223.2	223.2	223.2	223.2	223.2

(END OF REPORT)