

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332284-927

Luminaire Tested: **S123RDIP-S560D805U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332284-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D805U927-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4069.0 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	88	85	82	79	71	68	66	57	56	54	45	44	43	38
2	89	82	76	71	81	75	70	66	62	59	56	51	48	46	40	39	37	32
3	81	72	65	60	74	66	60	55	55	51	47	45	42	40	36	34	32	28
4	74	64	57	51	68	59	52	47	50	45	41	41	37	34	33	30	28	24
5	68	57	50	44	62	53	46	41	45	39	35	37	33	30	30	27	25	21
6	63	52	44	38	58	48	41	36	40	35	31	33	30	27	27	24	22	19
7	58	47	39	34	53	43	36	32	37	31	28	30	27	24	25	22	20	17
8	54	42	35	30	50	39	33	28	33	28	25	28	24	21	23	20	18	15
9	51	39	31	27	46	36	29	25	31	26	22	26	22	19	21	18	16	14
10	47	36	29	24	43	33	27	23	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7629	7629	7629	7629
5°	9095	7662	6748	7662
10°	11355	7618	6096	7618
15°	13329	7540	5558	7540
20°	14875	7424	5102	7424
25°	14638	7301	4822	7301
30°	10521	7188	4533	7188
35°	7025	7041	4346	7041
40°	5176	6864	4154	6864
45°	4341	6555	3962	6555
50°	3831	6149	3699	6149
55°	3359	5684	3337	5684
60°	2990	5240	3057	5240
65°	2626	4760	2845	4760
70°	2061	4337	2596	4337
75°	1817	3785	2371	3785
80°	1581	3217	2331	3217
85°	1272	2581	2470	2581



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.7	1.7
10°-20°	217.8	5.4
20°-30°	342.1	8.4
30°-40°	356.9	8.8
40°-50°	305.5	7.5
50°-60°	232.8	5.7
60°-70°	149.2	3.7
70°-80°	71.8	1.8
80°-90°	21.4	0.5
90°-100°	170.3	4.2
100°-110°	482.1	11.8
110°-120°	474.3	11.7
120°-130°	378.3	9.3
130°-140°	298.3	7.3
140°-150°	222.6	5.5
150°-160°	155.2	3.8
160°-170°	91.2	2.2
170°-180°	29.7	0.7
0°-30°	629.6	15.5
0°-40°	986.5	24.2
0°-60°	1524.8	37.5
0°-90°	1767.1	43.4
90°-120°	1126.7	27.7
90°-150°	2025.9	49.8
90°-180°	2302.0	56.6
0°-180°	4069.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	709	709	709	709	709	
5°	842	709	624	709	842	87
15°	1196	677	499	677	1196	339
25°	1232	615	406	615	1232	530
35°	535	536	331	536	535	351
45°	285	431	260	431	285	224
55°	179	303	178	303	179	162
65°	103	187	112	187	103	101
75°	44	91	57	91	44	47
85°	10	21	20	21	10	12
90°	18	1	18	1	18	10
95°	72	21	72	21	72	129
105°	788	72	788	72	788	777
115°	958	127	958	127	958	931
125°	756	176	756	176	756	685
135°	612	207	612	207	612	475
145°	479	236	479	236	479	304
155°	397	268	397	268	397	185
165°	346	293	346	293	346	99
175°	312	305	312	305	312	30
180°	306	306	306	306	306	



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	754.9	755.9	752.7	752.3	748.6	747.7	747.7	742.5	739.3	735.2	732.8
5°	841.7	846.5	844.1	838.7	829.6	827.4	821.7	812.5	802.2	789.5	783.5
7.5°	950.1	956.7	954.1	945.7	936.2	928.4	912.2	897.1	875.9	857.4	841.5
10°	1038.9	1031.9	1026.5	1018.3	1009.5	995.2	978.3	954.9	927.9	906.7	883.0
12.5°	1105.4	1104.3	1097.3	1088.9	1076.5	1063.0	1042.0	1013.6	982.2	951.5	924.5
15°	1196.1	1197.9	1193.3	1184.6	1167.0	1143.0	1111.4	1099.6	1054.7	1021.3	987.9
17.5°	1258.9	1258.5	1257.8	1245.6	1227.7	1210.6	1181.4	1150.2	1109.6	1062.6	1017.6
20°	1298.6	1295.6	1296.2	1282.5	1269.2	1249.5	1221.0	1175.8	1142.4	1088.1	1041.6
22.5°	1297.7	1297.0	1299.3	1294.7	1285.0	1269.9	1247.4	1209.3	1166.6	1111.8	1059.6
25°	1232.5	1230.1	1244.4	1248.2	1263.8	1266.5	1259.8	1238.9	1198.5	1142.1	1077.4
27.5°	1031.5	1030.2	1056.6	1089.7	1131.8	1164.4	1196.0	1211.2	1198.5	1158.1	1093.4
30°	846.5	875.0	888.4	936.4	989.8	1053.4	1109.3	1162.4	1175.4	1157.9	1104.8
32.5°	702.8	727.7	738.9	780.1	829.8	904.4	988.2	1063.3	1116.5	1130.0	1098.0
35°	534.6	535.0	560.4	578.6	624.7	701.5	782.8	883.5	983.7	1059.5	1067.5
37.5°	426.6	428.1	443.5	461.7	496.3	536.9	608.5	692.2	807.9	924.3	992.6
40°	368.4	371.1	382.6	400.5	425.4	456.1	511.9	590.7	687.2	816.8	922.7
42.5°	331.0	335.4	341.4	355.1	370.5	399.3	444.4	505.3	593.0	715.6	837.7
45°	285.2	287.6	292.2	298.6	312.5	332.6	362.9	403.9	476.7	575.3	697.6
47.5°	251.6	250.3	255.1	260.3	269.6	283.2	303.6	337.0	389.0	468.0	571.8
50°	228.8	228.5	231.8	235.8	244.5	254.6	271.2	296.4	337.7	403.2	498.2
52.5°	207.4	208.6	211.0	215.9	222.2	230.3	245.3	263.4	298.9	355.5	434.6
55°	179.0	179.9	183.2	186.0	190.5	198.8	208.2	223.3	247.6	287.0	352.3
57.5°	155.0	154.6	157.8	158.4	163.6	170.2	177.5	189.3	206.9	236.2	280.2
60°	138.9	138.1	140.8	142.9	145.6	151.1	157.2	168.7	182.7	204.2	241.9
62.5°	124.4	124.0	126.0	128.1	130.3	135.3	140.5	149.2	160.3	178.5	208.3
65°	103.1	104.1	105.0	105.9	107.1	110.1	115.0	121.0	128.7	141.4	163.0
67.5°	81.0	82.0	82.3	84.1	86.7	88.6	91.7	97.0	102.3	113.0	125.3
70°	65.5	65.2	65.5	66.5	69.8	73.1	77.1	81.0	84.4	92.0	102.3
72.5°	56.3	55.8	56.6	56.7	58.4	59.3	61.8	65.5	69.8	74.9	82.4
75°	43.7	43.7	43.7	43.7	44.9	45.6	46.4	47.4	48.9	51.3	56.7
77.5°	32.3	32.3	32.8	33.0	33.4	33.7	34.2	35.2	35.6	37.0	39.3
80°	25.5	25.8	25.5	25.8	25.8	26.4	26.7	27.6	27.9	29.5	30.3
82.5°	19.2	19.0	19.2	19.5	19.5	20.1	20.1	20.8	20.9	21.6	22.6
85°	10.3	9.7	10.3	10.0	10.6	10.0	10.3	10.9	10.9	11.2	12.4
87.5°	6.0	6.7	6.0	6.1	6.3	6.3	6.1	6.0	6.3	6.3	6.1
90°	18.0	18.6	18.0	17.3	18.0	16.7	16.1	15.4	14.9	15.4	13.6
92.5°	29.9	31.0	30.3	32.2	33.4	36.5	41.4	52.1	71.9	95.2	104.8
95°	71.9	74.3	78.7	84.2	96.0	118.3	151.1	223.0	297.9	367.3	327.0
97.5°	195.6	200.9	217.6	245.5	291.2	365.3	445.2	555.8	609.0	569.2	416.7
100°	388.3	387.7	411.9	457.1	519.6	607.6	680.0	730.2	708.5	586.5	396.4
102.5°	569.7	583.9	604.1	639.9	688.6	744.3	786.6	788.1	713.5	554.3	366.6
105°	787.8	790.9	810.7	834.2	862.8	878.8	867.0	805.2	675.7	498.0	330.1
107.5°	913.4	919.1	925.8	933.7	933.2	911.2	856.9	756.4	609.6	448.1	306.8
110°	965.0	966.1	967.4	962.4	945.2	901.7	823.7	709.8	567.9	419.9	297.9



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	975.3	975.1	970.4	955.1	923.3	867.6	780.1	663.7	531.8	401.1	292.9
115°	958.1	955.1	942.6	915.4	868.9	801.5	710.3	602.6	488.1	380.9	291.1
117.5°	903.4	899.1	881.3	850.1	801.7	733.2	651.4	558.4	461.7	369.0	292.2
120°	857.8	854.1	839.2	804.5	755.6	693.1	618.7	535.1	447.8	363.5	294.2
122.5°	815.2	810.5	794.1	762.9	719.5	661.3	592.5	516.8	436.4	360.1	297.6
125°	755.6	751.2	735.8	708.5	668.9	619.3	559.9	492.3	421.8	355.5	302.9
127.5°	706.5	702.6	688.6	665.3	630.0	584.9	531.2	471.1	408.9	353.3	308.8
130°	678.8	673.8	660.8	638.6	605.7	563.6	513.4	457.7	402.0	351.8	312.8
132.5°	651.6	648.1	636.6	614.3	583.4	543.3	496.6	445.3	395.5	351.3	315.8
135°	612.5	608.2	597.1	578.5	548.1	512.8	472.5	428.6	387.1	350.5	320.2
137.5°	571.3	568.5	559.0	540.2	514.7	484.1	449.4	413.4	379.8	349.2	323.2
140°	542.6	543.2	533.2	515.9	492.3	465.7	436.0	404.4	375.3	348.7	325.2
142.5°	515.8	516.4	507.5	492.1	472.1	448.9	423.1	396.0	371.4	347.7	326.6
145°	478.7	477.5	472.5	459.5	444.1	426.1	406.3	385.9	366.1	346.2	327.6
147.5°	448.3	447.8	443.1	434.3	422.6	409.8	393.8	377.6	360.8	343.9	327.6
150°	430.5	430.5	426.7	419.9	410.6	398.9	385.9	371.6	357.4	341.9	327.6
152.5°	415.6	415.6	413.4	407.0	399.7	389.9	378.4	366.1	353.4	339.4	326.1
155°	397.0	396.4	395.1	390.1	384.6	377.2	367.9	358.0	347.5	335.1	324.6
157.5°	380.0	380.2	379.1	375.4	370.6	364.8	357.6	349.3	340.8	331.2	322.4
160°	369.2	369.7	369.7	366.1	361.7	357.4	351.2	344.4	336.3	328.3	321.5
162.5°	359.3	359.8	359.8	356.6	353.8	349.9	344.2	338.4	331.8	325.3	319.5
165°	346.2	346.2	346.8	344.4	341.9	338.8	334.5	330.7	325.7	320.8	316.5
167.5°	333.8	333.8	334.5	332.7	331.6	329.4	326.9	324.0	320.0	316.4	313.5
170°	326.4	326.4	327.0	325.7	325.2	323.9	321.5	319.6	316.5	313.4	311.6
172.5°	319.5	320.0	321.1	319.8	319.7	318.9	317.0	315.6	313.0	310.9	310.1
175°	311.6	312.1	312.8	312.1	312.1	312.1	310.9	310.3	309.0	307.8	307.8
177.5°	307.0	307.0	307.9	307.4	307.9	307.9	307.4	307.0	306.4	305.9	306.4
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	731.8	731.1	727.7	723.8	718.7	715.3	712.6	711.2	706.9	701.5	697.8
5°	777.1	767.9	758.3	746.4	735.5	724.3	717.3	709.1	699.1	687.9	679.9
7.5°	825.5	807.6	788.4	768.6	748.9	731.3	715.8	702.5	686.6	670.5	659.2
10°	862.6	836.5	809.5	781.9	756.7	733.1	714.9	697.0	677.9	659.3	645.4
12.5°	896.4	862.1	830.9	796.9	764.8	736.5	710.3	689.2	666.2	646.5	630.6
15°	939.1	903.9	866.3	814.7	771.9	736.1	704.3	676.6	648.7	624.5	609.0
17.5°	979.0	926.1	875.5	832.4	776.9	732.1	693.2	660.2	629.6	603.9	584.8
20°	995.5	944.3	889.3	834.4	779.8	729.8	684.5	648.1	616.2	587.1	569.5
22.5°	1005.4	947.4	889.5	830.5	772.5	720.5	675.8	635.7	601.2	573.5	551.8
25°	1017.1	947.8	884.2	825.9	766.8	710.3	657.2	614.7	577.4	548.0	524.9
27.5°	1024.7	943.3	868.0	803.3	743.2	687.1	638.4	593.3	555.5	524.3	499.6
30°	1026.2	939.7	855.6	785.5	724.5	673.0	621.4	578.3	538.3	505.2	482.1
32.5°	1028.1	930.7	838.9	764.5	702.0	650.9	604.2	563.0	522.0	489.4	465.9
35°	1020.1	925.7	813.5	727.9	665.4	615.9	573.8	535.8	495.5	463.9	440.0
37.5°	985.6	906.0	787.1	686.7	621.4	575.6	541.2	508.2	471.2	437.1	414.5
40°	950.9	886.6	766.8	661.8	593.5	546.4	515.5	488.5	452.7	420.8	396.6
42.5°	899.2	860.2	747.3	635.6	561.9	516.6	490.5	465.2	433.8	401.4	378.6
45°	804.4	809.5	707.6	593.8	518.2	472.7	448.1	430.6	402.7	376.0	352.6
47.5°	685.4	733.6	660.9	549.3	472.2	429.4	408.0	392.6	373.8	347.6	326.3
50°	607.8	676.6	623.5	519.4	443.3	400.8	379.6	367.2	350.8	330.1	309.8
52.5°	536.1	610.1	578.4	486.2	412.0	373.1	352.4	342.1	329.2	309.7	291.4
55°	437.2	512.1	504.9	436.0	365.0	330.1	314.3	302.9	294.0	279.5	264.9
57.5°	353.6	424.7	428.5	380.2	323.6	289.1	275.6	266.9	261.1	250.2	236.7
60°	301.0	366.2	379.0	342.5	294.0	263.6	250.3	243.4	238.8	230.0	219.7
62.5°	257.3	312.8	327.3	301.0	265.6	237.2	226.8	220.1	217.0	209.4	200.3
65°	196.9	243.0	257.0	242.4	223.9	201.1	192.7	186.9	184.2	179.9	173.3
67.5°	148.1	181.7	197.0	186.7	180.1	165.6	160.3	157.2	154.7	151.9	146.2
70°	118.9	143.9	159.6	156.9	151.4	143.9	139.9	137.8	135.3	132.9	128.0
72.5°	95.6	112.7	127.5	129.0	124.5	122.9	119.5	118.6	117.1	114.2	111.5
75°	63.5	75.3	85.6	89.5	91.3	92.8	91.3	91.0	90.7	88.3	86.7
77.5°	41.6	47.9	54.4	61.2	64.0	66.1	66.5	67.7	66.9	65.6	64.9
80°	31.8	33.4	37.9	43.7	48.2	50.1	51.3	51.9	51.6	51.3	50.1
82.5°	23.1	24.4	26.5	30.6	34.4	37.5	38.2	38.0	38.7	38.9	37.9
85°	12.4	12.8	13.4	13.9	16.1	19.4	20.4	20.9	21.5	21.5	19.7
87.5°	6.3	5.6	5.7	5.5	5.9	5.9	7.1	8.0	8.5	7.8	8.2
90°	11.8	9.9	8.1	6.8	5.5	3.7	2.5	1.3	2.5	3.7	5.5
92.5°	78.7	52.0	35.8	26.6	21.5	16.6	11.4	7.7	11.4	16.6	21.5
95°	225.5	133.2	80.5	56.3	40.2	29.7	22.9	21.1	22.9	29.7	40.2
97.5°	247.4	143.3	93.0	66.9	51.0	41.9	36.5	35.9	36.5	41.9	51.0
100°	233.5	141.8	98.5	74.3	59.5	50.8	46.4	45.9	46.4	50.8	59.5
102.5°	221.6	143.8	104.9	82.8	69.4	61.2	57.4	56.2	57.4	61.2	69.4
105°	213.0	149.2	115.8	96.6	84.8	77.4	73.7	71.9	73.7	77.4	84.8
107.5°	212.5	159.4	130.1	112.3	101.2	93.9	90.3	88.4	90.3	93.9	101.2
110°	214.9	167.9	140.0	122.6	112.1	105.3	102.2	100.4	102.2	105.3	112.1



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	219.8	176.3	150.4	133.6	123.0	116.2	113.1	111.2	113.1	116.2	123.0
115°	227.9	190.1	166.6	149.9	139.3	133.2	129.4	127.0	129.4	133.2	139.3
117.5°	238.6	204.9	181.6	166.1	154.3	148.6	145.5	142.7	145.5	148.6	154.3
120°	246.5	214.3	192.0	176.5	164.8	158.5	155.4	153.6	155.4	158.5	164.8
122.5°	253.9	224.2	202.4	185.9	174.7	167.9	164.9	163.0	164.9	167.9	174.7
125°	265.7	238.4	216.7	200.0	188.3	181.5	177.8	176.5	177.8	181.5	188.3
127.5°	275.4	250.8	229.9	213.2	200.2	193.2	188.6	186.8	188.6	193.2	200.2
130°	281.8	258.3	237.8	221.1	208.1	200.7	195.1	193.2	195.1	200.7	208.1
132.5°	287.7	264.7	244.8	228.5	215.6	206.6	200.6	198.2	200.6	206.6	215.6
135°	295.4	274.3	255.2	238.4	225.5	216.2	209.4	206.8	209.4	216.2	225.5
137.5°	301.1	281.1	262.6	247.1	234.2	224.3	217.6	215.0	217.6	224.3	234.2
140°	304.1	285.5	267.5	252.1	239.7	229.8	223.6	220.5	223.6	229.8	239.7
142.5°	307.0	289.0	271.5	257.1	244.6	235.8	229.0	226.4	229.0	235.8	244.6
145°	310.3	293.6	277.5	263.2	252.7	243.4	237.8	236.0	237.8	243.4	252.7
147.5°	312.3	297.3	282.6	270.4	260.2	252.2	246.8	245.7	246.8	252.2	260.2
150°	312.8	299.8	285.5	274.3	265.7	257.6	252.7	252.1	252.7	257.6	265.7
152.5°	313.8	301.3	289.0	278.3	270.7	263.6	258.6	258.5	258.6	263.6	270.7
155°	314.0	304.1	293.6	284.9	278.1	271.9	268.2	268.2	268.2	271.9	278.1
157.5°	314.7	305.7	297.3	290.6	284.8	279.3	276.3	275.8	276.3	279.3	284.8
160°	314.7	307.2	299.8	293.6	289.2	284.3	281.8	281.8	281.8	284.3	289.2
162.5°	314.1	307.7	301.3	296.0	292.2	288.3	286.3	286.3	286.3	288.3	292.2
165°	312.8	308.4	303.5	299.1	296.7	293.6	292.3	292.9	292.3	293.6	296.7
167.5°	311.8	308.3	304.8	302.0	300.2	297.9	297.3	298.0	297.3	297.9	300.2
170°	310.3	307.8	304.8	303.5	302.2	300.4	299.8	301.0	299.8	300.4	302.2
172.5°	309.8	307.8	305.2	304.4	303.7	302.4	302.2	303.0	302.2	302.4	303.7
175°	308.4	307.2	305.9	305.3	305.3	304.1	304.8	305.3	304.8	304.1	305.3
177.5°	307.4	306.4	305.9	305.9	305.9	305.5	305.9	306.4	305.9	305.5	305.9
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	696.6	693.5	691.3	686.4	683.3	679.9	676.5	678.7	678.4	678.2	678.2
5°	673.3	666.3	660.0	651.7	646.6	640.2	635.3	634.8	636.0	631.7	629.3
7.5°	650.1	640.6	631.5	622.5	612.9	605.2	600.5	598.3	595.2	592.6	589.8
10°	633.8	622.7	613.8	602.6	592.3	583.2	577.4	573.5	571.3	569.2	565.3
12.5°	617.1	606.1	594.8	582.2	572.4	561.8	557.5	553.1	549.0	546.6	541.2
15°	592.6	578.3	566.5	553.1	542.2	531.9	525.9	517.1	515.8	512.8	507.3
17.5°	568.0	552.5	536.2	526.3	514.0	503.3	494.0	491.1	482.4	479.1	474.4
20°	548.6	534.3	521.9	508.8	490.9	480.9	473.6	469.7	462.7	458.4	455.4
22.5°	531.9	517.3	503.0	487.7	472.9	461.8	456.4	450.3	446.5	440.5	437.2
25°	507.9	492.2	474.8	458.4	447.8	439.3	430.9	425.4	419.9	417.2	411.1
27.5°	480.1	463.7	447.5	435.1	422.0	413.6	405.9	401.1	394.5	389.9	386.6
30°	464.9	445.4	431.5	420.3	403.5	395.7	389.9	383.8	379.0	374.1	370.7
32.5°	447.1	429.4	416.1	402.3	389.4	380.9	373.4	368.0	363.9	359.3	356.0
35°	419.3	404.5	390.8	376.8	367.4	358.6	349.8	345.3	341.4	337.1	334.1
37.5°	394.2	380.3	367.3	354.1	342.5	335.3	328.2	324.7	319.4	316.6	313.5
40°	378.7	365.0	351.1	338.3	326.1	320.8	314.3	309.2	304.4	302.2	298.9
42.5°	361.7	348.0	336.3	322.5	312.6	305.1	299.3	293.7	290.0	286.9	285.0
45°	336.5	324.3	312.8	299.2	289.8	283.4	276.7	271.6	268.2	266.1	262.8
47.5°	312.0	299.9	288.2	276.3	267.2	259.9	253.3	249.6	245.3	242.6	240.3
50°	294.3	283.4	270.9	260.0	251.0	243.7	238.2	233.6	229.7	226.3	224.8
52.5°	278.1	266.4	255.6	245.5	235.9	227.6	222.7	217.9	214.9	211.0	209.3
55°	251.2	240.0	230.9	220.9	211.5	204.5	198.4	194.2	191.2	186.9	184.5
57.5°	226.0	215.9	205.1	196.5	186.7	180.9	175.8	170.0	166.4	163.0	160.7
60°	209.1	197.5	188.1	179.9	171.4	163.8	159.3	154.7	150.8	147.4	145.4
62.5°	191.3	181.3	172.4	163.4	155.7	149.0	143.8	139.9	136.5	134.4	132.2
65°	164.1	156.3	147.2	139.9	132.6	127.8	123.5	120.2	117.7	116.2	114.4
67.5°	139.2	131.5	123.6	116.4	111.5	107.8	105.0	102.2	101.0	99.0	97.8
70°	122.9	115.0	108.1	102.6	97.7	95.0	93.2	91.0	89.8	87.4	86.2
72.5°	105.2	99.5	94.4	89.9	86.0	83.6	81.3	78.7	76.7	74.1	72.8
75°	82.9	77.7	73.8	70.7	68.3	65.0	61.6	58.9	58.0	57.0	56.7
77.5°	61.3	58.1	55.2	52.7	49.7	47.2	46.5	45.9	45.7	45.2	45.2
80°	48.2	45.2	43.1	40.1	38.3	38.3	38.3	37.6	37.9	37.9	37.9
82.5°	35.9	33.0	31.9	30.8	30.5	30.7	30.7	30.8	30.7	31.1	30.9
85°	18.5	18.8	19.4	19.1	19.4	19.4	20.0	19.7	20.0	19.4	20.0
87.5°	8.2	9.1	9.7	10.4	11.0	11.1	11.2	11.3	11.7	11.8	12.1
90°	6.8	8.1	9.9	11.8	13.6	15.4	14.9	15.4	16.1	16.7	18.0
92.5°	26.6	35.8	52.0	78.7	104.8	95.2	71.9	52.1	41.4	36.5	33.4
95°	56.3	80.5	133.2	225.5	327.0	367.3	297.9	223.0	151.1	118.3	96.0
97.5°	66.9	93.0	143.3	247.4	416.7	569.2	609.0	555.8	445.2	365.3	291.2
100°	74.3	98.5	141.8	233.5	396.4	586.5	708.5	730.2	680.0	607.6	519.6
102.5°	82.8	104.9	143.8	221.6	366.6	554.3	713.5	788.1	786.6	744.3	688.6
105°	96.6	115.8	149.2	213.0	330.1	498.0	675.7	805.2	867.0	878.8	862.8
107.5°	112.3	130.1	159.4	212.5	306.8	448.1	609.6	756.4	856.9	911.2	933.2
110°	122.6	140.0	167.9	214.9	297.9	419.9	567.9	709.8	823.7	901.7	945.2



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	133.6	150.4	176.3	219.8	292.9	401.1	531.8	663.7	780.1	867.6	923.3
115°	149.9	166.6	190.1	227.9	291.1	380.9	488.1	602.6	710.3	801.5	868.9
117.5°	166.1	181.6	204.9	238.6	292.2	369.0	461.7	558.4	651.4	733.2	801.7
120°	176.5	192.0	214.3	246.5	294.2	363.5	447.8	535.1	618.7	693.1	755.6
122.5°	185.9	202.4	224.2	253.9	297.6	360.1	436.4	516.8	592.5	661.3	719.5
125°	200.0	216.7	238.4	265.7	302.9	355.5	421.8	492.3	559.9	619.3	668.9
127.5°	213.2	229.9	250.8	275.4	308.8	353.3	408.9	471.1	531.2	584.9	630.0
130°	221.1	237.8	258.3	281.8	312.8	351.8	402.0	457.7	513.4	563.6	605.7
132.5°	228.5	244.8	264.7	287.7	315.8	351.3	395.5	445.3	496.6	543.3	583.4
135°	238.4	255.2	274.3	295.4	320.2	350.5	387.1	428.6	472.5	512.8	548.1
137.5°	247.1	262.6	281.1	301.1	323.2	349.2	379.8	413.4	449.4	484.1	514.7
140°	252.1	267.5	285.5	304.1	325.2	348.7	375.3	404.4	436.0	465.7	492.3
142.5°	257.1	271.5	289.0	307.0	326.6	347.7	371.4	396.0	423.1	448.9	472.1
145°	263.2	277.5	293.6	310.3	327.6	346.2	366.1	385.9	406.3	426.1	444.1
147.5°	270.4	282.6	297.3	312.3	327.6	343.9	360.8	377.6	393.8	409.8	422.6
150°	274.3	285.5	299.8	312.8	327.6	341.9	357.4	371.6	385.9	398.9	410.6
152.5°	278.3	289.0	301.3	313.8	326.1	339.4	353.4	366.1	378.4	389.9	399.7
155°	284.9	293.6	304.1	314.0	324.6	335.1	347.5	358.0	367.9	377.2	384.6
157.5°	290.6	297.3	305.7	314.7	322.4	331.2	340.8	349.3	357.6	364.8	370.6
160°	293.6	299.8	307.2	314.7	321.5	328.3	336.3	344.4	351.2	357.4	361.7
162.5°	296.0	301.3	307.7	314.1	319.5	325.3	331.8	338.4	344.2	349.9	353.8
165°	299.1	303.5	308.4	312.8	316.5	320.8	325.7	330.7	334.5	338.8	341.9
167.5°	302.0	304.8	308.3	311.8	313.5	316.4	320.0	324.0	326.9	329.4	331.6
170°	303.5	304.8	307.8	310.3	311.6	313.4	316.5	319.6	321.5	323.9	325.2
172.5°	304.4	305.2	307.8	309.8	310.1	310.9	313.0	315.6	317.0	318.9	319.7
175°	305.3	305.9	307.2	308.4	307.8	307.8	309.0	310.3	310.9	312.1	312.1
177.5°	305.9	305.9	306.4	307.4	306.4	305.9	306.4	307.0	307.4	307.9	307.9
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	675.3	675.0	675.3	674.3	675.3	675.0	675.3	678.2	678.2	678.4	678.7
5°	628.4	628.0	627.2	624.5	627.2	628.0	628.4	629.3	631.7	636.0	634.8
7.5°	587.4	587.0	584.3	584.4	584.3	587.0	587.4	589.8	592.6	595.2	598.3
10°	563.2	563.5	559.8	557.7	559.8	563.5	563.2	565.3	569.2	571.3	573.5
12.5°	539.6	538.2	535.3	532.9	535.3	538.2	539.6	541.2	546.6	549.0	553.1
15°	508.5	505.5	498.2	498.8	498.2	505.5	508.5	507.3	512.8	515.8	517.1
17.5°	471.9	469.7	469.6	465.3	469.6	469.7	471.9	474.4	479.1	482.4	491.1
20°	450.6	449.1	449.6	445.4	449.6	449.1	450.6	455.4	458.4	462.7	469.7
22.5°	433.8	432.3	429.8	428.4	429.8	432.3	433.8	437.2	440.5	446.5	450.3
25°	409.3	406.9	404.5	406.0	404.5	406.9	409.3	411.1	417.2	419.9	425.4
27.5°	384.8	382.9	380.6	380.2	380.6	382.9	384.8	386.6	389.9	394.5	401.1
30°	369.2	367.4	366.2	364.7	366.2	367.4	369.2	370.7	374.1	379.0	383.8
32.5°	353.5	353.2	350.9	350.6	350.9	353.2	353.5	356.0	359.3	363.9	368.0
35°	332.9	331.1	330.4	330.7	330.4	331.1	332.9	334.1	337.1	341.4	345.3
37.5°	313.2	310.9	309.7	308.6	309.7	310.9	313.2	313.5	316.6	319.4	324.7
40°	299.2	296.8	296.1	295.6	296.1	296.8	299.2	298.9	302.2	304.4	309.2
42.5°	283.4	282.4	282.1	281.0	282.1	282.4	283.4	285.0	286.9	290.0	293.7
45°	261.8	261.6	259.8	260.3	259.8	261.6	261.8	262.8	266.1	268.2	271.6
47.5°	239.2	237.8	236.5	237.4	236.5	237.8	239.2	240.3	242.6	245.3	249.6
50°	223.6	223.0	220.3	220.9	220.3	223.0	223.6	224.8	226.3	229.7	233.6
52.5°	208.1	205.8	204.8	204.4	204.8	205.8	208.1	209.3	211.0	214.9	217.9
55°	182.4	179.6	178.4	177.8	178.4	179.6	182.4	184.5	186.9	191.2	194.2
57.5°	157.1	156.4	155.4	156.1	155.4	156.4	157.1	160.7	163.0	166.4	170.0
60°	142.3	142.3	142.3	142.0	142.3	142.3	142.3	145.4	147.4	150.8	154.7
62.5°	130.9	130.2	129.9	130.3	129.9	130.2	130.9	132.2	134.4	136.5	139.9
65°	113.4	113.2	111.9	111.7	111.9	113.2	113.4	114.4	116.2	117.7	120.2
67.5°	97.0	95.9	95.6	95.1	95.6	95.9	97.0	97.8	99.0	101.0	102.2
70°	84.7	84.1	82.2	82.5	82.2	84.1	84.7	86.2	87.4	89.8	91.0
72.5°	71.3	70.7	70.3	69.9	70.3	70.7	71.3	72.8	74.1	76.7	78.7
75°	56.4	56.2	55.8	57.0	55.8	56.2	56.4	56.7	57.0	58.0	58.9
77.5°	45.2	45.2	45.4	44.9	45.4	45.2	45.2	45.2	45.2	45.7	45.9
80°	37.9	37.9	37.6	37.6	37.6	37.9	37.9	37.9	37.9	37.9	37.6
82.5°	30.4	30.7	30.8	30.3	30.8	30.7	30.4	30.9	31.1	30.7	30.8
85°	20.0	19.7	20.4	20.0	20.4	19.7	20.0	20.0	19.4	20.0	19.7
87.5°	12.4	12.1	12.2	12.4	12.2	12.1	12.4	12.1	11.8	11.7	11.3
90°	17.3	18.0	18.6	18.0	18.6	18.0	17.3	18.0	16.7	16.1	15.4
92.5°	32.2	30.3	31.0	29.9	31.0	30.3	32.2	33.4	36.5	41.4	52.1
95°	84.2	78.7	74.3	71.9	74.3	78.7	84.2	96.0	118.3	151.1	223.0
97.5°	245.5	217.6	200.9	195.6	200.9	217.6	245.5	291.2	365.3	445.2	555.8
100°	457.1	411.9	387.7	388.3	387.7	411.9	457.1	519.6	607.6	680.0	730.2
102.5°	639.9	604.1	583.9	569.7	583.9	604.1	639.9	688.6	744.3	786.6	788.1
105°	834.2	810.7	790.9	787.8	790.9	810.7	834.2	862.8	878.8	867.0	805.2
107.5°	933.7	925.8	919.1	913.4	919.1	925.8	933.7	933.2	911.2	856.9	756.4
110°	962.4	967.4	966.1	965.0	966.1	967.4	962.4	945.2	901.7	823.7	709.8



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	955.1	970.4	975.1	975.3	975.1	970.4	955.1	923.3	867.6	780.1	663.7
115°	915.4	942.6	955.1	958.1	955.1	942.6	915.4	868.9	801.5	710.3	602.6
117.5°	850.1	881.3	899.1	903.4	899.1	881.3	850.1	801.7	733.2	651.4	558.4
120°	804.5	839.2	854.1	857.8	854.1	839.2	804.5	755.6	693.1	618.7	535.1
122.5°	762.9	794.1	810.5	815.2	810.5	794.1	762.9	719.5	661.3	592.5	516.8
125°	708.5	735.8	751.2	755.6	751.2	735.8	708.5	668.9	619.3	559.9	492.3
127.5°	665.3	688.6	702.6	706.5	702.6	688.6	665.3	630.0	584.9	531.2	471.1
130°	638.6	660.8	673.8	678.8	673.8	660.8	638.6	605.7	563.6	513.4	457.7
132.5°	614.3	636.6	648.1	651.6	648.1	636.6	614.3	583.4	543.3	496.6	445.3
135°	578.5	597.1	608.2	612.5	608.2	597.1	578.5	548.1	512.8	472.5	428.6
137.5°	540.2	559.0	568.5	571.3	568.5	559.0	540.2	514.7	484.1	449.4	413.4
140°	515.9	533.2	543.2	542.6	543.2	533.2	515.9	492.3	465.7	436.0	404.4
142.5°	492.1	507.5	516.4	515.8	516.4	507.5	492.1	472.1	448.9	423.1	396.0
145°	459.5	472.5	477.5	478.7	477.5	472.5	459.5	444.1	426.1	406.3	385.9
147.5°	434.3	443.1	447.8	448.3	447.8	443.1	434.3	422.6	409.8	393.8	377.6
150°	419.9	426.7	430.5	430.5	430.5	426.7	419.9	410.6	398.9	385.9	371.6
152.5°	407.0	413.4	415.6	415.6	415.6	413.4	407.0	399.7	389.9	378.4	366.1
155°	390.1	395.1	396.4	397.0	396.4	395.1	390.1	384.6	377.2	367.9	358.0
157.5°	375.4	379.1	380.2	380.0	380.2	379.1	375.4	370.6	364.8	357.6	349.3
160°	366.1	369.7	369.7	369.2	369.7	369.7	366.1	361.7	357.4	351.2	344.4
162.5°	356.6	359.8	359.8	359.3	359.8	359.8	356.6	353.8	349.9	344.2	338.4
165°	344.4	346.8	346.2	346.2	346.2	346.8	344.4	341.9	338.8	334.5	330.7
167.5°	332.7	334.5	333.8	333.8	333.8	334.5	332.7	331.6	329.4	326.9	324.0
170°	325.7	327.0	326.4	326.4	326.4	327.0	325.7	325.2	323.9	321.5	319.6
172.5°	319.8	321.1	320.0	319.5	320.0	321.1	319.8	319.7	318.9	317.0	315.6
175°	312.1	312.8	312.1	311.6	312.1	312.8	312.1	312.1	312.1	310.9	310.3
177.5°	307.4	307.9	307.0	307.0	307.0	307.9	307.4	307.9	307.9	307.4	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	676.5	679.9	683.3	686.4	691.3	693.5	696.6	697.8	701.5	706.9	711.2
5°	635.3	640.2	646.6	651.7	660.0	666.3	673.3	679.9	687.9	699.1	709.1
7.5°	600.5	605.2	612.9	622.5	631.5	640.6	650.1	659.2	670.5	686.6	702.5
10°	577.4	583.2	592.3	602.6	613.8	622.7	633.8	645.4	659.3	677.9	697.0
12.5°	557.5	561.8	572.4	582.2	594.8	606.1	617.1	630.6	646.5	666.2	689.2
15°	525.9	531.9	542.2	553.1	566.5	578.3	592.6	609.0	624.5	648.7	676.6
17.5°	494.0	503.3	514.0	526.3	536.2	552.5	568.0	584.8	603.9	629.6	660.2
20°	473.6	480.9	490.9	508.8	521.9	534.3	548.6	569.5	587.1	616.2	648.1
22.5°	456.4	461.8	472.9	487.7	503.0	517.3	531.9	551.8	573.5	601.2	635.7
25°	430.9	439.3	447.8	458.4	474.8	492.2	507.9	524.9	548.0	577.4	614.7
27.5°	405.9	413.6	422.0	435.1	447.5	463.7	480.1	499.6	524.3	555.5	593.3
30°	389.9	395.7	403.5	420.3	431.5	445.4	464.9	482.1	505.2	538.3	578.3
32.5°	373.4	380.9	389.4	402.3	416.1	429.4	447.1	465.9	489.4	522.0	563.0
35°	349.8	358.6	367.4	376.8	390.8	404.5	419.3	440.0	463.9	495.5	535.8
37.5°	328.2	335.3	342.5	354.1	367.3	380.3	394.2	414.5	437.1	471.2	508.2
40°	314.3	320.8	326.1	338.3	351.1	365.0	378.7	396.6	420.8	452.7	488.5
42.5°	299.3	305.1	312.6	322.5	336.3	348.0	361.7	378.6	401.4	433.8	465.2
45°	276.7	283.4	289.8	299.2	312.8	324.3	336.5	352.6	376.0	402.7	430.6
47.5°	253.3	259.9	267.2	276.3	288.2	299.9	312.0	326.3	347.6	373.8	392.6
50°	238.2	243.7	251.0	260.0	270.9	283.4	294.3	309.8	330.1	350.8	367.2
52.5°	222.7	227.6	235.9	245.5	255.6	266.4	278.1	291.4	309.7	329.2	342.1
55°	198.4	204.5	211.5	220.9	230.9	240.0	251.2	264.9	279.5	294.0	302.9
57.5°	175.8	180.9	186.7	196.5	205.1	215.9	226.0	236.7	250.2	261.1	266.9
60°	159.3	163.8	171.4	179.9	188.1	197.5	209.1	219.7	230.0	238.8	243.4
62.5°	143.8	149.0	155.7	163.4	172.4	181.3	191.3	200.3	209.4	217.0	220.1
65°	123.5	127.8	132.6	139.9	147.2	156.3	164.1	173.3	179.9	184.2	186.9
67.5°	105.0	107.8	111.5	116.4	123.6	131.5	139.2	146.2	151.9	154.7	157.2
70°	93.2	95.0	97.7	102.6	108.1	115.0	122.9	128.0	132.9	135.3	137.8
72.5°	81.3	83.6	86.0	89.9	94.4	99.5	105.2	111.5	114.2	117.1	118.6
75°	61.6	65.0	68.3	70.7	73.8	77.7	82.9	86.7	88.3	90.7	91.0
77.5°	46.5	47.2	49.7	52.7	55.2	58.1	61.3	64.9	65.6	66.9	67.7
80°	38.3	38.3	38.3	40.1	43.1	45.2	48.2	50.1	51.3	51.6	51.9
82.5°	30.7	30.7	30.5	30.8	31.9	33.0	35.9	37.9	38.9	38.7	38.0
85°	20.0	19.4	19.4	19.1	19.4	18.8	18.5	19.7	21.5	21.5	20.9
87.5°	11.2	11.1	11.0	10.4	9.7	9.1	8.2	8.2	7.8	8.5	8.0
90°	14.9	15.4	13.6	11.8	9.9	8.1	6.8	5.5	3.7	2.5	1.3
92.5°	71.9	95.2	104.8	78.7	52.0	35.8	26.6	21.5	16.6	11.4	7.7
95°	297.9	367.3	327.0	225.5	133.2	80.5	56.3	40.2	29.7	22.9	21.1
97.5°	609.0	569.2	416.7	247.4	143.3	93.0	66.9	51.0	41.9	36.5	35.9
100°	708.5	586.5	396.4	233.5	141.8	98.5	74.3	59.5	50.8	46.4	45.9
102.5°	713.5	554.3	366.6	221.6	143.8	104.9	82.8	69.4	61.2	57.4	56.2
105°	675.7	498.0	330.1	213.0	149.2	115.8	96.6	84.8	77.4	73.7	71.9
107.5°	609.6	448.1	306.8	212.5	159.4	130.1	112.3	101.2	93.9	90.3	88.4
110°	567.9	419.9	297.9	214.9	167.9	140.0	122.6	112.1	105.3	102.2	100.4



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	531.8	401.1	292.9	219.8	176.3	150.4	133.6	123.0	116.2	113.1	111.2
115°	488.1	380.9	291.1	227.9	190.1	166.6	149.9	139.3	133.2	129.4	127.0
117.5°	461.7	369.0	292.2	238.6	204.9	181.6	166.1	154.3	148.6	145.5	142.7
120°	447.8	363.5	294.2	246.5	214.3	192.0	176.5	164.8	158.5	155.4	153.6
122.5°	436.4	360.1	297.6	253.9	224.2	202.4	185.9	174.7	167.9	164.9	163.0
125°	421.8	355.5	302.9	265.7	238.4	216.7	200.0	188.3	181.5	177.8	176.5
127.5°	408.9	353.3	308.8	275.4	250.8	229.9	213.2	200.2	193.2	188.6	186.8
130°	402.0	351.8	312.8	281.8	258.3	237.8	221.1	208.1	200.7	195.1	193.2
132.5°	395.5	351.3	315.8	287.7	264.7	244.8	228.5	215.6	206.6	200.6	198.2
135°	387.1	350.5	320.2	295.4	274.3	255.2	238.4	225.5	216.2	209.4	206.8
137.5°	379.8	349.2	323.2	301.1	281.1	262.6	247.1	234.2	224.3	217.6	215.0
140°	375.3	348.7	325.2	304.1	285.5	267.5	252.1	239.7	229.8	223.6	220.5
142.5°	371.4	347.7	326.6	307.0	289.0	271.5	257.1	244.6	235.8	229.0	226.4
145°	366.1	346.2	327.6	310.3	293.6	277.5	263.2	252.7	243.4	237.8	236.0
147.5°	360.8	343.9	327.6	312.3	297.3	282.6	270.4	260.2	252.2	246.8	245.7
150°	357.4	341.9	327.6	312.8	299.8	285.5	274.3	265.7	257.6	252.7	252.1
152.5°	353.4	339.4	326.1	313.8	301.3	289.0	278.3	270.7	263.6	258.6	258.5
155°	347.5	335.1	324.6	314.0	304.1	293.6	284.9	278.1	271.9	268.2	268.2
157.5°	340.8	331.2	322.4	314.7	305.7	297.3	290.6	284.8	279.3	276.3	275.8
160°	336.3	328.3	321.5	314.7	307.2	299.8	293.6	289.2	284.3	281.8	281.8
162.5°	331.8	325.3	319.5	314.1	307.7	301.3	296.0	292.2	288.3	286.3	286.3
165°	325.7	320.8	316.5	312.8	308.4	303.5	299.1	296.7	293.6	292.3	292.9
167.5°	320.0	316.4	313.5	311.8	308.3	304.8	302.0	300.2	297.9	297.3	298.0
170°	316.5	313.4	311.6	310.3	307.8	304.8	303.5	302.2	300.4	299.8	301.0
172.5°	313.0	310.9	310.1	309.8	307.8	305.2	304.4	303.7	302.4	302.2	303.0
175°	309.0	307.8	307.8	308.4	307.2	305.9	305.3	305.3	304.1	304.8	305.3
177.5°	306.4	305.9	306.4	307.4	306.4	305.9	305.9	305.9	305.5	305.9	306.4
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	712.6	715.3	718.7	723.8	727.7	731.1	731.8	732.8	735.2	739.3	742.5
5°	717.3	724.3	735.5	746.4	758.3	767.9	777.1	783.5	789.5	802.2	812.5
7.5°	715.8	731.3	748.9	768.6	788.4	807.6	825.5	841.5	857.4	875.9	897.1
10°	714.9	733.1	756.7	781.9	809.5	836.5	862.6	883.0	906.7	927.9	954.9
12.5°	710.3	736.5	764.8	796.9	830.9	862.1	896.4	924.5	951.5	982.2	1013.6
15°	704.3	736.1	771.9	814.7	866.3	903.9	939.1	987.9	1021.3	1054.7	1099.6
17.5°	693.2	732.1	776.9	832.4	875.5	926.1	979.0	1017.6	1062.6	1109.6	1150.2
20°	684.5	729.8	779.8	834.4	889.3	944.3	995.5	1041.6	1088.1	1142.4	1175.8
22.5°	675.8	720.5	772.5	830.5	889.5	947.4	1005.4	1059.6	1111.8	1166.6	1209.3
25°	657.2	710.3	766.8	825.9	884.2	947.8	1017.1	1077.4	1142.1	1198.5	1238.9
27.5°	638.4	687.1	743.2	803.3	868.0	943.3	1024.7	1093.4	1158.1	1198.5	1211.2
30°	621.4	673.0	724.5	785.5	855.6	939.7	1026.2	1104.8	1157.9	1175.4	1162.4
32.5°	604.2	650.9	702.0	764.5	838.9	930.7	1028.1	1098.0	1130.0	1116.5	1063.3
35°	573.8	615.9	665.4	727.9	813.5	925.7	1020.1	1067.5	1059.5	983.7	883.5
37.5°	541.2	575.6	621.4	686.7	787.1	906.0	985.6	992.6	924.3	807.9	692.2
40°	515.5	546.4	593.5	661.8	766.8	886.6	950.9	922.7	816.8	687.2	590.7
42.5°	490.5	516.6	561.9	635.6	747.3	860.2	899.2	837.7	715.6	593.0	505.3
45°	448.1	472.7	518.2	593.8	707.6	809.5	804.4	697.6	575.3	476.7	403.9
47.5°	408.0	429.4	472.2	549.3	660.9	733.6	685.4	571.8	468.0	389.0	337.0
50°	379.6	400.8	443.3	519.4	623.5	676.6	607.8	498.2	403.2	337.7	296.4
52.5°	352.4	373.1	412.0	486.2	578.4	610.1	536.1	434.6	355.5	298.9	263.4
55°	314.3	330.1	365.0	436.0	504.9	512.1	437.2	352.3	287.0	247.6	223.3
57.5°	275.6	289.1	323.6	380.2	428.5	424.7	353.6	280.2	236.2	206.9	189.3
60°	250.3	263.6	294.0	342.5	379.0	366.2	301.0	241.9	204.2	182.7	168.7
62.5°	226.8	237.2	265.6	301.0	327.3	312.8	257.3	208.3	178.5	160.3	149.2
65°	192.7	201.1	223.9	242.4	257.0	243.0	196.9	163.0	141.4	128.7	121.0
67.5°	160.3	165.6	180.1	186.7	197.0	181.7	148.1	125.3	113.0	102.3	97.0
70°	139.9	143.9	151.4	156.9	159.6	143.9	118.9	102.3	92.0	84.4	81.0
72.5°	119.5	122.9	124.5	129.0	127.5	112.7	95.6	82.4	74.9	69.8	65.5
75°	91.3	92.8	91.3	89.5	85.6	75.3	63.5	56.7	51.3	48.9	47.4
77.5°	66.5	66.1	64.0	61.2	54.4	47.9	41.6	39.3	37.0	35.6	35.2
80°	51.3	50.1	48.2	43.7	37.9	33.4	31.8	30.3	29.5	27.9	27.6
82.5°	38.2	37.5	34.4	30.6	26.5	24.4	23.1	22.6	21.6	20.9	20.8
85°	20.4	19.4	16.1	13.9	13.4	12.8	12.4	12.4	11.2	10.9	10.9
87.5°	7.1	5.9	5.9	5.5	5.7	5.6	6.3	6.1	6.3	6.3	6.0
90°	2.5	3.7	5.5	6.8	8.1	9.9	11.8	13.6	15.4	14.9	15.4
92.5°	11.4	16.6	21.5	26.6	35.8	52.0	78.7	104.8	95.2	71.9	52.1
95°	22.9	29.7	40.2	56.3	80.5	133.2	225.5	327.0	367.3	297.9	223.0
97.5°	36.5	41.9	51.0	66.9	93.0	143.3	247.4	416.7	569.2	609.0	555.8
100°	46.4	50.8	59.5	74.3	98.5	141.8	233.5	396.4	586.5	708.5	730.2
102.5°	57.4	61.2	69.4	82.8	104.9	143.8	221.6	366.6	554.3	713.5	788.1
105°	73.7	77.4	84.8	96.6	115.8	149.2	213.0	330.1	498.0	675.7	805.2
107.5°	90.3	93.9	101.2	112.3	130.1	159.4	212.5	306.8	448.1	609.6	756.4
110°	102.2	105.3	112.1	122.6	140.0	167.9	214.9	297.9	419.9	567.9	709.8



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	113.1	116.2	123.0	133.6	150.4	176.3	219.8	292.9	401.1	531.8	663.7
115°	129.4	133.2	139.3	149.9	166.6	190.1	227.9	291.1	380.9	488.1	602.6
117.5°	145.5	148.6	154.3	166.1	181.6	204.9	238.6	292.2	369.0	461.7	558.4
120°	155.4	158.5	164.8	176.5	192.0	214.3	246.5	294.2	363.5	447.8	535.1
122.5°	164.9	167.9	174.7	185.9	202.4	224.2	253.9	297.6	360.1	436.4	516.8
125°	177.8	181.5	188.3	200.0	216.7	238.4	265.7	302.9	355.5	421.8	492.3
127.5°	188.6	193.2	200.2	213.2	229.9	250.8	275.4	308.8	353.3	408.9	471.1
130°	195.1	200.7	208.1	221.1	237.8	258.3	281.8	312.8	351.8	402.0	457.7
132.5°	200.6	206.6	215.6	228.5	244.8	264.7	287.7	315.8	351.3	395.5	445.3
135°	209.4	216.2	225.5	238.4	255.2	274.3	295.4	320.2	350.5	387.1	428.6
137.5°	217.6	224.3	234.2	247.1	262.6	281.1	301.1	323.2	349.2	379.8	413.4
140°	223.6	229.8	239.7	252.1	267.5	285.5	304.1	325.2	348.7	375.3	404.4
142.5°	229.0	235.8	244.6	257.1	271.5	289.0	307.0	326.6	347.7	371.4	396.0
145°	237.8	243.4	252.7	263.2	277.5	293.6	310.3	327.6	346.2	366.1	385.9
147.5°	246.8	252.2	260.2	270.4	282.6	297.3	312.3	327.6	343.9	360.8	377.6
150°	252.7	257.6	265.7	274.3	285.5	299.8	312.8	327.6	341.9	357.4	371.6
152.5°	258.6	263.6	270.7	278.3	289.0	301.3	313.8	326.1	339.4	353.4	366.1
155°	268.2	271.9	278.1	284.9	293.6	304.1	314.0	324.6	335.1	347.5	358.0
157.5°	276.3	279.3	284.8	290.6	297.3	305.7	314.7	322.4	331.2	340.8	349.3
160°	281.8	284.3	289.2	293.6	299.8	307.2	314.7	321.5	328.3	336.3	344.4
162.5°	286.3	288.3	292.2	296.0	301.3	307.7	314.1	319.5	325.3	331.8	338.4
165°	292.3	293.6	296.7	299.1	303.5	308.4	312.8	316.5	320.8	325.7	330.7
167.5°	297.3	297.9	300.2	302.0	304.8	308.3	311.8	313.5	316.4	320.0	324.0
170°	299.8	300.4	302.2	303.5	304.8	307.8	310.3	311.6	313.4	316.5	319.6
172.5°	302.2	302.4	303.7	304.4	305.2	307.8	309.8	310.1	310.9	313.0	315.6
175°	304.8	304.1	305.3	305.3	305.9	307.2	308.4	307.8	307.8	309.0	310.3
177.5°	305.9	305.5	305.9	305.9	305.9	306.4	307.4	306.4	305.9	306.4	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	747.7	747.7	748.6	752.3	752.7	755.9	754.9
5°	821.7	827.4	829.6	838.7	844.1	846.5	841.7
7.5°	912.2	928.4	936.2	945.7	954.1	956.7	950.1
10°	978.3	995.2	1009.5	1018.3	1026.5	1031.9	1038.9
12.5°	1042.0	1063.0	1076.5	1088.9	1097.3	1104.3	1105.4
15°	1111.4	1143.0	1167.0	1184.6	1193.3	1197.9	1196.1
17.5°	1181.4	1210.6	1227.7	1245.6	1257.8	1258.5	1258.9
20°	1221.0	1249.5	1269.2	1282.5	1296.2	1295.6	1298.6
22.5°	1247.4	1269.9	1285.0	1294.7	1299.3	1297.0	1297.7
25°	1259.8	1266.5	1263.8	1248.2	1244.4	1230.1	1232.5
27.5°	1196.0	1164.4	1131.8	1089.7	1056.6	1030.2	1031.5
30°	1109.3	1053.4	989.8	936.4	888.4	875.0	846.5
32.5°	988.2	904.4	829.8	780.1	738.9	727.7	702.8
35°	782.8	701.5	624.7	578.6	560.4	535.0	534.6
37.5°	608.5	536.9	496.3	461.7	443.5	428.1	426.6
40°	511.9	456.1	425.4	400.5	382.6	371.1	368.4
42.5°	444.4	399.3	370.5	355.1	341.4	335.4	331.0
45°	362.9	332.6	312.5	298.6	292.2	287.6	285.2
47.5°	303.6	283.2	269.6	260.3	255.1	250.3	251.6
50°	271.2	254.6	244.5	235.8	231.8	228.5	228.8
52.5°	245.3	230.3	222.2	215.9	211.0	208.6	207.4
55°	208.2	198.8	190.5	186.0	183.2	179.9	179.0
57.5°	177.5	170.2	163.6	158.4	157.8	154.6	155.0
60°	157.2	151.1	145.6	142.9	140.8	138.1	138.9
62.5°	140.5	135.3	130.3	128.1	126.0	124.0	124.4
65°	115.0	110.1	107.1	105.9	105.0	104.1	103.1
67.5°	91.7	88.6	86.7	84.1	82.3	82.0	81.0
70°	77.1	73.1	69.8	66.5	65.5	65.2	65.5
72.5°	61.8	59.3	58.4	56.7	56.6	55.8	56.3
75°	46.4	45.6	44.9	43.7	43.7	43.7	43.7
77.5°	34.2	33.7	33.4	33.0	32.8	32.3	32.3
80°	26.7	26.4	25.8	25.8	25.5	25.8	25.5
82.5°	20.1	20.1	19.5	19.5	19.2	19.0	19.2
85°	10.3	10.0	10.6	10.0	10.3	9.7	10.3
87.5°	6.1	6.3	6.3	6.1	6.0	6.7	6.0
90°	16.1	16.7	18.0	17.3	18.0	18.6	18.0
92.5°	41.4	36.5	33.4	32.2	30.3	31.0	29.9
95°	151.1	118.3	96.0	84.2	78.7	74.3	71.9
97.5°	445.2	365.3	291.2	245.5	217.6	200.9	195.6
100°	680.0	607.6	519.6	457.1	411.9	387.7	388.3
102.5°	786.6	744.3	688.6	639.9	604.1	583.9	569.7
105°	867.0	878.8	862.8	834.2	810.7	790.9	787.8
107.5°	856.9	911.2	933.2	933.7	925.8	919.1	913.4
110°	823.7	901.7	945.2	962.4	967.4	966.1	965.0



TEST NUMBER: P332284-927

CATALOG NUMBER: S123RDIP-S560D805U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	780.1	867.6	923.3	955.1	970.4	975.1	975.3
115°	710.3	801.5	868.9	915.4	942.6	955.1	958.1
117.5°	651.4	733.2	801.7	850.1	881.3	899.1	903.4
120°	618.7	693.1	755.6	804.5	839.2	854.1	857.8
122.5°	592.5	661.3	719.5	762.9	794.1	810.5	815.2
125°	559.9	619.3	668.9	708.5	735.8	751.2	755.6
127.5°	531.2	584.9	630.0	665.3	688.6	702.6	706.5
130°	513.4	563.6	605.7	638.6	660.8	673.8	678.8
132.5°	496.6	543.3	583.4	614.3	636.6	648.1	651.6
135°	472.5	512.8	548.1	578.5	597.1	608.2	612.5
137.5°	449.4	484.1	514.7	540.2	559.0	568.5	571.3
140°	436.0	465.7	492.3	515.9	533.2	543.2	542.6
142.5°	423.1	448.9	472.1	492.1	507.5	516.4	515.8
145°	406.3	426.1	444.1	459.5	472.5	477.5	478.7
147.5°	393.8	409.8	422.6	434.3	443.1	447.8	448.3
150°	385.9	398.9	410.6	419.9	426.7	430.5	430.5
152.5°	378.4	389.9	399.7	407.0	413.4	415.6	415.6
155°	367.9	377.2	384.6	390.1	395.1	396.4	397.0
157.5°	357.6	364.8	370.6	375.4	379.1	380.2	380.0
160°	351.2	357.4	361.7	366.1	369.7	369.7	369.2
162.5°	344.2	349.9	353.8	356.6	359.8	359.8	359.3
165°	334.5	338.8	341.9	344.4	346.8	346.2	346.2
167.5°	326.9	329.4	331.6	332.7	334.5	333.8	333.8
170°	321.5	323.9	325.2	325.7	327.0	326.4	326.4
172.5°	317.0	318.9	319.7	319.8	321.1	320.0	319.5
175°	310.9	312.1	312.1	312.1	312.8	312.1	311.6
177.5°	307.4	307.9	307.9	307.4	307.9	307.0	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9

(END OF REPORT)