

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332319-927

Luminaire Tested: **S123RDIP-S775D1025U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332319-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1025U927-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5204.3 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	42	41	39	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	31	28	26	23
6	64	52	44	39	58	48	41	36	41	36	32	35	31	28	28	26	23	20
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	29	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	37	30	26	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10428	10428	10428	10428
5°	12431	10472	9223	10472
10°	15522	10413	8332	10413
15°	18219	10307	7598	10307
20°	20333	10148	6975	10148
25°	20009	9980	6590	9980
30°	14382	9825	6196	9825
35°	9603	9625	5941	9625
40°	7075	9382	5675	9382
45°	5934	8958	5416	8958
50°	5238	8403	5056	8403
55°	4592	7767	4560	7767
60°	4090	7160	4179	7160
65°	3591	6507	3889	6507
70°	2820	5926	3550	5926
75°	2483	5178	3244	5178
80°	2163	4395	3186	4395
85°	1741	3532	3384	3532



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.3	1.8
10°-20°	297.7	5.7
20°-30°	467.6	9.0
30°-40°	487.9	9.4
40°-50°	417.5	8.0
50°-60°	318.2	6.1
60°-70°	204.0	3.9
70°-80°	98.1	1.9
80°-90°	28.9	0.6
90°-100°	65.6	1.3
100°-110°	196.3	3.8
110°-120°	333.8	6.4
120°-130°	439.1	8.4
130°-140°	493.6	9.5
140°-150°	485.2	9.3
150°-160°	408.4	7.8
160°-170°	271.9	5.2
170°-180°	95.2	1.8
0°-30°	860.6	16.5
0°-40°	1348.4	25.9
0°-60°	2084.2	40.0
0°-90°	2415.3	46.4
90°-120°	595.7	11.4
90°-150°	2013.5	38.7
90°-180°	2789.0	53.6
0°-180°	5204.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1150	969	854	969	1150	119
15°	1635	925	682	925	1635	464
25°	1685	840	555	840	1685	724
35°	731	732	452	732	731	479
45°	390	588	356	588	390	307
55°	245	414	243	414	245	221
65°	141	256	153	256	141	139
75°	60	124	78	124	60	64
85°	14	29	27	29	14	17
90°	24	1	24	1	24	12
95°	62	47	62	47	62	63
105°	188	178	188	178	188	200
115°	337	336	337	336	337	333
125°	486	492	486	492	486	435
135°	637	638	637	638	637	490
145°	774	774	774	774	774	483
155°	885	886	885	886	885	407
165°	962	966	962	966	962	271
175°	1000	1004	1000	1004	1000	95
180°	1007	1007	1007	1007	1007	



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1031.9	1033.2	1028.9	1028.3	1023.3	1021.9	1021.9	1014.9	1010.7	1005.0	1001.7
5°	1150.5	1157.1	1153.8	1146.4	1133.9	1131.0	1123.2	1110.7	1096.6	1079.2	1070.9
7.5°	1298.6	1307.7	1304.2	1292.7	1279.7	1269.2	1246.9	1226.2	1197.3	1171.9	1150.2
10°	1420.1	1410.6	1403.1	1391.9	1379.9	1360.3	1337.1	1305.2	1268.3	1239.3	1206.9
12.5°	1511.0	1509.4	1500.0	1488.4	1471.5	1452.9	1424.4	1385.5	1342.6	1300.7	1263.7
15°	1634.9	1637.4	1631.2	1619.1	1595.1	1562.3	1519.2	1503.0	1441.7	1396.1	1350.4
17.5°	1720.7	1720.2	1719.4	1702.7	1678.2	1654.9	1614.9	1572.3	1516.7	1452.5	1391.0
20°	1775.1	1771.0	1771.8	1753.1	1734.9	1707.9	1669.0	1607.2	1561.5	1487.3	1423.8
22.5°	1773.8	1773.0	1776.2	1769.7	1756.4	1735.8	1705.1	1653.0	1594.7	1519.8	1448.3
25°	1684.7	1681.4	1700.9	1706.3	1727.4	1731.2	1722.0	1693.4	1638.2	1561.1	1472.7
27.5°	1410.0	1408.2	1444.3	1489.6	1547.0	1591.7	1634.7	1655.6	1638.2	1583.0	1494.5
30°	1157.1	1196.1	1214.4	1279.9	1352.9	1440.0	1516.3	1588.9	1606.7	1582.7	1510.1
32.5°	960.8	994.7	1010.0	1066.2	1134.2	1236.3	1350.8	1453.5	1526.1	1544.5	1500.8
35°	730.8	731.2	766.0	790.9	854.0	958.9	1070.1	1207.8	1344.6	1448.3	1459.0
37.5°	583.1	585.2	606.3	631.1	678.3	733.9	831.7	946.2	1104.3	1263.5	1356.8
40°	503.5	507.2	523.0	547.5	581.5	623.4	699.7	807.6	939.4	1116.5	1261.2
42.5°	452.4	458.4	466.6	485.4	506.5	545.7	607.4	690.7	810.6	978.1	1145.1
45°	389.8	393.2	399.4	408.1	427.2	454.6	496.1	552.0	651.6	786.4	953.5
47.5°	343.9	342.1	348.7	355.8	368.4	387.1	414.9	460.7	531.6	639.8	781.6
50°	312.8	312.3	316.9	322.3	334.3	348.0	370.8	405.2	461.6	551.2	681.0
52.5°	283.5	285.1	288.4	295.1	303.7	314.8	335.3	360.0	408.5	485.8	594.1
55°	244.7	246.0	250.5	254.2	260.5	271.6	284.6	305.2	338.4	392.4	481.5
57.5°	211.8	211.3	215.6	216.6	223.6	232.7	242.7	258.8	282.9	322.9	382.9
60°	190.0	188.7	192.4	195.4	199.1	206.5	214.8	230.6	249.7	279.1	330.6
62.5°	170.1	169.4	172.2	175.1	178.2	185.0	191.9	204.1	219.1	244.0	284.8
65°	141.0	142.3	143.5	144.7	146.4	150.5	157.2	165.5	175.9	193.3	222.7
67.5°	110.8	112.1	112.5	115.0	118.6	121.2	125.2	132.6	139.8	154.6	171.3
70°	89.6	89.2	89.6	90.9	95.4	100.0	105.4	110.7	115.3	125.6	139.7
72.5°	77.0	76.2	77.3	77.6	79.8	81.0	84.4	89.5	95.4	102.4	112.6
75°	59.7	59.7	59.7	59.7	61.4	62.2	63.5	64.7	66.8	70.1	77.6
77.5°	44.1	44.2	44.8	45.2	45.6	46.0	46.8	48.0	48.8	50.5	53.8
80°	34.9	35.3	34.9	35.3	35.3	36.0	36.5	37.7	38.2	40.2	41.5
82.5°	26.2	26.0	26.2	26.6	26.6	27.5	27.6	28.4	28.5	29.6	30.9
85°	14.1	13.3	14.1	13.7	14.5	13.7	14.1	14.9	14.9	15.4	17.0
87.5°	8.1	8.6	7.9	8.2	8.1	8.3	8.2	8.1	8.6	8.1	8.0
90°	23.7	23.4	23.1	22.7	22.3	21.8	21.1	20.4	19.6	19.0	16.7
92.5°	31.9	32.2	32.4	32.6	32.8	32.6	32.1	31.5	30.9	30.3	29.1
95°	61.7	61.7	61.7	61.7	61.7	61.3	60.6	59.9	59.3	58.5	57.1
97.5°	94.9	95.0	95.1	95.1	95.1	94.8	94.0	93.2	92.4	91.6	90.5
100°	120.2	119.9	119.5	119.1	118.8	118.4	117.8	117.3	116.8	116.2	115.3
102.5°	146.2	146.2	146.2	146.3	146.4	146.2	145.7	145.1	144.6	144.1	142.9
105°	188.2	187.8	187.5	187.1	186.8	186.6	186.6	186.6	186.6	186.6	185.1
107.5°	232.0	232.2	232.4	232.7	232.8	232.7	232.1	231.6	231.0	230.4	229.8
110°	261.7	262.1	262.4	262.8	263.2	263.0	262.3	261.6	260.9	260.2	259.8



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	293.3	293.4	293.5	293.6	293.7	293.3	292.4	291.6	290.7	289.9	289.9
115°	336.8	337.1	337.2	337.4	337.5	337.5	337.4	337.2	337.1	336.8	337.2
117.5°	381.0	381.5	382.0	382.5	382.9	383.3	383.3	383.3	383.3	383.3	383.8
120°	412.0	412.3	412.7	413.0	413.4	413.7	413.8	414.0	414.2	414.4	415.3
122.5°	441.7	442.2	442.7	443.2	443.7	444.2	444.7	445.0	445.5	446.0	446.5
125°	486.3	487.0	487.7	488.5	489.1	489.8	490.5	491.2	491.9	492.7	493.0
127.5°	530.8	531.6	532.3	533.2	534.0	534.9	535.9	536.9	537.8	538.8	539.2
130°	559.8	561.1	562.3	563.6	564.7	565.8	566.4	567.1	567.8	568.5	569.1
132.5°	590.3	591.2	592.2	593.1	594.1	594.9	595.8	596.6	597.5	598.3	598.7
135°	637.4	637.7	638.0	638.4	638.7	639.3	640.0	640.7	641.4	642.1	642.3
137.5°	679.0	679.6	680.2	681.0	681.6	682.3	683.1	683.8	684.5	685.2	684.8
140°	706.2	707.4	708.6	709.9	711.1	711.8	711.9	712.1	712.3	712.5	712.3
142.5°	734.0	734.9	735.9	736.8	737.8	738.3	738.6	738.7	738.9	739.0	738.7
145°	774.1	774.8	775.5	776.3	777.0	777.4	777.6	777.8	777.9	778.1	777.6
147.5°	809.9	811.0	812.0	813.1	814.1	814.7	814.7	814.7	814.7	814.7	814.1
150°	832.7	833.7	834.8	835.8	836.9	837.4	837.4	837.4	837.4	837.4	837.1
152.5°	854.8	855.7	856.7	857.5	858.5	858.8	858.5	858.3	857.9	857.7	857.5
155°	884.9	886.1	887.3	888.6	889.8	890.0	889.4	888.7	888.0	887.2	887.1
157.5°	912.2	913.2	914.2	915.2	916.2	916.3	915.5	914.8	914.1	913.3	913.2
160°	929.9	930.7	931.4	932.1	932.7	932.6	931.8	930.9	930.0	929.2	929.2
162.5°	943.3	944.4	945.5	946.6	947.7	947.8	947.0	946.1	945.2	944.4	944.2
165°	962.3	963.6	964.8	966.1	967.3	967.3	966.3	965.3	964.2	963.1	963.1
167.5°	978.7	979.8	980.8	981.9	983.0	983.0	981.9	980.8	979.8	978.7	978.5
170°	986.9	988.1	989.4	990.5	991.8	991.8	990.5	989.4	988.1	986.9	986.9
172.5°	993.2	994.4	995.7	996.9	998.1	998.1	997.1	996.0	994.9	993.8	993.8
175°	1000.3	1001.6	1002.7	1004.0	1005.2	1005.4	1004.2	1003.2	1002.2	1001.1	1001.1
177.5°	1004.1	1005.1	1006.1	1007.1	1008.1	1008.1	1007.3	1006.5	1005.6	1004.7	1004.7
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1000.4	999.3	994.7	989.4	982.5	977.8	974.1	972.2	966.2	958.9	953.9
5°	1062.2	1049.7	1036.5	1020.3	1005.4	990.0	980.5	969.2	955.6	940.2	929.5
7.5°	1128.4	1104.0	1077.7	1050.6	1023.7	999.7	978.5	960.3	938.5	916.5	901.1
10°	1179.2	1143.4	1106.5	1068.8	1034.4	1002.0	977.2	952.7	926.5	901.3	882.2
12.5°	1225.3	1178.3	1135.8	1089.4	1045.4	1006.7	970.8	942.1	910.6	883.7	861.9
15°	1283.7	1235.6	1184.1	1113.6	1055.1	1006.2	962.7	924.9	886.8	853.6	832.4
17.5°	1338.2	1265.8	1196.7	1137.9	1061.9	1000.8	947.6	902.5	860.6	825.5	799.4
20°	1360.8	1290.7	1215.6	1140.6	1065.9	997.4	935.6	885.9	842.3	802.6	778.5
22.5°	1374.4	1295.0	1215.9	1135.3	1056.0	984.8	923.8	868.9	821.8	783.9	754.2
25°	1390.2	1295.7	1208.6	1128.9	1048.1	970.9	898.3	840.3	789.3	749.0	717.5
27.5°	1400.7	1289.4	1186.5	1098.0	1016.0	939.1	872.6	811.1	759.3	716.8	682.9
30°	1402.6	1284.4	1169.6	1073.8	990.4	919.9	849.4	790.5	735.8	690.5	659.0
32.5°	1405.3	1272.2	1146.7	1044.9	959.6	889.7	825.9	769.6	713.5	669.0	636.8
35°	1394.4	1265.4	1111.9	995.0	909.5	841.9	784.3	732.5	677.3	634.1	601.3
37.5°	1347.3	1238.4	1075.9	938.7	849.4	786.8	739.8	694.6	644.0	597.5	566.6
40°	1299.8	1211.9	1048.1	904.6	811.3	746.9	704.6	667.7	618.8	575.3	542.1
42.5°	1229.2	1175.8	1021.5	868.7	768.1	706.2	670.5	635.9	592.9	548.7	517.5
45°	1099.5	1106.5	967.2	811.7	708.4	646.2	612.6	588.5	550.4	513.9	482.0
47.5°	936.9	1002.8	903.4	750.8	645.4	587.0	557.7	536.7	511.0	475.2	446.0
50°	830.8	924.9	852.3	710.0	605.9	547.9	518.9	501.8	479.4	451.2	423.4
52.5°	732.8	834.0	790.6	664.6	563.2	510.1	481.7	467.7	449.9	423.3	398.2
55°	597.6	700.1	690.1	596.0	498.9	451.2	429.7	413.9	401.9	382.0	362.1
57.5°	483.5	580.6	585.7	519.7	442.4	395.2	376.7	364.8	357.0	341.9	323.5
60°	411.5	500.6	518.0	468.3	401.9	360.4	342.1	332.6	326.4	314.4	300.3
62.5°	351.7	427.6	447.3	411.5	363.1	324.2	310.0	300.8	296.5	286.1	273.7
65°	269.2	332.2	351.3	331.4	306.1	275.0	263.4	255.5	251.8	246.0	236.8
67.5°	202.4	248.3	269.3	255.2	246.1	226.5	219.0	214.8	211.5	207.6	199.9
70°	162.6	196.6	218.2	214.4	207.0	196.6	191.2	188.3	185.0	181.6	175.0
72.5°	130.7	154.2	174.4	176.3	170.2	168.0	163.3	162.1	160.1	156.1	152.5
75°	86.7	102.8	116.9	122.3	124.8	126.9	124.8	124.5	124.0	120.7	118.6
77.5°	56.8	65.5	74.4	83.6	87.5	90.3	91.0	92.5	91.4	89.7	88.6
80°	43.6	45.6	51.8	59.7	65.9	68.4	70.1	70.9	70.5	70.1	68.4
82.5°	31.6	33.4	36.3	41.8	47.1	51.2	52.2	52.0	52.9	53.2	51.8
85°	17.0	17.4	18.2	19.1	21.9	26.5	27.8	28.6	29.5	29.5	26.9
87.5°	8.2	7.4	7.6	7.2	7.8	7.8	9.5	10.8	11.5	10.5	10.9
90°	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8	2.5	4.3	6.1
92.5°	27.7	26.5	25.2	23.9	22.7	21.5	20.4	19.2	20.4	21.5	22.7
95°	55.7	54.3	52.9	51.6	50.4	49.1	47.8	46.7	47.8	49.1	50.4
97.5°	89.5	88.5	87.5	86.5	85.6	84.7	83.8	82.9	83.8	84.7	85.6
100°	114.5	113.6	112.7	111.8	110.7	109.6	108.6	107.6	108.6	109.6	110.7
102.5°	141.7	140.6	139.4	138.6	137.9	137.3	136.7	136.0	136.7	137.3	137.9
105°	183.5	181.9	180.3	179.4	179.0	178.6	178.2	177.9	178.2	178.6	179.0
107.5°	229.2	228.5	227.9	227.5	227.3	227.0	226.9	226.6	226.9	227.0	227.3
110°	259.4	259.1	258.7	258.4	258.0	257.7	257.4	257.0	257.4	257.7	258.0



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	289.8	289.7	289.6	289.5	289.2	289.1	288.8	288.6	288.8	289.1	289.2
115°	337.5	337.9	338.3	338.2	337.6	337.2	336.6	336.0	336.6	337.2	337.6
117.5°	384.3	384.8	385.2	385.2	384.9	384.5	384.2	383.8	384.2	384.5	384.9
120°	416.1	417.0	417.9	417.8	416.8	415.7	414.6	413.6	414.6	415.7	416.8
122.5°	446.9	447.3	447.8	447.7	446.9	446.1	445.4	444.6	445.4	446.1	446.9
125°	493.4	493.7	494.1	493.9	493.5	492.9	492.4	491.9	492.4	492.9	493.5
127.5°	539.6	540.0	540.3	540.0	538.8	537.7	536.6	535.5	536.6	537.7	538.8
130°	569.6	570.1	570.7	570.2	568.8	567.4	566.0	564.6	566.0	567.4	568.8
132.5°	599.0	599.4	599.8	599.4	597.9	596.5	595.1	593.7	595.1	596.5	597.9
135°	642.5	642.6	642.8	642.4	641.3	640.2	639.2	638.2	639.2	640.2	641.3
137.5°	684.4	683.9	683.4	682.8	681.9	681.0	680.2	679.3	680.2	681.0	681.9
140°	712.1	711.9	711.8	711.2	710.3	709.5	708.6	707.7	708.6	709.5	710.3
142.5°	738.4	738.1	737.8	737.2	736.3	735.5	734.5	733.6	734.5	735.5	736.3
145°	777.1	776.5	776.0	775.5	775.2	774.8	774.5	774.1	774.5	774.8	775.2
147.5°	813.7	813.2	812.7	812.1	811.5	810.9	810.2	809.6	810.2	810.9	811.5
150°	836.7	836.4	836.0	835.7	835.3	835.0	834.6	834.2	834.6	835.0	835.3
152.5°	857.2	857.1	856.8	856.4	856.0	855.5	855.0	854.5	855.0	855.5	856.0
155°	886.8	886.7	886.5	886.5	886.5	886.5	886.5	886.5	886.5	886.5	886.5
157.5°	913.1	912.9	912.8	912.8	913.0	913.2	913.5	913.6	913.5	913.2	913.0
160°	929.2	929.2	929.2	929.3	929.7	930.0	930.3	930.7	930.3	930.0	929.7
162.5°	944.0	943.9	943.8	944.0	944.4	944.9	945.4	945.9	945.4	944.9	944.4
165°	963.1	963.1	963.1	963.5	963.9	964.5	965.0	965.5	965.0	964.5	963.9
167.5°	978.3	978.3	978.1	978.3	979.1	979.8	980.5	981.2	980.5	979.8	979.1
170°	986.9	986.9	986.9	987.2	987.9	988.6	989.4	990.1	989.4	988.6	987.9
172.5°	993.8	993.8	993.8	994.2	994.9	995.6	996.3	997.0	996.3	995.6	994.9
175°	1001.1	1001.1	1001.1	1001.5	1002.2	1002.8	1003.5	1004.2	1003.5	1002.8	1002.2
177.5°	1004.7	1004.7	1004.7	1005.0	1005.6	1006.2	1006.7	1007.3	1006.7	1006.2	1005.6
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	952.3	947.9	945.0	938.3	934.0	929.4	924.7	927.7	927.4	927.0	927.0
5°	920.4	910.8	902.1	890.9	883.8	875.1	868.5	867.7	869.3	863.5	860.2
7.5°	888.7	875.6	863.2	850.9	837.8	827.4	820.8	817.7	813.5	809.9	806.2
10°	866.4	851.0	839.0	823.7	809.6	797.2	789.3	783.9	780.9	778.1	772.7
12.5°	843.5	828.5	813.2	795.8	782.4	767.9	762.1	756.0	750.4	747.2	739.8
15°	810.0	790.5	774.4	756.1	741.2	727.1	718.7	706.7	705.0	700.9	693.5
17.5°	776.4	755.3	732.9	719.5	702.6	687.9	675.3	671.2	659.3	654.9	648.4
20°	749.9	730.4	713.4	695.5	671.1	657.4	647.5	642.1	632.5	626.7	622.5
22.5°	727.0	707.2	687.5	666.7	646.5	631.1	623.8	615.4	610.3	602.1	597.6
25°	694.3	672.7	649.1	626.7	612.2	600.6	588.9	581.5	574.0	570.3	562.0
27.5°	656.3	633.7	611.6	594.7	576.9	565.4	554.8	548.2	539.2	533.0	528.4
30°	635.4	608.9	589.8	574.4	551.6	540.8	533.0	524.7	518.0	511.4	506.8
32.5°	611.2	586.9	568.9	549.9	532.3	520.6	510.4	503.1	497.4	491.2	486.6
35°	573.1	552.9	534.2	515.1	502.2	490.2	478.2	472.0	466.6	460.8	456.6
37.5°	538.8	519.8	502.1	484.0	468.1	458.3	448.6	443.9	436.6	432.7	428.4
40°	517.6	498.9	479.8	462.5	445.8	438.4	429.7	422.6	416.0	413.1	408.5
42.5°	494.4	475.7	459.6	440.8	427.3	417.2	409.1	401.4	396.4	392.2	389.6
45°	459.9	443.4	427.6	408.9	396.1	387.4	378.3	371.2	366.6	363.8	359.2
47.5°	426.5	410.0	394.0	377.6	365.2	355.3	346.2	341.3	335.2	331.6	328.6
50°	402.3	387.4	370.3	355.5	343.0	333.0	325.6	319.3	313.9	309.4	307.4
52.5°	380.1	364.2	349.4	335.6	322.4	311.2	304.4	297.8	293.7	288.5	286.1
55°	343.4	328.0	315.6	301.9	289.1	279.6	271.2	265.5	261.3	255.5	252.2
57.5°	309.0	295.2	280.4	268.5	255.2	247.2	240.3	232.4	227.4	222.8	219.6
60°	285.7	270.0	257.1	246.0	234.3	223.9	217.8	211.5	206.1	201.5	198.7
62.5°	261.6	247.8	235.6	223.4	212.8	203.7	196.5	191.3	186.6	183.6	180.8
65°	224.3	213.6	201.1	191.2	181.3	174.6	168.8	164.2	160.9	158.8	156.4
67.5°	190.2	179.7	168.9	159.1	152.5	147.4	143.6	139.7	138.0	135.4	133.7
70°	167.9	157.2	147.7	140.2	133.6	129.8	127.3	124.5	122.8	119.5	117.8
72.5°	143.8	135.9	129.0	122.9	117.6	114.2	111.1	107.5	104.9	101.2	99.6
75°	113.2	106.2	100.8	96.6	93.3	88.7	84.2	80.5	79.2	78.0	77.6
77.5°	83.9	79.4	75.5	72.0	67.9	64.6	63.5	62.7	62.4	61.8	61.8
80°	65.9	61.8	58.9	54.7	52.3	52.3	52.3	51.4	51.8	51.8	51.8
82.5°	49.0	45.2	43.6	42.1	41.7	42.0	42.0	42.1	41.9	42.5	42.2
85°	25.3	25.7	26.5	26.1	26.5	26.5	27.4	26.9	27.4	26.5	27.4
87.5°	10.9	12.3	13.1	13.9	14.7	14.7	15.2	15.4	15.8	16.0	16.1
90°	7.8	9.8	12.1	14.4	16.7	19.0	19.6	20.4	21.1	21.8	22.3
92.5°	23.9	25.2	26.5	27.7	29.1	30.3	30.9	31.5	32.1	32.6	32.8
95°	51.6	52.9	54.3	55.7	57.1	58.5	59.3	59.9	60.6	61.3	61.7
97.5°	86.5	87.5	88.5	89.5	90.5	91.6	92.4	93.2	94.0	94.8	95.1
100°	111.8	112.7	113.6	114.5	115.3	116.2	116.8	117.3	117.8	118.4	118.8
102.5°	138.6	139.4	140.6	141.7	142.9	144.1	144.6	145.1	145.7	146.2	146.4
105°	179.4	180.3	181.9	183.5	185.1	186.6	186.6	186.6	186.6	186.6	186.8
107.5°	227.5	227.9	228.5	229.2	229.8	230.4	231.0	231.6	232.1	232.7	232.8
110°	258.4	258.7	259.1	259.4	259.8	260.2	260.9	261.6	262.3	263.0	263.2



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	289.5	289.6	289.7	289.8	289.9	289.9	290.7	291.6	292.4	293.3	293.7
115°	338.2	338.3	337.9	337.5	337.2	336.8	337.1	337.2	337.4	337.5	337.5
117.5°	385.2	385.2	384.8	384.3	383.8	383.3	383.3	383.3	383.3	383.3	382.9
120°	417.8	417.9	417.0	416.1	415.3	414.4	414.2	414.0	413.8	413.7	413.4
122.5°	447.7	447.8	447.3	446.9	446.5	446.0	445.5	445.0	444.7	444.2	443.7
125°	493.9	494.1	493.7	493.4	493.0	492.7	491.9	491.2	490.5	489.8	489.1
127.5°	540.0	540.3	540.0	539.6	539.2	538.8	537.8	536.9	535.9	534.9	534.0
130°	570.2	570.7	570.1	569.6	569.1	568.5	567.8	567.1	566.4	565.8	564.7
132.5°	599.4	599.8	599.4	599.0	598.7	598.3	597.5	596.6	595.8	594.9	594.1
135°	642.4	642.8	642.6	642.5	642.3	642.1	641.4	640.7	640.0	639.3	638.7
137.5°	682.8	683.4	683.9	684.4	684.8	685.2	684.5	683.8	683.1	682.3	681.6
140°	711.2	711.8	711.9	712.1	712.3	712.5	712.3	712.1	711.9	711.8	711.1
142.5°	737.2	737.8	738.1	738.4	738.7	739.0	738.9	738.7	738.6	738.3	737.8
145°	775.5	776.0	776.5	777.1	777.6	778.1	777.9	777.8	777.6	777.4	777.0
147.5°	812.1	812.7	813.2	813.7	814.1	814.7	814.7	814.7	814.7	814.7	814.1
150°	835.7	836.0	836.4	836.7	837.1	837.4	837.4	837.4	837.4	837.4	836.9
152.5°	856.4	856.8	857.1	857.2	857.5	857.7	857.9	858.3	858.5	858.8	858.5
155°	886.5	886.5	886.7	886.8	887.1	887.2	888.0	888.7	889.4	890.0	889.8
157.5°	912.8	912.8	912.9	913.1	913.2	913.3	914.1	914.8	915.5	916.3	916.2
160°	929.3	929.2	929.2	929.2	929.2	929.2	930.0	930.9	931.8	932.6	932.7
162.5°	944.0	943.8	943.9	944.0	944.2	944.4	945.2	946.1	947.0	947.8	947.7
165°	963.5	963.1	963.1	963.1	963.1	963.1	964.2	965.3	966.3	967.3	967.3
167.5°	978.3	978.1	978.3	978.3	978.5	978.7	979.8	980.8	981.9	983.0	983.0
170°	987.2	986.9	986.9	986.9	986.9	986.9	988.1	989.4	990.5	991.8	991.8
172.5°	994.2	993.8	993.8	993.8	993.8	993.8	994.9	996.0	997.1	998.1	998.1
175°	1001.5	1001.1	1001.1	1001.1	1001.1	1001.1	1002.2	1003.2	1004.2	1005.4	1005.2
177.5°	1005.0	1004.7	1004.7	1004.7	1004.7	1004.7	1005.6	1006.5	1007.3	1008.1	1008.1
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	923.1	922.7	923.1	921.7	923.1	922.7	923.1	927.0	927.0	927.4	927.7
5°	859.0	858.5	857.3	853.6	857.3	858.5	859.0	860.2	863.5	869.3	867.7
7.5°	803.0	802.4	798.8	798.8	798.8	802.4	803.0	806.2	809.9	813.5	817.7
10°	769.8	770.2	765.2	762.3	765.2	770.2	769.8	772.7	778.1	780.9	783.9
12.5°	737.6	735.7	731.7	728.5	731.7	735.7	737.6	739.8	747.2	750.4	756.0
15°	695.1	690.9	681.0	681.8	681.0	690.9	695.1	693.5	700.9	705.0	706.7
17.5°	645.1	642.1	641.8	636.0	641.8	642.1	645.1	648.4	654.9	659.3	671.2
20°	615.9	613.9	614.7	608.9	614.7	613.9	615.9	622.5	626.7	632.5	642.1
22.5°	593.0	591.0	587.5	585.7	587.5	591.0	593.0	597.6	602.1	610.3	615.4
25°	559.5	556.2	552.9	554.9	552.9	556.2	559.5	562.0	570.3	574.0	581.5
27.5°	526.0	523.5	520.1	519.8	520.1	523.5	526.0	528.4	533.0	539.2	548.2
30°	504.8	502.2	500.6	498.5	500.6	502.2	504.8	506.8	511.4	518.0	524.7
32.5°	483.2	482.7	479.7	479.3	479.7	482.7	483.2	486.6	491.2	497.4	503.1
35°	455.0	452.5	451.6	452.1	451.6	452.5	455.0	456.6	460.8	466.6	472.0
37.5°	428.2	424.8	423.3	421.9	423.3	424.8	428.2	428.4	432.7	436.6	443.9
40°	408.9	405.6	404.8	403.9	404.8	405.6	408.9	408.5	413.1	416.0	422.6
42.5°	387.4	386.0	385.6	384.0	385.6	386.0	387.4	389.6	392.2	396.4	401.4
45°	357.9	357.5	355.1	355.8	355.1	357.5	357.9	359.2	363.8	366.6	371.2
47.5°	326.9	325.1	323.4	324.5	323.4	325.1	326.9	328.6	331.6	335.2	341.3
50°	305.7	304.8	301.1	301.9	301.1	304.8	305.7	307.4	309.4	313.9	319.3
52.5°	284.5	281.3	279.9	279.4	279.9	281.3	284.5	286.1	288.5	293.7	297.8
55°	249.3	245.5	243.8	243.0	243.8	245.5	249.3	252.2	255.5	261.3	265.5
57.5°	214.8	213.7	212.5	213.3	212.5	213.7	214.8	219.6	222.8	227.4	232.4
60°	194.5	194.5	194.5	194.1	194.5	194.5	194.5	198.7	201.5	206.1	211.5
62.5°	179.0	177.9	177.6	178.2	177.6	177.9	179.0	180.8	183.6	186.6	191.3
65°	155.1	154.7	153.0	152.7	153.0	154.7	155.1	156.4	158.8	160.9	164.2
67.5°	132.6	131.1	130.6	130.1	130.6	131.1	132.6	133.7	135.4	138.0	139.7
70°	115.7	114.9	112.4	112.8	112.4	114.9	115.7	117.8	119.5	122.8	124.5
72.5°	97.4	96.6	96.2	95.5	96.2	96.6	97.4	99.6	101.2	104.9	107.5
75°	77.2	76.8	76.3	78.0	76.3	76.8	77.2	77.6	78.0	79.2	80.5
77.5°	61.8	61.8	62.0	61.4	62.0	61.8	61.8	61.8	61.8	62.4	62.7
80°	51.8	51.8	51.4	51.4	51.4	51.8	51.8	51.8	51.8	51.8	51.4
82.5°	41.6	41.9	42.1	41.5	42.1	41.9	41.6	42.2	42.5	41.9	42.1
85°	27.4	26.9	27.8	27.4	27.8	26.9	27.4	27.4	26.5	27.4	26.9
87.5°	16.8	16.2	16.3	16.7	16.3	16.2	16.8	16.1	16.0	15.8	15.4
90°	22.7	23.1	23.4	23.7	23.4	23.1	22.7	22.3	21.8	21.1	20.4
92.5°	32.6	32.4	32.2	31.9	32.2	32.4	32.6	32.8	32.6	32.1	31.5
95°	61.7	61.7	61.7	61.7	61.7	61.7	61.7	61.7	61.3	60.6	59.9
97.5°	95.1	95.1	95.0	94.9	95.0	95.1	95.1	95.1	94.8	94.0	93.2
100°	119.1	119.5	119.9	120.2	119.9	119.5	119.1	118.8	118.4	117.8	117.3
102.5°	146.3	146.2	146.2	146.2	146.2	146.2	146.3	146.4	146.2	145.7	145.1
105°	187.1	187.5	187.8	188.2	187.8	187.5	187.1	186.8	186.6	186.6	186.6
107.5°	232.7	232.4	232.2	232.0	232.2	232.4	232.7	232.8	232.7	232.1	231.6
110°	262.8	262.4	262.1	261.7	262.1	262.4	262.8	263.2	263.0	262.3	261.6



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	293.6	293.5	293.4	293.3	293.4	293.5	293.6	293.7	293.3	292.4	291.6
115°	337.4	337.2	337.1	336.8	337.1	337.2	337.4	337.5	337.5	337.4	337.2
117.5°	382.5	382.0	381.5	381.0	381.5	382.0	382.5	382.9	383.3	383.3	383.3
120°	413.0	412.7	412.3	412.0	412.3	412.7	413.0	413.4	413.7	413.8	414.0
122.5°	443.2	442.7	442.2	441.7	442.2	442.7	443.2	443.7	444.2	444.7	445.0
125°	488.5	487.7	487.0	486.3	487.0	487.7	488.5	489.1	489.8	490.5	491.2
127.5°	533.2	532.3	531.6	530.8	531.6	532.3	533.2	534.0	534.9	535.9	536.9
130°	563.6	562.3	561.1	559.8	561.1	562.3	563.6	564.7	565.8	566.4	567.1
132.5°	593.1	592.2	591.2	590.3	591.2	592.2	593.1	594.1	594.9	595.8	596.6
135°	638.4	638.0	637.7	637.4	637.7	638.0	638.4	638.7	639.3	640.0	640.7
137.5°	681.0	680.2	679.6	679.0	679.6	680.2	681.0	681.6	682.3	683.1	683.8
140°	709.9	708.6	707.4	706.2	707.4	708.6	709.9	711.1	711.8	711.9	712.1
142.5°	736.8	735.9	734.9	734.0	734.9	735.9	736.8	737.8	738.3	738.6	738.7
145°	776.3	775.5	774.8	774.1	774.8	775.5	776.3	777.0	777.4	777.6	777.8
147.5°	813.1	812.0	811.0	809.9	811.0	812.0	813.1	814.1	814.7	814.7	814.7
150°	835.8	834.8	833.7	832.7	833.7	834.8	835.8	836.9	837.4	837.4	837.4
152.5°	857.5	856.7	855.7	854.8	855.7	856.7	857.5	858.5	858.8	858.5	858.3
155°	888.6	887.3	886.1	884.9	886.1	887.3	888.6	889.8	890.0	889.4	888.7
157.5°	915.2	914.2	913.2	912.2	913.2	914.2	915.2	916.2	916.3	915.5	914.8
160°	932.1	931.4	930.7	929.9	930.7	931.4	932.1	932.7	932.6	931.8	930.9
162.5°	946.6	945.5	944.4	943.3	944.4	945.5	946.6	947.7	947.8	947.0	946.1
165°	966.1	964.8	963.6	962.3	963.6	964.8	966.1	967.3	967.3	966.3	965.3
167.5°	981.9	980.8	979.8	978.7	979.8	980.8	981.9	983.0	983.0	981.9	980.8
170°	990.5	989.4	988.1	986.9	988.1	989.4	990.5	991.8	991.8	990.5	989.4
172.5°	996.9	995.7	994.4	993.2	994.4	995.7	996.9	998.1	998.1	997.1	996.0
175°	1004.0	1002.7	1001.6	1000.3	1001.6	1002.7	1004.0	1005.2	1005.4	1004.2	1003.2
177.5°	1007.1	1006.1	1005.1	1004.1	1005.1	1006.1	1007.1	1008.1	1008.1	1007.3	1006.5
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	924.7	929.4	934.0	938.3	945.0	947.9	952.3	953.9	958.9	966.2	972.2
5°	868.5	875.1	883.8	890.9	902.1	910.8	920.4	929.5	940.2	955.6	969.2
7.5°	820.8	827.4	837.8	850.9	863.2	875.6	888.7	901.1	916.5	938.5	960.3
10°	789.3	797.2	809.6	823.7	839.0	851.0	866.4	882.2	901.3	926.5	952.7
12.5°	762.1	767.9	782.4	795.8	813.2	828.5	843.5	861.9	883.7	910.6	942.1
15°	718.7	727.1	741.2	756.1	774.4	790.5	810.0	832.4	853.6	886.8	924.9
17.5°	675.3	687.9	702.6	719.5	732.9	755.3	776.4	799.4	825.5	860.6	902.5
20°	647.5	657.4	671.1	695.5	713.4	730.4	749.9	778.5	802.6	842.3	885.9
22.5°	623.8	631.1	646.5	666.7	687.5	707.2	727.0	754.2	783.9	821.8	868.9
25°	588.9	600.6	612.2	626.7	649.1	672.7	694.3	717.5	749.0	789.3	840.3
27.5°	554.8	565.4	576.9	594.7	611.6	633.7	656.3	682.9	716.8	759.3	811.1
30°	533.0	540.8	551.6	574.4	589.8	608.9	635.4	659.0	690.5	735.8	790.5
32.5°	510.4	520.6	532.3	549.9	568.9	586.9	611.2	636.8	669.0	713.5	769.6
35°	478.2	490.2	502.2	515.1	534.2	552.9	573.1	601.3	634.1	677.3	732.5
37.5°	448.6	458.3	468.1	484.0	502.1	519.8	538.8	566.6	597.5	644.0	694.6
40°	429.7	438.4	445.8	462.5	479.8	498.9	517.6	542.1	575.3	618.8	667.7
42.5°	409.1	417.2	427.3	440.8	459.6	475.7	494.4	517.5	548.7	592.9	635.9
45°	378.3	387.4	396.1	408.9	427.6	443.4	459.9	482.0	513.9	550.4	588.5
47.5°	346.2	355.3	365.2	377.6	394.0	410.0	426.5	446.0	475.2	511.0	536.7
50°	325.6	333.0	343.0	355.5	370.3	387.4	402.3	423.4	451.2	479.4	501.8
52.5°	304.4	311.2	322.4	335.6	349.4	364.2	380.1	398.2	423.3	449.9	467.7
55°	271.2	279.6	289.1	301.9	315.6	328.0	343.4	362.1	382.0	401.9	413.9
57.5°	240.3	247.2	255.2	268.5	280.4	295.2	309.0	323.5	341.9	357.0	364.8
60°	217.8	223.9	234.3	246.0	257.1	270.0	285.7	300.3	314.4	326.4	332.6
62.5°	196.5	203.7	212.8	223.4	235.6	247.8	261.6	273.7	286.1	296.5	300.8
65°	168.8	174.6	181.3	191.2	201.1	213.6	224.3	236.8	246.0	251.8	255.5
67.5°	143.6	147.4	152.5	159.1	168.9	179.7	190.2	199.9	207.6	211.5	214.8
70°	127.3	129.8	133.6	140.2	147.7	157.2	167.9	175.0	181.6	185.0	188.3
72.5°	111.1	114.2	117.6	122.9	129.0	135.9	143.8	152.5	156.1	160.1	162.1
75°	84.2	88.7	93.3	96.6	100.8	106.2	113.2	118.6	120.7	124.0	124.5
77.5°	63.5	64.6	67.9	72.0	75.5	79.4	83.9	88.6	89.7	91.4	92.5
80°	52.3	52.3	52.3	54.7	58.9	61.8	65.9	68.4	70.1	70.5	70.9
82.5°	42.0	42.0	41.7	42.1	43.6	45.2	49.0	51.8	53.2	52.9	52.0
85°	27.4	26.5	26.5	26.1	26.5	25.7	25.3	26.9	29.5	29.5	28.6
87.5°	15.2	14.7	14.7	13.9	13.1	12.3	10.9	10.9	10.5	11.5	10.8
90°	19.6	19.0	16.7	14.4	12.1	9.8	7.8	6.1	4.3	2.5	0.8
92.5°	30.9	30.3	29.1	27.7	26.5	25.2	23.9	22.7	21.5	20.4	19.2
95°	59.3	58.5	57.1	55.7	54.3	52.9	51.6	50.4	49.1	47.8	46.7
97.5°	92.4	91.6	90.5	89.5	88.5	87.5	86.5	85.6	84.7	83.8	82.9
100°	116.8	116.2	115.3	114.5	113.6	112.7	111.8	110.7	109.6	108.6	107.6
102.5°	144.6	144.1	142.9	141.7	140.6	139.4	138.6	137.9	137.3	136.7	136.0
105°	186.6	186.6	185.1	183.5	181.9	180.3	179.4	179.0	178.6	178.2	177.9
107.5°	231.0	230.4	229.8	229.2	228.5	227.9	227.5	227.3	227.0	226.9	226.6
110°	260.9	260.2	259.8	259.4	259.1	258.7	258.4	258.0	257.7	257.4	257.0



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	290.7	289.9	289.9	289.8	289.7	289.6	289.5	289.2	289.1	288.8	288.6
115°	337.1	336.8	337.2	337.5	337.9	338.3	338.2	337.6	337.2	336.6	336.0
117.5°	383.3	383.3	383.8	384.3	384.8	385.2	385.2	384.9	384.5	384.2	383.8
120°	414.2	414.4	415.3	416.1	417.0	417.9	417.8	416.8	415.7	414.6	413.6
122.5°	445.5	446.0	446.5	446.9	447.3	447.8	447.7	446.9	446.1	445.4	444.6
125°	491.9	492.7	493.0	493.4	493.7	494.1	493.9	493.5	492.9	492.4	491.9
127.5°	537.8	538.8	539.2	539.6	540.0	540.3	540.0	538.8	537.7	536.6	535.5
130°	567.8	568.5	569.1	569.6	570.1	570.7	570.2	568.8	567.4	566.0	564.6
132.5°	597.5	598.3	598.7	599.0	599.4	599.8	599.4	597.9	596.5	595.1	593.7
135°	641.4	642.1	642.3	642.5	642.6	642.8	642.4	641.3	640.2	639.2	638.2
137.5°	684.5	685.2	684.8	684.4	683.9	683.4	682.8	681.9	681.0	680.2	679.3
140°	712.3	712.5	712.3	712.1	711.9	711.8	711.2	710.3	709.5	708.6	707.7
142.5°	738.9	739.0	738.7	738.4	738.1	737.8	737.2	736.3	735.5	734.5	733.6
145°	777.9	778.1	777.6	777.1	776.5	776.0	775.5	775.2	774.8	774.5	774.1
147.5°	814.7	814.7	814.1	813.7	813.2	812.7	812.1	811.5	810.9	810.2	809.6
150°	837.4	837.4	837.1	836.7	836.4	836.0	835.7	835.3	835.0	834.6	834.2
152.5°	857.9	857.7	857.5	857.2	857.1	856.8	856.4	856.0	855.5	855.0	854.5
155°	888.0	887.2	887.1	886.8	886.7	886.5	886.5	886.5	886.5	886.5	886.5
157.5°	914.1	913.3	913.2	913.1	912.9	912.8	912.8	913.0	913.2	913.5	913.6
160°	930.0	929.2	929.2	929.2	929.2	929.2	929.3	929.7	930.0	930.3	930.7
162.5°	945.2	944.4	944.2	944.0	943.9	943.8	944.0	944.4	944.9	945.4	945.9
165°	964.2	963.1	963.1	963.1	963.1	963.1	963.5	963.9	964.5	965.0	965.5
167.5°	979.8	978.7	978.5	978.3	978.3	978.1	978.3	979.1	979.8	980.5	981.2
170°	988.1	986.9	986.9	986.9	986.9	986.9	987.2	987.9	988.6	989.4	990.1
172.5°	994.9	993.8	993.8	993.8	993.8	993.8	994.2	994.9	995.6	996.3	997.0
175°	1002.2	1001.1	1001.1	1001.1	1001.1	1001.1	1001.5	1002.2	1002.8	1003.5	1004.2
177.5°	1005.6	1004.7	1004.7	1004.7	1004.7	1004.7	1005.0	1005.6	1006.2	1006.7	1007.3
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	974.1	977.8	982.5	989.4	994.7	999.3	1000.4	1001.7	1005.0	1010.7	1014.9
5°	980.5	990.0	1005.4	1020.3	1036.5	1049.7	1062.2	1070.9	1079.2	1096.6	1110.7
7.5°	978.5	999.7	1023.7	1050.6	1077.7	1104.0	1128.4	1150.2	1171.9	1197.3	1226.2
10°	977.2	1002.0	1034.4	1068.8	1106.5	1143.4	1179.2	1206.9	1239.3	1268.3	1305.2
12.5°	970.8	1006.7	1045.4	1089.4	1135.8	1178.3	1225.3	1263.7	1300.7	1342.6	1385.5
15°	962.7	1006.2	1055.1	1113.6	1184.1	1235.6	1283.7	1350.4	1396.1	1441.7	1503.0
17.5°	947.6	1000.8	1061.9	1137.9	1196.7	1265.8	1338.2	1391.0	1452.5	1516.7	1572.3
20°	935.6	997.4	1065.9	1140.6	1215.6	1290.7	1360.8	1423.8	1487.3	1561.5	1607.2
22.5°	923.8	984.8	1056.0	1135.3	1215.9	1295.0	1374.4	1448.3	1519.8	1594.7	1653.0
25°	898.3	970.9	1048.1	1128.9	1208.6	1295.7	1390.2	1472.7	1561.1	1638.2	1693.4
27.5°	872.6	939.1	1016.0	1098.0	1186.5	1289.4	1400.7	1494.5	1583.0	1638.2	1655.6
30°	849.4	919.9	990.4	1073.8	1169.6	1284.4	1402.6	1510.1	1582.7	1606.7	1588.9
32.5°	825.9	889.7	959.6	1044.9	1146.7	1272.2	1405.3	1500.8	1544.5	1526.1	1453.5
35°	784.3	841.9	909.5	995.0	1111.9	1265.4	1394.4	1459.0	1448.3	1344.6	1207.8
37.5°	739.8	786.8	849.4	938.7	1075.9	1238.4	1347.3	1356.8	1263.5	1104.3	946.2
40°	704.6	746.9	811.3	904.6	1048.1	1211.9	1299.8	1261.2	1116.5	939.4	807.6
42.5°	670.5	706.2	768.1	868.7	1021.5	1175.8	1229.2	1145.1	978.1	810.6	690.7
45°	612.6	646.2	708.4	811.7	967.2	1106.5	1099.5	953.5	786.4	651.6	552.0
47.5°	557.7	587.0	645.4	750.8	903.4	1002.8	936.9	781.6	639.8	531.6	460.7
50°	518.9	547.9	605.9	710.0	852.3	924.9	830.8	681.0	551.2	461.6	405.2
52.5°	481.7	510.1	563.2	664.6	790.6	834.0	732.8	594.1	485.8	408.5	360.0
55°	429.7	451.2	498.9	596.0	690.1	700.1	597.6	481.5	392.4	338.4	305.2
57.5°	376.7	395.2	442.4	519.7	585.7	580.6	483.5	382.9	322.9	282.9	258.8
60°	342.1	360.4	401.9	468.3	518.0	500.6	411.5	330.6	279.1	249.7	230.6
62.5°	310.0	324.2	363.1	411.5	447.3	427.6	351.7	284.8	244.0	219.1	204.1
65°	263.4	275.0	306.1	331.4	351.3	332.2	269.2	222.7	193.3	175.9	165.5
67.5°	219.0	226.5	246.1	255.2	269.3	248.3	202.4	171.3	154.6	139.8	132.6
70°	191.2	196.6	207.0	214.4	218.2	196.6	162.6	139.7	125.6	115.3	110.7
72.5°	163.3	168.0	170.2	176.3	174.4	154.2	130.7	112.6	102.4	95.4	89.5
75°	124.8	126.9	124.8	122.3	116.9	102.8	86.7	77.6	70.1	66.8	64.7
77.5°	91.0	90.3	87.5	83.6	74.4	65.5	56.8	53.8	50.5	48.8	48.0
80°	70.1	68.4	65.9	59.7	51.8	45.6	43.6	41.5	40.2	38.2	37.7
82.5°	52.2	51.2	47.1	41.8	36.3	33.4	31.6	30.9	29.6	28.5	28.4
85°	27.8	26.5	21.9	19.1	18.2	17.4	17.0	17.0	15.4	14.9	14.9
87.5°	9.5	7.8	7.8	7.2	7.6	7.4	8.2	8.0	8.1	8.6	8.1
90°	2.5	4.3	6.1	7.8	9.8	12.1	14.4	16.7	19.0	19.6	20.4
92.5°	20.4	21.5	22.7	23.9	25.2	26.5	27.7	29.1	30.3	30.9	31.5
95°	47.8	49.1	50.4	51.6	52.9	54.3	55.7	57.1	58.5	59.3	59.9
97.5°	83.8	84.7	85.6	86.5	87.5	88.5	89.5	90.5	91.6	92.4	93.2
100°	108.6	109.6	110.7	111.8	112.7	113.6	114.5	115.3	116.2	116.8	117.3
102.5°	136.7	137.3	137.9	138.6	139.4	140.6	141.7	142.9	144.1	144.6	145.1
105°	178.2	178.6	179.0	179.4	180.3	181.9	183.5	185.1	186.6	186.6	186.6
107.5°	226.9	227.0	227.3	227.5	227.9	228.5	229.2	229.8	230.4	231.0	231.6
110°	257.4	257.7	258.0	258.4	258.7	259.1	259.4	259.8	260.2	260.9	261.6



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	288.8	289.1	289.2	289.5	289.6	289.7	289.8	289.9	289.9	290.7	291.6
115°	336.6	337.2	337.6	338.2	338.3	337.9	337.5	337.2	336.8	337.1	337.2
117.5°	384.2	384.5	384.9	385.2	385.2	384.8	384.3	383.8	383.3	383.3	383.3
120°	414.6	415.7	416.8	417.8	417.9	417.0	416.1	415.3	414.4	414.2	414.0
122.5°	445.4	446.1	446.9	447.7	447.8	447.3	446.9	446.5	446.0	445.5	445.0
125°	492.4	492.9	493.5	493.9	494.1	493.7	493.4	493.0	492.7	491.9	491.2
127.5°	536.6	537.7	538.8	540.0	540.3	540.0	539.6	539.2	538.8	537.8	536.9
130°	566.0	567.4	568.8	570.2	570.7	570.1	569.6	569.1	568.5	567.8	567.1
132.5°	595.1	596.5	597.9	599.4	599.8	599.4	599.0	598.7	598.3	597.5	596.6
135°	639.2	640.2	641.3	642.4	642.8	642.6	642.5	642.3	642.1	641.4	640.7
137.5°	680.2	681.0	681.9	682.8	683.4	683.9	684.4	684.8	685.2	684.5	683.8
140°	708.6	709.5	710.3	711.2	711.8	711.9	712.1	712.3	712.5	712.3	712.1
142.5°	734.5	735.5	736.3	737.2	737.8	738.1	738.4	738.7	739.0	738.9	738.7
145°	774.5	774.8	775.2	775.5	776.0	776.5	777.1	777.6	778.1	777.9	777.8
147.5°	810.2	810.9	811.5	812.1	812.7	813.2	813.7	814.1	814.7	814.7	814.7
150°	834.6	835.0	835.3	835.7	836.0	836.4	836.7	837.1	837.4	837.4	837.4
152.5°	855.0	855.5	856.0	856.4	856.8	857.1	857.2	857.5	857.7	857.9	858.3
155°	886.5	886.5	886.5	886.5	886.5	886.7	886.8	887.1	887.2	888.0	888.7
157.5°	913.5	913.2	913.0	912.8	912.8	912.9	913.1	913.2	913.3	914.1	914.8
160°	930.3	930.0	929.7	929.3	929.2	929.2	929.2	929.2	929.2	930.0	930.9
162.5°	945.4	944.9	944.4	944.0	943.8	943.9	944.0	944.2	944.4	945.2	946.1
165°	965.0	964.5	963.9	963.5	963.1	963.1	963.1	963.1	963.1	964.2	965.3
167.5°	980.5	979.8	979.1	978.3	978.1	978.3	978.3	978.5	978.7	979.8	980.8
170°	989.4	988.6	987.9	987.2	986.9	986.9	986.9	986.9	986.9	988.1	989.4
172.5°	996.3	995.6	994.9	994.2	993.8	993.8	993.8	993.8	993.8	994.9	996.0
175°	1003.5	1002.8	1002.2	1001.5	1001.1	1001.1	1001.1	1001.1	1001.1	1002.2	1003.2
177.5°	1006.7	1006.2	1005.6	1005.0	1004.7	1004.7	1004.7	1004.7	1004.7	1005.6	1006.5
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1021.9	1021.9	1023.3	1028.3	1028.9	1033.2	1031.9
5°	1123.2	1131.0	1133.9	1146.4	1153.8	1157.1	1150.5
7.5°	1246.9	1269.2	1279.7	1292.7	1304.2	1307.7	1298.6
10°	1337.1	1360.3	1379.9	1391.9	1403.1	1410.6	1420.1
12.5°	1424.4	1452.9	1471.5	1488.4	1500.0	1509.4	1511.0
15°	1519.2	1562.3	1595.1	1619.1	1631.2	1637.4	1634.9
17.5°	1614.9	1654.9	1678.2	1702.7	1719.4	1720.2	1720.7
20°	1669.0	1707.9	1734.9	1753.1	1771.8	1771.0	1775.1
22.5°	1705.1	1735.8	1756.4	1769.7	1776.2	1773.0	1773.8
25°	1722.0	1731.2	1727.4	1706.3	1700.9	1681.4	1684.7
27.5°	1634.7	1591.7	1547.0	1489.6	1444.3	1408.2	1410.0
30°	1516.3	1440.0	1352.9	1279.9	1214.4	1196.1	1157.1
32.5°	1350.8	1236.3	1134.2	1066.2	1010.0	994.7	960.8
35°	1070.1	958.9	854.0	790.9	766.0	731.2	730.8
37.5°	831.7	733.9	678.3	631.1	606.3	585.2	583.1
40°	699.7	623.4	581.5	547.5	523.0	507.2	503.5
42.5°	607.4	545.7	506.5	485.4	466.6	458.4	452.4
45°	496.1	454.6	427.2	408.1	399.4	393.2	389.8
47.5°	414.9	387.1	368.4	355.8	348.7	342.1	343.9
50°	370.8	348.0	334.3	322.3	316.9	312.3	312.8
52.5°	335.3	314.8	303.7	295.1	288.4	285.1	283.5
55°	284.6	271.6	260.5	254.2	250.5	246.0	244.7
57.5°	242.7	232.7	223.6	216.6	215.6	211.3	211.8
60°	214.8	206.5	199.1	195.4	192.4	188.7	190.0
62.5°	191.9	185.0	178.2	175.1	172.2	169.4	170.1
65°	157.2	150.5	146.4	144.7	143.5	142.3	141.0
67.5°	125.2	121.2	118.6	115.0	112.5	112.1	110.8
70°	105.4	100.0	95.4	90.9	89.6	89.2	89.6
72.5°	84.4	81.0	79.8	77.6	77.3	76.2	77.0
75°	63.5	62.2	61.4	59.7	59.7	59.7	59.7
77.5°	46.8	46.0	45.6	45.2	44.8	44.2	44.1
80°	36.5	36.0	35.3	35.3	34.9	35.3	34.9
82.5°	27.6	27.5	26.6	26.6	26.2	26.0	26.2
85°	14.1	13.7	14.5	13.7	14.1	13.3	14.1
87.5°	8.2	8.3	8.1	8.2	7.9	8.6	8.1
90°	21.1	21.8	22.3	22.7	23.1	23.4	23.7
92.5°	32.1	32.6	32.8	32.6	32.4	32.2	31.9
95°	60.6	61.3	61.7	61.7	61.7	61.7	61.7
97.5°	94.0	94.8	95.1	95.1	95.1	95.0	94.9
100°	117.8	118.4	118.8	119.1	119.5	119.9	120.2
102.5°	145.7	146.2	146.4	146.3	146.2	146.2	146.2
105°	186.6	186.6	186.8	187.1	187.5	187.8	188.2
107.5°	232.1	232.7	232.8	232.7	232.4	232.2	232.0
110°	262.3	263.0	263.2	262.8	262.4	262.1	261.7



TEST NUMBER: P332319-927

CATALOG NUMBER: S123RDIP-S775D1025U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	292.4	293.3	293.7	293.6	293.5	293.4	293.3
115°	337.4	337.5	337.5	337.4	337.2	337.1	336.8
117.5°	383.3	383.3	382.9	382.5	382.0	381.5	381.0
120°	413.8	413.7	413.4	413.0	412.7	412.3	412.0
122.5°	444.7	444.2	443.7	443.2	442.7	442.2	441.7
125°	490.5	489.8	489.1	488.5	487.7	487.0	486.3
127.5°	535.9	534.9	534.0	533.2	532.3	531.6	530.8
130°	566.4	565.8	564.7	563.6	562.3	561.1	559.8
132.5°	595.8	594.9	594.1	593.1	592.2	591.2	590.3
135°	640.0	639.3	638.7	638.4	638.0	637.7	637.4
137.5°	683.1	682.3	681.6	681.0	680.2	679.6	679.0
140°	711.9	711.8	711.1	709.9	708.6	707.4	706.2
142.5°	738.6	738.3	737.8	736.8	735.9	734.9	734.0
145°	777.6	777.4	777.0	776.3	775.5	774.8	774.1
147.5°	814.7	814.7	814.1	813.1	812.0	811.0	809.9
150°	837.4	837.4	836.9	835.8	834.8	833.7	832.7
152.5°	858.5	858.8	858.5	857.5	856.7	855.7	854.8
155°	889.4	890.0	889.8	888.6	887.3	886.1	884.9
157.5°	915.5	916.3	916.2	915.2	914.2	913.2	912.2
160°	931.8	932.6	932.7	932.1	931.4	930.7	929.9
162.5°	947.0	947.8	947.7	946.6	945.5	944.4	943.3
165°	966.3	967.3	967.3	966.1	964.8	963.6	962.3
167.5°	981.9	983.0	983.0	981.9	980.8	979.8	978.7
170°	990.5	991.8	991.8	990.5	989.4	988.1	986.9
172.5°	997.1	998.1	998.1	996.9	995.7	994.4	993.2
175°	1004.2	1005.4	1005.2	1004.0	1002.7	1001.6	1000.3
177.5°	1007.3	1008.1	1008.1	1007.1	1006.1	1005.1	1004.1
180°	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6	1006.6

(END OF REPORT)