

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332302-927

Luminaire Tested: **S123RDIP-S775D365U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332302-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D365U927-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3453.8 lumens  
Efficiency: N/A  
Efficacy: 98.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	103	99	95	92	97	94	91	88	84	82	79	75	73	72	67	66	64	61
2	95	87	81	76	89	83	78	73	75	71	67	67	64	61	60	58	56	52
3	87	78	70	65	82	74	67	62	67	62	57	60	56	53	54	51	48	45
4	80	69	62	56	75	66	59	54	60	54	50	54	50	46	49	45	42	39
5	74	62	54	48	70	59	52	47	54	48	43	49	44	40	44	40	37	35
6	68	56	48	42	64	54	46	41	49	43	38	45	40	36	40	36	33	31
7	63	51	43	38	60	49	42	37	45	39	34	41	36	32	37	33	30	28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	34	30	27	25
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25	23
10	52	40	32	27	49	38	31	27	35	29	25	32	27	24	30	25	22	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10428	10428	10428	10428
5°	12431	10472	9223	10472
10°	15522	10413	8332	10413
15°	18219	10307	7598	10307
20°	20333	10148	6975	10148
25°	20009	9980	6590	9980
30°	14382	9825	6196	9825
35°	9603	9625	5941	9625
40°	7075	9382	5675	9382
45°	5934	8958	5416	8958
50°	5238	8403	5056	8403
55°	4592	7767	4560	7767
60°	4090	7160	4179	7160
65°	3591	6507	3889	6507
70°	2820	5926	3550	5926
75°	2483	5178	3244	5178
80°	2163	4395	3186	4395
85°	1741	3532	3384	3532



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.3	2.8
10°-20°	297.7	8.6
20°-30°	467.6	13.5
30°-40°	487.9	14.1
40°-50°	417.5	12.1
50°-60°	318.2	9.2
60°-70°	204.0	5.9
70°-80°	98.1	2.8
80°-90°	27.0	0.8
90°-100°	77.0	2.2
100°-110°	217.9	6.3
110°-120°	214.4	6.2
120°-130°	171.0	5.0
130°-140°	134.8	3.9
140°-150°	100.6	2.9
150°-160°	70.1	2.0
160°-170°	41.2	1.2
170°-180°	13.4	0.4
0°-30°	860.6	24.9
0°-40°	1348.4	39.0
0°-60°	2084.2	60.3
0°-90°	2413.3	69.9
90°-120°	509.3	14.7
90°-150°	915.7	26.5
90°-180°	1040.0	30.1
0°-180°	3453.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1150	969	854	969	1150	119
15°	1635	925	682	925	1635	464
25°	1685	840	555	840	1685	724
35°	731	732	452	732	731	479
45°	390	588	356	588	390	307
55°	245	414	243	414	245	221
65°	141	256	153	256	141	139
75°	60	124	78	124	60	64
85°	14	29	27	29	14	16
90°	8	1	8	1	8	5
95°	32	10	32	10	32	59
105°	356	32	356	32	356	351
115°	433	57	433	57	433	421
125°	342	80	342	80	342	309
135°	277	94	277	94	277	215
145°	216	107	216	107	216	138
155°	179	121	179	121	179	84
165°	156	132	156	132	156	45
175°	141	138	141	138	141	14
180°	138	138	138	138	138	



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1031.9	1033.2	1028.9	1028.3	1023.3	1021.9	1021.9	1014.9	1010.7	1005.0	1001.7
5°	1150.5	1157.1	1153.8	1146.4	1133.9	1131.0	1123.2	1110.7	1096.6	1079.2	1070.9
7.5°	1298.6	1307.7	1304.2	1292.7	1279.7	1269.2	1246.9	1226.2	1197.3	1171.9	1150.2
10°	1420.1	1410.6	1403.1	1391.9	1379.9	1360.3	1337.1	1305.2	1268.3	1239.3	1206.9
12.5°	1511.0	1509.4	1500.0	1488.4	1471.5	1452.9	1424.4	1385.5	1342.6	1300.7	1263.7
15°	1634.9	1637.4	1631.2	1619.1	1595.1	1562.3	1519.2	1503.0	1441.7	1396.1	1350.4
17.5°	1720.7	1720.2	1719.4	1702.7	1678.2	1654.9	1614.9	1572.3	1516.7	1452.5	1391.0
20°	1775.1	1771.0	1771.8	1753.1	1734.9	1707.9	1669.0	1607.2	1561.5	1487.3	1423.8
22.5°	1773.8	1773.0	1776.2	1769.7	1756.4	1735.8	1705.1	1653.0	1594.7	1519.8	1448.3
25°	1684.7	1681.4	1700.9	1706.3	1727.4	1731.2	1722.0	1693.4	1638.2	1561.1	1472.7
27.5°	1410.0	1408.2	1444.3	1489.6	1547.0	1591.7	1634.7	1655.6	1638.2	1583.0	1494.5
30°	1157.1	1196.1	1214.4	1279.9	1352.9	1440.0	1516.3	1588.9	1606.7	1582.7	1510.1
32.5°	960.8	994.7	1010.0	1066.2	1134.2	1236.3	1350.8	1453.5	1526.1	1544.5	1500.8
35°	730.8	731.2	766.0	790.9	854.0	958.9	1070.1	1207.8	1344.6	1448.3	1459.0
37.5°	583.1	585.2	606.3	631.1	678.3	733.9	831.7	946.2	1104.3	1263.5	1356.8
40°	503.5	507.2	523.0	547.5	581.5	623.4	699.7	807.6	939.4	1116.5	1261.2
42.5°	452.4	458.4	466.6	485.4	506.5	545.7	607.4	690.7	810.6	978.1	1145.1
45°	389.8	393.2	399.4	408.1	427.2	454.6	496.1	552.0	651.6	786.4	953.5
47.5°	343.9	342.1	348.7	355.8	368.4	387.1	414.9	460.7	531.6	639.8	781.6
50°	312.8	312.3	316.9	322.3	334.3	348.0	370.8	405.2	461.6	551.2	681.0
52.5°	283.5	285.1	288.4	295.1	303.7	314.8	335.3	360.0	408.5	485.8	594.1
55°	244.7	246.0	250.5	254.2	260.5	271.6	284.6	305.2	338.4	392.4	481.5
57.5°	211.8	211.3	215.6	216.6	223.6	232.7	242.7	258.8	282.9	322.9	382.9
60°	190.0	188.7	192.4	195.4	199.1	206.5	214.8	230.6	249.7	279.1	330.6
62.5°	170.1	169.4	172.2	175.1	178.2	185.0	191.9	204.1	219.1	244.0	284.8
65°	141.0	142.3	143.5	144.7	146.4	150.5	157.2	165.5	175.9	193.3	222.7
67.5°	110.8	112.1	112.5	115.0	118.6	121.2	125.2	132.6	139.8	154.6	171.3
70°	89.6	89.2	89.6	90.9	95.4	100.0	105.4	110.7	115.3	125.6	139.7
72.5°	77.0	76.2	77.3	77.6	79.8	81.0	84.4	89.5	95.4	102.4	112.6
75°	59.7	59.7	59.7	59.7	61.4	62.2	63.5	64.7	66.8	70.1	77.6
77.5°	44.1	44.2	44.8	45.2	45.6	46.0	46.8	48.0	48.8	50.5	53.8
80°	34.9	35.3	34.9	35.3	35.3	36.0	36.5	37.7	38.2	40.2	41.5
82.5°	26.2	26.0	26.2	26.6	26.6	27.5	27.6	28.4	28.5	29.6	30.9
85°	14.1	13.3	14.1	13.7	14.5	13.7	14.1	14.9	14.9	15.4	17.0
87.5°	4.9	5.6	4.9	5.2	5.3	5.5	5.5	5.4	6.0	5.7	5.9
90°	8.1	8.4	8.1	7.8	8.1	7.5	7.3	7.0	6.7	7.0	6.2
92.5°	13.5	14.0	13.7	14.6	15.1	16.5	18.7	23.6	32.5	43.0	47.4
95°	32.5	33.6	35.6	38.1	43.4	53.5	68.3	100.8	134.7	166.0	147.8
97.5°	88.4	90.8	98.4	111.0	131.7	165.1	201.2	251.2	275.2	257.3	188.4
100°	175.5	175.2	186.2	206.6	234.9	274.6	307.4	330.0	320.3	265.1	179.2
102.5°	257.5	264.0	273.1	289.2	311.2	336.4	355.5	356.2	322.5	250.6	165.7
105°	356.1	357.5	366.5	377.1	390.0	397.2	391.9	363.9	305.4	225.1	149.2
107.5°	412.9	415.4	418.4	422.1	421.8	411.9	387.3	341.8	275.5	202.6	138.7
110°	436.2	436.7	437.3	435.1	427.2	407.6	372.3	320.8	256.7	189.8	134.7



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	440.8	440.8	438.6	431.7	417.3	392.1	352.6	300.0	240.3	181.3	132.4
115°	433.1	431.7	426.0	413.8	392.8	362.3	321.1	272.4	220.6	172.1	131.6
117.5°	408.3	406.4	398.4	384.3	362.3	331.4	294.5	252.4	208.7	166.8	132.1
120°	387.7	386.0	379.3	363.6	341.5	313.2	279.6	241.9	202.4	164.3	133.0
122.5°	368.4	366.3	358.9	344.8	325.2	298.9	267.8	233.6	197.3	162.8	134.5
125°	341.5	339.6	332.6	320.3	302.4	280.0	253.1	222.5	190.7	160.7	136.9
127.5°	319.3	317.6	311.2	300.7	284.8	264.4	240.1	212.9	184.8	159.7	139.6
130°	306.8	304.6	298.7	288.6	273.8	254.8	232.1	206.8	181.6	159.0	141.4
132.5°	294.5	292.9	287.7	277.7	263.7	245.6	224.4	201.3	178.8	158.8	142.8
135°	276.9	274.9	269.9	261.5	247.7	231.8	213.6	193.7	175.0	158.4	144.7
137.5°	258.3	256.9	252.7	244.2	232.7	218.8	203.1	186.8	171.7	157.8	146.1
140°	245.3	245.5	241.1	233.2	222.5	210.5	197.1	182.8	169.6	157.6	146.9
142.5°	233.1	233.4	229.4	222.4	213.3	202.9	191.2	179.0	167.9	157.2	147.7
145°	216.4	215.9	213.6	207.7	200.7	192.6	183.6	174.4	165.4	156.5	148.1
147.5°	202.6	202.4	200.3	196.3	191.0	185.2	178.0	170.6	163.1	155.4	148.1
150°	194.6	194.6	192.9	189.8	185.6	180.3	174.4	167.9	161.5	154.6	148.1
152.5°	187.8	187.8	186.8	183.9	180.7	176.3	171.0	165.5	159.7	153.4	147.4
155°	179.4	179.2	178.6	176.3	173.8	170.5	166.3	161.8	157.0	151.5	146.7
157.5°	171.7	171.8	171.3	169.7	167.5	164.9	161.6	157.9	154.0	149.7	145.8
160°	166.8	167.2	167.2	165.4	163.5	161.5	158.8	155.7	152.0	148.4	145.3
162.5°	162.4	162.6	162.6	161.2	159.9	158.2	155.6	153.0	150.0	147.0	144.4
165°	156.5	156.5	156.8	155.7	154.6	153.1	151.1	149.5	147.3	145.0	143.1
167.5°	150.9	150.9	151.1	150.4	149.9	148.9	147.7	146.5	144.7	143.0	141.7
170°	147.5	147.5	147.8	147.3	146.9	146.4	145.3	144.4	143.1	141.6	140.9
172.5°	144.4	144.7	145.1	144.6	144.5	144.2	143.3	142.7	141.5	140.5	140.1
175°	140.9	141.1	141.4	141.1	141.1	141.1	140.5	140.2	139.7	139.1	139.1
177.5°	138.7	138.7	139.2	138.9	139.2	139.2	138.9	138.7	138.6	138.3	138.6
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1000.4	999.3	994.7	989.4	982.5	977.8	974.1	972.2	966.2	958.9	953.9
5°	1062.2	1049.7	1036.5	1020.3	1005.4	990.0	980.5	969.2	955.6	940.2	929.5
7.5°	1128.4	1104.0	1077.7	1050.6	1023.7	999.7	978.5	960.3	938.5	916.5	901.1
10°	1179.2	1143.4	1106.5	1068.8	1034.4	1002.0	977.2	952.7	926.5	901.3	882.2
12.5°	1225.3	1178.3	1135.8	1089.4	1045.4	1006.7	970.8	942.1	910.6	883.7	861.9
15°	1283.7	1235.6	1184.1	1113.6	1055.1	1006.2	962.7	924.9	886.8	853.6	832.4
17.5°	1338.2	1265.8	1196.7	1137.9	1061.9	1000.8	947.6	902.5	860.6	825.5	799.4
20°	1360.8	1290.7	1215.6	1140.6	1065.9	997.4	935.6	885.9	842.3	802.6	778.5
22.5°	1374.4	1295.0	1215.9	1135.3	1056.0	984.8	923.8	868.9	821.8	783.9	754.2
25°	1390.2	1295.7	1208.6	1128.9	1048.1	970.9	898.3	840.3	789.3	749.0	717.5
27.5°	1400.7	1289.4	1186.5	1098.0	1016.0	939.1	872.6	811.1	759.3	716.8	682.9
30°	1402.6	1284.4	1169.6	1073.8	990.4	919.9	849.4	790.5	735.8	690.5	659.0
32.5°	1405.3	1272.2	1146.7	1044.9	959.6	889.7	825.9	769.6	713.5	669.0	636.8
35°	1394.4	1265.4	1111.9	995.0	909.5	841.9	784.3	732.5	677.3	634.1	601.3
37.5°	1347.3	1238.4	1075.9	938.7	849.4	786.8	739.8	694.6	644.0	597.5	566.6
40°	1299.8	1211.9	1048.1	904.6	811.3	746.9	704.6	667.7	618.8	575.3	542.1
42.5°	1229.2	1175.8	1021.5	868.7	768.1	706.2	670.5	635.9	592.9	548.7	517.5
45°	1099.5	1106.5	967.2	811.7	708.4	646.2	612.6	588.5	550.4	513.9	482.0
47.5°	936.9	1002.8	903.4	750.8	645.4	587.0	557.7	536.7	511.0	475.2	446.0
50°	830.8	924.9	852.3	710.0	605.9	547.9	518.9	501.8	479.4	451.2	423.4
52.5°	732.8	834.0	790.6	664.6	563.2	510.1	481.7	467.7	449.9	423.3	398.2
55°	597.6	700.1	690.1	596.0	498.9	451.2	429.7	413.9	401.9	382.0	362.1
57.5°	483.5	580.6	585.7	519.7	442.4	395.2	376.7	364.8	357.0	341.9	323.5
60°	411.5	500.6	518.0	468.3	401.9	360.4	342.1	332.6	326.4	314.4	300.3
62.5°	351.7	427.6	447.3	411.5	363.1	324.2	310.0	300.8	296.5	286.1	273.7
65°	269.2	332.2	351.3	331.4	306.1	275.0	263.4	255.5	251.8	246.0	236.8
67.5°	202.4	248.3	269.3	255.2	246.1	226.5	219.0	214.8	211.5	207.6	199.9
70°	162.6	196.6	218.2	214.4	207.0	196.6	191.2	188.3	185.0	181.6	175.0
72.5°	130.7	154.2	174.4	176.3	170.2	168.0	163.3	162.1	160.1	156.1	152.5
75°	86.7	102.8	116.9	122.3	124.8	126.9	124.8	124.5	124.0	120.7	118.6
77.5°	56.8	65.5	74.4	83.6	87.5	90.3	91.0	92.5	91.4	89.7	88.6
80°	43.6	45.6	51.8	59.7	65.9	68.4	70.1	70.9	70.5	70.1	68.4
82.5°	31.6	33.4	36.3	41.8	47.1	51.2	52.2	52.0	52.9	53.2	51.8
85°	17.0	17.4	18.2	19.1	21.9	26.5	27.8	28.6	29.5	29.5	26.9
87.5°	6.3	5.9	6.3	6.3	7.1	7.3	9.2	10.7	11.2	10.0	10.1
90°	5.3	4.5	3.6	3.1	2.5	1.7	1.1	0.6	1.1	1.7	2.5
92.5°	35.6	23.5	16.2	12.0	9.7	7.5	5.1	3.5	5.1	7.5	9.7
95°	101.9	60.2	36.4	25.5	18.2	13.5	10.4	9.5	10.4	13.5	18.2
97.5°	111.8	64.8	42.1	30.3	23.1	18.9	16.5	16.2	16.5	18.9	23.1
100°	105.5	64.1	44.5	33.6	26.9	23.0	21.0	20.8	21.0	23.0	26.9
102.5°	100.1	65.0	47.5	37.4	31.4	27.6	25.9	25.4	25.9	27.6	31.4
105°	96.3	67.5	52.4	43.6	38.3	35.0	33.4	32.5	33.4	35.0	38.3
107.5°	96.0	72.1	58.8	50.7	45.7	42.5	40.8	40.0	40.8	42.5	45.7
110°	97.1	75.9	63.3	55.5	50.7	47.6	46.2	45.3	46.2	47.6	50.7





TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	99.4	79.7	68.0	60.4	55.6	52.5	51.1	50.3	51.1	52.5	55.6
115°	103.0	86.0	75.3	67.7	63.0	60.2	58.5	57.4	58.5	60.2	63.0
117.5°	107.8	92.6	82.1	75.1	69.8	67.2	65.8	64.5	65.8	67.2	69.8
120°	111.4	96.9	86.7	79.8	74.5	71.7	70.3	69.4	70.3	71.7	74.5
122.5°	114.8	101.3	91.5	84.1	79.0	75.9	74.5	73.7	74.5	75.9	79.0
125°	120.1	107.8	98.0	90.4	85.1	82.0	80.3	79.8	80.3	82.0	85.1
127.5°	124.5	113.4	103.9	96.3	90.5	87.4	85.2	84.4	85.2	87.4	90.5
130°	127.4	116.8	107.5	100.0	94.0	90.7	88.2	87.4	88.2	90.7	94.0
132.5°	130.1	119.6	110.7	103.3	97.4	93.4	90.6	89.6	90.6	93.4	97.4
135°	133.6	124.0	115.3	107.8	101.9	97.7	94.6	93.5	94.6	97.7	101.9
137.5°	136.1	127.1	118.7	111.7	105.8	101.4	98.4	97.2	98.4	101.4	105.8
140°	137.4	129.0	121.0	113.9	108.4	103.9	101.1	99.7	101.1	103.9	108.4
142.5°	138.8	130.6	122.7	116.2	110.6	106.5	103.5	102.3	103.5	106.5	110.6
145°	140.2	132.7	125.4	119.0	114.2	110.0	107.5	106.6	107.5	110.0	114.2
147.5°	141.2	134.4	127.7	122.2	117.6	114.0	111.5	111.1	111.5	114.0	117.6
150°	141.4	135.5	129.0	124.0	120.1	116.5	114.2	113.9	114.2	116.5	120.1
152.5°	141.8	136.2	130.6	125.8	122.3	119.1	116.9	116.8	116.9	119.1	122.3
155°	142.0	137.4	132.7	128.8	125.7	122.9	121.2	121.2	121.2	122.9	125.7
157.5°	142.2	138.2	134.4	131.3	128.7	126.3	124.9	124.7	124.9	126.3	128.7
160°	142.2	138.9	135.5	132.7	130.7	128.5	127.4	127.4	127.4	128.5	130.7
162.5°	142.0	139.1	136.2	133.8	132.1	130.3	129.4	129.4	129.4	130.3	132.1
165°	141.4	139.4	137.2	135.2	134.1	132.7	132.1	132.4	132.1	132.7	134.1
167.5°	140.9	139.3	137.8	136.5	135.7	134.7	134.4	134.7	134.4	134.7	135.7
170°	140.2	139.1	137.8	137.2	136.6	135.8	135.5	136.0	135.5	135.8	136.6
172.5°	140.1	139.1	137.9	137.6	137.3	136.7	136.6	137.0	136.6	136.7	137.3
175°	139.4	138.9	138.3	138.0	138.0	137.4	137.8	138.0	137.8	137.4	138.0
177.5°	138.9	138.6	138.3	138.3	138.3	138.1	138.3	138.6	138.3	138.1	138.3
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	952.3	947.9	945.0	938.3	934.0	929.4	924.7	927.7	927.4	927.0	927.0
5°	920.4	910.8	902.1	890.9	883.8	875.1	868.5	867.7	869.3	863.5	860.2
7.5°	888.7	875.6	863.2	850.9	837.8	827.4	820.8	817.7	813.5	809.9	806.2
10°	866.4	851.0	839.0	823.7	809.6	797.2	789.3	783.9	780.9	778.1	772.7
12.5°	843.5	828.5	813.2	795.8	782.4	767.9	762.1	756.0	750.4	747.2	739.8
15°	810.0	790.5	774.4	756.1	741.2	727.1	718.7	706.7	705.0	700.9	693.5
17.5°	776.4	755.3	732.9	719.5	702.6	687.9	675.3	671.2	659.3	654.9	648.4
20°	749.9	730.4	713.4	695.5	671.1	657.4	647.5	642.1	632.5	626.7	622.5
22.5°	727.0	707.2	687.5	666.7	646.5	631.1	623.8	615.4	610.3	602.1	597.6
25°	694.3	672.7	649.1	626.7	612.2	600.6	588.9	581.5	574.0	570.3	562.0
27.5°	656.3	633.7	611.6	594.7	576.9	565.4	554.8	548.2	539.2	533.0	528.4
30°	635.4	608.9	589.8	574.4	551.6	540.8	533.0	524.7	518.0	511.4	506.8
32.5°	611.2	586.9	568.9	549.9	532.3	520.6	510.4	503.1	497.4	491.2	486.6
35°	573.1	552.9	534.2	515.1	502.2	490.2	478.2	472.0	466.6	460.8	456.6
37.5°	538.8	519.8	502.1	484.0	468.1	458.3	448.6	443.9	436.6	432.7	428.4
40°	517.6	498.9	479.8	462.5	445.8	438.4	429.7	422.6	416.0	413.1	408.5
42.5°	494.4	475.7	459.6	440.8	427.3	417.2	409.1	401.4	396.4	392.2	389.6
45°	459.9	443.4	427.6	408.9	396.1	387.4	378.3	371.2	366.6	363.8	359.2
47.5°	426.5	410.0	394.0	377.6	365.2	355.3	346.2	341.3	335.2	331.6	328.6
50°	402.3	387.4	370.3	355.5	343.0	333.0	325.6	319.3	313.9	309.4	307.4
52.5°	380.1	364.2	349.4	335.6	322.4	311.2	304.4	297.8	293.7	288.5	286.1
55°	343.4	328.0	315.6	301.9	289.1	279.6	271.2	265.5	261.3	255.5	252.2
57.5°	309.0	295.2	280.4	268.5	255.2	247.2	240.3	232.4	227.4	222.8	219.6
60°	285.7	270.0	257.1	246.0	234.3	223.9	217.8	211.5	206.1	201.5	198.7
62.5°	261.6	247.8	235.6	223.4	212.8	203.7	196.5	191.3	186.6	183.6	180.8
65°	224.3	213.6	201.1	191.2	181.3	174.6	168.8	164.2	160.9	158.8	156.4
67.5°	190.2	179.7	168.9	159.1	152.5	147.4	143.6	139.7	138.0	135.4	133.7
70°	167.9	157.2	147.7	140.2	133.6	129.8	127.3	124.5	122.8	119.5	117.8
72.5°	143.8	135.9	129.0	122.9	117.6	114.2	111.1	107.5	104.9	101.2	99.6
75°	113.2	106.2	100.8	96.6	93.3	88.7	84.2	80.5	79.2	78.0	77.6
77.5°	83.9	79.4	75.5	72.0	67.9	64.6	63.5	62.7	62.4	61.8	61.8
80°	65.9	61.8	58.9	54.7	52.3	52.3	52.3	51.4	51.8	51.8	51.8
82.5°	49.0	45.2	43.6	42.1	41.7	42.0	42.0	42.1	41.9	42.5	42.2
85°	25.3	25.7	26.5	26.1	26.5	26.5	27.4	26.9	27.4	26.5	27.4
87.5°	9.9	11.0	11.5	12.0	12.5	12.4	12.6	12.7	13.1	13.2	13.2
90°	3.1	3.6	4.5	5.3	6.2	7.0	6.7	7.0	7.3	7.5	8.1
92.5°	12.0	16.2	23.5	35.6	47.4	43.0	32.5	23.6	18.7	16.5	15.1
95°	25.5	36.4	60.2	101.9	147.8	166.0	134.7	100.8	68.3	53.5	43.4
97.5°	30.3	42.1	64.8	111.8	188.4	257.3	275.2	251.2	201.2	165.1	131.7
100°	33.6	44.5	64.1	105.5	179.2	265.1	320.3	330.0	307.4	274.6	234.9
102.5°	37.4	47.5	65.0	100.1	165.7	250.6	322.5	356.2	355.5	336.4	311.2
105°	43.6	52.4	67.5	96.3	149.2	225.1	305.4	363.9	391.9	397.2	390.0
107.5°	50.7	58.8	72.1	96.0	138.7	202.6	275.5	341.8	387.3	411.9	421.8
110°	55.5	63.3	75.9	97.1	134.7	189.8	256.7	320.8	372.3	407.6	427.2



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	60.4	68.0	79.7	99.4	132.4	181.3	240.3	300.0	352.6	392.1	417.3
115°	67.7	75.3	86.0	103.0	131.6	172.1	220.6	272.4	321.1	362.3	392.8
117.5°	75.1	82.1	92.6	107.8	132.1	166.8	208.7	252.4	294.5	331.4	362.3
120°	79.8	86.7	96.9	111.4	133.0	164.3	202.4	241.9	279.6	313.2	341.5
122.5°	84.1	91.5	101.3	114.8	134.5	162.8	197.3	233.6	267.8	298.9	325.2
125°	90.4	98.0	107.8	120.1	136.9	160.7	190.7	222.5	253.1	280.0	302.4
127.5°	96.3	103.9	113.4	124.5	139.6	159.7	184.8	212.9	240.1	264.4	284.8
130°	100.0	107.5	116.8	127.4	141.4	159.0	181.6	206.8	232.1	254.8	273.8
132.5°	103.3	110.7	119.6	130.1	142.8	158.8	178.8	201.3	224.4	245.6	263.7
135°	107.8	115.3	124.0	133.6	144.7	158.4	175.0	193.7	213.6	231.8	247.7
137.5°	111.7	118.7	127.1	136.1	146.1	157.8	171.7	186.8	203.1	218.8	232.7
140°	113.9	121.0	129.0	137.4	146.9	157.6	169.6	182.8	197.1	210.5	222.5
142.5°	116.2	122.7	130.6	138.8	147.7	157.2	167.9	179.0	191.2	202.9	213.3
145°	119.0	125.4	132.7	140.2	148.1	156.5	165.4	174.4	183.6	192.6	200.7
147.5°	122.2	127.7	134.4	141.2	148.1	155.4	163.1	170.6	178.0	185.2	191.0
150°	124.0	129.0	135.5	141.4	148.1	154.6	161.5	167.9	174.4	180.3	185.6
152.5°	125.8	130.6	136.2	141.8	147.4	153.4	159.7	165.5	171.0	176.3	180.7
155°	128.8	132.7	137.4	142.0	146.7	151.5	157.0	161.8	166.3	170.5	173.8
157.5°	131.3	134.4	138.2	142.2	145.8	149.7	154.0	157.9	161.6	164.9	167.5
160°	132.7	135.5	138.9	142.2	145.3	148.4	152.0	155.7	158.8	161.5	163.5
162.5°	133.8	136.2	139.1	142.0	144.4	147.0	150.0	153.0	155.6	158.2	159.9
165°	135.2	137.2	139.4	141.4	143.1	145.0	147.3	149.5	151.1	153.1	154.6
167.5°	136.5	137.8	139.3	140.9	141.7	143.0	144.7	146.5	147.7	148.9	149.9
170°	137.2	137.8	139.1	140.2	140.9	141.6	143.1	144.4	145.3	146.4	146.9
172.5°	137.6	137.9	139.1	140.1	140.1	140.5	141.5	142.7	143.3	144.2	144.5
175°	138.0	138.3	138.9	139.4	139.1	139.1	139.7	140.2	140.5	141.1	141.1
177.5°	138.3	138.3	138.6	138.9	138.6	138.3	138.6	138.7	138.9	139.2	139.2
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	923.1	922.7	923.1	921.7	923.1	922.7	923.1	927.0	927.0	927.4	927.7
5°	859.0	858.5	857.3	853.6	857.3	858.5	859.0	860.2	863.5	869.3	867.7
7.5°	803.0	802.4	798.8	798.8	798.8	802.4	803.0	806.2	809.9	813.5	817.7
10°	769.8	770.2	765.2	762.3	765.2	770.2	769.8	772.7	778.1	780.9	783.9
12.5°	737.6	735.7	731.7	728.5	731.7	735.7	737.6	739.8	747.2	750.4	756.0
15°	695.1	690.9	681.0	681.8	681.0	690.9	695.1	693.5	700.9	705.0	706.7
17.5°	645.1	642.1	641.8	636.0	641.8	642.1	645.1	648.4	654.9	659.3	671.2
20°	615.9	613.9	614.7	608.9	614.7	613.9	615.9	622.5	626.7	632.5	642.1
22.5°	593.0	591.0	587.5	585.7	587.5	591.0	593.0	597.6	602.1	610.3	615.4
25°	559.5	556.2	552.9	554.9	552.9	556.2	559.5	562.0	570.3	574.0	581.5
27.5°	526.0	523.5	520.1	519.8	520.1	523.5	526.0	528.4	533.0	539.2	548.2
30°	504.8	502.2	500.6	498.5	500.6	502.2	504.8	506.8	511.4	518.0	524.7
32.5°	483.2	482.7	479.7	479.3	479.7	482.7	483.2	486.6	491.2	497.4	503.1
35°	455.0	452.5	451.6	452.1	451.6	452.5	455.0	456.6	460.8	466.6	472.0
37.5°	428.2	424.8	423.3	421.9	423.3	424.8	428.2	428.4	432.7	436.6	443.9
40°	408.9	405.6	404.8	403.9	404.8	405.6	408.9	408.5	413.1	416.0	422.6
42.5°	387.4	386.0	385.6	384.0	385.6	386.0	387.4	389.6	392.2	396.4	401.4
45°	357.9	357.5	355.1	355.8	355.1	357.5	357.9	359.2	363.8	366.6	371.2
47.5°	326.9	325.1	323.4	324.5	323.4	325.1	326.9	328.6	331.6	335.2	341.3
50°	305.7	304.8	301.1	301.9	301.1	304.8	305.7	307.4	309.4	313.9	319.3
52.5°	284.5	281.3	279.9	279.4	279.9	281.3	284.5	286.1	288.5	293.7	297.8
55°	249.3	245.5	243.8	243.0	243.8	245.5	249.3	252.2	255.5	261.3	265.5
57.5°	214.8	213.7	212.5	213.3	212.5	213.7	214.8	219.6	222.8	227.4	232.4
60°	194.5	194.5	194.5	194.1	194.5	194.5	194.5	198.7	201.5	206.1	211.5
62.5°	179.0	177.9	177.6	178.2	177.6	177.9	179.0	180.8	183.6	186.6	191.3
65°	155.1	154.7	153.0	152.7	153.0	154.7	155.1	156.4	158.8	160.9	164.2
67.5°	132.6	131.1	130.6	130.1	130.6	131.1	132.6	133.7	135.4	138.0	139.7
70°	115.7	114.9	112.4	112.8	112.4	114.9	115.7	117.8	119.5	122.8	124.5
72.5°	97.4	96.6	96.2	95.5	96.2	96.6	97.4	99.6	101.2	104.9	107.5
75°	77.2	76.8	76.3	78.0	76.3	76.8	77.2	77.6	78.0	79.2	80.5
77.5°	61.8	61.8	62.0	61.4	62.0	61.8	61.8	61.8	61.8	62.4	62.7
80°	51.8	51.8	51.4	51.4	51.4	51.8	51.8	51.8	51.8	51.8	51.4
82.5°	41.6	41.9	42.1	41.5	42.1	41.9	41.6	42.2	42.5	41.9	42.1
85°	27.4	26.9	27.8	27.4	27.8	26.9	27.4	27.4	26.5	27.4	26.9
87.5°	13.9	13.2	13.3	13.5	13.3	13.2	13.9	13.2	13.2	13.1	12.7
90°	7.8	8.1	8.4	8.1	8.4	8.1	7.8	8.1	7.5	7.3	7.0
92.5°	14.6	13.7	14.0	13.5	14.0	13.7	14.6	15.1	16.5	18.7	23.6
95°	38.1	35.6	33.6	32.5	33.6	35.6	38.1	43.4	53.5	68.3	100.8
97.5°	111.0	98.4	90.8	88.4	90.8	98.4	111.0	131.7	165.1	201.2	251.2
100°	206.6	186.2	175.2	175.5	175.2	186.2	206.6	234.9	274.6	307.4	330.0
102.5°	289.2	273.1	264.0	257.5	264.0	273.1	289.2	311.2	336.4	355.5	356.2
105°	377.1	366.5	357.5	356.1	357.5	366.5	377.1	390.0	397.2	391.9	363.9
107.5°	422.1	418.4	415.4	412.9	415.4	418.4	422.1	421.8	411.9	387.3	341.8
110°	435.1	437.3	436.7	436.2	436.7	437.3	435.1	427.2	407.6	372.3	320.8



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	431.7	438.6	440.8	440.8	440.8	438.6	431.7	417.3	392.1	352.6	300.0
115°	413.8	426.0	431.7	433.1	431.7	426.0	413.8	392.8	362.3	321.1	272.4
117.5°	384.3	398.4	406.4	408.3	406.4	398.4	384.3	362.3	331.4	294.5	252.4
120°	363.6	379.3	386.0	387.7	386.0	379.3	363.6	341.5	313.2	279.6	241.9
122.5°	344.8	358.9	366.3	368.4	366.3	358.9	344.8	325.2	298.9	267.8	233.6
125°	320.3	332.6	339.6	341.5	339.6	332.6	320.3	302.4	280.0	253.1	222.5
127.5°	300.7	311.2	317.6	319.3	317.6	311.2	300.7	284.8	264.4	240.1	212.9
130°	288.6	298.7	304.6	306.8	304.6	298.7	288.6	273.8	254.8	232.1	206.8
132.5°	277.7	287.7	292.9	294.5	292.9	287.7	277.7	263.7	245.6	224.4	201.3
135°	261.5	269.9	274.9	276.9	274.9	269.9	261.5	247.7	231.8	213.6	193.7
137.5°	244.2	252.7	256.9	258.3	256.9	252.7	244.2	232.7	218.8	203.1	186.8
140°	233.2	241.1	245.5	245.3	245.5	241.1	233.2	222.5	210.5	197.1	182.8
142.5°	222.4	229.4	233.4	233.1	233.4	229.4	222.4	213.3	202.9	191.2	179.0
145°	207.7	213.6	215.9	216.4	215.9	213.6	207.7	200.7	192.6	183.6	174.4
147.5°	196.3	200.3	202.4	202.6	202.4	200.3	196.3	191.0	185.2	178.0	170.6
150°	189.8	192.9	194.6	194.6	194.6	192.9	189.8	185.6	180.3	174.4	167.9
152.5°	183.9	186.8	187.8	187.8	187.8	186.8	183.9	180.7	176.3	171.0	165.5
155°	176.3	178.6	179.2	179.4	179.2	178.6	176.3	173.8	170.5	166.3	161.8
157.5°	169.7	171.3	171.8	171.7	171.8	171.3	169.7	167.5	164.9	161.6	157.9
160°	165.4	167.2	167.2	166.8	167.2	167.2	165.4	163.5	161.5	158.8	155.7
162.5°	161.2	162.6	162.6	162.4	162.6	162.6	161.2	159.9	158.2	155.6	153.0
165°	155.7	156.8	156.5	156.5	156.5	156.8	155.7	154.6	153.1	151.1	149.5
167.5°	150.4	151.1	150.9	150.9	150.9	151.1	150.4	149.9	148.9	147.7	146.5
170°	147.3	147.8	147.5	147.5	147.5	147.8	147.3	146.9	146.4	145.3	144.4
172.5°	144.6	145.1	144.7	144.4	144.7	145.1	144.6	144.5	144.2	143.3	142.7
175°	141.1	141.4	141.1	140.9	141.1	141.4	141.1	141.1	141.1	140.5	140.2
177.5°	138.9	139.2	138.7	138.7	138.7	139.2	138.9	139.2	139.2	138.9	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	924.7	929.4	934.0	938.3	945.0	947.9	952.3	953.9	958.9	966.2	972.2
5°	868.5	875.1	883.8	890.9	902.1	910.8	920.4	929.5	940.2	955.6	969.2
7.5°	820.8	827.4	837.8	850.9	863.2	875.6	888.7	901.1	916.5	938.5	960.3
10°	789.3	797.2	809.6	823.7	839.0	851.0	866.4	882.2	901.3	926.5	952.7
12.5°	762.1	767.9	782.4	795.8	813.2	828.5	843.5	861.9	883.7	910.6	942.1
15°	718.7	727.1	741.2	756.1	774.4	790.5	810.0	832.4	853.6	886.8	924.9
17.5°	675.3	687.9	702.6	719.5	732.9	755.3	776.4	799.4	825.5	860.6	902.5
20°	647.5	657.4	671.1	695.5	713.4	730.4	749.9	778.5	802.6	842.3	885.9
22.5°	623.8	631.1	646.5	666.7	687.5	707.2	727.0	754.2	783.9	821.8	868.9
25°	588.9	600.6	612.2	626.7	649.1	672.7	694.3	717.5	749.0	789.3	840.3
27.5°	554.8	565.4	576.9	594.7	611.6	633.7	656.3	682.9	716.8	759.3	811.1
30°	533.0	540.8	551.6	574.4	589.8	608.9	635.4	659.0	690.5	735.8	790.5
32.5°	510.4	520.6	532.3	549.9	568.9	586.9	611.2	636.8	669.0	713.5	769.6
35°	478.2	490.2	502.2	515.1	534.2	552.9	573.1	601.3	634.1	677.3	732.5
37.5°	448.6	458.3	468.1	484.0	502.1	519.8	538.8	566.6	597.5	644.0	694.6
40°	429.7	438.4	445.8	462.5	479.8	498.9	517.6	542.1	575.3	618.8	667.7
42.5°	409.1	417.2	427.3	440.8	459.6	475.7	494.4	517.5	548.7	592.9	635.9
45°	378.3	387.4	396.1	408.9	427.6	443.4	459.9	482.0	513.9	550.4	588.5
47.5°	346.2	355.3	365.2	377.6	394.0	410.0	426.5	446.0	475.2	511.0	536.7
50°	325.6	333.0	343.0	355.5	370.3	387.4	402.3	423.4	451.2	479.4	501.8
52.5°	304.4	311.2	322.4	335.6	349.4	364.2	380.1	398.2	423.3	449.9	467.7
55°	271.2	279.6	289.1	301.9	315.6	328.0	343.4	362.1	382.0	401.9	413.9
57.5°	240.3	247.2	255.2	268.5	280.4	295.2	309.0	323.5	341.9	357.0	364.8
60°	217.8	223.9	234.3	246.0	257.1	270.0	285.7	300.3	314.4	326.4	332.6
62.5°	196.5	203.7	212.8	223.4	235.6	247.8	261.6	273.7	286.1	296.5	300.8
65°	168.8	174.6	181.3	191.2	201.1	213.6	224.3	236.8	246.0	251.8	255.5
67.5°	143.6	147.4	152.5	159.1	168.9	179.7	190.2	199.9	207.6	211.5	214.8
70°	127.3	129.8	133.6	140.2	147.7	157.2	167.9	175.0	181.6	185.0	188.3
72.5°	111.1	114.2	117.6	122.9	129.0	135.9	143.8	152.5	156.1	160.1	162.1
75°	84.2	88.7	93.3	96.6	100.8	106.2	113.2	118.6	120.7	124.0	124.5
77.5°	63.5	64.6	67.9	72.0	75.5	79.4	83.9	88.6	89.7	91.4	92.5
80°	52.3	52.3	52.3	54.7	58.9	61.8	65.9	68.4	70.1	70.5	70.9
82.5°	42.0	42.0	41.7	42.1	43.6	45.2	49.0	51.8	53.2	52.9	52.0
85°	27.4	26.5	26.5	26.1	26.5	25.7	25.3	26.9	29.5	29.5	28.6
87.5°	12.6	12.4	12.5	12.0	11.5	11.0	9.9	10.1	10.0	11.2	10.7
90°	6.7	7.0	6.2	5.3	4.5	3.6	3.1	2.5	1.7	1.1	0.6
92.5°	32.5	43.0	47.4	35.6	23.5	16.2	12.0	9.7	7.5	5.1	3.5
95°	134.7	166.0	147.8	101.9	60.2	36.4	25.5	18.2	13.5	10.4	9.5
97.5°	275.2	257.3	188.4	111.8	64.8	42.1	30.3	23.1	18.9	16.5	16.2
100°	320.3	265.1	179.2	105.5	64.1	44.5	33.6	26.9	23.0	21.0	20.8
102.5°	322.5	250.6	165.7	100.1	65.0	47.5	37.4	31.4	27.6	25.9	25.4
105°	305.4	225.1	149.2	96.3	67.5	52.4	43.6	38.3	35.0	33.4	32.5
107.5°	275.5	202.6	138.7	96.0	72.1	58.8	50.7	45.7	42.5	40.8	40.0
110°	256.7	189.8	134.7	97.1	75.9	63.3	55.5	50.7	47.6	46.2	45.3



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	240.3	181.3	132.4	99.4	79.7	68.0	60.4	55.6	52.5	51.1	50.3
115°	220.6	172.1	131.6	103.0	86.0	75.3	67.7	63.0	60.2	58.5	57.4
117.5°	208.7	166.8	132.1	107.8	92.6	82.1	75.1	69.8	67.2	65.8	64.5
120°	202.4	164.3	133.0	111.4	96.9	86.7	79.8	74.5	71.7	70.3	69.4
122.5°	197.3	162.8	134.5	114.8	101.3	91.5	84.1	79.0	75.9	74.5	73.7
125°	190.7	160.7	136.9	120.1	107.8	98.0	90.4	85.1	82.0	80.3	79.8
127.5°	184.8	159.7	139.6	124.5	113.4	103.9	96.3	90.5	87.4	85.2	84.4
130°	181.6	159.0	141.4	127.4	116.8	107.5	100.0	94.0	90.7	88.2	87.4
132.5°	178.8	158.8	142.8	130.1	119.6	110.7	103.3	97.4	93.4	90.6	89.6
135°	175.0	158.4	144.7	133.6	124.0	115.3	107.8	101.9	97.7	94.6	93.5
137.5°	171.7	157.8	146.1	136.1	127.1	118.7	111.7	105.8	101.4	98.4	97.2
140°	169.6	157.6	146.9	137.4	129.0	121.0	113.9	108.4	103.9	101.1	99.7
142.5°	167.9	157.2	147.7	138.8	130.6	122.7	116.2	110.6	106.5	103.5	102.3
145°	165.4	156.5	148.1	140.2	132.7	125.4	119.0	114.2	110.0	107.5	106.6
147.5°	163.1	155.4	148.1	141.2	134.4	127.7	122.2	117.6	114.0	111.5	111.1
150°	161.5	154.6	148.1	141.4	135.5	129.0	124.0	120.1	116.5	114.2	113.9
152.5°	159.7	153.4	147.4	141.8	136.2	130.6	125.8	122.3	119.1	116.9	116.8
155°	157.0	151.5	146.7	142.0	137.4	132.7	128.8	125.7	122.9	121.2	121.2
157.5°	154.0	149.7	145.8	142.2	138.2	134.4	131.3	128.7	126.3	124.9	124.7
160°	152.0	148.4	145.3	142.2	138.9	135.5	132.7	130.7	128.5	127.4	127.4
162.5°	150.0	147.0	144.4	142.0	139.1	136.2	133.8	132.1	130.3	129.4	129.4
165°	147.3	145.0	143.1	141.4	139.4	137.2	135.2	134.1	132.7	132.1	132.4
167.5°	144.7	143.0	141.7	140.9	139.3	137.8	136.5	135.7	134.7	134.4	134.7
170°	143.1	141.6	140.9	140.2	139.1	137.8	137.2	136.6	135.8	135.5	136.0
172.5°	141.5	140.5	140.1	140.1	139.1	137.9	137.6	137.3	136.7	136.6	137.0
175°	139.7	139.1	139.1	139.4	138.9	138.3	138.0	138.0	137.4	137.8	138.0
177.5°	138.6	138.3	138.6	138.9	138.6	138.3	138.3	138.3	138.1	138.3	138.6
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	974.1	977.8	982.5	989.4	994.7	999.3	1000.4	1001.7	1005.0	1010.7	1014.9
5°	980.5	990.0	1005.4	1020.3	1036.5	1049.7	1062.2	1070.9	1079.2	1096.6	1110.7
7.5°	978.5	999.7	1023.7	1050.6	1077.7	1104.0	1128.4	1150.2	1171.9	1197.3	1226.2
10°	977.2	1002.0	1034.4	1068.8	1106.5	1143.4	1179.2	1206.9	1239.3	1268.3	1305.2
12.5°	970.8	1006.7	1045.4	1089.4	1135.8	1178.3	1225.3	1263.7	1300.7	1342.6	1385.5
15°	962.7	1006.2	1055.1	1113.6	1184.1	1235.6	1283.7	1350.4	1396.1	1441.7	1503.0
17.5°	947.6	1000.8	1061.9	1137.9	1196.7	1265.8	1338.2	1391.0	1452.5	1516.7	1572.3
20°	935.6	997.4	1065.9	1140.6	1215.6	1290.7	1360.8	1423.8	1487.3	1561.5	1607.2
22.5°	923.8	984.8	1056.0	1135.3	1215.9	1295.0	1374.4	1448.3	1519.8	1594.7	1653.0
25°	898.3	970.9	1048.1	1128.9	1208.6	1295.7	1390.2	1472.7	1561.1	1638.2	1693.4
27.5°	872.6	939.1	1016.0	1098.0	1186.5	1289.4	1400.7	1494.5	1583.0	1638.2	1655.6
30°	849.4	919.9	990.4	1073.8	1169.6	1284.4	1402.6	1510.1	1582.7	1606.7	1588.9
32.5°	825.9	889.7	959.6	1044.9	1146.7	1272.2	1405.3	1500.8	1544.5	1526.1	1453.5
35°	784.3	841.9	909.5	995.0	1111.9	1265.4	1394.4	1459.0	1448.3	1344.6	1207.8
37.5°	739.8	786.8	849.4	938.7	1075.9	1238.4	1347.3	1356.8	1263.5	1104.3	946.2
40°	704.6	746.9	811.3	904.6	1048.1	1211.9	1299.8	1261.2	1116.5	939.4	807.6
42.5°	670.5	706.2	768.1	868.7	1021.5	1175.8	1229.2	1145.1	978.1	810.6	690.7
45°	612.6	646.2	708.4	811.7	967.2	1106.5	1099.5	953.5	786.4	651.6	552.0
47.5°	557.7	587.0	645.4	750.8	903.4	1002.8	936.9	781.6	639.8	531.6	460.7
50°	518.9	547.9	605.9	710.0	852.3	924.9	830.8	681.0	551.2	461.6	405.2
52.5°	481.7	510.1	563.2	664.6	790.6	834.0	732.8	594.1	485.8	408.5	360.0
55°	429.7	451.2	498.9	596.0	690.1	700.1	597.6	481.5	392.4	338.4	305.2
57.5°	376.7	395.2	442.4	519.7	585.7	580.6	483.5	382.9	322.9	282.9	258.8
60°	342.1	360.4	401.9	468.3	518.0	500.6	411.5	330.6	279.1	249.7	230.6
62.5°	310.0	324.2	363.1	411.5	447.3	427.6	351.7	284.8	244.0	219.1	204.1
65°	263.4	275.0	306.1	331.4	351.3	332.2	269.2	222.7	193.3	175.9	165.5
67.5°	219.0	226.5	246.1	255.2	269.3	248.3	202.4	171.3	154.6	139.8	132.6
70°	191.2	196.6	207.0	214.4	218.2	196.6	162.6	139.7	125.6	115.3	110.7
72.5°	163.3	168.0	170.2	176.3	174.4	154.2	130.7	112.6	102.4	95.4	89.5
75°	124.8	126.9	124.8	122.3	116.9	102.8	86.7	77.6	70.1	66.8	64.7
77.5°	91.0	90.3	87.5	83.6	74.4	65.5	56.8	53.8	50.5	48.8	48.0
80°	70.1	68.4	65.9	59.7	51.8	45.6	43.6	41.5	40.2	38.2	37.7
82.5°	52.2	51.2	47.1	41.8	36.3	33.4	31.6	30.9	29.6	28.5	28.4
85°	27.8	26.5	21.9	19.1	18.2	17.4	17.0	17.0	15.4	14.9	14.9
87.5°	9.2	7.3	7.1	6.3	6.3	5.9	6.3	5.9	5.7	6.0	5.4
90°	1.1	1.7	2.5	3.1	3.6	4.5	5.3	6.2	7.0	6.7	7.0
92.5°	5.1	7.5	9.7	12.0	16.2	23.5	35.6	47.4	43.0	32.5	23.6
95°	10.4	13.5	18.2	25.5	36.4	60.2	101.9	147.8	166.0	134.7	100.8
97.5°	16.5	18.9	23.1	30.3	42.1	64.8	111.8	188.4	257.3	275.2	251.2
100°	21.0	23.0	26.9	33.6	44.5	64.1	105.5	179.2	265.1	320.3	330.0
102.5°	25.9	27.6	31.4	37.4	47.5	65.0	100.1	165.7	250.6	322.5	356.2
105°	33.4	35.0	38.3	43.6	52.4	67.5	96.3	149.2	225.1	305.4	363.9
107.5°	40.8	42.5	45.7	50.7	58.8	72.1	96.0	138.7	202.6	275.5	341.8
110°	46.2	47.6	50.7	55.5	63.3	75.9	97.1	134.7	189.8	256.7	320.8





TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	51.1	52.5	55.6	60.4	68.0	79.7	99.4	132.4	181.3	240.3	300.0
115°	58.5	60.2	63.0	67.7	75.3	86.0	103.0	131.6	172.1	220.6	272.4
117.5°	65.8	67.2	69.8	75.1	82.1	92.6	107.8	132.1	166.8	208.7	252.4
120°	70.3	71.7	74.5	79.8	86.7	96.9	111.4	133.0	164.3	202.4	241.9
122.5°	74.5	75.9	79.0	84.1	91.5	101.3	114.8	134.5	162.8	197.3	233.6
125°	80.3	82.0	85.1	90.4	98.0	107.8	120.1	136.9	160.7	190.7	222.5
127.5°	85.2	87.4	90.5	96.3	103.9	113.4	124.5	139.6	159.7	184.8	212.9
130°	88.2	90.7	94.0	100.0	107.5	116.8	127.4	141.4	159.0	181.6	206.8
132.5°	90.6	93.4	97.4	103.3	110.7	119.6	130.1	142.8	158.8	178.8	201.3
135°	94.6	97.7	101.9	107.8	115.3	124.0	133.6	144.7	158.4	175.0	193.7
137.5°	98.4	101.4	105.8	111.7	118.7	127.1	136.1	146.1	157.8	171.7	186.8
140°	101.1	103.9	108.4	113.9	121.0	129.0	137.4	146.9	157.6	169.6	182.8
142.5°	103.5	106.5	110.6	116.2	122.7	130.6	138.8	147.7	157.2	167.9	179.0
145°	107.5	110.0	114.2	119.0	125.4	132.7	140.2	148.1	156.5	165.4	174.4
147.5°	111.5	114.0	117.6	122.2	127.7	134.4	141.2	148.1	155.4	163.1	170.6
150°	114.2	116.5	120.1	124.0	129.0	135.5	141.4	148.1	154.6	161.5	167.9
152.5°	116.9	119.1	122.3	125.8	130.6	136.2	141.8	147.4	153.4	159.7	165.5
155°	121.2	122.9	125.7	128.8	132.7	137.4	142.0	146.7	151.5	157.0	161.8
157.5°	124.9	126.3	128.7	131.3	134.4	138.2	142.2	145.8	149.7	154.0	157.9
160°	127.4	128.5	130.7	132.7	135.5	138.9	142.2	145.3	148.4	152.0	155.7
162.5°	129.4	130.3	132.1	133.8	136.2	139.1	142.0	144.4	147.0	150.0	153.0
165°	132.1	132.7	134.1	135.2	137.2	139.4	141.4	143.1	145.0	147.3	149.5
167.5°	134.4	134.7	135.7	136.5	137.8	139.3	140.9	141.7	143.0	144.7	146.5
170°	135.5	135.8	136.6	137.2	137.8	139.1	140.2	140.9	141.6	143.1	144.4
172.5°	136.6	136.7	137.3	137.6	137.9	139.1	140.1	140.1	140.5	141.5	142.7
175°	137.8	137.4	138.0	138.0	138.3	138.9	139.4	139.1	139.1	139.7	140.2
177.5°	138.3	138.1	138.3	138.3	138.3	138.6	138.9	138.6	138.3	138.6	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3	138.3



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1021.9	1021.9	1023.3	1028.3	1028.9	1033.2	1031.9
5°	1123.2	1131.0	1133.9	1146.4	1153.8	1157.1	1150.5
7.5°	1246.9	1269.2	1279.7	1292.7	1304.2	1307.7	1298.6
10°	1337.1	1360.3	1379.9	1391.9	1403.1	1410.6	1420.1
12.5°	1424.4	1452.9	1471.5	1488.4	1500.0	1509.4	1511.0
15°	1519.2	1562.3	1595.1	1619.1	1631.2	1637.4	1634.9
17.5°	1614.9	1654.9	1678.2	1702.7	1719.4	1720.2	1720.7
20°	1669.0	1707.9	1734.9	1753.1	1771.8	1771.0	1775.1
22.5°	1705.1	1735.8	1756.4	1769.7	1776.2	1773.0	1773.8
25°	1722.0	1731.2	1727.4	1706.3	1700.9	1681.4	1684.7
27.5°	1634.7	1591.7	1547.0	1489.6	1444.3	1408.2	1410.0
30°	1516.3	1440.0	1352.9	1279.9	1214.4	1196.1	1157.1
32.5°	1350.8	1236.3	1134.2	1066.2	1010.0	994.7	960.8
35°	1070.1	958.9	854.0	790.9	766.0	731.2	730.8
37.5°	831.7	733.9	678.3	631.1	606.3	585.2	583.1
40°	699.7	623.4	581.5	547.5	523.0	507.2	503.5
42.5°	607.4	545.7	506.5	485.4	466.6	458.4	452.4
45°	496.1	454.6	427.2	408.1	399.4	393.2	389.8
47.5°	414.9	387.1	368.4	355.8	348.7	342.1	343.9
50°	370.8	348.0	334.3	322.3	316.9	312.3	312.8
52.5°	335.3	314.8	303.7	295.1	288.4	285.1	283.5
55°	284.6	271.6	260.5	254.2	250.5	246.0	244.7
57.5°	242.7	232.7	223.6	216.6	215.6	211.3	211.8
60°	214.8	206.5	199.1	195.4	192.4	188.7	190.0
62.5°	191.9	185.0	178.2	175.1	172.2	169.4	170.1
65°	157.2	150.5	146.4	144.7	143.5	142.3	141.0
67.5°	125.2	121.2	118.6	115.0	112.5	112.1	110.8
70°	105.4	100.0	95.4	90.9	89.6	89.2	89.6
72.5°	84.4	81.0	79.8	77.6	77.3	76.2	77.0
75°	63.5	62.2	61.4	59.7	59.7	59.7	59.7
77.5°	46.8	46.0	45.6	45.2	44.8	44.2	44.1
80°	36.5	36.0	35.3	35.3	34.9	35.3	34.9
82.5°	27.6	27.5	26.6	26.6	26.2	26.0	26.2
85°	14.1	13.7	14.5	13.7	14.1	13.3	14.1
87.5°	5.5	5.5	5.3	5.2	4.9	5.6	4.9
90°	7.3	7.5	8.1	7.8	8.1	8.4	8.1
92.5°	18.7	16.5	15.1	14.6	13.7	14.0	13.5
95°	68.3	53.5	43.4	38.1	35.6	33.6	32.5
97.5°	201.2	165.1	131.7	111.0	98.4	90.8	88.4
100°	307.4	274.6	234.9	206.6	186.2	175.2	175.5
102.5°	355.5	336.4	311.2	289.2	273.1	264.0	257.5
105°	391.9	397.2	390.0	377.1	366.5	357.5	356.1
107.5°	387.3	411.9	421.8	422.1	418.4	415.4	412.9
110°	372.3	407.6	427.2	435.1	437.3	436.7	436.2



TEST NUMBER: P332302-927

CATALOG NUMBER: S123RDIP-S775D365U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	352.6	392.1	417.3	431.7	438.6	440.8	440.8
115°	321.1	362.3	392.8	413.8	426.0	431.7	433.1
117.5°	294.5	331.4	362.3	384.3	398.4	406.4	408.3
120°	279.6	313.2	341.5	363.6	379.3	386.0	387.7
122.5°	267.8	298.9	325.2	344.8	358.9	366.3	368.4
125°	253.1	280.0	302.4	320.3	332.6	339.6	341.5
127.5°	240.1	264.4	284.8	300.7	311.2	317.6	319.3
130°	232.1	254.8	273.8	288.6	298.7	304.6	306.8
132.5°	224.4	245.6	263.7	277.7	287.7	292.9	294.5
135°	213.6	231.8	247.7	261.5	269.9	274.9	276.9
137.5°	203.1	218.8	232.7	244.2	252.7	256.9	258.3
140°	197.1	210.5	222.5	233.2	241.1	245.5	245.3
142.5°	191.2	202.9	213.3	222.4	229.4	233.4	233.1
145°	183.6	192.6	200.7	207.7	213.6	215.9	216.4
147.5°	178.0	185.2	191.0	196.3	200.3	202.4	202.6
150°	174.4	180.3	185.6	189.8	192.9	194.6	194.6
152.5°	171.0	176.3	180.7	183.9	186.8	187.8	187.8
155°	166.3	170.5	173.8	176.3	178.6	179.2	179.4
157.5°	161.6	164.9	167.5	169.7	171.3	171.8	171.7
160°	158.8	161.5	163.5	165.4	167.2	167.2	166.8
162.5°	155.6	158.2	159.9	161.2	162.6	162.6	162.4
165°	151.1	153.1	154.6	155.7	156.8	156.5	156.5
167.5°	147.7	148.9	149.9	150.4	151.1	150.9	150.9
170°	145.3	146.4	146.9	147.3	147.8	147.5	147.5
172.5°	143.3	144.2	144.5	144.6	145.1	144.7	144.4
175°	140.5	141.1	141.1	141.1	141.4	141.1	140.9
177.5°	138.9	139.2	139.2	138.9	139.2	138.7	138.7
180°	138.3	138.3	138.3	138.3	138.3	138.3	138.3

(END OF REPORT)