

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332314-927

Luminaire Tested: **S123RDIP-S775D805U927-4F0-1E-UDD-A4**


Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332314-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D805U927-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4716.5 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	95	91	88	91	88	84	82	75	72	70	63	61	60	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38
3	83	74	67	61	76	69	62	57	59	54	50	50	46	44	41	39	37	33
4	76	66	58	52	70	61	54	49	53	47	43	45	41	38	37	35	32	29
5	70	59	51	45	65	55	48	43	47	42	38	40	36	33	34	31	28	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	28	25	23	20
8	56	44	36	31	51	41	34	29	36	30	26	31	27	23	26	23	20	18
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	19	17
10	49	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10428	10428	10428	10428
5°	12431	10472	9223	10472
10°	15522	10413	8332	10413
15°	18219	10307	7598	10307
20°	20333	10148	6975	10148
25°	20009	9980	6590	9980
30°	14382	9825	6196	9825
35°	9603	9625	5941	9625
40°	7075	9382	5675	9382
45°	5934	8958	5416	8958
50°	5238	8403	5056	8403
55°	4592	7767	4560	7767
60°	4090	7160	4179	7160
65°	3591	6507	3889	6507
70°	2820	5926	3550	5926
75°	2483	5178	3244	5178
80°	2163	4395	3186	4395
85°	1741	3532	3384	3532



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.3	2.0
10°-20°	297.7	6.3
20°-30°	467.6	9.9
30°-40°	487.9	10.3
40°-50°	417.5	8.9
50°-60°	318.2	6.7
60°-70°	204.0	4.3
70°-80°	98.1	2.1
80°-90°	28.3	0.6
90°-100°	170.3	3.6
100°-110°	482.1	10.2
110°-120°	474.3	10.1
120°-130°	378.3	8.0
130°-140°	298.3	6.3
140°-150°	222.6	4.7
150°-160°	155.2	3.3
160°-170°	91.2	1.9
170°-180°	29.7	0.6
0°-30°	860.6	18.2
0°-40°	1348.4	28.6
0°-60°	2084.2	44.2
0°-90°	2414.6	51.2
90°-120°	1126.7	23.9
90°-150°	2025.9	43.0
90°-180°	2302.0	48.8
0°-180°	4716.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1150	969	854	969	1150	119
15°	1635	925	682	925	1635	464
25°	1685	840	555	840	1685	724
35°	731	732	452	732	731	479
45°	390	588	356	588	390	307
55°	245	414	243	414	245	221
65°	141	256	153	256	141	139
75°	60	124	78	124	60	64
85°	14	29	27	29	14	17
90°	18	1	18	1	18	10
95°	72	21	72	21	72	129
105°	788	72	788	72	788	777
115°	958	127	958	127	958	931
125°	756	176	756	176	756	685
135°	612	207	612	207	612	475
145°	479	236	479	236	479	304
155°	397	268	397	268	397	185
165°	346	293	346	293	346	99
175°	312	305	312	305	312	30
180°	306	306	306	306	306	



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1031.9	1033.2	1028.9	1028.3	1023.3	1021.9	1021.9	1014.9	1010.7	1005.0	1001.7
5°	1150.5	1157.1	1153.8	1146.4	1133.9	1131.0	1123.2	1110.7	1096.6	1079.2	1070.9
7.5°	1298.6	1307.7	1304.2	1292.7	1279.7	1269.2	1246.9	1226.2	1197.3	1171.9	1150.2
10°	1420.1	1410.6	1403.1	1391.9	1379.9	1360.3	1337.1	1305.2	1268.3	1239.3	1206.9
12.5°	1511.0	1509.4	1500.0	1488.4	1471.5	1452.9	1424.4	1385.5	1342.6	1300.7	1263.7
15°	1634.9	1637.4	1631.2	1619.1	1595.1	1562.3	1519.2	1503.0	1441.7	1396.1	1350.4
17.5°	1720.7	1720.2	1719.4	1702.7	1678.2	1654.9	1614.9	1572.3	1516.7	1452.5	1391.0
20°	1775.1	1771.0	1771.8	1753.1	1734.9	1707.9	1669.0	1607.2	1561.5	1487.3	1423.8
22.5°	1773.8	1773.0	1776.2	1769.7	1756.4	1735.8	1705.1	1653.0	1594.7	1519.8	1448.3
25°	1684.7	1681.4	1700.9	1706.3	1727.4	1731.2	1722.0	1693.4	1638.2	1561.1	1472.7
27.5°	1410.0	1408.2	1444.3	1489.6	1547.0	1591.7	1634.7	1655.6	1638.2	1583.0	1494.5
30°	1157.1	1196.1	1214.4	1279.9	1352.9	1440.0	1516.3	1588.9	1606.7	1582.7	1510.1
32.5°	960.8	994.7	1010.0	1066.2	1134.2	1236.3	1350.8	1453.5	1526.1	1544.5	1500.8
35°	730.8	731.2	766.0	790.9	854.0	958.9	1070.1	1207.8	1344.6	1448.3	1459.0
37.5°	583.1	585.2	606.3	631.1	678.3	733.9	831.7	946.2	1104.3	1263.5	1356.8
40°	503.5	507.2	523.0	547.5	581.5	623.4	699.7	807.6	939.4	1116.5	1261.2
42.5°	452.4	458.4	466.6	485.4	506.5	545.7	607.4	690.7	810.6	978.1	1145.1
45°	389.8	393.2	399.4	408.1	427.2	454.6	496.1	552.0	651.6	786.4	953.5
47.5°	343.9	342.1	348.7	355.8	368.4	387.1	414.9	460.7	531.6	639.8	781.6
50°	312.8	312.3	316.9	322.3	334.3	348.0	370.8	405.2	461.6	551.2	681.0
52.5°	283.5	285.1	288.4	295.1	303.7	314.8	335.3	360.0	408.5	485.8	594.1
55°	244.7	246.0	250.5	254.2	260.5	271.6	284.6	305.2	338.4	392.4	481.5
57.5°	211.8	211.3	215.6	216.6	223.6	232.7	242.7	258.8	282.9	322.9	382.9
60°	190.0	188.7	192.4	195.4	199.1	206.5	214.8	230.6	249.7	279.1	330.6
62.5°	170.1	169.4	172.2	175.1	178.2	185.0	191.9	204.1	219.1	244.0	284.8
65°	141.0	142.3	143.5	144.7	146.4	150.5	157.2	165.5	175.9	193.3	222.7
67.5°	110.8	112.1	112.5	115.0	118.6	121.2	125.2	132.6	139.8	154.6	171.3
70°	89.6	89.2	89.6	90.9	95.4	100.0	105.4	110.7	115.3	125.6	139.7
72.5°	77.0	76.2	77.3	77.6	79.8	81.0	84.4	89.5	95.4	102.4	112.6
75°	59.7	59.7	59.7	59.7	61.4	62.2	63.5	64.7	66.8	70.1	77.6
77.5°	44.1	44.2	44.8	45.2	45.6	46.0	46.8	48.0	48.8	50.5	53.8
80°	34.9	35.3	34.9	35.3	35.3	36.0	36.5	37.7	38.2	40.2	41.5
82.5°	26.2	26.0	26.2	26.6	26.6	27.5	27.6	28.4	28.5	29.6	30.9
85°	14.1	13.3	14.1	13.7	14.5	13.7	14.1	14.9	14.9	15.4	17.0
87.5°	6.9	7.7	6.9	7.1	7.2	7.3	7.2	7.1	7.6	7.4	7.4
90°	18.0	18.6	18.0	17.3	18.0	16.7	16.1	15.4	14.9	15.4	13.6
92.5°	29.9	31.0	30.3	32.2	33.4	36.5	41.4	52.1	71.9	95.2	104.8
95°	71.9	74.3	78.7	84.2	96.0	118.3	151.1	223.0	297.9	367.3	327.0
97.5°	195.6	200.9	217.6	245.5	291.2	365.3	445.2	555.8	609.0	569.2	416.7
100°	388.3	387.7	411.9	457.1	519.6	607.6	680.0	730.2	708.5	586.5	396.4
102.5°	569.7	583.9	604.1	639.9	688.6	744.3	786.6	788.1	713.5	554.3	366.6
105°	787.8	790.9	810.7	834.2	862.8	878.8	867.0	805.2	675.7	498.0	330.1
107.5°	913.4	919.1	925.8	933.7	933.2	911.2	856.9	756.4	609.6	448.1	306.8
110°	965.0	966.1	967.4	962.4	945.2	901.7	823.7	709.8	567.9	419.9	297.9



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	975.3	975.1	970.4	955.1	923.3	867.6	780.1	663.7	531.8	401.1	292.9
115°	958.1	955.1	942.6	915.4	868.9	801.5	710.3	602.6	488.1	380.9	291.1
117.5°	903.4	899.1	881.3	850.1	801.7	733.2	651.4	558.4	461.7	369.0	292.2
120°	857.8	854.1	839.2	804.5	755.6	693.1	618.7	535.1	447.8	363.5	294.2
122.5°	815.2	810.5	794.1	762.9	719.5	661.3	592.5	516.8	436.4	360.1	297.6
125°	755.6	751.2	735.8	708.5	668.9	619.3	559.9	492.3	421.8	355.5	302.9
127.5°	706.5	702.6	688.6	665.3	630.0	584.9	531.2	471.1	408.9	353.3	308.8
130°	678.8	673.8	660.8	638.6	605.7	563.6	513.4	457.7	402.0	351.8	312.8
132.5°	651.6	648.1	636.6	614.3	583.4	543.3	496.6	445.3	395.5	351.3	315.8
135°	612.5	608.2	597.1	578.5	548.1	512.8	472.5	428.6	387.1	350.5	320.2
137.5°	571.3	568.5	559.0	540.2	514.7	484.1	449.4	413.4	379.8	349.2	323.2
140°	542.6	543.2	533.2	515.9	492.3	465.7	436.0	404.4	375.3	348.7	325.2
142.5°	515.8	516.4	507.5	492.1	472.1	448.9	423.1	396.0	371.4	347.7	326.6
145°	478.7	477.5	472.5	459.5	444.1	426.1	406.3	385.9	366.1	346.2	327.6
147.5°	448.3	447.8	443.1	434.3	422.6	409.8	393.8	377.6	360.8	343.9	327.6
150°	430.5	430.5	426.7	419.9	410.6	398.9	385.9	371.6	357.4	341.9	327.6
152.5°	415.6	415.6	413.4	407.0	399.7	389.9	378.4	366.1	353.4	339.4	326.1
155°	397.0	396.4	395.1	390.1	384.6	377.2	367.9	358.0	347.5	335.1	324.6
157.5°	380.0	380.2	379.1	375.4	370.6	364.8	357.6	349.3	340.8	331.2	322.4
160°	369.2	369.7	369.7	366.1	361.7	357.4	351.2	344.4	336.3	328.3	321.5
162.5°	359.3	359.8	359.8	356.6	353.8	349.9	344.2	338.4	331.8	325.3	319.5
165°	346.2	346.2	346.8	344.4	341.9	338.8	334.5	330.7	325.7	320.8	316.5
167.5°	333.8	333.8	334.5	332.7	331.6	329.4	326.9	324.0	320.0	316.4	313.5
170°	326.4	326.4	327.0	325.7	325.2	323.9	321.5	319.6	316.5	313.4	311.6
172.5°	319.5	320.0	321.1	319.8	319.7	318.9	317.0	315.6	313.0	310.9	310.1
175°	311.6	312.1	312.8	312.1	312.1	312.1	310.9	310.3	309.0	307.8	307.8
177.5°	307.0	307.0	307.9	307.4	307.9	307.9	307.4	307.0	306.4	305.9	306.4
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1000.4	999.3	994.7	989.4	982.5	977.8	974.1	972.2	966.2	958.9	953.9
5°	1062.2	1049.7	1036.5	1020.3	1005.4	990.0	980.5	969.2	955.6	940.2	929.5
7.5°	1128.4	1104.0	1077.7	1050.6	1023.7	999.7	978.5	960.3	938.5	916.5	901.1
10°	1179.2	1143.4	1106.5	1068.8	1034.4	1002.0	977.2	952.7	926.5	901.3	882.2
12.5°	1225.3	1178.3	1135.8	1089.4	1045.4	1006.7	970.8	942.1	910.6	883.7	861.9
15°	1283.7	1235.6	1184.1	1113.6	1055.1	1006.2	962.7	924.9	886.8	853.6	832.4
17.5°	1338.2	1265.8	1196.7	1137.9	1061.9	1000.8	947.6	902.5	860.6	825.5	799.4
20°	1360.8	1290.7	1215.6	1140.6	1065.9	997.4	935.6	885.9	842.3	802.6	778.5
22.5°	1374.4	1295.0	1215.9	1135.3	1056.0	984.8	923.8	868.9	821.8	783.9	754.2
25°	1390.2	1295.7	1208.6	1128.9	1048.1	970.9	898.3	840.3	789.3	749.0	717.5
27.5°	1400.7	1289.4	1186.5	1098.0	1016.0	939.1	872.6	811.1	759.3	716.8	682.9
30°	1402.6	1284.4	1169.6	1073.8	990.4	919.9	849.4	790.5	735.8	690.5	659.0
32.5°	1405.3	1272.2	1146.7	1044.9	959.6	889.7	825.9	769.6	713.5	669.0	636.8
35°	1394.4	1265.4	1111.9	995.0	909.5	841.9	784.3	732.5	677.3	634.1	601.3
37.5°	1347.3	1238.4	1075.9	938.7	849.4	786.8	739.8	694.6	644.0	597.5	566.6
40°	1299.8	1211.9	1048.1	904.6	811.3	746.9	704.6	667.7	618.8	575.3	542.1
42.5°	1229.2	1175.8	1021.5	868.7	768.1	706.2	670.5	635.9	592.9	548.7	517.5
45°	1099.5	1106.5	967.2	811.7	708.4	646.2	612.6	588.5	550.4	513.9	482.0
47.5°	936.9	1002.8	903.4	750.8	645.4	587.0	557.7	536.7	511.0	475.2	446.0
50°	830.8	924.9	852.3	710.0	605.9	547.9	518.9	501.8	479.4	451.2	423.4
52.5°	732.8	834.0	790.6	664.6	563.2	510.1	481.7	467.7	449.9	423.3	398.2
55°	597.6	700.1	690.1	596.0	498.9	451.2	429.7	413.9	401.9	382.0	362.1
57.5°	483.5	580.6	585.7	519.7	442.4	395.2	376.7	364.8	357.0	341.9	323.5
60°	411.5	500.6	518.0	468.3	401.9	360.4	342.1	332.6	326.4	314.4	300.3
62.5°	351.7	427.6	447.3	411.5	363.1	324.2	310.0	300.8	296.5	286.1	273.7
65°	269.2	332.2	351.3	331.4	306.1	275.0	263.4	255.5	251.8	246.0	236.8
67.5°	202.4	248.3	269.3	255.2	246.1	226.5	219.0	214.8	211.5	207.6	199.9
70°	162.6	196.6	218.2	214.4	207.0	196.6	191.2	188.3	185.0	181.6	175.0
72.5°	130.7	154.2	174.4	176.3	170.2	168.0	163.3	162.1	160.1	156.1	152.5
75°	86.7	102.8	116.9	122.3	124.8	126.9	124.8	124.5	124.0	120.7	118.6
77.5°	56.8	65.5	74.4	83.6	87.5	90.3	91.0	92.5	91.4	89.7	88.6
80°	43.6	45.6	51.8	59.7	65.9	68.4	70.1	70.9	70.5	70.1	68.4
82.5°	31.6	33.4	36.3	41.8	47.1	51.2	52.2	52.0	52.9	53.2	51.8
85°	17.0	17.4	18.2	19.1	21.9	26.5	27.8	28.6	29.5	29.5	26.9
87.5°	7.7	7.0	7.3	7.0	7.8	7.7	9.4	10.9	11.4	10.4	10.8
90°	11.8	9.9	8.1	6.8	5.5	3.7	2.5	1.3	2.5	3.7	5.5
92.5°	78.7	52.0	35.8	26.6	21.5	16.6	11.4	7.7	11.4	16.6	21.5
95°	225.5	133.2	80.5	56.3	40.2	29.7	22.9	21.1	22.9	29.7	40.2
97.5°	247.4	143.3	93.0	66.9	51.0	41.9	36.5	35.9	36.5	41.9	51.0
100°	233.5	141.8	98.5	74.3	59.5	50.8	46.4	45.9	46.4	50.8	59.5
102.5°	221.6	143.8	104.9	82.8	69.4	61.2	57.4	56.2	57.4	61.2	69.4
105°	213.0	149.2	115.8	96.6	84.8	77.4	73.7	71.9	73.7	77.4	84.8
107.5°	212.5	159.4	130.1	112.3	101.2	93.9	90.3	88.4	90.3	93.9	101.2
110°	214.9	167.9	140.0	122.6	112.1	105.3	102.2	100.4	102.2	105.3	112.1





TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	219.8	176.3	150.4	133.6	123.0	116.2	113.1	111.2	113.1	116.2	123.0
115°	227.9	190.1	166.6	149.9	139.3	133.2	129.4	127.0	129.4	133.2	139.3
117.5°	238.6	204.9	181.6	166.1	154.3	148.6	145.5	142.7	145.5	148.6	154.3
120°	246.5	214.3	192.0	176.5	164.8	158.5	155.4	153.6	155.4	158.5	164.8
122.5°	253.9	224.2	202.4	185.9	174.7	167.9	164.9	163.0	164.9	167.9	174.7
125°	265.7	238.4	216.7	200.0	188.3	181.5	177.8	176.5	177.8	181.5	188.3
127.5°	275.4	250.8	229.9	213.2	200.2	193.2	188.6	186.8	188.6	193.2	200.2
130°	281.8	258.3	237.8	221.1	208.1	200.7	195.1	193.2	195.1	200.7	208.1
132.5°	287.7	264.7	244.8	228.5	215.6	206.6	200.6	198.2	200.6	206.6	215.6
135°	295.4	274.3	255.2	238.4	225.5	216.2	209.4	206.8	209.4	216.2	225.5
137.5°	301.1	281.1	262.6	247.1	234.2	224.3	217.6	215.0	217.6	224.3	234.2
140°	304.1	285.5	267.5	252.1	239.7	229.8	223.6	220.5	223.6	229.8	239.7
142.5°	307.0	289.0	271.5	257.1	244.6	235.8	229.0	226.4	229.0	235.8	244.6
145°	310.3	293.6	277.5	263.2	252.7	243.4	237.8	236.0	237.8	243.4	252.7
147.5°	312.3	297.3	282.6	270.4	260.2	252.2	246.8	245.7	246.8	252.2	260.2
150°	312.8	299.8	285.5	274.3	265.7	257.6	252.7	252.1	252.7	257.6	265.7
152.5°	313.8	301.3	289.0	278.3	270.7	263.6	258.6	258.5	258.6	263.6	270.7
155°	314.0	304.1	293.6	284.9	278.1	271.9	268.2	268.2	268.2	271.9	278.1
157.5°	314.7	305.7	297.3	290.6	284.8	279.3	276.3	275.8	276.3	279.3	284.8
160°	314.7	307.2	299.8	293.6	289.2	284.3	281.8	281.8	281.8	284.3	289.2
162.5°	314.1	307.7	301.3	296.0	292.2	288.3	286.3	286.3	286.3	288.3	292.2
165°	312.8	308.4	303.5	299.1	296.7	293.6	292.3	292.9	292.3	293.6	296.7
167.5°	311.8	308.3	304.8	302.0	300.2	297.9	297.3	298.0	297.3	297.9	300.2
170°	310.3	307.8	304.8	303.5	302.2	300.4	299.8	301.0	299.8	300.4	302.2
172.5°	309.8	307.8	305.2	304.4	303.7	302.4	302.2	303.0	302.2	302.4	303.7
175°	308.4	307.2	305.9	305.3	305.3	304.1	304.8	305.3	304.8	304.1	305.3
177.5°	307.4	306.4	305.9	305.9	305.9	305.5	305.9	306.4	305.9	305.5	305.9
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	952.3	947.9	945.0	938.3	934.0	929.4	924.7	927.7	927.4	927.0	927.0
5°	920.4	910.8	902.1	890.9	883.8	875.1	868.5	867.7	869.3	863.5	860.2
7.5°	888.7	875.6	863.2	850.9	837.8	827.4	820.8	817.7	813.5	809.9	806.2
10°	866.4	851.0	839.0	823.7	809.6	797.2	789.3	783.9	780.9	778.1	772.7
12.5°	843.5	828.5	813.2	795.8	782.4	767.9	762.1	756.0	750.4	747.2	739.8
15°	810.0	790.5	774.4	756.1	741.2	727.1	718.7	706.7	705.0	700.9	693.5
17.5°	776.4	755.3	732.9	719.5	702.6	687.9	675.3	671.2	659.3	654.9	648.4
20°	749.9	730.4	713.4	695.5	671.1	657.4	647.5	642.1	632.5	626.7	622.5
22.5°	727.0	707.2	687.5	666.7	646.5	631.1	623.8	615.4	610.3	602.1	597.6
25°	694.3	672.7	649.1	626.7	612.2	600.6	588.9	581.5	574.0	570.3	562.0
27.5°	656.3	633.7	611.6	594.7	576.9	565.4	554.8	548.2	539.2	533.0	528.4
30°	635.4	608.9	589.8	574.4	551.6	540.8	533.0	524.7	518.0	511.4	506.8
32.5°	611.2	586.9	568.9	549.9	532.3	520.6	510.4	503.1	497.4	491.2	486.6
35°	573.1	552.9	534.2	515.1	502.2	490.2	478.2	472.0	466.6	460.8	456.6
37.5°	538.8	519.8	502.1	484.0	468.1	458.3	448.6	443.9	436.6	432.7	428.4
40°	517.6	498.9	479.8	462.5	445.8	438.4	429.7	422.6	416.0	413.1	408.5
42.5°	494.4	475.7	459.6	440.8	427.3	417.2	409.1	401.4	396.4	392.2	389.6
45°	459.9	443.4	427.6	408.9	396.1	387.4	378.3	371.2	366.6	363.8	359.2
47.5°	426.5	410.0	394.0	377.6	365.2	355.3	346.2	341.3	335.2	331.6	328.6
50°	402.3	387.4	370.3	355.5	343.0	333.0	325.6	319.3	313.9	309.4	307.4
52.5°	380.1	364.2	349.4	335.6	322.4	311.2	304.4	297.8	293.7	288.5	286.1
55°	343.4	328.0	315.6	301.9	289.1	279.6	271.2	265.5	261.3	255.5	252.2
57.5°	309.0	295.2	280.4	268.5	255.2	247.2	240.3	232.4	227.4	222.8	219.6
60°	285.7	270.0	257.1	246.0	234.3	223.9	217.8	211.5	206.1	201.5	198.7
62.5°	261.6	247.8	235.6	223.4	212.8	203.7	196.5	191.3	186.6	183.6	180.8
65°	224.3	213.6	201.1	191.2	181.3	174.6	168.8	164.2	160.9	158.8	156.4
67.5°	190.2	179.7	168.9	159.1	152.5	147.4	143.6	139.7	138.0	135.4	133.7
70°	167.9	157.2	147.7	140.2	133.6	129.8	127.3	124.5	122.8	119.5	117.8
72.5°	143.8	135.9	129.0	122.9	117.6	114.2	111.1	107.5	104.9	101.2	99.6
75°	113.2	106.2	100.8	96.6	93.3	88.7	84.2	80.5	79.2	78.0	77.6
77.5°	83.9	79.4	75.5	72.0	67.9	64.6	63.5	62.7	62.4	61.8	61.8
80°	65.9	61.8	58.9	54.7	52.3	52.3	52.3	51.4	51.8	51.8	51.8
82.5°	49.0	45.2	43.6	42.1	41.7	42.0	42.0	42.1	41.9	42.5	42.2
85°	25.3	25.7	26.5	26.1	26.5	26.5	27.4	26.9	27.4	26.5	27.4
87.5°	10.6	11.9	12.6	13.3	14.0	14.0	14.3	14.3	14.8	15.0	15.2
90°	6.8	8.1	9.9	11.8	13.6	15.4	14.9	15.4	16.1	16.7	18.0
92.5°	26.6	35.8	52.0	78.7	104.8	95.2	71.9	52.1	41.4	36.5	33.4
95°	56.3	80.5	133.2	225.5	327.0	367.3	297.9	223.0	151.1	118.3	96.0
97.5°	66.9	93.0	143.3	247.4	416.7	569.2	609.0	555.8	445.2	365.3	291.2
100°	74.3	98.5	141.8	233.5	396.4	586.5	708.5	730.2	680.0	607.6	519.6
102.5°	82.8	104.9	143.8	221.6	366.6	554.3	713.5	788.1	786.6	744.3	688.6
105°	96.6	115.8	149.2	213.0	330.1	498.0	675.7	805.2	867.0	878.8	862.8
107.5°	112.3	130.1	159.4	212.5	306.8	448.1	609.6	756.4	856.9	911.2	933.2
110°	122.6	140.0	167.9	214.9	297.9	419.9	567.9	709.8	823.7	901.7	945.2



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	133.6	150.4	176.3	219.8	292.9	401.1	531.8	663.7	780.1	867.6	923.3
115°	149.9	166.6	190.1	227.9	291.1	380.9	488.1	602.6	710.3	801.5	868.9
117.5°	166.1	181.6	204.9	238.6	292.2	369.0	461.7	558.4	651.4	733.2	801.7
120°	176.5	192.0	214.3	246.5	294.2	363.5	447.8	535.1	618.7	693.1	755.6
122.5°	185.9	202.4	224.2	253.9	297.6	360.1	436.4	516.8	592.5	661.3	719.5
125°	200.0	216.7	238.4	265.7	302.9	355.5	421.8	492.3	559.9	619.3	668.9
127.5°	213.2	229.9	250.8	275.4	308.8	353.3	408.9	471.1	531.2	584.9	630.0
130°	221.1	237.8	258.3	281.8	312.8	351.8	402.0	457.7	513.4	563.6	605.7
132.5°	228.5	244.8	264.7	287.7	315.8	351.3	395.5	445.3	496.6	543.3	583.4
135°	238.4	255.2	274.3	295.4	320.2	350.5	387.1	428.6	472.5	512.8	548.1
137.5°	247.1	262.6	281.1	301.1	323.2	349.2	379.8	413.4	449.4	484.1	514.7
140°	252.1	267.5	285.5	304.1	325.2	348.7	375.3	404.4	436.0	465.7	492.3
142.5°	257.1	271.5	289.0	307.0	326.6	347.7	371.4	396.0	423.1	448.9	472.1
145°	263.2	277.5	293.6	310.3	327.6	346.2	366.1	385.9	406.3	426.1	444.1
147.5°	270.4	282.6	297.3	312.3	327.6	343.9	360.8	377.6	393.8	409.8	422.6
150°	274.3	285.5	299.8	312.8	327.6	341.9	357.4	371.6	385.9	398.9	410.6
152.5°	278.3	289.0	301.3	313.8	326.1	339.4	353.4	366.1	378.4	389.9	399.7
155°	284.9	293.6	304.1	314.0	324.6	335.1	347.5	358.0	367.9	377.2	384.6
157.5°	290.6	297.3	305.7	314.7	322.4	331.2	340.8	349.3	357.6	364.8	370.6
160°	293.6	299.8	307.2	314.7	321.5	328.3	336.3	344.4	351.2	357.4	361.7
162.5°	296.0	301.3	307.7	314.1	319.5	325.3	331.8	338.4	344.2	349.9	353.8
165°	299.1	303.5	308.4	312.8	316.5	320.8	325.7	330.7	334.5	338.8	341.9
167.5°	302.0	304.8	308.3	311.8	313.5	316.4	320.0	324.0	326.9	329.4	331.6
170°	303.5	304.8	307.8	310.3	311.6	313.4	316.5	319.6	321.5	323.9	325.2
172.5°	304.4	305.2	307.8	309.8	310.1	310.9	313.0	315.6	317.0	318.9	319.7
175°	305.3	305.9	307.2	308.4	307.8	307.8	309.0	310.3	310.9	312.1	312.1
177.5°	305.9	305.9	306.4	307.4	306.4	305.9	306.4	307.0	307.4	307.9	307.9
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	923.1	922.7	923.1	921.7	923.1	922.7	923.1	927.0	927.0	927.4	927.7
5°	859.0	858.5	857.3	853.6	857.3	858.5	859.0	860.2	863.5	869.3	867.7
7.5°	803.0	802.4	798.8	798.8	798.8	802.4	803.0	806.2	809.9	813.5	817.7
10°	769.8	770.2	765.2	762.3	765.2	770.2	769.8	772.7	778.1	780.9	783.9
12.5°	737.6	735.7	731.7	728.5	731.7	735.7	737.6	739.8	747.2	750.4	756.0
15°	695.1	690.9	681.0	681.8	681.0	690.9	695.1	693.5	700.9	705.0	706.7
17.5°	645.1	642.1	641.8	636.0	641.8	642.1	645.1	648.4	654.9	659.3	671.2
20°	615.9	613.9	614.7	608.9	614.7	613.9	615.9	622.5	626.7	632.5	642.1
22.5°	593.0	591.0	587.5	585.7	587.5	591.0	593.0	597.6	602.1	610.3	615.4
25°	559.5	556.2	552.9	554.9	552.9	556.2	559.5	562.0	570.3	574.0	581.5
27.5°	526.0	523.5	520.1	519.8	520.1	523.5	526.0	528.4	533.0	539.2	548.2
30°	504.8	502.2	500.6	498.5	500.6	502.2	504.8	506.8	511.4	518.0	524.7
32.5°	483.2	482.7	479.7	479.3	479.7	482.7	483.2	486.6	491.2	497.4	503.1
35°	455.0	452.5	451.6	452.1	451.6	452.5	455.0	456.6	460.8	466.6	472.0
37.5°	428.2	424.8	423.3	421.9	423.3	424.8	428.2	428.4	432.7	436.6	443.9
40°	408.9	405.6	404.8	403.9	404.8	405.6	408.9	408.5	413.1	416.0	422.6
42.5°	387.4	386.0	385.6	384.0	385.6	386.0	387.4	389.6	392.2	396.4	401.4
45°	357.9	357.5	355.1	355.8	355.1	357.5	357.9	359.2	363.8	366.6	371.2
47.5°	326.9	325.1	323.4	324.5	323.4	325.1	326.9	328.6	331.6	335.2	341.3
50°	305.7	304.8	301.1	301.9	301.1	304.8	305.7	307.4	309.4	313.9	319.3
52.5°	284.5	281.3	279.9	279.4	279.9	281.3	284.5	286.1	288.5	293.7	297.8
55°	249.3	245.5	243.8	243.0	243.8	245.5	249.3	252.2	255.5	261.3	265.5
57.5°	214.8	213.7	212.5	213.3	212.5	213.7	214.8	219.6	222.8	227.4	232.4
60°	194.5	194.5	194.5	194.1	194.5	194.5	194.5	198.7	201.5	206.1	211.5
62.5°	179.0	177.9	177.6	178.2	177.6	177.9	179.0	180.8	183.6	186.6	191.3
65°	155.1	154.7	153.0	152.7	153.0	154.7	155.1	156.4	158.8	160.9	164.2
67.5°	132.6	131.1	130.6	130.1	130.6	131.1	132.6	133.7	135.4	138.0	139.7
70°	115.7	114.9	112.4	112.8	112.4	114.9	115.7	117.8	119.5	122.8	124.5
72.5°	97.4	96.6	96.2	95.5	96.2	96.6	97.4	99.6	101.2	104.9	107.5
75°	77.2	76.8	76.3	78.0	76.3	76.8	77.2	77.6	78.0	79.2	80.5
77.5°	61.8	61.8	62.0	61.4	62.0	61.8	61.8	61.8	61.8	62.4	62.7
80°	51.8	51.8	51.4	51.4	51.4	51.8	51.8	51.8	51.8	51.8	51.4
82.5°	41.6	41.9	42.1	41.5	42.1	41.9	41.6	42.2	42.5	41.9	42.1
85°	27.4	26.9	27.8	27.4	27.8	26.9	27.4	27.4	26.5	27.4	26.9
87.5°	15.8	15.2	15.4	15.5	15.4	15.2	15.8	15.2	15.0	14.8	14.3
90°	17.3	18.0	18.6	18.0	18.6	18.0	17.3	18.0	16.7	16.1	15.4
92.5°	32.2	30.3	31.0	29.9	31.0	30.3	32.2	33.4	36.5	41.4	52.1
95°	84.2	78.7	74.3	71.9	74.3	78.7	84.2	96.0	118.3	151.1	223.0
97.5°	245.5	217.6	200.9	195.6	200.9	217.6	245.5	291.2	365.3	445.2	555.8
100°	457.1	411.9	387.7	388.3	387.7	411.9	457.1	519.6	607.6	680.0	730.2
102.5°	639.9	604.1	583.9	569.7	583.9	604.1	639.9	688.6	744.3	786.6	788.1
105°	834.2	810.7	790.9	787.8	790.9	810.7	834.2	862.8	878.8	867.0	805.2
107.5°	933.7	925.8	919.1	913.4	919.1	925.8	933.7	933.2	911.2	856.9	756.4
110°	962.4	967.4	966.1	965.0	966.1	967.4	962.4	945.2	901.7	823.7	709.8



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	955.1	970.4	975.1	975.3	975.1	970.4	955.1	923.3	867.6	780.1	663.7
115°	915.4	942.6	955.1	958.1	955.1	942.6	915.4	868.9	801.5	710.3	602.6
117.5°	850.1	881.3	899.1	903.4	899.1	881.3	850.1	801.7	733.2	651.4	558.4
120°	804.5	839.2	854.1	857.8	854.1	839.2	804.5	755.6	693.1	618.7	535.1
122.5°	762.9	794.1	810.5	815.2	810.5	794.1	762.9	719.5	661.3	592.5	516.8
125°	708.5	735.8	751.2	755.6	751.2	735.8	708.5	668.9	619.3	559.9	492.3
127.5°	665.3	688.6	702.6	706.5	702.6	688.6	665.3	630.0	584.9	531.2	471.1
130°	638.6	660.8	673.8	678.8	673.8	660.8	638.6	605.7	563.6	513.4	457.7
132.5°	614.3	636.6	648.1	651.6	648.1	636.6	614.3	583.4	543.3	496.6	445.3
135°	578.5	597.1	608.2	612.5	608.2	597.1	578.5	548.1	512.8	472.5	428.6
137.5°	540.2	559.0	568.5	571.3	568.5	559.0	540.2	514.7	484.1	449.4	413.4
140°	515.9	533.2	543.2	542.6	543.2	533.2	515.9	492.3	465.7	436.0	404.4
142.5°	492.1	507.5	516.4	515.8	516.4	507.5	492.1	472.1	448.9	423.1	396.0
145°	459.5	472.5	477.5	478.7	477.5	472.5	459.5	444.1	426.1	406.3	385.9
147.5°	434.3	443.1	447.8	448.3	447.8	443.1	434.3	422.6	409.8	393.8	377.6
150°	419.9	426.7	430.5	430.5	430.5	426.7	419.9	410.6	398.9	385.9	371.6
152.5°	407.0	413.4	415.6	415.6	415.6	413.4	407.0	399.7	389.9	378.4	366.1
155°	390.1	395.1	396.4	397.0	396.4	395.1	390.1	384.6	377.2	367.9	358.0
157.5°	375.4	379.1	380.2	380.0	380.2	379.1	375.4	370.6	364.8	357.6	349.3
160°	366.1	369.7	369.7	369.2	369.7	369.7	366.1	361.7	357.4	351.2	344.4
162.5°	356.6	359.8	359.8	359.3	359.8	359.8	356.6	353.8	349.9	344.2	338.4
165°	344.4	346.8	346.2	346.2	346.2	346.8	344.4	341.9	338.8	334.5	330.7
167.5°	332.7	334.5	333.8	333.8	333.8	334.5	332.7	331.6	329.4	326.9	324.0
170°	325.7	327.0	326.4	326.4	326.4	327.0	325.7	325.2	323.9	321.5	319.6
172.5°	319.8	321.1	320.0	319.5	320.0	321.1	319.8	319.7	318.9	317.0	315.6
175°	312.1	312.8	312.1	311.6	312.1	312.8	312.1	312.1	312.1	310.9	310.3
177.5°	307.4	307.9	307.0	307.0	307.0	307.9	307.4	307.9	307.9	307.4	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	924.7	929.4	934.0	938.3	945.0	947.9	952.3	953.9	958.9	966.2	972.2
5°	868.5	875.1	883.8	890.9	902.1	910.8	920.4	929.5	940.2	955.6	969.2
7.5°	820.8	827.4	837.8	850.9	863.2	875.6	888.7	901.1	916.5	938.5	960.3
10°	789.3	797.2	809.6	823.7	839.0	851.0	866.4	882.2	901.3	926.5	952.7
12.5°	762.1	767.9	782.4	795.8	813.2	828.5	843.5	861.9	883.7	910.6	942.1
15°	718.7	727.1	741.2	756.1	774.4	790.5	810.0	832.4	853.6	886.8	924.9
17.5°	675.3	687.9	702.6	719.5	732.9	755.3	776.4	799.4	825.5	860.6	902.5
20°	647.5	657.4	671.1	695.5	713.4	730.4	749.9	778.5	802.6	842.3	885.9
22.5°	623.8	631.1	646.5	666.7	687.5	707.2	727.0	754.2	783.9	821.8	868.9
25°	588.9	600.6	612.2	626.7	649.1	672.7	694.3	717.5	749.0	789.3	840.3
27.5°	554.8	565.4	576.9	594.7	611.6	633.7	656.3	682.9	716.8	759.3	811.1
30°	533.0	540.8	551.6	574.4	589.8	608.9	635.4	659.0	690.5	735.8	790.5
32.5°	510.4	520.6	532.3	549.9	568.9	586.9	611.2	636.8	669.0	713.5	769.6
35°	478.2	490.2	502.2	515.1	534.2	552.9	573.1	601.3	634.1	677.3	732.5
37.5°	448.6	458.3	468.1	484.0	502.1	519.8	538.8	566.6	597.5	644.0	694.6
40°	429.7	438.4	445.8	462.5	479.8	498.9	517.6	542.1	575.3	618.8	667.7
42.5°	409.1	417.2	427.3	440.8	459.6	475.7	494.4	517.5	548.7	592.9	635.9
45°	378.3	387.4	396.1	408.9	427.6	443.4	459.9	482.0	513.9	550.4	588.5
47.5°	346.2	355.3	365.2	377.6	394.0	410.0	426.5	446.0	475.2	511.0	536.7
50°	325.6	333.0	343.0	355.5	370.3	387.4	402.3	423.4	451.2	479.4	501.8
52.5°	304.4	311.2	322.4	335.6	349.4	364.2	380.1	398.2	423.3	449.9	467.7
55°	271.2	279.6	289.1	301.9	315.6	328.0	343.4	362.1	382.0	401.9	413.9
57.5°	240.3	247.2	255.2	268.5	280.4	295.2	309.0	323.5	341.9	357.0	364.8
60°	217.8	223.9	234.3	246.0	257.1	270.0	285.7	300.3	314.4	326.4	332.6
62.5°	196.5	203.7	212.8	223.4	235.6	247.8	261.6	273.7	286.1	296.5	300.8
65°	168.8	174.6	181.3	191.2	201.1	213.6	224.3	236.8	246.0	251.8	255.5
67.5°	143.6	147.4	152.5	159.1	168.9	179.7	190.2	199.9	207.6	211.5	214.8
70°	127.3	129.8	133.6	140.2	147.7	157.2	167.9	175.0	181.6	185.0	188.3
72.5°	111.1	114.2	117.6	122.9	129.0	135.9	143.8	152.5	156.1	160.1	162.1
75°	84.2	88.7	93.3	96.6	100.8	106.2	113.2	118.6	120.7	124.0	124.5
77.5°	63.5	64.6	67.9	72.0	75.5	79.4	83.9	88.6	89.7	91.4	92.5
80°	52.3	52.3	52.3	54.7	58.9	61.8	65.9	68.4	70.1	70.5	70.9
82.5°	42.0	42.0	41.7	42.1	43.6	45.2	49.0	51.8	53.2	52.9	52.0
85°	27.4	26.5	26.5	26.1	26.5	25.7	25.3	26.9	29.5	29.5	28.6
87.5°	14.3	14.0	14.0	13.3	12.6	11.9	10.6	10.8	10.4	11.4	10.9
90°	14.9	15.4	13.6	11.8	9.9	8.1	6.8	5.5	3.7	2.5	1.3
92.5°	71.9	95.2	104.8	78.7	52.0	35.8	26.6	21.5	16.6	11.4	7.7
95°	297.9	367.3	327.0	225.5	133.2	80.5	56.3	40.2	29.7	22.9	21.1
97.5°	609.0	569.2	416.7	247.4	143.3	93.0	66.9	51.0	41.9	36.5	35.9
100°	708.5	586.5	396.4	233.5	141.8	98.5	74.3	59.5	50.8	46.4	45.9
102.5°	713.5	554.3	366.6	221.6	143.8	104.9	82.8	69.4	61.2	57.4	56.2
105°	675.7	498.0	330.1	213.0	149.2	115.8	96.6	84.8	77.4	73.7	71.9
107.5°	609.6	448.1	306.8	212.5	159.4	130.1	112.3	101.2	93.9	90.3	88.4
110°	567.9	419.9	297.9	214.9	167.9	140.0	122.6	112.1	105.3	102.2	100.4



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	531.8	401.1	292.9	219.8	176.3	150.4	133.6	123.0	116.2	113.1	111.2
115°	488.1	380.9	291.1	227.9	190.1	166.6	149.9	139.3	133.2	129.4	127.0
117.5°	461.7	369.0	292.2	238.6	204.9	181.6	166.1	154.3	148.6	145.5	142.7
120°	447.8	363.5	294.2	246.5	214.3	192.0	176.5	164.8	158.5	155.4	153.6
122.5°	436.4	360.1	297.6	253.9	224.2	202.4	185.9	174.7	167.9	164.9	163.0
125°	421.8	355.5	302.9	265.7	238.4	216.7	200.0	188.3	181.5	177.8	176.5
127.5°	408.9	353.3	308.8	275.4	250.8	229.9	213.2	200.2	193.2	188.6	186.8
130°	402.0	351.8	312.8	281.8	258.3	237.8	221.1	208.1	200.7	195.1	193.2
132.5°	395.5	351.3	315.8	287.7	264.7	244.8	228.5	215.6	206.6	200.6	198.2
135°	387.1	350.5	320.2	295.4	274.3	255.2	238.4	225.5	216.2	209.4	206.8
137.5°	379.8	349.2	323.2	301.1	281.1	262.6	247.1	234.2	224.3	217.6	215.0
140°	375.3	348.7	325.2	304.1	285.5	267.5	252.1	239.7	229.8	223.6	220.5
142.5°	371.4	347.7	326.6	307.0	289.0	271.5	257.1	244.6	235.8	229.0	226.4
145°	366.1	346.2	327.6	310.3	293.6	277.5	263.2	252.7	243.4	237.8	236.0
147.5°	360.8	343.9	327.6	312.3	297.3	282.6	270.4	260.2	252.2	246.8	245.7
150°	357.4	341.9	327.6	312.8	299.8	285.5	274.3	265.7	257.6	252.7	252.1
152.5°	353.4	339.4	326.1	313.8	301.3	289.0	278.3	270.7	263.6	258.6	258.5
155°	347.5	335.1	324.6	314.0	304.1	293.6	284.9	278.1	271.9	268.2	268.2
157.5°	340.8	331.2	322.4	314.7	305.7	297.3	290.6	284.8	279.3	276.3	275.8
160°	336.3	328.3	321.5	314.7	307.2	299.8	293.6	289.2	284.3	281.8	281.8
162.5°	331.8	325.3	319.5	314.1	307.7	301.3	296.0	292.2	288.3	286.3	286.3
165°	325.7	320.8	316.5	312.8	308.4	303.5	299.1	296.7	293.6	292.3	292.9
167.5°	320.0	316.4	313.5	311.8	308.3	304.8	302.0	300.2	297.9	297.3	298.0
170°	316.5	313.4	311.6	310.3	307.8	304.8	303.5	302.2	300.4	299.8	301.0
172.5°	313.0	310.9	310.1	309.8	307.8	305.2	304.4	303.7	302.4	302.2	303.0
175°	309.0	307.8	307.8	308.4	307.2	305.9	305.3	305.3	304.1	304.8	305.3
177.5°	306.4	305.9	306.4	307.4	306.4	305.9	305.9	305.9	305.5	305.9	306.4
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	974.1	977.8	982.5	989.4	994.7	999.3	1000.4	1001.7	1005.0	1010.7	1014.9
5°	980.5	990.0	1005.4	1020.3	1036.5	1049.7	1062.2	1070.9	1079.2	1096.6	1110.7
7.5°	978.5	999.7	1023.7	1050.6	1077.7	1104.0	1128.4	1150.2	1171.9	1197.3	1226.2
10°	977.2	1002.0	1034.4	1068.8	1106.5	1143.4	1179.2	1206.9	1239.3	1268.3	1305.2
12.5°	970.8	1006.7	1045.4	1089.4	1135.8	1178.3	1225.3	1263.7	1300.7	1342.6	1385.5
15°	962.7	1006.2	1055.1	1113.6	1184.1	1235.6	1283.7	1350.4	1396.1	1441.7	1503.0
17.5°	947.6	1000.8	1061.9	1137.9	1196.7	1265.8	1338.2	1391.0	1452.5	1516.7	1572.3
20°	935.6	997.4	1065.9	1140.6	1215.6	1290.7	1360.8	1423.8	1487.3	1561.5	1607.2
22.5°	923.8	984.8	1056.0	1135.3	1215.9	1295.0	1374.4	1448.3	1519.8	1594.7	1653.0
25°	898.3	970.9	1048.1	1128.9	1208.6	1295.7	1390.2	1472.7	1561.1	1638.2	1693.4
27.5°	872.6	939.1	1016.0	1098.0	1186.5	1289.4	1400.7	1494.5	1583.0	1638.2	1655.6
30°	849.4	919.9	990.4	1073.8	1169.6	1284.4	1402.6	1510.1	1582.7	1606.7	1588.9
32.5°	825.9	889.7	959.6	1044.9	1146.7	1272.2	1405.3	1500.8	1544.5	1526.1	1453.5
35°	784.3	841.9	909.5	995.0	1111.9	1265.4	1394.4	1459.0	1448.3	1344.6	1207.8
37.5°	739.8	786.8	849.4	938.7	1075.9	1238.4	1347.3	1356.8	1263.5	1104.3	946.2
40°	704.6	746.9	811.3	904.6	1048.1	1211.9	1299.8	1261.2	1116.5	939.4	807.6
42.5°	670.5	706.2	768.1	868.7	1021.5	1175.8	1229.2	1145.1	978.1	810.6	690.7
45°	612.6	646.2	708.4	811.7	967.2	1106.5	1099.5	953.5	786.4	651.6	552.0
47.5°	557.7	587.0	645.4	750.8	903.4	1002.8	936.9	781.6	639.8	531.6	460.7
50°	518.9	547.9	605.9	710.0	852.3	924.9	830.8	681.0	551.2	461.6	405.2
52.5°	481.7	510.1	563.2	664.6	790.6	834.0	732.8	594.1	485.8	408.5	360.0
55°	429.7	451.2	498.9	596.0	690.1	700.1	597.6	481.5	392.4	338.4	305.2
57.5°	376.7	395.2	442.4	519.7	585.7	580.6	483.5	382.9	322.9	282.9	258.8
60°	342.1	360.4	401.9	468.3	518.0	500.6	411.5	330.6	279.1	249.7	230.6
62.5°	310.0	324.2	363.1	411.5	447.3	427.6	351.7	284.8	244.0	219.1	204.1
65°	263.4	275.0	306.1	331.4	351.3	332.2	269.2	222.7	193.3	175.9	165.5
67.5°	219.0	226.5	246.1	255.2	269.3	248.3	202.4	171.3	154.6	139.8	132.6
70°	191.2	196.6	207.0	214.4	218.2	196.6	162.6	139.7	125.6	115.3	110.7
72.5°	163.3	168.0	170.2	176.3	174.4	154.2	130.7	112.6	102.4	95.4	89.5
75°	124.8	126.9	124.8	122.3	116.9	102.8	86.7	77.6	70.1	66.8	64.7
77.5°	91.0	90.3	87.5	83.6	74.4	65.5	56.8	53.8	50.5	48.8	48.0
80°	70.1	68.4	65.9	59.7	51.8	45.6	43.6	41.5	40.2	38.2	37.7
82.5°	52.2	51.2	47.1	41.8	36.3	33.4	31.6	30.9	29.6	28.5	28.4
85°	27.8	26.5	21.9	19.1	18.2	17.4	17.0	17.0	15.4	14.9	14.9
87.5°	9.4	7.7	7.8	7.0	7.3	7.0	7.7	7.4	7.4	7.6	7.1
90°	2.5	3.7	5.5	6.8	8.1	9.9	11.8	13.6	15.4	14.9	15.4
92.5°	11.4	16.6	21.5	26.6	35.8	52.0	78.7	104.8	95.2	71.9	52.1
95°	22.9	29.7	40.2	56.3	80.5	133.2	225.5	327.0	367.3	297.9	223.0
97.5°	36.5	41.9	51.0	66.9	93.0	143.3	247.4	416.7	569.2	609.0	555.8
100°	46.4	50.8	59.5	74.3	98.5	141.8	233.5	396.4	586.5	708.5	730.2
102.5°	57.4	61.2	69.4	82.8	104.9	143.8	221.6	366.6	554.3	713.5	788.1
105°	73.7	77.4	84.8	96.6	115.8	149.2	213.0	330.1	498.0	675.7	805.2
107.5°	90.3	93.9	101.2	112.3	130.1	159.4	212.5	306.8	448.1	609.6	756.4
110°	102.2	105.3	112.1	122.6	140.0	167.9	214.9	297.9	419.9	567.9	709.8





TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	113.1	116.2	123.0	133.6	150.4	176.3	219.8	292.9	401.1	531.8	663.7
115°	129.4	133.2	139.3	149.9	166.6	190.1	227.9	291.1	380.9	488.1	602.6
117.5°	145.5	148.6	154.3	166.1	181.6	204.9	238.6	292.2	369.0	461.7	558.4
120°	155.4	158.5	164.8	176.5	192.0	214.3	246.5	294.2	363.5	447.8	535.1
122.5°	164.9	167.9	174.7	185.9	202.4	224.2	253.9	297.6	360.1	436.4	516.8
125°	177.8	181.5	188.3	200.0	216.7	238.4	265.7	302.9	355.5	421.8	492.3
127.5°	188.6	193.2	200.2	213.2	229.9	250.8	275.4	308.8	353.3	408.9	471.1
130°	195.1	200.7	208.1	221.1	237.8	258.3	281.8	312.8	351.8	402.0	457.7
132.5°	200.6	206.6	215.6	228.5	244.8	264.7	287.7	315.8	351.3	395.5	445.3
135°	209.4	216.2	225.5	238.4	255.2	274.3	295.4	320.2	350.5	387.1	428.6
137.5°	217.6	224.3	234.2	247.1	262.6	281.1	301.1	323.2	349.2	379.8	413.4
140°	223.6	229.8	239.7	252.1	267.5	285.5	304.1	325.2	348.7	375.3	404.4
142.5°	229.0	235.8	244.6	257.1	271.5	289.0	307.0	326.6	347.7	371.4	396.0
145°	237.8	243.4	252.7	263.2	277.5	293.6	310.3	327.6	346.2	366.1	385.9
147.5°	246.8	252.2	260.2	270.4	282.6	297.3	312.3	327.6	343.9	360.8	377.6
150°	252.7	257.6	265.7	274.3	285.5	299.8	312.8	327.6	341.9	357.4	371.6
152.5°	258.6	263.6	270.7	278.3	289.0	301.3	313.8	326.1	339.4	353.4	366.1
155°	268.2	271.9	278.1	284.9	293.6	304.1	314.0	324.6	335.1	347.5	358.0
157.5°	276.3	279.3	284.8	290.6	297.3	305.7	314.7	322.4	331.2	340.8	349.3
160°	281.8	284.3	289.2	293.6	299.8	307.2	314.7	321.5	328.3	336.3	344.4
162.5°	286.3	288.3	292.2	296.0	301.3	307.7	314.1	319.5	325.3	331.8	338.4
165°	292.3	293.6	296.7	299.1	303.5	308.4	312.8	316.5	320.8	325.7	330.7
167.5°	297.3	297.9	300.2	302.0	304.8	308.3	311.8	313.5	316.4	320.0	324.0
170°	299.8	300.4	302.2	303.5	304.8	307.8	310.3	311.6	313.4	316.5	319.6
172.5°	302.2	302.4	303.7	304.4	305.2	307.8	309.8	310.1	310.9	313.0	315.6
175°	304.8	304.1	305.3	305.3	305.9	307.2	308.4	307.8	307.8	309.0	310.3
177.5°	305.9	305.5	305.9	305.9	305.9	306.4	307.4	306.4	305.9	306.4	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9	305.9



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1021.9	1021.9	1023.3	1028.3	1028.9	1033.2	1031.9
5°	1123.2	1131.0	1133.9	1146.4	1153.8	1157.1	1150.5
7.5°	1246.9	1269.2	1279.7	1292.7	1304.2	1307.7	1298.6
10°	1337.1	1360.3	1379.9	1391.9	1403.1	1410.6	1420.1
12.5°	1424.4	1452.9	1471.5	1488.4	1500.0	1509.4	1511.0
15°	1519.2	1562.3	1595.1	1619.1	1631.2	1637.4	1634.9
17.5°	1614.9	1654.9	1678.2	1702.7	1719.4	1720.2	1720.7
20°	1669.0	1707.9	1734.9	1753.1	1771.8	1771.0	1775.1
22.5°	1705.1	1735.8	1756.4	1769.7	1776.2	1773.0	1773.8
25°	1722.0	1731.2	1727.4	1706.3	1700.9	1681.4	1684.7
27.5°	1634.7	1591.7	1547.0	1489.6	1444.3	1408.2	1410.0
30°	1516.3	1440.0	1352.9	1279.9	1214.4	1196.1	1157.1
32.5°	1350.8	1236.3	1134.2	1066.2	1010.0	994.7	960.8
35°	1070.1	958.9	854.0	790.9	766.0	731.2	730.8
37.5°	831.7	733.9	678.3	631.1	606.3	585.2	583.1
40°	699.7	623.4	581.5	547.5	523.0	507.2	503.5
42.5°	607.4	545.7	506.5	485.4	466.6	458.4	452.4
45°	496.1	454.6	427.2	408.1	399.4	393.2	389.8
47.5°	414.9	387.1	368.4	355.8	348.7	342.1	343.9
50°	370.8	348.0	334.3	322.3	316.9	312.3	312.8
52.5°	335.3	314.8	303.7	295.1	288.4	285.1	283.5
55°	284.6	271.6	260.5	254.2	250.5	246.0	244.7
57.5°	242.7	232.7	223.6	216.6	215.6	211.3	211.8
60°	214.8	206.5	199.1	195.4	192.4	188.7	190.0
62.5°	191.9	185.0	178.2	175.1	172.2	169.4	170.1
65°	157.2	150.5	146.4	144.7	143.5	142.3	141.0
67.5°	125.2	121.2	118.6	115.0	112.5	112.1	110.8
70°	105.4	100.0	95.4	90.9	89.6	89.2	89.6
72.5°	84.4	81.0	79.8	77.6	77.3	76.2	77.0
75°	63.5	62.2	61.4	59.7	59.7	59.7	59.7
77.5°	46.8	46.0	45.6	45.2	44.8	44.2	44.1
80°	36.5	36.0	35.3	35.3	34.9	35.3	34.9
82.5°	27.6	27.5	26.6	26.6	26.2	26.0	26.2
85°	14.1	13.7	14.5	13.7	14.1	13.3	14.1
87.5°	7.2	7.3	7.2	7.1	6.9	7.7	6.9
90°	16.1	16.7	18.0	17.3	18.0	18.6	18.0
92.5°	41.4	36.5	33.4	32.2	30.3	31.0	29.9
95°	151.1	118.3	96.0	84.2	78.7	74.3	71.9
97.5°	445.2	365.3	291.2	245.5	217.6	200.9	195.6
100°	680.0	607.6	519.6	457.1	411.9	387.7	388.3
102.5°	786.6	744.3	688.6	639.9	604.1	583.9	569.7
105°	867.0	878.8	862.8	834.2	810.7	790.9	787.8
107.5°	856.9	911.2	933.2	933.7	925.8	919.1	913.4
110°	823.7	901.7	945.2	962.4	967.4	966.1	965.0



TEST NUMBER: P332314-927

CATALOG NUMBER: S123RDIP-S775D805U927-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	780.1	867.6	923.3	955.1	970.4	975.1	975.3
115°	710.3	801.5	868.9	915.4	942.6	955.1	958.1
117.5°	651.4	733.2	801.7	850.1	881.3	899.1	903.4
120°	618.7	693.1	755.6	804.5	839.2	854.1	857.8
122.5°	592.5	661.3	719.5	762.9	794.1	810.5	815.2
125°	559.9	619.3	668.9	708.5	735.8	751.2	755.6
127.5°	531.2	584.9	630.0	665.3	688.6	702.6	706.5
130°	513.4	563.6	605.7	638.6	660.8	673.8	678.8
132.5°	496.6	543.3	583.4	614.3	636.6	648.1	651.6
135°	472.5	512.8	548.1	578.5	597.1	608.2	612.5
137.5°	449.4	484.1	514.7	540.2	559.0	568.5	571.3
140°	436.0	465.7	492.3	515.9	533.2	543.2	542.6
142.5°	423.1	448.9	472.1	492.1	507.5	516.4	515.8
145°	406.3	426.1	444.1	459.5	472.5	477.5	478.7
147.5°	393.8	409.8	422.6	434.3	443.1	447.8	448.3
150°	385.9	398.9	410.6	419.9	426.7	430.5	430.5
152.5°	378.4	389.9	399.7	407.0	413.4	415.6	415.6
155°	367.9	377.2	384.6	390.1	395.1	396.4	397.0
157.5°	357.6	364.8	370.6	375.4	379.1	380.2	380.0
160°	351.2	357.4	361.7	366.1	369.7	369.7	369.2
162.5°	344.2	349.9	353.8	356.6	359.8	359.8	359.3
165°	334.5	338.8	341.9	344.4	346.8	346.2	346.2
167.5°	326.9	329.4	331.6	332.7	334.5	333.8	333.8
170°	321.5	323.9	325.2	325.7	327.0	326.4	326.4
172.5°	317.0	318.9	319.7	319.8	321.1	320.0	319.5
175°	310.9	312.1	312.1	312.1	312.8	312.1	311.6
177.5°	307.4	307.9	307.9	307.4	307.9	307.0	307.0
180°	305.9	305.9	305.9	305.9	305.9	305.9	305.9

(END OF REPORT)