

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331894-830

Luminaire Tested: **S123DIP-S340D1025U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331894-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U830-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4868.2 lumens
Efficiency: N/A
Efficacy: 130.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	59	47	45	44	32	31	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26	20
3	77	68	61	56	69	61	56	51	48	44	41	36	34	31	25	24	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	23	21	19	15
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	40	35	53	43	37	32	35	30	26	26	23	20	18	16	15	12
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	46	35	29	24	28	24	20	22	18	16	15	13	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	23	19	24	19	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4878	4878	4878	4878
5°	5817	4900	4341	4900
10°	7282	4875	3922	4875
15°	8931	4835	3651	4835
20°	10639	4774	3477	4774
25°	11297	4700	3437	4700
30°	9684	4645	3455	4645
35°	6734	4568	3491	4568
40°	5073	4477	3481	4477
45°	4211	4341	3436	4341
50°	3773	4068	3404	4068
55°	3526	3772	3363	3772
60°	3309	3460	3328	3460
65°	3110	3156	3222	3156
70°	2917	2807	3068	2807
75°	2612	2458	2816	2458
80°	2287	2015	2424	2015
85°	1791	1470	1630	1470



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	0.9
10°-20°	143.2	2.9
20°-30°	240.3	4.9
30°-40°	272.0	5.6
40°-50°	244.0	5.0
50°-60°	196.9	4.0
60°-70°	137.2	2.8
70°-80°	72.1	1.5
80°-90°	21.2	0.4
90°-100°	258.6	5.3
100°-110°	732.4	15.0
110°-120°	720.5	14.8
120°-130°	574.7	11.8
130°-140°	453.1	9.3
140°-150°	338.2	6.9
150°-160°	235.7	4.8
160°-170°	138.5	2.8
170°-180°	45.1	0.9
0°-30°	428.1	8.8
0°-40°	700.1	14.4
0°-60°	1140.9	23.4
0°-90°	1371.5	28.2
90°-120°	1711.5	35.2
90°-150°	3077.4	63.2
90°-180°	3497.0	71.8
0°-180°	4868.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	453	453	453	453	453	
5°	538	454	402	454	538	56
15°	801	434	328	434	801	231
25°	951	396	289	396	951	417
35°	512	348	266	348	512	333
45°	277	285	226	285	277	219
55°	188	201	179	201	188	169
65°	122	124	126	124	122	122
75°	63	59	68	59	63	67
85°	14	12	13	12	14	18
90°	27	2	27	2	27	15
95°	109	32	109	32	109	197
105°	1197	109	1197	109	1197	1181
115°	1456	193	1456	193	1456	1414
125°	1148	268	1148	268	1148	1040
135°	930	314	930	314	930	722
145°	727	358	727	358	727	463
155°	603	407	603	407	603	281
165°	526	445	526	445	526	150
175°	473	464	473	464	473	46
180°	465	465	465	465	465	



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	481.0	480.6	479.8	480.4	479.0	477.1	476.9	475.1	470.0	469.8	468.3
5°	538.4	536.7	536.4	536.2	533.1	529.0	521.0	520.4	509.8	504.6	498.2
7.5°	612.8	613.7	610.5	607.8	598.3	592.1	583.6	572.8	559.9	546.7	538.0
10°	666.2	673.4	664.5	658.3	652.6	641.9	629.3	613.7	598.1	579.9	566.1
12.5°	723.5	727.0	725.2	719.4	710.6	694.2	672.0	654.8	640.5	610.1	597.9
15°	801.4	814.8	806.3	786.6	786.9	771.4	742.4	710.6	693.6	667.0	630.8
17.5°	884.6	886.2	882.6	866.1	855.2	833.7	806.9	776.5	742.2	710.0	671.6
20°	928.8	927.5	919.8	911.3	892.4	875.7	846.5	812.5	768.5	736.9	694.9
22.5°	953.4	951.2	947.5	940.4	924.7	906.8	880.5	843.4	801.5	758.0	709.5
25°	951.2	954.0	954.5	952.5	947.1	936.3	915.7	886.0	844.3	788.2	737.8
27.5°	865.2	869.2	880.9	891.4	903.0	914.8	913.2	898.5	867.6	819.3	757.5
30°	779.1	770.2	792.0	819.4	838.1	871.1	889.5	890.6	873.3	831.8	771.6
32.5°	659.6	669.3	678.9	712.7	753.5	790.4	827.2	856.7	860.1	832.5	779.9
35°	512.5	524.6	542.2	559.7	603.6	641.4	706.0	762.1	806.9	812.8	780.6
37.5°	413.0	419.0	430.1	447.7	476.4	521.2	571.1	642.2	707.1	755.4	757.4
40°	361.0	362.8	375.2	388.6	411.9	448.8	493.8	556.7	634.3	701.8	729.9
42.5°	322.0	325.8	331.2	344.0	362.6	390.3	432.2	484.1	555.3	632.9	687.9
45°	276.6	281.1	284.4	292.9	306.1	324.8	353.9	401.4	455.6	535.7	609.7
47.5°	246.8	247.0	249.5	256.0	264.9	279.0	299.6	330.1	379.8	444.9	520.8
50°	225.3	228.8	229.7	234.7	241.8	252.0	269.2	295.1	335.9	393.0	462.9
52.5°	210.2	211.2	213.7	217.4	223.5	231.5	246.4	266.6	298.7	347.4	411.6
55°	187.9	187.9	190.4	193.2	196.7	204.0	213.9	228.8	253.2	291.0	344.1
57.5°	167.4	168.5	170.2	171.1	174.1	178.9	187.1	198.5	216.6	245.7	287.9
60°	153.7	155.7	155.4	157.2	159.9	163.6	170.6	179.8	196.0	219.3	255.0
62.5°	141.8	141.7	141.6	143.7	146.3	149.9	154.5	162.4	176.3	196.9	227.2
65°	122.1	121.7	123.2	124.5	125.4	128.0	131.5	138.6	147.8	163.2	186.6
67.5°	104.6	103.3	104.2	104.6	106.1	108.2	111.5	115.8	123.1	135.4	153.2
70°	92.7	91.5	91.3	91.8	93.1	94.6	97.1	101.2	108.0	117.9	130.8
72.5°	80.4	79.6	79.6	80.6	81.2	82.2	83.9	87.7	93.1	100.6	112.6
75°	62.8	62.8	62.8	63.1	63.7	64.6	65.9	67.9	72.0	77.3	85.4
77.5°	47.0	47.0	46.8	46.8	47.7	48.1	48.4	50.2	52.6	56.1	62.0
80°	36.9	35.8	36.2	36.9	37.3	37.5	38.2	38.6	40.6	42.6	46.8
82.5°	27.4	26.5	26.6	27.6	27.7	27.9	28.6	29.1	29.9	31.7	33.9
85°	14.5	14.5	14.7	14.7	14.9	14.7	15.4	15.6	15.6	16.7	18.0
87.5°	10.7	10.6	10.6	10.6	10.6	10.4	10.4	10.4	10.3	10.7	10.3
90°	27.2	28.2	27.2	26.3	27.2	25.4	24.5	23.6	22.6	23.6	20.7
92.5°	45.3	47.0	46.1	48.9	50.6	55.5	62.9	79.2	109.1	144.7	159.2
95°	109.1	112.9	119.5	128.0	145.8	179.7	229.6	338.7	452.5	557.9	496.7
97.5°	297.1	305.2	330.6	373.0	442.3	554.9	676.3	844.3	925.0	864.6	633.0
100°	589.9	589.0	625.7	694.4	789.4	922.9	1033.0	1109.3	1076.3	891.0	602.1
102.5°	865.3	887.0	917.7	972.0	1046.0	1130.7	1194.9	1197.3	1083.8	842.1	556.9
105°	1196.7	1201.5	1231.5	1267.2	1310.6	1335.0	1317.2	1223.0	1026.4	756.4	501.4
107.5°	1387.5	1396.2	1406.4	1418.4	1417.7	1384.1	1301.7	1149.0	926.0	680.8	466.1
110°	1465.8	1467.7	1469.6	1462.1	1435.7	1369.8	1251.3	1078.2	862.7	637.9	452.5



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1481.6	1481.2	1474.0	1450.8	1402.6	1317.9	1185.1	1008.1	807.8	609.3	445.0
115°	1455.5	1450.8	1431.9	1390.5	1319.9	1217.4	1079.1	915.4	741.4	578.6	442.1
117.5°	1372.2	1365.9	1338.8	1291.4	1217.8	1113.7	989.6	848.3	701.3	560.5	443.8
120°	1303.1	1297.4	1274.8	1222.1	1147.8	1052.8	939.9	812.8	680.2	552.2	446.9
122.5°	1238.3	1231.1	1206.4	1159.0	1092.9	1004.7	900.0	785.0	662.9	547.0	452.1
125°	1147.8	1141.2	1117.7	1076.3	1016.1	940.8	850.6	748.0	640.7	540.1	460.1
127.5°	1073.3	1067.2	1046.0	1010.6	957.0	888.5	807.0	715.6	621.1	536.7	469.1
130°	1031.1	1023.6	1003.9	970.0	920.1	856.1	780.0	695.3	610.6	534.4	475.1
132.5°	989.8	984.5	967.0	933.1	886.3	825.3	754.3	676.5	600.8	533.7	479.7
135°	930.5	923.9	906.9	878.7	832.6	779.0	717.8	651.0	588.1	532.5	486.4
137.5°	867.8	863.5	849.2	820.6	781.8	735.4	682.7	627.9	576.9	530.5	490.9
140°	824.2	825.1	810.0	783.7	748.0	707.5	662.3	614.3	570.1	529.7	493.9
142.5°	783.5	784.5	770.9	747.6	717.1	681.9	642.8	601.5	564.1	528.2	496.2
145°	727.3	725.4	717.8	698.0	674.6	647.2	617.2	586.2	556.0	525.9	497.7
147.5°	681.0	680.2	673.1	659.7	641.9	622.5	598.1	573.5	548.1	522.4	497.7
150°	653.8	653.8	648.2	637.9	623.8	605.9	586.2	564.5	542.8	519.3	497.7
152.5°	631.3	631.3	627.9	618.3	607.2	592.4	574.9	556.2	536.9	515.6	495.4
155°	603.0	602.1	600.2	592.8	584.3	573.0	558.8	543.8	527.8	509.0	492.9
157.5°	577.3	577.5	576.0	570.3	563.0	554.1	543.2	530.7	517.6	503.1	489.8
160°	560.7	561.7	561.7	556.0	549.4	542.8	533.5	523.1	510.9	498.6	488.3
162.5°	545.6	546.6	546.6	541.8	537.4	531.6	522.9	514.1	504.1	494.1	485.3
165°	525.9	525.9	526.9	523.1	519.3	514.6	508.0	502.4	494.8	487.4	480.8
167.5°	507.1	507.1	508.0	505.4	503.7	500.3	496.5	492.2	486.1	480.6	476.3
170°	495.8	495.8	496.7	494.8	493.9	492.0	488.3	485.5	480.8	476.1	473.3
172.5°	485.3	486.1	487.8	485.9	485.7	484.6	481.5	479.5	475.5	472.3	471.0
175°	473.3	474.2	475.1	474.2	474.2	474.2	472.3	471.4	469.5	467.6	467.6
177.5°	466.3	466.3	467.8	467.0	467.8	467.8	467.0	466.3	465.5	464.8	465.5
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	467.2	465.9	464.5	462.0	459.9	456.9	456.0	455.0	451.8	449.0	446.9
5°	495.8	490.5	482.9	475.8	470.1	462.4	458.1	453.5	446.9	440.9	436.1
7.5°	525.7	515.3	503.3	490.5	478.4	466.8	457.5	449.1	439.9	431.2	424.3
10°	549.4	534.4	517.7	499.7	484.4	469.5	456.9	446.0	434.1	423.8	415.2
12.5°	576.5	554.3	531.3	509.4	491.3	470.5	455.3	441.4	427.9	415.6	406.0
15°	608.4	580.3	553.1	523.0	495.4	469.5	451.5	433.9	418.3	405.6	393.2
17.5°	637.6	605.8	569.9	533.3	499.9	469.2	444.0	424.1	404.6	389.1	376.8
20°	654.1	617.9	577.3	539.3	502.4	468.2	440.5	416.8	395.7	379.2	365.4
22.5°	668.4	625.9	583.9	543.3	502.2	465.3	433.9	409.5	386.7	370.6	355.9
25°	683.2	632.4	590.2	542.6	496.7	458.5	423.4	395.7	372.9	353.9	338.8
27.5°	695.8	632.0	581.9	530.7	488.0	449.7	412.2	382.5	358.3	337.7	322.3
30°	704.2	632.8	573.3	522.6	479.6	440.1	403.6	373.7	348.3	327.4	312.9
32.5°	709.5	632.3	565.4	511.3	466.2	431.2	394.3	363.4	337.1	316.7	302.7
35°	712.6	628.4	551.8	488.1	444.7	410.6	379.7	347.6	320.2	301.0	285.2
37.5°	706.3	620.3	536.0	465.7	418.1	384.7	358.5	331.3	305.0	284.0	270.3
40°	696.7	615.0	523.7	449.9	399.8	367.6	345.4	318.6	292.7	272.7	260.0
42.5°	678.3	604.4	510.2	432.3	380.9	348.6	328.2	305.8	281.3	262.5	249.8
45°	633.3	581.0	489.8	406.0	352.9	319.5	301.5	285.2	263.1	244.9	233.8
47.5°	570.8	545.9	460.5	378.2	323.6	291.5	272.8	259.8	243.6	228.8	218.3
50°	527.4	517.1	440.7	359.2	304.2	272.7	254.7	242.9	231.2	216.5	206.9
52.5°	477.4	483.7	417.5	339.6	284.3	253.4	236.5	227.1	216.5	204.3	196.0
55°	406.9	429.9	377.5	306.5	254.7	225.3	209.2	201.0	194.7	185.8	178.5
57.5°	340.9	370.2	334.1	272.5	225.6	200.3	184.9	175.9	171.9	167.2	161.5
60°	301.7	330.6	303.2	249.7	206.2	182.0	168.4	160.7	156.7	153.4	148.6
62.5°	266.7	296.1	273.1	226.5	187.0	164.7	152.8	145.2	142.2	140.5	136.4
65°	218.7	243.9	228.6	190.4	159.7	139.9	129.1	123.9	121.0	120.4	117.7
67.5°	178.0	197.2	186.1	157.9	133.7	116.7	107.5	103.0	100.9	100.6	98.6
70°	151.3	169.3	160.7	135.3	114.4	101.0	93.1	89.2	87.8	87.7	86.5
72.5°	130.5	143.1	136.3	115.1	99.0	86.8	81.0	76.8	75.4	75.7	74.9
75°	96.6	106.0	102.1	87.4	74.5	66.5	61.7	59.1	57.8	58.4	57.5
77.5°	69.6	75.5	71.9	61.7	53.7	48.1	44.5	42.9	41.7	41.7	41.3
80°	52.5	56.0	54.0	47.9	41.3	36.5	33.6	32.5	31.9	31.6	31.4
82.5°	37.4	40.3	38.0	33.8	29.3	26.4	24.8	23.4	22.9	23.0	22.8
85°	18.9	20.0	19.1	16.5	14.7	13.4	12.5	11.9	11.4	11.6	11.2
87.5°	10.1	9.7	8.6	7.5	6.8	5.7	5.3	4.6	4.6	5.0	5.4
90°	17.9	15.1	12.3	10.4	8.5	5.7	3.8	1.9	3.8	5.7	8.5
92.5°	119.5	79.0	54.4	40.4	32.5	25.3	17.3	11.7	17.3	25.3	32.5
95°	342.4	202.3	122.3	85.6	61.2	45.1	34.8	32.0	34.8	45.1	61.2
97.5°	375.8	217.7	141.3	101.6	77.5	63.6	55.5	54.6	55.5	63.6	77.5
100°	354.7	215.5	149.6	112.9	90.3	77.2	70.6	69.7	70.6	77.2	90.3
102.5°	336.6	218.5	159.4	125.7	105.4	92.9	87.1	85.4	87.1	92.9	105.4
105°	323.7	226.8	176.0	146.8	128.9	117.6	112.0	109.1	112.0	117.6	128.9
107.5°	322.7	242.1	197.6	170.5	153.7	142.6	137.1	134.3	137.1	142.6	153.7
110°	326.5	255.0	212.6	186.2	170.3	159.9	155.2	152.4	155.2	159.9	170.3



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.0	267.8	228.5	202.8	186.8	176.5	171.8	169.0	171.8	176.5	186.8
115°	346.2	288.8	253.1	227.7	211.7	202.3	196.6	192.8	196.6	202.3	211.7
117.5°	362.4	311.2	275.9	252.3	234.4	225.8	221.1	216.8	221.1	225.8	234.4
120°	374.5	325.6	291.6	268.2	250.2	240.8	236.1	233.3	236.1	240.8	250.2
122.5°	385.8	340.5	307.5	282.5	265.3	255.1	250.4	247.6	250.4	255.1	265.3
125°	403.6	362.2	329.3	303.9	286.0	275.7	270.0	268.2	270.0	275.7	286.0
127.5°	418.3	381.1	349.2	323.9	304.1	293.5	286.5	283.8	286.5	293.5	304.1
130°	428.1	392.3	361.3	335.8	316.1	304.8	296.3	293.5	296.3	304.8	316.1
132.5°	437.2	402.1	371.8	347.1	327.4	313.9	304.6	301.0	304.6	313.9	327.4
135°	448.7	416.8	387.6	362.2	342.4	328.4	318.0	314.2	318.0	328.4	342.4
137.5°	457.4	427.0	398.9	375.4	355.8	340.7	330.6	326.7	330.6	340.7	355.8
140°	461.9	433.8	406.4	383.0	364.1	349.0	339.6	335.0	339.6	349.0	364.1
142.5°	466.5	439.0	412.5	390.4	371.6	358.1	347.9	343.9	347.9	358.1	371.6
145°	471.4	445.9	421.5	399.8	383.9	369.8	361.3	358.4	361.3	369.8	383.9
147.5°	474.4	451.6	429.2	410.8	395.3	383.1	374.8	373.2	374.8	383.1	395.3
150°	475.1	455.3	433.8	416.8	403.6	391.3	383.9	383.0	383.9	391.3	403.6
152.5°	476.6	457.6	439.0	422.8	411.1	400.4	392.9	392.7	392.9	400.4	411.1
155°	477.0	461.9	445.9	432.8	422.4	413.0	407.4	407.4	407.4	413.0	422.4
157.5°	478.0	464.4	451.6	441.4	432.6	424.3	419.8	419.1	419.8	424.3	432.6
160°	478.0	466.7	455.3	445.9	439.3	431.9	428.1	428.1	428.1	431.9	439.3
162.5°	477.2	467.4	457.6	449.7	443.8	437.9	434.9	434.9	434.9	437.9	443.8
165°	475.1	468.5	461.0	454.4	450.6	445.9	444.0	445.0	444.0	445.9	450.6
167.5°	473.6	468.3	462.9	458.7	456.1	452.5	451.6	452.7	451.6	452.5	456.1
170°	471.4	467.6	462.9	461.0	459.1	456.3	455.3	457.2	455.3	456.3	459.1
172.5°	470.6	467.6	463.6	462.5	461.4	459.3	459.1	460.2	459.1	459.3	461.4
175°	468.5	466.7	464.8	463.8	463.8	461.9	462.9	463.8	462.9	461.9	463.8
177.5°	467.0	465.5	464.8	464.8	464.8	464.0	464.8	465.5	464.8	464.0	464.8
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	445.6	444.4	442.7	440.1	437.9	434.6	434.6	435.1	435.1	435.0	434.6
5°	432.2	428.9	424.9	420.3	415.5	410.6	409.7	407.9	406.7	405.8	404.7
7.5°	417.8	412.0	406.2	399.8	393.9	389.1	385.7	382.9	381.1	379.1	377.7
10°	408.2	401.0	394.2	387.4	379.8	373.9	370.2	367.6	365.6	363.8	363.0
12.5°	396.8	388.5	381.0	374.5	366.4	360.2	356.7	355.4	353.2	349.4	347.5
15°	380.1	372.4	363.4	353.5	349.6	342.1	337.9	335.9	334.6	331.8	330.9
17.5°	365.8	355.8	345.6	338.3	330.9	324.9	322.5	320.1	318.4	316.0	315.3
20°	354.4	345.4	336.2	328.3	320.6	314.0	312.0	310.3	308.5	307.5	306.5
22.5°	342.8	333.8	326.1	318.8	310.6	306.2	304.2	302.2	301.0	300.2	299.4
25°	326.5	318.6	310.0	303.5	296.9	294.0	292.7	291.6	290.7	289.6	289.4
27.5°	312.0	303.3	296.4	290.2	285.5	283.1	281.8	281.3	281.5	281.9	282.2
30°	301.0	293.1	287.5	282.2	277.8	275.6	275.3	275.3	276.3	276.4	276.9
32.5°	291.1	284.6	278.8	273.7	270.4	268.9	269.8	269.8	270.4	271.0	271.8
35°	276.4	270.7	266.4	261.9	259.1	259.8	260.2	260.6	261.7	263.1	263.9
37.5°	262.5	257.6	253.0	249.6	248.3	249.4	250.5	251.4	252.7	253.7	254.6
40°	252.5	248.7	244.4	241.3	241.8	242.4	243.3	244.4	245.5	246.2	247.0
42.5°	243.2	239.3	235.9	233.4	234.0	234.9	235.4	235.9	237.2	238.5	238.9
45°	229.0	225.9	222.9	221.3	221.8	222.3	222.6	223.3	224.4	225.3	225.6
47.5°	213.1	210.9	208.9	207.4	208.1	207.9	208.5	209.9	210.2	210.8	212.0
50°	202.9	201.0	198.5	198.0	198.0	198.0	198.3	200.0	200.0	201.0	201.8
52.5°	191.6	190.4	188.9	188.0	187.7	187.7	188.6	189.5	189.8	191.1	192.0
55°	175.0	173.7	172.4	171.7	171.3	171.7	173.4	173.9	175.0	175.7	176.3
57.5°	157.7	156.7	155.6	155.2	155.1	155.7	156.7	158.0	158.3	160.3	161.3
60°	146.3	144.7	143.8	143.8	143.4	145.3	145.0	147.1	147.6	148.9	150.4
62.5°	134.5	132.4	132.1	132.1	132.7	133.3	133.8	134.8	136.0	137.6	138.8
65°	115.5	114.4	115.9	115.7	115.3	116.6	116.6	117.7	119.0	120.6	123.0
67.5°	97.6	97.0	97.1	97.1	97.7	98.5	99.2	100.1	101.7	103.3	104.9
70°	85.4	86.1	85.0	85.9	86.5	86.7	87.2	88.5	90.2	91.3	93.1
72.5°	73.6	73.6	73.7	74.1	74.7	75.1	75.6	77.1	79.0	79.9	81.3
75°	56.6	56.5	57.1	57.1	58.2	58.6	59.1	59.8	61.5	62.8	63.9
77.5°	41.4	41.7	41.5	42.2	41.9	42.0	43.4	44.0	44.2	46.8	47.4
80°	31.2	31.6	31.9	32.0	32.2	31.9	33.4	34.0	34.0	35.5	36.7
82.5°	22.4	22.6	23.2	23.5	23.5	23.9	24.0	24.5	25.1	25.7	27.1
85°	11.2	11.9	12.1	11.9	12.1	11.6	12.3	12.5	12.7	12.7	12.7
87.5°	5.6	6.1	6.5	7.3	7.6	8.4	8.2	8.0	8.2	9.0	8.6
90°	10.4	12.3	15.1	17.9	20.7	23.6	22.6	23.6	24.5	25.4	27.2
92.5°	40.4	54.4	79.0	119.5	159.2	144.7	109.1	79.2	62.9	55.5	50.6
95°	85.6	122.3	202.3	342.4	496.7	557.9	452.5	338.7	229.6	179.7	145.8
97.5°	101.6	141.3	217.7	375.8	633.0	864.6	925.0	844.3	676.3	554.9	442.3
100°	112.9	149.6	215.5	354.7	602.1	891.0	1076.3	1109.3	1033.0	922.9	789.4
102.5°	125.7	159.4	218.5	336.6	556.9	842.1	1083.8	1197.3	1194.9	1130.7	1046.0
105°	146.8	176.0	226.8	323.7	501.4	756.4	1026.4	1223.0	1317.2	1335.0	1310.6
107.5°	170.5	197.6	242.1	322.7	466.1	680.8	926.0	1149.0	1301.7	1384.1	1417.7
110°	186.2	212.6	255.0	326.5	452.5	637.9	862.7	1078.2	1251.3	1369.8	1435.7



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	202.8	228.5	267.8	334.0	445.0	609.3	807.8	1008.1	1185.1	1317.9	1402.6
115°	227.7	253.1	288.8	346.2	442.1	578.6	741.4	915.4	1079.1	1217.4	1319.9
117.5°	252.3	275.9	311.2	362.4	443.8	560.5	701.3	848.3	989.6	1113.7	1217.8
120°	268.2	291.6	325.6	374.5	446.9	552.2	680.2	812.8	939.9	1052.8	1147.8
122.5°	282.5	307.5	340.5	385.8	452.1	547.0	662.9	785.0	900.0	1004.7	1092.9
125°	303.9	329.3	362.2	403.6	460.1	540.1	640.7	748.0	850.6	940.8	1016.1
127.5°	323.9	349.2	381.1	418.3	469.1	536.7	621.1	715.6	807.0	888.5	957.0
130°	335.8	361.3	392.3	428.1	475.1	534.4	610.6	695.3	780.0	856.1	920.1
132.5°	347.1	371.8	402.1	437.2	479.7	533.7	600.8	676.5	754.3	825.3	886.3
135°	362.2	387.6	416.8	448.7	486.4	532.5	588.1	651.0	717.8	779.0	832.6
137.5°	375.4	398.9	427.0	457.4	490.9	530.5	576.9	627.9	682.7	735.4	781.8
140°	383.0	406.4	433.8	461.9	493.9	529.7	570.1	614.3	662.3	707.5	748.0
142.5°	390.4	412.5	439.0	466.5	496.2	528.2	564.1	601.5	642.8	681.9	717.1
145°	399.8	421.5	445.9	471.4	497.7	525.9	556.0	586.2	617.2	647.2	674.6
147.5°	410.8	429.2	451.6	474.4	497.7	522.4	548.1	573.5	598.1	622.5	641.9
150°	416.8	433.8	455.3	475.1	497.7	519.3	542.8	564.5	586.2	605.9	623.8
152.5°	422.8	439.0	457.6	476.6	495.4	515.6	536.9	556.2	574.9	592.4	607.2
155°	432.8	445.9	461.9	477.0	492.9	509.0	527.8	543.8	558.8	573.0	584.3
157.5°	441.4	451.6	464.4	478.0	489.8	503.1	517.6	530.7	543.2	554.1	563.0
160°	445.9	455.3	466.7	478.0	488.3	498.6	510.9	523.1	533.5	542.8	549.4
162.5°	449.7	457.6	467.4	477.2	485.3	494.1	504.1	514.1	522.9	531.6	537.4
165°	454.4	461.0	468.5	475.1	480.8	487.4	494.8	502.4	508.0	514.6	519.3
167.5°	458.7	462.9	468.3	473.6	476.3	480.6	486.1	492.2	496.5	500.3	503.7
170°	461.0	462.9	467.6	471.4	473.3	476.1	480.8	485.5	488.3	492.0	493.9
172.5°	462.5	463.6	467.6	470.6	471.0	472.3	475.5	479.5	481.5	484.6	485.7
175°	463.8	464.8	466.7	468.5	467.6	467.6	469.5	471.4	472.3	474.2	474.2
177.5°	464.8	464.8	465.5	467.0	465.5	464.8	465.5	466.3	467.0	467.8	467.8
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	433.4	433.2	434.4	433.6	434.4	433.2	433.4	434.6	435.0	435.1	435.1
5°	403.4	404.1	401.8	401.8	401.8	404.1	403.4	404.7	405.8	406.7	407.9
7.5°	376.6	375.7	375.8	374.6	375.8	375.7	376.6	377.7	379.1	381.1	382.9
10°	360.3	359.0	358.5	358.8	358.5	359.0	360.3	363.0	363.8	365.6	367.6
12.5°	346.8	346.6	343.7	343.7	343.7	346.6	346.8	347.5	349.4	353.2	355.4
15°	330.9	326.8	326.3	327.6	326.3	326.8	330.9	330.9	331.8	334.6	335.9
17.5°	315.0	312.7	312.9	312.3	312.9	312.7	315.0	315.3	316.0	318.4	320.1
20°	306.5	305.2	305.0	303.5	305.0	305.2	306.5	306.5	307.5	308.5	310.3
22.5°	298.8	298.4	298.5	296.8	298.5	298.4	298.8	299.4	300.2	301.0	302.2
25°	289.2	290.3	289.4	289.4	289.4	290.3	289.2	289.4	289.6	290.7	291.6
27.5°	282.7	282.7	282.2	282.2	282.2	282.7	282.7	282.2	281.9	281.5	281.3
30°	277.8	277.6	278.0	278.0	278.0	277.6	277.8	276.9	276.4	276.3	275.3
32.5°	272.9	273.1	273.2	273.4	273.2	273.1	272.9	271.8	271.0	270.4	269.8
35°	265.2	265.5	266.2	265.7	266.2	265.5	265.2	263.9	263.1	261.7	260.6
37.5°	255.0	256.0	255.8	256.1	255.8	256.0	255.0	254.6	253.7	252.7	251.4
40°	247.2	247.9	247.7	247.7	247.7	247.9	247.2	247.0	246.2	245.5	244.4
42.5°	239.3	239.8	239.2	238.9	239.2	239.8	239.3	238.9	238.5	237.2	235.9
45°	226.4	225.9	226.6	225.7	226.6	225.9	226.4	225.6	225.3	224.4	223.3
47.5°	211.9	212.4	212.5	213.2	212.5	212.4	211.9	212.0	210.8	210.2	209.9
50°	202.3	203.6	203.6	203.3	203.6	203.6	202.3	201.8	201.0	200.0	200.0
52.5°	192.7	193.3	194.3	194.2	194.3	193.3	192.7	192.0	191.1	189.8	189.5
55°	178.0	178.5	179.0	179.2	179.0	178.5	178.0	176.3	175.7	175.0	173.9
57.5°	162.9	162.7	163.7	164.1	163.7	162.7	162.9	161.3	160.3	158.3	158.0
60°	152.1	152.1	153.9	154.6	153.9	152.1	152.1	150.4	148.9	147.6	147.1
62.5°	140.7	141.5	143.2	142.3	143.2	141.5	140.7	138.8	137.6	136.0	134.8
65°	124.0	125.8	125.6	126.5	125.6	125.8	124.0	123.0	120.6	119.0	117.7
67.5°	106.6	107.7	109.3	109.4	109.3	107.7	106.6	104.9	103.3	101.7	100.1
70°	94.8	96.0	96.8	97.5	96.8	96.0	94.8	93.1	91.3	90.2	88.5
72.5°	83.4	84.0	86.1	85.2	86.1	84.0	83.4	81.3	79.9	79.0	77.1
75°	65.4	67.0	68.3	67.7	68.3	67.0	65.4	63.9	62.8	61.5	59.8
77.5°	48.4	50.0	50.5	50.0	50.5	50.0	48.4	47.4	46.8	44.2	44.0
80°	38.2	38.0	39.3	39.1	39.3	38.0	38.2	36.7	35.5	34.0	34.0
82.5°	28.0	27.8	28.4	28.6	28.4	27.8	28.0	27.1	25.7	25.1	24.5
85°	13.6	14.2	13.4	13.2	13.4	14.2	13.6	12.7	12.7	12.7	12.5
87.5°	8.4	8.6	8.7	8.3	8.7	8.6	8.4	8.6	9.0	8.2	8.0
90°	26.3	27.2	28.2	27.2	28.2	27.2	26.3	27.2	25.4	24.5	23.6
92.5°	48.9	46.1	47.0	45.3	47.0	46.1	48.9	50.6	55.5	62.9	79.2
95°	128.0	119.5	112.9	109.1	112.9	119.5	128.0	145.8	179.7	229.6	338.7
97.5°	373.0	330.6	305.2	297.1	305.2	330.6	373.0	442.3	554.9	676.3	844.3
100°	694.4	625.7	589.0	589.9	589.0	625.7	694.4	789.4	922.9	1033.0	1109.3
102.5°	972.0	917.7	887.0	865.3	887.0	917.7	972.0	1046.0	1130.7	1194.9	1197.3
105°	1267.2	1231.5	1201.5	1196.7	1201.5	1231.5	1267.2	1310.6	1335.0	1317.2	1223.0
107.5°	1418.4	1406.4	1396.2	1387.5	1396.2	1406.4	1418.4	1417.7	1384.1	1301.7	1149.0
110°	1462.1	1469.6	1467.7	1465.8	1467.7	1469.6	1462.1	1435.7	1369.8	1251.3	1078.2



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1450.8	1474.0	1481.2	1481.6	1481.2	1474.0	1450.8	1402.6	1317.9	1185.1	1008.1
115°	1390.5	1431.9	1450.8	1455.5	1450.8	1431.9	1390.5	1319.9	1217.4	1079.1	915.4
117.5°	1291.4	1338.8	1365.9	1372.2	1365.9	1338.8	1291.4	1217.8	1113.7	989.6	848.3
120°	1222.1	1274.8	1297.4	1303.1	1297.4	1274.8	1222.1	1147.8	1052.8	939.9	812.8
122.5°	1159.0	1206.4	1231.1	1238.3	1231.1	1206.4	1159.0	1092.9	1004.7	900.0	785.0
125°	1076.3	1117.7	1141.2	1147.8	1141.2	1117.7	1076.3	1016.1	940.8	850.6	748.0
127.5°	1010.6	1046.0	1067.2	1073.3	1067.2	1046.0	1010.6	957.0	888.5	807.0	715.6
130°	970.0	1003.9	1023.6	1031.1	1023.6	1003.9	970.0	920.1	856.1	780.0	695.3
132.5°	933.1	967.0	984.5	989.8	984.5	967.0	933.1	886.3	825.3	754.3	676.5
135°	878.7	906.9	923.9	930.5	923.9	906.9	878.7	832.6	779.0	717.8	651.0
137.5°	820.6	849.2	863.5	867.8	863.5	849.2	820.6	781.8	735.4	682.7	627.9
140°	783.7	810.0	825.1	824.2	825.1	810.0	783.7	748.0	707.5	662.3	614.3
142.5°	747.6	770.9	784.5	783.5	784.5	770.9	747.6	717.1	681.9	642.8	601.5
145°	698.0	717.8	725.4	727.3	725.4	717.8	698.0	674.6	647.2	617.2	586.2
147.5°	659.7	673.1	680.2	681.0	680.2	673.1	659.7	641.9	622.5	598.1	573.5
150°	637.9	648.2	653.8	653.8	653.8	648.2	637.9	623.8	605.9	586.2	564.5
152.5°	618.3	627.9	631.3	631.3	631.3	627.9	618.3	607.2	592.4	574.9	556.2
155°	592.8	600.2	602.1	603.0	602.1	600.2	592.8	584.3	573.0	558.8	543.8
157.5°	570.3	576.0	577.5	577.3	577.5	576.0	570.3	563.0	554.1	543.2	530.7
160°	556.0	561.7	561.7	560.7	561.7	561.7	556.0	549.4	542.8	533.5	523.1
162.5°	541.8	546.6	546.6	545.6	546.6	546.6	541.8	537.4	531.6	522.9	514.1
165°	523.1	526.9	525.9	525.9	525.9	526.9	523.1	519.3	514.6	508.0	502.4
167.5°	505.4	508.0	507.1	507.1	507.1	508.0	505.4	503.7	500.3	496.5	492.2
170°	494.8	496.7	495.8	495.8	495.8	496.7	494.8	493.9	492.0	488.3	485.5
172.5°	485.9	487.8	486.1	485.3	486.1	487.8	485.9	485.7	484.6	481.5	479.5
175°	474.2	475.1	474.2	473.3	474.2	475.1	474.2	474.2	474.2	472.3	471.4
177.5°	467.0	467.8	466.3	466.3	466.3	467.8	467.0	467.8	467.8	467.0	466.3
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	434.6	434.6	437.9	440.1	442.7	444.4	445.6	446.9	449.0	451.8	455.0
5°	409.7	410.6	415.5	420.3	424.9	428.9	432.2	436.1	440.9	446.9	453.5
7.5°	385.7	389.1	393.9	399.8	406.2	412.0	417.8	424.3	431.2	439.9	449.1
10°	370.2	373.9	379.8	387.4	394.2	401.0	408.2	415.2	423.8	434.1	446.0
12.5°	356.7	360.2	366.4	374.5	381.0	388.5	396.8	406.0	415.6	427.9	441.4
15°	337.9	342.1	349.6	353.5	363.4	372.4	380.1	393.2	405.6	418.3	433.9
17.5°	322.5	324.9	330.9	338.3	345.6	355.8	365.8	376.8	389.1	404.6	424.1
20°	312.0	314.0	320.6	328.3	336.2	345.4	354.4	365.4	379.2	395.7	416.8
22.5°	304.2	306.2	310.6	318.8	326.1	333.8	342.8	355.9	370.6	386.7	409.5
25°	292.7	294.0	296.9	303.5	310.0	318.6	326.5	338.8	353.9	372.9	395.7
27.5°	281.8	283.1	285.5	290.2	296.4	303.3	312.0	322.3	337.7	358.3	382.5
30°	275.3	275.6	277.8	282.2	287.5	293.1	301.0	312.9	327.4	348.3	373.7
32.5°	269.8	268.9	270.4	273.7	278.8	284.6	291.1	302.7	316.7	337.1	363.4
35°	260.2	259.8	259.1	261.9	266.4	270.7	276.4	285.2	301.0	320.2	347.6
37.5°	250.5	249.4	248.3	249.6	253.0	257.6	262.5	270.3	284.0	305.0	331.3
40°	243.3	242.4	241.8	241.3	244.4	248.7	252.5	260.0	272.7	292.7	318.6
42.5°	235.4	234.9	234.0	233.4	235.9	239.3	243.2	249.8	262.5	281.3	305.8
45°	222.6	222.3	221.8	221.3	222.9	225.9	229.0	233.8	244.9	263.1	285.2
47.5°	208.5	207.9	208.1	207.4	208.9	210.9	213.1	218.3	228.8	243.6	259.8
50°	198.3	198.0	198.0	198.0	198.5	201.0	202.9	206.9	216.5	231.2	242.9
52.5°	188.6	187.7	187.7	188.0	188.9	190.4	191.6	196.0	204.3	216.5	227.1
55°	173.4	171.7	171.3	171.7	172.4	173.7	175.0	178.5	185.8	194.7	201.0
57.5°	156.7	155.7	155.1	155.2	155.6	156.7	157.7	161.5	167.2	171.9	175.9
60°	145.0	145.3	143.4	143.8	143.8	144.7	146.3	148.6	153.4	156.7	160.7
62.5°	133.8	133.3	132.7	132.1	132.1	132.4	134.5	136.4	140.5	142.2	145.2
65°	116.6	116.6	115.3	115.7	115.9	114.4	115.5	117.7	120.4	121.0	123.9
67.5°	99.2	98.5	97.7	97.1	97.1	97.0	97.6	98.6	100.6	100.9	103.0
70°	87.2	86.7	86.5	85.9	85.0	86.1	85.4	86.5	87.7	87.8	89.2
72.5°	75.6	75.1	74.7	74.1	73.7	73.6	73.6	74.9	75.7	75.4	76.8
75°	59.1	58.6	58.2	57.1	57.1	56.5	56.6	57.5	58.4	57.8	59.1
77.5°	43.4	42.0	41.9	42.2	41.5	41.7	41.4	41.3	41.7	41.7	42.9
80°	33.4	31.9	32.2	32.0	31.9	31.6	31.2	31.4	31.6	31.9	32.5
82.5°	24.0	23.9	23.5	23.5	23.2	22.6	22.4	22.8	23.0	22.9	23.4
85°	12.3	11.6	12.1	11.9	12.1	11.9	11.2	11.2	11.6	11.4	11.9
87.5°	8.2	8.4	7.6	7.3	6.5	6.1	5.6	5.4	5.0	4.6	4.6
90°	22.6	23.6	20.7	17.9	15.1	12.3	10.4	8.5	5.7	3.8	1.9
92.5°	109.1	144.7	159.2	119.5	79.0	54.4	40.4	32.5	25.3	17.3	11.7
95°	452.5	557.9	496.7	342.4	202.3	122.3	85.6	61.2	45.1	34.8	32.0
97.5°	925.0	864.6	633.0	375.8	217.7	141.3	101.6	77.5	63.6	55.5	54.6
100°	1076.3	891.0	602.1	354.7	215.5	149.6	112.9	90.3	77.2	70.6	69.7
102.5°	1083.8	842.1	556.9	336.6	218.5	159.4	125.7	105.4	92.9	87.1	85.4
105°	1026.4	756.4	501.4	323.7	226.8	176.0	146.8	128.9	117.6	112.0	109.1
107.5°	926.0	680.8	466.1	322.7	242.1	197.6	170.5	153.7	142.6	137.1	134.3
110°	862.7	637.9	452.5	326.5	255.0	212.6	186.2	170.3	159.9	155.2	152.4



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	807.8	609.3	445.0	334.0	267.8	228.5	202.8	186.8	176.5	171.8	169.0
115°	741.4	578.6	442.1	346.2	288.8	253.1	227.7	211.7	202.3	196.6	192.8
117.5°	701.3	560.5	443.8	362.4	311.2	275.9	252.3	234.4	225.8	221.1	216.8
120°	680.2	552.2	446.9	374.5	325.6	291.6	268.2	250.2	240.8	236.1	233.3
122.5°	662.9	547.0	452.1	385.8	340.5	307.5	282.5	265.3	255.1	250.4	247.6
125°	640.7	540.1	460.1	403.6	362.2	329.3	303.9	286.0	275.7	270.0	268.2
127.5°	621.1	536.7	469.1	418.3	381.1	349.2	323.9	304.1	293.5	286.5	283.8
130°	610.6	534.4	475.1	428.1	392.3	361.3	335.8	316.1	304.8	296.3	293.5
132.5°	600.8	533.7	479.7	437.2	402.1	371.8	347.1	327.4	313.9	304.6	301.0
135°	588.1	532.5	486.4	448.7	416.8	387.6	362.2	342.4	328.4	318.0	314.2
137.5°	576.9	530.5	490.9	457.4	427.0	398.9	375.4	355.8	340.7	330.6	326.7
140°	570.1	529.7	493.9	461.9	433.8	406.4	383.0	364.1	349.0	339.6	335.0
142.5°	564.1	528.2	496.2	466.5	439.0	412.5	390.4	371.6	358.1	347.9	343.9
145°	556.0	525.9	497.7	471.4	445.9	421.5	399.8	383.9	369.8	361.3	358.4
147.5°	548.1	522.4	497.7	474.4	451.6	429.2	410.8	395.3	383.1	374.8	373.2
150°	542.8	519.3	497.7	475.1	455.3	433.8	416.8	403.6	391.3	383.9	383.0
152.5°	536.9	515.6	495.4	476.6	457.6	439.0	422.8	411.1	400.4	392.9	392.7
155°	527.8	509.0	492.9	477.0	461.9	445.9	432.8	422.4	413.0	407.4	407.4
157.5°	517.6	503.1	489.8	478.0	464.4	451.6	441.4	432.6	424.3	419.8	419.1
160°	510.9	498.6	488.3	478.0	466.7	455.3	445.9	439.3	431.9	428.1	428.1
162.5°	504.1	494.1	485.3	477.2	467.4	457.6	449.7	443.8	437.9	434.9	434.9
165°	494.8	487.4	480.8	475.1	468.5	461.0	454.4	450.6	445.9	444.0	445.0
167.5°	486.1	480.6	476.3	473.6	468.3	462.9	458.7	456.1	452.5	451.6	452.7
170°	480.8	476.1	473.3	471.4	467.6	462.9	461.0	459.1	456.3	455.3	457.2
172.5°	475.5	472.3	471.0	470.6	467.6	463.6	462.5	461.4	459.3	459.1	460.2
175°	469.5	467.6	467.6	468.5	466.7	464.8	463.8	463.8	461.9	462.9	463.8
177.5°	465.5	464.8	465.5	467.0	465.5	464.8	464.8	464.8	464.0	464.8	465.5
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	456.0	456.9	459.9	462.0	464.5	465.9	467.2	468.3	469.8	470.0	475.1
5°	458.1	462.4	470.1	475.8	482.9	490.5	495.8	498.2	504.6	509.8	520.4
7.5°	457.5	466.8	478.4	490.5	503.3	515.3	525.7	538.0	546.7	559.9	572.8
10°	456.9	469.5	484.4	499.7	517.7	534.4	549.4	566.1	579.9	598.1	613.7
12.5°	455.3	470.5	491.3	509.4	531.3	554.3	576.5	597.9	610.1	640.5	654.8
15°	451.5	469.5	495.4	523.0	553.1	580.3	608.4	630.8	667.0	693.6	710.6
17.5°	444.0	469.2	499.9	533.3	569.9	605.8	637.6	671.6	710.0	742.2	776.5
20°	440.5	468.2	502.4	539.3	577.3	617.9	654.1	694.9	736.9	768.5	812.5
22.5°	433.9	465.3	502.2	543.3	583.9	625.9	668.4	709.5	758.0	801.5	843.4
25°	423.4	458.5	496.7	542.6	590.2	632.4	683.2	737.8	788.2	844.3	886.0
27.5°	412.2	449.7	488.0	530.7	581.9	632.0	695.8	757.5	819.3	867.6	898.5
30°	403.6	440.1	479.6	522.6	573.3	632.8	704.2	771.6	831.8	873.3	890.6
32.5°	394.3	431.2	466.2	511.3	565.4	632.3	709.5	779.9	832.5	860.1	856.7
35°	379.7	410.6	444.7	488.1	551.8	628.4	712.6	780.6	812.8	806.9	762.1
37.5°	358.5	384.7	418.1	465.7	536.0	620.3	706.3	757.4	755.4	707.1	642.2
40°	345.4	367.6	399.8	449.9	523.7	615.0	696.7	729.9	701.8	634.3	556.7
42.5°	328.2	348.6	380.9	432.3	510.2	604.4	678.3	687.9	632.9	555.3	484.1
45°	301.5	319.5	352.9	406.0	489.8	581.0	633.3	609.7	535.7	455.6	401.4
47.5°	272.8	291.5	323.6	378.2	460.5	545.9	570.8	520.8	444.9	379.8	330.1
50°	254.7	272.7	304.2	359.2	440.7	517.1	527.4	462.9	393.0	335.9	295.1
52.5°	236.5	253.4	284.3	339.6	417.5	483.7	477.4	411.6	347.4	298.7	266.6
55°	209.2	225.3	254.7	306.5	377.5	429.9	406.9	344.1	291.0	253.2	228.8
57.5°	184.9	200.3	225.6	272.5	334.1	370.2	340.9	287.9	245.7	216.6	198.5
60°	168.4	182.0	206.2	249.7	303.2	330.6	301.7	255.0	219.3	196.0	179.8
62.5°	152.8	164.7	187.0	226.5	273.1	296.1	266.7	227.2	196.9	176.3	162.4
65°	129.1	139.9	159.7	190.4	228.6	243.9	218.7	186.6	163.2	147.8	138.6
67.5°	107.5	116.7	133.7	157.9	186.1	197.2	178.0	153.2	135.4	123.1	115.8
70°	93.1	101.0	114.4	135.3	160.7	169.3	151.3	130.8	117.9	108.0	101.2
72.5°	81.0	86.8	99.0	115.1	136.3	143.1	130.5	112.6	100.6	93.1	87.7
75°	61.7	66.5	74.5	87.4	102.1	106.0	96.6	85.4	77.3	72.0	67.9
77.5°	44.5	48.1	53.7	61.7	71.9	75.5	69.6	62.0	56.1	52.6	50.2
80°	33.6	36.5	41.3	47.9	54.0	56.0	52.5	46.8	42.6	40.6	38.6
82.5°	24.8	26.4	29.3	33.8	38.0	40.3	37.4	33.9	31.7	29.9	29.1
85°	12.5	13.4	14.7	16.5	19.1	20.0	18.9	18.0	16.7	15.6	15.6
87.5°	5.3	5.7	6.8	7.5	8.6	9.7	10.1	10.3	10.7	10.3	10.4
90°	3.8	5.7	8.5	10.4	12.3	15.1	17.9	20.7	23.6	22.6	23.6
92.5°	17.3	25.3	32.5	40.4	54.4	79.0	119.5	159.2	144.7	109.1	79.2
95°	34.8	45.1	61.2	85.6	122.3	202.3	342.4	496.7	557.9	452.5	338.7
97.5°	55.5	63.6	77.5	101.6	141.3	217.7	375.8	633.0	864.6	925.0	844.3
100°	70.6	77.2	90.3	112.9	149.6	215.5	354.7	602.1	891.0	1076.3	1109.3
102.5°	87.1	92.9	105.4	125.7	159.4	218.5	336.6	556.9	842.1	1083.8	1197.3
105°	112.0	117.6	128.9	146.8	176.0	226.8	323.7	501.4	756.4	1026.4	1223.0
107.5°	137.1	142.6	153.7	170.5	197.6	242.1	322.7	466.1	680.8	926.0	1149.0
110°	155.2	159.9	170.3	186.2	212.6	255.0	326.5	452.5	637.9	862.7	1078.2



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	171.8	176.5	186.8	202.8	228.5	267.8	334.0	445.0	609.3	807.8	1008.1
115°	196.6	202.3	211.7	227.7	253.1	288.8	346.2	442.1	578.6	741.4	915.4
117.5°	221.1	225.8	234.4	252.3	275.9	311.2	362.4	443.8	560.5	701.3	848.3
120°	236.1	240.8	250.2	268.2	291.6	325.6	374.5	446.9	552.2	680.2	812.8
122.5°	250.4	255.1	265.3	282.5	307.5	340.5	385.8	452.1	547.0	662.9	785.0
125°	270.0	275.7	286.0	303.9	329.3	362.2	403.6	460.1	540.1	640.7	748.0
127.5°	286.5	293.5	304.1	323.9	349.2	381.1	418.3	469.1	536.7	621.1	715.6
130°	296.3	304.8	316.1	335.8	361.3	392.3	428.1	475.1	534.4	610.6	695.3
132.5°	304.6	313.9	327.4	347.1	371.8	402.1	437.2	479.7	533.7	600.8	676.5
135°	318.0	328.4	342.4	362.2	387.6	416.8	448.7	486.4	532.5	588.1	651.0
137.5°	330.6	340.7	355.8	375.4	398.9	427.0	457.4	490.9	530.5	576.9	627.9
140°	339.6	349.0	364.1	383.0	406.4	433.8	461.9	493.9	529.7	570.1	614.3
142.5°	347.9	358.1	371.6	390.4	412.5	439.0	466.5	496.2	528.2	564.1	601.5
145°	361.3	369.8	383.9	399.8	421.5	445.9	471.4	497.7	525.9	556.0	586.2
147.5°	374.8	383.1	395.3	410.8	429.2	451.6	474.4	497.7	522.4	548.1	573.5
150°	383.9	391.3	403.6	416.8	433.8	455.3	475.1	497.7	519.3	542.8	564.5
152.5°	392.9	400.4	411.1	422.8	439.0	457.6	476.6	495.4	515.6	536.9	556.2
155°	407.4	413.0	422.4	432.8	445.9	461.9	477.0	492.9	509.0	527.8	543.8
157.5°	419.8	424.3	432.6	441.4	451.6	464.4	478.0	489.8	503.1	517.6	530.7
160°	428.1	431.9	439.3	445.9	455.3	466.7	478.0	488.3	498.6	510.9	523.1
162.5°	434.9	437.9	443.8	449.7	457.6	467.4	477.2	485.3	494.1	504.1	514.1
165°	444.0	445.9	450.6	454.4	461.0	468.5	475.1	480.8	487.4	494.8	502.4
167.5°	451.6	452.5	456.1	458.7	462.9	468.3	473.6	476.3	480.6	486.1	492.2
170°	455.3	456.3	459.1	461.0	462.9	467.6	471.4	473.3	476.1	480.8	485.5
172.5°	459.1	459.3	461.4	462.5	463.6	467.6	470.6	471.0	472.3	475.5	479.5
175°	462.9	461.9	463.8	463.8	464.8	466.7	468.5	467.6	467.6	469.5	471.4
177.5°	464.8	464.0	464.8	464.8	464.8	465.5	467.0	465.5	464.8	465.5	466.3
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	476.9	477.1	479.0	480.4	479.8	480.6	481.0
5°	521.0	529.0	533.1	536.2	536.4	536.7	538.4
7.5°	583.6	592.1	598.3	607.8	610.5	613.7	612.8
10°	629.3	641.9	652.6	658.3	664.5	673.4	666.2
12.5°	672.0	694.2	710.6	719.4	725.2	727.0	723.5
15°	742.4	771.4	786.9	786.6	806.3	814.8	801.4
17.5°	806.9	833.7	855.2	866.1	882.6	886.2	884.6
20°	846.5	875.7	892.4	911.3	919.8	927.5	928.8
22.5°	880.5	906.8	924.7	940.4	947.5	951.2	953.4
25°	915.7	936.3	947.1	952.5	954.5	954.0	951.2
27.5°	913.2	914.8	903.0	891.4	880.9	869.2	865.2
30°	889.5	871.1	838.1	819.4	792.0	770.2	779.1
32.5°	827.2	790.4	753.5	712.7	678.9	669.3	659.6
35°	706.0	641.4	603.6	559.7	542.2	524.6	512.5
37.5°	571.1	521.2	476.4	447.7	430.1	419.0	413.0
40°	493.8	448.8	411.9	388.6	375.2	362.8	361.0
42.5°	432.2	390.3	362.6	344.0	331.2	325.8	322.0
45°	353.9	324.8	306.1	292.9	284.4	281.1	276.6
47.5°	299.6	279.0	264.9	256.0	249.5	247.0	246.8
50°	269.2	252.0	241.8	234.7	229.7	228.8	225.3
52.5°	246.4	231.5	223.5	217.4	213.7	211.2	210.2
55°	213.9	204.0	196.7	193.2	190.4	187.9	187.9
57.5°	187.1	178.9	174.1	171.1	170.2	168.5	167.4
60°	170.6	163.6	159.9	157.2	155.4	155.7	153.7
62.5°	154.5	149.9	146.3	143.7	141.6	141.7	141.8
65°	131.5	128.0	125.4	124.5	123.2	121.7	122.1
67.5°	111.5	108.2	106.1	104.6	104.2	103.3	104.6
70°	97.1	94.6	93.1	91.8	91.3	91.5	92.7
72.5°	83.9	82.2	81.2	80.6	79.6	79.6	80.4
75°	65.9	64.6	63.7	63.1	62.8	62.8	62.8
77.5°	48.4	48.1	47.7	46.8	46.8	47.0	47.0
80°	38.2	37.5	37.3	36.9	36.2	35.8	36.9
82.5°	28.6	27.9	27.7	27.6	26.6	26.5	27.4
85°	15.4	14.7	14.9	14.7	14.7	14.5	14.5
87.5°	10.4	10.4	10.6	10.6	10.6	10.6	10.7
90°	24.5	25.4	27.2	26.3	27.2	28.2	27.2
92.5°	62.9	55.5	50.6	48.9	46.1	47.0	45.3
95°	229.6	179.7	145.8	128.0	119.5	112.9	109.1
97.5°	676.3	554.9	442.3	373.0	330.6	305.2	297.1
100°	1033.0	922.9	789.4	694.4	625.7	589.0	589.9
102.5°	1194.9	1130.7	1046.0	972.0	917.7	887.0	865.3
105°	1317.2	1335.0	1310.6	1267.2	1231.5	1201.5	1196.7
107.5°	1301.7	1384.1	1417.7	1418.4	1406.4	1396.2	1387.5
110°	1251.3	1369.8	1435.7	1462.1	1469.6	1467.7	1465.8



TEST NUMBER: P331894-830

CATALOG NUMBER: S123DIP-S340D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	<i>1185.1</i>	<i>1317.9</i>	<i>1402.6</i>	<i>1450.8</i>	<i>1474.0</i>	<i>1481.2</i>	<i>1481.6</i>
115°	1079.1	1217.4	1319.9	1390.5	1431.9	1450.8	1455.5
117.5°	989.6	1113.7	1217.8	1291.4	1338.8	1365.9	1372.2
120°	939.9	1052.8	1147.8	1222.1	1274.8	1297.4	1303.1
122.5°	900.0	1004.7	1092.9	1159.0	1206.4	1231.1	1238.3
125°	850.6	940.8	1016.1	1076.3	1117.7	1141.2	1147.8
127.5°	807.0	888.5	957.0	1010.6	1046.0	1067.2	1073.3
130°	780.0	856.1	920.1	970.0	1003.9	1023.6	1031.1
132.5°	754.3	825.3	886.3	933.1	967.0	984.5	989.8
135°	717.8	779.0	832.6	878.7	906.9	923.9	930.5
137.5°	682.7	735.4	781.8	820.6	849.2	863.5	867.8
140°	662.3	707.5	748.0	783.7	810.0	825.1	824.2
142.5°	642.8	681.9	717.1	747.6	770.9	784.5	783.5
145°	617.2	647.2	674.6	698.0	717.8	725.4	727.3
147.5°	598.1	622.5	641.9	659.7	673.1	680.2	681.0
150°	586.2	605.9	623.8	637.9	648.2	653.8	653.8
152.5°	574.9	592.4	607.2	618.3	627.9	631.3	631.3
155°	558.8	573.0	584.3	592.8	600.2	602.1	603.0
157.5°	543.2	554.1	563.0	570.3	576.0	577.5	577.3
160°	533.5	542.8	549.4	556.0	561.7	561.7	560.7
162.5°	522.9	531.6	537.4	541.8	546.6	546.6	545.6
165°	508.0	514.6	519.3	523.1	526.9	525.9	525.9
167.5°	496.5	500.3	503.7	505.4	508.0	507.1	507.1
170°	488.3	492.0	493.9	494.8	496.7	495.8	495.8
172.5°	481.5	484.6	485.7	485.9	487.8	486.1	485.3
175°	472.3	474.2	474.2	474.2	475.1	474.2	473.3
177.5°	467.0	467.8	467.8	467.0	467.8	466.3	466.3
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8

(END OF REPORT)