

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331885-830

Luminaire Tested: **S123DIP-S340D805U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331885-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D805U830-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4109.5 lumens
Efficiency: N/A
Efficacy: 131.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	36	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	16
6	61	49	41	36	54	44	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4878	4878	4878	4878
5°	5817	4900	4341	4900
10°	7282	4875	3922	4875
15°	8931	4835	3651	4835
20°	10639	4774	3477	4774
25°	11297	4700	3437	4700
30°	9684	4645	3455	4645
35°	6734	4568	3491	4568
40°	5073	4477	3481	4477
45°	4211	4341	3436	4341
50°	3773	4068	3404	4068
55°	3526	3772	3363	3772
60°	3309	3460	3328	3460
65°	3110	3156	3222	3156
70°	2917	2807	3068	2807
75°	2612	2458	2816	2458
80°	2287	2015	2424	2015
85°	1791	1470	1630	1470



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.6	1.1
10°-20°	143.2	3.5
20°-30°	240.3	5.8
30°-40°	272.0	6.6
40°-50°	244.0	5.9
50°-60°	196.9	4.8
60°-70°	137.2	3.3
70°-80°	72.1	1.8
80°-90°	20.4	0.5
90°-100°	202.6	4.9
100°-110°	573.6	14.0
110°-120°	564.3	13.7
120°-130°	450.1	11.0
130°-140°	354.9	8.6
140°-150°	264.9	6.4
150°-160°	184.6	4.5
160°-170°	108.5	2.6
170°-180°	35.3	0.9
0°-30°	428.1	10.4
0°-40°	700.1	17.0
0°-60°	1140.9	27.8
0°-90°	1370.7	33.4
90°-120°	1340.5	32.6
90°-150°	2410.4	58.7
90°-180°	2739.0	66.7
0°-180°	4109.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	453	453	453	453	453	
5°	538	454	402	454	538	56
15°	801	434	328	434	801	231
25°	951	396	289	396	951	417
35°	512	348	266	348	512	333
45°	277	285	226	285	277	219
55°	188	201	179	201	188	169
65°	122	124	126	124	122	122
75°	63	59	68	59	63	67
85°	14	12	13	12	14	18
90°	21	2	21	2	21	12
95°	86	25	86	25	86	154
105°	937	86	937	86	937	925
115°	1140	151	1140	151	1140	1108
125°	899	210	899	210	899	815
135°	729	246	729	246	729	565
145°	570	281	570	281	570	362
155°	472	319	472	319	472	220
165°	412	349	412	349	412	118
175°	371	363	371	363	371	36
180°	364	364	364	364	364	



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	481.0	480.6	479.8	480.4	479.0	477.1	476.9	475.1	470.0	469.8	468.3
5°	538.4	536.7	536.4	536.2	533.1	529.0	521.0	520.4	509.8	504.6	498.2
7.5°	612.8	613.7	610.5	607.8	598.3	592.1	583.6	572.8	559.9	546.7	538.0
10°	666.2	673.4	664.5	658.3	652.6	641.9	629.3	613.7	598.1	579.9	566.1
12.5°	723.5	727.0	725.2	719.4	710.6	694.2	672.0	654.8	640.5	610.1	597.9
15°	801.4	814.8	806.3	786.6	786.9	771.4	742.4	710.6	693.6	667.0	630.8
17.5°	884.6	886.2	882.6	866.1	855.2	833.7	806.9	776.5	742.2	710.0	671.6
20°	928.8	927.5	919.8	911.3	892.4	875.7	846.5	812.5	768.5	736.9	694.9
22.5°	953.4	951.2	947.5	940.4	924.7	906.8	880.5	843.4	801.5	758.0	709.5
25°	951.2	954.0	954.5	952.5	947.1	936.3	915.7	886.0	844.3	788.2	737.8
27.5°	865.2	869.2	880.9	891.4	903.0	914.8	913.2	898.5	867.6	819.3	757.5
30°	779.1	770.2	792.0	819.4	838.1	871.1	889.5	890.6	873.3	831.8	771.6
32.5°	659.6	669.3	678.9	712.7	753.5	790.4	827.2	856.7	860.1	832.5	779.9
35°	512.5	524.6	542.2	559.7	603.6	641.4	706.0	762.1	806.9	812.8	780.6
37.5°	413.0	419.0	430.1	447.7	476.4	521.2	571.1	642.2	707.1	755.4	757.4
40°	361.0	362.8	375.2	388.6	411.9	448.8	493.8	556.7	634.3	701.8	729.9
42.5°	322.0	325.8	331.2	344.0	362.6	390.3	432.2	484.1	555.3	632.9	687.9
45°	276.6	281.1	284.4	292.9	306.1	324.8	353.9	401.4	455.6	535.7	609.7
47.5°	246.8	247.0	249.5	256.0	264.9	279.0	299.6	330.1	379.8	444.9	520.8
50°	225.3	228.8	229.7	234.7	241.8	252.0	269.2	295.1	335.9	393.0	462.9
52.5°	210.2	211.2	213.7	217.4	223.5	231.5	246.4	266.6	298.7	347.4	411.6
55°	187.9	187.9	190.4	193.2	196.7	204.0	213.9	228.8	253.2	291.0	344.1
57.5°	167.4	168.5	170.2	171.1	174.1	178.9	187.1	198.5	216.6	245.7	287.9
60°	153.7	155.7	155.4	157.2	159.9	163.6	170.6	179.8	196.0	219.3	255.0
62.5°	141.8	141.7	141.6	143.7	146.3	149.9	154.5	162.4	176.3	196.9	227.2
65°	122.1	121.7	123.2	124.5	125.4	128.0	131.5	138.6	147.8	163.2	186.6
67.5°	104.6	103.3	104.2	104.6	106.1	108.2	111.5	115.8	123.1	135.4	153.2
70°	92.7	91.5	91.3	91.8	93.1	94.6	97.1	101.2	108.0	117.9	130.8
72.5°	80.4	79.6	79.6	80.6	81.2	82.2	83.9	87.7	93.1	100.6	112.6
75°	62.8	62.8	62.8	63.1	63.7	64.6	65.9	67.9	72.0	77.3	85.4
77.5°	47.0	47.0	46.8	46.8	47.7	48.1	48.4	50.2	52.6	56.1	62.0
80°	36.9	35.8	36.2	36.9	37.3	37.5	38.2	38.6	40.6	42.6	46.8
82.5°	27.4	26.5	26.6	27.6	27.7	27.9	28.6	29.1	29.9	31.7	33.9
85°	14.5	14.5	14.7	14.7	14.9	14.7	15.4	15.6	15.6	16.7	18.0
87.5°	9.5	9.3	9.3	9.4	9.3	9.2	9.2	9.3	9.3	9.6	9.4
90°	21.4	22.1	21.4	20.6	21.4	19.9	19.1	18.4	17.7	18.4	16.2
92.5°	35.5	36.9	36.1	38.4	39.7	43.5	49.2	62.0	85.5	113.3	124.7
95°	85.5	88.4	93.6	100.2	114.2	140.7	179.8	265.3	354.5	437.0	389.1
97.5°	232.7	239.0	258.9	292.1	346.5	434.6	529.7	661.3	724.5	677.2	495.8
100°	462.0	461.3	490.0	543.8	618.2	722.9	809.1	868.8	843.0	697.9	471.6
102.5°	677.8	694.7	718.8	761.4	819.3	885.6	935.9	937.7	848.9	659.5	436.2
105°	937.4	941.0	964.6	992.6	1026.5	1045.7	1031.6	958.0	804.0	592.5	392.8
107.5°	1086.8	1093.5	1101.5	1111.0	1110.3	1084.1	1019.5	899.9	725.3	533.2	365.0
110°	1148.1	1149.5	1151.0	1145.1	1124.5	1072.9	980.1	844.5	675.7	499.6	354.5



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1160.5	1160.2	1154.6	1136.3	1098.5	1032.3	928.2	789.7	632.7	477.2	348.6
115°	1140.0	1136.3	1121.5	1089.1	1033.9	953.6	845.2	717.0	580.7	453.2	346.4
117.5°	1074.9	1069.8	1048.6	1011.4	953.9	872.3	775.1	664.4	549.3	439.0	347.7
120°	1020.6	1016.2	998.5	957.2	899.0	824.6	736.1	636.7	532.8	432.5	350.1
122.5°	969.9	964.3	944.8	907.7	856.0	786.8	704.9	614.9	519.2	428.5	354.1
125°	899.0	893.8	875.4	843.0	795.9	736.9	666.2	585.8	501.8	423.0	360.3
127.5°	840.7	835.9	819.3	791.5	749.6	696.0	632.1	560.5	486.5	420.4	367.4
130°	807.7	801.7	786.3	759.8	720.7	670.6	610.9	544.6	478.2	418.6	372.1
132.5°	775.2	771.1	757.4	730.8	694.2	646.4	590.9	529.8	470.6	417.9	375.7
135°	728.8	723.6	710.4	688.2	652.1	610.1	562.2	509.9	460.5	417.1	381.0
137.5°	679.8	676.4	665.2	642.7	612.4	576.0	534.7	491.8	451.9	415.5	384.6
140°	645.5	646.3	634.4	613.9	585.8	554.1	518.8	481.2	446.6	414.9	386.9
142.5°	613.7	614.4	603.8	585.5	561.7	534.1	503.4	471.2	441.9	413.7	388.6
145°	569.6	568.2	562.2	546.8	528.4	507.0	483.4	459.1	435.5	411.9	389.8
147.5°	533.4	532.8	527.2	516.7	502.8	487.6	468.5	449.2	429.3	409.2	389.8
150°	512.2	512.2	507.7	499.6	488.5	474.6	459.1	442.1	425.2	406.8	389.8
152.5°	494.5	494.5	491.8	484.3	475.6	463.9	450.3	435.6	420.5	403.8	388.0
155°	472.3	471.6	470.1	464.2	457.6	448.7	437.7	425.9	413.4	398.7	386.2
157.5°	452.1	452.3	451.1	446.7	440.9	434.0	425.5	415.6	405.5	394.1	383.6
160°	439.2	439.9	439.9	435.5	430.4	425.2	417.8	409.7	400.1	390.6	382.5
162.5°	427.4	428.1	428.1	424.3	420.9	416.3	409.5	402.7	394.8	387.0	380.1
165°	411.9	411.9	412.6	409.7	406.8	403.1	397.9	393.5	387.6	381.7	376.5
167.5°	397.2	397.2	397.9	395.9	394.5	391.9	388.9	385.5	380.7	376.5	373.1
170°	388.3	388.3	389.1	387.6	386.9	385.4	382.5	380.2	376.5	372.9	370.7
172.5°	380.1	380.7	382.0	380.5	380.4	379.5	377.1	375.5	372.4	369.9	368.9
175°	370.7	371.4	372.1	371.4	371.4	371.4	369.9	369.2	367.7	366.3	366.3
177.5°	365.2	365.2	366.4	365.8	366.4	366.4	365.8	365.2	364.6	364.0	364.6
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	467.2	465.9	464.5	462.0	459.9	456.9	456.0	455.0	451.8	449.0	446.9
5°	495.8	490.5	482.9	475.8	470.1	462.4	458.1	453.5	446.9	440.9	436.1
7.5°	525.7	515.3	503.3	490.5	478.4	466.8	457.5	449.1	439.9	431.2	424.3
10°	549.4	534.4	517.7	499.7	484.4	469.5	456.9	446.0	434.1	423.8	415.2
12.5°	576.5	554.3	531.3	509.4	491.3	470.5	455.3	441.4	427.9	415.6	406.0
15°	608.4	580.3	553.1	523.0	495.4	469.5	451.5	433.9	418.3	405.6	393.2
17.5°	637.6	605.8	569.9	533.3	499.9	469.2	444.0	424.1	404.6	389.1	376.8
20°	654.1	617.9	577.3	539.3	502.4	468.2	440.5	416.8	395.7	379.2	365.4
22.5°	668.4	625.9	583.9	543.3	502.2	465.3	433.9	409.5	386.7	370.6	355.9
25°	683.2	632.4	590.2	542.6	496.7	458.5	423.4	395.7	372.9	353.9	338.8
27.5°	695.8	632.0	581.9	530.7	488.0	449.7	412.2	382.5	358.3	337.7	322.3
30°	704.2	632.8	573.3	522.6	479.6	440.1	403.6	373.7	348.3	327.4	312.9
32.5°	709.5	632.3	565.4	511.3	466.2	431.2	394.3	363.4	337.1	316.7	302.7
35°	712.6	628.4	551.8	488.1	444.7	410.6	379.7	347.6	320.2	301.0	285.2
37.5°	706.3	620.3	536.0	465.7	418.1	384.7	358.5	331.3	305.0	284.0	270.3
40°	696.7	615.0	523.7	449.9	399.8	367.6	345.4	318.6	292.7	272.7	260.0
42.5°	678.3	604.4	510.2	432.3	380.9	348.6	328.2	305.8	281.3	262.5	249.8
45°	633.3	581.0	489.8	406.0	352.9	319.5	301.5	285.2	263.1	244.9	233.8
47.5°	570.8	545.9	460.5	378.2	323.6	291.5	272.8	259.8	243.6	228.8	218.3
50°	527.4	517.1	440.7	359.2	304.2	272.7	254.7	242.9	231.2	216.5	206.9
52.5°	477.4	483.7	417.5	339.6	284.3	253.4	236.5	227.1	216.5	204.3	196.0
55°	406.9	429.9	377.5	306.5	254.7	225.3	209.2	201.0	194.7	185.8	178.5
57.5°	340.9	370.2	334.1	272.5	225.6	200.3	184.9	175.9	171.9	167.2	161.5
60°	301.7	330.6	303.2	249.7	206.2	182.0	168.4	160.7	156.7	153.4	148.6
62.5°	266.7	296.1	273.1	226.5	187.0	164.7	152.8	145.2	142.2	140.5	136.4
65°	218.7	243.9	228.6	190.4	159.7	139.9	129.1	123.9	121.0	120.4	117.7
67.5°	178.0	197.2	186.1	157.9	133.7	116.7	107.5	103.0	100.9	100.6	98.6
70°	151.3	169.3	160.7	135.3	114.4	101.0	93.1	89.2	87.8	87.7	86.5
72.5°	130.5	143.1	136.3	115.1	99.0	86.8	81.0	76.8	75.4	75.7	74.9
75°	96.6	106.0	102.1	87.4	74.5	66.5	61.7	59.1	57.8	58.4	57.5
77.5°	69.6	75.5	71.9	61.7	53.7	48.1	44.5	42.9	41.7	41.7	41.3
80°	52.5	56.0	54.0	47.9	41.3	36.5	33.6	32.5	31.9	31.6	31.4
82.5°	37.4	40.3	38.0	33.8	29.3	26.4	24.8	23.4	22.9	23.0	22.8
85°	18.9	20.0	19.1	16.5	14.7	13.4	12.5	11.9	11.4	11.6	11.2
87.5°	9.3	9.0	8.1	7.1	6.4	5.5	5.2	4.5	4.4	4.7	5.0
90°	14.0	11.8	9.6	8.1	6.6	4.4	2.9	1.5	2.9	4.4	6.6
92.5°	93.6	61.9	42.6	31.7	25.5	19.8	13.6	9.1	13.6	19.8	25.5
95°	268.2	158.4	95.8	67.0	47.9	35.3	27.2	25.1	27.2	35.3	47.9
97.5°	294.4	170.5	110.7	79.6	60.7	49.9	43.5	42.7	43.5	49.9	60.7
100°	277.8	168.7	117.2	88.4	70.8	60.4	55.2	54.6	55.2	60.4	70.8
102.5°	263.6	171.1	124.8	98.5	82.6	72.8	68.2	66.9	68.2	72.8	82.6
105°	253.4	177.6	137.8	115.0	100.9	92.1	87.7	85.5	87.7	92.1	100.9
107.5°	252.8	189.6	154.8	133.6	120.4	111.7	107.4	105.2	107.4	111.7	120.4
110°	255.7	199.7	166.5	145.9	133.4	125.3	121.6	119.4	121.6	125.3	133.4



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.6	209.7	178.9	158.9	146.4	138.3	134.6	132.3	134.6	138.3	146.4
115°	271.2	226.2	198.2	178.3	165.8	158.4	154.0	151.1	154.0	158.4	165.8
117.5°	283.9	243.7	216.0	197.7	183.6	176.8	173.1	169.8	173.1	176.8	183.6
120°	293.3	255.0	228.5	210.0	196.0	188.6	184.9	182.8	184.9	188.6	196.0
122.5°	302.1	266.7	240.8	221.2	207.8	199.8	196.1	194.0	196.1	199.8	207.8
125°	316.1	283.7	257.9	238.0	224.0	215.9	211.5	210.0	211.5	215.9	224.0
127.5°	327.6	298.4	273.5	253.6	238.2	229.9	224.4	222.3	224.4	229.9	238.2
130°	335.3	307.3	283.0	263.1	247.6	238.7	232.1	229.9	232.1	238.7	247.6
132.5°	342.3	314.9	291.2	271.9	256.5	245.8	238.7	235.8	238.7	245.8	256.5
135°	351.5	326.4	303.6	283.7	268.2	257.2	249.1	246.1	249.1	257.2	268.2
137.5°	358.3	334.4	312.5	294.0	278.7	266.9	258.9	255.8	258.9	266.9	278.7
140°	361.8	339.7	318.3	299.9	285.2	273.4	266.0	262.3	266.0	273.4	285.2
142.5°	365.3	343.8	323.0	305.9	291.1	280.5	272.5	269.4	272.5	280.5	291.1
145°	369.2	349.3	330.2	313.2	300.7	289.6	283.0	280.8	283.0	289.6	300.7
147.5°	371.6	353.7	336.2	321.7	309.6	300.1	293.6	292.3	293.6	300.1	309.6
150°	372.1	356.7	339.7	326.4	316.1	306.5	300.7	299.9	300.7	306.5	316.1
152.5°	373.3	358.4	343.8	331.1	322.1	313.6	307.7	307.6	307.7	313.6	322.1
155°	373.6	361.8	349.3	338.9	330.8	323.5	319.1	319.1	319.1	323.5	330.8
157.5°	374.4	363.7	353.7	345.7	338.8	332.3	328.8	328.2	328.8	332.3	338.8
160°	374.4	365.5	356.7	349.3	344.1	338.3	335.3	335.3	335.3	338.3	344.1
162.5°	373.7	366.1	358.4	352.2	347.7	343.0	340.6	340.6	340.6	343.0	347.7
165°	372.1	366.9	361.1	355.9	353.0	349.3	347.8	348.6	347.8	349.3	353.0
167.5°	371.0	366.8	362.6	359.3	357.2	354.5	353.7	354.6	353.7	354.5	357.2
170°	369.2	366.3	362.6	361.1	359.6	357.4	356.7	358.2	356.7	357.4	359.6
172.5°	368.6	366.3	363.2	362.2	361.4	359.8	359.6	360.5	359.6	359.8	361.4
175°	366.9	365.5	364.0	363.3	363.3	361.8	362.6	363.3	362.6	361.8	363.3
177.5°	365.8	364.6	364.0	364.0	364.0	363.4	364.0	364.6	364.0	363.4	364.0
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	445.6	444.4	442.7	440.1	437.9	434.6	434.6	435.1	435.1	435.0	434.6
5°	432.2	428.9	424.9	420.3	415.5	410.6	409.7	407.9	406.7	405.8	404.7
7.5°	417.8	412.0	406.2	399.8	393.9	389.1	385.7	382.9	381.1	379.1	377.7
10°	408.2	401.0	394.2	387.4	379.8	373.9	370.2	367.6	365.6	363.8	363.0
12.5°	396.8	388.5	381.0	374.5	366.4	360.2	356.7	355.4	353.2	349.4	347.5
15°	380.1	372.4	363.4	353.5	349.6	342.1	337.9	335.9	334.6	331.8	330.9
17.5°	365.8	355.8	345.6	338.3	330.9	324.9	322.5	320.1	318.4	316.0	315.3
20°	354.4	345.4	336.2	328.3	320.6	314.0	312.0	310.3	308.5	307.5	306.5
22.5°	342.8	333.8	326.1	318.8	310.6	306.2	304.2	302.2	301.0	300.2	299.4
25°	326.5	318.6	310.0	303.5	296.9	294.0	292.7	291.6	290.7	289.6	289.4
27.5°	312.0	303.3	296.4	290.2	285.5	283.1	281.8	281.3	281.5	281.9	282.2
30°	301.0	293.1	287.5	282.2	277.8	275.6	275.3	275.3	276.3	276.4	276.9
32.5°	291.1	284.6	278.8	273.7	270.4	268.9	269.8	269.8	270.4	271.0	271.8
35°	276.4	270.7	266.4	261.9	259.1	259.8	260.2	260.6	261.7	263.1	263.9
37.5°	262.5	257.6	253.0	249.6	248.3	249.4	250.5	251.4	252.7	253.7	254.6
40°	252.5	248.7	244.4	241.3	241.8	242.4	243.3	244.4	245.5	246.2	247.0
42.5°	243.2	239.3	235.9	233.4	234.0	234.9	235.4	235.9	237.2	238.5	238.9
45°	229.0	225.9	222.9	221.3	221.8	222.3	222.6	223.3	224.4	225.3	225.6
47.5°	213.1	210.9	208.9	207.4	208.1	207.9	208.5	209.9	210.2	210.8	212.0
50°	202.9	201.0	198.5	198.0	198.0	198.0	198.3	200.0	200.0	201.0	201.8
52.5°	191.6	190.4	188.9	188.0	187.7	187.7	188.6	189.5	189.8	191.1	192.0
55°	175.0	173.7	172.4	171.7	171.3	171.7	173.4	173.9	175.0	175.7	176.3
57.5°	157.7	156.7	155.6	155.2	155.1	155.7	156.7	158.0	158.3	160.3	161.3
60°	146.3	144.7	143.8	143.8	143.4	145.3	145.0	147.1	147.6	148.9	150.4
62.5°	134.5	132.4	132.1	132.1	132.7	133.3	133.8	134.8	136.0	137.6	138.8
65°	115.5	114.4	115.9	115.7	115.3	116.6	116.6	117.7	119.0	120.6	123.0
67.5°	97.6	97.0	97.1	97.1	97.7	98.5	99.2	100.1	101.7	103.3	104.9
70°	85.4	86.1	85.0	85.9	86.5	86.7	87.2	88.5	90.2	91.3	93.1
72.5°	73.6	73.6	73.7	74.1	74.7	75.1	75.6	77.1	79.0	79.9	81.3
75°	56.6	56.5	57.1	57.1	58.2	58.6	59.1	59.8	61.5	62.8	63.9
77.5°	41.4	41.7	41.5	42.2	41.9	42.0	43.4	44.0	44.2	46.8	47.4
80°	31.2	31.6	31.9	32.0	32.2	31.9	33.4	34.0	34.0	35.5	36.7
82.5°	22.4	22.6	23.2	23.5	23.5	23.9	24.0	24.5	25.1	25.7	27.1
85°	11.2	11.9	12.1	11.9	12.1	11.6	12.3	12.5	12.7	12.7	12.7
87.5°	5.1	5.6	5.8	6.5	6.8	7.4	7.3	7.1	7.2	7.8	7.4
90°	8.1	9.6	11.8	14.0	16.2	18.4	17.7	18.4	19.1	19.9	21.4
92.5°	31.7	42.6	61.9	93.6	124.7	113.3	85.5	62.0	49.2	43.5	39.7
95°	67.0	95.8	158.4	268.2	389.1	437.0	354.5	265.3	179.8	140.7	114.2
97.5°	79.6	110.7	170.5	294.4	495.8	677.2	724.5	661.3	529.7	434.6	346.5
100°	88.4	117.2	168.7	277.8	471.6	697.9	843.0	868.8	809.1	722.9	618.2
102.5°	98.5	124.8	171.1	263.6	436.2	659.5	848.9	937.7	935.9	885.6	819.3
105°	115.0	137.8	177.6	253.4	392.8	592.5	804.0	958.0	1031.6	1045.7	1026.5
107.5°	133.6	154.8	189.6	252.8	365.0	533.2	725.3	899.9	1019.5	1084.1	1110.3
110°	145.9	166.5	199.7	255.7	354.5	499.6	675.7	844.5	980.1	1072.9	1124.5



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	158.9	178.9	209.7	261.6	348.6	477.2	632.7	789.7	928.2	1032.3	1098.5
115°	178.3	198.2	226.2	271.2	346.4	453.2	580.7	717.0	845.2	953.6	1033.9
117.5°	197.7	216.0	243.7	283.9	347.7	439.0	549.3	664.4	775.1	872.3	953.9
120°	210.0	228.5	255.0	293.3	350.1	432.5	532.8	636.7	736.1	824.6	899.0
122.5°	221.2	240.8	266.7	302.1	354.1	428.5	519.2	614.9	704.9	786.8	856.0
125°	238.0	257.9	283.7	316.1	360.3	423.0	501.8	585.8	666.2	736.9	795.9
127.5°	253.6	273.5	298.4	327.6	367.4	420.4	486.5	560.5	632.1	696.0	749.6
130°	263.1	283.0	307.3	335.3	372.1	418.6	478.2	544.6	610.9	670.6	720.7
132.5°	271.9	291.2	314.9	342.3	375.7	417.9	470.6	529.8	590.9	646.4	694.2
135°	283.7	303.6	326.4	351.5	381.0	417.1	460.5	509.9	562.2	610.1	652.1
137.5°	294.0	312.5	334.4	358.3	384.6	415.5	451.9	491.8	534.7	576.0	612.4
140°	299.9	318.3	339.7	361.8	386.9	414.9	446.6	481.2	518.8	554.1	585.8
142.5°	305.9	323.0	343.8	365.3	388.6	413.7	441.9	471.2	503.4	534.1	561.7
145°	313.2	330.2	349.3	369.2	389.8	411.9	435.5	459.1	483.4	507.0	528.4
147.5°	321.7	336.2	353.7	371.6	389.8	409.2	429.3	449.2	468.5	487.6	502.8
150°	326.4	339.7	356.7	372.1	389.8	406.8	425.2	442.1	459.1	474.6	488.5
152.5°	331.1	343.8	358.4	373.3	388.0	403.8	420.5	435.6	450.3	463.9	475.6
155°	338.9	349.3	361.8	373.6	386.2	398.7	413.4	425.9	437.7	448.7	457.6
157.5°	345.7	353.7	363.7	374.4	383.6	394.1	405.5	415.6	425.5	434.0	440.9
160°	349.3	356.7	365.5	374.4	382.5	390.6	400.1	409.7	417.8	425.2	430.4
162.5°	352.2	358.4	366.1	373.7	380.1	387.0	394.8	402.7	409.5	416.3	420.9
165°	355.9	361.1	366.9	372.1	376.5	381.7	387.6	393.5	397.9	403.1	406.8
167.5°	359.3	362.6	366.8	371.0	373.1	376.5	380.7	385.5	388.9	391.9	394.5
170°	361.1	362.6	366.3	369.2	370.7	372.9	376.5	380.2	382.5	385.4	386.9
172.5°	362.2	363.2	366.3	368.6	368.9	369.9	372.4	375.5	377.1	379.5	380.4
175°	363.3	364.0	365.5	366.9	366.3	366.3	367.7	369.2	369.9	371.4	371.4
177.5°	364.0	364.0	364.6	365.8	364.6	364.0	364.6	365.2	365.8	366.4	366.4
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	433.4	433.2	434.4	433.6	434.4	433.2	433.4	434.6	435.0	435.1	435.1
5°	403.4	404.1	401.8	401.8	401.8	404.1	403.4	404.7	405.8	406.7	407.9
7.5°	376.6	375.7	375.8	374.6	375.8	375.7	376.6	377.7	379.1	381.1	382.9
10°	360.3	359.0	358.5	358.8	358.5	359.0	360.3	363.0	363.8	365.6	367.6
12.5°	346.8	346.6	343.7	343.7	343.7	346.6	346.8	347.5	349.4	353.2	355.4
15°	330.9	326.8	326.3	327.6	326.3	326.8	330.9	330.9	331.8	334.6	335.9
17.5°	315.0	312.7	312.9	312.3	312.9	312.7	315.0	315.3	316.0	318.4	320.1
20°	306.5	305.2	305.0	303.5	305.0	305.2	306.5	306.5	307.5	308.5	310.3
22.5°	298.8	298.4	298.5	296.8	298.5	298.4	298.8	299.4	300.2	301.0	302.2
25°	289.2	290.3	289.4	289.4	289.4	290.3	289.2	289.4	289.6	290.7	291.6
27.5°	282.7	282.7	282.2	282.2	282.2	282.7	282.7	282.2	281.9	281.5	281.3
30°	277.8	277.6	278.0	278.0	278.0	277.6	277.8	276.9	276.4	276.3	275.3
32.5°	272.9	273.1	273.2	273.4	273.2	273.1	272.9	271.8	271.0	270.4	269.8
35°	265.2	265.5	266.2	265.7	266.2	265.5	265.2	263.9	263.1	261.7	260.6
37.5°	255.0	256.0	255.8	256.1	255.8	256.0	255.0	254.6	253.7	252.7	251.4
40°	247.2	247.9	247.7	247.7	247.7	247.9	247.2	247.0	246.2	245.5	244.4
42.5°	239.3	239.8	239.2	238.9	239.2	239.8	239.3	238.9	238.5	237.2	235.9
45°	226.4	225.9	226.6	225.7	226.6	225.9	226.4	225.6	225.3	224.4	223.3
47.5°	211.9	212.4	212.5	213.2	212.5	212.4	211.9	212.0	210.8	210.2	209.9
50°	202.3	203.6	203.6	203.3	203.6	203.6	202.3	201.8	201.0	200.0	200.0
52.5°	192.7	193.3	194.3	194.2	194.3	193.3	192.7	192.0	191.1	189.8	189.5
55°	178.0	178.5	179.0	179.2	179.0	178.5	178.0	176.3	175.7	175.0	173.9
57.5°	162.9	162.7	163.7	164.1	163.7	162.7	162.9	161.3	160.3	158.3	158.0
60°	152.1	152.1	153.9	154.6	153.9	152.1	152.1	150.4	148.9	147.6	147.1
62.5°	140.7	141.5	143.2	142.3	143.2	141.5	140.7	138.8	137.6	136.0	134.8
65°	124.0	125.8	125.6	126.5	125.6	125.8	124.0	123.0	120.6	119.0	117.7
67.5°	106.6	107.7	109.3	109.4	109.3	107.7	106.6	104.9	103.3	101.7	100.1
70°	94.8	96.0	96.8	97.5	96.8	96.0	94.8	93.1	91.3	90.2	88.5
72.5°	83.4	84.0	86.1	85.2	86.1	84.0	83.4	81.3	79.9	79.0	77.1
75°	65.4	67.0	68.3	67.7	68.3	67.0	65.4	63.9	62.8	61.5	59.8
77.5°	48.4	50.0	50.5	50.0	50.5	50.0	48.4	47.4	46.8	44.2	44.0
80°	38.2	38.0	39.3	39.1	39.3	38.0	38.2	36.7	35.5	34.0	34.0
82.5°	28.0	27.8	28.4	28.6	28.4	27.8	28.0	27.1	25.7	25.1	24.5
85°	13.6	14.2	13.4	13.2	13.4	14.2	13.6	12.7	12.7	12.7	12.5
87.5°	7.3	7.4	7.4	7.1	7.4	7.4	7.3	7.4	7.8	7.2	7.1
90°	20.6	21.4	22.1	21.4	22.1	21.4	20.6	21.4	19.9	19.1	18.4
92.5°	38.4	36.1	36.9	35.5	36.9	36.1	38.4	39.7	43.5	49.2	62.0
95°	100.2	93.6	88.4	85.5	88.4	93.6	100.2	114.2	140.7	179.8	265.3
97.5°	292.1	258.9	239.0	232.7	239.0	258.9	292.1	346.5	434.6	529.7	661.3
100°	543.8	490.0	461.3	462.0	461.3	490.0	543.8	618.2	722.9	809.1	868.8
102.5°	761.4	718.8	694.7	677.8	694.7	718.8	761.4	819.3	885.6	935.9	937.7
105°	992.6	964.6	941.0	937.4	941.0	964.6	992.6	1026.5	1045.7	1031.6	958.0
107.5°	1111.0	1101.5	1093.5	1086.8	1093.5	1101.5	1111.0	1110.3	1084.1	1019.5	899.9
110°	1145.1	1151.0	1149.5	1148.1	1149.5	1151.0	1145.1	1124.5	1072.9	980.1	844.5



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1136.3	1154.6	1160.2	1160.5	1160.2	1154.6	1136.3	1098.5	1032.3	928.2	789.7
115°	1089.1	1121.5	1136.3	1140.0	1136.3	1121.5	1089.1	1033.9	953.6	845.2	717.0
117.5°	1011.4	1048.6	1069.8	1074.9	1069.8	1048.6	1011.4	953.9	872.3	775.1	664.4
120°	957.2	998.5	1016.2	1020.6	1016.2	998.5	957.2	899.0	824.6	736.1	636.7
122.5°	907.7	944.8	964.3	969.9	964.3	944.8	907.7	856.0	786.8	704.9	614.9
125°	843.0	875.4	893.8	899.0	893.8	875.4	843.0	795.9	736.9	666.2	585.8
127.5°	791.5	819.3	835.9	840.7	835.9	819.3	791.5	749.6	696.0	632.1	560.5
130°	759.8	786.3	801.7	807.7	801.7	786.3	759.8	720.7	670.6	610.9	544.6
132.5°	730.8	757.4	771.1	775.2	771.1	757.4	730.8	694.2	646.4	590.9	529.8
135°	688.2	710.4	723.6	728.8	723.6	710.4	688.2	652.1	610.1	562.2	509.9
137.5°	642.7	665.2	676.4	679.8	676.4	665.2	642.7	612.4	576.0	534.7	491.8
140°	613.9	634.4	646.3	645.5	646.3	634.4	613.9	585.8	554.1	518.8	481.2
142.5°	585.5	603.8	614.4	613.7	614.4	603.8	585.5	561.7	534.1	503.4	471.2
145°	546.8	562.2	568.2	569.6	568.2	562.2	546.8	528.4	507.0	483.4	459.1
147.5°	516.7	527.2	532.8	533.4	532.8	527.2	516.7	502.8	487.6	468.5	449.2
150°	499.6	507.7	512.2	512.2	512.2	507.7	499.6	488.5	474.6	459.1	442.1
152.5°	484.3	491.8	494.5	494.5	494.5	491.8	484.3	475.6	463.9	450.3	435.6
155°	464.2	470.1	471.6	472.3	471.6	470.1	464.2	457.6	448.7	437.7	425.9
157.5°	446.7	451.1	452.3	452.1	452.3	451.1	446.7	440.9	434.0	425.5	415.6
160°	435.5	439.9	439.9	439.2	439.9	439.9	435.5	430.4	425.2	417.8	409.7
162.5°	424.3	428.1	428.1	427.4	428.1	428.1	424.3	420.9	416.3	409.5	402.7
165°	409.7	412.6	411.9	411.9	411.9	412.6	409.7	406.8	403.1	397.9	393.5
167.5°	395.9	397.9	397.2	397.2	397.2	397.9	395.9	394.5	391.9	388.9	385.5
170°	387.6	389.1	388.3	388.3	388.3	389.1	387.6	386.9	385.4	382.5	380.2
172.5°	380.5	382.0	380.7	380.1	380.7	382.0	380.5	380.4	379.5	377.1	375.5
175°	371.4	372.1	371.4	370.7	371.4	372.1	371.4	371.4	371.4	369.9	369.2
177.5°	365.8	366.4	365.2	365.2	365.2	366.4	365.8	366.4	366.4	365.8	365.2
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	434.6	434.6	437.9	440.1	442.7	444.4	445.6	446.9	449.0	451.8	455.0
5°	409.7	410.6	415.5	420.3	424.9	428.9	432.2	436.1	440.9	446.9	453.5
7.5°	385.7	389.1	393.9	399.8	406.2	412.0	417.8	424.3	431.2	439.9	449.1
10°	370.2	373.9	379.8	387.4	394.2	401.0	408.2	415.2	423.8	434.1	446.0
12.5°	356.7	360.2	366.4	374.5	381.0	388.5	396.8	406.0	415.6	427.9	441.4
15°	337.9	342.1	349.6	353.5	363.4	372.4	380.1	393.2	405.6	418.3	433.9
17.5°	322.5	324.9	330.9	338.3	345.6	355.8	365.8	376.8	389.1	404.6	424.1
20°	312.0	314.0	320.6	328.3	336.2	345.4	354.4	365.4	379.2	395.7	416.8
22.5°	304.2	306.2	310.6	318.8	326.1	333.8	342.8	355.9	370.6	386.7	409.5
25°	292.7	294.0	296.9	303.5	310.0	318.6	326.5	338.8	353.9	372.9	395.7
27.5°	281.8	283.1	285.5	290.2	296.4	303.3	312.0	322.3	337.7	358.3	382.5
30°	275.3	275.6	277.8	282.2	287.5	293.1	301.0	312.9	327.4	348.3	373.7
32.5°	269.8	268.9	270.4	273.7	278.8	284.6	291.1	302.7	316.7	337.1	363.4
35°	260.2	259.8	259.1	261.9	266.4	270.7	276.4	285.2	301.0	320.2	347.6
37.5°	250.5	249.4	248.3	249.6	253.0	257.6	262.5	270.3	284.0	305.0	331.3
40°	243.3	242.4	241.8	241.3	244.4	248.7	252.5	260.0	272.7	292.7	318.6
42.5°	235.4	234.9	234.0	233.4	235.9	239.3	243.2	249.8	262.5	281.3	305.8
45°	222.6	222.3	221.8	221.3	222.9	225.9	229.0	233.8	244.9	263.1	285.2
47.5°	208.5	207.9	208.1	207.4	208.9	210.9	213.1	218.3	228.8	243.6	259.8
50°	198.3	198.0	198.0	198.0	198.5	201.0	202.9	206.9	216.5	231.2	242.9
52.5°	188.6	187.7	187.7	188.0	188.9	190.4	191.6	196.0	204.3	216.5	227.1
55°	173.4	171.7	171.3	171.7	172.4	173.7	175.0	178.5	185.8	194.7	201.0
57.5°	156.7	155.7	155.1	155.2	155.6	156.7	157.7	161.5	167.2	171.9	175.9
60°	145.0	145.3	143.4	143.8	143.8	144.7	146.3	148.6	153.4	156.7	160.7
62.5°	133.8	133.3	132.7	132.1	132.1	132.4	134.5	136.4	140.5	142.2	145.2
65°	116.6	116.6	115.3	115.7	115.9	114.4	115.5	117.7	120.4	121.0	123.9
67.5°	99.2	98.5	97.7	97.1	97.1	97.0	97.6	98.6	100.6	100.9	103.0
70°	87.2	86.7	86.5	85.9	85.0	86.1	85.4	86.5	87.7	87.8	89.2
72.5°	75.6	75.1	74.7	74.1	73.7	73.6	73.6	74.9	75.7	75.4	76.8
75°	59.1	58.6	58.2	57.1	57.1	56.5	56.6	57.5	58.4	57.8	59.1
77.5°	43.4	42.0	41.9	42.2	41.5	41.7	41.4	41.3	41.7	41.7	42.9
80°	33.4	31.9	32.2	32.0	31.9	31.6	31.2	31.4	31.6	31.9	32.5
82.5°	24.0	23.9	23.5	23.5	23.2	22.6	22.4	22.8	23.0	22.9	23.4
85°	12.3	11.6	12.1	11.9	12.1	11.9	11.2	11.2	11.6	11.4	11.9
87.5°	7.3	7.4	6.8	6.5	5.8	5.6	5.1	5.0	4.7	4.4	4.5
90°	17.7	18.4	16.2	14.0	11.8	9.6	8.1	6.6	4.4	2.9	1.5
92.5°	85.5	113.3	124.7	93.6	61.9	42.6	31.7	25.5	19.8	13.6	9.1
95°	354.5	437.0	389.1	268.2	158.4	95.8	67.0	47.9	35.3	27.2	25.1
97.5°	724.5	677.2	495.8	294.4	170.5	110.7	79.6	60.7	49.9	43.5	42.7
100°	843.0	697.9	471.6	277.8	168.7	117.2	88.4	70.8	60.4	55.2	54.6
102.5°	848.9	659.5	436.2	263.6	171.1	124.8	98.5	82.6	72.8	68.2	66.9
105°	804.0	592.5	392.8	253.4	177.6	137.8	115.0	100.9	92.1	87.7	85.5
107.5°	725.3	533.2	365.0	252.8	189.6	154.8	133.6	120.4	111.7	107.4	105.2
110°	675.7	499.6	354.5	255.7	199.7	166.5	145.9	133.4	125.3	121.6	119.4



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	632.7	477.2	348.6	261.6	209.7	178.9	158.9	146.4	138.3	134.6	132.3
115°	580.7	453.2	346.4	271.2	226.2	198.2	178.3	165.8	158.4	154.0	151.1
117.5°	549.3	439.0	347.7	283.9	243.7	216.0	197.7	183.6	176.8	173.1	169.8
120°	532.8	432.5	350.1	293.3	255.0	228.5	210.0	196.0	188.6	184.9	182.8
122.5°	519.2	428.5	354.1	302.1	266.7	240.8	221.2	207.8	199.8	196.1	194.0
125°	501.8	423.0	360.3	316.1	283.7	257.9	238.0	224.0	215.9	211.5	210.0
127.5°	486.5	420.4	367.4	327.6	298.4	273.5	253.6	238.2	229.9	224.4	222.3
130°	478.2	418.6	372.1	335.3	307.3	283.0	263.1	247.6	238.7	232.1	229.9
132.5°	470.6	417.9	375.7	342.3	314.9	291.2	271.9	256.5	245.8	238.7	235.8
135°	460.5	417.1	381.0	351.5	326.4	303.6	283.7	268.2	257.2	249.1	246.1
137.5°	451.9	415.5	384.6	358.3	334.4	312.5	294.0	278.7	266.9	258.9	255.8
140°	446.6	414.9	386.9	361.8	339.7	318.3	299.9	285.2	273.4	266.0	262.3
142.5°	441.9	413.7	388.6	365.3	343.8	323.0	305.9	291.1	280.5	272.5	269.4
145°	435.5	411.9	389.8	369.2	349.3	330.2	313.2	300.7	289.6	283.0	280.8
147.5°	429.3	409.2	389.8	371.6	353.7	336.2	321.7	309.6	300.1	293.6	292.3
150°	425.2	406.8	389.8	372.1	356.7	339.7	326.4	316.1	306.5	300.7	299.9
152.5°	420.5	403.8	388.0	373.3	358.4	343.8	331.1	322.1	313.6	307.7	307.6
155°	413.4	398.7	386.2	373.6	361.8	349.3	338.9	330.8	323.5	319.1	319.1
157.5°	405.5	394.1	383.6	374.4	363.7	353.7	345.7	338.8	332.3	328.8	328.2
160°	400.1	390.6	382.5	374.4	365.5	356.7	349.3	344.1	338.3	335.3	335.3
162.5°	394.8	387.0	380.1	373.7	366.1	358.4	352.2	347.7	343.0	340.6	340.6
165°	387.6	381.7	376.5	372.1	366.9	361.1	355.9	353.0	349.3	347.8	348.6
167.5°	380.7	376.5	373.1	371.0	366.8	362.6	359.3	357.2	354.5	353.7	354.6
170°	376.5	372.9	370.7	369.2	366.3	362.6	361.1	359.6	357.4	356.7	358.2
172.5°	372.4	369.9	368.9	368.6	366.3	363.2	362.2	361.4	359.8	359.6	360.5
175°	367.7	366.3	366.3	366.9	365.5	364.0	363.3	363.3	361.8	362.6	363.3
177.5°	364.6	364.0	364.6	365.8	364.6	364.0	364.0	364.0	363.4	364.0	364.6
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	456.0	456.9	459.9	462.0	464.5	465.9	467.2	468.3	469.8	470.0	475.1
5°	458.1	462.4	470.1	475.8	482.9	490.5	495.8	498.2	504.6	509.8	520.4
7.5°	457.5	466.8	478.4	490.5	503.3	515.3	525.7	538.0	546.7	559.9	572.8
10°	456.9	469.5	484.4	499.7	517.7	534.4	549.4	566.1	579.9	598.1	613.7
12.5°	455.3	470.5	491.3	509.4	531.3	554.3	576.5	597.9	610.1	640.5	654.8
15°	451.5	469.5	495.4	523.0	553.1	580.3	608.4	630.8	667.0	693.6	710.6
17.5°	444.0	469.2	499.9	533.3	569.9	605.8	637.6	671.6	710.0	742.2	776.5
20°	440.5	468.2	502.4	539.3	577.3	617.9	654.1	694.9	736.9	768.5	812.5
22.5°	433.9	465.3	502.2	543.3	583.9	625.9	668.4	709.5	758.0	801.5	843.4
25°	423.4	458.5	496.7	542.6	590.2	632.4	683.2	737.8	788.2	844.3	886.0
27.5°	412.2	449.7	488.0	530.7	581.9	632.0	695.8	757.5	819.3	867.6	898.5
30°	403.6	440.1	479.6	522.6	573.3	632.8	704.2	771.6	831.8	873.3	890.6
32.5°	394.3	431.2	466.2	511.3	565.4	632.3	709.5	779.9	832.5	860.1	856.7
35°	379.7	410.6	444.7	488.1	551.8	628.4	712.6	780.6	812.8	806.9	762.1
37.5°	358.5	384.7	418.1	465.7	536.0	620.3	706.3	757.4	755.4	707.1	642.2
40°	345.4	367.6	399.8	449.9	523.7	615.0	696.7	729.9	701.8	634.3	556.7
42.5°	328.2	348.6	380.9	432.3	510.2	604.4	678.3	687.9	632.9	555.3	484.1
45°	301.5	319.5	352.9	406.0	489.8	581.0	633.3	609.7	535.7	455.6	401.4
47.5°	272.8	291.5	323.6	378.2	460.5	545.9	570.8	520.8	444.9	379.8	330.1
50°	254.7	272.7	304.2	359.2	440.7	517.1	527.4	462.9	393.0	335.9	295.1
52.5°	236.5	253.4	284.3	339.6	417.5	483.7	477.4	411.6	347.4	298.7	266.6
55°	209.2	225.3	254.7	306.5	377.5	429.9	406.9	344.1	291.0	253.2	228.8
57.5°	184.9	200.3	225.6	272.5	334.1	370.2	340.9	287.9	245.7	216.6	198.5
60°	168.4	182.0	206.2	249.7	303.2	330.6	301.7	255.0	219.3	196.0	179.8
62.5°	152.8	164.7	187.0	226.5	273.1	296.1	266.7	227.2	196.9	176.3	162.4
65°	129.1	139.9	159.7	190.4	228.6	243.9	218.7	186.6	163.2	147.8	138.6
67.5°	107.5	116.7	133.7	157.9	186.1	197.2	178.0	153.2	135.4	123.1	115.8
70°	93.1	101.0	114.4	135.3	160.7	169.3	151.3	130.8	117.9	108.0	101.2
72.5°	81.0	86.8	99.0	115.1	136.3	143.1	130.5	112.6	100.6	93.1	87.7
75°	61.7	66.5	74.5	87.4	102.1	106.0	96.6	85.4	77.3	72.0	67.9
77.5°	44.5	48.1	53.7	61.7	71.9	75.5	69.6	62.0	56.1	52.6	50.2
80°	33.6	36.5	41.3	47.9	54.0	56.0	52.5	46.8	42.6	40.6	38.6
82.5°	24.8	26.4	29.3	33.8	38.0	40.3	37.4	33.9	31.7	29.9	29.1
85°	12.5	13.4	14.7	16.5	19.1	20.0	18.9	18.0	16.7	15.6	15.6
87.5°	5.2	5.5	6.4	7.1	8.1	9.0	9.3	9.4	9.6	9.3	9.3
90°	2.9	4.4	6.6	8.1	9.6	11.8	14.0	16.2	18.4	17.7	18.4
92.5°	13.6	19.8	25.5	31.7	42.6	61.9	93.6	124.7	113.3	85.5	62.0
95°	27.2	35.3	47.9	67.0	95.8	158.4	268.2	389.1	437.0	354.5	265.3
97.5°	43.5	49.9	60.7	79.6	110.7	170.5	294.4	495.8	677.2	724.5	661.3
100°	55.2	60.4	70.8	88.4	117.2	168.7	277.8	471.6	697.9	843.0	868.8
102.5°	68.2	72.8	82.6	98.5	124.8	171.1	263.6	436.2	659.5	848.9	937.7
105°	87.7	92.1	100.9	115.0	137.8	177.6	253.4	392.8	592.5	804.0	958.0
107.5°	107.4	111.7	120.4	133.6	154.8	189.6	252.8	365.0	533.2	725.3	899.9
110°	121.6	125.3	133.4	145.9	166.5	199.7	255.7	354.5	499.6	675.7	844.5



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	134.6	138.3	146.4	158.9	178.9	209.7	261.6	348.6	477.2	632.7	789.7
115°	154.0	158.4	165.8	178.3	198.2	226.2	271.2	346.4	453.2	580.7	717.0
117.5°	173.1	176.8	183.6	197.7	216.0	243.7	283.9	347.7	439.0	549.3	664.4
120°	184.9	188.6	196.0	210.0	228.5	255.0	293.3	350.1	432.5	532.8	636.7
122.5°	196.1	199.8	207.8	221.2	240.8	266.7	302.1	354.1	428.5	519.2	614.9
125°	211.5	215.9	224.0	238.0	257.9	283.7	316.1	360.3	423.0	501.8	585.8
127.5°	224.4	229.9	238.2	253.6	273.5	298.4	327.6	367.4	420.4	486.5	560.5
130°	232.1	238.7	247.6	263.1	283.0	307.3	335.3	372.1	418.6	478.2	544.6
132.5°	238.7	245.8	256.5	271.9	291.2	314.9	342.3	375.7	417.9	470.6	529.8
135°	249.1	257.2	268.2	283.7	303.6	326.4	351.5	381.0	417.1	460.5	509.9
137.5°	258.9	266.9	278.7	294.0	312.5	334.4	358.3	384.6	415.5	451.9	491.8
140°	266.0	273.4	285.2	299.9	318.3	339.7	361.8	386.9	414.9	446.6	481.2
142.5°	272.5	280.5	291.1	305.9	323.0	343.8	365.3	388.6	413.7	441.9	471.2
145°	283.0	289.6	300.7	313.2	330.2	349.3	369.2	389.8	411.9	435.5	459.1
147.5°	293.6	300.1	309.6	321.7	336.2	353.7	371.6	389.8	409.2	429.3	449.2
150°	300.7	306.5	316.1	326.4	339.7	356.7	372.1	389.8	406.8	425.2	442.1
152.5°	307.7	313.6	322.1	331.1	343.8	358.4	373.3	388.0	403.8	420.5	435.6
155°	319.1	323.5	330.8	338.9	349.3	361.8	373.6	386.2	398.7	413.4	425.9
157.5°	328.8	332.3	338.8	345.7	353.7	363.7	374.4	383.6	394.1	405.5	415.6
160°	335.3	338.3	344.1	349.3	356.7	365.5	374.4	382.5	390.6	400.1	409.7
162.5°	340.6	343.0	347.7	352.2	358.4	366.1	373.7	380.1	387.0	394.8	402.7
165°	347.8	349.3	353.0	355.9	361.1	366.9	372.1	376.5	381.7	387.6	393.5
167.5°	353.7	354.5	357.2	359.3	362.6	366.8	371.0	373.1	376.5	380.7	385.5
170°	356.7	357.4	359.6	361.1	362.6	366.3	369.2	370.7	372.9	376.5	380.2
172.5°	359.6	359.8	361.4	362.2	363.2	366.3	368.6	368.9	369.9	372.4	375.5
175°	362.6	361.8	363.3	363.3	364.0	365.5	366.9	366.3	366.3	367.7	369.2
177.5°	364.0	363.4	364.0	364.0	364.0	364.6	365.8	364.6	364.0	364.6	365.2
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	453.2	453.2	453.2	453.2	453.2	453.2	453.2
2.5°	476.9	477.1	479.0	480.4	479.8	480.6	481.0
5°	521.0	529.0	533.1	536.2	536.4	536.7	538.4
7.5°	583.6	592.1	598.3	607.8	610.5	613.7	612.8
10°	629.3	641.9	652.6	658.3	664.5	673.4	666.2
12.5°	672.0	694.2	710.6	719.4	725.2	727.0	723.5
15°	742.4	771.4	786.9	786.6	806.3	814.8	801.4
17.5°	806.9	833.7	855.2	866.1	882.6	886.2	884.6
20°	846.5	875.7	892.4	911.3	919.8	927.5	928.8
22.5°	880.5	906.8	924.7	940.4	947.5	951.2	953.4
25°	915.7	936.3	947.1	952.5	954.5	954.0	951.2
27.5°	913.2	914.8	903.0	891.4	880.9	869.2	865.2
30°	889.5	871.1	838.1	819.4	792.0	770.2	779.1
32.5°	827.2	790.4	753.5	712.7	678.9	669.3	659.6
35°	706.0	641.4	603.6	559.7	542.2	524.6	512.5
37.5°	571.1	521.2	476.4	447.7	430.1	419.0	413.0
40°	493.8	448.8	411.9	388.6	375.2	362.8	361.0
42.5°	432.2	390.3	362.6	344.0	331.2	325.8	322.0
45°	353.9	324.8	306.1	292.9	284.4	281.1	276.6
47.5°	299.6	279.0	264.9	256.0	249.5	247.0	246.8
50°	269.2	252.0	241.8	234.7	229.7	228.8	225.3
52.5°	246.4	231.5	223.5	217.4	213.7	211.2	210.2
55°	213.9	204.0	196.7	193.2	190.4	187.9	187.9
57.5°	187.1	178.9	174.1	171.1	170.2	168.5	167.4
60°	170.6	163.6	159.9	157.2	155.4	155.7	153.7
62.5°	154.5	149.9	146.3	143.7	141.6	141.7	141.8
65°	131.5	128.0	125.4	124.5	123.2	121.7	122.1
67.5°	111.5	108.2	106.1	104.6	104.2	103.3	104.6
70°	97.1	94.6	93.1	91.8	91.3	91.5	92.7
72.5°	83.9	82.2	81.2	80.6	79.6	79.6	80.4
75°	65.9	64.6	63.7	63.1	62.8	62.8	62.8
77.5°	48.4	48.1	47.7	46.8	46.8	47.0	47.0
80°	38.2	37.5	37.3	36.9	36.2	35.8	36.9
82.5°	28.6	27.9	27.7	27.6	26.6	26.5	27.4
85°	15.4	14.7	14.9	14.7	14.7	14.5	14.5
87.5°	9.2	9.2	9.3	9.4	9.3	9.3	9.5
90°	19.1	19.9	21.4	20.6	21.4	22.1	21.4
92.5°	49.2	43.5	39.7	38.4	36.1	36.9	35.5
95°	179.8	140.7	114.2	100.2	93.6	88.4	85.5
97.5°	529.7	434.6	346.5	292.1	258.9	239.0	232.7
100°	809.1	722.9	618.2	543.8	490.0	461.3	462.0
102.5°	935.9	885.6	819.3	761.4	718.8	694.7	677.8
105°	1031.6	1045.7	1026.5	992.6	964.6	941.0	937.4
107.5°	1019.5	1084.1	1110.3	1111.0	1101.5	1093.5	1086.8
110°	980.1	1072.9	1124.5	1145.1	1151.0	1149.5	1148.1



TEST NUMBER: P331885-830

CATALOG NUMBER: S123DIP-S340D805U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	928.2	1032.3	1098.5	1136.3	1154.6	1160.2	1160.5
115°	845.2	953.6	1033.9	1089.1	1121.5	1136.3	1140.0
117.5°	775.1	872.3	953.9	1011.4	1048.6	1069.8	1074.9
120°	736.1	824.6	899.0	957.2	998.5	1016.2	1020.6
122.5°	704.9	786.8	856.0	907.7	944.8	964.3	969.9
125°	666.2	736.9	795.9	843.0	875.4	893.8	899.0
127.5°	632.1	696.0	749.6	791.5	819.3	835.9	840.7
130°	610.9	670.6	720.7	759.8	786.3	801.7	807.7
132.5°	590.9	646.4	694.2	730.8	757.4	771.1	775.2
135°	562.2	610.1	652.1	688.2	710.4	723.6	728.8
137.5°	534.7	576.0	612.4	642.7	665.2	676.4	679.8
140°	518.8	554.1	585.8	613.9	634.4	646.3	645.5
142.5°	503.4	534.1	561.7	585.5	603.8	614.4	613.7
145°	483.4	507.0	528.4	546.8	562.2	568.2	569.6
147.5°	468.5	487.6	502.8	516.7	527.2	532.8	533.4
150°	459.1	474.6	488.5	499.6	507.7	512.2	512.2
152.5°	450.3	463.9	475.6	484.3	491.8	494.5	494.5
155°	437.7	448.7	457.6	464.2	470.1	471.6	472.3
157.5°	425.5	434.0	440.9	446.7	451.1	452.3	452.1
160°	417.8	425.2	430.4	435.5	439.9	439.9	439.2
162.5°	409.5	416.3	420.9	424.3	428.1	428.1	427.4
165°	397.9	403.1	406.8	409.7	412.6	411.9	411.9
167.5°	388.9	391.9	394.5	395.9	397.9	397.2	397.2
170°	382.5	385.4	386.9	387.6	389.1	388.3	388.3
172.5°	377.1	379.5	380.4	380.5	382.0	380.7	380.1
175°	369.9	371.4	371.4	371.4	372.1	371.4	370.7
177.5°	365.8	366.4	366.4	365.8	366.4	365.2	365.2
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0

(END OF REPORT)