

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331919-830

Luminaire Tested: **S123DIP-S560D585U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331919-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D585U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4457.4 lumens
Efficiency: N/A
Efficacy: 135.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	50				
1	98	94	90	87	91	87	84	81	74	71	69	62	60	58	50	49	48	43				
2	90	82	76	71	83	76	71	67	65	61	58	54	52	49	45	43	41	37				
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31				
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27				
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	32	29	27	24				
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	24	21				
7	59	47	39	33	54	43	36	31	38	32	28	32	28	24	27	23	21	18				
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	16				
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15				
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8020	8020	8020	8020
5°	9564	8055	7138	8055
10°	11970	8014	6446	8014
15°	14683	7949	6002	7949
20°	17491	7848	5715	7848
25°	18573	7726	5651	7726
30°	15919	7636	5680	7636
35°	11071	7510	5740	7510
40°	8338	7360	5722	7360
45°	6925	7138	5649	7138
50°	6203	6687	5598	6687
55°	5799	6199	5527	6199
60°	5440	5690	5470	5690
65°	5112	5186	5295	5186
70°	4793	4614	5042	4614
75°	4292	4038	4625	4038
80°	3756	3310	3986	3310
85°	2939	2408	2680	2408



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.4	1.6
10°-20°	235.3	5.3
20°-30°	395.0	8.9
30°-40°	447.2	10.0
40°-50°	401.1	9.0
50°-60°	323.7	7.3
60°-70°	225.5	5.1
70°-80°	118.5	2.7
80°-90°	31.0	0.7
90°-100°	26.3	0.6
100°-110°	125.4	2.8
110°-120°	301.2	6.8
120°-130°	383.5	8.6
130°-140°	409.8	9.2
140°-150°	383.2	8.6
150°-160°	309.1	6.9
160°-170°	199.5	4.5
170°-180°	68.7	1.5
0°-30°	703.7	15.8
0°-40°	1151.0	25.8
0°-60°	1875.7	42.1
0°-90°	2250.8	50.5
90°-120°	452.8	10.2
90°-150°	1629.3	36.6
90°-180°	2207.0	49.5
0°-180°	4457.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	745	745	745	745	745	
5°	885	746	661	746	885	92
15°	1318	713	539	713	1318	380
25°	1564	650	476	650	1564	686
35°	842	572	437	572	842	547
45°	455	469	371	469	455	360
55°	309	330	294	330	309	277
65°	201	204	208	204	201	200
75°	103	97	111	97	103	110
85°	24	20	22	20	24	29
90°	16	1	16	1	16	8
95°	20	33	20	33	20	17
105°	24	160	24	160	24	54
115°	316	300	316	300	316	292
125°	432	424	432	424	432	386
135°	533	527	533	527	533	411
145°	614	608	614	608	614	384
155°	669	670	669	670	669	309
165°	705	707	705	707	705	199
175°	721	724	721	724	721	69
180°	724	724	724	724	724	



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	790.7	790.1	788.7	789.9	787.5	784.4	784.1	781.2	772.8	772.2	770.0
5°	885.1	882.2	881.9	881.6	876.5	869.6	856.6	855.5	838.2	829.5	819.1
7.5°	1007.5	1009.0	1003.7	999.1	983.6	973.5	959.5	941.7	920.4	898.8	884.4
10°	1095.2	1107.1	1092.3	1082.2	1072.9	1055.2	1034.6	1009.0	983.4	953.4	930.7
12.5°	1189.4	1195.2	1192.3	1182.7	1168.2	1141.2	1104.8	1076.6	1052.9	1003.1	982.9
15°	1317.6	1339.6	1325.6	1293.1	1293.8	1268.2	1220.5	1168.2	1140.4	1096.6	1037.1
17.5°	1454.2	1457.0	1451.0	1423.9	1405.8	1370.6	1326.6	1276.5	1220.1	1167.3	1104.1
20°	1527.0	1524.8	1512.2	1498.1	1467.1	1439.6	1391.6	1335.7	1263.5	1211.4	1142.6
22.5°	1567.4	1563.8	1557.8	1546.1	1520.2	1490.7	1447.7	1386.5	1317.8	1246.1	1166.5
25°	1563.8	1568.5	1569.2	1565.9	1557.0	1539.3	1505.3	1456.6	1388.0	1296.0	1213.0
27.5°	1422.3	1428.9	1448.2	1465.4	1484.5	1503.9	1501.4	1477.2	1426.4	1346.9	1245.4
30°	1280.8	1266.3	1302.1	1347.2	1377.9	1432.0	1462.4	1464.1	1435.7	1367.4	1268.5
32.5°	1084.4	1100.3	1116.1	1171.6	1238.7	1299.5	1359.8	1408.4	1414.0	1368.6	1282.0
35°	842.5	862.4	891.3	920.2	992.4	1054.4	1160.6	1253.0	1326.6	1336.3	1283.3
37.5°	678.9	688.8	707.0	735.9	783.2	856.9	939.0	1055.7	1162.4	1241.8	1245.3
40°	593.4	596.3	616.9	638.9	677.2	737.8	811.9	915.1	1042.9	1153.8	1200.0
42.5°	529.3	535.7	544.4	565.6	596.1	641.7	710.5	795.9	912.9	1040.5	1130.9
45°	454.9	462.0	467.5	481.5	503.2	533.9	581.9	659.9	749.0	880.8	1002.5
47.5°	405.6	406.1	410.2	420.8	435.5	458.6	492.6	542.6	624.5	731.3	856.3
50°	370.4	376.2	377.6	385.9	397.5	414.4	442.6	485.1	552.3	646.2	761.0
52.5°	345.5	347.2	351.3	357.3	367.4	380.6	405.0	438.4	491.1	571.1	676.7
55°	309.0	309.0	313.0	317.6	323.5	335.4	351.6	376.2	416.2	478.3	565.7
57.5°	275.2	277.0	279.8	281.3	286.2	294.1	307.6	326.3	356.2	404.0	473.4
60°	252.7	255.9	255.6	258.4	262.8	268.9	280.5	295.7	322.3	360.6	419.1
62.5°	233.1	232.8	232.8	236.2	240.5	246.4	253.9	267.0	289.7	323.7	373.4
65°	200.7	200.0	202.6	204.7	206.1	210.5	216.2	227.8	243.0	268.2	306.8
67.5°	172.0	169.8	171.3	172.0	174.5	177.9	183.2	190.4	202.5	222.7	251.8
70°	152.3	150.5	150.1	150.9	153.1	155.6	159.6	166.5	177.6	193.9	215.2
72.5°	132.1	130.9	130.8	132.4	133.5	135.1	137.9	144.2	153.1	165.2	185.1
75°	103.2	103.2	103.2	103.6	104.7	106.1	108.3	111.5	118.4	127.1	140.4
77.5°	77.4	77.3	76.9	76.8	78.4	79.1	79.6	82.6	86.4	92.3	102.0
80°	60.6	58.8	59.6	60.6	61.4	61.7	62.8	63.5	66.8	70.0	76.9
82.5°	45.1	43.5	43.6	45.3	45.5	45.8	46.9	48.0	49.2	52.1	55.8
85°	23.8	23.8	24.2	24.2	24.5	24.2	25.3	25.6	25.6	27.4	29.6
87.5°	11.9	11.3	11.5	11.8	11.4	11.6	11.8	12.0	12.3	12.4	12.3
90°	16.1	15.9	15.6	15.5	15.2	14.8	14.3	13.9	13.4	12.9	11.3
92.5°	17.8	17.7	17.5	17.4	17.2	16.8	16.0	15.3	14.5	13.8	12.6
95°	20.5	20.5	20.5	20.5	20.5	20.0	19.1	18.4	17.5	16.7	15.4
97.5°	22.1	22.1	21.9	21.8	21.7	21.1	20.2	19.2	18.3	17.3	25.9
100°	22.6	22.4	22.3	22.2	22.1	21.6	20.6	19.6	18.7	17.7	36.4
102.5°	23.0	22.8	22.6	22.3	22.1	23.6	26.5	29.4	32.4	35.3	55.7
105°	23.7	23.4	23.2	22.9	22.7	33.2	54.3	75.4	96.6	117.7	128.5
107.5°	74.3	90.2	106.1	122.1	138.1	153.7	169.3	184.7	200.3	215.7	214.1
110°	147.8	164.9	182.0	199.1	216.1	226.7	230.6	234.6	238.5	242.4	241.1



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	253.6	257.2	260.8	264.5	268.1	269.8	269.8	269.7	269.7	269.6	268.2
115°	316.1	315.7	315.2	314.6	314.1	313.4	312.2	310.9	309.8	308.6	307.5
117.5°	351.2	351.1	351.0	350.9	350.8	350.2	349.3	348.4	347.4	346.4	345.9
120°	375.2	375.2	375.2	375.2	375.2	374.8	373.8	372.9	371.9	370.9	370.6
122.5°	398.9	398.8	398.7	398.6	398.5	398.1	397.5	396.8	396.2	395.5	395.0
125°	432.3	432.0	431.8	431.5	431.3	431.0	430.7	430.6	430.3	430.1	429.6
127.5°	464.3	464.5	464.8	465.0	465.2	465.1	464.8	464.4	464.0	463.6	463.1
130°	484.9	485.1	485.4	485.6	485.9	485.7	485.2	484.7	484.3	483.8	483.3
132.5°	503.8	504.2	504.4	504.8	505.2	505.1	504.6	504.2	503.7	503.2	502.8
135°	532.7	533.1	533.5	533.9	534.1	534.1	533.9	533.5	533.1	532.7	532.3
137.5°	560.0	560.2	560.4	560.6	560.9	560.7	560.2	559.6	559.0	558.5	558.2
140°	576.3	576.6	576.7	577.0	577.2	577.1	576.6	576.2	575.7	575.2	574.9
142.5°	591.4	591.6	592.0	592.4	592.7	592.7	592.3	591.9	591.5	591.2	590.8
145°	614.4	614.4	614.4	614.4	614.4	614.3	614.1	613.9	613.6	613.4	613.1
147.5°	631.7	632.3	632.7	633.3	633.9	634.0	633.8	633.6	633.3	633.1	632.8
150°	644.6	644.9	645.3	645.6	646.0	646.0	645.8	645.5	645.4	645.1	644.9
152.5°	654.9	655.4	656.0	656.6	657.0	657.1	656.7	656.3	655.8	655.4	655.3
155°	669.3	670.1	670.7	671.5	672.1	672.2	671.7	671.0	670.4	669.9	669.7
157.5°	681.5	682.4	683.3	684.2	685.1	685.3	684.6	683.8	683.2	682.4	682.5
160°	689.2	690.0	690.9	691.7	692.5	692.6	691.8	691.2	690.4	689.8	689.8
162.5°	696.5	697.2	698.0	698.7	699.5	699.5	698.6	697.8	697.0	696.2	696.3
165°	705.3	706.2	707.0	707.8	708.7	708.6	707.7	706.7	705.8	704.7	704.9
167.5°	711.6	712.7	713.6	714.5	715.5	715.5	714.5	713.6	712.7	711.6	711.6
170°	715.5	716.5	717.5	718.4	719.3	719.3	718.4	717.5	716.5	715.5	715.5
172.5°	717.7	718.7	719.8	720.9	721.9	721.9	721.0	720.0	719.1	718.1	718.0
175°	720.9	721.9	722.8	723.8	724.7	724.8	724.0	723.1	722.3	721.4	721.3
177.5°	721.9	722.8	723.8	724.7	725.7	725.8	725.0	724.2	723.5	722.7	722.6
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	768.2	765.9	763.6	759.5	756.0	751.1	749.7	748.0	742.8	738.1	734.7
5°	815.1	806.4	793.8	782.2	772.9	760.3	753.0	745.5	734.6	724.9	716.9
7.5°	864.2	847.2	827.6	806.3	786.6	767.4	752.1	738.4	723.2	708.8	697.7
10°	903.2	878.6	851.2	821.6	796.4	771.8	751.2	733.2	713.7	696.7	682.6
12.5°	947.6	911.3	873.5	837.4	807.6	773.5	748.7	725.7	703.6	683.2	667.3
15°	1000.3	954.1	909.4	859.9	814.4	771.8	742.2	713.3	687.7	666.8	646.5
17.5°	1048.2	995.9	936.9	876.8	821.9	771.4	729.9	697.3	665.2	639.6	619.4
20°	1075.3	1015.8	949.0	886.6	826.0	769.6	724.2	685.1	650.5	623.4	600.7
22.5°	1098.8	1029.1	960.0	893.2	825.7	765.0	713.5	673.4	635.7	609.3	585.1
25°	1123.0	1039.6	970.3	892.0	816.5	753.8	696.0	650.5	612.9	581.9	557.0
27.5°	1143.9	1039.0	956.7	872.4	802.3	739.3	677.7	628.9	589.0	555.3	530.0
30°	1157.7	1040.4	942.5	859.1	788.4	723.4	663.5	614.4	572.5	538.2	514.4
32.5°	1166.4	1039.5	929.5	840.7	766.5	709.0	648.2	597.4	554.3	520.7	497.7
35°	1171.4	1033.1	907.2	802.5	731.0	675.0	624.2	571.5	526.3	494.9	468.9
37.5°	1161.3	1019.8	881.2	765.6	687.4	632.4	589.5	544.6	501.4	466.8	444.4
40°	1145.4	1011.2	860.9	739.7	657.3	604.3	567.9	523.8	481.2	448.4	427.4
42.5°	1115.1	993.5	838.8	710.8	626.1	573.1	539.5	502.8	462.4	431.6	410.7
45°	1041.1	955.2	805.4	667.5	580.1	525.3	495.7	468.9	432.4	402.5	384.5
47.5°	938.4	897.5	757.1	621.8	532.1	479.3	448.5	427.0	400.3	376.2	358.8
50°	867.1	850.2	724.5	590.6	499.9	448.4	418.8	399.3	380.1	355.9	340.1
52.5°	784.8	795.2	686.4	558.3	467.3	416.6	388.7	373.2	355.9	336.0	322.2
55°	668.9	706.8	620.6	504.0	418.8	370.4	344.0	330.3	320.2	305.4	293.5
57.5°	560.4	608.6	549.3	448.0	371.0	329.3	304.1	289.1	282.6	274.8	265.5
60°	496.0	543.7	498.5	410.5	338.9	299.3	276.9	264.3	257.8	252.3	244.4
62.5°	438.6	486.7	448.8	372.3	307.5	270.7	251.2	238.8	233.8	230.9	224.1
65°	359.6	401.1	375.8	313.0	262.4	230.0	212.3	203.6	198.9	197.8	193.5
67.5°	292.7	324.2	305.9	259.6	219.8	191.7	176.7	169.4	165.8	165.4	162.1
70°	248.7	278.3	264.3	222.3	188.0	166.1	153.1	146.6	144.4	144.0	142.2
72.5°	214.6	235.3	224.1	189.2	162.7	142.7	133.1	126.3	123.9	124.4	123.2
75°	158.8	174.4	167.9	143.6	122.3	109.3	101.4	97.1	94.9	96.0	94.5
77.5°	114.3	124.1	118.3	101.5	88.4	79.0	73.1	70.5	68.5	68.4	67.8
80°	86.2	92.1	88.8	78.7	67.9	59.9	55.2	53.4	52.3	52.0	51.7
82.5°	61.5	66.4	62.5	55.6	48.3	43.5	40.8	38.5	37.6	37.8	37.5
85°	31.0	32.9	31.4	27.1	24.2	22.1	20.5	19.5	18.8	19.1	18.4
87.5°	12.6	12.6	11.4	10.0	9.2	8.1	7.8	7.1	6.7	7.0	6.9
90°	9.8	8.2	6.7	5.3	4.1	2.9	1.7	0.6	1.7	2.9	4.1
92.5°	11.4	10.3	9.0	8.7	9.0	9.3	9.7	10.0	9.7	9.3	9.0
95°	14.0	12.7	11.4	13.2	18.1	23.0	27.9	32.8	27.9	23.0	18.1
97.5°	34.5	43.1	51.7	57.1	59.3	61.5	63.7	65.9	63.7	61.5	59.3
100°	55.0	73.6	92.3	100.4	98.0	95.7	93.2	90.9	93.2	95.7	98.0
102.5°	76.1	96.4	116.8	126.1	124.4	122.7	120.9	119.2	120.9	122.7	124.4
105°	139.2	150.0	160.7	165.4	164.1	162.9	161.6	160.2	161.6	162.9	164.1
107.5°	212.4	210.7	209.0	207.6	206.6	205.6	204.4	203.4	204.4	205.6	206.6
110°	239.8	238.5	237.2	236.0	235.1	234.1	233.2	232.2	233.2	234.1	235.1



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	266.9	265.6	264.3	263.2	262.3	261.5	260.6	259.8	260.6	261.5	262.3
115°	306.4	305.4	304.3	303.4	302.7	301.9	301.2	300.5	301.2	301.9	302.7
117.5°	345.3	344.8	344.2	343.5	342.6	341.8	340.8	340.0	340.8	341.8	342.6
120°	370.2	369.9	369.5	368.8	367.7	366.6	365.5	364.5	365.5	366.6	367.7
122.5°	394.5	394.1	393.6	392.9	392.1	391.2	390.3	389.5	390.3	391.2	392.1
125°	429.1	428.7	428.2	427.4	426.5	425.6	424.6	423.6	424.6	425.6	426.5
127.5°	462.5	461.8	461.3	460.5	459.6	458.6	457.7	456.8	457.7	458.6	459.6
130°	482.9	482.4	481.9	481.2	480.2	479.3	478.3	477.4	478.3	479.3	480.2
132.5°	502.4	502.0	501.6	501.0	500.0	499.1	498.1	497.2	498.1	499.1	500.0
135°	531.8	531.3	530.8	530.3	529.5	528.8	528.1	527.4	528.1	528.8	529.5
137.5°	557.9	557.6	557.4	556.8	555.9	555.0	554.1	553.2	554.1	555.0	555.9
140°	574.5	574.1	573.8	573.3	572.5	571.8	571.1	570.3	571.1	571.8	572.5
142.5°	590.4	590.0	589.7	589.2	588.4	587.8	587.0	586.3	587.0	587.8	588.4
145°	612.9	612.7	612.5	611.9	611.1	610.2	609.4	608.5	609.4	610.2	611.1
147.5°	632.5	632.4	632.1	631.7	631.1	630.7	630.1	629.5	630.1	630.7	631.1
150°	644.6	644.4	644.1	643.9	643.5	643.1	642.8	642.4	642.8	643.1	643.5
152.5°	655.2	655.0	654.9	654.7	654.5	654.3	654.2	654.0	654.2	654.3	654.5
155°	669.6	669.5	669.4	669.4	669.7	669.9	670.1	670.3	670.1	669.9	669.7
157.5°	682.7	682.8	682.9	683.0	683.0	683.0	683.1	683.1	683.1	683.0	683.0
160°	689.9	690.0	690.2	690.3	690.4	690.6	690.7	690.8	690.7	690.6	690.4
162.5°	696.4	696.5	696.6	696.8	697.2	697.5	697.8	698.1	697.8	697.5	697.2
165°	705.0	705.1	705.2	705.5	705.9	706.2	706.5	706.9	706.5	706.2	705.9
167.5°	711.6	711.6	711.6	711.9	712.4	712.8	713.3	713.8	713.3	712.8	712.4
170°	715.5	715.5	715.5	715.8	716.2	716.7	717.2	717.7	717.2	716.7	716.2
172.5°	717.9	717.8	717.7	717.9	718.5	719.1	719.7	720.3	719.7	719.1	718.5
175°	721.2	721.0	721.0	721.2	721.8	722.4	723.0	723.6	723.0	722.4	721.8
177.5°	722.6	722.5	722.4	722.6	723.0	723.5	724.0	724.4	724.0	723.5	723.0
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	732.6	730.7	727.7	723.4	719.9	714.4	714.4	715.3	715.3	715.0	714.4
5°	710.4	705.0	698.5	691.0	683.0	675.0	673.6	670.7	668.5	667.1	665.3
7.5°	686.9	677.4	667.9	657.3	647.6	639.6	634.0	629.4	626.4	623.3	620.9
10°	671.1	659.1	648.0	636.8	624.5	614.7	608.6	604.3	601.1	598.1	596.7
12.5°	652.3	638.7	626.3	615.7	602.3	592.2	586.4	584.4	580.5	574.5	571.3
15°	624.9	612.3	597.5	581.2	574.7	562.4	555.5	552.3	550.2	545.4	544.0
17.5°	601.4	584.8	568.3	556.1	544.0	534.1	530.3	526.2	523.4	519.5	518.4
20°	582.7	567.9	552.7	539.7	527.1	516.2	512.9	510.1	507.2	505.4	504.0
22.5°	563.5	548.7	536.2	524.1	510.6	503.5	499.9	496.8	494.7	493.5	492.1
25°	536.8	523.8	509.7	498.9	488.0	483.3	481.2	479.4	478.0	476.2	475.8
27.5°	512.8	498.7	487.3	477.1	469.4	465.4	463.4	462.5	462.8	463.4	463.8
30°	494.9	481.9	472.5	463.8	456.7	453.1	452.7	452.7	454.1	454.5	455.2
32.5°	478.4	467.8	458.4	450.0	444.5	442.1	443.5	443.5	444.6	445.5	446.9
35°	454.5	445.1	437.9	430.6	425.9	427.1	427.7	428.5	430.3	432.4	433.9
37.5°	431.6	423.5	415.9	410.3	408.1	410.1	411.8	413.3	415.5	417.1	418.5
40°	415.1	409.0	401.8	396.7	397.5	398.5	400.0	401.8	403.6	404.6	406.1
42.5°	399.8	393.4	388.0	383.7	384.7	386.2	387.0	388.0	390.0	392.0	392.9
45°	376.5	371.5	366.4	363.9	364.6	365.3	366.1	367.1	368.9	370.4	370.7
47.5°	350.3	346.8	343.4	340.9	342.0	341.8	342.7	345.1	345.6	346.5	348.5
50°	333.6	330.3	326.3	325.6	325.6	325.6	325.9	328.9	328.9	330.3	331.8
52.5°	315.1	313.0	310.5	309.2	308.6	308.6	310.1	311.5	312.1	314.1	315.6
55°	287.7	285.5	283.4	282.3	281.5	282.3	285.2	285.9	287.7	288.8	289.8
57.5°	259.2	257.5	255.8	255.2	255.1	256.0	257.6	259.8	260.2	263.5	265.1
60°	240.4	237.9	236.5	236.5	235.7	238.9	238.3	241.9	242.6	244.8	247.3
62.5°	221.0	217.6	217.1	217.1	218.1	219.0	220.1	221.7	223.6	226.3	228.2
65°	189.9	188.0	190.6	190.2	189.5	191.7	191.7	193.5	195.7	198.2	202.2
67.5°	160.3	159.4	159.7	159.7	160.7	161.9	163.0	164.6	167.1	169.8	172.4
70°	140.4	141.5	139.7	141.2	142.2	142.6	143.3	145.4	148.4	150.1	153.1
72.5°	121.1	121.0	121.2	121.8	122.9	123.6	124.2	126.7	129.9	131.4	133.7
75°	93.1	92.7	93.9	93.9	95.7	96.4	97.1	98.2	101.0	103.2	105.1
77.5°	68.1	68.4	68.2	69.5	69.0	69.1	71.4	72.4	72.7	77.0	77.9
80°	51.3	52.0	52.3	52.7	53.1	52.3	54.9	56.0	56.0	58.4	60.3
82.5°	36.9	37.2	38.2	38.5	38.6	39.3	39.6	40.3	41.2	42.3	44.7
85°	18.4	19.5	19.9	19.5	19.9	19.1	20.2	20.5	20.9	20.9	20.9
87.5°	6.9	7.4	7.4	8.0	8.0	8.7	8.8	8.3	8.4	9.3	8.2
90°	5.3	6.7	8.2	9.8	11.3	12.9	13.4	13.9	14.3	14.8	15.2
92.5°	8.7	9.0	10.3	11.4	12.6	13.8	14.5	15.3	16.0	16.8	17.2
95°	13.2	11.4	12.7	14.0	15.4	16.7	17.5	18.4	19.1	20.0	20.5
97.5°	57.1	51.7	43.1	34.5	25.9	17.3	18.3	19.2	20.2	21.1	21.7
100°	100.4	92.3	73.6	55.0	36.4	17.7	18.7	19.6	20.6	21.6	22.1
102.5°	126.1	116.8	96.4	76.1	55.7	35.3	32.4	29.4	26.5	23.6	22.1
105°	165.4	160.7	150.0	139.2	128.5	117.7	96.6	75.4	54.3	33.2	22.7
107.5°	207.6	209.0	210.7	212.4	214.1	215.7	200.3	184.7	169.3	153.7	138.1
110°	236.0	237.2	238.5	239.8	241.1	242.4	238.5	234.6	230.6	226.7	216.1



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	263.2	264.3	265.6	266.9	268.2	269.6	269.7	269.7	269.8	269.8	268.1
115°	303.4	304.3	305.4	306.4	307.5	308.6	309.8	310.9	312.2	313.4	314.1
117.5°	343.5	344.2	344.8	345.3	345.9	346.4	347.4	348.4	349.3	350.2	350.8
120°	368.8	369.5	369.9	370.2	370.6	370.9	371.9	372.9	373.8	374.8	375.2
122.5°	392.9	393.6	394.1	394.5	395.0	395.5	396.2	396.8	397.5	398.1	398.5
125°	427.4	428.2	428.7	429.1	429.6	430.1	430.3	430.6	430.7	431.0	431.3
127.5°	460.5	461.3	461.8	462.5	463.1	463.6	464.0	464.4	464.8	465.1	465.2
130°	481.2	481.9	482.4	482.9	483.3	483.8	484.3	484.7	485.2	485.7	485.9
132.5°	501.0	501.6	502.0	502.4	502.8	503.2	503.7	504.2	504.6	505.1	505.2
135°	530.3	530.8	531.3	531.8	532.3	532.7	533.1	533.5	533.9	534.1	534.1
137.5°	556.8	557.4	557.6	557.9	558.2	558.5	559.0	559.6	560.2	560.7	560.9
140°	573.3	573.8	574.1	574.5	574.9	575.2	575.7	576.2	576.6	577.1	577.2
142.5°	589.2	589.7	590.0	590.4	590.8	591.2	591.5	591.9	592.3	592.7	592.7
145°	611.9	612.5	612.7	612.9	613.1	613.4	613.6	613.9	614.1	614.3	614.4
147.5°	631.7	632.1	632.4	632.5	632.8	633.1	633.3	633.6	633.8	634.0	633.9
150°	643.9	644.1	644.4	644.6	644.9	645.1	645.4	645.5	645.8	646.0	646.0
152.5°	654.7	654.9	655.0	655.2	655.3	655.4	655.8	656.3	656.7	657.1	657.0
155°	669.4	669.4	669.5	669.6	669.7	669.9	670.4	671.0	671.7	672.2	672.1
157.5°	683.0	682.9	682.8	682.7	682.5	682.4	683.2	683.8	684.6	685.3	685.1
160°	690.3	690.2	690.0	689.9	689.8	689.8	690.4	691.2	691.8	692.6	692.5
162.5°	696.8	696.6	696.5	696.4	696.3	696.2	697.0	697.8	698.6	699.5	699.5
165°	705.5	705.2	705.1	705.0	704.9	704.7	705.8	706.7	707.7	708.6	708.7
167.5°	711.9	711.6	711.6	711.6	711.6	711.6	712.7	713.6	714.5	715.5	715.5
170°	715.8	715.5	715.5	715.5	715.5	715.5	716.5	717.5	718.4	719.3	719.3
172.5°	717.9	717.7	717.8	717.9	718.0	718.1	719.1	720.0	721.0	721.9	721.9
175°	721.2	721.0	721.0	721.2	721.3	721.4	722.3	723.1	724.0	724.8	724.7
177.5°	722.6	722.4	722.5	722.6	722.6	722.7	723.5	724.2	725.0	725.8	725.7
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	712.5	712.2	714.2	712.8	714.2	712.2	712.5	714.4	715.0	715.3	715.3
5°	663.2	664.2	660.6	660.6	660.6	664.2	663.2	665.3	667.1	668.5	670.7
7.5°	619.3	617.6	617.8	615.9	617.8	617.6	619.3	620.9	623.3	626.4	629.4
10°	592.4	590.2	589.5	589.8	589.5	590.2	592.4	596.7	598.1	601.1	604.3
12.5°	570.1	569.7	565.0	565.1	565.0	569.7	570.1	571.3	574.5	580.5	584.4
15°	544.0	537.2	536.4	538.6	536.4	537.2	544.0	544.0	545.4	550.2	552.3
17.5°	517.8	514.2	514.4	513.3	514.4	514.2	517.8	518.4	519.5	523.4	526.2
20°	504.0	501.8	501.4	498.9	501.4	501.8	504.0	504.0	505.4	507.2	510.1
22.5°	491.3	490.5	490.7	488.0	490.7	490.5	491.3	492.1	493.5	494.7	496.8
25°	475.4	477.2	475.8	475.8	475.8	477.2	475.4	475.8	476.2	478.0	479.4
27.5°	464.8	464.7	463.9	463.9	463.9	464.7	464.8	463.8	463.4	462.8	462.5
30°	456.7	456.3	457.0	457.0	457.0	456.3	456.7	455.2	454.5	454.1	452.7
32.5°	448.6	449.0	449.2	449.5	449.2	449.0	448.6	446.9	445.5	444.6	443.5
35°	436.1	436.4	437.5	436.8	437.5	436.4	436.1	433.9	432.4	430.3	428.5
37.5°	419.1	420.8	420.5	421.0	420.5	420.8	419.1	418.5	417.1	415.5	413.3
40°	406.5	407.6	407.2	407.2	407.2	407.6	406.5	406.1	404.6	403.6	401.8
42.5°	393.5	394.3	393.3	392.8	393.3	394.3	393.5	392.9	392.0	390.0	388.0
45°	372.2	371.5	372.6	371.1	372.6	371.5	372.2	370.7	370.4	368.9	367.1
47.5°	348.4	349.1	349.4	350.4	349.4	349.1	348.4	348.5	346.5	345.6	345.1
50°	332.4	334.6	334.6	334.3	334.6	334.6	332.4	331.8	330.3	328.9	328.9
52.5°	316.9	317.9	319.3	319.2	319.3	317.9	316.9	315.6	314.1	312.1	311.5
55°	292.8	293.5	294.2	294.5	294.2	293.5	292.8	289.8	288.8	287.7	285.9
57.5°	267.8	267.5	269.2	269.8	269.2	267.5	267.8	265.1	263.5	260.2	259.8
60°	250.2	250.2	253.1	254.1	253.1	250.2	250.2	247.3	244.8	242.6	241.9
62.5°	231.4	232.5	235.4	233.9	235.4	232.5	231.4	228.2	226.3	223.6	221.7
65°	204.0	206.9	206.5	207.9	206.5	206.9	204.0	202.2	198.2	195.7	193.5
67.5°	175.3	177.1	179.7	179.9	179.7	177.1	175.3	172.4	169.8	167.1	164.6
70°	156.0	157.8	159.2	160.2	159.2	157.8	156.0	153.1	150.1	148.4	145.4
72.5°	137.1	138.1	141.6	140.1	141.6	138.1	137.1	133.7	131.4	129.9	126.7
75°	107.5	110.1	112.3	111.2	112.3	110.1	107.5	105.1	103.2	101.0	98.2
77.5°	79.6	82.1	83.1	82.2	83.1	82.1	79.6	77.9	77.0	72.7	72.4
80°	62.8	62.5	64.7	64.3	64.7	62.5	62.8	60.3	58.4	56.0	56.0
82.5°	46.1	45.7	46.8	46.9	46.8	45.7	46.1	44.7	42.3	41.2	40.3
85°	22.3	23.5	22.1	21.7	22.1	23.5	22.3	20.9	20.9	20.9	20.5
87.5°	8.3	8.3	8.1	7.8	8.1	8.3	8.3	8.2	9.3	8.4	8.3
90°	15.5	15.6	15.9	16.1	15.9	15.6	15.5	15.2	14.8	14.3	13.9
92.5°	17.4	17.5	17.7	17.8	17.7	17.5	17.4	17.2	16.8	16.0	15.3
95°	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.0	19.1	18.4
97.5°	21.8	21.9	22.1	22.1	22.1	21.9	21.8	21.7	21.1	20.2	19.2
100°	22.2	22.3	22.4	22.6	22.4	22.3	22.2	22.1	21.6	20.6	19.6
102.5°	22.3	22.6	22.8	23.0	22.8	22.6	22.3	22.1	23.6	26.5	29.4
105°	22.9	23.2	23.4	23.7	23.4	23.2	22.9	22.7	33.2	54.3	75.4
107.5°	122.1	106.1	90.2	74.3	90.2	106.1	122.1	138.1	153.7	169.3	184.7
110°	199.1	182.0	164.9	147.8	164.9	182.0	199.1	216.1	226.7	230.6	234.6



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	264.5	260.8	257.2	253.6	257.2	260.8	264.5	268.1	269.8	269.8	269.7
115°	314.6	315.2	315.7	316.1	315.7	315.2	314.6	314.1	313.4	312.2	310.9
117.5°	350.9	351.0	351.1	351.2	351.1	351.0	350.9	350.8	350.2	349.3	348.4
120°	375.2	375.2	375.2	375.2	375.2	375.2	375.2	375.2	374.8	373.8	372.9
122.5°	398.6	398.7	398.8	398.9	398.8	398.7	398.6	398.5	398.1	397.5	396.8
125°	431.5	431.8	432.0	432.3	432.0	431.8	431.5	431.3	431.0	430.7	430.6
127.5°	465.0	464.8	464.5	464.3	464.5	464.8	465.0	465.2	465.1	464.8	464.4
130°	485.6	485.4	485.1	484.9	485.1	485.4	485.6	485.9	485.7	485.2	484.7
132.5°	504.8	504.4	504.2	503.8	504.2	504.4	504.8	505.2	505.1	504.6	504.2
135°	533.9	533.5	533.1	532.7	533.1	533.5	533.9	534.1	534.1	533.9	533.5
137.5°	560.6	560.4	560.2	560.0	560.2	560.4	560.6	560.9	560.7	560.2	559.6
140°	577.0	576.7	576.6	576.3	576.6	576.7	577.0	577.2	577.1	576.6	576.2
142.5°	592.4	592.0	591.6	591.4	591.6	592.0	592.4	592.7	592.7	592.3	591.9
145°	614.4	614.4	614.4	614.4	614.4	614.4	614.4	614.4	614.3	614.1	613.9
147.5°	633.3	632.7	632.3	631.7	632.3	632.7	633.3	633.9	634.0	633.8	633.6
150°	645.6	645.3	644.9	644.6	644.9	645.3	645.6	646.0	646.0	645.8	645.5
152.5°	656.6	656.0	655.4	654.9	655.4	656.0	656.6	657.0	657.1	656.7	656.3
155°	671.5	670.7	670.1	669.3	670.1	670.7	671.5	672.1	672.2	671.7	671.0
157.5°	684.2	683.3	682.4	681.5	682.4	683.3	684.2	685.1	685.3	684.6	683.8
160°	691.7	690.9	690.0	689.2	690.0	690.9	691.7	692.5	692.6	691.8	691.2
162.5°	698.7	698.0	697.2	696.5	697.2	698.0	698.7	699.5	699.5	698.6	697.8
165°	707.8	707.0	706.2	705.3	706.2	707.0	707.8	708.7	708.6	707.7	706.7
167.5°	714.5	713.6	712.7	711.6	712.7	713.6	714.5	715.5	715.5	714.5	713.6
170°	718.4	717.5	716.5	715.5	716.5	717.5	718.4	719.3	719.3	718.4	717.5
172.5°	720.9	719.8	718.7	717.7	718.7	719.8	720.9	721.9	721.9	721.0	720.0
175°	723.8	722.8	721.9	720.9	721.9	722.8	723.8	724.7	724.8	724.0	723.1
177.5°	724.7	723.8	722.8	721.9	722.8	723.8	724.7	725.7	725.8	725.0	724.2
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	714.4	714.4	719.9	723.4	727.7	730.7	732.6	734.7	738.1	742.8	748.0
5°	673.6	675.0	683.0	691.0	698.5	705.0	710.4	716.9	724.9	734.6	745.5
7.5°	634.0	639.6	647.6	657.3	667.9	677.4	686.9	697.7	708.8	723.2	738.4
10°	608.6	614.7	624.5	636.8	648.0	659.1	671.1	682.6	696.7	713.7	733.2
12.5°	586.4	592.2	602.3	615.7	626.3	638.7	652.3	667.3	683.2	703.6	725.7
15°	555.5	562.4	574.7	581.2	597.5	612.3	624.9	646.5	666.8	687.7	713.3
17.5°	530.3	534.1	544.0	556.1	568.3	584.8	601.4	619.4	639.6	665.2	697.3
20°	512.9	516.2	527.1	539.7	552.7	567.9	582.7	600.7	623.4	650.5	685.1
22.5°	499.9	503.5	510.6	524.1	536.2	548.7	563.5	585.1	609.3	635.7	673.4
25°	481.2	483.3	488.0	498.9	509.7	523.8	536.8	557.0	581.9	612.9	650.5
27.5°	463.4	465.4	469.4	477.1	487.3	498.7	512.8	530.0	555.3	589.0	628.9
30°	452.7	453.1	456.7	463.8	472.5	481.9	494.9	514.4	538.2	572.5	614.4
32.5°	443.5	442.1	444.5	450.0	458.4	467.8	478.4	497.7	520.7	554.3	597.4
35°	427.7	427.1	425.9	430.6	437.9	445.1	454.5	468.9	494.9	526.3	571.5
37.5°	411.8	410.1	408.1	410.3	415.9	423.5	431.6	444.4	466.8	501.4	544.6
40°	400.0	398.5	397.5	396.7	401.8	409.0	415.1	427.4	448.4	481.2	523.8
42.5°	387.0	386.2	384.7	383.7	388.0	393.4	399.8	410.7	431.6	462.4	502.8
45°	366.1	365.3	364.6	363.9	366.4	371.5	376.5	384.5	402.5	432.4	468.9
47.5°	342.7	341.8	342.0	340.9	343.4	346.8	350.3	358.8	376.2	400.3	427.0
50°	325.9	325.6	325.6	325.6	326.3	330.3	333.6	340.1	355.9	380.1	399.3
52.5°	310.1	308.6	308.6	309.2	310.5	313.0	315.1	322.2	336.0	355.9	373.2
55°	285.2	282.3	281.5	282.3	283.4	285.5	287.7	293.5	305.4	320.2	330.3
57.5°	257.6	256.0	255.1	255.2	255.8	257.5	259.2	265.5	274.8	282.6	289.1
60°	238.3	238.9	235.7	236.5	236.5	237.9	240.4	244.4	252.3	257.8	264.3
62.5°	220.1	219.0	218.1	217.1	217.1	217.6	221.0	224.1	230.9	233.8	238.8
65°	191.7	191.7	189.5	190.2	190.6	188.0	189.9	193.5	197.8	198.9	203.6
67.5°	163.0	161.9	160.7	159.7	159.7	159.4	160.3	162.1	165.4	165.8	169.4
70°	143.3	142.6	142.2	141.2	139.7	141.5	140.4	142.2	144.0	144.4	146.6
72.5°	124.2	123.6	122.9	121.8	121.2	121.0	121.1	123.2	124.4	123.9	126.3
75°	97.1	96.4	95.7	93.9	93.9	92.7	93.1	94.5	96.0	94.9	97.1
77.5°	71.4	69.1	69.0	69.5	68.2	68.4	68.1	67.8	68.4	68.5	70.5
80°	54.9	52.3	53.1	52.7	52.3	52.0	51.3	51.7	52.0	52.3	53.4
82.5°	39.6	39.3	38.6	38.5	38.2	37.2	36.9	37.5	37.8	37.6	38.5
85°	20.2	19.1	19.9	19.5	19.9	19.5	18.4	18.4	19.1	18.8	19.5
87.5°	8.8	8.7	8.0	8.0	7.4	7.4	6.9	6.9	7.0	6.7	7.1
90°	13.4	12.9	11.3	9.8	8.2	6.7	5.3	4.1	2.9	1.7	0.6
92.5°	14.5	13.8	12.6	11.4	10.3	9.0	8.7	9.0	9.3	9.7	10.0
95°	17.5	16.7	15.4	14.0	12.7	11.4	13.2	18.1	23.0	27.9	32.8
97.5°	18.3	17.3	25.9	34.5	43.1	51.7	57.1	59.3	61.5	63.7	65.9
100°	18.7	17.7	36.4	55.0	73.6	92.3	100.4	98.0	95.7	93.2	90.9
102.5°	32.4	35.3	55.7	76.1	96.4	116.8	126.1	124.4	122.7	120.9	119.2
105°	96.6	117.7	128.5	139.2	150.0	160.7	165.4	164.1	162.9	161.6	160.2
107.5°	200.3	215.7	214.1	212.4	210.7	209.0	207.6	206.6	205.6	204.4	203.4
110°	238.5	242.4	241.1	239.8	238.5	237.2	236.0	235.1	234.1	233.2	232.2



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	269.7	269.6	268.2	266.9	265.6	264.3	263.2	262.3	261.5	260.6	259.8
115°	309.8	308.6	307.5	306.4	305.4	304.3	303.4	302.7	301.9	301.2	300.5
117.5°	347.4	346.4	345.9	345.3	344.8	344.2	343.5	342.6	341.8	340.8	340.0
120°	371.9	370.9	370.6	370.2	369.9	369.5	368.8	367.7	366.6	365.5	364.5
122.5°	396.2	395.5	395.0	394.5	394.1	393.6	392.9	392.1	391.2	390.3	389.5
125°	430.3	430.1	429.6	429.1	428.7	428.2	427.4	426.5	425.6	424.6	423.6
127.5°	464.0	463.6	463.1	462.5	461.8	461.3	460.5	459.6	458.6	457.7	456.8
130°	484.3	483.8	483.3	482.9	482.4	481.9	481.2	480.2	479.3	478.3	477.4
132.5°	503.7	503.2	502.8	502.4	502.0	501.6	501.0	500.0	499.1	498.1	497.2
135°	533.1	532.7	532.3	531.8	531.3	530.8	530.3	529.5	528.8	528.1	527.4
137.5°	559.0	558.5	558.2	557.9	557.6	557.4	556.8	555.9	555.0	554.1	553.2
140°	575.7	575.2	574.9	574.5	574.1	573.8	573.3	572.5	571.8	571.1	570.3
142.5°	591.5	591.2	590.8	590.4	590.0	589.7	589.2	588.4	587.8	587.0	586.3
145°	613.6	613.4	613.1	612.9	612.7	612.5	611.9	611.1	610.2	609.4	608.5
147.5°	633.3	633.1	632.8	632.5	632.4	632.1	631.7	631.1	630.7	630.1	629.5
150°	645.4	645.1	644.9	644.6	644.4	644.1	643.9	643.5	643.1	642.8	642.4
152.5°	655.8	655.4	655.3	655.2	655.0	654.9	654.7	654.5	654.3	654.2	654.0
155°	670.4	669.9	669.7	669.6	669.5	669.4	669.4	669.7	669.9	670.1	670.3
157.5°	683.2	682.4	682.5	682.7	682.8	682.9	683.0	683.0	683.0	683.1	683.1
160°	690.4	689.8	689.8	689.9	690.0	690.2	690.3	690.4	690.6	690.7	690.8
162.5°	697.0	696.2	696.3	696.4	696.5	696.6	696.8	697.2	697.5	697.8	698.1
165°	705.8	704.7	704.9	705.0	705.1	705.2	705.5	705.9	706.2	706.5	706.9
167.5°	712.7	711.6	711.6	711.6	711.6	711.6	711.9	712.4	712.8	713.3	713.8
170°	716.5	715.5	715.5	715.5	715.5	715.5	715.8	716.2	716.7	717.2	717.7
172.5°	719.1	718.1	718.0	717.9	717.8	717.7	717.9	718.5	719.1	719.7	720.3
175°	722.3	721.4	721.3	721.2	721.0	721.0	721.2	721.8	722.4	723.0	723.6
177.5°	723.5	722.7	722.6	722.6	722.5	722.4	722.6	723.0	723.5	724.0	724.4
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	749.7	751.1	756.0	759.5	763.6	765.9	768.2	770.0	772.2	772.8	781.2
5°	753.0	760.3	772.9	782.2	793.8	806.4	815.1	819.1	829.5	838.2	855.5
7.5°	752.1	767.4	786.6	806.3	827.6	847.2	864.2	884.4	898.8	920.4	941.7
10°	751.2	771.8	796.4	821.6	851.2	878.6	903.2	930.7	953.4	983.4	1009.0
12.5°	748.7	773.5	807.6	837.4	873.5	911.3	947.6	982.9	1003.1	1052.9	1076.6
15°	742.2	771.8	814.4	859.9	909.4	954.1	1000.3	1037.1	1096.6	1140.4	1168.2
17.5°	729.9	771.4	821.9	876.8	936.9	995.9	1048.2	1104.1	1167.3	1220.1	1276.5
20°	724.2	769.6	826.0	886.6	949.0	1015.8	1075.3	1142.6	1211.4	1263.5	1335.7
22.5°	713.5	765.0	825.7	893.2	960.0	1029.1	1098.8	1166.5	1246.1	1317.8	1386.5
25°	696.0	753.8	816.5	892.0	970.3	1039.6	1123.0	1213.0	1296.0	1388.0	1456.6
27.5°	677.7	739.3	802.3	872.4	956.7	1039.0	1143.9	1245.4	1346.9	1426.4	1477.2
30°	663.5	723.4	788.4	859.1	942.5	1040.4	1157.7	1268.5	1367.4	1435.7	1464.1
32.5°	648.2	709.0	766.5	840.7	929.5	1039.5	1166.4	1282.0	1368.6	1414.0	1408.4
35°	624.2	675.0	731.0	802.5	907.2	1033.1	1171.4	1283.3	1336.3	1326.6	1253.0
37.5°	589.5	632.4	687.4	765.6	881.2	1019.8	1161.3	1245.3	1241.8	1162.4	1055.7
40°	567.9	604.3	657.3	739.7	860.9	1011.2	1145.4	1200.0	1153.8	1042.9	915.1
42.5°	539.5	573.1	626.1	710.8	838.8	993.5	1115.1	1130.9	1040.5	912.9	795.9
45°	495.7	525.3	580.1	667.5	805.4	955.2	1041.1	1002.5	880.8	749.0	659.9
47.5°	448.5	479.3	532.1	621.8	757.1	897.5	938.4	856.3	731.3	624.5	542.6
50°	418.8	448.4	499.9	590.6	724.5	850.2	867.1	761.0	646.2	552.3	485.1
52.5°	388.7	416.6	467.3	558.3	686.4	795.2	784.8	676.7	571.1	491.1	438.4
55°	344.0	370.4	418.8	504.0	620.6	706.8	668.9	565.7	478.3	416.2	376.2
57.5°	304.1	329.3	371.0	448.0	549.3	608.6	560.4	473.4	404.0	356.2	326.3
60°	276.9	299.3	338.9	410.5	498.5	543.7	496.0	419.1	360.6	322.3	295.7
62.5°	251.2	270.7	307.5	372.3	448.8	486.7	438.6	373.4	323.7	289.7	267.0
65°	212.3	230.0	262.4	313.0	375.8	401.1	359.6	306.8	268.2	243.0	227.8
67.5°	176.7	191.7	219.8	259.6	305.9	324.2	292.7	251.8	222.7	202.5	190.4
70°	153.1	166.1	188.0	222.3	264.3	278.3	248.7	215.2	193.9	177.6	166.5
72.5°	133.1	142.7	162.7	189.2	224.1	235.3	214.6	185.1	165.2	153.1	144.2
75°	101.4	109.3	122.3	143.6	167.9	174.4	158.8	140.4	127.1	118.4	111.5
77.5°	73.1	79.0	88.4	101.5	118.3	124.1	114.3	102.0	92.3	86.4	82.6
80°	55.2	59.9	67.9	78.7	88.8	92.1	86.2	76.9	70.0	66.8	63.5
82.5°	40.8	43.5	48.3	55.6	62.5	66.4	61.5	55.8	52.1	49.2	48.0
85°	20.5	22.1	24.2	27.1	31.4	32.9	31.0	29.6	27.4	25.6	25.6
87.5°	7.8	8.1	9.2	10.0	11.4	12.6	12.6	12.3	12.4	12.3	12.0
90°	1.7	2.9	4.1	5.3	6.7	8.2	9.8	11.3	12.9	13.4	13.9
92.5°	9.7	9.3	9.0	8.7	9.0	10.3	11.4	12.6	13.8	14.5	15.3
95°	27.9	23.0	18.1	13.2	11.4	12.7	14.0	15.4	16.7	17.5	18.4
97.5°	63.7	61.5	59.3	57.1	51.7	43.1	34.5	25.9	17.3	18.3	19.2
100°	93.2	95.7	98.0	100.4	92.3	73.6	55.0	36.4	17.7	18.7	19.6
102.5°	120.9	122.7	124.4	126.1	116.8	96.4	76.1	55.7	35.3	32.4	29.4
105°	161.6	162.9	164.1	165.4	160.7	150.0	139.2	128.5	117.7	96.6	75.4
107.5°	204.4	205.6	206.6	207.6	209.0	210.7	212.4	214.1	215.7	200.3	184.7
110°	233.2	234.1	235.1	236.0	237.2	238.5	239.8	241.1	242.4	238.5	234.6



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	260.6	261.5	262.3	263.2	264.3	265.6	266.9	268.2	269.6	269.7	269.7
115°	301.2	301.9	302.7	303.4	304.3	305.4	306.4	307.5	308.6	309.8	310.9
117.5°	340.8	341.8	342.6	343.5	344.2	344.8	345.3	345.9	346.4	347.4	348.4
120°	365.5	366.6	367.7	368.8	369.5	369.9	370.2	370.6	370.9	371.9	372.9
122.5°	390.3	391.2	392.1	392.9	393.6	394.1	394.5	395.0	395.5	396.2	396.8
125°	424.6	425.6	426.5	427.4	428.2	428.7	429.1	429.6	430.1	430.3	430.6
127.5°	457.7	458.6	459.6	460.5	461.3	461.8	462.5	463.1	463.6	464.0	464.4
130°	478.3	479.3	480.2	481.2	481.9	482.4	482.9	483.3	483.8	484.3	484.7
132.5°	498.1	499.1	500.0	501.0	501.6	502.0	502.4	502.8	503.2	503.7	504.2
135°	528.1	528.8	529.5	530.3	530.8	531.3	531.8	532.3	532.7	533.1	533.5
137.5°	554.1	555.0	555.9	556.8	557.4	557.6	557.9	558.2	558.5	559.0	559.6
140°	571.1	571.8	572.5	573.3	573.8	574.1	574.5	574.9	575.2	575.7	576.2
142.5°	587.0	587.8	588.4	589.2	589.7	590.0	590.4	590.8	591.2	591.5	591.9
145°	609.4	610.2	611.1	611.9	612.5	612.7	612.9	613.1	613.4	613.6	613.9
147.5°	630.1	630.7	631.1	631.7	632.1	632.4	632.5	632.8	633.1	633.3	633.6
150°	642.8	643.1	643.5	643.9	644.1	644.4	644.6	644.9	645.1	645.4	645.5
152.5°	654.2	654.3	654.5	654.7	654.9	655.0	655.2	655.3	655.4	655.8	656.3
155°	670.1	669.9	669.7	669.4	669.4	669.5	669.6	669.7	669.9	670.4	671.0
157.5°	683.1	683.0	683.0	683.0	682.9	682.8	682.7	682.5	682.4	683.2	683.8
160°	690.7	690.6	690.4	690.3	690.2	690.0	689.9	689.8	689.8	690.4	691.2
162.5°	697.8	697.5	697.2	696.8	696.6	696.5	696.4	696.3	696.2	697.0	697.8
165°	706.5	706.2	705.9	705.5	705.2	705.1	705.0	704.9	704.7	705.8	706.7
167.5°	713.3	712.8	712.4	711.9	711.6	711.6	711.6	711.6	711.6	712.7	713.6
170°	717.2	716.7	716.2	715.8	715.5	715.5	715.5	715.5	715.5	716.5	717.5
172.5°	719.7	719.1	718.5	717.9	717.7	717.8	717.9	718.0	718.1	719.1	720.0
175°	723.0	722.4	721.8	721.2	721.0	721.0	721.2	721.3	721.4	722.3	723.1
177.5°	724.0	723.5	723.0	722.6	722.4	722.5	722.6	722.6	722.7	723.5	724.2
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	784.1	784.4	787.5	789.9	788.7	790.1	790.7
5°	856.6	869.6	876.5	881.6	881.9	882.2	885.1
7.5°	959.5	973.5	983.6	999.1	1003.7	1009.0	1007.5
10°	1034.6	1055.2	1072.9	1082.2	1092.3	1107.1	1095.2
12.5°	1104.8	1141.2	1168.2	1182.7	1192.3	1195.2	1189.4
15°	1220.5	1268.2	1293.8	1293.1	1325.6	1339.6	1317.6
17.5°	1326.6	1370.6	1405.8	1423.9	1451.0	1457.0	1454.2
20°	1391.6	1439.6	1467.1	1498.1	1512.2	1524.8	1527.0
22.5°	1447.7	1490.7	1520.2	1546.1	1557.8	1563.8	1567.4
25°	1505.3	1539.3	1557.0	1565.9	1569.2	1568.5	1563.8
27.5°	1501.4	1503.9	1484.5	1465.4	1448.2	1428.9	1422.3
30°	1462.4	1432.0	1377.9	1347.2	1302.1	1266.3	1280.8
32.5°	1359.8	1299.5	1238.7	1171.6	1116.1	1100.3	1084.4
35°	1160.6	1054.4	992.4	920.2	891.3	862.4	842.5
37.5°	939.0	856.9	783.2	735.9	707.0	688.8	678.9
40°	811.9	737.8	677.2	638.9	616.9	596.3	593.4
42.5°	710.5	641.7	596.1	565.6	544.4	535.7	529.3
45°	581.9	533.9	503.2	481.5	467.5	462.0	454.9
47.5°	492.6	458.6	435.5	420.8	410.2	406.1	405.6
50°	442.6	414.4	397.5	385.9	377.6	376.2	370.4
52.5°	405.0	380.6	367.4	357.3	351.3	347.2	345.5
55°	351.6	335.4	323.5	317.6	313.0	309.0	309.0
57.5°	307.6	294.1	286.2	281.3	279.8	277.0	275.2
60°	280.5	268.9	262.8	258.4	255.6	255.9	252.7
62.5°	253.9	246.4	240.5	236.2	232.8	232.8	233.1
65°	216.2	210.5	206.1	204.7	202.6	200.0	200.7
67.5°	183.2	177.9	174.5	172.0	171.3	169.8	172.0
70°	159.6	155.6	153.1	150.9	150.1	150.5	152.3
72.5°	137.9	135.1	133.5	132.4	130.8	130.9	132.1
75°	108.3	106.1	104.7	103.6	103.2	103.2	103.2
77.5°	79.6	79.1	78.4	76.8	76.9	77.3	77.4
80°	62.8	61.7	61.4	60.6	59.6	58.8	60.6
82.5°	46.9	45.8	45.5	45.3	43.6	43.5	45.1
85°	25.3	24.2	24.5	24.2	24.2	23.8	23.8
87.5°	11.8	11.6	11.4	11.8	11.5	11.3	11.9
90°	14.3	14.8	15.2	15.5	15.6	15.9	16.1
92.5°	16.0	16.8	17.2	17.4	17.5	17.7	17.8
95°	19.1	20.0	20.5	20.5	20.5	20.5	20.5
97.5°	20.2	21.1	21.7	21.8	21.9	22.1	22.1
100°	20.6	21.6	22.1	22.2	22.3	22.4	22.6
102.5°	26.5	23.6	22.1	22.3	22.6	22.8	23.0
105°	54.3	33.2	22.7	22.9	23.2	23.4	23.7
107.5°	169.3	153.7	138.1	122.1	106.1	90.2	74.3
110°	230.6	226.7	216.1	199.1	182.0	164.9	147.8



TEST NUMBER: P331919-830

CATALOG NUMBER: S123DIP-S560D585U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	269.8	269.8	268.1	264.5	260.8	257.2	253.6
115°	312.2	313.4	314.1	314.6	315.2	315.7	316.1
117.5°	349.3	350.2	350.8	350.9	351.0	351.1	351.2
120°	373.8	374.8	375.2	375.2	375.2	375.2	375.2
122.5°	397.5	398.1	398.5	398.6	398.7	398.8	398.9
125°	430.7	431.0	431.3	431.5	431.8	432.0	432.3
127.5°	464.8	465.1	465.2	465.0	464.8	464.5	464.3
130°	485.2	485.7	485.9	485.6	485.4	485.1	484.9
132.5°	504.6	505.1	505.2	504.8	504.4	504.2	503.8
135°	533.9	534.1	534.1	533.9	533.5	533.1	532.7
137.5°	560.2	560.7	560.9	560.6	560.4	560.2	560.0
140°	576.6	577.1	577.2	577.0	576.7	576.6	576.3
142.5°	592.3	592.7	592.7	592.4	592.0	591.6	591.4
145°	614.1	614.3	614.4	614.4	614.4	614.4	614.4
147.5°	633.8	634.0	633.9	633.3	632.7	632.3	631.7
150°	645.8	646.0	646.0	645.6	645.3	644.9	644.6
152.5°	656.7	657.1	657.0	656.6	656.0	655.4	654.9
155°	671.7	672.2	672.1	671.5	670.7	670.1	669.3
157.5°	684.6	685.3	685.1	684.2	683.3	682.4	681.5
160°	691.8	692.6	692.5	691.7	690.9	690.0	689.2
162.5°	698.6	699.5	699.5	698.7	698.0	697.2	696.5
165°	707.7	708.6	708.7	707.8	707.0	706.2	705.3
167.5°	714.5	715.5	715.5	714.5	713.6	712.7	711.6
170°	718.4	719.3	719.3	718.4	717.5	716.5	715.5
172.5°	721.0	721.9	721.9	720.9	719.8	718.7	717.7
175°	724.0	724.8	724.7	723.8	722.8	721.9	720.9
177.5°	725.0	725.8	725.7	724.7	723.8	722.8	721.9
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6

(END OF REPORT)