

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331930-830

Luminaire Tested: **S123DIP-S560D805U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331930-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S560D805U830-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4990.4 lumens  
Efficiency: N/A  
Efficacy: 130.0 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				
2	88	81	75	70	81	75	70	65	62	59	56	51	49	46	41	39	37	33				
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	63	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	52	45	40	44	39	35	36	33	29	29	27	24	21				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18				
7	58	46	38	32	53	42	35	31	36	31	27	30	26	23	24	21	19	16				
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	15				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15	13				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8020	8020	8020	8020
5°	9564	8055	7138	8055
10°	11970	8014	6446	8014
15°	14683	7949	6002	7949
20°	17491	7848	5715	7848
25°	18573	7726	5651	7726
30°	15919	7636	5680	7636
35°	11071	7510	5740	7510
40°	8338	7360	5722	7360
45°	6925	7138	5649	7138
50°	6203	6687	5598	6687
55°	5799	6199	5527	6199
60°	5440	5690	5470	5690
65°	5112	5186	5295	5186
70°	4793	4614	5042	4614
75°	4292	4038	4625	4038
80°	3756	3310	3986	3310
85°	2939	2408	2680	2408



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.4	1.5
10°-20°	235.3	4.7
20°-30°	395.0	7.9
30°-40°	447.2	9.0
40°-50°	401.1	8.0
50°-60°	323.7	6.5
60°-70°	225.5	4.5
70°-80°	118.5	2.4
80°-90°	31.8	0.6
90°-100°	202.6	4.1
100°-110°	573.6	11.5
110°-120°	564.3	11.3
120°-130°	450.1	9.0
130°-140°	354.9	7.1
140°-150°	264.9	5.3
150°-160°	184.6	3.7
160°-170°	108.5	2.2
170°-180°	35.3	0.7
0°-30°	703.7	14.1
0°-40°	1151.0	23.1
0°-60°	1875.7	37.6
0°-90°	2251.6	45.1
90°-120°	1340.5	26.9
90°-150°	2410.4	48.3
90°-180°	2739.0	54.9
0°-180°	4990.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	745	745	745	745	745	
5°	885	746	661	746	885	92
15°	1318	713	539	713	1318	380
25°	1564	650	476	650	1564	686
35°	842	572	437	572	842	547
45°	455	469	371	469	455	360
55°	309	330	294	330	309	277
65°	201	204	208	204	201	200
75°	103	97	111	97	103	110
85°	24	20	22	20	24	29
90°	21	2	21	2	21	12
95°	86	25	86	25	86	154
105°	937	86	937	86	937	925
115°	1140	151	1140	151	1140	1108
125°	899	210	899	210	899	815
135°	729	246	729	246	729	565
145°	570	281	570	281	570	362
155°	472	319	472	319	472	220
165°	412	349	412	349	412	118
175°	371	363	371	363	371	36
180°	364	364	364	364	364	



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	790.7	790.1	788.7	789.9	787.5	784.4	784.1	781.2	772.8	772.2	770.0
5°	885.1	882.2	881.9	881.6	876.5	869.6	856.6	855.5	838.2	829.5	819.1
7.5°	1007.5	1009.0	1003.7	999.1	983.6	973.5	959.5	941.7	920.4	898.8	884.4
10°	1095.2	1107.1	1092.3	1082.2	1072.9	1055.2	1034.6	1009.0	983.4	953.4	930.7
12.5°	1189.4	1195.2	1192.3	1182.7	1168.2	1141.2	1104.8	1076.6	1052.9	1003.1	982.9
15°	1317.6	1339.6	1325.6	1293.1	1293.8	1268.2	1220.5	1168.2	1140.4	1096.6	1037.1
17.5°	1454.2	1457.0	1451.0	1423.9	1405.8	1370.6	1326.6	1276.5	1220.1	1167.3	1104.1
20°	1527.0	1524.8	1512.2	1498.1	1467.1	1439.6	1391.6	1335.7	1263.5	1211.4	1142.6
22.5°	1567.4	1563.8	1557.8	1546.1	1520.2	1490.7	1447.7	1386.5	1317.8	1246.1	1166.5
25°	1563.8	1568.5	1569.2	1565.9	1557.0	1539.3	1505.3	1456.6	1388.0	1296.0	1213.0
27.5°	1422.3	1428.9	1448.2	1465.4	1484.5	1503.9	1501.4	1477.2	1426.4	1346.9	1245.4
30°	1280.8	1266.3	1302.1	1347.2	1377.9	1432.0	1462.4	1464.1	1435.7	1367.4	1268.5
32.5°	1084.4	1100.3	1116.1	1171.6	1238.7	1299.5	1359.8	1408.4	1414.0	1368.6	1282.0
35°	842.5	862.4	891.3	920.2	992.4	1054.4	1160.6	1253.0	1326.6	1336.3	1283.3
37.5°	678.9	688.8	707.0	735.9	783.2	856.9	939.0	1055.7	1162.4	1241.8	1245.3
40°	593.4	596.3	616.9	638.9	677.2	737.8	811.9	915.1	1042.9	1153.8	1200.0
42.5°	529.3	535.7	544.4	565.6	596.1	641.7	710.5	795.9	912.9	1040.5	1130.9
45°	454.9	462.0	467.5	481.5	503.2	533.9	581.9	659.9	749.0	880.8	1002.5
47.5°	405.6	406.1	410.2	420.8	435.5	458.6	492.6	542.6	624.5	731.3	856.3
50°	370.4	376.2	377.6	385.9	397.5	414.4	442.6	485.1	552.3	646.2	761.0
52.5°	345.5	347.2	351.3	357.3	367.4	380.6	405.0	438.4	491.1	571.1	676.7
55°	309.0	309.0	313.0	317.6	323.5	335.4	351.6	376.2	416.2	478.3	565.7
57.5°	275.2	277.0	279.8	281.3	286.2	294.1	307.6	326.3	356.2	404.0	473.4
60°	252.7	255.9	255.6	258.4	262.8	268.9	280.5	295.7	322.3	360.6	419.1
62.5°	233.1	232.8	232.8	236.2	240.5	246.4	253.9	267.0	289.7	323.7	373.4
65°	200.7	200.0	202.6	204.7	206.1	210.5	216.2	227.8	243.0	268.2	306.8
67.5°	172.0	169.8	171.3	172.0	174.5	177.9	183.2	190.4	202.5	222.7	251.8
70°	152.3	150.5	150.1	150.9	153.1	155.6	159.6	166.5	177.6	193.9	215.2
72.5°	132.1	130.9	130.8	132.4	133.5	135.1	137.9	144.2	153.1	165.2	185.1
75°	103.2	103.2	103.2	103.6	104.7	106.1	108.3	111.5	118.4	127.1	140.4
77.5°	77.4	77.3	76.9	76.8	78.4	79.1	79.6	82.6	86.4	92.3	102.0
80°	60.6	58.8	59.6	60.6	61.4	61.7	62.8	63.5	66.8	70.0	76.9
82.5°	45.1	43.5	43.6	45.3	45.5	45.8	46.9	48.0	49.2	52.1	55.8
85°	23.8	23.8	24.2	24.2	24.5	24.2	25.3	25.6	25.6	27.4	29.6
87.5°	12.9	12.5	12.6	12.8	12.6	12.6	12.8	12.9	13.1	13.5	13.4
90°	21.4	22.1	21.4	20.6	21.4	19.9	19.1	18.4	17.7	18.4	16.2
92.5°	35.5	36.9	36.1	38.4	39.7	43.5	49.2	62.0	85.5	113.3	124.7
95°	85.5	88.4	93.6	100.2	114.2	140.7	179.8	265.3	354.5	437.0	389.1
97.5°	232.7	239.0	258.9	292.1	346.5	434.6	529.7	661.3	724.5	677.2	495.8
100°	462.0	461.3	490.0	543.8	618.2	722.9	809.1	868.8	843.0	697.9	471.6
102.5°	677.8	694.7	718.8	761.4	819.3	885.6	935.9	937.7	848.9	659.5	436.2
105°	937.4	941.0	964.6	992.6	1026.5	1045.7	1031.6	958.0	804.0	592.5	392.8
107.5°	1086.8	1093.5	1101.5	1111.0	1110.3	1084.1	1019.5	899.9	725.3	533.2	365.0
110°	1148.1	1149.5	1151.0	1145.1	1124.5	1072.9	980.1	844.5	675.7	499.6	354.5



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1160.5	1160.2	1154.6	1136.3	1098.5	1032.3	928.2	789.7	632.7	477.2	348.6
115°	1140.0	1136.3	1121.5	1089.1	1033.9	953.6	845.2	717.0	580.7	453.2	346.4
117.5°	1074.9	1069.8	1048.6	1011.4	953.9	872.3	775.1	664.4	549.3	439.0	347.7
120°	1020.6	1016.2	998.5	957.2	899.0	824.6	736.1	636.7	532.8	432.5	350.1
122.5°	969.9	964.3	944.8	907.7	856.0	786.8	704.9	614.9	519.2	428.5	354.1
125°	899.0	893.8	875.4	843.0	795.9	736.9	666.2	585.8	501.8	423.0	360.3
127.5°	840.7	835.9	819.3	791.5	749.6	696.0	632.1	560.5	486.5	420.4	367.4
130°	807.7	801.7	786.3	759.8	720.7	670.6	610.9	544.6	478.2	418.6	372.1
132.5°	775.2	771.1	757.4	730.8	694.2	646.4	590.9	529.8	470.6	417.9	375.7
135°	728.8	723.6	710.4	688.2	652.1	610.1	562.2	509.9	460.5	417.1	381.0
137.5°	679.8	676.4	665.2	642.7	612.4	576.0	534.7	491.8	451.9	415.5	384.6
140°	645.5	646.3	634.4	613.9	585.8	554.1	518.8	481.2	446.6	414.9	386.9
142.5°	613.7	614.4	603.8	585.5	561.7	534.1	503.4	471.2	441.9	413.7	388.6
145°	569.6	568.2	562.2	546.8	528.4	507.0	483.4	459.1	435.5	411.9	389.8
147.5°	533.4	532.8	527.2	516.7	502.8	487.6	468.5	449.2	429.3	409.2	389.8
150°	512.2	512.2	507.7	499.6	488.5	474.6	459.1	442.1	425.2	406.8	389.8
152.5°	494.5	494.5	491.8	484.3	475.6	463.9	450.3	435.6	420.5	403.8	388.0
155°	472.3	471.6	470.1	464.2	457.6	448.7	437.7	425.9	413.4	398.7	386.2
157.5°	452.1	452.3	451.1	446.7	440.9	434.0	425.5	415.6	405.5	394.1	383.6
160°	439.2	439.9	439.9	435.5	430.4	425.2	417.8	409.7	400.1	390.6	382.5
162.5°	427.4	428.1	428.1	424.3	420.9	416.3	409.5	402.7	394.8	387.0	380.1
165°	411.9	411.9	412.6	409.7	406.8	403.1	397.9	393.5	387.6	381.7	376.5
167.5°	397.2	397.2	397.9	395.9	394.5	391.9	388.9	385.5	380.7	376.5	373.1
170°	388.3	388.3	389.1	387.6	386.9	385.4	382.5	380.2	376.5	372.9	370.7
172.5°	380.1	380.7	382.0	380.5	380.4	379.5	377.1	375.5	372.4	369.9	368.9
175°	370.7	371.4	372.1	371.4	371.4	371.4	369.9	369.2	367.7	366.3	366.3
177.5°	365.2	365.2	366.4	365.8	366.4	366.4	365.8	365.2	364.6	364.0	364.6
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	768.2	765.9	763.6	759.5	756.0	751.1	749.7	748.0	742.8	738.1	734.7
5°	815.1	806.4	793.8	782.2	772.9	760.3	753.0	745.5	734.6	724.9	716.9
7.5°	864.2	847.2	827.6	806.3	786.6	767.4	752.1	738.4	723.2	708.8	697.7
10°	903.2	878.6	851.2	821.6	796.4	771.8	751.2	733.2	713.7	696.7	682.6
12.5°	947.6	911.3	873.5	837.4	807.6	773.5	748.7	725.7	703.6	683.2	667.3
15°	1000.3	954.1	909.4	859.9	814.4	771.8	742.2	713.3	687.7	666.8	646.5
17.5°	1048.2	995.9	936.9	876.8	821.9	771.4	729.9	697.3	665.2	639.6	619.4
20°	1075.3	1015.8	949.0	886.6	826.0	769.6	724.2	685.1	650.5	623.4	600.7
22.5°	1098.8	1029.1	960.0	893.2	825.7	765.0	713.5	673.4	635.7	609.3	585.1
25°	1123.0	1039.6	970.3	892.0	816.5	753.8	696.0	650.5	612.9	581.9	557.0
27.5°	1143.9	1039.0	956.7	872.4	802.3	739.3	677.7	628.9	589.0	555.3	530.0
30°	1157.7	1040.4	942.5	859.1	788.4	723.4	663.5	614.4	572.5	538.2	514.4
32.5°	1166.4	1039.5	929.5	840.7	766.5	709.0	648.2	597.4	554.3	520.7	497.7
35°	1171.4	1033.1	907.2	802.5	731.0	675.0	624.2	571.5	526.3	494.9	468.9
37.5°	1161.3	1019.8	881.2	765.6	687.4	632.4	589.5	544.6	501.4	466.8	444.4
40°	1145.4	1011.2	860.9	739.7	657.3	604.3	567.9	523.8	481.2	448.4	427.4
42.5°	1115.1	993.5	838.8	710.8	626.1	573.1	539.5	502.8	462.4	431.6	410.7
45°	1041.1	955.2	805.4	667.5	580.1	525.3	495.7	468.9	432.4	402.5	384.5
47.5°	938.4	897.5	757.1	621.8	532.1	479.3	448.5	427.0	400.3	376.2	358.8
50°	867.1	850.2	724.5	590.6	499.9	448.4	418.8	399.3	380.1	355.9	340.1
52.5°	784.8	795.2	686.4	558.3	467.3	416.6	388.7	373.2	355.9	336.0	322.2
55°	668.9	706.8	620.6	504.0	418.8	370.4	344.0	330.3	320.2	305.4	293.5
57.5°	560.4	608.6	549.3	448.0	371.0	329.3	304.1	289.1	282.6	274.8	265.5
60°	496.0	543.7	498.5	410.5	338.9	299.3	276.9	264.3	257.8	252.3	244.4
62.5°	438.6	486.7	448.8	372.3	307.5	270.7	251.2	238.8	233.8	230.9	224.1
65°	359.6	401.1	375.8	313.0	262.4	230.0	212.3	203.6	198.9	197.8	193.5
67.5°	292.7	324.2	305.9	259.6	219.8	191.7	176.7	169.4	165.8	165.4	162.1
70°	248.7	278.3	264.3	222.3	188.0	166.1	153.1	146.6	144.4	144.0	142.2
72.5°	214.6	235.3	224.1	189.2	162.7	142.7	133.1	126.3	123.9	124.4	123.2
75°	158.8	174.4	167.9	143.6	122.3	109.3	101.4	97.1	94.9	96.0	94.5
77.5°	114.3	124.1	118.3	101.5	88.4	79.0	73.1	70.5	68.5	68.4	67.8
80°	86.2	92.1	88.8	78.7	67.9	59.9	55.2	53.4	52.3	52.0	51.7
82.5°	61.5	66.4	62.5	55.6	48.3	43.5	40.8	38.5	37.6	37.8	37.5
85°	31.0	32.9	31.4	27.1	24.2	22.1	20.5	19.5	18.8	19.1	18.4
87.5°	13.5	13.3	12.1	10.6	9.7	8.4	8.1	7.3	7.0	7.3	7.4
90°	14.0	11.8	9.6	8.1	6.6	4.4	2.9	1.5	2.9	4.4	6.6
92.5°	93.6	61.9	42.6	31.7	25.5	19.8	13.6	9.1	13.6	19.8	25.5
95°	268.2	158.4	95.8	67.0	47.9	35.3	27.2	25.1	27.2	35.3	47.9
97.5°	294.4	170.5	110.7	79.6	60.7	49.9	43.5	42.7	43.5	49.9	60.7
100°	277.8	168.7	117.2	88.4	70.8	60.4	55.2	54.6	55.2	60.4	70.8
102.5°	263.6	171.1	124.8	98.5	82.6	72.8	68.2	66.9	68.2	72.8	82.6
105°	253.4	177.6	137.8	115.0	100.9	92.1	87.7	85.5	87.7	92.1	100.9
107.5°	252.8	189.6	154.8	133.6	120.4	111.7	107.4	105.2	107.4	111.7	120.4
110°	255.7	199.7	166.5	145.9	133.4	125.3	121.6	119.4	121.6	125.3	133.4





TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.6	209.7	178.9	158.9	146.4	138.3	134.6	132.3	134.6	138.3	146.4
115°	271.2	226.2	198.2	178.3	165.8	158.4	154.0	151.1	154.0	158.4	165.8
117.5°	283.9	243.7	216.0	197.7	183.6	176.8	173.1	169.8	173.1	176.8	183.6
120°	293.3	255.0	228.5	210.0	196.0	188.6	184.9	182.8	184.9	188.6	196.0
122.5°	302.1	266.7	240.8	221.2	207.8	199.8	196.1	194.0	196.1	199.8	207.8
125°	316.1	283.7	257.9	238.0	224.0	215.9	211.5	210.0	211.5	215.9	224.0
127.5°	327.6	298.4	273.5	253.6	238.2	229.9	224.4	222.3	224.4	229.9	238.2
130°	335.3	307.3	283.0	263.1	247.6	238.7	232.1	229.9	232.1	238.7	247.6
132.5°	342.3	314.9	291.2	271.9	256.5	245.8	238.7	235.8	238.7	245.8	256.5
135°	351.5	326.4	303.6	283.7	268.2	257.2	249.1	246.1	249.1	257.2	268.2
137.5°	358.3	334.4	312.5	294.0	278.7	266.9	258.9	255.8	258.9	266.9	278.7
140°	361.8	339.7	318.3	299.9	285.2	273.4	266.0	262.3	266.0	273.4	285.2
142.5°	365.3	343.8	323.0	305.9	291.1	280.5	272.5	269.4	272.5	280.5	291.1
145°	369.2	349.3	330.2	313.2	300.7	289.6	283.0	280.8	283.0	289.6	300.7
147.5°	371.6	353.7	336.2	321.7	309.6	300.1	293.6	292.3	293.6	300.1	309.6
150°	372.1	356.7	339.7	326.4	316.1	306.5	300.7	299.9	300.7	306.5	316.1
152.5°	373.3	358.4	343.8	331.1	322.1	313.6	307.7	307.6	307.7	313.6	322.1
155°	373.6	361.8	349.3	338.9	330.8	323.5	319.1	319.1	319.1	323.5	330.8
157.5°	374.4	363.7	353.7	345.7	338.8	332.3	328.8	328.2	328.8	332.3	338.8
160°	374.4	365.5	356.7	349.3	344.1	338.3	335.3	335.3	335.3	338.3	344.1
162.5°	373.7	366.1	358.4	352.2	347.7	343.0	340.6	340.6	340.6	343.0	347.7
165°	372.1	366.9	361.1	355.9	353.0	349.3	347.8	348.6	347.8	349.3	353.0
167.5°	371.0	366.8	362.6	359.3	357.2	354.5	353.7	354.6	353.7	354.5	357.2
170°	369.2	366.3	362.6	361.1	359.6	357.4	356.7	358.2	356.7	357.4	359.6
172.5°	368.6	366.3	363.2	362.2	361.4	359.8	359.6	360.5	359.6	359.8	361.4
175°	366.9	365.5	364.0	363.3	363.3	361.8	362.6	363.3	362.6	361.8	363.3
177.5°	365.8	364.6	364.0	364.0	364.0	363.4	364.0	364.6	364.0	363.4	364.0
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	732.6	730.7	727.7	723.4	719.9	714.4	714.4	715.3	715.3	715.0	714.4
5°	710.4	705.0	698.5	691.0	683.0	675.0	673.6	670.7	668.5	667.1	665.3
7.5°	686.9	677.4	667.9	657.3	647.6	639.6	634.0	629.4	626.4	623.3	620.9
10°	671.1	659.1	648.0	636.8	624.5	614.7	608.6	604.3	601.1	598.1	596.7
12.5°	652.3	638.7	626.3	615.7	602.3	592.2	586.4	584.4	580.5	574.5	571.3
15°	624.9	612.3	597.5	581.2	574.7	562.4	555.5	552.3	550.2	545.4	544.0
17.5°	601.4	584.8	568.3	556.1	544.0	534.1	530.3	526.2	523.4	519.5	518.4
20°	582.7	567.9	552.7	539.7	527.1	516.2	512.9	510.1	507.2	505.4	504.0
22.5°	563.5	548.7	536.2	524.1	510.6	503.5	499.9	496.8	494.7	493.5	492.1
25°	536.8	523.8	509.7	498.9	488.0	483.3	481.2	479.4	478.0	476.2	475.8
27.5°	512.8	498.7	487.3	477.1	469.4	465.4	463.4	462.5	462.8	463.4	463.8
30°	494.9	481.9	472.5	463.8	456.7	453.1	452.7	452.7	454.1	454.5	455.2
32.5°	478.4	467.8	458.4	450.0	444.5	442.1	443.5	443.5	444.6	445.5	446.9
35°	454.5	445.1	437.9	430.6	425.9	427.1	427.7	428.5	430.3	432.4	433.9
37.5°	431.6	423.5	415.9	410.3	408.1	410.1	411.8	413.3	415.5	417.1	418.5
40°	415.1	409.0	401.8	396.7	397.5	398.5	400.0	401.8	403.6	404.6	406.1
42.5°	399.8	393.4	388.0	383.7	384.7	386.2	387.0	388.0	390.0	392.0	392.9
45°	376.5	371.5	366.4	363.9	364.6	365.3	366.1	367.1	368.9	370.4	370.7
47.5°	350.3	346.8	343.4	340.9	342.0	341.8	342.7	345.1	345.6	346.5	348.5
50°	333.6	330.3	326.3	325.6	325.6	325.6	325.9	328.9	328.9	330.3	331.8
52.5°	315.1	313.0	310.5	309.2	308.6	308.6	310.1	311.5	312.1	314.1	315.6
55°	287.7	285.5	283.4	282.3	281.5	282.3	285.2	285.9	287.7	288.8	289.8
57.5°	259.2	257.5	255.8	255.2	255.1	256.0	257.6	259.8	260.2	263.5	265.1
60°	240.4	237.9	236.5	236.5	235.7	238.9	238.3	241.9	242.6	244.8	247.3
62.5°	221.0	217.6	217.1	217.1	218.1	219.0	220.1	221.7	223.6	226.3	228.2
65°	189.9	188.0	190.6	190.2	189.5	191.7	191.7	193.5	195.7	198.2	202.2
67.5°	160.3	159.4	159.7	159.7	160.7	161.9	163.0	164.6	167.1	169.8	172.4
70°	140.4	141.5	139.7	141.2	142.2	142.6	143.3	145.4	148.4	150.1	153.1
72.5°	121.1	121.0	121.2	121.8	122.9	123.6	124.2	126.7	129.9	131.4	133.7
75°	93.1	92.7	93.9	93.9	95.7	96.4	97.1	98.2	101.0	103.2	105.1
77.5°	68.1	68.4	68.2	69.5	69.0	69.1	71.4	72.4	72.7	77.0	77.9
80°	51.3	52.0	52.3	52.7	53.1	52.3	54.9	56.0	56.0	58.4	60.3
82.5°	36.9	37.2	38.2	38.5	38.6	39.3	39.6	40.3	41.2	42.3	44.7
85°	18.4	19.5	19.9	19.5	19.9	19.1	20.2	20.5	20.9	20.9	20.9
87.5°	7.4	8.0	8.1	8.9	9.0	9.7	9.6	9.1	9.3	10.4	9.4
90°	8.1	9.6	11.8	14.0	16.2	18.4	17.7	18.4	19.1	19.9	21.4
92.5°	31.7	42.6	61.9	93.6	124.7	113.3	85.5	62.0	49.2	43.5	39.7
95°	67.0	95.8	158.4	268.2	389.1	437.0	354.5	265.3	179.8	140.7	114.2
97.5°	79.6	110.7	170.5	294.4	495.8	677.2	724.5	661.3	529.7	434.6	346.5
100°	88.4	117.2	168.7	277.8	471.6	697.9	843.0	868.8	809.1	722.9	618.2
102.5°	98.5	124.8	171.1	263.6	436.2	659.5	848.9	937.7	935.9	885.6	819.3
105°	115.0	137.8	177.6	253.4	392.8	592.5	804.0	958.0	1031.6	1045.7	1026.5
107.5°	133.6	154.8	189.6	252.8	365.0	533.2	725.3	899.9	1019.5	1084.1	1110.3
110°	145.9	166.5	199.7	255.7	354.5	499.6	675.7	844.5	980.1	1072.9	1124.5



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	158.9	178.9	209.7	261.6	348.6	477.2	632.7	789.7	928.2	1032.3	1098.5
115°	178.3	198.2	226.2	271.2	346.4	453.2	580.7	717.0	845.2	953.6	1033.9
117.5°	197.7	216.0	243.7	283.9	347.7	439.0	549.3	664.4	775.1	872.3	953.9
120°	210.0	228.5	255.0	293.3	350.1	432.5	532.8	636.7	736.1	824.6	899.0
122.5°	221.2	240.8	266.7	302.1	354.1	428.5	519.2	614.9	704.9	786.8	856.0
125°	238.0	257.9	283.7	316.1	360.3	423.0	501.8	585.8	666.2	736.9	795.9
127.5°	253.6	273.5	298.4	327.6	367.4	420.4	486.5	560.5	632.1	696.0	749.6
130°	263.1	283.0	307.3	335.3	372.1	418.6	478.2	544.6	610.9	670.6	720.7
132.5°	271.9	291.2	314.9	342.3	375.7	417.9	470.6	529.8	590.9	646.4	694.2
135°	283.7	303.6	326.4	351.5	381.0	417.1	460.5	509.9	562.2	610.1	652.1
137.5°	294.0	312.5	334.4	358.3	384.6	415.5	451.9	491.8	534.7	576.0	612.4
140°	299.9	318.3	339.7	361.8	386.9	414.9	446.6	481.2	518.8	554.1	585.8
142.5°	305.9	323.0	343.8	365.3	388.6	413.7	441.9	471.2	503.4	534.1	561.7
145°	313.2	330.2	349.3	369.2	389.8	411.9	435.5	459.1	483.4	507.0	528.4
147.5°	321.7	336.2	353.7	371.6	389.8	409.2	429.3	449.2	468.5	487.6	502.8
150°	326.4	339.7	356.7	372.1	389.8	406.8	425.2	442.1	459.1	474.6	488.5
152.5°	331.1	343.8	358.4	373.3	388.0	403.8	420.5	435.6	450.3	463.9	475.6
155°	338.9	349.3	361.8	373.6	386.2	398.7	413.4	425.9	437.7	448.7	457.6
157.5°	345.7	353.7	363.7	374.4	383.6	394.1	405.5	415.6	425.5	434.0	440.9
160°	349.3	356.7	365.5	374.4	382.5	390.6	400.1	409.7	417.8	425.2	430.4
162.5°	352.2	358.4	366.1	373.7	380.1	387.0	394.8	402.7	409.5	416.3	420.9
165°	355.9	361.1	366.9	372.1	376.5	381.7	387.6	393.5	397.9	403.1	406.8
167.5°	359.3	362.6	366.8	371.0	373.1	376.5	380.7	385.5	388.9	391.9	394.5
170°	361.1	362.6	366.3	369.2	370.7	372.9	376.5	380.2	382.5	385.4	386.9
172.5°	362.2	363.2	366.3	368.6	368.9	369.9	372.4	375.5	377.1	379.5	380.4
175°	363.3	364.0	365.5	366.9	366.3	366.3	367.7	369.2	369.9	371.4	371.4
177.5°	364.0	364.0	364.6	365.8	364.6	364.0	364.6	365.2	365.8	366.4	366.4
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	712.5	712.2	714.2	712.8	714.2	712.2	712.5	714.4	715.0	715.3	715.3
5°	663.2	664.2	660.6	660.6	660.6	664.2	663.2	665.3	667.1	668.5	670.7
7.5°	619.3	617.6	617.8	615.9	617.8	617.6	619.3	620.9	623.3	626.4	629.4
10°	592.4	590.2	589.5	589.8	589.5	590.2	592.4	596.7	598.1	601.1	604.3
12.5°	570.1	569.7	565.0	565.1	565.0	569.7	570.1	571.3	574.5	580.5	584.4
15°	544.0	537.2	536.4	538.6	536.4	537.2	544.0	544.0	545.4	550.2	552.3
17.5°	517.8	514.2	514.4	513.3	514.4	514.2	517.8	518.4	519.5	523.4	526.2
20°	504.0	501.8	501.4	498.9	501.4	501.8	504.0	504.0	505.4	507.2	510.1
22.5°	491.3	490.5	490.7	488.0	490.7	490.5	491.3	492.1	493.5	494.7	496.8
25°	475.4	477.2	475.8	475.8	475.8	477.2	475.4	475.8	476.2	478.0	479.4
27.5°	464.8	464.7	463.9	463.9	463.9	464.7	464.8	463.8	463.4	462.8	462.5
30°	456.7	456.3	457.0	457.0	457.0	456.3	456.7	455.2	454.5	454.1	452.7
32.5°	448.6	449.0	449.2	449.5	449.2	449.0	448.6	446.9	445.5	444.6	443.5
35°	436.1	436.4	437.5	436.8	437.5	436.4	436.1	433.9	432.4	430.3	428.5
37.5°	419.1	420.8	420.5	421.0	420.5	420.8	419.1	418.5	417.1	415.5	413.3
40°	406.5	407.6	407.2	407.2	407.2	407.6	406.5	406.1	404.6	403.6	401.8
42.5°	393.5	394.3	393.3	392.8	393.3	394.3	393.5	392.9	392.0	390.0	388.0
45°	372.2	371.5	372.6	371.1	372.6	371.5	372.2	370.7	370.4	368.9	367.1
47.5°	348.4	349.1	349.4	350.4	349.4	349.1	348.4	348.5	346.5	345.6	345.1
50°	332.4	334.6	334.6	334.3	334.6	334.6	332.4	331.8	330.3	328.9	328.9
52.5°	316.9	317.9	319.3	319.2	319.3	317.9	316.9	315.6	314.1	312.1	311.5
55°	292.8	293.5	294.2	294.5	294.2	293.5	292.8	289.8	288.8	287.7	285.9
57.5°	267.8	267.5	269.2	269.8	269.2	267.5	267.8	265.1	263.5	260.2	259.8
60°	250.2	250.2	253.1	254.1	253.1	250.2	250.2	247.3	244.8	242.6	241.9
62.5°	231.4	232.5	235.4	233.9	235.4	232.5	231.4	228.2	226.3	223.6	221.7
65°	204.0	206.9	206.5	207.9	206.5	206.9	204.0	202.2	198.2	195.7	193.5
67.5°	175.3	177.1	179.7	179.9	179.7	177.1	175.3	172.4	169.8	167.1	164.6
70°	156.0	157.8	159.2	160.2	159.2	157.8	156.0	153.1	150.1	148.4	145.4
72.5°	137.1	138.1	141.6	140.1	141.6	138.1	137.1	133.7	131.4	129.9	126.7
75°	107.5	110.1	112.3	111.2	112.3	110.1	107.5	105.1	103.2	101.0	98.2
77.5°	79.6	82.1	83.1	82.2	83.1	82.1	79.6	77.9	77.0	72.7	72.4
80°	62.8	62.5	64.7	64.3	64.7	62.5	62.8	60.3	58.4	56.0	56.0
82.5°	46.1	45.7	46.8	46.9	46.8	45.7	46.1	44.7	42.3	41.2	40.3
85°	22.3	23.5	22.1	21.7	22.1	23.5	22.3	20.9	20.9	20.9	20.5
87.5°	9.3	9.4	9.3	8.9	9.3	9.4	9.3	9.4	10.4	9.3	9.1
90°	20.6	21.4	22.1	21.4	22.1	21.4	20.6	21.4	19.9	19.1	18.4
92.5°	38.4	36.1	36.9	35.5	36.9	36.1	38.4	39.7	43.5	49.2	62.0
95°	100.2	93.6	88.4	85.5	88.4	93.6	100.2	114.2	140.7	179.8	265.3
97.5°	292.1	258.9	239.0	232.7	239.0	258.9	292.1	346.5	434.6	529.7	661.3
100°	543.8	490.0	461.3	462.0	461.3	490.0	543.8	618.2	722.9	809.1	868.8
102.5°	761.4	718.8	694.7	677.8	694.7	718.8	761.4	819.3	885.6	935.9	937.7
105°	992.6	964.6	941.0	937.4	941.0	964.6	992.6	1026.5	1045.7	1031.6	958.0
107.5°	1111.0	1101.5	1093.5	1086.8	1093.5	1101.5	1111.0	1110.3	1084.1	1019.5	899.9
110°	1145.1	1151.0	1149.5	1148.1	1149.5	1151.0	1145.1	1124.5	1072.9	980.1	844.5



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1136.3	1154.6	1160.2	1160.5	1160.2	1154.6	1136.3	1098.5	1032.3	928.2	789.7
115°	1089.1	1121.5	1136.3	1140.0	1136.3	1121.5	1089.1	1033.9	953.6	845.2	717.0
117.5°	1011.4	1048.6	1069.8	1074.9	1069.8	1048.6	1011.4	953.9	872.3	775.1	664.4
120°	957.2	998.5	1016.2	1020.6	1016.2	998.5	957.2	899.0	824.6	736.1	636.7
122.5°	907.7	944.8	964.3	969.9	964.3	944.8	907.7	856.0	786.8	704.9	614.9
125°	843.0	875.4	893.8	899.0	893.8	875.4	843.0	795.9	736.9	666.2	585.8
127.5°	791.5	819.3	835.9	840.7	835.9	819.3	791.5	749.6	696.0	632.1	560.5
130°	759.8	786.3	801.7	807.7	801.7	786.3	759.8	720.7	670.6	610.9	544.6
132.5°	730.8	757.4	771.1	775.2	771.1	757.4	730.8	694.2	646.4	590.9	529.8
135°	688.2	710.4	723.6	728.8	723.6	710.4	688.2	652.1	610.1	562.2	509.9
137.5°	642.7	665.2	676.4	679.8	676.4	665.2	642.7	612.4	576.0	534.7	491.8
140°	613.9	634.4	646.3	645.5	646.3	634.4	613.9	585.8	554.1	518.8	481.2
142.5°	585.5	603.8	614.4	613.7	614.4	603.8	585.5	561.7	534.1	503.4	471.2
145°	546.8	562.2	568.2	569.6	568.2	562.2	546.8	528.4	507.0	483.4	459.1
147.5°	516.7	527.2	532.8	533.4	532.8	527.2	516.7	502.8	487.6	468.5	449.2
150°	499.6	507.7	512.2	512.2	512.2	507.7	499.6	488.5	474.6	459.1	442.1
152.5°	484.3	491.8	494.5	494.5	494.5	491.8	484.3	475.6	463.9	450.3	435.6
155°	464.2	470.1	471.6	472.3	471.6	470.1	464.2	457.6	448.7	437.7	425.9
157.5°	446.7	451.1	452.3	452.1	452.3	451.1	446.7	440.9	434.0	425.5	415.6
160°	435.5	439.9	439.9	439.2	439.9	439.9	435.5	430.4	425.2	417.8	409.7
162.5°	424.3	428.1	428.1	427.4	428.1	428.1	424.3	420.9	416.3	409.5	402.7
165°	409.7	412.6	411.9	411.9	411.9	412.6	409.7	406.8	403.1	397.9	393.5
167.5°	395.9	397.9	397.2	397.2	397.2	397.9	395.9	394.5	391.9	388.9	385.5
170°	387.6	389.1	388.3	388.3	388.3	389.1	387.6	386.9	385.4	382.5	380.2
172.5°	380.5	382.0	380.7	380.1	380.7	382.0	380.5	380.4	379.5	377.1	375.5
175°	371.4	372.1	371.4	370.7	371.4	372.1	371.4	371.4	371.4	369.9	369.2
177.5°	365.8	366.4	365.2	365.2	365.2	366.4	365.8	366.4	366.4	365.8	365.2
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	714.4	714.4	719.9	723.4	727.7	730.7	732.6	734.7	738.1	742.8	748.0
5°	673.6	675.0	683.0	691.0	698.5	705.0	710.4	716.9	724.9	734.6	745.5
7.5°	634.0	639.6	647.6	657.3	667.9	677.4	686.9	697.7	708.8	723.2	738.4
10°	608.6	614.7	624.5	636.8	648.0	659.1	671.1	682.6	696.7	713.7	733.2
12.5°	586.4	592.2	602.3	615.7	626.3	638.7	652.3	667.3	683.2	703.6	725.7
15°	555.5	562.4	574.7	581.2	597.5	612.3	624.9	646.5	666.8	687.7	713.3
17.5°	530.3	534.1	544.0	556.1	568.3	584.8	601.4	619.4	639.6	665.2	697.3
20°	512.9	516.2	527.1	539.7	552.7	567.9	582.7	600.7	623.4	650.5	685.1
22.5°	499.9	503.5	510.6	524.1	536.2	548.7	563.5	585.1	609.3	635.7	673.4
25°	481.2	483.3	488.0	498.9	509.7	523.8	536.8	557.0	581.9	612.9	650.5
27.5°	463.4	465.4	469.4	477.1	487.3	498.7	512.8	530.0	555.3	589.0	628.9
30°	452.7	453.1	456.7	463.8	472.5	481.9	494.9	514.4	538.2	572.5	614.4
32.5°	443.5	442.1	444.5	450.0	458.4	467.8	478.4	497.7	520.7	554.3	597.4
35°	427.7	427.1	425.9	430.6	437.9	445.1	454.5	468.9	494.9	526.3	571.5
37.5°	411.8	410.1	408.1	410.3	415.9	423.5	431.6	444.4	466.8	501.4	544.6
40°	400.0	398.5	397.5	396.7	401.8	409.0	415.1	427.4	448.4	481.2	523.8
42.5°	387.0	386.2	384.7	383.7	388.0	393.4	399.8	410.7	431.6	462.4	502.8
45°	366.1	365.3	364.6	363.9	366.4	371.5	376.5	384.5	402.5	432.4	468.9
47.5°	342.7	341.8	342.0	340.9	343.4	346.8	350.3	358.8	376.2	400.3	427.0
50°	325.9	325.6	325.6	325.6	326.3	330.3	333.6	340.1	355.9	380.1	399.3
52.5°	310.1	308.6	308.6	309.2	310.5	313.0	315.1	322.2	336.0	355.9	373.2
55°	285.2	282.3	281.5	282.3	283.4	285.5	287.7	293.5	305.4	320.2	330.3
57.5°	257.6	256.0	255.1	255.2	255.8	257.5	259.2	265.5	274.8	282.6	289.1
60°	238.3	238.9	235.7	236.5	236.5	237.9	240.4	244.4	252.3	257.8	264.3
62.5°	220.1	219.0	218.1	217.1	217.1	217.6	221.0	224.1	230.9	233.8	238.8
65°	191.7	191.7	189.5	190.2	190.6	188.0	189.9	193.5	197.8	198.9	203.6
67.5°	163.0	161.9	160.7	159.7	159.7	159.4	160.3	162.1	165.4	165.8	169.4
70°	143.3	142.6	142.2	141.2	139.7	141.5	140.4	142.2	144.0	144.4	146.6
72.5°	124.2	123.6	122.9	121.8	121.2	121.0	121.1	123.2	124.4	123.9	126.3
75°	97.1	96.4	95.7	93.9	93.9	92.7	93.1	94.5	96.0	94.9	97.1
77.5°	71.4	69.1	69.0	69.5	68.2	68.4	68.1	67.8	68.4	68.5	70.5
80°	54.9	52.3	53.1	52.7	52.3	52.0	51.3	51.7	52.0	52.3	53.4
82.5°	39.6	39.3	38.6	38.5	38.2	37.2	36.9	37.5	37.8	37.6	38.5
85°	20.2	19.1	19.9	19.5	19.9	19.5	18.4	18.4	19.1	18.8	19.5
87.5°	9.6	9.7	9.0	8.9	8.1	8.0	7.4	7.4	7.3	7.0	7.3
90°	17.7	18.4	16.2	14.0	11.8	9.6	8.1	6.6	4.4	2.9	1.5
92.5°	85.5	113.3	124.7	93.6	61.9	42.6	31.7	25.5	19.8	13.6	9.1
95°	354.5	437.0	389.1	268.2	158.4	95.8	67.0	47.9	35.3	27.2	25.1
97.5°	724.5	677.2	495.8	294.4	170.5	110.7	79.6	60.7	49.9	43.5	42.7
100°	843.0	697.9	471.6	277.8	168.7	117.2	88.4	70.8	60.4	55.2	54.6
102.5°	848.9	659.5	436.2	263.6	171.1	124.8	98.5	82.6	72.8	68.2	66.9
105°	804.0	592.5	392.8	253.4	177.6	137.8	115.0	100.9	92.1	87.7	85.5
107.5°	725.3	533.2	365.0	252.8	189.6	154.8	133.6	120.4	111.7	107.4	105.2
110°	675.7	499.6	354.5	255.7	199.7	166.5	145.9	133.4	125.3	121.6	119.4



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	632.7	477.2	348.6	261.6	209.7	178.9	158.9	146.4	138.3	134.6	132.3
115°	580.7	453.2	346.4	271.2	226.2	198.2	178.3	165.8	158.4	154.0	151.1
117.5°	549.3	439.0	347.7	283.9	243.7	216.0	197.7	183.6	176.8	173.1	169.8
120°	532.8	432.5	350.1	293.3	255.0	228.5	210.0	196.0	188.6	184.9	182.8
122.5°	519.2	428.5	354.1	302.1	266.7	240.8	221.2	207.8	199.8	196.1	194.0
125°	501.8	423.0	360.3	316.1	283.7	257.9	238.0	224.0	215.9	211.5	210.0
127.5°	486.5	420.4	367.4	327.6	298.4	273.5	253.6	238.2	229.9	224.4	222.3
130°	478.2	418.6	372.1	335.3	307.3	283.0	263.1	247.6	238.7	232.1	229.9
132.5°	470.6	417.9	375.7	342.3	314.9	291.2	271.9	256.5	245.8	238.7	235.8
135°	460.5	417.1	381.0	351.5	326.4	303.6	283.7	268.2	257.2	249.1	246.1
137.5°	451.9	415.5	384.6	358.3	334.4	312.5	294.0	278.7	266.9	258.9	255.8
140°	446.6	414.9	386.9	361.8	339.7	318.3	299.9	285.2	273.4	266.0	262.3
142.5°	441.9	413.7	388.6	365.3	343.8	323.0	305.9	291.1	280.5	272.5	269.4
145°	435.5	411.9	389.8	369.2	349.3	330.2	313.2	300.7	289.6	283.0	280.8
147.5°	429.3	409.2	389.8	371.6	353.7	336.2	321.7	309.6	300.1	293.6	292.3
150°	425.2	406.8	389.8	372.1	356.7	339.7	326.4	316.1	306.5	300.7	299.9
152.5°	420.5	403.8	388.0	373.3	358.4	343.8	331.1	322.1	313.6	307.7	307.6
155°	413.4	398.7	386.2	373.6	361.8	349.3	338.9	330.8	323.5	319.1	319.1
157.5°	405.5	394.1	383.6	374.4	363.7	353.7	345.7	338.8	332.3	328.8	328.2
160°	400.1	390.6	382.5	374.4	365.5	356.7	349.3	344.1	338.3	335.3	335.3
162.5°	394.8	387.0	380.1	373.7	366.1	358.4	352.2	347.7	343.0	340.6	340.6
165°	387.6	381.7	376.5	372.1	366.9	361.1	355.9	353.0	349.3	347.8	348.6
167.5°	380.7	376.5	373.1	371.0	366.8	362.6	359.3	357.2	354.5	353.7	354.6
170°	376.5	372.9	370.7	369.2	366.3	362.6	361.1	359.6	357.4	356.7	358.2
172.5°	372.4	369.9	368.9	368.6	366.3	363.2	362.2	361.4	359.8	359.6	360.5
175°	367.7	366.3	366.3	366.9	365.5	364.0	363.3	363.3	361.8	362.6	363.3
177.5°	364.6	364.0	364.6	365.8	364.6	364.0	364.0	364.0	363.4	364.0	364.6
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	749.7	751.1	756.0	759.5	763.6	765.9	768.2	770.0	772.2	772.8	781.2
5°	753.0	760.3	772.9	782.2	793.8	806.4	815.1	819.1	829.5	838.2	855.5
7.5°	752.1	767.4	786.6	806.3	827.6	847.2	864.2	884.4	898.8	920.4	941.7
10°	751.2	771.8	796.4	821.6	851.2	878.6	903.2	930.7	953.4	983.4	1009.0
12.5°	748.7	773.5	807.6	837.4	873.5	911.3	947.6	982.9	1003.1	1052.9	1076.6
15°	742.2	771.8	814.4	859.9	909.4	954.1	1000.3	1037.1	1096.6	1140.4	1168.2
17.5°	729.9	771.4	821.9	876.8	936.9	995.9	1048.2	1104.1	1167.3	1220.1	1276.5
20°	724.2	769.6	826.0	886.6	949.0	1015.8	1075.3	1142.6	1211.4	1263.5	1335.7
22.5°	713.5	765.0	825.7	893.2	960.0	1029.1	1098.8	1166.5	1246.1	1317.8	1386.5
25°	696.0	753.8	816.5	892.0	970.3	1039.6	1123.0	1213.0	1296.0	1388.0	1456.6
27.5°	677.7	739.3	802.3	872.4	956.7	1039.0	1143.9	1245.4	1346.9	1426.4	1477.2
30°	663.5	723.4	788.4	859.1	942.5	1040.4	1157.7	1268.5	1367.4	1435.7	1464.1
32.5°	648.2	709.0	766.5	840.7	929.5	1039.5	1166.4	1282.0	1368.6	1414.0	1408.4
35°	624.2	675.0	731.0	802.5	907.2	1033.1	1171.4	1283.3	1336.3	1326.6	1253.0
37.5°	589.5	632.4	687.4	765.6	881.2	1019.8	1161.3	1245.3	1241.8	1162.4	1055.7
40°	567.9	604.3	657.3	739.7	860.9	1011.2	1145.4	1200.0	1153.8	1042.9	915.1
42.5°	539.5	573.1	626.1	710.8	838.8	993.5	1115.1	1130.9	1040.5	912.9	795.9
45°	495.7	525.3	580.1	667.5	805.4	955.2	1041.1	1002.5	880.8	749.0	659.9
47.5°	448.5	479.3	532.1	621.8	757.1	897.5	938.4	856.3	731.3	624.5	542.6
50°	418.8	448.4	499.9	590.6	724.5	850.2	867.1	761.0	646.2	552.3	485.1
52.5°	388.7	416.6	467.3	558.3	686.4	795.2	784.8	676.7	571.1	491.1	438.4
55°	344.0	370.4	418.8	504.0	620.6	706.8	668.9	565.7	478.3	416.2	376.2
57.5°	304.1	329.3	371.0	448.0	549.3	608.6	560.4	473.4	404.0	356.2	326.3
60°	276.9	299.3	338.9	410.5	498.5	543.7	496.0	419.1	360.6	322.3	295.7
62.5°	251.2	270.7	307.5	372.3	448.8	486.7	438.6	373.4	323.7	289.7	267.0
65°	212.3	230.0	262.4	313.0	375.8	401.1	359.6	306.8	268.2	243.0	227.8
67.5°	176.7	191.7	219.8	259.6	305.9	324.2	292.7	251.8	222.7	202.5	190.4
70°	153.1	166.1	188.0	222.3	264.3	278.3	248.7	215.2	193.9	177.6	166.5
72.5°	133.1	142.7	162.7	189.2	224.1	235.3	214.6	185.1	165.2	153.1	144.2
75°	101.4	109.3	122.3	143.6	167.9	174.4	158.8	140.4	127.1	118.4	111.5
77.5°	73.1	79.0	88.4	101.5	118.3	124.1	114.3	102.0	92.3	86.4	82.6
80°	55.2	59.9	67.9	78.7	88.8	92.1	86.2	76.9	70.0	66.8	63.5
82.5°	40.8	43.5	48.3	55.6	62.5	66.4	61.5	55.8	52.1	49.2	48.0
85°	20.5	22.1	24.2	27.1	31.4	32.9	31.0	29.6	27.4	25.6	25.6
87.5°	8.1	8.4	9.7	10.6	12.1	13.3	13.5	13.4	13.5	13.1	12.9
90°	2.9	4.4	6.6	8.1	9.6	11.8	14.0	16.2	18.4	17.7	18.4
92.5°	13.6	19.8	25.5	31.7	42.6	61.9	93.6	124.7	113.3	85.5	62.0
95°	27.2	35.3	47.9	67.0	95.8	158.4	268.2	389.1	437.0	354.5	265.3
97.5°	43.5	49.9	60.7	79.6	110.7	170.5	294.4	495.8	677.2	724.5	661.3
100°	55.2	60.4	70.8	88.4	117.2	168.7	277.8	471.6	697.9	843.0	868.8
102.5°	68.2	72.8	82.6	98.5	124.8	171.1	263.6	436.2	659.5	848.9	937.7
105°	87.7	92.1	100.9	115.0	137.8	177.6	253.4	392.8	592.5	804.0	958.0
107.5°	107.4	111.7	120.4	133.6	154.8	189.6	252.8	365.0	533.2	725.3	899.9
110°	121.6	125.3	133.4	145.9	166.5	199.7	255.7	354.5	499.6	675.7	844.5





TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	134.6	138.3	146.4	158.9	178.9	209.7	261.6	348.6	477.2	632.7	789.7
115°	154.0	158.4	165.8	178.3	198.2	226.2	271.2	346.4	453.2	580.7	717.0
117.5°	173.1	176.8	183.6	197.7	216.0	243.7	283.9	347.7	439.0	549.3	664.4
120°	184.9	188.6	196.0	210.0	228.5	255.0	293.3	350.1	432.5	532.8	636.7
122.5°	196.1	199.8	207.8	221.2	240.8	266.7	302.1	354.1	428.5	519.2	614.9
125°	211.5	215.9	224.0	238.0	257.9	283.7	316.1	360.3	423.0	501.8	585.8
127.5°	224.4	229.9	238.2	253.6	273.5	298.4	327.6	367.4	420.4	486.5	560.5
130°	232.1	238.7	247.6	263.1	283.0	307.3	335.3	372.1	418.6	478.2	544.6
132.5°	238.7	245.8	256.5	271.9	291.2	314.9	342.3	375.7	417.9	470.6	529.8
135°	249.1	257.2	268.2	283.7	303.6	326.4	351.5	381.0	417.1	460.5	509.9
137.5°	258.9	266.9	278.7	294.0	312.5	334.4	358.3	384.6	415.5	451.9	491.8
140°	266.0	273.4	285.2	299.9	318.3	339.7	361.8	386.9	414.9	446.6	481.2
142.5°	272.5	280.5	291.1	305.9	323.0	343.8	365.3	388.6	413.7	441.9	471.2
145°	283.0	289.6	300.7	313.2	330.2	349.3	369.2	389.8	411.9	435.5	459.1
147.5°	293.6	300.1	309.6	321.7	336.2	353.7	371.6	389.8	409.2	429.3	449.2
150°	300.7	306.5	316.1	326.4	339.7	356.7	372.1	389.8	406.8	425.2	442.1
152.5°	307.7	313.6	322.1	331.1	343.8	358.4	373.3	388.0	403.8	420.5	435.6
155°	319.1	323.5	330.8	338.9	349.3	361.8	373.6	386.2	398.7	413.4	425.9
157.5°	328.8	332.3	338.8	345.7	353.7	363.7	374.4	383.6	394.1	405.5	415.6
160°	335.3	338.3	344.1	349.3	356.7	365.5	374.4	382.5	390.6	400.1	409.7
162.5°	340.6	343.0	347.7	352.2	358.4	366.1	373.7	380.1	387.0	394.8	402.7
165°	347.8	349.3	353.0	355.9	361.1	366.9	372.1	376.5	381.7	387.6	393.5
167.5°	353.7	354.5	357.2	359.3	362.6	366.8	371.0	373.1	376.5	380.7	385.5
170°	356.7	357.4	359.6	361.1	362.6	366.3	369.2	370.7	372.9	376.5	380.2
172.5°	359.6	359.8	361.4	362.2	363.2	366.3	368.6	368.9	369.9	372.4	375.5
175°	362.6	361.8	363.3	363.3	364.0	365.5	366.9	366.3	366.3	367.7	369.2
177.5°	364.0	363.4	364.0	364.0	364.0	364.6	365.8	364.6	364.0	364.6	365.2
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0	364.0



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	745.1	745.1	745.1	745.1	745.1	745.1	745.1
2.5°	784.1	784.4	787.5	789.9	788.7	790.1	790.7
5°	856.6	869.6	876.5	881.6	881.9	882.2	885.1
7.5°	959.5	973.5	983.6	999.1	1003.7	1009.0	1007.5
10°	1034.6	1055.2	1072.9	1082.2	1092.3	1107.1	1095.2
12.5°	1104.8	1141.2	1168.2	1182.7	1192.3	1195.2	1189.4
15°	1220.5	1268.2	1293.8	1293.1	1325.6	1339.6	1317.6
17.5°	1326.6	1370.6	1405.8	1423.9	1451.0	1457.0	1454.2
20°	1391.6	1439.6	1467.1	1498.1	1512.2	1524.8	1527.0
22.5°	1447.7	1490.7	1520.2	1546.1	1557.8	1563.8	1567.4
25°	1505.3	1539.3	1557.0	1565.9	1569.2	1568.5	1563.8
27.5°	1501.4	1503.9	1484.5	1465.4	1448.2	1428.9	1422.3
30°	1462.4	1432.0	1377.9	1347.2	1302.1	1266.3	1280.8
32.5°	1359.8	1299.5	1238.7	1171.6	1116.1	1100.3	1084.4
35°	1160.6	1054.4	992.4	920.2	891.3	862.4	842.5
37.5°	939.0	856.9	783.2	735.9	707.0	688.8	678.9
40°	811.9	737.8	677.2	638.9	616.9	596.3	593.4
42.5°	710.5	641.7	596.1	565.6	544.4	535.7	529.3
45°	581.9	533.9	503.2	481.5	467.5	462.0	454.9
47.5°	492.6	458.6	435.5	420.8	410.2	406.1	405.6
50°	442.6	414.4	397.5	385.9	377.6	376.2	370.4
52.5°	405.0	380.6	367.4	357.3	351.3	347.2	345.5
55°	351.6	335.4	323.5	317.6	313.0	309.0	309.0
57.5°	307.6	294.1	286.2	281.3	279.8	277.0	275.2
60°	280.5	268.9	262.8	258.4	255.6	255.9	252.7
62.5°	253.9	246.4	240.5	236.2	232.8	232.8	233.1
65°	216.2	210.5	206.1	204.7	202.6	200.0	200.7
67.5°	183.2	177.9	174.5	172.0	171.3	169.8	172.0
70°	159.6	155.6	153.1	150.9	150.1	150.5	152.3
72.5°	137.9	135.1	133.5	132.4	130.8	130.9	132.1
75°	108.3	106.1	104.7	103.6	103.2	103.2	103.2
77.5°	79.6	79.1	78.4	76.8	76.9	77.3	77.4
80°	62.8	61.7	61.4	60.6	59.6	58.8	60.6
82.5°	46.9	45.8	45.5	45.3	43.6	43.5	45.1
85°	25.3	24.2	24.5	24.2	24.2	23.8	23.8
87.5°	12.8	12.6	12.6	12.8	12.6	12.5	12.9
90°	19.1	19.9	21.4	20.6	21.4	22.1	21.4
92.5°	49.2	43.5	39.7	38.4	36.1	36.9	35.5
95°	179.8	140.7	114.2	100.2	93.6	88.4	85.5
97.5°	529.7	434.6	346.5	292.1	258.9	239.0	232.7
100°	809.1	722.9	618.2	543.8	490.0	461.3	462.0
102.5°	935.9	885.6	819.3	761.4	718.8	694.7	677.8
105°	1031.6	1045.7	1026.5	992.6	964.6	941.0	937.4
107.5°	1019.5	1084.1	1110.3	1111.0	1101.5	1093.5	1086.8
110°	980.1	1072.9	1124.5	1145.1	1151.0	1149.5	1148.1



TEST NUMBER: P331930-830

CATALOG NUMBER: S123DIP-S560D805U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	928.2	1032.3	1098.5	1136.3	1154.6	1160.2	1160.5
115°	845.2	953.6	1033.9	1089.1	1121.5	1136.3	1140.0
117.5°	775.1	872.3	953.9	1011.4	1048.6	1069.8	1074.9
120°	736.1	824.6	899.0	957.2	998.5	1016.2	1020.6
122.5°	704.9	786.8	856.0	907.7	944.8	964.3	969.9
125°	666.2	736.9	795.9	843.0	875.4	893.8	899.0
127.5°	632.1	696.0	749.6	791.5	819.3	835.9	840.7
130°	610.9	670.6	720.7	759.8	786.3	801.7	807.7
132.5°	590.9	646.4	694.2	730.8	757.4	771.1	775.2
135°	562.2	610.1	652.1	688.2	710.4	723.6	728.8
137.5°	534.7	576.0	612.4	642.7	665.2	676.4	679.8
140°	518.8	554.1	585.8	613.9	634.4	646.3	645.5
142.5°	503.4	534.1	561.7	585.5	603.8	614.4	613.7
145°	483.4	507.0	528.4	546.8	562.2	568.2	569.6
147.5°	468.5	487.6	502.8	516.7	527.2	532.8	533.4
150°	459.1	474.6	488.5	499.6	507.7	512.2	512.2
152.5°	450.3	463.9	475.6	484.3	491.8	494.5	494.5
155°	437.7	448.7	457.6	464.2	470.1	471.6	472.3
157.5°	425.5	434.0	440.9	446.7	451.1	452.3	452.1
160°	417.8	425.2	430.4	435.5	439.9	439.9	439.2
162.5°	409.5	416.3	420.9	424.3	428.1	428.1	427.4
165°	397.9	403.1	406.8	409.7	412.6	411.9	411.9
167.5°	388.9	391.9	394.5	395.9	397.9	397.2	397.2
170°	382.5	385.4	386.9	387.6	389.1	388.3	388.3
172.5°	377.1	379.5	380.4	380.5	382.0	380.7	380.1
175°	369.9	371.4	371.4	371.4	372.1	371.4	370.7
177.5°	365.8	366.4	366.4	365.8	366.4	365.2	365.2
180°	364.0	364.0	364.0	364.0	364.0	364.0	364.0

(END OF REPORT)