

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331966-830

Luminaire Tested: **S123DIP-S775D585U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331966-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D585U830-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5074.0 lumens
Efficiency: N/A
Efficacy: 125.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	96	92	89	94	90	87	84	79	76	74	68	67	65	59	58	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	64	58	62	56	52	54	50	47	46	44	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	44	39	34	39	34	31	34	30	28	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	25	22
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10962	10962	10962	10962
5°	13073	11010	9757	11010
10°	16363	10954	8813	10954
15°	20070	10866	8204	10866
20°	23909	10727	7811	10727
25°	25388	10561	7725	10561
30°	21760	10438	7764	10438
35°	15134	10264	7846	10264
40°	11398	10061	7821	10061
45°	9464	9758	7722	9758
50°	8477	9138	7651	9138
55°	7927	8473	7557	8473
60°	7436	7776	7479	7776
65°	6989	7088	7238	7088
70°	6552	6304	6892	6304
75°	5868	5519	6317	5519
80°	5139	4525	5442	4525
85°	4026	3298	3656	3298



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	2.0
10°-20°	321.7	6.3
20°-30°	539.9	10.6
30°-40°	611.3	12.0
40°-50°	548.2	10.8
50°-60°	442.4	8.7
60°-70°	308.3	6.1
70°-80°	162.0	3.2
80°-90°	41.7	0.8
90°-100°	147.8	2.9
100°-110°	418.5	8.2
110°-120°	411.7	8.1
120°-130°	328.4	6.5
130°-140°	258.9	5.1
140°-150°	193.2	3.8
150°-160°	134.7	2.7
160°-170°	79.1	1.6
170°-180°	25.7	0.5
0°-30°	961.9	19.0
0°-40°	1573.3	31.0
0°-60°	2563.9	50.5
0°-90°	3075.9	60.6
90°-120°	978.0	19.3
90°-150°	1758.5	34.7
90°-180°	1998.0	39.4
0°-180°	5074.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1018	1018	1018	1018	1018	
5°	1210	1019	903	1019	1210	125
15°	1801	975	736	975	1801	520
25°	2138	889	650	889	2138	937
35°	1152	781	597	781	1152	748
45°	622	641	507	641	622	492
55°	422	452	403	452	422	379
65°	274	278	284	278	274	273
75°	141	133	152	133	141	151
85°	33	27	30	27	33	39
90°	16	1	16	1	16	10
95°	62	18	62	18	62	112
105°	684	62	684	62	684	675
115°	832	110	832	110	832	808
125°	656	153	656	153	656	594
135°	532	180	532	180	532	412
145°	416	205	416	205	416	264
155°	345	233	345	233	345	161
165°	300	254	300	254	300	86
175°	270	265	270	265	270	26
180°	266	266	266	266	266	



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1080.8	1080.1	1078.1	1079.7	1076.5	1072.1	1071.8	1067.8	1056.3	1055.6	1052.4
5°	1209.9	1206.0	1205.5	1204.9	1198.1	1188.7	1170.9	1169.4	1145.8	1133.9	1119.6
7.5°	1377.1	1379.1	1372.0	1365.6	1344.5	1330.6	1311.5	1287.1	1258.1	1228.6	1208.9
10°	1497.1	1513.3	1493.2	1479.3	1466.5	1442.3	1414.2	1379.1	1344.2	1303.2	1272.1
12.5°	1625.8	1633.8	1629.8	1616.7	1596.8	1560.0	1510.1	1471.5	1439.3	1371.0	1343.5
15°	1801.0	1831.2	1811.9	1767.5	1768.5	1733.4	1668.3	1596.8	1558.8	1499.0	1417.7
17.5°	1987.7	1991.5	1983.3	1946.4	1921.7	1873.5	1813.4	1744.8	1667.8	1595.5	1509.2
20°	2087.3	2084.2	2067.0	2047.8	2005.4	1967.8	1902.2	1825.7	1727.0	1656.0	1561.7
22.5°	2142.5	2137.6	2129.4	2113.3	2077.9	2037.7	1978.8	1895.2	1801.3	1703.4	1594.5
25°	2137.6	2144.0	2144.9	2140.5	2128.2	2104.0	2057.7	1991.0	1897.2	1771.4	1657.9
27.5°	1944.2	1953.2	1979.6	2003.0	2029.1	2055.8	2052.2	2019.1	1949.7	1841.2	1702.3
30°	1750.7	1731.0	1779.8	1841.5	1883.5	1957.5	1998.9	2001.4	1962.4	1869.2	1733.9
32.5°	1482.2	1504.0	1525.6	1601.5	1693.2	1776.3	1858.8	1925.2	1932.8	1870.8	1752.5
35°	1151.7	1178.8	1218.3	1257.7	1356.5	1441.3	1586.4	1712.7	1813.4	1826.7	1754.2
37.5°	928.0	941.5	966.5	1006.0	1070.5	1171.2	1283.5	1443.1	1588.9	1697.4	1702.1
40°	811.2	815.2	843.3	873.4	925.7	1008.6	1109.7	1250.8	1425.5	1577.1	1640.2
42.5°	723.6	732.3	744.2	773.1	814.7	877.1	971.2	1087.8	1247.9	1422.3	1545.9
45°	621.7	631.6	639.0	658.3	687.9	729.8	795.4	902.0	1023.9	1204.0	1370.3
47.5°	554.4	555.3	560.7	575.2	595.4	626.9	673.3	741.8	853.7	999.7	1170.4
50°	506.2	514.2	516.1	527.4	543.3	566.5	604.9	663.2	755.0	883.3	1040.2
52.5°	472.3	474.7	480.2	488.4	502.2	520.3	553.6	599.3	671.3	780.6	924.9
55°	422.4	422.4	427.8	434.2	442.1	458.4	480.6	514.2	568.9	653.8	773.3
57.5°	376.2	378.6	382.5	384.5	391.2	402.0	420.5	446.0	486.8	552.1	647.1
60°	345.4	349.9	349.4	353.3	359.2	367.6	383.4	404.2	440.6	492.9	572.9
62.5°	318.6	318.3	318.2	322.9	328.9	336.9	347.0	365.0	396.1	442.4	510.5
65°	274.4	273.3	276.8	279.7	281.7	287.7	295.6	311.3	332.1	366.6	419.4
67.5°	235.1	232.2	234.1	235.1	238.5	243.1	250.4	260.2	276.7	304.4	344.2
70°	208.2	205.8	205.3	206.2	209.2	212.6	218.1	227.4	242.8	264.9	294.1
72.5°	180.6	178.9	178.8	181.0	182.4	184.6	188.5	197.1	209.2	225.9	253.1
75°	141.1	141.1	141.1	141.6	143.1	145.1	148.1	152.5	161.8	173.7	191.9
77.5°	105.8	105.7	105.1	105.0	107.2	108.1	108.8	112.9	118.1	126.1	139.4
80°	82.9	80.4	81.4	82.9	83.9	84.4	85.9	86.8	91.3	95.8	105.1
82.5°	61.5	59.5	59.7	62.0	62.2	62.7	64.2	65.5	67.2	71.3	76.3
85°	32.6	32.6	33.1	33.1	33.6	33.1	34.5	35.1	35.1	37.5	40.4
87.5°	15.0	14.2	14.6	14.9	14.6	14.7	15.0	15.4	15.6	16.1	16.2
90°	15.6	16.1	15.6	15.1	15.6	14.5	13.9	13.5	12.9	13.5	11.8
92.5°	25.9	26.9	26.3	28.0	28.9	31.8	35.9	45.2	62.4	82.7	91.0
95°	62.4	64.5	68.2	73.1	83.3	102.6	131.2	193.5	258.5	318.8	283.9
97.5°	169.8	174.4	188.9	213.1	252.8	317.1	386.4	482.5	528.6	494.1	361.7
100°	337.1	336.6	357.5	396.7	451.0	527.4	590.3	633.9	615.0	509.1	344.0
102.5°	494.5	506.8	524.3	555.4	597.7	646.1	682.8	684.2	619.3	481.2	318.3
105°	683.8	686.5	703.7	724.2	748.9	762.9	752.6	698.9	586.5	432.3	286.5
107.5°	792.9	797.8	803.6	810.5	810.0	790.9	743.9	656.5	529.1	389.0	266.4
110°	837.5	838.7	839.7	835.5	820.4	782.8	715.0	616.0	492.9	364.5	258.5



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	846.6	846.4	842.4	829.0	801.4	753.1	677.1	576.1	461.6	348.2	254.3
115°	831.7	829.0	818.2	794.6	754.2	695.7	616.6	523.1	423.7	330.6	252.7
117.5°	784.1	780.5	765.0	737.9	695.9	636.4	565.4	484.7	400.8	320.3	253.6
120°	744.6	741.3	728.5	698.3	655.9	601.5	537.1	464.5	388.7	315.6	255.3
122.5°	707.6	703.5	689.3	662.2	624.4	574.0	514.3	448.6	378.8	312.5	258.4
125°	655.9	652.1	638.7	615.0	580.6	537.6	486.0	427.3	366.1	308.6	262.9
127.5°	613.3	609.8	597.7	577.5	546.9	507.7	461.2	408.9	355.0	306.6	268.1
130°	589.2	584.9	573.6	554.3	525.8	489.2	445.6	397.3	348.9	305.4	271.5
132.5°	565.5	562.5	552.5	533.2	506.4	471.6	431.0	386.5	343.3	304.9	274.1
135°	531.7	527.9	518.2	502.1	475.8	445.2	410.2	372.0	336.0	304.3	278.0
137.5°	495.9	493.4	485.2	468.9	446.8	420.2	390.1	358.8	329.7	303.1	280.5
140°	470.9	471.5	462.9	447.8	427.3	404.3	378.4	351.1	325.7	302.7	282.2
142.5°	447.7	448.3	440.5	427.2	409.7	389.6	367.3	343.7	322.3	301.8	283.5
145°	415.6	414.5	410.2	398.9	385.5	369.9	352.7	334.9	317.7	300.5	284.4
147.5°	389.1	388.7	384.6	376.9	366.7	355.7	341.8	327.7	313.2	298.5	284.4
150°	373.6	373.6	370.4	364.5	356.5	346.2	334.9	322.5	310.2	296.7	284.4
152.5°	360.7	360.7	358.8	353.3	346.9	338.5	328.5	317.8	306.8	294.6	283.1
155°	344.6	344.0	343.0	338.7	333.8	327.4	319.3	310.8	301.6	290.9	281.7
157.5°	329.9	330.0	329.1	325.9	321.7	316.7	310.4	303.2	295.8	287.5	279.8
160°	320.4	320.9	320.9	317.7	314.0	310.2	304.8	298.9	291.9	284.9	279.0
162.5°	311.8	312.4	312.4	309.5	307.1	303.8	298.8	293.8	288.0	282.4	277.3
165°	300.5	300.5	301.0	298.9	296.7	294.1	290.3	287.1	282.8	278.5	274.8
167.5°	289.7	289.7	290.3	288.8	287.9	285.9	283.7	281.3	277.8	274.6	272.1
170°	283.3	283.3	283.9	282.8	282.2	281.2	279.0	277.4	274.8	272.0	270.4
172.5°	277.3	277.8	278.7	277.6	277.5	276.8	275.1	274.0	271.7	269.8	269.1
175°	270.4	271.0	271.5	271.0	271.0	271.0	269.8	269.4	268.2	267.2	267.2
177.5°	266.5	266.5	267.3	266.8	267.3	267.3	266.8	266.5	266.0	265.6	266.0
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1050.0	1046.9	1043.7	1038.2	1033.5	1026.7	1024.7	1022.4	1015.3	1009.0	1004.3
5°	1114.2	1102.3	1085.1	1069.3	1056.5	1039.2	1029.4	1019.0	1004.2	990.8	980.0
7.5°	1181.3	1158.0	1131.1	1102.1	1075.1	1049.0	1028.0	1009.3	988.5	968.9	953.7
10°	1234.5	1201.0	1163.6	1123.0	1088.5	1055.0	1026.8	1002.2	975.5	952.3	933.1
12.5°	1295.3	1245.7	1193.9	1144.8	1103.9	1057.3	1023.3	991.9	961.7	933.8	912.2
15°	1367.3	1304.2	1242.9	1175.4	1113.2	1055.0	1014.6	975.1	940.0	911.3	883.7
17.5°	1432.9	1361.3	1280.6	1198.4	1123.4	1054.4	997.8	953.1	909.3	874.3	846.8
20°	1470.0	1388.6	1297.2	1211.9	1129.0	1052.0	989.9	936.5	889.2	852.2	821.0
22.5°	1501.9	1406.7	1312.2	1221.0	1128.6	1045.7	975.2	920.4	869.0	832.8	799.7
25°	1535.1	1421.1	1326.3	1219.3	1116.2	1030.3	951.3	889.2	837.8	795.4	761.4
27.5°	1563.5	1420.1	1307.7	1192.5	1096.6	1010.6	926.2	859.6	805.1	759.0	724.4
30°	1582.4	1422.1	1288.4	1174.4	1077.7	988.8	906.9	839.8	782.6	735.7	703.1
32.5°	1594.3	1420.9	1270.6	1149.1	1047.6	969.1	886.0	816.5	757.7	711.6	680.2
35°	1601.2	1412.2	1240.0	1096.9	999.2	922.7	853.2	781.1	719.4	676.5	641.0
37.5°	1587.4	1393.9	1204.5	1046.6	939.6	864.3	805.8	744.4	685.4	638.1	607.6
40°	1565.7	1382.1	1176.9	1011.1	898.5	826.0	776.2	716.0	657.7	612.8	584.2
42.5°	1524.2	1358.0	1146.4	971.6	855.9	783.3	737.5	687.2	632.1	589.9	561.4
45°	1423.1	1305.6	1100.9	912.4	793.0	717.9	677.5	641.0	591.2	550.2	525.5
47.5°	1282.7	1226.8	1034.9	849.9	727.3	655.1	613.0	583.6	547.2	514.2	490.5
50°	1185.2	1162.1	990.3	807.3	683.4	612.8	572.4	545.7	519.6	486.5	464.9
52.5°	1072.7	1087.0	938.2	763.1	638.8	569.4	531.3	510.2	486.4	459.3	440.4
55°	914.4	966.1	848.2	688.8	572.4	506.2	470.2	451.5	437.7	417.5	401.1
57.5°	766.0	832.0	750.9	612.4	507.2	450.2	415.6	395.1	386.3	375.7	362.9
60°	678.0	743.1	681.5	561.0	463.4	409.1	378.4	361.2	352.3	344.9	334.0
62.5°	599.5	665.3	613.5	509.0	420.3	369.9	343.4	326.5	319.5	315.7	306.4
65°	491.4	548.2	513.7	427.8	358.7	314.3	290.1	278.3	271.9	270.4	264.5
67.5°	400.0	443.2	418.0	354.9	300.5	262.1	241.6	231.5	226.6	226.1	221.7
70°	340.0	380.4	361.2	304.0	257.1	227.0	209.2	200.3	197.4	196.9	194.4
72.5°	293.4	321.6	306.3	258.5	222.3	195.0	182.0	172.7	169.4	170.0	168.3
75°	217.1	238.4	229.4	196.4	167.3	149.5	138.6	132.7	129.8	131.3	129.3
77.5°	156.2	169.7	161.6	138.7	120.8	107.9	100.0	96.3	93.7	93.6	92.7
80°	117.9	125.8	121.4	107.5	92.7	81.9	75.5	73.0	71.5	71.1	70.6
82.5°	84.0	90.7	85.5	76.0	65.9	59.4	55.8	52.5	51.5	51.7	51.2
85°	42.4	44.9	42.9	37.0	33.1	30.1	28.1	26.7	25.6	26.1	25.2
87.5°	16.7	16.7	15.2	13.4	12.4	10.9	10.7	9.7	9.1	9.3	9.2
90°	10.2	8.6	7.0	5.9	4.8	3.2	2.2	1.0	2.2	3.2	4.8
92.5°	68.2	45.1	31.1	23.1	18.6	14.4	9.9	6.7	9.9	14.4	18.6
95°	195.7	115.6	69.8	48.9	35.0	25.8	19.9	18.3	19.9	25.8	35.0
97.5°	214.7	124.4	80.8	58.1	44.3	36.4	31.8	31.2	31.8	36.4	44.3
100°	202.6	123.1	85.5	64.5	51.7	44.1	40.3	39.8	40.3	44.1	51.7
102.5°	192.4	124.8	91.0	71.8	60.2	53.2	49.8	48.8	49.8	53.2	60.2
105°	184.9	129.6	100.6	83.9	73.6	67.2	64.0	62.4	64.0	67.2	73.6
107.5°	184.4	138.4	112.9	97.5	87.8	81.5	78.4	76.7	78.4	81.5	87.8
110°	186.5	145.7	121.5	106.4	97.3	91.4	88.7	87.1	88.7	91.4	97.3



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	190.9	153.0	130.5	115.9	106.8	100.9	98.2	96.5	98.2	100.9	106.8
115°	197.8	165.0	144.6	130.1	120.9	115.6	112.4	110.2	112.4	115.6	120.9
117.5°	207.1	177.9	157.6	144.2	133.9	129.0	126.3	123.9	126.3	129.0	133.9
120°	214.0	186.0	166.6	153.3	143.0	137.6	135.0	133.4	135.0	137.6	143.0
122.5°	220.5	194.6	175.7	161.4	151.6	145.8	143.1	141.5	143.1	145.8	151.6
125°	230.6	207.0	188.1	173.6	163.4	157.5	154.3	153.3	154.3	157.5	163.4
127.5°	239.0	217.7	199.5	185.0	173.7	167.8	163.7	162.1	163.7	167.8	173.7
130°	244.6	224.1	206.4	191.9	180.6	174.2	169.4	167.8	169.4	174.2	180.6
132.5°	249.8	229.8	212.4	198.4	187.1	179.4	174.1	172.0	174.1	179.4	187.1
135°	256.5	238.2	221.5	207.0	195.7	187.7	181.7	179.6	181.7	187.7	195.7
137.5°	261.4	243.9	227.9	214.5	203.3	194.7	188.9	186.6	188.9	194.7	203.3
140°	264.0	247.8	232.2	218.8	208.0	199.4	194.1	191.4	194.1	199.4	208.0
142.5°	266.6	250.8	235.7	223.1	212.4	204.6	198.8	196.5	198.8	204.6	212.4
145°	269.4	254.9	240.8	228.5	219.3	211.3	206.4	204.8	206.4	211.3	219.3
147.5°	271.1	258.1	245.2	234.7	225.9	219.0	214.1	213.2	214.1	219.0	225.9
150°	271.5	260.2	247.8	238.2	230.6	223.7	219.3	218.8	219.3	223.7	230.6
152.5°	272.4	261.5	250.8	241.6	235.0	228.8	224.5	224.4	224.5	228.8	235.0
155°	272.6	264.0	254.9	247.3	241.4	236.0	232.8	232.8	232.8	236.0	241.4
157.5°	273.1	265.3	258.1	252.2	247.2	242.4	239.9	239.4	239.9	242.4	247.2
160°	273.1	266.6	260.2	254.9	251.1	246.8	244.6	244.6	244.6	246.8	251.1
162.5°	272.7	267.1	261.5	256.9	253.6	250.2	248.5	248.5	248.5	250.2	253.6
165°	271.5	267.7	263.4	259.7	257.5	254.9	253.7	254.3	253.7	254.9	257.5
167.5°	270.6	267.6	264.5	262.1	260.6	258.5	258.1	258.7	258.1	258.5	260.6
170°	269.4	267.2	264.5	263.4	262.3	260.7	260.2	261.3	260.2	260.7	262.3
172.5°	268.9	267.2	264.9	264.3	263.6	262.5	262.3	263.0	262.3	262.5	263.6
175°	267.7	266.6	265.6	265.0	265.0	264.0	264.5	265.0	264.5	264.0	265.0
177.5°	266.8	266.0	265.6	265.6	265.6	265.1	265.6	266.0	265.6	265.1	265.6
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1001.5	998.7	994.8	988.8	984.1	976.6	976.6	977.8	977.8	977.4	976.6
5°	971.1	963.7	954.8	944.4	933.6	922.7	920.8	916.8	913.9	911.9	909.4
7.5°	939.1	925.9	912.9	898.4	885.2	874.3	866.7	860.4	856.3	852.0	848.9
10°	917.3	901.0	885.7	870.4	853.7	840.4	832.0	826.0	821.6	817.7	815.7
12.5°	891.6	873.0	856.1	841.6	823.2	809.5	801.5	798.8	793.5	785.2	780.9
15°	854.1	836.9	816.6	794.5	785.5	768.7	759.4	755.0	752.0	745.6	743.6
17.5°	822.1	799.5	776.7	760.2	743.7	730.1	724.8	719.3	715.4	710.1	708.6
20°	796.4	776.2	755.4	737.7	720.4	705.6	701.2	697.2	693.2	690.8	688.8
22.5°	770.3	750.2	732.9	716.3	698.0	688.2	683.4	679.1	676.3	674.7	672.7
25°	733.8	716.0	696.7	681.9	667.1	660.7	657.7	655.3	653.3	650.8	650.4
27.5°	701.0	681.6	666.0	652.2	641.6	636.2	633.4	632.2	632.6	633.5	634.0
30°	676.5	658.7	645.9	634.0	624.2	619.3	618.8	618.8	620.8	621.2	622.3
32.5°	654.0	639.4	626.6	615.1	607.7	604.3	606.1	606.1	607.8	609.0	610.8
35°	621.2	608.4	598.5	588.7	582.3	583.7	584.8	585.7	588.1	591.2	593.1
37.5°	589.9	578.8	568.5	560.8	557.9	560.5	562.9	565.0	567.9	570.1	572.1
40°	567.4	559.0	549.2	542.2	543.3	544.8	546.8	549.2	551.7	553.2	555.2
42.5°	546.5	537.7	530.3	524.5	525.9	527.8	529.0	530.3	533.1	535.7	537.0
45°	514.6	507.7	500.9	497.4	498.4	499.4	500.3	501.8	504.3	506.2	506.8
47.5°	478.8	474.0	469.4	466.0	467.6	467.2	468.4	471.6	472.4	473.6	476.4
50°	455.9	451.5	446.1	445.1	445.1	445.1	445.5	449.5	449.5	451.5	453.5
52.5°	430.6	427.8	424.3	422.5	421.8	421.8	423.9	425.8	426.6	429.4	431.4
55°	393.2	390.3	387.4	385.9	384.8	385.9	389.8	390.8	393.2	394.7	396.2
57.5°	354.3	352.0	349.7	348.8	348.6	350.0	352.1	355.1	355.7	360.2	362.5
60°	328.7	325.2	323.2	323.2	322.3	326.7	325.6	330.6	331.6	334.5	338.0
62.5°	302.2	297.6	296.7	296.7	298.1	299.4	300.8	302.9	305.6	309.2	312.0
65°	259.6	257.1	260.5	260.0	259.0	262.0	262.0	264.5	267.4	270.9	276.4
67.5°	219.1	217.9	218.2	218.2	219.7	221.4	222.7	224.9	228.5	232.1	235.6
70°	191.9	193.4	191.0	192.9	194.4	194.9	195.9	198.9	202.8	205.3	209.2
72.5°	165.5	165.4	165.7	166.5	168.0	168.8	169.8	173.2	177.6	179.6	182.8
75°	127.3	126.8	128.3	128.3	130.7	131.8	132.7	134.2	138.2	141.1	143.5
77.5°	92.9	93.6	93.2	94.9	94.3	94.4	97.5	99.0	99.3	105.2	106.5
80°	70.0	71.1	71.5	72.0	72.6	71.5	75.0	76.4	76.4	79.9	82.4
82.5°	50.3	50.9	52.2	52.7	52.8	53.8	54.1	55.1	56.4	57.9	61.1
85°	25.2	26.7	27.1	26.7	27.1	26.1	27.6	28.1	28.7	28.7	28.7
87.5°	9.0	9.7	9.6	10.4	10.3	10.9	10.8	10.2	10.3	11.6	10.2
90°	5.9	7.0	8.6	10.2	11.8	13.5	12.9	13.5	13.9	14.5	15.6
92.5°	23.1	31.1	45.1	68.2	91.0	82.7	62.4	45.2	35.9	31.8	28.9
95°	48.9	69.8	115.6	195.7	283.9	318.8	258.5	193.5	131.2	102.6	83.3
97.5°	58.1	80.8	124.4	214.7	361.7	494.1	528.6	482.5	386.4	317.1	252.8
100°	64.5	85.5	123.1	202.6	344.0	509.1	615.0	633.9	590.3	527.4	451.0
102.5°	71.8	91.0	124.8	192.4	318.3	481.2	619.3	684.2	682.8	646.1	597.7
105°	83.9	100.6	129.6	184.9	286.5	432.3	586.5	698.9	752.6	762.9	748.9
107.5°	97.5	112.9	138.4	184.4	266.4	389.0	529.1	656.5	743.9	790.9	810.0
110°	106.4	121.5	145.7	186.5	258.5	364.5	492.9	616.0	715.0	782.8	820.4



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	115.9	130.5	153.0	190.9	254.3	348.2	461.6	576.1	677.1	753.1	801.4
115°	130.1	144.6	165.0	197.8	252.7	330.6	423.7	523.1	616.6	695.7	754.2
117.5°	144.2	157.6	177.9	207.1	253.6	320.3	400.8	484.7	565.4	636.4	695.9
120°	153.3	166.6	186.0	214.0	255.3	315.6	388.7	464.5	537.1	601.5	655.9
122.5°	161.4	175.7	194.6	220.5	258.4	312.5	378.8	448.6	514.3	574.0	624.4
125°	173.6	188.1	207.0	230.6	262.9	308.6	366.1	427.3	486.0	537.6	580.6
127.5°	185.0	199.5	217.7	239.0	268.1	306.6	355.0	408.9	461.2	507.7	546.9
130°	191.9	206.4	224.1	244.6	271.5	305.4	348.9	397.3	445.6	489.2	525.8
132.5°	198.4	212.4	229.8	249.8	274.1	304.9	343.3	386.5	431.0	471.6	506.4
135°	207.0	221.5	238.2	256.5	278.0	304.3	336.0	372.0	410.2	445.2	475.8
137.5°	214.5	227.9	243.9	261.4	280.5	303.1	329.7	358.8	390.1	420.2	446.8
140°	218.8	232.2	247.8	264.0	282.2	302.7	325.7	351.1	378.4	404.3	427.3
142.5°	223.1	235.7	250.8	266.6	283.5	301.8	322.3	343.7	367.3	389.6	409.7
145°	228.5	240.8	254.9	269.4	284.4	300.5	317.7	334.9	352.7	369.9	385.5
147.5°	234.7	245.2	258.1	271.1	284.4	298.5	313.2	327.7	341.8	355.7	366.7
150°	238.2	247.8	260.2	271.5	284.4	296.7	310.2	322.5	334.9	346.2	356.5
152.5°	241.6	250.8	261.5	272.4	283.1	294.6	306.8	317.8	328.5	338.5	346.9
155°	247.3	254.9	264.0	272.6	281.7	290.9	301.6	310.8	319.3	327.4	333.8
157.5°	252.2	258.1	265.3	273.1	279.8	287.5	295.8	303.2	310.4	316.7	321.7
160°	254.9	260.2	266.6	273.1	279.0	284.9	291.9	298.9	304.8	310.2	314.0
162.5°	256.9	261.5	267.1	272.7	277.3	282.4	288.0	293.8	298.8	303.8	307.1
165°	259.7	263.4	267.7	271.5	274.8	278.5	282.8	287.1	290.3	294.1	296.7
167.5°	262.1	264.5	267.6	270.6	272.1	274.6	277.8	281.3	283.7	285.9	287.9
170°	263.4	264.5	267.2	269.4	270.4	272.0	274.8	277.4	279.0	281.2	282.2
172.5°	264.3	264.9	267.2	268.9	269.1	269.8	271.7	274.0	275.1	276.8	277.5
175°	265.0	265.6	266.6	267.7	267.2	267.2	268.2	269.4	269.8	271.0	271.0
177.5°	265.6	265.6	266.0	266.8	266.0	265.6	266.0	266.5	266.8	267.3	267.3
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	973.8	973.5	976.2	974.2	976.2	973.5	973.8	976.6	977.4	977.8	977.8
5°	906.4	908.0	903.0	903.0	903.0	908.0	906.4	909.4	911.9	913.9	916.8
7.5°	846.4	844.2	844.4	841.8	844.4	844.2	846.4	848.9	852.0	856.3	860.4
10°	809.7	806.8	805.8	806.3	805.8	806.8	809.7	815.7	817.7	821.6	826.0
12.5°	779.3	778.7	772.2	772.3	772.2	778.7	779.3	780.9	785.2	793.5	798.8
15°	743.6	734.2	733.2	736.2	733.2	734.2	743.6	743.6	745.6	752.0	755.0
17.5°	707.8	702.9	703.1	701.6	703.1	702.9	707.8	708.6	710.1	715.4	719.3
20°	688.8	685.9	685.4	681.9	685.4	685.9	688.8	688.8	690.8	693.2	697.2
22.5°	671.5	670.5	670.8	666.9	670.8	670.5	671.5	672.7	674.7	676.3	679.1
25°	649.9	652.3	650.4	650.4	650.4	652.3	649.9	650.4	650.8	653.3	655.3
27.5°	635.3	635.2	634.1	634.1	634.1	635.2	635.3	634.0	633.5	632.6	632.2
30°	624.2	623.7	624.7	624.7	624.7	623.7	624.2	622.3	621.2	620.8	618.8
32.5°	613.1	613.9	614.1	614.4	614.1	613.9	613.1	610.8	609.0	607.8	606.1
35°	596.1	596.5	598.0	597.1	598.0	596.5	596.1	593.1	591.2	588.1	585.7
37.5°	573.0	575.2	574.8	575.5	574.8	575.2	573.0	572.1	570.1	567.9	565.0
40°	555.6	557.1	556.6	556.6	556.6	557.1	555.6	555.2	553.2	551.7	549.2
42.5°	537.8	538.9	537.6	536.9	537.6	538.9	537.8	537.0	535.7	533.1	530.3
45°	508.7	507.7	509.3	507.3	509.3	507.7	508.7	506.8	506.2	504.3	501.8
47.5°	476.2	477.1	477.6	479.0	477.6	477.1	476.2	476.4	473.6	472.4	471.6
50°	454.5	457.4	457.4	456.9	457.4	457.4	454.5	453.5	451.5	449.5	449.5
52.5°	433.1	434.5	436.5	436.4	436.5	434.5	433.1	431.4	429.4	426.6	425.8
55°	400.2	401.1	402.2	402.7	402.2	401.1	400.2	396.2	394.7	393.2	390.8
57.5°	366.0	365.6	368.0	368.7	368.0	365.6	366.0	362.5	360.2	355.7	355.1
60°	342.0	342.0	345.9	347.4	345.9	342.0	342.0	338.0	334.5	331.6	330.6
62.5°	316.3	317.9	321.8	319.7	321.8	317.9	316.3	312.0	309.2	305.6	302.9
65°	278.8	282.8	282.3	284.2	282.3	282.8	278.8	276.4	270.9	267.4	264.5
67.5°	239.6	242.0	245.6	245.9	245.6	242.0	239.6	235.6	232.1	228.5	224.9
70°	213.2	215.7	217.6	219.0	217.6	215.7	213.2	209.2	205.3	202.8	198.9
72.5°	187.5	188.8	193.5	191.4	193.5	188.8	187.5	182.8	179.6	177.6	173.2
75°	147.0	150.5	153.4	151.9	153.4	150.5	147.0	143.5	141.1	138.2	134.2
77.5°	108.8	112.2	113.6	112.4	113.6	112.2	108.8	106.5	105.2	99.3	99.0
80°	85.9	85.4	88.3	87.8	88.3	85.4	85.9	82.4	79.9	76.4	76.4
82.5°	63.0	62.5	63.8	64.2	63.8	62.5	63.0	61.1	57.9	56.4	55.1
85°	30.6	32.0	30.1	29.6	30.1	32.0	30.6	28.7	28.7	28.7	28.1
87.5°	10.1	10.2	9.9	9.4	9.9	10.2	10.1	10.2	11.6	10.3	10.2
90°	15.1	15.6	16.1	15.6	16.1	15.6	15.1	15.6	14.5	13.9	13.5
92.5°	28.0	26.3	26.9	25.9	26.9	26.3	28.0	28.9	31.8	35.9	45.2
95°	73.1	68.2	64.5	62.4	64.5	68.2	73.1	83.3	102.6	131.2	193.5
97.5°	213.1	188.9	174.4	169.8	174.4	188.9	213.1	252.8	317.1	386.4	482.5
100°	396.7	357.5	336.6	337.1	336.6	357.5	396.7	451.0	527.4	590.3	633.9
102.5°	555.4	524.3	506.8	494.5	506.8	524.3	555.4	597.7	646.1	682.8	684.2
105°	724.2	703.7	686.5	683.8	686.5	703.7	724.2	748.9	762.9	752.6	698.9
107.5°	810.5	803.6	797.8	792.9	797.8	803.6	810.5	810.0	790.9	743.9	656.5
110°	835.5	839.7	838.7	837.5	838.7	839.7	835.5	820.4	782.8	715.0	616.0



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	829.0	842.4	846.4	846.6	846.4	842.4	829.0	801.4	753.1	677.1	576.1
115°	794.6	818.2	829.0	831.7	829.0	818.2	794.6	754.2	695.7	616.6	523.1
117.5°	737.9	765.0	780.5	784.1	780.5	765.0	737.9	695.9	636.4	565.4	484.7
120°	698.3	728.5	741.3	744.6	741.3	728.5	698.3	655.9	601.5	537.1	464.5
122.5°	662.2	689.3	703.5	707.6	703.5	689.3	662.2	624.4	574.0	514.3	448.6
125°	615.0	638.7	652.1	655.9	652.1	638.7	615.0	580.6	537.6	486.0	427.3
127.5°	577.5	597.7	609.8	613.3	609.8	597.7	577.5	546.9	507.7	461.2	408.9
130°	554.3	573.6	584.9	589.2	584.9	573.6	554.3	525.8	489.2	445.6	397.3
132.5°	533.2	552.5	562.5	565.5	562.5	552.5	533.2	506.4	471.6	431.0	386.5
135°	502.1	518.2	527.9	531.7	527.9	518.2	502.1	475.8	445.2	410.2	372.0
137.5°	468.9	485.2	493.4	495.9	493.4	485.2	468.9	446.8	420.2	390.1	358.8
140°	447.8	462.9	471.5	470.9	471.5	462.9	447.8	427.3	404.3	378.4	351.1
142.5°	427.2	440.5	448.3	447.7	448.3	440.5	427.2	409.7	389.6	367.3	343.7
145°	398.9	410.2	414.5	415.6	414.5	410.2	398.9	385.5	369.9	352.7	334.9
147.5°	376.9	384.6	388.7	389.1	388.7	384.6	376.9	366.7	355.7	341.8	327.7
150°	364.5	370.4	373.6	373.6	373.6	370.4	364.5	356.5	346.2	334.9	322.5
152.5°	353.3	358.8	360.7	360.7	360.7	358.8	353.3	346.9	338.5	328.5	317.8
155°	338.7	343.0	344.0	344.6	344.0	343.0	338.7	333.8	327.4	319.3	310.8
157.5°	325.9	329.1	330.0	329.9	330.0	329.1	325.9	321.7	316.7	310.4	303.2
160°	317.7	320.9	320.9	320.4	320.9	320.9	317.7	314.0	310.2	304.8	298.9
162.5°	309.5	312.4	312.4	311.8	312.4	312.4	309.5	307.1	303.8	298.8	293.8
165°	298.9	301.0	300.5	300.5	300.5	301.0	298.9	296.7	294.1	290.3	287.1
167.5°	288.8	290.3	289.7	289.7	289.7	290.3	288.8	287.9	285.9	283.7	281.3
170°	282.8	283.9	283.3	283.3	283.3	283.9	282.8	282.2	281.2	279.0	277.4
172.5°	277.6	278.7	277.8	277.3	277.8	278.7	277.6	277.5	276.8	275.1	274.0
175°	271.0	271.5	271.0	270.4	271.0	271.5	271.0	271.0	271.0	269.8	269.4
177.5°	266.8	267.3	266.5	266.5	266.5	267.3	266.8	267.3	267.3	266.8	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	976.6	976.6	984.1	988.8	994.8	998.7	1001.5	1004.3	1009.0	1015.3	1022.4
5°	920.8	922.7	933.6	944.4	954.8	963.7	971.1	980.0	990.8	1004.2	1019.0
7.5°	866.7	874.3	885.2	898.4	912.9	925.9	939.1	953.7	968.9	988.5	1009.3
10°	832.0	840.4	853.7	870.4	885.7	901.0	917.3	933.1	952.3	975.5	1002.2
12.5°	801.5	809.5	823.2	841.6	856.1	873.0	891.6	912.2	933.8	961.7	991.9
15°	759.4	768.7	785.5	794.5	816.6	836.9	854.1	883.7	911.3	940.0	975.1
17.5°	724.8	730.1	743.7	760.2	776.7	799.5	822.1	846.8	874.3	909.3	953.1
20°	701.2	705.6	720.4	737.7	755.4	776.2	796.4	821.0	852.2	889.2	936.5
22.5°	683.4	688.2	698.0	716.3	732.9	750.2	770.3	799.7	832.8	869.0	920.4
25°	657.7	660.7	667.1	681.9	696.7	716.0	733.8	761.4	795.4	837.8	889.2
27.5°	633.4	636.2	641.6	652.2	666.0	681.6	701.0	724.4	759.0	805.1	859.6
30°	618.8	619.3	624.2	634.0	645.9	658.7	676.5	703.1	735.7	782.6	839.8
32.5°	606.1	604.3	607.7	615.1	626.6	639.4	654.0	680.2	711.6	757.7	816.5
35°	584.8	583.7	582.3	588.7	598.5	608.4	621.2	641.0	676.5	719.4	781.1
37.5°	562.9	560.5	557.9	560.8	568.5	578.8	589.9	607.6	638.1	685.4	744.4
40°	546.8	544.8	543.3	542.2	549.2	559.0	567.4	584.2	612.8	657.7	716.0
42.5°	529.0	527.8	525.9	524.5	530.3	537.7	546.5	561.4	589.9	632.1	687.2
45°	500.3	499.4	498.4	497.4	500.9	507.7	514.6	525.5	550.2	591.2	641.0
47.5°	468.4	467.2	467.6	466.0	469.4	474.0	478.8	490.5	514.2	547.2	583.6
50°	445.5	445.1	445.1	445.1	446.1	451.5	455.9	464.9	486.5	519.6	545.7
52.5°	423.9	421.8	421.8	422.5	424.3	427.8	430.6	440.4	459.3	486.4	510.2
55°	389.8	385.9	384.8	385.9	387.4	390.3	393.2	401.1	417.5	437.7	451.5
57.5°	352.1	350.0	348.6	348.8	349.7	352.0	354.3	362.9	375.7	386.3	395.1
60°	325.6	326.7	322.3	323.2	323.2	325.2	328.7	334.0	344.9	352.3	361.2
62.5°	300.8	299.4	298.1	296.7	296.7	297.6	302.2	306.4	315.7	319.5	326.5
65°	262.0	262.0	259.0	260.0	260.5	257.1	259.6	264.5	270.4	271.9	278.3
67.5°	222.7	221.4	219.7	218.2	218.2	217.9	219.1	221.7	226.1	226.6	231.5
70°	195.9	194.9	194.4	192.9	191.0	193.4	191.9	194.4	196.9	197.4	200.3
72.5°	169.8	168.8	168.0	166.5	165.7	165.4	165.5	168.3	170.0	169.4	172.7
75°	132.7	131.8	130.7	128.3	128.3	126.8	127.3	129.3	131.3	129.8	132.7
77.5°	97.5	94.4	94.3	94.9	93.2	93.6	92.9	92.7	93.6	93.7	96.3
80°	75.0	71.5	72.6	72.0	71.5	71.1	70.0	70.6	71.1	71.5	73.0
82.5°	54.1	53.8	52.8	52.7	52.2	50.9	50.3	51.2	51.7	51.5	52.5
85°	27.6	26.1	27.1	26.7	27.1	26.7	25.2	25.2	26.1	25.6	26.7
87.5°	10.8	10.9	10.3	10.4	9.6	9.7	9.0	9.2	9.3	9.1	9.7
90°	12.9	13.5	11.8	10.2	8.6	7.0	5.9	4.8	3.2	2.2	1.0
92.5°	62.4	82.7	91.0	68.2	45.1	31.1	23.1	18.6	14.4	9.9	6.7
95°	258.5	318.8	283.9	195.7	115.6	69.8	48.9	35.0	25.8	19.9	18.3
97.5°	528.6	494.1	361.7	214.7	124.4	80.8	58.1	44.3	36.4	31.8	31.2
100°	615.0	509.1	344.0	202.6	123.1	85.5	64.5	51.7	44.1	40.3	39.8
102.5°	619.3	481.2	318.3	192.4	124.8	91.0	71.8	60.2	53.2	49.8	48.8
105°	586.5	432.3	286.5	184.9	129.6	100.6	83.9	73.6	67.2	64.0	62.4
107.5°	529.1	389.0	266.4	184.4	138.4	112.9	97.5	87.8	81.5	78.4	76.7
110°	492.9	364.5	258.5	186.5	145.7	121.5	106.4	97.3	91.4	88.7	87.1



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	461.6	348.2	254.3	190.9	153.0	130.5	115.9	106.8	100.9	98.2	96.5
115°	423.7	330.6	252.7	197.8	165.0	144.6	130.1	120.9	115.6	112.4	110.2
117.5°	400.8	320.3	253.6	207.1	177.9	157.6	144.2	133.9	129.0	126.3	123.9
120°	388.7	315.6	255.3	214.0	186.0	166.6	153.3	143.0	137.6	135.0	133.4
122.5°	378.8	312.5	258.4	220.5	194.6	175.7	161.4	151.6	145.8	143.1	141.5
125°	366.1	308.6	262.9	230.6	207.0	188.1	173.6	163.4	157.5	154.3	153.3
127.5°	355.0	306.6	268.1	239.0	217.7	199.5	185.0	173.7	167.8	163.7	162.1
130°	348.9	305.4	271.5	244.6	224.1	206.4	191.9	180.6	174.2	169.4	167.8
132.5°	343.3	304.9	274.1	249.8	229.8	212.4	198.4	187.1	179.4	174.1	172.0
135°	336.0	304.3	278.0	256.5	238.2	221.5	207.0	195.7	187.7	181.7	179.6
137.5°	329.7	303.1	280.5	261.4	243.9	227.9	214.5	203.3	194.7	188.9	186.6
140°	325.7	302.7	282.2	264.0	247.8	232.2	218.8	208.0	199.4	194.1	191.4
142.5°	322.3	301.8	283.5	266.6	250.8	235.7	223.1	212.4	204.6	198.8	196.5
145°	317.7	300.5	284.4	269.4	254.9	240.8	228.5	219.3	211.3	206.4	204.8
147.5°	313.2	298.5	284.4	271.1	258.1	245.2	234.7	225.9	219.0	214.1	213.2
150°	310.2	296.7	284.4	271.5	260.2	247.8	238.2	230.6	223.7	219.3	218.8
152.5°	306.8	294.6	283.1	272.4	261.5	250.8	241.6	235.0	228.8	224.5	224.4
155°	301.6	290.9	281.7	272.6	264.0	254.9	247.3	241.4	236.0	232.8	232.8
157.5°	295.8	287.5	279.8	273.1	265.3	258.1	252.2	247.2	242.4	239.9	239.4
160°	291.9	284.9	279.0	273.1	266.6	260.2	254.9	251.1	246.8	244.6	244.6
162.5°	288.0	282.4	277.3	272.7	267.1	261.5	256.9	253.6	250.2	248.5	248.5
165°	282.8	278.5	274.8	271.5	267.7	263.4	259.7	257.5	254.9	253.7	254.3
167.5°	277.8	274.6	272.1	270.6	267.6	264.5	262.1	260.6	258.5	258.1	258.7
170°	274.8	272.0	270.4	269.4	267.2	264.5	263.4	262.3	260.7	260.2	261.3
172.5°	271.7	269.8	269.1	268.9	267.2	264.9	264.3	263.6	262.5	262.3	263.0
175°	268.2	267.2	267.2	267.7	266.6	265.6	265.0	265.0	264.0	264.5	265.0
177.5°	266.0	265.6	266.0	266.8	266.0	265.6	265.6	265.6	265.1	265.6	266.0
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1024.7	1026.7	1033.5	1038.2	1043.7	1046.9	1050.0	1052.4	1055.6	1056.3	1067.8
5°	1029.4	1039.2	1056.5	1069.3	1085.1	1102.3	1114.2	1119.6	1133.9	1145.8	1169.4
7.5°	1028.0	1049.0	1075.1	1102.1	1131.1	1158.0	1181.3	1208.9	1228.6	1258.1	1287.1
10°	1026.8	1055.0	1088.5	1123.0	1163.6	1201.0	1234.5	1272.1	1303.2	1344.2	1379.1
12.5°	1023.3	1057.3	1103.9	1144.8	1193.9	1245.7	1295.3	1343.5	1371.0	1439.3	1471.5
15°	1014.6	1055.0	1113.2	1175.4	1242.9	1304.2	1367.3	1417.7	1499.0	1558.8	1596.8
17.5°	997.8	1054.4	1123.4	1198.4	1280.6	1361.3	1432.9	1509.2	1595.5	1667.8	1744.8
20°	989.9	1052.0	1129.0	1211.9	1297.2	1388.6	1470.0	1561.7	1656.0	1727.0	1825.7
22.5°	975.2	1045.7	1128.6	1221.0	1312.2	1406.7	1501.9	1594.5	1703.4	1801.3	1895.2
25°	951.3	1030.3	1116.2	1219.3	1326.3	1421.1	1535.1	1657.9	1771.4	1897.2	1991.0
27.5°	926.2	1010.6	1096.6	1192.5	1307.7	1420.1	1563.5	1702.3	1841.2	1949.7	2019.1
30°	906.9	988.8	1077.7	1174.4	1288.4	1422.1	1582.4	1733.9	1869.2	1962.4	2001.4
32.5°	886.0	969.1	1047.6	1149.1	1270.6	1420.9	1594.3	1752.5	1870.8	1932.8	1925.2
35°	853.2	922.7	999.2	1096.9	1240.0	1412.2	1601.2	1754.2	1826.7	1813.4	1712.7
37.5°	805.8	864.3	939.6	1046.6	1204.5	1393.9	1587.4	1702.1	1697.4	1588.9	1443.1
40°	776.2	826.0	898.5	1011.1	1176.9	1382.1	1565.7	1640.2	1577.1	1425.5	1250.8
42.5°	737.5	783.3	855.9	971.6	1146.4	1358.0	1524.2	1545.9	1422.3	1247.9	1087.8
45°	677.5	717.9	793.0	912.4	1100.9	1305.6	1423.1	1370.3	1204.0	1023.9	902.0
47.5°	613.0	655.1	727.3	849.9	1034.9	1226.8	1282.7	1170.4	999.7	853.7	741.8
50°	572.4	612.8	683.4	807.3	990.3	1162.1	1185.2	1040.2	883.3	755.0	663.2
52.5°	531.3	569.4	638.8	763.1	938.2	1087.0	1072.7	924.9	780.6	671.3	599.3
55°	470.2	506.2	572.4	688.8	848.2	966.1	914.4	773.3	653.8	568.9	514.2
57.5°	415.6	450.2	507.2	612.4	750.9	832.0	766.0	647.1	552.1	486.8	446.0
60°	378.4	409.1	463.4	561.0	681.5	743.1	678.0	572.9	492.9	440.6	404.2
62.5°	343.4	369.9	420.3	509.0	613.5	665.3	599.5	510.5	442.4	396.1	365.0
65°	290.1	314.3	358.7	427.8	513.7	548.2	491.4	419.4	366.6	332.1	311.3
67.5°	241.6	262.1	300.5	354.9	418.0	443.2	400.0	344.2	304.4	276.7	260.2
70°	209.2	227.0	257.1	304.0	361.2	380.4	340.0	294.1	264.9	242.8	227.4
72.5°	182.0	195.0	222.3	258.5	306.3	321.6	293.4	253.1	225.9	209.2	197.1
75°	138.6	149.5	167.3	196.4	229.4	238.4	217.1	191.9	173.7	161.8	152.5
77.5°	100.0	107.9	120.8	138.7	161.6	169.7	156.2	139.4	126.1	118.1	112.9
80°	75.5	81.9	92.7	107.5	121.4	125.8	117.9	105.1	95.8	91.3	86.8
82.5°	55.8	59.4	65.9	76.0	85.5	90.7	84.0	76.3	71.3	67.2	65.5
85°	28.1	30.1	33.1	37.0	42.9	44.9	42.4	40.4	37.5	35.1	35.1
87.5°	10.7	10.9	12.4	13.4	15.2	16.7	16.7	16.2	16.1	15.6	15.4
90°	2.2	3.2	4.8	5.9	7.0	8.6	10.2	11.8	13.5	12.9	13.5
92.5°	9.9	14.4	18.6	23.1	31.1	45.1	68.2	91.0	82.7	62.4	45.2
95°	19.9	25.8	35.0	48.9	69.8	115.6	195.7	283.9	318.8	258.5	193.5
97.5°	31.8	36.4	44.3	58.1	80.8	124.4	214.7	361.7	494.1	528.6	482.5
100°	40.3	44.1	51.7	64.5	85.5	123.1	202.6	344.0	509.1	615.0	633.9
102.5°	49.8	53.2	60.2	71.8	91.0	124.8	192.4	318.3	481.2	619.3	684.2
105°	64.0	67.2	73.6	83.9	100.6	129.6	184.9	286.5	432.3	586.5	698.9
107.5°	78.4	81.5	87.8	97.5	112.9	138.4	184.4	266.4	389.0	529.1	656.5
110°	88.7	91.4	97.3	106.4	121.5	145.7	186.5	258.5	364.5	492.9	616.0



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	98.2	100.9	106.8	115.9	130.5	153.0	190.9	254.3	348.2	461.6	576.1
115°	112.4	115.6	120.9	130.1	144.6	165.0	197.8	252.7	330.6	423.7	523.1
117.5°	126.3	129.0	133.9	144.2	157.6	177.9	207.1	253.6	320.3	400.8	484.7
120°	135.0	137.6	143.0	153.3	166.6	186.0	214.0	255.3	315.6	388.7	464.5
122.5°	143.1	145.8	151.6	161.4	175.7	194.6	220.5	258.4	312.5	378.8	448.6
125°	154.3	157.5	163.4	173.6	188.1	207.0	230.6	262.9	308.6	366.1	427.3
127.5°	163.7	167.8	173.7	185.0	199.5	217.7	239.0	268.1	306.6	355.0	408.9
130°	169.4	174.2	180.6	191.9	206.4	224.1	244.6	271.5	305.4	348.9	397.3
132.5°	174.1	179.4	187.1	198.4	212.4	229.8	249.8	274.1	304.9	343.3	386.5
135°	181.7	187.7	195.7	207.0	221.5	238.2	256.5	278.0	304.3	336.0	372.0
137.5°	188.9	194.7	203.3	214.5	227.9	243.9	261.4	280.5	303.1	329.7	358.8
140°	194.1	199.4	208.0	218.8	232.2	247.8	264.0	282.2	302.7	325.7	351.1
142.5°	198.8	204.6	212.4	223.1	235.7	250.8	266.6	283.5	301.8	322.3	343.7
145°	206.4	211.3	219.3	228.5	240.8	254.9	269.4	284.4	300.5	317.7	334.9
147.5°	214.1	219.0	225.9	234.7	245.2	258.1	271.1	284.4	298.5	313.2	327.7
150°	219.3	223.7	230.6	238.2	247.8	260.2	271.5	284.4	296.7	310.2	322.5
152.5°	224.5	228.8	235.0	241.6	250.8	261.5	272.4	283.1	294.6	306.8	317.8
155°	232.8	236.0	241.4	247.3	254.9	264.0	272.6	281.7	290.9	301.6	310.8
157.5°	239.9	242.4	247.2	252.2	258.1	265.3	273.1	279.8	287.5	295.8	303.2
160°	244.6	246.8	251.1	254.9	260.2	266.6	273.1	279.0	284.9	291.9	298.9
162.5°	248.5	250.2	253.6	256.9	261.5	267.1	272.7	277.3	282.4	288.0	293.8
165°	253.7	254.9	257.5	259.7	263.4	267.7	271.5	274.8	278.5	282.8	287.1
167.5°	258.1	258.5	260.6	262.1	264.5	267.6	270.6	272.1	274.6	277.8	281.3
170°	260.2	260.7	262.3	263.4	264.5	267.2	269.4	270.4	272.0	274.8	277.4
172.5°	262.3	262.5	263.6	264.3	264.9	267.2	268.9	269.1	269.8	271.7	274.0
175°	264.5	264.0	265.0	265.0	265.6	266.6	267.7	267.2	267.2	268.2	269.4
177.5°	265.6	265.1	265.6	265.6	265.6	266.0	266.8	266.0	265.6	266.0	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1071.8	1072.1	1076.5	1079.7	1078.1	1080.1	1080.8
5°	1170.9	1188.7	1198.1	1204.9	1205.5	1206.0	1209.9
7.5°	1311.5	1330.6	1344.5	1365.6	1372.0	1379.1	1377.1
10°	1414.2	1442.3	1466.5	1479.3	1493.2	1513.3	1497.1
12.5°	1510.1	1560.0	1596.8	1616.7	1629.8	1633.8	1625.8
15°	1668.3	1733.4	1768.5	1767.5	1811.9	1831.2	1801.0
17.5°	1813.4	1873.5	1921.7	1946.4	1983.3	1991.5	1987.7
20°	1902.2	1967.8	2005.4	2047.8	2067.0	2084.2	2087.3
22.5°	1978.8	2037.7	2077.9	2113.3	2129.4	2137.6	2142.5
25°	2057.7	2104.0	2128.2	2140.5	2144.9	2144.0	2137.6
27.5°	2052.2	2055.8	2029.1	2003.0	1979.6	1953.2	1944.2
30°	1998.9	1957.5	1883.5	1841.5	1779.8	1731.0	1750.7
32.5°	1858.8	1776.3	1693.2	1601.5	1525.6	1504.0	1482.2
35°	1586.4	1441.3	1356.5	1257.7	1218.3	1178.8	1151.7
37.5°	1283.5	1171.2	1070.5	1006.0	966.5	941.5	928.0
40°	1109.7	1008.6	925.7	873.4	843.3	815.2	811.2
42.5°	971.2	877.1	814.7	773.1	744.2	732.3	723.6
45°	795.4	729.8	687.9	658.3	639.0	631.6	621.7
47.5°	673.3	626.9	595.4	575.2	560.7	555.3	554.4
50°	604.9	566.5	543.3	527.4	516.1	514.2	506.2
52.5°	553.6	520.3	502.2	488.4	480.2	474.7	472.3
55°	480.6	458.4	442.1	434.2	427.8	422.4	422.4
57.5°	420.5	402.0	391.2	384.5	382.5	378.6	376.2
60°	383.4	367.6	359.2	353.3	349.4	349.9	345.4
62.5°	347.0	336.9	328.9	322.9	318.2	318.3	318.6
65°	295.6	287.7	281.7	279.7	276.8	273.3	274.4
67.5°	250.4	243.1	238.5	235.1	234.1	232.2	235.1
70°	218.1	212.6	209.2	206.2	205.3	205.8	208.2
72.5°	188.5	184.6	182.4	181.0	178.8	178.9	180.6
75°	148.1	145.1	143.1	141.6	141.1	141.1	141.1
77.5°	108.8	108.1	107.2	105.0	105.1	105.7	105.8
80°	85.9	84.4	83.9	82.9	81.4	80.4	82.9
82.5°	64.2	62.7	62.2	62.0	59.7	59.5	61.5
85°	34.5	33.1	33.6	33.1	33.1	32.6	32.6
87.5°	15.0	14.7	14.6	14.9	14.6	14.2	15.0
90°	13.9	14.5	15.6	15.1	15.6	16.1	15.6
92.5°	35.9	31.8	28.9	28.0	26.3	26.9	25.9
95°	131.2	102.6	83.3	73.1	68.2	64.5	62.4
97.5°	386.4	317.1	252.8	213.1	188.9	174.4	169.8
100°	590.3	527.4	451.0	396.7	357.5	336.6	337.1
102.5°	682.8	646.1	597.7	555.4	524.3	506.8	494.5
105°	752.6	762.9	748.9	724.2	703.7	686.5	683.8
107.5°	743.9	790.9	810.0	810.5	803.6	797.8	792.9
110°	715.0	782.8	820.4	835.5	839.7	838.7	837.5



TEST NUMBER: P331966-830

CATALOG NUMBER: S123DIP-S775D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	677.1	753.1	801.4	829.0	842.4	846.4	846.6
115°	616.6	695.7	754.2	794.6	818.2	829.0	831.7
117.5°	565.4	636.4	695.9	737.9	765.0	780.5	784.1
120°	537.1	601.5	655.9	698.3	728.5	741.3	744.6
122.5°	514.3	574.0	624.4	662.2	689.3	703.5	707.6
125°	486.0	537.6	580.6	615.0	638.7	652.1	655.9
127.5°	461.2	507.7	546.9	577.5	597.7	609.8	613.3
130°	445.6	489.2	525.8	554.3	573.6	584.9	589.2
132.5°	431.0	471.6	506.4	533.2	552.5	562.5	565.5
135°	410.2	445.2	475.8	502.1	518.2	527.9	531.7
137.5°	390.1	420.2	446.8	468.9	485.2	493.4	495.9
140°	378.4	404.3	427.3	447.8	462.9	471.5	470.9
142.5°	367.3	389.6	409.7	427.2	440.5	448.3	447.7
145°	352.7	369.9	385.5	398.9	410.2	414.5	415.6
147.5°	341.8	355.7	366.7	376.9	384.6	388.7	389.1
150°	334.9	346.2	356.5	364.5	370.4	373.6	373.6
152.5°	328.5	338.5	346.9	353.3	358.8	360.7	360.7
155°	319.3	327.4	333.8	338.7	343.0	344.0	344.6
157.5°	310.4	316.7	321.7	325.9	329.1	330.0	329.9
160°	304.8	310.2	314.0	317.7	320.9	320.9	320.4
162.5°	298.8	303.8	307.1	309.5	312.4	312.4	311.8
165°	290.3	294.1	296.7	298.9	301.0	300.5	300.5
167.5°	283.7	285.9	287.9	288.8	290.3	289.7	289.7
170°	279.0	281.2	282.2	282.8	283.9	283.3	283.3
172.5°	275.1	276.8	277.5	277.6	278.7	277.8	277.3
175°	269.8	271.0	271.0	271.0	271.5	271.0	270.4
177.5°	266.8	267.3	267.3	266.8	267.3	266.5	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6

(END OF REPORT)