

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332351-830

Luminaire Tested: **S123RDIP-S1000D1025U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332351-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1025U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7438.5 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332351-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332351-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	98	93	90	86	90	86	83	80	73	70	68	60	58	57	49	47	47
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34
4	75	64	56	51	69	59	53	47	51	45	41	42	38	35	35	32	30
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17
10	47	35	28	24	44	33	27	22	29	24	20	25	20	18	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17026	17026	17026
5°	17091	16855	16953
10°	16994	16644	16587
15°	16811	16254	16082
20°	16561	15767	15400
25°	16302	15221	14733
30°	15960	14589	13793
35°	15609	13958	12929
40°	15286	13212	11861
45°	14862	12478	10898
50°	14393	11643	9818
55°	13915	10689	8811
60°	13476	9666	7705
65°	12905	8560	6599
70°	12192	7188	5331
75°	11154	5656	5016
80°	9937	5009	4612
85°	8398	4434	4125



TEST NUMBER: P332351-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	2.0
10°-20°	413.3	5.6
20°-30°	595.1	8.0
30°-40°	670.3	9.0
40°-50°	641.3	8.6
50°-60°	525.1	7.1
60°-70°	354.3	4.8
70°-80°	178.2	2.4
80°-90°	50.7	0.7
90°-100°	46.0	0.6
100°-110°	219.4	2.9
110°-120°	527.0	7.1
120°-130°	671.1	9.0
130°-140°	717.1	9.6
140°-150°	670.6	9.0
150°-160°	540.9	7.3
160°-170°	349.1	4.7
170°-180°	120.3	1.6
0°-30°	1156.9	15.6
0°-40°	1827.2	24.6
0°-60°	2993.6	40.2
0°-90°	3576.8	48.1
90°-120°	792.5	10.7
90°-150°	2851.3	38.3
90°-180°	3862.0	51.9
0°-180°	7438.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1582	1582	1582	1582	1582	
5°	1582	1575	1560	1571	1569	150
15°	1509	1493	1459	1452	1443	425
25°	1373	1339	1282	1255	1240	631
35°	1188	1140	1062	1009	984	743
45°	976	916	820	749	716	753
55°	742	676	570	498	470	665
65°	507	435	336	276	259	501
75°	268	206	136	124	121	286
85°	68	41	36	34	33	76
90°	1	10	23	26	28	6
95°	57	22	29	35	36	71
105°	280	285	206	49	41	297
115°	526	532	540	549	553	519
125°	741	749	753	754	756	662
135°	923	928	932	935	932	710
145°	1065	1071	1074	1075	1075	666
155°	1173	1171	1172	1176	1171	540
165°	1237	1234	1233	1240	1234	349
175°	1266	1262	1262	1268	1262	120
180°	1266	1266	1266	1266	1266	



TEST NUMBER: P332351-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1586.9	1585.9	1585.1	1584.1	1583.2	1581.4	1578.7	1575.9	1573.2	1570.5	1572.9
5°	1581.8	1580.3	1578.9	1577.4	1576.0	1573.6	1570.2	1566.8	1563.4	1559.9	1562.5
7.5°	1567.1	1565.6	1564.1	1562.5	1560.9	1557.9	1553.5	1549.1	1544.6	1540.2	1541.6
10°	1554.8	1552.8	1550.8	1548.8	1546.8	1543.2	1538.1	1533.0	1527.9	1522.8	1523.1
12.5°	1537.4	1535.1	1533.0	1530.7	1528.4	1524.2	1518.0	1511.6	1505.4	1499.1	1498.9
15°	1508.6	1505.5	1502.3	1499.2	1496.1	1490.5	1482.5	1474.5	1466.6	1458.6	1457.2
17.5°	1472.4	1468.8	1465.2	1461.5	1457.8	1451.0	1440.8	1430.7	1420.5	1410.3	1407.3
20°	1445.8	1441.2	1436.6	1432.1	1427.5	1419.8	1409.0	1398.2	1387.3	1376.5	1372.8
22.5°	1416.0	1410.8	1405.5	1400.2	1395.1	1386.7	1375.1	1363.6	1352.1	1340.6	1336.0
25°	1372.6	1365.6	1358.4	1351.2	1344.2	1334.0	1320.9	1307.8	1294.7	1281.6	1275.5
27.5°	1320.0	1312.2	1304.3	1296.5	1288.5	1277.3	1262.7	1248.1	1233.5	1219.0	1210.6
30°	1284.1	1275.5	1267.1	1258.5	1249.9	1237.7	1221.7	1205.7	1189.8	1173.8	1164.1
32.5°	1248.2	1238.5	1228.8	1219.1	1209.5	1196.2	1179.3	1162.4	1145.5	1128.6	1118.0
35°	1187.9	1177.6	1167.3	1157.2	1146.9	1132.8	1115.2	1097.5	1079.9	1062.2	1049.9
37.5°	1126.8	1115.4	1104.0	1092.6	1081.2	1066.1	1047.3	1028.3	1009.5	990.6	976.7
40°	1087.9	1075.3	1062.7	1050.2	1037.6	1021.2	1001.1	980.8	960.5	940.3	925.5
42.5°	1043.7	1031.1	1018.6	1006.1	993.5	976.9	955.9	935.0	914.1	893.2	876.9
45°	976.3	963.4	950.6	937.7	924.9	907.6	885.6	863.7	841.7	819.7	803.5
47.5°	908.8	894.7	880.6	866.5	852.4	834.4	812.5	790.5	768.5	746.6	729.0
50°	859.5	846.1	832.7	819.4	805.9	787.7	764.6	741.5	718.4	695.3	677.6
52.5°	815.4	800.9	786.3	771.8	757.2	738.5	715.7	692.8	670.0	647.1	628.7
55°	741.5	727.5	713.5	699.6	685.6	666.5	642.2	618.0	593.8	569.6	553.1
57.5°	673.3	658.0	642.8	627.5	612.4	592.6	568.2	543.8	519.5	495.2	479.6
60°	626.0	610.4	594.7	579.0	563.3	543.7	520.0	496.3	472.7	449.0	433.6
62.5°	578.8	563.2	547.4	531.8	516.1	496.4	472.8	449.1	425.5	401.8	387.3
65°	506.7	491.1	475.3	459.7	444.0	425.1	402.8	380.6	358.4	336.1	322.2
67.5°	434.6	418.8	402.9	387.1	371.3	352.6	331.3	310.0	288.7	267.3	256.9
70°	387.4	372.0	356.7	341.2	325.8	308.2	288.2	268.2	248.3	228.4	218.4
72.5°	340.2	325.1	309.9	294.7	279.6	262.9	244.8	226.7	208.5	190.4	182.2
75°	268.2	254.4	240.7	227.1	213.4	198.7	183.0	167.3	151.7	136.0	133.1
77.5°	202.5	190.0	177.7	165.3	153.0	141.7	131.6	121.5	111.4	101.3	99.8
80°	160.3	148.6	137.0	125.3	113.6	104.8	98.8	92.7	86.8	80.8	79.9
82.5°	120.4	110.3	100.2	90.0	79.9	73.5	70.7	68.0	65.1	62.3	61.5
85°	68.0	61.7	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.8	22.7	20.6	18.6	16.5	15.6	16.2	16.8	17.3	17.8	17.8
90°	0.9	3.0	5.1	7.3	9.3	11.7	14.4	17.2	19.9	22.6	23.4
92.5°	17.5	16.9	16.3	15.7	15.2	15.9	17.9	20.0	22.1	24.1	25.4
95°	57.4	48.8	40.2	31.7	23.1	20.0	22.2	24.6	26.9	29.1	30.6
97.5°	115.4	111.5	107.6	103.8	99.9	90.5	75.5	60.4	45.3	30.3	32.0
100°	159.0	163.2	167.4	171.5	175.7	161.5	128.8	96.2	63.6	31.0	32.7
102.5°	208.7	211.7	214.7	217.7	220.7	204.4	168.8	133.2	97.6	61.9	56.7
105°	280.3	282.7	284.9	287.3	289.5	281.3	262.5	243.6	224.9	206.0	169.0
107.5°	356.0	357.9	359.7	361.6	363.4	365.8	368.7	371.7	374.7	377.7	350.5
110°	406.4	408.1	409.7	411.4	413.1	415.1	417.4	419.7	422.0	424.3	417.4



TEST NUMBER: P332351-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	454.6	456.1	457.6	459.1	460.6	462.5	464.9	467.1	469.4	471.7	471.8
115°	525.9	527.2	528.4	529.7	530.9	532.5	534.3	536.2	538.1	540.0	542.2
117.5°	594.9	596.5	598.0	599.6	601.2	602.4	603.3	604.4	605.3	606.2	607.9
120°	637.8	639.7	641.6	643.5	645.4	646.7	647.2	647.9	648.6	649.1	650.8
122.5°	681.6	683.1	684.6	686.2	687.7	688.9	689.7	690.5	691.3	692.0	693.2
125°	741.3	743.0	744.7	746.4	748.0	749.3	750.2	750.9	751.8	752.6	753.1
127.5°	799.3	801.0	802.7	804.3	806.0	807.3	808.3	809.4	810.3	811.3	812.0
130°	835.5	837.1	838.8	840.5	842.2	843.4	844.2	845.1	845.8	846.7	847.5
132.5°	870.1	871.8	873.4	875.1	876.8	877.9	878.5	879.2	880.0	880.6	881.5
135°	922.9	924.2	925.4	926.7	927.9	929.0	929.8	930.7	931.5	932.4	932.9
137.5°	968.1	969.7	971.3	972.9	974.4	975.4	975.9	976.4	976.9	977.3	978.3
140°	998.2	999.5	1000.7	1001.9	1003.2	1004.2	1004.8	1005.4	1006.1	1006.6	1007.5
142.5°	1026.1	1027.3	1028.5	1029.8	1031.0	1032.0	1032.6	1033.2	1033.9	1034.5	1035.2
145°	1065.0	1066.5	1067.9	1069.4	1070.8	1071.8	1072.2	1072.6	1073.0	1073.5	1073.8
147.5°	1101.6	1102.7	1103.6	1104.6	1105.5	1106.2	1106.6	1107.0	1107.5	1107.9	1108.3
150°	1124.3	1124.9	1125.5	1126.1	1126.7	1127.3	1127.7	1128.1	1128.5	1129.0	1129.4
152.5°	1144.5	1144.9	1145.2	1145.5	1145.8	1146.0	1146.2	1146.5	1146.8	1147.0	1147.7
155°	1173.2	1172.7	1172.3	1172.0	1171.5	1171.4	1171.6	1171.8	1172.1	1172.2	1173.3
157.5°	1195.3	1195.3	1195.3	1195.2	1195.2	1195.0	1194.9	1194.7	1194.5	1194.2	1195.5
160°	1208.9	1208.7	1208.5	1208.3	1208.1	1207.9	1207.7	1207.5	1207.2	1207.0	1208.3
162.5°	1221.7	1221.2	1220.6	1220.1	1219.6	1219.2	1219.0	1218.7	1218.5	1218.3	1219.7
165°	1237.2	1236.5	1235.9	1235.3	1234.6	1234.3	1234.0	1233.8	1233.6	1233.4	1235.0
167.5°	1249.2	1248.4	1247.5	1246.7	1245.9	1245.4	1245.4	1245.4	1245.4	1245.4	1247.1
170°	1255.9	1255.1	1254.3	1253.5	1252.6	1252.2	1252.2	1252.2	1252.2	1252.2	1253.9
172.5°	1260.5	1259.5	1258.5	1257.4	1256.5	1256.0	1256.2	1256.4	1256.5	1256.7	1258.4
175°	1266.3	1265.3	1264.2	1263.2	1262.2	1261.7	1261.9	1262.2	1262.3	1262.5	1264.0
177.5°	1267.8	1267.0	1266.1	1265.3	1264.5	1264.1	1264.3	1264.5	1264.6	1264.8	1266.1
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3



TEST NUMBER: P332351-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1575.5	1578.0	1580.5	1581.5	1581.0	1580.6	1580.2	1579.7
5°	1565.1	1567.6	1570.2	1571.2	1570.7	1570.1	1569.5	1569.0
7.5°	1543.0	1544.5	1545.9	1546.1	1545.1	1544.2	1543.2	1542.2
10°	1523.3	1523.6	1523.9	1523.3	1521.8	1520.4	1519.0	1517.6
12.5°	1498.7	1498.6	1498.5	1497.5	1495.9	1494.2	1492.6	1490.9
15°	1455.8	1454.3	1452.9	1451.1	1449.2	1447.2	1445.2	1443.2
17.5°	1404.3	1401.3	1398.3	1395.2	1392.3	1389.3	1386.4	1383.4
20°	1369.0	1365.4	1361.7	1358.1	1354.7	1351.2	1347.8	1344.4
22.5°	1331.3	1326.7	1322.1	1318.1	1315.0	1311.8	1308.6	1305.4
25°	1269.6	1263.6	1257.6	1253.0	1249.9	1246.8	1243.7	1240.5
27.5°	1202.3	1194.0	1185.6	1179.1	1174.3	1169.5	1164.7	1160.0
30°	1154.4	1144.7	1135.0	1127.9	1123.3	1118.8	1114.2	1109.7
32.5°	1107.4	1096.8	1086.2	1078.6	1073.7	1068.9	1064.1	1059.3
35°	1037.6	1025.4	1013.1	1004.5	999.4	994.2	989.1	983.9
37.5°	962.8	948.9	935.0	924.8	918.5	912.2	905.9	899.6
40°	910.7	895.9	881.0	870.3	863.7	857.2	850.6	844.1
42.5°	860.7	844.5	828.3	817.3	811.4	805.6	799.7	793.8
45°	787.2	771.0	754.7	743.2	736.3	729.5	722.6	715.9
47.5°	711.2	693.6	675.9	664.0	657.9	651.9	645.7	639.6
50°	660.0	642.2	624.6	612.5	606.0	599.4	592.9	586.3
52.5°	610.4	592.0	573.6	561.5	555.6	549.8	543.9	538.0
55°	536.5	520.0	503.4	492.3	486.6	480.9	475.2	469.5
57.5°	463.9	448.3	432.7	422.4	417.6	412.7	407.9	403.0
60°	418.2	402.8	387.4	377.3	372.5	367.6	362.8	357.9
62.5°	372.8	358.4	343.8	334.0	329.0	324.0	318.9	313.8
65°	308.2	294.2	280.2	271.6	268.5	265.4	262.3	259.1
67.5°	246.5	236.0	225.6	218.7	215.4	212.0	208.6	205.3
70°	208.4	198.4	188.4	181.9	178.7	175.6	172.5	169.4
72.5°	174.1	165.9	157.8	153.1	151.7	150.4	149.1	147.8
75°	130.3	127.4	124.6	122.9	122.3	121.7	121.1	120.6
77.5°	98.3	96.7	95.2	94.2	93.6	93.0	92.5	91.9
80°	79.1	78.2	77.4	76.7	76.2	75.6	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.2	58.1	58.0
85°	34.8	34.2	33.6	33.4	33.4	33.4	33.4	33.4
87.5°	17.7	17.7	17.6	17.5	17.3	17.2	17.1	17.0
90°	24.2	25.1	25.9	26.6	27.0	27.4	27.8	28.2
92.5°	26.8	28.1	29.4	30.3	30.4	30.7	31.0	31.2
95°	32.0	33.6	35.1	35.7	35.7	35.7	35.7	35.7
97.5°	33.6	35.3	36.9	37.9	38.2	38.4	38.5	38.7
100°	34.4	36.1	37.7	38.6	38.9	39.1	39.3	39.5
102.5°	51.6	46.4	41.2	38.7	39.1	39.5	39.9	40.2
105°	132.1	95.0	58.1	39.7	40.2	40.5	41.0	41.4
107.5°	323.4	296.2	269.1	241.6	213.7	185.8	157.9	130.0
110°	410.5	403.6	396.7	378.3	348.4	318.5	288.6	258.7



TEST NUMBER: P332351-830

CATALOG NUMBER: S123RDIP-S1000D1025U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	471.9	472.1	472.2	469.1	462.8	456.5	450.2	443.8
115°	544.2	546.3	548.4	549.9	550.6	551.5	552.3	553.2
117.5°	609.6	611.2	612.9	613.9	614.1	614.2	614.3	614.5
120°	652.5	654.1	655.8	656.7	656.7	656.7	656.7	656.7
122.5°	694.4	695.6	696.7	697.4	697.6	697.8	697.9	698.0
125°	753.5	753.8	754.3	754.7	755.2	755.5	756.0	756.4
127.5°	812.7	813.3	814.0	814.2	813.7	813.3	812.8	812.5
130°	848.4	849.2	850.1	850.3	849.9	849.4	849.0	848.6
132.5°	882.2	883.1	883.9	884.0	883.4	882.9	882.3	881.7
135°	933.6	934.2	934.8	934.8	934.2	933.6	932.9	932.4
137.5°	979.3	980.3	981.3	981.6	981.2	980.8	980.3	980.0
140°	1008.3	1009.2	1010.0	1010.2	1009.7	1009.4	1009.0	1008.5
142.5°	1035.9	1036.5	1037.2	1037.2	1036.6	1036.0	1035.5	1034.9
145°	1074.3	1074.7	1075.2	1075.3	1075.3	1075.3	1075.3	1075.3
147.5°	1108.7	1109.1	1109.6	1109.3	1108.3	1107.4	1106.4	1105.4
150°	1129.8	1130.2	1130.7	1130.5	1129.9	1129.3	1128.6	1128.0
152.5°	1148.5	1149.2	1150.0	1149.9	1149.0	1148.0	1147.1	1146.0
155°	1174.3	1175.4	1176.4	1176.3	1175.1	1173.8	1172.5	1171.3
157.5°	1196.7	1198.0	1199.3	1199.1	1197.4	1195.8	1194.2	1192.6
160°	1209.6	1210.8	1212.0	1211.9	1210.5	1209.0	1207.6	1206.1
162.5°	1221.2	1222.6	1224.0	1224.1	1222.8	1221.4	1220.2	1218.9
165°	1236.7	1238.4	1240.1	1240.2	1238.7	1237.3	1235.8	1234.4
167.5°	1248.8	1250.5	1252.1	1252.1	1250.5	1248.8	1247.1	1245.4
170°	1255.6	1257.3	1258.9	1258.9	1257.3	1255.6	1253.9	1252.2
172.5°	1260.1	1261.7	1263.4	1263.3	1261.5	1259.6	1257.8	1255.9
175°	1265.5	1267.0	1268.4	1268.3	1266.6	1265.0	1263.3	1261.6
177.5°	1267.4	1268.9	1270.2	1270.0	1268.3	1266.7	1265.0	1263.3
180°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3

(END OF REPORT)