

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332334-830

Luminaire Tested: **S123RDIP-S1000D365U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332334-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D365U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4749.3 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332334-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332334-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75					75			
1	104	100	96	92	99	95	92	89	86	84	81	78	76	74	71	69	68	64					64			
2	95	88	81	76	90	84	78	73	76	72	68	69	66	63	63	60	58	55					55			
3	87	77	70	64	83	74	67	62	68	62	58	62	57	54	56	53	50	47					47			
4	80	69	61	55	76	66	59	53	61	55	50	55	51	47	51	47	43	41					41			
5	74	62	54	47	70	59	52	46	54	48	43	50	45	41	46	42	38	36					36			
6	68	56	48	42	65	54	46	40	49	43	38	45	40	36	42	37	34	31					31			
7	63	51	43	37	60	49	41	36	45	39	34	42	36	32	38	34	30	28					28			
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	35	31	27	25					25			
9	55	42	35	30	52	41	34	29	38	32	28	35	30	26	33	28	25	23					23			
10	52	39	32	27	49	38	31	26	35	29	25	33	27	24	30	26	23	21					21			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17026	17026	17026
5°	17091	16855	16953
10°	16994	16644	16587
15°	16811	16254	16082
20°	16561	15767	15400
25°	16302	15221	14733
30°	15960	14589	13793
35°	15609	13958	12929
40°	15286	13212	11861
45°	14862	12478	10898
50°	14393	11643	9818
55°	13915	10689	8811
60°	13476	9666	7705
65°	12905	8560	6599
70°	12192	7188	5331
75°	11154	5656	5016
80°	9937	5009	4612
85°	8398	4434	4125



TEST NUMBER: P332334-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	3.1
10°-20°	413.3	8.7
20°-30°	595.1	12.5
30°-40°	670.3	14.1
40°-50°	641.3	13.5
50°-60°	525.1	11.1
60°-70°	354.3	7.5
70°-80°	178.2	3.8
80°-90°	48.4	1.0
90°-100°	27.6	0.6
100°-110°	82.7	1.7
110°-120°	140.6	3.0
120°-130°	185.0	3.9
130°-140°	207.9	4.4
140°-150°	204.4	4.3
150°-160°	172.0	3.6
160°-170°	114.5	2.4
170°-180°	40.1	0.8
0°-30°	1156.9	24.4
0°-40°	1827.2	38.5
0°-60°	2993.6	63.0
0°-90°	3574.5	75.3
90°-120°	250.9	5.3
90°-150°	848.1	17.9
90°-180°	1175.0	24.7
0°-180°	4749.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1582	1582	1582	1582	1582	
5°	1582	1575	1560	1571	1569	150
15°	1509	1493	1459	1452	1443	425
25°	1373	1339	1282	1255	1240	631
35°	1188	1140	1062	1009	984	743
45°	976	916	820	749	716	753
55°	742	676	570	498	470	665
65°	507	435	336	276	259	501
75°	268	206	136	124	121	286
85°	68	41	36	34	33	76
90°	0	4	8	9	10	5
95°	20	22	25	26	26	22
105°	75	76	79	79	79	80
115°	142	142	142	142	142	140
125°	207	208	208	206	205	185
135°	269	271	270	269	268	207
145°	326	327	328	327	326	204
155°	373	373	374	375	373	172
165°	407	406	406	408	405	115
175°	423	422	422	423	421	40
180°	424	424	424	424	424	



TEST NUMBER: P332334-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1586.9	1585.9	1585.1	1584.1	1583.2	1581.4	1578.7	1575.9	1573.2	1570.5	1572.9
5°	1581.8	1580.3	1578.9	1577.4	1576.0	1573.6	1570.2	1566.8	1563.4	1559.9	1562.5
7.5°	1567.1	1565.6	1564.1	1562.5	1560.9	1557.9	1553.5	1549.1	1544.6	1540.2	1541.6
10°	1554.8	1552.8	1550.8	1548.8	1546.8	1543.2	1538.1	1533.0	1527.9	1522.8	1523.1
12.5°	1537.4	1535.1	1533.0	1530.7	1528.4	1524.2	1518.0	1511.6	1505.4	1499.1	1498.9
15°	1508.6	1505.5	1502.3	1499.2	1496.1	1490.5	1482.5	1474.5	1466.6	1458.6	1457.2
17.5°	1472.4	1468.8	1465.2	1461.5	1457.8	1451.0	1440.8	1430.7	1420.5	1410.3	1407.3
20°	1445.8	1441.2	1436.6	1432.1	1427.5	1419.8	1409.0	1398.2	1387.3	1376.5	1372.8
22.5°	1416.0	1410.8	1405.5	1400.2	1395.1	1386.7	1375.1	1363.6	1352.1	1340.6	1336.0
25°	1372.6	1365.6	1358.4	1351.2	1344.2	1334.0	1320.9	1307.8	1294.7	1281.6	1275.5
27.5°	1320.0	1312.2	1304.3	1296.5	1288.5	1277.3	1262.7	1248.1	1233.5	1219.0	1210.6
30°	1284.1	1275.5	1267.1	1258.5	1249.9	1237.7	1221.7	1205.7	1189.8	1173.8	1164.1
32.5°	1248.2	1238.5	1228.8	1219.1	1209.5	1196.2	1179.3	1162.4	1145.5	1128.6	1118.0
35°	1187.9	1177.6	1167.3	1157.2	1146.9	1132.8	1115.2	1097.5	1079.9	1062.2	1049.9
37.5°	1126.8	1115.4	1104.0	1092.6	1081.2	1066.1	1047.3	1028.3	1009.5	990.6	976.7
40°	1087.9	1075.3	1062.7	1050.2	1037.6	1021.2	1001.1	980.8	960.5	940.3	925.5
42.5°	1043.7	1031.1	1018.6	1006.1	993.5	976.9	955.9	935.0	914.1	893.2	876.9
45°	976.3	963.4	950.6	937.7	924.9	907.6	885.6	863.7	841.7	819.7	803.5
47.5°	908.8	894.7	880.6	866.5	852.4	834.4	812.5	790.5	768.5	746.6	729.0
50°	859.5	846.1	832.7	819.4	805.9	787.7	764.6	741.5	718.4	695.3	677.6
52.5°	815.4	800.9	786.3	771.8	757.2	738.5	715.7	692.8	670.0	647.1	628.7
55°	741.5	727.5	713.5	699.6	685.6	666.5	642.2	618.0	593.8	569.6	553.1
57.5°	673.3	658.0	642.8	627.5	612.4	592.6	568.2	543.8	519.5	495.2	479.6
60°	626.0	610.4	594.7	579.0	563.3	543.7	520.0	496.3	472.7	449.0	433.6
62.5°	578.8	563.2	547.4	531.8	516.1	496.4	472.8	449.1	425.5	401.8	387.3
65°	506.7	491.1	475.3	459.7	444.0	425.1	402.8	380.6	358.4	336.1	322.2
67.5°	434.6	418.8	402.9	387.1	371.3	352.6	331.3	310.0	288.7	267.3	256.9
70°	387.4	372.0	356.7	341.2	325.8	308.2	288.2	268.2	248.3	228.4	218.4
72.5°	340.2	325.1	309.9	294.7	279.6	262.9	244.8	226.7	208.5	190.4	182.2
75°	268.2	254.4	240.7	227.1	213.4	198.7	183.0	167.3	151.7	136.0	133.1
77.5°	202.5	190.0	177.7	165.3	153.0	141.7	131.6	121.5	111.4	101.3	99.8
80°	160.3	148.6	137.0	125.3	113.6	104.8	98.8	92.7	86.8	80.8	79.9
82.5°	120.4	110.3	100.2	90.0	79.9	73.5	70.7	68.0	65.1	62.3	61.5
85°	68.0	61.7	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.7	22.3	20.0	17.6	15.3	14.1	14.3	14.5	14.7	15.0	14.8
90°	0.4	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3
92.5°	8.1	8.6	9.0	9.6	10.1	10.6	11.1	11.7	12.3	12.8	13.0
95°	19.7	20.2	20.6	21.2	21.7	22.2	22.9	23.5	24.0	24.7	25.0
97.5°	34.9	35.3	35.7	36.1	36.5	36.9	37.3	37.7	38.2	38.5	38.9
100°	45.3	45.7	46.2	46.7	47.0	47.5	47.9	48.3	48.6	48.9	49.2
102.5°	57.3	57.6	57.8	58.1	58.3	58.7	59.2	59.8	60.2	60.7	60.9
105°	74.9	75.1	75.2	75.4	75.5	76.0	76.6	77.3	77.9	78.6	78.6
107.5°	95.5	95.6	95.7	95.8	95.9	96.0	96.2	96.5	96.8	97.1	97.3
110°	108.3	108.4	108.6	108.7	108.9	109.0	109.1	109.3	109.4	109.6	109.9



TEST NUMBER: P332334-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.6	121.7	121.8	121.9	122.0	122.0	122.1	122.1	122.1	122.2	122.4
115°	141.6	141.8	142.0	142.2	142.4	142.5	142.3	142.2	142.0	141.9	141.9
117.5°	161.6	161.8	162.0	162.1	162.3	162.2	162.0	161.8	161.6	161.5	161.5
120°	174.2	174.7	175.1	175.5	176.0	176.0	175.7	175.3	174.9	174.6	174.5
122.5°	187.3	187.6	187.9	188.2	188.6	188.6	188.4	188.2	188.0	187.8	187.7
125°	207.2	207.4	207.6	207.8	208.1	208.1	207.9	207.8	207.6	207.5	207.2
127.5°	225.6	226.0	226.5	227.0	227.4	227.6	227.4	227.2	227.2	227.0	226.6
130°	237.8	238.4	239.0	239.6	240.2	240.3	240.2	240.0	239.7	239.5	239.2
132.5°	250.1	250.7	251.3	251.8	252.4	252.7	252.5	252.3	252.1	252.0	251.7
135°	268.8	269.3	269.7	270.1	270.6	270.8	270.7	270.6	270.5	270.5	270.1
137.5°	286.2	286.5	286.8	287.2	287.6	287.9	288.0	288.2	288.4	288.6	288.3
140°	298.1	298.5	298.9	299.3	299.6	299.8	299.9	299.9	300.0	300.1	300.0
142.5°	309.1	309.4	309.8	310.2	310.5	310.8	310.9	311.0	311.1	311.3	311.2
145°	326.1	326.2	326.4	326.5	326.7	326.9	327.1	327.3	327.5	327.7	327.7
147.5°	341.0	341.3	341.6	341.9	342.0	342.3	342.5	342.7	342.9	343.2	343.2
150°	351.4	351.6	351.7	351.9	352.0	352.1	352.3	352.4	352.6	352.7	352.7
152.5°	360.0	360.1	360.3	360.5	360.8	360.9	361.0	361.1	361.2	361.3	361.4
155°	373.4	373.4	373.4	373.4	373.4	373.4	373.5	373.5	373.6	373.7	374.0
157.5°	384.8	384.7	384.7	384.6	384.5	384.5	384.6	384.6	384.7	384.7	385.0
160°	392.0	391.9	391.7	391.6	391.4	391.3	391.3	391.3	391.3	391.3	391.7
162.5°	398.4	398.2	398.0	397.8	397.6	397.6	397.6	397.7	397.8	397.8	398.1
165°	406.7	406.5	406.2	406.0	405.8	405.7	405.7	405.7	405.7	405.7	406.1
167.5°	413.3	413.0	412.7	412.4	412.1	412.0	412.1	412.1	412.2	412.3	412.6
170°	417.0	416.7	416.4	416.1	415.8	415.7	415.7	415.7	415.7	415.7	416.2
172.5°	420.0	419.6	419.3	419.1	418.8	418.6	418.6	418.6	418.6	418.6	419.1
175°	423.0	422.7	422.4	422.2	421.9	421.7	421.7	421.7	421.7	421.7	422.2
177.5°	424.2	424.0	423.8	423.6	423.3	423.2	423.2	423.2	423.2	423.2	423.6
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P332334-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1575.5	1578.0	1580.5	1581.5	1581.0	1580.6	1580.2	1579.7
5°	1565.1	1567.6	1570.2	1571.2	1570.7	1570.1	1569.5	1569.0
7.5°	1543.0	1544.5	1545.9	1546.1	1545.1	1544.2	1543.2	1542.2
10°	1523.3	1523.6	1523.9	1523.3	1521.8	1520.4	1519.0	1517.6
12.5°	1498.7	1498.6	1498.5	1497.5	1495.9	1494.2	1492.6	1490.9
15°	1455.8	1454.3	1452.9	1451.1	1449.2	1447.2	1445.2	1443.2
17.5°	1404.3	1401.3	1398.3	1395.2	1392.3	1389.3	1386.4	1383.4
20°	1369.0	1365.4	1361.7	1358.1	1354.7	1351.2	1347.8	1344.4
22.5°	1331.3	1326.7	1322.1	1318.1	1315.0	1311.8	1308.6	1305.4
25°	1269.6	1263.6	1257.6	1253.0	1249.9	1246.8	1243.7	1240.5
27.5°	1202.3	1194.0	1185.6	1179.1	1174.3	1169.5	1164.7	1160.0
30°	1154.4	1144.7	1135.0	1127.9	1123.3	1118.8	1114.2	1109.7
32.5°	1107.4	1096.8	1086.2	1078.6	1073.7	1068.9	1064.1	1059.3
35°	1037.6	1025.4	1013.1	1004.5	999.4	994.2	989.1	983.9
37.5°	962.8	948.9	935.0	924.8	918.5	912.2	905.9	899.6
40°	910.7	895.9	881.0	870.3	863.7	857.2	850.6	844.1
42.5°	860.7	844.5	828.3	817.3	811.4	805.6	799.7	793.8
45°	787.2	771.0	754.7	743.2	736.3	729.5	722.6	715.9
47.5°	711.2	693.6	675.9	664.0	657.9	651.9	645.7	639.6
50°	660.0	642.2	624.6	612.5	606.0	599.4	592.9	586.3
52.5°	610.4	592.0	573.6	561.5	555.6	549.8	543.9	538.0
55°	536.5	520.0	503.4	492.3	486.6	480.9	475.2	469.5
57.5°	463.9	448.3	432.7	422.4	417.6	412.7	407.9	403.0
60°	418.2	402.8	387.4	377.3	372.5	367.6	362.8	357.9
62.5°	372.8	358.4	343.8	334.0	329.0	324.0	318.9	313.8
65°	308.2	294.2	280.2	271.6	268.5	265.4	262.3	259.1
67.5°	246.5	236.0	225.6	218.7	215.4	212.0	208.6	205.3
70°	208.4	198.4	188.4	181.9	178.7	175.6	172.5	169.4
72.5°	174.1	165.9	157.8	153.1	151.7	150.4	149.1	147.8
75°	130.3	127.4	124.6	122.9	122.3	121.7	121.1	120.6
77.5°	98.3	96.7	95.2	94.2	93.6	93.0	92.5	91.9
80°	79.1	78.2	77.4	76.7	76.2	75.6	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.2	58.1	58.0
85°	34.8	34.2	33.6	33.4	33.4	33.4	33.4	33.4
87.5°	14.6	14.4	14.2	14.0	13.9	13.7	13.5	13.3
90°	8.6	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	13.3	13.5	13.8	13.9	13.8	13.7	13.6	13.5
95°	25.3	25.5	25.8	26.0	26.0	26.0	26.0	26.0
97.5°	39.2	39.6	40.0	40.1	40.1	40.1	40.0	40.0
100°	49.4	49.7	49.9	50.0	50.1	50.3	50.5	50.6
102.5°	61.2	61.4	61.5	61.6	61.6	61.6	61.5	61.5
105°	78.6	78.6	78.6	78.7	78.8	79.0	79.2	79.3
107.5°	97.6	97.7	98.0	98.1	98.0	97.9	97.8	97.7
110°	110.2	110.5	110.7	110.8	110.7	110.6	110.4	110.3



TEST NUMBER: P332334-830

CATALOG NUMBER: S123RDIP-S1000D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	122.8	123.2	123.6	123.7	123.7	123.7	123.6	123.6
115°	142.0	142.1	142.2	142.2	142.1	142.0	141.9	141.9
117.5°	161.5	161.5	161.5	161.3	161.1	160.9	160.7	160.5
120°	174.4	174.3	174.3	174.1	174.0	173.8	173.7	173.5
122.5°	187.5	187.3	187.1	186.9	186.7	186.4	186.2	186.1
125°	206.9	206.6	206.3	206.0	205.8	205.5	205.1	204.8
127.5°	226.1	225.7	225.3	224.9	224.6	224.2	223.9	223.6
130°	238.9	238.6	238.3	237.9	237.4	236.9	236.4	235.8
132.5°	251.3	250.9	250.6	250.2	249.8	249.4	249.0	248.6
135°	269.8	269.6	269.3	269.1	268.9	268.7	268.6	268.4
137.5°	288.0	287.8	287.4	287.1	286.8	286.5	286.3	286.0
140°	299.9	299.9	299.8	299.5	299.0	298.5	297.9	297.5
142.5°	311.1	311.0	311.0	310.8	310.4	310.0	309.5	309.2
145°	327.6	327.5	327.4	327.3	327.0	326.7	326.4	326.1
147.5°	343.2	343.2	343.2	342.9	342.5	342.0	341.6	341.1
150°	352.7	352.7	352.7	352.5	352.0	351.7	351.2	350.7
152.5°	361.5	361.7	361.7	361.6	361.2	360.8	360.4	360.1
155°	374.3	374.6	374.9	374.8	374.3	373.7	373.2	372.7
157.5°	385.3	385.7	386.0	385.9	385.5	385.1	384.7	384.3
160°	392.1	392.5	392.9	392.9	392.6	392.3	392.0	391.7
162.5°	398.5	398.9	399.3	399.2	398.7	398.2	397.8	397.3
165°	406.6	407.0	407.5	407.5	406.9	406.4	405.9	405.4
167.5°	413.1	413.6	414.1	414.1	413.6	413.1	412.6	412.3
170°	416.7	417.3	417.7	417.7	417.3	416.7	416.2	415.7
172.5°	419.5	420.0	420.5	420.5	419.9	419.4	418.9	418.4
175°	422.5	423.0	423.5	423.4	422.9	422.4	421.9	421.3
177.5°	424.0	424.2	424.6	424.6	424.2	423.8	423.4	422.9
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0

(END OF REPORT)