

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332340-830

Luminaire Tested: **S123RDIP-S1000D585U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332340-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D585U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5471.5 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332340-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332340-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65				
1	102	97	94	90	95	92	88	85	81	79	76	72	70	68	63	61	60	56				
2	93	86	79	74	87	81	75	71	72	68	64	63	60	58	56	53	51	47				
3	85	76	68	62	80	71	65	60	64	59	54	56	52	49	50	47	44	41				
4	78	67	59	53	73	64	57	51	57	51	47	51	46	42	45	41	38	35				
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34	31				
6	66	54	46	40	62	51	44	39	46	40	36	41	37	33	37	33	30	27				
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27	24				
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	31	27	24	22				
9	53	41	34	28	50	39	32	27	36	30	26	32	27	24	29	25	22	20				
10	50	38	31	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17026	17026	17026
5°	17091	16855	16953
10°	16994	16644	16587
15°	16811	16254	16082
20°	16561	15767	15400
25°	16302	15221	14733
30°	15960	14589	13793
35°	15609	13958	12929
40°	15286	13212	11861
45°	14862	12478	10898
50°	14393	11643	9818
55°	13915	10689	8811
60°	13476	9666	7705
65°	12905	8560	6599
70°	12192	7188	5331
75°	11154	5656	5016
80°	9937	5009	4612
85°	8398	4434	4125



TEST NUMBER: P332340-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	2.7
10°-20°	413.3	7.6
20°-30°	595.1	10.9
30°-40°	670.3	12.3
40°-50°	641.3	11.7
50°-60°	525.1	9.6
60°-70°	354.3	6.5
70°-80°	178.2	3.3
80°-90°	49.2	0.9
90°-100°	44.6	0.8
100°-110°	133.4	2.4
110°-120°	227.0	4.1
120°-130°	298.5	5.5
130°-140°	335.6	6.1
140°-150°	329.8	6.0
150°-160°	277.7	5.1
160°-170°	184.8	3.4
170°-180°	64.7	1.2
0°-30°	1156.9	21.1
0°-40°	1827.2	33.4
0°-60°	2993.6	54.7
0°-90°	3575.3	65.3
90°-120°	405.0	7.4
90°-150°	1368.9	25.0
90°-180°	1896.0	34.7
0°-180°	5471.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1582	1582	1582	1582	1582	
5°	1582	1575	1560	1571	1569	150
15°	1509	1493	1459	1452	1443	425
25°	1373	1339	1282	1255	1240	631
35°	1188	1140	1062	1009	984	743
45°	976	916	820	749	716	753
55°	742	676	570	498	470	665
65°	507	435	336	276	259	501
75°	268	206	136	124	121	286
85°	68	41	36	34	33	76
90°	1	6	13	15	16	5
95°	32	36	40	42	42	36
105°	121	122	127	127	128	130
115°	228	230	229	230	229	226
125°	334	336	335	333	331	298
135°	434	437	437	434	433	334
145°	526	527	529	528	526	329
155°	603	603	603	605	602	277
165°	656	655	655	658	654	185
175°	683	681	681	683	680	65
180°	684	684	684	684	684	



TEST NUMBER: P332340-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1586.9	1585.9	1585.1	1584.1	1583.2	1581.4	1578.7	1575.9	1573.2	1570.5	1572.9
5°	1581.8	1580.3	1578.9	1577.4	1576.0	1573.6	1570.2	1566.8	1563.4	1559.9	1562.5
7.5°	1567.1	1565.6	1564.1	1562.5	1560.9	1557.9	1553.5	1549.1	1544.6	1540.2	1541.6
10°	1554.8	1552.8	1550.8	1548.8	1546.8	1543.2	1538.1	1533.0	1527.9	1522.8	1523.1
12.5°	1537.4	1535.1	1533.0	1530.7	1528.4	1524.2	1518.0	1511.6	1505.4	1499.1	1498.9
15°	1508.6	1505.5	1502.3	1499.2	1496.1	1490.5	1482.5	1474.5	1466.6	1458.6	1457.2
17.5°	1472.4	1468.8	1465.2	1461.5	1457.8	1451.0	1440.8	1430.7	1420.5	1410.3	1407.3
20°	1445.8	1441.2	1436.6	1432.1	1427.5	1419.8	1409.0	1398.2	1387.3	1376.5	1372.8
22.5°	1416.0	1410.8	1405.5	1400.2	1395.1	1386.7	1375.1	1363.6	1352.1	1340.6	1336.0
25°	1372.6	1365.6	1358.4	1351.2	1344.2	1334.0	1320.9	1307.8	1294.7	1281.6	1275.5
27.5°	1320.0	1312.2	1304.3	1296.5	1288.5	1277.3	1262.7	1248.1	1233.5	1219.0	1210.6
30°	1284.1	1275.5	1267.1	1258.5	1249.9	1237.7	1221.7	1205.7	1189.8	1173.8	1164.1
32.5°	1248.2	1238.5	1228.8	1219.1	1209.5	1196.2	1179.3	1162.4	1145.5	1128.6	1118.0
35°	1187.9	1177.6	1167.3	1157.2	1146.9	1132.8	1115.2	1097.5	1079.9	1062.2	1049.9
37.5°	1126.8	1115.4	1104.0	1092.6	1081.2	1066.1	1047.3	1028.3	1009.5	990.6	976.7
40°	1087.9	1075.3	1062.7	1050.2	1037.6	1021.2	1001.1	980.8	960.5	940.3	925.5
42.5°	1043.7	1031.1	1018.6	1006.1	993.5	976.9	955.9	935.0	914.1	893.2	876.9
45°	976.3	963.4	950.6	937.7	924.9	907.6	885.6	863.7	841.7	819.7	803.5
47.5°	908.8	894.7	880.6	866.5	852.4	834.4	812.5	790.5	768.5	746.6	729.0
50°	859.5	846.1	832.7	819.4	805.9	787.7	764.6	741.5	718.4	695.3	677.6
52.5°	815.4	800.9	786.3	771.8	757.2	738.5	715.7	692.8	670.0	647.1	628.7
55°	741.5	727.5	713.5	699.6	685.6	666.5	642.2	618.0	593.8	569.6	553.1
57.5°	673.3	658.0	642.8	627.5	612.4	592.6	568.2	543.8	519.5	495.2	479.6
60°	626.0	610.4	594.7	579.0	563.3	543.7	520.0	496.3	472.7	449.0	433.6
62.5°	578.8	563.2	547.4	531.8	516.1	496.4	472.8	449.1	425.5	401.8	387.3
65°	506.7	491.1	475.3	459.7	444.0	425.1	402.8	380.6	358.4	336.1	322.2
67.5°	434.6	418.8	402.9	387.1	371.3	352.6	331.3	310.0	288.7	267.3	256.9
70°	387.4	372.0	356.7	341.2	325.8	308.2	288.2	268.2	248.3	228.4	218.4
72.5°	340.2	325.1	309.9	294.7	279.6	262.9	244.8	226.7	208.5	190.4	182.2
75°	268.2	254.4	240.7	227.1	213.4	198.7	183.0	167.3	151.7	136.0	133.1
77.5°	202.5	190.0	177.7	165.3	153.0	141.7	131.6	121.5	111.4	101.3	99.8
80°	160.3	148.6	137.0	125.3	113.6	104.8	98.8	92.7	86.8	80.8	79.9
82.5°	120.4	110.3	100.2	90.0	79.9	73.5	70.7	68.0	65.1	62.3	61.5
85°	68.0	61.7	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.7	22.4	20.2	17.9	15.6	14.7	15.0	15.3	15.6	15.9	15.8
90°	0.6	1.7	2.9	4.1	5.3	6.7	8.2	9.8	11.3	12.9	13.4
92.5°	13.0	13.9	14.6	15.5	16.3	17.2	18.0	18.9	19.8	20.6	21.0
95°	31.8	32.5	33.4	34.2	35.1	36.0	36.9	37.9	38.8	39.8	40.2
97.5°	56.4	56.9	57.6	58.2	58.8	59.5	60.1	60.9	61.5	62.3	62.8
100°	73.1	73.8	74.6	75.3	76.0	76.6	77.2	77.9	78.4	79.0	79.4
102.5°	92.5	92.9	93.3	93.8	94.2	94.8	95.6	96.4	97.2	97.9	98.3
105°	120.9	121.2	121.4	121.7	122.0	122.5	123.7	124.7	125.8	126.9	126.9
107.5°	154.1	154.2	154.4	154.5	154.7	155.0	155.3	155.8	156.3	156.7	157.0
110°	174.7	174.9	175.2	175.4	175.7	175.9	176.2	176.4	176.6	176.9	177.4



TEST NUMBER: P332340-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	196.2	196.3	196.5	196.6	196.8	196.9	197.0	197.0	197.1	197.1	197.7
115°	228.5	228.8	229.2	229.6	229.9	230.0	229.7	229.5	229.2	229.0	229.1
117.5°	261.0	261.2	261.5	261.6	261.9	261.8	261.6	261.3	261.0	260.6	260.6
120°	281.2	281.9	282.6	283.3	284.1	284.1	283.5	283.0	282.3	281.7	281.6
122.5°	302.3	302.7	303.3	303.8	304.3	304.4	304.2	303.9	303.5	303.2	302.9
125°	334.4	334.8	335.1	335.5	335.8	335.9	335.6	335.5	335.2	335.0	334.4
127.5°	364.1	364.9	365.6	366.4	367.1	367.4	367.1	366.8	366.6	366.4	365.7
130°	383.9	384.8	385.8	386.7	387.7	388.0	387.7	387.3	386.9	386.5	386.1
132.5°	403.6	404.6	405.6	406.5	407.5	407.8	407.6	407.3	407.0	406.8	406.1
135°	433.9	434.6	435.3	436.0	436.7	437.1	436.9	436.8	436.7	436.6	436.1
137.5°	461.8	462.4	463.0	463.6	464.2	464.7	465.0	465.2	465.6	465.9	465.4
140°	481.2	481.7	482.4	483.0	483.5	483.9	484.0	484.2	484.3	484.4	484.3
142.5°	498.8	499.4	500.0	500.6	501.1	501.6	501.8	502.0	502.3	502.5	502.4
145°	526.3	526.6	526.8	527.1	527.3	527.5	527.9	528.3	528.7	529.0	528.9
147.5°	550.4	550.8	551.3	551.7	552.1	552.5	552.9	553.2	553.6	553.8	553.8
150°	567.2	567.4	567.7	567.9	568.2	568.4	568.6	568.8	569.1	569.3	569.3
152.5°	581.0	581.3	581.6	581.9	582.3	582.5	582.7	582.8	583.0	583.1	583.2
155°	602.7	602.7	602.7	602.7	602.7	602.8	602.9	602.9	603.1	603.2	603.7
157.5°	621.1	621.0	620.9	620.8	620.6	620.6	620.7	620.8	620.9	620.9	621.4
160°	632.7	632.5	632.3	632.1	631.8	631.7	631.7	631.7	631.7	631.7	632.3
162.5°	643.1	642.7	642.4	642.1	641.8	641.7	641.8	641.9	642.0	642.1	642.6
165°	656.4	656.1	655.7	655.3	655.0	654.8	654.8	654.8	654.8	654.8	655.5
167.5°	667.0	666.6	666.1	665.6	665.2	665.0	665.1	665.2	665.2	665.3	666.1
170°	673.1	672.6	672.1	671.7	671.2	670.9	670.9	670.9	670.9	670.9	671.8
172.5°	677.8	677.3	676.8	676.4	675.9	675.7	675.7	675.7	675.7	675.7	676.5
175°	682.8	682.3	681.8	681.4	680.9	680.6	680.6	680.6	680.6	680.6	681.4
177.5°	684.9	684.5	684.1	683.6	683.2	683.1	683.1	683.1	683.1	683.1	683.6
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4



TEST NUMBER: P332340-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1575.5	1578.0	1580.5	1581.5	1581.0	1580.6	1580.2	1579.7
5°	1565.1	1567.6	1570.2	1571.2	1570.7	1570.1	1569.5	1569.0
7.5°	1543.0	1544.5	1545.9	1546.1	1545.1	1544.2	1543.2	1542.2
10°	1523.3	1523.6	1523.9	1523.3	1521.8	1520.4	1519.0	1517.6
12.5°	1498.7	1498.6	1498.5	1497.5	1495.9	1494.2	1492.6	1490.9
15°	1455.8	1454.3	1452.9	1451.1	1449.2	1447.2	1445.2	1443.2
17.5°	1404.3	1401.3	1398.3	1395.2	1392.3	1389.3	1386.4	1383.4
20°	1369.0	1365.4	1361.7	1358.1	1354.7	1351.2	1347.8	1344.4
22.5°	1331.3	1326.7	1322.1	1318.1	1315.0	1311.8	1308.6	1305.4
25°	1269.6	1263.6	1257.6	1253.0	1249.9	1246.8	1243.7	1240.5
27.5°	1202.3	1194.0	1185.6	1179.1	1174.3	1169.5	1164.7	1160.0
30°	1154.4	1144.7	1135.0	1127.9	1123.3	1118.8	1114.2	1109.7
32.5°	1107.4	1096.8	1086.2	1078.6	1073.7	1068.9	1064.1	1059.3
35°	1037.6	1025.4	1013.1	1004.5	999.4	994.2	989.1	983.9
37.5°	962.8	948.9	935.0	924.8	918.5	912.2	905.9	899.6
40°	910.7	895.9	881.0	870.3	863.7	857.2	850.6	844.1
42.5°	860.7	844.5	828.3	817.3	811.4	805.6	799.7	793.8
45°	787.2	771.0	754.7	743.2	736.3	729.5	722.6	715.9
47.5°	711.2	693.6	675.9	664.0	657.9	651.9	645.7	639.6
50°	660.0	642.2	624.6	612.5	606.0	599.4	592.9	586.3
52.5°	610.4	592.0	573.6	561.5	555.6	549.8	543.9	538.0
55°	536.5	520.0	503.4	492.3	486.6	480.9	475.2	469.5
57.5°	463.9	448.3	432.7	422.4	417.6	412.7	407.9	403.0
60°	418.2	402.8	387.4	377.3	372.5	367.6	362.8	357.9
62.5°	372.8	358.4	343.8	334.0	329.0	324.0	318.9	313.8
65°	308.2	294.2	280.2	271.6	268.5	265.4	262.3	259.1
67.5°	246.5	236.0	225.6	218.7	215.4	212.0	208.6	205.3
70°	208.4	198.4	188.4	181.9	178.7	175.6	172.5	169.4
72.5°	174.1	165.9	157.8	153.1	151.7	150.4	149.1	147.8
75°	130.3	127.4	124.6	122.9	122.3	121.7	121.1	120.6
77.5°	98.3	96.7	95.2	94.2	93.6	93.0	92.5	91.9
80°	79.1	78.2	77.4	76.7	76.2	75.6	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.2	58.1	58.0
85°	34.8	34.2	33.6	33.4	33.4	33.4	33.4	33.4
87.5°	15.6	15.6	15.4	15.3	15.1	14.9	14.7	14.5
90°	13.9	14.3	14.8	15.2	15.5	15.6	15.9	16.1
92.5°	21.4	21.8	22.1	22.3	22.1	22.0	21.9	21.7
95°	40.7	41.2	41.7	41.9	41.9	41.9	41.9	41.9
97.5°	63.3	63.9	64.5	64.7	64.7	64.6	64.6	64.5
100°	79.7	80.1	80.5	80.8	81.0	81.2	81.4	81.7
102.5°	98.7	99.1	99.3	99.5	99.5	99.4	99.4	99.3
105°	126.9	126.9	126.9	127.0	127.2	127.4	127.7	128.0
107.5°	157.4	157.8	158.2	158.3	158.2	158.1	157.9	157.8
110°	177.9	178.3	178.8	178.9	178.7	178.4	178.2	178.0



TEST NUMBER: P332340-830

CATALOG NUMBER: S123RDIP-S1000D585U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.2	198.8	199.3	199.6	199.6	199.5	199.5	199.4
115°	229.2	229.4	229.5	229.5	229.4	229.2	229.1	229.0
117.5°	260.6	260.5	260.5	260.3	260.0	259.7	259.4	259.0
120°	281.4	281.3	281.3	281.1	280.8	280.6	280.3	280.1
122.5°	302.6	302.3	302.0	301.6	301.3	301.0	300.7	300.3
125°	333.9	333.5	333.0	332.5	332.1	331.6	331.1	330.6
127.5°	365.0	364.3	363.6	363.1	362.5	361.9	361.4	360.8
130°	385.6	385.1	384.7	384.0	383.1	382.3	381.4	380.6
132.5°	405.6	405.0	404.4	403.9	403.2	402.6	401.9	401.2
135°	435.5	435.1	434.6	434.2	434.0	433.8	433.6	433.3
137.5°	464.9	464.4	463.9	463.4	463.0	462.5	462.0	461.6
140°	484.2	484.0	483.9	483.4	482.6	481.7	480.9	480.1
142.5°	502.2	502.1	502.0	501.6	501.0	500.3	499.6	499.0
145°	528.8	528.7	528.6	528.2	527.7	527.3	526.8	526.3
147.5°	553.8	553.8	553.8	553.5	552.8	552.0	551.4	550.6
150°	569.3	569.3	569.3	569.0	568.3	567.5	566.8	566.1
152.5°	583.5	583.7	583.9	583.6	583.1	582.4	581.8	581.2
155°	604.2	604.6	605.1	604.9	604.1	603.2	602.5	601.6
157.5°	622.0	622.5	622.9	622.8	622.2	621.5	620.9	620.2
160°	632.9	633.5	634.0	634.1	633.7	633.2	632.7	632.3
162.5°	643.2	643.9	644.4	644.3	643.6	642.8	642.1	641.3
165°	656.3	657.0	657.7	657.6	656.8	655.9	655.2	654.3
167.5°	666.8	667.6	668.4	668.4	667.6	666.8	666.1	665.3
170°	672.6	673.4	674.3	674.3	673.4	672.6	671.8	670.9
172.5°	677.1	677.9	678.6	678.6	677.8	676.9	676.1	675.2
175°	682.0	682.8	683.5	683.4	682.6	681.7	680.9	680.0
177.5°	684.3	684.9	685.4	685.3	684.7	684.0	683.3	682.7
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4

(END OF REPORT)