

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332364-830

Luminaire Tested: **S123RDIP-S1165D365U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332364-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D365U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5302.9 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332364-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332364-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78
1	105	100	96	93	100	96	92	89	88	85	82	80	78	76	73	72	70	67
2	96	88	82	77	91	84	79	74	77	73	69	71	67	64	65	62	60	57
3	88	78	71	65	83	75	68	63	69	63	59	63	59	55	58	54	51	48
4	80	69	61	55	77	67	59	54	61	55	51	57	52	48	52	48	45	42
5	74	62	54	48	71	60	52	47	55	49	44	51	46	42	47	43	39	37
6	69	56	48	42	65	54	46	41	50	44	39	46	41	37	43	38	35	32
7	64	51	43	37	61	49	42	36	46	39	35	42	37	33	39	35	31	29
8	59	47	39	33	57	45	38	32	42	36	31	39	34	30	36	32	28	26
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	40	32	27	50	38	31	27	36	30	25	33	28	24	31	27	23	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19664	19664	19664
5°	19739	19466	19578
10°	19627	19223	19158
15°	19417	18773	18574
20°	19126	18211	17786
25°	18828	17579	17016
30°	18434	16850	15929
35°	18029	16119	14933
40°	17654	15260	13699
45°	17163	14411	12584
50°	16623	13447	11338
55°	16071	12344	10175
60°	15565	11164	8900
65°	14905	9885	7623
70°	14080	8299	6156
75°	12876	6529	5793
80°	11480	5783	5331
85°	9695	5125	4755



TEST NUMBER: P332364-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.5	3.2
10°-20°	477.3	9.0
20°-30°	687.3	13.0
30°-40°	774.2	14.6
40°-50°	740.6	14.0
50°-60°	606.5	11.4
60°-70°	409.2	7.7
70°-80°	205.9	3.9
80°-90°	55.7	1.1
90°-100°	27.6	0.5
100°-110°	82.7	1.6
110°-120°	140.6	2.7
120°-130°	185.0	3.5
130°-140°	207.9	3.9
140°-150°	204.4	3.9
150°-160°	172.0	3.2
160°-170°	114.5	2.2
170°-180°	40.1	0.8
0°-30°	1336.1	25.2
0°-40°	2110.3	39.8
0°-60°	3457.4	65.2
0°-90°	4128.1	77.8
90°-120°	250.9	4.7
90°-150°	848.1	16.0
90°-180°	1175.0	22.2
0°-180°	5302.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1827	1827	1827	1827	1827	
5°	1827	1819	1802	1814	1812	173
15°	1742	1725	1685	1677	1667	491
25°	1585	1547	1480	1450	1433	729
35°	1372	1316	1227	1165	1136	858
45°	1128	1058	947	865	827	870
55°	856	781	658	575	542	768
65°	585	502	388	319	299	579
75°	310	238	157	143	139	330
85°	78	48	42	39	38	88
90°	0	4	8	9	10	5
95°	20	22	25	26	26	22
105°	75	76	79	79	79	80
115°	142	142	142	142	142	140
125°	207	208	208	206	205	185
135°	269	271	270	269	268	207
145°	326	327	328	327	326	204
155°	373	373	374	375	373	172
165°	407	406	406	408	405	115
175°	423	422	422	423	421	40
180°	424	424	424	424	424	



TEST NUMBER: P332364-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1832.8	1831.6	1830.6	1829.6	1828.5	1826.4	1823.3	1820.0	1816.9	1813.7	1816.7
5°	1826.8	1825.1	1823.5	1821.8	1820.2	1817.4	1813.5	1809.5	1805.5	1801.6	1804.6
7.5°	1809.9	1808.2	1806.4	1804.6	1802.8	1799.3	1794.2	1789.0	1784.0	1778.8	1780.5
10°	1795.7	1793.4	1791.1	1788.8	1786.5	1782.3	1776.4	1770.5	1764.5	1758.7	1759.0
12.5°	1775.6	1773.0	1770.4	1767.8	1765.3	1760.4	1753.1	1745.9	1738.6	1731.4	1731.2
15°	1742.4	1738.7	1735.1	1731.5	1727.9	1721.5	1712.2	1703.0	1693.7	1684.6	1682.9
17.5°	1700.5	1696.4	1692.1	1687.9	1683.8	1675.7	1664.1	1652.3	1640.6	1628.9	1625.4
20°	1669.7	1664.5	1659.3	1654.0	1648.7	1639.8	1627.3	1614.8	1602.2	1589.8	1585.5
22.5°	1635.4	1629.3	1623.2	1617.2	1611.2	1601.5	1588.2	1574.9	1561.6	1548.2	1542.9
25°	1585.3	1577.1	1568.9	1560.6	1552.4	1540.7	1525.5	1510.4	1495.2	1480.1	1473.2
27.5°	1524.6	1515.5	1506.4	1497.3	1488.2	1475.3	1458.4	1441.5	1424.7	1407.8	1398.2
30°	1483.1	1473.2	1463.3	1453.4	1443.6	1429.4	1411.0	1392.5	1374.1	1355.7	1344.4
32.5°	1441.6	1430.4	1419.2	1408.0	1396.8	1381.5	1362.0	1342.5	1323.0	1303.5	1291.3
35°	1372.0	1360.1	1348.2	1336.4	1324.6	1308.4	1288.0	1267.6	1247.2	1226.7	1212.6
37.5°	1301.5	1288.3	1275.1	1261.9	1248.8	1231.2	1209.5	1187.7	1165.9	1144.1	1128.0
40°	1256.4	1241.9	1227.4	1213.0	1198.4	1179.5	1156.1	1132.7	1109.4	1086.0	1068.8
42.5°	1205.4	1190.9	1176.5	1162.0	1147.5	1128.1	1104.0	1079.8	1055.6	1031.5	1012.8
45°	1127.5	1112.7	1097.9	1083.1	1068.2	1048.1	1022.8	997.4	972.0	946.7	927.9
47.5°	1049.5	1033.3	1017.0	1000.8	984.5	963.7	938.3	912.9	887.6	862.3	841.9
50°	992.7	977.2	961.7	946.2	930.8	909.7	883.1	856.4	829.7	803.0	782.6
52.5°	941.7	924.9	908.1	891.4	874.5	852.9	826.5	800.1	773.7	747.3	726.1
55°	856.4	840.2	824.1	807.9	791.8	769.8	741.8	713.8	685.8	657.8	638.8
57.5°	777.5	760.0	742.3	724.8	707.2	684.4	656.3	628.1	600.0	571.9	553.8
60°	723.0	704.9	686.8	668.7	650.5	627.8	600.5	573.3	545.9	518.6	500.8
62.5°	668.5	650.4	632.3	614.2	596.1	573.3	546.0	518.7	491.3	464.0	447.3
65°	585.2	567.1	549.0	530.9	512.8	490.9	465.2	439.5	413.9	388.1	372.0
67.5°	502.0	483.6	465.3	447.0	428.8	407.3	382.7	358.0	333.4	308.8	296.7
70°	447.4	429.7	411.9	394.1	376.4	355.9	332.9	309.8	286.8	263.7	252.2
72.5°	392.9	375.4	357.9	340.4	322.8	303.6	282.7	261.7	240.8	219.9	210.5
75°	309.6	293.9	278.1	262.2	246.5	229.5	211.4	193.2	175.1	157.0	153.7
77.5°	233.8	219.5	205.2	191.0	176.6	163.6	152.0	140.3	128.7	117.1	115.3
80°	185.2	171.7	158.2	144.7	131.2	121.0	114.0	107.2	100.3	93.3	92.4
82.5°	138.9	127.3	115.6	104.0	92.4	84.9	81.7	78.4	75.2	72.0	71.0
85°	78.5	71.3	64.0	56.8	49.6	45.4	44.5	43.5	42.5	41.5	40.8
87.5°	28.6	25.7	23.0	20.3	17.5	16.2	16.4	16.6	16.8	17.0	16.8
90°	0.4	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3
92.5°	8.1	8.6	9.0	9.6	10.1	10.6	11.1	11.7	12.3	12.8	13.0
95°	19.7	20.2	20.6	21.2	21.7	22.2	22.9	23.5	24.0	24.7	25.0
97.5°	34.9	35.3	35.7	36.1	36.5	36.9	37.3	37.7	38.2	38.5	38.9
100°	45.3	45.7	46.2	46.7	47.0	47.5	47.9	48.3	48.6	48.9	49.2
102.5°	57.3	57.6	57.8	58.1	58.3	58.7	59.2	59.8	60.2	60.7	60.9
105°	74.9	75.1	75.2	75.4	75.5	76.0	76.6	77.3	77.9	78.6	78.6
107.5°	95.5	95.6	95.7	95.8	95.9	96.0	96.2	96.5	96.8	97.1	97.3
110°	108.3	108.4	108.6	108.7	108.9	109.0	109.1	109.3	109.4	109.6	109.9



TEST NUMBER: P332364-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.6	121.7	121.8	121.9	122.0	122.0	122.1	122.1	122.1	122.2	122.4
115°	141.6	141.8	142.0	142.2	142.4	142.5	142.3	142.2	142.0	141.9	141.9
117.5°	161.6	161.8	162.0	162.1	162.3	162.2	162.0	161.8	161.6	161.5	161.5
120°	174.2	174.7	175.1	175.5	176.0	176.0	175.7	175.3	174.9	174.6	174.5
122.5°	187.3	187.6	187.9	188.2	188.6	188.6	188.4	188.2	188.0	187.8	187.7
125°	207.2	207.4	207.6	207.8	208.1	208.1	207.9	207.8	207.6	207.5	207.2
127.5°	225.6	226.0	226.5	227.0	227.4	227.6	227.4	227.2	227.2	227.0	226.6
130°	237.8	238.4	239.0	239.6	240.2	240.3	240.2	240.0	239.7	239.5	239.2
132.5°	250.1	250.7	251.3	251.8	252.4	252.7	252.5	252.3	252.1	252.0	251.7
135°	268.8	269.3	269.7	270.1	270.6	270.8	270.7	270.6	270.5	270.5	270.1
137.5°	286.2	286.5	286.8	287.2	287.6	287.9	288.0	288.2	288.4	288.6	288.3
140°	298.1	298.5	298.9	299.3	299.6	299.8	299.9	299.9	300.0	300.1	300.0
142.5°	309.1	309.4	309.8	310.2	310.5	310.8	310.9	311.0	311.1	311.3	311.2
145°	326.1	326.2	326.4	326.5	326.7	326.9	327.1	327.3	327.5	327.7	327.7
147.5°	341.0	341.3	341.6	341.9	342.0	342.3	342.5	342.7	342.9	343.2	343.2
150°	351.4	351.6	351.7	351.9	352.0	352.1	352.3	352.4	352.6	352.7	352.7
152.5°	360.0	360.1	360.3	360.5	360.8	360.9	361.0	361.1	361.2	361.3	361.4
155°	373.4	373.4	373.4	373.4	373.4	373.4	373.5	373.5	373.6	373.7	374.0
157.5°	384.8	384.7	384.7	384.6	384.5	384.5	384.6	384.6	384.7	384.7	385.0
160°	392.0	391.9	391.7	391.6	391.4	391.3	391.3	391.3	391.3	391.3	391.7
162.5°	398.4	398.2	398.0	397.8	397.6	397.6	397.6	397.7	397.8	397.8	398.1
165°	406.7	406.5	406.2	406.0	405.8	405.7	405.7	405.7	405.7	405.7	406.1
167.5°	413.3	413.0	412.7	412.4	412.1	412.0	412.1	412.1	412.2	412.3	412.6
170°	417.0	416.7	416.4	416.1	415.8	415.7	415.7	415.7	415.7	415.7	416.2
172.5°	420.0	419.6	419.3	419.1	418.8	418.6	418.6	418.6	418.6	418.6	419.1
175°	423.0	422.7	422.4	422.2	421.9	421.7	421.7	421.7	421.7	421.7	422.2
177.5°	424.2	424.0	423.8	423.6	423.3	423.2	423.2	423.2	423.2	423.2	423.6
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0



TEST NUMBER: P332364-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1819.6	1822.5	1825.3	1826.6	1826.0	1825.5	1825.0	1824.4
5°	1807.5	1810.5	1813.5	1814.6	1813.9	1813.3	1812.6	1811.9
7.5°	1782.1	1783.8	1785.4	1785.6	1784.5	1783.4	1782.3	1781.1
10°	1759.3	1759.6	1760.0	1759.3	1757.7	1756.1	1754.4	1752.8
12.5°	1731.0	1730.8	1730.6	1729.6	1727.7	1725.7	1723.8	1721.9
15°	1681.3	1679.6	1678.0	1676.0	1673.7	1671.4	1669.1	1666.8
17.5°	1621.9	1618.3	1614.9	1611.5	1608.0	1604.6	1601.2	1597.7
20°	1581.2	1576.9	1572.6	1568.5	1564.5	1560.6	1556.7	1552.7
22.5°	1537.6	1532.3	1526.9	1522.4	1518.7	1515.0	1511.4	1507.7
25°	1466.3	1459.3	1452.5	1447.2	1443.6	1439.9	1436.3	1432.7
27.5°	1388.6	1378.9	1369.3	1361.8	1356.2	1350.8	1345.2	1339.6
30°	1333.2	1322.1	1310.9	1302.7	1297.4	1292.1	1286.9	1281.6
32.5°	1279.0	1266.8	1254.5	1245.7	1240.1	1234.5	1229.1	1223.5
35°	1198.4	1184.3	1170.2	1160.1	1154.1	1148.2	1142.3	1136.4
37.5°	1111.9	1095.9	1079.8	1068.1	1060.8	1053.5	1046.2	1038.9
40°	1051.8	1034.6	1017.6	1005.2	997.6	990.0	982.5	974.9
42.5°	994.1	975.3	956.7	944.0	937.2	930.4	923.6	916.8
45°	909.2	890.4	871.7	858.4	850.5	842.5	834.6	826.7
47.5°	821.4	801.1	780.6	766.9	759.9	752.8	745.7	738.8
50°	762.2	741.8	721.3	707.4	699.8	692.2	684.7	677.1
52.5°	704.9	683.7	662.5	648.5	641.7	635.0	628.2	621.4
55°	619.6	600.5	581.5	568.6	562.0	555.4	548.8	542.2
57.5°	535.8	517.7	499.7	487.9	482.3	476.7	471.1	465.5
60°	483.0	465.2	447.4	435.7	430.2	424.5	419.0	413.4
62.5°	430.6	413.9	397.1	385.9	379.9	374.1	368.3	362.4
65°	355.9	339.8	323.7	313.8	310.2	306.5	302.9	299.3
67.5°	284.6	272.6	260.5	252.6	248.7	244.8	240.9	237.0
70°	240.6	229.1	217.6	210.1	206.4	202.8	199.2	195.6
72.5°	201.0	191.6	182.2	176.7	175.2	173.7	172.2	170.7
75°	150.4	147.1	143.8	141.9	141.3	140.6	140.0	139.3
77.5°	113.5	111.7	109.9	108.7	108.0	107.4	106.7	106.0
80°	91.3	90.4	89.4	88.6	87.9	87.3	86.6	86.0
82.5°	70.0	69.1	68.1	67.5	67.4	67.2	67.1	67.0
85°	40.2	39.5	38.8	38.5	38.5	38.5	38.5	38.5
87.5°	16.6	16.4	16.2	15.9	15.7	15.5	15.3	15.1
90°	8.6	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	13.3	13.5	13.8	13.9	13.8	13.7	13.6	13.5
95°	25.3	25.5	25.8	26.0	26.0	26.0	26.0	26.0
97.5°	39.2	39.6	40.0	40.1	40.1	40.1	40.0	40.0
100°	49.4	49.7	49.9	50.0	50.1	50.3	50.5	50.6
102.5°	61.2	61.4	61.5	61.6	61.6	61.6	61.5	61.5
105°	78.6	78.6	78.6	78.7	78.8	79.0	79.2	79.3
107.5°	97.6	97.7	98.0	98.1	98.0	97.9	97.8	97.7
110°	110.2	110.5	110.7	110.8	110.7	110.6	110.4	110.3



TEST NUMBER: P332364-830

CATALOG NUMBER: S123RDIP-S1165D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	122.8	123.2	123.6	123.7	123.7	123.7	123.6	123.6
115°	142.0	142.1	142.2	142.2	142.1	142.0	141.9	141.9
117.5°	161.5	161.5	161.5	161.3	161.1	160.9	160.7	160.5
120°	174.4	174.3	174.3	174.1	174.0	173.8	173.7	173.5
122.5°	187.5	187.3	187.1	186.9	186.7	186.4	186.2	186.1
125°	206.9	206.6	206.3	206.0	205.8	205.5	205.1	204.8
127.5°	226.1	225.7	225.3	224.9	224.6	224.2	223.9	223.6
130°	238.9	238.6	238.3	237.9	237.4	236.9	236.4	235.8
132.5°	251.3	250.9	250.6	250.2	249.8	249.4	249.0	248.6
135°	269.8	269.6	269.3	269.1	268.9	268.7	268.6	268.4
137.5°	288.0	287.8	287.4	287.1	286.8	286.5	286.3	286.0
140°	299.9	299.9	299.8	299.5	299.0	298.5	297.9	297.5
142.5°	311.1	311.0	311.0	310.8	310.4	310.0	309.5	309.2
145°	327.6	327.5	327.4	327.3	327.0	326.7	326.4	326.1
147.5°	343.2	343.2	343.2	342.9	342.5	342.0	341.6	341.1
150°	352.7	352.7	352.7	352.5	352.0	351.7	351.2	350.7
152.5°	361.5	361.7	361.7	361.6	361.2	360.8	360.4	360.1
155°	374.3	374.6	374.9	374.8	374.3	373.7	373.2	372.7
157.5°	385.3	385.7	386.0	385.9	385.5	385.1	384.7	384.3
160°	392.1	392.5	392.9	392.9	392.6	392.3	392.0	391.7
162.5°	398.5	398.9	399.3	399.2	398.7	398.2	397.8	397.3
165°	406.6	407.0	407.5	407.5	406.9	406.4	405.9	405.4
167.5°	413.1	413.6	414.1	414.1	413.6	413.1	412.6	412.3
170°	416.7	417.3	417.7	417.7	417.3	416.7	416.2	415.7
172.5°	419.5	420.0	420.5	420.5	419.9	419.4	418.9	418.4
175°	422.5	423.0	423.5	423.4	422.9	422.4	421.9	421.3
177.5°	424.0	424.2	424.6	424.6	424.2	423.8	423.4	422.9
180°	424.0	424.0	424.0	424.0	424.0	424.0	424.0	424.0

(END OF REPORT)