

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332369-830

Luminaire Tested: **S123RDIP-S1165D585U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332369-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D585U830-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 585 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6335.5 lumens  
Efficiency: N/A  
Efficacy: 115.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332369-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332369-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	102	97	94	90	95	92	88	85	81	79	76	72	70	68	63	61	60	56
2	93	86	79	74	87	81	75	71	72	68	64	63	60	57	56	53	51	47
3	85	76	68	62	80	71	65	60	64	58	54	56	52	49	50	47	44	41
4	78	67	59	53	73	64	57	51	57	51	47	50	46	42	45	41	38	35
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34	31
6	66	54	46	40	62	51	44	39	46	40	36	41	36	33	37	33	30	27
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	32	54	43	35	31	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	30	26	32	27	24	29	25	22	20
10	50	38	31	26	47	36	29	25	33	27	23	30	25	22	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19664	19664	19664
5°	19739	19466	19578
10°	19627	19223	19158
15°	19417	18773	18574
20°	19126	18211	17786
25°	18828	17579	17016
30°	18434	16850	15929
35°	18029	16119	14933
40°	17654	15260	13699
45°	17163	14411	12584
50°	16623	13447	11338
55°	16071	12344	10175
60°	15565	11164	8900
65°	14905	9885	7623
70°	14080	8299	6156
75°	12876	6529	5793
80°	11480	5783	5331
85°	9695	5125	4755



TEST NUMBER: P332369-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.5	2.7
10°-20°	477.3	7.5
20°-30°	687.3	10.8
30°-40°	774.2	12.2
40°-50°	740.6	11.7
50°-60°	606.5	9.6
60°-70°	409.2	6.5
70°-80°	205.9	3.2
80°-90°	56.5	0.9
90°-100°	26.3	0.4
100°-110°	125.4	2.0
110°-120°	301.2	4.8
120°-130°	383.5	6.1
130°-140°	409.8	6.5
140°-150°	383.2	6.0
150°-160°	309.1	4.9
160°-170°	199.5	3.1
170°-180°	68.7	1.1
0°-30°	1336.1	21.1
0°-40°	2110.3	33.3
0°-60°	3457.4	54.6
0°-90°	4128.9	65.2
90°-120°	452.8	7.1
90°-150°	1629.3	25.7
90°-180°	2207.0	34.8
0°-180°	6335.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1827	1827	1827	1827	1827	
5°	1827	1819	1802	1814	1812	173
15°	1742	1725	1685	1677	1667	491
25°	1585	1547	1480	1450	1433	729
35°	1372	1316	1227	1165	1136	858
45°	1128	1058	947	865	827	870
55°	856	781	658	575	542	768
65°	585	502	388	319	299	579
75°	310	238	157	143	139	330
85°	78	48	42	39	38	88
90°	1	6	13	15	16	5
95°	33	12	17	20	20	41
105°	160	163	118	28	24	170
115°	300	304	309	314	316	297
125°	424	428	430	431	432	378
135°	527	531	533	534	533	406
145°	608	612	613	614	614	381
155°	670	669	670	672	669	309
165°	707	705	705	709	705	200
175°	724	721	721	725	721	69
180°	724	724	724	724	724	



TEST NUMBER: P332369-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1832.8	1831.6	1830.6	1829.6	1828.5	1826.4	1823.3	1820.0	1816.9	1813.7	1816.7
5°	1826.8	1825.1	1823.5	1821.8	1820.2	1817.4	1813.5	1809.5	1805.5	1801.6	1804.6
7.5°	1809.9	1808.2	1806.4	1804.6	1802.8	1799.3	1794.2	1789.0	1784.0	1778.8	1780.5
10°	1795.7	1793.4	1791.1	1788.8	1786.5	1782.3	1776.4	1770.5	1764.5	1758.7	1759.0
12.5°	1775.6	1773.0	1770.4	1767.8	1765.3	1760.4	1753.1	1745.9	1738.6	1731.4	1731.2
15°	1742.4	1738.7	1735.1	1731.5	1727.9	1721.5	1712.2	1703.0	1693.7	1684.6	1682.9
17.5°	1700.5	1696.4	1692.1	1687.9	1683.8	1675.7	1664.1	1652.3	1640.6	1628.9	1625.4
20°	1669.7	1664.5	1659.3	1654.0	1648.7	1639.8	1627.3	1614.8	1602.2	1589.8	1585.5
22.5°	1635.4	1629.3	1623.2	1617.2	1611.2	1601.5	1588.2	1574.9	1561.6	1548.2	1542.9
25°	1585.3	1577.1	1568.9	1560.6	1552.4	1540.7	1525.5	1510.4	1495.2	1480.1	1473.2
27.5°	1524.6	1515.5	1506.4	1497.3	1488.2	1475.3	1458.4	1441.5	1424.7	1407.8	1398.2
30°	1483.1	1473.2	1463.3	1453.4	1443.6	1429.4	1411.0	1392.5	1374.1	1355.7	1344.4
32.5°	1441.6	1430.4	1419.2	1408.0	1396.8	1381.5	1362.0	1342.5	1323.0	1303.5	1291.3
35°	1372.0	1360.1	1348.2	1336.4	1324.6	1308.4	1288.0	1267.6	1247.2	1226.7	1212.6
37.5°	1301.5	1288.3	1275.1	1261.9	1248.8	1231.2	1209.5	1187.7	1165.9	1144.1	1128.0
40°	1256.4	1241.9	1227.4	1213.0	1198.4	1179.5	1156.1	1132.7	1109.4	1086.0	1068.8
42.5°	1205.4	1190.9	1176.5	1162.0	1147.5	1128.1	1104.0	1079.8	1055.6	1031.5	1012.8
45°	1127.5	1112.7	1097.9	1083.1	1068.2	1048.1	1022.8	997.4	972.0	946.7	927.9
47.5°	1049.5	1033.3	1017.0	1000.8	984.5	963.7	938.3	912.9	887.6	862.3	841.9
50°	992.7	977.2	961.7	946.2	930.8	909.7	883.1	856.4	829.7	803.0	782.6
52.5°	941.7	924.9	908.1	891.4	874.5	852.9	826.5	800.1	773.7	747.3	726.1
55°	856.4	840.2	824.1	807.9	791.8	769.8	741.8	713.8	685.8	657.8	638.8
57.5°	777.5	760.0	742.3	724.8	707.2	684.4	656.3	628.1	600.0	571.9	553.8
60°	723.0	704.9	686.8	668.7	650.5	627.8	600.5	573.3	545.9	518.6	500.8
62.5°	668.5	650.4	632.3	614.2	596.1	573.3	546.0	518.7	491.3	464.0	447.3
65°	585.2	567.1	549.0	530.9	512.8	490.9	465.2	439.5	413.9	388.1	372.0
67.5°	502.0	483.6	465.3	447.0	428.8	407.3	382.7	358.0	333.4	308.8	296.7
70°	447.4	429.7	411.9	394.1	376.4	355.9	332.9	309.8	286.8	263.7	252.2
72.5°	392.9	375.4	357.9	340.4	322.8	303.6	282.7	261.7	240.8	219.9	210.5
75°	309.6	293.9	278.1	262.2	246.5	229.5	211.4	193.2	175.1	157.0	153.7
77.5°	233.8	219.5	205.2	191.0	176.6	163.6	152.0	140.3	128.7	117.1	115.3
80°	185.2	171.7	158.2	144.7	131.2	121.0	114.0	107.2	100.3	93.3	92.4
82.5°	138.9	127.3	115.6	104.0	92.4	84.9	81.7	78.4	75.2	72.0	71.0
85°	78.5	71.3	64.0	56.8	49.6	45.4	44.5	43.5	42.5	41.5	40.8
87.5°	28.6	25.9	23.3	20.5	17.9	16.8	17.1	17.3	17.7	18.0	17.8
90°	0.6	1.7	2.9	4.1	5.3	6.7	8.2	9.8	11.3	12.9	13.4
92.5°	10.0	9.7	9.3	9.0	8.7	9.0	10.3	11.4	12.6	13.8	14.5
95°	32.8	27.9	23.0	18.1	13.2	11.4	12.7	14.0	15.4	16.7	17.5
97.5°	65.9	63.7	61.5	59.3	57.1	51.7	43.1	34.5	25.9	17.3	18.3
100°	90.9	93.2	95.7	98.0	100.4	92.3	73.6	55.0	36.4	17.7	18.7
102.5°	119.2	120.9	122.7	124.4	126.1	116.8	96.4	76.1	55.7	35.3	32.4
105°	160.2	161.6	162.9	164.1	165.4	160.7	150.0	139.2	128.5	117.7	96.6
107.5°	203.4	204.4	205.6	206.6	207.6	209.0	210.7	212.4	214.1	215.7	200.3
110°	232.2	233.2	234.1	235.1	236.0	237.2	238.5	239.8	241.1	242.4	238.5



TEST NUMBER: P332369-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	259.8	260.6	261.5	262.3	263.2	264.3	265.6	266.9	268.2	269.6	269.7
115°	300.5	301.2	301.9	302.7	303.4	304.3	305.4	306.4	307.5	308.6	309.8
117.5°	340.0	340.8	341.8	342.6	343.5	344.2	344.8	345.3	345.9	346.4	347.4
120°	364.5	365.5	366.6	367.7	368.8	369.5	369.9	370.2	370.6	370.9	371.9
122.5°	389.5	390.3	391.2	392.1	392.9	393.6	394.1	394.5	395.0	395.5	396.2
125°	423.6	424.6	425.6	426.5	427.4	428.2	428.7	429.1	429.6	430.1	430.3
127.5°	456.8	457.7	458.6	459.6	460.5	461.3	461.8	462.5	463.1	463.6	464.0
130°	477.4	478.3	479.3	480.2	481.2	481.9	482.4	482.9	483.3	483.8	484.3
132.5°	497.2	498.1	499.1	500.0	501.0	501.6	502.0	502.4	502.8	503.2	503.7
135°	527.4	528.1	528.8	529.5	530.3	530.8	531.3	531.8	532.3	532.7	533.1
137.5°	553.2	554.1	555.0	555.9	556.8	557.4	557.6	557.9	558.2	558.5	559.0
140°	570.3	571.1	571.8	572.5	573.3	573.8	574.1	574.5	574.9	575.2	575.7
142.5°	586.3	587.0	587.8	588.4	589.2	589.7	590.0	590.4	590.8	591.2	591.5
145°	608.5	609.4	610.2	611.1	611.9	612.5	612.7	612.9	613.1	613.4	613.6
147.5°	629.5	630.1	630.7	631.1	631.7	632.1	632.4	632.5	632.8	633.1	633.3
150°	642.4	642.8	643.1	643.5	643.9	644.1	644.4	644.6	644.9	645.1	645.4
152.5°	654.0	654.2	654.3	654.5	654.7	654.9	655.0	655.2	655.3	655.4	655.8
155°	670.3	670.1	669.9	669.7	669.4	669.4	669.5	669.6	669.7	669.9	670.4
157.5°	683.1	683.1	683.0	683.0	683.0	682.9	682.8	682.7	682.5	682.4	683.2
160°	690.8	690.7	690.6	690.4	690.3	690.2	690.0	689.9	689.8	689.8	690.4
162.5°	698.1	697.8	697.5	697.2	696.8	696.6	696.5	696.4	696.3	696.2	697.0
165°	706.9	706.5	706.2	705.9	705.5	705.2	705.1	705.0	704.9	704.7	705.8
167.5°	713.8	713.3	712.8	712.4	711.9	711.6	711.6	711.6	711.6	711.6	712.7
170°	717.7	717.2	716.7	716.2	715.8	715.5	715.5	715.5	715.5	715.5	716.5
172.5°	720.3	719.7	719.1	718.5	717.9	717.7	717.8	717.9	718.0	718.1	719.1
175°	723.6	723.0	722.4	721.8	721.2	721.0	721.0	721.2	721.3	721.4	722.3
177.5°	724.4	724.0	723.5	723.0	722.6	722.4	722.5	722.6	722.6	722.7	723.5
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6



TEST NUMBER: P332369-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1819.6	1822.5	1825.3	1826.6	1826.0	1825.5	1825.0	1824.4
5°	1807.5	1810.5	1813.5	1814.6	1813.9	1813.3	1812.6	1811.9
7.5°	1782.1	1783.8	1785.4	1785.6	1784.5	1783.4	1782.3	1781.1
10°	1759.3	1759.6	1760.0	1759.3	1757.7	1756.1	1754.4	1752.8
12.5°	1731.0	1730.8	1730.6	1729.6	1727.7	1725.7	1723.8	1721.9
15°	1681.3	1679.6	1678.0	1676.0	1673.7	1671.4	1669.1	1666.8
17.5°	1621.9	1618.3	1614.9	1611.5	1608.0	1604.6	1601.2	1597.7
20°	1581.2	1576.9	1572.6	1568.5	1564.5	1560.6	1556.7	1552.7
22.5°	1537.6	1532.3	1526.9	1522.4	1518.7	1515.0	1511.4	1507.7
25°	1466.3	1459.3	1452.5	1447.2	1443.6	1439.9	1436.3	1432.7
27.5°	1388.6	1378.9	1369.3	1361.8	1356.2	1350.8	1345.2	1339.6
30°	1333.2	1322.1	1310.9	1302.7	1297.4	1292.1	1286.9	1281.6
32.5°	1279.0	1266.8	1254.5	1245.7	1240.1	1234.5	1229.1	1223.5
35°	1198.4	1184.3	1170.2	1160.1	1154.1	1148.2	1142.3	1136.4
37.5°	1111.9	1095.9	1079.8	1068.1	1060.8	1053.5	1046.2	1038.9
40°	1051.8	1034.6	1017.6	1005.2	997.6	990.0	982.5	974.9
42.5°	994.1	975.3	956.7	944.0	937.2	930.4	923.6	916.8
45°	909.2	890.4	871.7	858.4	850.5	842.5	834.6	826.7
47.5°	821.4	801.1	780.6	766.9	759.9	752.8	745.7	738.8
50°	762.2	741.8	721.3	707.4	699.8	692.2	684.7	677.1
52.5°	704.9	683.7	662.5	648.5	641.7	635.0	628.2	621.4
55°	619.6	600.5	581.5	568.6	562.0	555.4	548.8	542.2
57.5°	535.8	517.7	499.7	487.9	482.3	476.7	471.1	465.5
60°	483.0	465.2	447.4	435.7	430.2	424.5	419.0	413.4
62.5°	430.6	413.9	397.1	385.9	379.9	374.1	368.3	362.4
65°	355.9	339.8	323.7	313.8	310.2	306.5	302.9	299.3
67.5°	284.6	272.6	260.5	252.6	248.7	244.8	240.9	237.0
70°	240.6	229.1	217.6	210.1	206.4	202.8	199.2	195.6
72.5°	201.0	191.6	182.2	176.7	175.2	173.7	172.2	170.7
75°	150.4	147.1	143.8	141.9	141.3	140.6	140.0	139.3
77.5°	113.5	111.7	109.9	108.7	108.0	107.4	106.7	106.0
80°	91.3	90.4	89.4	88.6	87.9	87.3	86.6	86.0
82.5°	70.0	69.1	68.1	67.5	67.4	67.2	67.1	67.0
85°	40.2	39.5	38.8	38.5	38.5	38.5	38.5	38.5
87.5°	17.6	17.5	17.3	17.2	16.9	16.7	16.5	16.3
90°	13.9	14.3	14.8	15.2	15.5	15.6	15.9	16.1
92.5°	15.3	16.0	16.8	17.2	17.4	17.5	17.7	17.8
95°	18.4	19.1	20.0	20.5	20.5	20.5	20.5	20.5
97.5°	19.2	20.2	21.1	21.7	21.8	21.9	22.1	22.1
100°	19.6	20.6	21.6	22.1	22.2	22.3	22.4	22.6
102.5°	29.4	26.5	23.6	22.1	22.3	22.6	22.8	23.0
105°	75.4	54.3	33.2	22.7	22.9	23.2	23.4	23.7
107.5°	184.7	169.3	153.7	138.1	122.1	106.1	90.2	74.3
110°	234.6	230.6	226.7	216.1	199.1	182.0	164.9	147.8





TEST NUMBER: P332369-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	269.7	269.8	269.8	268.1	264.5	260.8	257.2	253.6
115°	310.9	312.2	313.4	314.1	314.6	315.2	315.7	316.1
117.5°	348.4	349.3	350.2	350.8	350.9	351.0	351.1	351.2
120°	372.9	373.8	374.8	375.2	375.2	375.2	375.2	375.2
122.5°	396.8	397.5	398.1	398.5	398.6	398.7	398.8	398.9
125°	430.6	430.7	431.0	431.3	431.5	431.8	432.0	432.3
127.5°	464.4	464.8	465.1	465.2	465.0	464.8	464.5	464.3
130°	484.7	485.2	485.7	485.9	485.6	485.4	485.1	484.9
132.5°	504.2	504.6	505.1	505.2	504.8	504.4	504.2	503.8
135°	533.5	533.9	534.1	534.1	533.9	533.5	533.1	532.7
137.5°	559.6	560.2	560.7	560.9	560.6	560.4	560.2	560.0
140°	576.2	576.6	577.1	577.2	577.0	576.7	576.6	576.3
142.5°	591.9	592.3	592.7	592.7	592.4	592.0	591.6	591.4
145°	613.9	614.1	614.3	614.4	614.4	614.4	614.4	614.4
147.5°	633.6	633.8	634.0	633.9	633.3	632.7	632.3	631.7
150°	645.5	645.8	646.0	646.0	645.6	645.3	644.9	644.6
152.5°	656.3	656.7	657.1	657.0	656.6	656.0	655.4	654.9
155°	671.0	671.7	672.2	672.1	671.5	670.7	670.1	669.3
157.5°	683.8	684.6	685.3	685.1	684.2	683.3	682.4	681.5
160°	691.2	691.8	692.6	692.5	691.7	690.9	690.0	689.2
162.5°	697.8	698.6	699.5	699.5	698.7	698.0	697.2	696.5
165°	706.7	707.7	708.6	708.7	707.8	707.0	706.2	705.3
167.5°	713.6	714.5	715.5	715.5	714.5	713.6	712.7	711.6
170°	717.5	718.4	719.3	719.3	718.4	717.5	716.5	715.5
172.5°	720.0	721.0	721.9	721.9	720.9	719.8	718.7	717.7
175°	723.1	724.0	724.8	724.7	723.8	722.8	721.9	720.9
177.5°	724.2	725.0	725.8	725.7	724.7	723.8	722.8	721.9
180°	723.6	723.6	723.6	723.6	723.6	723.6	723.6	723.6

(END OF REPORT)