

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332370-830

Luminaire Tested: **S123RDIP-S1165D585U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332370-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D585U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 585 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6025.1 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332370-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332370-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69
1	102	98	94	91	97	93	89	86	83	80	78	74	72	70	65	64	63	59
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	58	56	53	50
3	86	76	69	63	81	72	66	60	65	60	55	58	54	51	52	49	46	43
4	79	68	60	54	74	64	57	52	58	52	48	52	48	44	47	43	40	37
5	72	61	53	46	68	58	50	45	52	46	42	47	42	38	42	38	35	32
6	67	55	47	41	63	52	45	39	47	41	37	43	38	34	38	34	31	29
7	62	50	42	36	59	47	40	35	43	37	32	39	34	30	35	31	28	26
8	58	45	37	32	55	43	36	31	39	33	29	36	31	27	32	28	25	23
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	30	26	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19664	19664	19664
5°	19739	19466	19578
10°	19627	19223	19158
15°	19417	18773	18574
20°	19126	18211	17786
25°	18828	17579	17016
30°	18434	16850	15929
35°	18029	16119	14933
40°	17654	15260	13699
45°	17163	14411	12584
50°	16623	13447	11338
55°	16071	12344	10175
60°	15565	11164	8900
65°	14905	9885	7623
70°	14080	8299	6156
75°	12876	6529	5793
80°	11480	5783	5331
85°	9695	5125	4755



TEST NUMBER: P332370-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.5	2.8
10°-20°	477.3	7.9
20°-30°	687.3	11.4
30°-40°	774.2	12.8
40°-50°	740.6	12.3
50°-60°	606.5	10.1
60°-70°	409.2	6.8
70°-80°	205.9	3.4
80°-90°	56.5	0.9
90°-100°	44.6	0.7
100°-110°	133.4	2.2
110°-120°	227.0	3.8
120°-130°	298.5	5.0
130°-140°	335.6	5.6
140°-150°	329.8	5.5
150°-160°	277.7	4.6
160°-170°	184.8	3.1
170°-180°	64.7	1.1
0°-30°	1336.1	22.2
0°-40°	2110.3	35.0
0°-60°	3457.4	57.4
0°-90°	4128.9	68.5
90°-120°	405.0	6.7
90°-150°	1368.9	22.7
90°-180°	1896.0	31.5
0°-180°	6025.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1827	1827	1827	1827	1827	
5°	1827	1819	1802	1814	1812	173
15°	1742	1725	1685	1677	1667	491
25°	1585	1547	1480	1450	1433	729
35°	1372	1316	1227	1165	1136	858
45°	1128	1058	947	865	827	870
55°	856	781	658	575	542	768
65°	585	502	388	319	299	579
75°	310	238	157	143	139	330
85°	78	48	42	39	38	88
90°	1	6	13	15	16	6
95°	32	36	40	42	42	36
105°	121	122	127	127	128	130
115°	228	230	229	230	229	226
125°	334	336	335	333	331	298
135°	434	437	437	434	433	334
145°	526	527	529	528	526	329
155°	603	603	603	605	602	277
165°	656	655	655	658	654	185
175°	683	681	681	683	680	65
180°	684	684	684	684	684	



TEST NUMBER: P332370-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1832.8	1831.6	1830.6	1829.6	1828.5	1826.4	1823.3	1820.0	1816.9	1813.7	1816.7
5°	1826.8	1825.1	1823.5	1821.8	1820.2	1817.4	1813.5	1809.5	1805.5	1801.6	1804.6
7.5°	1809.9	1808.2	1806.4	1804.6	1802.8	1799.3	1794.2	1789.0	1784.0	1778.8	1780.5
10°	1795.7	1793.4	1791.1	1788.8	1786.5	1782.3	1776.4	1770.5	1764.5	1758.7	1759.0
12.5°	1775.6	1773.0	1770.4	1767.8	1765.3	1760.4	1753.1	1745.9	1738.6	1731.4	1731.2
15°	1742.4	1738.7	1735.1	1731.5	1727.9	1721.5	1712.2	1703.0	1693.7	1684.6	1682.9
17.5°	1700.5	1696.4	1692.1	1687.9	1683.8	1675.7	1664.1	1652.3	1640.6	1628.9	1625.4
20°	1669.7	1664.5	1659.3	1654.0	1648.7	1639.8	1627.3	1614.8	1602.2	1589.8	1585.5
22.5°	1635.4	1629.3	1623.2	1617.2	1611.2	1601.5	1588.2	1574.9	1561.6	1548.2	1542.9
25°	1585.3	1577.1	1568.9	1560.6	1552.4	1540.7	1525.5	1510.4	1495.2	1480.1	1473.2
27.5°	1524.6	1515.5	1506.4	1497.3	1488.2	1475.3	1458.4	1441.5	1424.7	1407.8	1398.2
30°	1483.1	1473.2	1463.3	1453.4	1443.6	1429.4	1411.0	1392.5	1374.1	1355.7	1344.4
32.5°	1441.6	1430.4	1419.2	1408.0	1396.8	1381.5	1362.0	1342.5	1323.0	1303.5	1291.3
35°	1372.0	1360.1	1348.2	1336.4	1324.6	1308.4	1288.0	1267.6	1247.2	1226.7	1212.6
37.5°	1301.5	1288.3	1275.1	1261.9	1248.8	1231.2	1209.5	1187.7	1165.9	1144.1	1128.0
40°	1256.4	1241.9	1227.4	1213.0	1198.4	1179.5	1156.1	1132.7	1109.4	1086.0	1068.8
42.5°	1205.4	1190.9	1176.5	1162.0	1147.5	1128.1	1104.0	1079.8	1055.6	1031.5	1012.8
45°	1127.5	1112.7	1097.9	1083.1	1068.2	1048.1	1022.8	997.4	972.0	946.7	927.9
47.5°	1049.5	1033.3	1017.0	1000.8	984.5	963.7	938.3	912.9	887.6	862.3	841.9
50°	992.7	977.2	961.7	946.2	930.8	909.7	883.1	856.4	829.7	803.0	782.6
52.5°	941.7	924.9	908.1	891.4	874.5	852.9	826.5	800.1	773.7	747.3	726.1
55°	856.4	840.2	824.1	807.9	791.8	769.8	741.8	713.8	685.8	657.8	638.8
57.5°	777.5	760.0	742.3	724.8	707.2	684.4	656.3	628.1	600.0	571.9	553.8
60°	723.0	704.9	686.8	668.7	650.5	627.8	600.5	573.3	545.9	518.6	500.8
62.5°	668.5	650.4	632.3	614.2	596.1	573.3	546.0	518.7	491.3	464.0	447.3
65°	585.2	567.1	549.0	530.9	512.8	490.9	465.2	439.5	413.9	388.1	372.0
67.5°	502.0	483.6	465.3	447.0	428.8	407.3	382.7	358.0	333.4	308.8	296.7
70°	447.4	429.7	411.9	394.1	376.4	355.9	332.9	309.8	286.8	263.7	252.2
72.5°	392.9	375.4	357.9	340.4	322.8	303.6	282.7	261.7	240.8	219.9	210.5
75°	309.6	293.9	278.1	262.2	246.5	229.5	211.4	193.2	175.1	157.0	153.7
77.5°	233.8	219.5	205.2	191.0	176.6	163.6	152.0	140.3	128.7	117.1	115.3
80°	185.2	171.7	158.2	144.7	131.2	121.0	114.0	107.2	100.3	93.3	92.4
82.5°	138.9	127.3	115.6	104.0	92.4	84.9	81.7	78.4	75.2	72.0	71.0
85°	78.5	71.3	64.0	56.8	49.6	45.4	44.5	43.5	42.5	41.5	40.8
87.5°	28.6	25.9	23.3	20.5	17.9	16.8	17.1	17.3	17.7	18.0	17.8
90°	0.6	1.7	2.9	4.1	5.3	6.7	8.2	9.8	11.3	12.9	13.4
92.5°	13.0	13.9	14.6	15.5	16.3	17.2	18.0	18.9	19.8	20.6	21.0
95°	31.8	32.5	33.4	34.2	35.1	36.0	36.9	37.9	38.8	39.8	40.2
97.5°	56.4	56.9	57.6	58.2	58.8	59.5	60.1	60.9	61.5	62.3	62.8
100°	73.1	73.8	74.6	75.3	76.0	76.6	77.2	77.9	78.4	79.0	79.4
102.5°	92.5	92.9	93.3	93.8	94.2	94.8	95.6	96.4	97.2	97.9	98.3
105°	120.9	121.2	121.4	121.7	122.0	122.5	123.7	124.7	125.8	126.9	126.9
107.5°	154.1	154.2	154.4	154.5	154.7	155.0	155.3	155.8	156.3	156.7	157.0
110°	174.7	174.9	175.2	175.4	175.7	175.9	176.2	176.4	176.6	176.9	177.4



TEST NUMBER: P332370-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	196.2	196.3	196.5	196.6	196.8	196.9	197.0	197.0	197.1	197.1	197.7
115°	228.5	228.8	229.2	229.6	229.9	230.0	229.7	229.5	229.2	229.0	229.1
117.5°	261.0	261.2	261.5	261.6	261.9	261.8	261.6	261.3	261.0	260.6	260.6
120°	281.2	281.9	282.6	283.3	284.1	284.1	283.5	283.0	282.3	281.7	281.6
122.5°	302.3	302.7	303.3	303.8	304.3	304.4	304.2	303.9	303.5	303.2	302.9
125°	334.4	334.8	335.1	335.5	335.8	335.9	335.6	335.5	335.2	335.0	334.4
127.5°	364.1	364.9	365.6	366.4	367.1	367.4	367.1	366.8	366.6	366.4	365.7
130°	383.9	384.8	385.8	386.7	387.7	388.0	387.7	387.3	386.9	386.5	386.1
132.5°	403.6	404.6	405.6	406.5	407.5	407.8	407.6	407.3	407.0	406.8	406.1
135°	433.9	434.6	435.3	436.0	436.7	437.1	436.9	436.8	436.7	436.6	436.1
137.5°	461.8	462.4	463.0	463.6	464.2	464.7	465.0	465.2	465.6	465.9	465.4
140°	481.2	481.7	482.4	483.0	483.5	483.9	484.0	484.2	484.3	484.4	484.3
142.5°	498.8	499.4	500.0	500.6	501.1	501.6	501.8	502.0	502.3	502.5	502.4
145°	526.3	526.6	526.8	527.1	527.3	527.5	527.9	528.3	528.7	529.0	528.9
147.5°	550.4	550.8	551.3	551.7	552.1	552.5	552.9	553.2	553.6	553.8	553.8
150°	567.2	567.4	567.7	567.9	568.2	568.4	568.6	568.8	569.1	569.3	569.3
152.5°	581.0	581.3	581.6	581.9	582.3	582.5	582.7	582.8	583.0	583.1	583.2
155°	602.7	602.7	602.7	602.7	602.7	602.8	602.9	602.9	603.1	603.2	603.7
157.5°	621.1	621.0	620.9	620.8	620.6	620.6	620.7	620.8	620.9	620.9	621.4
160°	632.7	632.5	632.3	632.1	631.8	631.7	631.7	631.7	631.7	631.7	632.3
162.5°	643.1	642.7	642.4	642.1	641.8	641.7	641.8	641.9	642.0	642.1	642.6
165°	656.4	656.1	655.7	655.3	655.0	654.8	654.8	654.8	654.8	654.8	655.5
167.5°	667.0	666.6	666.1	665.6	665.2	665.0	665.1	665.2	665.2	665.3	666.1
170°	673.1	672.6	672.1	671.7	671.2	670.9	670.9	670.9	670.9	670.9	671.8
172.5°	677.8	677.3	676.8	676.4	675.9	675.7	675.7	675.7	675.7	675.7	676.5
175°	682.8	682.3	681.8	681.4	680.9	680.6	680.6	680.6	680.6	680.6	681.4
177.5°	684.9	684.5	684.1	683.6	683.2	683.1	683.1	683.1	683.1	683.1	683.6
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4



TEST NUMBER: P332370-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1819.6	1822.5	1825.3	1826.6	1826.0	1825.5	1825.0	1824.4
5°	1807.5	1810.5	1813.5	1814.6	1813.9	1813.3	1812.6	1811.9
7.5°	1782.1	1783.8	1785.4	1785.6	1784.5	1783.4	1782.3	1781.1
10°	1759.3	1759.6	1760.0	1759.3	1757.7	1756.1	1754.4	1752.8
12.5°	1731.0	1730.8	1730.6	1729.6	1727.7	1725.7	1723.8	1721.9
15°	1681.3	1679.6	1678.0	1676.0	1673.7	1671.4	1669.1	1666.8
17.5°	1621.9	1618.3	1614.9	1611.5	1608.0	1604.6	1601.2	1597.7
20°	1581.2	1576.9	1572.6	1568.5	1564.5	1560.6	1556.7	1552.7
22.5°	1537.6	1532.3	1526.9	1522.4	1518.7	1515.0	1511.4	1507.7
25°	1466.3	1459.3	1452.5	1447.2	1443.6	1439.9	1436.3	1432.7
27.5°	1388.6	1378.9	1369.3	1361.8	1356.2	1350.8	1345.2	1339.6
30°	1333.2	1322.1	1310.9	1302.7	1297.4	1292.1	1286.9	1281.6
32.5°	1279.0	1266.8	1254.5	1245.7	1240.1	1234.5	1229.1	1223.5
35°	1198.4	1184.3	1170.2	1160.1	1154.1	1148.2	1142.3	1136.4
37.5°	1111.9	1095.9	1079.8	1068.1	1060.8	1053.5	1046.2	1038.9
40°	1051.8	1034.6	1017.6	1005.2	997.6	990.0	982.5	974.9
42.5°	994.1	975.3	956.7	944.0	937.2	930.4	923.6	916.8
45°	909.2	890.4	871.7	858.4	850.5	842.5	834.6	826.7
47.5°	821.4	801.1	780.6	766.9	759.9	752.8	745.7	738.8
50°	762.2	741.8	721.3	707.4	699.8	692.2	684.7	677.1
52.5°	704.9	683.7	662.5	648.5	641.7	635.0	628.2	621.4
55°	619.6	600.5	581.5	568.6	562.0	555.4	548.8	542.2
57.5°	535.8	517.7	499.7	487.9	482.3	476.7	471.1	465.5
60°	483.0	465.2	447.4	435.7	430.2	424.5	419.0	413.4
62.5°	430.6	413.9	397.1	385.9	379.9	374.1	368.3	362.4
65°	355.9	339.8	323.7	313.8	310.2	306.5	302.9	299.3
67.5°	284.6	272.6	260.5	252.6	248.7	244.8	240.9	237.0
70°	240.6	229.1	217.6	210.1	206.4	202.8	199.2	195.6
72.5°	201.0	191.6	182.2	176.7	175.2	173.7	172.2	170.7
75°	150.4	147.1	143.8	141.9	141.3	140.6	140.0	139.3
77.5°	113.5	111.7	109.9	108.7	108.0	107.4	106.7	106.0
80°	91.3	90.4	89.4	88.6	87.9	87.3	86.6	86.0
82.5°	70.0	69.1	68.1	67.5	67.4	67.2	67.1	67.0
85°	40.2	39.5	38.8	38.5	38.5	38.5	38.5	38.5
87.5°	17.6	17.5	17.3	17.2	16.9	16.7	16.5	16.3
90°	13.9	14.3	14.8	15.2	15.5	15.6	15.9	16.1
92.5°	21.4	21.8	22.1	22.3	22.1	22.0	21.9	21.7
95°	40.7	41.2	41.7	41.9	41.9	41.9	41.9	41.9
97.5°	63.3	63.9	64.5	64.7	64.7	64.6	64.6	64.5
100°	79.7	80.1	80.5	80.8	81.0	81.2	81.4	81.7
102.5°	98.7	99.1	99.3	99.5	99.5	99.4	99.4	99.3
105°	126.9	126.9	126.9	127.0	127.2	127.4	127.7	128.0
107.5°	157.4	157.8	158.2	158.3	158.2	158.1	157.9	157.8
110°	177.9	178.3	178.8	178.9	178.7	178.4	178.2	178.0



TEST NUMBER: P332370-830

CATALOG NUMBER: S123RDIP-S1165D585U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.2	198.8	199.3	199.6	199.6	199.5	199.5	199.4
115°	229.2	229.4	229.5	229.5	229.4	229.2	229.1	229.0
117.5°	260.6	260.5	260.5	260.3	260.0	259.7	259.4	259.0
120°	281.4	281.3	281.3	281.1	280.8	280.6	280.3	280.1
122.5°	302.6	302.3	302.0	301.6	301.3	301.0	300.7	300.3
125°	333.9	333.5	333.0	332.5	332.1	331.6	331.1	330.6
127.5°	365.0	364.3	363.6	363.1	362.5	361.9	361.4	360.8
130°	385.6	385.1	384.7	384.0	383.1	382.3	381.4	380.6
132.5°	405.6	405.0	404.4	403.9	403.2	402.6	401.9	401.2
135°	435.5	435.1	434.6	434.2	434.0	433.8	433.6	433.3
137.5°	464.9	464.4	463.9	463.4	463.0	462.5	462.0	461.6
140°	484.2	484.0	483.9	483.4	482.6	481.7	480.9	480.1
142.5°	502.2	502.1	502.0	501.6	501.0	500.3	499.6	499.0
145°	528.8	528.7	528.6	528.2	527.7	527.3	526.8	526.3
147.5°	553.8	553.8	553.8	553.5	552.8	552.0	551.4	550.6
150°	569.3	569.3	569.3	569.0	568.3	567.5	566.8	566.1
152.5°	583.5	583.7	583.9	583.6	583.1	582.4	581.8	581.2
155°	604.2	604.6	605.1	604.9	604.1	603.2	602.5	601.6
157.5°	622.0	622.5	622.9	622.8	622.2	621.5	620.9	620.2
160°	632.9	633.5	634.0	634.1	633.7	633.2	632.7	632.3
162.5°	643.2	643.9	644.4	644.3	643.6	642.8	642.1	641.3
165°	656.3	657.0	657.7	657.6	656.8	655.9	655.2	654.3
167.5°	666.8	667.6	668.4	668.4	667.6	666.8	666.1	665.3
170°	672.6	673.4	674.3	674.3	673.4	672.6	671.8	670.9
172.5°	677.1	677.9	678.6	678.6	677.8	676.9	676.1	675.2
175°	682.0	682.8	683.5	683.4	682.6	681.7	680.9	680.0
177.5°	684.3	684.9	685.4	685.3	684.7	684.0	683.3	682.7
180°	684.4	684.4	684.4	684.4	684.4	684.4	684.4	684.4

(END OF REPORT)