

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332242-830

Luminaire Tested: **S123RDIP-S340D365U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332242-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U830-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2516.4 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	38
3	83	74	67	61	76	68	62	57	59	54	50	49	46	43	41	39	37	33
4	76	66	58	52	70	61	54	49	52	47	43	44	41	38	37	34	32	29
5	70	59	51	45	64	55	48	43	47	42	38	40	36	33	34	31	28	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23	20
8	56	44	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	18	16
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5521	5521	5521	5521
5°	6582	5545	4883	5545
10°	8218	5513	4411	5513
15°	9646	5457	4023	5457
20°	10766	5372	3692	5372
25°	10594	5284	3489	5284
30°	7615	5203	3280	5203
35°	5084	5096	3144	5096
40°	3746	4967	3006	4967
45°	3142	4743	2868	4743
50°	2773	4449	2678	4449
55°	2432	4112	2415	4112
60°	2166	3791	2211	3791
65°	1900	3446	2058	3446
70°	1492	3138	1882	3138
75°	1314	2741	1718	2741
80°	1147	2325	1686	2325
85°	914	1877	1791	1877



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	2.0
10°-20°	157.6	6.3
20°-30°	247.6	9.8
30°-40°	258.3	10.3
40°-50°	221.1	8.8
50°-60°	168.5	6.7
60°-70°	108.0	4.3
70°-80°	52.0	2.1
80°-90°	15.0	0.6
90°-100°	91.6	3.6
100°-110°	259.3	10.3
110°-120°	255.1	10.1
120°-130°	203.5	8.1
130°-140°	160.4	6.4
140°-150°	119.7	4.8
150°-160°	83.4	3.3
160°-170°	49.0	1.9
170°-180°	16.0	0.6
0°-30°	455.6	18.1
0°-40°	714.0	28.4
0°-60°	1103.5	43.9
0°-90°	1278.5	50.8
90°-120°	605.9	24.1
90°-150°	1089.5	43.3
90°-180°	1238.0	49.2
0°-180°	2516.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	513	513	513	513	513	
5°	609	513	452	513	609	63
15°	866	490	361	490	866	245
25°	892	445	294	445	892	383
35°	387	388	239	388	387	254
45°	206	312	188	312	206	162
55°	130	219	129	219	130	117
65°	75	135	81	135	75	73
75°	32	66	41	66	32	34
85°	7	15	14	15	7	9
90°	10	1	10	1	10	5
95°	39	11	39	11	39	70
105°	424	39	424	39	424	418
115°	515	68	515	68	515	501
125°	406	95	406	95	406	368
135°	329	111	329	111	329	256
145°	258	127	258	127	258	164
155°	214	144	214	144	214	100
165°	186	158	186	158	186	53
175°	168	164	168	164	168	16
180°	165	165	165	165	165	



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	546.4	547.1	544.8	544.4	541.8	541.1	541.1	537.3	535.1	532.2	530.4
5°	609.2	612.7	610.9	607.0	600.4	598.8	594.7	588.1	580.6	571.4	567.0
7.5°	687.6	692.4	690.5	684.5	677.5	671.9	660.2	649.2	634.0	620.5	609.0
10°	751.9	746.9	742.9	737.0	730.6	720.3	707.9	691.1	671.6	656.1	639.0
12.5°	800.0	799.2	794.2	788.1	779.1	769.3	754.1	733.6	710.9	688.6	669.0
15°	865.6	867.0	863.7	857.3	844.5	827.2	804.4	795.8	763.3	739.1	715.0
17.5°	911.1	910.8	910.3	901.5	888.5	876.2	855.0	832.5	803.0	769.0	736.5
20°	939.9	937.6	938.1	928.2	918.6	904.3	883.6	850.9	826.8	787.5	753.8
22.5°	939.1	938.7	940.4	937.0	930.0	919.1	902.8	875.2	844.3	804.6	766.9
25°	892.0	890.2	900.5	903.4	914.6	916.6	911.7	896.6	867.4	826.5	779.8
27.5°	746.5	745.6	764.7	788.7	819.1	842.7	865.5	876.6	867.4	838.1	791.3
30°	612.7	633.3	643.0	677.7	716.3	762.4	802.9	841.2	850.7	837.9	799.6
32.5°	508.7	526.7	534.8	564.5	600.6	654.6	715.2	769.6	808.0	817.7	794.7
35°	386.9	387.1	405.6	418.8	452.1	507.7	566.6	639.4	711.9	766.9	772.5
37.5°	308.8	309.8	321.0	334.1	359.2	388.5	440.4	501.0	584.7	668.9	718.4
40°	266.6	268.5	276.9	289.8	307.8	330.1	370.4	427.5	497.4	591.2	667.8
42.5°	239.5	242.7	247.0	257.0	268.2	289.0	321.6	365.7	429.2	517.9	606.3
45°	206.4	208.2	211.5	216.1	226.2	240.6	262.6	292.3	345.0	416.3	504.8
47.5°	182.1	181.2	184.6	188.3	195.1	205.0	219.7	243.8	281.4	338.7	413.8
50°	165.6	165.3	167.8	170.6	177.0	184.3	196.3	214.5	244.4	291.8	360.6
52.5°	150.1	150.9	152.7	156.2	160.8	166.6	177.5	190.7	216.3	257.2	314.5
55°	129.6	130.3	132.6	134.6	137.9	143.8	150.6	161.6	179.2	207.7	255.0
57.5°	112.2	111.9	114.1	114.7	118.4	123.2	128.5	137.0	149.8	171.0	202.7
60°	100.6	99.9	101.9	103.4	105.4	109.3	113.8	122.1	132.2	147.8	175.0
62.5°	90.0	89.7	91.1	92.7	94.3	97.9	101.6	108.0	116.0	129.1	150.8
65°	74.6	75.3	76.0	76.6	77.5	79.7	83.2	87.7	93.1	102.4	117.9
67.5°	58.7	59.4	59.6	60.9	62.8	64.2	66.4	70.2	74.1	81.8	90.7
70°	47.4	47.2	47.4	48.1	50.5	52.9	55.8	58.6	61.1	66.5	74.0
72.5°	40.7	40.3	40.9	41.1	42.2	42.9	44.7	47.4	50.5	54.2	59.6
75°	31.6	31.6	31.6	31.6	32.5	32.9	33.6	34.2	35.3	37.1	41.1
77.5°	23.4	23.4	23.8	23.9	24.1	24.4	24.8	25.4	25.8	26.8	28.5
80°	18.5	18.7	18.5	18.7	18.7	19.1	19.3	20.0	20.2	21.3	22.0
82.5°	13.9	13.8	13.9	14.1	14.1	14.5	14.6	15.1	15.1	15.6	16.3
85°	7.4	7.1	7.4	7.3	7.7	7.3	7.4	7.9	7.9	8.1	9.0
87.5°	3.7	4.1	3.7	3.8	3.9	3.9	3.9	3.8	4.1	4.0	4.0
90°	9.6	10.0	9.6	9.3	9.6	9.0	8.7	8.3	8.0	8.3	7.4
92.5°	16.0	16.7	16.3	17.3	17.9	19.6	22.2	28.1	38.6	51.2	56.4
95°	38.6	40.0	42.3	45.3	51.7	63.6	81.2	119.9	160.2	197.6	175.9
97.5°	105.2	108.0	117.1	132.1	156.7	196.4	239.4	298.9	327.4	306.1	224.1
100°	208.9	208.5	221.5	245.8	279.5	326.8	365.7	392.7	381.1	315.5	213.2
102.5°	306.3	314.1	324.9	344.1	370.3	400.3	423.0	423.9	383.7	298.1	197.2
105°	423.7	425.4	436.0	448.7	464.0	472.6	466.3	433.0	363.4	267.8	177.6
107.5°	491.3	494.3	497.9	502.2	501.9	490.0	460.8	406.7	327.8	241.0	165.0
110°	519.0	519.6	520.3	517.6	508.3	484.9	443.0	381.7	305.5	225.8	160.2



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	524.5	524.4	521.9	513.6	496.5	466.6	419.5	356.9	286.0	215.7	157.5
115°	515.3	513.6	506.9	492.3	467.3	431.0	382.0	324.0	262.5	204.8	156.6
117.5°	485.8	483.5	474.0	457.2	431.1	394.3	350.3	300.3	248.3	198.4	157.1
120°	461.3	459.3	451.3	432.6	406.3	372.7	332.7	287.8	240.8	195.5	158.3
122.5°	438.4	435.8	427.1	410.3	386.9	355.6	318.6	278.0	234.7	193.7	160.0
125°	406.3	404.1	395.7	381.1	359.8	333.1	301.1	264.8	226.9	191.1	162.9
127.5°	379.9	377.9	370.3	357.8	338.8	314.5	285.7	253.4	219.9	190.0	166.1
130°	365.0	362.4	355.4	343.4	325.7	303.1	276.2	246.1	216.1	189.2	168.2
132.5°	350.4	348.6	342.3	330.4	313.8	292.2	267.0	239.5	212.7	188.9	169.8
135°	329.4	327.1	321.1	311.1	294.7	275.8	254.1	230.5	208.2	188.5	172.2
137.5°	307.3	305.7	300.7	290.5	276.8	260.3	241.7	222.3	204.2	187.8	173.8
140°	291.8	292.1	286.8	277.5	264.8	250.4	234.5	217.5	201.8	187.6	174.8
142.5°	277.4	277.7	273.0	264.7	253.8	241.4	227.5	213.0	199.7	187.0	175.7
145°	257.5	256.8	254.1	247.1	238.8	229.1	218.5	207.5	196.8	186.2	176.2
147.5°	241.1	240.8	238.3	233.6	227.2	220.4	211.8	203.0	194.1	184.9	176.2
150°	231.5	231.5	229.5	225.8	220.8	214.5	207.5	199.8	192.2	183.9	176.2
152.5°	223.5	223.5	222.3	218.9	215.0	209.7	203.5	196.9	190.0	182.6	175.4
155°	213.5	213.2	212.5	209.8	206.8	202.8	197.8	192.6	186.8	180.2	174.6
157.5°	204.3	204.4	203.9	201.9	199.3	196.1	192.3	187.8	183.2	178.1	173.4
160°	198.5	198.9	198.9	196.8	194.5	192.2	188.9	185.2	180.9	176.5	172.9
162.5°	193.2	193.5	193.5	191.8	190.3	188.2	185.1	182.0	178.4	174.9	171.8
165°	186.2	186.2	186.5	185.2	183.9	182.2	179.8	177.9	175.2	172.6	170.2
167.5°	179.6	179.6	179.8	178.9	178.3	177.1	175.8	174.3	172.1	170.1	168.6
170°	175.5	175.5	175.9	175.2	174.8	174.2	172.9	171.8	170.2	168.5	167.6
172.5°	171.8	172.1	172.7	172.0	171.9	171.5	170.5	169.8	168.3	167.2	166.7
175°	167.6	167.9	168.2	167.9	167.9	167.9	167.2	166.8	166.2	165.5	165.5
177.5°	165.0	165.0	165.6	165.3	165.6	165.6	165.3	165.0	164.9	164.6	164.9
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	529.6	529.1	526.7	523.9	520.2	517.7	515.8	514.7	511.5	507.7	505.1
5°	562.4	555.8	548.7	540.2	532.3	524.1	519.2	513.2	506.0	497.9	492.1
7.5°	597.4	584.5	570.6	556.2	542.1	529.3	518.0	508.4	496.9	485.2	477.1
10°	624.3	605.4	585.9	565.9	547.7	530.6	517.4	504.4	490.6	477.2	467.0
12.5°	648.8	623.9	601.3	576.7	553.5	533.0	514.1	498.8	482.1	467.9	456.4
15°	679.7	654.1	627.0	589.6	558.6	532.7	509.6	489.7	469.5	451.9	440.7
17.5°	708.5	670.2	633.6	602.5	562.2	529.9	501.7	477.9	455.6	437.1	423.2
20°	720.5	683.3	643.7	603.9	564.4	528.1	495.4	469.0	446.0	424.9	412.2
22.5°	727.6	685.7	643.8	601.1	559.1	521.4	489.1	460.1	435.1	415.1	399.4
25°	736.0	686.0	639.9	597.8	554.9	514.1	475.6	444.9	417.9	396.6	379.9
27.5°	741.6	682.7	628.2	581.4	537.9	497.3	462.0	429.4	402.0	379.5	361.6
30°	742.6	680.0	619.3	568.5	524.4	487.0	449.7	418.6	389.6	365.6	348.9
32.5°	744.0	673.5	607.1	553.3	508.0	471.1	437.2	407.5	377.8	354.2	337.1
35°	738.3	670.0	588.7	526.8	481.5	445.7	415.3	387.8	358.6	335.7	318.4
37.5°	713.3	655.7	569.7	497.0	449.7	416.6	391.7	367.8	341.0	316.3	300.0
40°	688.2	641.7	554.9	478.9	429.5	395.5	373.1	353.5	327.6	304.5	287.0
42.5°	650.8	622.5	540.8	460.0	406.7	373.9	355.0	336.7	314.0	290.5	274.0
45°	582.1	585.9	512.1	429.7	375.0	342.1	324.3	311.6	291.4	272.1	255.1
47.5°	496.1	530.9	478.3	397.6	341.8	310.9	295.3	284.2	270.5	251.6	236.1
50°	439.9	489.7	451.3	376.0	320.8	290.1	274.8	265.7	253.8	238.9	224.2
52.5°	388.0	441.6	418.6	351.9	298.1	270.0	255.1	247.6	238.2	224.1	210.8
55°	316.4	370.7	365.4	315.6	264.2	238.9	227.5	219.1	212.8	202.3	191.7
57.5°	256.0	307.4	310.1	275.1	234.2	209.2	199.4	193.1	189.0	181.1	171.3
60°	217.8	265.0	274.3	247.9	212.8	190.9	181.2	176.1	172.9	166.5	159.0
62.5°	186.2	226.4	236.9	217.9	192.3	171.6	164.1	159.3	157.0	151.6	145.0
65°	142.5	175.9	186.0	175.5	162.0	145.6	139.4	135.3	133.3	130.3	125.4
67.5°	107.2	131.5	142.6	135.2	130.3	119.9	116.0	113.8	112.0	109.9	105.8
70°	86.1	104.1	115.5	113.6	109.6	104.1	101.2	99.7	97.9	96.1	92.7
72.5°	69.2	81.6	92.3	93.3	90.1	89.0	86.4	85.8	84.7	82.7	80.7
75°	45.9	54.5	61.9	64.8	66.1	67.2	66.1	65.9	65.7	63.9	62.8
77.5°	30.1	34.7	39.4	44.3	46.4	47.8	48.2	49.0	48.4	47.5	46.9
80°	23.1	24.1	27.4	31.6	34.9	36.2	37.1	37.5	37.3	37.1	36.2
82.5°	16.8	17.6	19.2	22.1	24.9	27.1	27.6	27.5	28.0	28.2	27.4
85°	9.0	9.2	9.7	10.1	11.6	14.0	14.7	15.2	15.6	15.6	14.2
87.5°	4.1	3.7	3.9	3.7	4.1	4.1	5.0	5.7	6.0	5.5	5.7
90°	6.3	5.4	4.3	3.7	3.0	2.0	1.3	0.7	1.3	2.0	3.0
92.5°	42.3	28.0	19.2	14.3	11.5	9.0	6.1	4.1	6.1	9.0	11.5
95°	121.2	71.6	43.3	30.3	21.7	16.0	12.3	11.3	12.3	16.0	21.7
97.5°	133.0	77.1	50.0	36.0	27.4	22.5	19.6	19.3	19.6	22.5	27.4
100°	125.5	76.3	53.0	40.0	32.0	27.3	25.0	24.7	25.0	27.3	32.0
102.5°	119.1	77.4	56.5	44.5	37.3	32.9	30.8	30.3	30.8	32.9	37.3
105°	114.6	80.3	62.3	51.9	45.6	41.7	39.7	38.6	39.7	41.7	45.6
107.5°	114.2	85.8	69.9	60.3	54.4	50.5	48.5	47.6	48.5	50.5	54.4
110°	115.6	90.3	75.3	66.0	60.3	56.6	55.0	53.9	55.0	56.6	60.3



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	118.3	94.8	80.9	71.8	66.2	62.5	60.8	59.9	60.8	62.5	66.2
115°	122.5	102.3	89.6	80.6	74.9	71.6	69.7	68.2	69.7	71.6	74.9
117.5°	128.3	110.2	97.6	89.4	83.0	79.9	78.2	76.7	78.2	79.9	83.0
120°	132.5	115.3	103.2	94.9	88.6	85.3	83.6	82.6	83.6	85.3	88.6
122.5°	136.6	120.6	108.9	100.0	94.0	90.3	88.7	87.7	88.7	90.3	94.0
125°	142.9	128.3	116.6	107.5	101.2	97.6	95.6	94.9	95.6	97.6	101.2
127.5°	148.1	134.9	123.7	114.6	107.6	104.0	101.4	100.5	101.4	104.0	107.6
130°	151.6	138.9	127.9	118.9	111.9	107.9	104.9	104.0	104.9	107.9	111.9
132.5°	154.8	142.3	131.7	122.9	115.9	111.1	107.8	106.6	107.8	111.1	115.9
135°	158.9	147.5	137.2	128.3	121.2	116.2	112.5	111.2	112.5	116.2	121.2
137.5°	161.9	151.2	141.2	132.9	125.9	120.6	117.1	115.6	117.1	120.6	125.9
140°	163.5	153.5	143.9	135.5	128.9	123.6	120.3	118.6	120.3	123.6	128.9
142.5°	165.1	155.4	146.0	138.3	131.6	126.8	123.2	121.8	123.2	126.8	131.6
145°	166.8	157.9	149.2	141.6	135.9	130.9	127.9	126.9	127.9	130.9	135.9
147.5°	168.0	159.9	151.9	145.4	140.0	135.6	132.7	132.1	132.7	135.6	140.0
150°	168.2	161.2	153.5	147.5	142.9	138.6	135.9	135.5	135.9	138.6	142.9
152.5°	168.7	162.0	155.4	149.7	145.5	141.8	139.1	139.0	139.1	141.8	145.5
155°	168.9	163.5	157.9	153.3	149.6	146.2	144.2	144.2	144.2	146.2	149.6
157.5°	169.2	164.4	159.9	156.3	153.2	150.2	148.6	148.4	148.6	150.2	153.2
160°	169.2	165.2	161.2	157.9	155.5	152.9	151.6	151.6	151.6	152.9	155.5
162.5°	168.9	165.5	162.0	159.2	157.1	155.0	153.9	153.9	153.9	155.0	157.1
165°	168.2	165.9	163.2	160.9	159.6	157.9	157.2	157.5	157.2	157.9	159.6
167.5°	167.7	165.8	163.9	162.4	161.5	160.2	159.9	160.2	159.9	160.2	161.5
170°	166.8	165.5	163.9	163.2	162.5	161.6	161.2	161.8	161.2	161.6	162.5
172.5°	166.6	165.5	164.1	163.7	163.3	162.6	162.5	163.0	162.5	162.6	163.3
175°	165.9	165.2	164.6	164.2	164.2	163.5	163.9	164.2	163.9	163.5	164.2
177.5°	165.3	164.9	164.6	164.6	164.6	164.3	164.6	164.9	164.6	164.3	164.6
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	504.2	501.9	500.3	496.8	494.6	492.1	489.7	491.2	491.0	490.9	490.9
5°	487.3	482.2	477.6	471.6	468.0	463.4	459.9	459.4	460.2	457.2	455.4
7.5°	470.5	463.6	457.0	450.5	443.6	438.0	434.6	432.9	430.7	428.9	426.9
10°	458.7	450.6	444.2	436.1	428.7	422.1	417.9	415.0	413.5	412.0	409.1
12.5°	446.6	438.7	430.6	421.3	414.2	406.6	403.5	400.3	397.4	395.6	391.7
15°	428.9	418.6	410.0	400.3	392.4	384.9	380.6	374.2	373.3	371.1	367.1
17.5°	411.0	399.9	388.0	380.9	372.0	364.2	357.5	355.4	349.1	346.8	343.3
20°	397.0	386.7	377.7	368.3	355.3	348.1	342.8	340.0	334.9	331.8	329.6
22.5°	384.9	374.4	364.0	353.0	342.3	334.1	330.3	325.8	323.1	318.8	316.4
25°	367.6	356.2	343.7	331.8	324.1	318.0	311.8	307.8	303.9	301.9	297.6
27.5°	347.5	335.5	323.9	314.8	305.4	299.4	293.8	290.3	285.5	282.2	279.7
30°	336.4	322.3	312.3	304.2	292.1	286.3	282.2	277.8	274.3	270.8	268.3
32.5°	323.6	310.8	301.2	291.2	281.9	275.6	270.2	266.4	263.3	260.0	257.6
35°	303.5	292.8	282.9	272.8	265.9	259.6	253.2	249.9	247.0	243.9	241.8
37.5°	285.3	275.2	265.8	256.3	247.8	242.6	237.5	235.0	231.1	229.0	226.9
40°	274.1	264.2	254.1	244.9	236.1	232.1	227.5	223.8	220.3	218.7	216.3
42.5°	261.7	251.8	243.4	233.5	226.2	220.8	216.6	212.5	209.9	207.6	206.3
45°	243.6	234.8	226.4	216.5	209.7	205.1	200.3	196.5	194.2	192.6	190.2
47.5°	225.8	217.1	208.6	200.0	193.4	188.1	183.2	180.7	177.5	175.6	174.0
50°	213.0	205.1	196.1	188.2	181.6	176.3	172.4	169.1	166.3	163.8	162.7
52.5°	201.2	192.8	185.0	177.7	170.7	164.8	161.2	157.7	155.5	152.8	151.5
55°	181.8	173.7	167.1	159.9	153.1	148.0	143.6	140.5	138.4	135.3	133.6
57.5°	163.6	156.3	148.5	142.1	135.2	130.9	127.2	123.1	120.4	118.0	116.2
60°	151.3	143.0	136.1	130.3	124.0	118.6	115.3	112.0	109.1	106.7	105.2
62.5°	138.5	131.2	124.7	118.3	112.6	107.8	104.1	101.3	98.8	97.3	95.7
65°	118.8	113.1	106.5	101.2	96.0	92.5	89.4	87.0	85.2	84.1	82.8
67.5°	100.7	95.2	89.4	84.3	80.7	78.0	76.1	74.0	73.0	71.6	70.8
70°	89.0	83.2	78.1	74.2	70.7	68.7	67.4	65.9	65.0	63.2	62.4
72.5°	76.2	72.0	68.3	65.1	62.3	60.5	58.8	56.9	55.5	53.5	52.7
75°	59.9	56.2	53.3	51.2	49.4	47.0	44.6	42.6	41.9	41.3	41.1
77.5°	44.4	42.0	40.0	38.1	35.9	34.2	33.6	33.2	33.1	32.7	32.7
80°	34.9	32.7	31.2	29.0	27.7	27.7	27.7	27.2	27.4	27.4	27.4
82.5°	25.9	23.9	23.1	22.3	22.1	22.2	22.2	22.3	22.1	22.5	22.3
85°	13.4	13.6	14.0	13.9	14.0	14.0	14.5	14.2	14.5	14.0	14.5
87.5°	5.7	6.3	6.7	7.1	7.4	7.4	7.5	7.6	7.9	7.9	8.1
90°	3.7	4.3	5.4	6.3	7.4	8.3	8.0	8.3	8.7	9.0	9.6
92.5°	14.3	19.2	28.0	42.3	56.4	51.2	38.6	28.1	22.2	19.6	17.9
95°	30.3	43.3	71.6	121.2	175.9	197.6	160.2	119.9	81.2	63.6	51.7
97.5°	36.0	50.0	77.1	133.0	224.1	306.1	327.4	298.9	239.4	196.4	156.7
100°	40.0	53.0	76.3	125.5	213.2	315.5	381.1	392.7	365.7	326.8	279.5
102.5°	44.5	56.5	77.4	119.1	197.2	298.1	383.7	423.9	423.0	400.3	370.3
105°	51.9	62.3	80.3	114.6	177.6	267.8	363.4	433.0	466.3	472.6	464.0
107.5°	60.3	69.9	85.8	114.2	165.0	241.0	327.8	406.7	460.8	490.0	501.9
110°	66.0	75.3	90.3	115.6	160.2	225.8	305.5	381.7	443.0	484.9	508.3



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	71.8	80.9	94.8	118.3	157.5	215.7	286.0	356.9	419.5	466.6	496.5
115°	80.6	89.6	102.3	122.5	156.6	204.8	262.5	324.0	382.0	431.0	467.3
117.5°	89.4	97.6	110.2	128.3	157.1	198.4	248.3	300.3	350.3	394.3	431.1
120°	94.9	103.2	115.3	132.5	158.3	195.5	240.8	287.8	332.7	372.7	406.3
122.5°	100.0	108.9	120.6	136.6	160.0	193.7	234.7	278.0	318.6	355.6	386.9
125°	107.5	116.6	128.3	142.9	162.9	191.1	226.9	264.8	301.1	333.1	359.8
127.5°	114.6	123.7	134.9	148.1	166.1	190.0	219.9	253.4	285.7	314.5	338.8
130°	118.9	127.9	138.9	151.6	168.2	189.2	216.1	246.1	276.2	303.1	325.7
132.5°	122.9	131.7	142.3	154.8	169.8	188.9	212.7	239.5	267.0	292.2	313.8
135°	128.3	137.2	147.5	158.9	172.2	188.5	208.2	230.5	254.1	275.8	294.7
137.5°	132.9	141.2	151.2	161.9	173.8	187.8	204.2	222.3	241.7	260.3	276.8
140°	135.5	143.9	153.5	163.5	174.8	187.6	201.8	217.5	234.5	250.4	264.8
142.5°	138.3	146.0	155.4	165.1	175.7	187.0	199.7	213.0	227.5	241.4	253.8
145°	141.6	149.2	157.9	166.8	176.2	186.2	196.8	207.5	218.5	229.1	238.8
147.5°	145.4	151.9	159.9	168.0	176.2	184.9	194.1	203.0	211.8	220.4	227.2
150°	147.5	153.5	161.2	168.2	176.2	183.9	192.2	199.8	207.5	214.5	220.8
152.5°	149.7	155.4	162.0	168.7	175.4	182.6	190.0	196.9	203.5	209.7	215.0
155°	153.3	157.9	163.5	168.9	174.6	180.2	186.8	192.6	197.8	202.8	206.8
157.5°	156.3	159.9	164.4	169.2	173.4	178.1	183.2	187.8	192.3	196.1	199.3
160°	157.9	161.2	165.2	169.2	172.9	176.5	180.9	185.2	188.9	192.2	194.5
162.5°	159.2	162.0	165.5	168.9	171.8	174.9	178.4	182.0	185.1	188.2	190.3
165°	160.9	163.2	165.9	168.2	170.2	172.6	175.2	177.9	179.8	182.2	183.9
167.5°	162.4	163.9	165.8	167.7	168.6	170.1	172.1	174.3	175.8	177.1	178.3
170°	163.2	163.9	165.5	166.8	167.6	168.5	170.2	171.8	172.9	174.2	174.8
172.5°	163.7	164.1	165.5	166.6	166.7	167.2	168.3	169.8	170.5	171.5	171.9
175°	164.2	164.6	165.2	165.9	165.5	165.5	166.2	166.8	167.2	167.9	167.9
177.5°	164.6	164.6	164.9	165.3	164.9	164.6	164.9	165.0	165.3	165.6	165.6
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	488.7	488.5	488.7	488.0	488.7	488.5	488.7	490.9	490.9	491.0	491.2
5°	454.8	454.6	453.9	451.9	453.9	454.6	454.8	455.4	457.2	460.2	459.4
7.5°	425.1	424.8	422.9	422.9	422.9	424.8	425.1	426.9	428.9	430.7	432.9
10°	407.6	407.7	405.1	403.6	405.1	407.7	407.6	409.1	412.0	413.5	415.0
12.5°	390.5	389.6	387.4	385.7	387.4	389.6	390.5	391.7	395.6	397.4	400.3
15°	368.1	365.8	360.6	361.0	360.6	365.8	368.1	367.1	371.1	373.3	374.2
17.5°	341.6	340.0	339.9	336.8	339.9	340.0	341.6	343.3	346.8	349.1	355.4
20°	326.1	325.0	325.5	322.3	325.5	325.0	326.1	329.6	331.8	334.9	340.0
22.5°	314.0	312.8	311.0	310.1	311.0	312.8	314.0	316.4	318.8	323.1	325.8
25°	296.2	294.5	292.8	293.8	292.8	294.5	296.2	297.6	301.9	303.9	307.8
27.5°	278.5	277.2	275.4	275.2	275.4	277.2	278.5	279.7	282.2	285.5	290.3
30°	267.2	265.9	265.0	263.9	265.0	265.9	267.2	268.3	270.8	274.3	277.8
32.5°	255.8	255.5	254.0	253.7	254.0	255.5	255.8	257.6	260.0	263.3	266.4
35°	240.9	239.6	239.1	239.3	239.1	239.6	240.9	241.8	243.9	247.0	249.9
37.5°	226.7	225.0	224.1	223.4	224.1	225.0	226.7	226.9	229.0	231.1	235.0
40°	216.5	214.8	214.3	213.9	214.3	214.8	216.5	216.3	218.7	220.3	223.8
42.5°	205.1	204.4	204.2	203.3	204.2	204.4	205.1	206.3	207.6	209.9	212.5
45°	189.5	189.3	187.9	188.4	187.9	189.3	189.5	190.2	192.6	194.2	196.5
47.5°	173.1	172.1	171.2	171.8	171.2	172.1	173.1	174.0	175.6	177.5	180.7
50°	161.8	161.4	159.4	159.9	159.4	161.4	161.8	162.7	163.8	166.3	169.1
52.5°	150.6	148.9	148.2	147.9	148.2	148.9	150.6	151.5	152.8	155.5	157.7
55°	132.0	130.0	129.1	128.7	129.1	130.0	132.0	133.6	135.3	138.4	140.5
57.5°	113.7	113.2	112.4	112.9	112.4	113.2	113.7	116.2	118.0	120.4	123.1
60°	103.0	103.0	103.0	102.7	103.0	103.0	103.0	105.2	106.7	109.1	112.0
62.5°	94.7	94.2	94.1	94.3	94.1	94.2	94.7	95.7	97.3	98.8	101.3
65°	82.1	81.9	81.1	80.8	81.1	81.9	82.1	82.8	84.1	85.2	87.0
67.5°	70.2	69.5	69.2	68.9	69.2	69.5	70.2	70.8	71.6	73.0	74.0
70°	61.3	60.8	59.5	59.8	59.5	60.8	61.3	62.4	63.2	65.0	65.9
72.5°	51.7	51.2	50.9	50.6	50.9	51.2	51.7	52.7	53.5	55.5	56.9
75°	40.8	40.6	40.4	41.3	40.4	40.6	40.8	41.1	41.3	41.9	42.6
77.5°	32.7	32.7	32.9	32.5	32.9	32.7	32.7	32.7	32.7	33.1	33.2
80°	27.4	27.4	27.2	27.2	27.2	27.4	27.4	27.4	27.4	27.4	27.2
82.5°	22.0	22.1	22.3	22.0	22.3	22.1	22.0	22.3	22.5	22.1	22.3
85°	14.5	14.2	14.7	14.5	14.7	14.2	14.5	14.5	14.0	14.5	14.2
87.5°	8.4	8.1	8.1	8.3	8.1	8.1	8.4	8.1	7.9	7.9	7.6
90°	9.3	9.6	10.0	9.6	10.0	9.6	9.3	9.6	9.0	8.7	8.3
92.5°	17.3	16.3	16.7	16.0	16.7	16.3	17.3	17.9	19.6	22.2	28.1
95°	45.3	42.3	40.0	38.6	40.0	42.3	45.3	51.7	63.6	81.2	119.9
97.5°	132.1	117.1	108.0	105.2	108.0	117.1	132.1	156.7	196.4	239.4	298.9
100°	245.8	221.5	208.5	208.9	208.5	221.5	245.8	279.5	326.8	365.7	392.7
102.5°	344.1	324.9	314.1	306.3	314.1	324.9	344.1	370.3	400.3	423.0	423.9
105°	448.7	436.0	425.4	423.7	425.4	436.0	448.7	464.0	472.6	466.3	433.0
107.5°	502.2	497.9	494.3	491.3	494.3	497.9	502.2	501.9	490.0	460.8	406.7
110°	517.6	520.3	519.6	519.0	519.6	520.3	517.6	508.3	484.9	443.0	381.7



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	513.6	521.9	524.4	524.5	524.4	521.9	513.6	496.5	466.6	419.5	356.9
115°	492.3	506.9	513.6	515.3	513.6	506.9	492.3	467.3	431.0	382.0	324.0
117.5°	457.2	474.0	483.5	485.8	483.5	474.0	457.2	431.1	394.3	350.3	300.3
120°	432.6	451.3	459.3	461.3	459.3	451.3	432.6	406.3	372.7	332.7	287.8
122.5°	410.3	427.1	435.8	438.4	435.8	427.1	410.3	386.9	355.6	318.6	278.0
125°	381.1	395.7	404.1	406.3	404.1	395.7	381.1	359.8	333.1	301.1	264.8
127.5°	357.8	370.3	377.9	379.9	377.9	370.3	357.8	338.8	314.5	285.7	253.4
130°	343.4	355.4	362.4	365.0	362.4	355.4	343.4	325.7	303.1	276.2	246.1
132.5°	330.4	342.3	348.6	350.4	348.6	342.3	330.4	313.8	292.2	267.0	239.5
135°	311.1	321.1	327.1	329.4	327.1	321.1	311.1	294.7	275.8	254.1	230.5
137.5°	290.5	300.7	305.7	307.3	305.7	300.7	290.5	276.8	260.3	241.7	222.3
140°	277.5	286.8	292.1	291.8	292.1	286.8	277.5	264.8	250.4	234.5	217.5
142.5°	264.7	273.0	277.7	277.4	277.7	273.0	264.7	253.8	241.4	227.5	213.0
145°	247.1	254.1	256.8	257.5	256.8	254.1	247.1	238.8	229.1	218.5	207.5
147.5°	233.6	238.3	240.8	241.1	240.8	238.3	233.6	227.2	220.4	211.8	203.0
150°	225.8	229.5	231.5	231.5	231.5	229.5	225.8	220.8	214.5	207.5	199.8
152.5°	218.9	222.3	223.5	223.5	223.5	222.3	218.9	215.0	209.7	203.5	196.9
155°	209.8	212.5	213.2	213.5	213.2	212.5	209.8	206.8	202.8	197.8	192.6
157.5°	201.9	203.9	204.4	204.3	204.4	203.9	201.9	199.3	196.1	192.3	187.8
160°	196.8	198.9	198.9	198.5	198.9	198.9	196.8	194.5	192.2	188.9	185.2
162.5°	191.8	193.5	193.5	193.2	193.5	193.5	191.8	190.3	188.2	185.1	182.0
165°	185.2	186.5	186.2	186.2	186.2	186.5	185.2	183.9	182.2	179.8	177.9
167.5°	178.9	179.8	179.6	179.6	179.6	179.8	178.9	178.3	177.1	175.8	174.3
170°	175.2	175.9	175.5	175.5	175.5	175.9	175.2	174.8	174.2	172.9	171.8
172.5°	172.0	172.7	172.1	171.8	172.1	172.7	172.0	171.9	171.5	170.5	169.8
175°	167.9	168.2	167.9	167.6	167.9	168.2	167.9	167.9	167.9	167.2	166.8
177.5°	165.3	165.6	165.0	165.0	165.0	165.6	165.3	165.6	165.6	165.3	165.0
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	489.7	492.1	494.6	496.8	500.3	501.9	504.2	505.1	507.7	511.5	514.7
5°	459.9	463.4	468.0	471.6	477.6	482.2	487.3	492.1	497.9	506.0	513.2
7.5°	434.6	438.0	443.6	450.5	457.0	463.6	470.5	477.1	485.2	496.9	508.4
10°	417.9	422.1	428.7	436.1	444.2	450.6	458.7	467.0	477.2	490.6	504.4
12.5°	403.5	406.6	414.2	421.3	430.6	438.7	446.6	456.4	467.9	482.1	498.8
15°	380.6	384.9	392.4	400.3	410.0	418.6	428.9	440.7	451.9	469.5	489.7
17.5°	357.5	364.2	372.0	380.9	388.0	399.9	411.0	423.2	437.1	455.6	477.9
20°	342.8	348.1	355.3	368.3	377.7	386.7	397.0	412.2	424.9	446.0	469.0
22.5°	330.3	334.1	342.3	353.0	364.0	374.4	384.9	399.4	415.1	435.1	460.1
25°	311.8	318.0	324.1	331.8	343.7	356.2	367.6	379.9	396.6	417.9	444.9
27.5°	293.8	299.4	305.4	314.8	323.9	335.5	347.5	361.6	379.5	402.0	429.4
30°	282.2	286.3	292.1	304.2	312.3	322.3	336.4	348.9	365.6	389.6	418.6
32.5°	270.2	275.6	281.9	291.2	301.2	310.8	323.6	337.1	354.2	377.8	407.5
35°	253.2	259.6	265.9	272.8	282.9	292.8	303.5	318.4	335.7	358.6	387.8
37.5°	237.5	242.6	247.8	256.3	265.8	275.2	285.3	300.0	316.3	341.0	367.8
40°	227.5	232.1	236.1	244.9	254.1	264.2	274.1	287.0	304.5	327.6	353.5
42.5°	216.6	220.8	226.2	233.5	243.4	251.8	261.7	274.0	290.5	314.0	336.7
45°	200.3	205.1	209.7	216.5	226.4	234.8	243.6	255.1	272.1	291.4	311.6
47.5°	183.2	188.1	193.4	200.0	208.6	217.1	225.8	236.1	251.6	270.5	284.2
50°	172.4	176.3	181.6	188.2	196.1	205.1	213.0	224.2	238.9	253.8	265.7
52.5°	161.2	164.8	170.7	177.7	185.0	192.8	201.2	210.8	224.1	238.2	247.6
55°	143.6	148.0	153.1	159.9	167.1	173.7	181.8	191.7	202.3	212.8	219.1
57.5°	127.2	130.9	135.2	142.1	148.5	156.3	163.6	171.3	181.1	189.0	193.1
60°	115.3	118.6	124.0	130.3	136.1	143.0	151.3	159.0	166.5	172.9	176.1
62.5°	104.1	107.8	112.6	118.3	124.7	131.2	138.5	145.0	151.6	157.0	159.3
65°	89.4	92.5	96.0	101.2	106.5	113.1	118.8	125.4	130.3	133.3	135.3
67.5°	76.1	78.0	80.7	84.3	89.4	95.2	100.7	105.8	109.9	112.0	113.8
70°	67.4	68.7	70.7	74.2	78.1	83.2	89.0	92.7	96.1	97.9	99.7
72.5°	58.8	60.5	62.3	65.1	68.3	72.0	76.2	80.7	82.7	84.7	85.8
75°	44.6	47.0	49.4	51.2	53.3	56.2	59.9	62.8	63.9	65.7	65.9
77.5°	33.6	34.2	35.9	38.1	40.0	42.0	44.4	46.9	47.5	48.4	49.0
80°	27.7	27.7	27.7	29.0	31.2	32.7	34.9	36.2	37.1	37.3	37.5
82.5°	22.2	22.2	22.1	22.3	23.1	23.9	25.9	27.4	28.2	28.0	27.5
85°	14.5	14.0	14.0	13.9	14.0	13.6	13.4	14.2	15.6	15.6	15.2
87.5°	7.5	7.4	7.4	7.1	6.7	6.3	5.7	5.7	5.5	6.0	5.7
90°	8.0	8.3	7.4	6.3	5.4	4.3	3.7	3.0	2.0	1.3	0.7
92.5°	38.6	51.2	56.4	42.3	28.0	19.2	14.3	11.5	9.0	6.1	4.1
95°	160.2	197.6	175.9	121.2	71.6	43.3	30.3	21.7	16.0	12.3	11.3
97.5°	327.4	306.1	224.1	133.0	77.1	50.0	36.0	27.4	22.5	19.6	19.3
100°	381.1	315.5	213.2	125.5	76.3	53.0	40.0	32.0	27.3	25.0	24.7
102.5°	383.7	298.1	197.2	119.1	77.4	56.5	44.5	37.3	32.9	30.8	30.3
105°	363.4	267.8	177.6	114.6	80.3	62.3	51.9	45.6	41.7	39.7	38.6
107.5°	327.8	241.0	165.0	114.2	85.8	69.9	60.3	54.4	50.5	48.5	47.6
110°	305.5	225.8	160.2	115.6	90.3	75.3	66.0	60.3	56.6	55.0	53.9



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	286.0	215.7	157.5	118.3	94.8	80.9	71.8	66.2	62.5	60.8	59.9
115°	262.5	204.8	156.6	122.5	102.3	89.6	80.6	74.9	71.6	69.7	68.2
117.5°	248.3	198.4	157.1	128.3	110.2	97.6	89.4	83.0	79.9	78.2	76.7
120°	240.8	195.5	158.3	132.5	115.3	103.2	94.9	88.6	85.3	83.6	82.6
122.5°	234.7	193.7	160.0	136.6	120.6	108.9	100.0	94.0	90.3	88.7	87.7
125°	226.9	191.1	162.9	142.9	128.3	116.6	107.5	101.2	97.6	95.6	94.9
127.5°	219.9	190.0	166.1	148.1	134.9	123.7	114.6	107.6	104.0	101.4	100.5
130°	216.1	189.2	168.2	151.6	138.9	127.9	118.9	111.9	107.9	104.9	104.0
132.5°	212.7	188.9	169.8	154.8	142.3	131.7	122.9	115.9	111.1	107.8	106.6
135°	208.2	188.5	172.2	158.9	147.5	137.2	128.3	121.2	116.2	112.5	111.2
137.5°	204.2	187.8	173.8	161.9	151.2	141.2	132.9	125.9	120.6	117.1	115.6
140°	201.8	187.6	174.8	163.5	153.5	143.9	135.5	128.9	123.6	120.3	118.6
142.5°	199.7	187.0	175.7	165.1	155.4	146.0	138.3	131.6	126.8	123.2	121.8
145°	196.8	186.2	176.2	166.8	157.9	149.2	141.6	135.9	130.9	127.9	126.9
147.5°	194.1	184.9	176.2	168.0	159.9	151.9	145.4	140.0	135.6	132.7	132.1
150°	192.2	183.9	176.2	168.2	161.2	153.5	147.5	142.9	138.6	135.9	135.5
152.5°	190.0	182.6	175.4	168.7	162.0	155.4	149.7	145.5	141.8	139.1	139.0
155°	186.8	180.2	174.6	168.9	163.5	157.9	153.3	149.6	146.2	144.2	144.2
157.5°	183.2	178.1	173.4	169.2	164.4	159.9	156.3	153.2	150.2	148.6	148.4
160°	180.9	176.5	172.9	169.2	165.2	161.2	157.9	155.5	152.9	151.6	151.6
162.5°	178.4	174.9	171.8	168.9	165.5	162.0	159.2	157.1	155.0	153.9	153.9
165°	175.2	172.6	170.2	168.2	165.9	163.2	160.9	159.6	157.9	157.2	157.5
167.5°	172.1	170.1	168.6	167.7	165.8	163.9	162.4	161.5	160.2	159.9	160.2
170°	170.2	168.5	167.6	166.8	165.5	163.9	163.2	162.5	161.6	161.2	161.8
172.5°	168.3	167.2	166.7	166.6	165.5	164.1	163.7	163.3	162.6	162.5	163.0
175°	166.2	165.5	165.5	165.9	165.2	164.6	164.2	164.2	163.5	163.9	164.2
177.5°	164.9	164.6	164.9	165.3	164.9	164.6	164.6	164.6	164.3	164.6	164.9
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	515.8	517.7	520.2	523.9	526.7	529.1	529.6	530.4	532.2	535.1	537.3
5°	519.2	524.1	532.3	540.2	548.7	555.8	562.4	567.0	571.4	580.6	588.1
7.5°	518.0	529.3	542.1	556.2	570.6	584.5	597.4	609.0	620.5	634.0	649.2
10°	517.4	530.6	547.7	565.9	585.9	605.4	624.3	639.0	656.1	671.6	691.1
12.5°	514.1	533.0	553.5	576.7	601.3	623.9	648.8	669.0	688.6	710.9	733.6
15°	509.6	532.7	558.6	589.6	627.0	654.1	679.7	715.0	739.1	763.3	795.8
17.5°	501.7	529.9	562.2	602.5	633.6	670.2	708.5	736.5	769.0	803.0	832.5
20°	495.4	528.1	564.4	603.9	643.7	683.3	720.5	753.8	787.5	826.8	850.9
22.5°	489.1	521.4	559.1	601.1	643.8	685.7	727.6	766.9	804.6	844.3	875.2
25°	475.6	514.1	554.9	597.8	639.9	686.0	736.0	779.8	826.5	867.4	896.6
27.5°	462.0	497.3	537.9	581.4	628.2	682.7	741.6	791.3	838.1	867.4	876.6
30°	449.7	487.0	524.4	568.5	619.3	680.0	742.6	799.6	837.9	850.7	841.2
32.5°	437.2	471.1	508.0	553.3	607.1	673.5	744.0	794.7	817.7	808.0	769.6
35°	415.3	445.7	481.5	526.8	588.7	670.0	738.3	772.5	766.9	711.9	639.4
37.5°	391.7	416.6	449.7	497.0	569.7	655.7	713.3	718.4	668.9	584.7	501.0
40°	373.1	395.5	429.5	478.9	554.9	641.7	688.2	667.8	591.2	497.4	427.5
42.5°	355.0	373.9	406.7	460.0	540.8	622.5	650.8	606.3	517.9	429.2	365.7
45°	324.3	342.1	375.0	429.7	512.1	585.9	582.1	504.8	416.3	345.0	292.3
47.5°	295.3	310.9	341.8	397.6	478.3	530.9	496.1	413.8	338.7	281.4	243.8
50°	274.8	290.1	320.8	376.0	451.3	489.7	439.9	360.6	291.8	244.4	214.5
52.5°	255.1	270.0	298.1	351.9	418.6	441.6	388.0	314.5	257.2	216.3	190.7
55°	227.5	238.9	264.2	315.6	365.4	370.7	316.4	255.0	207.7	179.2	161.6
57.5°	199.4	209.2	234.2	275.1	310.1	307.4	256.0	202.7	171.0	149.8	137.0
60°	181.2	190.9	212.8	247.9	274.3	265.0	217.8	175.0	147.8	132.2	122.1
62.5°	164.1	171.6	192.3	217.9	236.9	226.4	186.2	150.8	129.1	116.0	108.0
65°	139.4	145.6	162.0	175.5	186.0	175.9	142.5	117.9	102.4	93.1	87.7
67.5°	116.0	119.9	130.3	135.2	142.6	131.5	107.2	90.7	81.8	74.1	70.2
70°	101.2	104.1	109.6	113.6	115.5	104.1	86.1	74.0	66.5	61.1	58.6
72.5°	86.4	89.0	90.1	93.3	92.3	81.6	69.2	59.6	54.2	50.5	47.4
75°	66.1	67.2	66.1	64.8	61.9	54.5	45.9	41.1	37.1	35.3	34.2
77.5°	48.2	47.8	46.4	44.3	39.4	34.7	30.1	28.5	26.8	25.8	25.4
80°	37.1	36.2	34.9	31.6	27.4	24.1	23.1	22.0	21.3	20.2	20.0
82.5°	27.6	27.1	24.9	22.1	19.2	17.6	16.8	16.3	15.6	15.1	15.1
85°	14.7	14.0	11.6	10.1	9.7	9.2	9.0	9.0	8.1	7.9	7.9
87.5°	5.0	4.1	4.1	3.7	3.9	3.7	4.1	4.0	4.0	4.1	3.8
90°	1.3	2.0	3.0	3.7	4.3	5.4	6.3	7.4	8.3	8.0	8.3
92.5°	6.1	9.0	11.5	14.3	19.2	28.0	42.3	56.4	51.2	38.6	28.1
95°	12.3	16.0	21.7	30.3	43.3	71.6	121.2	175.9	197.6	160.2	119.9
97.5°	19.6	22.5	27.4	36.0	50.0	77.1	133.0	224.1	306.1	327.4	298.9
100°	25.0	27.3	32.0	40.0	53.0	76.3	125.5	213.2	315.5	381.1	392.7
102.5°	30.8	32.9	37.3	44.5	56.5	77.4	119.1	197.2	298.1	383.7	423.9
105°	39.7	41.7	45.6	51.9	62.3	80.3	114.6	177.6	267.8	363.4	433.0
107.5°	48.5	50.5	54.4	60.3	69.9	85.8	114.2	165.0	241.0	327.8	406.7
110°	55.0	56.6	60.3	66.0	75.3	90.3	115.6	160.2	225.8	305.5	381.7



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	60.8	62.5	66.2	71.8	80.9	94.8	118.3	157.5	215.7	286.0	356.9
115°	69.7	71.6	74.9	80.6	89.6	102.3	122.5	156.6	204.8	262.5	324.0
117.5°	78.2	79.9	83.0	89.4	97.6	110.2	128.3	157.1	198.4	248.3	300.3
120°	83.6	85.3	88.6	94.9	103.2	115.3	132.5	158.3	195.5	240.8	287.8
122.5°	88.7	90.3	94.0	100.0	108.9	120.6	136.6	160.0	193.7	234.7	278.0
125°	95.6	97.6	101.2	107.5	116.6	128.3	142.9	162.9	191.1	226.9	264.8
127.5°	101.4	104.0	107.6	114.6	123.7	134.9	148.1	166.1	190.0	219.9	253.4
130°	104.9	107.9	111.9	118.9	127.9	138.9	151.6	168.2	189.2	216.1	246.1
132.5°	107.8	111.1	115.9	122.9	131.7	142.3	154.8	169.8	188.9	212.7	239.5
135°	112.5	116.2	121.2	128.3	137.2	147.5	158.9	172.2	188.5	208.2	230.5
137.5°	117.1	120.6	125.9	132.9	141.2	151.2	161.9	173.8	187.8	204.2	222.3
140°	120.3	123.6	128.9	135.5	143.9	153.5	163.5	174.8	187.6	201.8	217.5
142.5°	123.2	126.8	131.6	138.3	146.0	155.4	165.1	175.7	187.0	199.7	213.0
145°	127.9	130.9	135.9	141.6	149.2	157.9	166.8	176.2	186.2	196.8	207.5
147.5°	132.7	135.6	140.0	145.4	151.9	159.9	168.0	176.2	184.9	194.1	203.0
150°	135.9	138.6	142.9	147.5	153.5	161.2	168.2	176.2	183.9	192.2	199.8
152.5°	139.1	141.8	145.5	149.7	155.4	162.0	168.7	175.4	182.6	190.0	196.9
155°	144.2	146.2	149.6	153.3	157.9	163.5	168.9	174.6	180.2	186.8	192.6
157.5°	148.6	150.2	153.2	156.3	159.9	164.4	169.2	173.4	178.1	183.2	187.8
160°	151.6	152.9	155.5	157.9	161.2	165.2	169.2	172.9	176.5	180.9	185.2
162.5°	153.9	155.0	157.1	159.2	162.0	165.5	168.9	171.8	174.9	178.4	182.0
165°	157.2	157.9	159.6	160.9	163.2	165.9	168.2	170.2	172.6	175.2	177.9
167.5°	159.9	160.2	161.5	162.4	163.9	165.8	167.7	168.6	170.1	172.1	174.3
170°	161.2	161.6	162.5	163.2	163.9	165.5	166.8	167.6	168.5	170.2	171.8
172.5°	162.5	162.6	163.3	163.7	164.1	165.5	166.6	166.7	167.2	168.3	169.8
175°	163.9	163.5	164.2	164.2	164.6	165.2	165.9	165.5	165.5	166.2	166.8
177.5°	164.6	164.3	164.6	164.6	164.6	164.9	165.3	164.9	164.6	164.9	165.0
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6	164.6



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	541.1	541.1	541.8	544.4	544.8	547.1	546.4
5°	594.7	598.8	600.4	607.0	610.9	612.7	609.2
7.5°	660.2	671.9	677.5	684.5	690.5	692.4	687.6
10°	707.9	720.3	730.6	737.0	742.9	746.9	751.9
12.5°	754.1	769.3	779.1	788.1	794.2	799.2	800.0
15°	804.4	827.2	844.5	857.3	863.7	867.0	865.6
17.5°	855.0	876.2	888.5	901.5	910.3	910.8	911.1
20°	883.6	904.3	918.6	928.2	938.1	937.6	939.9
22.5°	902.8	919.1	930.0	937.0	940.4	938.7	939.1
25°	911.7	916.6	914.6	903.4	900.5	890.2	892.0
27.5°	865.5	842.7	819.1	788.7	764.7	745.6	746.5
30°	802.9	762.4	716.3	677.7	643.0	633.3	612.7
32.5°	715.2	654.6	600.6	564.5	534.8	526.7	508.7
35°	566.6	507.7	452.1	418.8	405.6	387.1	386.9
37.5°	440.4	388.5	359.2	334.1	321.0	309.8	308.8
40°	370.4	330.1	307.8	289.8	276.9	268.5	266.6
42.5°	321.6	289.0	268.2	257.0	247.0	242.7	239.5
45°	262.6	240.6	226.2	216.1	211.5	208.2	206.4
47.5°	219.7	205.0	195.1	188.3	184.6	181.2	182.1
50°	196.3	184.3	177.0	170.6	167.8	165.3	165.6
52.5°	177.5	166.6	160.8	156.2	152.7	150.9	150.1
55°	150.6	143.8	137.9	134.6	132.6	130.3	129.6
57.5°	128.5	123.2	118.4	114.7	114.1	111.9	112.2
60°	113.8	109.3	105.4	103.4	101.9	99.9	100.6
62.5°	101.6	97.9	94.3	92.7	91.1	89.7	90.0
65°	83.2	79.7	77.5	76.6	76.0	75.3	74.6
67.5°	66.4	64.2	62.8	60.9	59.6	59.4	58.7
70°	55.8	52.9	50.5	48.1	47.4	47.2	47.4
72.5°	44.7	42.9	42.2	41.1	40.9	40.3	40.7
75°	33.6	32.9	32.5	31.6	31.6	31.6	31.6
77.5°	24.8	24.4	24.1	23.9	23.8	23.4	23.4
80°	19.3	19.1	18.7	18.7	18.5	18.7	18.5
82.5°	14.6	14.5	14.1	14.1	13.9	13.8	13.9
85°	7.4	7.3	7.7	7.3	7.4	7.1	7.4
87.5°	3.9	3.9	3.9	3.8	3.7	4.1	3.7
90°	8.7	9.0	9.6	9.3	9.6	10.0	9.6
92.5°	22.2	19.6	17.9	17.3	16.3	16.7	16.0
95°	81.2	63.6	51.7	45.3	42.3	40.0	38.6
97.5°	239.4	196.4	156.7	132.1	117.1	108.0	105.2
100°	365.7	326.8	279.5	245.8	221.5	208.5	208.9
102.5°	423.0	400.3	370.3	344.1	324.9	314.1	306.3
105°	466.3	472.6	464.0	448.7	436.0	425.4	423.7
107.5°	460.8	490.0	501.9	502.2	497.9	494.3	491.3
110°	443.0	484.9	508.3	517.6	520.3	519.6	519.0



TEST NUMBER: P332242-830

CATALOG NUMBER: S123RDIP-S340D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	419.5	466.6	496.5	513.6	521.9	524.4	524.5
115°	382.0	431.0	467.3	492.3	506.9	513.6	515.3
117.5°	350.3	394.3	431.1	457.2	474.0	483.5	485.8
120°	332.7	372.7	406.3	432.6	451.3	459.3	461.3
122.5°	318.6	355.6	386.9	410.3	427.1	435.8	438.4
125°	301.1	333.1	359.8	381.1	395.7	404.1	406.3
127.5°	285.7	314.5	338.8	357.8	370.3	377.9	379.9
130°	276.2	303.1	325.7	343.4	355.4	362.4	365.0
132.5°	267.0	292.2	313.8	330.4	342.3	348.6	350.4
135°	254.1	275.8	294.7	311.1	321.1	327.1	329.4
137.5°	241.7	260.3	276.8	290.5	300.7	305.7	307.3
140°	234.5	250.4	264.8	277.5	286.8	292.1	291.8
142.5°	227.5	241.4	253.8	264.7	273.0	277.7	277.4
145°	218.5	229.1	238.8	247.1	254.1	256.8	257.5
147.5°	211.8	220.4	227.2	233.6	238.3	240.8	241.1
150°	207.5	214.5	220.8	225.8	229.5	231.5	231.5
152.5°	203.5	209.7	215.0	218.9	222.3	223.5	223.5
155°	197.8	202.8	206.8	209.8	212.5	213.2	213.5
157.5°	192.3	196.1	199.3	201.9	203.9	204.4	204.3
160°	188.9	192.2	194.5	196.8	198.9	198.9	198.5
162.5°	185.1	188.2	190.3	191.8	193.5	193.5	193.2
165°	179.8	182.2	183.9	185.2	186.5	186.2	186.2
167.5°	175.8	177.1	178.3	178.9	179.8	179.6	179.6
170°	172.9	174.2	174.8	175.2	175.9	175.5	175.5
172.5°	170.5	171.5	171.9	172.0	172.7	172.1	171.8
175°	167.2	167.9	167.9	167.9	168.2	167.9	167.6
177.5°	165.3	165.6	165.6	165.3	165.6	165.0	165.0
180°	164.6	164.6	164.6	164.6	164.6	164.6	164.6

(END OF REPORT)