

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332248-830

Luminaire Tested: **S123RDIP-S340D585U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332248-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D585U830-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3277.3 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	41	41	40	34
2	88	81	75	70	79	74	69	64	60	57	54	48	46	44	37	35	34	29
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5521	5521	5521	5521
5°	6582	5545	4883	5545
10°	8218	5513	4411	5513
15°	9646	5457	4023	5457
20°	10766	5372	3692	5372
25°	10594	5284	3489	5284
30°	7615	5203	3280	5203
35°	5084	5096	3144	5096
40°	3746	4967	3006	4967
45°	3142	4743	2868	4743
50°	2773	4449	2678	4449
55°	2432	4112	2415	4112
60°	2166	3791	2211	3791
65°	1900	3446	2058	3446
70°	1492	3138	1882	3138
75°	1314	2741	1718	2741
80°	1147	2325	1686	2325
85°	914	1877	1791	1877



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	1.5
10°-20°	157.6	4.8
20°-30°	247.6	7.6
30°-40°	258.3	7.9
40°-50°	221.1	6.7
50°-60°	168.5	5.1
60°-70°	108.0	3.3
70°-80°	52.0	1.6
80°-90°	15.8	0.5
90°-100°	147.8	4.5
100°-110°	418.5	12.8
110°-120°	411.7	12.6
120°-130°	328.4	10.0
130°-140°	258.9	7.9
140°-150°	193.2	5.9
150°-160°	134.7	4.1
160°-170°	79.1	2.4
170°-180°	25.7	0.8
0°-30°	455.6	13.9
0°-40°	714.0	21.8
0°-60°	1103.5	33.7
0°-90°	1279.3	39.0
90°-120°	978.0	29.8
90°-150°	1758.5	53.7
90°-180°	1998.0	61.0
0°-180°	3277.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	513	513	513	513	513	
5°	609	513	452	513	609	63
15°	866	490	361	490	866	245
25°	892	445	294	445	892	383
35°	387	388	239	388	387	254
45°	206	312	188	312	206	162
55°	130	219	129	219	130	117
65°	75	135	81	135	75	73
75°	32	66	41	66	32	34
85°	7	15	14	15	7	9
90°	16	1	16	1	16	8
95°	62	18	62	18	62	112
105°	684	62	684	62	684	675
115°	832	110	832	110	832	808
125°	656	153	656	153	656	594
135°	532	180	532	180	532	412
145°	416	205	416	205	416	264
155°	345	233	345	233	345	161
165°	300	254	300	254	300	86
175°	270	265	270	265	270	26
180°	266	266	266	266	266	



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	546.4	547.1	544.8	544.4	541.8	541.1	541.1	537.3	535.1	532.2	530.4
5°	609.2	612.7	610.9	607.0	600.4	598.8	594.7	588.1	580.6	571.4	567.0
7.5°	687.6	692.4	690.5	684.5	677.5	671.9	660.2	649.2	634.0	620.5	609.0
10°	751.9	746.9	742.9	737.0	730.6	720.3	707.9	691.1	671.6	656.1	639.0
12.5°	800.0	799.2	794.2	788.1	779.1	769.3	754.1	733.6	710.9	688.6	669.0
15°	865.6	867.0	863.7	857.3	844.5	827.2	804.4	795.8	763.3	739.1	715.0
17.5°	911.1	910.8	910.3	901.5	888.5	876.2	855.0	832.5	803.0	769.0	736.5
20°	939.9	937.6	938.1	928.2	918.6	904.3	883.6	850.9	826.8	787.5	753.8
22.5°	939.1	938.7	940.4	937.0	930.0	919.1	902.8	875.2	844.3	804.6	766.9
25°	892.0	890.2	900.5	903.4	914.6	916.6	911.7	896.6	867.4	826.5	779.8
27.5°	746.5	745.6	764.7	788.7	819.1	842.7	865.5	876.6	867.4	838.1	791.3
30°	612.7	633.3	643.0	677.7	716.3	762.4	802.9	841.2	850.7	837.9	799.6
32.5°	508.7	526.7	534.8	564.5	600.6	654.6	715.2	769.6	808.0	817.7	794.7
35°	386.9	387.1	405.6	418.8	452.1	507.7	566.6	639.4	711.9	766.9	772.5
37.5°	308.8	309.8	321.0	334.1	359.2	388.5	440.4	501.0	584.7	668.9	718.4
40°	266.6	268.5	276.9	289.8	307.8	330.1	370.4	427.5	497.4	591.2	667.8
42.5°	239.5	242.7	247.0	257.0	268.2	289.0	321.6	365.7	429.2	517.9	606.3
45°	206.4	208.2	211.5	216.1	226.2	240.6	262.6	292.3	345.0	416.3	504.8
47.5°	182.1	181.2	184.6	188.3	195.1	205.0	219.7	243.8	281.4	338.7	413.8
50°	165.6	165.3	167.8	170.6	177.0	184.3	196.3	214.5	244.4	291.8	360.6
52.5°	150.1	150.9	152.7	156.2	160.8	166.6	177.5	190.7	216.3	257.2	314.5
55°	129.6	130.3	132.6	134.6	137.9	143.8	150.6	161.6	179.2	207.7	255.0
57.5°	112.2	111.9	114.1	114.7	118.4	123.2	128.5	137.0	149.8	171.0	202.7
60°	100.6	99.9	101.9	103.4	105.4	109.3	113.8	122.1	132.2	147.8	175.0
62.5°	90.0	89.7	91.1	92.7	94.3	97.9	101.6	108.0	116.0	129.1	150.8
65°	74.6	75.3	76.0	76.6	77.5	79.7	83.2	87.7	93.1	102.4	117.9
67.5°	58.7	59.4	59.6	60.9	62.8	64.2	66.4	70.2	74.1	81.8	90.7
70°	47.4	47.2	47.4	48.1	50.5	52.9	55.8	58.6	61.1	66.5	74.0
72.5°	40.7	40.3	40.9	41.1	42.2	42.9	44.7	47.4	50.5	54.2	59.6
75°	31.6	31.6	31.6	31.6	32.5	32.9	33.6	34.2	35.3	37.1	41.1
77.5°	23.4	23.4	23.8	23.9	24.1	24.4	24.8	25.4	25.8	26.8	28.5
80°	18.5	18.7	18.5	18.7	18.7	19.1	19.3	20.0	20.2	21.3	22.0
82.5°	13.9	13.8	13.9	14.1	14.1	14.5	14.6	15.1	15.1	15.6	16.3
85°	7.4	7.1	7.4	7.3	7.7	7.3	7.4	7.9	7.9	8.1	9.0
87.5°	4.9	5.4	4.9	4.9	5.1	5.0	4.9	4.8	5.0	5.0	4.8
90°	15.6	16.1	15.6	15.1	15.6	14.5	13.9	13.5	12.9	13.5	11.8
92.5°	25.9	26.9	26.3	28.0	28.9	31.8	35.9	45.2	62.4	82.7	91.0
95°	62.4	64.5	68.2	73.1	83.3	102.6	131.2	193.5	258.5	318.8	283.9
97.5°	169.8	174.4	188.9	213.1	252.8	317.1	386.4	482.5	528.6	494.1	361.7
100°	337.1	336.6	357.5	396.7	451.0	527.4	590.3	633.9	615.0	509.1	344.0
102.5°	494.5	506.8	524.3	555.4	597.7	646.1	682.8	684.2	619.3	481.2	318.3
105°	683.8	686.5	703.7	724.2	748.9	762.9	752.6	698.9	586.5	432.3	286.5
107.5°	792.9	797.8	803.6	810.5	810.0	790.9	743.9	656.5	529.1	389.0	266.4
110°	837.5	838.7	839.7	835.5	820.4	782.8	715.0	616.0	492.9	364.5	258.5



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	846.6	846.4	842.4	829.0	801.4	753.1	677.1	576.1	461.6	348.2	254.3
115°	831.7	829.0	818.2	794.6	754.2	695.7	616.6	523.1	423.7	330.6	252.7
117.5°	784.1	780.5	765.0	737.9	695.9	636.4	565.4	484.7	400.8	320.3	253.6
120°	744.6	741.3	728.5	698.3	655.9	601.5	537.1	464.5	388.7	315.6	255.3
122.5°	707.6	703.5	689.3	662.2	624.4	574.0	514.3	448.6	378.8	312.5	258.4
125°	655.9	652.1	638.7	615.0	580.6	537.6	486.0	427.3	366.1	308.6	262.9
127.5°	613.3	609.8	597.7	577.5	546.9	507.7	461.2	408.9	355.0	306.6	268.1
130°	589.2	584.9	573.6	554.3	525.8	489.2	445.6	397.3	348.9	305.4	271.5
132.5°	565.5	562.5	552.5	533.2	506.4	471.6	431.0	386.5	343.3	304.9	274.1
135°	531.7	527.9	518.2	502.1	475.8	445.2	410.2	372.0	336.0	304.3	278.0
137.5°	495.9	493.4	485.2	468.9	446.8	420.2	390.1	358.8	329.7	303.1	280.5
140°	470.9	471.5	462.9	447.8	427.3	404.3	378.4	351.1	325.7	302.7	282.2
142.5°	447.7	448.3	440.5	427.2	409.7	389.6	367.3	343.7	322.3	301.8	283.5
145°	415.6	414.5	410.2	398.9	385.5	369.9	352.7	334.9	317.7	300.5	284.4
147.5°	389.1	388.7	384.6	376.9	366.7	355.7	341.8	327.7	313.2	298.5	284.4
150°	373.6	373.6	370.4	364.5	356.5	346.2	334.9	322.5	310.2	296.7	284.4
152.5°	360.7	360.7	358.8	353.3	346.9	338.5	328.5	317.8	306.8	294.6	283.1
155°	344.6	344.0	343.0	338.7	333.8	327.4	319.3	310.8	301.6	290.9	281.7
157.5°	329.9	330.0	329.1	325.9	321.7	316.7	310.4	303.2	295.8	287.5	279.8
160°	320.4	320.9	320.9	317.7	314.0	310.2	304.8	298.9	291.9	284.9	279.0
162.5°	311.8	312.4	312.4	309.5	307.1	303.8	298.8	293.8	288.0	282.4	277.3
165°	300.5	300.5	301.0	298.9	296.7	294.1	290.3	287.1	282.8	278.5	274.8
167.5°	289.7	289.7	290.3	288.8	287.9	285.9	283.7	281.3	277.8	274.6	272.1
170°	283.3	283.3	283.9	282.8	282.2	281.2	279.0	277.4	274.8	272.0	270.4
172.5°	277.3	277.8	278.7	277.6	277.5	276.8	275.1	274.0	271.7	269.8	269.1
175°	270.4	271.0	271.5	271.0	271.0	271.0	269.8	269.4	268.2	267.2	267.2
177.5°	266.5	266.5	267.3	266.8	267.3	267.3	266.8	266.5	266.0	265.6	266.0
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	529.6	529.1	526.7	523.9	520.2	517.7	515.8	514.7	511.5	507.7	505.1
5°	562.4	555.8	548.7	540.2	532.3	524.1	519.2	513.2	506.0	497.9	492.1
7.5°	597.4	584.5	570.6	556.2	542.1	529.3	518.0	508.4	496.9	485.2	477.1
10°	624.3	605.4	585.9	565.9	547.7	530.6	517.4	504.4	490.6	477.2	467.0
12.5°	648.8	623.9	601.3	576.7	553.5	533.0	514.1	498.8	482.1	467.9	456.4
15°	679.7	654.1	627.0	589.6	558.6	532.7	509.6	489.7	469.5	451.9	440.7
17.5°	708.5	670.2	633.6	602.5	562.2	529.9	501.7	477.9	455.6	437.1	423.2
20°	720.5	683.3	643.7	603.9	564.4	528.1	495.4	469.0	446.0	424.9	412.2
22.5°	727.6	685.7	643.8	601.1	559.1	521.4	489.1	460.1	435.1	415.1	399.4
25°	736.0	686.0	639.9	597.8	554.9	514.1	475.6	444.9	417.9	396.6	379.9
27.5°	741.6	682.7	628.2	581.4	537.9	497.3	462.0	429.4	402.0	379.5	361.6
30°	742.6	680.0	619.3	568.5	524.4	487.0	449.7	418.6	389.6	365.6	348.9
32.5°	744.0	673.5	607.1	553.3	508.0	471.1	437.2	407.5	377.8	354.2	337.1
35°	738.3	670.0	588.7	526.8	481.5	445.7	415.3	387.8	358.6	335.7	318.4
37.5°	713.3	655.7	569.7	497.0	449.7	416.6	391.7	367.8	341.0	316.3	300.0
40°	688.2	641.7	554.9	478.9	429.5	395.5	373.1	353.5	327.6	304.5	287.0
42.5°	650.8	622.5	540.8	460.0	406.7	373.9	355.0	336.7	314.0	290.5	274.0
45°	582.1	585.9	512.1	429.7	375.0	342.1	324.3	311.6	291.4	272.1	255.1
47.5°	496.1	530.9	478.3	397.6	341.8	310.9	295.3	284.2	270.5	251.6	236.1
50°	439.9	489.7	451.3	376.0	320.8	290.1	274.8	265.7	253.8	238.9	224.2
52.5°	388.0	441.6	418.6	351.9	298.1	270.0	255.1	247.6	238.2	224.1	210.8
55°	316.4	370.7	365.4	315.6	264.2	238.9	227.5	219.1	212.8	202.3	191.7
57.5°	256.0	307.4	310.1	275.1	234.2	209.2	199.4	193.1	189.0	181.1	171.3
60°	217.8	265.0	274.3	247.9	212.8	190.9	181.2	176.1	172.9	166.5	159.0
62.5°	186.2	226.4	236.9	217.9	192.3	171.6	164.1	159.3	157.0	151.6	145.0
65°	142.5	175.9	186.0	175.5	162.0	145.6	139.4	135.3	133.3	130.3	125.4
67.5°	107.2	131.5	142.6	135.2	130.3	119.9	116.0	113.8	112.0	109.9	105.8
70°	86.1	104.1	115.5	113.6	109.6	104.1	101.2	99.7	97.9	96.1	92.7
72.5°	69.2	81.6	92.3	93.3	90.1	89.0	86.4	85.8	84.7	82.7	80.7
75°	45.9	54.5	61.9	64.8	66.1	67.2	66.1	65.9	65.7	63.9	62.8
77.5°	30.1	34.7	39.4	44.3	46.4	47.8	48.2	49.0	48.4	47.5	46.9
80°	23.1	24.1	27.4	31.6	34.9	36.2	37.1	37.5	37.3	37.1	36.2
82.5°	16.8	17.6	19.2	22.1	24.9	27.1	27.6	27.5	28.0	28.2	27.4
85°	9.0	9.2	9.7	10.1	11.6	14.0	14.7	15.2	15.6	15.6	14.2
87.5°	4.8	4.3	4.4	4.1	4.5	4.3	5.2	5.8	6.2	5.7	6.0
90°	10.2	8.6	7.0	5.9	4.8	3.2	2.2	1.0	2.2	3.2	4.8
92.5°	68.2	45.1	31.1	23.1	18.6	14.4	9.9	6.7	9.9	14.4	18.6
95°	195.7	115.6	69.8	48.9	35.0	25.8	19.9	18.3	19.9	25.8	35.0
97.5°	214.7	124.4	80.8	58.1	44.3	36.4	31.8	31.2	31.8	36.4	44.3
100°	202.6	123.1	85.5	64.5	51.7	44.1	40.3	39.8	40.3	44.1	51.7
102.5°	192.4	124.8	91.0	71.8	60.2	53.2	49.8	48.8	49.8	53.2	60.2
105°	184.9	129.6	100.6	83.9	73.6	67.2	64.0	62.4	64.0	67.2	73.6
107.5°	184.4	138.4	112.9	97.5	87.8	81.5	78.4	76.7	78.4	81.5	87.8
110°	186.5	145.7	121.5	106.4	97.3	91.4	88.7	87.1	88.7	91.4	97.3



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	190.9	153.0	130.5	115.9	106.8	100.9	98.2	96.5	98.2	100.9	106.8
115°	197.8	165.0	144.6	130.1	120.9	115.6	112.4	110.2	112.4	115.6	120.9
117.5°	207.1	177.9	157.6	144.2	133.9	129.0	126.3	123.9	126.3	129.0	133.9
120°	214.0	186.0	166.6	153.3	143.0	137.6	135.0	133.4	135.0	137.6	143.0
122.5°	220.5	194.6	175.7	161.4	151.6	145.8	143.1	141.5	143.1	145.8	151.6
125°	230.6	207.0	188.1	173.6	163.4	157.5	154.3	153.3	154.3	157.5	163.4
127.5°	239.0	217.7	199.5	185.0	173.7	167.8	163.7	162.1	163.7	167.8	173.7
130°	244.6	224.1	206.4	191.9	180.6	174.2	169.4	167.8	169.4	174.2	180.6
132.5°	249.8	229.8	212.4	198.4	187.1	179.4	174.1	172.0	174.1	179.4	187.1
135°	256.5	238.2	221.5	207.0	195.7	187.7	181.7	179.6	181.7	187.7	195.7
137.5°	261.4	243.9	227.9	214.5	203.3	194.7	188.9	186.6	188.9	194.7	203.3
140°	264.0	247.8	232.2	218.8	208.0	199.4	194.1	191.4	194.1	199.4	208.0
142.5°	266.6	250.8	235.7	223.1	212.4	204.6	198.8	196.5	198.8	204.6	212.4
145°	269.4	254.9	240.8	228.5	219.3	211.3	206.4	204.8	206.4	211.3	219.3
147.5°	271.1	258.1	245.2	234.7	225.9	219.0	214.1	213.2	214.1	219.0	225.9
150°	271.5	260.2	247.8	238.2	230.6	223.7	219.3	218.8	219.3	223.7	230.6
152.5°	272.4	261.5	250.8	241.6	235.0	228.8	224.5	224.4	224.5	228.8	235.0
155°	272.6	264.0	254.9	247.3	241.4	236.0	232.8	232.8	232.8	236.0	241.4
157.5°	273.1	265.3	258.1	252.2	247.2	242.4	239.9	239.4	239.9	242.4	247.2
160°	273.1	266.6	260.2	254.9	251.1	246.8	244.6	244.6	244.6	246.8	251.1
162.5°	272.7	267.1	261.5	256.9	253.6	250.2	248.5	248.5	248.5	250.2	253.6
165°	271.5	267.7	263.4	259.7	257.5	254.9	253.7	254.3	253.7	254.9	257.5
167.5°	270.6	267.6	264.5	262.1	260.6	258.5	258.1	258.7	258.1	258.5	260.6
170°	269.4	267.2	264.5	263.4	262.3	260.7	260.2	261.3	260.2	260.7	262.3
172.5°	268.9	267.2	264.9	264.3	263.6	262.5	262.3	263.0	262.3	262.5	263.6
175°	267.7	266.6	265.6	265.0	265.0	264.0	264.5	265.0	264.5	264.0	265.0
177.5°	266.8	266.0	265.6	265.6	265.6	265.1	265.6	266.0	265.6	265.1	265.6
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	504.2	501.9	500.3	496.8	494.6	492.1	489.7	491.2	491.0	490.9	490.9
5°	487.3	482.2	477.6	471.6	468.0	463.4	459.9	459.4	460.2	457.2	455.4
7.5°	470.5	463.6	457.0	450.5	443.6	438.0	434.6	432.9	430.7	428.9	426.9
10°	458.7	450.6	444.2	436.1	428.7	422.1	417.9	415.0	413.5	412.0	409.1
12.5°	446.6	438.7	430.6	421.3	414.2	406.6	403.5	400.3	397.4	395.6	391.7
15°	428.9	418.6	410.0	400.3	392.4	384.9	380.6	374.2	373.3	371.1	367.1
17.5°	411.0	399.9	388.0	380.9	372.0	364.2	357.5	355.4	349.1	346.8	343.3
20°	397.0	386.7	377.7	368.3	355.3	348.1	342.8	340.0	334.9	331.8	329.6
22.5°	384.9	374.4	364.0	353.0	342.3	334.1	330.3	325.8	323.1	318.8	316.4
25°	367.6	356.2	343.7	331.8	324.1	318.0	311.8	307.8	303.9	301.9	297.6
27.5°	347.5	335.5	323.9	314.8	305.4	299.4	293.8	290.3	285.5	282.2	279.7
30°	336.4	322.3	312.3	304.2	292.1	286.3	282.2	277.8	274.3	270.8	268.3
32.5°	323.6	310.8	301.2	291.2	281.9	275.6	270.2	266.4	263.3	260.0	257.6
35°	303.5	292.8	282.9	272.8	265.9	259.6	253.2	249.9	247.0	243.9	241.8
37.5°	285.3	275.2	265.8	256.3	247.8	242.6	237.5	235.0	231.1	229.0	226.9
40°	274.1	264.2	254.1	244.9	236.1	232.1	227.5	223.8	220.3	218.7	216.3
42.5°	261.7	251.8	243.4	233.5	226.2	220.8	216.6	212.5	209.9	207.6	206.3
45°	243.6	234.8	226.4	216.5	209.7	205.1	200.3	196.5	194.2	192.6	190.2
47.5°	225.8	217.1	208.6	200.0	193.4	188.1	183.2	180.7	177.5	175.6	174.0
50°	213.0	205.1	196.1	188.2	181.6	176.3	172.4	169.1	166.3	163.8	162.7
52.5°	201.2	192.8	185.0	177.7	170.7	164.8	161.2	157.7	155.5	152.8	151.5
55°	181.8	173.7	167.1	159.9	153.1	148.0	143.6	140.5	138.4	135.3	133.6
57.5°	163.6	156.3	148.5	142.1	135.2	130.9	127.2	123.1	120.4	118.0	116.2
60°	151.3	143.0	136.1	130.3	124.0	118.6	115.3	112.0	109.1	106.7	105.2
62.5°	138.5	131.2	124.7	118.3	112.6	107.8	104.1	101.3	98.8	97.3	95.7
65°	118.8	113.1	106.5	101.2	96.0	92.5	89.4	87.0	85.2	84.1	82.8
67.5°	100.7	95.2	89.4	84.3	80.7	78.0	76.1	74.0	73.0	71.6	70.8
70°	89.0	83.2	78.1	74.2	70.7	68.7	67.4	65.9	65.0	63.2	62.4
72.5°	76.2	72.0	68.3	65.1	62.3	60.5	58.8	56.9	55.5	53.5	52.7
75°	59.9	56.2	53.3	51.2	49.4	47.0	44.6	42.6	41.9	41.3	41.1
77.5°	44.4	42.0	40.0	38.1	35.9	34.2	33.6	33.2	33.1	32.7	32.7
80°	34.9	32.7	31.2	29.0	27.7	27.7	27.7	27.2	27.4	27.4	27.4
82.5°	25.9	23.9	23.1	22.3	22.1	22.2	22.2	22.3	22.1	22.5	22.3
85°	13.4	13.6	14.0	13.9	14.0	14.0	14.5	14.2	14.5	14.0	14.5
87.5°	6.1	6.9	7.4	7.8	8.3	8.5	8.6	8.7	9.0	9.0	9.2
90°	5.9	7.0	8.6	10.2	11.8	13.5	12.9	13.5	13.9	14.5	15.6
92.5°	23.1	31.1	45.1	68.2	91.0	82.7	62.4	45.2	35.9	31.8	28.9
95°	48.9	69.8	115.6	195.7	283.9	318.8	258.5	193.5	131.2	102.6	83.3
97.5°	58.1	80.8	124.4	214.7	361.7	494.1	528.6	482.5	386.4	317.1	252.8
100°	64.5	85.5	123.1	202.6	344.0	509.1	615.0	633.9	590.3	527.4	451.0
102.5°	71.8	91.0	124.8	192.4	318.3	481.2	619.3	684.2	682.8	646.1	597.7
105°	83.9	100.6	129.6	184.9	286.5	432.3	586.5	698.9	752.6	762.9	748.9
107.5°	97.5	112.9	138.4	184.4	266.4	389.0	529.1	656.5	743.9	790.9	810.0
110°	106.4	121.5	145.7	186.5	258.5	364.5	492.9	616.0	715.0	782.8	820.4



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	115.9	130.5	153.0	190.9	254.3	348.2	461.6	576.1	677.1	753.1	801.4
115°	130.1	144.6	165.0	197.8	252.7	330.6	423.7	523.1	616.6	695.7	754.2
117.5°	144.2	157.6	177.9	207.1	253.6	320.3	400.8	484.7	565.4	636.4	695.9
120°	153.3	166.6	186.0	214.0	255.3	315.6	388.7	464.5	537.1	601.5	655.9
122.5°	161.4	175.7	194.6	220.5	258.4	312.5	378.8	448.6	514.3	574.0	624.4
125°	173.6	188.1	207.0	230.6	262.9	308.6	366.1	427.3	486.0	537.6	580.6
127.5°	185.0	199.5	217.7	239.0	268.1	306.6	355.0	408.9	461.2	507.7	546.9
130°	191.9	206.4	224.1	244.6	271.5	305.4	348.9	397.3	445.6	489.2	525.8
132.5°	198.4	212.4	229.8	249.8	274.1	304.9	343.3	386.5	431.0	471.6	506.4
135°	207.0	221.5	238.2	256.5	278.0	304.3	336.0	372.0	410.2	445.2	475.8
137.5°	214.5	227.9	243.9	261.4	280.5	303.1	329.7	358.8	390.1	420.2	446.8
140°	218.8	232.2	247.8	264.0	282.2	302.7	325.7	351.1	378.4	404.3	427.3
142.5°	223.1	235.7	250.8	266.6	283.5	301.8	322.3	343.7	367.3	389.6	409.7
145°	228.5	240.8	254.9	269.4	284.4	300.5	317.7	334.9	352.7	369.9	385.5
147.5°	234.7	245.2	258.1	271.1	284.4	298.5	313.2	327.7	341.8	355.7	366.7
150°	238.2	247.8	260.2	271.5	284.4	296.7	310.2	322.5	334.9	346.2	356.5
152.5°	241.6	250.8	261.5	272.4	283.1	294.6	306.8	317.8	328.5	338.5	346.9
155°	247.3	254.9	264.0	272.6	281.7	290.9	301.6	310.8	319.3	327.4	333.8
157.5°	252.2	258.1	265.3	273.1	279.8	287.5	295.8	303.2	310.4	316.7	321.7
160°	254.9	260.2	266.6	273.1	279.0	284.9	291.9	298.9	304.8	310.2	314.0
162.5°	256.9	261.5	267.1	272.7	277.3	282.4	288.0	293.8	298.8	303.8	307.1
165°	259.7	263.4	267.7	271.5	274.8	278.5	282.8	287.1	290.3	294.1	296.7
167.5°	262.1	264.5	267.6	270.6	272.1	274.6	277.8	281.3	283.7	285.9	287.9
170°	263.4	264.5	267.2	269.4	270.4	272.0	274.8	277.4	279.0	281.2	282.2
172.5°	264.3	264.9	267.2	268.9	269.1	269.8	271.7	274.0	275.1	276.8	277.5
175°	265.0	265.6	266.6	267.7	267.2	267.2	268.2	269.4	269.8	271.0	271.0
177.5°	265.6	265.6	266.0	266.8	266.0	265.6	266.0	266.5	266.8	267.3	267.3
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	488.7	488.5	488.7	488.0	488.7	488.5	488.7	490.9	490.9	491.0	491.2
5°	454.8	454.6	453.9	451.9	453.9	454.6	454.8	455.4	457.2	460.2	459.4
7.5°	425.1	424.8	422.9	422.9	422.9	424.8	425.1	426.9	428.9	430.7	432.9
10°	407.6	407.7	405.1	403.6	405.1	407.7	407.6	409.1	412.0	413.5	415.0
12.5°	390.5	389.6	387.4	385.7	387.4	389.6	390.5	391.7	395.6	397.4	400.3
15°	368.1	365.8	360.6	361.0	360.6	365.8	368.1	367.1	371.1	373.3	374.2
17.5°	341.6	340.0	339.9	336.8	339.9	340.0	341.6	343.3	346.8	349.1	355.4
20°	326.1	325.0	325.5	322.3	325.5	325.0	326.1	329.6	331.8	334.9	340.0
22.5°	314.0	312.8	311.0	310.1	311.0	312.8	314.0	316.4	318.8	323.1	325.8
25°	296.2	294.5	292.8	293.8	292.8	294.5	296.2	297.6	301.9	303.9	307.8
27.5°	278.5	277.2	275.4	275.2	275.4	277.2	278.5	279.7	282.2	285.5	290.3
30°	267.2	265.9	265.0	263.9	265.0	265.9	267.2	268.3	270.8	274.3	277.8
32.5°	255.8	255.5	254.0	253.7	254.0	255.5	255.8	257.6	260.0	263.3	266.4
35°	240.9	239.6	239.1	239.3	239.1	239.6	240.9	241.8	243.9	247.0	249.9
37.5°	226.7	225.0	224.1	223.4	224.1	225.0	226.7	226.9	229.0	231.1	235.0
40°	216.5	214.8	214.3	213.9	214.3	214.8	216.5	216.3	218.7	220.3	223.8
42.5°	205.1	204.4	204.2	203.3	204.2	204.4	205.1	206.3	207.6	209.9	212.5
45°	189.5	189.3	187.9	188.4	187.9	189.3	189.5	190.2	192.6	194.2	196.5
47.5°	173.1	172.1	171.2	171.8	171.2	172.1	173.1	174.0	175.6	177.5	180.7
50°	161.8	161.4	159.4	159.9	159.4	161.4	161.8	162.7	163.8	166.3	169.1
52.5°	150.6	148.9	148.2	147.9	148.2	148.9	150.6	151.5	152.8	155.5	157.7
55°	132.0	130.0	129.1	128.7	129.1	130.0	132.0	133.6	135.3	138.4	140.5
57.5°	113.7	113.2	112.4	112.9	112.4	113.2	113.7	116.2	118.0	120.4	123.1
60°	103.0	103.0	103.0	102.7	103.0	103.0	103.0	105.2	106.7	109.1	112.0
62.5°	94.7	94.2	94.1	94.3	94.1	94.2	94.7	95.7	97.3	98.8	101.3
65°	82.1	81.9	81.1	80.8	81.1	81.9	82.1	82.8	84.1	85.2	87.0
67.5°	70.2	69.5	69.2	68.9	69.2	69.5	70.2	70.8	71.6	73.0	74.0
70°	61.3	60.8	59.5	59.8	59.5	60.8	61.3	62.4	63.2	65.0	65.9
72.5°	51.7	51.2	50.9	50.6	50.9	51.2	51.7	52.7	53.5	55.5	56.9
75°	40.8	40.6	40.4	41.3	40.4	40.6	40.8	41.1	41.3	41.9	42.6
77.5°	32.7	32.7	32.9	32.5	32.9	32.7	32.7	32.7	32.7	33.1	33.2
80°	27.4	27.4	27.2	27.2	27.2	27.4	27.4	27.4	27.4	27.4	27.2
82.5°	22.0	22.1	22.3	22.0	22.3	22.1	22.0	22.3	22.5	22.1	22.3
85°	14.5	14.2	14.7	14.5	14.7	14.2	14.5	14.5	14.0	14.5	14.2
87.5°	9.5	9.2	9.3	9.4	9.3	9.2	9.5	9.2	9.0	9.0	8.7
90°	15.1	15.6	16.1	15.6	16.1	15.6	15.1	15.6	14.5	13.9	13.5
92.5°	28.0	26.3	26.9	25.9	26.9	26.3	28.0	28.9	31.8	35.9	45.2
95°	73.1	68.2	64.5	62.4	64.5	68.2	73.1	83.3	102.6	131.2	193.5
97.5°	213.1	188.9	174.4	169.8	174.4	188.9	213.1	252.8	317.1	386.4	482.5
100°	396.7	357.5	336.6	337.1	336.6	357.5	396.7	451.0	527.4	590.3	633.9
102.5°	555.4	524.3	506.8	494.5	506.8	524.3	555.4	597.7	646.1	682.8	684.2
105°	724.2	703.7	686.5	683.8	686.5	703.7	724.2	748.9	762.9	752.6	698.9
107.5°	810.5	803.6	797.8	792.9	797.8	803.6	810.5	810.0	790.9	743.9	656.5
110°	835.5	839.7	838.7	837.5	838.7	839.7	835.5	820.4	782.8	715.0	616.0



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	829.0	842.4	846.4	846.6	846.4	842.4	829.0	801.4	753.1	677.1	576.1
115°	794.6	818.2	829.0	831.7	829.0	818.2	794.6	754.2	695.7	616.6	523.1
117.5°	737.9	765.0	780.5	784.1	780.5	765.0	737.9	695.9	636.4	565.4	484.7
120°	698.3	728.5	741.3	744.6	741.3	728.5	698.3	655.9	601.5	537.1	464.5
122.5°	662.2	689.3	703.5	707.6	703.5	689.3	662.2	624.4	574.0	514.3	448.6
125°	615.0	638.7	652.1	655.9	652.1	638.7	615.0	580.6	537.6	486.0	427.3
127.5°	577.5	597.7	609.8	613.3	609.8	597.7	577.5	546.9	507.7	461.2	408.9
130°	554.3	573.6	584.9	589.2	584.9	573.6	554.3	525.8	489.2	445.6	397.3
132.5°	533.2	552.5	562.5	565.5	562.5	552.5	533.2	506.4	471.6	431.0	386.5
135°	502.1	518.2	527.9	531.7	527.9	518.2	502.1	475.8	445.2	410.2	372.0
137.5°	468.9	485.2	493.4	495.9	493.4	485.2	468.9	446.8	420.2	390.1	358.8
140°	447.8	462.9	471.5	470.9	471.5	462.9	447.8	427.3	404.3	378.4	351.1
142.5°	427.2	440.5	448.3	447.7	448.3	440.5	427.2	409.7	389.6	367.3	343.7
145°	398.9	410.2	414.5	415.6	414.5	410.2	398.9	385.5	369.9	352.7	334.9
147.5°	376.9	384.6	388.7	389.1	388.7	384.6	376.9	366.7	355.7	341.8	327.7
150°	364.5	370.4	373.6	373.6	373.6	370.4	364.5	356.5	346.2	334.9	322.5
152.5°	353.3	358.8	360.7	360.7	360.7	358.8	353.3	346.9	338.5	328.5	317.8
155°	338.7	343.0	344.0	344.6	344.0	343.0	338.7	333.8	327.4	319.3	310.8
157.5°	325.9	329.1	330.0	329.9	330.0	329.1	325.9	321.7	316.7	310.4	303.2
160°	317.7	320.9	320.9	320.4	320.9	320.9	317.7	314.0	310.2	304.8	298.9
162.5°	309.5	312.4	312.4	311.8	312.4	312.4	309.5	307.1	303.8	298.8	293.8
165°	298.9	301.0	300.5	300.5	300.5	301.0	298.9	296.7	294.1	290.3	287.1
167.5°	288.8	290.3	289.7	289.7	289.7	290.3	288.8	287.9	285.9	283.7	281.3
170°	282.8	283.9	283.3	283.3	283.3	283.9	282.8	282.2	281.2	279.0	277.4
172.5°	277.6	278.7	277.8	277.3	277.8	278.7	277.6	277.5	276.8	275.1	274.0
175°	271.0	271.5	271.0	270.4	271.0	271.5	271.0	271.0	271.0	269.8	269.4
177.5°	266.8	267.3	266.5	266.5	266.5	267.3	266.8	267.3	267.3	266.8	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	489.7	492.1	494.6	496.8	500.3	501.9	504.2	505.1	507.7	511.5	514.7
5°	459.9	463.4	468.0	471.6	477.6	482.2	487.3	492.1	497.9	506.0	513.2
7.5°	434.6	438.0	443.6	450.5	457.0	463.6	470.5	477.1	485.2	496.9	508.4
10°	417.9	422.1	428.7	436.1	444.2	450.6	458.7	467.0	477.2	490.6	504.4
12.5°	403.5	406.6	414.2	421.3	430.6	438.7	446.6	456.4	467.9	482.1	498.8
15°	380.6	384.9	392.4	400.3	410.0	418.6	428.9	440.7	451.9	469.5	489.7
17.5°	357.5	364.2	372.0	380.9	388.0	399.9	411.0	423.2	437.1	455.6	477.9
20°	342.8	348.1	355.3	368.3	377.7	386.7	397.0	412.2	424.9	446.0	469.0
22.5°	330.3	334.1	342.3	353.0	364.0	374.4	384.9	399.4	415.1	435.1	460.1
25°	311.8	318.0	324.1	331.8	343.7	356.2	367.6	379.9	396.6	417.9	444.9
27.5°	293.8	299.4	305.4	314.8	323.9	335.5	347.5	361.6	379.5	402.0	429.4
30°	282.2	286.3	292.1	304.2	312.3	322.3	336.4	348.9	365.6	389.6	418.6
32.5°	270.2	275.6	281.9	291.2	301.2	310.8	323.6	337.1	354.2	377.8	407.5
35°	253.2	259.6	265.9	272.8	282.9	292.8	303.5	318.4	335.7	358.6	387.8
37.5°	237.5	242.6	247.8	256.3	265.8	275.2	285.3	300.0	316.3	341.0	367.8
40°	227.5	232.1	236.1	244.9	254.1	264.2	274.1	287.0	304.5	327.6	353.5
42.5°	216.6	220.8	226.2	233.5	243.4	251.8	261.7	274.0	290.5	314.0	336.7
45°	200.3	205.1	209.7	216.5	226.4	234.8	243.6	255.1	272.1	291.4	311.6
47.5°	183.2	188.1	193.4	200.0	208.6	217.1	225.8	236.1	251.6	270.5	284.2
50°	172.4	176.3	181.6	188.2	196.1	205.1	213.0	224.2	238.9	253.8	265.7
52.5°	161.2	164.8	170.7	177.7	185.0	192.8	201.2	210.8	224.1	238.2	247.6
55°	143.6	148.0	153.1	159.9	167.1	173.7	181.8	191.7	202.3	212.8	219.1
57.5°	127.2	130.9	135.2	142.1	148.5	156.3	163.6	171.3	181.1	189.0	193.1
60°	115.3	118.6	124.0	130.3	136.1	143.0	151.3	159.0	166.5	172.9	176.1
62.5°	104.1	107.8	112.6	118.3	124.7	131.2	138.5	145.0	151.6	157.0	159.3
65°	89.4	92.5	96.0	101.2	106.5	113.1	118.8	125.4	130.3	133.3	135.3
67.5°	76.1	78.0	80.7	84.3	89.4	95.2	100.7	105.8	109.9	112.0	113.8
70°	67.4	68.7	70.7	74.2	78.1	83.2	89.0	92.7	96.1	97.9	99.7
72.5°	58.8	60.5	62.3	65.1	68.3	72.0	76.2	80.7	82.7	84.7	85.8
75°	44.6	47.0	49.4	51.2	53.3	56.2	59.9	62.8	63.9	65.7	65.9
77.5°	33.6	34.2	35.9	38.1	40.0	42.0	44.4	46.9	47.5	48.4	49.0
80°	27.7	27.7	27.7	29.0	31.2	32.7	34.9	36.2	37.1	37.3	37.5
82.5°	22.2	22.2	22.1	22.3	23.1	23.9	25.9	27.4	28.2	28.0	27.5
85°	14.5	14.0	14.0	13.9	14.0	13.6	13.4	14.2	15.6	15.6	15.2
87.5°	8.6	8.5	8.3	7.8	7.4	6.9	6.1	6.0	5.7	6.2	5.8
90°	12.9	13.5	11.8	10.2	8.6	7.0	5.9	4.8	3.2	2.2	1.0
92.5°	62.4	82.7	91.0	68.2	45.1	31.1	23.1	18.6	14.4	9.9	6.7
95°	258.5	318.8	283.9	195.7	115.6	69.8	48.9	35.0	25.8	19.9	18.3
97.5°	528.6	494.1	361.7	214.7	124.4	80.8	58.1	44.3	36.4	31.8	31.2
100°	615.0	509.1	344.0	202.6	123.1	85.5	64.5	51.7	44.1	40.3	39.8
102.5°	619.3	481.2	318.3	192.4	124.8	91.0	71.8	60.2	53.2	49.8	48.8
105°	586.5	432.3	286.5	184.9	129.6	100.6	83.9	73.6	67.2	64.0	62.4
107.5°	529.1	389.0	266.4	184.4	138.4	112.9	97.5	87.8	81.5	78.4	76.7
110°	492.9	364.5	258.5	186.5	145.7	121.5	106.4	97.3	91.4	88.7	87.1



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	461.6	348.2	254.3	190.9	153.0	130.5	115.9	106.8	100.9	98.2	96.5
115°	423.7	330.6	252.7	197.8	165.0	144.6	130.1	120.9	115.6	112.4	110.2
117.5°	400.8	320.3	253.6	207.1	177.9	157.6	144.2	133.9	129.0	126.3	123.9
120°	388.7	315.6	255.3	214.0	186.0	166.6	153.3	143.0	137.6	135.0	133.4
122.5°	378.8	312.5	258.4	220.5	194.6	175.7	161.4	151.6	145.8	143.1	141.5
125°	366.1	308.6	262.9	230.6	207.0	188.1	173.6	163.4	157.5	154.3	153.3
127.5°	355.0	306.6	268.1	239.0	217.7	199.5	185.0	173.7	167.8	163.7	162.1
130°	348.9	305.4	271.5	244.6	224.1	206.4	191.9	180.6	174.2	169.4	167.8
132.5°	343.3	304.9	274.1	249.8	229.8	212.4	198.4	187.1	179.4	174.1	172.0
135°	336.0	304.3	278.0	256.5	238.2	221.5	207.0	195.7	187.7	181.7	179.6
137.5°	329.7	303.1	280.5	261.4	243.9	227.9	214.5	203.3	194.7	188.9	186.6
140°	325.7	302.7	282.2	264.0	247.8	232.2	218.8	208.0	199.4	194.1	191.4
142.5°	322.3	301.8	283.5	266.6	250.8	235.7	223.1	212.4	204.6	198.8	196.5
145°	317.7	300.5	284.4	269.4	254.9	240.8	228.5	219.3	211.3	206.4	204.8
147.5°	313.2	298.5	284.4	271.1	258.1	245.2	234.7	225.9	219.0	214.1	213.2
150°	310.2	296.7	284.4	271.5	260.2	247.8	238.2	230.6	223.7	219.3	218.8
152.5°	306.8	294.6	283.1	272.4	261.5	250.8	241.6	235.0	228.8	224.5	224.4
155°	301.6	290.9	281.7	272.6	264.0	254.9	247.3	241.4	236.0	232.8	232.8
157.5°	295.8	287.5	279.8	273.1	265.3	258.1	252.2	247.2	242.4	239.9	239.4
160°	291.9	284.9	279.0	273.1	266.6	260.2	254.9	251.1	246.8	244.6	244.6
162.5°	288.0	282.4	277.3	272.7	267.1	261.5	256.9	253.6	250.2	248.5	248.5
165°	282.8	278.5	274.8	271.5	267.7	263.4	259.7	257.5	254.9	253.7	254.3
167.5°	277.8	274.6	272.1	270.6	267.6	264.5	262.1	260.6	258.5	258.1	258.7
170°	274.8	272.0	270.4	269.4	267.2	264.5	263.4	262.3	260.7	260.2	261.3
172.5°	271.7	269.8	269.1	268.9	267.2	264.9	264.3	263.6	262.5	262.3	263.0
175°	268.2	267.2	267.2	267.7	266.6	265.6	265.0	265.0	264.0	264.5	265.0
177.5°	266.0	265.6	266.0	266.8	266.0	265.6	265.6	265.6	265.1	265.6	266.0
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	515.8	517.7	520.2	523.9	526.7	529.1	529.6	530.4	532.2	535.1	537.3
5°	519.2	524.1	532.3	540.2	548.7	555.8	562.4	567.0	571.4	580.6	588.1
7.5°	518.0	529.3	542.1	556.2	570.6	584.5	597.4	609.0	620.5	634.0	649.2
10°	517.4	530.6	547.7	565.9	585.9	605.4	624.3	639.0	656.1	671.6	691.1
12.5°	514.1	533.0	553.5	576.7	601.3	623.9	648.8	669.0	688.6	710.9	733.6
15°	509.6	532.7	558.6	589.6	627.0	654.1	679.7	715.0	739.1	763.3	795.8
17.5°	501.7	529.9	562.2	602.5	633.6	670.2	708.5	736.5	769.0	803.0	832.5
20°	495.4	528.1	564.4	603.9	643.7	683.3	720.5	753.8	787.5	826.8	850.9
22.5°	489.1	521.4	559.1	601.1	643.8	685.7	727.6	766.9	804.6	844.3	875.2
25°	475.6	514.1	554.9	597.8	639.9	686.0	736.0	779.8	826.5	867.4	896.6
27.5°	462.0	497.3	537.9	581.4	628.2	682.7	741.6	791.3	838.1	867.4	876.6
30°	449.7	487.0	524.4	568.5	619.3	680.0	742.6	799.6	837.9	850.7	841.2
32.5°	437.2	471.1	508.0	553.3	607.1	673.5	744.0	794.7	817.7	808.0	769.6
35°	415.3	445.7	481.5	526.8	588.7	670.0	738.3	772.5	766.9	711.9	639.4
37.5°	391.7	416.6	449.7	497.0	569.7	655.7	713.3	718.4	668.9	584.7	501.0
40°	373.1	395.5	429.5	478.9	554.9	641.7	688.2	667.8	591.2	497.4	427.5
42.5°	355.0	373.9	406.7	460.0	540.8	622.5	650.8	606.3	517.9	429.2	365.7
45°	324.3	342.1	375.0	429.7	512.1	585.9	582.1	504.8	416.3	345.0	292.3
47.5°	295.3	310.9	341.8	397.6	478.3	530.9	496.1	413.8	338.7	281.4	243.8
50°	274.8	290.1	320.8	376.0	451.3	489.7	439.9	360.6	291.8	244.4	214.5
52.5°	255.1	270.0	298.1	351.9	418.6	441.6	388.0	314.5	257.2	216.3	190.7
55°	227.5	238.9	264.2	315.6	365.4	370.7	316.4	255.0	207.7	179.2	161.6
57.5°	199.4	209.2	234.2	275.1	310.1	307.4	256.0	202.7	171.0	149.8	137.0
60°	181.2	190.9	212.8	247.9	274.3	265.0	217.8	175.0	147.8	132.2	122.1
62.5°	164.1	171.6	192.3	217.9	236.9	226.4	186.2	150.8	129.1	116.0	108.0
65°	139.4	145.6	162.0	175.5	186.0	175.9	142.5	117.9	102.4	93.1	87.7
67.5°	116.0	119.9	130.3	135.2	142.6	131.5	107.2	90.7	81.8	74.1	70.2
70°	101.2	104.1	109.6	113.6	115.5	104.1	86.1	74.0	66.5	61.1	58.6
72.5°	86.4	89.0	90.1	93.3	92.3	81.6	69.2	59.6	54.2	50.5	47.4
75°	66.1	67.2	66.1	64.8	61.9	54.5	45.9	41.1	37.1	35.3	34.2
77.5°	48.2	47.8	46.4	44.3	39.4	34.7	30.1	28.5	26.8	25.8	25.4
80°	37.1	36.2	34.9	31.6	27.4	24.1	23.1	22.0	21.3	20.2	20.0
82.5°	27.6	27.1	24.9	22.1	19.2	17.6	16.8	16.3	15.6	15.1	15.1
85°	14.7	14.0	11.6	10.1	9.7	9.2	9.0	9.0	8.1	7.9	7.9
87.5°	5.2	4.3	4.5	4.1	4.4	4.3	4.8	4.8	5.0	5.0	4.8
90°	2.2	3.2	4.8	5.9	7.0	8.6	10.2	11.8	13.5	12.9	13.5
92.5°	9.9	14.4	18.6	23.1	31.1	45.1	68.2	91.0	82.7	62.4	45.2
95°	19.9	25.8	35.0	48.9	69.8	115.6	195.7	283.9	318.8	258.5	193.5
97.5°	31.8	36.4	44.3	58.1	80.8	124.4	214.7	361.7	494.1	528.6	482.5
100°	40.3	44.1	51.7	64.5	85.5	123.1	202.6	344.0	509.1	615.0	633.9
102.5°	49.8	53.2	60.2	71.8	91.0	124.8	192.4	318.3	481.2	619.3	684.2
105°	64.0	67.2	73.6	83.9	100.6	129.6	184.9	286.5	432.3	586.5	698.9
107.5°	78.4	81.5	87.8	97.5	112.9	138.4	184.4	266.4	389.0	529.1	656.5
110°	88.7	91.4	97.3	106.4	121.5	145.7	186.5	258.5	364.5	492.9	616.0



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	98.2	100.9	106.8	115.9	130.5	153.0	190.9	254.3	348.2	461.6	576.1
115°	112.4	115.6	120.9	130.1	144.6	165.0	197.8	252.7	330.6	423.7	523.1
117.5°	126.3	129.0	133.9	144.2	157.6	177.9	207.1	253.6	320.3	400.8	484.7
120°	135.0	137.6	143.0	153.3	166.6	186.0	214.0	255.3	315.6	388.7	464.5
122.5°	143.1	145.8	151.6	161.4	175.7	194.6	220.5	258.4	312.5	378.8	448.6
125°	154.3	157.5	163.4	173.6	188.1	207.0	230.6	262.9	308.6	366.1	427.3
127.5°	163.7	167.8	173.7	185.0	199.5	217.7	239.0	268.1	306.6	355.0	408.9
130°	169.4	174.2	180.6	191.9	206.4	224.1	244.6	271.5	305.4	348.9	397.3
132.5°	174.1	179.4	187.1	198.4	212.4	229.8	249.8	274.1	304.9	343.3	386.5
135°	181.7	187.7	195.7	207.0	221.5	238.2	256.5	278.0	304.3	336.0	372.0
137.5°	188.9	194.7	203.3	214.5	227.9	243.9	261.4	280.5	303.1	329.7	358.8
140°	194.1	199.4	208.0	218.8	232.2	247.8	264.0	282.2	302.7	325.7	351.1
142.5°	198.8	204.6	212.4	223.1	235.7	250.8	266.6	283.5	301.8	322.3	343.7
145°	206.4	211.3	219.3	228.5	240.8	254.9	269.4	284.4	300.5	317.7	334.9
147.5°	214.1	219.0	225.9	234.7	245.2	258.1	271.1	284.4	298.5	313.2	327.7
150°	219.3	223.7	230.6	238.2	247.8	260.2	271.5	284.4	296.7	310.2	322.5
152.5°	224.5	228.8	235.0	241.6	250.8	261.5	272.4	283.1	294.6	306.8	317.8
155°	232.8	236.0	241.4	247.3	254.9	264.0	272.6	281.7	290.9	301.6	310.8
157.5°	239.9	242.4	247.2	252.2	258.1	265.3	273.1	279.8	287.5	295.8	303.2
160°	244.6	246.8	251.1	254.9	260.2	266.6	273.1	279.0	284.9	291.9	298.9
162.5°	248.5	250.2	253.6	256.9	261.5	267.1	272.7	277.3	282.4	288.0	293.8
165°	253.7	254.9	257.5	259.7	263.4	267.7	271.5	274.8	278.5	282.8	287.1
167.5°	258.1	258.5	260.6	262.1	264.5	267.6	270.6	272.1	274.6	277.8	281.3
170°	260.2	260.7	262.3	263.4	264.5	267.2	269.4	270.4	272.0	274.8	277.4
172.5°	262.3	262.5	263.6	264.3	264.9	267.2	268.9	269.1	269.8	271.7	274.0
175°	264.5	264.0	265.0	265.0	265.6	266.6	267.7	267.2	267.2	268.2	269.4
177.5°	265.6	265.1	265.6	265.6	265.6	266.0	266.8	266.0	265.6	266.0	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6	265.6



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	541.1	541.1	541.8	544.4	544.8	547.1	546.4
5°	594.7	598.8	600.4	607.0	610.9	612.7	609.2
7.5°	660.2	671.9	677.5	684.5	690.5	692.4	687.6
10°	707.9	720.3	730.6	737.0	742.9	746.9	751.9
12.5°	754.1	769.3	779.1	788.1	794.2	799.2	800.0
15°	804.4	827.2	844.5	857.3	863.7	867.0	865.6
17.5°	855.0	876.2	888.5	901.5	910.3	910.8	911.1
20°	883.6	904.3	918.6	928.2	938.1	937.6	939.9
22.5°	902.8	919.1	930.0	937.0	940.4	938.7	939.1
25°	911.7	916.6	914.6	903.4	900.5	890.2	892.0
27.5°	865.5	842.7	819.1	788.7	764.7	745.6	746.5
30°	802.9	762.4	716.3	677.7	643.0	633.3	612.7
32.5°	715.2	654.6	600.6	564.5	534.8	526.7	508.7
35°	566.6	507.7	452.1	418.8	405.6	387.1	386.9
37.5°	440.4	388.5	359.2	334.1	321.0	309.8	308.8
40°	370.4	330.1	307.8	289.8	276.9	268.5	266.6
42.5°	321.6	289.0	268.2	257.0	247.0	242.7	239.5
45°	262.6	240.6	226.2	216.1	211.5	208.2	206.4
47.5°	219.7	205.0	195.1	188.3	184.6	181.2	182.1
50°	196.3	184.3	177.0	170.6	167.8	165.3	165.6
52.5°	177.5	166.6	160.8	156.2	152.7	150.9	150.1
55°	150.6	143.8	137.9	134.6	132.6	130.3	129.6
57.5°	128.5	123.2	118.4	114.7	114.1	111.9	112.2
60°	113.8	109.3	105.4	103.4	101.9	99.9	100.6
62.5°	101.6	97.9	94.3	92.7	91.1	89.7	90.0
65°	83.2	79.7	77.5	76.6	76.0	75.3	74.6
67.5°	66.4	64.2	62.8	60.9	59.6	59.4	58.7
70°	55.8	52.9	50.5	48.1	47.4	47.2	47.4
72.5°	44.7	42.9	42.2	41.1	40.9	40.3	40.7
75°	33.6	32.9	32.5	31.6	31.6	31.6	31.6
77.5°	24.8	24.4	24.1	23.9	23.8	23.4	23.4
80°	19.3	19.1	18.7	18.7	18.5	18.7	18.5
82.5°	14.6	14.5	14.1	14.1	13.9	13.8	13.9
85°	7.4	7.3	7.7	7.3	7.4	7.1	7.4
87.5°	4.9	5.0	5.1	4.9	4.9	5.4	4.9
90°	13.9	14.5	15.6	15.1	15.6	16.1	15.6
92.5°	35.9	31.8	28.9	28.0	26.3	26.9	25.9
95°	131.2	102.6	83.3	73.1	68.2	64.5	62.4
97.5°	386.4	317.1	252.8	213.1	188.9	174.4	169.8
100°	590.3	527.4	451.0	396.7	357.5	336.6	337.1
102.5°	682.8	646.1	597.7	555.4	524.3	506.8	494.5
105°	752.6	762.9	748.9	724.2	703.7	686.5	683.8
107.5°	743.9	790.9	810.0	810.5	803.6	797.8	792.9
110°	715.0	782.8	820.4	835.5	839.7	838.7	837.5



TEST NUMBER: P332248-830

CATALOG NUMBER: S123RDIP-S340D585U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	677.1	753.1	801.4	829.0	842.4	846.4	846.6
115°	616.6	695.7	754.2	794.6	818.2	829.0	831.7
117.5°	565.4	636.4	695.9	737.9	765.0	780.5	784.1
120°	537.1	601.5	655.9	698.3	728.5	741.3	744.6
122.5°	514.3	574.0	624.4	662.2	689.3	703.5	707.6
125°	486.0	537.6	580.6	615.0	638.7	652.1	655.9
127.5°	461.2	507.7	546.9	577.5	597.7	609.8	613.3
130°	445.6	489.2	525.8	554.3	573.6	584.9	589.2
132.5°	431.0	471.6	506.4	533.2	552.5	562.5	565.5
135°	410.2	445.2	475.8	502.1	518.2	527.9	531.7
137.5°	390.1	420.2	446.8	468.9	485.2	493.4	495.9
140°	378.4	404.3	427.3	447.8	462.9	471.5	470.9
142.5°	367.3	389.6	409.7	427.2	440.5	448.3	447.7
145°	352.7	369.9	385.5	398.9	410.2	414.5	415.6
147.5°	341.8	355.7	366.7	376.9	384.6	388.7	389.1
150°	334.9	346.2	356.5	364.5	370.4	373.6	373.6
152.5°	328.5	338.5	346.9	353.3	358.8	360.7	360.7
155°	319.3	327.4	333.8	338.7	343.0	344.0	344.6
157.5°	310.4	316.7	321.7	325.9	329.1	330.0	329.9
160°	304.8	310.2	314.0	317.7	320.9	320.9	320.4
162.5°	298.8	303.8	307.1	309.5	312.4	312.4	311.8
165°	290.3	294.1	296.7	298.9	301.0	300.5	300.5
167.5°	283.7	285.9	287.9	288.8	290.3	289.7	289.7
170°	279.0	281.2	282.2	282.8	283.9	283.3	283.3
172.5°	275.1	276.8	277.5	277.6	278.7	277.8	277.3
175°	269.8	271.0	271.0	271.0	271.5	271.0	270.4
177.5°	266.8	267.3	267.3	266.8	267.3	266.5	266.5
180°	265.6	265.6	265.6	265.6	265.6	265.6	265.6

(END OF REPORT)