

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332253-830

Luminaire Tested: **S123RDIP-S340D805U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332253-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D805U830-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3879.1 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35	29
2	86	79	73	69	78	72	67	63	58	54	51	45	42	40	32	31	30	25
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	29	27	26	21
4	72	62	55	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	19	18	15
7	57	45	37	32	51	41	34	30	33	28	25	26	23	20	20	18	16	13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5521	5521	5521	5521
5°	6582	5545	4883	5545
10°	8218	5513	4411	5513
15°	9646	5457	4023	5457
20°	10766	5372	3692	5372
25°	10594	5284	3489	5284
30°	7615	5203	3280	5203
35°	5084	5096	3144	5096
40°	3746	4967	3006	4967
45°	3142	4743	2868	4743
50°	2773	4449	2678	4449
55°	2432	4112	2415	4112
60°	2166	3791	2211	3791
65°	1900	3446	2058	3446
70°	1492	3138	1882	3138
75°	1314	2741	1718	2741
80°	1147	2325	1686	2325
85°	914	1877	1791	1877



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	1.3
10°-20°	157.6	4.1
20°-30°	247.6	6.4
30°-40°	258.3	6.7
40°-50°	221.1	5.7
50°-60°	168.5	4.3
60°-70°	108.0	2.8
70°-80°	52.0	1.3
80°-90°	16.5	0.4
90°-100°	61.1	1.6
100°-110°	182.9	4.7
110°-120°	311.1	8.0
120°-130°	409.2	10.5
130°-140°	460.0	11.9
140°-150°	452.1	11.7
150°-160°	380.6	9.8
160°-170°	253.4	6.5
170°-180°	88.7	2.3
0°-30°	455.6	11.7
0°-40°	714.0	18.4
0°-60°	1103.5	28.4
0°-90°	1280.0	33.0
90°-120°	555.1	14.3
90°-150°	1876.4	48.4
90°-180°	2599.0	67.0
0°-180°	3879.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	513	513	513	513	513	
5°	609	513	452	513	609	63
15°	866	490	361	490	866	245
25°	892	445	294	445	892	383
35°	387	388	239	388	387	254
45°	206	312	188	312	206	162
55°	130	219	129	219	130	117
65°	75	135	81	135	75	73
75°	32	66	41	66	32	34
85°	7	15	14	15	7	9
90°	22	1	22	1	22	11
95°	58	44	58	44	58	59
105°	175	166	175	166	175	186
115°	314	313	314	313	314	311
125°	453	458	453	458	453	405
135°	594	595	594	595	594	457
145°	721	721	721	721	721	450
155°	825	826	825	826	825	380
165°	897	900	897	900	897	253
175°	932	936	932	936	932	89
180°	938	938	938	938	938	



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	546.4	547.1	544.8	544.4	541.8	541.1	541.1	537.3	535.1	532.2	530.4
5°	609.2	612.7	610.9	607.0	600.4	598.8	594.7	588.1	580.6	571.4	567.0
7.5°	687.6	692.4	690.5	684.5	677.5	671.9	660.2	649.2	634.0	620.5	609.0
10°	751.9	746.9	742.9	737.0	730.6	720.3	707.9	691.1	671.6	656.1	639.0
12.5°	800.0	799.2	794.2	788.1	779.1	769.3	754.1	733.6	710.9	688.6	669.0
15°	865.6	867.0	863.7	857.3	844.5	827.2	804.4	795.8	763.3	739.1	715.0
17.5°	911.1	910.8	910.3	901.5	888.5	876.2	855.0	832.5	803.0	769.0	736.5
20°	939.9	937.6	938.1	928.2	918.6	904.3	883.6	850.9	826.8	787.5	753.8
22.5°	939.1	938.7	940.4	937.0	930.0	919.1	902.8	875.2	844.3	804.6	766.9
25°	892.0	890.2	900.5	903.4	914.6	916.6	911.7	896.6	867.4	826.5	779.8
27.5°	746.5	745.6	764.7	788.7	819.1	842.7	865.5	876.6	867.4	838.1	791.3
30°	612.7	633.3	643.0	677.7	716.3	762.4	802.9	841.2	850.7	837.9	799.6
32.5°	508.7	526.7	534.8	564.5	600.6	654.6	715.2	769.6	808.0	817.7	794.7
35°	386.9	387.1	405.6	418.8	452.1	507.7	566.6	639.4	711.9	766.9	772.5
37.5°	308.8	309.8	321.0	334.1	359.2	388.5	440.4	501.0	584.7	668.9	718.4
40°	266.6	268.5	276.9	289.8	307.8	330.1	370.4	427.5	497.4	591.2	667.8
42.5°	239.5	242.7	247.0	257.0	268.2	289.0	321.6	365.7	429.2	517.9	606.3
45°	206.4	208.2	211.5	216.1	226.2	240.6	262.6	292.3	345.0	416.3	504.8
47.5°	182.1	181.2	184.6	188.3	195.1	205.0	219.7	243.8	281.4	338.7	413.8
50°	165.6	165.3	167.8	170.6	177.0	184.3	196.3	214.5	244.4	291.8	360.6
52.5°	150.1	150.9	152.7	156.2	160.8	166.6	177.5	190.7	216.3	257.2	314.5
55°	129.6	130.3	132.6	134.6	137.9	143.8	150.6	161.6	179.2	207.7	255.0
57.5°	112.2	111.9	114.1	114.7	118.4	123.2	128.5	137.0	149.8	171.0	202.7
60°	100.6	99.9	101.9	103.4	105.4	109.3	113.8	122.1	132.2	147.8	175.0
62.5°	90.0	89.7	91.1	92.7	94.3	97.9	101.6	108.0	116.0	129.1	150.8
65°	74.6	75.3	76.0	76.6	77.5	79.7	83.2	87.7	93.1	102.4	117.9
67.5°	58.7	59.4	59.6	60.9	62.8	64.2	66.4	70.2	74.1	81.8	90.7
70°	47.4	47.2	47.4	48.1	50.5	52.9	55.8	58.6	61.1	66.5	74.0
72.5°	40.7	40.3	40.9	41.1	42.2	42.9	44.7	47.4	50.5	54.2	59.6
75°	31.6	31.6	31.6	31.6	32.5	32.9	33.6	34.2	35.3	37.1	41.1
77.5°	23.4	23.4	23.8	23.9	24.1	24.4	24.8	25.4	25.8	26.8	28.5
80°	18.5	18.7	18.5	18.7	18.7	19.1	19.3	20.0	20.2	21.3	22.0
82.5°	13.9	13.8	13.9	14.1	14.1	14.5	14.6	15.1	15.1	15.6	16.3
85°	7.4	7.1	7.4	7.3	7.7	7.3	7.4	7.9	7.9	8.1	9.0
87.5°	6.2	6.5	6.0	6.1	6.1	6.1	6.0	5.9	6.1	5.8	5.6
90°	22.1	21.8	21.5	21.1	20.8	20.3	19.6	19.0	18.4	17.7	15.6
92.5°	29.8	30.0	30.2	30.3	30.5	30.3	29.9	29.3	28.8	28.3	27.1
95°	57.5	57.5	57.5	57.5	57.5	57.1	56.5	55.8	55.2	54.6	53.3
97.5°	88.4	88.5	88.6	88.6	88.7	88.3	87.6	86.8	86.1	85.3	84.4
100°	112.0	111.7	111.3	111.0	110.7	110.3	109.8	109.3	108.9	108.3	107.5
102.5°	136.2	136.3	136.3	136.4	136.5	136.2	135.7	135.3	134.8	134.3	133.2
105°	175.4	175.0	174.7	174.4	174.1	173.9	173.9	173.9	173.9	173.9	172.5
107.5°	216.2	216.4	216.6	216.8	217.0	216.9	216.3	215.7	215.3	214.7	214.1
110°	243.9	244.2	244.6	244.9	245.2	245.1	244.4	243.7	243.1	242.4	242.1



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	273.4	273.4	273.5	273.6	273.6	273.3	272.5	271.7	271.0	270.1	270.1
115°	314.0	314.1	314.2	314.4	314.6	314.6	314.4	314.2	314.1	314.0	314.2
117.5°	355.1	355.5	356.0	356.5	356.8	357.1	357.1	357.2	357.2	357.2	357.7
120°	383.9	384.3	384.6	384.9	385.2	385.5	385.7	385.8	386.0	386.2	387.0
122.5°	411.6	412.1	412.6	413.0	413.5	414.0	414.3	414.8	415.2	415.7	416.0
125°	453.2	453.8	454.5	455.2	455.8	456.5	457.1	457.8	458.5	459.1	459.4
127.5°	494.6	495.4	496.2	496.9	497.7	498.5	499.4	500.3	501.2	502.1	502.5
130°	521.7	522.9	524.1	525.2	526.3	527.3	527.9	528.6	529.1	529.8	530.4
132.5°	550.1	550.9	551.8	552.7	553.6	554.4	555.2	556.0	556.8	557.5	557.9
135°	594.0	594.3	594.7	594.9	595.3	595.8	596.4	597.1	597.8	598.4	598.5
137.5°	632.7	633.4	634.0	634.6	635.2	635.8	636.6	637.3	637.9	638.6	638.2
140°	658.1	659.2	660.3	661.5	662.7	663.3	663.5	663.6	663.8	663.9	663.8
142.5°	684.0	684.9	685.8	686.6	687.6	688.1	688.2	688.4	688.5	688.7	688.4
145°	721.4	722.1	722.7	723.4	724.1	724.4	724.6	724.8	725.0	725.1	724.6
147.5°	754.8	755.7	756.7	757.7	758.7	759.2	759.2	759.2	759.2	759.2	758.7
150°	776.0	776.9	778.0	778.9	780.0	780.4	780.4	780.4	780.4	780.4	780.0
152.5°	796.6	797.5	798.3	799.2	800.0	800.3	800.0	799.7	799.6	799.3	799.1
155°	824.6	825.8	826.9	828.0	829.2	829.4	828.8	828.1	827.5	826.8	826.7
157.5°	850.1	851.0	852.0	852.9	853.8	853.8	853.2	852.5	851.9	851.1	851.0
160°	866.6	867.2	867.9	868.6	869.2	869.1	868.4	867.5	866.7	865.9	865.9
162.5°	879.0	880.1	881.1	882.1	883.2	883.4	882.5	881.7	880.8	880.1	879.9
165°	896.8	898.0	899.1	900.3	901.4	901.5	900.5	899.6	898.5	897.6	897.6
167.5°	912.0	913.0	914.1	915.0	916.1	916.1	915.0	914.1	913.0	912.0	911.9
170°	919.6	920.9	922.0	923.1	924.3	924.3	923.1	922.0	920.9	919.6	919.6
172.5°	925.6	926.7	927.8	929.0	930.2	930.2	929.3	928.2	927.2	926.1	926.1
175°	932.2	933.3	934.5	935.7	936.8	936.9	935.9	934.9	934.0	932.9	932.9
177.5°	935.8	936.7	937.5	938.5	939.4	939.4	938.7	937.9	937.1	936.3	936.3
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	529.6	529.1	526.7	523.9	520.2	517.7	515.8	514.7	511.5	507.7	505.1
5°	562.4	555.8	548.7	540.2	532.3	524.1	519.2	513.2	506.0	497.9	492.1
7.5°	597.4	584.5	570.6	556.2	542.1	529.3	518.0	508.4	496.9	485.2	477.1
10°	624.3	605.4	585.9	565.9	547.7	530.6	517.4	504.4	490.6	477.2	467.0
12.5°	648.8	623.9	601.3	576.7	553.5	533.0	514.1	498.8	482.1	467.9	456.4
15°	679.7	654.1	627.0	589.6	558.6	532.7	509.6	489.7	469.5	451.9	440.7
17.5°	708.5	670.2	633.6	602.5	562.2	529.9	501.7	477.9	455.6	437.1	423.2
20°	720.5	683.3	643.7	603.9	564.4	528.1	495.4	469.0	446.0	424.9	412.2
22.5°	727.6	685.7	643.8	601.1	559.1	521.4	489.1	460.1	435.1	415.1	399.4
25°	736.0	686.0	639.9	597.8	554.9	514.1	475.6	444.9	417.9	396.6	379.9
27.5°	741.6	682.7	628.2	581.4	537.9	497.3	462.0	429.4	402.0	379.5	361.6
30°	742.6	680.0	619.3	568.5	524.4	487.0	449.7	418.6	389.6	365.6	348.9
32.5°	744.0	673.5	607.1	553.3	508.0	471.1	437.2	407.5	377.8	354.2	337.1
35°	738.3	670.0	588.7	526.8	481.5	445.7	415.3	387.8	358.6	335.7	318.4
37.5°	713.3	655.7	569.7	497.0	449.7	416.6	391.7	367.8	341.0	316.3	300.0
40°	688.2	641.7	554.9	478.9	429.5	395.5	373.1	353.5	327.6	304.5	287.0
42.5°	650.8	622.5	540.8	460.0	406.7	373.9	355.0	336.7	314.0	290.5	274.0
45°	582.1	585.9	512.1	429.7	375.0	342.1	324.3	311.6	291.4	272.1	255.1
47.5°	496.1	530.9	478.3	397.6	341.8	310.9	295.3	284.2	270.5	251.6	236.1
50°	439.9	489.7	451.3	376.0	320.8	290.1	274.8	265.7	253.8	238.9	224.2
52.5°	388.0	441.6	418.6	351.9	298.1	270.0	255.1	247.6	238.2	224.1	210.8
55°	316.4	370.7	365.4	315.6	264.2	238.9	227.5	219.1	212.8	202.3	191.7
57.5°	256.0	307.4	310.1	275.1	234.2	209.2	199.4	193.1	189.0	181.1	171.3
60°	217.8	265.0	274.3	247.9	212.8	190.9	181.2	176.1	172.9	166.5	159.0
62.5°	186.2	226.4	236.9	217.9	192.3	171.6	164.1	159.3	157.0	151.6	145.0
65°	142.5	175.9	186.0	175.5	162.0	145.6	139.4	135.3	133.3	130.3	125.4
67.5°	107.2	131.5	142.6	135.2	130.3	119.9	116.0	113.8	112.0	109.9	105.8
70°	86.1	104.1	115.5	113.6	109.6	104.1	101.2	99.7	97.9	96.1	92.7
72.5°	69.2	81.6	92.3	93.3	90.1	89.0	86.4	85.8	84.7	82.7	80.7
75°	45.9	54.5	61.9	64.8	66.1	67.2	66.1	65.9	65.7	63.9	62.8
77.5°	30.1	34.7	39.4	44.3	46.4	47.8	48.2	49.0	48.4	47.5	46.9
80°	23.1	24.1	27.4	31.6	34.9	36.2	37.1	37.5	37.3	37.1	36.2
82.5°	16.8	17.6	19.2	22.1	24.9	27.1	27.6	27.5	28.0	28.2	27.4
85°	9.0	9.2	9.7	10.1	11.6	14.0	14.7	15.2	15.6	15.6	14.2
87.5°	5.5	4.9	4.8	4.4	4.6	4.5	5.2	5.7	6.3	5.9	6.2
90°	13.4	11.3	9.1	7.3	5.7	4.1	2.4	0.8	2.4	4.1	5.7
92.5°	25.9	24.7	23.5	22.2	21.2	20.1	18.9	17.8	18.9	20.1	21.2
95°	51.9	50.6	49.3	48.1	46.9	45.8	44.6	43.5	44.6	45.8	46.9
97.5°	83.4	82.5	81.5	80.7	79.7	78.9	78.0	77.2	78.0	78.9	79.7
100°	106.7	105.8	105.1	104.2	103.2	102.2	101.2	100.2	101.2	102.2	103.2
102.5°	132.1	131.0	130.0	129.1	128.6	127.9	127.3	126.8	127.3	127.9	128.6
105°	171.0	169.5	168.1	167.1	166.8	166.5	166.2	165.8	166.2	166.5	166.8
107.5°	213.6	213.0	212.4	212.0	211.8	211.6	211.4	211.2	211.4	211.6	211.8
110°	241.8	241.5	241.1	240.8	240.4	240.2	239.8	239.5	239.8	240.2	240.4



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	270.0	269.9	269.8	269.8	269.6	269.4	269.2	269.0	269.2	269.4	269.6
115°	314.6	314.9	315.3	315.2	314.6	314.1	313.7	313.2	313.7	314.1	314.6
117.5°	358.1	358.5	358.9	359.0	358.6	358.4	358.1	357.7	358.1	358.4	358.6
120°	387.8	388.6	389.5	389.4	388.3	387.4	386.3	385.4	386.3	387.4	388.3
122.5°	416.5	416.9	417.4	417.2	416.4	415.8	415.0	414.3	415.0	415.8	416.4
125°	459.8	460.1	460.4	460.3	459.9	459.3	458.8	458.4	458.8	459.3	459.9
127.5°	502.8	503.2	503.6	503.2	502.2	501.1	500.1	499.1	500.1	501.1	502.2
130°	530.8	531.3	531.8	531.4	530.1	528.8	527.4	526.1	527.4	528.8	530.1
132.5°	558.3	558.6	559.0	558.6	557.2	555.9	554.6	553.3	554.6	555.9	557.2
135°	598.7	598.9	599.1	598.6	597.7	596.6	595.7	594.7	595.7	596.6	597.7
137.5°	637.7	637.3	636.9	636.3	635.5	634.6	633.9	633.0	633.9	634.6	635.5
140°	663.6	663.5	663.3	662.8	662.0	661.2	660.3	659.5	660.3	661.2	662.0
142.5°	688.2	687.9	687.6	687.0	686.2	685.3	684.6	683.7	684.6	685.3	686.2
145°	724.2	723.7	723.1	722.7	722.5	722.1	721.8	721.4	721.8	722.1	722.5
147.5°	758.3	757.8	757.3	756.9	756.2	755.6	755.1	754.5	755.1	755.6	756.2
150°	779.8	779.4	779.1	778.7	778.4	778.1	777.8	777.4	777.8	778.1	778.4
152.5°	798.9	798.7	798.5	798.1	797.7	797.2	796.7	796.4	796.7	797.2	797.7
155°	826.5	826.3	826.1	826.0	826.0	826.0	826.0	826.0	826.0	826.0	826.0
157.5°	850.9	850.7	850.6	850.6	850.8	851.0	851.2	851.4	851.2	851.0	850.8
160°	865.9	865.9	865.9	866.0	866.4	866.7	867.0	867.3	867.0	866.7	866.4
162.5°	879.8	879.7	879.5	879.7	880.1	880.6	881.1	881.5	881.1	880.6	880.1
165°	897.6	897.6	897.6	897.8	898.3	898.8	899.3	899.8	899.3	898.8	898.3
167.5°	911.7	911.6	911.5	911.7	912.4	913.0	913.7	914.4	913.7	913.0	912.4
170°	919.6	919.6	919.6	920.0	920.7	921.3	922.0	922.7	922.0	921.3	920.7
172.5°	926.1	926.1	926.1	926.5	927.2	927.8	928.5	929.1	928.5	927.8	927.2
175°	932.9	932.9	932.9	933.3	934.0	934.6	935.2	935.9	935.2	934.6	934.0
177.5°	936.3	936.3	936.3	936.6	937.1	937.6	938.2	938.7	938.2	937.6	937.1
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	504.2	501.9	500.3	496.8	494.6	492.1	489.7	491.2	491.0	490.9	490.9
5°	487.3	482.2	477.6	471.6	468.0	463.4	459.9	459.4	460.2	457.2	455.4
7.5°	470.5	463.6	457.0	450.5	443.6	438.0	434.6	432.9	430.7	428.9	426.9
10°	458.7	450.6	444.2	436.1	428.7	422.1	417.9	415.0	413.5	412.0	409.1
12.5°	446.6	438.7	430.6	421.3	414.2	406.6	403.5	400.3	397.4	395.6	391.7
15°	428.9	418.6	410.0	400.3	392.4	384.9	380.6	374.2	373.3	371.1	367.1
17.5°	411.0	399.9	388.0	380.9	372.0	364.2	357.5	355.4	349.1	346.8	343.3
20°	397.0	386.7	377.7	368.3	355.3	348.1	342.8	340.0	334.9	331.8	329.6
22.5°	384.9	374.4	364.0	353.0	342.3	334.1	330.3	325.8	323.1	318.8	316.4
25°	367.6	356.2	343.7	331.8	324.1	318.0	311.8	307.8	303.9	301.9	297.6
27.5°	347.5	335.5	323.9	314.8	305.4	299.4	293.8	290.3	285.5	282.2	279.7
30°	336.4	322.3	312.3	304.2	292.1	286.3	282.2	277.8	274.3	270.8	268.3
32.5°	323.6	310.8	301.2	291.2	281.9	275.6	270.2	266.4	263.3	260.0	257.6
35°	303.5	292.8	282.9	272.8	265.9	259.6	253.2	249.9	247.0	243.9	241.8
37.5°	285.3	275.2	265.8	256.3	247.8	242.6	237.5	235.0	231.1	229.0	226.9
40°	274.1	264.2	254.1	244.9	236.1	232.1	227.5	223.8	220.3	218.7	216.3
42.5°	261.7	251.8	243.4	233.5	226.2	220.8	216.6	212.5	209.9	207.6	206.3
45°	243.6	234.8	226.4	216.5	209.7	205.1	200.3	196.5	194.2	192.6	190.2
47.5°	225.8	217.1	208.6	200.0	193.4	188.1	183.2	180.7	177.5	175.6	174.0
50°	213.0	205.1	196.1	188.2	181.6	176.3	172.4	169.1	166.3	163.8	162.7
52.5°	201.2	192.8	185.0	177.7	170.7	164.8	161.2	157.7	155.5	152.8	151.5
55°	181.8	173.7	167.1	159.9	153.1	148.0	143.6	140.5	138.4	135.3	133.6
57.5°	163.6	156.3	148.5	142.1	135.2	130.9	127.2	123.1	120.4	118.0	116.2
60°	151.3	143.0	136.1	130.3	124.0	118.6	115.3	112.0	109.1	106.7	105.2
62.5°	138.5	131.2	124.7	118.3	112.6	107.8	104.1	101.3	98.8	97.3	95.7
65°	118.8	113.1	106.5	101.2	96.0	92.5	89.4	87.0	85.2	84.1	82.8
67.5°	100.7	95.2	89.4	84.3	80.7	78.0	76.1	74.0	73.0	71.6	70.8
70°	89.0	83.2	78.1	74.2	70.7	68.7	67.4	65.9	65.0	63.2	62.4
72.5°	76.2	72.0	68.3	65.1	62.3	60.5	58.8	56.9	55.5	53.5	52.7
75°	59.9	56.2	53.3	51.2	49.4	47.0	44.6	42.6	41.9	41.3	41.1
77.5°	44.4	42.0	40.0	38.1	35.9	34.2	33.6	33.2	33.1	32.7	32.7
80°	34.9	32.7	31.2	29.0	27.7	27.7	27.7	27.2	27.4	27.4	27.4
82.5°	25.9	23.9	23.1	22.3	22.1	22.2	22.2	22.3	22.1	22.5	22.3
85°	13.4	13.6	14.0	13.9	14.0	14.0	14.5	14.2	14.5	14.0	14.5
87.5°	6.4	7.3	7.9	8.5	9.0	9.3	9.6	9.8	10.1	10.2	10.3
90°	7.3	9.1	11.3	13.4	15.6	17.7	18.4	19.0	19.6	20.3	20.8
92.5°	22.2	23.5	24.7	25.9	27.1	28.3	28.8	29.3	29.9	30.3	30.5
95°	48.1	49.3	50.6	51.9	53.3	54.6	55.2	55.8	56.5	57.1	57.5
97.5°	80.7	81.5	82.5	83.4	84.4	85.3	86.1	86.8	87.6	88.3	88.7
100°	104.2	105.1	105.8	106.7	107.5	108.3	108.9	109.3	109.8	110.3	110.7
102.5°	129.1	130.0	131.0	132.1	133.2	134.3	134.8	135.3	135.7	136.2	136.5
105°	167.1	168.1	169.5	171.0	172.5	173.9	173.9	173.9	173.9	173.9	174.1
107.5°	212.0	212.4	213.0	213.6	214.1	214.7	215.3	215.7	216.3	216.9	217.0
110°	240.8	241.1	241.5	241.8	242.1	242.4	243.1	243.7	244.4	245.1	245.2



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	269.8	269.8	269.9	270.0	270.1	270.1	271.0	271.7	272.5	273.3	273.6
115°	315.2	315.3	314.9	314.6	314.2	314.0	314.1	314.2	314.4	314.6	314.6
117.5°	359.0	358.9	358.5	358.1	357.7	357.2	357.2	357.2	357.1	357.1	356.8
120°	389.4	389.5	388.6	387.8	387.0	386.2	386.0	385.8	385.7	385.5	385.2
122.5°	417.2	417.4	416.9	416.5	416.0	415.7	415.2	414.8	414.3	414.0	413.5
125°	460.3	460.4	460.1	459.8	459.4	459.1	458.5	457.8	457.1	456.5	455.8
127.5°	503.2	503.6	503.2	502.8	502.5	502.1	501.2	500.3	499.4	498.5	497.7
130°	531.4	531.8	531.3	530.8	530.4	529.8	529.1	528.6	527.9	527.3	526.3
132.5°	558.6	559.0	558.6	558.3	557.9	557.5	556.8	556.0	555.2	554.4	553.6
135°	598.6	599.1	598.9	598.7	598.5	598.4	597.8	597.1	596.4	595.8	595.3
137.5°	636.3	636.9	637.3	637.7	638.2	638.6	637.9	637.3	636.6	635.8	635.2
140°	662.8	663.3	663.5	663.6	663.8	663.9	663.8	663.6	663.5	663.3	662.7
142.5°	687.0	687.6	687.9	688.2	688.4	688.7	688.5	688.4	688.2	688.1	687.6
145°	722.7	723.1	723.7	724.2	724.6	725.1	725.0	724.8	724.6	724.4	724.1
147.5°	756.9	757.3	757.8	758.3	758.7	759.2	759.2	759.2	759.2	759.2	758.7
150°	778.7	779.1	779.4	779.8	780.0	780.4	780.4	780.4	780.4	780.4	780.0
152.5°	798.1	798.5	798.7	798.9	799.1	799.3	799.6	799.7	800.0	800.3	800.0
155°	826.0	826.1	826.3	826.5	826.7	826.8	827.5	828.1	828.8	829.4	829.2
157.5°	850.6	850.6	850.7	850.9	851.0	851.1	851.9	852.5	853.2	853.8	853.8
160°	866.0	865.9	865.9	865.9	865.9	865.9	866.7	867.5	868.4	869.1	869.2
162.5°	879.7	879.5	879.7	879.8	879.9	880.1	880.8	881.7	882.5	883.4	883.2
165°	897.8	897.6	897.6	897.6	897.6	897.6	898.5	899.6	900.5	901.5	901.4
167.5°	911.7	911.5	911.6	911.7	911.9	912.0	913.0	914.1	915.0	916.1	916.1
170°	920.0	919.6	919.6	919.6	919.6	919.6	920.9	922.0	923.1	924.3	924.3
172.5°	926.5	926.1	926.1	926.1	926.1	926.1	927.2	928.2	929.3	930.2	930.2
175°	933.3	932.9	932.9	932.9	932.9	932.9	934.0	934.9	935.9	936.9	936.8
177.5°	936.6	936.3	936.3	936.3	936.3	936.3	937.1	937.9	938.7	939.4	939.4
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	488.7	488.5	488.7	488.0	488.7	488.5	488.7	490.9	490.9	491.0	491.2
5°	454.8	454.6	453.9	451.9	453.9	454.6	454.8	455.4	457.2	460.2	459.4
7.5°	425.1	424.8	422.9	422.9	422.9	424.8	425.1	426.9	428.9	430.7	432.9
10°	407.6	407.7	405.1	403.6	405.1	407.7	407.6	409.1	412.0	413.5	415.0
12.5°	390.5	389.6	387.4	385.7	387.4	389.6	390.5	391.7	395.6	397.4	400.3
15°	368.1	365.8	360.6	361.0	360.6	365.8	368.1	367.1	371.1	373.3	374.2
17.5°	341.6	340.0	339.9	336.8	339.9	340.0	341.6	343.3	346.8	349.1	355.4
20°	326.1	325.0	325.5	322.3	325.5	325.0	326.1	329.6	331.8	334.9	340.0
22.5°	314.0	312.8	311.0	310.1	311.0	312.8	314.0	316.4	318.8	323.1	325.8
25°	296.2	294.5	292.8	293.8	292.8	294.5	296.2	297.6	301.9	303.9	307.8
27.5°	278.5	277.2	275.4	275.2	275.4	277.2	278.5	279.7	282.2	285.5	290.3
30°	267.2	265.9	265.0	263.9	265.0	265.9	267.2	268.3	270.8	274.3	277.8
32.5°	255.8	255.5	254.0	253.7	254.0	255.5	255.8	257.6	260.0	263.3	266.4
35°	240.9	239.6	239.1	239.3	239.1	239.6	240.9	241.8	243.9	247.0	249.9
37.5°	226.7	225.0	224.1	223.4	224.1	225.0	226.7	226.9	229.0	231.1	235.0
40°	216.5	214.8	214.3	213.9	214.3	214.8	216.5	216.3	218.7	220.3	223.8
42.5°	205.1	204.4	204.2	203.3	204.2	204.4	205.1	206.3	207.6	209.9	212.5
45°	189.5	189.3	187.9	188.4	187.9	189.3	189.5	190.2	192.6	194.2	196.5
47.5°	173.1	172.1	171.2	171.8	171.2	172.1	173.1	174.0	175.6	177.5	180.7
50°	161.8	161.4	159.4	159.9	159.4	161.4	161.8	162.7	163.8	166.3	169.1
52.5°	150.6	148.9	148.2	147.9	148.2	148.9	150.6	151.5	152.8	155.5	157.7
55°	132.0	130.0	129.1	128.7	129.1	130.0	132.0	133.6	135.3	138.4	140.5
57.5°	113.7	113.2	112.4	112.9	112.4	113.2	113.7	116.2	118.0	120.4	123.1
60°	103.0	103.0	103.0	102.7	103.0	103.0	103.0	105.2	106.7	109.1	112.0
62.5°	94.7	94.2	94.1	94.3	94.1	94.2	94.7	95.7	97.3	98.8	101.3
65°	82.1	81.9	81.1	80.8	81.1	81.9	82.1	82.8	84.1	85.2	87.0
67.5°	70.2	69.5	69.2	68.9	69.2	69.5	70.2	70.8	71.6	73.0	74.0
70°	61.3	60.8	59.5	59.8	59.5	60.8	61.3	62.4	63.2	65.0	65.9
72.5°	51.7	51.2	50.9	50.6	50.9	51.2	51.7	52.7	53.5	55.5	56.9
75°	40.8	40.6	40.4	41.3	40.4	40.6	40.8	41.1	41.3	41.9	42.6
77.5°	32.7	32.7	32.9	32.5	32.9	32.7	32.7	32.7	32.7	33.1	33.2
80°	27.4	27.4	27.2	27.2	27.2	27.4	27.4	27.4	27.4	27.4	27.2
82.5°	22.0	22.1	22.3	22.0	22.3	22.1	22.0	22.3	22.5	22.1	22.3
85°	14.5	14.2	14.7	14.5	14.7	14.2	14.5	14.5	14.0	14.5	14.2
87.5°	10.7	10.5	10.5	10.7	10.5	10.5	10.7	10.3	10.2	10.1	9.8
90°	21.1	21.5	21.8	22.1	21.8	21.5	21.1	20.8	20.3	19.6	19.0
92.5°	30.3	30.2	30.0	29.8	30.0	30.2	30.3	30.5	30.3	29.9	29.3
95°	57.5	57.5	57.5	57.5	57.5	57.5	57.5	57.5	57.1	56.5	55.8
97.5°	88.6	88.6	88.5	88.4	88.5	88.6	88.6	88.7	88.3	87.6	86.8
100°	111.0	111.3	111.7	112.0	111.7	111.3	111.0	110.7	110.3	109.8	109.3
102.5°	136.4	136.3	136.3	136.2	136.3	136.3	136.4	136.5	136.2	135.7	135.3
105°	174.4	174.7	175.0	175.4	175.0	174.7	174.4	174.1	173.9	173.9	173.9
107.5°	216.8	216.6	216.4	216.2	216.4	216.6	216.8	217.0	216.9	216.3	215.7
110°	244.9	244.6	244.2	243.9	244.2	244.6	244.9	245.2	245.1	244.4	243.7



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	273.6	273.5	273.4	273.4	273.4	273.5	273.6	273.6	273.3	272.5	271.7
115°	314.4	314.2	314.1	314.0	314.1	314.2	314.4	314.6	314.6	314.4	314.2
117.5°	356.5	356.0	355.5	355.1	355.5	356.0	356.5	356.8	357.1	357.1	357.2
120°	384.9	384.6	384.3	383.9	384.3	384.6	384.9	385.2	385.5	385.7	385.8
122.5°	413.0	412.6	412.1	411.6	412.1	412.6	413.0	413.5	414.0	414.3	414.8
125°	455.2	454.5	453.8	453.2	453.8	454.5	455.2	455.8	456.5	457.1	457.8
127.5°	496.9	496.2	495.4	494.6	495.4	496.2	496.9	497.7	498.5	499.4	500.3
130°	525.2	524.1	522.9	521.7	522.9	524.1	525.2	526.3	527.3	527.9	528.6
132.5°	552.7	551.8	550.9	550.1	550.9	551.8	552.7	553.6	554.4	555.2	556.0
135°	594.9	594.7	594.3	594.0	594.3	594.7	594.9	595.3	595.8	596.4	597.1
137.5°	634.6	634.0	633.4	632.7	633.4	634.0	634.6	635.2	635.8	636.6	637.3
140°	661.5	660.3	659.2	658.1	659.2	660.3	661.5	662.7	663.3	663.5	663.6
142.5°	686.6	685.8	684.9	684.0	684.9	685.8	686.6	687.6	688.1	688.2	688.4
145°	723.4	722.7	722.1	721.4	722.1	722.7	723.4	724.1	724.4	724.6	724.8
147.5°	757.7	756.7	755.7	754.8	755.7	756.7	757.7	758.7	759.2	759.2	759.2
150°	778.9	778.0	776.9	776.0	776.9	778.0	778.9	780.0	780.4	780.4	780.4
152.5°	799.2	798.3	797.5	796.6	797.5	798.3	799.2	800.0	800.3	800.0	799.7
155°	828.0	826.9	825.8	824.6	825.8	826.9	828.0	829.2	829.4	828.8	828.1
157.5°	852.9	852.0	851.0	850.1	851.0	852.0	852.9	853.8	853.8	853.2	852.5
160°	868.6	867.9	867.2	866.6	867.2	867.9	868.6	869.2	869.1	868.4	867.5
162.5°	882.1	881.1	880.1	879.0	880.1	881.1	882.1	883.2	883.4	882.5	881.7
165°	900.3	899.1	898.0	896.8	898.0	899.1	900.3	901.4	901.5	900.5	899.6
167.5°	915.0	914.1	913.0	912.0	913.0	914.1	915.0	916.1	916.1	915.0	914.1
170°	923.1	922.0	920.9	919.6	920.9	922.0	923.1	924.3	924.3	923.1	922.0
172.5°	929.0	927.8	926.7	925.6	926.7	927.8	929.0	930.2	930.2	929.3	928.2
175°	935.7	934.5	933.3	932.2	933.3	934.5	935.7	936.8	936.9	935.9	934.9
177.5°	938.5	937.5	936.7	935.8	936.7	937.5	938.5	939.4	939.4	938.7	937.9
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	489.7	492.1	494.6	496.8	500.3	501.9	504.2	505.1	507.7	511.5	514.7
5°	459.9	463.4	468.0	471.6	477.6	482.2	487.3	492.1	497.9	506.0	513.2
7.5°	434.6	438.0	443.6	450.5	457.0	463.6	470.5	477.1	485.2	496.9	508.4
10°	417.9	422.1	428.7	436.1	444.2	450.6	458.7	467.0	477.2	490.6	504.4
12.5°	403.5	406.6	414.2	421.3	430.6	438.7	446.6	456.4	467.9	482.1	498.8
15°	380.6	384.9	392.4	400.3	410.0	418.6	428.9	440.7	451.9	469.5	489.7
17.5°	357.5	364.2	372.0	380.9	388.0	399.9	411.0	423.2	437.1	455.6	477.9
20°	342.8	348.1	355.3	368.3	377.7	386.7	397.0	412.2	424.9	446.0	469.0
22.5°	330.3	334.1	342.3	353.0	364.0	374.4	384.9	399.4	415.1	435.1	460.1
25°	311.8	318.0	324.1	331.8	343.7	356.2	367.6	379.9	396.6	417.9	444.9
27.5°	293.8	299.4	305.4	314.8	323.9	335.5	347.5	361.6	379.5	402.0	429.4
30°	282.2	286.3	292.1	304.2	312.3	322.3	336.4	348.9	365.6	389.6	418.6
32.5°	270.2	275.6	281.9	291.2	301.2	310.8	323.6	337.1	354.2	377.8	407.5
35°	253.2	259.6	265.9	272.8	282.9	292.8	303.5	318.4	335.7	358.6	387.8
37.5°	237.5	242.6	247.8	256.3	265.8	275.2	285.3	300.0	316.3	341.0	367.8
40°	227.5	232.1	236.1	244.9	254.1	264.2	274.1	287.0	304.5	327.6	353.5
42.5°	216.6	220.8	226.2	233.5	243.4	251.8	261.7	274.0	290.5	314.0	336.7
45°	200.3	205.1	209.7	216.5	226.4	234.8	243.6	255.1	272.1	291.4	311.6
47.5°	183.2	188.1	193.4	200.0	208.6	217.1	225.8	236.1	251.6	270.5	284.2
50°	172.4	176.3	181.6	188.2	196.1	205.1	213.0	224.2	238.9	253.8	265.7
52.5°	161.2	164.8	170.7	177.7	185.0	192.8	201.2	210.8	224.1	238.2	247.6
55°	143.6	148.0	153.1	159.9	167.1	173.7	181.8	191.7	202.3	212.8	219.1
57.5°	127.2	130.9	135.2	142.1	148.5	156.3	163.6	171.3	181.1	189.0	193.1
60°	115.3	118.6	124.0	130.3	136.1	143.0	151.3	159.0	166.5	172.9	176.1
62.5°	104.1	107.8	112.6	118.3	124.7	131.2	138.5	145.0	151.6	157.0	159.3
65°	89.4	92.5	96.0	101.2	106.5	113.1	118.8	125.4	130.3	133.3	135.3
67.5°	76.1	78.0	80.7	84.3	89.4	95.2	100.7	105.8	109.9	112.0	113.8
70°	67.4	68.7	70.7	74.2	78.1	83.2	89.0	92.7	96.1	97.9	99.7
72.5°	58.8	60.5	62.3	65.1	68.3	72.0	76.2	80.7	82.7	84.7	85.8
75°	44.6	47.0	49.4	51.2	53.3	56.2	59.9	62.8	63.9	65.7	65.9
77.5°	33.6	34.2	35.9	38.1	40.0	42.0	44.4	46.9	47.5	48.4	49.0
80°	27.7	27.7	27.7	29.0	31.2	32.7	34.9	36.2	37.1	37.3	37.5
82.5°	22.2	22.2	22.1	22.3	23.1	23.9	25.9	27.4	28.2	28.0	27.5
85°	14.5	14.0	14.0	13.9	14.0	13.6	13.4	14.2	15.6	15.6	15.2
87.5°	9.6	9.3	9.0	8.5	7.9	7.3	6.4	6.2	5.9	6.3	5.7
90°	18.4	17.7	15.6	13.4	11.3	9.1	7.3	5.7	4.1	2.4	0.8
92.5°	28.8	28.3	27.1	25.9	24.7	23.5	22.2	21.2	20.1	18.9	17.8
95°	55.2	54.6	53.3	51.9	50.6	49.3	48.1	46.9	45.8	44.6	43.5
97.5°	86.1	85.3	84.4	83.4	82.5	81.5	80.7	79.7	78.9	78.0	77.2
100°	108.9	108.3	107.5	106.7	105.8	105.1	104.2	103.2	102.2	101.2	100.2
102.5°	134.8	134.3	133.2	132.1	131.0	130.0	129.1	128.6	127.9	127.3	126.8
105°	173.9	173.9	172.5	171.0	169.5	168.1	167.1	166.8	166.5	166.2	165.8
107.5°	215.3	214.7	214.1	213.6	213.0	212.4	212.0	211.8	211.6	211.4	211.2
110°	243.1	242.4	242.1	241.8	241.5	241.1	240.8	240.4	240.2	239.8	239.5



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	271.0	270.1	270.1	270.0	269.9	269.8	269.8	269.6	269.4	269.2	269.0
115°	314.1	314.0	314.2	314.6	314.9	315.3	315.2	314.6	314.1	313.7	313.2
117.5°	357.2	357.2	357.7	358.1	358.5	358.9	359.0	358.6	358.4	358.1	357.7
120°	386.0	386.2	387.0	387.8	388.6	389.5	389.4	388.3	387.4	386.3	385.4
122.5°	415.2	415.7	416.0	416.5	416.9	417.4	417.2	416.4	415.8	415.0	414.3
125°	458.5	459.1	459.4	459.8	460.1	460.4	460.3	459.9	459.3	458.8	458.4
127.5°	501.2	502.1	502.5	502.8	503.2	503.6	503.2	502.2	501.1	500.1	499.1
130°	529.1	529.8	530.4	530.8	531.3	531.8	531.4	530.1	528.8	527.4	526.1
132.5°	556.8	557.5	557.9	558.3	558.6	559.0	558.6	557.2	555.9	554.6	553.3
135°	597.8	598.4	598.5	598.7	598.9	599.1	598.6	597.7	596.6	595.7	594.7
137.5°	637.9	638.6	638.2	637.7	637.3	636.9	636.3	635.5	634.6	633.9	633.0
140°	663.8	663.9	663.8	663.6	663.5	663.3	662.8	662.0	661.2	660.3	659.5
142.5°	688.5	688.7	688.4	688.2	687.9	687.6	687.0	686.2	685.3	684.6	683.7
145°	725.0	725.1	724.6	724.2	723.7	723.1	722.7	722.5	722.1	721.8	721.4
147.5°	759.2	759.2	758.7	758.3	757.8	757.3	756.9	756.2	755.6	755.1	754.5
150°	780.4	780.4	780.0	779.8	779.4	779.1	778.7	778.4	778.1	777.8	777.4
152.5°	799.6	799.3	799.1	798.9	798.7	798.5	798.1	797.7	797.2	796.7	796.4
155°	827.5	826.8	826.7	826.5	826.3	826.1	826.0	826.0	826.0	826.0	826.0
157.5°	851.9	851.1	851.0	850.9	850.7	850.6	850.6	850.8	851.0	851.2	851.4
160°	866.7	865.9	865.9	865.9	865.9	865.9	866.0	866.4	866.7	867.0	867.3
162.5°	880.8	880.1	879.9	879.8	879.7	879.5	879.7	880.1	880.6	881.1	881.5
165°	898.5	897.6	897.6	897.6	897.6	897.6	897.8	898.3	898.8	899.3	899.8
167.5°	913.0	912.0	911.9	911.7	911.6	911.5	911.7	912.4	913.0	913.7	914.4
170°	920.9	919.6	919.6	919.6	919.6	919.6	920.0	920.7	921.3	922.0	922.7
172.5°	927.2	926.1	926.1	926.1	926.1	926.1	926.5	927.2	927.8	928.5	929.1
175°	934.0	932.9	932.9	932.9	932.9	932.9	933.3	934.0	934.6	935.2	935.9
177.5°	937.1	936.3	936.3	936.3	936.3	936.3	936.6	937.1	937.6	938.2	938.7
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	515.8	517.7	520.2	523.9	526.7	529.1	529.6	530.4	532.2	535.1	537.3
5°	519.2	524.1	532.3	540.2	548.7	555.8	562.4	567.0	571.4	580.6	588.1
7.5°	518.0	529.3	542.1	556.2	570.6	584.5	597.4	609.0	620.5	634.0	649.2
10°	517.4	530.6	547.7	565.9	585.9	605.4	624.3	639.0	656.1	671.6	691.1
12.5°	514.1	533.0	553.5	576.7	601.3	623.9	648.8	669.0	688.6	710.9	733.6
15°	509.6	532.7	558.6	589.6	627.0	654.1	679.7	715.0	739.1	763.3	795.8
17.5°	501.7	529.9	562.2	602.5	633.6	670.2	708.5	736.5	769.0	803.0	832.5
20°	495.4	528.1	564.4	603.9	643.7	683.3	720.5	753.8	787.5	826.8	850.9
22.5°	489.1	521.4	559.1	601.1	643.8	685.7	727.6	766.9	804.6	844.3	875.2
25°	475.6	514.1	554.9	597.8	639.9	686.0	736.0	779.8	826.5	867.4	896.6
27.5°	462.0	497.3	537.9	581.4	628.2	682.7	741.6	791.3	838.1	867.4	876.6
30°	449.7	487.0	524.4	568.5	619.3	680.0	742.6	799.6	837.9	850.7	841.2
32.5°	437.2	471.1	508.0	553.3	607.1	673.5	744.0	794.7	817.7	808.0	769.6
35°	415.3	445.7	481.5	526.8	588.7	670.0	738.3	772.5	766.9	711.9	639.4
37.5°	391.7	416.6	449.7	497.0	569.7	655.7	713.3	718.4	668.9	584.7	501.0
40°	373.1	395.5	429.5	478.9	554.9	641.7	688.2	667.8	591.2	497.4	427.5
42.5°	355.0	373.9	406.7	460.0	540.8	622.5	650.8	606.3	517.9	429.2	365.7
45°	324.3	342.1	375.0	429.7	512.1	585.9	582.1	504.8	416.3	345.0	292.3
47.5°	295.3	310.9	341.8	397.6	478.3	530.9	496.1	413.8	338.7	281.4	243.8
50°	274.8	290.1	320.8	376.0	451.3	489.7	439.9	360.6	291.8	244.4	214.5
52.5°	255.1	270.0	298.1	351.9	418.6	441.6	388.0	314.5	257.2	216.3	190.7
55°	227.5	238.9	264.2	315.6	365.4	370.7	316.4	255.0	207.7	179.2	161.6
57.5°	199.4	209.2	234.2	275.1	310.1	307.4	256.0	202.7	171.0	149.8	137.0
60°	181.2	190.9	212.8	247.9	274.3	265.0	217.8	175.0	147.8	132.2	122.1
62.5°	164.1	171.6	192.3	217.9	236.9	226.4	186.2	150.8	129.1	116.0	108.0
65°	139.4	145.6	162.0	175.5	186.0	175.9	142.5	117.9	102.4	93.1	87.7
67.5°	116.0	119.9	130.3	135.2	142.6	131.5	107.2	90.7	81.8	74.1	70.2
70°	101.2	104.1	109.6	113.6	115.5	104.1	86.1	74.0	66.5	61.1	58.6
72.5°	86.4	89.0	90.1	93.3	92.3	81.6	69.2	59.6	54.2	50.5	47.4
75°	66.1	67.2	66.1	64.8	61.9	54.5	45.9	41.1	37.1	35.3	34.2
77.5°	48.2	47.8	46.4	44.3	39.4	34.7	30.1	28.5	26.8	25.8	25.4
80°	37.1	36.2	34.9	31.6	27.4	24.1	23.1	22.0	21.3	20.2	20.0
82.5°	27.6	27.1	24.9	22.1	19.2	17.6	16.8	16.3	15.6	15.1	15.1
85°	14.7	14.0	11.6	10.1	9.7	9.2	9.0	9.0	8.1	7.9	7.9
87.5°	5.2	4.5	4.6	4.4	4.8	4.9	5.5	5.6	5.8	6.1	5.9
90°	2.4	4.1	5.7	7.3	9.1	11.3	13.4	15.6	17.7	18.4	19.0
92.5°	18.9	20.1	21.2	22.2	23.5	24.7	25.9	27.1	28.3	28.8	29.3
95°	44.6	45.8	46.9	48.1	49.3	50.6	51.9	53.3	54.6	55.2	55.8
97.5°	78.0	78.9	79.7	80.7	81.5	82.5	83.4	84.4	85.3	86.1	86.8
100°	101.2	102.2	103.2	104.2	105.1	105.8	106.7	107.5	108.3	108.9	109.3
102.5°	127.3	127.9	128.6	129.1	130.0	131.0	132.1	133.2	134.3	134.8	135.3
105°	166.2	166.5	166.8	167.1	168.1	169.5	171.0	172.5	173.9	173.9	173.9
107.5°	211.4	211.6	211.8	212.0	212.4	213.0	213.6	214.1	214.7	215.3	215.7
110°	239.8	240.2	240.4	240.8	241.1	241.5	241.8	242.1	242.4	243.1	243.7



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	269.2	269.4	269.6	269.8	269.8	269.9	270.0	270.1	270.1	271.0	271.7
115°	313.7	314.1	314.6	315.2	315.3	314.9	314.6	314.2	314.0	314.1	314.2
117.5°	358.1	358.4	358.6	359.0	358.9	358.5	358.1	357.7	357.2	357.2	357.2
120°	386.3	387.4	388.3	389.4	389.5	388.6	387.8	387.0	386.2	386.0	385.8
122.5°	415.0	415.8	416.4	417.2	417.4	416.9	416.5	416.0	415.7	415.2	414.8
125°	458.8	459.3	459.9	460.3	460.4	460.1	459.8	459.4	459.1	458.5	457.8
127.5°	500.1	501.1	502.2	503.2	503.6	503.2	502.8	502.5	502.1	501.2	500.3
130°	527.4	528.8	530.1	531.4	531.8	531.3	530.8	530.4	529.8	529.1	528.6
132.5°	554.6	555.9	557.2	558.6	559.0	558.6	558.3	557.9	557.5	556.8	556.0
135°	595.7	596.6	597.7	598.6	599.1	598.9	598.7	598.5	598.4	597.8	597.1
137.5°	633.9	634.6	635.5	636.3	636.9	637.3	637.7	638.2	638.6	637.9	637.3
140°	660.3	661.2	662.0	662.8	663.3	663.5	663.6	663.8	663.9	663.8	663.6
142.5°	684.6	685.3	686.2	687.0	687.6	687.9	688.2	688.4	688.7	688.5	688.4
145°	721.8	722.1	722.5	722.7	723.1	723.7	724.2	724.6	725.1	725.0	724.8
147.5°	755.1	755.6	756.2	756.9	757.3	757.8	758.3	758.7	759.2	759.2	759.2
150°	777.8	778.1	778.4	778.7	779.1	779.4	779.8	780.0	780.4	780.4	780.4
152.5°	796.7	797.2	797.7	798.1	798.5	798.7	798.9	799.1	799.3	799.6	799.7
155°	826.0	826.0	826.0	826.0	826.1	826.3	826.5	826.7	826.8	827.5	828.1
157.5°	851.2	851.0	850.8	850.6	850.6	850.7	850.9	851.0	851.1	851.9	852.5
160°	867.0	866.7	866.4	866.0	865.9	865.9	865.9	865.9	865.9	866.7	867.5
162.5°	881.1	880.6	880.1	879.7	879.5	879.7	879.8	879.9	880.1	880.8	881.7
165°	899.3	898.8	898.3	897.8	897.6	897.6	897.6	897.6	897.6	898.5	899.6
167.5°	913.7	913.0	912.4	911.7	911.5	911.6	911.7	911.9	912.0	913.0	914.1
170°	922.0	921.3	920.7	920.0	919.6	919.6	919.6	919.6	919.6	920.9	922.0
172.5°	928.5	927.8	927.2	926.5	926.1	926.1	926.1	926.1	926.1	927.2	928.2
175°	935.2	934.6	934.0	933.3	932.9	932.9	932.9	932.9	932.9	934.0	934.9
177.5°	938.2	937.6	937.1	936.6	936.3	936.3	936.3	936.3	936.3	937.1	937.9
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1	938.1



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	512.9	512.9	512.9	512.9	512.9	512.9	512.9
2.5°	541.1	541.1	541.8	544.4	544.8	547.1	546.4
5°	594.7	598.8	600.4	607.0	610.9	612.7	609.2
7.5°	660.2	671.9	677.5	684.5	690.5	692.4	687.6
10°	707.9	720.3	730.6	737.0	742.9	746.9	751.9
12.5°	754.1	769.3	779.1	788.1	794.2	799.2	800.0
15°	804.4	827.2	844.5	857.3	863.7	867.0	865.6
17.5°	855.0	876.2	888.5	901.5	910.3	910.8	911.1
20°	883.6	904.3	918.6	928.2	938.1	937.6	939.9
22.5°	902.8	919.1	930.0	937.0	940.4	938.7	939.1
25°	911.7	916.6	914.6	903.4	900.5	890.2	892.0
27.5°	865.5	842.7	819.1	788.7	764.7	745.6	746.5
30°	802.9	762.4	716.3	677.7	643.0	633.3	612.7
32.5°	715.2	654.6	600.6	564.5	534.8	526.7	508.7
35°	566.6	507.7	452.1	418.8	405.6	387.1	386.9
37.5°	440.4	388.5	359.2	334.1	321.0	309.8	308.8
40°	370.4	330.1	307.8	289.8	276.9	268.5	266.6
42.5°	321.6	289.0	268.2	257.0	247.0	242.7	239.5
45°	262.6	240.6	226.2	216.1	211.5	208.2	206.4
47.5°	219.7	205.0	195.1	188.3	184.6	181.2	182.1
50°	196.3	184.3	177.0	170.6	167.8	165.3	165.6
52.5°	177.5	166.6	160.8	156.2	152.7	150.9	150.1
55°	150.6	143.8	137.9	134.6	132.6	130.3	129.6
57.5°	128.5	123.2	118.4	114.7	114.1	111.9	112.2
60°	113.8	109.3	105.4	103.4	101.9	99.9	100.6
62.5°	101.6	97.9	94.3	92.7	91.1	89.7	90.0
65°	83.2	79.7	77.5	76.6	76.0	75.3	74.6
67.5°	66.4	64.2	62.8	60.9	59.6	59.4	58.7
70°	55.8	52.9	50.5	48.1	47.4	47.2	47.4
72.5°	44.7	42.9	42.2	41.1	40.9	40.3	40.7
75°	33.6	32.9	32.5	31.6	31.6	31.6	31.6
77.5°	24.8	24.4	24.1	23.9	23.8	23.4	23.4
80°	19.3	19.1	18.7	18.7	18.5	18.7	18.5
82.5°	14.6	14.5	14.1	14.1	13.9	13.8	13.9
85°	7.4	7.3	7.7	7.3	7.4	7.1	7.4
87.5°	6.0	6.1	6.1	6.1	6.0	6.5	6.2
90°	19.6	20.3	20.8	21.1	21.5	21.8	22.1
92.5°	29.9	30.3	30.5	30.3	30.2	30.0	29.8
95°	56.5	57.1	57.5	57.5	57.5	57.5	57.5
97.5°	87.6	88.3	88.7	88.6	88.6	88.5	88.4
100°	109.8	110.3	110.7	111.0	111.3	111.7	112.0
102.5°	135.7	136.2	136.5	136.4	136.3	136.3	136.2
105°	173.9	173.9	174.1	174.4	174.7	175.0	175.4
107.5°	216.3	216.9	217.0	216.8	216.6	216.4	216.2
110°	244.4	245.1	245.2	244.9	244.6	244.2	243.9



TEST NUMBER: P332253-830

CATALOG NUMBER: S123RDIP-S340D805U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	272.5	273.3	273.6	273.6	273.5	273.4	273.4
115°	314.4	314.6	314.6	314.4	314.2	314.1	314.0
117.5°	357.1	357.1	356.8	356.5	356.0	355.5	355.1
120°	385.7	385.5	385.2	384.9	384.6	384.3	383.9
122.5°	414.3	414.0	413.5	413.0	412.6	412.1	411.6
125°	457.1	456.5	455.8	455.2	454.5	453.8	453.2
127.5°	499.4	498.5	497.7	496.9	496.2	495.4	494.6
130°	527.9	527.3	526.3	525.2	524.1	522.9	521.7
132.5°	555.2	554.4	553.6	552.7	551.8	550.9	550.1
135°	596.4	595.8	595.3	594.9	594.7	594.3	594.0
137.5°	636.6	635.8	635.2	634.6	634.0	633.4	632.7
140°	663.5	663.3	662.7	661.5	660.3	659.2	658.1
142.5°	688.2	688.1	687.6	686.6	685.8	684.9	684.0
145°	724.6	724.4	724.1	723.4	722.7	722.1	721.4
147.5°	759.2	759.2	758.7	757.7	756.7	755.7	754.8
150°	780.4	780.4	780.0	778.9	778.0	776.9	776.0
152.5°	800.0	800.3	800.0	799.2	798.3	797.5	796.6
155°	828.8	829.4	829.2	828.0	826.9	825.8	824.6
157.5°	853.2	853.8	853.8	852.9	852.0	851.0	850.1
160°	868.4	869.1	869.2	868.6	867.9	867.2	866.6
162.5°	882.5	883.4	883.2	882.1	881.1	880.1	879.0
165°	900.5	901.5	901.4	900.3	899.1	898.0	896.8
167.5°	915.0	916.1	916.1	915.0	914.1	913.0	912.0
170°	923.1	924.3	924.3	923.1	922.0	920.9	919.6
172.5°	929.3	930.2	930.2	929.0	927.8	926.7	925.6
175°	935.9	936.9	936.8	935.7	934.5	933.3	932.2
177.5°	938.7	939.4	939.4	938.5	937.5	936.7	935.8
180°	938.1	938.1	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)