

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332290-830

Luminaire Tested: **S123RDIP-S560D1025U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332290-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S560D1025U830-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5600.0 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38
1	95	91	88	84	86	83	80	77	68	65	63	53	52	51	40	39	39	32
2	87	80	74	70	79	73	68	64	60	56	53	47	45	43	36	34	33	28
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29	24
4	73	63	55	50	66	58	51	46	47	43	39	38	35	32	29	27	25	21
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22	19
6	62	50	43	37	56	46	40	35	38	33	29	31	27	24	24	22	20	17
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	19	18	15
8	53	41	34	29	48	38	32	27	32	27	23	26	22	19	20	18	16	13
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14	12
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9077	9077	9077	9077
5°	10821	9116	8028	9116
10°	13511	9063	7252	9063
15°	15858	8971	6614	8971
20°	17699	8833	6071	8833
25°	17416	8687	5738	8687
30°	12519	8552	5393	8552
35°	8359	8377	5171	8377
40°	6159	8168	4942	8168
45°	5165	7798	4714	7798
50°	4558	7316	4401	7316
55°	3997	6762	3969	6762
60°	3559	6232	3638	6232
65°	3125	5662	3385	5662
70°	2452	5158	3091	5158
75°	2163	4504	2824	4504
80°	1878	3825	2777	3825
85°	1519	3075	2939	3075



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	1.5
10°-20°	259.1	4.6
20°-30°	407.0	7.3
30°-40°	424.7	7.6
40°-50°	363.4	6.5
50°-60°	277.0	4.9
60°-70°	177.6	3.2
70°-80°	85.4	1.5
80°-90°	26.2	0.5
90°-100°	258.6	4.6
100°-110°	732.4	13.1
110°-120°	720.5	12.9
120°-130°	574.7	10.3
130°-140°	453.1	8.1
140°-150°	338.2	6.0
150°-160°	235.7	4.2
160°-170°	138.5	2.5
170°-180°	45.1	0.8
0°-30°	749.1	13.4
0°-40°	1173.7	21.0
0°-60°	1814.2	32.4
0°-90°	2103.3	37.6
90°-120°	1711.5	30.6
90°-150°	3077.4	55.0
90°-180°	3497.0	62.4
0°-180°	5600.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	843	843	843	843	843	
5°	1002	844	743	844	1002	103
15°	1423	805	594	805	1423	404
25°	1466	731	483	731	1466	630
35°	636	638	394	638	636	417
45°	339	512	310	512	339	267
55°	213	360	212	360	213	193
65°	123	222	133	222	123	121
75°	52	108	68	108	52	56
85°	12	25	24	25	12	15
90°	27	2	27	2	27	15
95°	109	32	109	32	109	197
105°	1197	109	1197	109	1197	1181
115°	1456	193	1456	193	1456	1414
125°	1148	268	1148	268	1148	1040
135°	930	314	930	314	930	722
145°	727	358	727	358	727	463
155°	603	407	603	407	603	281
165°	526	445	526	445	526	150
175°	473	464	473	464	473	46
180°	465	465	465	465	465	



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	898.1	899.4	895.6	895.0	890.7	889.6	889.6	883.4	879.7	874.8	871.9
5°	1001.5	1007.2	1004.4	997.9	987.0	984.5	977.6	966.8	954.5	939.3	932.2
7.5°	1130.4	1138.3	1135.2	1125.2	1113.9	1104.7	1085.3	1067.3	1042.2	1020.1	1001.2
10°	1236.1	1227.8	1221.3	1211.5	1201.1	1184.1	1163.9	1136.1	1104.0	1078.7	1050.6
12.5°	1315.2	1313.9	1305.6	1295.6	1280.8	1264.7	1239.8	1206.0	1168.7	1132.1	1099.9
15°	1423.1	1425.3	1419.8	1409.4	1388.5	1359.9	1322.4	1308.3	1254.9	1215.1	1175.4
17.5°	1497.8	1497.3	1496.6	1482.1	1460.8	1440.4	1405.6	1368.6	1320.2	1264.2	1210.8
20°	1545.1	1541.5	1542.3	1526.0	1510.1	1486.7	1452.7	1398.9	1359.2	1294.6	1239.3
22.5°	1544.0	1543.2	1546.0	1540.4	1528.9	1510.9	1484.2	1438.8	1388.1	1322.9	1260.7
25°	1466.4	1463.6	1480.5	1485.2	1503.6	1506.8	1498.9	1474.0	1426.0	1358.9	1282.0
27.5°	1227.3	1225.7	1257.2	1296.6	1346.6	1385.4	1423.0	1441.1	1426.0	1377.9	1300.9
30°	1007.2	1041.1	1057.1	1114.1	1177.6	1253.4	1319.8	1383.0	1398.5	1377.6	1314.5
32.5°	836.2	865.8	879.1	928.1	987.3	1076.1	1175.7	1265.2	1328.4	1344.4	1306.4
35°	636.1	636.5	666.8	688.4	743.3	834.6	931.4	1051.2	1170.4	1260.7	1270.1
37.5°	507.6	509.3	527.7	549.3	590.5	638.8	724.0	823.6	961.2	1099.8	1181.0
40°	438.3	441.5	455.2	476.5	506.1	542.6	609.1	702.9	817.7	971.9	1097.9
42.5°	393.8	399.1	406.1	422.5	440.8	475.0	528.8	601.2	705.6	851.4	996.7
45°	339.3	342.2	347.6	355.2	371.8	395.7	431.8	480.5	567.1	684.5	830.0
47.5°	299.4	297.8	303.5	309.7	320.7	337.0	361.2	401.0	462.8	556.9	680.3
50°	272.2	271.8	275.8	280.5	291.0	302.9	322.7	352.7	401.8	479.8	592.8
52.5°	246.8	248.2	251.0	256.8	264.4	274.0	291.8	313.4	355.6	422.9	517.1
55°	213.0	214.1	218.0	221.3	226.7	236.5	247.7	265.7	294.5	341.5	419.1
57.5°	184.4	183.9	187.8	188.5	194.6	202.6	211.2	225.3	246.2	281.1	333.4
60°	165.3	164.3	167.5	170.0	173.2	179.7	187.0	200.8	217.4	243.0	287.8
62.5°	148.0	147.5	149.9	152.4	155.0	161.0	167.1	177.6	190.8	212.4	247.9
65°	122.7	123.9	124.9	126.0	127.4	131.0	136.9	144.0	153.1	168.2	193.9
67.5°	96.4	97.6	97.9	100.1	103.2	105.5	109.1	115.5	121.8	134.5	149.1
70°	77.9	77.6	77.9	79.1	83.0	87.0	91.7	96.4	100.4	109.4	121.7
72.5°	67.0	66.4	67.3	67.5	69.5	70.5	73.5	77.9	83.0	89.2	98.0
75°	52.0	52.0	52.0	52.0	53.4	54.2	55.2	56.4	58.2	61.0	67.5
77.5°	38.5	38.5	39.0	39.3	39.7	40.1	40.7	41.8	42.4	44.0	46.8
80°	30.3	30.7	30.3	30.7	30.7	31.4	31.8	32.9	33.2	35.1	36.1
82.5°	22.8	22.6	22.8	23.2	23.2	23.9	23.9	24.8	24.9	25.7	26.9
85°	12.3	11.6	12.3	11.9	12.6	11.9	12.3	13.0	13.0	13.4	14.8
87.5°	8.4	9.1	8.4	8.5	8.7	8.6	8.4	8.2	8.6	8.5	8.2
90°	27.2	28.2	27.2	26.3	27.2	25.4	24.5	23.6	22.6	23.6	20.7
92.5°	45.3	47.0	46.1	48.9	50.6	55.5	62.9	79.2	109.1	144.7	159.2
95°	109.1	112.9	119.5	128.0	145.8	179.7	229.6	338.7	452.5	557.9	496.7
97.5°	297.1	305.2	330.6	373.0	442.3	554.9	676.3	844.3	925.0	864.6	633.0
100°	589.9	589.0	625.7	694.4	789.4	922.9	1033.0	1109.3	1076.3	891.0	602.1
102.5°	865.3	887.0	917.7	972.0	1046.0	1130.7	1194.9	1197.3	1083.8	842.1	556.9
105°	1196.7	1201.5	1231.5	1267.2	1310.6	1335.0	1317.2	1223.0	1026.4	756.4	501.4
107.5°	1387.5	1396.2	1406.4	1418.4	1417.7	1384.1	1301.7	1149.0	926.0	680.8	466.1
110°	1465.8	1467.7	1469.6	1462.1	1435.7	1369.8	1251.3	1078.2	862.7	637.9	452.5



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1481.6	1481.2	1474.0	1450.8	1402.6	1317.9	1185.1	1008.1	807.8	609.3	445.0
115°	1455.5	1450.8	1431.9	1390.5	1319.9	1217.4	1079.1	915.4	741.4	578.6	442.1
117.5°	1372.2	1365.9	1338.8	1291.4	1217.8	1113.7	989.6	848.3	701.3	560.5	443.8
120°	1303.1	1297.4	1274.8	1222.1	1147.8	1052.8	939.9	812.8	680.2	552.2	446.9
122.5°	1238.3	1231.1	1206.4	1159.0	1092.9	1004.7	900.0	785.0	662.9	547.0	452.1
125°	1147.8	1141.2	1117.7	1076.3	1016.1	940.8	850.6	748.0	640.7	540.1	460.1
127.5°	1073.3	1067.2	1046.0	1010.6	957.0	888.5	807.0	715.6	621.1	536.7	469.1
130°	1031.1	1023.6	1003.9	970.0	920.1	856.1	780.0	695.3	610.6	534.4	475.1
132.5°	989.8	984.5	967.0	933.1	886.3	825.3	754.3	676.5	600.8	533.7	479.7
135°	930.5	923.9	906.9	878.7	832.6	779.0	717.8	651.0	588.1	532.5	486.4
137.5°	867.8	863.5	849.2	820.6	781.8	735.4	682.7	627.9	576.9	530.5	490.9
140°	824.2	825.1	810.0	783.7	748.0	707.5	662.3	614.3	570.1	529.7	493.9
142.5°	783.5	784.5	770.9	747.6	717.1	681.9	642.8	601.5	564.1	528.2	496.2
145°	727.3	725.4	717.8	698.0	674.6	647.2	617.2	586.2	556.0	525.9	497.7
147.5°	681.0	680.2	673.1	659.7	641.9	622.5	598.1	573.5	548.1	522.4	497.7
150°	653.8	653.8	648.2	637.9	623.8	605.9	586.2	564.5	542.8	519.3	497.7
152.5°	631.3	631.3	627.9	618.3	607.2	592.4	574.9	556.2	536.9	515.6	495.4
155°	603.0	602.1	600.2	592.8	584.3	573.0	558.8	543.8	527.8	509.0	492.9
157.5°	577.3	577.5	576.0	570.3	563.0	554.1	543.2	530.7	517.6	503.1	489.8
160°	560.7	561.7	561.7	556.0	549.4	542.8	533.5	523.1	510.9	498.6	488.3
162.5°	545.6	546.6	546.6	541.8	537.4	531.6	522.9	514.1	504.1	494.1	485.3
165°	525.9	525.9	526.9	523.1	519.3	514.6	508.0	502.4	494.8	487.4	480.8
167.5°	507.1	507.1	508.0	505.4	503.7	500.3	496.5	492.2	486.1	480.6	476.3
170°	495.8	495.8	496.7	494.8	493.9	492.0	488.3	485.5	480.8	476.1	473.3
172.5°	485.3	486.1	487.8	485.9	485.7	484.6	481.5	479.5	475.5	472.3	471.0
175°	473.3	474.2	475.1	474.2	474.2	474.2	472.3	471.4	469.5	467.6	467.6
177.5°	466.3	466.3	467.8	467.0	467.8	467.8	467.0	466.3	465.5	464.8	465.5
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	870.7	869.9	865.8	861.2	855.2	851.1	847.9	846.2	841.0	834.6	830.3
5°	924.5	913.7	902.2	888.1	875.1	861.8	853.5	843.7	831.8	818.4	809.0
7.5°	982.1	960.9	938.0	914.5	891.1	870.2	851.7	835.8	816.9	797.8	784.3
10°	1026.3	995.3	963.2	930.3	900.3	872.2	850.6	829.2	806.5	784.5	767.9
12.5°	1066.5	1025.7	988.6	948.2	909.9	876.3	845.1	820.0	792.7	769.2	750.3
15°	1117.3	1075.4	1030.7	969.3	918.4	875.8	837.9	805.0	771.8	743.0	724.5
17.5°	1164.8	1101.8	1041.7	990.4	924.4	871.1	824.8	785.5	749.1	718.5	695.8
20°	1184.5	1123.5	1058.1	992.8	927.8	868.3	814.5	771.1	733.2	698.5	677.6
22.5°	1196.3	1127.2	1058.4	988.2	919.2	857.2	804.1	756.4	715.3	682.4	656.6
25°	1210.1	1127.8	1052.0	982.7	912.3	845.1	781.9	731.4	687.0	652.0	624.5
27.5°	1219.2	1122.4	1032.7	955.7	884.3	817.5	759.6	706.0	660.9	623.9	594.5
30°	1221.0	1118.0	1018.0	934.6	862.0	800.7	739.3	688.1	640.5	601.1	573.6
32.5°	1223.2	1107.4	998.2	909.6	835.3	774.5	718.9	669.9	621.0	582.3	554.3
35°	1213.7	1101.5	967.9	866.1	791.7	732.8	682.7	637.5	589.6	552.0	523.5
37.5°	1172.7	1078.0	936.5	817.1	739.3	684.9	643.9	604.6	560.6	520.1	493.2
40°	1131.4	1054.9	912.3	787.4	706.2	650.2	613.3	581.3	538.7	500.7	471.8
42.5°	1069.9	1023.4	889.2	756.2	668.5	614.6	583.6	553.5	516.1	477.6	450.4
45°	957.1	963.2	841.9	706.5	616.6	562.4	533.2	512.3	479.1	447.3	419.5
47.5°	815.5	872.9	786.4	653.6	561.8	511.0	485.4	467.1	444.8	413.6	388.2
50°	723.1	805.0	741.9	618.0	527.4	476.9	451.7	436.9	417.4	392.8	368.6
52.5°	637.9	725.9	688.2	578.4	490.2	443.9	419.2	407.1	391.6	368.5	346.7
55°	520.2	609.4	600.7	518.8	434.3	392.8	374.0	360.3	349.8	332.5	315.2
57.5°	420.8	505.3	509.8	452.3	385.0	344.0	327.9	317.5	310.7	297.7	281.6
60°	358.2	435.7	450.9	407.6	349.8	313.7	297.8	289.5	284.1	273.6	261.4
62.5°	306.1	372.2	389.4	358.2	316.0	282.2	269.8	261.8	258.2	249.1	238.3
65°	234.3	289.2	305.8	288.4	266.5	239.3	229.2	222.3	219.1	214.1	206.1
67.5°	176.2	216.2	234.4	222.2	214.2	197.1	190.7	187.0	184.1	180.7	174.0
70°	141.5	171.2	189.9	186.6	180.1	171.2	166.5	163.9	161.0	158.2	152.3
72.5°	113.8	134.1	151.7	153.4	148.1	146.3	142.1	141.1	139.3	135.9	132.7
75°	75.5	89.5	101.8	106.5	108.7	110.5	108.7	108.3	107.9	105.1	103.2
77.5°	49.5	57.0	64.8	72.8	76.2	78.6	79.2	80.5	79.6	78.0	77.2
80°	37.9	39.7	45.1	52.0	57.4	59.6	61.0	61.7	61.4	61.0	59.6
82.5°	27.5	29.0	31.6	36.4	40.9	44.6	45.4	45.2	46.1	46.3	45.1
85°	14.8	15.2	15.9	16.6	19.1	23.1	24.2	24.9	25.6	25.6	23.5
87.5°	8.2	7.4	7.4	7.0	7.4	7.2	8.6	9.6	10.3	9.5	10.1
90°	17.9	15.1	12.3	10.4	8.5	5.7	3.8	1.9	3.8	5.7	8.5
92.5°	119.5	79.0	54.4	40.4	32.5	25.3	17.3	11.7	17.3	25.3	32.5
95°	342.4	202.3	122.3	85.6	61.2	45.1	34.8	32.0	34.8	45.1	61.2
97.5°	375.8	217.7	141.3	101.6	77.5	63.6	55.5	54.6	55.5	63.6	77.5
100°	354.7	215.5	149.6	112.9	90.3	77.2	70.6	69.7	70.6	77.2	90.3
102.5°	336.6	218.5	159.4	125.7	105.4	92.9	87.1	85.4	87.1	92.9	105.4
105°	323.7	226.8	176.0	146.8	128.9	117.6	112.0	109.1	112.0	117.6	128.9
107.5°	322.7	242.1	197.6	170.5	153.7	142.6	137.1	134.3	137.1	142.6	153.7
110°	326.5	255.0	212.6	186.2	170.3	159.9	155.2	152.4	155.2	159.9	170.3



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	334.0	267.8	228.5	202.8	186.8	176.5	171.8	169.0	171.8	176.5	186.8
115°	346.2	288.8	253.1	227.7	211.7	202.3	196.6	192.8	196.6	202.3	211.7
117.5°	362.4	311.2	275.9	252.3	234.4	225.8	221.1	216.8	221.1	225.8	234.4
120°	374.5	325.6	291.6	268.2	250.2	240.8	236.1	233.3	236.1	240.8	250.2
122.5°	385.8	340.5	307.5	282.5	265.3	255.1	250.4	247.6	250.4	255.1	265.3
125°	403.6	362.2	329.3	303.9	286.0	275.7	270.0	268.2	270.0	275.7	286.0
127.5°	418.3	381.1	349.2	323.9	304.1	293.5	286.5	283.8	286.5	293.5	304.1
130°	428.1	392.3	361.3	335.8	316.1	304.8	296.3	293.5	296.3	304.8	316.1
132.5°	437.2	402.1	371.8	347.1	327.4	313.9	304.6	301.0	304.6	313.9	327.4
135°	448.7	416.8	387.6	362.2	342.4	328.4	318.0	314.2	318.0	328.4	342.4
137.5°	457.4	427.0	398.9	375.4	355.8	340.7	330.6	326.7	330.6	340.7	355.8
140°	461.9	433.8	406.4	383.0	364.1	349.0	339.6	335.0	339.6	349.0	364.1
142.5°	466.5	439.0	412.5	390.4	371.6	358.1	347.9	343.9	347.9	358.1	371.6
145°	471.4	445.9	421.5	399.8	383.9	369.8	361.3	358.4	361.3	369.8	383.9
147.5°	474.4	451.6	429.2	410.8	395.3	383.1	374.8	373.2	374.8	383.1	395.3
150°	475.1	455.3	433.8	416.8	403.6	391.3	383.9	383.0	383.9	391.3	403.6
152.5°	476.6	457.6	439.0	422.8	411.1	400.4	392.9	392.7	392.9	400.4	411.1
155°	477.0	461.9	445.9	432.8	422.4	413.0	407.4	407.4	407.4	413.0	422.4
157.5°	478.0	464.4	451.6	441.4	432.6	424.3	419.8	419.1	419.8	424.3	432.6
160°	478.0	466.7	455.3	445.9	439.3	431.9	428.1	428.1	428.1	431.9	439.3
162.5°	477.2	467.4	457.6	449.7	443.8	437.9	434.9	434.9	434.9	437.9	443.8
165°	475.1	468.5	461.0	454.4	450.6	445.9	444.0	445.0	444.0	445.9	450.6
167.5°	473.6	468.3	462.9	458.7	456.1	452.5	451.6	452.7	451.6	452.5	456.1
170°	471.4	467.6	462.9	461.0	459.1	456.3	455.3	457.2	455.3	456.3	459.1
172.5°	470.6	467.6	463.6	462.5	461.4	459.3	459.1	460.2	459.1	459.3	461.4
175°	468.5	466.7	464.8	463.8	463.8	461.9	462.9	463.8	462.9	461.9	463.8
177.5°	467.0	465.5	464.8	464.8	464.8	464.0	464.8	465.5	464.8	464.0	464.8
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	828.9	825.1	822.6	816.7	813.0	809.0	804.9	807.5	807.2	806.9	806.9
5°	801.1	792.8	785.2	775.4	769.3	761.8	755.9	755.3	756.7	751.6	748.8
7.5°	773.5	762.1	751.4	740.6	729.2	720.1	714.4	711.8	708.1	705.0	701.7
10°	754.1	740.8	730.3	717.0	704.7	693.9	687.0	682.3	679.8	677.2	672.6
12.5°	734.2	721.1	707.8	692.7	681.0	668.5	663.4	658.1	653.2	650.4	643.9
15°	705.0	688.1	674.0	658.1	645.2	632.8	625.7	615.2	613.7	610.1	603.6
17.5°	675.8	657.4	638.0	626.2	611.5	598.8	587.8	584.3	573.9	570.0	564.4
20°	652.7	635.7	620.9	605.4	584.1	572.2	563.5	558.8	550.5	545.4	541.9
22.5°	632.8	615.5	598.4	580.3	562.7	549.4	543.0	535.7	531.2	524.1	520.2
25°	604.4	585.6	565.0	545.4	532.8	522.7	512.6	506.1	499.6	496.3	489.2
27.5°	571.3	551.7	532.4	517.6	502.1	492.1	483.0	477.2	469.4	463.9	460.0
30°	553.1	530.0	513.4	500.0	480.1	470.8	463.9	456.7	450.9	445.2	441.1
32.5°	532.0	510.9	495.1	478.6	463.4	453.2	444.2	437.9	433.0	427.5	423.6
35°	498.9	481.3	465.0	448.4	437.2	426.7	416.2	410.9	406.1	401.1	397.5
37.5°	469.0	452.5	437.1	421.3	407.5	398.9	390.5	386.3	380.0	376.6	373.0
40°	450.5	434.3	417.7	402.6	388.0	381.6	374.0	367.9	362.1	359.6	355.6
42.5°	430.4	414.1	400.1	383.7	371.9	363.1	356.1	349.4	345.1	341.4	339.1
45°	400.4	385.9	372.2	356.0	344.8	337.1	329.2	323.1	319.1	316.6	312.6
47.5°	371.3	356.8	342.9	328.8	317.9	309.2	301.3	297.0	291.8	288.7	286.0
50°	350.2	337.1	322.3	309.3	298.6	289.9	283.4	278.0	273.2	269.3	267.5
52.5°	330.8	317.0	304.2	292.1	280.7	270.8	264.9	259.2	255.7	251.1	249.0
55°	298.9	285.6	274.8	262.8	251.7	243.4	236.1	231.0	227.4	222.3	219.5
57.5°	268.9	256.9	244.0	233.8	222.2	215.2	209.2	202.3	197.9	194.0	191.1
60°	248.7	235.0	223.9	214.1	204.0	194.9	189.5	184.1	179.5	175.4	173.0
62.5°	227.6	215.7	205.1	194.4	185.2	177.3	171.1	166.5	162.4	159.9	157.3
65°	195.3	186.0	175.1	166.5	157.8	152.0	146.9	143.0	140.1	138.3	136.1
67.5°	165.6	156.5	147.0	138.5	132.7	128.3	125.0	121.6	120.2	117.8	116.4
70°	146.2	136.9	128.6	122.1	116.2	113.0	110.8	108.3	106.9	104.0	102.5
72.5°	125.2	118.4	112.4	107.0	102.4	99.4	96.7	93.6	91.2	88.1	86.6
75°	98.6	92.5	87.8	84.1	81.2	77.3	73.3	70.0	69.0	67.9	67.5
77.5°	73.0	69.1	65.7	62.7	59.1	56.2	55.3	54.6	54.4	53.8	53.8
80°	57.4	53.8	51.3	47.7	45.5	45.5	45.5	44.8	45.1	45.1	45.1
82.5°	42.7	39.3	38.0	36.7	36.3	36.6	36.6	36.7	36.5	37.0	36.8
85°	22.1	22.3	23.1	22.7	23.1	23.1	23.8	23.5	23.8	23.1	23.8
87.5°	10.2	11.4	12.3	13.1	13.9	14.2	14.3	14.5	15.0	15.2	15.6
90°	10.4	12.3	15.1	17.9	20.7	23.6	22.6	23.6	24.5	25.4	27.2
92.5°	40.4	54.4	79.0	119.5	159.2	144.7	109.1	79.2	62.9	55.5	50.6
95°	85.6	122.3	202.3	342.4	496.7	557.9	452.5	338.7	229.6	179.7	145.8
97.5°	101.6	141.3	217.7	375.8	633.0	864.6	925.0	844.3	676.3	554.9	442.3
100°	112.9	149.6	215.5	354.7	602.1	891.0	1076.3	1109.3	1033.0	922.9	789.4
102.5°	125.7	159.4	218.5	336.6	556.9	842.1	1083.8	1197.3	1194.9	1130.7	1046.0
105°	146.8	176.0	226.8	323.7	501.4	756.4	1026.4	1223.0	1317.2	1335.0	1310.6
107.5°	170.5	197.6	242.1	322.7	466.1	680.8	926.0	1149.0	1301.7	1384.1	1417.7
110°	186.2	212.6	255.0	326.5	452.5	637.9	862.7	1078.2	1251.3	1369.8	1435.7



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	202.8	228.5	267.8	334.0	445.0	609.3	807.8	1008.1	1185.1	1317.9	1402.6
115°	227.7	253.1	288.8	346.2	442.1	578.6	741.4	915.4	1079.1	1217.4	1319.9
117.5°	252.3	275.9	311.2	362.4	443.8	560.5	701.3	848.3	989.6	1113.7	1217.8
120°	268.2	291.6	325.6	374.5	446.9	552.2	680.2	812.8	939.9	1052.8	1147.8
122.5°	282.5	307.5	340.5	385.8	452.1	547.0	662.9	785.0	900.0	1004.7	1092.9
125°	303.9	329.3	362.2	403.6	460.1	540.1	640.7	748.0	850.6	940.8	1016.1
127.5°	323.9	349.2	381.1	418.3	469.1	536.7	621.1	715.6	807.0	888.5	957.0
130°	335.8	361.3	392.3	428.1	475.1	534.4	610.6	695.3	780.0	856.1	920.1
132.5°	347.1	371.8	402.1	437.2	479.7	533.7	600.8	676.5	754.3	825.3	886.3
135°	362.2	387.6	416.8	448.7	486.4	532.5	588.1	651.0	717.8	779.0	832.6
137.5°	375.4	398.9	427.0	457.4	490.9	530.5	576.9	627.9	682.7	735.4	781.8
140°	383.0	406.4	433.8	461.9	493.9	529.7	570.1	614.3	662.3	707.5	748.0
142.5°	390.4	412.5	439.0	466.5	496.2	528.2	564.1	601.5	642.8	681.9	717.1
145°	399.8	421.5	445.9	471.4	497.7	525.9	556.0	586.2	617.2	647.2	674.6
147.5°	410.8	429.2	451.6	474.4	497.7	522.4	548.1	573.5	598.1	622.5	641.9
150°	416.8	433.8	455.3	475.1	497.7	519.3	542.8	564.5	586.2	605.9	623.8
152.5°	422.8	439.0	457.6	476.6	495.4	515.6	536.9	556.2	574.9	592.4	607.2
155°	432.8	445.9	461.9	477.0	492.9	509.0	527.8	543.8	558.8	573.0	584.3
157.5°	441.4	451.6	464.4	478.0	489.8	503.1	517.6	530.7	543.2	554.1	563.0
160°	445.9	455.3	466.7	478.0	488.3	498.6	510.9	523.1	533.5	542.8	549.4
162.5°	449.7	457.6	467.4	477.2	485.3	494.1	504.1	514.1	522.9	531.6	537.4
165°	454.4	461.0	468.5	475.1	480.8	487.4	494.8	502.4	508.0	514.6	519.3
167.5°	458.7	462.9	468.3	473.6	476.3	480.6	486.1	492.2	496.5	500.3	503.7
170°	461.0	462.9	467.6	471.4	473.3	476.1	480.8	485.5	488.3	492.0	493.9
172.5°	462.5	463.6	467.6	470.6	471.0	472.3	475.5	479.5	481.5	484.6	485.7
175°	463.8	464.8	466.7	468.5	467.6	467.6	469.5	471.4	472.3	474.2	474.2
177.5°	464.8	464.8	465.5	467.0	465.5	464.8	465.5	466.3	467.0	467.8	467.8
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	803.4	803.1	803.4	802.3	803.4	803.1	803.4	806.9	806.9	807.2	807.5
5°	747.6	747.2	746.2	743.0	746.2	747.2	747.6	748.8	751.6	756.7	755.3
7.5°	698.9	698.4	695.2	695.3	695.2	698.4	698.9	701.7	705.0	708.1	711.8
10°	670.1	670.4	666.1	663.5	666.1	670.4	670.1	672.6	677.2	679.8	682.3
12.5°	642.1	640.4	636.9	634.0	636.9	640.4	642.1	643.9	650.4	653.2	658.1
15°	605.0	601.4	592.8	593.5	592.8	601.4	605.0	603.6	610.1	613.7	615.2
17.5°	561.5	558.8	558.7	553.6	558.7	558.8	561.5	564.4	570.0	573.9	584.3
20°	536.1	534.3	535.0	530.0	535.0	534.3	536.1	541.9	545.4	550.5	558.8
22.5°	516.1	514.3	511.3	509.7	511.3	514.3	516.1	520.2	524.1	531.2	535.7
25°	487.0	484.1	481.3	483.1	481.3	484.1	487.0	489.2	496.3	499.6	506.1
27.5°	457.8	455.6	452.8	452.4	452.8	455.6	457.8	460.0	463.9	469.4	477.2
30°	439.3	437.2	435.7	433.9	435.7	437.2	439.3	441.1	445.2	450.9	456.7
32.5°	420.6	420.2	417.5	417.2	417.5	420.2	420.6	423.6	427.5	433.0	437.9
35°	396.1	393.9	393.1	393.5	393.1	393.9	396.1	397.5	401.1	406.1	410.9
37.5°	372.7	369.9	368.5	367.2	368.5	369.9	372.7	373.0	376.6	380.0	386.3
40°	356.0	353.1	352.3	351.7	352.3	353.1	356.0	355.6	359.6	362.1	367.9
42.5°	337.1	336.0	335.6	334.3	335.6	336.0	337.1	339.1	341.4	345.1	349.4
45°	311.5	311.2	309.1	309.7	309.1	311.2	311.5	312.6	316.6	319.1	323.1
47.5°	284.6	283.0	281.4	282.5	281.4	283.0	284.6	286.0	288.7	291.8	297.0
50°	266.1	265.3	262.1	262.8	262.1	265.3	266.1	267.5	269.3	273.2	278.0
52.5°	247.6	244.9	243.6	243.2	243.6	244.9	247.6	249.0	251.1	255.7	259.2
55°	217.0	213.7	212.3	211.5	212.3	213.7	217.0	219.5	222.3	227.4	231.0
57.5°	186.9	186.1	184.9	185.7	184.9	186.1	186.9	191.1	194.0	197.9	202.3
60°	169.3	169.3	169.3	169.0	169.3	169.3	169.3	173.0	175.4	179.5	184.1
62.5°	155.7	154.9	154.6	155.0	154.6	154.9	155.7	157.3	159.9	162.4	166.5
65°	135.0	134.7	133.2	132.9	133.2	134.7	135.0	136.1	138.3	140.1	143.0
67.5°	115.5	114.1	113.8	113.2	113.8	114.1	115.5	116.4	117.8	120.2	121.6
70°	100.8	100.0	97.8	98.2	97.8	100.0	100.8	102.5	104.0	106.9	108.3
72.5°	84.8	84.1	83.7	83.1	83.7	84.1	84.8	86.6	88.1	91.2	93.6
75°	67.1	66.8	66.4	67.9	66.4	66.8	67.1	67.5	67.9	69.0	70.0
77.5°	53.8	53.8	54.0	53.4	54.0	53.8	53.8	53.8	53.8	54.4	54.6
80°	45.1	45.1	44.8	44.8	44.8	45.1	45.1	45.1	45.1	45.1	44.8
82.5°	36.2	36.5	36.7	36.1	36.7	36.5	36.2	36.8	37.0	36.5	36.7
85°	23.8	23.5	24.2	23.8	24.2	23.5	23.8	23.8	23.1	23.8	23.5
87.5°	15.9	15.6	15.7	15.8	15.7	15.6	15.9	15.6	15.2	15.0	14.5
90°	26.3	27.2	28.2	27.2	28.2	27.2	26.3	27.2	25.4	24.5	23.6
92.5°	48.9	46.1	47.0	45.3	47.0	46.1	48.9	50.6	55.5	62.9	79.2
95°	128.0	119.5	112.9	109.1	112.9	119.5	128.0	145.8	179.7	229.6	338.7
97.5°	373.0	330.6	305.2	297.1	305.2	330.6	373.0	442.3	554.9	676.3	844.3
100°	694.4	625.7	589.0	589.9	589.0	625.7	694.4	789.4	922.9	1033.0	1109.3
102.5°	972.0	917.7	887.0	865.3	887.0	917.7	972.0	1046.0	1130.7	1194.9	1197.3
105°	1267.2	1231.5	1201.5	1196.7	1201.5	1231.5	1267.2	1310.6	1335.0	1317.2	1223.0
107.5°	1418.4	1406.4	1396.2	1387.5	1396.2	1406.4	1418.4	1417.7	1384.1	1301.7	1149.0
110°	1462.1	1469.6	1467.7	1465.8	1467.7	1469.6	1462.1	1435.7	1369.8	1251.3	1078.2



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1450.8	1474.0	1481.2	1481.6	1481.2	1474.0	1450.8	1402.6	1317.9	1185.1	1008.1
115°	1390.5	1431.9	1450.8	1455.5	1450.8	1431.9	1390.5	1319.9	1217.4	1079.1	915.4
117.5°	1291.4	1338.8	1365.9	1372.2	1365.9	1338.8	1291.4	1217.8	1113.7	989.6	848.3
120°	1222.1	1274.8	1297.4	1303.1	1297.4	1274.8	1222.1	1147.8	1052.8	939.9	812.8
122.5°	1159.0	1206.4	1231.1	1238.3	1231.1	1206.4	1159.0	1092.9	1004.7	900.0	785.0
125°	1076.3	1117.7	1141.2	1147.8	1141.2	1117.7	1076.3	1016.1	940.8	850.6	748.0
127.5°	1010.6	1046.0	1067.2	1073.3	1067.2	1046.0	1010.6	957.0	888.5	807.0	715.6
130°	970.0	1003.9	1023.6	1031.1	1023.6	1003.9	970.0	920.1	856.1	780.0	695.3
132.5°	933.1	967.0	984.5	989.8	984.5	967.0	933.1	886.3	825.3	754.3	676.5
135°	878.7	906.9	923.9	930.5	923.9	906.9	878.7	832.6	779.0	717.8	651.0
137.5°	820.6	849.2	863.5	867.8	863.5	849.2	820.6	781.8	735.4	682.7	627.9
140°	783.7	810.0	825.1	824.2	825.1	810.0	783.7	748.0	707.5	662.3	614.3
142.5°	747.6	770.9	784.5	783.5	784.5	770.9	747.6	717.1	681.9	642.8	601.5
145°	698.0	717.8	725.4	727.3	725.4	717.8	698.0	674.6	647.2	617.2	586.2
147.5°	659.7	673.1	680.2	681.0	680.2	673.1	659.7	641.9	622.5	598.1	573.5
150°	637.9	648.2	653.8	653.8	653.8	648.2	637.9	623.8	605.9	586.2	564.5
152.5°	618.3	627.9	631.3	631.3	631.3	627.9	618.3	607.2	592.4	574.9	556.2
155°	592.8	600.2	602.1	603.0	602.1	600.2	592.8	584.3	573.0	558.8	543.8
157.5°	570.3	576.0	577.5	577.3	577.5	576.0	570.3	563.0	554.1	543.2	530.7
160°	556.0	561.7	561.7	560.7	561.7	561.7	556.0	549.4	542.8	533.5	523.1
162.5°	541.8	546.6	546.6	545.6	546.6	546.6	541.8	537.4	531.6	522.9	514.1
165°	523.1	526.9	525.9	525.9	525.9	526.9	523.1	519.3	514.6	508.0	502.4
167.5°	505.4	508.0	507.1	507.1	507.1	508.0	505.4	503.7	500.3	496.5	492.2
170°	494.8	496.7	495.8	495.8	495.8	496.7	494.8	493.9	492.0	488.3	485.5
172.5°	485.9	487.8	486.1	485.3	486.1	487.8	485.9	485.7	484.6	481.5	479.5
175°	474.2	475.1	474.2	473.3	474.2	475.1	474.2	474.2	474.2	472.3	471.4
177.5°	467.0	467.8	466.3	466.3	466.3	467.8	467.0	467.8	467.8	467.0	466.3
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	804.9	809.0	813.0	816.7	822.6	825.1	828.9	830.3	834.6	841.0	846.2
5°	755.9	761.8	769.3	775.4	785.2	792.8	801.1	809.0	818.4	831.8	843.7
7.5°	714.4	720.1	729.2	740.6	751.4	762.1	773.5	784.3	797.8	816.9	835.8
10°	687.0	693.9	704.7	717.0	730.3	740.8	754.1	767.9	784.5	806.5	829.2
12.5°	663.4	668.5	681.0	692.7	707.8	721.1	734.2	750.3	769.2	792.7	820.0
15°	625.7	632.8	645.2	658.1	674.0	688.1	705.0	724.5	743.0	771.8	805.0
17.5°	587.8	598.8	611.5	626.2	638.0	657.4	675.8	695.8	718.5	749.1	785.5
20°	563.5	572.2	584.1	605.4	620.9	635.7	652.7	677.6	698.5	733.2	771.1
22.5°	543.0	549.4	562.7	580.3	598.4	615.5	632.8	656.6	682.4	715.3	756.4
25°	512.6	522.7	532.8	545.4	565.0	585.6	604.4	624.5	652.0	687.0	731.4
27.5°	483.0	492.1	502.1	517.6	532.4	551.7	571.3	594.5	623.9	660.9	706.0
30°	463.9	470.8	480.1	500.0	513.4	530.0	553.1	573.6	601.1	640.5	688.1
32.5°	444.2	453.2	463.4	478.6	495.1	510.9	532.0	554.3	582.3	621.0	669.9
35°	416.2	426.7	437.2	448.4	465.0	481.3	498.9	523.5	552.0	589.6	637.5
37.5°	390.5	398.9	407.5	421.3	437.1	452.5	469.0	493.2	520.1	560.6	604.6
40°	374.0	381.6	388.0	402.6	417.7	434.3	450.5	471.8	500.7	538.7	581.3
42.5°	356.1	363.1	371.9	383.7	400.1	414.1	430.4	450.4	477.6	516.1	553.5
45°	329.2	337.1	344.8	356.0	372.2	385.9	400.4	419.5	447.3	479.1	512.3
47.5°	301.3	309.2	317.9	328.8	342.9	356.8	371.3	388.2	413.6	444.8	467.1
50°	283.4	289.9	298.6	309.3	322.3	337.1	350.2	368.6	392.8	417.4	436.9
52.5°	264.9	270.8	280.7	292.1	304.2	317.0	330.8	346.7	368.5	391.6	407.1
55°	236.1	243.4	251.7	262.8	274.8	285.6	298.9	315.2	332.5	349.8	360.3
57.5°	209.2	215.2	222.2	233.8	244.0	256.9	268.9	281.6	297.7	310.7	317.5
60°	189.5	194.9	204.0	214.1	223.9	235.0	248.7	261.4	273.6	284.1	289.5
62.5°	171.1	177.3	185.2	194.4	205.1	215.7	227.6	238.3	249.1	258.2	261.8
65°	146.9	152.0	157.8	166.5	175.1	186.0	195.3	206.1	214.1	219.1	222.3
67.5°	125.0	128.3	132.7	138.5	147.0	156.5	165.6	174.0	180.7	184.1	187.0
70°	110.8	113.0	116.2	122.1	128.6	136.9	146.2	152.3	158.2	161.0	163.9
72.5°	96.7	99.4	102.4	107.0	112.4	118.4	125.2	132.7	135.9	139.3	141.1
75°	73.3	77.3	81.2	84.1	87.8	92.5	98.6	103.2	105.1	107.9	108.3
77.5°	55.3	56.2	59.1	62.7	65.7	69.1	73.0	77.2	78.0	79.6	80.5
80°	45.5	45.5	45.5	47.7	51.3	53.8	57.4	59.6	61.0	61.4	61.7
82.5°	36.6	36.6	36.3	36.7	38.0	39.3	42.7	45.1	46.3	46.1	45.2
85°	23.8	23.1	23.1	22.7	23.1	22.3	22.1	23.5	25.6	25.6	24.9
87.5°	14.3	14.2	13.9	13.1	12.3	11.4	10.2	10.1	9.5	10.3	9.6
90°	22.6	23.6	20.7	17.9	15.1	12.3	10.4	8.5	5.7	3.8	1.9
92.5°	109.1	144.7	159.2	119.5	79.0	54.4	40.4	32.5	25.3	17.3	11.7
95°	452.5	557.9	496.7	342.4	202.3	122.3	85.6	61.2	45.1	34.8	32.0
97.5°	925.0	864.6	633.0	375.8	217.7	141.3	101.6	77.5	63.6	55.5	54.6
100°	1076.3	891.0	602.1	354.7	215.5	149.6	112.9	90.3	77.2	70.6	69.7
102.5°	1083.8	842.1	556.9	336.6	218.5	159.4	125.7	105.4	92.9	87.1	85.4
105°	1026.4	756.4	501.4	323.7	226.8	176.0	146.8	128.9	117.6	112.0	109.1
107.5°	926.0	680.8	466.1	322.7	242.1	197.6	170.5	153.7	142.6	137.1	134.3
110°	862.7	637.9	452.5	326.5	255.0	212.6	186.2	170.3	159.9	155.2	152.4



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	807.8	609.3	445.0	334.0	267.8	228.5	202.8	186.8	176.5	171.8	169.0
115°	741.4	578.6	442.1	346.2	288.8	253.1	227.7	211.7	202.3	196.6	192.8
117.5°	701.3	560.5	443.8	362.4	311.2	275.9	252.3	234.4	225.8	221.1	216.8
120°	680.2	552.2	446.9	374.5	325.6	291.6	268.2	250.2	240.8	236.1	233.3
122.5°	662.9	547.0	452.1	385.8	340.5	307.5	282.5	265.3	255.1	250.4	247.6
125°	640.7	540.1	460.1	403.6	362.2	329.3	303.9	286.0	275.7	270.0	268.2
127.5°	621.1	536.7	469.1	418.3	381.1	349.2	323.9	304.1	293.5	286.5	283.8
130°	610.6	534.4	475.1	428.1	392.3	361.3	335.8	316.1	304.8	296.3	293.5
132.5°	600.8	533.7	479.7	437.2	402.1	371.8	347.1	327.4	313.9	304.6	301.0
135°	588.1	532.5	486.4	448.7	416.8	387.6	362.2	342.4	328.4	318.0	314.2
137.5°	576.9	530.5	490.9	457.4	427.0	398.9	375.4	355.8	340.7	330.6	326.7
140°	570.1	529.7	493.9	461.9	433.8	406.4	383.0	364.1	349.0	339.6	335.0
142.5°	564.1	528.2	496.2	466.5	439.0	412.5	390.4	371.6	358.1	347.9	343.9
145°	556.0	525.9	497.7	471.4	445.9	421.5	399.8	383.9	369.8	361.3	358.4
147.5°	548.1	522.4	497.7	474.4	451.6	429.2	410.8	395.3	383.1	374.8	373.2
150°	542.8	519.3	497.7	475.1	455.3	433.8	416.8	403.6	391.3	383.9	383.0
152.5°	536.9	515.6	495.4	476.6	457.6	439.0	422.8	411.1	400.4	392.9	392.7
155°	527.8	509.0	492.9	477.0	461.9	445.9	432.8	422.4	413.0	407.4	407.4
157.5°	517.6	503.1	489.8	478.0	464.4	451.6	441.4	432.6	424.3	419.8	419.1
160°	510.9	498.6	488.3	478.0	466.7	455.3	445.9	439.3	431.9	428.1	428.1
162.5°	504.1	494.1	485.3	477.2	467.4	457.6	449.7	443.8	437.9	434.9	434.9
165°	494.8	487.4	480.8	475.1	468.5	461.0	454.4	450.6	445.9	444.0	445.0
167.5°	486.1	480.6	476.3	473.6	468.3	462.9	458.7	456.1	452.5	451.6	452.7
170°	480.8	476.1	473.3	471.4	467.6	462.9	461.0	459.1	456.3	455.3	457.2
172.5°	475.5	472.3	471.0	470.6	467.6	463.6	462.5	461.4	459.3	459.1	460.2
175°	469.5	467.6	467.6	468.5	466.7	464.8	463.8	463.8	461.9	462.9	463.8
177.5°	465.5	464.8	465.5	467.0	465.5	464.8	464.8	464.8	464.0	464.8	465.5
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	847.9	851.1	855.2	861.2	865.8	869.9	870.7	871.9	874.8	879.7	883.4
5°	853.5	861.8	875.1	888.1	902.2	913.7	924.5	932.2	939.3	954.5	966.8
7.5°	851.7	870.2	891.1	914.5	938.0	960.9	982.1	1001.2	1020.1	1042.2	1067.3
10°	850.6	872.2	900.3	930.3	963.2	995.3	1026.3	1050.6	1078.7	1104.0	1136.1
12.5°	845.1	876.3	909.9	948.2	988.6	1025.7	1066.5	1099.9	1132.1	1168.7	1206.0
15°	837.9	875.8	918.4	969.3	1030.7	1075.4	1117.3	1175.4	1215.1	1254.9	1308.3
17.5°	824.8	871.1	924.4	990.4	1041.7	1101.8	1164.8	1210.8	1264.2	1320.2	1368.6
20°	814.5	868.3	927.8	992.8	1058.1	1123.5	1184.5	1239.3	1294.6	1359.2	1398.9
22.5°	804.1	857.2	919.2	988.2	1058.4	1127.2	1196.3	1260.7	1322.9	1388.1	1438.8
25°	781.9	845.1	912.3	982.7	1052.0	1127.8	1210.1	1282.0	1358.9	1426.0	1474.0
27.5°	759.6	817.5	884.3	955.7	1032.7	1122.4	1219.2	1300.9	1377.9	1426.0	1441.1
30°	739.3	800.7	862.0	934.6	1018.0	1118.0	1221.0	1314.5	1377.6	1398.5	1383.0
32.5°	718.9	774.5	835.3	909.6	998.2	1107.4	1223.2	1306.4	1344.4	1328.4	1265.2
35°	682.7	732.8	791.7	866.1	967.9	1101.5	1213.7	1270.1	1260.7	1170.4	1051.2
37.5°	643.9	684.9	739.3	817.1	936.5	1078.0	1172.7	1181.0	1099.8	961.2	823.6
40°	613.3	650.2	706.2	787.4	912.3	1054.9	1131.4	1097.9	971.9	817.7	702.9
42.5°	583.6	614.6	668.5	756.2	889.2	1023.4	1069.9	996.7	851.4	705.6	601.2
45°	533.2	562.4	616.6	706.5	841.9	963.2	957.1	830.0	684.5	567.1	480.5
47.5°	485.4	511.0	561.8	653.6	786.4	872.9	815.5	680.3	556.9	462.8	401.0
50°	451.7	476.9	527.4	618.0	741.9	805.0	723.1	592.8	479.8	401.8	352.7
52.5°	419.2	443.9	490.2	578.4	688.2	725.9	637.9	517.1	422.9	355.6	313.4
55°	374.0	392.8	434.3	518.8	600.7	609.4	520.2	419.1	341.5	294.5	265.7
57.5°	327.9	344.0	385.0	452.3	509.8	505.3	420.8	333.4	281.1	246.2	225.3
60°	297.8	313.7	349.8	407.6	450.9	435.7	358.2	287.8	243.0	217.4	200.8
62.5°	269.8	282.2	316.0	358.2	389.4	372.2	306.1	247.9	212.4	190.8	177.6
65°	229.2	239.3	266.5	288.4	305.8	289.2	234.3	193.9	168.2	153.1	144.0
67.5°	190.7	197.1	214.2	222.2	234.4	216.2	176.2	149.1	134.5	121.8	115.5
70°	166.5	171.2	180.1	186.6	189.9	171.2	141.5	121.7	109.4	100.4	96.4
72.5°	142.1	146.3	148.1	153.4	151.7	134.1	113.8	98.0	89.2	83.0	77.9
75°	108.7	110.5	108.7	106.5	101.8	89.5	75.5	67.5	61.0	58.2	56.4
77.5°	79.2	78.6	76.2	72.8	64.8	57.0	49.5	46.8	44.0	42.4	41.8
80°	61.0	59.6	57.4	52.0	45.1	39.7	37.9	36.1	35.1	33.2	32.9
82.5°	45.4	44.6	40.9	36.4	31.6	29.0	27.5	26.9	25.7	24.9	24.8
85°	24.2	23.1	19.1	16.6	15.9	15.2	14.8	14.8	13.4	13.0	13.0
87.5°	8.6	7.2	7.4	7.0	7.4	7.4	8.2	8.2	8.5	8.6	8.2
90°	3.8	5.7	8.5	10.4	12.3	15.1	17.9	20.7	23.6	22.6	23.6
92.5°	17.3	25.3	32.5	40.4	54.4	79.0	119.5	159.2	144.7	109.1	79.2
95°	34.8	45.1	61.2	85.6	122.3	202.3	342.4	496.7	557.9	452.5	338.7
97.5°	55.5	63.6	77.5	101.6	141.3	217.7	375.8	633.0	864.6	925.0	844.3
100°	70.6	77.2	90.3	112.9	149.6	215.5	354.7	602.1	891.0	1076.3	1109.3
102.5°	87.1	92.9	105.4	125.7	159.4	218.5	336.6	556.9	842.1	1083.8	1197.3
105°	112.0	117.6	128.9	146.8	176.0	226.8	323.7	501.4	756.4	1026.4	1223.0
107.5°	137.1	142.6	153.7	170.5	197.6	242.1	322.7	466.1	680.8	926.0	1149.0
110°	155.2	159.9	170.3	186.2	212.6	255.0	326.5	452.5	637.9	862.7	1078.2



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	171.8	176.5	186.8	202.8	228.5	267.8	334.0	445.0	609.3	807.8	1008.1
115°	196.6	202.3	211.7	227.7	253.1	288.8	346.2	442.1	578.6	741.4	915.4
117.5°	221.1	225.8	234.4	252.3	275.9	311.2	362.4	443.8	560.5	701.3	848.3
120°	236.1	240.8	250.2	268.2	291.6	325.6	374.5	446.9	552.2	680.2	812.8
122.5°	250.4	255.1	265.3	282.5	307.5	340.5	385.8	452.1	547.0	662.9	785.0
125°	270.0	275.7	286.0	303.9	329.3	362.2	403.6	460.1	540.1	640.7	748.0
127.5°	286.5	293.5	304.1	323.9	349.2	381.1	418.3	469.1	536.7	621.1	715.6
130°	296.3	304.8	316.1	335.8	361.3	392.3	428.1	475.1	534.4	610.6	695.3
132.5°	304.6	313.9	327.4	347.1	371.8	402.1	437.2	479.7	533.7	600.8	676.5
135°	318.0	328.4	342.4	362.2	387.6	416.8	448.7	486.4	532.5	588.1	651.0
137.5°	330.6	340.7	355.8	375.4	398.9	427.0	457.4	490.9	530.5	576.9	627.9
140°	339.6	349.0	364.1	383.0	406.4	433.8	461.9	493.9	529.7	570.1	614.3
142.5°	347.9	358.1	371.6	390.4	412.5	439.0	466.5	496.2	528.2	564.1	601.5
145°	361.3	369.8	383.9	399.8	421.5	445.9	471.4	497.7	525.9	556.0	586.2
147.5°	374.8	383.1	395.3	410.8	429.2	451.6	474.4	497.7	522.4	548.1	573.5
150°	383.9	391.3	403.6	416.8	433.8	455.3	475.1	497.7	519.3	542.8	564.5
152.5°	392.9	400.4	411.1	422.8	439.0	457.6	476.6	495.4	515.6	536.9	556.2
155°	407.4	413.0	422.4	432.8	445.9	461.9	477.0	492.9	509.0	527.8	543.8
157.5°	419.8	424.3	432.6	441.4	451.6	464.4	478.0	489.8	503.1	517.6	530.7
160°	428.1	431.9	439.3	445.9	455.3	466.7	478.0	488.3	498.6	510.9	523.1
162.5°	434.9	437.9	443.8	449.7	457.6	467.4	477.2	485.3	494.1	504.1	514.1
165°	444.0	445.9	450.6	454.4	461.0	468.5	475.1	480.8	487.4	494.8	502.4
167.5°	451.6	452.5	456.1	458.7	462.9	468.3	473.6	476.3	480.6	486.1	492.2
170°	455.3	456.3	459.1	461.0	462.9	467.6	471.4	473.3	476.1	480.8	485.5
172.5°	459.1	459.3	461.4	462.5	463.6	467.6	470.6	471.0	472.3	475.5	479.5
175°	462.9	461.9	463.8	463.8	464.8	466.7	468.5	467.6	467.6	469.5	471.4
177.5°	464.8	464.0	464.8	464.8	464.8	465.5	467.0	465.5	464.8	465.5	466.3
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8	464.8



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	889.6	889.6	890.7	895.0	895.6	899.4	898.1
5°	977.6	984.5	987.0	997.9	1004.4	1007.2	1001.5
7.5°	1085.3	1104.7	1113.9	1125.2	1135.2	1138.3	1130.4
10°	1163.9	1184.1	1201.1	1211.5	1221.3	1227.8	1236.1
12.5°	1239.8	1264.7	1280.8	1295.6	1305.6	1313.9	1315.2
15°	1322.4	1359.9	1388.5	1409.4	1419.8	1425.3	1423.1
17.5°	1405.6	1440.4	1460.8	1482.1	1496.6	1497.3	1497.8
20°	1452.7	1486.7	1510.1	1526.0	1542.3	1541.5	1545.1
22.5°	1484.2	1510.9	1528.9	1540.4	1546.0	1543.2	1544.0
25°	1498.9	1506.8	1503.6	1485.2	1480.5	1463.6	1466.4
27.5°	1423.0	1385.4	1346.6	1296.6	1257.2	1225.7	1227.3
30°	1319.8	1253.4	1177.6	1114.1	1057.1	1041.1	1007.2
32.5°	1175.7	1076.1	987.3	928.1	879.1	865.8	836.2
35°	931.4	834.6	743.3	688.4	666.8	636.5	636.1
37.5°	724.0	638.8	590.5	549.3	527.7	509.3	507.6
40°	609.1	542.6	506.1	476.5	455.2	441.5	438.3
42.5°	528.8	475.0	440.8	422.5	406.1	399.1	393.8
45°	431.8	395.7	371.8	355.2	347.6	342.2	339.3
47.5°	361.2	337.0	320.7	309.7	303.5	297.8	299.4
50°	322.7	302.9	291.0	280.5	275.8	271.8	272.2
52.5°	291.8	274.0	264.4	256.8	251.0	248.2	246.8
55°	247.7	236.5	226.7	221.3	218.0	214.1	213.0
57.5°	211.2	202.6	194.6	188.5	187.8	183.9	184.4
60°	187.0	179.7	173.2	170.0	167.5	164.3	165.3
62.5°	167.1	161.0	155.0	152.4	149.9	147.5	148.0
65°	136.9	131.0	127.4	126.0	124.9	123.9	122.7
67.5°	109.1	105.5	103.2	100.1	97.9	97.6	96.4
70°	91.7	87.0	83.0	79.1	77.9	77.6	77.9
72.5°	73.5	70.5	69.5	67.5	67.3	66.4	67.0
75°	55.2	54.2	53.4	52.0	52.0	52.0	52.0
77.5°	40.7	40.1	39.7	39.3	39.0	38.5	38.5
80°	31.8	31.4	30.7	30.7	30.3	30.7	30.3
82.5°	23.9	23.9	23.2	23.2	22.8	22.6	22.8
85°	12.3	11.9	12.6	11.9	12.3	11.6	12.3
87.5°	8.4	8.6	8.7	8.5	8.4	9.1	8.4
90°	24.5	25.4	27.2	26.3	27.2	28.2	27.2
92.5°	62.9	55.5	50.6	48.9	46.1	47.0	45.3
95°	229.6	179.7	145.8	128.0	119.5	112.9	109.1
97.5°	676.3	554.9	442.3	373.0	330.6	305.2	297.1
100°	1033.0	922.9	789.4	694.4	625.7	589.0	589.9
102.5°	1194.9	1130.7	1046.0	972.0	917.7	887.0	865.3
105°	1317.2	1335.0	1310.6	1267.2	1231.5	1201.5	1196.7
107.5°	1301.7	1384.1	1417.7	1418.4	1406.4	1396.2	1387.5
110°	1251.3	1369.8	1435.7	1462.1	1469.6	1467.7	1465.8



TEST NUMBER: P332290-830

CATALOG NUMBER: S123RDIP-S560D1025U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1185.1	1317.9	1402.6	1450.8	1474.0	1481.2	1481.6
115°	1079.1	1217.4	1319.9	1390.5	1431.9	1450.8	1455.5
117.5°	989.6	1113.7	1217.8	1291.4	1338.8	1365.9	1372.2
120°	939.9	1052.8	1147.8	1222.1	1274.8	1297.4	1303.1
122.5°	900.0	1004.7	1092.9	1159.0	1206.4	1231.1	1238.3
125°	850.6	940.8	1016.1	1076.3	1117.7	1141.2	1147.8
127.5°	807.0	888.5	957.0	1010.6	1046.0	1067.2	1073.3
130°	780.0	856.1	920.1	970.0	1003.9	1023.6	1031.1
132.5°	754.3	825.3	886.3	933.1	967.0	984.5	989.8
135°	717.8	779.0	832.6	878.7	906.9	923.9	930.5
137.5°	682.7	735.4	781.8	820.6	849.2	863.5	867.8
140°	662.3	707.5	748.0	783.7	810.0	825.1	824.2
142.5°	642.8	681.9	717.1	747.6	770.9	784.5	783.5
145°	617.2	647.2	674.6	698.0	717.8	725.4	727.3
147.5°	598.1	622.5	641.9	659.7	673.1	680.2	681.0
150°	586.2	605.9	623.8	637.9	648.2	653.8	653.8
152.5°	574.9	592.4	607.2	618.3	627.9	631.3	631.3
155°	558.8	573.0	584.3	592.8	600.2	602.1	603.0
157.5°	543.2	554.1	563.0	570.3	576.0	577.5	577.3
160°	533.5	542.8	549.4	556.0	561.7	561.7	560.7
162.5°	522.9	531.6	537.4	541.8	546.6	546.6	545.6
165°	508.0	514.6	519.3	523.1	526.9	525.9	525.9
167.5°	496.5	500.3	503.7	505.4	508.0	507.1	507.1
170°	488.3	492.0	493.9	494.8	496.7	495.8	495.8
172.5°	481.5	484.6	485.7	485.9	487.8	486.1	485.3
175°	472.3	474.2	474.2	474.2	475.1	474.2	473.3
177.5°	467.0	467.8	467.8	467.0	467.8	466.3	466.3
180°	464.8	464.8	464.8	464.8	464.8	464.8	464.8

(END OF REPORT)