

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332270-830

Luminaire Tested: **S123RDIP-S560D365U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332270-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S560D365U830-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3468.1 lumens  
Efficiency: N/A  
Efficacy: 126.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	93	90	94	91	87	85	79	77	75	69	67	66	59	58	57	52
2	92	85	79	74	86	80	75	71	70	66	63	61	58	56	53	51	49	45
3	85	76	69	63	79	71	65	60	63	58	54	55	51	48	48	45	43	39
4	78	67	60	54	73	64	57	51	56	51	47	49	45	42	43	40	37	34
5	72	60	53	47	67	57	50	45	51	45	41	45	40	37	39	36	33	30
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	29	27
7	62	50	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26	24
8	57	45	38	32	54	43	36	31	38	33	29	34	30	26	30	27	24	22
9	53	41	34	29	50	39	33	28	35	30	26	32	27	24	28	24	22	20
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9077	9077	9077	9077
5°	10821	9116	8028	9116
10°	13511	9063	7252	9063
15°	15858	8971	6614	8971
20°	17699	8833	6071	8833
25°	17416	8687	5738	8687
30°	12519	8552	5393	8552
35°	8359	8377	5171	8377
40°	6159	8168	4942	8168
45°	5165	7798	4714	7798
50°	4558	7316	4401	7316
55°	3997	6762	3969	6762
60°	3559	6232	3638	6232
65°	3125	5662	3385	5662
70°	2452	5158	3091	5158
75°	2163	4504	2824	4504
80°	1878	3825	2777	3825
85°	1519	3075	2939	3075



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.9	2.4
10°-20°	259.1	7.5
20°-30°	407.0	11.7
30°-40°	424.7	12.2
40°-50°	363.4	10.5
50°-60°	277.0	8.0
60°-70°	177.6	5.1
70°-80°	85.4	2.5
80°-90°	23.9	0.7
90°-100°	16.3	0.5
100°-110°	77.7	2.2
110°-120°	186.6	5.4
120°-130°	237.6	6.9
130°-140°	253.9	7.3
140°-150°	237.4	6.8
150°-160°	191.5	5.5
160°-170°	123.6	3.6
170°-180°	42.6	1.2
0°-30°	749.1	21.6
0°-40°	1173.7	33.8
0°-60°	1814.2	52.3
0°-90°	2101.0	60.6
90°-120°	280.6	8.1
90°-150°	1009.4	29.1
90°-180°	1367.0	39.4
0°-180°	3468.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	843	843	843	843	843	
5°	1002	844	743	844	1002	103
15°	1423	805	594	805	1423	404
25°	1466	731	483	731	1466	630
35°	636	638	394	638	636	417
45°	339	512	310	512	339	267
55°	213	360	212	360	213	193
65°	123	222	133	222	123	121
75°	52	108	68	108	52	56
85°	12	25	24	25	12	14
90°	10	0	10	0	10	5
95°	13	20	13	20	13	11
105°	15	99	15	99	15	33
115°	196	186	196	186	196	181
125°	268	262	268	262	268	239
135°	330	327	330	327	330	255
145°	381	377	381	377	381	238
155°	415	415	415	415	415	191
165°	437	438	437	438	437	123
175°	447	448	447	448	447	43
180°	448	448	448	448	448	



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	898.1	899.4	895.6	895.0	890.7	889.6	889.6	883.4	879.7	874.8	871.9
5°	1001.5	1007.2	1004.4	997.9	987.0	984.5	977.6	966.8	954.5	939.3	932.2
7.5°	1130.4	1138.3	1135.2	1125.2	1113.9	1104.7	1085.3	1067.3	1042.2	1020.1	1001.2
10°	1236.1	1227.8	1221.3	1211.5	1201.1	1184.1	1163.9	1136.1	1104.0	1078.7	1050.6
12.5°	1315.2	1313.9	1305.6	1295.6	1280.8	1264.7	1239.8	1206.0	1168.7	1132.1	1099.9
15°	1423.1	1425.3	1419.8	1409.4	1388.5	1359.9	1322.4	1308.3	1254.9	1215.1	1175.4
17.5°	1497.8	1497.3	1496.6	1482.1	1460.8	1440.4	1405.6	1368.6	1320.2	1264.2	1210.8
20°	1545.1	1541.5	1542.3	1526.0	1510.1	1486.7	1452.7	1398.9	1359.2	1294.6	1239.3
22.5°	1544.0	1543.2	1546.0	1540.4	1528.9	1510.9	1484.2	1438.8	1388.1	1322.9	1260.7
25°	1466.4	1463.6	1480.5	1485.2	1503.6	1506.8	1498.9	1474.0	1426.0	1358.9	1282.0
27.5°	1227.3	1225.7	1257.2	1296.6	1346.6	1385.4	1423.0	1441.1	1426.0	1377.9	1300.9
30°	1007.2	1041.1	1057.1	1114.1	1177.6	1253.4	1319.8	1383.0	1398.5	1377.6	1314.5
32.5°	836.2	865.8	879.1	928.1	987.3	1076.1	1175.7	1265.2	1328.4	1344.4	1306.4
35°	636.1	636.5	666.8	688.4	743.3	834.6	931.4	1051.2	1170.4	1260.7	1270.1
37.5°	507.6	509.3	527.7	549.3	590.5	638.8	724.0	823.6	961.2	1099.8	1181.0
40°	438.3	441.5	455.2	476.5	506.1	542.6	609.1	702.9	817.7	971.9	1097.9
42.5°	393.8	399.1	406.1	422.5	440.8	475.0	528.8	601.2	705.6	851.4	996.7
45°	339.3	342.2	347.6	355.2	371.8	395.7	431.8	480.5	567.1	684.5	830.0
47.5°	299.4	297.8	303.5	309.7	320.7	337.0	361.2	401.0	462.8	556.9	680.3
50°	272.2	271.8	275.8	280.5	291.0	302.9	322.7	352.7	401.8	479.8	592.8
52.5°	246.8	248.2	251.0	256.8	264.4	274.0	291.8	313.4	355.6	422.9	517.1
55°	213.0	214.1	218.0	221.3	226.7	236.5	247.7	265.7	294.5	341.5	419.1
57.5°	184.4	183.9	187.8	188.5	194.6	202.6	211.2	225.3	246.2	281.1	333.4
60°	165.3	164.3	167.5	170.0	173.2	179.7	187.0	200.8	217.4	243.0	287.8
62.5°	148.0	147.5	149.9	152.4	155.0	161.0	167.1	177.6	190.8	212.4	247.9
65°	122.7	123.9	124.9	126.0	127.4	131.0	136.9	144.0	153.1	168.2	193.9
67.5°	96.4	97.6	97.9	100.1	103.2	105.5	109.1	115.5	121.8	134.5	149.1
70°	77.9	77.6	77.9	79.1	83.0	87.0	91.7	96.4	100.4	109.4	121.7
72.5°	67.0	66.4	67.3	67.5	69.5	70.5	73.5	77.9	83.0	89.2	98.0
75°	52.0	52.0	52.0	52.0	53.4	54.2	55.2	56.4	58.2	61.0	67.5
77.5°	38.5	38.5	39.0	39.3	39.7	40.1	40.7	41.8	42.4	44.0	46.8
80°	30.3	30.7	30.3	30.7	30.7	31.4	31.8	32.9	33.2	35.1	36.1
82.5°	22.8	22.6	22.8	23.2	23.2	23.9	23.9	24.8	24.9	25.7	26.9
85°	12.3	11.6	12.3	11.9	12.6	11.9	12.3	13.0	13.0	13.4	14.8
87.5°	4.9	5.5	4.8	5.1	5.1	5.3	5.3	5.2	5.7	5.4	5.5
90°	10.0	9.8	9.7	9.5	9.4	9.1	8.9	8.6	8.3	8.0	7.1
92.5°	11.0	10.9	10.8	10.7	10.7	10.5	10.0	9.5	9.0	8.5	7.8
95°	12.6	12.6	12.6	12.6	12.6	12.4	11.9	11.4	10.8	10.4	9.5
97.5°	13.8	13.7	13.6	13.5	13.4	13.1	12.5	11.9	11.3	10.7	16.0
100°	13.9	13.9	13.9	13.8	13.7	13.4	12.7	12.2	11.6	11.0	22.5
102.5°	14.2	14.1	13.9	13.9	13.8	14.6	16.4	18.3	20.1	22.0	34.5
105°	14.6	14.5	14.3	14.2	14.0	20.5	33.6	46.8	59.9	73.0	79.6
107.5°	46.0	55.9	65.8	75.7	85.5	95.3	104.9	114.5	124.0	133.7	132.6
110°	91.6	102.2	112.7	123.4	133.9	140.4	142.9	145.3	147.8	150.2	149.4



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	157.1	159.4	161.6	163.8	166.1	167.2	167.1	167.1	167.0	167.0	166.2
115°	195.9	195.6	195.3	194.9	194.6	194.2	193.4	192.7	191.9	191.1	190.5
117.5°	217.5	217.5	217.4	217.4	217.4	217.0	216.4	215.8	215.2	214.6	214.3
120°	232.5	232.5	232.5	232.5	232.5	232.1	231.6	231.0	230.5	229.8	229.6
122.5°	247.1	247.0	247.0	246.9	246.9	246.7	246.3	245.8	245.4	245.0	244.7
125°	267.8	267.7	267.5	267.3	267.2	267.0	266.9	266.7	266.6	266.5	266.2
127.5°	287.7	287.8	287.9	288.0	288.2	288.2	287.9	287.7	287.5	287.2	286.9
130°	300.4	300.6	300.8	300.9	301.0	301.0	300.7	300.4	300.0	299.7	299.4
132.5°	312.2	312.4	312.5	312.7	313.0	312.9	312.6	312.4	312.1	311.8	311.5
135°	330.1	330.3	330.5	330.7	330.9	330.9	330.7	330.5	330.3	330.1	329.8
137.5°	346.9	347.0	347.2	347.3	347.5	347.4	347.0	346.7	346.4	346.0	345.8
140°	357.0	357.2	357.3	357.5	357.6	357.6	357.2	356.9	356.7	356.4	356.2
142.5°	366.4	366.6	366.7	367.0	367.2	367.2	366.9	366.7	366.5	366.3	366.0
145°	380.7	380.7	380.7	380.7	380.7	380.6	380.5	380.3	380.2	380.0	379.8
147.5°	391.3	391.7	392.0	392.4	392.8	392.9	392.7	392.5	392.4	392.2	392.1
150°	399.4	399.5	399.8	400.0	400.2	400.3	400.1	400.0	399.8	399.6	399.5
152.5°	405.8	406.0	406.4	406.8	407.1	407.2	406.9	406.6	406.3	406.0	406.0
155°	414.6	415.1	415.6	416.0	416.4	416.5	416.1	415.8	415.4	415.0	414.9
157.5°	422.2	422.7	423.4	424.0	424.5	424.6	424.1	423.7	423.2	422.8	422.8
160°	427.0	427.5	428.0	428.6	429.0	429.1	428.7	428.2	427.7	427.3	427.4
162.5°	431.5	432.0	432.4	432.9	433.4	433.3	432.8	432.3	431.8	431.3	431.4
165°	437.0	437.5	438.0	438.6	439.0	439.0	438.5	437.8	437.2	436.7	436.7
167.5°	440.9	441.5	442.1	442.7	443.3	443.3	442.7	442.1	441.5	440.9	440.9
170°	443.3	443.9	444.5	445.1	445.6	445.6	445.1	444.5	443.9	443.3	443.3
172.5°	444.6	445.3	445.9	446.6	447.2	447.2	446.7	446.1	445.5	444.9	444.9
175°	446.7	447.2	447.8	448.5	449.0	449.0	448.6	448.0	447.5	447.0	446.9
177.5°	447.2	447.8	448.5	449.0	449.6	449.7	449.2	448.7	448.3	447.8	447.7
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	870.7	869.9	865.8	861.2	855.2	851.1	847.9	846.2	841.0	834.6	830.3
5°	924.5	913.7	902.2	888.1	875.1	861.8	853.5	843.7	831.8	818.4	809.0
7.5°	982.1	960.9	938.0	914.5	891.1	870.2	851.7	835.8	816.9	797.8	784.3
10°	1026.3	995.3	963.2	930.3	900.3	872.2	850.6	829.2	806.5	784.5	767.9
12.5°	1066.5	1025.7	988.6	948.2	909.9	876.3	845.1	820.0	792.7	769.2	750.3
15°	1117.3	1075.4	1030.7	969.3	918.4	875.8	837.9	805.0	771.8	743.0	724.5
17.5°	1164.8	1101.8	1041.7	990.4	924.4	871.1	824.8	785.5	749.1	718.5	695.8
20°	1184.5	1123.5	1058.1	992.8	927.8	868.3	814.5	771.1	733.2	698.5	677.6
22.5°	1196.3	1127.2	1058.4	988.2	919.2	857.2	804.1	756.4	715.3	682.4	656.6
25°	1210.1	1127.8	1052.0	982.7	912.3	845.1	781.9	731.4	687.0	652.0	624.5
27.5°	1219.2	1122.4	1032.7	955.7	884.3	817.5	759.6	706.0	660.9	623.9	594.5
30°	1221.0	1118.0	1018.0	934.6	862.0	800.7	739.3	688.1	640.5	601.1	573.6
32.5°	1223.2	1107.4	998.2	909.6	835.3	774.5	718.9	669.9	621.0	582.3	554.3
35°	1213.7	1101.5	967.9	866.1	791.7	732.8	682.7	637.5	589.6	552.0	523.5
37.5°	1172.7	1078.0	936.5	817.1	739.3	684.9	643.9	604.6	560.6	520.1	493.2
40°	1131.4	1054.9	912.3	787.4	706.2	650.2	613.3	581.3	538.7	500.7	471.8
42.5°	1069.9	1023.4	889.2	756.2	668.5	614.6	583.6	553.5	516.1	477.6	450.4
45°	957.1	963.2	841.9	706.5	616.6	562.4	533.2	512.3	479.1	447.3	419.5
47.5°	815.5	872.9	786.4	653.6	561.8	511.0	485.4	467.1	444.8	413.6	388.2
50°	723.1	805.0	741.9	618.0	527.4	476.9	451.7	436.9	417.4	392.8	368.6
52.5°	637.9	725.9	688.2	578.4	490.2	443.9	419.2	407.1	391.6	368.5	346.7
55°	520.2	609.4	600.7	518.8	434.3	392.8	374.0	360.3	349.8	332.5	315.2
57.5°	420.8	505.3	509.8	452.3	385.0	344.0	327.9	317.5	310.7	297.7	281.6
60°	358.2	435.7	450.9	407.6	349.8	313.7	297.8	289.5	284.1	273.6	261.4
62.5°	306.1	372.2	389.4	358.2	316.0	282.2	269.8	261.8	258.2	249.1	238.3
65°	234.3	289.2	305.8	288.4	266.5	239.3	229.2	222.3	219.1	214.1	206.1
67.5°	176.2	216.2	234.4	222.2	214.2	197.1	190.7	187.0	184.1	180.7	174.0
70°	141.5	171.2	189.9	186.6	180.1	171.2	166.5	163.9	161.0	158.2	152.3
72.5°	113.8	134.1	151.7	153.4	148.1	146.3	142.1	141.1	139.3	135.9	132.7
75°	75.5	89.5	101.8	106.5	108.7	110.5	108.7	108.3	107.9	105.1	103.2
77.5°	49.5	57.0	64.8	72.8	76.2	78.6	79.2	80.5	79.6	78.0	77.2
80°	37.9	39.7	45.1	52.0	57.4	59.6	61.0	61.7	61.4	61.0	59.6
82.5°	27.5	29.0	31.6	36.4	40.9	44.6	45.4	45.2	46.1	46.3	45.1
85°	14.8	15.2	15.9	16.6	19.1	23.1	24.2	24.9	25.6	25.6	23.5
87.5°	5.8	5.4	5.7	5.6	6.3	6.4	8.0	9.3	9.7	8.8	8.9
90°	6.0	5.1	4.1	3.3	2.5	1.8	1.0	0.4	1.0	1.8	2.5
92.5°	7.1	6.3	5.7	5.4	5.6	5.7	6.0	6.2	6.0	5.7	5.6
95°	8.7	7.9	7.1	8.2	11.2	14.2	17.2	20.4	17.2	14.2	11.2
97.5°	21.4	26.7	32.0	35.3	36.8	38.1	39.5	40.8	39.5	38.1	36.8
100°	34.1	45.6	57.2	62.2	60.7	59.3	57.8	56.3	57.8	59.3	60.7
102.5°	47.1	59.8	72.4	78.1	77.1	76.0	74.9	73.9	74.9	76.0	77.1
105°	86.2	92.9	99.6	102.5	101.7	100.9	100.1	99.2	100.1	100.9	101.7
107.5°	131.6	130.5	129.5	128.7	128.0	127.3	126.7	126.0	126.7	127.3	128.0
110°	148.5	147.8	146.9	146.3	145.6	145.1	144.5	143.9	144.5	145.1	145.6





TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	165.4	164.6	163.7	163.1	162.5	162.0	161.5	160.9	161.5	162.0	162.5
115°	189.8	189.2	188.5	187.9	187.5	187.1	186.6	186.2	186.6	187.1	187.5
117.5°	214.0	213.6	213.3	212.8	212.3	211.7	211.2	210.7	211.2	211.7	212.3
120°	229.4	229.1	228.9	228.5	227.8	227.2	226.5	225.8	226.5	227.2	227.8
122.5°	244.4	244.1	243.8	243.5	242.9	242.3	241.9	241.3	241.9	242.3	242.9
125°	265.9	265.6	265.2	264.9	264.2	263.6	263.1	262.5	263.1	263.6	264.2
127.5°	286.5	286.2	285.8	285.3	284.7	284.2	283.6	283.0	283.6	284.2	284.7
130°	299.2	298.9	298.6	298.1	297.6	296.9	296.3	295.8	296.3	296.9	297.6
132.5°	311.3	311.0	310.8	310.4	309.8	309.2	308.6	308.0	308.6	309.2	309.8
135°	329.5	329.1	328.9	328.5	328.1	327.6	327.2	326.8	327.2	327.6	328.1
137.5°	345.6	345.5	345.3	345.0	344.4	343.8	343.3	342.7	343.3	343.8	344.4
140°	355.9	355.7	355.5	355.2	354.7	354.3	353.8	353.4	353.8	354.3	354.7
142.5°	365.8	365.6	365.3	365.0	364.6	364.1	363.7	363.3	363.7	364.1	364.6
145°	379.8	379.6	379.5	379.1	378.6	378.1	377.6	377.0	377.6	378.1	378.6
147.5°	391.9	391.8	391.6	391.3	391.1	390.7	390.4	390.0	390.4	390.7	391.1
150°	399.4	399.3	399.1	398.9	398.7	398.4	398.2	398.0	398.2	398.4	398.7
152.5°	405.9	405.8	405.8	405.6	405.5	405.4	405.3	405.2	405.3	405.4	405.5
155°	414.8	414.8	414.7	414.7	414.9	415.0	415.2	415.4	415.2	415.0	414.9
157.5°	422.9	423.0	423.1	423.1	423.1	423.2	423.2	423.2	423.2	423.2	423.1
160°	427.4	427.5	427.6	427.7	427.7	427.8	427.9	428.0	427.9	427.8	427.7
162.5°	431.5	431.5	431.6	431.8	432.0	432.2	432.3	432.5	432.3	432.2	432.0
165°	436.8	436.9	437.0	437.1	437.3	437.5	437.7	438.0	437.7	437.5	437.3
167.5°	440.9	440.9	440.9	441.0	441.4	441.7	442.0	442.2	442.0	441.7	441.4
170°	443.3	443.3	443.3	443.5	443.7	444.0	444.3	444.6	444.3	444.0	443.7
172.5°	444.8	444.7	444.7	444.8	445.2	445.5	445.9	446.2	445.9	445.5	445.2
175°	446.9	446.8	446.7	446.9	447.2	447.5	447.9	448.3	447.9	447.5	447.2
177.5°	447.6	447.6	447.5	447.6	448.0	448.3	448.6	448.8	448.6	448.3	448.0
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	828.9	825.1	822.6	816.7	813.0	809.0	804.9	807.5	807.2	806.9	806.9
5°	801.1	792.8	785.2	775.4	769.3	761.8	755.9	755.3	756.7	751.6	748.8
7.5°	773.5	762.1	751.4	740.6	729.2	720.1	714.4	711.8	708.1	705.0	701.7
10°	754.1	740.8	730.3	717.0	704.7	693.9	687.0	682.3	679.8	677.2	672.6
12.5°	734.2	721.1	707.8	692.7	681.0	668.5	663.4	658.1	653.2	650.4	643.9
15°	705.0	688.1	674.0	658.1	645.2	632.8	625.7	615.2	613.7	610.1	603.6
17.5°	675.8	657.4	638.0	626.2	611.5	598.8	587.8	584.3	573.9	570.0	564.4
20°	652.7	635.7	620.9	605.4	584.1	572.2	563.5	558.8	550.5	545.4	541.9
22.5°	632.8	615.5	598.4	580.3	562.7	549.4	543.0	535.7	531.2	524.1	520.2
25°	604.4	585.6	565.0	545.4	532.8	522.7	512.6	506.1	499.6	496.3	489.2
27.5°	571.3	551.7	532.4	517.6	502.1	492.1	483.0	477.2	469.4	463.9	460.0
30°	553.1	530.0	513.4	500.0	480.1	470.8	463.9	456.7	450.9	445.2	441.1
32.5°	532.0	510.9	495.1	478.6	463.4	453.2	444.2	437.9	433.0	427.5	423.6
35°	498.9	481.3	465.0	448.4	437.2	426.7	416.2	410.9	406.1	401.1	397.5
37.5°	469.0	452.5	437.1	421.3	407.5	398.9	390.5	386.3	380.0	376.6	373.0
40°	450.5	434.3	417.7	402.6	388.0	381.6	374.0	367.9	362.1	359.6	355.6
42.5°	430.4	414.1	400.1	383.7	371.9	363.1	356.1	349.4	345.1	341.4	339.1
45°	400.4	385.9	372.2	356.0	344.8	337.1	329.2	323.1	319.1	316.6	312.6
47.5°	371.3	356.8	342.9	328.8	317.9	309.2	301.3	297.0	291.8	288.7	286.0
50°	350.2	337.1	322.3	309.3	298.6	289.9	283.4	278.0	273.2	269.3	267.5
52.5°	330.8	317.0	304.2	292.1	280.7	270.8	264.9	259.2	255.7	251.1	249.0
55°	298.9	285.6	274.8	262.8	251.7	243.4	236.1	231.0	227.4	222.3	219.5
57.5°	268.9	256.9	244.0	233.8	222.2	215.2	209.2	202.3	197.9	194.0	191.1
60°	248.7	235.0	223.9	214.1	204.0	194.9	189.5	184.1	179.5	175.4	173.0
62.5°	227.6	215.7	205.1	194.4	185.2	177.3	171.1	166.5	162.4	159.9	157.3
65°	195.3	186.0	175.1	166.5	157.8	152.0	146.9	143.0	140.1	138.3	136.1
67.5°	165.6	156.5	147.0	138.5	132.7	128.3	125.0	121.6	120.2	117.8	116.4
70°	146.2	136.9	128.6	122.1	116.2	113.0	110.8	108.3	106.9	104.0	102.5
72.5°	125.2	118.4	112.4	107.0	102.4	99.4	96.7	93.6	91.2	88.1	86.6
75°	98.6	92.5	87.8	84.1	81.2	77.3	73.3	70.0	69.0	67.9	67.5
77.5°	73.0	69.1	65.7	62.7	59.1	56.2	55.3	54.6	54.4	53.8	53.8
80°	57.4	53.8	51.3	47.7	45.5	45.5	45.5	44.8	45.1	45.1	45.1
82.5°	42.7	39.3	38.0	36.7	36.3	36.6	36.6	36.7	36.5	37.0	36.8
85°	22.1	22.3	23.1	22.7	23.1	23.1	23.8	23.5	23.8	23.1	23.8
87.5°	8.8	9.8	10.3	10.7	11.2	11.1	11.5	11.5	11.9	12.0	12.0
90°	3.3	4.1	5.1	6.0	7.1	8.0	8.3	8.6	8.9	9.1	9.4
92.5°	5.4	5.7	6.3	7.1	7.8	8.5	9.0	9.5	10.0	10.5	10.7
95°	8.2	7.1	7.9	8.7	9.5	10.4	10.8	11.4	11.9	12.4	12.6
97.5°	35.3	32.0	26.7	21.4	16.0	10.7	11.3	11.9	12.5	13.1	13.4
100°	62.2	57.2	45.6	34.1	22.5	11.0	11.6	12.2	12.7	13.4	13.7
102.5°	78.1	72.4	59.8	47.1	34.5	22.0	20.1	18.3	16.4	14.6	13.8
105°	102.5	99.6	92.9	86.2	79.6	73.0	59.9	46.8	33.6	20.5	14.0
107.5°	128.7	129.5	130.5	131.6	132.6	133.7	124.0	114.5	104.9	95.3	85.5
110°	146.3	146.9	147.8	148.5	149.4	150.2	147.8	145.3	142.9	140.4	133.9



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	163.1	163.7	164.6	165.4	166.2	167.0	167.0	167.1	167.1	167.2	166.1
115°	187.9	188.5	189.2	189.8	190.5	191.1	191.9	192.7	193.4	194.2	194.6
117.5°	212.8	213.3	213.6	214.0	214.3	214.6	215.2	215.8	216.4	217.0	217.4
120°	228.5	228.9	229.1	229.4	229.6	229.8	230.5	231.0	231.6	232.1	232.5
122.5°	243.5	243.8	244.1	244.4	244.7	245.0	245.4	245.8	246.3	246.7	246.9
125°	264.9	265.2	265.6	265.9	266.2	266.5	266.6	266.7	266.9	267.0	267.2
127.5°	285.3	285.8	286.2	286.5	286.9	287.2	287.5	287.7	287.9	288.2	288.2
130°	298.1	298.6	298.9	299.2	299.4	299.7	300.0	300.4	300.7	301.0	301.0
132.5°	310.4	310.8	311.0	311.3	311.5	311.8	312.1	312.4	312.6	312.9	313.0
135°	328.5	328.9	329.1	329.5	329.8	330.1	330.3	330.5	330.7	330.9	330.9
137.5°	345.0	345.3	345.5	345.6	345.8	346.0	346.4	346.7	347.0	347.4	347.5
140°	355.2	355.5	355.7	355.9	356.2	356.4	356.7	356.9	357.2	357.6	357.6
142.5°	365.0	365.3	365.6	365.8	366.0	366.3	366.5	366.7	366.9	367.2	367.2
145°	379.1	379.5	379.6	379.8	379.8	380.0	380.2	380.3	380.5	380.6	380.7
147.5°	391.3	391.6	391.8	391.9	392.1	392.2	392.4	392.5	392.7	392.9	392.8
150°	398.9	399.1	399.3	399.4	399.5	399.6	399.8	400.0	400.1	400.3	400.2
152.5°	405.6	405.8	405.8	405.9	406.0	406.0	406.3	406.6	406.9	407.2	407.1
155°	414.7	414.7	414.8	414.8	414.9	415.0	415.4	415.8	416.1	416.5	416.4
157.5°	423.1	423.1	423.0	422.9	422.8	422.8	423.2	423.7	424.1	424.6	424.5
160°	427.7	427.6	427.5	427.4	427.4	427.3	427.7	428.2	428.7	429.1	429.0
162.5°	431.8	431.6	431.5	431.5	431.4	431.3	431.8	432.3	432.8	433.3	433.4
165°	437.1	437.0	436.9	436.8	436.7	436.7	437.2	437.8	438.5	439.0	439.0
167.5°	441.0	440.9	440.9	440.9	440.9	440.9	441.5	442.1	442.7	443.3	443.3
170°	443.5	443.3	443.3	443.3	443.3	443.3	443.9	444.5	445.1	445.6	445.6
172.5°	444.8	444.7	444.7	444.8	444.9	444.9	445.5	446.1	446.7	447.2	447.2
175°	446.9	446.7	446.8	446.9	446.9	447.0	447.5	448.0	448.6	449.0	449.0
177.5°	447.6	447.5	447.6	447.6	447.7	447.8	448.3	448.7	449.2	449.7	449.6
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	803.4	803.1	803.4	802.3	803.4	803.1	803.4	806.9	806.9	807.2	807.5
5°	747.6	747.2	746.2	743.0	746.2	747.2	747.6	748.8	751.6	756.7	755.3
7.5°	698.9	698.4	695.2	695.3	695.2	698.4	698.9	701.7	705.0	708.1	711.8
10°	670.1	670.4	666.1	663.5	666.1	670.4	670.1	672.6	677.2	679.8	682.3
12.5°	642.1	640.4	636.9	634.0	636.9	640.4	642.1	643.9	650.4	653.2	658.1
15°	605.0	601.4	592.8	593.5	592.8	601.4	605.0	603.6	610.1	613.7	615.2
17.5°	561.5	558.8	558.7	553.6	558.7	558.8	561.5	564.4	570.0	573.9	584.3
20°	536.1	534.3	535.0	530.0	535.0	534.3	536.1	541.9	545.4	550.5	558.8
22.5°	516.1	514.3	511.3	509.7	511.3	514.3	516.1	520.2	524.1	531.2	535.7
25°	487.0	484.1	481.3	483.1	481.3	484.1	487.0	489.2	496.3	499.6	506.1
27.5°	457.8	455.6	452.8	452.4	452.8	455.6	457.8	460.0	463.9	469.4	477.2
30°	439.3	437.2	435.7	433.9	435.7	437.2	439.3	441.1	445.2	450.9	456.7
32.5°	420.6	420.2	417.5	417.2	417.5	420.2	420.6	423.6	427.5	433.0	437.9
35°	396.1	393.9	393.1	393.5	393.1	393.9	396.1	397.5	401.1	406.1	410.9
37.5°	372.7	369.9	368.5	367.2	368.5	369.9	372.7	373.0	376.6	380.0	386.3
40°	356.0	353.1	352.3	351.7	352.3	353.1	356.0	355.6	359.6	362.1	367.9
42.5°	337.1	336.0	335.6	334.3	335.6	336.0	337.1	339.1	341.4	345.1	349.4
45°	311.5	311.2	309.1	309.7	309.1	311.2	311.5	312.6	316.6	319.1	323.1
47.5°	284.6	283.0	281.4	282.5	281.4	283.0	284.6	286.0	288.7	291.8	297.0
50°	266.1	265.3	262.1	262.8	262.1	265.3	266.1	267.5	269.3	273.2	278.0
52.5°	247.6	244.9	243.6	243.2	243.6	244.9	247.6	249.0	251.1	255.7	259.2
55°	217.0	213.7	212.3	211.5	212.3	213.7	217.0	219.5	222.3	227.4	231.0
57.5°	186.9	186.1	184.9	185.7	184.9	186.1	186.9	191.1	194.0	197.9	202.3
60°	169.3	169.3	169.3	169.0	169.3	169.3	169.3	173.0	175.4	179.5	184.1
62.5°	155.7	154.9	154.6	155.0	154.6	154.9	155.7	157.3	159.9	162.4	166.5
65°	135.0	134.7	133.2	132.9	133.2	134.7	135.0	136.1	138.3	140.1	143.0
67.5°	115.5	114.1	113.8	113.2	113.8	114.1	115.5	116.4	117.8	120.2	121.6
70°	100.8	100.0	97.8	98.2	97.8	100.0	100.8	102.5	104.0	106.9	108.3
72.5°	84.8	84.1	83.7	83.1	83.7	84.1	84.8	86.6	88.1	91.2	93.6
75°	67.1	66.8	66.4	67.9	66.4	66.8	67.1	67.5	67.9	69.0	70.0
77.5°	53.8	53.8	54.0	53.4	54.0	53.8	53.8	53.8	53.8	54.4	54.6
80°	45.1	45.1	44.8	44.8	44.8	45.1	45.1	45.1	45.1	45.1	44.8
82.5°	36.2	36.5	36.7	36.1	36.7	36.5	36.2	36.8	37.0	36.5	36.7
85°	23.8	23.5	24.2	23.8	24.2	23.5	23.8	23.8	23.1	23.8	23.5
87.5°	12.6	12.1	12.1	12.4	12.1	12.1	12.6	12.0	12.0	11.9	11.5
90°	9.5	9.7	9.8	10.0	9.8	9.7	9.5	9.4	9.1	8.9	8.6
92.5°	10.7	10.8	10.9	11.0	10.9	10.8	10.7	10.7	10.5	10.0	9.5
95°	12.6	12.6	12.6	12.6	12.6	12.6	12.6	12.6	12.4	11.9	11.4
97.5°	13.5	13.6	13.7	13.8	13.7	13.6	13.5	13.4	13.1	12.5	11.9
100°	13.8	13.9	13.9	13.9	13.9	13.9	13.8	13.7	13.4	12.7	12.2
102.5°	13.9	13.9	14.1	14.2	14.1	13.9	13.9	13.8	14.6	16.4	18.3
105°	14.2	14.3	14.5	14.6	14.5	14.3	14.2	14.0	20.5	33.6	46.8
107.5°	75.7	65.8	55.9	46.0	55.9	65.8	75.7	85.5	95.3	104.9	114.5
110°	123.4	112.7	102.2	91.6	102.2	112.7	123.4	133.9	140.4	142.9	145.3



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	163.8	161.6	159.4	157.1	159.4	161.6	163.8	166.1	167.2	167.1	167.1
115°	194.9	195.3	195.6	195.9	195.6	195.3	194.9	194.6	194.2	193.4	192.7
117.5°	217.4	217.4	217.5	217.5	217.5	217.4	217.4	217.4	217.0	216.4	215.8
120°	232.5	232.5	232.5	232.5	232.5	232.5	232.5	232.5	232.1	231.6	231.0
122.5°	246.9	247.0	247.0	247.1	247.0	247.0	246.9	246.9	246.7	246.3	245.8
125°	267.3	267.5	267.7	267.8	267.7	267.5	267.3	267.2	267.0	266.9	266.7
127.5°	288.0	287.9	287.8	287.7	287.8	287.9	288.0	288.2	288.2	287.9	287.7
130°	300.9	300.8	300.6	300.4	300.6	300.8	300.9	301.0	301.0	300.7	300.4
132.5°	312.7	312.5	312.4	312.2	312.4	312.5	312.7	313.0	312.9	312.6	312.4
135°	330.7	330.5	330.3	330.1	330.3	330.5	330.7	330.9	330.9	330.7	330.5
137.5°	347.3	347.2	347.0	346.9	347.0	347.2	347.3	347.5	347.4	347.0	346.7
140°	357.5	357.3	357.2	357.0	357.2	357.3	357.5	357.6	357.6	357.2	356.9
142.5°	367.0	366.7	366.6	366.4	366.6	366.7	367.0	367.2	367.2	366.9	366.7
145°	380.7	380.7	380.7	380.7	380.7	380.7	380.7	380.7	380.6	380.5	380.3
147.5°	392.4	392.0	391.7	391.3	391.7	392.0	392.4	392.8	392.9	392.7	392.5
150°	400.0	399.8	399.5	399.4	399.5	399.8	400.0	400.2	400.3	400.1	400.0
152.5°	406.8	406.4	406.0	405.8	406.0	406.4	406.8	407.1	407.2	406.9	406.6
155°	416.0	415.6	415.1	414.6	415.1	415.6	416.0	416.4	416.5	416.1	415.8
157.5°	424.0	423.4	422.7	422.2	422.7	423.4	424.0	424.5	424.6	424.1	423.7
160°	428.6	428.0	427.5	427.0	427.5	428.0	428.6	429.0	429.1	428.7	428.2
162.5°	432.9	432.4	432.0	431.5	432.0	432.4	432.9	433.4	433.3	432.8	432.3
165°	438.6	438.0	437.5	437.0	437.5	438.0	438.6	439.0	439.0	438.5	437.8
167.5°	442.7	442.1	441.5	440.9	441.5	442.1	442.7	443.3	443.3	442.7	442.1
170°	445.1	444.5	443.9	443.3	443.9	444.5	445.1	445.6	445.6	445.1	444.5
172.5°	446.6	445.9	445.3	444.6	445.3	445.9	446.6	447.2	447.2	446.7	446.1
175°	448.5	447.8	447.2	446.7	447.2	447.8	448.5	449.0	449.0	448.6	448.0
177.5°	449.0	448.5	447.8	447.2	447.8	448.5	449.0	449.6	449.7	449.2	448.7
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	804.9	809.0	813.0	816.7	822.6	825.1	828.9	830.3	834.6	841.0	846.2
5°	755.9	761.8	769.3	775.4	785.2	792.8	801.1	809.0	818.4	831.8	843.7
7.5°	714.4	720.1	729.2	740.6	751.4	762.1	773.5	784.3	797.8	816.9	835.8
10°	687.0	693.9	704.7	717.0	730.3	740.8	754.1	767.9	784.5	806.5	829.2
12.5°	663.4	668.5	681.0	692.7	707.8	721.1	734.2	750.3	769.2	792.7	820.0
15°	625.7	632.8	645.2	658.1	674.0	688.1	705.0	724.5	743.0	771.8	805.0
17.5°	587.8	598.8	611.5	626.2	638.0	657.4	675.8	695.8	718.5	749.1	785.5
20°	563.5	572.2	584.1	605.4	620.9	635.7	652.7	677.6	698.5	733.2	771.1
22.5°	543.0	549.4	562.7	580.3	598.4	615.5	632.8	656.6	682.4	715.3	756.4
25°	512.6	522.7	532.8	545.4	565.0	585.6	604.4	624.5	652.0	687.0	731.4
27.5°	483.0	492.1	502.1	517.6	532.4	551.7	571.3	594.5	623.9	660.9	706.0
30°	463.9	470.8	480.1	500.0	513.4	530.0	553.1	573.6	601.1	640.5	688.1
32.5°	444.2	453.2	463.4	478.6	495.1	510.9	532.0	554.3	582.3	621.0	669.9
35°	416.2	426.7	437.2	448.4	465.0	481.3	498.9	523.5	552.0	589.6	637.5
37.5°	390.5	398.9	407.5	421.3	437.1	452.5	469.0	493.2	520.1	560.6	604.6
40°	374.0	381.6	388.0	402.6	417.7	434.3	450.5	471.8	500.7	538.7	581.3
42.5°	356.1	363.1	371.9	383.7	400.1	414.1	430.4	450.4	477.6	516.1	553.5
45°	329.2	337.1	344.8	356.0	372.2	385.9	400.4	419.5	447.3	479.1	512.3
47.5°	301.3	309.2	317.9	328.8	342.9	356.8	371.3	388.2	413.6	444.8	467.1
50°	283.4	289.9	298.6	309.3	322.3	337.1	350.2	368.6	392.8	417.4	436.9
52.5°	264.9	270.8	280.7	292.1	304.2	317.0	330.8	346.7	368.5	391.6	407.1
55°	236.1	243.4	251.7	262.8	274.8	285.6	298.9	315.2	332.5	349.8	360.3
57.5°	209.2	215.2	222.2	233.8	244.0	256.9	268.9	281.6	297.7	310.7	317.5
60°	189.5	194.9	204.0	214.1	223.9	235.0	248.7	261.4	273.6	284.1	289.5
62.5°	171.1	177.3	185.2	194.4	205.1	215.7	227.6	238.3	249.1	258.2	261.8
65°	146.9	152.0	157.8	166.5	175.1	186.0	195.3	206.1	214.1	219.1	222.3
67.5°	125.0	128.3	132.7	138.5	147.0	156.5	165.6	174.0	180.7	184.1	187.0
70°	110.8	113.0	116.2	122.1	128.6	136.9	146.2	152.3	158.2	161.0	163.9
72.5°	96.7	99.4	102.4	107.0	112.4	118.4	125.2	132.7	135.9	139.3	141.1
75°	73.3	77.3	81.2	84.1	87.8	92.5	98.6	103.2	105.1	107.9	108.3
77.5°	55.3	56.2	59.1	62.7	65.7	69.1	73.0	77.2	78.0	79.6	80.5
80°	45.5	45.5	45.5	47.7	51.3	53.8	57.4	59.6	61.0	61.4	61.7
82.5°	36.6	36.6	36.3	36.7	38.0	39.3	42.7	45.1	46.3	46.1	45.2
85°	23.8	23.1	23.1	22.7	23.1	22.3	22.1	23.5	25.6	25.6	24.9
87.5°	11.5	11.1	11.2	10.7	10.3	9.8	8.8	8.9	8.8	9.7	9.3
90°	8.3	8.0	7.1	6.0	5.1	4.1	3.3	2.5	1.8	1.0	0.4
92.5°	9.0	8.5	7.8	7.1	6.3	5.7	5.4	5.6	5.7	6.0	6.2
95°	10.8	10.4	9.5	8.7	7.9	7.1	8.2	11.2	14.2	17.2	20.4
97.5°	11.3	10.7	16.0	21.4	26.7	32.0	35.3	36.8	38.1	39.5	40.8
100°	11.6	11.0	22.5	34.1	45.6	57.2	62.2	60.7	59.3	57.8	56.3
102.5°	20.1	22.0	34.5	47.1	59.8	72.4	78.1	77.1	76.0	74.9	73.9
105°	59.9	73.0	79.6	86.2	92.9	99.6	102.5	101.7	100.9	100.1	99.2
107.5°	124.0	133.7	132.6	131.6	130.5	129.5	128.7	128.0	127.3	126.7	126.0
110°	147.8	150.2	149.4	148.5	147.8	146.9	146.3	145.6	145.1	144.5	143.9



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	167.0	167.0	166.2	165.4	164.6	163.7	163.1	162.5	162.0	161.5	160.9
115°	191.9	191.1	190.5	189.8	189.2	188.5	187.9	187.5	187.1	186.6	186.2
117.5°	215.2	214.6	214.3	214.0	213.6	213.3	212.8	212.3	211.7	211.2	210.7
120°	230.5	229.8	229.6	229.4	229.1	228.9	228.5	227.8	227.2	226.5	225.8
122.5°	245.4	245.0	244.7	244.4	244.1	243.8	243.5	242.9	242.3	241.9	241.3
125°	266.6	266.5	266.2	265.9	265.6	265.2	264.9	264.2	263.6	263.1	262.5
127.5°	287.5	287.2	286.9	286.5	286.2	285.8	285.3	284.7	284.2	283.6	283.0
130°	300.0	299.7	299.4	299.2	298.9	298.6	298.1	297.6	296.9	296.3	295.8
132.5°	312.1	311.8	311.5	311.3	311.0	310.8	310.4	309.8	309.2	308.6	308.0
135°	330.3	330.1	329.8	329.5	329.1	328.9	328.5	328.1	327.6	327.2	326.8
137.5°	346.4	346.0	345.8	345.6	345.5	345.3	345.0	344.4	343.8	343.3	342.7
140°	356.7	356.4	356.2	355.9	355.7	355.5	355.2	354.7	354.3	353.8	353.4
142.5°	366.5	366.3	366.0	365.8	365.6	365.3	365.0	364.6	364.1	363.7	363.3
145°	380.2	380.0	379.8	379.8	379.6	379.5	379.1	378.6	378.1	377.6	377.0
147.5°	392.4	392.2	392.1	391.9	391.8	391.6	391.3	391.1	390.7	390.4	390.0
150°	399.8	399.6	399.5	399.4	399.3	399.1	398.9	398.7	398.4	398.2	398.0
152.5°	406.3	406.0	406.0	405.9	405.8	405.8	405.6	405.5	405.4	405.3	405.2
155°	415.4	415.0	414.9	414.8	414.8	414.7	414.7	414.9	415.0	415.2	415.4
157.5°	423.2	422.8	422.8	422.9	423.0	423.1	423.1	423.1	423.2	423.2	423.2
160°	427.7	427.3	427.4	427.4	427.5	427.6	427.7	427.7	427.8	427.9	428.0
162.5°	431.8	431.3	431.4	431.5	431.5	431.6	431.8	432.0	432.2	432.3	432.5
165°	437.2	436.7	436.7	436.8	436.9	437.0	437.1	437.3	437.5	437.7	438.0
167.5°	441.5	440.9	440.9	440.9	440.9	440.9	441.0	441.4	441.7	442.0	442.2
170°	443.9	443.3	443.3	443.3	443.3	443.3	443.5	443.7	444.0	444.3	444.6
172.5°	445.5	444.9	444.9	444.8	444.7	444.7	444.8	445.2	445.5	445.9	446.2
175°	447.5	447.0	446.9	446.9	446.8	446.7	446.9	447.2	447.5	447.9	448.3
177.5°	448.3	447.8	447.7	447.6	447.6	447.5	447.6	448.0	448.3	448.6	448.8
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	847.9	851.1	855.2	861.2	865.8	869.9	870.7	871.9	874.8	879.7	883.4
5°	853.5	861.8	875.1	888.1	902.2	913.7	924.5	932.2	939.3	954.5	966.8
7.5°	851.7	870.2	891.1	914.5	938.0	960.9	982.1	1001.2	1020.1	1042.2	1067.3
10°	850.6	872.2	900.3	930.3	963.2	995.3	1026.3	1050.6	1078.7	1104.0	1136.1
12.5°	845.1	876.3	909.9	948.2	988.6	1025.7	1066.5	1099.9	1132.1	1168.7	1206.0
15°	837.9	875.8	918.4	969.3	1030.7	1075.4	1117.3	1175.4	1215.1	1254.9	1308.3
17.5°	824.8	871.1	924.4	990.4	1041.7	1101.8	1164.8	1210.8	1264.2	1320.2	1368.6
20°	814.5	868.3	927.8	992.8	1058.1	1123.5	1184.5	1239.3	1294.6	1359.2	1398.9
22.5°	804.1	857.2	919.2	988.2	1058.4	1127.2	1196.3	1260.7	1322.9	1388.1	1438.8
25°	781.9	845.1	912.3	982.7	1052.0	1127.8	1210.1	1282.0	1358.9	1426.0	1474.0
27.5°	759.6	817.5	884.3	955.7	1032.7	1122.4	1219.2	1300.9	1377.9	1426.0	1441.1
30°	739.3	800.7	862.0	934.6	1018.0	1118.0	1221.0	1314.5	1377.6	1398.5	1383.0
32.5°	718.9	774.5	835.3	909.6	998.2	1107.4	1223.2	1306.4	1344.4	1328.4	1265.2
35°	682.7	732.8	791.7	866.1	967.9	1101.5	1213.7	1270.1	1260.7	1170.4	1051.2
37.5°	643.9	684.9	739.3	817.1	936.5	1078.0	1172.7	1181.0	1099.8	961.2	823.6
40°	613.3	650.2	706.2	787.4	912.3	1054.9	1131.4	1097.9	971.9	817.7	702.9
42.5°	583.6	614.6	668.5	756.2	889.2	1023.4	1069.9	996.7	851.4	705.6	601.2
45°	533.2	562.4	616.6	706.5	841.9	963.2	957.1	830.0	684.5	567.1	480.5
47.5°	485.4	511.0	561.8	653.6	786.4	872.9	815.5	680.3	556.9	462.8	401.0
50°	451.7	476.9	527.4	618.0	741.9	805.0	723.1	592.8	479.8	401.8	352.7
52.5°	419.2	443.9	490.2	578.4	688.2	725.9	637.9	517.1	422.9	355.6	313.4
55°	374.0	392.8	434.3	518.8	600.7	609.4	520.2	419.1	341.5	294.5	265.7
57.5°	327.9	344.0	385.0	452.3	509.8	505.3	420.8	333.4	281.1	246.2	225.3
60°	297.8	313.7	349.8	407.6	450.9	435.7	358.2	287.8	243.0	217.4	200.8
62.5°	269.8	282.2	316.0	358.2	389.4	372.2	306.1	247.9	212.4	190.8	177.6
65°	229.2	239.3	266.5	288.4	305.8	289.2	234.3	193.9	168.2	153.1	144.0
67.5°	190.7	197.1	214.2	222.2	234.4	216.2	176.2	149.1	134.5	121.8	115.5
70°	166.5	171.2	180.1	186.6	189.9	171.2	141.5	121.7	109.4	100.4	96.4
72.5°	142.1	146.3	148.1	153.4	151.7	134.1	113.8	98.0	89.2	83.0	77.9
75°	108.7	110.5	108.7	106.5	101.8	89.5	75.5	67.5	61.0	58.2	56.4
77.5°	79.2	78.6	76.2	72.8	64.8	57.0	49.5	46.8	44.0	42.4	41.8
80°	61.0	59.6	57.4	52.0	45.1	39.7	37.9	36.1	35.1	33.2	32.9
82.5°	45.4	44.6	40.9	36.4	31.6	29.0	27.5	26.9	25.7	24.9	24.8
85°	24.2	23.1	19.1	16.6	15.9	15.2	14.8	14.8	13.4	13.0	13.0
87.5°	8.0	6.4	6.3	5.6	5.7	5.4	5.8	5.5	5.4	5.7	5.2
90°	1.0	1.8	2.5	3.3	4.1	5.1	6.0	7.1	8.0	8.3	8.6
92.5°	6.0	5.7	5.6	5.4	5.7	6.3	7.1	7.8	8.5	9.0	9.5
95°	17.2	14.2	11.2	8.2	7.1	7.9	8.7	9.5	10.4	10.8	11.4
97.5°	39.5	38.1	36.8	35.3	32.0	26.7	21.4	16.0	10.7	11.3	11.9
100°	57.8	59.3	60.7	62.2	57.2	45.6	34.1	22.5	11.0	11.6	12.2
102.5°	74.9	76.0	77.1	78.1	72.4	59.8	47.1	34.5	22.0	20.1	18.3
105°	100.1	100.9	101.7	102.5	99.6	92.9	86.2	79.6	73.0	59.9	46.8
107.5°	126.7	127.3	128.0	128.7	129.5	130.5	131.6	132.6	133.7	124.0	114.5
110°	144.5	145.1	145.6	146.3	146.9	147.8	148.5	149.4	150.2	147.8	145.3





TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	161.5	162.0	162.5	163.1	163.7	164.6	165.4	166.2	167.0	167.0	167.1
115°	186.6	187.1	187.5	187.9	188.5	189.2	189.8	190.5	191.1	191.9	192.7
117.5°	211.2	211.7	212.3	212.8	213.3	213.6	214.0	214.3	214.6	215.2	215.8
120°	226.5	227.2	227.8	228.5	228.9	229.1	229.4	229.6	229.8	230.5	231.0
122.5°	241.9	242.3	242.9	243.5	243.8	244.1	244.4	244.7	245.0	245.4	245.8
125°	263.1	263.6	264.2	264.9	265.2	265.6	265.9	266.2	266.5	266.6	266.7
127.5°	283.6	284.2	284.7	285.3	285.8	286.2	286.5	286.9	287.2	287.5	287.7
130°	296.3	296.9	297.6	298.1	298.6	298.9	299.2	299.4	299.7	300.0	300.4
132.5°	308.6	309.2	309.8	310.4	310.8	311.0	311.3	311.5	311.8	312.1	312.4
135°	327.2	327.6	328.1	328.5	328.9	329.1	329.5	329.8	330.1	330.3	330.5
137.5°	343.3	343.8	344.4	345.0	345.3	345.5	345.6	345.8	346.0	346.4	346.7
140°	353.8	354.3	354.7	355.2	355.5	355.7	355.9	356.2	356.4	356.7	356.9
142.5°	363.7	364.1	364.6	365.0	365.3	365.6	365.8	366.0	366.3	366.5	366.7
145°	377.6	378.1	378.6	379.1	379.5	379.6	379.8	379.8	380.0	380.2	380.3
147.5°	390.4	390.7	391.1	391.3	391.6	391.8	391.9	392.1	392.2	392.4	392.5
150°	398.2	398.4	398.7	398.9	399.1	399.3	399.4	399.5	399.6	399.8	400.0
152.5°	405.3	405.4	405.5	405.6	405.8	405.8	405.9	406.0	406.0	406.3	406.6
155°	415.2	415.0	414.9	414.7	414.7	414.8	414.8	414.9	415.0	415.4	415.8
157.5°	423.2	423.2	423.1	423.1	423.1	423.0	422.9	422.8	422.8	423.2	423.7
160°	427.9	427.8	427.7	427.7	427.6	427.5	427.4	427.4	427.3	427.7	428.2
162.5°	432.3	432.2	432.0	431.8	431.6	431.5	431.5	431.4	431.3	431.8	432.3
165°	437.7	437.5	437.3	437.1	437.0	436.9	436.8	436.7	436.7	437.2	437.8
167.5°	442.0	441.7	441.4	441.0	440.9	440.9	440.9	440.9	440.9	441.5	442.1
170°	444.3	444.0	443.7	443.5	443.3	443.3	443.3	443.3	443.3	443.9	444.5
172.5°	445.9	445.5	445.2	444.8	444.7	444.7	444.8	444.9	444.9	445.5	446.1
175°	447.9	447.5	447.2	446.9	446.7	446.8	446.9	446.9	447.0	447.5	448.0
177.5°	448.6	448.3	448.0	447.6	447.5	447.6	447.6	447.7	447.8	448.3	448.7
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3	448.3



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	843.3	843.3	843.3	843.3	843.3	843.3	843.3
2.5°	889.6	889.6	890.7	895.0	895.6	899.4	898.1
5°	977.6	984.5	987.0	997.9	1004.4	1007.2	1001.5
7.5°	1085.3	1104.7	1113.9	1125.2	1135.2	1138.3	1130.4
10°	1163.9	1184.1	1201.1	1211.5	1221.3	1227.8	1236.1
12.5°	1239.8	1264.7	1280.8	1295.6	1305.6	1313.9	1315.2
15°	1322.4	1359.9	1388.5	1409.4	1419.8	1425.3	1423.1
17.5°	1405.6	1440.4	1460.8	1482.1	1496.6	1497.3	1497.8
20°	1452.7	1486.7	1510.1	1526.0	1542.3	1541.5	1545.1
22.5°	1484.2	1510.9	1528.9	1540.4	1546.0	1543.2	1544.0
25°	1498.9	1506.8	1503.6	1485.2	1480.5	1463.6	1466.4
27.5°	1423.0	1385.4	1346.6	1296.6	1257.2	1225.7	1227.3
30°	1319.8	1253.4	1177.6	1114.1	1057.1	1041.1	1007.2
32.5°	1175.7	1076.1	987.3	928.1	879.1	865.8	836.2
35°	931.4	834.6	743.3	688.4	666.8	636.5	636.1
37.5°	724.0	638.8	590.5	549.3	527.7	509.3	507.6
40°	609.1	542.6	506.1	476.5	455.2	441.5	438.3
42.5°	528.8	475.0	440.8	422.5	406.1	399.1	393.8
45°	431.8	395.7	371.8	355.2	347.6	342.2	339.3
47.5°	361.2	337.0	320.7	309.7	303.5	297.8	299.4
50°	322.7	302.9	291.0	280.5	275.8	271.8	272.2
52.5°	291.8	274.0	264.4	256.8	251.0	248.2	246.8
55°	247.7	236.5	226.7	221.3	218.0	214.1	213.0
57.5°	211.2	202.6	194.6	188.5	187.8	183.9	184.4
60°	187.0	179.7	173.2	170.0	167.5	164.3	165.3
62.5°	167.1	161.0	155.0	152.4	149.9	147.5	148.0
65°	136.9	131.0	127.4	126.0	124.9	123.9	122.7
67.5°	109.1	105.5	103.2	100.1	97.9	97.6	96.4
70°	91.7	87.0	83.0	79.1	77.9	77.6	77.9
72.5°	73.5	70.5	69.5	67.5	67.3	66.4	67.0
75°	55.2	54.2	53.4	52.0	52.0	52.0	52.0
77.5°	40.7	40.1	39.7	39.3	39.0	38.5	38.5
80°	31.8	31.4	30.7	30.7	30.3	30.7	30.3
82.5°	23.9	23.9	23.2	23.2	22.8	22.6	22.8
85°	12.3	11.9	12.6	11.9	12.3	11.6	12.3
87.5°	5.3	5.3	5.1	5.1	4.8	5.5	4.9
90°	8.9	9.1	9.4	9.5	9.7	9.8	10.0
92.5°	10.0	10.5	10.7	10.7	10.8	10.9	11.0
95°	11.9	12.4	12.6	12.6	12.6	12.6	12.6
97.5°	12.5	13.1	13.4	13.5	13.6	13.7	13.8
100°	12.7	13.4	13.7	13.8	13.9	13.9	13.9
102.5°	16.4	14.6	13.8	13.9	13.9	14.1	14.2
105°	33.6	20.5	14.0	14.2	14.3	14.5	14.6
107.5°	104.9	95.3	85.5	75.7	65.8	55.9	46.0
110°	142.9	140.4	133.9	123.4	112.7	102.2	91.6



TEST NUMBER: P332270-830

CATALOG NUMBER: S123RDIP-S560D365U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	167.1	167.2	166.1	163.8	161.6	159.4	157.1
115°	193.4	194.2	194.6	194.9	195.3	195.6	195.9
117.5°	216.4	217.0	217.4	217.4	217.4	217.5	217.5
120°	231.6	232.1	232.5	232.5	232.5	232.5	232.5
122.5°	246.3	246.7	246.9	246.9	247.0	247.0	247.1
125°	266.9	267.0	267.2	267.3	267.5	267.7	267.8
127.5°	287.9	288.2	288.2	288.0	287.9	287.8	287.7
130°	300.7	301.0	301.0	300.9	300.8	300.6	300.4
132.5°	312.6	312.9	313.0	312.7	312.5	312.4	312.2
135°	330.7	330.9	330.9	330.7	330.5	330.3	330.1
137.5°	347.0	347.4	347.5	347.3	347.2	347.0	346.9
140°	357.2	357.6	357.6	357.5	357.3	357.2	357.0
142.5°	366.9	367.2	367.2	367.0	366.7	366.6	366.4
145°	380.5	380.6	380.7	380.7	380.7	380.7	380.7
147.5°	392.7	392.9	392.8	392.4	392.0	391.7	391.3
150°	400.1	400.3	400.2	400.0	399.8	399.5	399.4
152.5°	406.9	407.2	407.1	406.8	406.4	406.0	405.8
155°	416.1	416.5	416.4	416.0	415.6	415.1	414.6
157.5°	424.1	424.6	424.5	424.0	423.4	422.7	422.2
160°	428.7	429.1	429.0	428.6	428.0	427.5	427.0
162.5°	432.8	433.3	433.4	432.9	432.4	432.0	431.5
165°	438.5	439.0	439.0	438.6	438.0	437.5	437.0
167.5°	442.7	443.3	443.3	442.7	442.1	441.5	440.9
170°	445.1	445.6	445.6	445.1	444.5	443.9	443.3
172.5°	446.7	447.2	447.2	446.6	445.9	445.3	444.6
175°	448.6	449.0	449.0	448.5	447.8	447.2	446.7
177.5°	449.2	449.7	449.6	449.0	448.5	447.8	447.2
180°	448.3	448.3	448.3	448.3	448.3	448.3	448.3

(END OF REPORT)