

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332319-830

Luminaire Tested: **S123RDIP-S775D1025U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332319-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D1025U830-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6192.1 lumens  
Efficiency: N/A  
Efficacy: 119.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	42	41	39	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	31	28	26	23
6	64	52	44	39	58	48	41	36	41	36	32	35	31	28	28	26	23	20
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	29	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	37	30	26	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12408	12408	12408	12408
5°	14791	12460	10974	12460
10°	18467	12389	9913	12389
15°	21677	12262	9040	12262
20°	24192	12073	8298	12073
25°	23807	11874	7842	11874
30°	17112	11691	7372	11691
35°	11426	11452	7068	11452
40°	8418	11164	6753	11164
45°	7060	10659	6445	10659
50°	6231	9999	6015	9999
55°	5465	9242	5427	9242
60°	4865	8521	4971	8521
65°	4274	7743	4625	7743
70°	3355	7050	4223	7050
75°	2957	6159	3855	6159
80°	2572	5232	3794	5232
85°	2075	4199	4026	4199



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.4	1.8
10°-20°	354.2	5.7
20°-30°	556.4	9.0
30°-40°	580.5	9.4
40°-50°	496.8	8.0
50°-60°	378.6	6.1
60°-70°	242.7	3.9
70°-80°	116.7	1.9
80°-90°	34.4	0.6
90°-100°	78.0	1.3
100°-110°	233.5	3.8
110°-120°	397.2	6.4
120°-130°	522.5	8.4
130°-140°	587.2	9.5
140°-150°	577.2	9.3
150°-160°	486.0	7.8
160°-170°	323.5	5.2
170°-180°	113.3	1.8
0°-30°	1023.9	16.5
0°-40°	1604.4	25.9
0°-60°	2479.8	40.0
0°-90°	2873.7	46.4
90°-120°	708.8	11.4
90°-150°	2395.7	38.7
90°-180°	3318.0	53.6
0°-180°	6192.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1153	1153	1153	1153	1153	
5°	1369	1153	1016	1153	1369	141
15°	1945	1100	811	1100	1945	552
25°	2004	1000	660	1000	2004	862
35°	870	872	538	872	870	570
45°	464	700	423	700	464	365
55°	291	492	289	492	291	263
65°	168	304	182	304	168	165
75°	71	148	93	148	71	76
85°	17	34	33	34	17	20
90°	28	1	28	1	28	14
95°	73	56	73	56	73	75
105°	224	212	224	212	224	238
115°	401	400	401	400	401	397
125°	579	585	579	585	579	517
135°	758	759	758	759	758	583
145°	921	921	921	921	921	575
155°	1053	1055	1053	1055	1053	485
165°	1145	1149	1145	1149	1145	323
175°	1190	1195	1190	1195	1190	113
180°	1198	1198	1198	1198	1198	



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1227.8	1229.4	1224.2	1223.4	1217.5	1215.9	1215.9	1207.6	1202.5	1195.8	1191.8
5°	1368.9	1376.8	1372.8	1364.0	1349.2	1345.7	1336.3	1321.5	1304.8	1284.0	1274.1
7.5°	1545.1	1555.9	1551.8	1538.0	1522.6	1510.0	1483.6	1459.0	1424.6	1394.3	1368.5
10°	1689.6	1678.3	1669.4	1656.0	1641.8	1618.5	1590.9	1552.9	1509.0	1474.5	1436.0
12.5°	1797.8	1795.9	1784.7	1770.9	1750.8	1728.7	1694.8	1648.5	1597.4	1547.6	1503.5
15°	1945.2	1948.2	1940.8	1926.5	1897.9	1858.9	1807.6	1788.3	1715.3	1661.0	1606.8
17.5°	2047.3	2046.7	2045.7	2025.9	1996.7	1969.0	1921.4	1870.8	1804.6	1728.2	1655.0
20°	2112.0	2107.1	2108.1	2085.8	2064.2	2032.1	1985.7	1912.2	1857.9	1769.6	1694.0
22.5°	2110.4	2109.5	2113.3	2105.6	2089.8	2065.3	2028.7	1966.7	1897.4	1808.3	1723.3
25°	2004.5	2000.5	2023.7	2030.1	2055.3	2059.7	2048.9	2014.9	1949.2	1857.4	1752.3
27.5°	1677.6	1675.5	1718.4	1772.4	1840.6	1893.8	1945.0	1969.8	1949.2	1883.5	1778.2
30°	1376.8	1423.1	1444.9	1522.9	1609.7	1713.4	1804.1	1890.5	1911.7	1883.1	1796.7
32.5°	1143.1	1183.6	1201.6	1268.6	1349.5	1470.9	1607.1	1729.4	1815.8	1837.7	1785.6
35°	869.5	870.0	911.4	941.0	1016.1	1140.9	1273.2	1437.0	1599.8	1723.2	1736.0
37.5°	693.8	696.3	721.3	750.8	807.1	873.2	989.6	1125.8	1313.9	1503.3	1614.3
40°	599.1	603.5	622.3	651.4	691.8	741.7	832.5	960.8	1117.7	1328.4	1500.6
42.5°	538.3	545.4	555.2	577.6	602.7	649.3	722.7	821.8	964.5	1163.8	1362.4
45°	463.8	467.8	475.2	485.6	508.3	540.8	590.2	656.8	775.2	935.7	1134.4
47.5°	409.2	407.1	414.9	423.3	438.4	460.6	493.7	548.1	632.5	761.2	929.9
50°	372.1	371.6	377.0	383.4	397.8	414.1	441.2	482.1	549.2	655.8	810.3
52.5°	337.3	339.2	343.1	351.1	361.4	374.6	398.9	428.4	486.1	578.1	706.8
55°	291.2	292.7	298.0	302.5	309.9	323.2	338.6	363.2	402.7	466.8	572.9
57.5°	252.0	251.4	256.6	257.7	266.1	276.9	288.8	307.9	336.6	384.2	455.6
60°	226.0	224.5	228.9	232.4	236.9	245.7	255.6	274.4	297.1	332.1	393.3
62.5°	202.4	201.6	204.9	208.3	212.0	220.1	228.4	242.8	260.7	290.3	338.8
65°	167.8	169.3	170.7	172.2	174.2	179.1	187.0	196.9	209.2	230.0	264.9
67.5°	131.9	133.4	133.8	136.9	141.1	144.2	149.0	157.8	166.4	183.9	203.8
70°	106.6	106.1	106.6	108.1	113.5	118.9	125.4	131.8	137.1	149.5	166.3
72.5°	91.6	90.7	92.0	92.3	94.9	96.4	100.5	106.5	113.5	121.9	133.9
75°	71.1	71.1	71.1	71.1	73.0	74.0	75.5	77.0	79.5	83.4	92.3
77.5°	52.5	52.6	53.3	53.8	54.2	54.8	55.7	57.1	58.1	60.1	64.0
80°	41.5	41.9	41.5	41.9	41.9	42.9	43.5	44.9	45.4	47.9	49.4
82.5°	31.2	30.9	31.2	31.7	31.7	32.7	32.8	33.8	33.9	35.3	36.8
85°	16.8	15.8	16.8	16.3	17.2	16.3	16.8	17.7	17.7	18.3	20.3
87.5°	9.6	10.3	9.4	9.7	9.6	9.9	9.7	9.6	10.2	9.6	9.5
90°	28.2	27.8	27.4	27.0	26.6	25.9	25.1	24.2	23.4	22.6	19.9
92.5°	38.0	38.3	38.5	38.7	39.0	38.8	38.2	37.5	36.8	36.1	34.6
95°	73.4	73.4	73.4	73.4	73.4	73.0	72.1	71.3	70.5	69.7	68.0
97.5°	112.9	113.0	113.1	113.2	113.2	112.8	111.9	110.8	109.9	109.0	107.7
100°	143.0	142.6	142.1	141.8	141.4	140.8	140.2	139.6	138.9	138.3	137.2
102.5°	173.9	174.0	174.0	174.1	174.2	173.9	173.3	172.7	172.0	171.4	170.0
105°	223.9	223.5	223.1	222.6	222.3	222.1	222.1	222.1	222.1	222.1	220.2
107.5°	276.1	276.3	276.5	276.8	277.0	276.8	276.2	275.5	274.8	274.2	273.4
110°	311.4	311.9	312.3	312.6	313.1	312.9	312.1	311.2	310.4	309.5	309.2



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	349.0	349.1	349.2	349.3	349.4	348.9	347.9	346.9	345.9	344.9	344.9
115°	400.8	401.1	401.2	401.4	401.6	401.6	401.4	401.2	401.1	400.8	401.2
117.5°	453.3	453.9	454.5	455.1	455.6	456.0	456.0	456.0	456.1	456.1	456.7
120°	490.2	490.6	491.1	491.4	491.8	492.2	492.4	492.6	492.8	493.0	494.1
122.5°	525.6	526.1	526.7	527.4	527.9	528.5	529.0	529.5	530.1	530.7	531.2
125°	578.6	579.5	580.3	581.2	581.9	582.8	583.6	584.5	585.3	586.2	586.5
127.5°	631.5	632.4	633.4	634.4	635.4	636.4	637.6	638.8	639.9	641.1	641.6
130°	666.1	667.6	669.0	670.5	671.9	673.2	673.9	674.8	675.6	676.5	677.1
132.5°	702.3	703.4	704.6	705.7	706.8	707.8	708.9	709.8	710.9	711.8	712.3
135°	758.4	758.7	759.1	759.6	760.0	760.6	761.5	762.3	763.2	763.9	764.2
137.5°	807.9	808.6	809.4	810.2	811.0	811.8	812.8	813.6	814.5	815.3	814.8
140°	840.2	841.7	843.1	844.6	846.0	846.9	847.1	847.3	847.5	847.7	847.5
142.5°	873.3	874.4	875.5	876.7	877.8	878.4	878.7	878.9	879.1	879.3	878.9
145°	921.1	921.9	922.7	923.6	924.4	924.9	925.2	925.4	925.6	925.8	925.2
147.5°	963.7	964.9	966.1	967.4	968.7	969.3	969.3	969.3	969.3	969.3	968.7
150°	990.7	991.9	993.3	994.5	995.7	996.4	996.4	996.4	996.4	996.4	996.0
152.5°	1017.1	1018.1	1019.3	1020.3	1021.4	1021.8	1021.4	1021.2	1020.8	1020.5	1020.2
155°	1052.8	1054.2	1055.7	1057.2	1058.7	1058.9	1058.2	1057.3	1056.5	1055.6	1055.5
157.5°	1085.3	1086.6	1087.7	1088.9	1090.1	1090.2	1089.3	1088.4	1087.6	1086.7	1086.6
160°	1106.5	1107.3	1108.1	1109.0	1109.7	1109.7	1108.6	1107.6	1106.5	1105.5	1105.5
162.5°	1122.3	1123.6	1124.9	1126.2	1127.6	1127.8	1126.7	1125.7	1124.6	1123.6	1123.4
165°	1145.0	1146.5	1147.9	1149.4	1150.8	1150.9	1149.7	1148.5	1147.2	1145.9	1145.9
167.5°	1164.4	1165.7	1167.0	1168.3	1169.6	1169.6	1168.3	1167.0	1165.7	1164.4	1164.2
170°	1174.2	1175.6	1177.1	1178.6	1180.1	1180.1	1178.6	1177.1	1175.6	1174.2	1174.2
172.5°	1181.7	1183.2	1184.7	1186.1	1187.6	1187.6	1186.4	1185.1	1183.7	1182.4	1182.4
175°	1190.1	1191.7	1193.1	1194.6	1196.0	1196.2	1194.9	1193.6	1192.4	1191.1	1191.1
177.5°	1194.7	1195.9	1197.0	1198.3	1199.4	1199.5	1198.4	1197.5	1196.5	1195.4	1195.4
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1190.2	1189.0	1183.6	1177.2	1168.9	1163.4	1159.0	1156.7	1149.6	1140.9	1135.0
5°	1263.8	1249.0	1233.2	1213.9	1196.2	1177.9	1166.6	1153.2	1137.0	1118.7	1105.9
7.5°	1342.6	1313.5	1282.2	1250.0	1218.0	1189.5	1164.2	1142.6	1116.6	1090.4	1072.1
10°	1403.0	1360.5	1316.5	1271.7	1230.7	1192.2	1162.6	1133.5	1102.4	1072.3	1049.6
12.5°	1457.8	1401.9	1351.3	1296.2	1243.8	1197.8	1155.1	1120.9	1083.5	1051.4	1025.5
15°	1527.3	1470.1	1408.8	1324.9	1255.4	1197.1	1145.4	1100.4	1055.1	1015.6	990.4
17.5°	1592.2	1506.1	1423.9	1353.9	1263.5	1190.7	1127.5	1073.7	1024.0	982.1	951.1
20°	1619.1	1535.7	1446.3	1357.1	1268.2	1186.8	1113.2	1054.0	1002.2	954.9	926.2
22.5°	1635.2	1540.8	1446.7	1350.8	1256.4	1171.8	1099.1	1033.9	977.8	932.7	897.4
25°	1654.1	1541.6	1437.9	1343.2	1247.0	1155.2	1068.8	999.8	939.1	891.2	853.7
27.5°	1666.5	1534.2	1411.7	1306.4	1208.8	1117.4	1038.2	965.1	903.4	852.8	812.6
30°	1668.9	1528.2	1391.6	1277.6	1178.4	1094.5	1010.6	940.6	875.4	821.6	784.1
32.5°	1672.1	1513.6	1364.3	1243.2	1141.7	1058.6	982.6	915.7	848.9	796.0	757.7
35°	1659.1	1505.6	1323.0	1183.8	1082.1	1001.7	933.1	871.5	805.9	754.5	715.5
37.5°	1603.0	1473.5	1280.2	1116.9	1010.6	936.1	880.2	826.4	766.3	710.9	674.2
40°	1546.5	1441.9	1247.0	1076.3	965.3	888.7	838.4	794.5	736.2	684.5	645.0
42.5°	1462.4	1398.9	1215.4	1033.6	913.9	840.2	797.8	756.6	705.5	652.9	615.8
45°	1308.2	1316.5	1150.8	965.7	842.8	768.8	728.9	700.2	654.9	611.4	573.4
47.5°	1114.7	1193.2	1074.9	893.3	767.9	698.4	663.5	638.6	607.9	565.3	530.7
50°	988.4	1100.4	1014.1	844.8	721.0	651.9	617.4	597.1	570.4	536.9	503.8
52.5°	871.9	992.3	940.7	790.7	670.1	606.9	573.2	556.5	535.3	503.7	473.8
55°	711.1	833.0	821.1	709.1	593.6	536.9	511.2	492.5	478.2	454.5	430.8
57.5°	575.2	690.8	696.9	618.3	526.3	470.2	448.2	434.0	424.7	406.8	384.9
60°	489.6	595.6	616.3	557.1	478.2	428.9	407.1	395.8	388.3	374.1	357.3
62.5°	418.5	508.8	532.3	489.7	432.0	385.8	368.8	357.9	352.8	340.4	325.6
65°	320.3	395.3	417.9	394.3	364.2	327.2	313.4	304.0	299.5	292.7	281.7
67.5°	240.8	295.5	320.4	303.7	292.8	269.5	260.6	255.6	251.7	246.9	237.9
70°	193.4	233.9	259.6	255.1	246.3	233.9	227.5	224.0	220.1	216.1	208.2
72.5°	155.5	183.4	207.5	209.7	202.5	199.9	194.4	192.8	190.5	185.8	181.4
75°	103.1	122.3	139.1	145.5	148.5	151.0	148.5	148.1	147.5	143.6	141.1
77.5°	67.6	77.9	88.5	99.4	104.2	107.4	108.3	110.1	108.8	106.7	105.5
80°	51.8	54.3	61.6	71.1	78.4	81.4	83.4	84.4	83.9	83.4	81.4
82.5°	37.6	39.7	43.2	49.8	56.0	60.9	62.1	61.9	63.0	63.2	61.6
85°	20.3	20.7	21.7	22.7	26.1	31.6	33.1	34.0	35.1	35.1	32.0
87.5°	9.7	8.8	9.0	8.6	9.3	9.3	11.3	12.8	13.7	12.4	12.9
90°	17.2	14.4	11.7	9.3	7.3	5.1	3.0	0.9	3.0	5.1	7.3
92.5°	33.0	31.5	30.0	28.5	27.1	25.6	24.2	22.8	24.2	25.6	27.1
95°	66.3	64.6	63.0	61.4	59.9	58.4	56.9	55.5	56.9	58.4	59.9
97.5°	106.5	105.3	104.1	102.9	101.9	100.8	99.7	98.6	99.7	100.8	101.9
100°	136.2	135.2	134.1	133.0	131.7	130.4	129.2	128.0	129.2	130.4	131.7
102.5°	168.6	167.3	165.9	164.9	164.1	163.3	162.6	161.8	162.6	163.3	164.1
105°	218.3	216.4	214.5	213.4	212.9	212.5	212.1	211.7	212.1	212.5	212.9
107.5°	272.7	271.9	271.2	270.7	270.4	270.1	269.9	269.7	269.9	270.1	270.4
110°	308.7	308.3	307.8	307.5	307.0	306.6	306.2	305.8	306.2	306.6	307.0





TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	344.8	344.7	344.6	344.4	344.1	343.9	343.7	343.4	343.7	343.9	344.1
115°	401.6	402.1	402.5	402.4	401.7	401.1	400.5	399.8	400.5	401.1	401.7
117.5°	457.2	457.8	458.3	458.4	458.0	457.5	457.1	456.7	457.1	457.5	458.0
120°	495.1	496.2	497.2	497.1	495.9	494.6	493.3	492.1	493.3	494.6	495.9
122.5°	531.7	532.3	532.8	532.6	531.7	530.7	529.9	529.0	529.9	530.7	531.7
125°	587.0	587.4	587.9	587.7	587.1	586.4	585.9	585.2	585.9	586.4	587.1
127.5°	642.1	642.4	642.9	642.5	641.1	639.8	638.5	637.2	638.5	639.8	641.1
130°	677.7	678.3	679.0	678.4	676.7	675.1	673.4	671.8	673.4	675.1	676.7
132.5°	712.8	713.2	713.7	713.1	711.4	709.7	708.0	706.4	708.0	709.7	711.4
135°	764.4	764.6	764.8	764.3	763.0	761.8	760.5	759.3	760.5	761.8	763.0
137.5°	814.3	813.7	813.1	812.4	811.3	810.3	809.3	808.2	809.3	810.3	811.3
140°	847.3	847.1	846.9	846.2	845.2	844.1	843.1	842.1	843.1	844.1	845.2
142.5°	878.5	878.2	877.8	877.1	876.1	875.1	873.9	872.9	873.9	875.1	876.1
145°	924.5	923.9	923.3	922.7	922.4	921.9	921.5	921.1	921.5	921.9	922.4
147.5°	968.1	967.5	967.0	966.3	965.5	964.8	964.0	963.3	964.0	964.8	965.5
150°	995.5	995.1	994.7	994.3	993.8	993.4	993.1	992.6	993.1	993.4	993.8
152.5°	1019.9	1019.7	1019.5	1019.0	1018.4	1017.9	1017.3	1016.7	1017.3	1017.9	1018.4
155°	1055.2	1055.0	1054.8	1054.7	1054.7	1054.7	1054.7	1054.7	1054.7	1054.7	1054.7
157.5°	1086.4	1086.2	1086.0	1086.1	1086.3	1086.6	1086.8	1087.0	1086.8	1086.6	1086.3
160°	1105.5	1105.5	1105.5	1105.7	1106.2	1106.5	1106.9	1107.4	1106.9	1106.5	1106.2
162.5°	1123.2	1123.0	1122.9	1123.1	1123.7	1124.3	1124.8	1125.5	1124.8	1124.3	1123.7
165°	1145.9	1145.9	1145.9	1146.3	1146.9	1147.5	1148.1	1148.8	1148.1	1147.5	1146.9
167.5°	1164.0	1163.9	1163.8	1164.0	1164.9	1165.7	1166.6	1167.4	1166.6	1165.7	1164.9
170°	1174.2	1174.2	1174.2	1174.6	1175.4	1176.3	1177.1	1178.0	1177.1	1176.3	1175.4
172.5°	1182.4	1182.4	1182.4	1182.9	1183.7	1184.6	1185.4	1186.2	1185.4	1184.6	1183.7
175°	1191.1	1191.1	1191.1	1191.6	1192.4	1193.2	1194.0	1194.9	1194.0	1193.2	1192.4
177.5°	1195.4	1195.4	1195.4	1195.8	1196.5	1197.1	1197.8	1198.4	1197.8	1197.1	1196.5
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1133.0	1127.8	1124.4	1116.4	1111.3	1105.8	1100.2	1103.8	1103.4	1103.0	1103.0
5°	1095.0	1083.6	1073.3	1060.0	1051.6	1041.2	1033.3	1032.4	1034.3	1027.4	1023.4
7.5°	1057.3	1041.8	1027.1	1012.4	996.8	984.4	976.6	972.9	967.9	963.7	959.2
10°	1030.9	1012.6	998.2	980.1	963.3	948.5	939.1	932.6	929.2	925.8	919.4
12.5°	1003.6	985.7	967.5	946.9	930.9	913.7	906.7	899.5	892.9	889.0	880.2
15°	963.7	940.6	921.3	899.6	881.8	865.1	855.2	840.8	838.9	834.0	825.1
17.5°	923.8	898.6	872.0	856.0	835.9	818.5	803.4	798.6	784.5	779.2	771.5
20°	892.2	869.0	848.8	827.6	798.4	782.1	770.3	763.9	752.5	745.6	740.6
22.5°	865.0	841.4	817.9	793.2	769.2	750.9	742.3	732.3	726.1	716.4	711.1
25°	826.0	800.4	772.3	745.6	728.4	714.5	700.7	691.8	683.0	678.5	668.6
27.5°	780.9	754.0	727.7	707.6	686.4	672.7	660.2	652.2	641.6	634.1	628.7
30°	756.0	724.4	701.7	683.4	656.3	643.5	634.1	624.2	616.3	608.4	603.0
32.5°	727.2	698.3	676.8	654.2	633.4	619.4	607.3	598.6	591.8	584.4	578.9
35°	681.9	657.8	635.6	612.8	597.6	583.2	569.0	561.6	555.2	548.3	543.3
37.5°	641.1	618.5	597.4	575.9	556.9	545.3	533.8	528.1	519.4	514.8	509.7
40°	615.9	593.6	570.9	550.3	530.5	521.6	511.2	502.8	494.9	491.5	486.1
42.5°	588.2	566.0	546.9	524.5	508.4	496.3	486.7	477.6	471.6	466.7	463.5
45°	547.2	527.5	508.8	486.5	471.3	460.9	450.1	441.7	436.2	432.8	427.3
47.5°	507.5	487.8	468.7	449.3	434.5	422.7	411.9	406.0	398.8	394.5	391.0
50°	478.6	460.9	440.6	422.9	408.1	396.2	387.4	379.9	373.5	368.2	365.7
52.5°	452.2	433.3	415.8	399.3	383.6	370.2	362.1	354.3	349.5	343.3	340.4
55°	408.6	390.3	375.5	359.2	343.9	332.6	322.7	315.8	310.9	304.0	300.0
57.5°	367.6	351.3	333.6	319.4	303.7	294.1	285.9	276.5	270.5	265.1	261.3
60°	340.0	321.2	305.9	292.7	278.8	266.5	259.1	251.7	245.2	239.8	236.4
62.5°	311.2	294.8	280.3	265.8	253.2	242.4	233.8	227.6	222.0	218.5	215.1
65°	266.9	254.1	239.3	227.5	215.7	207.7	200.9	195.4	191.4	189.0	186.1
67.5°	226.3	213.9	201.0	189.3	181.4	175.4	170.9	166.2	164.2	161.1	159.1
70°	199.8	187.0	175.7	166.8	158.9	154.5	151.5	148.1	146.1	142.1	140.2
72.5°	171.1	161.7	153.5	146.3	140.0	135.9	132.1	127.9	124.8	120.4	118.5
75°	134.7	126.3	119.9	115.0	111.0	105.6	100.2	95.8	94.3	92.7	92.3
77.5°	99.8	94.4	89.8	85.7	80.8	76.8	75.6	74.6	74.3	73.5	73.5
80°	78.4	73.5	70.0	65.1	62.2	62.2	62.2	61.2	61.6	61.6	61.6
82.5°	58.3	53.8	51.9	50.1	49.6	50.0	50.0	50.1	49.9	50.6	50.2
85°	30.1	30.6	31.6	31.1	31.6	31.6	32.6	32.0	32.6	31.6	32.6
87.5°	12.9	14.6	15.6	16.5	17.4	17.5	18.1	18.3	18.9	19.0	19.1
90°	9.3	11.7	14.4	17.2	19.9	22.6	23.4	24.2	25.1	25.9	26.6
92.5°	28.5	30.0	31.5	33.0	34.6	36.1	36.8	37.5	38.2	38.8	39.0
95°	61.4	63.0	64.6	66.3	68.0	69.7	70.5	71.3	72.1	73.0	73.4
97.5°	102.9	104.1	105.3	106.5	107.7	109.0	109.9	110.8	111.9	112.8	113.2
100°	133.0	134.1	135.2	136.2	137.2	138.3	138.9	139.6	140.2	140.8	141.4
102.5°	164.9	165.9	167.3	168.6	170.0	171.4	172.0	172.7	173.3	173.9	174.2
105°	213.4	214.5	216.4	218.3	220.2	222.1	222.1	222.1	222.1	222.1	222.3
107.5°	270.7	271.2	271.9	272.7	273.4	274.2	274.8	275.5	276.2	276.8	277.0
110°	307.5	307.8	308.3	308.7	309.2	309.5	310.4	311.2	312.1	312.9	313.1



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	344.4	344.6	344.7	344.8	344.9	344.9	345.9	346.9	347.9	348.9	349.4
115°	402.4	402.5	402.1	401.6	401.2	400.8	401.1	401.2	401.4	401.6	401.6
117.5°	458.4	458.3	457.8	457.2	456.7	456.1	456.1	456.0	456.0	456.0	455.6
120°	497.1	497.2	496.2	495.1	494.1	493.0	492.8	492.6	492.4	492.2	491.8
122.5°	532.6	532.8	532.3	531.7	531.2	530.7	530.1	529.5	529.0	528.5	527.9
125°	587.7	587.9	587.4	587.0	586.5	586.2	585.3	584.5	583.6	582.8	581.9
127.5°	642.5	642.9	642.4	642.1	641.6	641.1	639.9	638.8	637.6	636.4	635.4
130°	678.4	679.0	678.3	677.7	677.1	676.5	675.6	674.8	673.9	673.2	671.9
132.5°	713.1	713.7	713.2	712.8	712.3	711.8	710.9	709.8	708.9	707.8	706.8
135°	764.3	764.8	764.6	764.4	764.2	763.9	763.2	762.3	761.5	760.6	760.0
137.5°	812.4	813.1	813.7	814.3	814.8	815.3	814.5	813.6	812.8	811.8	811.0
140°	846.2	846.9	847.1	847.3	847.5	847.7	847.5	847.3	847.1	846.9	846.0
142.5°	877.1	877.8	878.2	878.5	878.9	879.3	879.1	878.9	878.7	878.4	877.8
145°	922.7	923.3	923.9	924.5	925.2	925.8	925.6	925.4	925.2	924.9	924.4
147.5°	966.3	967.0	967.5	968.1	968.7	969.3	969.3	969.3	969.3	969.3	968.7
150°	994.3	994.7	995.1	995.5	996.0	996.4	996.4	996.4	996.4	996.4	995.7
152.5°	1019.0	1019.5	1019.7	1019.9	1020.2	1020.5	1020.8	1021.2	1021.4	1021.8	1021.4
155°	1054.7	1054.8	1055.0	1055.2	1055.5	1055.6	1056.5	1057.3	1058.2	1058.9	1058.7
157.5°	1086.1	1086.0	1086.2	1086.4	1086.6	1086.7	1087.6	1088.4	1089.3	1090.2	1090.1
160°	1105.7	1105.5	1105.5	1105.5	1105.5	1105.5	1106.5	1107.6	1108.6	1109.7	1109.7
162.5°	1123.1	1122.9	1123.0	1123.2	1123.4	1123.6	1124.6	1125.7	1126.7	1127.8	1127.6
165°	1146.3	1145.9	1145.9	1145.9	1145.9	1145.9	1147.2	1148.5	1149.7	1150.9	1150.8
167.5°	1164.0	1163.8	1163.9	1164.0	1164.2	1164.4	1165.7	1167.0	1168.3	1169.6	1169.6
170°	1174.6	1174.2	1174.2	1174.2	1174.2	1174.2	1175.6	1177.1	1178.6	1180.1	1180.1
172.5°	1182.9	1182.4	1182.4	1182.4	1182.4	1182.4	1183.7	1185.1	1186.4	1187.6	1187.6
175°	1191.6	1191.1	1191.1	1191.1	1191.1	1191.1	1192.4	1193.6	1194.9	1196.2	1196.0
177.5°	1195.8	1195.4	1195.4	1195.4	1195.4	1195.4	1196.5	1197.5	1198.4	1199.5	1199.4
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1098.3	1097.9	1098.3	1096.6	1098.3	1097.9	1098.3	1103.0	1103.0	1103.4	1103.8
5°	1022.0	1021.4	1020.0	1015.6	1020.0	1021.4	1022.0	1023.4	1027.4	1034.3	1032.4
7.5°	955.4	954.7	950.4	950.5	950.4	954.7	955.4	959.2	963.7	967.9	972.9
10°	915.9	916.3	910.5	907.0	910.5	916.3	915.9	919.4	925.8	929.2	932.6
12.5°	877.6	875.3	870.5	866.8	870.5	875.3	877.6	880.2	889.0	892.9	899.5
15°	827.1	822.1	810.3	811.2	810.3	822.1	827.1	825.1	834.0	838.9	840.8
17.5°	767.5	763.9	763.6	756.8	763.6	763.9	767.5	771.5	779.2	784.5	798.6
20°	732.8	730.4	731.3	724.4	731.3	730.4	732.8	740.6	745.6	752.5	763.9
22.5°	705.6	703.1	699.0	696.8	699.0	703.1	705.6	711.1	716.4	726.1	732.3
25°	665.7	661.8	657.8	660.3	657.8	661.8	665.7	668.6	678.5	683.0	691.8
27.5°	625.8	622.8	618.9	618.4	618.9	622.8	625.8	628.7	634.1	641.6	652.2
30°	600.6	597.6	595.6	593.1	595.6	597.6	600.6	603.0	608.4	616.3	624.2
32.5°	574.9	574.3	570.7	570.2	570.7	574.3	574.9	578.9	584.4	591.8	598.6
35°	541.3	538.4	537.3	537.9	537.3	538.4	541.3	543.3	548.3	555.2	561.6
37.5°	509.4	505.5	503.7	502.0	503.7	505.5	509.4	509.7	514.8	519.4	528.1
40°	486.5	482.6	481.6	480.6	481.6	482.6	486.5	486.1	491.5	494.9	502.8
42.5°	460.9	459.3	458.7	456.9	458.7	459.3	460.9	463.5	466.7	471.6	477.6
45°	425.8	425.4	422.4	423.4	422.4	425.4	425.8	427.3	432.8	436.2	441.7
47.5°	389.0	386.8	384.7	386.1	384.7	386.8	389.0	391.0	394.5	398.8	406.0
50°	363.7	362.7	358.3	359.2	358.3	362.7	363.7	365.7	368.2	373.5	379.9
52.5°	338.5	334.7	333.0	332.4	333.0	334.7	338.5	340.4	343.3	349.5	354.3
55°	296.6	292.1	290.1	289.2	290.1	292.1	296.6	300.0	304.0	310.9	315.8
57.5°	255.5	254.3	252.8	253.8	252.8	254.3	255.5	261.3	265.1	270.5	276.5
60°	231.4	231.4	231.4	230.9	231.4	231.4	231.4	236.4	239.8	245.2	251.7
62.5°	212.9	211.7	211.3	212.0	211.3	211.7	212.9	215.1	218.5	222.0	227.6
65°	184.5	184.1	182.1	181.6	182.1	184.1	184.5	186.1	189.0	191.4	195.4
67.5°	157.8	156.0	155.4	154.8	155.4	156.0	157.8	159.1	161.1	164.2	166.2
70°	137.7	136.7	133.7	134.2	133.7	136.7	137.7	140.2	142.1	146.1	148.1
72.5°	115.9	115.0	114.4	113.7	114.4	115.0	115.9	118.5	120.4	124.8	127.9
75°	91.8	91.3	90.8	92.7	90.8	91.3	91.8	92.3	92.7	94.3	95.8
77.5°	73.5	73.5	73.8	73.0	73.8	73.5	73.5	73.5	73.5	74.3	74.6
80°	61.6	61.6	61.2	61.2	61.2	61.6	61.6	61.6	61.6	61.6	61.2
82.5°	49.5	49.9	50.1	49.4	50.1	49.9	49.5	50.2	50.6	49.9	50.1
85°	32.6	32.0	33.1	32.6	33.1	32.0	32.6	32.6	31.6	32.6	32.0
87.5°	20.0	19.3	19.4	19.9	19.4	19.3	20.0	19.1	19.0	18.9	18.3
90°	27.0	27.4	27.8	28.2	27.8	27.4	27.0	26.6	25.9	25.1	24.2
92.5°	38.7	38.5	38.3	38.0	38.3	38.5	38.7	39.0	38.8	38.2	37.5
95°	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.4	73.0	72.1	71.3
97.5°	113.2	113.1	113.0	112.9	113.0	113.1	113.2	113.2	112.8	111.9	110.8
100°	141.8	142.1	142.6	143.0	142.6	142.1	141.8	141.4	140.8	140.2	139.6
102.5°	174.1	174.0	174.0	173.9	174.0	174.0	174.1	174.2	173.9	173.3	172.7
105°	222.6	223.1	223.5	223.9	223.5	223.1	222.6	222.3	222.1	222.1	222.1
107.5°	276.8	276.5	276.3	276.1	276.3	276.5	276.8	277.0	276.8	276.2	275.5
110°	312.6	312.3	311.9	311.4	311.9	312.3	312.6	313.1	312.9	312.1	311.2



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	349.3	349.2	349.1	349.0	349.1	349.2	349.3	349.4	348.9	347.9	346.9
115°	401.4	401.2	401.1	400.8	401.1	401.2	401.4	401.6	401.6	401.4	401.2
117.5°	455.1	454.5	453.9	453.3	453.9	454.5	455.1	455.6	456.0	456.0	456.0
120°	491.4	491.1	490.6	490.2	490.6	491.1	491.4	491.8	492.2	492.4	492.6
122.5°	527.4	526.7	526.1	525.6	526.1	526.7	527.4	527.9	528.5	529.0	529.5
125°	581.2	580.3	579.5	578.6	579.5	580.3	581.2	581.9	582.8	583.6	584.5
127.5°	634.4	633.4	632.4	631.5	632.4	633.4	634.4	635.4	636.4	637.6	638.8
130°	670.5	669.0	667.6	666.1	667.6	669.0	670.5	671.9	673.2	673.9	674.8
132.5°	705.7	704.6	703.4	702.3	703.4	704.6	705.7	706.8	707.8	708.9	709.8
135°	759.6	759.1	758.7	758.4	758.7	759.1	759.6	760.0	760.6	761.5	762.3
137.5°	810.2	809.4	808.6	807.9	808.6	809.4	810.2	811.0	811.8	812.8	813.6
140°	844.6	843.1	841.7	840.2	841.7	843.1	844.6	846.0	846.9	847.1	847.3
142.5°	876.7	875.5	874.4	873.3	874.4	875.5	876.7	877.8	878.4	878.7	878.9
145°	923.6	922.7	921.9	921.1	921.9	922.7	923.6	924.4	924.9	925.2	925.4
147.5°	967.4	966.1	964.9	963.7	964.9	966.1	967.4	968.7	969.3	969.3	969.3
150°	994.5	993.3	991.9	990.7	991.9	993.3	994.5	995.7	996.4	996.4	996.4
152.5°	1020.3	1019.3	1018.1	1017.1	1018.1	1019.3	1020.3	1021.4	1021.8	1021.4	1021.2
155°	1057.2	1055.7	1054.2	1052.8	1054.2	1055.7	1057.2	1058.7	1058.9	1058.2	1057.3
157.5°	1088.9	1087.7	1086.6	1085.3	1086.6	1087.7	1088.9	1090.1	1090.2	1089.3	1088.4
160°	1109.0	1108.1	1107.3	1106.5	1107.3	1108.1	1109.0	1109.7	1109.7	1108.6	1107.6
162.5°	1126.2	1124.9	1123.6	1122.3	1123.6	1124.9	1126.2	1127.6	1127.8	1126.7	1125.7
165°	1149.4	1147.9	1146.5	1145.0	1146.5	1147.9	1149.4	1150.8	1150.9	1149.7	1148.5
167.5°	1168.3	1167.0	1165.7	1164.4	1165.7	1167.0	1168.3	1169.6	1169.6	1168.3	1167.0
170°	1178.6	1177.1	1175.6	1174.2	1175.6	1177.1	1178.6	1180.1	1180.1	1178.6	1177.1
172.5°	1186.1	1184.7	1183.2	1181.7	1183.2	1184.7	1186.1	1187.6	1187.6	1186.4	1185.1
175°	1194.6	1193.1	1191.7	1190.1	1191.7	1193.1	1194.6	1196.0	1196.2	1194.9	1193.6
177.5°	1198.3	1197.0	1195.9	1194.7	1195.9	1197.0	1198.3	1199.4	1199.5	1198.4	1197.5
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1100.2	1105.8	1111.3	1116.4	1124.4	1127.8	1133.0	1135.0	1140.9	1149.6	1156.7
5°	1033.3	1041.2	1051.6	1060.0	1073.3	1083.6	1095.0	1105.9	1118.7	1137.0	1153.2
7.5°	976.6	984.4	996.8	1012.4	1027.1	1041.8	1057.3	1072.1	1090.4	1116.6	1142.6
10°	939.1	948.5	963.3	980.1	998.2	1012.6	1030.9	1049.6	1072.3	1102.4	1133.5
12.5°	906.7	913.7	930.9	946.9	967.5	985.7	1003.6	1025.5	1051.4	1083.5	1120.9
15°	855.2	865.1	881.8	899.6	921.3	940.6	963.7	990.4	1015.6	1055.1	1100.4
17.5°	803.4	818.5	835.9	856.0	872.0	898.6	923.8	951.1	982.1	1024.0	1073.7
20°	770.3	782.1	798.4	827.6	848.8	869.0	892.2	926.2	954.9	1002.2	1054.0
22.5°	742.3	750.9	769.2	793.2	817.9	841.4	865.0	897.4	932.7	977.8	1033.9
25°	700.7	714.5	728.4	745.6	772.3	800.4	826.0	853.7	891.2	939.1	999.8
27.5°	660.2	672.7	686.4	707.6	727.7	754.0	780.9	812.6	852.8	903.4	965.1
30°	634.1	643.5	656.3	683.4	701.7	724.4	756.0	784.1	821.6	875.4	940.6
32.5°	607.3	619.4	633.4	654.2	676.8	698.3	727.2	757.7	796.0	848.9	915.7
35°	569.0	583.2	597.6	612.8	635.6	657.8	681.9	715.5	754.5	805.9	871.5
37.5°	533.8	545.3	556.9	575.9	597.4	618.5	641.1	674.2	710.9	766.3	826.4
40°	511.2	521.6	530.5	550.3	570.9	593.6	615.9	645.0	684.5	736.2	794.5
42.5°	486.7	496.3	508.4	524.5	546.9	566.0	588.2	615.8	652.9	705.5	756.6
45°	450.1	460.9	471.3	486.5	508.8	527.5	547.2	573.4	611.4	654.9	700.2
47.5°	411.9	422.7	434.5	449.3	468.7	487.8	507.5	530.7	565.3	607.9	638.6
50°	387.4	396.2	408.1	422.9	440.6	460.9	478.6	503.8	536.9	570.4	597.1
52.5°	362.1	370.2	383.6	399.3	415.8	433.3	452.2	473.8	503.7	535.3	556.5
55°	322.7	332.6	343.9	359.2	375.5	390.3	408.6	430.8	454.5	478.2	492.5
57.5°	285.9	294.1	303.7	319.4	333.6	351.3	367.6	384.9	406.8	424.7	434.0
60°	259.1	266.5	278.8	292.7	305.9	321.2	340.0	357.3	374.1	388.3	395.8
62.5°	233.8	242.4	253.2	265.8	280.3	294.8	311.2	325.6	340.4	352.8	357.9
65°	200.9	207.7	215.7	227.5	239.3	254.1	266.9	281.7	292.7	299.5	304.0
67.5°	170.9	175.4	181.4	189.3	201.0	213.9	226.3	237.9	246.9	251.7	255.6
70°	151.5	154.5	158.9	166.8	175.7	187.0	199.8	208.2	216.1	220.1	224.0
72.5°	132.1	135.9	140.0	146.3	153.5	161.7	171.1	181.4	185.8	190.5	192.8
75°	100.2	105.6	111.0	115.0	119.9	126.3	134.7	141.1	143.6	147.5	148.1
77.5°	75.6	76.8	80.8	85.7	89.8	94.4	99.8	105.5	106.7	108.8	110.1
80°	62.2	62.2	62.2	65.1	70.0	73.5	78.4	81.4	83.4	83.9	84.4
82.5°	50.0	50.0	49.6	50.1	51.9	53.8	58.3	61.6	63.2	63.0	61.9
85°	32.6	31.6	31.6	31.1	31.6	30.6	30.1	32.0	35.1	35.1	34.0
87.5°	18.1	17.5	17.4	16.5	15.6	14.6	12.9	12.9	12.4	13.7	12.8
90°	23.4	22.6	19.9	17.2	14.4	11.7	9.3	7.3	5.1	3.0	0.9
92.5°	36.8	36.1	34.6	33.0	31.5	30.0	28.5	27.1	25.6	24.2	22.8
95°	70.5	69.7	68.0	66.3	64.6	63.0	61.4	59.9	58.4	56.9	55.5
97.5°	109.9	109.0	107.7	106.5	105.3	104.1	102.9	101.9	100.8	99.7	98.6
100°	138.9	138.3	137.2	136.2	135.2	134.1	133.0	131.7	130.4	129.2	128.0
102.5°	172.0	171.4	170.0	168.6	167.3	165.9	164.9	164.1	163.3	162.6	161.8
105°	222.1	222.1	220.2	218.3	216.4	214.5	213.4	212.9	212.5	212.1	211.7
107.5°	274.8	274.2	273.4	272.7	271.9	271.2	270.7	270.4	270.1	269.9	269.7
110°	310.4	309.5	309.2	308.7	308.3	307.8	307.5	307.0	306.6	306.2	305.8



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	345.9	344.9	344.9	344.8	344.7	344.6	344.4	344.1	343.9	343.7	343.4
115°	401.1	400.8	401.2	401.6	402.1	402.5	402.4	401.7	401.1	400.5	399.8
117.5°	456.1	456.1	456.7	457.2	457.8	458.3	458.4	458.0	457.5	457.1	456.7
120°	492.8	493.0	494.1	495.1	496.2	497.2	497.1	495.9	494.6	493.3	492.1
122.5°	530.1	530.7	531.2	531.7	532.3	532.8	532.6	531.7	530.7	529.9	529.0
125°	585.3	586.2	586.5	587.0	587.4	587.9	587.7	587.1	586.4	585.9	585.2
127.5°	639.9	641.1	641.6	642.1	642.4	642.9	642.5	641.1	639.8	638.5	637.2
130°	675.6	676.5	677.1	677.7	678.3	679.0	678.4	676.7	675.1	673.4	671.8
132.5°	710.9	711.8	712.3	712.8	713.2	713.7	713.1	711.4	709.7	708.0	706.4
135°	763.2	763.9	764.2	764.4	764.6	764.8	764.3	763.0	761.8	760.5	759.3
137.5°	814.5	815.3	814.8	814.3	813.7	813.1	812.4	811.3	810.3	809.3	808.2
140°	847.5	847.7	847.5	847.3	847.1	846.9	846.2	845.2	844.1	843.1	842.1
142.5°	879.1	879.3	878.9	878.5	878.2	877.8	877.1	876.1	875.1	873.9	872.9
145°	925.6	925.8	925.2	924.5	923.9	923.3	922.7	922.4	921.9	921.5	921.1
147.5°	969.3	969.3	968.7	968.1	967.5	967.0	966.3	965.5	964.8	964.0	963.3
150°	996.4	996.4	996.0	995.5	995.1	994.7	994.3	993.8	993.4	993.1	992.6
152.5°	1020.8	1020.5	1020.2	1019.9	1019.7	1019.5	1019.0	1018.4	1017.9	1017.3	1016.7
155°	1056.5	1055.6	1055.5	1055.2	1055.0	1054.8	1054.7	1054.7	1054.7	1054.7	1054.7
157.5°	1087.6	1086.7	1086.6	1086.4	1086.2	1086.0	1086.1	1086.3	1086.6	1086.8	1087.0
160°	1106.5	1105.5	1105.5	1105.5	1105.5	1105.5	1105.7	1106.2	1106.5	1106.9	1107.4
162.5°	1124.6	1123.6	1123.4	1123.2	1123.0	1122.9	1123.1	1123.7	1124.3	1124.8	1125.5
165°	1147.2	1145.9	1145.9	1145.9	1145.9	1145.9	1146.3	1146.9	1147.5	1148.1	1148.8
167.5°	1165.7	1164.4	1164.2	1164.0	1163.9	1163.8	1164.0	1164.9	1165.7	1166.6	1167.4
170°	1175.6	1174.2	1174.2	1174.2	1174.2	1174.2	1174.6	1175.4	1176.3	1177.1	1178.0
172.5°	1183.7	1182.4	1182.4	1182.4	1182.4	1182.4	1182.9	1183.7	1184.6	1185.4	1186.2
175°	1192.4	1191.1	1191.1	1191.1	1191.1	1191.1	1191.6	1192.4	1193.2	1194.0	1194.9
177.5°	1196.5	1195.4	1195.4	1195.4	1195.4	1195.4	1195.8	1196.5	1197.1	1197.8	1198.4
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1159.0	1163.4	1168.9	1177.2	1183.6	1189.0	1190.2	1191.8	1195.8	1202.5	1207.6
5°	1166.6	1177.9	1196.2	1213.9	1233.2	1249.0	1263.8	1274.1	1284.0	1304.8	1321.5
7.5°	1164.2	1189.5	1218.0	1250.0	1282.2	1313.5	1342.6	1368.5	1394.3	1424.6	1459.0
10°	1162.6	1192.2	1230.7	1271.7	1316.5	1360.5	1403.0	1436.0	1474.5	1509.0	1552.9
12.5°	1155.1	1197.8	1243.8	1296.2	1351.3	1401.9	1457.8	1503.5	1547.6	1597.4	1648.5
15°	1145.4	1197.1	1255.4	1324.9	1408.8	1470.1	1527.3	1606.8	1661.0	1715.3	1788.3
17.5°	1127.5	1190.7	1263.5	1353.9	1423.9	1506.1	1592.2	1655.0	1728.2	1804.6	1870.8
20°	1113.2	1186.8	1268.2	1357.1	1446.3	1535.7	1619.1	1694.0	1769.6	1857.9	1912.2
22.5°	1099.1	1171.8	1256.4	1350.8	1446.7	1540.8	1635.2	1723.3	1808.3	1897.4	1966.7
25°	1068.8	1155.2	1247.0	1343.2	1437.9	1541.6	1654.1	1752.3	1857.4	1949.2	2014.9
27.5°	1038.2	1117.4	1208.8	1306.4	1411.7	1534.2	1666.5	1778.2	1883.5	1949.2	1969.8
30°	1010.6	1094.5	1178.4	1277.6	1391.6	1528.2	1668.9	1796.7	1883.1	1911.7	1890.5
32.5°	982.6	1058.6	1141.7	1243.2	1364.3	1513.6	1672.1	1785.6	1837.7	1815.8	1729.4
35°	933.1	1001.7	1082.1	1183.8	1323.0	1505.6	1659.1	1736.0	1723.2	1599.8	1437.0
37.5°	880.2	936.1	1010.6	1116.9	1280.2	1473.5	1603.0	1614.3	1503.3	1313.9	1125.8
40°	838.4	888.7	965.3	1076.3	1247.0	1441.9	1546.5	1500.6	1328.4	1117.7	960.8
42.5°	797.8	840.2	913.9	1033.6	1215.4	1398.9	1462.4	1362.4	1163.8	964.5	821.8
45°	728.9	768.8	842.8	965.7	1150.8	1316.5	1308.2	1134.4	935.7	775.2	656.8
47.5°	663.5	698.4	767.9	893.3	1074.9	1193.2	1114.7	929.9	761.2	632.5	548.1
50°	617.4	651.9	721.0	844.8	1014.1	1100.4	988.4	810.3	655.8	549.2	482.1
52.5°	573.2	606.9	670.1	790.7	940.7	992.3	871.9	706.8	578.1	486.1	428.4
55°	511.2	536.9	593.6	709.1	821.1	833.0	711.1	572.9	466.8	402.7	363.2
57.5°	448.2	470.2	526.3	618.3	696.9	690.8	575.2	455.6	384.2	336.6	307.9
60°	407.1	428.9	478.2	557.1	616.3	595.6	489.6	393.3	332.1	297.1	274.4
62.5°	368.8	385.8	432.0	489.7	532.3	508.8	418.5	338.8	290.3	260.7	242.8
65°	313.4	327.2	364.2	394.3	417.9	395.3	320.3	264.9	230.0	209.2	196.9
67.5°	260.6	269.5	292.8	303.7	320.4	295.5	240.8	203.8	183.9	166.4	157.8
70°	227.5	233.9	246.3	255.1	259.6	233.9	193.4	166.3	149.5	137.1	131.8
72.5°	194.4	199.9	202.5	209.7	207.5	183.4	155.5	133.9	121.9	113.5	106.5
75°	148.5	151.0	148.5	145.5	139.1	122.3	103.1	92.3	83.4	79.5	77.0
77.5°	108.3	107.4	104.2	99.4	88.5	77.9	67.6	64.0	60.1	58.1	57.1
80°	83.4	81.4	78.4	71.1	61.6	54.3	51.8	49.4	47.9	45.4	44.9
82.5°	62.1	60.9	56.0	49.8	43.2	39.7	37.6	36.8	35.3	33.9	33.8
85°	33.1	31.6	26.1	22.7	21.7	20.7	20.3	20.3	18.3	17.7	17.7
87.5°	11.3	9.3	9.3	8.6	9.0	8.8	9.7	9.5	9.6	10.2	9.6
90°	3.0	5.1	7.3	9.3	11.7	14.4	17.2	19.9	22.6	23.4	24.2
92.5°	24.2	25.6	27.1	28.5	30.0	31.5	33.0	34.6	36.1	36.8	37.5
95°	56.9	58.4	59.9	61.4	63.0	64.6	66.3	68.0	69.7	70.5	71.3
97.5°	99.7	100.8	101.9	102.9	104.1	105.3	106.5	107.7	109.0	109.9	110.8
100°	129.2	130.4	131.7	133.0	134.1	135.2	136.2	137.2	138.3	138.9	139.6
102.5°	162.6	163.3	164.1	164.9	165.9	167.3	168.6	170.0	171.4	172.0	172.7
105°	212.1	212.5	212.9	213.4	214.5	216.4	218.3	220.2	222.1	222.1	222.1
107.5°	269.9	270.1	270.4	270.7	271.2	271.9	272.7	273.4	274.2	274.8	275.5
110°	306.2	306.6	307.0	307.5	307.8	308.3	308.7	309.2	309.5	310.4	311.2





TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	343.7	343.9	344.1	344.4	344.6	344.7	344.8	344.9	344.9	345.9	346.9
115°	400.5	401.1	401.7	402.4	402.5	402.1	401.6	401.2	400.8	401.1	401.2
117.5°	457.1	457.5	458.0	458.4	458.3	457.8	457.2	456.7	456.1	456.1	456.0
120°	493.3	494.6	495.9	497.1	497.2	496.2	495.1	494.1	493.0	492.8	492.6
122.5°	529.9	530.7	531.7	532.6	532.8	532.3	531.7	531.2	530.7	530.1	529.5
125°	585.9	586.4	587.1	587.7	587.9	587.4	587.0	586.5	586.2	585.3	584.5
127.5°	638.5	639.8	641.1	642.5	642.9	642.4	642.1	641.6	641.1	639.9	638.8
130°	673.4	675.1	676.7	678.4	679.0	678.3	677.7	677.1	676.5	675.6	674.8
132.5°	708.0	709.7	711.4	713.1	713.7	713.2	712.8	712.3	711.8	710.9	709.8
135°	760.5	761.8	763.0	764.3	764.8	764.6	764.4	764.2	763.9	763.2	762.3
137.5°	809.3	810.3	811.3	812.4	813.1	813.7	814.3	814.8	815.3	814.5	813.6
140°	843.1	844.1	845.2	846.2	846.9	847.1	847.3	847.5	847.7	847.5	847.3
142.5°	873.9	875.1	876.1	877.1	877.8	878.2	878.5	878.9	879.3	879.1	878.9
145°	921.5	921.9	922.4	922.7	923.3	923.9	924.5	925.2	925.8	925.6	925.4
147.5°	964.0	964.8	965.5	966.3	967.0	967.5	968.1	968.7	969.3	969.3	969.3
150°	993.1	993.4	993.8	994.3	994.7	995.1	995.5	996.0	996.4	996.4	996.4
152.5°	1017.3	1017.9	1018.4	1019.0	1019.5	1019.7	1019.9	1020.2	1020.5	1020.8	1021.2
155°	1054.7	1054.7	1054.7	1054.7	1054.8	1055.0	1055.2	1055.5	1055.6	1056.5	1057.3
157.5°	1086.8	1086.6	1086.3	1086.1	1086.0	1086.2	1086.4	1086.6	1086.7	1087.6	1088.4
160°	1106.9	1106.5	1106.2	1105.7	1105.5	1105.5	1105.5	1105.5	1105.5	1106.5	1107.6
162.5°	1124.8	1124.3	1123.7	1123.1	1122.9	1123.0	1123.2	1123.4	1123.6	1124.6	1125.7
165°	1148.1	1147.5	1146.9	1146.3	1145.9	1145.9	1145.9	1145.9	1145.9	1147.2	1148.5
167.5°	1166.6	1165.7	1164.9	1164.0	1163.8	1163.9	1164.0	1164.2	1164.4	1165.7	1167.0
170°	1177.1	1176.3	1175.4	1174.6	1174.2	1174.2	1174.2	1174.2	1174.2	1175.6	1177.1
172.5°	1185.4	1184.6	1183.7	1182.9	1182.4	1182.4	1182.4	1182.4	1182.4	1183.7	1185.1
175°	1194.0	1193.2	1192.4	1191.6	1191.1	1191.1	1191.1	1191.1	1191.1	1192.4	1193.6
177.5°	1197.8	1197.1	1196.5	1195.8	1195.4	1195.4	1195.4	1195.4	1195.4	1196.5	1197.5
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1215.9	1215.9	1217.5	1223.4	1224.2	1229.4	1227.8
5°	1336.3	1345.7	1349.2	1364.0	1372.8	1376.8	1368.9
7.5°	1483.6	1510.0	1522.6	1538.0	1551.8	1555.9	1545.1
10°	1590.9	1618.5	1641.8	1656.0	1669.4	1678.3	1689.6
12.5°	1694.8	1728.7	1750.8	1770.9	1784.7	1795.9	1797.8
15°	1807.6	1858.9	1897.9	1926.5	1940.8	1948.2	1945.2
17.5°	1921.4	1969.0	1996.7	2025.9	2045.7	2046.7	2047.3
20°	1985.7	2032.1	2064.2	2085.8	2108.1	2107.1	2112.0
22.5°	2028.7	2065.3	2089.8	2105.6	2113.3	2109.5	2110.4
25°	2048.9	2059.7	2055.3	2030.1	2023.7	2000.5	2004.5
27.5°	1945.0	1893.8	1840.6	1772.4	1718.4	1675.5	1677.6
30°	1804.1	1713.4	1609.7	1522.9	1444.9	1423.1	1376.8
32.5°	1607.1	1470.9	1349.5	1268.6	1201.6	1183.6	1143.1
35°	1273.2	1140.9	1016.1	941.0	911.4	870.0	869.5
37.5°	989.6	873.2	807.1	750.8	721.3	696.3	693.8
40°	832.5	741.7	691.8	651.4	622.3	603.5	599.1
42.5°	722.7	649.3	602.7	577.6	555.2	545.4	538.3
45°	590.2	540.8	508.3	485.6	475.2	467.8	463.8
47.5°	493.7	460.6	438.4	423.3	414.9	407.1	409.2
50°	441.2	414.1	397.8	383.4	377.0	371.6	372.1
52.5°	398.9	374.6	361.4	351.1	343.1	339.2	337.3
55°	338.6	323.2	309.9	302.5	298.0	292.7	291.2
57.5°	288.8	276.9	266.1	257.7	256.6	251.4	252.0
60°	255.6	245.7	236.9	232.4	228.9	224.5	226.0
62.5°	228.4	220.1	212.0	208.3	204.9	201.6	202.4
65°	187.0	179.1	174.2	172.2	170.7	169.3	167.8
67.5°	149.0	144.2	141.1	136.9	133.8	133.4	131.9
70°	125.4	118.9	113.5	108.1	106.6	106.1	106.6
72.5°	100.5	96.4	94.9	92.3	92.0	90.7	91.6
75°	75.5	74.0	73.0	71.1	71.1	71.1	71.1
77.5°	55.7	54.8	54.2	53.8	53.3	52.6	52.5
80°	43.5	42.9	41.9	41.9	41.5	41.9	41.5
82.5°	32.8	32.7	31.7	31.7	31.2	30.9	31.2
85°	16.8	16.3	17.2	16.3	16.8	15.8	16.8
87.5°	9.7	9.9	9.6	9.7	9.4	10.3	9.6
90°	25.1	25.9	26.6	27.0	27.4	27.8	28.2
92.5°	38.2	38.8	39.0	38.7	38.5	38.3	38.0
95°	72.1	73.0	73.4	73.4	73.4	73.4	73.4
97.5°	111.9	112.8	113.2	113.2	113.1	113.0	112.9
100°	140.2	140.8	141.4	141.8	142.1	142.6	143.0
102.5°	173.3	173.9	174.2	174.1	174.0	174.0	173.9
105°	222.1	222.1	222.3	222.6	223.1	223.5	223.9
107.5°	276.2	276.8	277.0	276.8	276.5	276.3	276.1
110°	312.1	312.9	313.1	312.6	312.3	311.9	311.4



TEST NUMBER: P332319-830

CATALOG NUMBER: S123RDIP-S775D1025U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	347.9	348.9	349.4	349.3	349.2	349.1	349.0
115°	401.4	401.6	401.6	401.4	401.2	401.1	400.8
117.5°	456.0	456.0	455.6	455.1	454.5	453.9	453.3
120°	492.4	492.2	491.8	491.4	491.1	490.6	490.2
122.5°	529.0	528.5	527.9	527.4	526.7	526.1	525.6
125°	583.6	582.8	581.9	581.2	580.3	579.5	578.6
127.5°	637.6	636.4	635.4	634.4	633.4	632.4	631.5
130°	673.9	673.2	671.9	670.5	669.0	667.6	666.1
132.5°	708.9	707.8	706.8	705.7	704.6	703.4	702.3
135°	761.5	760.6	760.0	759.6	759.1	758.7	758.4
137.5°	812.8	811.8	811.0	810.2	809.4	808.6	807.9
140°	847.1	846.9	846.0	844.6	843.1	841.7	840.2
142.5°	878.7	878.4	877.8	876.7	875.5	874.4	873.3
145°	925.2	924.9	924.4	923.6	922.7	921.9	921.1
147.5°	969.3	969.3	968.7	967.4	966.1	964.9	963.7
150°	996.4	996.4	995.7	994.5	993.3	991.9	990.7
152.5°	1021.4	1021.8	1021.4	1020.3	1019.3	1018.1	1017.1
155°	1058.2	1058.9	1058.7	1057.2	1055.7	1054.2	1052.8
157.5°	1089.3	1090.2	1090.1	1088.9	1087.7	1086.6	1085.3
160°	1108.6	1109.7	1109.7	1109.0	1108.1	1107.3	1106.5
162.5°	1126.7	1127.8	1127.6	1126.2	1124.9	1123.6	1122.3
165°	1149.7	1150.9	1150.8	1149.4	1147.9	1146.5	1145.0
167.5°	1168.3	1169.6	1169.6	1168.3	1167.0	1165.7	1164.4
170°	1178.6	1180.1	1180.1	1178.6	1177.1	1175.6	1174.2
172.5°	1186.4	1187.6	1187.6	1186.1	1184.7	1183.2	1181.7
175°	1194.9	1196.2	1196.0	1194.6	1193.1	1191.7	1190.1
177.5°	1198.4	1199.5	1199.4	1198.3	1197.0	1195.9	1194.7
180°	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7	1197.7

(END OF REPORT)