

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332324-830

Luminaire Tested: **S123RDIP-S775D1195U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332324-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1195U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7369.1 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39																				
1	96	92	88	85	87	84	80	78	68	66	64	54	53	52	41	40	40	34																				
2	88	81	75	70	79	74	69	64	60	57	54	48	46	44	37	35	34	29																				
3	80	71	64	59	73	65	59	54	54	49	46	43	40	38	33	31	30	25																				
4	73	63	56	50	67	58	51	46	48	43	39	39	35	32	30	28	26	22																				
5	68	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19																				
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	22	20	17																				
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15																				
8	53	42	34	29	49	38	32	27	32	27	24	26	23	20	21	18	16	14																				
9	50	38	31	26	45	35	29	24	30	25	21	24	21	18	19	17	15	13																				
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12408	12408	12408	12408
5°	14791	12460	10974	12460
10°	18467	12389	9913	12389
15°	21677	12262	9040	12262
20°	24192	12073	8298	12073
25°	23807	11874	7842	11874
30°	17112	11691	7372	11691
35°	11426	11452	7068	11452
40°	8418	11164	6753	11164
45°	7060	10659	6445	10659
50°	6231	9999	6015	9999
55°	5465	9242	5427	9242
60°	4865	8521	4971	8521
65°	4274	7743	4625	7743
70°	3355	7050	4223	7050
75°	2957	6159	3855	6159
80°	2572	5232	3794	5232
85°	2075	4199	4026	4199



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.4	1.5
10°-20°	354.2	4.8
20°-30°	556.4	7.6
30°-40°	580.5	7.9
40°-50°	496.8	6.7
50°-60°	378.6	5.1
60°-70°	242.7	3.3
70°-80°	116.7	1.6
80°-90°	35.0	0.5
90°-100°	53.6	0.7
100°-110°	255.4	3.5
110°-120°	613.5	8.3
120°-130°	781.2	10.6
130°-140°	834.7	11.3
140°-150°	780.5	10.6
150°-160°	629.6	8.5
160°-170°	406.3	5.5
170°-180°	140.0	1.9
0°-30°	1023.9	13.9
0°-40°	1604.4	21.8
0°-60°	2479.8	33.7
0°-90°	2874.3	39.0
90°-120°	922.4	12.5
90°-150°	3318.8	45.0
90°-180°	4495.0	61.0
0°-180°	7369.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1153	1153	1153	1153	1153	
5°	1369	1153	1016	1153	1369	141
15°	1945	1100	811	1100	1945	552
25°	2004	1000	660	1000	2004	862
35°	870	872	538	872	870	570
45°	464	700	423	700	464	365
55°	291	492	289	492	291	263
65°	168	304	182	304	168	165
75°	71	148	93	148	71	76
85°	17	34	33	34	17	20
90°	33	1	33	1	33	15
95°	42	67	42	67	42	35
105°	48	326	48	326	48	110
115°	644	612	644	612	644	595
125°	880	863	880	863	880	786
135°	1085	1074	1085	1074	1085	837
145°	1252	1240	1252	1240	1252	781
155°	1363	1366	1363	1366	1363	629
165°	1437	1440	1437	1440	1437	406
175°	1468	1474	1468	1474	1468	140
180°	1474	1474	1474	1474	1474	



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1227.8	1229.4	1224.2	1223.4	1217.5	1215.9	1215.9	1207.6	1202.5	1195.8	1191.8
5°	1368.9	1376.8	1372.8	1364.0	1349.2	1345.7	1336.3	1321.5	1304.8	1284.0	1274.1
7.5°	1545.1	1555.9	1551.8	1538.0	1522.6	1510.0	1483.6	1459.0	1424.6	1394.3	1368.5
10°	1689.6	1678.3	1669.4	1656.0	1641.8	1618.5	1590.9	1552.9	1509.0	1474.5	1436.0
12.5°	1797.8	1795.9	1784.7	1770.9	1750.8	1728.7	1694.8	1648.5	1597.4	1547.6	1503.5
15°	1945.2	1948.2	1940.8	1926.5	1897.9	1858.9	1807.6	1788.3	1715.3	1661.0	1606.8
17.5°	2047.3	2046.7	2045.7	2025.9	1996.7	1969.0	1921.4	1870.8	1804.6	1728.2	1655.0
20°	2112.0	2107.1	2108.1	2085.8	2064.2	2032.1	1985.7	1912.2	1857.9	1769.6	1694.0
22.5°	2110.4	2109.5	2113.3	2105.6	2089.8	2065.3	2028.7	1966.7	1897.4	1808.3	1723.3
25°	2004.5	2000.5	2023.7	2030.1	2055.3	2059.7	2048.9	2014.9	1949.2	1857.4	1752.3
27.5°	1677.6	1675.5	1718.4	1772.4	1840.6	1893.8	1945.0	1969.8	1949.2	1883.5	1778.2
30°	1376.8	1423.1	1444.9	1522.9	1609.7	1713.4	1804.1	1890.5	1911.7	1883.1	1796.7
32.5°	1143.1	1183.6	1201.6	1268.6	1349.5	1470.9	1607.1	1729.4	1815.8	1837.7	1785.6
35°	869.5	870.0	911.4	941.0	1016.1	1140.9	1273.2	1437.0	1599.8	1723.2	1736.0
37.5°	693.8	696.3	721.3	750.8	807.1	873.2	989.6	1125.8	1313.9	1503.3	1614.3
40°	599.1	603.5	622.3	651.4	691.8	741.7	832.5	960.8	1117.7	1328.4	1500.6
42.5°	538.3	545.4	555.2	577.6	602.7	649.3	722.7	821.8	964.5	1163.8	1362.4
45°	463.8	467.8	475.2	485.6	508.3	540.8	590.2	656.8	775.2	935.7	1134.4
47.5°	409.2	407.1	414.9	423.3	438.4	460.6	493.7	548.1	632.5	761.2	929.9
50°	372.1	371.6	377.0	383.4	397.8	414.1	441.2	482.1	549.2	655.8	810.3
52.5°	337.3	339.2	343.1	351.1	361.4	374.6	398.9	428.4	486.1	578.1	706.8
55°	291.2	292.7	298.0	302.5	309.9	323.2	338.6	363.2	402.7	466.8	572.9
57.5°	252.0	251.4	256.6	257.7	266.1	276.9	288.8	307.9	336.6	384.2	455.6
60°	226.0	224.5	228.9	232.4	236.9	245.7	255.6	274.4	297.1	332.1	393.3
62.5°	202.4	201.6	204.9	208.3	212.0	220.1	228.4	242.8	260.7	290.3	338.8
65°	167.8	169.3	170.7	172.2	174.2	179.1	187.0	196.9	209.2	230.0	264.9
67.5°	131.9	133.4	133.8	136.9	141.1	144.2	149.0	157.8	166.4	183.9	203.8
70°	106.6	106.1	106.6	108.1	113.5	118.9	125.4	131.8	137.1	149.5	166.3
72.5°	91.6	90.7	92.0	92.3	94.9	96.4	100.5	106.5	113.5	121.9	133.9
75°	71.1	71.1	71.1	71.1	73.0	74.0	75.5	77.0	79.5	83.4	92.3
77.5°	52.5	52.6	53.3	53.8	54.2	54.8	55.7	57.1	58.1	60.1	64.0
80°	41.5	41.9	41.5	41.9	41.9	42.9	43.5	44.9	45.4	47.9	49.4
82.5°	31.2	30.9	31.2	31.7	31.7	32.7	32.8	33.8	33.9	35.3	36.8
85°	16.8	15.8	16.8	16.3	17.2	16.3	16.8	17.7	17.7	18.3	20.3
87.5°	10.6	11.2	10.4	10.7	10.6	10.7	10.6	10.4	10.9	10.4	10.2
90°	32.9	32.3	31.9	31.4	30.9	30.2	29.2	28.2	27.2	26.3	23.1
92.5°	36.4	36.1	35.8	35.4	35.2	34.3	32.7	31.1	29.6	28.0	25.6
95°	41.6	41.6	41.6	41.6	41.6	40.7	39.0	37.3	35.6	33.9	31.3
97.5°	45.1	44.9	44.7	44.4	44.1	43.1	41.1	39.1	37.2	35.3	32.8
100°	46.0	45.7	45.5	45.2	45.1	43.9	41.9	40.1	38.1	36.1	34.1
102.5°	46.8	46.5	46.0	45.5	45.1	47.9	53.9	59.9	66.0	72.0	113.5
105°	48.2	47.7	47.2	46.8	46.3	67.5	110.6	153.6	196.7	239.8	261.7
107.5°	151.4	183.8	216.2	248.7	281.2	313.2	344.8	376.4	407.9	439.6	436.1
110°	301.1	335.9	370.7	405.6	440.4	461.8	469.8	477.8	485.9	493.9	491.2



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	516.6	524.0	531.3	538.7	546.0	549.7	549.5	549.3	549.2	549.0	546.4
115°	643.9	642.9	642.0	640.9	640.0	638.3	635.8	633.4	631.0	628.6	626.4
117.5°	715.3	715.1	714.9	714.7	714.5	713.4	711.5	709.5	707.6	705.7	704.6
120°	764.3	764.3	764.3	764.3	764.3	763.4	761.4	759.5	757.5	755.5	754.9
122.5°	812.6	812.4	812.1	811.9	811.7	811.0	809.6	808.2	806.9	805.5	804.6
125°	880.4	880.0	879.5	878.9	878.4	878.0	877.5	877.0	876.6	876.0	875.1
127.5°	945.7	946.2	946.7	947.2	947.6	947.4	946.7	945.9	945.2	944.3	943.2
130°	987.8	988.3	988.7	989.2	989.7	989.5	988.4	987.5	986.6	985.5	984.6
132.5°	1026.2	1027.0	1027.7	1028.3	1029.0	1028.9	1027.9	1026.9	1026.0	1025.0	1024.2
135°	1085.2	1085.9	1086.7	1087.4	1088.2	1088.2	1087.4	1086.7	1085.9	1085.2	1084.2
137.5°	1140.6	1141.1	1141.6	1142.1	1142.6	1142.2	1141.0	1139.9	1138.7	1137.6	1137.0
140°	1173.9	1174.4	1174.9	1175.4	1175.8	1175.6	1174.6	1173.7	1172.7	1171.7	1171.0
142.5°	1204.6	1205.2	1205.9	1206.6	1207.3	1207.2	1206.5	1205.7	1204.9	1204.1	1203.4
145°	1251.6	1251.6	1251.6	1251.6	1251.6	1251.4	1250.9	1250.5	1249.9	1249.4	1249.0
147.5°	1286.7	1287.8	1288.9	1290.1	1291.2	1291.5	1291.0	1290.5	1290.1	1289.5	1289.0
150°	1313.0	1313.7	1314.5	1315.1	1315.9	1316.0	1315.5	1315.0	1314.6	1314.1	1313.6
152.5°	1334.0	1335.1	1336.2	1337.4	1338.5	1338.6	1337.8	1336.8	1336.0	1335.1	1334.8
155°	1363.4	1364.8	1366.3	1367.7	1369.1	1369.3	1368.1	1366.9	1365.6	1364.4	1364.2
157.5°	1388.1	1390.0	1391.9	1393.8	1395.7	1395.9	1394.4	1393.0	1391.6	1390.1	1390.3
160°	1403.8	1405.5	1407.3	1409.0	1410.7	1410.8	1409.3	1407.9	1406.5	1405.0	1405.2
162.5°	1418.7	1420.2	1421.7	1423.2	1424.7	1424.7	1423.1	1421.4	1419.8	1418.1	1418.3
165°	1436.7	1438.4	1440.1	1441.8	1443.5	1443.4	1441.4	1439.5	1437.6	1435.6	1435.9
167.5°	1449.6	1451.6	1453.5	1455.5	1457.5	1457.5	1455.5	1453.5	1451.6	1449.6	1449.6
170°	1457.5	1459.4	1461.4	1463.4	1465.3	1465.3	1463.4	1461.4	1459.4	1457.5	1457.5
172.5°	1461.9	1464.1	1466.2	1468.3	1470.5	1470.6	1468.6	1466.7	1464.7	1462.7	1462.5
175°	1468.5	1470.5	1472.3	1474.3	1476.2	1476.4	1474.7	1473.0	1471.3	1469.5	1469.3
177.5°	1470.5	1472.3	1474.3	1476.3	1478.2	1478.4	1476.9	1475.3	1473.8	1472.2	1472.0
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1190.2	1189.0	1183.6	1177.2	1168.9	1163.4	1159.0	1156.7	1149.6	1140.9	1135.0
5°	1263.8	1249.0	1233.2	1213.9	1196.2	1177.9	1166.6	1153.2	1137.0	1118.7	1105.9
7.5°	1342.6	1313.5	1282.2	1250.0	1218.0	1189.5	1164.2	1142.6	1116.6	1090.4	1072.1
10°	1403.0	1360.5	1316.5	1271.7	1230.7	1192.2	1162.6	1133.5	1102.4	1072.3	1049.6
12.5°	1457.8	1401.9	1351.3	1296.2	1243.8	1197.8	1155.1	1120.9	1083.5	1051.4	1025.5
15°	1527.3	1470.1	1408.8	1324.9	1255.4	1197.1	1145.4	1100.4	1055.1	1015.6	990.4
17.5°	1592.2	1506.1	1423.9	1353.9	1263.5	1190.7	1127.5	1073.7	1024.0	982.1	951.1
20°	1619.1	1535.7	1446.3	1357.1	1268.2	1186.8	1113.2	1054.0	1002.2	954.9	926.2
22.5°	1635.2	1540.8	1446.7	1350.8	1256.4	1171.8	1099.1	1033.9	977.8	932.7	897.4
25°	1654.1	1541.6	1437.9	1343.2	1247.0	1155.2	1068.8	999.8	939.1	891.2	853.7
27.5°	1666.5	1534.2	1411.7	1306.4	1208.8	1117.4	1038.2	965.1	903.4	852.8	812.6
30°	1668.9	1528.2	1391.6	1277.6	1178.4	1094.5	1010.6	940.6	875.4	821.6	784.1
32.5°	1672.1	1513.6	1364.3	1243.2	1141.7	1058.6	982.6	915.7	848.9	796.0	757.7
35°	1659.1	1505.6	1323.0	1183.8	1082.1	1001.7	933.1	871.5	805.9	754.5	715.5
37.5°	1603.0	1473.5	1280.2	1116.9	1010.6	936.1	880.2	826.4	766.3	710.9	674.2
40°	1546.5	1441.9	1247.0	1076.3	965.3	888.7	838.4	794.5	736.2	684.5	645.0
42.5°	1462.4	1398.9	1215.4	1033.6	913.9	840.2	797.8	756.6	705.5	652.9	615.8
45°	1308.2	1316.5	1150.8	965.7	842.8	768.8	728.9	700.2	654.9	611.4	573.4
47.5°	1114.7	1193.2	1074.9	893.3	767.9	698.4	663.5	638.6	607.9	565.3	530.7
50°	988.4	1100.4	1014.1	844.8	721.0	651.9	617.4	597.1	570.4	536.9	503.8
52.5°	871.9	992.3	940.7	790.7	670.1	606.9	573.2	556.5	535.3	503.7	473.8
55°	711.1	833.0	821.1	709.1	593.6	536.9	511.2	492.5	478.2	454.5	430.8
57.5°	575.2	690.8	696.9	618.3	526.3	470.2	448.2	434.0	424.7	406.8	384.9
60°	489.6	595.6	616.3	557.1	478.2	428.9	407.1	395.8	388.3	374.1	357.3
62.5°	418.5	508.8	532.3	489.7	432.0	385.8	368.8	357.9	352.8	340.4	325.6
65°	320.3	395.3	417.9	394.3	364.2	327.2	313.4	304.0	299.5	292.7	281.7
67.5°	240.8	295.5	320.4	303.7	292.8	269.5	260.6	255.6	251.7	246.9	237.9
70°	193.4	233.9	259.6	255.1	246.3	233.9	227.5	224.0	220.1	216.1	208.2
72.5°	155.5	183.4	207.5	209.7	202.5	199.9	194.4	192.8	190.5	185.8	181.4
75°	103.1	122.3	139.1	145.5	148.5	151.0	148.5	148.1	147.5	143.6	141.1
77.5°	67.6	77.9	88.5	99.4	104.2	107.4	108.3	110.1	108.8	106.7	105.5
80°	51.8	54.3	61.6	71.1	78.4	81.4	83.4	84.4	83.9	83.4	81.4
82.5°	37.6	39.7	43.2	49.8	56.0	60.9	62.1	61.9	63.0	63.2	61.6
85°	20.3	20.7	21.7	22.7	26.1	31.6	33.1	34.0	35.1	35.1	32.0
87.5°	10.3	9.2	9.4	8.9	9.6	9.5	11.4	12.8	13.8	12.6	13.1
90°	20.0	16.8	13.7	10.8	8.4	5.9	3.5	1.1	3.5	5.9	8.4
92.5°	23.3	20.9	18.5	17.6	18.3	19.0	19.7	20.4	19.7	19.0	18.3
95°	28.6	25.9	23.3	26.9	36.9	46.8	56.8	66.8	56.8	46.8	36.9
97.5°	70.3	87.8	105.4	116.3	120.8	125.3	129.8	134.2	129.8	125.3	120.8
100°	112.1	150.1	187.9	204.5	199.6	194.8	189.9	185.0	189.9	194.8	199.6
102.5°	155.0	196.4	237.9	256.9	253.4	249.9	246.4	242.9	246.4	249.9	253.4
105°	283.6	305.5	327.4	337.1	334.3	331.7	329.0	326.3	329.0	331.7	334.3
107.5°	432.6	429.2	425.7	422.9	420.8	418.7	416.5	414.3	416.5	418.7	420.8
110°	488.5	485.9	483.1	480.9	478.9	476.9	475.0	473.1	475.0	476.9	478.9



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	543.8	541.0	538.4	536.1	534.4	532.6	530.8	529.1	530.8	532.6	534.4
115°	624.2	622.0	619.8	617.9	616.5	615.0	613.6	612.2	613.6	615.0	616.5
117.5°	703.4	702.3	701.2	699.7	698.0	696.1	694.3	692.5	694.3	696.1	698.0
120°	754.1	753.4	752.7	751.2	749.0	746.9	744.6	742.4	744.6	746.9	749.0
122.5°	803.7	802.8	801.8	800.5	798.6	796.8	795.0	793.2	795.0	796.8	798.6
125°	874.1	873.1	872.1	870.7	868.7	866.8	864.9	862.9	864.9	866.8	868.7
127.5°	942.1	940.8	939.7	938.1	936.2	934.2	932.3	930.4	932.3	934.2	936.2
130°	983.6	982.6	981.7	980.1	978.3	976.3	974.4	972.4	974.4	976.3	978.3
132.5°	1023.4	1022.7	1021.8	1020.5	1018.5	1016.6	1014.6	1012.7	1014.6	1016.6	1018.5
135°	1083.3	1082.3	1081.3	1080.1	1078.6	1077.1	1075.7	1074.2	1075.7	1077.1	1078.6
137.5°	1136.5	1136.0	1135.4	1134.3	1132.4	1130.5	1128.7	1126.8	1128.7	1130.5	1132.4
140°	1170.3	1169.5	1168.8	1167.7	1166.2	1164.8	1163.3	1161.9	1163.3	1164.8	1166.2
142.5°	1202.7	1201.9	1201.2	1200.1	1198.6	1197.2	1195.7	1194.3	1195.7	1197.2	1198.6
145°	1248.5	1248.0	1247.5	1246.4	1244.7	1243.0	1241.3	1239.6	1241.3	1243.0	1244.7
147.5°	1288.5	1288.1	1287.6	1286.8	1285.6	1284.6	1283.5	1282.3	1283.5	1284.6	1285.6
150°	1313.1	1312.6	1312.1	1311.5	1310.8	1310.0	1309.3	1308.6	1309.3	1310.0	1310.8
152.5°	1334.5	1334.2	1333.9	1333.6	1333.2	1332.9	1332.6	1332.3	1332.6	1332.9	1333.2
155°	1364.0	1363.7	1363.5	1363.6	1364.0	1364.5	1365.1	1365.6	1365.1	1364.5	1364.0
157.5°	1390.5	1390.8	1391.0	1391.2	1391.2	1391.3	1391.3	1391.4	1391.3	1391.3	1391.2
160°	1405.4	1405.7	1405.9	1406.2	1406.5	1406.7	1406.9	1407.1	1406.9	1406.7	1406.5
162.5°	1418.6	1418.8	1419.1	1419.5	1420.1	1420.8	1421.4	1422.0	1421.4	1420.8	1420.1
165°	1436.1	1436.3	1436.6	1437.1	1437.8	1438.5	1439.3	1440.0	1439.3	1438.5	1437.8
167.5°	1449.6	1449.6	1449.6	1450.1	1451.1	1452.1	1453.0	1454.1	1453.0	1452.1	1451.1
170°	1457.5	1457.5	1457.5	1458.0	1459.0	1460.0	1460.9	1461.9	1460.9	1460.0	1459.0
172.5°	1462.4	1462.2	1462.0	1462.4	1463.7	1464.8	1466.0	1467.2	1466.0	1464.8	1463.7
175°	1469.0	1468.9	1468.6	1469.0	1470.3	1471.5	1472.7	1473.9	1472.7	1471.5	1470.3
177.5°	1471.8	1471.6	1471.4	1471.8	1472.8	1473.8	1474.7	1475.7	1474.7	1473.8	1472.8
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1133.0	1127.8	1124.4	1116.4	1111.3	1105.8	1100.2	1103.8	1103.4	1103.0	1103.0
5°	1095.0	1083.6	1073.3	1060.0	1051.6	1041.2	1033.3	1032.4	1034.3	1027.4	1023.4
7.5°	1057.3	1041.8	1027.1	1012.4	996.8	984.4	976.6	972.9	967.9	963.7	959.2
10°	1030.9	1012.6	998.2	980.1	963.3	948.5	939.1	932.6	929.2	925.8	919.4
12.5°	1003.6	985.7	967.5	946.9	930.9	913.7	906.7	899.5	892.9	889.0	880.2
15°	963.7	940.6	921.3	899.6	881.8	865.1	855.2	840.8	838.9	834.0	825.1
17.5°	923.8	898.6	872.0	856.0	835.9	818.5	803.4	798.6	784.5	779.2	771.5
20°	892.2	869.0	848.8	827.6	798.4	782.1	770.3	763.9	752.5	745.6	740.6
22.5°	865.0	841.4	817.9	793.2	769.2	750.9	742.3	732.3	726.1	716.4	711.1
25°	826.0	800.4	772.3	745.6	728.4	714.5	700.7	691.8	683.0	678.5	668.6
27.5°	780.9	754.0	727.7	707.6	686.4	672.7	660.2	652.2	641.6	634.1	628.7
30°	756.0	724.4	701.7	683.4	656.3	643.5	634.1	624.2	616.3	608.4	603.0
32.5°	727.2	698.3	676.8	654.2	633.4	619.4	607.3	598.6	591.8	584.4	578.9
35°	681.9	657.8	635.6	612.8	597.6	583.2	569.0	561.6	555.2	548.3	543.3
37.5°	641.1	618.5	597.4	575.9	556.9	545.3	533.8	528.1	519.4	514.8	509.7
40°	615.9	593.6	570.9	550.3	530.5	521.6	511.2	502.8	494.9	491.5	486.1
42.5°	588.2	566.0	546.9	524.5	508.4	496.3	486.7	477.6	471.6	466.7	463.5
45°	547.2	527.5	508.8	486.5	471.3	460.9	450.1	441.7	436.2	432.8	427.3
47.5°	507.5	487.8	468.7	449.3	434.5	422.7	411.9	406.0	398.8	394.5	391.0
50°	478.6	460.9	440.6	422.9	408.1	396.2	387.4	379.9	373.5	368.2	365.7
52.5°	452.2	433.3	415.8	399.3	383.6	370.2	362.1	354.3	349.5	343.3	340.4
55°	408.6	390.3	375.5	359.2	343.9	332.6	322.7	315.8	310.9	304.0	300.0
57.5°	367.6	351.3	333.6	319.4	303.7	294.1	285.9	276.5	270.5	265.1	261.3
60°	340.0	321.2	305.9	292.7	278.8	266.5	259.1	251.7	245.2	239.8	236.4
62.5°	311.2	294.8	280.3	265.8	253.2	242.4	233.8	227.6	222.0	218.5	215.1
65°	266.9	254.1	239.3	227.5	215.7	207.7	200.9	195.4	191.4	189.0	186.1
67.5°	226.3	213.9	201.0	189.3	181.4	175.4	170.9	166.2	164.2	161.1	159.1
70°	199.8	187.0	175.7	166.8	158.9	154.5	151.5	148.1	146.1	142.1	140.2
72.5°	171.1	161.7	153.5	146.3	140.0	135.9	132.1	127.9	124.8	120.4	118.5
75°	134.7	126.3	119.9	115.0	111.0	105.6	100.2	95.8	94.3	92.7	92.3
77.5°	99.8	94.4	89.8	85.7	80.8	76.8	75.6	74.6	74.3	73.5	73.5
80°	78.4	73.5	70.0	65.1	62.2	62.2	62.2	61.2	61.6	61.6	61.6
82.5°	58.3	53.8	51.9	50.1	49.6	50.0	50.0	50.1	49.9	50.6	50.2
85°	30.1	30.6	31.6	31.1	31.6	31.6	32.6	32.0	32.6	31.6	32.6
87.5°	13.2	15.0	16.0	17.1	18.0	18.3	18.9	19.0	19.7	19.9	20.0
90°	10.8	13.7	16.8	20.0	23.1	26.3	27.2	28.2	29.2	30.2	30.9
92.5°	17.6	18.5	20.9	23.3	25.6	28.0	29.6	31.1	32.7	34.3	35.2
95°	26.9	23.3	25.9	28.6	31.3	33.9	35.6	37.3	39.0	40.7	41.6
97.5°	116.3	105.4	87.8	70.3	52.8	35.3	37.2	39.1	41.1	43.1	44.1
100°	204.5	187.9	150.1	112.1	74.1	36.1	38.1	40.1	41.9	43.9	45.1
102.5°	256.9	237.9	196.4	155.0	113.5	72.0	66.0	59.9	53.9	47.9	45.1
105°	337.1	327.4	305.5	283.6	261.7	239.8	196.7	153.6	110.6	67.5	46.3
107.5°	422.9	425.7	429.2	432.6	436.1	439.6	407.9	376.4	344.8	313.2	281.2
110°	480.9	483.1	485.9	488.5	491.2	493.9	485.9	477.8	469.8	461.8	440.4



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	536.1	538.4	541.0	543.8	546.4	549.0	549.2	549.3	549.5	549.7	546.0
115°	617.9	619.8	622.0	624.2	626.4	628.6	631.0	633.4	635.8	638.3	640.0
117.5°	699.7	701.2	702.3	703.4	704.6	705.7	707.6	709.5	711.5	713.4	714.5
120°	751.2	752.7	753.4	754.1	754.9	755.5	757.5	759.5	761.4	763.4	764.3
122.5°	800.5	801.8	802.8	803.7	804.6	805.5	806.9	808.2	809.6	811.0	811.7
125°	870.7	872.1	873.1	874.1	875.1	876.0	876.6	877.0	877.5	878.0	878.4
127.5°	938.1	939.7	940.8	942.1	943.2	944.3	945.2	945.9	946.7	947.4	947.6
130°	980.1	981.7	982.6	983.6	984.6	985.5	986.6	987.5	988.4	989.5	989.7
132.5°	1020.5	1021.8	1022.7	1023.4	1024.2	1025.0	1026.0	1026.9	1027.9	1028.9	1029.0
135°	1080.1	1081.3	1082.3	1083.3	1084.2	1085.2	1085.9	1086.7	1087.4	1088.2	1088.2
137.5°	1134.3	1135.4	1136.0	1136.5	1137.0	1137.6	1138.7	1139.9	1141.0	1142.2	1142.6
140°	1167.7	1168.8	1169.5	1170.3	1171.0	1171.7	1172.7	1173.7	1174.6	1175.6	1175.8
142.5°	1200.1	1201.2	1201.9	1202.7	1203.4	1204.1	1204.9	1205.7	1206.5	1207.2	1207.3
145°	1246.4	1247.5	1248.0	1248.5	1249.0	1249.4	1249.9	1250.5	1250.9	1251.4	1251.6
147.5°	1286.8	1287.6	1288.1	1288.5	1289.0	1289.5	1290.1	1290.5	1291.0	1291.5	1291.2
150°	1311.5	1312.1	1312.6	1313.1	1313.6	1314.1	1314.6	1315.0	1315.5	1316.0	1315.9
152.5°	1333.6	1333.9	1334.2	1334.5	1334.8	1335.1	1336.0	1336.8	1337.8	1338.6	1338.5
155°	1363.6	1363.5	1363.7	1364.0	1364.2	1364.4	1365.6	1366.9	1368.1	1369.3	1369.1
157.5°	1391.2	1391.0	1390.8	1390.5	1390.3	1390.1	1391.6	1393.0	1394.4	1395.9	1395.7
160°	1406.2	1405.9	1405.7	1405.4	1405.2	1405.0	1406.5	1407.9	1409.3	1410.8	1410.7
162.5°	1419.5	1419.1	1418.8	1418.6	1418.3	1418.1	1419.8	1421.4	1423.1	1424.7	1424.7
165°	1437.1	1436.6	1436.3	1436.1	1435.9	1435.6	1437.6	1439.5	1441.4	1443.4	1443.5
167.5°	1450.1	1449.6	1449.6	1449.6	1449.6	1449.6	1451.6	1453.5	1455.5	1457.5	1457.5
170°	1458.0	1457.5	1457.5	1457.5	1457.5	1457.5	1459.4	1461.4	1463.4	1465.3	1465.3
172.5°	1462.4	1462.0	1462.2	1462.4	1462.5	1462.7	1464.7	1466.7	1468.6	1470.6	1470.5
175°	1469.0	1468.6	1468.9	1469.0	1469.3	1469.5	1471.3	1473.0	1474.7	1476.4	1476.2
177.5°	1471.8	1471.4	1471.6	1471.8	1472.0	1472.2	1473.8	1475.3	1476.9	1478.4	1478.2
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1098.3	1097.9	1098.3	1096.6	1098.3	1097.9	1098.3	1103.0	1103.0	1103.4	1103.8
5°	1022.0	1021.4	1020.0	1015.6	1020.0	1021.4	1022.0	1023.4	1027.4	1034.3	1032.4
7.5°	955.4	954.7	950.4	950.5	950.4	954.7	955.4	959.2	963.7	967.9	972.9
10°	915.9	916.3	910.5	907.0	910.5	916.3	915.9	919.4	925.8	929.2	932.6
12.5°	877.6	875.3	870.5	866.8	870.5	875.3	877.6	880.2	889.0	892.9	899.5
15°	827.1	822.1	810.3	811.2	810.3	822.1	827.1	825.1	834.0	838.9	840.8
17.5°	767.5	763.9	763.6	756.8	763.6	763.9	767.5	771.5	779.2	784.5	798.6
20°	732.8	730.4	731.3	724.4	731.3	730.4	732.8	740.6	745.6	752.5	763.9
22.5°	705.6	703.1	699.0	696.8	699.0	703.1	705.6	711.1	716.4	726.1	732.3
25°	665.7	661.8	657.8	660.3	657.8	661.8	665.7	668.6	678.5	683.0	691.8
27.5°	625.8	622.8	618.9	618.4	618.9	622.8	625.8	628.7	634.1	641.6	652.2
30°	600.6	597.6	595.6	593.1	595.6	597.6	600.6	603.0	608.4	616.3	624.2
32.5°	574.9	574.3	570.7	570.2	570.7	574.3	574.9	578.9	584.4	591.8	598.6
35°	541.3	538.4	537.3	537.9	537.3	538.4	541.3	543.3	548.3	555.2	561.6
37.5°	509.4	505.5	503.7	502.0	503.7	505.5	509.4	509.7	514.8	519.4	528.1
40°	486.5	482.6	481.6	480.6	481.6	482.6	486.5	486.1	491.5	494.9	502.8
42.5°	460.9	459.3	458.7	456.9	458.7	459.3	460.9	463.5	466.7	471.6	477.6
45°	425.8	425.4	422.4	423.4	422.4	425.4	425.8	427.3	432.8	436.2	441.7
47.5°	389.0	386.8	384.7	386.1	384.7	386.8	389.0	391.0	394.5	398.8	406.0
50°	363.7	362.7	358.3	359.2	358.3	362.7	363.7	365.7	368.2	373.5	379.9
52.5°	338.5	334.7	333.0	332.4	333.0	334.7	338.5	340.4	343.3	349.5	354.3
55°	296.6	292.1	290.1	289.2	290.1	292.1	296.6	300.0	304.0	310.9	315.8
57.5°	255.5	254.3	252.8	253.8	252.8	254.3	255.5	261.3	265.1	270.5	276.5
60°	231.4	231.4	231.4	230.9	231.4	231.4	231.4	236.4	239.8	245.2	251.7
62.5°	212.9	211.7	211.3	212.0	211.3	211.7	212.9	215.1	218.5	222.0	227.6
65°	184.5	184.1	182.1	181.6	182.1	184.1	184.5	186.1	189.0	191.4	195.4
67.5°	157.8	156.0	155.4	154.8	155.4	156.0	157.8	159.1	161.1	164.2	166.2
70°	137.7	136.7	133.7	134.2	133.7	136.7	137.7	140.2	142.1	146.1	148.1
72.5°	115.9	115.0	114.4	113.7	114.4	115.0	115.9	118.5	120.4	124.8	127.9
75°	91.8	91.3	90.8	92.7	90.8	91.3	91.8	92.3	92.7	94.3	95.8
77.5°	73.5	73.5	73.8	73.0	73.8	73.5	73.5	73.5	73.5	74.3	74.6
80°	61.6	61.6	61.2	61.2	61.2	61.6	61.6	61.6	61.6	61.6	61.2
82.5°	49.5	49.9	50.1	49.4	50.1	49.9	49.5	50.2	50.6	49.9	50.1
85°	32.6	32.0	33.1	32.6	33.1	32.0	32.6	32.6	31.6	32.6	32.0
87.5°	20.9	20.2	20.3	20.7	20.3	20.2	20.9	20.0	19.9	19.7	19.0
90°	31.4	31.9	32.3	32.9	32.3	31.9	31.4	30.9	30.2	29.2	28.2
92.5°	35.4	35.8	36.1	36.4	36.1	35.8	35.4	35.2	34.3	32.7	31.1
95°	41.6	41.6	41.6	41.6	41.6	41.6	41.6	41.6	40.7	39.0	37.3
97.5°	44.4	44.7	44.9	45.1	44.9	44.7	44.4	44.1	43.1	41.1	39.1
100°	45.2	45.5	45.7	46.0	45.7	45.5	45.2	45.1	43.9	41.9	40.1
102.5°	45.5	46.0	46.5	46.8	46.5	46.0	45.5	45.1	47.9	53.9	59.9
105°	46.8	47.2	47.7	48.2	47.7	47.2	46.8	46.3	67.5	110.6	153.6
107.5°	248.7	216.2	183.8	151.4	183.8	216.2	248.7	281.2	313.2	344.8	376.4
110°	405.6	370.7	335.9	301.1	335.9	370.7	405.6	440.4	461.8	469.8	477.8



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	538.7	531.3	524.0	516.6	524.0	531.3	538.7	546.0	549.7	549.5	549.3
115°	640.9	642.0	642.9	643.9	642.9	642.0	640.9	640.0	638.3	635.8	633.4
117.5°	714.7	714.9	715.1	715.3	715.1	714.9	714.7	714.5	713.4	711.5	709.5
120°	764.3	764.3	764.3	764.3	764.3	764.3	764.3	764.3	763.4	761.4	759.5
122.5°	811.9	812.1	812.4	812.6	812.4	812.1	811.9	811.7	811.0	809.6	808.2
125°	878.9	879.5	880.0	880.4	880.0	879.5	878.9	878.4	878.0	877.5	877.0
127.5°	947.2	946.7	946.2	945.7	946.2	946.7	947.2	947.6	947.4	946.7	945.9
130°	989.2	988.7	988.3	987.8	988.3	988.7	989.2	989.7	989.5	988.4	987.5
132.5°	1028.3	1027.7	1027.0	1026.2	1027.0	1027.7	1028.3	1029.0	1028.9	1027.9	1026.9
135°	1087.4	1086.7	1085.9	1085.2	1085.9	1086.7	1087.4	1088.2	1088.2	1087.4	1086.7
137.5°	1142.1	1141.6	1141.1	1140.6	1141.1	1141.6	1142.1	1142.6	1142.2	1141.0	1139.9
140°	1175.4	1174.9	1174.4	1173.9	1174.4	1174.9	1175.4	1175.8	1175.6	1174.6	1173.7
142.5°	1206.6	1205.9	1205.2	1204.6	1205.2	1205.9	1206.6	1207.3	1207.2	1206.5	1205.7
145°	1251.6	1251.6	1251.6	1251.6	1251.6	1251.6	1251.6	1251.6	1251.4	1250.9	1250.5
147.5°	1290.1	1288.9	1287.8	1286.7	1287.8	1288.9	1290.1	1291.2	1291.5	1291.0	1290.5
150°	1315.1	1314.5	1313.7	1313.0	1313.7	1314.5	1315.1	1315.9	1316.0	1315.5	1315.0
152.5°	1337.4	1336.2	1335.1	1334.0	1335.1	1336.2	1337.4	1338.5	1338.6	1337.8	1336.8
155°	1367.7	1366.3	1364.8	1363.4	1364.8	1366.3	1367.7	1369.1	1369.3	1368.1	1366.9
157.5°	1393.8	1391.9	1390.0	1388.1	1390.0	1391.9	1393.8	1395.7	1395.9	1394.4	1393.0
160°	1409.0	1407.3	1405.5	1403.8	1405.5	1407.3	1409.0	1410.7	1410.8	1409.3	1407.9
162.5°	1423.2	1421.7	1420.2	1418.7	1420.2	1421.7	1423.2	1424.7	1424.7	1423.1	1421.4
165°	1441.8	1440.1	1438.4	1436.7	1438.4	1440.1	1441.8	1443.5	1443.4	1441.4	1439.5
167.5°	1455.5	1453.5	1451.6	1449.6	1451.6	1453.5	1455.5	1457.5	1457.5	1455.5	1453.5
170°	1463.4	1461.4	1459.4	1457.5	1459.4	1461.4	1463.4	1465.3	1465.3	1463.4	1461.4
172.5°	1468.3	1466.2	1464.1	1461.9	1464.1	1466.2	1468.3	1470.5	1470.6	1468.6	1466.7
175°	1474.3	1472.3	1470.5	1468.5	1470.5	1472.3	1474.3	1476.2	1476.4	1474.7	1473.0
177.5°	1476.3	1474.3	1472.3	1470.5	1472.3	1474.3	1476.3	1478.2	1478.4	1476.9	1475.3
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1100.2	1105.8	1111.3	1116.4	1124.4	1127.8	1133.0	1135.0	1140.9	1149.6	1156.7
5°	1033.3	1041.2	1051.6	1060.0	1073.3	1083.6	1095.0	1105.9	1118.7	1137.0	1153.2
7.5°	976.6	984.4	996.8	1012.4	1027.1	1041.8	1057.3	1072.1	1090.4	1116.6	1142.6
10°	939.1	948.5	963.3	980.1	998.2	1012.6	1030.9	1049.6	1072.3	1102.4	1133.5
12.5°	906.7	913.7	930.9	946.9	967.5	985.7	1003.6	1025.5	1051.4	1083.5	1120.9
15°	855.2	865.1	881.8	899.6	921.3	940.6	963.7	990.4	1015.6	1055.1	1100.4
17.5°	803.4	818.5	835.9	856.0	872.0	898.6	923.8	951.1	982.1	1024.0	1073.7
20°	770.3	782.1	798.4	827.6	848.8	869.0	892.2	926.2	954.9	1002.2	1054.0
22.5°	742.3	750.9	769.2	793.2	817.9	841.4	865.0	897.4	932.7	977.8	1033.9
25°	700.7	714.5	728.4	745.6	772.3	800.4	826.0	853.7	891.2	939.1	999.8
27.5°	660.2	672.7	686.4	707.6	727.7	754.0	780.9	812.6	852.8	903.4	965.1
30°	634.1	643.5	656.3	683.4	701.7	724.4	756.0	784.1	821.6	875.4	940.6
32.5°	607.3	619.4	633.4	654.2	676.8	698.3	727.2	757.7	796.0	848.9	915.7
35°	569.0	583.2	597.6	612.8	635.6	657.8	681.9	715.5	754.5	805.9	871.5
37.5°	533.8	545.3	556.9	575.9	597.4	618.5	641.1	674.2	710.9	766.3	826.4
40°	511.2	521.6	530.5	550.3	570.9	593.6	615.9	645.0	684.5	736.2	794.5
42.5°	486.7	496.3	508.4	524.5	546.9	566.0	588.2	615.8	652.9	705.5	756.6
45°	450.1	460.9	471.3	486.5	508.8	527.5	547.2	573.4	611.4	654.9	700.2
47.5°	411.9	422.7	434.5	449.3	468.7	487.8	507.5	530.7	565.3	607.9	638.6
50°	387.4	396.2	408.1	422.9	440.6	460.9	478.6	503.8	536.9	570.4	597.1
52.5°	362.1	370.2	383.6	399.3	415.8	433.3	452.2	473.8	503.7	535.3	556.5
55°	322.7	332.6	343.9	359.2	375.5	390.3	408.6	430.8	454.5	478.2	492.5
57.5°	285.9	294.1	303.7	319.4	333.6	351.3	367.6	384.9	406.8	424.7	434.0
60°	259.1	266.5	278.8	292.7	305.9	321.2	340.0	357.3	374.1	388.3	395.8
62.5°	233.8	242.4	253.2	265.8	280.3	294.8	311.2	325.6	340.4	352.8	357.9
65°	200.9	207.7	215.7	227.5	239.3	254.1	266.9	281.7	292.7	299.5	304.0
67.5°	170.9	175.4	181.4	189.3	201.0	213.9	226.3	237.9	246.9	251.7	255.6
70°	151.5	154.5	158.9	166.8	175.7	187.0	199.8	208.2	216.1	220.1	224.0
72.5°	132.1	135.9	140.0	146.3	153.5	161.7	171.1	181.4	185.8	190.5	192.8
75°	100.2	105.6	111.0	115.0	119.9	126.3	134.7	141.1	143.6	147.5	148.1
77.5°	75.6	76.8	80.8	85.7	89.8	94.4	99.8	105.5	106.7	108.8	110.1
80°	62.2	62.2	62.2	65.1	70.0	73.5	78.4	81.4	83.4	83.9	84.4
82.5°	50.0	50.0	49.6	50.1	51.9	53.8	58.3	61.6	63.2	63.0	61.9
85°	32.6	31.6	31.6	31.1	31.6	30.6	30.1	32.0	35.1	35.1	34.0
87.5°	18.9	18.3	18.0	17.1	16.0	15.0	13.2	13.1	12.6	13.8	12.8
90°	27.2	26.3	23.1	20.0	16.8	13.7	10.8	8.4	5.9	3.5	1.1
92.5°	29.6	28.0	25.6	23.3	20.9	18.5	17.6	18.3	19.0	19.7	20.4
95°	35.6	33.9	31.3	28.6	25.9	23.3	26.9	36.9	46.8	56.8	66.8
97.5°	37.2	35.3	52.8	70.3	87.8	105.4	116.3	120.8	125.3	129.8	134.2
100°	38.1	36.1	74.1	112.1	150.1	187.9	204.5	199.6	194.8	189.9	185.0
102.5°	66.0	72.0	113.5	155.0	196.4	237.9	256.9	253.4	249.9	246.4	242.9
105°	196.7	239.8	261.7	283.6	305.5	327.4	337.1	334.3	331.7	329.0	326.3
107.5°	407.9	439.6	436.1	432.6	429.2	425.7	422.9	420.8	418.7	416.5	414.3
110°	485.9	493.9	491.2	488.5	485.9	483.1	480.9	478.9	476.9	475.0	473.1



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	549.2	549.0	546.4	543.8	541.0	538.4	536.1	534.4	532.6	530.8	529.1
115°	631.0	628.6	626.4	624.2	622.0	619.8	617.9	616.5	615.0	613.6	612.2
117.5°	707.6	705.7	704.6	703.4	702.3	701.2	699.7	698.0	696.1	694.3	692.5
120°	757.5	755.5	754.9	754.1	753.4	752.7	751.2	749.0	746.9	744.6	742.4
122.5°	806.9	805.5	804.6	803.7	802.8	801.8	800.5	798.6	796.8	795.0	793.2
125°	876.6	876.0	875.1	874.1	873.1	872.1	870.7	868.7	866.8	864.9	862.9
127.5°	945.2	944.3	943.2	942.1	940.8	939.7	938.1	936.2	934.2	932.3	930.4
130°	986.6	985.5	984.6	983.6	982.6	981.7	980.1	978.3	976.3	974.4	972.4
132.5°	1026.0	1025.0	1024.2	1023.4	1022.7	1021.8	1020.5	1018.5	1016.6	1014.6	1012.7
135°	1085.9	1085.2	1084.2	1083.3	1082.3	1081.3	1080.1	1078.6	1077.1	1075.7	1074.2
137.5°	1138.7	1137.6	1137.0	1136.5	1136.0	1135.4	1134.3	1132.4	1130.5	1128.7	1126.8
140°	1172.7	1171.7	1171.0	1170.3	1169.5	1168.8	1167.7	1166.2	1164.8	1163.3	1161.9
142.5°	1204.9	1204.1	1203.4	1202.7	1201.9	1201.2	1200.1	1198.6	1197.2	1195.7	1194.3
145°	1249.9	1249.4	1249.0	1248.5	1248.0	1247.5	1246.4	1244.7	1243.0	1241.3	1239.6
147.5°	1290.1	1289.5	1289.0	1288.5	1288.1	1287.6	1286.8	1285.6	1284.6	1283.5	1282.3
150°	1314.6	1314.1	1313.6	1313.1	1312.6	1312.1	1311.5	1310.8	1310.0	1309.3	1308.6
152.5°	1336.0	1335.1	1334.8	1334.5	1334.2	1333.9	1333.6	1333.2	1332.9	1332.6	1332.3
155°	1365.6	1364.4	1364.2	1364.0	1363.7	1363.5	1363.6	1364.0	1364.5	1365.1	1365.6
157.5°	1391.6	1390.1	1390.3	1390.5	1390.8	1391.0	1391.2	1391.2	1391.3	1391.3	1391.4
160°	1406.5	1405.0	1405.2	1405.4	1405.7	1405.9	1406.2	1406.5	1406.7	1406.9	1407.1
162.5°	1419.8	1418.1	1418.3	1418.6	1418.8	1419.1	1419.5	1420.1	1420.8	1421.4	1422.0
165°	1437.6	1435.6	1435.9	1436.1	1436.3	1436.6	1437.1	1437.8	1438.5	1439.3	1440.0
167.5°	1451.6	1449.6	1449.6	1449.6	1449.6	1449.6	1450.1	1451.1	1452.1	1453.0	1454.1
170°	1459.4	1457.5	1457.5	1457.5	1457.5	1457.5	1458.0	1459.0	1460.0	1460.9	1461.9
172.5°	1464.7	1462.7	1462.5	1462.4	1462.2	1462.0	1462.4	1463.7	1464.8	1466.0	1467.2
175°	1471.3	1469.5	1469.3	1469.0	1468.9	1468.6	1469.0	1470.3	1471.5	1472.7	1473.9
177.5°	1473.8	1472.2	1472.0	1471.8	1471.6	1471.4	1471.8	1472.8	1473.8	1474.7	1475.7
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1159.0	1163.4	1168.9	1177.2	1183.6	1189.0	1190.2	1191.8	1195.8	1202.5	1207.6
5°	1166.6	1177.9	1196.2	1213.9	1233.2	1249.0	1263.8	1274.1	1284.0	1304.8	1321.5
7.5°	1164.2	1189.5	1218.0	1250.0	1282.2	1313.5	1342.6	1368.5	1394.3	1424.6	1459.0
10°	1162.6	1192.2	1230.7	1271.7	1316.5	1360.5	1403.0	1436.0	1474.5	1509.0	1552.9
12.5°	1155.1	1197.8	1243.8	1296.2	1351.3	1401.9	1457.8	1503.5	1547.6	1597.4	1648.5
15°	1145.4	1197.1	1255.4	1324.9	1408.8	1470.1	1527.3	1606.8	1661.0	1715.3	1788.3
17.5°	1127.5	1190.7	1263.5	1353.9	1423.9	1506.1	1592.2	1655.0	1728.2	1804.6	1870.8
20°	1113.2	1186.8	1268.2	1357.1	1446.3	1535.7	1619.1	1694.0	1769.6	1857.9	1912.2
22.5°	1099.1	1171.8	1256.4	1350.8	1446.7	1540.8	1635.2	1723.3	1808.3	1897.4	1966.7
25°	1068.8	1155.2	1247.0	1343.2	1437.9	1541.6	1654.1	1752.3	1857.4	1949.2	2014.9
27.5°	1038.2	1117.4	1208.8	1306.4	1411.7	1534.2	1666.5	1778.2	1883.5	1949.2	1969.8
30°	1010.6	1094.5	1178.4	1277.6	1391.6	1528.2	1668.9	1796.7	1883.1	1911.7	1890.5
32.5°	982.6	1058.6	1141.7	1243.2	1364.3	1513.6	1672.1	1785.6	1837.7	1815.8	1729.4
35°	933.1	1001.7	1082.1	1183.8	1323.0	1505.6	1659.1	1736.0	1723.2	1599.8	1437.0
37.5°	880.2	936.1	1010.6	1116.9	1280.2	1473.5	1603.0	1614.3	1503.3	1313.9	1125.8
40°	838.4	888.7	965.3	1076.3	1247.0	1441.9	1546.5	1500.6	1328.4	1117.7	960.8
42.5°	797.8	840.2	913.9	1033.6	1215.4	1398.9	1462.4	1362.4	1163.8	964.5	821.8
45°	728.9	768.8	842.8	965.7	1150.8	1316.5	1308.2	1134.4	935.7	775.2	656.8
47.5°	663.5	698.4	767.9	893.3	1074.9	1193.2	1114.7	929.9	761.2	632.5	548.1
50°	617.4	651.9	721.0	844.8	1014.1	1100.4	988.4	810.3	655.8	549.2	482.1
52.5°	573.2	606.9	670.1	790.7	940.7	992.3	871.9	706.8	578.1	486.1	428.4
55°	511.2	536.9	593.6	709.1	821.1	833.0	711.1	572.9	466.8	402.7	363.2
57.5°	448.2	470.2	526.3	618.3	696.9	690.8	575.2	455.6	384.2	336.6	307.9
60°	407.1	428.9	478.2	557.1	616.3	595.6	489.6	393.3	332.1	297.1	274.4
62.5°	368.8	385.8	432.0	489.7	532.3	508.8	418.5	338.8	290.3	260.7	242.8
65°	313.4	327.2	364.2	394.3	417.9	395.3	320.3	264.9	230.0	209.2	196.9
67.5°	260.6	269.5	292.8	303.7	320.4	295.5	240.8	203.8	183.9	166.4	157.8
70°	227.5	233.9	246.3	255.1	259.6	233.9	193.4	166.3	149.5	137.1	131.8
72.5°	194.4	199.9	202.5	209.7	207.5	183.4	155.5	133.9	121.9	113.5	106.5
75°	148.5	151.0	148.5	145.5	139.1	122.3	103.1	92.3	83.4	79.5	77.0
77.5°	108.3	107.4	104.2	99.4	88.5	77.9	67.6	64.0	60.1	58.1	57.1
80°	83.4	81.4	78.4	71.1	61.6	54.3	51.8	49.4	47.9	45.4	44.9
82.5°	62.1	60.9	56.0	49.8	43.2	39.7	37.6	36.8	35.3	33.9	33.8
85°	33.1	31.6	26.1	22.7	21.7	20.7	20.3	20.3	18.3	17.7	17.7
87.5°	11.4	9.5	9.6	8.9	9.4	9.2	10.3	10.2	10.4	10.9	10.4
90°	3.5	5.9	8.4	10.8	13.7	16.8	20.0	23.1	26.3	27.2	28.2
92.5°	19.7	19.0	18.3	17.6	18.5	20.9	23.3	25.6	28.0	29.6	31.1
95°	56.8	46.8	36.9	26.9	23.3	25.9	28.6	31.3	33.9	35.6	37.3
97.5°	129.8	125.3	120.8	116.3	105.4	87.8	70.3	52.8	35.3	37.2	39.1
100°	189.9	194.8	199.6	204.5	187.9	150.1	112.1	74.1	36.1	38.1	40.1
102.5°	246.4	249.9	253.4	256.9	237.9	196.4	155.0	113.5	72.0	66.0	59.9
105°	329.0	331.7	334.3	337.1	327.4	305.5	283.6	261.7	239.8	196.7	153.6
107.5°	416.5	418.7	420.8	422.9	425.7	429.2	432.6	436.1	439.6	407.9	376.4
110°	475.0	476.9	478.9	480.9	483.1	485.9	488.5	491.2	493.9	485.9	477.8



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	530.8	532.6	534.4	536.1	538.4	541.0	543.8	546.4	549.0	549.2	549.3
115°	613.6	615.0	616.5	617.9	619.8	622.0	624.2	626.4	628.6	631.0	633.4
117.5°	694.3	696.1	698.0	699.7	701.2	702.3	703.4	704.6	705.7	707.6	709.5
120°	744.6	746.9	749.0	751.2	752.7	753.4	754.1	754.9	755.5	757.5	759.5
122.5°	795.0	796.8	798.6	800.5	801.8	802.8	803.7	804.6	805.5	806.9	808.2
125°	864.9	866.8	868.7	870.7	872.1	873.1	874.1	875.1	876.0	876.6	877.0
127.5°	932.3	934.2	936.2	938.1	939.7	940.8	942.1	943.2	944.3	945.2	945.9
130°	974.4	976.3	978.3	980.1	981.7	982.6	983.6	984.6	985.5	986.6	987.5
132.5°	1014.6	1016.6	1018.5	1020.5	1021.8	1022.7	1023.4	1024.2	1025.0	1026.0	1026.9
135°	1075.7	1077.1	1078.6	1080.1	1081.3	1082.3	1083.3	1084.2	1085.2	1085.9	1086.7
137.5°	1128.7	1130.5	1132.4	1134.3	1135.4	1136.0	1136.5	1137.0	1137.6	1138.7	1139.9
140°	1163.3	1164.8	1166.2	1167.7	1168.8	1169.5	1170.3	1171.0	1171.7	1172.7	1173.7
142.5°	1195.7	1197.2	1198.6	1200.1	1201.2	1201.9	1202.7	1203.4	1204.1	1204.9	1205.7
145°	1241.3	1243.0	1244.7	1246.4	1247.5	1248.0	1248.5	1249.0	1249.4	1249.9	1250.5
147.5°	1283.5	1284.6	1285.6	1286.8	1287.6	1288.1	1288.5	1289.0	1289.5	1290.1	1290.5
150°	1309.3	1310.0	1310.8	1311.5	1312.1	1312.6	1313.1	1313.6	1314.1	1314.6	1315.0
152.5°	1332.6	1332.9	1333.2	1333.6	1333.9	1334.2	1334.5	1334.8	1335.1	1336.0	1336.8
155°	1365.1	1364.5	1364.0	1363.6	1363.5	1363.7	1364.0	1364.2	1364.4	1365.6	1366.9
157.5°	1391.3	1391.3	1391.2	1391.2	1391.0	1390.8	1390.5	1390.3	1390.1	1391.6	1393.0
160°	1406.9	1406.7	1406.5	1406.2	1405.9	1405.7	1405.4	1405.2	1405.0	1406.5	1407.9
162.5°	1421.4	1420.8	1420.1	1419.5	1419.1	1418.8	1418.6	1418.3	1418.1	1419.8	1421.4
165°	1439.3	1438.5	1437.8	1437.1	1436.6	1436.3	1436.1	1435.9	1435.6	1437.6	1439.5
167.5°	1453.0	1452.1	1451.1	1450.1	1449.6	1449.6	1449.6	1449.6	1449.6	1451.6	1453.5
170°	1460.9	1460.0	1459.0	1458.0	1457.5	1457.5	1457.5	1457.5	1457.5	1459.4	1461.4
172.5°	1466.0	1464.8	1463.7	1462.4	1462.0	1462.2	1462.4	1462.5	1462.7	1464.7	1466.7
175°	1472.7	1471.5	1470.3	1469.0	1468.6	1468.9	1469.0	1469.3	1469.5	1471.3	1473.0
177.5°	1474.7	1473.8	1472.8	1471.8	1471.4	1471.6	1471.8	1472.0	1472.2	1473.8	1475.3
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7	1152.7
2.5°	1215.9	1215.9	1217.5	1223.4	1224.2	1229.4	1227.8
5°	1336.3	1345.7	1349.2	1364.0	1372.8	1376.8	1368.9
7.5°	1483.6	1510.0	1522.6	1538.0	1551.8	1555.9	1545.1
10°	1590.9	1618.5	1641.8	1656.0	1669.4	1678.3	1689.6
12.5°	1694.8	1728.7	1750.8	1770.9	1784.7	1795.9	1797.8
15°	1807.6	1858.9	1897.9	1926.5	1940.8	1948.2	1945.2
17.5°	1921.4	1969.0	1996.7	2025.9	2045.7	2046.7	2047.3
20°	1985.7	2032.1	2064.2	2085.8	2108.1	2107.1	2112.0
22.5°	2028.7	2065.3	2089.8	2105.6	2113.3	2109.5	2110.4
25°	2048.9	2059.7	2055.3	2030.1	2023.7	2000.5	2004.5
27.5°	1945.0	1893.8	1840.6	1772.4	1718.4	1675.5	1677.6
30°	1804.1	1713.4	1609.7	1522.9	1444.9	1423.1	1376.8
32.5°	1607.1	1470.9	1349.5	1268.6	1201.6	1183.6	1143.1
35°	1273.2	1140.9	1016.1	941.0	911.4	870.0	869.5
37.5°	989.6	873.2	807.1	750.8	721.3	696.3	693.8
40°	832.5	741.7	691.8	651.4	622.3	603.5	599.1
42.5°	722.7	649.3	602.7	577.6	555.2	545.4	538.3
45°	590.2	540.8	508.3	485.6	475.2	467.8	463.8
47.5°	493.7	460.6	438.4	423.3	414.9	407.1	409.2
50°	441.2	414.1	397.8	383.4	377.0	371.6	372.1
52.5°	398.9	374.6	361.4	351.1	343.1	339.2	337.3
55°	338.6	323.2	309.9	302.5	298.0	292.7	291.2
57.5°	288.8	276.9	266.1	257.7	256.6	251.4	252.0
60°	255.6	245.7	236.9	232.4	228.9	224.5	226.0
62.5°	228.4	220.1	212.0	208.3	204.9	201.6	202.4
65°	187.0	179.1	174.2	172.2	170.7	169.3	167.8
67.5°	149.0	144.2	141.1	136.9	133.8	133.4	131.9
70°	125.4	118.9	113.5	108.1	106.6	106.1	106.6
72.5°	100.5	96.4	94.9	92.3	92.0	90.7	91.6
75°	75.5	74.0	73.0	71.1	71.1	71.1	71.1
77.5°	55.7	54.8	54.2	53.8	53.3	52.6	52.5
80°	43.5	42.9	41.9	41.9	41.5	41.9	41.5
82.5°	32.8	32.7	31.7	31.7	31.2	30.9	31.2
85°	16.8	16.3	17.2	16.3	16.8	15.8	16.8
87.5°	10.6	10.7	10.6	10.7	10.4	11.2	10.6
90°	29.2	30.2	30.9	31.4	31.9	32.3	32.9
92.5°	32.7	34.3	35.2	35.4	35.8	36.1	36.4
95°	39.0	40.7	41.6	41.6	41.6	41.6	41.6
97.5°	41.1	43.1	44.1	44.4	44.7	44.9	45.1
100°	41.9	43.9	45.1	45.2	45.5	45.7	46.0
102.5°	53.9	47.9	45.1	45.5	46.0	46.5	46.8
105°	110.6	67.5	46.3	46.8	47.2	47.7	48.2
107.5°	344.8	313.2	281.2	248.7	216.2	183.8	151.4
110°	469.8	461.8	440.4	405.6	370.7	335.9	301.1



TEST NUMBER: P332324-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	549.5	549.7	546.0	538.7	531.3	524.0	516.6
115°	635.8	638.3	640.0	640.9	642.0	642.9	643.9
117.5°	711.5	713.4	714.5	714.7	714.9	715.1	715.3
120°	761.4	763.4	764.3	764.3	764.3	764.3	764.3
122.5°	809.6	811.0	811.7	811.9	812.1	812.4	812.6
125°	877.5	878.0	878.4	878.9	879.5	880.0	880.4
127.5°	946.7	947.4	947.6	947.2	946.7	946.2	945.7
130°	988.4	989.5	989.7	989.2	988.7	988.3	987.8
132.5°	1027.9	1028.9	1029.0	1028.3	1027.7	1027.0	1026.2
135°	1087.4	1088.2	1088.2	1087.4	1086.7	1085.9	1085.2
137.5°	1141.0	1142.2	1142.6	1142.1	1141.6	1141.1	1140.6
140°	1174.6	1175.6	1175.8	1175.4	1174.9	1174.4	1173.9
142.5°	1206.5	1207.2	1207.3	1206.6	1205.9	1205.2	1204.6
145°	1250.9	1251.4	1251.6	1251.6	1251.6	1251.6	1251.6
147.5°	1291.0	1291.5	1291.2	1290.1	1288.9	1287.8	1286.7
150°	1315.5	1316.0	1315.9	1315.1	1314.5	1313.7	1313.0
152.5°	1337.8	1338.6	1338.5	1337.4	1336.2	1335.1	1334.0
155°	1368.1	1369.3	1369.1	1367.7	1366.3	1364.8	1363.4
157.5°	1394.4	1395.9	1395.7	1393.8	1391.9	1390.0	1388.1
160°	1409.3	1410.8	1410.7	1409.0	1407.3	1405.5	1403.8
162.5°	1423.1	1424.7	1424.7	1423.2	1421.7	1420.2	1418.7
165°	1441.4	1443.4	1443.5	1441.8	1440.1	1438.4	1436.7
167.5°	1455.5	1457.5	1457.5	1455.5	1453.5	1451.6	1449.6
170°	1463.4	1465.3	1465.3	1463.4	1461.4	1459.4	1457.5
172.5°	1468.6	1470.6	1470.5	1468.3	1466.2	1464.1	1461.9
175°	1474.7	1476.4	1476.2	1474.3	1472.3	1470.5	1468.5
177.5°	1476.9	1478.4	1478.2	1476.3	1474.3	1472.3	1470.5
180°	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9	1473.9

(END OF REPORT)