

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332329-830

Luminaire Tested: **S123RDIP-S775D1195U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332329-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S775D1195U830-4F0-1E-UDD-F4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6823.2 lumens  
Efficiency: N/A  
Efficacy: 119.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332329-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332329-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	33	31	30	25
4	73	63	55	49	66	58	51	46	48	43	39	38	35	32	30	28	26	22
5	67	56	48	42	61	51	45	39	43	38	34	35	31	28	27	25	22	19
6	62	50	42	37	56	46	39	34	39	33	29	31	27	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16	13
9	49	38	30	25	45	35	28	24	29	24	21	24	20	17	19	16	14	12
10	46	34	27	23	42	32	26	21	27	22	19	22	18	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13099	13099	13099
5°	13149	12967	13042
10°	13074	12804	12761
15°	12933	12504	12373
20°	12741	12129	11848
25°	12542	11709	11334
30°	12279	11225	10611
35°	12009	10738	9947
40°	11760	10165	9125
45°	11432	9601	8383
50°	11072	8957	7552
55°	10704	8223	6778
60°	10368	7436	5927
65°	9928	6584	5076
70°	9379	5530	4101
75°	8576	4350	3855
80°	7649	3856	3546
85°	6459	3409	3162



TEST NUMBER: P332329-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.3	1.7
10°-20°	317.9	4.7
20°-30°	457.8	6.7
30°-40°	515.7	7.6
40°-50°	493.3	7.2
50°-60°	404.0	5.9
60°-70°	272.6	4.0
70°-80°	137.1	2.0
80°-90°	40.5	0.6
90°-100°	301.1	4.4
100°-110°	852.5	12.5
110°-120°	838.6	12.3
120°-130°	668.9	9.8
130°-140°	527.4	7.7
140°-150°	393.6	5.8
150°-160°	274.4	4.0
160°-170°	161.2	2.4
170°-180°	52.4	0.8
0°-30°	890.0	13.0
0°-40°	1405.7	20.6
0°-60°	2303.0	33.8
0°-90°	2753.2	40.4
90°-120°	1992.1	29.2
90°-150°	3582.0	52.5
90°-180°	4070.0	59.6
0°-180°	6823.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1217	1217	1217	1217	1217	
5°	1217	1212	1200	1208	1207	115
15°	1161	1149	1122	1117	1110	327
25°	1056	1030	986	966	954	485
35°	914	877	817	776	757	572
45°	751	705	631	576	551	579
55°	570	520	438	383	361	511
65°	390	334	258	212	199	386
75°	206	159	105	95	93	220
85°	52	32	28	26	26	59
90°	2	13	27	31	32	5
95°	37	121	649	190	127	40
105°	127	188	880	1540	1393	135
115°	224	280	673	1477	1694	222
125°	312	368	629	1139	1336	277
135°	366	436	620	938	1083	283
145°	417	478	612	769	846	261
155°	474	511	592	673	702	218
165°	518	533	567	602	612	146
175°	540	540	544	552	551	51
180°	541	541	541	541	541	



TEST NUMBER: P332329-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1220.8	1220.1	1219.4	1218.7	1218.0	1216.6	1214.5	1212.4	1210.3	1208.2	1210.1
5°	1216.9	1215.8	1214.7	1213.6	1212.5	1210.6	1208.0	1205.3	1202.7	1200.1	1202.0
7.5°	1205.6	1204.5	1203.2	1202.0	1200.9	1198.5	1195.1	1191.8	1188.4	1184.9	1186.0
10°	1196.2	1194.6	1193.1	1191.6	1190.0	1187.2	1183.3	1179.4	1175.4	1171.5	1171.7
12.5°	1182.7	1181.0	1179.3	1177.6	1175.9	1172.6	1167.8	1163.0	1158.1	1153.3	1153.2
15°	1160.6	1158.2	1155.7	1153.4	1150.9	1146.7	1140.6	1134.4	1128.2	1122.1	1121.1
17.5°	1132.7	1130.0	1127.2	1124.4	1121.5	1116.3	1108.4	1100.6	1092.8	1085.1	1082.7
20°	1112.3	1108.7	1105.2	1101.7	1098.3	1092.3	1083.9	1075.6	1067.3	1058.9	1056.1
22.5°	1089.4	1085.3	1081.3	1077.2	1073.2	1066.8	1057.9	1049.0	1040.2	1031.3	1027.7
25°	1056.0	1050.6	1045.0	1039.5	1034.1	1026.2	1016.2	1006.1	996.0	985.9	981.3
27.5°	1015.5	1009.5	1003.4	997.4	991.4	982.7	971.5	960.3	949.0	937.7	931.3
30°	987.9	981.3	974.8	968.2	961.6	952.2	939.9	927.6	915.3	903.1	895.6
32.5°	960.3	952.8	945.4	937.9	930.5	920.2	907.2	894.3	881.3	868.3	860.2
35°	913.9	906.0	898.1	890.2	882.3	871.6	858.0	844.3	830.8	817.2	807.8
37.5°	867.0	858.1	849.3	840.6	831.8	820.2	805.7	791.2	776.7	762.1	751.4
40°	836.9	827.3	817.6	807.9	798.3	785.7	770.2	754.6	739.0	723.4	712.0
42.5°	803.0	793.3	783.6	774.0	764.4	751.5	735.4	719.3	703.2	687.1	674.7
45°	751.0	741.2	731.3	721.4	711.5	698.2	681.3	664.4	647.5	630.7	618.1
47.5°	699.2	688.3	677.5	666.7	655.8	642.0	625.1	608.1	591.3	574.4	560.8
50°	661.2	650.9	640.6	630.3	620.0	606.0	588.2	570.4	552.7	534.9	521.3
52.5°	627.3	616.1	604.9	593.7	582.6	568.2	550.5	533.0	515.4	497.8	483.7
55°	570.4	559.7	548.9	538.2	527.4	512.7	494.1	475.5	456.9	438.2	425.5
57.5°	517.9	506.2	494.6	482.8	471.1	455.9	437.2	418.4	399.6	381.0	368.9
60°	481.6	469.6	457.5	445.4	433.4	418.2	400.0	381.8	363.6	345.4	333.6
62.5°	445.3	433.2	421.1	409.1	397.1	381.9	363.7	345.5	327.3	309.1	297.9
65°	389.8	377.8	365.7	353.6	341.6	327.0	309.9	292.8	275.7	258.5	247.8
67.5°	334.4	322.2	310.0	297.7	285.6	271.3	254.9	238.5	222.1	205.7	197.7
70°	298.0	286.3	274.4	262.5	250.7	237.0	221.7	206.4	191.1	175.7	168.0
72.5°	261.7	250.1	238.4	226.7	215.1	202.3	188.3	174.4	160.4	146.5	140.2
75°	206.2	195.8	185.2	174.7	164.2	152.9	140.8	128.8	116.7	104.6	102.5
77.5°	155.7	146.2	136.7	127.1	117.6	109.1	101.2	93.5	85.8	77.9	76.8
80°	123.4	114.3	105.4	96.4	87.4	80.6	76.0	71.4	66.8	62.2	61.5
82.5°	92.6	84.8	77.0	69.3	61.5	56.6	54.4	52.2	50.1	48.0	47.3
85°	52.3	47.5	42.7	37.8	33.0	30.3	29.6	28.9	28.3	27.6	27.2
87.5°	19.4	17.9	16.4	15.2	13.7	13.1	13.8	14.4	15.1	15.7	15.4
90°	2.2	4.3	6.6	9.9	12.1	14.2	17.5	20.8	24.1	27.3	26.3
92.5°	13.6	20.2	29.3	37.9	47.1	63.3	92.0	139.1	185.3	168.4	127.1
95°	37.2	40.5	52.6	71.2	99.6	142.3	235.4	398.6	578.2	649.4	526.7
97.5°	63.5	64.6	74.0	90.2	118.3	164.5	253.4	437.3	736.8	1006.4	1076.7
100°	81.1	82.1	89.8	105.1	131.4	174.1	250.8	412.8	700.9	1037.1	1252.8
102.5°	99.4	101.4	108.2	122.6	146.3	185.5	254.3	391.8	648.3	980.1	1261.5
105°	127.1	130.4	136.9	150.1	170.8	204.8	263.9	376.7	583.7	880.4	1194.8
107.5°	156.4	159.7	166.0	178.9	198.4	230.0	281.9	375.6	542.5	792.4	1077.8
110°	177.4	180.7	186.2	198.2	216.8	247.5	296.8	380.0	526.7	742.4	1004.2



TEST NUMBER: P332329-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	196.7	200.0	205.5	217.4	236.1	265.9	311.7	388.8	518.0	709.2	940.3
115°	224.5	228.8	235.4	246.4	265.0	294.5	336.2	403.0	514.7	673.4	862.9
117.5°	252.3	257.3	262.8	272.9	293.7	321.1	362.2	421.8	516.7	652.4	816.2
120°	271.5	274.8	280.3	291.3	312.1	339.5	378.9	435.8	520.2	642.8	791.7
122.5°	288.2	291.5	297.0	308.8	328.8	357.9	396.4	449.0	526.3	636.7	771.6
125°	312.1	314.3	320.8	332.9	353.7	383.2	421.6	469.8	535.5	628.6	745.7
127.5°	330.3	333.6	341.7	353.9	376.9	406.5	443.5	486.9	546.0	624.6	723.0
130°	341.7	345.0	354.8	368.0	391.0	420.5	456.7	498.2	553.0	622.0	710.7
132.5°	350.4	354.6	365.3	381.1	404.1	432.8	468.1	508.8	558.3	621.1	699.4
135°	365.8	370.1	382.2	398.6	421.6	451.2	485.1	522.4	566.2	619.8	684.5
137.5°	380.2	384.8	396.6	414.2	437.0	464.3	496.9	532.4	571.5	617.4	671.5
140°	389.8	395.3	406.2	423.8	445.7	473.1	504.8	537.7	575.0	616.5	663.6
142.5°	400.4	405.0	416.8	432.5	454.5	480.1	511.0	542.9	577.6	614.8	656.6
145°	417.3	420.5	430.4	446.8	465.4	490.6	519.1	548.7	579.3	612.2	647.2
147.5°	434.3	436.3	445.9	460.1	478.2	499.5	525.7	552.1	579.3	608.0	638.0
150°	445.7	446.8	455.5	469.8	485.1	504.8	530.0	553.0	579.3	604.5	631.9
152.5°	457.1	457.3	466.1	478.5	492.1	511.0	532.6	554.8	576.6	600.1	624.9
155°	474.2	474.2	480.8	491.7	503.7	519.1	537.7	555.3	573.8	592.5	614.3
157.5°	487.8	488.6	493.9	503.5	513.8	525.7	540.5	556.3	570.1	585.7	602.5
160°	498.2	498.2	502.7	511.4	519.1	530.0	543.2	556.3	568.4	580.4	594.7
162.5°	506.1	506.1	509.6	516.7	523.5	532.6	544.0	555.4	564.9	575.1	586.7
165°	518.0	516.9	519.1	524.5	529.0	536.6	545.4	553.0	559.6	567.2	576.0
167.5°	527.0	525.7	526.7	530.9	534.0	538.8	545.2	551.3	554.3	559.4	565.7
170°	532.3	530.0	531.1	534.4	536.6	538.8	544.2	548.7	550.8	554.1	559.6
172.5°	535.7	534.4	534.6	537.1	538.4	539.7	544.2	547.8	548.2	549.7	553.5
175°	539.9	538.8	537.7	539.9	539.9	541.0	543.2	545.4	544.2	544.2	546.5
177.5°	541.9	541.0	540.1	541.0	541.0	541.0	541.9	543.6	541.9	541.0	541.9
180°	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0



TEST NUMBER: P332329-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9	1216.9
2.5°	1212.0	1214.0	1215.9	1216.7	1216.4	1216.0	1215.6	1215.3
5°	1204.0	1206.0	1208.0	1208.7	1208.3	1207.9	1207.4	1207.0
7.5°	1187.1	1188.2	1189.3	1189.5	1188.7	1188.0	1187.2	1186.5
10°	1172.0	1172.1	1172.3	1172.0	1170.8	1169.7	1168.7	1167.5
12.5°	1153.0	1152.9	1152.8	1152.1	1150.8	1149.5	1148.3	1147.0
15°	1119.9	1118.8	1117.8	1116.4	1114.9	1113.3	1111.8	1110.3
17.5°	1080.3	1078.1	1075.7	1073.5	1071.1	1068.8	1066.6	1064.3
20°	1053.3	1050.4	1047.5	1044.8	1042.2	1039.5	1036.9	1034.3
22.5°	1024.3	1020.7	1017.1	1014.1	1011.6	1009.2	1006.7	1004.3
25°	976.8	972.1	967.5	964.0	961.6	959.1	956.8	954.3
27.5°	924.9	918.6	912.2	907.1	903.4	899.8	896.1	892.4
30°	888.2	880.6	873.2	867.7	864.2	860.7	857.1	853.7
32.5°	852.0	843.9	835.7	829.7	826.0	822.4	818.7	815.0
35°	798.3	788.9	779.5	772.8	768.8	764.9	760.9	757.0
37.5°	740.6	730.0	719.3	711.5	706.6	701.7	696.9	692.0
40°	700.6	689.2	677.8	669.6	664.5	659.5	654.4	649.4
42.5°	662.1	649.7	637.3	628.8	624.2	619.7	615.2	610.7
45°	605.7	593.1	580.6	571.7	566.5	561.2	556.0	550.7
47.5°	547.1	533.6	520.0	510.9	506.1	501.4	496.8	492.1
50°	507.7	494.1	480.5	471.2	466.2	461.1	456.1	451.0
52.5°	469.6	455.4	441.3	432.0	427.4	422.9	418.4	413.9
55°	412.7	400.0	387.3	378.7	374.4	369.9	365.6	361.2
57.5°	356.9	344.9	332.9	325.0	321.3	317.5	313.8	310.1
60°	321.7	309.9	298.0	290.3	286.5	282.8	279.1	275.3
62.5°	286.8	275.7	264.6	257.0	253.1	249.2	245.3	241.4
65°	237.0	226.3	215.6	209.0	206.6	204.2	201.8	199.3
67.5°	189.6	181.6	173.5	168.2	165.7	163.1	160.5	157.9
70°	160.3	152.6	145.0	140.0	137.5	135.1	132.7	130.3
72.5°	133.9	127.6	121.4	117.7	116.7	115.7	114.7	113.7
75°	100.2	98.0	95.9	94.5	94.1	93.7	93.2	92.7
77.5°	75.6	74.4	73.2	72.4	72.0	71.5	71.1	70.7
80°	60.9	60.2	59.6	59.0	58.5	58.2	57.7	57.2
82.5°	46.7	46.0	45.3	45.0	44.9	44.8	44.7	44.6
85°	26.8	26.3	25.9	25.6	25.6	25.6	25.6	25.6
87.5°	15.4	15.5	15.5	15.7	15.4	15.4	15.5	15.1
90°	27.3	28.5	29.6	31.8	30.6	31.8	32.9	31.8
92.5°	92.2	73.1	64.6	58.9	56.9	53.6	54.8	52.8
95°	394.3	267.2	209.2	169.8	148.9	139.1	131.4	127.1
97.5°	982.7	787.1	645.9	514.9	434.1	384.8	355.2	345.8
100°	1291.1	1202.4	1074.3	918.8	808.1	728.2	685.5	686.6
102.5°	1393.6	1390.7	1316.1	1217.5	1131.4	1068.2	1032.5	1007.3
105°	1423.6	1533.1	1554.0	1525.5	1475.1	1433.5	1398.5	1393.0
107.5°	1337.3	1515.1	1611.1	1650.1	1651.0	1636.9	1625.1	1615.0
110°	1255.0	1456.5	1594.5	1671.1	1701.8	1710.5	1708.4	1706.2





TEST NUMBER: P332329-830

CATALOG NUMBER: S123RDIP-S775D1195U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1173.5	1379.4	1534.0	1632.6	1688.7	1715.8	1724.1	1724.6
115°	1065.5	1256.0	1417.0	1536.4	1618.5	1666.7	1688.7	1694.1
117.5°	987.3	1151.8	1296.4	1417.5	1503.2	1558.3	1589.9	1597.3
120°	946.1	1094.0	1225.4	1336.1	1422.5	1483.8	1510.1	1516.7
122.5°	913.7	1047.5	1169.3	1272.1	1349.0	1404.1	1433.0	1441.3
125°	870.6	990.0	1095.0	1182.7	1252.8	1301.0	1328.3	1336.1
127.5°	832.9	939.3	1034.2	1113.9	1176.4	1217.5	1242.3	1249.2
130°	809.3	907.9	996.6	1071.0	1129.1	1168.5	1191.5	1200.2
132.5°	787.4	878.1	960.6	1031.6	1086.1	1125.5	1145.9	1152.1
135°	757.8	835.6	906.7	969.1	1022.8	1055.6	1075.3	1083.1
137.5°	730.8	794.6	855.9	910.0	955.2	988.4	1005.0	1010.1
140°	715.1	770.9	823.5	870.6	912.2	942.9	960.4	959.3
142.5°	700.2	748.2	793.7	834.7	870.2	897.3	913.0	912.0
145°	682.2	718.4	753.5	785.1	812.6	835.6	844.3	846.5
147.5°	667.6	696.3	724.5	747.1	767.9	783.4	791.7	792.6
150°	657.0	682.2	705.2	726.0	742.4	754.5	761.1	761.1
152.5°	647.4	669.1	689.5	706.8	719.7	730.8	734.8	734.8
155°	632.9	650.4	666.9	680.0	689.9	698.7	700.9	701.9
157.5°	617.6	632.4	645.0	655.3	663.8	670.4	672.1	671.9
160°	608.9	620.9	631.9	639.5	647.2	653.7	653.7	652.7
162.5°	598.3	608.7	618.7	625.5	630.6	636.2	636.2	635.2
165°	584.8	591.4	599.0	604.5	608.9	613.2	612.2	612.2
167.5°	573.0	578.0	582.4	586.4	588.2	591.4	590.2	590.2
170°	565.1	568.4	572.7	575.0	576.0	578.2	577.1	577.1
172.5°	558.1	560.4	564.0	565.2	565.5	567.7	565.7	564.9
175°	548.7	549.7	552.0	552.0	552.0	553.0	552.0	550.8
177.5°	542.7	543.6	544.5	544.5	543.6	544.5	542.7	542.7
180°	541.0	541.0	541.0	541.0	541.0	541.0	541.0	541.0

(END OF REPORT)