

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332079-930

Luminaire Tested: **S123DIP-S1165D1025U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332079-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S1165D1025U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6751.9 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332079-930
CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332079-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	99	95	91	87	92	89	85	82	77	74	72	66	64	62	56	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	58	55	52	49	47	45	40
3	83	73	65	59	77	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	56	50	70	60	53	48	53	47	43	45	41	38	39	35	33	29
5	69	57	49	43	64	54	46	41	47	41	37	41	36	33	35	31	28	25
6	64	52	43	37	59	48	41	36	42	36	32	37	32	29	32	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16043	16043	16043
5°	16119	15896	16008
10°	16010	15759	15856
15°	15824	15581	15610
20°	15605	15326	15340
25°	15311	15023	14992
30°	14989	14686	14574
35°	14651	14331	14146
40°	14299	13939	13722
45°	13910	13577	13247
50°	13520	13134	12769
55°	13011	12675	12288
60°	12499	12140	11752
65°	12045	11556	11196
70°	11374	10889	10408
75°	10393	10019	9590
80°	9372	8976	8901
85°	8225	7916	7608



TEST NUMBER: P332079-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.4	2.1
10°-20°	396.4	5.9
20°-30°	585.6	8.7
30°-40°	684.0	10.1
40°-50°	687.7	10.2
50°-60°	604.1	8.9
60°-70°	450.0	6.7
70°-80°	256.4	3.8
80°-90°	76.7	1.1
90°-100°	67.5	1.0
100°-110°	202.0	3.0
110°-120°	343.6	5.1
120°-130°	451.9	6.7
130°-140°	508.0	7.5
140°-150°	499.3	7.4
150°-160°	420.4	6.2
160°-170°	279.8	4.1
170°-180°	98.0	1.5
0°-30°	1122.4	16.6
0°-40°	1806.5	26.8
0°-60°	3098.3	45.9
0°-90°	3881.4	57.5
90°-120°	613.1	9.1
90°-150°	2072.3	30.7
90°-180°	2870.0	42.5
0°-180°	6751.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1490	1490	1490	1490	1490	
5°	1492	1485	1471	1483	1482	141
15°	1420	1414	1398	1407	1401	400
25°	1289	1281	1265	1266	1262	594
35°	1115	1107	1091	1083	1076	697
45°	914	908	892	877	870	705
55°	693	691	675	662	655	621
65°	473	466	454	444	440	466
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	9	20	23	24	7
95°	48	54	60	63	64	54
105°	183	185	192	192	194	196
115°	346	348	347	347	347	342
125°	506	508	507	504	500	451
135°	657	661	661	658	656	506
145°	797	798	801	800	797	497
155°	912	912	913	916	911	420
165°	994	991	991	996	990	280
175°	1034	1030	1030	1035	1030	98
180°	1036	1036	1036	1036	1036	



TEST NUMBER: P332079-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1495.6	1494.7	1493.8	1492.9	1491.9	1490.2	1487.8	1485.2	1482.7	1480.2	1482.5
5°	1491.8	1490.4	1488.9	1487.5	1486.0	1483.8	1480.7	1477.5	1474.4	1471.2	1474.1
7.5°	1477.2	1475.7	1474.3	1472.8	1471.5	1469.1	1465.8	1462.6	1459.4	1456.1	1458.7
10°	1464.8	1463.4	1462.0	1460.5	1459.1	1456.6	1452.9	1449.2	1445.4	1441.8	1444.3
12.5°	1448.5	1447.2	1446.0	1444.9	1443.7	1441.3	1437.9	1434.4	1430.9	1427.4	1429.3
15°	1420.0	1418.9	1417.7	1416.6	1415.4	1413.0	1409.3	1405.6	1401.9	1398.2	1400.4
17.5°	1386.9	1385.4	1384.0	1382.5	1381.0	1378.4	1374.7	1371.0	1367.3	1363.6	1365.2
20°	1362.3	1360.6	1358.9	1357.1	1355.5	1352.7	1349.1	1345.4	1341.7	1338.0	1339.1
22.5°	1334.6	1332.9	1331.2	1329.5	1327.8	1325.1	1321.4	1317.7	1314.0	1310.3	1311.2
25°	1289.2	1287.5	1285.8	1284.1	1282.5	1279.7	1276.0	1272.4	1268.6	1264.9	1265.2
27.5°	1240.8	1239.2	1237.5	1235.8	1234.2	1231.4	1227.4	1223.4	1219.4	1215.4	1215.7
30°	1206.0	1204.5	1203.1	1201.7	1200.3	1197.6	1193.6	1189.6	1185.6	1181.6	1181.6
32.5°	1171.1	1169.2	1167.3	1165.5	1163.6	1161.1	1158.1	1155.0	1151.9	1148.8	1147.2
35°	1115.0	1113.3	1111.6	1109.9	1108.2	1105.5	1101.7	1098.0	1094.3	1090.6	1088.9
37.5°	1057.5	1055.4	1053.2	1051.1	1048.9	1045.9	1042.2	1038.4	1034.7	1030.9	1028.8
40°	1017.6	1015.9	1014.2	1012.4	1010.7	1007.9	1003.9	999.9	995.9	992.0	989.7
42.5°	977.5	975.7	973.7	971.8	969.8	966.9	962.9	958.9	954.9	951.0	948.7
45°	913.8	912.6	911.5	910.4	909.2	906.8	903.1	899.4	895.7	891.9	888.6
47.5°	850.4	848.8	847.2	845.5	843.8	841.3	837.8	834.3	830.9	827.4	824.0
50°	807.4	806.0	804.5	803.2	801.7	799.2	795.4	791.7	788.0	784.3	781.2
52.5°	762.3	761.3	760.3	759.4	758.4	755.9	752.0	748.1	744.2	740.2	737.5
55°	693.3	693.1	692.8	692.5	692.2	690.2	686.5	682.8	679.1	675.4	672.3
57.5°	627.7	626.7	625.7	624.8	623.9	621.9	618.9	616.0	613.0	610.0	607.2
60°	580.6	580.2	580.0	579.7	579.4	577.6	574.1	570.7	567.3	563.9	561.3
62.5°	538.5	537.8	537.0	536.3	535.6	533.5	530.0	526.6	523.3	519.8	517.2
65°	472.9	471.5	470.0	468.6	467.2	465.0	462.2	459.3	456.5	453.7	451.4
67.5°	403.4	402.2	401.0	399.7	398.4	396.7	394.5	392.4	390.2	388.1	386.0
70°	361.4	359.7	358.0	356.3	354.6	352.9	351.1	349.4	347.7	346.0	344.1
72.5°	317.3	316.1	314.8	313.6	312.3	310.7	308.8	306.8	304.9	303.0	301.2
75°	249.9	248.7	247.6	246.5	245.3	244.3	243.5	242.6	241.8	240.9	239.5
77.5°	190.2	189.6	188.9	188.3	187.7	186.9	185.8	184.8	183.8	182.8	181.8
80°	151.2	150.3	149.5	148.6	147.8	147.1	146.5	145.9	145.4	144.8	144.6
82.5°	113.3	113.1	112.9	112.8	112.6	112.4	112.3	112.3	112.1	112.0	111.5
85°	66.6	66.0	65.5	64.9	64.3	64.1	64.1	64.1	64.1	64.1	63.5
87.5°	26.8	26.5	26.2	25.8	25.5	25.5	25.8	26.0	26.3	26.5	26.4
90°	0.8	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2
92.5°	19.7	21.0	22.2	23.4	24.6	25.9	27.2	28.5	29.9	31.2	31.8
95°	48.0	49.2	50.5	51.9	53.1	54.5	55.8	57.3	58.8	60.3	61.0
97.5°	85.3	86.3	87.2	88.1	89.0	90.0	91.1	92.1	93.2	94.2	95.1
100°	110.7	111.8	112.8	113.9	115.0	116.0	116.9	117.8	118.7	119.6	120.2
102.5°	140.0	140.6	141.3	141.9	142.6	143.5	144.7	145.9	147.1	148.3	148.8
105°	183.1	183.4	183.8	184.2	184.6	185.6	187.2	188.8	190.5	192.1	192.1
107.5°	233.3	233.5	233.7	233.9	234.2	234.6	235.2	235.9	236.5	237.2	237.7
110°	264.5	264.9	265.2	265.5	266.0	266.3	266.7	267.0	267.4	267.7	268.5



TEST NUMBER: P332079-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	297.0	297.3	297.5	297.7	297.9	298.1	298.2	298.2	298.3	298.3	299.2
115°	345.8	346.4	347.0	347.5	348.1	348.1	347.8	347.4	347.1	346.7	346.9
117.5°	395.0	395.4	395.7	396.2	396.5	396.4	396.0	395.5	395.0	394.5	394.5
120°	425.7	426.7	427.8	428.9	430.0	430.1	429.2	428.3	427.4	426.5	426.2
122.5°	457.5	458.4	459.1	459.9	460.7	460.9	460.4	459.9	459.5	459.0	458.5
125°	506.2	506.8	507.3	507.8	508.3	508.5	508.1	507.8	507.4	507.0	506.3
127.5°	551.1	552.3	553.4	554.6	555.8	556.1	555.7	555.4	555.0	554.6	553.5
130°	581.1	582.5	584.0	585.4	586.9	587.3	586.8	586.2	585.7	585.1	584.4
132.5°	611.1	612.5	613.9	615.4	616.9	617.3	616.9	616.5	616.1	615.7	614.9
135°	656.8	657.9	658.9	660.0	661.1	661.5	661.4	661.2	661.0	660.8	660.1
137.5°	699.1	700.0	700.9	701.8	702.7	703.4	703.8	704.3	704.8	705.2	704.5
140°	728.4	729.3	730.2	731.1	732.0	732.5	732.7	732.9	733.1	733.3	733.1
142.5°	755.0	755.9	756.9	757.8	758.7	759.3	759.6	759.9	760.3	760.6	760.4
145°	796.7	797.1	797.4	797.9	798.2	798.7	799.2	799.7	800.3	800.8	800.6
147.5°	833.2	833.9	834.5	835.2	835.8	836.4	836.9	837.4	837.9	838.5	838.5
150°	858.6	859.0	859.3	859.7	860.1	860.4	860.8	861.1	861.5	861.9	861.9
152.5°	879.5	880.0	880.4	880.9	881.4	881.8	882.1	882.2	882.5	882.7	883.0
155°	912.3	912.3	912.3	912.3	912.3	912.4	912.6	912.7	913.0	913.1	913.9
157.5°	940.3	940.1	939.9	939.6	939.5	939.4	939.6	939.7	939.9	940.0	940.8
160°	957.9	957.5	957.2	956.8	956.4	956.3	956.3	956.3	956.3	956.3	957.2
162.5°	973.5	973.0	972.5	972.0	971.5	971.3	971.4	971.6	971.8	971.9	972.8
165°	993.7	993.1	992.6	992.1	991.6	991.2	991.2	991.2	991.2	991.2	992.3
167.5°	1009.8	1009.1	1008.4	1007.6	1006.9	1006.7	1006.8	1006.9	1007.1	1007.2	1008.4
170°	1019.0	1018.2	1017.5	1016.8	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9
172.5°	1026.1	1025.4	1024.7	1023.9	1023.2	1022.8	1022.8	1022.8	1022.8	1022.8	1023.9
175°	1033.6	1032.8	1032.1	1031.4	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4
177.5°	1036.7	1036.1	1035.5	1034.9	1034.4	1034.0	1034.0	1034.0	1034.0	1034.0	1034.9
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332079-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4	1490.4
2.5°	1484.7	1487.0	1489.3	1490.4	1490.1	1489.9	1489.6	1489.5
5°	1476.9	1479.8	1482.6	1483.8	1483.2	1482.6	1482.1	1481.5
7.5°	1461.3	1463.8	1466.4	1467.5	1467.1	1466.8	1466.5	1466.2
10°	1446.9	1449.4	1452.0	1453.0	1452.5	1451.9	1451.3	1450.7
12.5°	1431.2	1433.1	1434.9	1435.7	1435.3	1435.0	1434.7	1434.4
15°	1402.7	1405.0	1407.3	1407.6	1405.9	1404.2	1402.5	1400.8
17.5°	1366.8	1368.4	1369.9	1370.4	1369.9	1369.2	1368.6	1368.0
20°	1340.3	1341.4	1342.6	1342.6	1341.8	1340.9	1340.1	1339.2
22.5°	1312.1	1313.0	1313.9	1313.9	1312.8	1311.7	1310.6	1309.5
25°	1265.5	1265.8	1266.1	1265.8	1264.9	1264.0	1263.2	1262.3
27.5°	1215.9	1216.1	1216.3	1215.9	1214.9	1213.7	1212.7	1211.6
30°	1181.6	1181.6	1181.6	1180.6	1178.6	1176.6	1174.6	1172.6
32.5°	1145.6	1144.0	1142.4	1141.1	1140.0	1138.9	1137.8	1136.8
35°	1087.2	1085.5	1083.8	1082.2	1080.8	1079.4	1077.9	1076.5
37.5°	1026.8	1024.7	1022.7	1021.2	1020.3	1019.4	1018.5	1017.6
40°	987.4	985.1	982.8	981.1	980.0	978.8	977.7	976.6
42.5°	946.4	944.1	941.8	940.1	939.0	937.8	936.7	935.6
45°	885.2	881.7	878.3	875.9	874.5	873.0	871.6	870.2
47.5°	820.7	817.3	813.9	811.6	810.4	809.1	807.9	806.7
50°	778.0	774.9	771.8	769.4	767.7	766.0	764.3	762.5
52.5°	734.9	732.2	729.5	727.3	725.6	723.9	722.2	720.5
55°	669.1	666.0	662.8	660.6	659.2	657.7	656.3	654.8
57.5°	604.5	601.7	598.8	596.6	595.0	593.4	591.7	590.0
60°	558.8	556.2	553.7	551.6	550.2	548.8	547.4	545.9
62.5°	514.7	512.1	509.6	507.8	506.8	505.8	504.9	503.9
65°	449.1	446.9	444.6	443.0	442.1	441.3	440.4	439.6
67.5°	384.1	382.0	380.1	378.5	377.3	376.1	374.9	373.7
70°	342.0	340.1	338.0	336.3	334.9	333.5	332.1	330.7
72.5°	299.5	297.7	295.9	294.6	293.9	293.2	292.4	291.7
75°	238.1	236.7	235.2	234.1	233.3	232.4	231.5	230.6
77.5°	180.8	179.9	178.9	178.4	178.4	178.4	178.4	178.4
80°	144.2	144.0	143.7	143.6	143.6	143.6	143.6	143.6
82.5°	111.0	110.5	110.0	109.6	109.3	109.2	108.9	108.7
85°	62.9	62.4	61.8	61.6	61.6	61.6	61.6	61.6
87.5°	26.3	26.3	26.1	26.1	26.2	26.3	26.3	26.4
90°	21.0	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	32.4	33.0	33.6	33.8	33.5	33.3	33.1	32.9
95°	61.6	62.4	63.1	63.5	63.5	63.5	63.5	63.5
97.5°	95.9	96.8	97.6	97.9	97.9	97.8	97.8	97.7
100°	120.7	121.2	121.8	122.3	122.6	122.9	123.4	123.7
102.5°	149.4	149.9	150.4	150.7	150.6	150.5	150.5	150.4
105°	192.1	192.1	192.1	192.2	192.6	193.0	193.3	193.7
107.5°	238.3	238.9	239.5	239.6	239.5	239.2	239.0	238.8
110°	269.2	269.9	270.7	270.8	270.4	270.1	269.8	269.4



TEST NUMBER: P332079-930

CATALOG NUMBER: S123DIP-S1165D1025U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	300.1	300.9	301.8	302.2	302.1	302.1	302.0	301.9
115°	347.1	347.2	347.4	347.4	347.2	347.1	346.9	346.7
117.5°	394.4	394.4	394.4	394.1	393.6	393.1	392.6	392.1
120°	426.1	425.9	425.7	425.4	425.1	424.8	424.4	424.0
122.5°	458.0	457.6	457.1	456.6	456.2	455.6	455.1	454.6
125°	505.6	504.8	504.1	503.4	502.7	502.0	501.2	500.5
127.5°	552.5	551.5	550.5	549.6	548.8	547.9	547.1	546.3
130°	583.7	582.9	582.3	581.2	580.0	578.7	577.5	576.2
132.5°	614.0	613.2	612.3	611.4	610.4	609.4	608.5	607.5
135°	659.4	658.7	657.9	657.4	657.0	656.6	656.3	656.0
137.5°	703.8	703.0	702.2	701.5	700.8	700.1	699.4	698.8
140°	732.9	732.7	732.5	731.8	730.6	729.3	728.1	726.8
142.5°	760.3	760.1	759.9	759.3	758.3	757.3	756.4	755.4
145°	800.5	800.3	800.1	799.6	798.9	798.2	797.4	796.7
147.5°	838.5	838.5	838.5	837.9	836.8	835.7	834.6	833.6
150°	861.9	861.9	861.9	861.3	860.2	859.2	858.0	857.0
152.5°	883.3	883.5	883.9	883.5	882.6	881.7	880.7	879.8
155°	914.6	915.3	916.0	915.7	914.5	913.2	911.9	910.7
157.5°	941.5	942.2	943.1	942.9	941.9	940.9	939.9	938.8
160°	958.1	959.0	959.9	959.9	959.3	958.5	957.8	957.1
162.5°	973.7	974.6	975.5	975.3	974.2	973.1	971.9	970.8
165°	993.4	994.5	995.6	995.5	994.3	993.0	991.7	990.4
167.5°	1009.4	1010.6	1011.7	1011.7	1010.6	1009.4	1008.4	1007.2
170°	1018.2	1019.5	1020.8	1020.8	1019.5	1018.2	1016.9	1015.7
172.5°	1025.1	1026.2	1027.3	1027.3	1026.0	1024.7	1023.4	1022.1
175°	1032.5	1033.6	1034.7	1034.5	1033.3	1032.0	1030.8	1029.5
177.5°	1035.8	1036.7	1037.5	1037.5	1036.5	1035.4	1034.5	1033.4
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0

(END OF REPORT)