

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331894-930

Luminaire Tested: **S123DIP-S340D1025U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331894-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S340D1025U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4211.0 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	59	47	45	44	32	31	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26	20
3	77	68	61	56	69	61	56	51	48	44	41	36	34	31	25	24	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	23	21	19	15
5	65	54	46	40	58	48	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	40	35	53	43	37	32	35	30	26	26	23	20	18	16	15	12
7	55	43	36	30	49	39	33	28	31	26	23	24	20	18	17	15	13	10
8	51	39	32	27	46	35	29	24	28	24	20	22	18	16	15	13	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8
10	44	33	26	21	40	30	23	19	24	19	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4219	4219	4219	4219
5°	5032	4238	3756	4238
10°	6299	4217	3393	4217
15°	7725	4182	3158	4182
20°	9203	4129	3007	4129
25°	9772	4065	2973	4065
30°	8376	4018	2988	4018
35°	5825	3951	3020	3951
40°	4388	3873	3011	3873
45°	3643	3755	2973	3755
50°	3264	3518	2946	3518
55°	3051	3262	2909	3262
60°	2863	2992	2878	2992
65°	2690	2728	2786	2728
70°	2521	2426	2653	2426
75°	2258	2125	2433	2125
80°	1977	1742	2095	1742
85°	1556	1272	1408	1272



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.6	0.9
10°-20°	123.8	2.9
20°-30°	207.8	4.9
30°-40°	235.3	5.6
40°-50°	211.0	5.0
50°-60°	170.3	4.0
60°-70°	118.7	2.8
70°-80°	62.4	1.5
80°-90°	18.4	0.4
90°-100°	223.7	5.3
100°-110°	633.5	15.0
110°-120°	623.2	14.8
120°-130°	497.1	11.8
130°-140°	391.9	9.3
140°-150°	292.5	6.9
150°-160°	203.9	4.8
160°-170°	119.8	2.8
170°-180°	39.0	0.9
0°-30°	370.3	8.8
0°-40°	605.6	14.4
0°-60°	986.9	23.4
0°-90°	1186.3	28.2
90°-120°	1480.5	35.2
90°-150°	2662.0	63.2
90°-180°	3025.0	71.8
0°-180°	4211.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	392	392	392	392	392	
5°	466	392	348	392	466	48
15°	693	375	283	375	693	200
25°	823	342	250	342	823	361
35°	443	301	230	301	443	288
45°	239	247	195	247	239	189
55°	163	174	155	174	163	146
65°	106	107	109	107	106	105
75°	54	51	58	51	54	58
85°	13	10	11	10	13	15
90°	24	2	24	2	24	13
95°	94	28	94	28	94	170
105°	1035	94	1035	94	1035	1021
115°	1259	167	1259	167	1259	1223
125°	993	232	993	232	993	900
135°	805	272	805	272	805	624
145°	629	310	629	310	629	400
155°	522	352	522	352	522	243
165°	455	385	455	385	455	130
175°	409	401	409	401	409	40
180°	402	402	402	402	402	



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	416.0	415.7	415.0	415.6	414.3	412.7	412.5	411.0	406.6	406.3	405.1
5°	465.7	464.2	464.0	463.8	461.1	457.5	450.7	450.1	441.0	436.5	431.0
7.5°	530.1	530.8	528.1	525.7	517.6	512.2	504.8	495.5	484.3	472.9	465.4
10°	576.3	582.5	574.8	569.4	564.5	555.2	544.4	530.8	517.4	501.7	489.7
12.5°	625.8	628.8	627.3	622.3	614.7	600.5	581.3	566.4	554.0	527.7	517.1
15°	693.2	704.8	697.4	680.4	680.7	667.2	642.2	614.7	600.0	577.0	545.7
17.5°	765.2	766.5	763.4	749.2	739.7	721.1	698.0	671.6	642.0	614.2	580.9
20°	803.4	802.3	795.7	788.2	771.9	757.5	732.2	702.8	664.8	637.4	601.1
22.5°	824.7	822.8	819.6	813.4	799.9	784.4	761.7	729.5	693.3	655.7	613.8
25°	822.8	825.2	825.7	823.9	819.2	809.9	792.1	766.4	730.3	681.8	638.2
27.5°	748.4	751.9	762.0	771.0	781.1	791.3	789.9	777.2	750.5	708.7	655.3
30°	673.9	666.3	685.1	708.8	725.0	753.5	769.4	770.4	755.4	719.5	667.4
32.5°	570.5	578.9	587.3	616.4	651.8	683.7	715.5	741.0	744.0	720.1	674.6
35°	443.3	453.8	469.0	484.1	522.1	554.8	610.7	659.3	698.0	703.1	675.2
37.5°	357.3	362.4	372.0	387.3	412.1	450.9	494.0	555.5	611.6	653.4	655.2
40°	312.3	313.8	324.6	336.1	356.3	388.2	427.1	481.5	548.7	607.1	631.4
42.5°	278.5	281.8	286.5	297.6	313.6	337.6	373.8	418.7	480.4	547.5	595.0
45°	239.3	243.1	246.0	253.4	264.8	281.0	306.1	347.2	394.1	463.4	527.4
47.5°	213.4	213.7	215.8	221.4	229.2	241.3	259.2	285.5	328.6	384.8	450.5
50°	194.9	197.9	198.7	203.0	209.1	218.0	232.8	255.3	290.6	340.0	400.4
52.5°	181.8	182.7	184.8	188.0	193.3	200.2	213.1	230.6	258.4	300.5	356.0
55°	162.6	162.6	164.7	167.1	170.2	176.4	185.0	197.9	219.0	251.7	297.7
57.5°	144.8	145.8	147.2	148.0	150.6	154.7	161.8	171.7	187.4	212.5	249.1
60°	133.0	134.7	134.4	136.0	138.3	141.5	147.6	155.6	169.6	189.7	220.5
62.5°	122.6	122.5	122.5	124.3	126.5	129.6	133.6	140.5	152.5	170.3	196.5
65°	105.6	105.3	106.6	107.7	108.4	110.7	113.7	119.8	127.8	141.1	161.4
67.5°	90.5	89.4	90.1	90.5	91.8	93.6	96.4	100.2	106.5	117.2	132.5
70°	80.1	79.2	79.0	79.4	80.6	81.9	84.0	87.6	93.4	102.0	113.2
72.5°	69.5	68.9	68.8	69.7	70.2	71.1	72.6	75.8	80.6	87.0	97.4
75°	54.3	54.3	54.3	54.5	55.1	55.8	57.0	58.7	62.3	66.9	73.9
77.5°	40.7	40.7	40.4	40.4	41.3	41.6	41.8	43.5	45.5	48.5	53.6
80°	31.9	31.0	31.3	31.9	32.3	32.4	33.0	33.4	35.1	36.9	40.4
82.5°	23.7	22.9	23.0	23.9	24.0	24.1	24.7	25.2	25.8	27.4	29.4
85°	12.6	12.6	12.7	12.7	12.9	12.7	13.3	13.5	13.5	14.4	15.6
87.5°	9.3	9.1	9.1	9.1	9.1	9.0	9.0	9.0	8.9	9.2	8.9
90°	23.6	24.4	23.6	22.7	23.6	22.0	21.2	20.4	19.6	20.4	17.9
92.5°	39.2	40.7	39.9	42.3	43.8	48.0	54.4	68.5	94.4	125.1	137.7
95°	94.4	97.7	103.4	110.7	126.1	155.5	198.6	292.9	391.4	482.6	429.7
97.5°	257.0	264.0	286.0	322.6	382.6	480.0	585.0	730.3	800.1	747.9	547.6
100°	510.3	509.5	541.2	600.6	682.8	798.3	893.6	959.5	931.0	770.7	520.8
102.5°	748.5	767.3	793.8	840.8	904.8	978.0	1033.6	1035.7	937.5	728.4	481.8
105°	1035.2	1039.3	1065.3	1096.2	1133.7	1154.8	1139.4	1057.9	887.9	654.3	433.7
107.5°	1200.2	1207.7	1216.5	1226.9	1226.3	1197.3	1126.0	993.8	801.0	588.9	403.2
110°	1268.0	1269.6	1271.2	1264.7	1241.9	1184.9	1082.4	932.6	746.2	551.8	391.4



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1281.6	1281.2	1275.0	1254.9	1213.2	1140.0	1025.1	872.0	698.7	527.0	384.9
115°	1259.0	1254.9	1238.6	1202.8	1141.7	1053.0	933.4	791.8	641.3	500.5	382.5
117.5°	1187.0	1181.5	1158.1	1117.0	1053.4	963.4	856.0	733.8	606.6	484.9	383.9
120°	1127.2	1122.3	1102.7	1057.1	992.9	910.7	813.0	703.1	588.4	477.7	386.5
122.5°	1071.1	1064.9	1043.5	1002.5	945.3	869.0	778.5	679.1	573.4	473.1	391.1
125°	992.9	987.2	966.8	931.0	878.9	813.8	735.7	647.0	554.2	467.2	397.9
127.5°	928.4	923.2	904.8	874.2	827.8	768.6	698.1	619.0	537.3	464.2	405.8
130°	891.9	885.4	868.4	839.0	795.9	740.5	674.7	601.4	528.2	462.3	411.0
132.5°	856.1	851.6	836.4	807.1	766.6	713.9	652.5	585.1	519.7	461.6	414.9
135°	804.9	799.2	784.5	760.1	720.2	673.8	620.9	563.1	508.7	460.6	420.8
137.5°	750.6	746.9	734.6	709.8	676.3	636.1	590.5	543.2	499.0	458.9	424.6
140°	712.9	713.7	700.7	677.9	647.0	612.0	572.9	531.4	493.2	458.2	427.2
142.5°	677.8	678.6	666.8	646.7	620.3	589.9	556.0	520.3	488.0	456.9	429.2
145°	629.1	627.5	620.9	603.8	583.5	559.9	533.9	507.0	480.9	454.9	430.5
147.5°	589.1	588.4	582.2	570.6	555.2	538.4	517.4	496.1	474.1	451.8	430.5
150°	565.6	565.6	560.7	551.8	539.6	524.1	507.0	488.3	469.5	449.2	430.5
152.5°	546.1	546.1	543.2	534.8	525.2	512.4	497.3	481.1	464.4	446.0	428.5
155°	521.6	520.8	519.2	512.7	505.4	495.6	483.4	470.3	456.6	440.3	426.4
157.5°	499.4	499.5	498.2	493.3	487.0	479.3	469.9	459.0	447.8	435.2	423.7
160°	485.0	485.8	485.8	480.9	475.2	469.5	461.5	452.5	441.9	431.3	422.4
162.5°	472.0	472.8	472.8	468.6	464.9	459.8	452.3	444.7	436.0	427.4	419.8
165°	454.9	454.9	455.8	452.5	449.2	445.2	439.4	434.6	428.0	421.6	415.9
167.5°	438.6	438.6	439.4	437.2	435.7	432.8	429.5	425.7	420.4	415.7	412.0
170°	428.8	428.8	429.7	428.0	427.2	425.6	422.4	420.0	415.9	411.8	409.4
172.5°	419.8	420.4	421.9	420.3	420.1	419.1	416.5	414.7	411.3	408.5	407.4
175°	409.4	410.2	411.0	410.2	410.2	410.2	408.5	407.7	406.1	404.5	404.5
177.5°	403.3	403.3	404.6	404.0	404.6	404.6	404.0	403.3	402.7	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	404.1	403.0	401.8	399.7	397.8	395.3	394.4	393.5	390.8	388.4	386.5
5°	428.8	424.3	417.7	411.6	406.7	400.0	396.2	392.2	386.5	381.4	377.2
7.5°	454.7	445.7	435.4	424.3	413.8	403.8	395.7	388.5	380.5	373.0	367.0
10°	475.2	462.3	447.8	432.3	419.0	406.1	395.3	385.8	375.5	366.6	359.1
12.5°	498.6	479.5	459.6	440.7	424.9	407.0	393.9	381.8	370.1	359.5	351.1
15°	526.3	502.0	478.4	452.4	428.5	406.1	390.5	375.3	361.8	350.8	340.1
17.5°	551.5	524.0	492.9	461.3	432.4	405.9	384.1	366.9	350.0	336.6	326.0
20°	565.8	534.5	499.4	466.5	434.6	405.0	381.0	360.5	342.3	328.0	316.1
22.5°	578.1	541.4	505.1	469.9	434.4	402.5	375.4	354.2	334.5	320.6	307.9
25°	590.9	547.0	510.5	469.4	429.7	396.6	366.2	342.3	322.5	306.1	293.1
27.5°	601.9	546.7	503.4	459.0	422.1	389.0	356.5	330.8	309.9	292.1	278.8
30°	609.1	547.4	495.9	452.1	414.8	380.7	349.1	323.3	301.3	283.2	270.7
32.5°	613.7	546.9	489.1	442.3	403.2	373.0	341.0	314.3	291.6	273.9	261.9
35°	616.4	543.6	477.3	422.2	384.7	355.1	328.4	300.7	277.0	260.4	246.7
37.5°	611.0	536.5	463.7	402.8	361.7	332.7	310.1	286.6	263.8	245.6	233.8
40°	602.7	532.0	453.0	389.1	345.8	318.0	298.8	275.6	253.2	235.9	224.9
42.5°	586.7	522.8	441.3	374.0	329.5	301.6	283.9	264.5	243.3	227.1	216.1
45°	547.8	502.6	423.7	351.2	305.2	276.4	260.8	246.7	227.6	211.8	202.3
47.5°	493.7	472.2	398.4	327.2	279.9	252.2	235.9	224.7	210.7	197.9	188.8
50°	456.2	447.3	381.2	310.7	263.1	235.9	220.3	210.1	200.0	187.3	179.0
52.5°	412.9	418.4	361.2	293.8	245.9	219.2	204.6	196.4	187.3	176.8	169.5
55°	352.0	371.9	326.5	265.1	220.3	194.9	181.0	173.8	168.4	160.7	154.4
57.5°	294.9	320.2	289.0	235.7	195.2	173.3	160.0	152.1	148.7	144.6	139.7
60°	261.0	286.0	262.3	216.0	178.4	157.4	145.7	139.0	135.6	132.7	128.6
62.5°	230.7	256.1	236.2	195.9	161.8	142.4	132.2	125.6	123.0	121.6	118.0
65°	189.1	211.0	197.7	164.7	138.1	121.0	111.7	107.1	104.7	104.1	101.8
67.5°	153.9	170.6	160.9	136.6	115.7	100.9	93.0	89.1	87.2	87.0	85.3
70°	130.9	146.4	139.0	117.0	99.0	87.4	80.6	77.1	76.0	75.8	74.8
72.5°	112.9	123.8	117.9	99.5	85.6	75.1	70.0	66.4	65.2	65.5	64.8
75°	83.6	91.7	88.3	75.6	64.4	57.6	53.4	51.1	50.0	50.5	49.7
77.5°	60.2	65.3	62.2	53.4	46.5	41.6	38.5	37.1	36.0	36.0	35.7
80°	45.4	48.4	46.7	41.4	35.7	31.6	29.0	28.1	27.6	27.3	27.1
82.5°	32.4	34.9	32.9	29.3	25.4	22.8	21.4	20.2	19.8	19.9	19.7
85°	16.3	17.3	16.6	14.3	12.7	11.6	10.8	10.3	9.9	10.0	9.7
87.5°	8.7	8.4	7.4	6.5	5.9	4.9	4.6	4.0	4.0	4.3	4.6
90°	15.5	13.0	10.6	9.0	7.3	4.9	3.3	1.6	3.3	4.9	7.3
92.5°	103.4	68.3	47.0	35.0	28.1	21.9	15.0	10.1	15.0	21.9	28.1
95°	296.2	175.0	105.8	74.0	52.9	39.1	30.1	27.6	30.1	39.1	52.9
97.5°	325.1	188.3	122.2	87.9	67.0	55.0	48.0	47.2	48.0	55.0	67.0
100°	306.8	186.4	129.4	97.7	78.1	66.8	61.1	60.3	61.1	66.8	78.1
102.5°	291.1	189.0	137.9	108.8	91.2	80.4	75.3	73.9	75.3	80.4	91.2
105°	280.0	196.2	152.2	126.9	111.5	101.7	96.9	94.4	96.9	101.7	111.5
107.5°	279.2	209.5	170.9	147.5	133.0	123.4	118.6	116.2	118.6	123.4	133.0
110°	282.4	220.5	183.9	161.1	147.3	138.4	134.3	131.8	134.3	138.4	147.3



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	288.9	231.6	197.6	175.5	161.6	152.7	148.6	146.2	148.6	152.7	161.6
115°	299.5	249.8	218.9	197.0	183.1	175.0	170.1	166.8	170.1	175.0	183.1
117.5°	313.5	269.2	238.6	218.3	202.8	195.3	191.3	187.5	191.3	195.3	202.8
120°	323.9	281.6	252.3	232.0	216.5	208.3	204.2	201.8	204.2	208.3	216.5
122.5°	333.7	294.6	266.0	244.3	229.5	220.7	216.6	214.2	216.6	220.7	229.5
125°	349.1	313.3	284.9	262.9	247.4	238.5	233.6	232.0	233.6	238.5	247.4
127.5°	361.8	329.6	302.1	280.1	263.0	253.9	247.9	245.5	247.9	253.9	263.0
130°	370.3	339.3	312.5	290.5	273.5	263.7	256.3	253.9	256.3	263.7	273.5
132.5°	378.1	347.8	321.6	300.3	283.2	271.5	263.5	260.4	263.5	271.5	283.2
135°	388.2	360.5	335.3	313.3	296.2	284.1	275.1	271.8	275.1	284.1	296.2
137.5°	395.7	369.3	345.0	324.7	307.8	294.7	286.0	282.6	286.0	294.7	307.8
140°	399.6	375.2	351.6	331.3	315.0	301.9	293.8	289.8	293.8	301.9	315.0
142.5°	403.5	379.8	356.8	337.7	321.5	309.7	300.9	297.5	300.9	309.7	321.5
145°	407.7	385.7	364.6	345.8	332.1	319.8	312.5	310.1	312.5	319.8	332.1
147.5°	410.3	390.6	371.3	355.3	341.9	331.4	324.2	322.8	324.2	331.4	341.9
150°	411.0	393.9	375.2	360.5	349.1	338.5	332.1	331.3	332.1	338.5	349.1
152.5°	412.3	395.8	379.8	365.7	355.6	346.3	339.8	339.7	339.8	346.3	355.6
155°	412.6	399.6	385.7	374.4	365.4	357.3	352.4	352.4	352.4	357.3	365.4
157.5°	413.4	401.7	390.6	381.8	374.2	367.0	363.1	362.5	363.1	367.0	374.2
160°	413.4	403.7	393.9	385.7	380.0	373.6	370.3	370.3	370.3	373.6	380.0
162.5°	412.8	404.3	395.8	389.0	383.9	378.8	376.2	376.2	376.2	378.8	383.9
165°	411.0	405.3	398.8	393.1	389.8	385.7	384.1	384.9	384.1	385.7	389.8
167.5°	409.7	405.1	400.4	396.8	394.5	391.4	390.6	391.6	390.6	391.4	394.5
170°	407.7	404.5	400.4	398.8	397.1	394.7	393.9	395.5	393.9	394.7	397.1
172.5°	407.1	404.5	401.0	400.1	399.1	397.3	397.1	398.1	397.1	397.3	399.1
175°	405.3	403.7	402.0	401.2	401.2	399.6	400.4	401.2	400.4	399.6	401.2
177.5°	404.0	402.7	402.0	402.0	402.0	401.4	402.0	402.7	402.0	401.4	402.0
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	385.5	384.4	382.9	380.7	378.8	375.9	375.9	376.3	376.3	376.3	375.9
5°	373.8	371.0	367.5	363.5	359.4	355.1	354.4	352.9	351.8	351.0	350.1
7.5°	361.4	356.4	351.4	345.8	340.7	336.6	333.6	331.2	329.6	327.9	326.7
10°	353.1	346.8	341.0	335.1	328.6	323.4	320.2	318.0	316.3	314.7	314.0
12.5°	343.2	336.1	329.5	323.9	316.9	311.6	308.5	307.4	305.5	302.2	300.6
15°	328.8	322.1	314.4	305.8	302.4	296.0	292.3	290.6	289.4	287.0	286.3
17.5°	316.4	307.8	299.0	292.6	286.3	281.0	279.0	276.9	275.4	273.4	272.7
20°	306.6	298.8	290.8	284.0	277.3	271.6	269.9	268.4	266.8	266.0	265.1
22.5°	296.5	288.8	282.1	275.7	268.6	264.9	263.1	261.4	260.3	259.7	258.9
25°	282.4	275.6	268.2	262.5	256.8	254.3	253.2	252.3	251.4	250.5	250.3
27.5°	269.9	262.4	256.4	251.0	247.0	244.9	243.8	243.4	243.5	243.9	244.1
30°	260.4	253.6	248.7	244.1	240.3	238.4	238.1	238.1	239.0	239.1	239.5
32.5°	251.8	246.1	241.2	236.8	233.9	232.6	233.3	233.3	233.9	234.4	235.1
35°	239.1	234.2	230.4	226.6	224.1	224.7	225.1	225.4	226.4	227.6	228.3
37.5°	227.1	222.8	218.8	215.9	214.7	215.7	216.7	217.4	218.6	219.5	220.2
40°	218.4	215.2	211.4	208.7	209.1	209.7	210.4	211.4	212.4	213.0	213.7
42.5°	210.3	207.0	204.1	201.9	202.4	203.2	203.6	204.1	205.2	206.3	206.7
45°	198.1	195.4	192.8	191.4	191.8	192.2	192.6	193.1	194.1	194.9	195.1
47.5°	184.3	182.5	180.7	179.4	180.0	179.9	180.3	181.6	181.8	182.3	183.4
50°	175.5	173.8	171.7	171.3	171.3	171.3	171.5	173.0	173.0	173.8	174.6
52.5°	165.8	164.7	163.4	162.7	162.3	162.3	163.1	163.9	164.2	165.3	166.1
55°	151.4	150.3	149.1	148.5	148.1	148.5	150.0	150.4	151.4	152.0	152.5
57.5°	136.4	135.5	134.6	134.3	134.2	134.7	135.5	136.6	136.9	138.7	139.5
60°	126.5	125.1	124.4	124.4	124.0	125.7	125.4	127.3	127.7	128.8	130.1
62.5°	116.3	114.5	114.2	114.2	114.8	115.3	115.8	116.6	117.6	119.0	120.1
65°	99.9	99.0	100.3	100.1	99.7	100.9	100.9	101.8	103.0	104.3	106.4
67.5°	84.4	83.9	84.0	84.0	84.5	85.2	85.8	86.6	88.0	89.4	90.7
70°	73.9	74.4	73.5	74.3	74.8	75.0	75.4	76.6	78.0	79.0	80.6
72.5°	63.7	63.7	63.8	64.1	64.7	65.0	65.4	66.7	68.3	69.1	70.4
75°	49.0	48.8	49.4	49.4	50.3	50.7	51.1	51.7	53.2	54.3	55.3
77.5°	35.8	36.0	35.9	36.5	36.3	36.4	37.5	38.1	38.2	40.5	41.0
80°	27.0	27.3	27.6	27.7	27.9	27.6	28.9	29.4	29.4	30.7	31.7
82.5°	19.4	19.6	20.1	20.3	20.3	20.7	20.8	21.2	21.7	22.3	23.5
85°	9.7	10.3	10.4	10.3	10.4	10.0	10.6	10.8	11.0	11.0	11.0
87.5°	4.8	5.3	5.6	6.3	6.6	7.3	7.1	6.9	7.1	7.7	7.4
90°	9.0	10.6	13.0	15.5	17.9	20.4	19.6	20.4	21.2	22.0	23.6
92.5°	35.0	47.0	68.3	103.4	137.7	125.1	94.4	68.5	54.4	48.0	43.8
95°	74.0	105.8	175.0	296.2	429.7	482.6	391.4	292.9	198.6	155.5	126.1
97.5°	87.9	122.2	188.3	325.1	547.6	747.9	800.1	730.3	585.0	480.0	382.6
100°	97.7	129.4	186.4	306.8	520.8	770.7	931.0	959.5	893.6	798.3	682.8
102.5°	108.8	137.9	189.0	291.1	481.8	728.4	937.5	1035.7	1033.6	978.0	904.8
105°	126.9	152.2	196.2	280.0	433.7	654.3	887.9	1057.9	1139.4	1154.8	1133.7
107.5°	147.5	170.9	209.5	279.2	403.2	588.9	801.0	993.8	1126.0	1197.3	1226.3
110°	161.1	183.9	220.5	282.4	391.4	551.8	746.2	932.6	1082.4	1184.9	1241.9



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	175.5	197.6	231.6	288.9	384.9	527.0	698.7	872.0	1025.1	1140.0	1213.2
115°	197.0	218.9	249.8	299.5	382.5	500.5	641.3	791.8	933.4	1053.0	1141.7
117.5°	218.3	238.6	269.2	313.5	383.9	484.9	606.6	733.8	856.0	963.4	1053.4
120°	232.0	252.3	281.6	323.9	386.5	477.7	588.4	703.1	813.0	910.7	992.9
122.5°	244.3	266.0	294.6	333.7	391.1	473.1	573.4	679.1	778.5	869.0	945.3
125°	262.9	284.9	313.3	349.1	397.9	467.2	554.2	647.0	735.7	813.8	878.9
127.5°	280.1	302.1	329.6	361.8	405.8	464.2	537.3	619.0	698.1	768.6	827.8
130°	290.5	312.5	339.3	370.3	411.0	462.3	528.2	601.4	674.7	740.5	795.9
132.5°	300.3	321.6	347.8	378.1	414.9	461.6	519.7	585.1	652.5	713.9	766.6
135°	313.3	335.3	360.5	388.2	420.8	460.6	508.7	563.1	620.9	673.8	720.2
137.5°	324.7	345.0	369.3	395.7	424.6	458.9	499.0	543.2	590.5	636.1	676.3
140°	331.3	351.6	375.2	399.6	427.2	458.2	493.2	531.4	572.9	612.0	647.0
142.5°	337.7	356.8	379.8	403.5	429.2	456.9	488.0	520.3	556.0	589.9	620.3
145°	345.8	364.6	385.7	407.7	430.5	454.9	480.9	507.0	533.9	559.9	583.5
147.5°	355.3	371.3	390.6	410.3	430.5	451.8	474.1	496.1	517.4	538.4	555.2
150°	360.5	375.2	393.9	411.0	430.5	449.2	469.5	488.3	507.0	524.1	539.6
152.5°	365.7	379.8	395.8	412.3	428.5	446.0	464.4	481.1	497.3	512.4	525.2
155°	374.4	385.7	399.6	412.6	426.4	440.3	456.6	470.3	483.4	495.6	505.4
157.5°	381.8	390.6	401.7	413.4	423.7	435.2	447.8	459.0	469.9	479.3	487.0
160°	385.7	393.9	403.7	413.4	422.4	431.3	441.9	452.5	461.5	469.5	475.2
162.5°	389.0	395.8	404.3	412.8	419.8	427.4	436.0	444.7	452.3	459.8	464.9
165°	393.1	398.8	405.3	411.0	415.9	421.6	428.0	434.6	439.4	445.2	449.2
167.5°	396.8	400.4	405.1	409.7	412.0	415.7	420.4	425.7	429.5	432.8	435.7
170°	398.8	400.4	404.5	407.7	409.4	411.8	415.9	420.0	422.4	425.6	427.2
172.5°	400.1	401.0	404.5	407.1	407.4	408.5	411.3	414.7	416.5	419.1	420.1
175°	401.2	402.0	403.7	405.3	404.5	404.5	406.1	407.7	408.5	410.2	410.2
177.5°	402.0	402.0	402.7	404.0	402.7	402.0	402.7	403.3	404.0	404.6	404.6
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	374.9	374.7	375.8	375.0	375.8	374.7	374.9	375.9	376.3	376.3	376.3
5°	348.9	349.5	347.6	347.6	347.6	349.5	348.9	350.1	351.0	351.8	352.9
7.5°	325.8	325.0	325.1	324.0	325.1	325.0	325.8	326.7	327.9	329.6	331.2
10°	311.7	310.5	310.1	310.4	310.1	310.5	311.7	314.0	314.7	316.3	318.0
12.5°	299.9	299.8	297.3	297.3	297.3	299.8	299.9	300.6	302.2	305.5	307.4
15°	286.3	282.7	282.3	283.4	282.3	282.7	286.3	286.3	287.0	289.4	290.6
17.5°	272.5	270.5	270.7	270.1	270.7	270.5	272.5	272.7	273.4	275.4	276.9
20°	265.1	264.0	263.8	262.5	263.8	264.0	265.1	265.1	266.0	266.8	268.4
22.5°	258.4	258.1	258.2	256.7	258.2	258.1	258.4	258.9	259.7	260.3	261.4
25°	250.1	251.1	250.3	250.3	250.3	251.1	250.1	250.3	250.5	251.4	252.3
27.5°	244.5	244.5	244.1	244.1	244.1	244.5	244.5	244.1	243.9	243.5	243.4
30°	240.3	240.1	240.4	240.4	240.4	240.1	240.3	239.5	239.1	239.0	238.1
32.5°	236.0	236.3	236.4	236.5	236.4	236.3	236.0	235.1	234.4	233.9	233.3
35°	229.4	229.7	230.2	229.8	230.2	229.7	229.4	228.3	227.6	226.4	225.4
37.5°	220.5	221.4	221.3	221.5	221.3	221.4	220.5	220.2	219.5	218.6	217.4
40°	213.9	214.4	214.3	214.3	214.3	214.4	213.9	213.7	213.0	212.4	211.4
42.5°	207.0	207.4	206.9	206.7	206.9	207.4	207.0	206.7	206.3	205.2	204.1
45°	195.8	195.4	196.0	195.3	196.0	195.4	195.8	195.1	194.9	194.1	193.1
47.5°	183.3	183.7	183.8	184.4	183.8	183.7	183.3	183.4	182.3	181.8	181.6
50°	175.0	176.1	176.1	175.9	176.1	176.1	175.0	174.6	173.8	173.0	173.0
52.5°	166.7	167.2	168.0	168.0	168.0	167.2	166.7	166.1	165.3	164.2	163.9
55°	154.0	154.4	154.8	155.0	154.8	154.4	154.0	152.5	152.0	151.4	150.4
57.5°	140.9	140.7	141.6	141.9	141.6	140.7	140.9	139.5	138.7	136.9	136.6
60°	131.6	131.6	133.1	133.7	133.1	131.6	131.6	130.1	128.8	127.7	127.3
62.5°	121.7	122.4	123.8	123.1	123.8	122.4	121.7	120.1	119.0	117.6	116.6
65°	107.3	108.8	108.7	109.4	108.7	108.8	107.3	106.4	104.3	103.0	101.8
67.5°	92.2	93.2	94.6	94.7	94.6	93.2	92.2	90.7	89.4	88.0	86.6
70°	82.0	83.0	83.7	84.3	83.7	83.0	82.0	80.6	79.0	78.0	76.6
72.5°	72.2	72.6	74.5	73.7	74.5	72.6	72.2	70.4	69.1	68.3	66.7
75°	56.6	58.0	59.1	58.5	59.1	58.0	56.6	55.3	54.3	53.2	51.7
77.5°	41.8	43.2	43.7	43.2	43.7	43.2	41.8	41.0	40.5	38.2	38.1
80°	33.0	32.9	34.0	33.8	34.0	32.9	33.0	31.7	30.7	29.4	29.4
82.5°	24.2	24.1	24.5	24.7	24.5	24.1	24.2	23.5	22.3	21.7	21.2
85°	11.7	12.3	11.6	11.4	11.6	12.3	11.7	11.0	11.0	11.0	10.8
87.5°	7.3	7.4	7.5	7.2	7.5	7.4	7.3	7.4	7.7	7.1	6.9
90°	22.7	23.6	24.4	23.6	24.4	23.6	22.7	23.6	22.0	21.2	20.4
92.5°	42.3	39.9	40.7	39.2	40.7	39.9	42.3	43.8	48.0	54.4	68.5
95°	110.7	103.4	97.7	94.4	97.7	103.4	110.7	126.1	155.5	198.6	292.9
97.5°	322.6	286.0	264.0	257.0	264.0	286.0	322.6	382.6	480.0	585.0	730.3
100°	600.6	541.2	509.5	510.3	509.5	541.2	600.6	682.8	798.3	893.6	959.5
102.5°	840.8	793.8	767.3	748.5	767.3	793.8	840.8	904.8	978.0	1033.6	1035.7
105°	1096.2	1065.3	1039.3	1035.2	1039.3	1065.3	1096.2	1133.7	1154.8	1139.4	1057.9
107.5°	1226.9	1216.5	1207.7	1200.2	1207.7	1216.5	1226.9	1226.3	1197.3	1126.0	993.8
110°	1264.7	1271.2	1269.6	1268.0	1269.6	1271.2	1264.7	1241.9	1184.9	1082.4	932.6



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1254.9	1275.0	1281.2	1281.6	1281.2	1275.0	1254.9	1213.2	1140.0	1025.1	872.0
115°	1202.8	1238.6	1254.9	1259.0	1254.9	1238.6	1202.8	1141.7	1053.0	933.4	791.8
117.5°	1117.0	1158.1	1181.5	1187.0	1181.5	1158.1	1117.0	1053.4	963.4	856.0	733.8
120°	1057.1	1102.7	1122.3	1127.2	1122.3	1102.7	1057.1	992.9	910.7	813.0	703.1
122.5°	1002.5	1043.5	1064.9	1071.1	1064.9	1043.5	1002.5	945.3	869.0	778.5	679.1
125°	931.0	966.8	987.2	992.9	987.2	966.8	931.0	878.9	813.8	735.7	647.0
127.5°	874.2	904.8	923.2	928.4	923.2	904.8	874.2	827.8	768.6	698.1	619.0
130°	839.0	868.4	885.4	891.9	885.4	868.4	839.0	795.9	740.5	674.7	601.4
132.5°	807.1	836.4	851.6	856.1	851.6	836.4	807.1	766.6	713.9	652.5	585.1
135°	760.1	784.5	799.2	804.9	799.2	784.5	760.1	720.2	673.8	620.9	563.1
137.5°	709.8	734.6	746.9	750.6	746.9	734.6	709.8	676.3	636.1	590.5	543.2
140°	677.9	700.7	713.7	712.9	713.7	700.7	677.9	647.0	612.0	572.9	531.4
142.5°	646.7	666.8	678.6	677.8	678.6	666.8	646.7	620.3	589.9	556.0	520.3
145°	603.8	620.9	627.5	629.1	627.5	620.9	603.8	583.5	559.9	533.9	507.0
147.5°	570.6	582.2	588.4	589.1	588.4	582.2	570.6	555.2	538.4	517.4	496.1
150°	551.8	560.7	565.6	565.6	565.6	560.7	551.8	539.6	524.1	507.0	488.3
152.5°	534.8	543.2	546.1	546.1	546.1	543.2	534.8	525.2	512.4	497.3	481.1
155°	512.7	519.2	520.8	521.6	520.8	519.2	512.7	505.4	495.6	483.4	470.3
157.5°	493.3	498.2	499.5	499.4	499.5	498.2	493.3	487.0	479.3	469.9	459.0
160°	480.9	485.8	485.8	485.0	485.8	485.8	480.9	475.2	469.5	461.5	452.5
162.5°	468.6	472.8	472.8	472.0	472.8	472.8	468.6	464.9	459.8	452.3	444.7
165°	452.5	455.8	454.9	454.9	454.9	455.8	452.5	449.2	445.2	439.4	434.6
167.5°	437.2	439.4	438.6	438.6	438.6	439.4	437.2	435.7	432.8	429.5	425.7
170°	428.0	429.7	428.8	428.8	428.8	429.7	428.0	427.2	425.6	422.4	420.0
172.5°	420.3	421.9	420.4	419.8	420.4	421.9	420.3	420.1	419.1	416.5	414.7
175°	410.2	411.0	410.2	409.4	410.2	411.0	410.2	410.2	410.2	408.5	407.7
177.5°	404.0	404.6	403.3	403.3	403.3	404.6	404.0	404.6	404.6	404.0	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	375.9	375.9	378.8	380.7	382.9	384.4	385.5	386.5	388.4	390.8	393.5
5°	354.4	355.1	359.4	363.5	367.5	371.0	373.8	377.2	381.4	386.5	392.2
7.5°	333.6	336.6	340.7	345.8	351.4	356.4	361.4	367.0	373.0	380.5	388.5
10°	320.2	323.4	328.6	335.1	341.0	346.8	353.1	359.1	366.6	375.5	385.8
12.5°	308.5	311.6	316.9	323.9	329.5	336.1	343.2	351.1	359.5	370.1	381.8
15°	292.3	296.0	302.4	305.8	314.4	322.1	328.8	340.1	350.8	361.8	375.3
17.5°	279.0	281.0	286.3	292.6	299.0	307.8	316.4	326.0	336.6	350.0	366.9
20°	269.9	271.6	277.3	284.0	290.8	298.8	306.6	316.1	328.0	342.3	360.5
22.5°	263.1	264.9	268.6	275.7	282.1	288.8	296.5	307.9	320.6	334.5	354.2
25°	253.2	254.3	256.8	262.5	268.2	275.6	282.4	293.1	306.1	322.5	342.3
27.5°	243.8	244.9	247.0	251.0	256.4	262.4	269.9	278.8	292.1	309.9	330.8
30°	238.1	238.4	240.3	244.1	248.7	253.6	260.4	270.7	283.2	301.3	323.3
32.5°	233.3	232.6	233.9	236.8	241.2	246.1	251.8	261.9	273.9	291.6	314.3
35°	225.1	224.7	224.1	226.6	230.4	234.2	239.1	246.7	260.4	277.0	300.7
37.5°	216.7	215.7	214.7	215.9	218.8	222.8	227.1	233.8	245.6	263.8	286.6
40°	210.4	209.7	209.1	208.7	211.4	215.2	218.4	224.9	235.9	253.2	275.6
42.5°	203.6	203.2	202.4	201.9	204.1	207.0	210.3	216.1	227.1	243.3	264.5
45°	192.6	192.2	191.8	191.4	192.8	195.4	198.1	202.3	211.8	227.6	246.7
47.5°	180.3	179.9	180.0	179.4	180.7	182.5	184.3	188.8	197.9	210.7	224.7
50°	171.5	171.3	171.3	171.3	171.7	173.8	175.5	179.0	187.3	200.0	210.1
52.5°	163.1	162.3	162.3	162.7	163.4	164.7	165.8	169.5	176.8	187.3	196.4
55°	150.0	148.5	148.1	148.5	149.1	150.3	151.4	154.4	160.7	168.4	173.8
57.5°	135.5	134.7	134.2	134.3	134.6	135.5	136.4	139.7	144.6	148.7	152.1
60°	125.4	125.7	124.0	124.4	124.4	125.1	126.5	128.6	132.7	135.6	139.0
62.5°	115.8	115.3	114.8	114.2	114.2	114.5	116.3	118.0	121.6	123.0	125.6
65°	100.9	100.9	99.7	100.1	100.3	99.0	99.9	101.8	104.1	104.7	107.1
67.5°	85.8	85.2	84.5	84.0	84.0	83.9	84.4	85.3	87.0	87.2	89.1
70°	75.4	75.0	74.8	74.3	73.5	74.4	73.9	74.8	75.8	76.0	77.1
72.5°	65.4	65.0	64.7	64.1	63.8	63.7	63.7	64.8	65.5	65.2	66.4
75°	51.1	50.7	50.3	49.4	49.4	48.8	49.0	49.7	50.5	50.0	51.1
77.5°	37.5	36.4	36.3	36.5	35.9	36.0	35.8	35.7	36.0	36.0	37.1
80°	28.9	27.6	27.9	27.7	27.6	27.3	27.0	27.1	27.3	27.6	28.1
82.5°	20.8	20.7	20.3	20.3	20.1	19.6	19.4	19.7	19.9	19.8	20.2
85°	10.6	10.0	10.4	10.3	10.4	10.3	9.7	9.7	10.0	9.9	10.3
87.5°	7.1	7.3	6.6	6.3	5.6	5.3	4.8	4.6	4.3	4.0	4.0
90°	19.6	20.4	17.9	15.5	13.0	10.6	9.0	7.3	4.9	3.3	1.6
92.5°	94.4	125.1	137.7	103.4	68.3	47.0	35.0	28.1	21.9	15.0	10.1
95°	391.4	482.6	429.7	296.2	175.0	105.8	74.0	52.9	39.1	30.1	27.6
97.5°	800.1	747.9	547.6	325.1	188.3	122.2	87.9	67.0	55.0	48.0	47.2
100°	931.0	770.7	520.8	306.8	186.4	129.4	97.7	78.1	66.8	61.1	60.3
102.5°	937.5	728.4	481.8	291.1	189.0	137.9	108.8	91.2	80.4	75.3	73.9
105°	887.9	654.3	433.7	280.0	196.2	152.2	126.9	111.5	101.7	96.9	94.4
107.5°	801.0	588.9	403.2	279.2	209.5	170.9	147.5	133.0	123.4	118.6	116.2
110°	746.2	551.8	391.4	282.4	220.5	183.9	161.1	147.3	138.4	134.3	131.8



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	698.7	527.0	384.9	288.9	231.6	197.6	175.5	161.6	152.7	148.6	146.2
115°	641.3	500.5	382.5	299.5	249.8	218.9	197.0	183.1	175.0	170.1	166.8
117.5°	606.6	484.9	383.9	313.5	269.2	238.6	218.3	202.8	195.3	191.3	187.5
120°	588.4	477.7	386.5	323.9	281.6	252.3	232.0	216.5	208.3	204.2	201.8
122.5°	573.4	473.1	391.1	333.7	294.6	266.0	244.3	229.5	220.7	216.6	214.2
125°	554.2	467.2	397.9	349.1	313.3	284.9	262.9	247.4	238.5	233.6	232.0
127.5°	537.3	464.2	405.8	361.8	329.6	302.1	280.1	263.0	253.9	247.9	245.5
130°	528.2	462.3	411.0	370.3	339.3	312.5	290.5	273.5	263.7	256.3	253.9
132.5°	519.7	461.6	414.9	378.1	347.8	321.6	300.3	283.2	271.5	263.5	260.4
135°	508.7	460.6	420.8	388.2	360.5	335.3	313.3	296.2	284.1	275.1	271.8
137.5°	499.0	458.9	424.6	395.7	369.3	345.0	324.7	307.8	294.7	286.0	282.6
140°	493.2	458.2	427.2	399.6	375.2	351.6	331.3	315.0	301.9	293.8	289.8
142.5°	488.0	456.9	429.2	403.5	379.8	356.8	337.7	321.5	309.7	300.9	297.5
145°	480.9	454.9	430.5	407.7	385.7	364.6	345.8	332.1	319.8	312.5	310.1
147.5°	474.1	451.8	430.5	410.3	390.6	371.3	355.3	341.9	331.4	324.2	322.8
150°	469.5	449.2	430.5	411.0	393.9	375.2	360.5	349.1	338.5	332.1	331.3
152.5°	464.4	446.0	428.5	412.3	395.8	379.8	365.7	355.6	346.3	339.8	339.7
155°	456.6	440.3	426.4	412.6	399.6	385.7	374.4	365.4	357.3	352.4	352.4
157.5°	447.8	435.2	423.7	413.4	401.7	390.6	381.8	374.2	367.0	363.1	362.5
160°	441.9	431.3	422.4	413.4	403.7	393.9	385.7	380.0	373.6	370.3	370.3
162.5°	436.0	427.4	419.8	412.8	404.3	395.8	389.0	383.9	378.8	376.2	376.2
165°	428.0	421.6	415.9	411.0	405.3	398.8	393.1	389.8	385.7	384.1	384.9
167.5°	420.4	415.7	412.0	409.7	405.1	400.4	396.8	394.5	391.4	390.6	391.6
170°	415.9	411.8	409.4	407.7	404.5	400.4	398.8	397.1	394.7	393.9	395.5
172.5°	411.3	408.5	407.4	407.1	404.5	401.0	400.1	399.1	397.3	397.1	398.1
175°	406.1	404.5	404.5	405.3	403.7	402.0	401.2	401.2	399.6	400.4	401.2
177.5°	402.7	402.0	402.7	404.0	402.7	402.0	402.0	402.0	401.4	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	394.4	395.3	397.8	399.7	401.8	403.0	404.1	405.1	406.3	406.6	411.0
5°	396.2	400.0	406.7	411.6	417.7	424.3	428.8	431.0	436.5	441.0	450.1
7.5°	395.7	403.8	413.8	424.3	435.4	445.7	454.7	465.4	472.9	484.3	495.5
10°	395.3	406.1	419.0	432.3	447.8	462.3	475.2	489.7	501.7	517.4	530.8
12.5°	393.9	407.0	424.9	440.7	459.6	479.5	498.6	517.1	527.7	554.0	566.4
15°	390.5	406.1	428.5	452.4	478.4	502.0	526.3	545.7	577.0	600.0	614.7
17.5°	384.1	405.9	432.4	461.3	492.9	524.0	551.5	580.9	614.2	642.0	671.6
20°	381.0	405.0	434.6	466.5	499.4	534.5	565.8	601.1	637.4	664.8	702.8
22.5°	375.4	402.5	434.4	469.9	505.1	541.4	578.1	613.8	655.7	693.3	729.5
25°	366.2	396.6	429.7	469.4	510.5	547.0	590.9	638.2	681.8	730.3	766.4
27.5°	356.5	389.0	422.1	459.0	503.4	546.7	601.9	655.3	708.7	750.5	777.2
30°	349.1	380.7	414.8	452.1	495.9	547.4	609.1	667.4	719.5	755.4	770.4
32.5°	341.0	373.0	403.2	442.3	489.1	546.9	613.7	674.6	720.1	744.0	741.0
35°	328.4	355.1	384.7	422.2	477.3	543.6	616.4	675.2	703.1	698.0	659.3
37.5°	310.1	332.7	361.7	402.8	463.7	536.5	611.0	655.2	653.4	611.6	555.5
40°	298.8	318.0	345.8	389.1	453.0	532.0	602.7	631.4	607.1	548.7	481.5
42.5°	283.9	301.6	329.5	374.0	441.3	522.8	586.7	595.0	547.5	480.4	418.7
45°	260.8	276.4	305.2	351.2	423.7	502.6	547.8	527.4	463.4	394.1	347.2
47.5°	235.9	252.2	279.9	327.2	398.4	472.2	493.7	450.5	384.8	328.6	285.5
50°	220.3	235.9	263.1	310.7	381.2	447.3	456.2	400.4	340.0	290.6	255.3
52.5°	204.6	219.2	245.9	293.8	361.2	418.4	412.9	356.0	300.5	258.4	230.6
55°	181.0	194.9	220.3	265.1	326.5	371.9	352.0	297.7	251.7	219.0	197.9
57.5°	160.0	173.3	195.2	235.7	289.0	320.2	294.9	249.1	212.5	187.4	171.7
60°	145.7	157.4	178.4	216.0	262.3	286.0	261.0	220.5	189.7	169.6	155.6
62.5°	132.2	142.4	161.8	195.9	236.2	256.1	230.7	196.5	170.3	152.5	140.5
65°	111.7	121.0	138.1	164.7	197.7	211.0	189.1	161.4	141.1	127.8	119.8
67.5°	93.0	100.9	115.7	136.6	160.9	170.6	153.9	132.5	117.2	106.5	100.2
70°	80.6	87.4	99.0	117.0	139.0	146.4	130.9	113.2	102.0	93.4	87.6
72.5°	70.0	75.1	85.6	99.5	117.9	123.8	112.9	97.4	87.0	80.6	75.8
75°	53.4	57.6	64.4	75.6	88.3	91.7	83.6	73.9	66.9	62.3	58.7
77.5°	38.5	41.6	46.5	53.4	62.2	65.3	60.2	53.6	48.5	45.5	43.5
80°	29.0	31.6	35.7	41.4	46.7	48.4	45.4	40.4	36.9	35.1	33.4
82.5°	21.4	22.8	25.4	29.3	32.9	34.9	32.4	29.4	27.4	25.8	25.2
85°	10.8	11.6	12.7	14.3	16.6	17.3	16.3	15.6	14.4	13.5	13.5
87.5°	4.6	4.9	5.9	6.5	7.4	8.4	8.7	8.9	9.2	8.9	9.0
90°	3.3	4.9	7.3	9.0	10.6	13.0	15.5	17.9	20.4	19.6	20.4
92.5°	15.0	21.9	28.1	35.0	47.0	68.3	103.4	137.7	125.1	94.4	68.5
95°	30.1	39.1	52.9	74.0	105.8	175.0	296.2	429.7	482.6	391.4	292.9
97.5°	48.0	55.0	67.0	87.9	122.2	188.3	325.1	547.6	747.9	800.1	730.3
100°	61.1	66.8	78.1	97.7	129.4	186.4	306.8	520.8	770.7	931.0	959.5
102.5°	75.3	80.4	91.2	108.8	137.9	189.0	291.1	481.8	728.4	937.5	1035.7
105°	96.9	101.7	111.5	126.9	152.2	196.2	280.0	433.7	654.3	887.9	1057.9
107.5°	118.6	123.4	133.0	147.5	170.9	209.5	279.2	403.2	588.9	801.0	993.8
110°	134.3	138.4	147.3	161.1	183.9	220.5	282.4	391.4	551.8	746.2	932.6



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	148.6	152.7	161.6	175.5	197.6	231.6	288.9	384.9	527.0	698.7	872.0
115°	170.1	175.0	183.1	197.0	218.9	249.8	299.5	382.5	500.5	641.3	791.8
117.5°	191.3	195.3	202.8	218.3	238.6	269.2	313.5	383.9	484.9	606.6	733.8
120°	204.2	208.3	216.5	232.0	252.3	281.6	323.9	386.5	477.7	588.4	703.1
122.5°	216.6	220.7	229.5	244.3	266.0	294.6	333.7	391.1	473.1	573.4	679.1
125°	233.6	238.5	247.4	262.9	284.9	313.3	349.1	397.9	467.2	554.2	647.0
127.5°	247.9	253.9	263.0	280.1	302.1	329.6	361.8	405.8	464.2	537.3	619.0
130°	256.3	263.7	273.5	290.5	312.5	339.3	370.3	411.0	462.3	528.2	601.4
132.5°	263.5	271.5	283.2	300.3	321.6	347.8	378.1	414.9	461.6	519.7	585.1
135°	275.1	284.1	296.2	313.3	335.3	360.5	388.2	420.8	460.6	508.7	563.1
137.5°	286.0	294.7	307.8	324.7	345.0	369.3	395.7	424.6	458.9	499.0	543.2
140°	293.8	301.9	315.0	331.3	351.6	375.2	399.6	427.2	458.2	493.2	531.4
142.5°	300.9	309.7	321.5	337.7	356.8	379.8	403.5	429.2	456.9	488.0	520.3
145°	312.5	319.8	332.1	345.8	364.6	385.7	407.7	430.5	454.9	480.9	507.0
147.5°	324.2	331.4	341.9	355.3	371.3	390.6	410.3	430.5	451.8	474.1	496.1
150°	332.1	338.5	349.1	360.5	375.2	393.9	411.0	430.5	449.2	469.5	488.3
152.5°	339.8	346.3	355.6	365.7	379.8	395.8	412.3	428.5	446.0	464.4	481.1
155°	352.4	357.3	365.4	374.4	385.7	399.6	412.6	426.4	440.3	456.6	470.3
157.5°	363.1	367.0	374.2	381.8	390.6	401.7	413.4	423.7	435.2	447.8	459.0
160°	370.3	373.6	380.0	385.7	393.9	403.7	413.4	422.4	431.3	441.9	452.5
162.5°	376.2	378.8	383.9	389.0	395.8	404.3	412.8	419.8	427.4	436.0	444.7
165°	384.1	385.7	389.8	393.1	398.8	405.3	411.0	415.9	421.6	428.0	434.6
167.5°	390.6	391.4	394.5	396.8	400.4	405.1	409.7	412.0	415.7	420.4	425.7
170°	393.9	394.7	397.1	398.8	400.4	404.5	407.7	409.4	411.8	415.9	420.0
172.5°	397.1	397.3	399.1	400.1	401.0	404.5	407.1	407.4	408.5	411.3	414.7
175°	400.4	399.6	401.2	401.2	402.0	403.7	405.3	404.5	404.5	406.1	407.7
177.5°	402.0	401.4	402.0	402.0	402.0	402.7	404.0	402.7	402.0	402.7	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	392.0	392.0	392.0	392.0	392.0	392.0	392.0
2.5°	412.5	412.7	414.3	415.6	415.0	415.7	416.0
5°	450.7	457.5	461.1	463.8	464.0	464.2	465.7
7.5°	504.8	512.2	517.6	525.7	528.1	530.8	530.1
10°	544.4	555.2	564.5	569.4	574.8	582.5	576.3
12.5°	581.3	600.5	614.7	622.3	627.3	628.8	625.8
15°	642.2	667.2	680.7	680.4	697.4	704.8	693.2
17.5°	698.0	721.1	739.7	749.2	763.4	766.5	765.2
20°	732.2	757.5	771.9	788.2	795.7	802.3	803.4
22.5°	761.7	784.4	799.9	813.4	819.6	822.8	824.7
25°	792.1	809.9	819.2	823.9	825.7	825.2	822.8
27.5°	789.9	791.3	781.1	771.0	762.0	751.9	748.4
30°	769.4	753.5	725.0	708.8	685.1	666.3	673.9
32.5°	715.5	683.7	651.8	616.4	587.3	578.9	570.5
35°	610.7	554.8	522.1	484.1	469.0	453.8	443.3
37.5°	494.0	450.9	412.1	387.3	372.0	362.4	357.3
40°	427.1	388.2	356.3	336.1	324.6	313.8	312.3
42.5°	373.8	337.6	313.6	297.6	286.5	281.8	278.5
45°	306.1	281.0	264.8	253.4	246.0	243.1	239.3
47.5°	259.2	241.3	229.2	221.4	215.8	213.7	213.4
50°	232.8	218.0	209.1	203.0	198.7	197.9	194.9
52.5°	213.1	200.2	193.3	188.0	184.8	182.7	181.8
55°	185.0	176.4	170.2	167.1	164.7	162.6	162.6
57.5°	161.8	154.7	150.6	148.0	147.2	145.8	144.8
60°	147.6	141.5	138.3	136.0	134.4	134.7	133.0
62.5°	133.6	129.6	126.5	124.3	122.5	122.5	122.6
65°	113.7	110.7	108.4	107.7	106.6	105.3	105.6
67.5°	96.4	93.6	91.8	90.5	90.1	89.4	90.5
70°	84.0	81.9	80.6	79.4	79.0	79.2	80.1
72.5°	72.6	71.1	70.2	69.7	68.8	68.9	69.5
75°	57.0	55.8	55.1	54.5	54.3	54.3	54.3
77.5°	41.8	41.6	41.3	40.4	40.4	40.7	40.7
80°	33.0	32.4	32.3	31.9	31.3	31.0	31.9
82.5°	24.7	24.1	24.0	23.9	23.0	22.9	23.7
85°	13.3	12.7	12.9	12.7	12.7	12.6	12.6
87.5°	9.0	9.0	9.1	9.1	9.1	9.1	9.3
90°	21.2	22.0	23.6	22.7	23.6	24.4	23.6
92.5°	54.4	48.0	43.8	42.3	39.9	40.7	39.2
95°	198.6	155.5	126.1	110.7	103.4	97.7	94.4
97.5°	585.0	480.0	382.6	322.6	286.0	264.0	257.0
100°	893.6	798.3	682.8	600.6	541.2	509.5	510.3
102.5°	1033.6	978.0	904.8	840.8	793.8	767.3	748.5
105°	1139.4	1154.8	1133.7	1096.2	1065.3	1039.3	1035.2
107.5°	1126.0	1197.3	1226.3	1226.9	1216.5	1207.7	1200.2
110°	1082.4	1184.9	1241.9	1264.7	1271.2	1269.6	1268.0



TEST NUMBER: P331894-930

CATALOG NUMBER: S123DIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1025.1	1140.0	1213.2	1254.9	1275.0	1281.2	1281.6
115°	933.4	1053.0	1141.7	1202.8	1238.6	1254.9	1259.0
117.5°	856.0	963.4	1053.4	1117.0	1158.1	1181.5	1187.0
120°	813.0	910.7	992.9	1057.1	1102.7	1122.3	1127.2
122.5°	778.5	869.0	945.3	1002.5	1043.5	1064.9	1071.1
125°	735.7	813.8	878.9	931.0	966.8	987.2	992.9
127.5°	698.1	768.6	827.8	874.2	904.8	923.2	928.4
130°	674.7	740.5	795.9	839.0	868.4	885.4	891.9
132.5°	652.5	713.9	766.6	807.1	836.4	851.6	856.1
135°	620.9	673.8	720.2	760.1	784.5	799.2	804.9
137.5°	590.5	636.1	676.3	709.8	734.6	746.9	750.6
140°	572.9	612.0	647.0	677.9	700.7	713.7	712.9
142.5°	556.0	589.9	620.3	646.7	666.8	678.6	677.8
145°	533.9	559.9	583.5	603.8	620.9	627.5	629.1
147.5°	517.4	538.4	555.2	570.6	582.2	588.4	589.1
150°	507.0	524.1	539.6	551.8	560.7	565.6	565.6
152.5°	497.3	512.4	525.2	534.8	543.2	546.1	546.1
155°	483.4	495.6	505.4	512.7	519.2	520.8	521.6
157.5°	469.9	479.3	487.0	493.3	498.2	499.5	499.4
160°	461.5	469.5	475.2	480.9	485.8	485.8	485.0
162.5°	452.3	459.8	464.9	468.6	472.8	472.8	472.0
165°	439.4	445.2	449.2	452.5	455.8	454.9	454.9
167.5°	429.5	432.8	435.7	437.2	439.4	438.6	438.6
170°	422.4	425.6	427.2	428.0	429.7	428.8	428.8
172.5°	416.5	419.1	420.1	420.3	421.9	420.4	419.8
175°	408.5	410.2	410.2	410.2	411.0	410.2	409.4
177.5°	404.0	404.6	404.6	404.0	404.6	403.3	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0

(END OF REPORT)