

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331939-930

Luminaire Tested: **S123DIP-S560D1025U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331939-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D1025U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4973.0 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	39	33
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33	28
3	80	70	63	58	72	64	58	53	53	48	45	42	39	37	32	30	29	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	41	34	30	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6937	6937	6937	6937
5°	8272	6967	6174	6967
10°	10355	6932	5576	6932
15°	12700	6876	5192	6876
20°	15131	6788	4943	6788
25°	16066	6683	4888	6683
30°	13770	6606	4913	6606
35°	9577	6495	4964	6495
40°	7213	6367	4949	6367
45°	5990	6174	4886	6174
50°	5365	5784	4843	5784
55°	5016	5362	4782	5362
60°	4706	4921	4732	4921
65°	4422	4485	4582	4485
70°	4148	3991	4362	3991
75°	3714	3493	4001	3493
80°	3248	2864	3446	2864
85°	2544	2087	2322	2087



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.5	1.3
10°-20°	203.6	4.1
20°-30°	341.7	6.9
30°-40°	386.9	7.8
40°-50°	346.9	7.0
50°-60°	280.0	5.6
60°-70°	195.1	3.9
70°-80°	102.5	2.1
80°-90°	28.2	0.6
90°-100°	223.7	4.5
100°-110°	633.5	12.7
110°-120°	623.2	12.5
120°-130°	497.1	10.0
130°-140°	391.9	7.9
140°-150°	292.5	5.9
150°-160°	203.9	4.1
160°-170°	119.8	2.4
170°-180°	39.0	0.8
0°-30°	608.7	12.2
0°-40°	995.6	20.0
0°-60°	1622.5	32.6
0°-90°	1948.3	39.2
90°-120°	1480.5	29.8
90°-150°	2662.0	53.5
90°-180°	3025.0	60.8
0°-180°	4973.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	644	644	644	644	644	
5°	766	645	571	645	766	79
15°	1140	617	466	617	1140	329
25°	1353	563	412	563	1353	593
35°	729	494	378	494	729	473
45°	394	406	321	406	394	311
55°	267	286	255	286	267	240
65°	174	176	180	176	174	173
75°	89	84	96	84	89	96
85°	21	17	19	17	21	25
90°	24	2	24	2	24	14
95°	94	28	94	28	94	170
105°	1035	94	1035	94	1035	1021
115°	1259	167	1259	167	1259	1223
125°	993	232	993	232	993	900
135°	805	272	805	272	805	624
145°	629	310	629	310	629	400
155°	522	352	522	352	522	243
165°	455	385	455	385	455	130
175°	409	401	409	401	409	40
180°	402	402	402	402	402	



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	684.0	683.5	682.2	683.2	681.2	678.5	678.2	675.7	668.5	668.0	666.0
5°	765.6	763.1	762.9	762.5	758.1	752.2	740.9	740.0	725.0	717.5	708.5
7.5°	871.5	872.8	868.2	864.2	850.8	842.0	830.0	814.6	796.1	777.5	765.0
10°	947.4	957.7	944.9	936.1	928.1	912.7	895.0	872.8	850.6	824.7	805.0
12.5°	1028.8	1033.9	1031.4	1023.0	1010.5	987.2	955.6	931.2	910.8	867.6	850.2
15°	1139.7	1158.8	1146.6	1118.5	1119.2	1097.0	1055.7	1010.5	986.4	948.6	897.1
17.5°	1257.9	1260.3	1255.1	1231.7	1216.0	1185.6	1147.5	1104.2	1055.4	1009.7	955.0
20°	1320.9	1319.0	1308.1	1295.8	1269.0	1245.3	1203.7	1155.4	1092.9	1047.9	988.3
22.5°	1355.8	1352.7	1347.5	1337.3	1315.0	1289.5	1252.2	1199.3	1139.9	1077.9	1009.0
25°	1352.7	1356.7	1357.4	1354.5	1346.8	1331.5	1302.1	1260.0	1200.6	1121.0	1049.2
27.5°	1230.3	1236.0	1252.7	1267.5	1284.1	1300.9	1298.7	1277.7	1233.9	1165.1	1077.3
30°	1107.9	1095.4	1126.3	1165.3	1191.9	1238.7	1264.9	1266.5	1241.9	1182.8	1097.2
32.5°	938.0	951.8	965.4	1013.4	1071.5	1124.1	1176.2	1218.3	1223.1	1183.8	1109.0
35°	728.8	746.0	770.9	796.0	858.4	912.1	1003.9	1083.9	1147.5	1155.9	1110.0
37.5°	587.3	595.8	611.6	636.6	677.4	741.2	812.2	913.2	1005.5	1074.2	1077.2
40°	513.3	515.8	533.6	552.7	585.8	638.2	702.3	791.6	902.1	998.0	1038.0
42.5°	457.9	463.4	470.9	489.3	515.6	555.1	614.6	688.4	789.7	900.0	978.2
45°	393.5	399.7	404.4	416.5	435.3	461.8	503.4	570.8	647.9	761.9	867.2
47.5°	350.8	351.3	354.8	364.0	376.7	396.7	426.1	469.4	540.2	632.6	740.7
50°	320.4	325.4	326.6	333.8	343.8	358.5	382.9	419.6	477.8	559.0	658.3
52.5°	298.9	300.4	303.9	309.1	317.8	329.2	350.3	379.2	424.8	494.0	585.3
55°	267.3	267.3	270.8	274.8	279.8	290.1	304.1	325.4	360.0	413.8	489.3
57.5°	238.1	239.6	242.1	243.3	247.5	254.4	266.1	282.3	308.1	349.4	409.5
60°	218.6	221.4	221.1	223.6	227.3	232.6	242.6	255.8	278.8	311.9	362.6
62.5°	201.6	201.4	201.4	204.3	208.1	213.1	219.6	231.0	250.6	280.0	323.0
65°	173.6	173.0	175.2	177.1	178.3	182.1	187.0	197.1	210.2	232.0	265.4
67.5°	148.8	146.9	148.1	148.8	150.9	153.8	158.5	164.7	175.1	192.7	217.8
70°	131.8	130.2	129.9	130.5	132.4	134.6	138.0	144.0	153.6	167.7	186.1
72.5°	114.3	113.2	113.2	114.5	115.4	116.8	119.3	124.7	132.4	142.9	160.1
75°	89.3	89.3	89.3	89.6	90.6	91.8	93.7	96.4	102.4	109.9	121.5
77.5°	66.9	66.9	66.5	66.4	67.8	68.4	68.8	71.4	74.8	79.8	88.2
80°	52.4	50.9	51.5	52.4	53.1	53.4	54.3	55.0	57.8	60.6	66.5
82.5°	39.0	37.7	37.7	39.2	39.4	39.6	40.6	41.5	42.6	45.1	48.3
85°	20.6	20.6	21.0	21.0	21.2	21.0	21.9	22.2	22.2	23.7	25.6
87.5°	12.2	11.9	12.0	12.1	12.0	11.9	12.0	12.1	12.1	12.6	12.3
90°	23.6	24.4	23.6	22.7	23.6	22.0	21.2	20.4	19.6	20.4	17.9
92.5°	39.2	40.7	39.9	42.3	43.8	48.0	54.4	68.5	94.4	125.1	137.7
95°	94.4	97.7	103.4	110.7	126.1	155.5	198.6	292.9	391.4	482.6	429.7
97.5°	257.0	264.0	286.0	322.6	382.6	480.0	585.0	730.3	800.1	747.9	547.6
100°	510.3	509.5	541.2	600.6	682.8	798.3	893.6	959.5	931.0	770.7	520.8
102.5°	748.5	767.3	793.8	840.8	904.8	978.0	1033.6	1035.7	937.5	728.4	481.8
105°	1035.2	1039.3	1065.3	1096.2	1133.7	1154.8	1139.4	1057.9	887.9	654.3	433.7
107.5°	1200.2	1207.7	1216.5	1226.9	1226.3	1197.3	1126.0	993.8	801.0	588.9	403.2
110°	1268.0	1269.6	1271.2	1264.7	1241.9	1184.9	1082.4	932.6	746.2	551.8	391.4



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1281.6	1281.2	1275.0	1254.9	1213.2	1140.0	1025.1	872.0	698.7	527.0	384.9
115°	1259.0	1254.9	1238.6	1202.8	1141.7	1053.0	933.4	791.8	641.3	500.5	382.5
117.5°	1187.0	1181.5	1158.1	1117.0	1053.4	963.4	856.0	733.8	606.6	484.9	383.9
120°	1127.2	1122.3	1102.7	1057.1	992.9	910.7	813.0	703.1	588.4	477.7	386.5
122.5°	1071.1	1064.9	1043.5	1002.5	945.3	869.0	778.5	679.1	573.4	473.1	391.1
125°	992.9	987.2	966.8	931.0	878.9	813.8	735.7	647.0	554.2	467.2	397.9
127.5°	928.4	923.2	904.8	874.2	827.8	768.6	698.1	619.0	537.3	464.2	405.8
130°	891.9	885.4	868.4	839.0	795.9	740.5	674.7	601.4	528.2	462.3	411.0
132.5°	856.1	851.6	836.4	807.1	766.6	713.9	652.5	585.1	519.7	461.6	414.9
135°	804.9	799.2	784.5	760.1	720.2	673.8	620.9	563.1	508.7	460.6	420.8
137.5°	750.6	746.9	734.6	709.8	676.3	636.1	590.5	543.2	499.0	458.9	424.6
140°	712.9	713.7	700.7	677.9	647.0	612.0	572.9	531.4	493.2	458.2	427.2
142.5°	677.8	678.6	666.8	646.7	620.3	589.9	556.0	520.3	488.0	456.9	429.2
145°	629.1	627.5	620.9	603.8	583.5	559.9	533.9	507.0	480.9	454.9	430.5
147.5°	589.1	588.4	582.2	570.6	555.2	538.4	517.4	496.1	474.1	451.8	430.5
150°	565.6	565.6	560.7	551.8	539.6	524.1	507.0	488.3	469.5	449.2	430.5
152.5°	546.1	546.1	543.2	534.8	525.2	512.4	497.3	481.1	464.4	446.0	428.5
155°	521.6	520.8	519.2	512.7	505.4	495.6	483.4	470.3	456.6	440.3	426.4
157.5°	499.4	499.5	498.2	493.3	487.0	479.3	469.9	459.0	447.8	435.2	423.7
160°	485.0	485.8	485.8	480.9	475.2	469.5	461.5	452.5	441.9	431.3	422.4
162.5°	472.0	472.8	472.8	468.6	464.9	459.8	452.3	444.7	436.0	427.4	419.8
165°	454.9	454.9	455.8	452.5	449.2	445.2	439.4	434.6	428.0	421.6	415.9
167.5°	438.6	438.6	439.4	437.2	435.7	432.8	429.5	425.7	420.4	415.7	412.0
170°	428.8	428.8	429.7	428.0	427.2	425.6	422.4	420.0	415.9	411.8	409.4
172.5°	419.8	420.4	421.9	420.3	420.1	419.1	416.5	414.7	411.3	408.5	407.4
175°	409.4	410.2	411.0	410.2	410.2	410.2	408.5	407.7	406.1	404.5	404.5
177.5°	403.3	403.3	404.6	404.0	404.6	404.6	404.0	403.3	402.7	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	664.5	662.5	660.5	657.0	654.0	649.7	648.5	647.0	642.5	638.5	635.5
5°	705.1	697.6	686.6	676.6	668.5	657.6	651.3	644.8	635.4	627.0	620.1
7.5°	747.5	732.8	715.8	697.5	680.4	663.8	650.5	638.7	625.6	613.1	603.5
10°	781.3	760.0	736.3	710.7	688.8	667.6	649.8	634.2	617.3	602.7	590.4
12.5°	819.7	788.2	755.5	724.4	698.5	669.1	647.6	627.7	608.6	590.9	577.2
15°	865.3	825.3	786.6	743.8	704.4	667.6	642.0	617.0	594.8	576.7	559.2
17.5°	906.7	861.4	810.4	758.4	710.9	667.2	631.4	603.2	575.4	553.3	535.8
20°	930.2	878.6	820.9	766.9	714.4	665.7	626.4	592.6	562.7	539.2	519.6
22.5°	950.5	890.1	830.4	772.7	714.2	661.7	617.2	582.4	549.9	527.0	506.1
25°	971.4	899.3	839.4	771.6	706.3	652.0	602.0	562.7	530.2	503.4	481.8
27.5°	989.4	898.7	827.5	754.6	694.0	639.5	586.2	544.0	509.5	480.3	458.4
30°	1001.4	899.9	815.3	743.1	682.0	625.7	573.9	531.5	495.2	465.5	445.0
32.5°	1008.9	899.2	804.0	727.2	663.0	613.3	560.7	516.7	479.5	450.4	430.5
35°	1013.3	893.6	784.7	694.1	632.3	583.9	539.9	494.3	455.3	428.1	405.6
37.5°	1004.5	882.2	762.2	662.3	594.6	547.0	509.9	471.1	433.7	403.8	384.4
40°	990.8	874.7	744.7	639.8	568.6	522.7	491.2	453.1	416.2	387.8	369.7
42.5°	964.6	859.4	725.5	614.8	541.6	495.7	466.7	434.9	400.0	373.3	355.2
45°	900.6	826.2	696.7	577.4	501.8	454.4	428.8	405.6	374.1	348.1	332.6
47.5°	811.7	776.3	654.9	537.9	460.2	414.6	387.9	369.3	346.3	325.4	310.4
50°	750.1	735.4	626.7	510.9	432.4	387.8	362.2	345.4	328.8	307.9	294.2
52.5°	678.8	687.9	593.7	482.9	404.2	360.4	336.2	322.9	307.9	290.7	278.7
55°	578.6	611.4	536.8	435.9	362.2	320.4	297.6	285.7	277.0	264.2	253.9
57.5°	484.8	526.4	475.2	387.5	320.9	284.9	263.0	250.1	244.4	237.7	229.7
60°	429.0	470.3	431.2	355.1	293.2	258.9	239.5	228.6	223.0	218.3	211.4
62.5°	379.4	421.0	388.2	322.0	266.0	234.2	217.3	206.6	202.2	199.7	193.9
65°	311.0	346.9	325.1	270.8	227.0	198.9	183.6	176.1	172.0	171.1	167.4
67.5°	253.2	280.5	264.6	224.5	190.1	165.8	152.9	146.5	143.4	143.1	140.2
70°	215.2	240.8	228.6	192.3	162.7	143.7	132.4	126.8	124.9	124.6	123.0
72.5°	185.6	203.5	193.9	163.6	140.7	123.4	115.1	109.3	107.1	107.6	106.6
75°	137.4	150.8	145.2	124.3	105.8	94.6	87.7	84.0	82.1	83.1	81.8
77.5°	98.9	107.4	102.3	87.8	76.5	68.3	63.3	61.0	59.3	59.2	58.6
80°	74.6	79.7	76.8	68.1	58.7	51.9	47.8	46.2	45.2	45.0	44.7
82.5°	53.2	57.4	54.1	48.1	41.7	37.6	35.3	33.3	32.5	32.7	32.4
85°	26.8	28.5	27.1	23.4	21.0	19.1	17.8	16.9	16.2	16.6	15.9
87.5°	12.3	12.1	10.8	9.5	8.7	7.5	7.2	6.4	6.1	6.4	6.7
90°	15.5	13.0	10.6	9.0	7.3	4.9	3.3	1.6	3.3	4.9	7.3
92.5°	103.4	68.3	47.0	35.0	28.1	21.9	15.0	10.1	15.0	21.9	28.1
95°	296.2	175.0	105.8	74.0	52.9	39.1	30.1	27.6	30.1	39.1	52.9
97.5°	325.1	188.3	122.2	87.9	67.0	55.0	48.0	47.2	48.0	55.0	67.0
100°	306.8	186.4	129.4	97.7	78.1	66.8	61.1	60.3	61.1	66.8	78.1
102.5°	291.1	189.0	137.9	108.8	91.2	80.4	75.3	73.9	75.3	80.4	91.2
105°	280.0	196.2	152.2	126.9	111.5	101.7	96.9	94.4	96.9	101.7	111.5
107.5°	279.2	209.5	170.9	147.5	133.0	123.4	118.6	116.2	118.6	123.4	133.0
110°	282.4	220.5	183.9	161.1	147.3	138.4	134.3	131.8	134.3	138.4	147.3



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	288.9	231.6	197.6	175.5	161.6	152.7	148.6	146.2	148.6	152.7	161.6
115°	299.5	249.8	218.9	197.0	183.1	175.0	170.1	166.8	170.1	175.0	183.1
117.5°	313.5	269.2	238.6	218.3	202.8	195.3	191.3	187.5	191.3	195.3	202.8
120°	323.9	281.6	252.3	232.0	216.5	208.3	204.2	201.8	204.2	208.3	216.5
122.5°	333.7	294.6	266.0	244.3	229.5	220.7	216.6	214.2	216.6	220.7	229.5
125°	349.1	313.3	284.9	262.9	247.4	238.5	233.6	232.0	233.6	238.5	247.4
127.5°	361.8	329.6	302.1	280.1	263.0	253.9	247.9	245.5	247.9	253.9	263.0
130°	370.3	339.3	312.5	290.5	273.5	263.7	256.3	253.9	256.3	263.7	273.5
132.5°	378.1	347.8	321.6	300.3	283.2	271.5	263.5	260.4	263.5	271.5	283.2
135°	388.2	360.5	335.3	313.3	296.2	284.1	275.1	271.8	275.1	284.1	296.2
137.5°	395.7	369.3	345.0	324.7	307.8	294.7	286.0	282.6	286.0	294.7	307.8
140°	399.6	375.2	351.6	331.3	315.0	301.9	293.8	289.8	293.8	301.9	315.0
142.5°	403.5	379.8	356.8	337.7	321.5	309.7	300.9	297.5	300.9	309.7	321.5
145°	407.7	385.7	364.6	345.8	332.1	319.8	312.5	310.1	312.5	319.8	332.1
147.5°	410.3	390.6	371.3	355.3	341.9	331.4	324.2	322.8	324.2	331.4	341.9
150°	411.0	393.9	375.2	360.5	349.1	338.5	332.1	331.3	332.1	338.5	349.1
152.5°	412.3	395.8	379.8	365.7	355.6	346.3	339.8	339.7	339.8	346.3	355.6
155°	412.6	399.6	385.7	374.4	365.4	357.3	352.4	352.4	352.4	357.3	365.4
157.5°	413.4	401.7	390.6	381.8	374.2	367.0	363.1	362.5	363.1	367.0	374.2
160°	413.4	403.7	393.9	385.7	380.0	373.6	370.3	370.3	370.3	373.6	380.0
162.5°	412.8	404.3	395.8	389.0	383.9	378.8	376.2	376.2	376.2	378.8	383.9
165°	411.0	405.3	398.8	393.1	389.8	385.7	384.1	384.9	384.1	385.7	389.8
167.5°	409.7	405.1	400.4	396.8	394.5	391.4	390.6	391.6	390.6	391.4	394.5
170°	407.7	404.5	400.4	398.8	397.1	394.7	393.9	395.5	393.9	394.7	397.1
172.5°	407.1	404.5	401.0	400.1	399.1	397.3	397.1	398.1	397.1	397.3	399.1
175°	405.3	403.7	402.0	401.2	401.2	399.6	400.4	401.2	400.4	399.6	401.2
177.5°	404.0	402.7	402.0	402.0	402.0	401.4	402.0	402.7	402.0	401.4	402.0
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	633.7	632.0	629.5	625.7	622.7	618.0	618.0	618.7	618.7	618.5	618.0
5°	614.5	609.8	604.2	597.7	590.8	583.9	582.7	580.2	578.3	577.1	575.5
7.5°	594.2	586.0	577.7	568.6	560.2	553.3	548.5	544.5	541.8	539.2	537.1
10°	580.5	570.1	560.5	550.8	540.2	531.7	526.4	522.7	519.9	517.4	516.2
12.5°	564.3	552.4	541.8	532.6	521.0	512.3	507.2	505.5	502.1	496.9	494.2
15°	540.5	529.6	516.8	502.7	497.1	486.5	480.5	477.8	475.9	471.8	470.6
17.5°	520.2	505.9	491.5	481.0	470.6	462.0	458.7	455.2	452.7	449.4	448.4
20°	504.0	491.2	478.1	466.8	455.9	446.5	443.7	441.2	438.7	437.2	435.9
22.5°	487.5	474.7	463.8	453.3	441.6	435.5	432.4	429.7	428.0	426.9	425.7
25°	464.3	453.1	440.9	431.5	422.2	418.1	416.2	414.7	413.4	411.9	411.6
27.5°	443.6	431.4	421.5	412.7	406.0	402.6	400.8	400.1	400.3	400.9	401.2
30°	428.1	416.9	408.7	401.2	395.0	391.9	391.6	391.6	392.8	393.1	393.8
32.5°	413.8	404.6	396.5	389.2	384.5	382.4	383.6	383.6	384.6	385.4	386.5
35°	393.1	385.0	378.8	372.5	368.4	369.4	370.0	370.6	372.2	374.1	375.4
37.5°	373.3	366.3	359.8	354.9	353.0	354.7	356.2	357.5	359.4	360.8	362.0
40°	359.1	353.8	347.6	343.2	343.8	344.7	346.0	347.6	349.1	350.0	351.3
42.5°	345.8	340.3	335.6	331.9	332.8	334.0	334.8	335.6	337.4	339.1	339.8
45°	325.7	321.3	316.9	314.8	315.4	316.0	316.7	317.6	319.1	320.4	320.7
47.5°	303.0	299.9	297.0	294.9	295.9	295.6	296.4	298.5	299.0	299.7	301.4
50°	288.5	285.7	282.3	281.7	281.7	281.7	281.9	284.5	284.5	285.7	287.0
52.5°	272.6	270.8	268.6	267.4	266.9	266.9	268.2	269.5	269.9	271.7	273.0
55°	248.8	247.0	245.2	244.2	243.5	244.2	246.7	247.3	248.8	249.8	250.7
57.5°	224.2	222.7	221.3	220.8	220.6	221.4	222.8	224.7	225.1	228.0	229.3
60°	208.0	205.8	204.6	204.6	203.9	206.7	206.1	209.2	209.9	211.7	213.9
62.5°	191.2	188.3	187.8	187.8	188.7	189.5	190.4	191.8	193.4	195.8	197.4
65°	164.3	162.7	164.9	164.5	164.0	165.8	165.8	167.4	169.3	171.5	174.9
67.5°	138.7	137.9	138.1	138.1	139.0	140.1	141.0	142.4	144.6	146.9	149.1
70°	121.5	122.4	120.8	122.1	123.0	123.4	123.9	125.8	128.3	129.9	132.4
72.5°	104.8	104.7	104.8	105.3	106.3	106.9	107.5	109.6	112.3	113.7	115.7
75°	80.6	80.2	81.2	81.2	82.8	83.4	84.0	85.0	87.4	89.3	90.9
77.5°	58.9	59.2	59.0	60.1	59.7	59.8	61.7	62.6	62.9	66.6	67.4
80°	44.4	45.0	45.2	45.6	45.9	45.2	47.5	48.4	48.4	50.5	52.2
82.5°	31.9	32.2	33.0	33.3	33.4	34.0	34.2	34.9	35.6	36.6	38.6
85°	15.9	16.9	17.2	16.9	17.2	16.6	17.4	17.8	18.1	18.1	18.1
87.5°	6.8	7.3	7.6	8.3	8.6	9.3	9.1	8.8	9.0	9.9	9.2
90°	9.0	10.6	13.0	15.5	17.9	20.4	19.6	20.4	21.2	22.0	23.6
92.5°	35.0	47.0	68.3	103.4	137.7	125.1	94.4	68.5	54.4	48.0	43.8
95°	74.0	105.8	175.0	296.2	429.7	482.6	391.4	292.9	198.6	155.5	126.1
97.5°	87.9	122.2	188.3	325.1	547.6	747.9	800.1	730.3	585.0	480.0	382.6
100°	97.7	129.4	186.4	306.8	520.8	770.7	931.0	959.5	893.6	798.3	682.8
102.5°	108.8	137.9	189.0	291.1	481.8	728.4	937.5	1035.7	1033.6	978.0	904.8
105°	126.9	152.2	196.2	280.0	433.7	654.3	887.9	1057.9	1139.4	1154.8	1133.7
107.5°	147.5	170.9	209.5	279.2	403.2	588.9	801.0	993.8	1126.0	1197.3	1226.3
110°	161.1	183.9	220.5	282.4	391.4	551.8	746.2	932.6	1082.4	1184.9	1241.9



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	175.5	197.6	231.6	288.9	384.9	527.0	698.7	872.0	1025.1	1140.0	1213.2
115°	197.0	218.9	249.8	299.5	382.5	500.5	641.3	791.8	933.4	1053.0	1141.7
117.5°	218.3	238.6	269.2	313.5	383.9	484.9	606.6	733.8	856.0	963.4	1053.4
120°	232.0	252.3	281.6	323.9	386.5	477.7	588.4	703.1	813.0	910.7	992.9
122.5°	244.3	266.0	294.6	333.7	391.1	473.1	573.4	679.1	778.5	869.0	945.3
125°	262.9	284.9	313.3	349.1	397.9	467.2	554.2	647.0	735.7	813.8	878.9
127.5°	280.1	302.1	329.6	361.8	405.8	464.2	537.3	619.0	698.1	768.6	827.8
130°	290.5	312.5	339.3	370.3	411.0	462.3	528.2	601.4	674.7	740.5	795.9
132.5°	300.3	321.6	347.8	378.1	414.9	461.6	519.7	585.1	652.5	713.9	766.6
135°	313.3	335.3	360.5	388.2	420.8	460.6	508.7	563.1	620.9	673.8	720.2
137.5°	324.7	345.0	369.3	395.7	424.6	458.9	499.0	543.2	590.5	636.1	676.3
140°	331.3	351.6	375.2	399.6	427.2	458.2	493.2	531.4	572.9	612.0	647.0
142.5°	337.7	356.8	379.8	403.5	429.2	456.9	488.0	520.3	556.0	589.9	620.3
145°	345.8	364.6	385.7	407.7	430.5	454.9	480.9	507.0	533.9	559.9	583.5
147.5°	355.3	371.3	390.6	410.3	430.5	451.8	474.1	496.1	517.4	538.4	555.2
150°	360.5	375.2	393.9	411.0	430.5	449.2	469.5	488.3	507.0	524.1	539.6
152.5°	365.7	379.8	395.8	412.3	428.5	446.0	464.4	481.1	497.3	512.4	525.2
155°	374.4	385.7	399.6	412.6	426.4	440.3	456.6	470.3	483.4	495.6	505.4
157.5°	381.8	390.6	401.7	413.4	423.7	435.2	447.8	459.0	469.9	479.3	487.0
160°	385.7	393.9	403.7	413.4	422.4	431.3	441.9	452.5	461.5	469.5	475.2
162.5°	389.0	395.8	404.3	412.8	419.8	427.4	436.0	444.7	452.3	459.8	464.9
165°	393.1	398.8	405.3	411.0	415.9	421.6	428.0	434.6	439.4	445.2	449.2
167.5°	396.8	400.4	405.1	409.7	412.0	415.7	420.4	425.7	429.5	432.8	435.7
170°	398.8	400.4	404.5	407.7	409.4	411.8	415.9	420.0	422.4	425.6	427.2
172.5°	400.1	401.0	404.5	407.1	407.4	408.5	411.3	414.7	416.5	419.1	420.1
175°	401.2	402.0	403.7	405.3	404.5	404.5	406.1	407.7	408.5	410.2	410.2
177.5°	402.0	402.0	402.7	404.0	402.7	402.0	402.7	403.3	404.0	404.6	404.6
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	616.3	616.0	617.8	616.5	617.8	616.0	616.3	618.0	618.5	618.7	618.7
5°	573.6	574.5	571.4	571.4	571.4	574.5	573.6	575.5	577.1	578.3	580.2
7.5°	535.7	534.3	534.4	532.7	534.4	534.3	535.7	537.1	539.2	541.8	544.5
10°	512.4	510.5	509.9	510.2	509.9	510.5	512.4	516.2	517.4	519.9	522.7
12.5°	493.2	492.8	488.7	488.8	488.7	492.8	493.2	494.2	496.9	502.1	505.5
15°	470.6	464.6	464.0	465.9	464.0	464.6	470.6	470.6	471.8	475.9	477.8
17.5°	447.9	444.7	445.0	444.0	445.0	444.7	447.9	448.4	449.4	452.7	455.2
20°	435.9	434.1	433.7	431.5	433.7	434.1	435.9	435.9	437.2	438.7	441.2
22.5°	424.9	424.3	424.4	422.1	424.4	424.3	424.9	425.7	426.9	428.0	429.7
25°	411.2	412.8	411.6	411.6	411.6	412.8	411.2	411.6	411.9	413.4	414.7
27.5°	402.0	401.9	401.3	401.3	401.3	401.9	402.0	401.2	400.9	400.3	400.1
30°	395.0	394.7	395.3	395.3	395.3	394.7	395.0	393.8	393.1	392.8	391.6
32.5°	388.0	388.4	388.6	388.8	388.6	388.4	388.0	386.5	385.4	384.6	383.6
35°	377.2	377.5	378.5	377.8	378.5	377.5	377.2	375.4	374.1	372.2	370.6
37.5°	362.6	364.0	363.7	364.2	363.7	364.0	362.6	362.0	360.8	359.4	357.5
40°	351.6	352.5	352.2	352.2	352.2	352.5	351.6	351.3	350.0	349.1	347.6
42.5°	340.4	341.0	340.2	339.7	340.2	341.0	340.4	339.8	339.1	337.4	335.6
45°	322.0	321.3	322.3	321.0	322.3	321.3	322.0	320.7	320.4	319.1	317.6
47.5°	301.3	302.0	302.2	303.1	302.2	302.0	301.3	301.4	299.7	299.0	298.5
50°	287.6	289.4	289.4	289.2	289.4	289.4	287.6	287.0	285.7	284.5	284.5
52.5°	274.1	275.0	276.2	276.1	276.2	275.0	274.1	273.0	271.7	269.9	269.5
55°	253.2	253.9	254.5	254.8	254.5	253.9	253.2	250.7	249.8	248.8	247.3
57.5°	231.6	231.4	232.8	233.3	232.8	231.4	231.6	229.3	228.0	225.1	224.7
60°	216.4	216.4	218.9	219.8	218.9	216.4	216.4	213.9	211.7	209.9	209.2
62.5°	200.2	201.1	203.7	202.4	203.7	201.1	200.2	197.4	195.8	193.4	191.8
65°	176.4	179.0	178.6	179.9	178.6	179.0	176.4	174.9	171.5	169.3	167.4
67.5°	151.6	153.2	155.5	155.6	155.5	153.2	151.6	149.1	146.9	144.6	142.4
70°	134.9	136.5	137.7	138.6	137.7	136.5	134.9	132.4	129.9	128.3	125.8
72.5°	118.6	119.4	122.5	121.2	122.5	119.4	118.6	115.7	113.7	112.3	109.6
75°	93.0	95.2	97.1	96.2	97.1	95.2	93.0	90.9	89.3	87.4	85.0
77.5°	68.8	71.0	71.9	71.1	71.9	71.0	68.8	67.4	66.6	62.9	62.6
80°	54.3	54.1	55.9	55.6	55.9	54.1	54.3	52.2	50.5	48.4	48.4
82.5°	39.9	39.5	40.4	40.6	40.4	39.5	39.9	38.6	36.6	35.6	34.9
85°	19.3	20.3	19.1	18.8	19.1	20.3	19.3	18.1	18.1	18.1	17.8
87.5°	9.0	9.2	9.1	8.7	9.1	9.2	9.0	9.2	9.9	9.0	8.8
90°	22.7	23.6	24.4	23.6	24.4	23.6	22.7	23.6	22.0	21.2	20.4
92.5°	42.3	39.9	40.7	39.2	40.7	39.9	42.3	43.8	48.0	54.4	68.5
95°	110.7	103.4	97.7	94.4	97.7	103.4	110.7	126.1	155.5	198.6	292.9
97.5°	322.6	286.0	264.0	257.0	264.0	286.0	322.6	382.6	480.0	585.0	730.3
100°	600.6	541.2	509.5	510.3	509.5	541.2	600.6	682.8	798.3	893.6	959.5
102.5°	840.8	793.8	767.3	748.5	767.3	793.8	840.8	904.8	978.0	1033.6	1035.7
105°	1096.2	1065.3	1039.3	1035.2	1039.3	1065.3	1096.2	1133.7	1154.8	1139.4	1057.9
107.5°	1226.9	1216.5	1207.7	1200.2	1207.7	1216.5	1226.9	1226.3	1197.3	1126.0	993.8
110°	1264.7	1271.2	1269.6	1268.0	1269.6	1271.2	1264.7	1241.9	1184.9	1082.4	932.6



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1254.9	1275.0	1281.2	1281.6	1281.2	1275.0	1254.9	1213.2	1140.0	1025.1	872.0
115°	1202.8	1238.6	1254.9	1259.0	1254.9	1238.6	1202.8	1141.7	1053.0	933.4	791.8
117.5°	1117.0	1158.1	1181.5	1187.0	1181.5	1158.1	1117.0	1053.4	963.4	856.0	733.8
120°	1057.1	1102.7	1122.3	1127.2	1122.3	1102.7	1057.1	992.9	910.7	813.0	703.1
122.5°	1002.5	1043.5	1064.9	1071.1	1064.9	1043.5	1002.5	945.3	869.0	778.5	679.1
125°	931.0	966.8	987.2	992.9	987.2	966.8	931.0	878.9	813.8	735.7	647.0
127.5°	874.2	904.8	923.2	928.4	923.2	904.8	874.2	827.8	768.6	698.1	619.0
130°	839.0	868.4	885.4	891.9	885.4	868.4	839.0	795.9	740.5	674.7	601.4
132.5°	807.1	836.4	851.6	856.1	851.6	836.4	807.1	766.6	713.9	652.5	585.1
135°	760.1	784.5	799.2	804.9	799.2	784.5	760.1	720.2	673.8	620.9	563.1
137.5°	709.8	734.6	746.9	750.6	746.9	734.6	709.8	676.3	636.1	590.5	543.2
140°	677.9	700.7	713.7	712.9	713.7	700.7	677.9	647.0	612.0	572.9	531.4
142.5°	646.7	666.8	678.6	677.8	678.6	666.8	646.7	620.3	589.9	556.0	520.3
145°	603.8	620.9	627.5	629.1	627.5	620.9	603.8	583.5	559.9	533.9	507.0
147.5°	570.6	582.2	588.4	589.1	588.4	582.2	570.6	555.2	538.4	517.4	496.1
150°	551.8	560.7	565.6	565.6	565.6	560.7	551.8	539.6	524.1	507.0	488.3
152.5°	534.8	543.2	546.1	546.1	546.1	543.2	534.8	525.2	512.4	497.3	481.1
155°	512.7	519.2	520.8	521.6	520.8	519.2	512.7	505.4	495.6	483.4	470.3
157.5°	493.3	498.2	499.5	499.4	499.5	498.2	493.3	487.0	479.3	469.9	459.0
160°	480.9	485.8	485.8	485.0	485.8	485.8	480.9	475.2	469.5	461.5	452.5
162.5°	468.6	472.8	472.8	472.0	472.8	472.8	468.6	464.9	459.8	452.3	444.7
165°	452.5	455.8	454.9	454.9	454.9	455.8	452.5	449.2	445.2	439.4	434.6
167.5°	437.2	439.4	438.6	438.6	438.6	439.4	437.2	435.7	432.8	429.5	425.7
170°	428.0	429.7	428.8	428.8	428.8	429.7	428.0	427.2	425.6	422.4	420.0
172.5°	420.3	421.9	420.4	419.8	420.4	421.9	420.3	420.1	419.1	416.5	414.7
175°	410.2	411.0	410.2	409.4	410.2	411.0	410.2	410.2	410.2	408.5	407.7
177.5°	404.0	404.6	403.3	403.3	403.3	404.6	404.0	404.6	404.6	404.0	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	618.0	618.0	622.7	625.7	629.5	632.0	633.7	635.5	638.5	642.5	647.0
5°	582.7	583.9	590.8	597.7	604.2	609.8	614.5	620.1	627.0	635.4	644.8
7.5°	548.5	553.3	560.2	568.6	577.7	586.0	594.2	603.5	613.1	625.6	638.7
10°	526.4	531.7	540.2	550.8	560.5	570.1	580.5	590.4	602.7	617.3	634.2
12.5°	507.2	512.3	521.0	532.6	541.8	552.4	564.3	577.2	590.9	608.6	627.7
15°	480.5	486.5	497.1	502.7	516.8	529.6	540.5	559.2	576.7	594.8	617.0
17.5°	458.7	462.0	470.6	481.0	491.5	505.9	520.2	535.8	553.3	575.4	603.2
20°	443.7	446.5	455.9	466.8	478.1	491.2	504.0	519.6	539.2	562.7	592.6
22.5°	432.4	435.5	441.6	453.3	463.8	474.7	487.5	506.1	527.0	549.9	582.4
25°	416.2	418.1	422.2	431.5	440.9	453.1	464.3	481.8	503.4	530.2	562.7
27.5°	400.8	402.6	406.0	412.7	421.5	431.4	443.6	458.4	480.3	509.5	544.0
30°	391.6	391.9	395.0	401.2	408.7	416.9	428.1	445.0	465.5	495.2	531.5
32.5°	383.6	382.4	384.5	389.2	396.5	404.6	413.8	430.5	450.4	479.5	516.7
35°	370.0	369.4	368.4	372.5	378.8	385.0	393.1	405.6	428.1	455.3	494.3
37.5°	356.2	354.7	353.0	354.9	359.8	366.3	373.3	384.4	403.8	433.7	471.1
40°	346.0	344.7	343.8	343.2	347.6	353.8	359.1	369.7	387.8	416.2	453.1
42.5°	334.8	334.0	332.8	331.9	335.6	340.3	345.8	355.2	373.3	400.0	434.9
45°	316.7	316.0	315.4	314.8	316.9	321.3	325.7	332.6	348.1	374.1	405.6
47.5°	296.4	295.6	295.9	294.9	297.0	299.9	303.0	310.4	325.4	346.3	369.3
50°	281.9	281.7	281.7	281.7	282.3	285.7	288.5	294.2	307.9	328.8	345.4
52.5°	268.2	266.9	266.9	267.4	268.6	270.8	272.6	278.7	290.7	307.9	322.9
55°	246.7	244.2	243.5	244.2	245.2	247.0	248.8	253.9	264.2	277.0	285.7
57.5°	222.8	221.4	220.6	220.8	221.3	222.7	224.2	229.7	237.7	244.4	250.1
60°	206.1	206.7	203.9	204.6	204.6	205.8	208.0	211.4	218.3	223.0	228.6
62.5°	190.4	189.5	188.7	187.8	187.8	188.3	191.2	193.9	199.7	202.2	206.6
65°	165.8	165.8	164.0	164.5	164.9	162.7	164.3	167.4	171.1	172.0	176.1
67.5°	141.0	140.1	139.0	138.1	138.1	137.9	138.7	140.2	143.1	143.4	146.5
70°	123.9	123.4	123.0	122.1	120.8	122.4	121.5	123.0	124.6	124.9	126.8
72.5°	107.5	106.9	106.3	105.3	104.8	104.7	104.8	106.6	107.6	107.1	109.3
75°	84.0	83.4	82.8	81.2	81.2	80.2	80.6	81.8	83.1	82.1	84.0
77.5°	61.7	59.8	59.7	60.1	59.0	59.2	58.9	58.6	59.2	59.3	61.0
80°	47.5	45.2	45.9	45.6	45.2	45.0	44.4	44.7	45.0	45.2	46.2
82.5°	34.2	34.0	33.4	33.3	33.0	32.2	31.9	32.4	32.7	32.5	33.3
85°	17.4	16.6	17.2	16.9	17.2	16.9	15.9	15.9	16.6	16.2	16.9
87.5°	9.1	9.3	8.6	8.3	7.6	7.3	6.8	6.7	6.4	6.1	6.4
90°	19.6	20.4	17.9	15.5	13.0	10.6	9.0	7.3	4.9	3.3	1.6
92.5°	94.4	125.1	137.7	103.4	68.3	47.0	35.0	28.1	21.9	15.0	10.1
95°	391.4	482.6	429.7	296.2	175.0	105.8	74.0	52.9	39.1	30.1	27.6
97.5°	800.1	747.9	547.6	325.1	188.3	122.2	87.9	67.0	55.0	48.0	47.2
100°	931.0	770.7	520.8	306.8	186.4	129.4	97.7	78.1	66.8	61.1	60.3
102.5°	937.5	728.4	481.8	291.1	189.0	137.9	108.8	91.2	80.4	75.3	73.9
105°	887.9	654.3	433.7	280.0	196.2	152.2	126.9	111.5	101.7	96.9	94.4
107.5°	801.0	588.9	403.2	279.2	209.5	170.9	147.5	133.0	123.4	118.6	116.2
110°	746.2	551.8	391.4	282.4	220.5	183.9	161.1	147.3	138.4	134.3	131.8



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	698.7	527.0	384.9	288.9	231.6	197.6	175.5	161.6	152.7	148.6	146.2
115°	641.3	500.5	382.5	299.5	249.8	218.9	197.0	183.1	175.0	170.1	166.8
117.5°	606.6	484.9	383.9	313.5	269.2	238.6	218.3	202.8	195.3	191.3	187.5
120°	588.4	477.7	386.5	323.9	281.6	252.3	232.0	216.5	208.3	204.2	201.8
122.5°	573.4	473.1	391.1	333.7	294.6	266.0	244.3	229.5	220.7	216.6	214.2
125°	554.2	467.2	397.9	349.1	313.3	284.9	262.9	247.4	238.5	233.6	232.0
127.5°	537.3	464.2	405.8	361.8	329.6	302.1	280.1	263.0	253.9	247.9	245.5
130°	528.2	462.3	411.0	370.3	339.3	312.5	290.5	273.5	263.7	256.3	253.9
132.5°	519.7	461.6	414.9	378.1	347.8	321.6	300.3	283.2	271.5	263.5	260.4
135°	508.7	460.6	420.8	388.2	360.5	335.3	313.3	296.2	284.1	275.1	271.8
137.5°	499.0	458.9	424.6	395.7	369.3	345.0	324.7	307.8	294.7	286.0	282.6
140°	493.2	458.2	427.2	399.6	375.2	351.6	331.3	315.0	301.9	293.8	289.8
142.5°	488.0	456.9	429.2	403.5	379.8	356.8	337.7	321.5	309.7	300.9	297.5
145°	480.9	454.9	430.5	407.7	385.7	364.6	345.8	332.1	319.8	312.5	310.1
147.5°	474.1	451.8	430.5	410.3	390.6	371.3	355.3	341.9	331.4	324.2	322.8
150°	469.5	449.2	430.5	411.0	393.9	375.2	360.5	349.1	338.5	332.1	331.3
152.5°	464.4	446.0	428.5	412.3	395.8	379.8	365.7	355.6	346.3	339.8	339.7
155°	456.6	440.3	426.4	412.6	399.6	385.7	374.4	365.4	357.3	352.4	352.4
157.5°	447.8	435.2	423.7	413.4	401.7	390.6	381.8	374.2	367.0	363.1	362.5
160°	441.9	431.3	422.4	413.4	403.7	393.9	385.7	380.0	373.6	370.3	370.3
162.5°	436.0	427.4	419.8	412.8	404.3	395.8	389.0	383.9	378.8	376.2	376.2
165°	428.0	421.6	415.9	411.0	405.3	398.8	393.1	389.8	385.7	384.1	384.9
167.5°	420.4	415.7	412.0	409.7	405.1	400.4	396.8	394.5	391.4	390.6	391.6
170°	415.9	411.8	409.4	407.7	404.5	400.4	398.8	397.1	394.7	393.9	395.5
172.5°	411.3	408.5	407.4	407.1	404.5	401.0	400.1	399.1	397.3	397.1	398.1
175°	406.1	404.5	404.5	405.3	403.7	402.0	401.2	401.2	399.6	400.4	401.2
177.5°	402.7	402.0	402.7	404.0	402.7	402.0	402.0	402.0	401.4	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	648.5	649.7	654.0	657.0	660.5	662.5	664.5	666.0	668.0	668.5	675.7
5°	651.3	657.6	668.5	676.6	686.6	697.6	705.1	708.5	717.5	725.0	740.0
7.5°	650.5	663.8	680.4	697.5	715.8	732.8	747.5	765.0	777.5	796.1	814.6
10°	649.8	667.6	688.8	710.7	736.3	760.0	781.3	805.0	824.7	850.6	872.8
12.5°	647.6	669.1	698.5	724.4	755.5	788.2	819.7	850.2	867.6	910.8	931.2
15°	642.0	667.6	704.4	743.8	786.6	825.3	865.3	897.1	948.6	986.4	1010.5
17.5°	631.4	667.2	710.9	758.4	810.4	861.4	906.7	955.0	1009.7	1055.4	1104.2
20°	626.4	665.7	714.4	766.9	820.9	878.6	930.2	988.3	1047.9	1092.9	1155.4
22.5°	617.2	661.7	714.2	772.7	830.4	890.1	950.5	1009.0	1077.9	1139.9	1199.3
25°	602.0	652.0	706.3	771.6	839.4	899.3	971.4	1049.2	1121.0	1200.6	1260.0
27.5°	586.2	639.5	694.0	754.6	827.5	898.7	989.4	1077.3	1165.1	1233.9	1277.7
30°	573.9	625.7	682.0	743.1	815.3	899.9	1001.4	1097.2	1182.8	1241.9	1266.5
32.5°	560.7	613.3	663.0	727.2	804.0	899.2	1008.9	1109.0	1183.8	1223.1	1218.3
35°	539.9	583.9	632.3	694.1	784.7	893.6	1013.3	1110.0	1155.9	1147.5	1083.9
37.5°	509.9	547.0	594.6	662.3	762.2	882.2	1004.5	1077.2	1074.2	1005.5	913.2
40°	491.2	522.7	568.6	639.8	744.7	874.7	990.8	1038.0	998.0	902.1	791.6
42.5°	466.7	495.7	541.6	614.8	725.5	859.4	964.6	978.2	900.0	789.7	688.4
45°	428.8	454.4	501.8	577.4	696.7	826.2	900.6	867.2	761.9	647.9	570.8
47.5°	387.9	414.6	460.2	537.9	654.9	776.3	811.7	740.7	632.6	540.2	469.4
50°	362.2	387.8	432.4	510.9	626.7	735.4	750.1	658.3	559.0	477.8	419.6
52.5°	336.2	360.4	404.2	482.9	593.7	687.9	678.8	585.3	494.0	424.8	379.2
55°	297.6	320.4	362.2	435.9	536.8	611.4	578.6	489.3	413.8	360.0	325.4
57.5°	263.0	284.9	320.9	387.5	475.2	526.4	484.8	409.5	349.4	308.1	282.3
60°	239.5	258.9	293.2	355.1	431.2	470.3	429.0	362.6	311.9	278.8	255.8
62.5°	217.3	234.2	266.0	322.0	388.2	421.0	379.4	323.0	280.0	250.6	231.0
65°	183.6	198.9	227.0	270.8	325.1	346.9	311.0	265.4	232.0	210.2	197.1
67.5°	152.9	165.8	190.1	224.5	264.6	280.5	253.2	217.8	192.7	175.1	164.7
70°	132.4	143.7	162.7	192.3	228.6	240.8	215.2	186.1	167.7	153.6	144.0
72.5°	115.1	123.4	140.7	163.6	193.9	203.5	185.6	160.1	142.9	132.4	124.7
75°	87.7	94.6	105.8	124.3	145.2	150.8	137.4	121.5	109.9	102.4	96.4
77.5°	63.3	68.3	76.5	87.8	102.3	107.4	98.9	88.2	79.8	74.8	71.4
80°	47.8	51.9	58.7	68.1	76.8	79.7	74.6	66.5	60.6	57.8	55.0
82.5°	35.3	37.6	41.7	48.1	54.1	57.4	53.2	48.3	45.1	42.6	41.5
85°	17.8	19.1	21.0	23.4	27.1	28.5	26.8	25.6	23.7	22.2	22.2
87.5°	7.2	7.5	8.7	9.5	10.8	12.1	12.3	12.3	12.6	12.1	12.1
90°	3.3	4.9	7.3	9.0	10.6	13.0	15.5	17.9	20.4	19.6	20.4
92.5°	15.0	21.9	28.1	35.0	47.0	68.3	103.4	137.7	125.1	94.4	68.5
95°	30.1	39.1	52.9	74.0	105.8	175.0	296.2	429.7	482.6	391.4	292.9
97.5°	48.0	55.0	67.0	87.9	122.2	188.3	325.1	547.6	747.9	800.1	730.3
100°	61.1	66.8	78.1	97.7	129.4	186.4	306.8	520.8	770.7	931.0	959.5
102.5°	75.3	80.4	91.2	108.8	137.9	189.0	291.1	481.8	728.4	937.5	1035.7
105°	96.9	101.7	111.5	126.9	152.2	196.2	280.0	433.7	654.3	887.9	1057.9
107.5°	118.6	123.4	133.0	147.5	170.9	209.5	279.2	403.2	588.9	801.0	993.8
110°	134.3	138.4	147.3	161.1	183.9	220.5	282.4	391.4	551.8	746.2	932.6



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	148.6	152.7	161.6	175.5	197.6	231.6	288.9	384.9	527.0	698.7	872.0
115°	170.1	175.0	183.1	197.0	218.9	249.8	299.5	382.5	500.5	641.3	791.8
117.5°	191.3	195.3	202.8	218.3	238.6	269.2	313.5	383.9	484.9	606.6	733.8
120°	204.2	208.3	216.5	232.0	252.3	281.6	323.9	386.5	477.7	588.4	703.1
122.5°	216.6	220.7	229.5	244.3	266.0	294.6	333.7	391.1	473.1	573.4	679.1
125°	233.6	238.5	247.4	262.9	284.9	313.3	349.1	397.9	467.2	554.2	647.0
127.5°	247.9	253.9	263.0	280.1	302.1	329.6	361.8	405.8	464.2	537.3	619.0
130°	256.3	263.7	273.5	290.5	312.5	339.3	370.3	411.0	462.3	528.2	601.4
132.5°	263.5	271.5	283.2	300.3	321.6	347.8	378.1	414.9	461.6	519.7	585.1
135°	275.1	284.1	296.2	313.3	335.3	360.5	388.2	420.8	460.6	508.7	563.1
137.5°	286.0	294.7	307.8	324.7	345.0	369.3	395.7	424.6	458.9	499.0	543.2
140°	293.8	301.9	315.0	331.3	351.6	375.2	399.6	427.2	458.2	493.2	531.4
142.5°	300.9	309.7	321.5	337.7	356.8	379.8	403.5	429.2	456.9	488.0	520.3
145°	312.5	319.8	332.1	345.8	364.6	385.7	407.7	430.5	454.9	480.9	507.0
147.5°	324.2	331.4	341.9	355.3	371.3	390.6	410.3	430.5	451.8	474.1	496.1
150°	332.1	338.5	349.1	360.5	375.2	393.9	411.0	430.5	449.2	469.5	488.3
152.5°	339.8	346.3	355.6	365.7	379.8	395.8	412.3	428.5	446.0	464.4	481.1
155°	352.4	357.3	365.4	374.4	385.7	399.6	412.6	426.4	440.3	456.6	470.3
157.5°	363.1	367.0	374.2	381.8	390.6	401.7	413.4	423.7	435.2	447.8	459.0
160°	370.3	373.6	380.0	385.7	393.9	403.7	413.4	422.4	431.3	441.9	452.5
162.5°	376.2	378.8	383.9	389.0	395.8	404.3	412.8	419.8	427.4	436.0	444.7
165°	384.1	385.7	389.8	393.1	398.8	405.3	411.0	415.9	421.6	428.0	434.6
167.5°	390.6	391.4	394.5	396.8	400.4	405.1	409.7	412.0	415.7	420.4	425.7
170°	393.9	394.7	397.1	398.8	400.4	404.5	407.7	409.4	411.8	415.9	420.0
172.5°	397.1	397.3	399.1	400.1	401.0	404.5	407.1	407.4	408.5	411.3	414.7
175°	400.4	399.6	401.2	401.2	402.0	403.7	405.3	404.5	404.5	406.1	407.7
177.5°	402.0	401.4	402.0	402.0	402.0	402.7	404.0	402.7	402.0	402.7	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	678.2	678.5	681.2	683.2	682.2	683.5	684.0
5°	740.9	752.2	758.1	762.5	762.9	763.1	765.6
7.5°	830.0	842.0	850.8	864.2	868.2	872.8	871.5
10°	895.0	912.7	928.1	936.1	944.9	957.7	947.4
12.5°	955.6	987.2	1010.5	1023.0	1031.4	1033.9	1028.8
15°	1055.7	1097.0	1119.2	1118.5	1146.6	1158.8	1139.7
17.5°	1147.5	1185.6	1216.0	1231.7	1255.1	1260.3	1257.9
20°	1203.7	1245.3	1269.0	1295.8	1308.1	1319.0	1320.9
22.5°	1252.2	1289.5	1315.0	1337.3	1347.5	1352.7	1355.8
25°	1302.1	1331.5	1346.8	1354.5	1357.4	1356.7	1352.7
27.5°	1298.7	1300.9	1284.1	1267.5	1252.7	1236.0	1230.3
30°	1264.9	1238.7	1191.9	1165.3	1126.3	1095.4	1107.9
32.5°	1176.2	1124.1	1071.5	1013.4	965.4	951.8	938.0
35°	1003.9	912.1	858.4	796.0	770.9	746.0	728.8
37.5°	812.2	741.2	677.4	636.6	611.6	595.8	587.3
40°	702.3	638.2	585.8	552.7	533.6	515.8	513.3
42.5°	614.6	555.1	515.6	489.3	470.9	463.4	457.9
45°	503.4	461.8	435.3	416.5	404.4	399.7	393.5
47.5°	426.1	396.7	376.7	364.0	354.8	351.3	350.8
50°	382.9	358.5	343.8	333.8	326.6	325.4	320.4
52.5°	350.3	329.2	317.8	309.1	303.9	300.4	298.9
55°	304.1	290.1	279.8	274.8	270.8	267.3	267.3
57.5°	266.1	254.4	247.5	243.3	242.1	239.6	238.1
60°	242.6	232.6	227.3	223.6	221.1	221.4	218.6
62.5°	219.6	213.1	208.1	204.3	201.4	201.4	201.6
65°	187.0	182.1	178.3	177.1	175.2	173.0	173.6
67.5°	158.5	153.8	150.9	148.8	148.1	146.9	148.8
70°	138.0	134.6	132.4	130.5	129.9	130.2	131.8
72.5°	119.3	116.8	115.4	114.5	113.2	113.2	114.3
75°	93.7	91.8	90.6	89.6	89.3	89.3	89.3
77.5°	68.8	68.4	67.8	66.4	66.5	66.9	66.9
80°	54.3	53.4	53.1	52.4	51.5	50.9	52.4
82.5°	40.6	39.6	39.4	39.2	37.7	37.7	39.0
85°	21.9	21.0	21.2	21.0	21.0	20.6	20.6
87.5°	12.0	11.9	12.0	12.1	12.0	11.9	12.2
90°	21.2	22.0	23.6	22.7	23.6	24.4	23.6
92.5°	54.4	48.0	43.8	42.3	39.9	40.7	39.2
95°	198.6	155.5	126.1	110.7	103.4	97.7	94.4
97.5°	585.0	480.0	382.6	322.6	286.0	264.0	257.0
100°	893.6	798.3	682.8	600.6	541.2	509.5	510.3
102.5°	1033.6	978.0	904.8	840.8	793.8	767.3	748.5
105°	1139.4	1154.8	1133.7	1096.2	1065.3	1039.3	1035.2
107.5°	1126.0	1197.3	1226.3	1226.9	1216.5	1207.7	1200.2
110°	1082.4	1184.9	1241.9	1264.7	1271.2	1269.6	1268.0



TEST NUMBER: P331939-930

CATALOG NUMBER: S123DIP-S560D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1025.1	1140.0	1213.2	1254.9	1275.0	1281.2	1281.6
115°	933.4	1053.0	1141.7	1202.8	1238.6	1254.9	1259.0
117.5°	856.0	963.4	1053.4	1117.0	1158.1	1181.5	1187.0
120°	813.0	910.7	992.9	1057.1	1102.7	1122.3	1127.2
122.5°	778.5	869.0	945.3	1002.5	1043.5	1064.9	1071.1
125°	735.7	813.8	878.9	931.0	966.8	987.2	992.9
127.5°	698.1	768.6	827.8	874.2	904.8	923.2	928.4
130°	674.7	740.5	795.9	839.0	868.4	885.4	891.9
132.5°	652.5	713.9	766.6	807.1	836.4	851.6	856.1
135°	620.9	673.8	720.2	760.1	784.5	799.2	804.9
137.5°	590.5	636.1	676.3	709.8	734.6	746.9	750.6
140°	572.9	612.0	647.0	677.9	700.7	713.7	712.9
142.5°	556.0	589.9	620.3	646.7	666.8	678.6	677.8
145°	533.9	559.9	583.5	603.8	620.9	627.5	629.1
147.5°	517.4	538.4	555.2	570.6	582.2	588.4	589.1
150°	507.0	524.1	539.6	551.8	560.7	565.6	565.6
152.5°	497.3	512.4	525.2	534.8	543.2	546.1	546.1
155°	483.4	495.6	505.4	512.7	519.2	520.8	521.6
157.5°	469.9	479.3	487.0	493.3	498.2	499.5	499.4
160°	461.5	469.5	475.2	480.9	485.8	485.8	485.0
162.5°	452.3	459.8	464.9	468.6	472.8	472.8	472.0
165°	439.4	445.2	449.2	452.5	455.8	454.9	454.9
167.5°	429.5	432.8	435.7	437.2	439.4	438.6	438.6
170°	422.4	425.6	427.2	428.0	429.7	428.8	428.8
172.5°	416.5	419.1	420.1	420.3	421.9	420.4	419.8
175°	408.5	410.2	410.2	410.2	411.0	410.2	409.4
177.5°	404.0	404.6	404.6	404.0	404.6	403.3	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0

(END OF REPORT)