

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331921-930

Luminaire Tested: **S123DIP-S560D585U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331921-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S560D585U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3675.3 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6937	6937	6937	6937
5°	8272	6967	6174	6967
10°	10355	6932	5576	6932
15°	12700	6876	5192	6876
20°	15131	6788	4943	6788
25°	16066	6683	4888	6683
30°	13770	6606	4913	6606
35°	9577	6495	4964	6495
40°	7213	6367	4949	6367
45°	5990	6174	4886	6174
50°	5365	5784	4843	5784
55°	5016	5362	4782	5362
60°	4706	4921	4732	4921
65°	4422	4485	4582	4485
70°	4148	3991	4362	3991
75°	3714	3493	4001	3493
80°	3248	2864	3446	2864
85°	2544	2087	2322	2087



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.5	1.7
10°-20°	203.6	5.5
20°-30°	341.7	9.3
30°-40°	386.9	10.5
40°-50°	346.9	9.4
50°-60°	280.0	7.6
60°-70°	195.1	5.3
70°-80°	102.5	2.8
80°-90°	26.9	0.7
90°-100°	127.8	3.5
100°-110°	362.0	9.8
110°-120°	356.1	9.7
120°-130°	284.0	7.7
130°-140°	224.0	6.1
140°-150°	167.1	4.5
150°-160°	116.5	3.2
160°-170°	68.4	1.9
170°-180°	22.3	0.6
0°-30°	608.7	16.6
0°-40°	995.6	27.1
0°-60°	1622.5	44.1
0°-90°	1947.0	53.0
90°-120°	846.0	23.0
90°-150°	1521.1	41.4
90°-180°	1728.0	47.0
0°-180°	3675.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	644	644	644	644	644	
5°	766	645	571	645	766	79
15°	1140	617	466	617	1140	329
25°	1353	563	412	563	1353	593
35°	729	494	378	494	729	473
45°	394	406	321	406	394	311
55°	267	286	255	286	267	240
65°	174	176	180	176	174	173
75°	89	84	96	84	89	96
85°	21	17	19	17	21	25
90°	14	1	14	1	14	8
95°	54	16	54	16	54	97
105°	592	54	592	54	592	584
115°	719	95	719	95	719	699
125°	567	133	567	133	567	514
135°	460	155	460	155	460	357
145°	360	177	360	177	360	229
155°	298	201	298	201	298	139
165°	260	220	260	220	260	74
175°	234	229	234	229	234	23
180°	230	230	230	230	230	



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	684.0	683.5	682.2	683.2	681.2	678.5	678.2	675.7	668.5	668.0	666.0
5°	765.6	763.1	762.9	762.5	758.1	752.2	740.9	740.0	725.0	717.5	708.5
7.5°	871.5	872.8	868.2	864.2	850.8	842.0	830.0	814.6	796.1	777.5	765.0
10°	947.4	957.7	944.9	936.1	928.1	912.7	895.0	872.8	850.6	824.7	805.0
12.5°	1028.8	1033.9	1031.4	1023.0	1010.5	987.2	955.6	931.2	910.8	867.6	850.2
15°	1139.7	1158.8	1146.6	1118.5	1119.2	1097.0	1055.7	1010.5	986.4	948.6	897.1
17.5°	1257.9	1260.3	1255.1	1231.7	1216.0	1185.6	1147.5	1104.2	1055.4	1009.7	955.0
20°	1320.9	1319.0	1308.1	1295.8	1269.0	1245.3	1203.7	1155.4	1092.9	1047.9	988.3
22.5°	1355.8	1352.7	1347.5	1337.3	1315.0	1289.5	1252.2	1199.3	1139.9	1077.9	1009.0
25°	1352.7	1356.7	1357.4	1354.5	1346.8	1331.5	1302.1	1260.0	1200.6	1121.0	1049.2
27.5°	1230.3	1236.0	1252.7	1267.5	1284.1	1300.9	1298.7	1277.7	1233.9	1165.1	1077.3
30°	1107.9	1095.4	1126.3	1165.3	1191.9	1238.7	1264.9	1266.5	1241.9	1182.8	1097.2
32.5°	938.0	951.8	965.4	1013.4	1071.5	1124.1	1176.2	1218.3	1223.1	1183.8	1109.0
35°	728.8	746.0	770.9	796.0	858.4	912.1	1003.9	1083.9	1147.5	1155.9	1110.0
37.5°	587.3	595.8	611.6	636.6	677.4	741.2	812.2	913.2	1005.5	1074.2	1077.2
40°	513.3	515.8	533.6	552.7	585.8	638.2	702.3	791.6	902.1	998.0	1038.0
42.5°	457.9	463.4	470.9	489.3	515.6	555.1	614.6	688.4	789.7	900.0	978.2
45°	393.5	399.7	404.4	416.5	435.3	461.8	503.4	570.8	647.9	761.9	867.2
47.5°	350.8	351.3	354.8	364.0	376.7	396.7	426.1	469.4	540.2	632.6	740.7
50°	320.4	325.4	326.6	333.8	343.8	358.5	382.9	419.6	477.8	559.0	658.3
52.5°	298.9	300.4	303.9	309.1	317.8	329.2	350.3	379.2	424.8	494.0	585.3
55°	267.3	267.3	270.8	274.8	279.8	290.1	304.1	325.4	360.0	413.8	489.3
57.5°	238.1	239.6	242.1	243.3	247.5	254.4	266.1	282.3	308.1	349.4	409.5
60°	218.6	221.4	221.1	223.6	227.3	232.6	242.6	255.8	278.8	311.9	362.6
62.5°	201.6	201.4	201.4	204.3	208.1	213.1	219.6	231.0	250.6	280.0	323.0
65°	173.6	173.0	175.2	177.1	178.3	182.1	187.0	197.1	210.2	232.0	265.4
67.5°	148.8	146.9	148.1	148.8	150.9	153.8	158.5	164.7	175.1	192.7	217.8
70°	131.8	130.2	129.9	130.5	132.4	134.6	138.0	144.0	153.6	167.7	186.1
72.5°	114.3	113.2	113.2	114.5	115.4	116.8	119.3	124.7	132.4	142.9	160.1
75°	89.3	89.3	89.3	89.6	90.6	91.8	93.7	96.4	102.4	109.9	121.5
77.5°	66.9	66.9	66.5	66.4	67.8	68.4	68.8	71.4	74.8	79.8	88.2
80°	52.4	50.9	51.5	52.4	53.1	53.4	54.3	55.0	57.8	60.6	66.5
82.5°	39.0	37.7	37.7	39.2	39.4	39.6	40.6	41.5	42.6	45.1	48.3
85°	20.6	20.6	21.0	21.0	21.2	21.0	21.9	22.2	22.2	23.7	25.6
87.5°	10.2	9.8	9.9	10.1	9.9	10.0	10.2	10.4	10.4	10.8	10.8
90°	13.5	13.9	13.5	13.0	13.5	12.6	12.1	11.7	11.2	11.7	10.2
92.5°	22.4	23.2	22.7	24.2	25.0	27.5	31.1	39.1	54.0	71.5	78.7
95°	54.0	55.8	59.0	63.3	72.1	88.8	113.5	167.4	223.6	275.7	245.6
97.5°	146.8	150.8	163.4	184.3	218.7	274.3	334.3	417.4	457.2	427.4	312.8
100°	291.6	291.1	309.2	343.2	390.1	456.2	510.6	548.3	532.0	440.3	297.6
102.5°	427.7	438.4	453.6	480.5	517.0	558.9	590.6	591.8	535.7	416.2	275.3
105°	591.5	593.9	608.7	626.4	647.8	659.9	651.0	604.5	507.4	373.9	247.9
107.5°	685.8	690.1	695.1	701.5	700.7	684.1	643.4	567.9	457.7	336.5	230.4
110°	724.5	725.5	726.4	722.7	709.6	677.1	618.5	532.9	426.4	315.3	223.6



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	732.3	732.1	728.6	717.1	693.2	651.4	585.7	498.3	399.3	301.2	220.0
115°	719.4	717.1	707.8	687.3	652.4	601.8	533.4	452.5	366.5	286.0	218.6
117.5°	678.2	675.1	661.7	638.3	601.9	550.5	489.1	419.2	346.7	277.0	219.4
120°	644.1	641.2	630.1	604.1	567.4	520.3	464.6	401.8	336.2	273.0	220.9
122.5°	612.0	608.5	596.2	572.8	540.1	496.5	444.8	388.0	327.7	270.4	223.5
125°	567.4	564.1	552.4	532.0	502.2	465.0	420.4	369.7	316.7	266.9	227.4
127.5°	530.5	527.5	517.0	499.5	473.0	439.2	398.9	353.7	307.0	265.2	231.9
130°	509.6	506.0	496.2	479.5	454.8	423.1	385.5	343.6	301.8	264.2	234.8
132.5°	489.2	486.6	477.9	461.2	438.1	407.9	372.8	334.4	296.9	263.7	237.1
135°	459.9	456.6	448.3	434.3	411.6	385.1	354.8	321.8	290.7	263.2	240.4
137.5°	428.9	426.8	419.7	405.6	386.5	363.5	337.5	310.4	285.2	262.2	242.6
140°	407.3	407.8	400.4	387.3	369.7	349.7	327.3	303.7	281.8	261.8	244.1
142.5°	387.3	387.8	381.1	369.5	354.4	337.0	317.7	297.3	278.8	261.1	245.2
145°	359.5	358.6	354.8	345.0	333.5	319.9	305.1	289.7	274.8	259.9	246.0
147.5°	336.6	336.2	332.6	326.0	317.2	307.7	295.6	283.5	270.9	258.2	246.0
150°	323.2	323.2	320.4	315.3	308.3	299.5	289.7	279.0	268.3	256.7	246.0
152.5°	312.0	312.0	310.4	305.6	300.1	292.8	284.1	274.9	265.4	254.9	244.9
155°	298.1	297.6	296.7	292.9	288.8	283.2	276.2	268.8	260.9	251.6	243.7
157.5°	285.4	285.4	284.7	281.9	278.3	273.9	268.5	262.3	255.8	248.7	242.1
160°	277.1	277.6	277.6	274.8	271.6	268.3	263.7	258.5	252.5	246.5	241.3
162.5°	269.7	270.2	270.2	267.7	265.6	262.8	258.4	254.1	249.2	244.3	239.9
165°	259.9	259.9	260.4	258.5	256.7	254.4	251.1	248.3	244.6	240.9	237.7
167.5°	250.6	250.6	251.1	249.8	249.0	247.3	245.4	243.3	240.3	237.5	235.4
170°	245.1	245.1	245.6	244.6	244.1	243.2	241.3	239.9	237.7	235.3	233.9
172.5°	239.9	240.3	241.1	240.1	240.0	239.5	238.0	237.0	235.1	233.4	232.8
175°	233.9	234.4	234.8	234.4	234.4	234.4	233.4	233.0	232.0	231.1	231.1
177.5°	230.5	230.5	231.2	230.8	231.2	231.2	230.8	230.5	230.1	229.8	230.1
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	664.5	662.5	660.5	657.0	654.0	649.7	648.5	647.0	642.5	638.5	635.5
5°	705.1	697.6	686.6	676.6	668.5	657.6	651.3	644.8	635.4	627.0	620.1
7.5°	747.5	732.8	715.8	697.5	680.4	663.8	650.5	638.7	625.6	613.1	603.5
10°	781.3	760.0	736.3	710.7	688.8	667.6	649.8	634.2	617.3	602.7	590.4
12.5°	819.7	788.2	755.5	724.4	698.5	669.1	647.6	627.7	608.6	590.9	577.2
15°	865.3	825.3	786.6	743.8	704.4	667.6	642.0	617.0	594.8	576.7	559.2
17.5°	906.7	861.4	810.4	758.4	710.9	667.2	631.4	603.2	575.4	553.3	535.8
20°	930.2	878.6	820.9	766.9	714.4	665.7	626.4	592.6	562.7	539.2	519.6
22.5°	950.5	890.1	830.4	772.7	714.2	661.7	617.2	582.4	549.9	527.0	506.1
25°	971.4	899.3	839.4	771.6	706.3	652.0	602.0	562.7	530.2	503.4	481.8
27.5°	989.4	898.7	827.5	754.6	694.0	639.5	586.2	544.0	509.5	480.3	458.4
30°	1001.4	899.9	815.3	743.1	682.0	625.7	573.9	531.5	495.2	465.5	445.0
32.5°	1008.9	899.2	804.0	727.2	663.0	613.3	560.7	516.7	479.5	450.4	430.5
35°	1013.3	893.6	784.7	694.1	632.3	583.9	539.9	494.3	455.3	428.1	405.6
37.5°	1004.5	882.2	762.2	662.3	594.6	547.0	509.9	471.1	433.7	403.8	384.4
40°	990.8	874.7	744.7	639.8	568.6	522.7	491.2	453.1	416.2	387.8	369.7
42.5°	964.6	859.4	725.5	614.8	541.6	495.7	466.7	434.9	400.0	373.3	355.2
45°	900.6	826.2	696.7	577.4	501.8	454.4	428.8	405.6	374.1	348.1	332.6
47.5°	811.7	776.3	654.9	537.9	460.2	414.6	387.9	369.3	346.3	325.4	310.4
50°	750.1	735.4	626.7	510.9	432.4	387.8	362.2	345.4	328.8	307.9	294.2
52.5°	678.8	687.9	593.7	482.9	404.2	360.4	336.2	322.9	307.9	290.7	278.7
55°	578.6	611.4	536.8	435.9	362.2	320.4	297.6	285.7	277.0	264.2	253.9
57.5°	484.8	526.4	475.2	387.5	320.9	284.9	263.0	250.1	244.4	237.7	229.7
60°	429.0	470.3	431.2	355.1	293.2	258.9	239.5	228.6	223.0	218.3	211.4
62.5°	379.4	421.0	388.2	322.0	266.0	234.2	217.3	206.6	202.2	199.7	193.9
65°	311.0	346.9	325.1	270.8	227.0	198.9	183.6	176.1	172.0	171.1	167.4
67.5°	253.2	280.5	264.6	224.5	190.1	165.8	152.9	146.5	143.4	143.1	140.2
70°	215.2	240.8	228.6	192.3	162.7	143.7	132.4	126.8	124.9	124.6	123.0
72.5°	185.6	203.5	193.9	163.6	140.7	123.4	115.1	109.3	107.1	107.6	106.6
75°	137.4	150.8	145.2	124.3	105.8	94.6	87.7	84.0	82.1	83.1	81.8
77.5°	98.9	107.4	102.3	87.8	76.5	68.3	63.3	61.0	59.3	59.2	58.6
80°	74.6	79.7	76.8	68.1	58.7	51.9	47.8	46.2	45.2	45.0	44.7
82.5°	53.2	57.4	54.1	48.1	41.7	37.6	35.3	33.3	32.5	32.7	32.4
85°	26.8	28.5	27.1	23.4	21.0	19.1	17.8	16.9	16.2	16.6	15.9
87.5°	11.0	11.0	9.9	8.8	8.1	7.1	6.8	6.2	5.9	6.0	6.1
90°	8.8	7.4	6.0	5.1	4.2	2.8	1.9	0.9	1.9	2.8	4.2
92.5°	59.0	39.1	26.9	20.0	16.1	12.5	8.6	5.8	8.6	12.5	16.1
95°	169.3	100.0	60.4	42.3	30.2	22.3	17.2	15.8	17.2	22.3	30.2
97.5°	185.7	107.6	69.9	50.2	38.3	31.5	27.5	27.0	27.5	31.5	38.3
100°	175.3	106.5	73.9	55.8	44.7	38.2	34.9	34.4	34.9	38.2	44.7
102.5°	166.4	107.9	78.8	62.1	52.1	46.0	43.0	42.2	43.0	46.0	52.1
105°	160.0	112.1	87.0	72.6	63.7	58.1	55.4	54.0	55.4	58.1	63.7
107.5°	159.5	119.7	97.7	84.3	76.0	70.5	67.8	66.4	67.8	70.5	76.0
110°	161.3	126.0	105.1	92.0	84.1	79.1	76.7	75.3	76.7	79.1	84.1



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	165.1	132.3	112.9	100.3	92.4	87.2	85.0	83.5	85.0	87.2	92.4
115°	171.1	142.8	125.1	112.5	104.6	100.0	97.2	95.3	97.2	100.0	104.6
117.5°	179.1	153.8	136.3	124.7	115.9	111.6	109.3	107.1	109.3	111.6	115.9
120°	185.1	160.9	144.1	132.6	123.7	119.0	116.8	115.4	116.8	119.0	123.7
122.5°	190.7	168.4	152.0	139.6	131.1	126.1	123.8	122.4	123.8	126.1	131.1
125°	199.5	179.0	162.7	150.2	141.4	136.2	133.5	132.6	133.5	136.2	141.4
127.5°	206.8	188.3	172.6	160.0	150.3	145.1	141.6	140.2	141.6	145.1	150.3
130°	211.6	193.9	178.6	166.0	156.2	150.7	146.5	145.1	146.5	150.7	156.2
132.5°	216.1	198.8	183.8	171.6	161.8	155.2	150.6	148.8	150.6	155.2	161.8
135°	221.8	206.0	191.6	179.0	169.3	162.3	157.2	155.3	157.2	162.3	169.3
137.5°	226.1	211.0	197.1	185.6	175.9	168.4	163.4	161.4	163.4	168.4	175.9
140°	228.4	214.3	200.9	189.2	179.9	172.5	167.9	165.6	167.9	172.5	179.9
142.5°	230.6	217.0	203.9	193.0	183.7	177.0	171.9	170.0	171.9	177.0	183.7
145°	233.0	220.5	208.3	197.6	189.7	182.8	178.6	177.2	178.6	182.8	189.7
147.5°	234.5	223.2	212.1	203.0	195.4	189.4	185.2	184.4	185.2	189.4	195.4
150°	234.8	225.1	214.3	206.0	199.5	193.5	189.7	189.2	189.7	193.5	199.5
152.5°	235.6	226.2	217.0	209.0	203.3	198.0	194.2	194.1	194.2	198.0	203.3
155°	235.8	228.4	220.5	213.9	208.8	204.2	201.4	201.4	201.4	204.2	208.8
157.5°	236.3	229.5	223.2	218.2	213.9	209.7	207.5	207.1	207.5	209.7	213.9
160°	236.3	230.6	225.1	220.5	217.2	213.4	211.6	211.6	211.6	213.4	217.2
162.5°	235.9	231.1	226.2	222.3	219.4	216.5	214.9	214.9	214.9	216.5	219.4
165°	234.8	231.5	227.9	224.6	222.7	220.5	219.5	220.0	219.5	220.5	222.7
167.5°	234.1	231.5	228.8	226.7	225.4	223.6	223.2	223.8	223.2	223.6	225.4
170°	233.0	231.1	228.8	227.9	226.9	225.5	225.1	226.0	225.1	225.5	226.9
172.5°	232.6	231.1	229.2	228.6	228.0	227.1	226.9	227.5	226.9	227.1	228.0
175°	231.5	230.6	229.8	229.3	229.3	228.4	228.8	229.3	228.8	228.4	229.3
177.5°	230.8	230.1	229.8	229.8	229.8	229.3	229.8	230.1	229.8	229.3	229.8
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	633.7	632.0	629.5	625.7	622.7	618.0	618.0	618.7	618.7	618.5	618.0
5°	614.5	609.8	604.2	597.7	590.8	583.9	582.7	580.2	578.3	577.1	575.5
7.5°	594.2	586.0	577.7	568.6	560.2	553.3	548.5	544.5	541.8	539.2	537.1
10°	580.5	570.1	560.5	550.8	540.2	531.7	526.4	522.7	519.9	517.4	516.2
12.5°	564.3	552.4	541.8	532.6	521.0	512.3	507.2	505.5	502.1	496.9	494.2
15°	540.5	529.6	516.8	502.7	497.1	486.5	480.5	477.8	475.9	471.8	470.6
17.5°	520.2	505.9	491.5	481.0	470.6	462.0	458.7	455.2	452.7	449.4	448.4
20°	504.0	491.2	478.1	466.8	455.9	446.5	443.7	441.2	438.7	437.2	435.9
22.5°	487.5	474.7	463.8	453.3	441.6	435.5	432.4	429.7	428.0	426.9	425.7
25°	464.3	453.1	440.9	431.5	422.2	418.1	416.2	414.7	413.4	411.9	411.6
27.5°	443.6	431.4	421.5	412.7	406.0	402.6	400.8	400.1	400.3	400.9	401.2
30°	428.1	416.9	408.7	401.2	395.0	391.9	391.6	391.6	392.8	393.1	393.8
32.5°	413.8	404.6	396.5	389.2	384.5	382.4	383.6	383.6	384.6	385.4	386.5
35°	393.1	385.0	378.8	372.5	368.4	369.4	370.0	370.6	372.2	374.1	375.4
37.5°	373.3	366.3	359.8	354.9	353.0	354.7	356.2	357.5	359.4	360.8	362.0
40°	359.1	353.8	347.6	343.2	343.8	344.7	346.0	347.6	349.1	350.0	351.3
42.5°	345.8	340.3	335.6	331.9	332.8	334.0	334.8	335.6	337.4	339.1	339.8
45°	325.7	321.3	316.9	314.8	315.4	316.0	316.7	317.6	319.1	320.4	320.7
47.5°	303.0	299.9	297.0	294.9	295.9	295.6	296.4	298.5	299.0	299.7	301.4
50°	288.5	285.7	282.3	281.7	281.7	281.7	281.9	284.5	284.5	285.7	287.0
52.5°	272.6	270.8	268.6	267.4	266.9	266.9	268.2	269.5	269.9	271.7	273.0
55°	248.8	247.0	245.2	244.2	243.5	244.2	246.7	247.3	248.8	249.8	250.7
57.5°	224.2	222.7	221.3	220.8	220.6	221.4	222.8	224.7	225.1	228.0	229.3
60°	208.0	205.8	204.6	204.6	203.9	206.7	206.1	209.2	209.9	211.7	213.9
62.5°	191.2	188.3	187.8	187.8	188.7	189.5	190.4	191.8	193.4	195.8	197.4
65°	164.3	162.7	164.9	164.5	164.0	165.8	165.8	167.4	169.3	171.5	174.9
67.5°	138.7	137.9	138.1	138.1	139.0	140.1	141.0	142.4	144.6	146.9	149.1
70°	121.5	122.4	120.8	122.1	123.0	123.4	123.9	125.8	128.3	129.9	132.4
72.5°	104.8	104.7	104.8	105.3	106.3	106.9	107.5	109.6	112.3	113.7	115.7
75°	80.6	80.2	81.2	81.2	82.8	83.4	84.0	85.0	87.4	89.3	90.9
77.5°	58.9	59.2	59.0	60.1	59.7	59.8	61.7	62.6	62.9	66.6	67.4
80°	44.4	45.0	45.2	45.6	45.9	45.2	47.5	48.4	48.4	50.5	52.2
82.5°	31.9	32.2	33.0	33.3	33.4	34.0	34.2	34.9	35.6	36.6	38.6
85°	15.9	16.9	17.2	16.9	17.2	16.6	17.4	17.8	18.1	18.1	18.1
87.5°	6.0	6.4	6.5	7.0	7.0	7.6	7.5	7.1	7.2	8.0	7.2
90°	5.1	6.0	7.4	8.8	10.2	11.7	11.2	11.7	12.1	12.6	13.5
92.5°	20.0	26.9	39.1	59.0	78.7	71.5	54.0	39.1	31.1	27.5	25.0
95°	42.3	60.4	100.0	169.3	245.6	275.7	223.6	167.4	113.5	88.8	72.1
97.5°	50.2	69.9	107.6	185.7	312.8	427.4	457.2	417.4	334.3	274.3	218.7
100°	55.8	73.9	106.5	175.3	297.6	440.3	532.0	548.3	510.6	456.2	390.1
102.5°	62.1	78.8	107.9	166.4	275.3	416.2	535.7	591.8	590.6	558.9	517.0
105°	72.6	87.0	112.1	160.0	247.9	373.9	507.4	604.5	651.0	659.9	647.8
107.5°	84.3	97.7	119.7	159.5	230.4	336.5	457.7	567.9	643.4	684.1	700.7
110°	92.0	105.1	126.0	161.3	223.6	315.3	426.4	532.9	618.5	677.1	709.6



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	100.3	112.9	132.3	165.1	220.0	301.2	399.3	498.3	585.7	651.4	693.2
115°	112.5	125.1	142.8	171.1	218.6	286.0	366.5	452.5	533.4	601.8	652.4
117.5°	124.7	136.3	153.8	179.1	219.4	277.0	346.7	419.2	489.1	550.5	601.9
120°	132.6	144.1	160.9	185.1	220.9	273.0	336.2	401.8	464.6	520.3	567.4
122.5°	139.6	152.0	168.4	190.7	223.5	270.4	327.7	388.0	444.8	496.5	540.1
125°	150.2	162.7	179.0	199.5	227.4	266.9	316.7	369.7	420.4	465.0	502.2
127.5°	160.0	172.6	188.3	206.8	231.9	265.2	307.0	353.7	398.9	439.2	473.0
130°	166.0	178.6	193.9	211.6	234.8	264.2	301.8	343.6	385.5	423.1	454.8
132.5°	171.6	183.8	198.8	216.1	237.1	263.7	296.9	334.4	372.8	407.9	438.1
135°	179.0	191.6	206.0	221.8	240.4	263.2	290.7	321.8	354.8	385.1	411.6
137.5°	185.6	197.1	211.0	226.1	242.6	262.2	285.2	310.4	337.5	363.5	386.5
140°	189.2	200.9	214.3	228.4	244.1	261.8	281.8	303.7	327.3	349.7	369.7
142.5°	193.0	203.9	217.0	230.6	245.2	261.1	278.8	297.3	317.7	337.0	354.4
145°	197.6	208.3	220.5	233.0	246.0	259.9	274.8	289.7	305.1	319.9	333.5
147.5°	203.0	212.1	223.2	234.5	246.0	258.2	270.9	283.5	295.6	307.7	317.2
150°	206.0	214.3	225.1	234.8	246.0	256.7	268.3	279.0	289.7	299.5	308.3
152.5°	209.0	217.0	226.2	235.6	244.9	254.9	265.4	274.9	284.1	292.8	300.1
155°	213.9	220.5	228.4	235.8	243.7	251.6	260.9	268.8	276.2	283.2	288.8
157.5°	218.2	223.2	229.5	236.3	242.1	248.7	255.8	262.3	268.5	273.9	278.3
160°	220.5	225.1	230.6	236.3	241.3	246.5	252.5	258.5	263.7	268.3	271.6
162.5°	222.3	226.2	231.1	235.9	239.9	244.3	249.2	254.1	258.4	262.8	265.6
165°	224.6	227.9	231.5	234.8	237.7	240.9	244.6	248.3	251.1	254.4	256.7
167.5°	226.7	228.8	231.5	234.1	235.4	237.5	240.3	243.3	245.4	247.3	249.0
170°	227.9	228.8	231.1	233.0	233.9	235.3	237.7	239.9	241.3	243.2	244.1
172.5°	228.6	229.2	231.1	232.6	232.8	233.4	235.1	237.0	238.0	239.5	240.0
175°	229.3	229.8	230.6	231.5	231.1	231.1	232.0	233.0	233.4	234.4	234.4
177.5°	229.8	229.8	230.1	230.8	230.1	229.8	230.1	230.5	230.8	231.2	231.2
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	616.3	616.0	617.8	616.5	617.8	616.0	616.3	618.0	618.5	618.7	618.7
5°	573.6	574.5	571.4	571.4	571.4	574.5	573.6	575.5	577.1	578.3	580.2
7.5°	535.7	534.3	534.4	532.7	534.4	534.3	535.7	537.1	539.2	541.8	544.5
10°	512.4	510.5	509.9	510.2	509.9	510.5	512.4	516.2	517.4	519.9	522.7
12.5°	493.2	492.8	488.7	488.8	488.7	492.8	493.2	494.2	496.9	502.1	505.5
15°	470.6	464.6	464.0	465.9	464.0	464.6	470.6	470.6	471.8	475.9	477.8
17.5°	447.9	444.7	445.0	444.0	445.0	444.7	447.9	448.4	449.4	452.7	455.2
20°	435.9	434.1	433.7	431.5	433.7	434.1	435.9	435.9	437.2	438.7	441.2
22.5°	424.9	424.3	424.4	422.1	424.4	424.3	424.9	425.7	426.9	428.0	429.7
25°	411.2	412.8	411.6	411.6	411.6	412.8	411.2	411.6	411.9	413.4	414.7
27.5°	402.0	401.9	401.3	401.3	401.3	401.9	402.0	401.2	400.9	400.3	400.1
30°	395.0	394.7	395.3	395.3	395.3	394.7	395.0	393.8	393.1	392.8	391.6
32.5°	388.0	388.4	388.6	388.8	388.6	388.4	388.0	386.5	385.4	384.6	383.6
35°	377.2	377.5	378.5	377.8	378.5	377.5	377.2	375.4	374.1	372.2	370.6
37.5°	362.6	364.0	363.7	364.2	363.7	364.0	362.6	362.0	360.8	359.4	357.5
40°	351.6	352.5	352.2	352.2	352.2	352.5	351.6	351.3	350.0	349.1	347.6
42.5°	340.4	341.0	340.2	339.7	340.2	341.0	340.4	339.8	339.1	337.4	335.6
45°	322.0	321.3	322.3	321.0	322.3	321.3	322.0	320.7	320.4	319.1	317.6
47.5°	301.3	302.0	302.2	303.1	302.2	302.0	301.3	301.4	299.7	299.0	298.5
50°	287.6	289.4	289.4	289.2	289.4	289.4	287.6	287.0	285.7	284.5	284.5
52.5°	274.1	275.0	276.2	276.1	276.2	275.0	274.1	273.0	271.7	269.9	269.5
55°	253.2	253.9	254.5	254.8	254.5	253.9	253.2	250.7	249.8	248.8	247.3
57.5°	231.6	231.4	232.8	233.3	232.8	231.4	231.6	229.3	228.0	225.1	224.7
60°	216.4	216.4	218.9	219.8	218.9	216.4	216.4	213.9	211.7	209.9	209.2
62.5°	200.2	201.1	203.7	202.4	203.7	201.1	200.2	197.4	195.8	193.4	191.8
65°	176.4	179.0	178.6	179.9	178.6	179.0	176.4	174.9	171.5	169.3	167.4
67.5°	151.6	153.2	155.5	155.6	155.5	153.2	151.6	149.1	146.9	144.6	142.4
70°	134.9	136.5	137.7	138.6	137.7	136.5	134.9	132.4	129.9	128.3	125.8
72.5°	118.6	119.4	122.5	121.2	122.5	119.4	118.6	115.7	113.7	112.3	109.6
75°	93.0	95.2	97.1	96.2	97.1	95.2	93.0	90.9	89.3	87.4	85.0
77.5°	68.8	71.0	71.9	71.1	71.9	71.0	68.8	67.4	66.6	62.9	62.6
80°	54.3	54.1	55.9	55.6	55.9	54.1	54.3	52.2	50.5	48.4	48.4
82.5°	39.9	39.5	40.4	40.6	40.4	39.5	39.9	38.6	36.6	35.6	34.9
85°	19.3	20.3	19.1	18.8	19.1	20.3	19.3	18.1	18.1	18.1	17.8
87.5°	7.1	7.2	7.0	6.7	7.0	7.2	7.1	7.2	8.0	7.2	7.1
90°	13.0	13.5	13.9	13.5	13.9	13.5	13.0	13.5	12.6	12.1	11.7
92.5°	24.2	22.7	23.2	22.4	23.2	22.7	24.2	25.0	27.5	31.1	39.1
95°	63.3	59.0	55.8	54.0	55.8	59.0	63.3	72.1	88.8	113.5	167.4
97.5°	184.3	163.4	150.8	146.8	150.8	163.4	184.3	218.7	274.3	334.3	417.4
100°	343.2	309.2	291.1	291.6	291.1	309.2	343.2	390.1	456.2	510.6	548.3
102.5°	480.5	453.6	438.4	427.7	438.4	453.6	480.5	517.0	558.9	590.6	591.8
105°	626.4	608.7	593.9	591.5	593.9	608.7	626.4	647.8	659.9	651.0	604.5
107.5°	701.1	695.1	690.1	685.8	690.1	695.1	701.1	700.7	684.1	643.4	567.9
110°	722.7	726.4	725.5	724.5	725.5	726.4	722.7	709.6	677.1	618.5	532.9



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	717.1	728.6	732.1	732.3	732.1	728.6	717.1	693.2	651.4	585.7	498.3
115°	687.3	707.8	717.1	719.4	717.1	707.8	687.3	652.4	601.8	533.4	452.5
117.5°	638.3	661.7	675.1	678.2	675.1	661.7	638.3	601.9	550.5	489.1	419.2
120°	604.1	630.1	641.2	644.1	641.2	630.1	604.1	567.4	520.3	464.6	401.8
122.5°	572.8	596.2	608.5	612.0	608.5	596.2	572.8	540.1	496.5	444.8	388.0
125°	532.0	552.4	564.1	567.4	564.1	552.4	532.0	502.2	465.0	420.4	369.7
127.5°	499.5	517.0	527.5	530.5	527.5	517.0	499.5	473.0	439.2	398.9	353.7
130°	479.5	496.2	506.0	509.6	506.0	496.2	479.5	454.8	423.1	385.5	343.6
132.5°	461.2	477.9	486.6	489.2	486.6	477.9	461.2	438.1	407.9	372.8	334.4
135°	434.3	448.3	456.6	459.9	456.6	448.3	434.3	411.6	385.1	354.8	321.8
137.5°	405.6	419.7	426.8	428.9	426.8	419.7	405.6	386.5	363.5	337.5	310.4
140°	387.3	400.4	407.8	407.3	407.8	400.4	387.3	369.7	349.7	327.3	303.7
142.5°	369.5	381.1	387.8	387.3	387.8	381.1	369.5	354.4	337.0	317.7	297.3
145°	345.0	354.8	358.6	359.5	358.6	354.8	345.0	333.5	319.9	305.1	289.7
147.5°	326.0	332.6	336.2	336.6	336.2	332.6	326.0	317.2	307.7	295.6	283.5
150°	315.3	320.4	323.2	323.2	323.2	320.4	315.3	308.3	299.5	289.7	279.0
152.5°	305.6	310.4	312.0	312.0	312.0	310.4	305.6	300.1	292.8	284.1	274.9
155°	292.9	296.7	297.6	298.1	297.6	296.7	292.9	288.8	283.2	276.2	268.8
157.5°	281.9	284.7	285.4	285.4	285.4	284.7	281.9	278.3	273.9	268.5	262.3
160°	274.8	277.6	277.6	277.1	277.6	277.6	274.8	271.6	268.3	263.7	258.5
162.5°	267.7	270.2	270.2	269.7	270.2	270.2	267.7	265.6	262.8	258.4	254.1
165°	258.5	260.4	259.9	259.9	259.9	260.4	258.5	256.7	254.4	251.1	248.3
167.5°	249.8	251.1	250.6	250.6	250.6	251.1	249.8	249.0	247.3	245.4	243.3
170°	244.6	245.6	245.1	245.1	245.1	245.6	244.6	244.1	243.2	241.3	239.9
172.5°	240.1	241.1	240.3	239.9	240.3	241.1	240.1	240.0	239.5	238.0	237.0
175°	234.4	234.8	234.4	233.9	234.4	234.8	234.4	234.4	234.4	233.4	233.0
177.5°	230.8	231.2	230.5	230.5	230.5	231.2	230.8	231.2	231.2	230.8	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	618.0	618.0	622.7	625.7	629.5	632.0	633.7	635.5	638.5	642.5	647.0
5°	582.7	583.9	590.8	597.7	604.2	609.8	614.5	620.1	627.0	635.4	644.8
7.5°	548.5	553.3	560.2	568.6	577.7	586.0	594.2	603.5	613.1	625.6	638.7
10°	526.4	531.7	540.2	550.8	560.5	570.1	580.5	590.4	602.7	617.3	634.2
12.5°	507.2	512.3	521.0	532.6	541.8	552.4	564.3	577.2	590.9	608.6	627.7
15°	480.5	486.5	497.1	502.7	516.8	529.6	540.5	559.2	576.7	594.8	617.0
17.5°	458.7	462.0	470.6	481.0	491.5	505.9	520.2	535.8	553.3	575.4	603.2
20°	443.7	446.5	455.9	466.8	478.1	491.2	504.0	519.6	539.2	562.7	592.6
22.5°	432.4	435.5	441.6	453.3	463.8	474.7	487.5	506.1	527.0	549.9	582.4
25°	416.2	418.1	422.2	431.5	440.9	453.1	464.3	481.8	503.4	530.2	562.7
27.5°	400.8	402.6	406.0	412.7	421.5	431.4	443.6	458.4	480.3	509.5	544.0
30°	391.6	391.9	395.0	401.2	408.7	416.9	428.1	445.0	465.5	495.2	531.5
32.5°	383.6	382.4	384.5	389.2	396.5	404.6	413.8	430.5	450.4	479.5	516.7
35°	370.0	369.4	368.4	372.5	378.8	385.0	393.1	405.6	428.1	455.3	494.3
37.5°	356.2	354.7	353.0	354.9	359.8	366.3	373.3	384.4	403.8	433.7	471.1
40°	346.0	344.7	343.8	343.2	347.6	353.8	359.1	369.7	387.8	416.2	453.1
42.5°	334.8	334.0	332.8	331.9	335.6	340.3	345.8	355.2	373.3	400.0	434.9
45°	316.7	316.0	315.4	314.8	316.9	321.3	325.7	332.6	348.1	374.1	405.6
47.5°	296.4	295.6	295.9	294.9	297.0	299.9	303.0	310.4	325.4	346.3	369.3
50°	281.9	281.7	281.7	281.7	282.3	285.7	288.5	294.2	307.9	328.8	345.4
52.5°	268.2	266.9	266.9	267.4	268.6	270.8	272.6	278.7	290.7	307.9	322.9
55°	246.7	244.2	243.5	244.2	245.2	247.0	248.8	253.9	264.2	277.0	285.7
57.5°	222.8	221.4	220.6	220.8	221.3	222.7	224.2	229.7	237.7	244.4	250.1
60°	206.1	206.7	203.9	204.6	204.6	205.8	208.0	211.4	218.3	223.0	228.6
62.5°	190.4	189.5	188.7	187.8	187.8	188.3	191.2	193.9	199.7	202.2	206.6
65°	165.8	165.8	164.0	164.5	164.9	162.7	164.3	167.4	171.1	172.0	176.1
67.5°	141.0	140.1	139.0	138.1	138.1	137.9	138.7	140.2	143.1	143.4	146.5
70°	123.9	123.4	123.0	122.1	120.8	122.4	121.5	123.0	124.6	124.9	126.8
72.5°	107.5	106.9	106.3	105.3	104.8	104.7	104.8	106.6	107.6	107.1	109.3
75°	84.0	83.4	82.8	81.2	81.2	80.2	80.6	81.8	83.1	82.1	84.0
77.5°	61.7	59.8	59.7	60.1	59.0	59.2	58.9	58.6	59.2	59.3	61.0
80°	47.5	45.2	45.9	45.6	45.2	45.0	44.4	44.7	45.0	45.2	46.2
82.5°	34.2	34.0	33.4	33.3	33.0	32.2	31.9	32.4	32.7	32.5	33.3
85°	17.4	16.6	17.2	16.9	17.2	16.9	15.9	15.9	16.6	16.2	16.9
87.5°	7.5	7.6	7.0	7.0	6.5	6.4	6.0	6.1	6.0	5.9	6.2
90°	11.2	11.7	10.2	8.8	7.4	6.0	5.1	4.2	2.8	1.9	0.9
92.5°	54.0	71.5	78.7	59.0	39.1	26.9	20.0	16.1	12.5	8.6	5.8
95°	223.6	275.7	245.6	169.3	100.0	60.4	42.3	30.2	22.3	17.2	15.8
97.5°	457.2	427.4	312.8	185.7	107.6	69.9	50.2	38.3	31.5	27.5	27.0
100°	532.0	440.3	297.6	175.3	106.5	73.9	55.8	44.7	38.2	34.9	34.4
102.5°	535.7	416.2	275.3	166.4	107.9	78.8	62.1	52.1	46.0	43.0	42.2
105°	507.4	373.9	247.9	160.0	112.1	87.0	72.6	63.7	58.1	55.4	54.0
107.5°	457.7	336.5	230.4	159.5	119.7	97.7	84.3	76.0	70.5	67.8	66.4
110°	426.4	315.3	223.6	161.3	126.0	105.1	92.0	84.1	79.1	76.7	75.3



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	399.3	301.2	220.0	165.1	132.3	112.9	100.3	92.4	87.2	85.0	83.5
115°	366.5	286.0	218.6	171.1	142.8	125.1	112.5	104.6	100.0	97.2	95.3
117.5°	346.7	277.0	219.4	179.1	153.8	136.3	124.7	115.9	111.6	109.3	107.1
120°	336.2	273.0	220.9	185.1	160.9	144.1	132.6	123.7	119.0	116.8	115.4
122.5°	327.7	270.4	223.5	190.7	168.4	152.0	139.6	131.1	126.1	123.8	122.4
125°	316.7	266.9	227.4	199.5	179.0	162.7	150.2	141.4	136.2	133.5	132.6
127.5°	307.0	265.2	231.9	206.8	188.3	172.6	160.0	150.3	145.1	141.6	140.2
130°	301.8	264.2	234.8	211.6	193.9	178.6	166.0	156.2	150.7	146.5	145.1
132.5°	296.9	263.7	237.1	216.1	198.8	183.8	171.6	161.8	155.2	150.6	148.8
135°	290.7	263.2	240.4	221.8	206.0	191.6	179.0	169.3	162.3	157.2	155.3
137.5°	285.2	262.2	242.6	226.1	211.0	197.1	185.6	175.9	168.4	163.4	161.4
140°	281.8	261.8	244.1	228.4	214.3	200.9	189.2	179.9	172.5	167.9	165.6
142.5°	278.8	261.1	245.2	230.6	217.0	203.9	193.0	183.7	177.0	171.9	170.0
145°	274.8	259.9	246.0	233.0	220.5	208.3	197.6	189.7	182.8	178.6	177.2
147.5°	270.9	258.2	246.0	234.5	223.2	212.1	203.0	195.4	189.4	185.2	184.4
150°	268.3	256.7	246.0	234.8	225.1	214.3	206.0	199.5	193.5	189.7	189.2
152.5°	265.4	254.9	244.9	235.6	226.2	217.0	209.0	203.3	198.0	194.2	194.1
155°	260.9	251.6	243.7	235.8	228.4	220.5	213.9	208.8	204.2	201.4	201.4
157.5°	255.8	248.7	242.1	236.3	229.5	223.2	218.2	213.9	209.7	207.5	207.1
160°	252.5	246.5	241.3	236.3	230.6	225.1	220.5	217.2	213.4	211.6	211.6
162.5°	249.2	244.3	239.9	235.9	231.1	226.2	222.3	219.4	216.5	214.9	214.9
165°	244.6	240.9	237.7	234.8	231.5	227.9	224.6	222.7	220.5	219.5	220.0
167.5°	240.3	237.5	235.4	234.1	231.5	228.8	226.7	225.4	223.6	223.2	223.8
170°	237.7	235.3	233.9	233.0	231.1	228.8	227.9	226.9	225.5	225.1	226.0
172.5°	235.1	233.4	232.8	232.6	231.1	229.2	228.6	228.0	227.1	226.9	227.5
175°	232.0	231.1	231.1	231.5	230.6	229.8	229.3	229.3	228.4	228.8	229.3
177.5°	230.1	229.8	230.1	230.8	230.1	229.8	229.8	229.8	229.3	229.8	230.1
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	648.5	649.7	654.0	657.0	660.5	662.5	664.5	666.0	668.0	668.5	675.7
5°	651.3	657.6	668.5	676.6	686.6	697.6	705.1	708.5	717.5	725.0	740.0
7.5°	650.5	663.8	680.4	697.5	715.8	732.8	747.5	765.0	777.5	796.1	814.6
10°	649.8	667.6	688.8	710.7	736.3	760.0	781.3	805.0	824.7	850.6	872.8
12.5°	647.6	669.1	698.5	724.4	755.5	788.2	819.7	850.2	867.6	910.8	931.2
15°	642.0	667.6	704.4	743.8	786.6	825.3	865.3	897.1	948.6	986.4	1010.5
17.5°	631.4	667.2	710.9	758.4	810.4	861.4	906.7	955.0	1009.7	1055.4	1104.2
20°	626.4	665.7	714.4	766.9	820.9	878.6	930.2	988.3	1047.9	1092.9	1155.4
22.5°	617.2	661.7	714.2	772.7	830.4	890.1	950.5	1009.0	1077.9	1139.9	1199.3
25°	602.0	652.0	706.3	771.6	839.4	899.3	971.4	1049.2	1121.0	1200.6	1260.0
27.5°	586.2	639.5	694.0	754.6	827.5	898.7	989.4	1077.3	1165.1	1233.9	1277.7
30°	573.9	625.7	682.0	743.1	815.3	899.9	1001.4	1097.2	1182.8	1241.9	1266.5
32.5°	560.7	613.3	663.0	727.2	804.0	899.2	1008.9	1109.0	1183.8	1223.1	1218.3
35°	539.9	583.9	632.3	694.1	784.7	893.6	1013.3	1110.0	1155.9	1147.5	1083.9
37.5°	509.9	547.0	594.6	662.3	762.2	882.2	1004.5	1077.2	1074.2	1005.5	913.2
40°	491.2	522.7	568.6	639.8	744.7	874.7	990.8	1038.0	998.0	902.1	791.6
42.5°	466.7	495.7	541.6	614.8	725.5	859.4	964.6	978.2	900.0	789.7	688.4
45°	428.8	454.4	501.8	577.4	696.7	826.2	900.6	867.2	761.9	647.9	570.8
47.5°	387.9	414.6	460.2	537.9	654.9	776.3	811.7	740.7	632.6	540.2	469.4
50°	362.2	387.8	432.4	510.9	626.7	735.4	750.1	658.3	559.0	477.8	419.6
52.5°	336.2	360.4	404.2	482.9	593.7	687.9	678.8	585.3	494.0	424.8	379.2
55°	297.6	320.4	362.2	435.9	536.8	611.4	578.6	489.3	413.8	360.0	325.4
57.5°	263.0	284.9	320.9	387.5	475.2	526.4	484.8	409.5	349.4	308.1	282.3
60°	239.5	258.9	293.2	355.1	431.2	470.3	429.0	362.6	311.9	278.8	255.8
62.5°	217.3	234.2	266.0	322.0	388.2	421.0	379.4	323.0	280.0	250.6	231.0
65°	183.6	198.9	227.0	270.8	325.1	346.9	311.0	265.4	232.0	210.2	197.1
67.5°	152.9	165.8	190.1	224.5	264.6	280.5	253.2	217.8	192.7	175.1	164.7
70°	132.4	143.7	162.7	192.3	228.6	240.8	215.2	186.1	167.7	153.6	144.0
72.5°	115.1	123.4	140.7	163.6	193.9	203.5	185.6	160.1	142.9	132.4	124.7
75°	87.7	94.6	105.8	124.3	145.2	150.8	137.4	121.5	109.9	102.4	96.4
77.5°	63.3	68.3	76.5	87.8	102.3	107.4	98.9	88.2	79.8	74.8	71.4
80°	47.8	51.9	58.7	68.1	76.8	79.7	74.6	66.5	60.6	57.8	55.0
82.5°	35.3	37.6	41.7	48.1	54.1	57.4	53.2	48.3	45.1	42.6	41.5
85°	17.8	19.1	21.0	23.4	27.1	28.5	26.8	25.6	23.7	22.2	22.2
87.5°	6.8	7.1	8.1	8.8	9.9	11.0	11.0	10.8	10.8	10.4	10.4
90°	1.9	2.8	4.2	5.1	6.0	7.4	8.8	10.2	11.7	11.2	11.7
92.5°	8.6	12.5	16.1	20.0	26.9	39.1	59.0	78.7	71.5	54.0	39.1
95°	17.2	22.3	30.2	42.3	60.4	100.0	169.3	245.6	275.7	223.6	167.4
97.5°	27.5	31.5	38.3	50.2	69.9	107.6	185.7	312.8	427.4	457.2	417.4
100°	34.9	38.2	44.7	55.8	73.9	106.5	175.3	297.6	440.3	532.0	548.3
102.5°	43.0	46.0	52.1	62.1	78.8	107.9	166.4	275.3	416.2	535.7	591.8
105°	55.4	58.1	63.7	72.6	87.0	112.1	160.0	247.9	373.9	507.4	604.5
107.5°	67.8	70.5	76.0	84.3	97.7	119.7	159.5	230.4	336.5	457.7	567.9
110°	76.7	79.1	84.1	92.0	105.1	126.0	161.3	223.6	315.3	426.4	532.9



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	85.0	87.2	92.4	100.3	112.9	132.3	165.1	220.0	301.2	399.3	498.3
115°	97.2	100.0	104.6	112.5	125.1	142.8	171.1	218.6	286.0	366.5	452.5
117.5°	109.3	111.6	115.9	124.7	136.3	153.8	179.1	219.4	277.0	346.7	419.2
120°	116.8	119.0	123.7	132.6	144.1	160.9	185.1	220.9	273.0	336.2	401.8
122.5°	123.8	126.1	131.1	139.6	152.0	168.4	190.7	223.5	270.4	327.7	388.0
125°	133.5	136.2	141.4	150.2	162.7	179.0	199.5	227.4	266.9	316.7	369.7
127.5°	141.6	145.1	150.3	160.0	172.6	188.3	206.8	231.9	265.2	307.0	353.7
130°	146.5	150.7	156.2	166.0	178.6	193.9	211.6	234.8	264.2	301.8	343.6
132.5°	150.6	155.2	161.8	171.6	183.8	198.8	216.1	237.1	263.7	296.9	334.4
135°	157.2	162.3	169.3	179.0	191.6	206.0	221.8	240.4	263.2	290.7	321.8
137.5°	163.4	168.4	175.9	185.6	197.1	211.0	226.1	242.6	262.2	285.2	310.4
140°	167.9	172.5	179.9	189.2	200.9	214.3	228.4	244.1	261.8	281.8	303.7
142.5°	171.9	177.0	183.7	193.0	203.9	217.0	230.6	245.2	261.1	278.8	297.3
145°	178.6	182.8	189.7	197.6	208.3	220.5	233.0	246.0	259.9	274.8	289.7
147.5°	185.2	189.4	195.4	203.0	212.1	223.2	234.5	246.0	258.2	270.9	283.5
150°	189.7	193.5	199.5	206.0	214.3	225.1	234.8	246.0	256.7	268.3	279.0
152.5°	194.2	198.0	203.3	209.0	217.0	226.2	235.6	244.9	254.9	265.4	274.9
155°	201.4	204.2	208.8	213.9	220.5	228.4	235.8	243.7	251.6	260.9	268.8
157.5°	207.5	209.7	213.9	218.2	223.2	229.5	236.3	242.1	248.7	255.8	262.3
160°	211.6	213.4	217.2	220.5	225.1	230.6	236.3	241.3	246.5	252.5	258.5
162.5°	214.9	216.5	219.4	222.3	226.2	231.1	235.9	239.9	244.3	249.2	254.1
165°	219.5	220.5	222.7	224.6	227.9	231.5	234.8	237.7	240.9	244.6	248.3
167.5°	223.2	223.6	225.4	226.7	228.8	231.5	234.1	235.4	237.5	240.3	243.3
170°	225.1	225.5	226.9	227.9	228.8	231.1	233.0	233.9	235.3	237.7	239.9
172.5°	226.9	227.1	228.0	228.6	229.2	231.1	232.6	232.8	233.4	235.1	237.0
175°	228.8	228.4	229.3	229.3	229.8	230.6	231.5	231.1	231.1	232.0	233.0
177.5°	229.8	229.3	229.8	229.8	229.8	230.1	230.8	230.1	229.8	230.1	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	644.5	644.5	644.5	644.5	644.5	644.5	644.5
2.5°	678.2	678.5	681.2	683.2	682.2	683.5	684.0
5°	740.9	752.2	758.1	762.5	762.9	763.1	765.6
7.5°	830.0	842.0	850.8	864.2	868.2	872.8	871.5
10°	895.0	912.7	928.1	936.1	944.9	957.7	947.4
12.5°	955.6	987.2	1010.5	1023.0	1031.4	1033.9	1028.8
15°	1055.7	1097.0	1119.2	1118.5	1146.6	1158.8	1139.7
17.5°	1147.5	1185.6	1216.0	1231.7	1255.1	1260.3	1257.9
20°	1203.7	1245.3	1269.0	1295.8	1308.1	1319.0	1320.9
22.5°	1252.2	1289.5	1315.0	1337.3	1347.5	1352.7	1355.8
25°	1302.1	1331.5	1346.8	1354.5	1357.4	1356.7	1352.7
27.5°	1298.7	1300.9	1284.1	1267.5	1252.7	1236.0	1230.3
30°	1264.9	1238.7	1191.9	1165.3	1126.3	1095.4	1107.9
32.5°	1176.2	1124.1	1071.5	1013.4	965.4	951.8	938.0
35°	1003.9	912.1	858.4	796.0	770.9	746.0	728.8
37.5°	812.2	741.2	677.4	636.6	611.6	595.8	587.3
40°	702.3	638.2	585.8	552.7	533.6	515.8	513.3
42.5°	614.6	555.1	515.6	489.3	470.9	463.4	457.9
45°	503.4	461.8	435.3	416.5	404.4	399.7	393.5
47.5°	426.1	396.7	376.7	364.0	354.8	351.3	350.8
50°	382.9	358.5	343.8	333.8	326.6	325.4	320.4
52.5°	350.3	329.2	317.8	309.1	303.9	300.4	298.9
55°	304.1	290.1	279.8	274.8	270.8	267.3	267.3
57.5°	266.1	254.4	247.5	243.3	242.1	239.6	238.1
60°	242.6	232.6	227.3	223.6	221.1	221.4	218.6
62.5°	219.6	213.1	208.1	204.3	201.4	201.4	201.6
65°	187.0	182.1	178.3	177.1	175.2	173.0	173.6
67.5°	158.5	153.8	150.9	148.8	148.1	146.9	148.8
70°	138.0	134.6	132.4	130.5	129.9	130.2	131.8
72.5°	119.3	116.8	115.4	114.5	113.2	113.2	114.3
75°	93.7	91.8	90.6	89.6	89.3	89.3	89.3
77.5°	68.8	68.4	67.8	66.4	66.5	66.9	66.9
80°	54.3	53.4	53.1	52.4	51.5	50.9	52.4
82.5°	40.6	39.6	39.4	39.2	37.7	37.7	39.0
85°	21.9	21.0	21.2	21.0	21.0	20.6	20.6
87.5°	10.2	10.0	9.9	10.1	9.9	9.8	10.2
90°	12.1	12.6	13.5	13.0	13.5	13.9	13.5
92.5°	31.1	27.5	25.0	24.2	22.7	23.2	22.4
95°	113.5	88.8	72.1	63.3	59.0	55.8	54.0
97.5°	334.3	274.3	218.7	184.3	163.4	150.8	146.8
100°	510.6	456.2	390.1	343.2	309.2	291.1	291.6
102.5°	590.6	558.9	517.0	480.5	453.6	438.4	427.7
105°	651.0	659.9	647.8	626.4	608.7	593.9	591.5
107.5°	643.4	684.1	700.7	701.1	695.1	690.1	685.8
110°	618.5	677.1	709.6	722.7	726.4	725.5	724.5



TEST NUMBER: P331921-930

CATALOG NUMBER: S123DIP-S560D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	585.7	651.4	693.2	717.1	728.6	732.1	732.3
115°	533.4	601.8	652.4	687.3	707.8	717.1	719.4
117.5°	489.1	550.5	601.9	638.3	661.7	675.1	678.2
120°	464.6	520.3	567.4	604.1	630.1	641.2	644.1
122.5°	444.8	496.5	540.1	572.8	596.2	608.5	612.0
125°	420.4	465.0	502.2	532.0	552.4	564.1	567.4
127.5°	398.9	439.2	473.0	499.5	517.0	527.5	530.5
130°	385.5	423.1	454.8	479.5	496.2	506.0	509.6
132.5°	372.8	407.9	438.1	461.2	477.9	486.6	489.2
135°	354.8	385.1	411.6	434.3	448.3	456.6	459.9
137.5°	337.5	363.5	386.5	405.6	419.7	426.8	428.9
140°	327.3	349.7	369.7	387.3	400.4	407.8	407.3
142.5°	317.7	337.0	354.4	369.5	381.1	387.8	387.3
145°	305.1	319.9	333.5	345.0	354.8	358.6	359.5
147.5°	295.6	307.7	317.2	326.0	332.6	336.2	336.6
150°	289.7	299.5	308.3	315.3	320.4	323.2	323.2
152.5°	284.1	292.8	300.1	305.6	310.4	312.0	312.0
155°	276.2	283.2	288.8	292.9	296.7	297.6	298.1
157.5°	268.5	273.9	278.3	281.9	284.7	285.4	285.4
160°	263.7	268.3	271.6	274.8	277.6	277.6	277.1
162.5°	258.4	262.8	265.6	267.7	270.2	270.2	269.7
165°	251.1	254.4	256.7	258.5	260.4	259.9	259.9
167.5°	245.4	247.3	249.0	249.8	251.1	250.6	250.6
170°	241.3	243.2	244.1	244.6	245.6	245.1	245.1
172.5°	238.0	239.5	240.0	240.1	241.1	240.3	239.9
175°	233.4	234.4	234.4	234.4	234.8	234.4	233.9
177.5°	230.8	231.2	231.2	230.8	231.2	230.5	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8

(END OF REPORT)