

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331957-930

Luminaire Tested: **S123DIP-S775D365U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331957-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIP-S775D365U930-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3730.8 lumens  
Efficiency: N/A  
Efficacy: 106.6 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331957-930  
CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	99	95	91	97	94	90	87	84	82	79	76	74	72	68	66	65	61
2	94	87	80	75	89	82	77	72	74	70	66	67	63	61	60	57	55	52
3	86	76	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	38
5	73	61	53	46	69	58	51	45	53	47	42	48	43	39	43	39	36	33
6	67	55	46	41	63	52	45	39	48	41	37	43	38	34	39	35	32	29
7	62	50	41	36	59	47	40	35	43	37	33	40	34	30	36	32	28	26
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	25	31	26	23	21
10	50	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9482	9482	9482	9482
5°	11309	9524	8440	9524
10°	14154	9475	7623	9475
15°	17361	9399	7096	9399
20°	20681	9279	6757	9279
25°	21960	9136	6682	9136
30°	18821	9028	6717	9028
35°	13090	8878	6787	8878
40°	9860	8702	6764	8702
45°	8187	8441	6680	8441
50°	7333	7906	6620	7906
55°	6855	7328	6536	7328
60°	6433	6725	6469	6725
65°	6044	6133	6260	6133
70°	5668	5454	5964	5454
75°	5078	4774	5465	4774
80°	4444	3918	4711	3918
85°	3483	2853	3162	2853



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.8	2.3
10°-20°	278.3	7.5
20°-30°	467.0	12.5
30°-40°	528.8	14.2
40°-50°	474.2	12.7
50°-60°	382.7	10.3
60°-70°	266.7	7.1
70°-80°	140.2	3.8
80°-90°	35.4	0.9
90°-100°	79.2	2.1
100°-110°	224.3	6.0
110°-120°	220.6	5.9
120°-130°	176.0	4.7
130°-140°	138.8	3.7
140°-150°	103.6	2.8
150°-160°	72.2	1.9
160°-170°	42.4	1.1
170°-180°	13.8	0.4
0°-30°	832.1	22.3
0°-40°	1360.9	36.5
0°-60°	2217.8	59.4
0°-90°	2660.0	71.3
90°-120°	524.1	14.0
90°-150°	942.4	25.3
90°-180°	1071.0	28.7
0°-180°	3730.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	881	881	881	881	881	
5°	1047	881	781	881	1047	108
15°	1558	843	637	843	1558	450
25°	1849	769	563	769	1849	811
35°	996	676	516	676	996	647
45°	538	554	439	554	538	426
55°	365	390	348	390	365	328
65°	237	241	246	241	237	236
75°	122	115	131	115	122	131
85°	28	23	26	23	28	33
90°	8	1	8	1	8	6
95°	33	10	33	10	33	60
105°	366	33	366	33	366	362
115°	446	59	446	59	446	433
125°	352	82	352	82	352	319
135°	285	96	285	96	285	221
145°	223	110	223	110	223	142
155°	185	125	185	125	185	86
165°	161	136	161	136	161	46
175°	145	142	145	142	145	14
180°	142	142	142	142	142	



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	934.9	934.3	932.5	933.9	931.2	927.4	927.1	923.7	913.7	913.1	910.4
5°	1046.6	1043.2	1042.8	1042.3	1036.3	1028.3	1012.8	1011.5	991.1	980.8	968.5
7.5°	1191.2	1192.9	1186.7	1181.3	1163.0	1151.0	1134.5	1113.4	1088.3	1062.7	1045.7
10°	1295.0	1309.0	1291.6	1279.6	1268.5	1247.6	1223.3	1192.9	1162.7	1127.2	1100.3
12.5°	1406.3	1413.2	1409.7	1398.5	1381.2	1349.4	1306.3	1272.8	1245.0	1185.9	1162.1
15°	1557.9	1584.0	1567.3	1528.8	1529.7	1499.4	1443.1	1381.2	1348.3	1296.7	1226.3
17.5°	1719.4	1722.6	1715.6	1683.6	1662.2	1620.6	1568.6	1509.3	1442.7	1380.1	1305.5
20°	1805.5	1802.9	1788.0	1771.3	1734.6	1702.2	1645.4	1579.2	1493.9	1432.4	1350.9
22.5°	1853.3	1849.0	1841.9	1828.0	1797.4	1762.6	1711.6	1639.3	1558.1	1473.4	1379.2
25°	1849.0	1854.6	1855.4	1851.5	1840.9	1820.0	1779.9	1722.2	1641.1	1532.3	1434.1
27.5°	1681.7	1689.5	1712.4	1732.6	1755.2	1778.2	1775.2	1746.5	1686.5	1592.6	1472.5
30°	1514.3	1497.3	1539.5	1592.9	1629.2	1693.2	1729.1	1731.2	1697.5	1616.8	1499.8
32.5°	1282.1	1301.0	1319.6	1385.3	1464.6	1536.5	1607.9	1665.3	1671.9	1618.2	1515.9
35°	996.2	1019.7	1053.9	1087.9	1173.4	1246.8	1372.2	1481.5	1568.6	1580.1	1517.4
37.5°	802.7	814.4	836.0	870.2	926.0	1013.1	1110.2	1248.3	1374.4	1468.3	1472.3
40°	701.7	705.2	729.4	755.5	800.7	872.5	959.9	1082.0	1233.1	1364.2	1418.8
42.5°	625.9	633.4	643.8	668.7	704.7	758.7	840.1	940.9	1079.5	1230.3	1337.2
45°	537.8	546.3	552.8	569.4	595.0	631.3	688.0	780.2	885.7	1041.5	1185.3
47.5°	479.6	480.3	485.0	497.6	515.0	542.3	582.4	641.6	738.4	864.7	1012.4
50°	437.9	444.7	446.5	456.2	469.9	490.0	523.3	573.6	653.1	764.0	899.8
52.5°	408.5	410.6	415.4	422.5	434.4	450.0	478.9	518.4	580.7	675.2	800.1
55°	365.3	365.3	370.1	375.6	382.5	396.5	415.7	444.7	492.1	565.6	668.9
57.5°	325.4	327.5	330.8	332.6	338.3	347.7	363.7	385.8	421.1	477.6	559.7
60°	298.8	302.6	302.2	305.6	310.7	318.0	331.7	349.6	381.2	426.4	495.5
62.5°	275.6	275.3	275.2	279.3	284.5	291.4	300.2	315.8	342.6	382.7	441.6
65°	237.3	236.4	239.5	242.0	243.7	248.8	255.7	269.3	287.2	317.2	362.8
67.5°	203.3	200.9	202.5	203.3	206.3	210.3	216.6	225.1	239.4	263.3	297.7
70°	180.1	178.0	177.6	178.4	181.0	183.9	188.7	196.7	210.0	229.2	254.4
72.5°	156.2	154.7	154.7	156.5	157.8	159.7	163.1	170.5	181.0	195.4	218.9
75°	122.1	122.1	122.1	122.5	123.8	125.5	128.1	131.9	140.0	150.3	166.0
77.5°	91.5	91.4	90.9	90.8	92.7	93.5	94.1	97.7	102.2	109.1	120.6
80°	71.7	69.5	70.4	71.7	72.6	73.0	74.3	75.1	79.0	82.8	90.9
82.5°	53.2	51.4	51.6	53.6	53.8	54.2	55.5	56.7	58.1	61.6	66.0
85°	28.2	28.2	28.6	28.6	29.0	28.6	29.8	30.3	30.3	32.4	35.0
87.5°	11.9	11.3	11.6	11.8	11.6	11.8	12.1	12.4	12.6	13.0	13.2
90°	8.3	8.6	8.3	8.1	8.3	7.7	7.5	7.2	6.9	7.2	6.4
92.5°	13.9	14.4	14.1	15.0	15.5	17.0	19.2	24.3	33.4	44.3	48.8
95°	33.4	34.6	36.6	39.2	44.7	55.0	70.3	103.7	138.6	170.9	152.1
97.5°	91.0	93.4	101.3	114.2	135.5	169.9	207.1	258.5	283.2	264.8	193.9
100°	180.7	180.3	191.6	212.6	241.7	282.7	316.3	339.7	329.6	272.9	184.4
102.5°	265.0	271.7	281.0	297.7	320.3	346.3	365.9	366.6	331.9	257.9	170.6
105°	366.5	367.9	377.2	388.1	401.4	408.8	403.3	374.5	314.3	231.6	153.6
107.5°	424.9	427.5	430.6	434.4	434.1	423.9	398.6	351.8	283.6	208.5	142.8
110°	448.9	449.5	450.0	447.8	439.7	419.5	383.2	330.2	264.2	195.3	138.6



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	453.7	453.6	451.4	444.3	429.5	403.6	362.9	308.8	247.4	186.5	136.2
115°	445.7	444.3	438.5	425.8	404.2	372.8	330.4	280.3	227.1	177.2	135.4
117.5°	420.2	418.2	410.0	395.5	372.9	341.0	303.0	259.8	214.7	171.6	135.9
120°	399.0	397.3	390.4	374.2	351.5	322.4	287.8	248.9	208.3	169.1	136.9
122.5°	379.2	377.0	369.4	354.9	334.7	307.6	275.6	240.4	203.0	167.5	138.4
125°	351.5	349.5	342.3	329.6	311.2	288.1	260.5	229.0	196.2	165.3	140.9
127.5°	328.6	326.9	320.3	309.5	293.1	272.1	247.1	219.2	190.2	164.4	143.7
130°	315.8	313.5	307.4	297.0	281.8	262.2	238.9	212.9	186.9	163.6	145.5
132.5°	303.1	301.5	296.1	285.8	271.4	252.7	231.0	207.2	184.0	163.4	146.9
135°	284.9	282.9	277.8	269.1	254.9	238.6	219.8	199.3	180.1	163.1	149.0
137.5°	265.8	264.4	260.1	251.3	239.5	225.2	209.0	192.2	176.7	162.4	150.3
140°	252.4	252.7	248.1	240.0	229.0	216.6	202.8	188.2	174.6	162.2	151.2
142.5°	239.9	240.2	236.1	228.9	219.6	208.8	196.8	184.3	172.8	161.8	152.0
145°	222.7	222.2	219.8	213.8	206.6	198.2	189.0	179.5	170.2	161.0	152.4
147.5°	208.6	208.3	206.1	202.0	196.6	190.6	183.2	175.6	167.9	160.0	152.4
150°	200.2	200.2	198.5	195.3	191.0	185.6	179.5	172.8	166.2	159.1	152.4
152.5°	193.3	193.3	192.2	189.3	186.0	181.4	176.0	170.3	164.4	157.9	151.7
155°	184.7	184.4	183.8	181.5	178.9	175.5	171.1	166.6	161.6	155.9	151.0
157.5°	176.8	176.8	176.3	174.6	172.4	169.7	166.3	162.5	158.5	154.1	150.0
160°	171.7	172.0	172.0	170.2	168.3	166.2	163.4	160.2	156.5	152.7	149.5
162.5°	167.1	167.4	167.4	165.9	164.6	162.8	160.1	157.4	154.3	151.3	148.6
165°	161.0	161.0	161.3	160.2	159.1	157.6	155.6	153.8	151.6	149.3	147.2
167.5°	155.3	155.3	155.6	154.7	154.3	153.2	152.1	150.7	148.9	147.2	145.9
170°	151.8	151.8	152.1	151.6	151.2	150.7	149.5	148.6	147.2	145.8	145.0
172.5°	148.6	148.9	149.4	148.8	148.7	148.4	147.5	146.8	145.6	144.6	144.2
175°	145.0	145.2	145.5	145.2	145.2	145.2	144.6	144.3	143.7	143.2	143.2
177.5°	142.8	142.8	143.2	143.0	143.2	143.2	143.0	142.8	142.6	142.4	142.6
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	908.2	905.6	902.8	898.1	894.0	888.1	886.4	884.4	878.2	872.8	868.7
5°	963.8	953.5	938.6	925.0	913.9	898.9	890.4	881.4	868.6	857.0	847.7
7.5°	1021.8	1001.7	978.4	953.3	929.9	907.4	889.2	873.0	855.1	838.1	824.9
10°	1067.9	1038.9	1006.5	971.4	941.6	912.6	888.2	866.9	843.8	823.8	807.1
12.5°	1120.5	1077.5	1032.7	990.3	954.9	914.6	885.2	858.0	831.8	807.7	789.0
15°	1182.8	1128.1	1075.1	1016.7	963.0	912.6	877.6	843.4	813.1	788.3	764.4
17.5°	1239.4	1177.5	1107.7	1036.7	971.8	912.1	863.1	824.4	786.5	756.3	732.5
20°	1271.5	1201.1	1122.1	1048.3	976.6	910.0	856.2	810.1	769.2	737.1	710.2
22.5°	1299.2	1216.8	1135.1	1056.1	976.2	904.5	843.6	796.1	751.7	720.4	691.8
25°	1327.9	1229.2	1147.3	1054.7	965.5	891.2	822.9	769.2	724.7	688.0	658.6
27.5°	1352.4	1228.4	1131.1	1031.5	948.6	874.2	801.2	743.6	696.4	656.6	626.6
30°	1368.8	1230.1	1114.4	1015.9	932.2	855.3	784.5	726.4	676.9	636.4	608.2
32.5°	1379.1	1229.1	1099.1	994.0	906.2	838.3	766.4	706.3	655.4	615.6	588.4
35°	1385.0	1221.6	1072.6	948.8	864.3	798.2	738.0	675.6	622.3	585.1	554.5
37.5°	1373.1	1205.7	1041.9	905.3	812.8	747.6	697.0	643.9	592.9	552.0	525.5
40°	1354.3	1195.6	1018.0	874.6	777.2	714.5	671.4	619.3	568.9	530.1	505.3
42.5°	1318.4	1174.7	991.6	840.4	740.4	677.6	638.0	594.4	546.7	510.3	485.6
45°	1230.9	1129.4	952.3	789.2	685.9	621.0	586.0	554.5	511.4	475.9	454.5
47.5°	1109.5	1061.2	895.2	735.2	629.1	566.6	530.3	504.8	473.4	444.7	424.3
50°	1025.2	1005.2	856.6	698.3	591.2	530.1	495.1	472.1	449.5	420.9	402.1
52.5°	927.9	940.3	811.5	660.1	552.5	492.5	459.6	441.3	420.8	397.3	380.9
55°	790.9	835.7	733.7	595.8	495.1	437.9	406.8	390.5	378.6	361.1	347.0
57.5°	662.6	719.7	649.5	529.7	438.7	389.4	359.5	341.8	334.1	325.0	313.9
60°	586.4	642.8	589.5	485.3	400.8	353.8	327.3	312.4	304.8	298.3	288.9
62.5°	518.5	575.5	530.7	440.3	363.5	320.0	297.0	282.4	276.4	273.0	265.1
65°	425.1	474.2	444.3	370.1	310.3	271.9	250.9	240.8	235.2	233.9	228.8
67.5°	346.0	383.4	361.6	307.0	259.9	226.7	209.0	200.2	196.0	195.6	191.8
70°	294.1	329.1	312.4	262.9	222.4	196.3	181.0	173.3	170.7	170.3	168.2
72.5°	253.8	278.2	265.0	223.6	192.3	168.7	157.4	149.4	146.5	147.1	145.6
75°	187.8	206.2	198.4	169.9	144.7	129.3	119.9	114.8	112.3	113.6	111.9
77.5°	135.1	146.8	139.8	120.0	104.5	93.4	86.5	83.3	81.0	81.0	80.1
80°	102.0	108.8	105.0	93.0	80.2	70.8	65.3	63.2	61.9	61.5	61.1
82.5°	72.6	78.4	73.9	65.7	57.0	51.4	48.3	45.4	44.5	44.8	44.3
85°	36.7	38.8	37.1	32.0	28.6	26.0	24.3	23.1	22.2	22.6	21.8
87.5°	13.7	13.9	12.7	11.3	10.4	9.2	9.1	8.3	7.7	7.8	7.7
90°	5.5	4.6	3.8	3.2	2.6	1.7	1.1	0.6	1.1	1.7	2.6
92.5°	36.6	24.2	16.6	12.4	9.9	7.7	5.3	3.6	5.3	7.7	9.9
95°	104.8	62.0	37.4	26.3	18.8	13.9	10.7	9.8	10.7	13.9	18.8
97.5°	115.0	66.7	43.3	31.1	23.7	19.5	17.0	16.7	17.0	19.5	23.7
100°	108.6	66.0	45.8	34.6	27.6	23.6	21.6	21.4	21.6	23.6	27.6
102.5°	103.1	66.9	48.8	38.5	32.3	28.5	26.7	26.2	26.7	28.5	32.3
105°	99.1	69.5	53.9	44.9	39.5	36.0	34.3	33.4	34.3	36.0	39.5
107.5°	98.8	74.2	60.5	52.2	47.0	43.7	42.0	41.2	42.0	43.7	47.0
110°	100.0	78.1	65.1	57.1	52.2	49.0	47.5	46.6	47.5	49.0	52.2





TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	102.3	82.0	70.0	62.1	57.2	54.1	52.6	51.8	52.6	54.1	57.2
115°	106.0	88.5	77.5	69.7	64.8	62.0	60.3	59.0	60.3	62.0	64.8
117.5°	111.0	95.3	84.5	77.3	71.8	69.1	67.7	66.4	67.7	69.1	71.8
120°	114.6	99.7	89.3	82.1	76.6	73.8	72.3	71.4	72.3	73.8	76.6
122.5°	118.1	104.3	94.2	86.5	81.3	78.1	76.7	75.8	76.7	78.1	81.3
125°	123.6	111.0	100.9	93.0	87.6	84.4	82.7	82.1	82.7	84.4	87.6
127.5°	128.1	116.7	107.0	99.1	93.1	89.9	87.7	86.9	87.7	89.9	93.1
130°	131.1	120.2	110.6	102.9	96.8	93.4	90.7	89.9	90.7	93.4	96.8
132.5°	133.9	123.1	113.9	106.3	100.3	96.1	93.3	92.2	93.3	96.1	100.3
135°	137.5	127.6	118.7	111.0	104.8	100.5	97.3	96.2	97.3	100.5	104.8
137.5°	140.1	130.8	122.1	115.0	108.9	104.4	101.3	100.0	101.3	104.4	108.9
140°	141.5	132.8	124.5	117.2	111.5	106.9	104.0	102.6	104.0	106.9	111.5
142.5°	142.8	134.4	126.3	119.6	113.8	109.7	106.6	105.3	106.6	109.7	113.8
145°	144.3	136.6	129.1	122.5	117.6	113.2	110.6	109.7	110.6	113.2	117.6
147.5°	145.3	138.3	131.4	125.8	121.1	117.3	114.8	114.3	114.8	117.3	121.1
150°	145.5	139.4	132.8	127.6	123.6	119.8	117.6	117.2	117.6	119.8	123.6
152.5°	145.9	140.1	134.4	129.5	125.9	122.6	120.3	120.3	120.3	122.6	125.9
155°	146.1	141.5	136.6	132.6	129.4	126.5	124.7	124.7	124.7	126.5	129.4
157.5°	146.3	142.2	138.3	135.2	132.5	130.0	128.6	128.3	128.6	130.0	132.5
160°	146.3	142.9	139.4	136.6	134.5	132.2	131.1	131.1	131.1	132.2	134.5
162.5°	146.1	143.2	140.1	137.7	135.9	134.1	133.1	133.1	133.1	134.1	135.9
165°	145.5	143.5	141.2	139.2	138.0	136.6	136.0	136.2	136.0	136.6	138.0
167.5°	145.0	143.4	141.8	140.5	139.7	138.6	138.3	138.6	138.3	138.6	139.7
170°	144.3	143.2	141.8	141.2	140.6	139.7	139.4	140.0	139.4	139.7	140.6
172.5°	144.1	143.2	141.9	141.6	141.3	140.6	140.6	141.0	140.6	140.6	141.3
175°	143.5	142.9	142.4	142.0	142.0	141.5	141.8	142.0	141.8	141.5	142.0
177.5°	143.0	142.6	142.4	142.4	142.4	142.1	142.4	142.6	142.4	142.1	142.4
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	866.3	863.9	860.5	855.3	851.3	844.7	844.7	845.8	845.8	845.5	844.7
5°	840.0	833.6	825.9	816.9	807.6	798.2	796.5	793.0	790.5	788.8	786.6
7.5°	812.3	800.9	789.7	777.1	765.7	756.3	749.7	744.2	740.7	736.9	734.3
10°	793.4	779.3	766.1	752.9	738.4	726.9	719.7	714.5	710.7	707.3	705.6
12.5°	771.3	755.1	740.5	728.0	712.1	700.3	693.3	691.0	686.4	679.2	675.5
15°	738.8	723.9	706.4	687.2	679.5	665.0	656.9	653.1	650.4	644.9	643.2
17.5°	711.1	691.5	671.9	657.5	643.3	631.5	627.0	622.2	618.8	614.2	612.9
20°	688.9	671.4	653.5	638.1	623.1	610.3	606.5	603.1	599.7	597.5	595.8
22.5°	666.3	648.9	634.0	619.6	603.7	595.3	591.2	587.4	585.0	583.6	581.9
25°	634.7	619.3	602.7	589.9	577.1	571.5	568.9	566.8	565.1	563.0	562.6
27.5°	606.3	589.6	576.1	564.2	555.0	550.3	547.9	546.8	547.2	548.0	548.5
30°	585.1	569.8	558.7	548.5	540.0	535.7	535.2	535.2	537.0	537.4	538.3
32.5°	565.7	553.1	542.0	532.1	525.6	522.7	524.3	524.3	525.7	526.8	528.3
35°	537.4	526.3	517.7	509.2	503.7	504.9	505.8	506.6	508.7	511.4	513.1
37.5°	510.3	500.7	491.8	485.1	482.6	484.9	486.9	488.7	491.2	493.2	494.9
40°	490.8	483.6	475.1	469.0	469.9	471.2	473.0	475.1	477.2	478.5	480.2
42.5°	472.7	465.1	458.7	453.7	454.9	456.6	457.5	458.7	461.1	463.4	464.5
45°	445.2	439.2	433.3	430.2	431.1	431.9	432.8	434.1	436.2	437.9	438.4
47.5°	414.2	410.0	406.0	403.1	404.5	404.1	405.2	408.0	408.6	409.7	412.1
50°	394.4	390.5	385.9	385.0	385.0	385.0	385.4	388.8	388.8	390.5	392.2
52.5°	372.5	370.1	367.0	365.5	364.8	364.8	366.6	368.4	369.0	371.5	373.2
55°	340.1	337.6	335.1	333.8	332.9	333.8	337.2	338.0	340.1	341.4	342.8
57.5°	306.5	304.5	302.5	301.7	301.6	302.7	304.6	307.1	307.7	311.6	313.6
60°	284.3	281.3	279.6	279.6	278.8	282.6	281.7	286.0	286.8	289.3	292.4
62.5°	261.4	257.4	256.7	256.7	257.9	259.0	260.2	262.0	264.3	267.5	269.9
65°	224.5	222.4	225.3	224.9	224.0	226.7	226.7	228.8	231.3	234.3	239.0
67.5°	189.6	188.5	188.7	188.7	190.0	191.5	192.7	194.5	197.6	200.8	203.8
70°	166.0	167.3	165.2	166.9	168.2	168.6	169.4	172.0	175.5	177.6	181.0
72.5°	143.2	143.1	143.3	144.0	145.3	146.0	146.9	149.9	153.6	155.4	158.1
75°	110.1	109.7	111.0	111.0	113.1	114.0	114.8	116.1	119.5	122.1	124.2
77.5°	80.4	81.0	80.6	82.1	81.5	81.7	84.3	85.6	85.9	91.0	92.1
80°	60.6	61.5	61.9	62.3	62.8	61.9	64.9	66.1	66.1	69.1	71.3
82.5°	43.5	44.0	45.2	45.6	45.7	46.6	46.8	47.7	48.8	50.1	52.8
85°	21.8	23.1	23.5	23.1	23.5	22.6	23.9	24.3	24.8	24.8	24.8
87.5°	7.5	7.9	7.7	8.2	8.1	8.6	8.6	7.9	8.0	9.0	7.8
90°	3.2	3.8	4.6	5.5	6.4	7.2	6.9	7.2	7.5	7.7	8.3
92.5°	12.4	16.6	24.2	36.6	48.8	44.3	33.4	24.3	19.2	17.0	15.5
95°	26.3	37.4	62.0	104.8	152.1	170.9	138.6	103.7	70.3	55.0	44.7
97.5°	31.1	43.3	66.7	115.0	193.9	264.8	283.2	258.5	207.1	169.9	135.5
100°	34.6	45.8	66.0	108.6	184.4	272.9	329.6	339.7	316.3	282.7	241.7
102.5°	38.5	48.8	66.9	103.1	170.6	257.9	331.9	366.6	365.9	346.3	320.3
105°	44.9	53.9	69.5	99.1	153.6	231.6	314.3	374.5	403.3	408.8	401.4
107.5°	52.2	60.5	74.2	98.8	142.8	208.5	283.6	351.8	398.6	423.9	434.1
110°	57.1	65.1	78.1	100.0	138.6	195.3	264.2	330.2	383.2	419.5	439.7



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	62.1	70.0	82.0	102.3	136.2	186.5	247.4	308.8	362.9	403.6	429.5
115°	69.7	77.5	88.5	106.0	135.4	177.2	227.1	280.3	330.4	372.8	404.2
117.5°	77.3	84.5	95.3	111.0	135.9	171.6	214.7	259.8	303.0	341.0	372.9
120°	82.1	89.3	99.7	114.6	136.9	169.1	208.3	248.9	287.8	322.4	351.5
122.5°	86.5	94.2	104.3	118.1	138.4	167.5	203.0	240.4	275.6	307.6	334.7
125°	93.0	100.9	111.0	123.6	140.9	165.3	196.2	229.0	260.5	288.1	311.2
127.5°	99.1	107.0	116.7	128.1	143.7	164.4	190.2	219.2	247.1	272.1	293.1
130°	102.9	110.6	120.2	131.1	145.5	163.6	186.9	212.9	238.9	262.2	281.8
132.5°	106.3	113.9	123.1	133.9	146.9	163.4	184.0	207.2	231.0	252.7	271.4
135°	111.0	118.7	127.6	137.5	149.0	163.1	180.1	199.3	219.8	238.6	254.9
137.5°	115.0	122.1	130.8	140.1	150.3	162.4	176.7	192.2	209.0	225.2	239.5
140°	117.2	124.5	132.8	141.5	151.2	162.2	174.6	188.2	202.8	216.6	229.0
142.5°	119.6	126.3	134.4	142.8	152.0	161.8	172.8	184.3	196.8	208.8	219.6
145°	122.5	129.1	136.6	144.3	152.4	161.0	170.2	179.5	189.0	198.2	206.6
147.5°	125.8	131.4	138.3	145.3	152.4	160.0	167.9	175.6	183.2	190.6	196.6
150°	127.6	132.8	139.4	145.5	152.4	159.1	166.2	172.8	179.5	185.6	191.0
152.5°	129.5	134.4	140.1	145.9	151.7	157.9	164.4	170.3	176.0	181.4	186.0
155°	132.6	136.6	141.5	146.1	151.0	155.9	161.6	166.6	171.1	175.5	178.9
157.5°	135.2	138.3	142.2	146.3	150.0	154.1	158.5	162.5	166.3	169.7	172.4
160°	136.6	139.4	142.9	146.3	149.5	152.7	156.5	160.2	163.4	166.2	168.3
162.5°	137.7	140.1	143.2	146.1	148.6	151.3	154.3	157.4	160.1	162.8	164.6
165°	139.2	141.2	143.5	145.5	147.2	149.3	151.6	153.8	155.6	157.6	159.1
167.5°	140.5	141.8	143.4	145.0	145.9	147.2	148.9	150.7	152.1	153.2	154.3
170°	141.2	141.8	143.2	144.3	145.0	145.8	147.2	148.6	149.5	150.7	151.2
172.5°	141.6	141.9	143.2	144.1	144.2	144.6	145.6	146.8	147.5	148.4	148.7
175°	142.0	142.4	142.9	143.5	143.2	143.2	143.7	144.3	144.6	145.2	145.2
177.5°	142.4	142.4	142.6	143.0	142.6	142.4	142.6	142.8	143.0	143.2	143.2
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	842.4	842.0	844.4	842.7	844.4	842.0	842.4	844.7	845.5	845.8	845.8
5°	784.1	785.4	781.1	781.1	781.1	785.4	784.1	786.6	788.8	790.5	793.0
7.5°	732.1	730.3	730.4	728.1	730.4	730.3	732.1	734.3	736.9	740.7	744.2
10°	700.4	697.9	697.0	697.4	697.0	697.9	700.4	705.6	707.3	710.7	714.5
12.5°	674.1	673.6	668.0	668.1	668.0	673.6	674.1	675.5	679.2	686.4	691.0
15°	643.2	635.1	634.2	636.8	634.2	635.1	643.2	643.2	644.9	650.4	653.1
17.5°	612.2	608.0	608.2	606.9	608.2	608.0	612.2	612.9	614.2	618.8	622.2
20°	595.8	593.3	592.9	589.9	592.9	593.3	595.8	595.8	597.5	599.7	603.1
22.5°	580.8	580.0	580.2	576.9	580.2	580.0	580.8	581.9	583.6	585.0	587.4
25°	562.1	564.3	562.6	562.6	562.6	564.3	562.1	562.6	563.0	565.1	566.8
27.5°	549.5	549.4	548.5	548.5	548.5	549.4	549.5	548.5	548.0	547.2	546.8
30°	540.0	539.5	540.4	540.4	540.4	539.5	540.0	538.3	537.4	537.0	535.2
32.5°	530.4	531.0	531.2	531.5	531.2	531.0	530.4	528.3	526.8	525.7	524.3
35°	515.6	516.0	517.3	516.5	517.3	516.0	515.6	513.1	511.4	508.7	506.6
37.5°	495.6	497.6	497.2	497.8	497.2	497.6	495.6	494.9	493.2	491.2	488.7
40°	480.6	481.9	481.4	481.4	481.4	481.9	480.6	480.2	478.5	477.2	475.1
42.5°	465.2	466.2	465.0	464.4	465.0	466.2	465.2	464.5	463.4	461.1	458.7
45°	440.0	439.2	440.5	438.8	440.5	439.2	440.0	438.4	437.9	436.2	434.1
47.5°	411.9	412.7	413.1	414.3	413.1	412.7	411.9	412.1	409.7	408.6	408.0
50°	393.1	395.7	395.7	395.3	395.7	395.7	393.1	392.2	390.5	388.8	388.8
52.5°	374.6	375.9	377.6	377.5	377.6	375.9	374.6	373.2	371.5	369.0	368.4
55°	346.2	347.0	347.9	348.3	347.9	347.0	346.2	342.8	341.4	340.1	338.0
57.5°	316.6	316.3	318.3	318.9	318.3	316.3	316.6	313.6	311.6	307.7	307.1
60°	295.8	295.8	299.2	300.5	299.2	295.8	295.8	292.4	289.3	286.8	286.0
62.5°	273.6	275.0	278.3	276.5	278.3	275.0	273.6	269.9	267.5	264.3	262.0
65°	241.2	244.6	244.2	245.8	244.2	244.6	241.2	239.0	234.3	231.3	228.8
67.5°	207.2	209.4	212.5	212.7	212.5	209.4	207.2	203.8	200.8	197.6	194.5
70°	184.4	186.5	188.3	189.5	188.3	186.5	184.4	181.0	177.6	175.5	172.0
72.5°	162.2	163.3	167.4	165.6	167.4	163.3	162.2	158.1	155.4	153.6	149.9
75°	127.2	130.2	132.7	131.4	132.7	130.2	127.2	124.2	122.1	119.5	116.1
77.5°	94.1	97.0	98.2	97.2	98.2	97.0	94.1	92.1	91.0	85.9	85.6
80°	74.3	73.9	76.4	76.0	76.4	73.9	74.3	71.3	69.1	66.1	66.1
82.5°	54.5	54.1	55.2	55.5	55.2	54.1	54.5	52.8	50.1	48.8	47.7
85°	26.5	27.7	26.0	25.6	26.0	27.7	26.5	24.8	24.8	24.8	24.3
87.5°	7.7	7.8	7.5	7.2	7.5	7.8	7.7	7.8	9.0	8.0	7.9
90°	8.1	8.3	8.6	8.3	8.6	8.3	8.1	8.3	7.7	7.5	7.2
92.5°	15.0	14.1	14.4	13.9	14.4	14.1	15.0	15.5	17.0	19.2	24.3
95°	39.2	36.6	34.6	33.4	34.6	36.6	39.2	44.7	55.0	70.3	103.7
97.5°	114.2	101.3	93.4	91.0	93.4	101.3	114.2	135.5	169.9	207.1	258.5
100°	212.6	191.6	180.3	180.7	180.3	191.6	212.6	241.7	282.7	316.3	339.7
102.5°	297.7	281.0	271.7	265.0	271.7	281.0	297.7	320.3	346.3	365.9	366.6
105°	388.1	377.2	367.9	366.5	367.9	377.2	388.1	401.4	408.8	403.3	374.5
107.5°	434.4	430.6	427.5	424.9	427.5	430.6	434.4	434.1	423.9	398.6	351.8
110°	447.8	450.0	449.5	448.9	449.5	450.0	447.8	439.7	419.5	383.2	330.2



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	444.3	451.4	453.6	453.7	453.6	451.4	444.3	429.5	403.6	362.9	308.8
115°	425.8	438.5	444.3	445.7	444.3	438.5	425.8	404.2	372.8	330.4	280.3
117.5°	395.5	410.0	418.2	420.2	418.2	410.0	395.5	372.9	341.0	303.0	259.8
120°	374.2	390.4	397.3	399.0	397.3	390.4	374.2	351.5	322.4	287.8	248.9
122.5°	354.9	369.4	377.0	379.2	377.0	369.4	354.9	334.7	307.6	275.6	240.4
125°	329.6	342.3	349.5	351.5	349.5	342.3	329.6	311.2	288.1	260.5	229.0
127.5°	309.5	320.3	326.9	328.6	326.9	320.3	309.5	293.1	272.1	247.1	219.2
130°	297.0	307.4	313.5	315.8	313.5	307.4	297.0	281.8	262.2	238.9	212.9
132.5°	285.8	296.1	301.5	303.1	301.5	296.1	285.8	271.4	252.7	231.0	207.2
135°	269.1	277.8	282.9	284.9	282.9	277.8	269.1	254.9	238.6	219.8	199.3
137.5°	251.3	260.1	264.4	265.8	264.4	260.1	251.3	239.5	225.2	209.0	192.2
140°	240.0	248.1	252.7	252.4	252.7	248.1	240.0	229.0	216.6	202.8	188.2
142.5°	228.9	236.1	240.2	239.9	240.2	236.1	228.9	219.6	208.8	196.8	184.3
145°	213.8	219.8	222.2	222.7	222.2	219.8	213.8	206.6	198.2	189.0	179.5
147.5°	202.0	206.1	208.3	208.6	208.3	206.1	202.0	196.6	190.6	183.2	175.6
150°	195.3	198.5	200.2	200.2	200.2	198.5	195.3	191.0	185.6	179.5	172.8
152.5°	189.3	192.2	193.3	193.3	193.3	192.2	189.3	186.0	181.4	176.0	170.3
155°	181.5	183.8	184.4	184.7	184.4	183.8	181.5	178.9	175.5	171.1	166.6
157.5°	174.6	176.3	176.8	176.8	176.8	176.3	174.6	172.4	169.7	166.3	162.5
160°	170.2	172.0	172.0	171.7	172.0	172.0	170.2	168.3	166.2	163.4	160.2
162.5°	165.9	167.4	167.4	167.1	167.4	167.4	165.9	164.6	162.8	160.1	157.4
165°	160.2	161.3	161.0	161.0	161.0	161.3	160.2	159.1	157.6	155.6	153.8
167.5°	154.7	155.6	155.3	155.3	155.3	155.6	154.7	154.3	153.2	152.1	150.7
170°	151.6	152.1	151.8	151.8	151.8	152.1	151.6	151.2	150.7	149.5	148.6
172.5°	148.8	149.4	148.9	148.6	148.9	149.4	148.8	148.7	148.4	147.5	146.8
175°	145.2	145.5	145.2	145.0	145.2	145.5	145.2	145.2	145.2	144.6	144.3
177.5°	143.0	143.2	142.8	142.8	142.8	143.2	143.0	143.2	143.2	143.0	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	844.7	844.7	851.3	855.3	860.5	863.9	866.3	868.7	872.8	878.2	884.4
5°	796.5	798.2	807.6	816.9	825.9	833.6	840.0	847.7	857.0	868.6	881.4
7.5°	749.7	756.3	765.7	777.1	789.7	800.9	812.3	824.9	838.1	855.1	873.0
10°	719.7	726.9	738.4	752.9	766.1	779.3	793.4	807.1	823.8	843.8	866.9
12.5°	693.3	700.3	712.1	728.0	740.5	755.1	771.3	789.0	807.7	831.8	858.0
15°	656.9	665.0	679.5	687.2	706.4	723.9	738.8	764.4	788.3	813.1	843.4
17.5°	627.0	631.5	643.3	657.5	671.9	691.5	711.1	732.5	756.3	786.5	824.4
20°	606.5	610.3	623.1	638.1	653.5	671.4	688.9	710.2	737.1	769.2	810.1
22.5°	591.2	595.3	603.7	619.6	634.0	648.9	666.3	691.8	720.4	751.7	796.1
25°	568.9	571.5	577.1	589.9	602.7	619.3	634.7	658.6	688.0	724.7	769.2
27.5°	547.9	550.3	555.0	564.2	576.1	589.6	606.3	626.6	656.6	696.4	743.6
30°	535.2	535.7	540.0	548.5	558.7	569.8	585.1	608.2	636.4	676.9	726.4
32.5°	524.3	522.7	525.6	532.1	542.0	553.1	565.7	588.4	615.6	655.4	706.3
35°	505.8	504.9	503.7	509.2	517.7	526.3	537.4	554.5	585.1	622.3	675.6
37.5°	486.9	484.9	482.6	485.1	491.8	500.7	510.3	525.5	552.0	592.9	643.9
40°	473.0	471.2	469.9	469.0	475.1	483.6	490.8	505.3	530.1	568.9	619.3
42.5°	457.5	456.6	454.9	453.7	458.7	465.1	472.7	485.6	510.3	546.7	594.4
45°	432.8	431.9	431.1	430.2	433.3	439.2	445.2	454.5	475.9	511.4	554.5
47.5°	405.2	404.1	404.5	403.1	406.0	410.0	414.2	424.3	444.7	473.4	504.8
50°	385.4	385.0	385.0	385.0	385.9	390.5	394.4	402.1	420.9	449.5	472.1
52.5°	366.6	364.8	364.8	365.5	367.0	370.1	372.5	380.9	397.3	420.8	441.3
55°	337.2	333.8	332.9	333.8	335.1	337.6	340.1	347.0	361.1	378.6	390.5
57.5°	304.6	302.7	301.6	301.7	302.5	304.5	306.5	313.9	325.0	334.1	341.8
60°	281.7	282.6	278.8	279.6	279.6	281.3	284.3	288.9	298.3	304.8	312.4
62.5°	260.2	259.0	257.9	256.7	256.7	257.4	261.4	265.1	273.0	276.4	282.4
65°	226.7	226.7	224.0	224.9	225.3	222.4	224.5	228.8	233.9	235.2	240.8
67.5°	192.7	191.5	190.0	188.7	188.7	188.5	189.6	191.8	195.6	196.0	200.2
70°	169.4	168.6	168.2	166.9	165.2	167.3	166.0	168.2	170.3	170.7	173.3
72.5°	146.9	146.0	145.3	144.0	143.3	143.1	143.2	145.6	147.1	146.5	149.4
75°	114.8	114.0	113.1	111.0	111.0	109.7	110.1	111.9	113.6	112.3	114.8
77.5°	84.3	81.7	81.5	82.1	80.6	81.0	80.4	80.1	81.0	81.0	83.3
80°	64.9	61.9	62.8	62.3	61.9	61.5	60.6	61.1	61.5	61.9	63.2
82.5°	46.8	46.6	45.7	45.6	45.2	44.0	43.5	44.3	44.8	44.5	45.4
85°	23.9	22.6	23.5	23.1	23.5	23.1	21.8	21.8	22.6	22.2	23.1
87.5°	8.6	8.6	8.1	8.2	7.7	7.9	7.5	7.7	7.8	7.7	8.3
90°	6.9	7.2	6.4	5.5	4.6	3.8	3.2	2.6	1.7	1.1	0.6
92.5°	33.4	44.3	48.8	36.6	24.2	16.6	12.4	9.9	7.7	5.3	3.6
95°	138.6	170.9	152.1	104.8	62.0	37.4	26.3	18.8	13.9	10.7	9.8
97.5°	283.2	264.8	193.9	115.0	66.7	43.3	31.1	23.7	19.5	17.0	16.7
100°	329.6	272.9	184.4	108.6	66.0	45.8	34.6	27.6	23.6	21.6	21.4
102.5°	331.9	257.9	170.6	103.1	66.9	48.8	38.5	32.3	28.5	26.7	26.2
105°	314.3	231.6	153.6	99.1	69.5	53.9	44.9	39.5	36.0	34.3	33.4
107.5°	283.6	208.5	142.8	98.8	74.2	60.5	52.2	47.0	43.7	42.0	41.2
110°	264.2	195.3	138.6	100.0	78.1	65.1	57.1	52.2	49.0	47.5	46.6



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	247.4	186.5	136.2	102.3	82.0	70.0	62.1	57.2	54.1	52.6	51.8
115°	227.1	177.2	135.4	106.0	88.5	77.5	69.7	64.8	62.0	60.3	59.0
117.5°	214.7	171.6	135.9	111.0	95.3	84.5	77.3	71.8	69.1	67.7	66.4
120°	208.3	169.1	136.9	114.6	99.7	89.3	82.1	76.6	73.8	72.3	71.4
122.5°	203.0	167.5	138.4	118.1	104.3	94.2	86.5	81.3	78.1	76.7	75.8
125°	196.2	165.3	140.9	123.6	111.0	100.9	93.0	87.6	84.4	82.7	82.1
127.5°	190.2	164.4	143.7	128.1	116.7	107.0	99.1	93.1	89.9	87.7	86.9
130°	186.9	163.6	145.5	131.1	120.2	110.6	102.9	96.8	93.4	90.7	89.9
132.5°	184.0	163.4	146.9	133.9	123.1	113.9	106.3	100.3	96.1	93.3	92.2
135°	180.1	163.1	149.0	137.5	127.6	118.7	111.0	104.8	100.5	97.3	96.2
137.5°	176.7	162.4	150.3	140.1	130.8	122.1	115.0	108.9	104.4	101.3	100.0
140°	174.6	162.2	151.2	141.5	132.8	124.5	117.2	111.5	106.9	104.0	102.6
142.5°	172.8	161.8	152.0	142.8	134.4	126.3	119.6	113.8	109.7	106.6	105.3
145°	170.2	161.0	152.4	144.3	136.6	129.1	122.5	117.6	113.2	110.6	109.7
147.5°	167.9	160.0	152.4	145.3	138.3	131.4	125.8	121.1	117.3	114.8	114.3
150°	166.2	159.1	152.4	145.5	139.4	132.8	127.6	123.6	119.8	117.6	117.2
152.5°	164.4	157.9	151.7	145.9	140.1	134.4	129.5	125.9	122.6	120.3	120.3
155°	161.6	155.9	151.0	146.1	141.5	136.6	132.6	129.4	126.5	124.7	124.7
157.5°	158.5	154.1	150.0	146.3	142.2	138.3	135.2	132.5	130.0	128.6	128.3
160°	156.5	152.7	149.5	146.3	142.9	139.4	136.6	134.5	132.2	131.1	131.1
162.5°	154.3	151.3	148.6	146.1	143.2	140.1	137.7	135.9	134.1	133.1	133.1
165°	151.6	149.3	147.2	145.5	143.5	141.2	139.2	138.0	136.6	136.0	136.2
167.5°	148.9	147.2	145.9	145.0	143.4	141.8	140.5	139.7	138.6	138.3	138.6
170°	147.2	145.8	145.0	144.3	143.2	141.8	141.2	140.6	139.7	139.4	140.0
172.5°	145.6	144.6	144.2	144.1	143.2	141.9	141.6	141.3	140.6	140.6	141.0
175°	143.7	143.2	143.2	143.5	142.9	142.4	142.0	142.0	141.5	141.8	142.0
177.5°	142.6	142.4	142.6	143.0	142.6	142.4	142.4	142.4	142.1	142.4	142.6
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	886.4	888.1	894.0	898.1	902.8	905.6	908.2	910.4	913.1	913.7	923.7
5°	890.4	898.9	913.9	925.0	938.6	953.5	963.8	968.5	980.8	991.1	1011.5
7.5°	889.2	907.4	929.9	953.3	978.4	1001.7	1021.8	1045.7	1062.7	1088.3	1113.4
10°	888.2	912.6	941.6	971.4	1006.5	1038.9	1067.9	1100.3	1127.2	1162.7	1192.9
12.5°	885.2	914.6	954.9	990.3	1032.7	1077.5	1120.5	1162.1	1185.9	1245.0	1272.8
15°	877.6	912.6	963.0	1016.7	1075.1	1128.1	1182.8	1226.3	1296.7	1348.3	1381.2
17.5°	863.1	912.1	971.8	1036.7	1107.7	1177.5	1239.4	1305.5	1380.1	1442.7	1509.3
20°	856.2	910.0	976.6	1048.3	1122.1	1201.1	1271.5	1350.9	1432.4	1493.9	1579.2
22.5°	843.6	904.5	976.2	1056.1	1135.1	1216.8	1299.2	1379.2	1473.4	1558.1	1639.3
25°	822.9	891.2	965.5	1054.7	1147.3	1229.2	1327.9	1434.1	1532.3	1641.1	1722.2
27.5°	801.2	874.2	948.6	1031.5	1131.1	1228.4	1352.4	1472.5	1592.6	1686.5	1746.5
30°	784.5	855.3	932.2	1015.9	1114.4	1230.1	1368.8	1499.8	1616.8	1697.5	1731.2
32.5°	766.4	838.3	906.2	994.0	1099.1	1229.1	1379.1	1515.9	1618.2	1671.9	1665.3
35°	738.0	798.2	864.3	948.8	1072.6	1221.6	1385.0	1517.4	1580.1	1568.6	1481.5
37.5°	697.0	747.6	812.8	905.3	1041.9	1205.7	1373.1	1472.3	1468.3	1374.4	1248.3
40°	671.4	714.5	777.2	874.6	1018.0	1195.6	1354.3	1418.8	1364.2	1233.1	1082.0
42.5°	638.0	677.6	740.4	840.4	991.6	1174.7	1318.4	1337.2	1230.3	1079.5	940.9
45°	586.0	621.0	685.9	789.2	952.3	1129.4	1230.9	1185.3	1041.5	885.7	780.2
47.5°	530.3	566.6	629.1	735.2	895.2	1061.2	1109.5	1012.4	864.7	738.4	641.6
50°	495.1	530.1	591.2	698.3	856.6	1005.2	1025.2	899.8	764.0	653.1	573.6
52.5°	459.6	492.5	552.5	660.1	811.5	940.3	927.9	800.1	675.2	580.7	518.4
55°	406.8	437.9	495.1	595.8	733.7	835.7	790.9	668.9	565.6	492.1	444.7
57.5°	359.5	389.4	438.7	529.7	649.5	719.7	662.6	559.7	477.6	421.1	385.8
60°	327.3	353.8	400.8	485.3	589.5	642.8	586.4	495.5	426.4	381.2	349.6
62.5°	297.0	320.0	363.5	440.3	530.7	575.5	518.5	441.6	382.7	342.6	315.8
65°	250.9	271.9	310.3	370.1	444.3	474.2	425.1	362.8	317.2	287.2	269.3
67.5°	209.0	226.7	259.9	307.0	361.6	383.4	346.0	297.7	263.3	239.4	225.1
70°	181.0	196.3	222.4	262.9	312.4	329.1	294.1	254.4	229.2	210.0	196.7
72.5°	157.4	168.7	192.3	223.6	265.0	278.2	253.8	218.9	195.4	181.0	170.5
75°	119.9	129.3	144.7	169.9	198.4	206.2	187.8	166.0	150.3	140.0	131.9
77.5°	86.5	93.4	104.5	120.0	139.8	146.8	135.1	120.6	109.1	102.2	97.7
80°	65.3	70.8	80.2	93.0	105.0	108.8	102.0	90.9	82.8	79.0	75.1
82.5°	48.3	51.4	57.0	65.7	73.9	78.4	72.6	66.0	61.6	58.1	56.7
85°	24.3	26.0	28.6	32.0	37.1	38.8	36.7	35.0	32.4	30.3	30.3
87.5°	9.1	9.2	10.4	11.3	12.7	13.9	13.7	13.2	13.0	12.6	12.4
90°	1.1	1.7	2.6	3.2	3.8	4.6	5.5	6.4	7.2	6.9	7.2
92.5°	5.3	7.7	9.9	12.4	16.6	24.2	36.6	48.8	44.3	33.4	24.3
95°	10.7	13.9	18.8	26.3	37.4	62.0	104.8	152.1	170.9	138.6	103.7
97.5°	17.0	19.5	23.7	31.1	43.3	66.7	115.0	193.9	264.8	283.2	258.5
100°	21.6	23.6	27.6	34.6	45.8	66.0	108.6	184.4	272.9	329.6	339.7
102.5°	26.7	28.5	32.3	38.5	48.8	66.9	103.1	170.6	257.9	331.9	366.6
105°	34.3	36.0	39.5	44.9	53.9	69.5	99.1	153.6	231.6	314.3	374.5
107.5°	42.0	43.7	47.0	52.2	60.5	74.2	98.8	142.8	208.5	283.6	351.8
110°	47.5	49.0	52.2	57.1	65.1	78.1	100.0	138.6	195.3	264.2	330.2





TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	52.6	54.1	57.2	62.1	70.0	82.0	102.3	136.2	186.5	247.4	308.8
115°	60.3	62.0	64.8	69.7	77.5	88.5	106.0	135.4	177.2	227.1	280.3
117.5°	67.7	69.1	71.8	77.3	84.5	95.3	111.0	135.9	171.6	214.7	259.8
120°	72.3	73.8	76.6	82.1	89.3	99.7	114.6	136.9	169.1	208.3	248.9
122.5°	76.7	78.1	81.3	86.5	94.2	104.3	118.1	138.4	167.5	203.0	240.4
125°	82.7	84.4	87.6	93.0	100.9	111.0	123.6	140.9	165.3	196.2	229.0
127.5°	87.7	89.9	93.1	99.1	107.0	116.7	128.1	143.7	164.4	190.2	219.2
130°	90.7	93.4	96.8	102.9	110.6	120.2	131.1	145.5	163.6	186.9	212.9
132.5°	93.3	96.1	100.3	106.3	113.9	123.1	133.9	146.9	163.4	184.0	207.2
135°	97.3	100.5	104.8	111.0	118.7	127.6	137.5	149.0	163.1	180.1	199.3
137.5°	101.3	104.4	108.9	115.0	122.1	130.8	140.1	150.3	162.4	176.7	192.2
140°	104.0	106.9	111.5	117.2	124.5	132.8	141.5	151.2	162.2	174.6	188.2
142.5°	106.6	109.7	113.8	119.6	126.3	134.4	142.8	152.0	161.8	172.8	184.3
145°	110.6	113.2	117.6	122.5	129.1	136.6	144.3	152.4	161.0	170.2	179.5
147.5°	114.8	117.3	121.1	125.8	131.4	138.3	145.3	152.4	160.0	167.9	175.6
150°	117.6	119.8	123.6	127.6	132.8	139.4	145.5	152.4	159.1	166.2	172.8
152.5°	120.3	122.6	125.9	129.5	134.4	140.1	145.9	151.7	157.9	164.4	170.3
155°	124.7	126.5	129.4	132.6	136.6	141.5	146.1	151.0	155.9	161.6	166.6
157.5°	128.6	130.0	132.5	135.2	138.3	142.2	146.3	150.0	154.1	158.5	162.5
160°	131.1	132.2	134.5	136.6	139.4	142.9	146.3	149.5	152.7	156.5	160.2
162.5°	133.1	134.1	135.9	137.7	140.1	143.2	146.1	148.6	151.3	154.3	157.4
165°	136.0	136.6	138.0	139.2	141.2	143.5	145.5	147.2	149.3	151.6	153.8
167.5°	138.3	138.6	139.7	140.5	141.8	143.4	145.0	145.9	147.2	148.9	150.7
170°	139.4	139.7	140.6	141.2	141.8	143.2	144.3	145.0	145.8	147.2	148.6
172.5°	140.6	140.6	141.3	141.6	141.9	143.2	144.1	144.2	144.6	145.6	146.8
175°	141.8	141.5	142.0	142.0	142.4	142.9	143.5	143.2	143.2	143.7	144.3
177.5°	142.4	142.1	142.4	142.4	142.4	142.6	143.0	142.6	142.4	142.6	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	927.1	927.4	931.2	933.9	932.5	934.3	934.9
5°	1012.8	1028.3	1036.3	1042.3	1042.8	1043.2	1046.6
7.5°	1134.5	1151.0	1163.0	1181.3	1186.7	1192.9	1191.2
10°	1223.3	1247.6	1268.5	1279.6	1291.6	1309.0	1295.0
12.5°	1306.3	1349.4	1381.2	1398.5	1409.7	1413.2	1406.3
15°	1443.1	1499.4	1529.7	1528.8	1567.3	1584.0	1557.9
17.5°	1568.6	1620.6	1662.2	1683.6	1715.6	1722.6	1719.4
20°	1645.4	1702.2	1734.6	1771.3	1788.0	1802.9	1805.5
22.5°	1711.6	1762.6	1797.4	1828.0	1841.9	1849.0	1853.3
25°	1779.9	1820.0	1840.9	1851.5	1855.4	1854.6	1849.0
27.5°	1775.2	1778.2	1755.2	1732.6	1712.4	1689.5	1681.7
30°	1729.1	1693.2	1629.2	1592.9	1539.5	1497.3	1514.3
32.5°	1607.9	1536.5	1464.6	1385.3	1319.6	1301.0	1282.1
35°	1372.2	1246.8	1173.4	1087.9	1053.9	1019.7	996.2
37.5°	1110.2	1013.1	926.0	870.2	836.0	814.4	802.7
40°	959.9	872.5	800.7	755.5	729.4	705.2	701.7
42.5°	840.1	758.7	704.7	668.7	643.8	633.4	625.9
45°	688.0	631.3	595.0	569.4	552.8	546.3	537.8
47.5°	582.4	542.3	515.0	497.6	485.0	480.3	479.6
50°	523.3	490.0	469.9	456.2	446.5	444.7	437.9
52.5°	478.9	450.0	434.4	422.5	415.4	410.6	408.5
55°	415.7	396.5	382.5	375.6	370.1	365.3	365.3
57.5°	363.7	347.7	338.3	332.6	330.8	327.5	325.4
60°	331.7	318.0	310.7	305.6	302.2	302.6	298.8
62.5°	300.2	291.4	284.5	279.3	275.2	275.3	275.6
65°	255.7	248.8	243.7	242.0	239.5	236.4	237.3
67.5°	216.6	210.3	206.3	203.3	202.5	200.9	203.3
70°	188.7	183.9	181.0	178.4	177.6	178.0	180.1
72.5°	163.1	159.7	157.8	156.5	154.7	154.7	156.2
75°	128.1	125.5	123.8	122.5	122.1	122.1	122.1
77.5°	94.1	93.5	92.7	90.8	90.9	91.4	91.5
80°	74.3	73.0	72.6	71.7	70.4	69.5	71.7
82.5°	55.5	54.2	53.8	53.6	51.6	51.4	53.2
85°	29.8	28.6	29.0	28.6	28.6	28.2	28.2
87.5°	12.1	11.8	11.6	11.8	11.6	11.3	11.9
90°	7.5	7.7	8.3	8.1	8.3	8.6	8.3
92.5°	19.2	17.0	15.5	15.0	14.1	14.4	13.9
95°	70.3	55.0	44.7	39.2	36.6	34.6	33.4
97.5°	207.1	169.9	135.5	114.2	101.3	93.4	91.0
100°	316.3	282.7	241.7	212.6	191.6	180.3	180.7
102.5°	365.9	346.3	320.3	297.7	281.0	271.7	265.0
105°	403.3	408.8	401.4	388.1	377.2	367.9	366.5
107.5°	398.6	423.9	434.1	434.4	430.6	427.5	424.9
110°	383.2	419.5	439.7	447.8	450.0	449.5	448.9



TEST NUMBER: P331957-930

CATALOG NUMBER: S123DIP-S775D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	362.9	403.6	429.5	444.3	451.4	453.6	453.7
115°	330.4	372.8	404.2	425.8	438.5	444.3	445.7
117.5°	303.0	341.0	372.9	395.5	410.0	418.2	420.2
120°	287.8	322.4	351.5	374.2	390.4	397.3	399.0
122.5°	275.6	307.6	334.7	354.9	369.4	377.0	379.2
125°	260.5	288.1	311.2	329.6	342.3	349.5	351.5
127.5°	247.1	272.1	293.1	309.5	320.3	326.9	328.6
130°	238.9	262.2	281.8	297.0	307.4	313.5	315.8
132.5°	231.0	252.7	271.4	285.8	296.1	301.5	303.1
135°	219.8	238.6	254.9	269.1	277.8	282.9	284.9
137.5°	209.0	225.2	239.5	251.3	260.1	264.4	265.8
140°	202.8	216.6	229.0	240.0	248.1	252.7	252.4
142.5°	196.8	208.8	219.6	228.9	236.1	240.2	239.9
145°	189.0	198.2	206.6	213.8	219.8	222.2	222.7
147.5°	183.2	190.6	196.6	202.0	206.1	208.3	208.6
150°	179.5	185.6	191.0	195.3	198.5	200.2	200.2
152.5°	176.0	181.4	186.0	189.3	192.2	193.3	193.3
155°	171.1	175.5	178.9	181.5	183.8	184.4	184.7
157.5°	166.3	169.7	172.4	174.6	176.3	176.8	176.8
160°	163.4	166.2	168.3	170.2	172.0	172.0	171.7
162.5°	160.1	162.8	164.6	165.9	167.4	167.4	167.1
165°	155.6	157.6	159.1	160.2	161.3	161.0	161.0
167.5°	152.1	153.2	154.3	154.7	155.6	155.3	155.3
170°	149.5	150.7	151.2	151.6	152.1	151.8	151.8
172.5°	147.5	148.4	148.7	148.8	149.4	148.9	148.6
175°	144.6	145.2	145.2	145.2	145.5	145.2	145.0
177.5°	143.0	143.2	143.2	143.0	143.2	142.8	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4

(END OF REPORT)