

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331966-930

Luminaire Tested: **S123DIP-S775D585U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331966-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D585U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 585 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4389.0 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	96	92	89	94	90	87	84	79	76	74	68	67	65	59	58	56	52
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44
3	84	74	67	61	78	70	64	58	62	56	52	54	50	47	46	44	41	37
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	44	39	34	39	34	31	34	30	28	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	25	22
8	56	44	36	31	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9482	9482	9482	9482
5°	11309	9524	8440	9524
10°	14154	9475	7623	9475
15°	17361	9399	7096	9399
20°	20681	9279	6757	9279
25°	21960	9136	6682	9136
30°	18821	9028	6717	9028
35°	13090	8878	6787	8878
40°	9860	8702	6764	8702
45°	8187	8441	6680	8441
50°	7333	7906	6620	7906
55°	6855	7328	6536	7328
60°	6433	6725	6469	6725
65°	6044	6133	6260	6133
70°	5668	5454	5964	5454
75°	5078	4774	5465	4774
80°	4444	3918	4711	3918
85°	3483	2853	3162	2853



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	2.0
10°-20°	278.3	6.3
20°-30°	467.0	10.6
30°-40°	528.8	12.0
40°-50°	474.2	10.8
50°-60°	382.7	8.7
60°-70°	266.7	6.1
70°-80°	140.2	3.2
80°-90°	36.1	0.8
90°-100°	127.8	2.9
100°-110°	362.0	8.2
110°-120°	356.1	8.1
120°-130°	284.0	6.5
130°-140°	224.0	5.1
140°-150°	167.1	3.8
150°-160°	116.5	2.7
160°-170°	68.4	1.6
170°-180°	22.3	0.5
0°-30°	832.1	19.0
0°-40°	1360.9	31.0
0°-60°	2217.8	50.5
0°-90°	2660.7	60.6
90°-120°	846.0	19.3
90°-150°	1521.1	34.7
90°-180°	1728.0	39.4
0°-180°	4389.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	881	881	881	881	881	
5°	1047	881	781	881	1047	108
15°	1558	843	637	843	1558	450
25°	1849	769	563	769	1849	811
35°	996	676	516	676	996	647
45°	538	554	439	554	538	426
55°	365	390	348	390	365	328
65°	237	241	246	241	237	236
75°	122	115	131	115	122	131
85°	28	23	26	23	28	34
90°	14	1	14	1	14	9
95°	54	16	54	16	54	97
105°	592	54	592	54	592	584
115°	719	95	719	95	719	699
125°	567	133	567	133	567	514
135°	460	155	460	155	460	357
145°	360	177	360	177	360	229
155°	298	201	298	201	298	139
165°	260	220	260	220	260	74
175°	234	229	234	229	234	23
180°	230	230	230	230	230	



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	934.9	934.3	932.5	933.9	931.2	927.4	927.1	923.7	913.7	913.1	910.4
5°	1046.6	1043.2	1042.8	1042.3	1036.3	1028.3	1012.8	1011.5	991.1	980.8	968.5
7.5°	1191.2	1192.9	1186.7	1181.3	1163.0	1151.0	1134.5	1113.4	1088.3	1062.7	1045.7
10°	1295.0	1309.0	1291.6	1279.6	1268.5	1247.6	1223.3	1192.9	1162.7	1127.2	1100.3
12.5°	1406.3	1413.2	1409.7	1398.5	1381.2	1349.4	1306.3	1272.8	1245.0	1185.9	1162.1
15°	1557.9	1584.0	1567.3	1528.8	1529.7	1499.4	1443.1	1381.2	1348.3	1296.7	1226.3
17.5°	1719.4	1722.6	1715.6	1683.6	1662.2	1620.6	1568.6	1509.3	1442.7	1380.1	1305.5
20°	1805.5	1802.9	1788.0	1771.3	1734.6	1702.2	1645.4	1579.2	1493.9	1432.4	1350.9
22.5°	1853.3	1849.0	1841.9	1828.0	1797.4	1762.6	1711.6	1639.3	1558.1	1473.4	1379.2
25°	1849.0	1854.6	1855.4	1851.5	1840.9	1820.0	1779.9	1722.2	1641.1	1532.3	1434.1
27.5°	1681.7	1689.5	1712.4	1732.6	1755.2	1778.2	1775.2	1746.5	1686.5	1592.6	1472.5
30°	1514.3	1497.3	1539.5	1592.9	1629.2	1693.2	1729.1	1731.2	1697.5	1616.8	1499.8
32.5°	1282.1	1301.0	1319.6	1385.3	1464.6	1536.5	1607.9	1665.3	1671.9	1618.2	1515.9
35°	996.2	1019.7	1053.9	1087.9	1173.4	1246.8	1372.2	1481.5	1568.6	1580.1	1517.4
37.5°	802.7	814.4	836.0	870.2	926.0	1013.1	1110.2	1248.3	1374.4	1468.3	1472.3
40°	701.7	705.2	729.4	755.5	800.7	872.5	959.9	1082.0	1233.1	1364.2	1418.8
42.5°	625.9	633.4	643.8	668.7	704.7	758.7	840.1	940.9	1079.5	1230.3	1337.2
45°	537.8	546.3	552.8	569.4	595.0	631.3	688.0	780.2	885.7	1041.5	1185.3
47.5°	479.6	480.3	485.0	497.6	515.0	542.3	582.4	641.6	738.4	864.7	1012.4
50°	437.9	444.7	446.5	456.2	469.9	490.0	523.3	573.6	653.1	764.0	899.8
52.5°	408.5	410.6	415.4	422.5	434.4	450.0	478.9	518.4	580.7	675.2	800.1
55°	365.3	365.3	370.1	375.6	382.5	396.5	415.7	444.7	492.1	565.6	668.9
57.5°	325.4	327.5	330.8	332.6	338.3	347.7	363.7	385.8	421.1	477.6	559.7
60°	298.8	302.6	302.2	305.6	310.7	318.0	331.7	349.6	381.2	426.4	495.5
62.5°	275.6	275.3	275.2	279.3	284.5	291.4	300.2	315.8	342.6	382.7	441.6
65°	237.3	236.4	239.5	242.0	243.7	248.8	255.7	269.3	287.2	317.2	362.8
67.5°	203.3	200.9	202.5	203.3	206.3	210.3	216.6	225.1	239.4	263.3	297.7
70°	180.1	178.0	177.6	178.4	181.0	183.9	188.7	196.7	210.0	229.2	254.4
72.5°	156.2	154.7	154.7	156.5	157.8	159.7	163.1	170.5	181.0	195.4	218.9
75°	122.1	122.1	122.1	122.5	123.8	125.5	128.1	131.9	140.0	150.3	166.0
77.5°	91.5	91.4	90.9	90.8	92.7	93.5	94.1	97.7	102.2	109.1	120.6
80°	71.7	69.5	70.4	71.7	72.6	73.0	74.3	75.1	79.0	82.8	90.9
82.5°	53.2	51.4	51.6	53.6	53.8	54.2	55.5	56.7	58.1	61.6	66.0
85°	28.2	28.2	28.6	28.6	29.0	28.6	29.8	30.3	30.3	32.4	35.0
87.5°	13.0	12.3	12.6	12.9	12.6	12.7	13.0	13.3	13.5	13.9	14.0
90°	13.5	13.9	13.5	13.0	13.5	12.6	12.1	11.7	11.2	11.7	10.2
92.5°	22.4	23.2	22.7	24.2	25.0	27.5	31.1	39.1	54.0	71.5	78.7
95°	54.0	55.8	59.0	63.3	72.1	88.8	113.5	167.4	223.6	275.7	245.6
97.5°	146.8	150.8	163.4	184.3	218.7	274.3	334.3	417.4	457.2	427.4	312.8
100°	291.6	291.1	309.2	343.2	390.1	456.2	510.6	548.3	532.0	440.3	297.6
102.5°	427.7	438.4	453.6	480.5	517.0	558.9	590.6	591.8	535.7	416.2	275.3
105°	591.5	593.9	608.7	626.4	647.8	659.9	651.0	604.5	507.4	373.9	247.9
107.5°	685.8	690.1	695.1	701.1	700.7	684.1	643.4	567.9	457.7	336.5	230.4
110°	724.5	725.5	726.4	722.7	709.6	677.1	618.5	532.9	426.4	315.3	223.6



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	732.3	732.1	728.6	717.1	693.2	651.4	585.7	498.3	399.3	301.2	220.0
115°	719.4	717.1	707.8	687.3	652.4	601.8	533.4	452.5	366.5	286.0	218.6
117.5°	678.2	675.1	661.7	638.3	601.9	550.5	489.1	419.2	346.7	277.0	219.4
120°	644.1	641.2	630.1	604.1	567.4	520.3	464.6	401.8	336.2	273.0	220.9
122.5°	612.0	608.5	596.2	572.8	540.1	496.5	444.8	388.0	327.7	270.4	223.5
125°	567.4	564.1	552.4	532.0	502.2	465.0	420.4	369.7	316.7	266.9	227.4
127.5°	530.5	527.5	517.0	499.5	473.0	439.2	398.9	353.7	307.0	265.2	231.9
130°	509.6	506.0	496.2	479.5	454.8	423.1	385.5	343.6	301.8	264.2	234.8
132.5°	489.2	486.6	477.9	461.2	438.1	407.9	372.8	334.4	296.9	263.7	237.1
135°	459.9	456.6	448.3	434.3	411.6	385.1	354.8	321.8	290.7	263.2	240.4
137.5°	428.9	426.8	419.7	405.6	386.5	363.5	337.5	310.4	285.2	262.2	242.6
140°	407.3	407.8	400.4	387.3	369.7	349.7	327.3	303.7	281.8	261.8	244.1
142.5°	387.3	387.8	381.1	369.5	354.4	337.0	317.7	297.3	278.8	261.1	245.2
145°	359.5	358.6	354.8	345.0	333.5	319.9	305.1	289.7	274.8	259.9	246.0
147.5°	336.6	336.2	332.6	326.0	317.2	307.7	295.6	283.5	270.9	258.2	246.0
150°	323.2	323.2	320.4	315.3	308.3	299.5	289.7	279.0	268.3	256.7	246.0
152.5°	312.0	312.0	310.4	305.6	300.1	292.8	284.1	274.9	265.4	254.9	244.9
155°	298.1	297.6	296.7	292.9	288.8	283.2	276.2	268.8	260.9	251.6	243.7
157.5°	285.4	285.4	284.7	281.9	278.3	273.9	268.5	262.3	255.8	248.7	242.1
160°	277.1	277.6	277.6	274.8	271.6	268.3	263.7	258.5	252.5	246.5	241.3
162.5°	269.7	270.2	270.2	267.7	265.6	262.8	258.4	254.1	249.2	244.3	239.9
165°	259.9	259.9	260.4	258.5	256.7	254.4	251.1	248.3	244.6	240.9	237.7
167.5°	250.6	250.6	251.1	249.8	249.0	247.3	245.4	243.3	240.3	237.5	235.4
170°	245.1	245.1	245.6	244.6	244.1	243.2	241.3	239.9	237.7	235.3	233.9
172.5°	239.9	240.3	241.1	240.1	240.0	239.5	238.0	237.0	235.1	233.4	232.8
175°	233.9	234.4	234.8	234.4	234.4	234.4	233.4	233.0	232.0	231.1	231.1
177.5°	230.5	230.5	231.2	230.8	231.2	231.2	230.8	230.5	230.1	229.8	230.1
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	908.2	905.6	902.8	898.1	894.0	888.1	886.4	884.4	878.2	872.8	868.7
5°	963.8	953.5	938.6	925.0	913.9	898.9	890.4	881.4	868.6	857.0	847.7
7.5°	1021.8	1001.7	978.4	953.3	929.9	907.4	889.2	873.0	855.1	838.1	824.9
10°	1067.9	1038.9	1006.5	971.4	941.6	912.6	888.2	866.9	843.8	823.8	807.1
12.5°	1120.5	1077.5	1032.7	990.3	954.9	914.6	885.2	858.0	831.8	807.7	789.0
15°	1182.8	1128.1	1075.1	1016.7	963.0	912.6	877.6	843.4	813.1	788.3	764.4
17.5°	1239.4	1177.5	1107.7	1036.7	971.8	912.1	863.1	824.4	786.5	756.3	732.5
20°	1271.5	1201.1	1122.1	1048.3	976.6	910.0	856.2	810.1	769.2	737.1	710.2
22.5°	1299.2	1216.8	1135.1	1056.1	976.2	904.5	843.6	796.1	751.7	720.4	691.8
25°	1327.9	1229.2	1147.3	1054.7	965.5	891.2	822.9	769.2	724.7	688.0	658.6
27.5°	1352.4	1228.4	1131.1	1031.5	948.6	874.2	801.2	743.6	696.4	656.6	626.6
30°	1368.8	1230.1	1114.4	1015.9	932.2	855.3	784.5	726.4	676.9	636.4	608.2
32.5°	1379.1	1229.1	1099.1	994.0	906.2	838.3	766.4	706.3	655.4	615.6	588.4
35°	1385.0	1221.6	1072.6	948.8	864.3	798.2	738.0	675.6	622.3	585.1	554.5
37.5°	1373.1	1205.7	1041.9	905.3	812.8	747.6	697.0	643.9	592.9	552.0	525.5
40°	1354.3	1195.6	1018.0	874.6	777.2	714.5	671.4	619.3	568.9	530.1	505.3
42.5°	1318.4	1174.7	991.6	840.4	740.4	677.6	638.0	594.4	546.7	510.3	485.6
45°	1230.9	1129.4	952.3	789.2	685.9	621.0	586.0	554.5	511.4	475.9	454.5
47.5°	1109.5	1061.2	895.2	735.2	629.1	566.6	530.3	504.8	473.4	444.7	424.3
50°	1025.2	1005.2	856.6	698.3	591.2	530.1	495.1	472.1	449.5	420.9	402.1
52.5°	927.9	940.3	811.5	660.1	552.5	492.5	459.6	441.3	420.8	397.3	380.9
55°	790.9	835.7	733.7	595.8	495.1	437.9	406.8	390.5	378.6	361.1	347.0
57.5°	662.6	719.7	649.5	529.7	438.7	389.4	359.5	341.8	334.1	325.0	313.9
60°	586.4	642.8	589.5	485.3	400.8	353.8	327.3	312.4	304.8	298.3	288.9
62.5°	518.5	575.5	530.7	440.3	363.5	320.0	297.0	282.4	276.4	273.0	265.1
65°	425.1	474.2	444.3	370.1	310.3	271.9	250.9	240.8	235.2	233.9	228.8
67.5°	346.0	383.4	361.6	307.0	259.9	226.7	209.0	200.2	196.0	195.6	191.8
70°	294.1	329.1	312.4	262.9	222.4	196.3	181.0	173.3	170.7	170.3	168.2
72.5°	253.8	278.2	265.0	223.6	192.3	168.7	157.4	149.4	146.5	147.1	145.6
75°	187.8	206.2	198.4	169.9	144.7	129.3	119.9	114.8	112.3	113.6	111.9
77.5°	135.1	146.8	139.8	120.0	104.5	93.4	86.5	83.3	81.0	81.0	80.1
80°	102.0	108.8	105.0	93.0	80.2	70.8	65.3	63.2	61.9	61.5	61.1
82.5°	72.6	78.4	73.9	65.7	57.0	51.4	48.3	45.4	44.5	44.8	44.3
85°	36.7	38.8	37.1	32.0	28.6	26.0	24.3	23.1	22.2	22.6	21.8
87.5°	14.4	14.4	13.1	11.6	10.8	9.5	9.2	8.4	7.9	8.1	8.0
90°	8.8	7.4	6.0	5.1	4.2	2.8	1.9	0.9	1.9	2.8	4.2
92.5°	59.0	39.1	26.9	20.0	16.1	12.5	8.6	5.8	8.6	12.5	16.1
95°	169.3	100.0	60.4	42.3	30.2	22.3	17.2	15.8	17.2	22.3	30.2
97.5°	185.7	107.6	69.9	50.2	38.3	31.5	27.5	27.0	27.5	31.5	38.3
100°	175.3	106.5	73.9	55.8	44.7	38.2	34.9	34.4	34.9	38.2	44.7
102.5°	166.4	107.9	78.8	62.1	52.1	46.0	43.0	42.2	43.0	46.0	52.1
105°	160.0	112.1	87.0	72.6	63.7	58.1	55.4	54.0	55.4	58.1	63.7
107.5°	159.5	119.7	97.7	84.3	76.0	70.5	67.8	66.4	67.8	70.5	76.0
110°	161.3	126.0	105.1	92.0	84.1	79.1	76.7	75.3	76.7	79.1	84.1



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	165.1	132.3	112.9	100.3	92.4	87.2	85.0	83.5	85.0	87.2	92.4
115°	171.1	142.8	125.1	112.5	104.6	100.0	97.2	95.3	97.2	100.0	104.6
117.5°	179.1	153.8	136.3	124.7	115.9	111.6	109.3	107.1	109.3	111.6	115.9
120°	185.1	160.9	144.1	132.6	123.7	119.0	116.8	115.4	116.8	119.0	123.7
122.5°	190.7	168.4	152.0	139.6	131.1	126.1	123.8	122.4	123.8	126.1	131.1
125°	199.5	179.0	162.7	150.2	141.4	136.2	133.5	132.6	133.5	136.2	141.4
127.5°	206.8	188.3	172.6	160.0	150.3	145.1	141.6	140.2	141.6	145.1	150.3
130°	211.6	193.9	178.6	166.0	156.2	150.7	146.5	145.1	146.5	150.7	156.2
132.5°	216.1	198.8	183.8	171.6	161.8	155.2	150.6	148.8	150.6	155.2	161.8
135°	221.8	206.0	191.6	179.0	169.3	162.3	157.2	155.3	157.2	162.3	169.3
137.5°	226.1	211.0	197.1	185.6	175.9	168.4	163.4	161.4	163.4	168.4	175.9
140°	228.4	214.3	200.9	189.2	179.9	172.5	167.9	165.6	167.9	172.5	179.9
142.5°	230.6	217.0	203.9	193.0	183.7	177.0	171.9	170.0	171.9	177.0	183.7
145°	233.0	220.5	208.3	197.6	189.7	182.8	178.6	177.2	178.6	182.8	189.7
147.5°	234.5	223.2	212.1	203.0	195.4	189.4	185.2	184.4	185.2	189.4	195.4
150°	234.8	225.1	214.3	206.0	199.5	193.5	189.7	189.2	189.7	193.5	199.5
152.5°	235.6	226.2	217.0	209.0	203.3	198.0	194.2	194.1	194.2	198.0	203.3
155°	235.8	228.4	220.5	213.9	208.8	204.2	201.4	201.4	201.4	204.2	208.8
157.5°	236.3	229.5	223.2	218.2	213.9	209.7	207.5	207.1	207.5	209.7	213.9
160°	236.3	230.6	225.1	220.5	217.2	213.4	211.6	211.6	211.6	213.4	217.2
162.5°	235.9	231.1	226.2	222.3	219.4	216.5	214.9	214.9	214.9	216.5	219.4
165°	234.8	231.5	227.9	224.6	222.7	220.5	219.5	220.0	219.5	220.5	222.7
167.5°	234.1	231.5	228.8	226.7	225.4	223.6	223.2	223.8	223.2	223.6	225.4
170°	233.0	231.1	228.8	227.9	226.9	225.5	225.1	226.0	225.1	225.5	226.9
172.5°	232.6	231.1	229.2	228.6	228.0	227.1	226.9	227.5	226.9	227.1	228.0
175°	231.5	230.6	229.8	229.3	229.3	228.4	228.8	229.3	228.8	228.4	229.3
177.5°	230.8	230.1	229.8	229.8	229.8	229.3	229.8	230.1	229.8	229.3	229.8
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	866.3	863.9	860.5	855.3	851.3	844.7	844.7	845.8	845.8	845.5	844.7
5°	840.0	833.6	825.9	816.9	807.6	798.2	796.5	793.0	790.5	788.8	786.6
7.5°	812.3	800.9	789.7	777.1	765.7	756.3	749.7	744.2	740.7	736.9	734.3
10°	793.4	779.3	766.1	752.9	738.4	726.9	719.7	714.5	710.7	707.3	705.6
12.5°	771.3	755.1	740.5	728.0	712.1	700.3	693.3	691.0	686.4	679.2	675.5
15°	738.8	723.9	706.4	687.2	679.5	665.0	656.9	653.1	650.4	644.9	643.2
17.5°	711.1	691.5	671.9	657.5	643.3	631.5	627.0	622.2	618.8	614.2	612.9
20°	688.9	671.4	653.5	638.1	623.1	610.3	606.5	603.1	599.7	597.5	595.8
22.5°	666.3	648.9	634.0	619.6	603.7	595.3	591.2	587.4	585.0	583.6	581.9
25°	634.7	619.3	602.7	589.9	577.1	571.5	568.9	566.8	565.1	563.0	562.6
27.5°	606.3	589.6	576.1	564.2	555.0	550.3	547.9	546.8	547.2	548.0	548.5
30°	585.1	569.8	558.7	548.5	540.0	535.7	535.2	535.2	537.0	537.4	538.3
32.5°	565.7	553.1	542.0	532.1	525.6	522.7	524.3	524.3	525.7	526.8	528.3
35°	537.4	526.3	517.7	509.2	503.7	504.9	505.8	506.6	508.7	511.4	513.1
37.5°	510.3	500.7	491.8	485.1	482.6	484.9	486.9	488.7	491.2	493.2	494.9
40°	490.8	483.6	475.1	469.0	469.9	471.2	473.0	475.1	477.2	478.5	480.2
42.5°	472.7	465.1	458.7	453.7	454.9	456.6	457.5	458.7	461.1	463.4	464.5
45°	445.2	439.2	433.3	430.2	431.1	431.9	432.8	434.1	436.2	437.9	438.4
47.5°	414.2	410.0	406.0	403.1	404.5	404.1	405.2	408.0	408.6	409.7	412.1
50°	394.4	390.5	385.9	385.0	385.0	385.0	385.4	388.8	388.8	390.5	392.2
52.5°	372.5	370.1	367.0	365.5	364.8	364.8	366.6	368.4	369.0	371.5	373.2
55°	340.1	337.6	335.1	333.8	332.9	333.8	337.2	338.0	340.1	341.4	342.8
57.5°	306.5	304.5	302.5	301.7	301.6	302.7	304.6	307.1	307.7	311.6	313.6
60°	284.3	281.3	279.6	279.6	278.8	282.6	281.7	286.0	286.8	289.3	292.4
62.5°	261.4	257.4	256.7	256.7	257.9	259.0	260.2	262.0	264.3	267.5	269.9
65°	224.5	222.4	225.3	224.9	224.0	226.7	226.7	228.8	231.3	234.3	239.0
67.5°	189.6	188.5	188.7	188.7	190.0	191.5	192.7	194.5	197.6	200.8	203.8
70°	166.0	167.3	165.2	166.9	168.2	168.6	169.4	172.0	175.5	177.6	181.0
72.5°	143.2	143.1	143.3	144.0	145.3	146.0	146.9	149.9	153.6	155.4	158.1
75°	110.1	109.7	111.0	111.0	113.1	114.0	114.8	116.1	119.5	122.1	124.2
77.5°	80.4	81.0	80.6	82.1	81.5	81.7	84.3	85.6	85.9	91.0	92.1
80°	60.6	61.5	61.9	62.3	62.8	61.9	64.9	66.1	66.1	69.1	71.3
82.5°	43.5	44.0	45.2	45.6	45.7	46.6	46.8	47.7	48.8	50.1	52.8
85°	21.8	23.1	23.5	23.1	23.5	22.6	23.9	24.3	24.8	24.8	24.8
87.5°	7.8	8.4	8.3	9.0	8.9	9.5	9.4	8.8	8.9	10.0	8.8
90°	5.1	6.0	7.4	8.8	10.2	11.7	11.2	11.7	12.1	12.6	13.5
92.5°	20.0	26.9	39.1	59.0	78.7	71.5	54.0	39.1	31.1	27.5	25.0
95°	42.3	60.4	100.0	169.3	245.6	275.7	223.6	167.4	113.5	88.8	72.1
97.5°	50.2	69.9	107.6	185.7	312.8	427.4	457.2	417.4	334.3	274.3	218.7
100°	55.8	73.9	106.5	175.3	297.6	440.3	532.0	548.3	510.6	456.2	390.1
102.5°	62.1	78.8	107.9	166.4	275.3	416.2	535.7	591.8	590.6	558.9	517.0
105°	72.6	87.0	112.1	160.0	247.9	373.9	507.4	604.5	651.0	659.9	647.8
107.5°	84.3	97.7	119.7	159.5	230.4	336.5	457.7	567.9	643.4	684.1	700.7
110°	92.0	105.1	126.0	161.3	223.6	315.3	426.4	532.9	618.5	677.1	709.6



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	100.3	112.9	132.3	165.1	220.0	301.2	399.3	498.3	585.7	651.4	693.2
115°	112.5	125.1	142.8	171.1	218.6	286.0	366.5	452.5	533.4	601.8	652.4
117.5°	124.7	136.3	153.8	179.1	219.4	277.0	346.7	419.2	489.1	550.5	601.9
120°	132.6	144.1	160.9	185.1	220.9	273.0	336.2	401.8	464.6	520.3	567.4
122.5°	139.6	152.0	168.4	190.7	223.5	270.4	327.7	388.0	444.8	496.5	540.1
125°	150.2	162.7	179.0	199.5	227.4	266.9	316.7	369.7	420.4	465.0	502.2
127.5°	160.0	172.6	188.3	206.8	231.9	265.2	307.0	353.7	398.9	439.2	473.0
130°	166.0	178.6	193.9	211.6	234.8	264.2	301.8	343.6	385.5	423.1	454.8
132.5°	171.6	183.8	198.8	216.1	237.1	263.7	296.9	334.4	372.8	407.9	438.1
135°	179.0	191.6	206.0	221.8	240.4	263.2	290.7	321.8	354.8	385.1	411.6
137.5°	185.6	197.1	211.0	226.1	242.6	262.2	285.2	310.4	337.5	363.5	386.5
140°	189.2	200.9	214.3	228.4	244.1	261.8	281.8	303.7	327.3	349.7	369.7
142.5°	193.0	203.9	217.0	230.6	245.2	261.1	278.8	297.3	317.7	337.0	354.4
145°	197.6	208.3	220.5	233.0	246.0	259.9	274.8	289.7	305.1	319.9	333.5
147.5°	203.0	212.1	223.2	234.5	246.0	258.2	270.9	283.5	295.6	307.7	317.2
150°	206.0	214.3	225.1	234.8	246.0	256.7	268.3	279.0	289.7	299.5	308.3
152.5°	209.0	217.0	226.2	235.6	244.9	254.9	265.4	274.9	284.1	292.8	300.1
155°	213.9	220.5	228.4	235.8	243.7	251.6	260.9	268.8	276.2	283.2	288.8
157.5°	218.2	223.2	229.5	236.3	242.1	248.7	255.8	262.3	268.5	273.9	278.3
160°	220.5	225.1	230.6	236.3	241.3	246.5	252.5	258.5	263.7	268.3	271.6
162.5°	222.3	226.2	231.1	235.9	239.9	244.3	249.2	254.1	258.4	262.8	265.6
165°	224.6	227.9	231.5	234.8	237.7	240.9	244.6	248.3	251.1	254.4	256.7
167.5°	226.7	228.8	231.5	234.1	235.4	237.5	240.3	243.3	245.4	247.3	249.0
170°	227.9	228.8	231.1	233.0	233.9	235.3	237.7	239.9	241.3	243.2	244.1
172.5°	228.6	229.2	231.1	232.6	232.8	233.4	235.1	237.0	238.0	239.5	240.0
175°	229.3	229.8	230.6	231.5	231.1	231.1	232.0	233.0	233.4	234.4	234.4
177.5°	229.8	229.8	230.1	230.8	230.1	229.8	230.1	230.5	230.8	231.2	231.2
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	842.4	842.0	844.4	842.7	844.4	842.0	842.4	844.7	845.5	845.8	845.8
5°	784.1	785.4	781.1	781.1	781.1	785.4	784.1	786.6	788.8	790.5	793.0
7.5°	732.1	730.3	730.4	728.1	730.4	730.3	732.1	734.3	736.9	740.7	744.2
10°	700.4	697.9	697.0	697.4	697.0	697.9	700.4	705.6	707.3	710.7	714.5
12.5°	674.1	673.6	668.0	668.1	668.0	673.6	674.1	675.5	679.2	686.4	691.0
15°	643.2	635.1	634.2	636.8	634.2	635.1	643.2	643.2	644.9	650.4	653.1
17.5°	612.2	608.0	608.2	606.9	608.2	608.0	612.2	612.9	614.2	618.8	622.2
20°	595.8	593.3	592.9	589.9	592.9	593.3	595.8	595.8	597.5	599.7	603.1
22.5°	580.8	580.0	580.2	576.9	580.2	580.0	580.8	581.9	583.6	585.0	587.4
25°	562.1	564.3	562.6	562.6	562.6	564.3	562.1	562.6	563.0	565.1	566.8
27.5°	549.5	549.4	548.5	548.5	548.5	549.4	549.5	548.5	548.0	547.2	546.8
30°	540.0	539.5	540.4	540.4	540.4	539.5	540.0	538.3	537.4	537.0	535.2
32.5°	530.4	531.0	531.2	531.5	531.2	531.0	530.4	528.3	526.8	525.7	524.3
35°	515.6	516.0	517.3	516.5	517.3	516.0	515.6	513.1	511.4	508.7	506.6
37.5°	495.6	497.6	497.2	497.8	497.2	497.6	495.6	494.9	493.2	491.2	488.7
40°	480.6	481.9	481.4	481.4	481.4	481.9	480.6	480.2	478.5	477.2	475.1
42.5°	465.2	466.2	465.0	464.4	465.0	466.2	465.2	464.5	463.4	461.1	458.7
45°	440.0	439.2	440.5	438.8	440.5	439.2	440.0	438.4	437.9	436.2	434.1
47.5°	411.9	412.7	413.1	414.3	413.1	412.7	411.9	412.1	409.7	408.6	408.0
50°	393.1	395.7	395.7	395.3	395.7	395.7	393.1	392.2	390.5	388.8	388.8
52.5°	374.6	375.9	377.6	377.5	377.6	375.9	374.6	373.2	371.5	369.0	368.4
55°	346.2	347.0	347.9	348.3	347.9	347.0	346.2	342.8	341.4	340.1	338.0
57.5°	316.6	316.3	318.3	318.9	318.3	316.3	316.6	313.6	311.6	307.7	307.1
60°	295.8	295.8	299.2	300.5	299.2	295.8	295.8	292.4	289.3	286.8	286.0
62.5°	273.6	275.0	278.3	276.5	278.3	275.0	273.6	269.9	267.5	264.3	262.0
65°	241.2	244.6	244.2	245.8	244.2	244.6	241.2	239.0	234.3	231.3	228.8
67.5°	207.2	209.4	212.5	212.7	212.5	209.4	207.2	203.8	200.8	197.6	194.5
70°	184.4	186.5	188.3	189.5	188.3	186.5	184.4	181.0	177.6	175.5	172.0
72.5°	162.2	163.3	167.4	165.6	167.4	163.3	162.2	158.1	155.4	153.6	149.9
75°	127.2	130.2	132.7	131.4	132.7	130.2	127.2	124.2	122.1	119.5	116.1
77.5°	94.1	97.0	98.2	97.2	98.2	97.0	94.1	92.1	91.0	85.9	85.6
80°	74.3	73.9	76.4	76.0	76.4	73.9	74.3	71.3	69.1	66.1	66.1
82.5°	54.5	54.1	55.2	55.5	55.2	54.1	54.5	52.8	50.1	48.8	47.7
85°	26.5	27.7	26.0	25.6	26.0	27.7	26.5	24.8	24.8	24.8	24.3
87.5°	8.7	8.8	8.6	8.2	8.6	8.8	8.7	8.8	10.0	8.9	8.8
90°	13.0	13.5	13.9	13.5	13.9	13.5	13.0	13.5	12.6	12.1	11.7
92.5°	24.2	22.7	23.2	22.4	23.2	22.7	24.2	25.0	27.5	31.1	39.1
95°	63.3	59.0	55.8	54.0	55.8	59.0	63.3	72.1	88.8	113.5	167.4
97.5°	184.3	163.4	150.8	146.8	150.8	163.4	184.3	218.7	274.3	334.3	417.4
100°	343.2	309.2	291.1	291.6	291.1	309.2	343.2	390.1	456.2	510.6	548.3
102.5°	480.5	453.6	438.4	427.7	438.4	453.6	480.5	517.0	558.9	590.6	591.8
105°	626.4	608.7	593.9	591.5	593.9	608.7	626.4	647.8	659.9	651.0	604.5
107.5°	701.1	695.1	690.1	685.8	690.1	695.1	701.1	700.7	684.1	643.4	567.9
110°	722.7	726.4	725.5	724.5	725.5	726.4	722.7	709.6	677.1	618.5	532.9



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	717.1	728.6	732.1	732.3	732.1	728.6	717.1	693.2	651.4	585.7	498.3
115°	687.3	707.8	717.1	719.4	717.1	707.8	687.3	652.4	601.8	533.4	452.5
117.5°	638.3	661.7	675.1	678.2	675.1	661.7	638.3	601.9	550.5	489.1	419.2
120°	604.1	630.1	641.2	644.1	641.2	630.1	604.1	567.4	520.3	464.6	401.8
122.5°	572.8	596.2	608.5	612.0	608.5	596.2	572.8	540.1	496.5	444.8	388.0
125°	532.0	552.4	564.1	567.4	564.1	552.4	532.0	502.2	465.0	420.4	369.7
127.5°	499.5	517.0	527.5	530.5	527.5	517.0	499.5	473.0	439.2	398.9	353.7
130°	479.5	496.2	506.0	509.6	506.0	496.2	479.5	454.8	423.1	385.5	343.6
132.5°	461.2	477.9	486.6	489.2	486.6	477.9	461.2	438.1	407.9	372.8	334.4
135°	434.3	448.3	456.6	459.9	456.6	448.3	434.3	411.6	385.1	354.8	321.8
137.5°	405.6	419.7	426.8	428.9	426.8	419.7	405.6	386.5	363.5	337.5	310.4
140°	387.3	400.4	407.8	407.3	407.8	400.4	387.3	369.7	349.7	327.3	303.7
142.5°	369.5	381.1	387.8	387.3	387.8	381.1	369.5	354.4	337.0	317.7	297.3
145°	345.0	354.8	358.6	359.5	358.6	354.8	345.0	333.5	319.9	305.1	289.7
147.5°	326.0	332.6	336.2	336.6	336.2	332.6	326.0	317.2	307.7	295.6	283.5
150°	315.3	320.4	323.2	323.2	323.2	320.4	315.3	308.3	299.5	289.7	279.0
152.5°	305.6	310.4	312.0	312.0	312.0	310.4	305.6	300.1	292.8	284.1	274.9
155°	292.9	296.7	297.6	298.1	297.6	296.7	292.9	288.8	283.2	276.2	268.8
157.5°	281.9	284.7	285.4	285.4	285.4	284.7	281.9	278.3	273.9	268.5	262.3
160°	274.8	277.6	277.6	277.1	277.6	277.6	274.8	271.6	268.3	263.7	258.5
162.5°	267.7	270.2	270.2	269.7	270.2	270.2	267.7	265.6	262.8	258.4	254.1
165°	258.5	260.4	259.9	259.9	259.9	260.4	258.5	256.7	254.4	251.1	248.3
167.5°	249.8	251.1	250.6	250.6	250.6	251.1	249.8	249.0	247.3	245.4	243.3
170°	244.6	245.6	245.1	245.1	245.1	245.6	244.6	244.1	243.2	241.3	239.9
172.5°	240.1	241.1	240.3	239.9	240.3	241.1	240.1	240.0	239.5	238.0	237.0
175°	234.4	234.8	234.4	233.9	234.4	234.8	234.4	234.4	234.4	233.4	233.0
177.5°	230.8	231.2	230.5	230.5	230.5	231.2	230.8	231.2	231.2	230.8	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	844.7	844.7	851.3	855.3	860.5	863.9	866.3	868.7	872.8	878.2	884.4
5°	796.5	798.2	807.6	816.9	825.9	833.6	840.0	847.7	857.0	868.6	881.4
7.5°	749.7	756.3	765.7	777.1	789.7	800.9	812.3	824.9	838.1	855.1	873.0
10°	719.7	726.9	738.4	752.9	766.1	779.3	793.4	807.1	823.8	843.8	866.9
12.5°	693.3	700.3	712.1	728.0	740.5	755.1	771.3	789.0	807.7	831.8	858.0
15°	656.9	665.0	679.5	687.2	706.4	723.9	738.8	764.4	788.3	813.1	843.4
17.5°	627.0	631.5	643.3	657.5	671.9	691.5	711.1	732.5	756.3	786.5	824.4
20°	606.5	610.3	623.1	638.1	653.5	671.4	688.9	710.2	737.1	769.2	810.1
22.5°	591.2	595.3	603.7	619.6	634.0	648.9	666.3	691.8	720.4	751.7	796.1
25°	568.9	571.5	577.1	589.9	602.7	619.3	634.7	658.6	688.0	724.7	769.2
27.5°	547.9	550.3	555.0	564.2	576.1	589.6	606.3	626.6	656.6	696.4	743.6
30°	535.2	535.7	540.0	548.5	558.7	569.8	585.1	608.2	636.4	676.9	726.4
32.5°	524.3	522.7	525.6	532.1	542.0	553.1	565.7	588.4	615.6	655.4	706.3
35°	505.8	504.9	503.7	509.2	517.7	526.3	537.4	554.5	585.1	622.3	675.6
37.5°	486.9	484.9	482.6	485.1	491.8	500.7	510.3	525.5	552.0	592.9	643.9
40°	473.0	471.2	469.9	469.0	475.1	483.6	490.8	505.3	530.1	568.9	619.3
42.5°	457.5	456.6	454.9	453.7	458.7	465.1	472.7	485.6	510.3	546.7	594.4
45°	432.8	431.9	431.1	430.2	433.3	439.2	445.2	454.5	475.9	511.4	554.5
47.5°	405.2	404.1	404.5	403.1	406.0	410.0	414.2	424.3	444.7	473.4	504.8
50°	385.4	385.0	385.0	385.0	385.9	390.5	394.4	402.1	420.9	449.5	472.1
52.5°	366.6	364.8	364.8	365.5	367.0	370.1	372.5	380.9	397.3	420.8	441.3
55°	337.2	333.8	332.9	333.8	335.1	337.6	340.1	347.0	361.1	378.6	390.5
57.5°	304.6	302.7	301.6	301.7	302.5	304.5	306.5	313.9	325.0	334.1	341.8
60°	281.7	282.6	278.8	279.6	279.6	281.3	284.3	288.9	298.3	304.8	312.4
62.5°	260.2	259.0	257.9	256.7	256.7	257.4	261.4	265.1	273.0	276.4	282.4
65°	226.7	226.7	224.0	224.9	225.3	222.4	224.5	228.8	233.9	235.2	240.8
67.5°	192.7	191.5	190.0	188.7	188.7	188.5	189.6	191.8	195.6	196.0	200.2
70°	169.4	168.6	168.2	166.9	165.2	167.3	166.0	168.2	170.3	170.7	173.3
72.5°	146.9	146.0	145.3	144.0	143.3	143.1	143.2	145.6	147.1	146.5	149.4
75°	114.8	114.0	113.1	111.0	111.0	109.7	110.1	111.9	113.6	112.3	114.8
77.5°	84.3	81.7	81.5	82.1	80.6	81.0	80.4	80.1	81.0	81.0	83.3
80°	64.9	61.9	62.8	62.3	61.9	61.5	60.6	61.1	61.5	61.9	63.2
82.5°	46.8	46.6	45.7	45.6	45.2	44.0	43.5	44.3	44.8	44.5	45.4
85°	23.9	22.6	23.5	23.1	23.5	23.1	21.8	21.8	22.6	22.2	23.1
87.5°	9.4	9.5	8.9	9.0	8.3	8.4	7.8	8.0	8.1	7.9	8.4
90°	11.2	11.7	10.2	8.8	7.4	6.0	5.1	4.2	2.8	1.9	0.9
92.5°	54.0	71.5	78.7	59.0	39.1	26.9	20.0	16.1	12.5	8.6	5.8
95°	223.6	275.7	245.6	169.3	100.0	60.4	42.3	30.2	22.3	17.2	15.8
97.5°	457.2	427.4	312.8	185.7	107.6	69.9	50.2	38.3	31.5	27.5	27.0
100°	532.0	440.3	297.6	175.3	106.5	73.9	55.8	44.7	38.2	34.9	34.4
102.5°	535.7	416.2	275.3	166.4	107.9	78.8	62.1	52.1	46.0	43.0	42.2
105°	507.4	373.9	247.9	160.0	112.1	87.0	72.6	63.7	58.1	55.4	54.0
107.5°	457.7	336.5	230.4	159.5	119.7	97.7	84.3	76.0	70.5	67.8	66.4
110°	426.4	315.3	223.6	161.3	126.0	105.1	92.0	84.1	79.1	76.7	75.3



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	399.3	301.2	220.0	165.1	132.3	112.9	100.3	92.4	87.2	85.0	83.5
115°	366.5	286.0	218.6	171.1	142.8	125.1	112.5	104.6	100.0	97.2	95.3
117.5°	346.7	277.0	219.4	179.1	153.8	136.3	124.7	115.9	111.6	109.3	107.1
120°	336.2	273.0	220.9	185.1	160.9	144.1	132.6	123.7	119.0	116.8	115.4
122.5°	327.7	270.4	223.5	190.7	168.4	152.0	139.6	131.1	126.1	123.8	122.4
125°	316.7	266.9	227.4	199.5	179.0	162.7	150.2	141.4	136.2	133.5	132.6
127.5°	307.0	265.2	231.9	206.8	188.3	172.6	160.0	150.3	145.1	141.6	140.2
130°	301.8	264.2	234.8	211.6	193.9	178.6	166.0	156.2	150.7	146.5	145.1
132.5°	296.9	263.7	237.1	216.1	198.8	183.8	171.6	161.8	155.2	150.6	148.8
135°	290.7	263.2	240.4	221.8	206.0	191.6	179.0	169.3	162.3	157.2	155.3
137.5°	285.2	262.2	242.6	226.1	211.0	197.1	185.6	175.9	168.4	163.4	161.4
140°	281.8	261.8	244.1	228.4	214.3	200.9	189.2	179.9	172.5	167.9	165.6
142.5°	278.8	261.1	245.2	230.6	217.0	203.9	193.0	183.7	177.0	171.9	170.0
145°	274.8	259.9	246.0	233.0	220.5	208.3	197.6	189.7	182.8	178.6	177.2
147.5°	270.9	258.2	246.0	234.5	223.2	212.1	203.0	195.4	189.4	185.2	184.4
150°	268.3	256.7	246.0	234.8	225.1	214.3	206.0	199.5	193.5	189.7	189.2
152.5°	265.4	254.9	244.9	235.6	226.2	217.0	209.0	203.3	198.0	194.2	194.1
155°	260.9	251.6	243.7	235.8	228.4	220.5	213.9	208.8	204.2	201.4	201.4
157.5°	255.8	248.7	242.1	236.3	229.5	223.2	218.2	213.9	209.7	207.5	207.1
160°	252.5	246.5	241.3	236.3	230.6	225.1	220.5	217.2	213.4	211.6	211.6
162.5°	249.2	244.3	239.9	235.9	231.1	226.2	222.3	219.4	216.5	214.9	214.9
165°	244.6	240.9	237.7	234.8	231.5	227.9	224.6	222.7	220.5	219.5	220.0
167.5°	240.3	237.5	235.4	234.1	231.5	228.8	226.7	225.4	223.6	223.2	223.8
170°	237.7	235.3	233.9	233.0	231.1	228.8	227.9	226.9	225.5	225.1	226.0
172.5°	235.1	233.4	232.8	232.6	231.1	229.2	228.6	228.0	227.1	226.9	227.5
175°	232.0	231.1	231.1	231.5	230.6	229.8	229.3	229.3	228.4	228.8	229.3
177.5°	230.1	229.8	230.1	230.8	230.1	229.8	229.8	229.8	229.3	229.8	230.1
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	886.4	888.1	894.0	898.1	902.8	905.6	908.2	910.4	913.1	913.7	923.7
5°	890.4	898.9	913.9	925.0	938.6	953.5	963.8	968.5	980.8	991.1	1011.5
7.5°	889.2	907.4	929.9	953.3	978.4	1001.7	1021.8	1045.7	1062.7	1088.3	1113.4
10°	888.2	912.6	941.6	971.4	1006.5	1038.9	1067.9	1100.3	1127.2	1162.7	1192.9
12.5°	885.2	914.6	954.9	990.3	1032.7	1077.5	1120.5	1162.1	1185.9	1245.0	1272.8
15°	877.6	912.6	963.0	1016.7	1075.1	1128.1	1182.8	1226.3	1296.7	1348.3	1381.2
17.5°	863.1	912.1	971.8	1036.7	1107.7	1177.5	1239.4	1305.5	1380.1	1442.7	1509.3
20°	856.2	910.0	976.6	1048.3	1122.1	1201.1	1271.5	1350.9	1432.4	1493.9	1579.2
22.5°	843.6	904.5	976.2	1056.1	1135.1	1216.8	1299.2	1379.2	1473.4	1558.1	1639.3
25°	822.9	891.2	965.5	1054.7	1147.3	1229.2	1327.9	1434.1	1532.3	1641.1	1722.2
27.5°	801.2	874.2	948.6	1031.5	1131.1	1228.4	1352.4	1472.5	1592.6	1686.5	1746.5
30°	784.5	855.3	932.2	1015.9	1114.4	1230.1	1368.8	1499.8	1616.8	1697.5	1731.2
32.5°	766.4	838.3	906.2	994.0	1099.1	1229.1	1379.1	1515.9	1618.2	1671.9	1665.3
35°	738.0	798.2	864.3	948.8	1072.6	1221.6	1385.0	1517.4	1580.1	1568.6	1481.5
37.5°	697.0	747.6	812.8	905.3	1041.9	1205.7	1373.1	1472.3	1468.3	1374.4	1248.3
40°	671.4	714.5	777.2	874.6	1018.0	1195.6	1354.3	1418.8	1364.2	1233.1	1082.0
42.5°	638.0	677.6	740.4	840.4	991.6	1174.7	1318.4	1337.2	1230.3	1079.5	940.9
45°	586.0	621.0	685.9	789.2	952.3	1129.4	1230.9	1185.3	1041.5	885.7	780.2
47.5°	530.3	566.6	629.1	735.2	895.2	1061.2	1109.5	1012.4	864.7	738.4	641.6
50°	495.1	530.1	591.2	698.3	856.6	1005.2	1025.2	899.8	764.0	653.1	573.6
52.5°	459.6	492.5	552.5	660.1	811.5	940.3	927.9	800.1	675.2	580.7	518.4
55°	406.8	437.9	495.1	595.8	733.7	835.7	790.9	668.9	565.6	492.1	444.7
57.5°	359.5	389.4	438.7	529.7	649.5	719.7	662.6	559.7	477.6	421.1	385.8
60°	327.3	353.8	400.8	485.3	589.5	642.8	586.4	495.5	426.4	381.2	349.6
62.5°	297.0	320.0	363.5	440.3	530.7	575.5	518.5	441.6	382.7	342.6	315.8
65°	250.9	271.9	310.3	370.1	444.3	474.2	425.1	362.8	317.2	287.2	269.3
67.5°	209.0	226.7	259.9	307.0	361.6	383.4	346.0	297.7	263.3	239.4	225.1
70°	181.0	196.3	222.4	262.9	312.4	329.1	294.1	254.4	229.2	210.0	196.7
72.5°	157.4	168.7	192.3	223.6	265.0	278.2	253.8	218.9	195.4	181.0	170.5
75°	119.9	129.3	144.7	169.9	198.4	206.2	187.8	166.0	150.3	140.0	131.9
77.5°	86.5	93.4	104.5	120.0	139.8	146.8	135.1	120.6	109.1	102.2	97.7
80°	65.3	70.8	80.2	93.0	105.0	108.8	102.0	90.9	82.8	79.0	75.1
82.5°	48.3	51.4	57.0	65.7	73.9	78.4	72.6	66.0	61.6	58.1	56.7
85°	24.3	26.0	28.6	32.0	37.1	38.8	36.7	35.0	32.4	30.3	30.3
87.5°	9.2	9.5	10.8	11.6	13.1	14.4	14.4	14.0	13.9	13.5	13.3
90°	1.9	2.8	4.2	5.1	6.0	7.4	8.8	10.2	11.7	11.2	11.7
92.5°	8.6	12.5	16.1	20.0	26.9	39.1	59.0	78.7	71.5	54.0	39.1
95°	17.2	22.3	30.2	42.3	60.4	100.0	169.3	245.6	275.7	223.6	167.4
97.5°	27.5	31.5	38.3	50.2	69.9	107.6	185.7	312.8	427.4	457.2	417.4
100°	34.9	38.2	44.7	55.8	73.9	106.5	175.3	297.6	440.3	532.0	548.3
102.5°	43.0	46.0	52.1	62.1	78.8	107.9	166.4	275.3	416.2	535.7	591.8
105°	55.4	58.1	63.7	72.6	87.0	112.1	160.0	247.9	373.9	507.4	604.5
107.5°	67.8	70.5	76.0	84.3	97.7	119.7	159.5	230.4	336.5	457.7	567.9
110°	76.7	79.1	84.1	92.0	105.1	126.0	161.3	223.6	315.3	426.4	532.9



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	85.0	87.2	92.4	100.3	112.9	132.3	165.1	220.0	301.2	399.3	498.3
115°	97.2	100.0	104.6	112.5	125.1	142.8	171.1	218.6	286.0	366.5	452.5
117.5°	109.3	111.6	115.9	124.7	136.3	153.8	179.1	219.4	277.0	346.7	419.2
120°	116.8	119.0	123.7	132.6	144.1	160.9	185.1	220.9	273.0	336.2	401.8
122.5°	123.8	126.1	131.1	139.6	152.0	168.4	190.7	223.5	270.4	327.7	388.0
125°	133.5	136.2	141.4	150.2	162.7	179.0	199.5	227.4	266.9	316.7	369.7
127.5°	141.6	145.1	150.3	160.0	172.6	188.3	206.8	231.9	265.2	307.0	353.7
130°	146.5	150.7	156.2	166.0	178.6	193.9	211.6	234.8	264.2	301.8	343.6
132.5°	150.6	155.2	161.8	171.6	183.8	198.8	216.1	237.1	263.7	296.9	334.4
135°	157.2	162.3	169.3	179.0	191.6	206.0	221.8	240.4	263.2	290.7	321.8
137.5°	163.4	168.4	175.9	185.6	197.1	211.0	226.1	242.6	262.2	285.2	310.4
140°	167.9	172.5	179.9	189.2	200.9	214.3	228.4	244.1	261.8	281.8	303.7
142.5°	171.9	177.0	183.7	193.0	203.9	217.0	230.6	245.2	261.1	278.8	297.3
145°	178.6	182.8	189.7	197.6	208.3	220.5	233.0	246.0	259.9	274.8	289.7
147.5°	185.2	189.4	195.4	203.0	212.1	223.2	234.5	246.0	258.2	270.9	283.5
150°	189.7	193.5	199.5	206.0	214.3	225.1	234.8	246.0	256.7	268.3	279.0
152.5°	194.2	198.0	203.3	209.0	217.0	226.2	235.6	244.9	254.9	265.4	274.9
155°	201.4	204.2	208.8	213.9	220.5	228.4	235.8	243.7	251.6	260.9	268.8
157.5°	207.5	209.7	213.9	218.2	223.2	229.5	236.3	242.1	248.7	255.8	262.3
160°	211.6	213.4	217.2	220.5	225.1	230.6	236.3	241.3	246.5	252.5	258.5
162.5°	214.9	216.5	219.4	222.3	226.2	231.1	235.9	239.9	244.3	249.2	254.1
165°	219.5	220.5	222.7	224.6	227.9	231.5	234.8	237.7	240.9	244.6	248.3
167.5°	223.2	223.6	225.4	226.7	228.8	231.5	234.1	235.4	237.5	240.3	243.3
170°	225.1	225.5	226.9	227.9	228.8	231.1	233.0	233.9	235.3	237.7	239.9
172.5°	226.9	227.1	228.0	228.6	229.2	231.1	232.6	232.8	233.4	235.1	237.0
175°	228.8	228.4	229.3	229.3	229.8	230.6	231.5	231.1	231.1	232.0	233.0
177.5°	229.8	229.3	229.8	229.8	229.8	230.1	230.8	230.1	229.8	230.1	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8	229.8



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	927.1	927.4	931.2	933.9	932.5	934.3	934.9
5°	1012.8	1028.3	1036.3	1042.3	1042.8	1043.2	1046.6
7.5°	1134.5	1151.0	1163.0	1181.3	1186.7	1192.9	1191.2
10°	1223.3	1247.6	1268.5	1279.6	1291.6	1309.0	1295.0
12.5°	1306.3	1349.4	1381.2	1398.5	1409.7	1413.2	1406.3
15°	1443.1	1499.4	1529.7	1528.8	1567.3	1584.0	1557.9
17.5°	1568.6	1620.6	1662.2	1683.6	1715.6	1722.6	1719.4
20°	1645.4	1702.2	1734.6	1771.3	1788.0	1802.9	1805.5
22.5°	1711.6	1762.6	1797.4	1828.0	1841.9	1849.0	1853.3
25°	1779.9	1820.0	1840.9	1851.5	1855.4	1854.6	1849.0
27.5°	1775.2	1778.2	1755.2	1732.6	1712.4	1689.5	1681.7
30°	1729.1	1693.2	1629.2	1592.9	1539.5	1497.3	1514.3
32.5°	1607.9	1536.5	1464.6	1385.3	1319.6	1301.0	1282.1
35°	1372.2	1246.8	1173.4	1087.9	1053.9	1019.7	996.2
37.5°	1110.2	1013.1	926.0	870.2	836.0	814.4	802.7
40°	959.9	872.5	800.7	755.5	729.4	705.2	701.7
42.5°	840.1	758.7	704.7	668.7	643.8	633.4	625.9
45°	688.0	631.3	595.0	569.4	552.8	546.3	537.8
47.5°	582.4	542.3	515.0	497.6	485.0	480.3	479.6
50°	523.3	490.0	469.9	456.2	446.5	444.7	437.9
52.5°	478.9	450.0	434.4	422.5	415.4	410.6	408.5
55°	415.7	396.5	382.5	375.6	370.1	365.3	365.3
57.5°	363.7	347.7	338.3	332.6	330.8	327.5	325.4
60°	331.7	318.0	310.7	305.6	302.2	302.6	298.8
62.5°	300.2	291.4	284.5	279.3	275.2	275.3	275.6
65°	255.7	248.8	243.7	242.0	239.5	236.4	237.3
67.5°	216.6	210.3	206.3	203.3	202.5	200.9	203.3
70°	188.7	183.9	181.0	178.4	177.6	178.0	180.1
72.5°	163.1	159.7	157.8	156.5	154.7	154.7	156.2
75°	128.1	125.5	123.8	122.5	122.1	122.1	122.1
77.5°	94.1	93.5	92.7	90.8	90.9	91.4	91.5
80°	74.3	73.0	72.6	71.7	70.4	69.5	71.7
82.5°	55.5	54.2	53.8	53.6	51.6	51.4	53.2
85°	29.8	28.6	29.0	28.6	28.6	28.2	28.2
87.5°	13.0	12.7	12.6	12.9	12.6	12.3	13.0
90°	12.1	12.6	13.5	13.0	13.5	13.9	13.5
92.5°	31.1	27.5	25.0	24.2	22.7	23.2	22.4
95°	113.5	88.8	72.1	63.3	59.0	55.8	54.0
97.5°	334.3	274.3	218.7	184.3	163.4	150.8	146.8
100°	510.6	456.2	390.1	343.2	309.2	291.1	291.6
102.5°	590.6	558.9	517.0	480.5	453.6	438.4	427.7
105°	651.0	659.9	647.8	626.4	608.7	593.9	591.5
107.5°	643.4	684.1	700.7	701.1	695.1	690.1	685.8
110°	618.5	677.1	709.6	722.7	726.4	725.5	724.5



TEST NUMBER: P331966-930

CATALOG NUMBER: S123DIP-S775D585U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	585.7	651.4	693.2	717.1	728.6	732.1	732.3
115°	533.4	601.8	652.4	687.3	707.8	717.1	719.4
117.5°	489.1	550.5	601.9	638.3	661.7	675.1	678.2
120°	464.6	520.3	567.4	604.1	630.1	641.2	644.1
122.5°	444.8	496.5	540.1	572.8	596.2	608.5	612.0
125°	420.4	465.0	502.2	532.0	552.4	564.1	567.4
127.5°	398.9	439.2	473.0	499.5	517.0	527.5	530.5
130°	385.5	423.1	454.8	479.5	496.2	506.0	509.6
132.5°	372.8	407.9	438.1	461.2	477.9	486.6	489.2
135°	354.8	385.1	411.6	434.3	448.3	456.6	459.9
137.5°	337.5	363.5	386.5	405.6	419.7	426.8	428.9
140°	327.3	349.7	369.7	387.3	400.4	407.8	407.3
142.5°	317.7	337.0	354.4	369.5	381.1	387.8	387.3
145°	305.1	319.9	333.5	345.0	354.8	358.6	359.5
147.5°	295.6	307.7	317.2	326.0	332.6	336.2	336.6
150°	289.7	299.5	308.3	315.3	320.4	323.2	323.2
152.5°	284.1	292.8	300.1	305.6	310.4	312.0	312.0
155°	276.2	283.2	288.8	292.9	296.7	297.6	298.1
157.5°	268.5	273.9	278.3	281.9	284.7	285.4	285.4
160°	263.7	268.3	271.6	274.8	277.6	277.6	277.1
162.5°	258.4	262.8	265.6	267.7	270.2	270.2	269.7
165°	251.1	254.4	256.7	258.5	260.4	259.9	259.9
167.5°	245.4	247.3	249.0	249.8	251.1	250.6	250.6
170°	241.3	243.2	244.1	244.6	245.6	245.1	245.1
172.5°	238.0	239.5	240.0	240.1	241.1	240.3	239.9
175°	233.4	234.4	234.4	234.4	234.8	234.4	233.9
177.5°	230.8	231.2	231.2	230.8	231.2	230.5	230.5
180°	229.8	229.8	229.8	229.8	229.8	229.8	229.8

(END OF REPORT)