

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331975-930

Luminaire Tested: **S123DIP-S775D805U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331975-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIP-S775D805U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 805 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5030.4 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	46	44	43	38
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	43	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9482	9482	9482	9482
5°	11309	9524	8440	9524
10°	14154	9475	7623	9475
15°	17361	9399	7096	9399
20°	20681	9279	6757	9279
25°	21960	9136	6682	9136
30°	18821	9028	6717	9028
35°	13090	8878	6787	8878
40°	9860	8702	6764	8702
45°	8187	8441	6680	8441
50°	7333	7906	6620	7906
55°	6855	7328	6536	7328
60°	6433	6725	6469	6725
65°	6044	6133	6260	6133
70°	5668	5454	5964	5454
75°	5078	4774	5465	4774
80°	4444	3918	4711	3918
85°	3483	2853	3162	2853



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.7
10°-20°	278.3	5.5
20°-30°	467.0	9.3
30°-40°	528.8	10.5
40°-50°	474.2	9.4
50°-60°	382.7	7.6
60°-70°	266.7	5.3
70°-80°	140.2	2.8
80°-90°	36.7	0.7
90°-100°	175.2	3.5
100°-110°	496.2	9.9
110°-120°	488.1	9.7
120°-130°	389.3	7.7
130°-140°	307.0	6.1
140°-150°	229.1	4.6
150°-160°	159.7	3.2
160°-170°	93.8	1.9
170°-180°	30.5	0.6
0°-30°	832.1	16.5
0°-40°	1360.9	27.1
0°-60°	2217.8	44.1
0°-90°	2661.4	52.9
90°-120°	1159.6	23.1
90°-150°	2085.0	41.4
90°-180°	2369.0	47.1
0°-180°	5030.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	881	881	881	881	881	
5°	1047	881	781	881	1047	108
15°	1558	843	637	843	1558	450
25°	1849	769	563	769	1849	811
35°	996	676	516	676	996	647
45°	538	554	439	554	538	426
55°	365	390	348	390	365	328
65°	237	241	246	241	237	236
75°	122	115	131	115	122	131
85°	28	23	26	23	28	34
90°	18	1	18	1	18	11
95°	74	22	74	22	74	133
105°	811	74	811	74	811	800
115°	986	131	986	131	986	958
125°	778	182	778	182	778	705
135°	630	213	630	213	630	489
145°	493	243	493	243	493	313
155°	408	276	408	276	408	191
165°	356	302	356	302	356	102
175°	321	314	321	314	321	31
180°	315	315	315	315	315	



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	934.9	934.3	932.5	933.9	931.2	927.4	927.1	923.7	913.7	913.1	910.4
5°	1046.6	1043.2	1042.8	1042.3	1036.3	1028.3	1012.8	1011.5	991.1	980.8	968.5
7.5°	1191.2	1192.9	1186.7	1181.3	1163.0	1151.0	1134.5	1113.4	1088.3	1062.7	1045.7
10°	1295.0	1309.0	1291.6	1279.6	1268.5	1247.6	1223.3	1192.9	1162.7	1127.2	1100.3
12.5°	1406.3	1413.2	1409.7	1398.5	1381.2	1349.4	1306.3	1272.8	1245.0	1185.9	1162.1
15°	1557.9	1584.0	1567.3	1528.8	1529.7	1499.4	1443.1	1381.2	1348.3	1296.7	1226.3
17.5°	1719.4	1722.6	1715.6	1683.6	1662.2	1620.6	1568.6	1509.3	1442.7	1380.1	1305.5
20°	1805.5	1802.9	1788.0	1771.3	1734.6	1702.2	1645.4	1579.2	1493.9	1432.4	1350.9
22.5°	1853.3	1849.0	1841.9	1828.0	1797.4	1762.6	1711.6	1639.3	1558.1	1473.4	1379.2
25°	1849.0	1854.6	1855.4	1851.5	1840.9	1820.0	1779.9	1722.2	1641.1	1532.3	1434.1
27.5°	1681.7	1689.5	1712.4	1732.6	1755.2	1778.2	1775.2	1746.5	1686.5	1592.6	1472.5
30°	1514.3	1497.3	1539.5	1592.9	1629.2	1693.2	1729.1	1731.2	1697.5	1616.8	1499.8
32.5°	1282.1	1301.0	1319.6	1385.3	1464.6	1536.5	1607.9	1665.3	1671.9	1618.2	1515.9
35°	996.2	1019.7	1053.9	1087.9	1173.4	1246.8	1372.2	1481.5	1568.6	1580.1	1517.4
37.5°	802.7	814.4	836.0	870.2	926.0	1013.1	1110.2	1248.3	1374.4	1468.3	1472.3
40°	701.7	705.2	729.4	755.5	800.7	872.5	959.9	1082.0	1233.1	1364.2	1418.8
42.5°	625.9	633.4	643.8	668.7	704.7	758.7	840.1	940.9	1079.5	1230.3	1337.2
45°	537.8	546.3	552.8	569.4	595.0	631.3	688.0	780.2	885.7	1041.5	1185.3
47.5°	479.6	480.3	485.0	497.6	515.0	542.3	582.4	641.6	738.4	864.7	1012.4
50°	437.9	444.7	446.5	456.2	469.9	490.0	523.3	573.6	653.1	764.0	899.8
52.5°	408.5	410.6	415.4	422.5	434.4	450.0	478.9	518.4	580.7	675.2	800.1
55°	365.3	365.3	370.1	375.6	382.5	396.5	415.7	444.7	492.1	565.6	668.9
57.5°	325.4	327.5	330.8	332.6	338.3	347.7	363.7	385.8	421.1	477.6	559.7
60°	298.8	302.6	302.2	305.6	310.7	318.0	331.7	349.6	381.2	426.4	495.5
62.5°	275.6	275.3	275.2	279.3	284.5	291.4	300.2	315.8	342.6	382.7	441.6
65°	237.3	236.4	239.5	242.0	243.7	248.8	255.7	269.3	287.2	317.2	362.8
67.5°	203.3	200.9	202.5	203.3	206.3	210.3	216.6	225.1	239.4	263.3	297.7
70°	180.1	178.0	177.6	178.4	181.0	183.9	188.7	196.7	210.0	229.2	254.4
72.5°	156.2	154.7	154.7	156.5	157.8	159.7	163.1	170.5	181.0	195.4	218.9
75°	122.1	122.1	122.1	122.5	123.8	125.5	128.1	131.9	140.0	150.3	166.0
77.5°	91.5	91.4	90.9	90.8	92.7	93.5	94.1	97.7	102.2	109.1	120.6
80°	71.7	69.5	70.4	71.7	72.6	73.0	74.3	75.1	79.0	82.8	90.9
82.5°	53.2	51.4	51.6	53.6	53.8	54.2	55.5	56.7	58.1	61.6	66.0
85°	28.2	28.2	28.6	28.6	29.0	28.6	29.8	30.3	30.3	32.4	35.0
87.5°	13.9	13.4	13.6	13.8	13.6	13.7	13.9	14.1	14.3	14.8	14.8
90°	18.5	19.2	18.5	17.9	18.5	17.2	16.6	15.9	15.3	15.9	14.0
92.5°	30.7	31.9	31.2	33.2	34.3	37.6	42.6	53.6	73.9	98.0	107.9
95°	73.9	76.5	81.0	86.7	98.8	121.7	155.6	229.5	306.6	378.0	336.6
97.5°	201.3	206.8	224.0	252.7	299.7	375.9	458.2	572.0	626.7	585.8	428.8
100°	399.7	399.0	423.9	470.4	534.8	625.3	699.9	751.5	729.2	603.6	408.0
102.5°	586.3	601.0	621.7	658.6	708.7	766.1	809.5	811.1	734.3	570.5	377.3
105°	810.8	814.0	834.4	858.6	887.9	904.5	892.3	828.7	695.5	512.5	339.7
107.5°	940.0	945.9	952.8	961.0	960.4	937.8	881.9	778.4	627.4	461.2	315.8
110°	993.1	994.3	995.6	990.5	972.7	928.1	847.7	730.5	584.5	432.2	306.6



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1003.8	1003.6	998.7	982.9	950.2	892.9	802.9	683.1	547.3	412.8	301.5
115°	986.1	982.9	970.1	942.1	894.3	824.8	731.1	620.2	502.3	392.0	299.6
117.5°	929.8	925.4	907.0	874.9	825.1	754.6	670.4	574.7	475.2	379.8	300.8
120°	882.8	879.0	863.7	828.0	777.6	713.3	636.7	550.7	460.9	374.1	302.8
122.5°	838.9	834.1	817.3	785.1	740.5	680.6	609.8	531.9	449.1	370.6	306.3
125°	777.6	773.1	757.2	729.2	688.4	637.4	576.3	506.7	434.1	365.9	311.7
127.5°	727.2	723.1	708.7	684.7	648.4	602.0	546.7	484.9	420.9	363.6	317.8
130°	698.6	693.5	680.1	657.2	623.4	580.1	528.4	471.1	413.7	362.1	321.9
132.5°	670.6	667.0	655.2	632.2	600.5	559.1	511.1	458.3	407.1	361.5	325.0
135°	630.4	625.9	614.5	595.3	564.1	527.7	486.3	441.1	398.4	360.8	329.5
137.5°	588.0	585.1	575.4	556.0	529.7	498.2	462.5	425.4	390.9	359.4	332.6
140°	558.4	559.1	548.8	531.0	506.7	479.3	448.7	416.2	386.3	358.9	334.7
142.5°	530.8	531.5	522.3	506.5	485.8	462.0	435.5	407.6	382.2	357.8	336.1
145°	492.7	491.5	486.3	473.0	457.1	438.5	418.2	397.1	376.7	356.3	337.2
147.5°	461.4	460.9	456.0	446.9	434.9	421.8	405.3	388.6	371.4	353.9	337.2
150°	443.0	443.0	439.2	432.2	422.6	410.5	397.1	382.5	367.8	351.9	337.2
152.5°	427.7	427.7	425.4	418.9	411.4	401.3	389.5	376.8	363.7	349.3	335.7
155°	408.5	408.0	406.7	401.5	395.8	388.2	378.6	368.4	357.6	344.9	334.0
157.5°	391.1	391.3	390.2	386.4	381.4	375.4	368.0	359.5	350.7	340.9	331.8
160°	379.9	380.5	380.5	376.7	372.3	367.8	361.4	354.4	346.1	337.9	330.8
162.5°	369.7	370.3	370.3	367.0	364.1	360.1	354.2	348.3	341.5	334.8	328.8
165°	356.3	356.3	356.9	354.4	351.9	348.7	344.2	340.4	335.3	330.2	325.7
167.5°	343.6	343.6	344.2	342.4	341.3	339.0	336.4	333.5	329.3	325.6	322.7
170°	335.9	335.9	336.6	335.3	334.7	333.4	330.8	328.9	325.7	322.5	320.7
172.5°	328.8	329.3	330.4	329.1	329.1	328.2	326.2	324.8	322.1	320.0	319.1
175°	320.7	321.2	321.9	321.2	321.2	321.2	320.0	319.4	318.0	316.8	316.8
177.5°	315.9	315.9	316.9	316.4	316.9	316.9	316.4	315.9	315.4	314.9	315.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	908.2	905.6	902.8	898.1	894.0	888.1	886.4	884.4	878.2	872.8	868.7
5°	963.8	953.5	938.6	925.0	913.9	898.9	890.4	881.4	868.6	857.0	847.7
7.5°	1021.8	1001.7	978.4	953.3	929.9	907.4	889.2	873.0	855.1	838.1	824.9
10°	1067.9	1038.9	1006.5	971.4	941.6	912.6	888.2	866.9	843.8	823.8	807.1
12.5°	1120.5	1077.5	1032.7	990.3	954.9	914.6	885.2	858.0	831.8	807.7	789.0
15°	1182.8	1128.1	1075.1	1016.7	963.0	912.6	877.6	843.4	813.1	788.3	764.4
17.5°	1239.4	1177.5	1107.7	1036.7	971.8	912.1	863.1	824.4	786.5	756.3	732.5
20°	1271.5	1201.1	1122.1	1048.3	976.6	910.0	856.2	810.1	769.2	737.1	710.2
22.5°	1299.2	1216.8	1135.1	1056.1	976.2	904.5	843.6	796.1	751.7	720.4	691.8
25°	1327.9	1229.2	1147.3	1054.7	965.5	891.2	822.9	769.2	724.7	688.0	658.6
27.5°	1352.4	1228.4	1131.1	1031.5	948.6	874.2	801.2	743.6	696.4	656.6	626.6
30°	1368.8	1230.1	1114.4	1015.9	932.2	855.3	784.5	726.4	676.9	636.4	608.2
32.5°	1379.1	1229.1	1099.1	994.0	906.2	838.3	766.4	706.3	655.4	615.6	588.4
35°	1385.0	1221.6	1072.6	948.8	864.3	798.2	738.0	675.6	622.3	585.1	554.5
37.5°	1373.1	1205.7	1041.9	905.3	812.8	747.6	697.0	643.9	592.9	552.0	525.5
40°	1354.3	1195.6	1018.0	874.6	777.2	714.5	671.4	619.3	568.9	530.1	505.3
42.5°	1318.4	1174.7	991.6	840.4	740.4	677.6	638.0	594.4	546.7	510.3	485.6
45°	1230.9	1129.4	952.3	789.2	685.9	621.0	586.0	554.5	511.4	475.9	454.5
47.5°	1109.5	1061.2	895.2	735.2	629.1	566.6	530.3	504.8	473.4	444.7	424.3
50°	1025.2	1005.2	856.6	698.3	591.2	530.1	495.1	472.1	449.5	420.9	402.1
52.5°	927.9	940.3	811.5	660.1	552.5	492.5	459.6	441.3	420.8	397.3	380.9
55°	790.9	835.7	733.7	595.8	495.1	437.9	406.8	390.5	378.6	361.1	347.0
57.5°	662.6	719.7	649.5	529.7	438.7	389.4	359.5	341.8	334.1	325.0	313.9
60°	586.4	642.8	589.5	485.3	400.8	353.8	327.3	312.4	304.8	298.3	288.9
62.5°	518.5	575.5	530.7	440.3	363.5	320.0	297.0	282.4	276.4	273.0	265.1
65°	425.1	474.2	444.3	370.1	310.3	271.9	250.9	240.8	235.2	233.9	228.8
67.5°	346.0	383.4	361.6	307.0	259.9	226.7	209.0	200.2	196.0	195.6	191.8
70°	294.1	329.1	312.4	262.9	222.4	196.3	181.0	173.3	170.7	170.3	168.2
72.5°	253.8	278.2	265.0	223.6	192.3	168.7	157.4	149.4	146.5	147.1	145.6
75°	187.8	206.2	198.4	169.9	144.7	129.3	119.9	114.8	112.3	113.6	111.9
77.5°	135.1	146.8	139.8	120.0	104.5	93.4	86.5	83.3	81.0	81.0	80.1
80°	102.0	108.8	105.0	93.0	80.2	70.8	65.3	63.2	61.9	61.5	61.1
82.5°	72.6	78.4	73.9	65.7	57.0	51.4	48.3	45.4	44.5	44.8	44.3
85°	36.7	38.8	37.1	32.0	28.6	26.0	24.3	23.1	22.2	22.6	21.8
87.5°	15.1	15.0	13.6	12.0	11.1	9.6	9.4	8.5	8.0	8.3	8.3
90°	12.1	10.2	8.3	7.0	5.7	3.8	2.5	1.3	2.5	3.8	5.7
92.5°	81.0	53.6	36.9	27.4	22.1	17.1	11.7	7.9	11.7	17.1	22.1
95°	232.0	137.1	82.8	58.0	41.4	30.6	23.6	21.7	23.6	30.6	41.4
97.5°	254.6	147.5	95.7	68.8	52.5	43.1	37.6	36.9	37.6	43.1	52.5
100°	240.3	145.9	101.3	76.5	61.2	52.3	47.8	47.2	47.8	52.3	61.2
102.5°	228.0	148.0	107.9	85.2	71.4	62.9	59.0	57.9	59.0	62.9	71.4
105°	219.2	153.6	119.2	99.5	87.3	79.7	75.8	73.9	75.8	79.7	87.3
107.5°	218.7	164.0	133.9	115.5	104.1	96.6	92.9	91.0	92.9	96.6	104.1
110°	221.2	172.8	144.1	126.2	115.4	108.4	105.2	103.3	105.2	108.4	115.4



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	226.2	181.4	154.7	137.5	126.6	119.6	116.4	114.5	116.4	119.6	126.6
115°	234.6	195.7	171.5	154.3	143.4	137.1	133.2	130.7	133.2	137.1	143.4
117.5°	245.6	210.8	186.9	171.0	158.8	153.0	149.8	146.8	149.8	153.0	158.8
120°	253.7	220.5	197.6	181.6	169.6	163.1	160.0	158.1	160.0	163.1	169.6
122.5°	261.3	230.7	208.3	191.4	179.8	172.8	169.7	167.8	169.7	172.8	179.8
125°	273.5	245.4	223.1	205.9	193.8	186.8	183.0	181.6	183.0	186.8	193.8
127.5°	283.4	258.1	236.6	219.4	206.0	198.9	194.1	192.2	194.1	198.9	206.0
130°	290.0	265.8	244.8	227.6	214.2	206.5	200.8	198.9	200.8	206.5	214.2
132.5°	296.1	272.4	251.9	235.2	221.8	212.6	206.4	204.0	206.4	212.6	221.8
135°	304.0	282.3	262.6	245.4	232.0	222.5	215.5	212.9	215.5	222.5	232.0
137.5°	309.9	289.3	270.3	254.3	241.1	230.9	224.0	221.3	224.0	230.9	241.1
140°	313.0	293.8	275.3	259.4	246.7	236.5	230.1	226.9	230.1	236.5	246.7
142.5°	316.0	297.4	279.4	264.6	251.8	242.6	235.7	233.0	235.7	242.6	251.8
145°	319.4	302.1	285.6	270.9	260.1	250.5	244.8	242.9	244.8	250.5	260.1
147.5°	321.4	306.0	290.8	278.3	267.8	259.6	254.0	252.8	254.0	259.6	267.8
150°	321.9	308.5	293.8	282.3	273.5	265.1	260.1	259.4	260.1	265.1	273.5
152.5°	322.9	310.1	297.4	286.4	278.6	271.3	266.2	266.0	266.2	271.3	278.6
155°	323.2	313.0	302.1	293.2	286.2	279.8	276.0	276.0	276.0	279.8	286.2
157.5°	323.8	314.6	306.0	299.1	293.1	287.5	284.4	283.9	284.4	287.5	293.1
160°	323.8	316.2	308.5	302.1	297.7	292.6	290.0	290.0	290.0	292.6	297.7
162.5°	323.3	316.7	310.1	304.7	300.8	296.7	294.6	294.6	294.6	296.7	300.8
165°	321.9	317.4	312.3	307.9	305.3	302.1	300.8	301.5	300.8	302.1	305.3
167.5°	320.9	317.3	313.6	310.8	309.0	306.6	306.0	306.7	306.0	306.6	309.0
170°	319.4	316.8	313.6	312.3	311.0	309.2	308.5	309.8	308.5	309.2	311.0
172.5°	318.9	316.8	314.1	313.3	312.6	311.2	311.0	311.9	311.0	311.2	312.6
175°	317.4	316.2	314.9	314.2	314.2	313.0	313.6	314.2	313.6	313.0	314.2
177.5°	316.4	315.4	314.9	314.9	314.9	314.4	314.9	315.4	314.9	314.4	314.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	866.3	863.9	860.5	855.3	851.3	844.7	844.7	845.8	845.8	845.5	844.7
5°	840.0	833.6	825.9	816.9	807.6	798.2	796.5	793.0	790.5	788.8	786.6
7.5°	812.3	800.9	789.7	777.1	765.7	756.3	749.7	744.2	740.7	736.9	734.3
10°	793.4	779.3	766.1	752.9	738.4	726.9	719.7	714.5	710.7	707.3	705.6
12.5°	771.3	755.1	740.5	728.0	712.1	700.3	693.3	691.0	686.4	679.2	675.5
15°	738.8	723.9	706.4	687.2	679.5	665.0	656.9	653.1	650.4	644.9	643.2
17.5°	711.1	691.5	671.9	657.5	643.3	631.5	627.0	622.2	618.8	614.2	612.9
20°	688.9	671.4	653.5	638.1	623.1	610.3	606.5	603.1	599.7	597.5	595.8
22.5°	666.3	648.9	634.0	619.6	603.7	595.3	591.2	587.4	585.0	583.6	581.9
25°	634.7	619.3	602.7	589.9	577.1	571.5	568.9	566.8	565.1	563.0	562.6
27.5°	606.3	589.6	576.1	564.2	555.0	550.3	547.9	546.8	547.2	548.0	548.5
30°	585.1	569.8	558.7	548.5	540.0	535.7	535.2	535.2	537.0	537.4	538.3
32.5°	565.7	553.1	542.0	532.1	525.6	522.7	524.3	524.3	525.7	526.8	528.3
35°	537.4	526.3	517.7	509.2	503.7	504.9	505.8	506.6	508.7	511.4	513.1
37.5°	510.3	500.7	491.8	485.1	482.6	484.9	486.9	488.7	491.2	493.2	494.9
40°	490.8	483.6	475.1	469.0	469.9	471.2	473.0	475.1	477.2	478.5	480.2
42.5°	472.7	465.1	458.7	453.7	454.9	456.6	457.5	458.7	461.1	463.4	464.5
45°	445.2	439.2	433.3	430.2	431.1	431.9	432.8	434.1	436.2	437.9	438.4
47.5°	414.2	410.0	406.0	403.1	404.5	404.1	405.2	408.0	408.6	409.7	412.1
50°	394.4	390.5	385.9	385.0	385.0	385.0	385.4	388.8	388.8	390.5	392.2
52.5°	372.5	370.1	367.0	365.5	364.8	364.8	366.6	368.4	369.0	371.5	373.2
55°	340.1	337.6	335.1	333.8	332.9	333.8	337.2	338.0	340.1	341.4	342.8
57.5°	306.5	304.5	302.5	301.7	301.6	302.7	304.6	307.1	307.7	311.6	313.6
60°	284.3	281.3	279.6	279.6	278.8	282.6	281.7	286.0	286.8	289.3	292.4
62.5°	261.4	257.4	256.7	256.7	257.9	259.0	260.2	262.0	264.3	267.5	269.9
65°	224.5	222.4	225.3	224.9	224.0	226.7	226.7	228.8	231.3	234.3	239.0
67.5°	189.6	188.5	188.7	188.7	190.0	191.5	192.7	194.5	197.6	200.8	203.8
70°	166.0	167.3	165.2	166.9	168.2	168.6	169.4	172.0	175.5	177.6	181.0
72.5°	143.2	143.1	143.3	144.0	145.3	146.0	146.9	149.9	153.6	155.4	158.1
75°	110.1	109.7	111.0	111.0	113.1	114.0	114.8	116.1	119.5	122.1	124.2
77.5°	80.4	81.0	80.6	82.1	81.5	81.7	84.3	85.6	85.9	91.0	92.1
80°	60.6	61.5	61.9	62.3	62.8	61.9	64.9	66.1	66.1	69.1	71.3
82.5°	43.5	44.0	45.2	45.6	45.7	46.6	46.8	47.7	48.8	50.1	52.8
85°	21.8	23.1	23.5	23.1	23.5	22.6	23.9	24.3	24.8	24.8	24.8
87.5°	8.2	8.8	8.9	9.6	9.6	10.4	10.2	9.7	9.8	10.9	9.9
90°	7.0	8.3	10.2	12.1	14.0	15.9	15.3	15.9	16.6	17.2	18.5
92.5°	27.4	36.9	53.6	81.0	107.9	98.0	73.9	53.6	42.6	37.6	34.3
95°	58.0	82.8	137.1	232.0	336.6	378.0	306.6	229.5	155.6	121.7	98.8
97.5°	68.8	95.7	147.5	254.6	428.8	585.8	626.7	572.0	458.2	375.9	299.7
100°	76.5	101.3	145.9	240.3	408.0	603.6	729.2	751.5	699.9	625.3	534.8
102.5°	85.2	107.9	148.0	228.0	377.3	570.5	734.3	811.1	809.5	766.1	708.7
105°	99.5	119.2	153.6	219.2	339.7	512.5	695.5	828.7	892.3	904.5	887.9
107.5°	115.5	133.9	164.0	218.7	315.8	461.2	627.4	778.4	881.9	937.8	960.4
110°	126.2	144.1	172.8	221.2	306.6	432.2	584.5	730.5	847.7	928.1	972.7



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	137.5	154.7	181.4	226.2	301.5	412.8	547.3	683.1	802.9	892.9	950.2
115°	154.3	171.5	195.7	234.6	299.6	392.0	502.3	620.2	731.1	824.8	894.3
117.5°	171.0	186.9	210.8	245.6	300.8	379.8	475.2	574.7	670.4	754.6	825.1
120°	181.6	197.6	220.5	253.7	302.8	374.1	460.9	550.7	636.7	713.3	777.6
122.5°	191.4	208.3	230.7	261.3	306.3	370.6	449.1	531.9	609.8	680.6	740.5
125°	205.9	223.1	245.4	273.5	311.7	365.9	434.1	506.7	576.3	637.4	688.4
127.5°	219.4	236.6	258.1	283.4	317.8	363.6	420.9	484.9	546.7	602.0	648.4
130°	227.6	244.8	265.8	290.0	321.9	362.1	413.7	471.1	528.4	580.1	623.4
132.5°	235.2	251.9	272.4	296.1	325.0	361.5	407.1	458.3	511.1	559.1	600.5
135°	245.4	262.6	282.3	304.0	329.5	360.8	398.4	441.1	486.3	527.7	564.1
137.5°	254.3	270.3	289.3	309.9	332.6	359.4	390.9	425.4	462.5	498.2	529.7
140°	259.4	275.3	293.8	313.0	334.7	358.9	386.3	416.2	448.7	479.3	506.7
142.5°	264.6	279.4	297.4	316.0	336.1	357.8	382.2	407.6	435.5	462.0	485.8
145°	270.9	285.6	302.1	319.4	337.2	356.3	376.7	397.1	418.2	438.5	457.1
147.5°	278.3	290.8	306.0	321.4	337.2	353.9	371.4	388.6	405.3	421.8	434.9
150°	282.3	293.8	308.5	321.9	337.2	351.9	367.8	382.5	397.1	410.5	422.6
152.5°	286.4	297.4	310.1	322.9	335.7	349.3	363.7	376.8	389.5	401.3	411.4
155°	293.2	302.1	313.0	323.2	334.0	344.9	357.6	368.4	378.6	388.2	395.8
157.5°	299.1	306.0	314.6	323.8	331.8	340.9	350.7	359.5	368.0	375.4	381.4
160°	302.1	308.5	316.2	323.8	330.8	337.9	346.1	354.4	361.4	367.8	372.3
162.5°	304.7	310.1	316.7	323.3	328.8	334.8	341.5	348.3	354.2	360.1	364.1
165°	307.9	312.3	317.4	321.9	325.7	330.2	335.3	340.4	344.2	348.7	351.9
167.5°	310.8	313.6	317.3	320.9	322.7	325.6	329.3	333.5	336.4	339.0	341.3
170°	312.3	313.6	316.8	319.4	320.7	322.5	325.7	328.9	330.8	333.4	334.7
172.5°	313.3	314.1	316.8	318.9	319.1	320.0	322.1	324.8	326.2	328.2	329.1
175°	314.2	314.9	316.2	317.4	316.8	316.8	318.0	319.4	320.0	321.2	321.2
177.5°	314.9	314.9	315.4	316.4	315.4	314.9	315.4	315.9	316.4	316.9	316.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	842.4	842.0	844.4	842.7	844.4	842.0	842.4	844.7	845.5	845.8	845.8
5°	784.1	785.4	781.1	781.1	781.1	785.4	784.1	786.6	788.8	790.5	793.0
7.5°	732.1	730.3	730.4	728.1	730.4	730.3	732.1	734.3	736.9	740.7	744.2
10°	700.4	697.9	697.0	697.4	697.0	697.9	700.4	705.6	707.3	710.7	714.5
12.5°	674.1	673.6	668.0	668.1	668.0	673.6	674.1	675.5	679.2	686.4	691.0
15°	643.2	635.1	634.2	636.8	634.2	635.1	643.2	643.2	644.9	650.4	653.1
17.5°	612.2	608.0	608.2	606.9	608.2	608.0	612.2	612.9	614.2	618.8	622.2
20°	595.8	593.3	592.9	589.9	592.9	593.3	595.8	595.8	597.5	599.7	603.1
22.5°	580.8	580.0	580.2	576.9	580.2	580.0	580.8	581.9	583.6	585.0	587.4
25°	562.1	564.3	562.6	562.6	562.6	564.3	562.1	562.6	563.0	565.1	566.8
27.5°	549.5	549.4	548.5	548.5	548.5	549.4	549.5	548.5	548.0	547.2	546.8
30°	540.0	539.5	540.4	540.4	540.4	539.5	540.0	538.3	537.4	537.0	535.2
32.5°	530.4	531.0	531.2	531.5	531.2	531.0	530.4	528.3	526.8	525.7	524.3
35°	515.6	516.0	517.3	516.5	517.3	516.0	515.6	513.1	511.4	508.7	506.6
37.5°	495.6	497.6	497.2	497.8	497.2	497.6	495.6	494.9	493.2	491.2	488.7
40°	480.6	481.9	481.4	481.4	481.4	481.9	480.6	480.2	478.5	477.2	475.1
42.5°	465.2	466.2	465.0	464.4	465.0	466.2	465.2	464.5	463.4	461.1	458.7
45°	440.0	439.2	440.5	438.8	440.5	439.2	440.0	438.4	437.9	436.2	434.1
47.5°	411.9	412.7	413.1	414.3	413.1	412.7	411.9	412.1	409.7	408.6	408.0
50°	393.1	395.7	395.7	395.3	395.7	395.7	393.1	392.2	390.5	388.8	388.8
52.5°	374.6	375.9	377.6	377.5	377.6	375.9	374.6	373.2	371.5	369.0	368.4
55°	346.2	347.0	347.9	348.3	347.9	347.0	346.2	342.8	341.4	340.1	338.0
57.5°	316.6	316.3	318.3	318.9	318.3	316.3	316.6	313.6	311.6	307.7	307.1
60°	295.8	295.8	299.2	300.5	299.2	295.8	295.8	292.4	289.3	286.8	286.0
62.5°	273.6	275.0	278.3	276.5	278.3	275.0	273.6	269.9	267.5	264.3	262.0
65°	241.2	244.6	244.2	245.8	244.2	244.6	241.2	239.0	234.3	231.3	228.8
67.5°	207.2	209.4	212.5	212.7	212.5	209.4	207.2	203.8	200.8	197.6	194.5
70°	184.4	186.5	188.3	189.5	188.3	186.5	184.4	181.0	177.6	175.5	172.0
72.5°	162.2	163.3	167.4	165.6	167.4	163.3	162.2	158.1	155.4	153.6	149.9
75°	127.2	130.2	132.7	131.4	132.7	130.2	127.2	124.2	122.1	119.5	116.1
77.5°	94.1	97.0	98.2	97.2	98.2	97.0	94.1	92.1	91.0	85.9	85.6
80°	74.3	73.9	76.4	76.0	76.4	73.9	74.3	71.3	69.1	66.1	66.1
82.5°	54.5	54.1	55.2	55.5	55.2	54.1	54.5	52.8	50.1	48.8	47.7
85°	26.5	27.7	26.0	25.6	26.0	27.7	26.5	24.8	24.8	24.8	24.3
87.5°	9.7	9.9	9.6	9.1	9.6	9.9	9.7	9.9	10.9	9.8	9.7
90°	17.9	18.5	19.2	18.5	19.2	18.5	17.9	18.5	17.2	16.6	15.9
92.5°	33.2	31.2	31.9	30.7	31.9	31.2	33.2	34.3	37.6	42.6	53.6
95°	86.7	81.0	76.5	73.9	76.5	81.0	86.7	98.8	121.7	155.6	229.5
97.5°	252.7	224.0	206.8	201.3	206.8	224.0	252.7	299.7	375.9	458.2	572.0
100°	470.4	423.9	399.0	399.7	399.0	423.9	470.4	534.8	625.3	699.9	751.5
102.5°	658.6	621.7	601.0	586.3	601.0	621.7	658.6	708.7	766.1	809.5	811.1
105°	858.6	834.4	814.0	810.8	814.0	834.4	858.6	887.9	904.5	892.3	828.7
107.5°	961.0	952.8	945.9	940.0	945.9	952.8	961.0	960.4	937.8	881.9	778.4
110°	990.5	995.6	994.3	993.1	994.3	995.6	990.5	972.7	928.1	847.7	730.5



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	982.9	998.7	1003.6	1003.8	1003.6	998.7	982.9	950.2	892.9	802.9	683.1
115°	942.1	970.1	982.9	986.1	982.9	970.1	942.1	894.3	824.8	731.1	620.2
117.5°	874.9	907.0	925.4	929.8	925.4	907.0	874.9	825.1	754.6	670.4	574.7
120°	828.0	863.7	879.0	882.8	879.0	863.7	828.0	777.6	713.3	636.7	550.7
122.5°	785.1	817.3	834.1	838.9	834.1	817.3	785.1	740.5	680.6	609.8	531.9
125°	729.2	757.2	773.1	777.6	773.1	757.2	729.2	688.4	637.4	576.3	506.7
127.5°	684.7	708.7	723.1	727.2	723.1	708.7	684.7	648.4	602.0	546.7	484.9
130°	657.2	680.1	693.5	698.6	693.5	680.1	657.2	623.4	580.1	528.4	471.1
132.5°	632.2	655.2	667.0	670.6	667.0	655.2	632.2	600.5	559.1	511.1	458.3
135°	595.3	614.5	625.9	630.4	625.9	614.5	595.3	564.1	527.7	486.3	441.1
137.5°	556.0	575.4	585.1	588.0	585.1	575.4	556.0	529.7	498.2	462.5	425.4
140°	531.0	548.8	559.1	558.4	559.1	548.8	531.0	506.7	479.3	448.7	416.2
142.5°	506.5	522.3	531.5	530.8	531.5	522.3	506.5	485.8	462.0	435.5	407.6
145°	473.0	486.3	491.5	492.7	491.5	486.3	473.0	457.1	438.5	418.2	397.1
147.5°	446.9	456.0	460.9	461.4	460.9	456.0	446.9	434.9	421.8	405.3	388.6
150°	432.2	439.2	443.0	443.0	443.0	439.2	432.2	422.6	410.5	397.1	382.5
152.5°	418.9	425.4	427.7	427.7	427.7	425.4	418.9	411.4	401.3	389.5	376.8
155°	401.5	406.7	408.0	408.5	408.0	406.7	401.5	395.8	388.2	378.6	368.4
157.5°	386.4	390.2	391.3	391.1	391.3	390.2	386.4	381.4	375.4	368.0	359.5
160°	376.7	380.5	380.5	379.9	380.5	380.5	376.7	372.3	367.8	361.4	354.4
162.5°	367.0	370.3	370.3	369.7	370.3	370.3	367.0	364.1	360.1	354.2	348.3
165°	354.4	356.9	356.3	356.3	356.3	356.9	354.4	351.9	348.7	344.2	340.4
167.5°	342.4	344.2	343.6	343.6	343.6	344.2	342.4	341.3	339.0	336.4	333.5
170°	335.3	336.6	335.9	335.9	335.9	336.6	335.3	334.7	333.4	330.8	328.9
172.5°	329.1	330.4	329.3	328.8	329.3	330.4	329.1	329.1	328.2	326.2	324.8
175°	321.2	321.9	321.2	320.7	321.2	321.9	321.2	321.2	321.2	320.0	319.4
177.5°	316.4	316.9	315.9	315.9	315.9	316.9	316.4	316.9	316.9	316.4	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	844.7	844.7	851.3	855.3	860.5	863.9	866.3	868.7	872.8	878.2	884.4
5°	796.5	798.2	807.6	816.9	825.9	833.6	840.0	847.7	857.0	868.6	881.4
7.5°	749.7	756.3	765.7	777.1	789.7	800.9	812.3	824.9	838.1	855.1	873.0
10°	719.7	726.9	738.4	752.9	766.1	779.3	793.4	807.1	823.8	843.8	866.9
12.5°	693.3	700.3	712.1	728.0	740.5	755.1	771.3	789.0	807.7	831.8	858.0
15°	656.9	665.0	679.5	687.2	706.4	723.9	738.8	764.4	788.3	813.1	843.4
17.5°	627.0	631.5	643.3	657.5	671.9	691.5	711.1	732.5	756.3	786.5	824.4
20°	606.5	610.3	623.1	638.1	653.5	671.4	688.9	710.2	737.1	769.2	810.1
22.5°	591.2	595.3	603.7	619.6	634.0	648.9	666.3	691.8	720.4	751.7	796.1
25°	568.9	571.5	577.1	589.9	602.7	619.3	634.7	658.6	688.0	724.7	769.2
27.5°	547.9	550.3	555.0	564.2	576.1	589.6	606.3	626.6	656.6	696.4	743.6
30°	535.2	535.7	540.0	548.5	558.7	569.8	585.1	608.2	636.4	676.9	726.4
32.5°	524.3	522.7	525.6	532.1	542.0	553.1	565.7	588.4	615.6	655.4	706.3
35°	505.8	504.9	503.7	509.2	517.7	526.3	537.4	554.5	585.1	622.3	675.6
37.5°	486.9	484.9	482.6	485.1	491.8	500.7	510.3	525.5	552.0	592.9	643.9
40°	473.0	471.2	469.9	469.0	475.1	483.6	490.8	505.3	530.1	568.9	619.3
42.5°	457.5	456.6	454.9	453.7	458.7	465.1	472.7	485.6	510.3	546.7	594.4
45°	432.8	431.9	431.1	430.2	433.3	439.2	445.2	454.5	475.9	511.4	554.5
47.5°	405.2	404.1	404.5	403.1	406.0	410.0	414.2	424.3	444.7	473.4	504.8
50°	385.4	385.0	385.0	385.0	385.9	390.5	394.4	402.1	420.9	449.5	472.1
52.5°	366.6	364.8	364.8	365.5	367.0	370.1	372.5	380.9	397.3	420.8	441.3
55°	337.2	333.8	332.9	333.8	335.1	337.6	340.1	347.0	361.1	378.6	390.5
57.5°	304.6	302.7	301.6	301.7	302.5	304.5	306.5	313.9	325.0	334.1	341.8
60°	281.7	282.6	278.8	279.6	279.6	281.3	284.3	288.9	298.3	304.8	312.4
62.5°	260.2	259.0	257.9	256.7	256.7	257.4	261.4	265.1	273.0	276.4	282.4
65°	226.7	226.7	224.0	224.9	225.3	222.4	224.5	228.8	233.9	235.2	240.8
67.5°	192.7	191.5	190.0	188.7	188.7	188.5	189.6	191.8	195.6	196.0	200.2
70°	169.4	168.6	168.2	166.9	165.2	167.3	166.0	168.2	170.3	170.7	173.3
72.5°	146.9	146.0	145.3	144.0	143.3	143.1	143.2	145.6	147.1	146.5	149.4
75°	114.8	114.0	113.1	111.0	111.0	109.7	110.1	111.9	113.6	112.3	114.8
77.5°	84.3	81.7	81.5	82.1	80.6	81.0	80.4	80.1	81.0	81.0	83.3
80°	64.9	61.9	62.8	62.3	61.9	61.5	60.6	61.1	61.5	61.9	63.2
82.5°	46.8	46.6	45.7	45.6	45.2	44.0	43.5	44.3	44.8	44.5	45.4
85°	23.9	22.6	23.5	23.1	23.5	23.1	21.8	21.8	22.6	22.2	23.1
87.5°	10.2	10.4	9.6	9.6	8.9	8.8	8.2	8.3	8.3	8.0	8.5
90°	15.3	15.9	14.0	12.1	10.2	8.3	7.0	5.7	3.8	2.5	1.3
92.5°	73.9	98.0	107.9	81.0	53.6	36.9	27.4	22.1	17.1	11.7	7.9
95°	306.6	378.0	336.6	232.0	137.1	82.8	58.0	41.4	30.6	23.6	21.7
97.5°	626.7	585.8	428.8	254.6	147.5	95.7	68.8	52.5	43.1	37.6	36.9
100°	729.2	603.6	408.0	240.3	145.9	101.3	76.5	61.2	52.3	47.8	47.2
102.5°	734.3	570.5	377.3	228.0	148.0	107.9	85.2	71.4	62.9	59.0	57.9
105°	695.5	512.5	339.7	219.2	153.6	119.2	99.5	87.3	79.7	75.8	73.9
107.5°	627.4	461.2	315.8	218.7	164.0	133.9	115.5	104.1	96.6	92.9	91.0
110°	584.5	432.2	306.6	221.2	172.8	144.1	126.2	115.4	108.4	105.2	103.3



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	547.3	412.8	301.5	226.2	181.4	154.7	137.5	126.6	119.6	116.4	114.5
115°	502.3	392.0	299.6	234.6	195.7	171.5	154.3	143.4	137.1	133.2	130.7
117.5°	475.2	379.8	300.8	245.6	210.8	186.9	171.0	158.8	153.0	149.8	146.8
120°	460.9	374.1	302.8	253.7	220.5	197.6	181.6	169.6	163.1	160.0	158.1
122.5°	449.1	370.6	306.3	261.3	230.7	208.3	191.4	179.8	172.8	169.7	167.8
125°	434.1	365.9	311.7	273.5	245.4	223.1	205.9	193.8	186.8	183.0	181.6
127.5°	420.9	363.6	317.8	283.4	258.1	236.6	219.4	206.0	198.9	194.1	192.2
130°	413.7	362.1	321.9	290.0	265.8	244.8	227.6	214.2	206.5	200.8	198.9
132.5°	407.1	361.5	325.0	296.1	272.4	251.9	235.2	221.8	212.6	206.4	204.0
135°	398.4	360.8	329.5	304.0	282.3	262.6	245.4	232.0	222.5	215.5	212.9
137.5°	390.9	359.4	332.6	309.9	289.3	270.3	254.3	241.1	230.9	224.0	221.3
140°	386.3	358.9	334.7	313.0	293.8	275.3	259.4	246.7	236.5	230.1	226.9
142.5°	382.2	357.8	336.1	316.0	297.4	279.4	264.6	251.8	242.6	235.7	233.0
145°	376.7	356.3	337.2	319.4	302.1	285.6	270.9	260.1	250.5	244.8	242.9
147.5°	371.4	353.9	337.2	321.4	306.0	290.8	278.3	267.8	259.6	254.0	252.8
150°	367.8	351.9	337.2	321.9	308.5	293.8	282.3	273.5	265.1	260.1	259.4
152.5°	363.7	349.3	335.7	322.9	310.1	297.4	286.4	278.6	271.3	266.2	266.0
155°	357.6	344.9	334.0	323.2	313.0	302.1	293.2	286.2	279.8	276.0	276.0
157.5°	350.7	340.9	331.8	323.8	314.6	306.0	299.1	293.1	287.5	284.4	283.9
160°	346.1	337.9	330.8	323.8	316.2	308.5	302.1	297.7	292.6	290.0	290.0
162.5°	341.5	334.8	328.8	323.3	316.7	310.1	304.7	300.8	296.7	294.6	294.6
165°	335.3	330.2	325.7	321.9	317.4	312.3	307.9	305.3	302.1	300.8	301.5
167.5°	329.3	325.6	322.7	320.9	317.3	313.6	310.8	309.0	306.6	306.0	306.7
170°	325.7	322.5	320.7	319.4	316.8	313.6	312.3	311.0	309.2	308.5	309.8
172.5°	322.1	320.0	319.1	318.9	316.8	314.1	313.3	312.6	311.2	311.0	311.9
175°	318.0	316.8	316.8	317.4	316.2	314.9	314.2	314.2	313.0	313.6	314.2
177.5°	315.4	314.9	315.4	316.4	315.4	314.9	314.9	314.9	314.4	314.9	315.4
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	886.4	888.1	894.0	898.1	902.8	905.6	908.2	910.4	913.1	913.7	923.7
5°	890.4	898.9	913.9	925.0	938.6	953.5	963.8	968.5	980.8	991.1	1011.5
7.5°	889.2	907.4	929.9	953.3	978.4	1001.7	1021.8	1045.7	1062.7	1088.3	1113.4
10°	888.2	912.6	941.6	971.4	1006.5	1038.9	1067.9	1100.3	1127.2	1162.7	1192.9
12.5°	885.2	914.6	954.9	990.3	1032.7	1077.5	1120.5	1162.1	1185.9	1245.0	1272.8
15°	877.6	912.6	963.0	1016.7	1075.1	1128.1	1182.8	1226.3	1296.7	1348.3	1381.2
17.5°	863.1	912.1	971.8	1036.7	1107.7	1177.5	1239.4	1305.5	1380.1	1442.7	1509.3
20°	856.2	910.0	976.6	1048.3	1122.1	1201.1	1271.5	1350.9	1432.4	1493.9	1579.2
22.5°	843.6	904.5	976.2	1056.1	1135.1	1216.8	1299.2	1379.2	1473.4	1558.1	1639.3
25°	822.9	891.2	965.5	1054.7	1147.3	1229.2	1327.9	1434.1	1532.3	1641.1	1722.2
27.5°	801.2	874.2	948.6	1031.5	1131.1	1228.4	1352.4	1472.5	1592.6	1686.5	1746.5
30°	784.5	855.3	932.2	1015.9	1114.4	1230.1	1368.8	1499.8	1616.8	1697.5	1731.2
32.5°	766.4	838.3	906.2	994.0	1099.1	1229.1	1379.1	1515.9	1618.2	1671.9	1665.3
35°	738.0	798.2	864.3	948.8	1072.6	1221.6	1385.0	1517.4	1580.1	1568.6	1481.5
37.5°	697.0	747.6	812.8	905.3	1041.9	1205.7	1373.1	1472.3	1468.3	1374.4	1248.3
40°	671.4	714.5	777.2	874.6	1018.0	1195.6	1354.3	1418.8	1364.2	1233.1	1082.0
42.5°	638.0	677.6	740.4	840.4	991.6	1174.7	1318.4	1337.2	1230.3	1079.5	940.9
45°	586.0	621.0	685.9	789.2	952.3	1129.4	1230.9	1185.3	1041.5	885.7	780.2
47.5°	530.3	566.6	629.1	735.2	895.2	1061.2	1109.5	1012.4	864.7	738.4	641.6
50°	495.1	530.1	591.2	698.3	856.6	1005.2	1025.2	899.8	764.0	653.1	573.6
52.5°	459.6	492.5	552.5	660.1	811.5	940.3	927.9	800.1	675.2	580.7	518.4
55°	406.8	437.9	495.1	595.8	733.7	835.7	790.9	668.9	565.6	492.1	444.7
57.5°	359.5	389.4	438.7	529.7	649.5	719.7	662.6	559.7	477.6	421.1	385.8
60°	327.3	353.8	400.8	485.3	589.5	642.8	586.4	495.5	426.4	381.2	349.6
62.5°	297.0	320.0	363.5	440.3	530.7	575.5	518.5	441.6	382.7	342.6	315.8
65°	250.9	271.9	310.3	370.1	444.3	474.2	425.1	362.8	317.2	287.2	269.3
67.5°	209.0	226.7	259.9	307.0	361.6	383.4	346.0	297.7	263.3	239.4	225.1
70°	181.0	196.3	222.4	262.9	312.4	329.1	294.1	254.4	229.2	210.0	196.7
72.5°	157.4	168.7	192.3	223.6	265.0	278.2	253.8	218.9	195.4	181.0	170.5
75°	119.9	129.3	144.7	169.9	198.4	206.2	187.8	166.0	150.3	140.0	131.9
77.5°	86.5	93.4	104.5	120.0	139.8	146.8	135.1	120.6	109.1	102.2	97.7
80°	65.3	70.8	80.2	93.0	105.0	108.8	102.0	90.9	82.8	79.0	75.1
82.5°	48.3	51.4	57.0	65.7	73.9	78.4	72.6	66.0	61.6	58.1	56.7
85°	24.3	26.0	28.6	32.0	37.1	38.8	36.7	35.0	32.4	30.3	30.3
87.5°	9.4	9.6	11.1	12.0	13.6	15.0	15.1	14.8	14.8	14.3	14.1
90°	2.5	3.8	5.7	7.0	8.3	10.2	12.1	14.0	15.9	15.3	15.9
92.5°	11.7	17.1	22.1	27.4	36.9	53.6	81.0	107.9	98.0	73.9	53.6
95°	23.6	30.6	41.4	58.0	82.8	137.1	232.0	336.6	378.0	306.6	229.5
97.5°	37.6	43.1	52.5	68.8	95.7	147.5	254.6	428.8	585.8	626.7	572.0
100°	47.8	52.3	61.2	76.5	101.3	145.9	240.3	408.0	603.6	729.2	751.5
102.5°	59.0	62.9	71.4	85.2	107.9	148.0	228.0	377.3	570.5	734.3	811.1
105°	75.8	79.7	87.3	99.5	119.2	153.6	219.2	339.7	512.5	695.5	828.7
107.5°	92.9	96.6	104.1	115.5	133.9	164.0	218.7	315.8	461.2	627.4	778.4
110°	105.2	108.4	115.4	126.2	144.1	172.8	221.2	306.6	432.2	584.5	730.5



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	116.4	119.6	126.6	137.5	154.7	181.4	226.2	301.5	412.8	547.3	683.1
115°	133.2	137.1	143.4	154.3	171.5	195.7	234.6	299.6	392.0	502.3	620.2
117.5°	149.8	153.0	158.8	171.0	186.9	210.8	245.6	300.8	379.8	475.2	574.7
120°	160.0	163.1	169.6	181.6	197.6	220.5	253.7	302.8	374.1	460.9	550.7
122.5°	169.7	172.8	179.8	191.4	208.3	230.7	261.3	306.3	370.6	449.1	531.9
125°	183.0	186.8	193.8	205.9	223.1	245.4	273.5	311.7	365.9	434.1	506.7
127.5°	194.1	198.9	206.0	219.4	236.6	258.1	283.4	317.8	363.6	420.9	484.9
130°	200.8	206.5	214.2	227.6	244.8	265.8	290.0	321.9	362.1	413.7	471.1
132.5°	206.4	212.6	221.8	235.2	251.9	272.4	296.1	325.0	361.5	407.1	458.3
135°	215.5	222.5	232.0	245.4	262.6	282.3	304.0	329.5	360.8	398.4	441.1
137.5°	224.0	230.9	241.1	254.3	270.3	289.3	309.9	332.6	359.4	390.9	425.4
140°	230.1	236.5	246.7	259.4	275.3	293.8	313.0	334.7	358.9	386.3	416.2
142.5°	235.7	242.6	251.8	264.6	279.4	297.4	316.0	336.1	357.8	382.2	407.6
145°	244.8	250.5	260.1	270.9	285.6	302.1	319.4	337.2	356.3	376.7	397.1
147.5°	254.0	259.6	267.8	278.3	290.8	306.0	321.4	337.2	353.9	371.4	388.6
150°	260.1	265.1	273.5	282.3	293.8	308.5	321.9	337.2	351.9	367.8	382.5
152.5°	266.2	271.3	278.6	286.4	297.4	310.1	322.9	335.7	349.3	363.7	376.8
155°	276.0	279.8	286.2	293.2	302.1	313.0	323.2	334.0	344.9	357.6	368.4
157.5°	284.4	287.5	293.1	299.1	306.0	314.6	323.8	331.8	340.9	350.7	359.5
160°	290.0	292.6	297.7	302.1	308.5	316.2	323.8	330.8	337.9	346.1	354.4
162.5°	294.6	296.7	300.8	304.7	310.1	316.7	323.3	328.8	334.8	341.5	348.3
165°	300.8	302.1	305.3	307.9	312.3	317.4	321.9	325.7	330.2	335.3	340.4
167.5°	306.0	306.6	309.0	310.8	313.6	317.3	320.9	322.7	325.6	329.3	333.5
170°	308.5	309.2	311.0	312.3	313.6	316.8	319.4	320.7	322.5	325.7	328.9
172.5°	311.0	311.2	312.6	313.3	314.1	316.8	318.9	319.1	320.0	322.1	324.8
175°	313.6	313.0	314.2	314.2	314.9	316.2	317.4	316.8	316.8	318.0	319.4
177.5°	314.9	314.4	314.9	314.9	314.9	315.4	316.4	315.4	314.9	315.4	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9	314.9



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	880.9	880.9	880.9	880.9	880.9	880.9	880.9
2.5°	927.1	927.4	931.2	933.9	932.5	934.3	934.9
5°	1012.8	1028.3	1036.3	1042.3	1042.8	1043.2	1046.6
7.5°	1134.5	1151.0	1163.0	1181.3	1186.7	1192.9	1191.2
10°	1223.3	1247.6	1268.5	1279.6	1291.6	1309.0	1295.0
12.5°	1306.3	1349.4	1381.2	1398.5	1409.7	1413.2	1406.3
15°	1443.1	1499.4	1529.7	1528.8	1567.3	1584.0	1557.9
17.5°	1568.6	1620.6	1662.2	1683.6	1715.6	1722.6	1719.4
20°	1645.4	1702.2	1734.6	1771.3	1788.0	1802.9	1805.5
22.5°	1711.6	1762.6	1797.4	1828.0	1841.9	1849.0	1853.3
25°	1779.9	1820.0	1840.9	1851.5	1855.4	1854.6	1849.0
27.5°	1775.2	1778.2	1755.2	1732.6	1712.4	1689.5	1681.7
30°	1729.1	1693.2	1629.2	1592.9	1539.5	1497.3	1514.3
32.5°	1607.9	1536.5	1464.6	1385.3	1319.6	1301.0	1282.1
35°	1372.2	1246.8	1173.4	1087.9	1053.9	1019.7	996.2
37.5°	1110.2	1013.1	926.0	870.2	836.0	814.4	802.7
40°	959.9	872.5	800.7	755.5	729.4	705.2	701.7
42.5°	840.1	758.7	704.7	668.7	643.8	633.4	625.9
45°	688.0	631.3	595.0	569.4	552.8	546.3	537.8
47.5°	582.4	542.3	515.0	497.6	485.0	480.3	479.6
50°	523.3	490.0	469.9	456.2	446.5	444.7	437.9
52.5°	478.9	450.0	434.4	422.5	415.4	410.6	408.5
55°	415.7	396.5	382.5	375.6	370.1	365.3	365.3
57.5°	363.7	347.7	338.3	332.6	330.8	327.5	325.4
60°	331.7	318.0	310.7	305.6	302.2	302.6	298.8
62.5°	300.2	291.4	284.5	279.3	275.2	275.3	275.6
65°	255.7	248.8	243.7	242.0	239.5	236.4	237.3
67.5°	216.6	210.3	206.3	203.3	202.5	200.9	203.3
70°	188.7	183.9	181.0	178.4	177.6	178.0	180.1
72.5°	163.1	159.7	157.8	156.5	154.7	154.7	156.2
75°	128.1	125.5	123.8	122.5	122.1	122.1	122.1
77.5°	94.1	93.5	92.7	90.8	90.9	91.4	91.5
80°	74.3	73.0	72.6	71.7	70.4	69.5	71.7
82.5°	55.5	54.2	53.8	53.6	51.6	51.4	53.2
85°	29.8	28.6	29.0	28.6	28.6	28.2	28.2
87.5°	13.9	13.7	13.6	13.8	13.6	13.4	13.9
90°	16.6	17.2	18.5	17.9	18.5	19.2	18.5
92.5°	42.6	37.6	34.3	33.2	31.2	31.9	30.7
95°	155.6	121.7	98.8	86.7	81.0	76.5	73.9
97.5°	458.2	375.9	299.7	252.7	224.0	206.8	201.3
100°	699.9	625.3	534.8	470.4	423.9	399.0	399.7
102.5°	809.5	766.1	708.7	658.6	621.7	601.0	586.3
105°	892.3	904.5	887.9	858.6	834.4	814.0	810.8
107.5°	881.9	937.8	960.4	961.0	952.8	945.9	940.0
110°	847.7	928.1	972.7	990.5	995.6	994.3	993.1



TEST NUMBER: P331975-930

CATALOG NUMBER: S123DIP-S775D805U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	802.9	892.9	950.2	982.9	998.7	1003.6	1003.8
115°	731.1	824.8	894.3	942.1	970.1	982.9	986.1
117.5°	670.4	754.6	825.1	874.9	907.0	925.4	929.8
120°	636.7	713.3	777.6	828.0	863.7	879.0	882.8
122.5°	609.8	680.6	740.5	785.1	817.3	834.1	838.9
125°	576.3	637.4	688.4	729.2	757.2	773.1	777.6
127.5°	546.7	602.0	648.4	684.7	708.7	723.1	727.2
130°	528.4	580.1	623.4	657.2	680.1	693.5	698.6
132.5°	511.1	559.1	600.5	632.2	655.2	667.0	670.6
135°	486.3	527.7	564.1	595.3	614.5	625.9	630.4
137.5°	462.5	498.2	529.7	556.0	575.4	585.1	588.0
140°	448.7	479.3	506.7	531.0	548.8	559.1	558.4
142.5°	435.5	462.0	485.8	506.5	522.3	531.5	530.8
145°	418.2	438.5	457.1	473.0	486.3	491.5	492.7
147.5°	405.3	421.8	434.9	446.9	456.0	460.9	461.4
150°	397.1	410.5	422.6	432.2	439.2	443.0	443.0
152.5°	389.5	401.3	411.4	418.9	425.4	427.7	427.7
155°	378.6	388.2	395.8	401.5	406.7	408.0	408.5
157.5°	368.0	375.4	381.4	386.4	390.2	391.3	391.1
160°	361.4	367.8	372.3	376.7	380.5	380.5	379.9
162.5°	354.2	360.1	364.1	367.0	370.3	370.3	369.7
165°	344.2	348.7	351.9	354.4	356.9	356.3	356.3
167.5°	336.4	339.0	341.3	342.4	344.2	343.6	343.6
170°	330.8	333.4	334.7	335.3	336.6	335.9	335.9
172.5°	326.2	328.2	329.1	329.1	330.4	329.3	328.8
175°	320.0	321.2	321.2	321.2	321.9	321.2	320.7
177.5°	316.4	316.9	316.9	316.4	316.9	315.9	315.9
180°	314.9	314.9	314.9	314.9	314.9	314.9	314.9

(END OF REPORT)