

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332351-930

Luminaire Tested: **S123RDIP-S1000D1025U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332351-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1025U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6434.3 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332351-930

CATALOG NUMBER: S123RDIP-S1000D1025U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332351-930

CATALOG NUMBER: S123RDIP-S1000D1025U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48				48
1	98	93	90	86	90	86	83	80	73	70	68	60	58	57	49	47	47	41				41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35				35
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30				30
4	75	64	56	51	69	59	53	47	51	45	41	42	38	35	35	32	30	26				26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23				23
6	63	51	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20				20
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21	18				18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18	16				16
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15				15
10	47	35	28	24	44	33	27	22	29	24	20	25	20	18	21	17	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14727	14727	14727
5°	14783	14579	14664
10°	14700	14397	14348
15°	14542	14060	13912
20°	14325	13639	13321
25°	14101	13166	12744
30°	13806	12621	11931
35°	13502	12073	11184
40°	13222	11428	10260
45°	12855	10794	9426
50°	12450	10071	8492
55°	12037	9246	7621
60°	11657	8361	6665
65°	11163	7404	5708
70°	10546	6216	4611
75°	9649	4891	4338
80°	8598	4333	3986
85°	7262	3841	3569



TEST NUMBER: P332351-930

CATALOG NUMBER: S123RDIP-S1000D1025U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.5	2.0
10°-20°	357.5	5.6
20°-30°	514.7	8.0
30°-40°	579.8	9.0
40°-50°	554.7	8.6
50°-60°	454.2	7.1
60°-70°	306.5	4.8
70°-80°	154.2	2.4
80°-90°	43.9	0.7
90°-100°	39.8	0.6
100°-110°	189.8	2.9
110°-120°	455.9	7.1
120°-130°	580.5	9.0
130°-140°	620.3	9.6
140°-150°	580.0	9.0
150°-160°	467.9	7.3
160°-170°	302.0	4.7
170°-180°	104.1	1.6
0°-30°	1000.7	15.6
0°-40°	1580.5	24.6
0°-60°	2589.5	40.2
0°-90°	3094.0	48.1
90°-120°	685.5	10.7
90°-150°	2466.4	38.3
90°-180°	3340.0	51.9
0°-180°	6434.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1368	1368	1368	1368	1368	
5°	1368	1362	1349	1359	1357	130
15°	1305	1292	1262	1256	1248	367
25°	1187	1158	1109	1086	1073	546
35°	1028	986	919	873	851	643
45°	844	793	709	648	619	651
55°	641	585	493	431	406	575
65°	438	376	291	239	224	434
75°	232	178	118	107	104	247
85°	59	36	31	29	29	66
90°	1	9	20	23	24	5
95°	50	19	25	31	31	61
105°	242	247	178	42	36	257
115°	455	460	467	475	478	449
125°	641	648	651	653	654	572
135°	798	803	806	809	806	614
145°	921	927	928	930	930	576
155°	1015	1013	1014	1018	1013	467
165°	1070	1068	1067	1073	1068	302
175°	1095	1092	1092	1097	1091	104
180°	1095	1095	1095	1095	1095	



TEST NUMBER: P332351-930

CATALOG NUMBER: S123RDIP-S1000D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1372.6	1371.8	1371.1	1370.3	1369.5	1367.9	1365.5	1363.2	1360.8	1358.5	1360.6
5°	1368.2	1366.9	1365.7	1364.5	1363.3	1361.1	1358.2	1355.3	1352.3	1349.3	1351.5
7.5°	1355.5	1354.2	1352.9	1351.5	1350.2	1347.6	1343.8	1339.9	1336.1	1332.3	1333.5
10°	1344.9	1343.2	1341.4	1339.7	1338.0	1334.9	1330.5	1326.0	1321.6	1317.2	1317.4
12.5°	1329.8	1327.9	1326.0	1324.0	1322.1	1318.4	1313.0	1307.6	1302.2	1296.7	1296.6
15°	1305.0	1302.3	1299.5	1296.8	1294.1	1289.3	1282.4	1275.5	1268.6	1261.7	1260.5
17.5°	1273.7	1270.5	1267.4	1264.2	1261.0	1255.1	1246.3	1237.5	1228.7	1219.9	1217.3
20°	1250.6	1246.7	1242.7	1238.8	1234.8	1228.2	1218.8	1209.4	1200.0	1190.7	1187.5
22.5°	1224.8	1220.3	1215.8	1211.2	1206.7	1199.5	1189.4	1179.5	1169.5	1159.6	1155.6
25°	1187.3	1181.2	1175.0	1168.8	1162.7	1153.9	1142.6	1131.2	1119.9	1108.6	1103.3
27.5°	1141.8	1135.1	1128.2	1121.4	1114.6	1104.9	1092.3	1079.6	1067.0	1054.4	1047.2
30°	1110.8	1103.3	1096.0	1088.6	1081.2	1070.6	1056.8	1042.9	1029.2	1015.4	1007.0
32.5°	1079.7	1071.3	1062.9	1054.5	1046.2	1034.7	1020.1	1005.5	990.8	976.2	967.1
35°	1027.5	1018.6	1009.7	1000.9	992.1	979.9	964.7	949.3	934.1	918.8	908.2
37.5°	974.7	964.8	955.0	945.1	935.2	922.2	905.9	889.5	873.2	856.9	844.8
40°	941.0	930.2	919.2	908.4	897.6	883.4	865.9	848.4	830.9	813.3	800.5
42.5°	902.8	891.9	881.1	870.3	859.4	845.0	826.9	808.8	790.7	772.6	758.6
45°	844.5	833.3	822.2	811.1	800.1	785.1	766.1	747.1	728.1	709.1	695.0
47.5°	786.1	773.9	761.7	749.5	737.4	721.8	702.8	683.8	664.8	645.8	630.6
50°	743.5	731.9	720.3	708.7	697.1	681.3	661.4	641.4	621.4	601.4	586.1
52.5°	705.3	692.8	680.1	667.6	655.0	638.8	619.1	599.2	579.5	559.7	543.8
55°	641.4	629.3	617.2	605.1	593.0	576.5	555.5	534.6	513.6	492.7	478.4
57.5°	582.4	569.2	556.0	542.8	529.7	512.6	491.5	470.4	449.4	428.4	414.8
60°	541.5	528.0	514.4	500.8	487.2	470.3	449.8	429.3	408.9	388.4	375.0
62.5°	500.7	487.1	473.5	460.0	446.5	429.4	409.0	388.5	368.0	347.6	335.0
65°	438.3	424.8	411.2	397.6	384.1	367.7	348.5	329.2	310.0	290.7	278.7
67.5°	375.9	362.2	348.5	334.8	321.1	305.0	286.6	268.2	249.7	231.2	222.3
70°	335.1	321.8	308.5	295.1	281.8	266.6	249.3	232.0	214.7	197.5	188.9
72.5°	294.2	281.2	268.1	254.9	241.8	227.4	211.7	196.1	180.3	164.7	157.6
75°	232.0	220.0	208.2	196.4	184.6	171.9	158.3	144.7	131.2	117.6	115.1
77.5°	175.1	164.4	153.7	143.0	132.3	122.5	113.8	105.1	96.4	87.6	86.3
80°	138.7	128.6	118.5	108.4	98.2	90.7	85.4	80.2	75.1	69.9	69.1
82.5°	104.1	95.4	86.7	77.9	69.1	63.6	61.1	58.8	56.3	53.9	53.2
85°	58.8	53.4	47.9	42.6	37.1	34.0	33.3	32.5	31.8	31.1	30.6
87.5°	21.4	19.6	17.9	16.1	14.3	13.5	14.0	14.5	15.0	15.4	15.4
90°	0.8	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2
92.5°	15.2	14.6	14.1	13.6	13.1	13.8	15.5	17.3	19.1	20.9	22.0
95°	49.7	42.2	34.8	27.4	20.0	17.3	19.2	21.3	23.2	25.2	26.5
97.5°	99.8	96.4	93.1	89.8	86.4	78.3	65.3	52.3	39.2	26.2	27.6
100°	137.5	141.1	144.8	148.4	152.0	139.7	111.5	83.2	55.0	26.8	28.3
102.5°	180.5	183.1	185.7	188.3	190.9	176.8	146.0	115.2	84.4	53.6	49.1
105°	242.5	244.5	246.5	248.5	250.5	243.3	227.1	210.8	194.5	178.2	146.2
107.5°	307.9	309.6	311.1	312.7	314.3	316.4	318.9	321.6	324.1	326.7	303.2
110°	351.6	353.0	354.4	355.9	357.3	359.1	361.0	363.1	365.0	367.0	361.0



TEST NUMBER: P332351-930

CATALOG NUMBER: S123RDIP-S1000D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.2	394.5	395.8	397.1	398.4	400.1	402.1	404.1	406.0	408.1	408.1
115°	454.9	456.0	457.1	458.2	459.3	460.6	462.2	463.8	465.5	467.1	469.0
117.5°	514.6	516.0	517.3	518.7	520.0	521.1	521.9	522.8	523.6	524.4	525.9
120°	551.7	553.3	555.0	556.6	558.2	559.4	559.9	560.4	561.0	561.5	563.0
122.5°	589.5	590.8	592.2	593.5	594.8	595.9	596.6	597.3	597.9	598.6	599.7
125°	641.2	642.7	644.2	645.6	647.0	648.2	648.9	649.5	650.3	651.0	651.4
127.5°	691.4	692.8	694.3	695.7	697.2	698.3	699.2	700.1	700.9	701.8	702.4
130°	722.7	724.1	725.5	727.0	728.5	729.5	730.3	731.0	731.6	732.4	733.1
132.5°	752.6	754.1	755.5	756.9	758.4	759.4	759.9	760.5	761.2	761.7	762.5
135°	798.3	799.4	800.5	801.6	802.7	803.6	804.3	805.0	805.8	806.5	807.0
137.5°	837.4	838.8	840.2	841.6	842.9	843.8	844.2	844.6	845.0	845.4	846.2
140°	863.4	864.5	865.6	866.7	867.8	868.6	869.1	869.7	870.3	870.7	871.5
142.5°	887.5	888.6	889.7	890.8	891.9	892.7	893.2	893.7	894.3	894.9	895.4
145°	921.2	922.5	923.7	925.0	926.3	927.1	927.5	927.8	928.1	928.5	928.9
147.5°	952.9	953.8	954.6	955.4	956.3	956.8	957.2	957.6	958.0	958.3	958.7
150°	972.5	973.1	973.5	974.1	974.6	975.1	975.4	975.8	976.2	976.6	976.9
152.5°	990.0	990.3	990.6	990.8	991.1	991.3	991.5	991.7	992.0	992.1	992.8
155°	1014.8	1014.4	1014.1	1013.7	1013.3	1013.3	1013.4	1013.6	1013.8	1014.0	1014.9
157.5°	1034.0	1034.0	1034.0	1033.9	1033.9	1033.7	1033.6	1033.4	1033.2	1033.0	1034.1
160°	1045.7	1045.5	1045.4	1045.2	1045.0	1044.8	1044.6	1044.5	1044.2	1044.1	1045.2
162.5°	1056.8	1056.3	1055.8	1055.4	1054.9	1054.6	1054.4	1054.2	1054.0	1053.9	1055.1
165°	1070.2	1069.6	1069.0	1068.5	1068.0	1067.6	1067.4	1067.2	1067.1	1066.9	1068.3
167.5°	1080.5	1079.9	1079.1	1078.4	1077.7	1077.3	1077.3	1077.3	1077.3	1077.3	1078.7
170°	1086.4	1085.7	1085.0	1084.3	1083.5	1083.1	1083.1	1083.1	1083.1	1083.1	1084.6
172.5°	1090.3	1089.5	1088.6	1087.7	1086.9	1086.5	1086.6	1086.8	1086.9	1087.0	1088.5
175°	1095.4	1094.5	1093.6	1092.7	1091.8	1091.4	1091.5	1091.8	1091.9	1092.1	1093.4
177.5°	1096.7	1095.9	1095.2	1094.5	1093.8	1093.5	1093.6	1093.8	1093.9	1094.1	1095.2
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332351-930

CATALOG NUMBER: S123RDIP-S1000D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1362.8	1365.0	1367.1	1368.0	1367.6	1367.3	1366.8	1366.4
5°	1353.8	1356.0	1358.2	1359.1	1358.6	1358.1	1357.6	1357.1
7.5°	1334.7	1335.9	1337.2	1337.4	1336.5	1335.7	1334.9	1334.0
10°	1317.7	1317.9	1318.2	1317.7	1316.4	1315.2	1313.9	1312.7
12.5°	1296.4	1296.3	1296.2	1295.3	1294.0	1292.5	1291.1	1289.6
15°	1259.2	1258.0	1256.8	1255.2	1253.5	1251.8	1250.1	1248.4
17.5°	1214.7	1212.1	1209.5	1206.9	1204.4	1201.8	1199.2	1196.6
20°	1184.2	1181.0	1177.9	1174.8	1171.8	1168.8	1165.9	1162.9
22.5°	1151.6	1147.6	1143.6	1140.2	1137.5	1134.7	1132.0	1129.2
25°	1098.2	1093.0	1087.9	1083.9	1081.2	1078.5	1075.8	1073.0
27.5°	1040.0	1032.8	1025.6	1019.9	1015.8	1011.6	1007.5	1003.4
30°	998.6	990.2	981.8	975.7	971.7	967.8	963.8	959.9
32.5°	957.9	948.8	939.6	932.9	928.8	924.6	920.5	916.3
35°	897.6	887.0	876.4	868.9	864.5	860.0	855.6	851.1
37.5°	832.8	820.8	808.8	800.0	794.5	789.0	783.6	778.1
40°	787.7	774.9	762.1	752.8	747.1	741.5	735.8	730.2
42.5°	744.5	730.5	716.5	706.9	701.9	696.8	691.7	686.6
45°	680.9	666.9	652.8	642.9	636.9	631.0	625.1	619.2
47.5°	615.2	600.0	584.7	574.4	569.1	563.9	558.6	553.3
50°	570.9	555.5	540.3	529.8	524.2	518.4	512.8	507.1
52.5°	528.0	512.1	496.2	485.7	480.6	475.6	470.5	465.4
55°	464.1	449.8	435.5	425.8	420.9	416.0	411.1	406.1
57.5°	401.3	387.8	374.3	365.4	361.3	357.0	352.9	348.6
60°	361.7	348.5	335.1	326.4	322.2	318.0	313.8	309.6
62.5°	322.5	310.0	297.4	288.9	284.6	280.2	275.8	271.4
65°	266.6	254.5	242.4	235.0	232.3	229.6	226.9	224.1
67.5°	213.2	204.2	195.2	189.1	186.3	183.4	180.4	177.6
70°	180.3	171.6	163.0	157.4	154.6	151.9	149.2	146.5
72.5°	150.6	143.5	136.5	132.4	131.3	130.1	129.0	127.8
75°	112.7	110.2	107.8	106.3	105.8	105.3	104.8	104.3
77.5°	85.0	83.6	82.3	81.4	81.0	80.5	80.0	79.5
80°	68.4	67.7	66.9	66.4	65.9	65.4	64.8	64.3
82.5°	52.4	51.7	51.0	50.5	50.5	50.4	50.2	50.1
85°	30.1	29.6	29.1	28.9	28.9	28.9	28.9	28.9
87.5°	15.3	15.3	15.2	15.2	15.0	14.9	14.8	14.7
90°	21.0	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	23.2	24.3	25.4	26.2	26.3	26.6	26.8	27.0
95°	27.7	29.0	30.3	30.9	30.9	30.9	30.9	30.9
97.5°	29.1	30.6	32.0	32.8	33.0	33.2	33.3	33.5
100°	29.8	31.2	32.6	33.4	33.7	33.8	34.0	34.2
102.5°	44.6	40.1	35.6	33.5	33.8	34.2	34.5	34.8
105°	114.2	82.2	50.2	34.3	34.7	35.1	35.5	35.8
107.5°	279.7	256.2	232.8	209.0	184.8	160.7	136.6	112.4
110°	355.1	349.1	343.2	327.3	301.3	275.5	249.6	223.8



TEST NUMBER: P332351-930

CATALOG NUMBER: S123RDIP-S1000D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	408.2	408.4	408.5	405.8	400.3	394.8	389.4	383.9
115°	470.8	472.5	474.3	475.6	476.3	477.0	477.8	478.5
117.5°	527.3	528.7	530.2	531.0	531.2	531.2	531.4	531.6
120°	564.4	565.8	567.3	568.0	568.0	568.0	568.0	568.0
122.5°	600.6	601.7	602.7	603.2	603.4	603.6	603.6	603.8
125°	651.8	652.1	652.5	652.8	653.2	653.5	654.0	654.3
127.5°	703.0	703.5	704.1	704.3	703.8	703.5	703.1	702.8
130°	733.9	734.6	735.3	735.5	735.2	734.7	734.4	734.0
132.5°	763.1	763.9	764.6	764.7	764.2	763.7	763.2	762.7
135°	807.6	808.1	808.6	808.6	808.1	807.6	807.0	806.5
137.5°	847.1	848.0	848.8	849.1	848.7	848.4	848.0	847.7
140°	872.2	872.9	873.7	873.8	873.4	873.1	872.8	872.4
142.5°	896.0	896.6	897.2	897.2	896.7	896.2	895.7	895.2
145°	929.3	929.6	930.0	930.2	930.2	930.2	930.2	930.2
147.5°	959.0	959.4	959.8	959.5	958.7	957.9	957.0	956.2
150°	977.3	977.6	978.0	977.9	977.4	976.8	976.2	975.8
152.5°	993.4	994.1	994.7	994.7	993.8	993.0	992.2	991.3
155°	1015.8	1016.7	1017.6	1017.5	1016.4	1015.4	1014.2	1013.2
157.5°	1035.2	1036.2	1037.4	1037.2	1035.8	1034.4	1033.0	1031.6
160°	1046.3	1047.3	1048.4	1048.3	1047.1	1045.8	1044.6	1043.3
162.5°	1056.3	1057.5	1058.7	1058.8	1057.7	1056.5	1055.5	1054.3
165°	1069.8	1071.2	1072.7	1072.8	1071.5	1070.2	1068.9	1067.7
167.5°	1080.2	1081.7	1083.0	1083.0	1081.7	1080.2	1078.7	1077.3
170°	1086.1	1087.5	1088.9	1088.9	1087.5	1086.1	1084.6	1083.1
172.5°	1090.0	1091.4	1092.8	1092.7	1091.2	1089.6	1088.0	1086.4
175°	1094.6	1095.9	1097.1	1097.1	1095.6	1094.2	1092.7	1091.3
177.5°	1096.3	1097.6	1098.7	1098.5	1097.1	1095.7	1094.2	1092.7
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4

(END OF REPORT)