

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332356-930

Luminaire Tested: **S123RDIP-S1000D1195U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332356-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1195 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6751.3 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	94	90	87	90	86	83	81	73	71	69	60	59	57	49	48	47	41
2	90	83	77	72	82	76	71	67	64	61	58	54	51	49	44	42	40	36
3	82	73	66	60	75	68	61	57	57	53	49	48	45	42	39	37	35	31
4	75	65	57	52	69	60	54	48	51	46	42	43	39	36	35	33	31	27
5	69	58	50	45	64	54	47	42	46	41	37	39	35	32	32	29	27	24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	29	26	24	21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	21	19
8	55	43	36	30	51	40	33	29	35	29	26	30	25	22	25	22	19	17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	15
10	48	36	29	24	44	34	28	23	29	24	21	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13951	13951	13951	13951
5°	16630	14011	12337	14011
10°	20764	13930	11146	13930
15°	24373	13788	10165	13788
20°	27202	13575	9330	13575
25°	26766	13351	8817	13351
30°	19240	13144	8289	13144
35°	12846	12875	7947	12875
40°	9465	12552	7593	12552
45°	7939	11985	7247	11985
50°	7005	11241	6764	11241
55°	6142	10393	6101	10393
60°	5470	9580	5591	9580
65°	4806	8706	5201	8706
70°	3770	7928	4749	7928
75°	3323	6924	4338	6924
80°	2889	5883	4265	5883
85°	2322	4730	4520	4730



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.5	1.9
10°-20°	398.2	5.9
20°-30°	625.6	9.3
30°-40°	652.7	9.7
40°-50°	558.6	8.3
50°-60°	425.7	6.3
60°-70°	272.9	4.0
70°-80°	131.3	1.9
80°-90°	38.4	0.6
90°-100°	260.4	3.9
100°-110°	737.4	10.9
110°-120°	725.4	10.7
120°-130°	578.6	8.6
130°-140°	456.2	6.8
140°-150°	340.5	5.0
150°-160°	237.3	3.5
160°-170°	139.4	2.1
170°-180°	45.4	0.7
0°-30°	1151.2	17.1
0°-40°	1803.9	26.7
0°-60°	2788.2	41.3
0°-90°	3230.7	47.9
90°-120°	1723.2	25.5
90°-150°	3098.5	45.9
90°-180°	3521.0	52.2
0°-180°	6751.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1296	1296	1296	1296	1296	
5°	1539	1297	1142	1297	1539	159
15°	2187	1237	912	1237	2187	620
25°	2254	1124	742	1124	2254	969
35°	978	980	605	980	978	641
45°	522	787	476	787	522	410
55°	327	554	325	554	327	296
65°	189	342	204	342	189	186
75°	80	166	104	166	80	86
85°	19	38	37	38	19	22
90°	28	2	28	2	28	15
95°	110	32	110	32	110	198
105°	1205	110	1205	110	1205	1189
115°	1465	194	1465	194	1465	1424
125°	1156	270	1156	270	1156	1047
135°	937	316	937	316	937	727
145°	732	361	732	361	732	466
155°	607	410	607	410	607	283
165°	530	448	530	448	530	151
175°	476	467	476	467	476	46
180°	468	468	468	468	468	



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1380.5	1382.2	1376.5	1375.6	1368.9	1367.1	1367.1	1357.8	1352.0	1344.5	1340.0
5°	1539.1	1548.0	1543.5	1533.6	1516.9	1513.0	1502.5	1485.9	1467.0	1443.7	1432.6
7.5°	1737.3	1749.4	1744.7	1729.3	1711.9	1697.8	1668.1	1640.5	1601.7	1567.7	1538.7
10°	1899.7	1887.0	1877.0	1862.1	1845.9	1819.8	1788.8	1746.0	1696.7	1657.8	1614.6
12.5°	2021.4	2019.3	2006.6	1991.2	1968.5	1943.7	1905.5	1853.5	1796.1	1740.0	1690.4
15°	2187.2	2190.5	2182.1	2166.1	2133.9	2090.1	2032.4	2010.8	1928.6	1867.6	1806.5
17.5°	2301.9	2301.3	2300.1	2277.9	2245.0	2213.8	2160.3	2103.4	2029.0	1943.0	1860.8
20°	2374.7	2369.2	2370.2	2345.3	2320.9	2284.8	2232.7	2150.0	2089.0	1989.7	1904.8
22.5°	2372.9	2371.8	2376.0	2367.5	2349.8	2322.1	2281.0	2211.3	2133.3	2033.1	1937.6
25°	2253.7	2249.3	2275.4	2282.6	2310.9	2315.9	2303.7	2265.4	2191.6	2088.4	1970.3
27.5°	1886.2	1883.7	1932.2	1992.8	2069.6	2129.2	2187.0	2214.8	2191.6	2117.7	1999.3
30°	1548.0	1600.2	1624.6	1712.2	1809.9	1926.4	2028.5	2125.6	2149.5	2117.3	2020.1
32.5°	1285.2	1330.7	1351.1	1426.4	1517.4	1653.8	1807.0	1944.5	2041.6	2066.2	2007.8
35°	977.6	978.2	1024.7	1058.1	1142.4	1282.8	1431.5	1615.7	1798.8	1937.5	1951.9
37.5°	780.1	782.9	811.1	844.2	907.5	981.7	1112.6	1265.8	1477.3	1690.3	1815.1
40°	673.6	678.6	699.7	732.4	777.9	833.9	936.0	1080.3	1256.7	1493.6	1687.3
42.5°	605.2	613.3	624.2	649.4	677.6	730.0	812.6	924.1	1084.5	1308.6	1531.9
45°	521.5	525.9	534.3	545.9	571.4	608.1	663.6	738.5	871.6	1052.0	1275.5
47.5°	460.1	457.7	466.5	476.0	492.9	517.9	555.1	616.2	711.2	855.9	1045.5
50°	418.3	417.8	423.9	431.1	447.2	465.5	496.0	542.1	617.5	737.4	911.0
52.5°	379.3	381.4	385.7	394.7	406.3	421.1	448.5	481.7	546.5	650.0	794.8
55°	327.3	329.1	335.1	340.1	348.5	363.4	380.6	408.4	452.7	524.9	644.2
57.5°	283.4	282.7	288.5	289.8	299.1	311.4	324.7	346.3	378.4	432.0	512.3
60°	254.1	252.4	257.5	261.3	266.4	276.3	287.4	308.5	334.0	373.4	442.2
62.5°	227.5	226.7	230.4	234.2	238.4	247.4	256.8	273.0	293.2	326.4	381.0
65°	188.7	190.3	192.0	193.6	195.8	201.4	210.3	221.4	235.2	258.5	297.9
67.5°	148.2	149.9	150.5	153.9	158.7	162.2	167.5	177.4	187.1	206.8	229.2
70°	119.8	119.3	119.8	121.5	127.6	133.7	141.0	148.1	154.3	168.1	186.9
72.5°	103.0	102.0	103.5	103.8	106.7	108.4	113.0	119.8	127.6	137.1	150.6
75°	79.9	79.9	79.9	79.9	82.1	83.2	84.9	86.6	89.4	93.8	103.8
77.5°	59.0	59.1	59.9	60.5	60.9	61.6	62.6	64.2	65.2	67.6	71.9
80°	46.6	47.1	46.6	47.1	47.1	48.3	48.8	50.5	51.0	53.8	55.5
82.5°	35.1	34.7	35.1	35.6	35.6	36.8	36.9	38.1	38.2	39.6	41.3
85°	18.8	17.8	18.8	18.3	19.4	18.3	18.8	20.0	20.0	20.5	22.7
87.5°	9.9	11.0	9.9	10.2	10.4	10.4	10.3	10.0	10.8	10.5	10.4
90°	27.5	28.5	27.5	26.5	27.5	25.6	24.6	23.6	22.7	23.6	20.9
92.5°	45.7	47.4	46.4	49.2	51.0	55.8	63.3	79.7	109.9	145.7	160.3
95°	109.9	113.7	120.3	128.8	146.8	180.9	231.1	341.0	455.6	561.7	500.2
97.5°	299.1	307.3	332.9	375.5	445.4	558.7	680.9	850.0	931.3	870.5	637.3
100°	593.9	593.0	629.9	699.0	794.8	929.3	1040.1	1116.8	1083.7	897.1	606.3
102.5°	871.3	893.1	924.0	978.7	1053.1	1138.4	1203.0	1205.5	1091.2	847.8	560.8
105°	1204.9	1209.7	1240.0	1275.9	1319.6	1344.2	1326.2	1231.4	1033.5	761.6	504.9
107.5°	1397.0	1405.7	1415.9	1428.1	1427.3	1393.6	1310.6	1156.7	932.3	685.4	469.3
110°	1475.9	1477.7	1479.6	1472.0	1445.5	1379.2	1259.9	1085.6	868.6	642.2	455.6



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1491.8	1491.3	1484.2	1460.7	1412.2	1326.9	1193.2	1015.0	813.3	613.4	448.1
115°	1465.4	1460.7	1441.7	1400.0	1329.0	1225.7	1086.5	921.7	746.4	582.5	445.2
117.5°	1381.7	1375.2	1347.9	1300.2	1226.1	1121.4	996.3	854.0	706.0	564.4	446.9
120°	1312.0	1306.3	1283.5	1230.4	1155.7	1060.0	946.3	818.4	684.9	556.0	450.0
122.5°	1246.8	1239.6	1214.6	1166.9	1100.3	1011.5	906.1	790.4	667.4	550.7	455.3
125°	1155.7	1149.0	1125.4	1083.7	1023.0	947.2	856.3	753.1	645.1	543.7	463.2
127.5°	1080.6	1074.6	1053.1	1017.6	963.5	894.5	812.5	720.5	625.4	540.3	472.3
130°	1038.2	1030.6	1010.7	976.6	926.4	862.0	785.3	700.0	614.7	538.0	478.3
132.5°	996.5	991.2	973.5	939.5	892.3	831.0	759.5	681.1	605.0	537.3	482.9
135°	936.9	930.2	913.1	884.8	838.3	784.3	722.8	655.5	592.1	536.1	489.8
137.5°	873.8	869.4	855.0	826.2	787.2	740.4	687.3	632.2	580.8	534.0	494.3
140°	829.8	830.7	815.6	789.0	753.1	712.3	666.8	618.6	574.1	533.3	497.3
142.5°	788.9	789.8	776.2	752.7	722.0	686.6	647.2	605.7	567.9	531.8	499.6
145°	732.2	730.3	722.8	702.9	679.1	651.8	621.4	590.1	559.9	529.5	501.1
147.5°	685.6	684.9	677.7	664.2	646.2	626.7	602.3	577.5	551.9	525.9	501.1
150°	658.4	658.4	652.6	642.2	628.0	610.0	590.1	568.3	546.6	522.9	501.1
152.5°	635.6	635.6	632.2	622.6	611.4	596.4	578.8	560.0	540.5	519.1	498.8
155°	607.2	606.3	604.4	596.8	588.2	576.9	562.6	547.5	531.4	512.5	496.4
157.5°	581.2	581.4	579.9	574.2	566.8	557.9	547.0	534.3	521.1	506.6	493.2
160°	564.6	565.5	565.5	559.9	553.2	546.6	537.1	526.7	514.4	502.1	491.6
162.5°	549.4	550.3	550.3	545.4	541.0	535.2	526.5	517.6	507.5	497.5	488.6
165°	529.5	529.5	530.4	526.7	522.9	518.1	511.5	505.8	498.2	490.6	484.0
167.5°	510.5	510.5	511.5	508.8	507.2	503.8	499.9	495.6	489.3	483.9	479.5
170°	499.2	499.2	500.2	498.2	497.3	495.4	491.6	488.8	484.0	479.3	476.5
172.5°	488.6	489.3	491.1	489.2	488.9	487.9	484.8	482.7	478.7	475.5	474.2
175°	476.5	477.4	478.3	477.4	477.4	477.4	475.5	474.6	472.7	470.8	470.8
177.5°	469.4	469.4	471.0	470.2	471.0	471.0	470.2	469.4	468.7	468.0	468.7
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1338.2	1336.9	1330.7	1323.6	1314.3	1308.1	1303.2	1300.6	1292.6	1282.8	1276.1
5°	1420.9	1404.3	1386.6	1364.9	1344.9	1324.4	1311.7	1296.7	1278.3	1257.8	1243.4
7.5°	1509.5	1476.8	1441.7	1405.4	1369.5	1337.4	1309.0	1284.7	1255.5	1226.0	1205.4
10°	1577.4	1529.7	1480.3	1429.8	1383.7	1340.5	1307.2	1274.5	1239.5	1205.7	1180.1
12.5°	1639.1	1576.3	1519.4	1457.3	1398.4	1346.7	1298.8	1260.3	1218.2	1182.1	1153.1
15°	1717.2	1652.9	1584.0	1489.7	1411.5	1346.1	1287.8	1237.3	1186.3	1141.8	1113.5
17.5°	1790.2	1693.4	1600.9	1522.2	1420.6	1338.8	1267.7	1207.3	1151.3	1104.2	1069.4
20°	1820.4	1726.6	1626.2	1525.8	1426.0	1334.4	1251.7	1185.1	1126.9	1073.6	1041.5
22.5°	1838.6	1732.4	1626.7	1518.7	1412.6	1317.5	1235.7	1162.5	1099.3	1048.7	1009.0
25°	1859.8	1733.3	1616.8	1510.3	1402.1	1298.9	1201.8	1124.1	1055.9	1002.0	959.9
27.5°	1873.8	1725.0	1587.3	1468.8	1359.1	1256.4	1167.3	1085.0	1015.8	958.9	913.6
30°	1876.5	1718.3	1564.6	1436.5	1324.9	1230.6	1136.3	1057.5	984.3	923.8	881.7
32.5°	1880.0	1701.9	1534.0	1397.8	1283.7	1190.3	1104.8	1029.6	954.6	895.0	851.9
35°	1865.4	1692.8	1487.5	1331.1	1216.8	1126.3	1049.2	979.8	906.0	848.3	804.5
37.5°	1802.3	1656.8	1439.3	1255.8	1136.3	1052.6	989.7	929.3	861.5	799.3	758.0
40°	1738.9	1621.2	1402.1	1210.1	1085.2	999.2	942.6	893.3	827.9	769.6	725.2
42.5°	1644.3	1572.9	1366.6	1162.1	1027.5	944.7	896.9	850.7	793.2	734.0	692.4
45°	1470.9	1480.3	1293.9	1085.8	947.6	864.5	819.5	787.3	736.3	687.5	644.7
47.5°	1253.4	1341.6	1208.5	1004.4	863.4	785.3	746.0	718.0	683.5	635.6	596.6
50°	1111.3	1237.3	1140.2	949.9	810.7	733.0	694.1	671.3	641.4	603.6	566.5
52.5°	980.4	1115.7	1057.6	889.1	753.3	682.3	644.4	625.7	601.9	566.4	532.7
55°	799.5	936.5	923.2	797.3	667.5	603.6	574.8	553.8	537.6	511.0	484.4
57.5°	646.7	776.7	783.5	695.2	591.8	528.7	503.9	488.0	477.5	457.4	432.8
60°	550.4	669.7	693.0	626.4	537.6	482.2	457.7	445.0	436.7	420.5	401.7
62.5°	470.5	572.0	598.4	550.5	485.7	433.7	414.7	402.4	396.7	382.9	366.2
65°	360.1	444.4	469.9	443.3	409.4	367.9	352.3	341.8	336.8	329.1	316.8
67.5°	270.8	332.2	360.2	341.4	329.2	303.0	293.1	287.4	283.0	277.6	267.4
70°	217.5	263.0	291.9	286.8	276.9	263.0	255.8	251.9	247.4	243.0	234.2
72.5°	174.9	206.2	233.3	235.8	227.6	224.9	218.5	216.9	214.2	208.9	204.0
75°	115.9	137.6	156.5	163.7	167.0	169.7	167.0	166.5	165.9	161.4	158.7
77.5°	76.0	87.6	99.5	111.9	117.1	120.8	121.7	123.8	122.3	119.9	118.6
80°	58.3	61.1	69.4	79.9	88.2	91.6	93.8	94.9	94.3	93.8	91.6
82.5°	42.3	44.6	48.5	55.9	62.9	68.5	69.8	69.5	70.8	71.1	69.4
85°	22.7	23.3	24.4	25.5	29.4	35.5	37.2	38.3	39.4	39.4	36.0
87.5°	10.7	9.7	10.0	9.6	10.6	10.4	12.7	14.6	15.4	14.0	14.6
90°	18.0	15.2	12.3	10.4	8.6	5.7	3.8	1.9	3.8	5.7	8.6
92.5°	120.3	79.6	54.8	40.8	32.8	25.4	17.4	11.7	17.4	25.4	32.8
95°	344.8	203.7	123.1	86.2	61.6	45.5	35.1	32.2	35.1	45.5	61.6
97.5°	378.3	219.2	142.3	102.3	78.0	64.0	55.8	55.0	55.8	64.0	78.0
100°	357.1	217.0	150.6	113.7	90.9	77.7	71.0	70.1	71.0	77.7	90.9
102.5°	338.9	220.0	160.5	126.5	106.1	93.6	87.7	86.0	87.7	93.6	106.1
105°	325.9	228.3	177.2	147.7	129.8	118.4	112.8	109.9	112.8	118.4	129.8
107.5°	324.9	243.9	198.9	171.6	154.7	143.6	138.1	135.3	138.1	143.6	154.7
110°	328.7	256.7	214.1	187.5	171.5	161.0	156.3	153.4	156.3	161.0	171.5



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	336.3	269.6	230.0	204.2	188.1	177.7	173.0	170.2	173.0	177.7	188.1
115°	348.6	290.8	254.8	229.3	213.1	203.7	198.0	194.2	198.0	203.7	213.1
117.5°	364.8	313.3	277.8	254.0	236.0	227.3	222.6	218.3	222.6	227.3	236.0
120°	377.0	327.8	293.7	269.9	252.0	242.5	237.7	234.9	237.7	242.5	252.0
122.5°	388.4	342.9	309.6	284.4	267.1	256.9	252.2	249.3	252.2	256.9	267.1
125°	406.3	364.7	331.5	306.0	288.0	277.5	271.9	269.9	271.9	277.5	288.0
127.5°	421.2	383.6	351.6	326.0	306.1	295.5	288.5	285.7	288.5	295.5	306.1
130°	431.0	395.0	363.7	338.2	318.3	306.9	298.4	295.5	298.4	306.9	318.3
132.5°	440.1	404.9	374.4	349.5	329.6	316.0	306.7	303.1	306.7	316.0	329.6
135°	451.8	419.6	390.3	364.7	344.8	330.6	320.2	316.4	320.2	330.6	344.8
137.5°	460.6	429.8	401.6	378.0	358.2	343.1	332.9	328.9	332.9	343.1	358.2
140°	465.1	436.7	409.2	385.6	366.6	351.4	341.9	337.2	341.9	351.4	366.6
142.5°	469.6	442.0	415.3	393.1	374.1	360.5	350.3	346.3	350.3	360.5	374.1
145°	474.6	449.0	424.4	402.6	386.5	372.3	363.7	360.9	363.7	372.3	386.5
147.5°	477.6	454.7	432.1	413.6	398.0	385.7	377.4	375.7	377.4	385.7	398.0
150°	478.3	458.4	436.7	419.6	406.3	394.0	386.5	385.6	386.5	394.0	406.3
152.5°	479.9	460.7	442.0	425.7	413.9	403.2	395.6	395.4	395.6	403.2	413.9
155°	480.3	465.1	449.0	435.7	425.3	415.9	410.2	410.2	410.2	415.9	425.3
157.5°	481.2	467.6	454.7	444.4	435.5	427.2	422.7	421.9	422.7	427.2	435.5
160°	481.2	469.9	458.4	449.0	442.4	434.8	431.0	431.0	431.0	434.8	442.4
162.5°	480.5	470.6	460.7	452.8	446.9	440.8	437.8	437.8	437.8	440.8	446.9
165°	478.3	471.7	464.1	457.5	453.7	449.0	447.1	448.1	447.1	449.0	453.7
167.5°	476.9	471.6	466.0	461.9	459.3	455.6	454.7	455.8	454.7	455.6	459.3
170°	474.6	470.8	466.0	464.1	462.3	459.4	458.4	460.4	458.4	459.4	462.3
172.5°	473.9	470.8	466.8	465.7	464.6	462.4	462.3	463.4	462.3	462.4	464.6
175°	471.7	469.9	468.0	467.0	467.0	465.1	466.0	467.0	466.0	465.1	467.0
177.5°	470.2	468.7	468.0	468.0	468.0	467.2	468.0	468.7	468.0	467.2	468.0
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1273.9	1268.1	1264.1	1255.2	1249.5	1243.2	1237.1	1241.0	1240.6	1240.2	1240.2
5°	1231.2	1218.4	1206.8	1191.8	1182.3	1170.7	1161.8	1160.7	1162.9	1155.2	1150.7
7.5°	1188.8	1171.3	1154.9	1138.3	1120.8	1106.8	1098.0	1093.9	1088.3	1083.5	1078.5
10°	1159.0	1138.6	1122.4	1101.9	1083.0	1066.4	1055.9	1048.6	1044.7	1040.9	1033.6
12.5°	1128.5	1108.3	1087.9	1064.6	1046.7	1027.4	1019.5	1011.4	1004.0	999.6	989.7
15°	1083.6	1057.5	1035.9	1011.5	991.5	972.7	961.6	945.4	943.2	937.7	927.7
17.5°	1038.7	1010.3	980.5	962.5	939.9	920.2	903.4	898.0	882.1	876.1	867.4
20°	1003.1	977.1	954.3	930.5	897.7	879.4	866.1	858.9	846.1	838.4	832.8
22.5°	972.5	946.0	919.7	891.9	864.9	844.3	834.6	823.4	816.4	805.5	799.5
25°	928.8	899.9	868.3	838.4	819.0	803.4	787.9	777.9	767.9	762.9	751.8
27.5°	878.0	847.8	818.2	795.5	771.7	756.4	742.2	733.4	721.4	713.0	706.9
30°	850.0	814.5	789.0	768.4	737.9	723.5	713.0	701.9	693.0	684.1	678.0
32.5°	817.6	785.2	761.0	735.6	712.2	696.4	682.8	673.0	665.4	657.0	650.9
35°	766.8	739.6	714.6	689.1	671.9	655.8	639.8	631.4	624.2	616.4	610.9
37.5°	720.8	695.5	671.7	647.5	626.1	613.1	600.1	593.8	584.0	578.8	573.2
40°	692.4	667.5	642.0	618.6	596.5	586.4	574.8	565.4	556.5	552.6	546.5
42.5°	661.4	636.4	614.9	589.8	571.6	558.1	547.3	537.0	530.4	524.6	521.2
45°	615.3	593.1	572.0	547.1	529.9	518.2	506.0	496.6	490.5	486.6	480.5
47.5°	570.6	548.4	527.0	505.2	488.6	475.2	463.1	456.5	448.4	443.7	439.5
50°	538.2	518.2	495.5	475.5	458.9	445.6	435.5	427.2	420.0	413.9	411.2
52.5°	508.4	487.1	467.5	448.9	431.3	416.2	407.2	398.4	393.0	386.0	382.7
55°	459.4	438.9	422.2	403.9	386.7	374.0	362.9	355.1	349.5	341.8	337.4
57.5°	413.4	394.9	375.0	359.2	341.4	330.7	321.5	311.0	304.2	298.1	293.8
60°	382.3	361.2	344.0	329.1	313.5	299.6	291.3	283.0	275.7	269.6	265.8
62.5°	349.8	331.5	315.1	298.8	284.6	272.6	262.9	255.9	249.6	245.6	241.8
65°	300.2	285.8	269.1	255.8	242.5	233.6	225.8	219.7	215.2	212.5	209.2
67.5°	254.5	240.4	225.9	212.9	204.0	197.2	192.1	186.9	184.7	181.1	178.9
70°	224.7	210.3	197.5	187.5	178.6	173.7	170.3	166.5	164.2	159.8	157.6
72.5°	192.3	181.9	172.7	164.4	157.4	152.8	148.5	143.8	140.2	135.3	133.1
75°	151.5	142.0	134.9	129.3	124.8	118.7	112.6	107.6	106.0	104.3	103.8
77.5°	112.2	106.2	101.0	96.3	90.7	86.3	85.0	83.9	83.6	82.7	82.7
80°	88.2	82.7	78.8	73.2	69.9	69.9	69.9	68.8	69.4	69.4	69.4
82.5°	65.6	60.5	58.4	56.3	55.7	56.2	56.2	56.3	56.0	56.9	56.5
85°	33.8	34.4	35.5	35.0	35.5	35.5	36.6	36.0	36.6	35.5	36.6
87.5°	14.5	16.2	17.2	18.3	19.2	19.4	19.6	19.8	20.5	20.6	21.0
90°	10.4	12.3	15.2	18.0	20.9	23.6	22.7	23.6	24.6	25.6	27.5
92.5°	40.8	54.8	79.6	120.3	160.3	145.7	109.9	79.7	63.3	55.8	51.0
95°	86.2	123.1	203.7	344.8	500.2	561.7	455.6	341.0	231.1	180.9	146.8
97.5°	102.3	142.3	219.2	378.3	637.3	870.5	931.3	850.0	680.9	558.7	445.4
100°	113.7	150.6	217.0	357.1	606.3	897.1	1083.7	1116.8	1040.1	929.3	794.8
102.5°	126.5	160.5	220.0	338.9	560.8	847.8	1091.2	1205.5	1203.0	1138.4	1053.1
105°	147.7	177.2	228.3	325.9	504.9	761.6	1033.5	1231.4	1326.2	1344.2	1319.6
107.5°	171.6	198.9	243.9	324.9	469.3	685.4	932.3	1156.7	1310.6	1393.6	1427.3
110°	187.5	214.1	256.7	328.7	455.6	642.2	868.6	1085.6	1259.9	1379.2	1445.5



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.2	230.0	269.6	336.3	448.1	613.4	813.3	1015.0	1193.2	1326.9	1412.2
115°	229.3	254.8	290.8	348.6	445.2	582.5	746.4	921.7	1086.5	1225.7	1329.0
117.5°	254.0	277.8	313.3	364.8	446.9	564.4	706.0	854.0	996.3	1121.4	1226.1
120°	269.9	293.7	327.8	377.0	450.0	556.0	684.9	818.4	946.3	1060.0	1155.7
122.5°	284.4	309.6	342.9	388.4	455.3	550.7	667.4	790.4	906.1	1011.5	1100.3
125°	306.0	331.5	364.7	406.3	463.2	543.7	645.1	753.1	856.3	947.2	1023.0
127.5°	326.0	351.6	383.6	421.2	472.3	540.3	625.4	720.5	812.5	894.5	963.5
130°	338.2	363.7	395.0	431.0	478.3	538.0	614.7	700.0	785.3	862.0	926.4
132.5°	349.5	374.4	404.9	440.1	482.9	537.3	605.0	681.1	759.5	831.0	892.3
135°	364.7	390.3	419.6	451.8	489.8	536.1	592.1	655.5	722.8	784.3	838.3
137.5°	378.0	401.6	429.8	460.6	494.3	534.0	580.8	632.2	687.3	740.4	787.2
140°	385.6	409.2	436.7	465.1	497.3	533.3	574.1	618.6	666.8	712.3	753.1
142.5°	393.1	415.3	442.0	469.6	499.6	531.8	567.9	605.7	647.2	686.6	722.0
145°	402.6	424.4	449.0	474.6	501.1	529.5	559.9	590.1	621.4	651.8	679.1
147.5°	413.6	432.1	454.7	477.6	501.1	525.9	551.9	577.5	602.3	626.7	646.2
150°	419.6	436.7	458.4	478.3	501.1	522.9	546.6	568.3	590.1	610.0	628.0
152.5°	425.7	442.0	460.7	479.9	498.8	519.1	540.5	560.0	578.8	596.4	611.4
155°	435.7	449.0	465.1	480.3	496.4	512.5	531.4	547.5	562.6	576.9	588.2
157.5°	444.4	454.7	467.6	481.2	493.2	506.6	521.1	534.3	547.0	557.9	566.8
160°	449.0	458.4	469.9	481.2	491.6	502.1	514.4	526.7	537.1	546.6	553.2
162.5°	452.8	460.7	470.6	480.5	488.6	497.5	507.5	517.6	526.5	535.2	541.0
165°	457.5	464.1	471.7	478.3	484.0	490.6	498.2	505.8	511.5	518.1	522.9
167.5°	461.9	466.0	471.6	476.9	479.5	483.9	489.3	495.6	499.9	503.8	507.2
170°	464.1	466.0	470.8	474.6	476.5	479.3	484.0	488.8	491.6	495.4	497.3
172.5°	465.7	466.8	470.8	473.9	474.2	475.5	478.7	482.7	484.8	487.9	488.9
175°	467.0	468.0	469.9	471.7	470.8	470.8	472.7	474.6	475.5	477.4	477.4
177.5°	468.0	468.0	468.7	470.2	468.7	468.0	468.7	469.4	470.2	471.0	471.0
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1234.9	1234.4	1234.9	1233.1	1234.9	1234.4	1234.9	1240.2	1240.2	1240.6	1241.0
5°	1149.1	1148.5	1146.9	1141.8	1146.9	1148.5	1149.1	1150.7	1155.2	1162.9	1160.7
7.5°	1074.2	1073.4	1068.5	1068.6	1068.5	1073.4	1074.2	1078.5	1083.5	1088.3	1093.9
10°	1029.8	1030.3	1023.7	1019.8	1023.7	1030.3	1029.8	1033.6	1040.9	1044.7	1048.6
12.5°	986.8	984.1	978.8	974.5	978.8	984.1	986.8	989.7	999.6	1004.0	1011.4
15°	929.9	924.4	911.0	912.2	911.0	924.4	929.9	927.7	937.7	943.2	945.4
17.5°	863.0	858.9	858.7	850.9	858.7	858.9	863.0	867.4	876.1	882.1	898.0
20°	823.9	821.2	822.2	814.5	822.2	821.2	823.9	832.8	838.4	846.1	858.9
22.5°	793.3	790.5	785.9	783.4	785.9	790.5	793.3	799.5	805.5	816.4	823.4
25°	748.4	744.0	739.6	742.4	739.6	744.0	748.4	751.8	762.9	767.9	777.9
27.5°	703.7	700.3	695.9	695.3	695.9	700.3	703.7	706.9	713.0	721.4	733.4
30°	675.2	671.9	669.7	666.9	669.7	671.9	675.2	678.0	684.1	693.0	701.9
32.5°	646.4	645.7	641.7	641.2	641.7	645.7	646.4	650.9	657.0	665.4	673.0
35°	608.6	605.4	604.2	604.8	604.2	605.4	608.6	610.9	616.4	624.2	631.4
37.5°	572.8	568.3	566.4	564.4	566.4	568.3	572.8	573.2	578.8	584.0	593.8
40°	547.1	542.7	541.5	540.4	541.5	542.7	547.1	546.5	552.6	556.5	565.4
42.5°	518.2	516.4	515.8	513.8	515.8	516.4	518.2	521.2	524.6	530.4	537.0
45°	478.8	478.3	474.9	476.1	474.9	478.3	478.8	480.5	486.6	490.5	496.6
47.5°	437.3	434.9	432.5	434.1	432.5	434.9	437.3	439.5	443.7	448.4	456.5
50°	409.0	407.8	402.8	403.9	402.8	407.8	409.0	411.2	413.9	420.0	427.2
52.5°	380.5	376.3	374.4	373.7	374.4	376.3	380.5	382.7	386.0	393.0	398.4
55°	333.5	328.5	326.3	325.1	326.3	328.5	333.5	337.4	341.8	349.5	355.1
57.5°	287.3	285.9	284.2	285.4	284.2	285.9	287.3	293.8	298.1	304.2	311.0
60°	260.2	260.2	260.2	259.7	260.2	260.2	260.2	265.8	269.6	275.7	283.0
62.5°	239.4	238.0	237.6	238.4	237.6	238.0	239.4	241.8	245.6	249.6	255.9
65°	207.5	206.9	204.7	204.2	204.7	206.9	207.5	209.2	212.5	215.2	219.7
67.5°	177.4	175.5	174.8	174.0	174.8	175.5	177.4	178.9	181.1	184.7	186.9
70°	154.8	153.7	150.3	150.9	150.3	153.7	154.8	157.6	159.8	164.2	166.5
72.5°	130.4	129.3	128.6	127.8	128.6	129.3	130.4	133.1	135.3	140.2	143.8
75°	103.2	102.6	102.1	104.3	102.1	102.6	103.2	103.8	104.3	106.0	107.6
77.5°	82.7	82.7	83.0	82.1	83.0	82.7	82.7	82.7	82.7	83.6	83.9
80°	69.4	69.4	68.8	68.8	68.8	69.4	69.4	69.4	69.4	69.4	68.8
82.5°	55.6	56.0	56.3	55.5	56.3	56.0	55.6	56.5	56.9	56.0	56.3
85°	36.6	36.0	37.2	36.6	37.2	36.0	36.6	36.6	35.5	36.6	36.0
87.5°	21.8	21.0	21.2	21.4	21.2	21.0	21.8	21.0	20.6	20.5	19.8
90°	26.5	27.5	28.5	27.5	28.5	27.5	26.5	27.5	25.6	24.6	23.6
92.5°	49.2	46.4	47.4	45.7	47.4	46.4	49.2	51.0	55.8	63.3	79.7
95°	128.8	120.3	113.7	109.9	113.7	120.3	128.8	146.8	180.9	231.1	341.0
97.5°	375.5	332.9	307.3	299.1	307.3	332.9	375.5	445.4	558.7	680.9	850.0
100°	699.0	629.9	593.0	593.9	593.0	629.9	699.0	794.8	929.3	1040.1	1116.8
102.5°	978.7	924.0	893.1	871.3	893.1	924.0	978.7	1053.1	1138.4	1203.0	1205.5
105°	1275.9	1240.0	1209.7	1204.9	1209.7	1240.0	1275.9	1319.6	1344.2	1326.2	1231.4
107.5°	1428.1	1415.9	1405.7	1397.0	1405.7	1415.9	1428.1	1427.3	1393.6	1310.6	1156.7
110°	1472.0	1479.6	1477.7	1475.9	1477.7	1479.6	1472.0	1445.5	1379.2	1259.9	1085.6



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1460.7	1484.2	1491.3	1491.8	1491.3	1484.2	1460.7	1412.2	1326.9	1193.2	1015.0
115°	1400.0	1441.7	1460.7	1465.4	1460.7	1441.7	1400.0	1329.0	1225.7	1086.5	921.7
117.5°	1300.2	1347.9	1375.2	1381.7	1375.2	1347.9	1300.2	1226.1	1121.4	996.3	854.0
120°	1230.4	1283.5	1306.3	1312.0	1306.3	1283.5	1230.4	1155.7	1060.0	946.3	818.4
122.5°	1166.9	1214.6	1239.6	1246.8	1239.6	1214.6	1166.9	1100.3	1011.5	906.1	790.4
125°	1083.7	1125.4	1149.0	1155.7	1149.0	1125.4	1083.7	1023.0	947.2	856.3	753.1
127.5°	1017.6	1053.1	1074.6	1080.6	1074.6	1053.1	1017.6	963.5	894.5	812.5	720.5
130°	976.6	1010.7	1030.6	1038.2	1030.6	1010.7	976.6	926.4	862.0	785.3	700.0
132.5°	939.5	973.5	991.2	996.5	991.2	973.5	939.5	892.3	831.0	759.5	681.1
135°	884.8	913.1	930.2	936.9	930.2	913.1	884.8	838.3	784.3	722.8	655.5
137.5°	826.2	855.0	869.4	873.8	869.4	855.0	826.2	787.2	740.4	687.3	632.2
140°	789.0	815.6	830.7	829.8	830.7	815.6	789.0	753.1	712.3	666.8	618.6
142.5°	752.7	776.2	789.8	788.9	789.8	776.2	752.7	722.0	686.6	647.2	605.7
145°	702.9	722.8	730.3	732.2	730.3	722.8	702.9	679.1	651.8	621.4	590.1
147.5°	664.2	677.7	684.9	685.6	684.9	677.7	664.2	646.2	626.7	602.3	577.5
150°	642.2	652.6	658.4	658.4	658.4	652.6	642.2	628.0	610.0	590.1	568.3
152.5°	622.6	632.2	635.6	635.6	635.6	632.2	622.6	611.4	596.4	578.8	560.0
155°	596.8	604.4	606.3	607.2	606.3	604.4	596.8	588.2	576.9	562.6	547.5
157.5°	574.2	579.9	581.4	581.2	581.4	579.9	574.2	566.8	557.9	547.0	534.3
160°	559.9	565.5	565.5	564.6	565.5	565.5	559.9	553.2	546.6	537.1	526.7
162.5°	545.4	550.3	550.3	549.4	550.3	550.3	545.4	541.0	535.2	526.5	517.6
165°	526.7	530.4	529.5	529.5	529.5	530.4	526.7	522.9	518.1	511.5	505.8
167.5°	508.8	511.5	510.5	510.5	510.5	511.5	508.8	507.2	503.8	499.9	495.6
170°	498.2	500.2	499.2	499.2	499.2	500.2	498.2	497.3	495.4	491.6	488.8
172.5°	489.2	491.1	489.3	488.6	489.3	491.1	489.2	488.9	487.9	484.8	482.7
175°	477.4	478.3	477.4	476.5	477.4	478.3	477.4	477.4	477.4	475.5	474.6
177.5°	470.2	471.0	469.4	469.4	469.4	471.0	470.2	471.0	471.0	470.2	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1237.1	1243.2	1249.5	1255.2	1264.1	1268.1	1273.9	1276.1	1282.8	1292.6	1300.6
5°	1161.8	1170.7	1182.3	1191.8	1206.8	1218.4	1231.2	1243.4	1257.8	1278.3	1296.7
7.5°	1098.0	1106.8	1120.8	1138.3	1154.9	1171.3	1188.8	1205.4	1226.0	1255.5	1284.7
10°	1055.9	1066.4	1083.0	1101.9	1122.4	1138.6	1159.0	1180.1	1205.7	1239.5	1274.5
12.5°	1019.5	1027.4	1046.7	1064.6	1087.9	1108.3	1128.5	1153.1	1182.1	1218.2	1260.3
15°	961.6	972.7	991.5	1011.5	1035.9	1057.5	1083.6	1113.5	1141.8	1186.3	1237.3
17.5°	903.4	920.2	939.9	962.5	980.5	1010.3	1038.7	1069.4	1104.2	1151.3	1207.3
20°	866.1	879.4	897.7	930.5	954.3	977.1	1003.1	1041.5	1073.6	1126.9	1185.1
22.5°	834.6	844.3	864.9	891.9	919.7	946.0	972.5	1009.0	1048.7	1099.3	1162.5
25°	787.9	803.4	819.0	838.4	868.3	899.9	928.8	959.9	1002.0	1055.9	1124.1
27.5°	742.2	756.4	771.7	795.5	818.2	847.8	878.0	913.6	958.9	1015.8	1085.0
30°	713.0	723.5	737.9	768.4	789.0	814.5	850.0	881.7	923.8	984.3	1057.5
32.5°	682.8	696.4	712.2	735.6	761.0	785.2	817.6	851.9	895.0	954.6	1029.6
35°	639.8	655.8	671.9	689.1	714.6	739.6	766.8	804.5	848.3	906.0	979.8
37.5°	600.1	613.1	626.1	647.5	671.7	695.5	720.8	758.0	799.3	861.5	929.3
40°	574.8	586.4	596.5	618.6	642.0	667.5	692.4	725.2	769.6	827.9	893.3
42.5°	547.3	558.1	571.6	589.8	614.9	636.4	661.4	692.4	734.0	793.2	850.7
45°	506.0	518.2	529.9	547.1	572.0	593.1	615.3	644.7	687.5	736.3	787.3
47.5°	463.1	475.2	488.6	505.2	527.0	548.4	570.6	596.6	635.6	683.5	718.0
50°	435.5	445.6	458.9	475.5	495.5	518.2	538.2	566.5	603.6	641.4	671.3
52.5°	407.2	416.2	431.3	448.9	467.5	487.1	508.4	532.7	566.4	601.9	625.7
55°	362.9	374.0	386.7	403.9	422.2	438.9	459.4	484.4	511.0	537.6	553.8
57.5°	321.5	330.7	341.4	359.2	375.0	394.9	413.4	432.8	457.4	477.5	488.0
60°	291.3	299.6	313.5	329.1	344.0	361.2	382.3	401.7	420.5	436.7	445.0
62.5°	262.9	272.6	284.6	298.8	315.1	331.5	349.8	366.2	382.9	396.7	402.4
65°	225.8	233.6	242.5	255.8	269.1	285.8	300.2	316.8	329.1	336.8	341.8
67.5°	192.1	197.2	204.0	212.9	225.9	240.4	254.5	267.4	277.6	283.0	287.4
70°	170.3	173.7	178.6	187.5	197.5	210.3	224.7	234.2	243.0	247.4	251.9
72.5°	148.5	152.8	157.4	164.4	172.7	181.9	192.3	204.0	208.9	214.2	216.9
75°	112.6	118.7	124.8	129.3	134.9	142.0	151.5	158.7	161.4	165.9	166.5
77.5°	85.0	86.3	90.7	96.3	101.0	106.2	112.2	118.6	119.9	122.3	123.8
80°	69.9	69.9	69.9	73.2	78.8	82.7	88.2	91.6	93.8	94.3	94.9
82.5°	56.2	56.2	55.7	56.3	58.4	60.5	65.6	69.4	71.1	70.8	69.5
85°	36.6	35.5	35.5	35.0	35.5	34.4	33.8	36.0	39.4	39.4	38.3
87.5°	19.6	19.4	19.2	18.3	17.2	16.2	14.5	14.6	14.0	15.4	14.6
90°	22.7	23.6	20.9	18.0	15.2	12.3	10.4	8.6	5.7	3.8	1.9
92.5°	109.9	145.7	160.3	120.3	79.6	54.8	40.8	32.8	25.4	17.4	11.7
95°	455.6	561.7	500.2	344.8	203.7	123.1	86.2	61.6	45.5	35.1	32.2
97.5°	931.3	870.5	637.3	378.3	219.2	142.3	102.3	78.0	64.0	55.8	55.0
100°	1083.7	897.1	606.3	357.1	217.0	150.6	113.7	90.9	77.7	71.0	70.1
102.5°	1091.2	847.8	560.8	338.9	220.0	160.5	126.5	106.1	93.6	87.7	86.0
105°	1033.5	761.6	504.9	325.9	228.3	177.2	147.7	129.8	118.4	112.8	109.9
107.5°	932.3	685.4	469.3	324.9	243.9	198.9	171.6	154.7	143.6	138.1	135.3
110°	868.6	642.2	455.6	328.7	256.7	214.1	187.5	171.5	161.0	156.3	153.4



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	813.3	613.4	448.1	336.3	269.6	230.0	204.2	188.1	177.7	173.0	170.2
115°	746.4	582.5	445.2	348.6	290.8	254.8	229.3	213.1	203.7	198.0	194.2
117.5°	706.0	564.4	446.9	364.8	313.3	277.8	254.0	236.0	227.3	222.6	218.3
120°	684.9	556.0	450.0	377.0	327.8	293.7	269.9	252.0	242.5	237.7	234.9
122.5°	667.4	550.7	455.3	388.4	342.9	309.6	284.4	267.1	256.9	252.2	249.3
125°	645.1	543.7	463.2	406.3	364.7	331.5	306.0	288.0	277.5	271.9	269.9
127.5°	625.4	540.3	472.3	421.2	383.6	351.6	326.0	306.1	295.5	288.5	285.7
130°	614.7	538.0	478.3	431.0	395.0	363.7	338.2	318.3	306.9	298.4	295.5
132.5°	605.0	537.3	482.9	440.1	404.9	374.4	349.5	329.6	316.0	306.7	303.1
135°	592.1	536.1	489.8	451.8	419.6	390.3	364.7	344.8	330.6	320.2	316.4
137.5°	580.8	534.0	494.3	460.6	429.8	401.6	378.0	358.2	343.1	332.9	328.9
140°	574.1	533.3	497.3	465.1	436.7	409.2	385.6	366.6	351.4	341.9	337.2
142.5°	567.9	531.8	499.6	469.6	442.0	415.3	393.1	374.1	360.5	350.3	346.3
145°	559.9	529.5	501.1	474.6	449.0	424.4	402.6	386.5	372.3	363.7	360.9
147.5°	551.9	525.9	501.1	477.6	454.7	432.1	413.6	398.0	385.7	377.4	375.7
150°	546.6	522.9	501.1	478.3	458.4	436.7	419.6	406.3	394.0	386.5	385.6
152.5°	540.5	519.1	498.8	479.9	460.7	442.0	425.7	413.9	403.2	395.6	395.4
155°	531.4	512.5	496.4	480.3	465.1	449.0	435.7	425.3	415.9	410.2	410.2
157.5°	521.1	506.6	493.2	481.2	467.6	454.7	444.4	435.5	427.2	422.7	421.9
160°	514.4	502.1	491.6	481.2	469.9	458.4	449.0	442.4	434.8	431.0	431.0
162.5°	507.5	497.5	488.6	480.5	470.6	460.7	452.8	446.9	440.8	437.8	437.8
165°	498.2	490.6	484.0	478.3	471.7	464.1	457.5	453.7	449.0	447.1	448.1
167.5°	489.3	483.9	479.5	476.9	471.6	466.0	461.9	459.3	455.6	454.7	455.8
170°	484.0	479.3	476.5	474.6	470.8	466.0	464.1	462.3	459.4	458.4	460.4
172.5°	478.7	475.5	474.2	473.9	470.8	466.8	465.7	464.6	462.4	462.3	463.4
175°	472.7	470.8	470.8	471.7	469.9	468.0	467.0	467.0	465.1	466.0	467.0
177.5°	468.7	468.0	468.7	470.2	468.7	468.0	468.0	468.0	467.2	468.0	468.7
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1303.2	1308.1	1314.3	1323.6	1330.7	1336.9	1338.2	1340.0	1344.5	1352.0	1357.8
5°	1311.7	1324.4	1344.9	1364.9	1386.6	1404.3	1420.9	1432.6	1443.7	1467.0	1485.9
7.5°	1309.0	1337.4	1369.5	1405.4	1441.7	1476.8	1509.5	1538.7	1567.7	1601.7	1640.5
10°	1307.2	1340.5	1383.7	1429.8	1480.3	1529.7	1577.4	1614.6	1657.8	1696.7	1746.0
12.5°	1298.8	1346.7	1398.4	1457.3	1519.4	1576.3	1639.1	1690.4	1740.0	1796.1	1853.5
15°	1287.8	1346.1	1411.5	1489.7	1584.0	1652.9	1717.2	1806.5	1867.6	1928.6	2010.8
17.5°	1267.7	1338.8	1420.6	1522.2	1600.9	1693.4	1790.2	1860.8	1943.0	2029.0	2103.4
20°	1251.7	1334.4	1426.0	1525.8	1626.2	1726.6	1820.4	1904.8	1989.7	2089.0	2150.0
22.5°	1235.7	1317.5	1412.6	1518.7	1626.7	1732.4	1838.6	1937.6	2033.1	2133.3	2211.3
25°	1201.8	1298.9	1402.1	1510.3	1616.8	1733.3	1859.8	1970.3	2088.4	2191.6	2265.4
27.5°	1167.3	1256.4	1359.1	1468.8	1587.3	1725.0	1873.8	1999.3	2117.7	2191.6	2214.8
30°	1136.3	1230.6	1324.9	1436.5	1564.6	1718.3	1876.5	2020.1	2117.3	2149.5	2125.6
32.5°	1104.8	1190.3	1283.7	1397.8	1534.0	1701.9	1880.0	2007.8	2066.2	2041.6	1944.5
35°	1049.2	1126.3	1216.8	1331.1	1487.5	1692.8	1865.4	1951.9	1937.5	1798.8	1615.7
37.5°	989.7	1052.6	1136.3	1255.8	1439.3	1656.8	1802.3	1815.1	1690.3	1477.3	1265.8
40°	942.6	999.2	1085.2	1210.1	1402.1	1621.2	1738.9	1687.3	1493.6	1256.7	1080.3
42.5°	896.9	944.7	1027.5	1162.1	1366.6	1572.9	1644.3	1531.9	1308.6	1084.5	924.1
45°	819.5	864.5	947.6	1085.8	1293.9	1480.3	1470.9	1275.5	1052.0	871.6	738.5
47.5°	746.0	785.3	863.4	1004.4	1208.5	1341.6	1253.4	1045.5	855.9	711.2	616.2
50°	694.1	733.0	810.7	949.9	1140.2	1237.3	1111.3	911.0	737.4	617.5	542.1
52.5°	644.4	682.3	753.3	889.1	1057.6	1115.7	980.4	794.8	650.0	546.5	481.7
55°	574.8	603.6	667.5	797.3	923.2	936.5	799.5	644.2	524.9	452.7	408.4
57.5°	503.9	528.7	591.8	695.2	783.5	776.7	646.7	512.3	432.0	378.4	346.3
60°	457.7	482.2	537.6	626.4	693.0	669.7	550.4	442.2	373.4	334.0	308.5
62.5°	414.7	433.7	485.7	550.5	598.4	572.0	470.5	381.0	326.4	293.2	273.0
65°	352.3	367.9	409.4	443.3	469.9	444.4	360.1	297.9	258.5	235.2	221.4
67.5°	293.1	303.0	329.2	341.4	360.2	332.2	270.8	229.2	206.8	187.1	177.4
70°	255.8	263.0	276.9	286.8	291.9	263.0	217.5	186.9	168.1	154.3	148.1
72.5°	218.5	224.9	227.6	235.8	233.3	206.2	174.9	150.6	137.1	127.6	119.8
75°	167.0	169.7	167.0	163.7	156.5	137.6	115.9	103.8	93.8	89.4	86.6
77.5°	121.7	120.8	117.1	111.9	99.5	87.6	76.0	71.9	67.6	65.2	64.2
80°	93.8	91.6	88.2	79.9	69.4	61.1	58.3	55.5	53.8	51.0	50.5
82.5°	69.8	68.5	62.9	55.9	48.5	44.6	42.3	41.3	39.6	38.2	38.1
85°	37.2	35.5	29.4	25.5	24.4	23.3	22.7	22.7	20.5	20.0	20.0
87.5°	12.7	10.4	10.6	9.6	10.0	9.7	10.7	10.4	10.5	10.8	10.0
90°	3.8	5.7	8.6	10.4	12.3	15.2	18.0	20.9	23.6	22.7	23.6
92.5°	17.4	25.4	32.8	40.8	54.8	79.6	120.3	160.3	145.7	109.9	79.7
95°	35.1	45.5	61.6	86.2	123.1	203.7	344.8	500.2	561.7	455.6	341.0
97.5°	55.8	64.0	78.0	102.3	142.3	219.2	378.3	637.3	870.5	931.3	850.0
100°	71.0	77.7	90.9	113.7	150.6	217.0	357.1	606.3	897.1	1083.7	1116.8
102.5°	87.7	93.6	106.1	126.5	160.5	220.0	338.9	560.8	847.8	1091.2	1205.5
105°	112.8	118.4	129.8	147.7	177.2	228.3	325.9	504.9	761.6	1033.5	1231.4
107.5°	138.1	143.6	154.7	171.6	198.9	243.9	324.9	469.3	685.4	932.3	1156.7
110°	156.3	161.0	171.5	187.5	214.1	256.7	328.7	455.6	642.2	868.6	1085.6



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.0	177.7	188.1	204.2	230.0	269.6	336.3	448.1	613.4	813.3	1015.0
115°	198.0	203.7	213.1	229.3	254.8	290.8	348.6	445.2	582.5	746.4	921.7
117.5°	222.6	227.3	236.0	254.0	277.8	313.3	364.8	446.9	564.4	706.0	854.0
120°	237.7	242.5	252.0	269.9	293.7	327.8	377.0	450.0	556.0	684.9	818.4
122.5°	252.2	256.9	267.1	284.4	309.6	342.9	388.4	455.3	550.7	667.4	790.4
125°	271.9	277.5	288.0	306.0	331.5	364.7	406.3	463.2	543.7	645.1	753.1
127.5°	288.5	295.5	306.1	326.0	351.6	383.6	421.2	472.3	540.3	625.4	720.5
130°	298.4	306.9	318.3	338.2	363.7	395.0	431.0	478.3	538.0	614.7	700.0
132.5°	306.7	316.0	329.6	349.5	374.4	404.9	440.1	482.9	537.3	605.0	681.1
135°	320.2	330.6	344.8	364.7	390.3	419.6	451.8	489.8	536.1	592.1	655.5
137.5°	332.9	343.1	358.2	378.0	401.6	429.8	460.6	494.3	534.0	580.8	632.2
140°	341.9	351.4	366.6	385.6	409.2	436.7	465.1	497.3	533.3	574.1	618.6
142.5°	350.3	360.5	374.1	393.1	415.3	442.0	469.6	499.6	531.8	567.9	605.7
145°	363.7	372.3	386.5	402.6	424.4	449.0	474.6	501.1	529.5	559.9	590.1
147.5°	377.4	385.7	398.0	413.6	432.1	454.7	477.6	501.1	525.9	551.9	577.5
150°	386.5	394.0	406.3	419.6	436.7	458.4	478.3	501.1	522.9	546.6	568.3
152.5°	395.6	403.2	413.9	425.7	442.0	460.7	479.9	498.8	519.1	540.5	560.0
155°	410.2	415.9	425.3	435.7	449.0	465.1	480.3	496.4	512.5	531.4	547.5
157.5°	422.7	427.2	435.5	444.4	454.7	467.6	481.2	493.2	506.6	521.1	534.3
160°	431.0	434.8	442.4	449.0	458.4	469.9	481.2	491.6	502.1	514.4	526.7
162.5°	437.8	440.8	446.9	452.8	460.7	470.6	480.5	488.6	497.5	507.5	517.6
165°	447.1	449.0	453.7	457.5	464.1	471.7	478.3	484.0	490.6	498.2	505.8
167.5°	454.7	455.6	459.3	461.9	466.0	471.6	476.9	479.5	483.9	489.3	495.6
170°	458.4	459.4	462.3	464.1	466.0	470.8	474.6	476.5	479.3	484.0	488.8
172.5°	462.3	462.4	464.6	465.7	466.8	470.8	473.9	474.2	475.5	478.7	482.7
175°	466.0	465.1	467.0	467.0	468.0	469.9	471.7	470.8	470.8	472.7	474.6
177.5°	468.0	467.2	468.0	468.0	468.0	468.7	470.2	468.7	468.0	468.7	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0	468.0



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1367.1	1367.1	1368.9	1375.6	1376.5	1382.2	1380.5
5°	1502.5	1513.0	1516.9	1533.6	1543.5	1548.0	1539.1
7.5°	1668.1	1697.8	1711.9	1729.3	1744.7	1749.4	1737.3
10°	1788.8	1819.8	1845.9	1862.1	1877.0	1887.0	1899.7
12.5°	1905.5	1943.7	1968.5	1991.2	2006.6	2019.3	2021.4
15°	2032.4	2090.1	2133.9	2166.1	2182.1	2190.5	2187.2
17.5°	2160.3	2213.8	2245.0	2277.9	2300.1	2301.3	2301.9
20°	2232.7	2284.8	2320.9	2345.3	2370.2	2369.2	2374.7
22.5°	2281.0	2322.1	2349.8	2367.5	2376.0	2371.8	2372.9
25°	2303.7	2315.9	2310.9	2282.6	2275.4	2249.3	2253.7
27.5°	2187.0	2129.2	2069.6	1992.8	1932.2	1883.7	1886.2
30°	2028.5	1926.4	1809.9	1712.2	1624.6	1600.2	1548.0
32.5°	1807.0	1653.8	1517.4	1426.4	1351.1	1330.7	1285.2
35°	1431.5	1282.8	1142.4	1058.1	1024.7	978.2	977.6
37.5°	1112.6	981.7	907.5	844.2	811.1	782.9	780.1
40°	936.0	833.9	777.9	732.4	699.7	678.6	673.6
42.5°	812.6	730.0	677.6	649.4	624.2	613.3	605.2
45°	663.6	608.1	571.4	545.9	534.3	525.9	521.5
47.5°	555.1	517.9	492.9	476.0	466.5	457.7	460.1
50°	496.0	465.5	447.2	431.1	423.9	417.8	418.3
52.5°	448.5	421.1	406.3	394.7	385.7	381.4	379.3
55°	380.6	363.4	348.5	340.1	335.1	329.1	327.3
57.5°	324.7	311.4	299.1	289.8	288.5	282.7	283.4
60°	287.4	276.3	266.4	261.3	257.5	252.4	254.1
62.5°	256.8	247.4	238.4	234.2	230.4	226.7	227.5
65°	210.3	201.4	195.8	193.6	192.0	190.3	188.7
67.5°	167.5	162.2	158.7	153.9	150.5	149.9	148.2
70°	141.0	133.7	127.6	121.5	119.8	119.3	119.8
72.5°	113.0	108.4	106.7	103.8	103.5	102.0	103.0
75°	84.9	83.2	82.1	79.9	79.9	79.9	79.9
77.5°	62.6	61.6	60.9	60.5	59.9	59.1	59.0
80°	48.8	48.3	47.1	47.1	46.6	47.1	46.6
82.5°	36.9	36.8	35.6	35.6	35.1	34.7	35.1
85°	18.8	18.3	19.4	18.3	18.8	17.8	18.8
87.5°	10.3	10.4	10.4	10.2	9.9	11.0	9.9
90°	24.6	25.6	27.5	26.5	27.5	28.5	27.5
92.5°	63.3	55.8	51.0	49.2	46.4	47.4	45.7
95°	231.1	180.9	146.8	128.8	120.3	113.7	109.9
97.5°	680.9	558.7	445.4	375.5	332.9	307.3	299.1
100°	1040.1	929.3	794.8	699.0	629.9	593.0	593.9
102.5°	1203.0	1138.4	1053.1	978.7	924.0	893.1	871.3
105°	1326.2	1344.2	1319.6	1275.9	1240.0	1209.7	1204.9
107.5°	1310.6	1393.6	1427.3	1428.1	1415.9	1405.7	1397.0
110°	1259.9	1379.2	1445.5	1472.0	1479.6	1477.7	1475.9



TEST NUMBER: P332356-930

CATALOG NUMBER: S123RDIP-S1000D1195U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1193.2	1326.9	1412.2	1460.7	1484.2	1491.3	1491.8
115°	1086.5	1225.7	1329.0	1400.0	1441.7	1460.7	1465.4
117.5°	996.3	1121.4	1226.1	1300.2	1347.9	1375.2	1381.7
120°	946.3	1060.0	1155.7	1230.4	1283.5	1306.3	1312.0
122.5°	906.1	1011.5	1100.3	1166.9	1214.6	1239.6	1246.8
125°	856.3	947.2	1023.0	1083.7	1125.4	1149.0	1155.7
127.5°	812.5	894.5	963.5	1017.6	1053.1	1074.6	1080.6
130°	785.3	862.0	926.4	976.6	1010.7	1030.6	1038.2
132.5°	759.5	831.0	892.3	939.5	973.5	991.2	996.5
135°	722.8	784.3	838.3	884.8	913.1	930.2	936.9
137.5°	687.3	740.4	787.2	826.2	855.0	869.4	873.8
140°	666.8	712.3	753.1	789.0	815.6	830.7	829.8
142.5°	647.2	686.6	722.0	752.7	776.2	789.8	788.9
145°	621.4	651.8	679.1	702.9	722.8	730.3	732.2
147.5°	602.3	626.7	646.2	664.2	677.7	684.9	685.6
150°	590.1	610.0	628.0	642.2	652.6	658.4	658.4
152.5°	578.8	596.4	611.4	622.6	632.2	635.6	635.6
155°	562.6	576.9	588.2	596.8	604.4	606.3	607.2
157.5°	547.0	557.9	566.8	574.2	579.9	581.4	581.2
160°	537.1	546.6	553.2	559.9	565.5	565.5	564.6
162.5°	526.5	535.2	541.0	545.4	550.3	550.3	549.4
165°	511.5	518.1	522.9	526.7	530.4	529.5	529.5
167.5°	499.9	503.8	507.2	508.8	511.5	510.5	510.5
170°	491.6	495.4	497.3	498.2	500.2	499.2	499.2
172.5°	484.8	487.9	488.9	489.2	491.1	489.3	488.6
175°	475.5	477.4	477.4	477.4	478.3	477.4	476.5
177.5°	470.2	471.0	471.0	470.2	471.0	469.4	469.4
180°	468.0	468.0	468.0	468.0	468.0	468.0	468.0

(END OF REPORT)