

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332346-930

Luminaire Tested: **S123RDIP-S1000D805U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332346-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1000D805U930-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 805 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5341.6 lumens  
Efficiency: N/A  
Efficacy: 98.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332346-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332346-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	88	93	89	86	83	78	75	73	67	65	63	57	55	54	50
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	84	74	67	61	78	69	63	58	61	56	52	52	49	46	45	42	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	40	37	35	31
5	70	59	51	45	66	55	48	43	49	43	39	42	38	34	36	33	30	27
6	65	53	45	39	61	50	43	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	22
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	24	22	19
9	52	40	33	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14727	14727	14727
5°	14783	14579	14664
10°	14700	14397	14348
15°	14542	14060	13912
20°	14325	13639	13321
25°	14101	13166	12744
30°	13806	12621	11931
35°	13502	12073	11184
40°	13222	11428	10260
45°	12855	10794	9426
50°	12450	10071	8492
55°	12037	9246	7621
60°	11657	8361	6665
65°	11163	7404	5708
70°	10546	6216	4611
75°	9649	4891	4338
80°	8598	4333	3986
85°	7262	3841	3569



TEST NUMBER: P332346-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	128.5	2.4
10°-20°	357.5	6.7
20°-30°	514.7	9.6
30°-40°	579.8	10.9
40°-50°	554.7	10.4
50°-60°	454.2	8.5
60°-70°	306.5	5.7
70°-80°	154.2	2.9
80°-90°	43.2	0.8
90°-100°	52.9	1.0
100°-110°	158.2	3.0
110°-120°	269.1	5.0
120°-130°	354.0	6.6
130°-140°	397.9	7.4
140°-150°	391.1	7.3
150°-160°	329.2	6.2
160°-170°	219.2	4.1
170°-180°	76.7	1.4
0°-30°	1000.7	18.7
0°-40°	1580.5	29.6
0°-60°	2589.5	48.5
0°-90°	3093.3	57.9
90°-120°	480.2	9.0
90°-150°	1623.1	30.4
90°-180°	2248.0	42.1
0°-180°	5341.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1368	1368	1368	1368	1368	
5°	1368	1362	1349	1359	1357	130
15°	1305	1292	1262	1256	1248	367
25°	1187	1158	1109	1086	1073	546
35°	1028	986	919	873	851	643
45°	844	793	709	648	619	651
55°	641	585	493	431	406	575
65°	438	376	291	239	224	434
75°	232	178	118	107	104	247
85°	59	36	31	29	29	66
90°	1	7	15	18	19	5
95°	38	42	47	50	50	42
105°	143	145	150	150	152	154
115°	271	273	272	272	272	268
125°	396	398	397	395	392	353
135°	514	518	518	515	514	396
145°	624	625	627	626	624	390
155°	714	715	715	717	713	329
165°	778	776	776	780	776	219
175°	810	807	807	810	806	77
180°	812	812	812	812	812	



TEST NUMBER: P332346-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1372.6	1371.8	1371.1	1370.3	1369.5	1367.9	1365.5	1363.2	1360.8	1358.5	1360.6
5°	1368.2	1366.9	1365.7	1364.5	1363.3	1361.1	1358.2	1355.3	1352.3	1349.3	1351.5
7.5°	1355.5	1354.2	1352.9	1351.5	1350.2	1347.6	1343.8	1339.9	1336.1	1332.3	1333.5
10°	1344.9	1343.2	1341.4	1339.7	1338.0	1334.9	1330.5	1326.0	1321.6	1317.2	1317.4
12.5°	1329.8	1327.9	1326.0	1324.0	1322.1	1318.4	1313.0	1307.6	1302.2	1296.7	1296.6
15°	1305.0	1302.3	1299.5	1296.8	1294.1	1289.3	1282.4	1275.5	1268.6	1261.7	1260.5
17.5°	1273.7	1270.5	1267.4	1264.2	1261.0	1255.1	1246.3	1237.5	1228.7	1219.9	1217.3
20°	1250.6	1246.7	1242.7	1238.8	1234.8	1228.2	1218.8	1209.4	1200.0	1190.7	1187.5
22.5°	1224.8	1220.3	1215.8	1211.2	1206.7	1199.5	1189.4	1179.5	1169.5	1159.6	1155.6
25°	1187.3	1181.2	1175.0	1168.8	1162.7	1153.9	1142.6	1131.2	1119.9	1108.6	1103.3
27.5°	1141.8	1135.1	1128.2	1121.4	1114.6	1104.9	1092.3	1079.6	1067.0	1054.4	1047.2
30°	1110.8	1103.3	1096.0	1088.6	1081.2	1070.6	1056.8	1042.9	1029.2	1015.4	1007.0
32.5°	1079.7	1071.3	1062.9	1054.5	1046.2	1034.7	1020.1	1005.5	990.8	976.2	967.1
35°	1027.5	1018.6	1009.7	1000.9	992.1	979.9	964.7	949.3	934.1	918.8	908.2
37.5°	974.7	964.8	955.0	945.1	935.2	922.2	905.9	889.5	873.2	856.9	844.8
40°	941.0	930.2	919.2	908.4	897.6	883.4	865.9	848.4	830.9	813.3	800.5
42.5°	902.8	891.9	881.1	870.3	859.4	845.0	826.9	808.8	790.7	772.6	758.6
45°	844.5	833.3	822.2	811.1	800.1	785.1	766.1	747.1	728.1	709.1	695.0
47.5°	786.1	773.9	761.7	749.5	737.4	721.8	702.8	683.8	664.8	645.8	630.6
50°	743.5	731.9	720.3	708.7	697.1	681.3	661.4	641.4	621.4	601.4	586.1
52.5°	705.3	692.8	680.1	667.6	655.0	638.8	619.1	599.2	579.5	559.7	543.8
55°	641.4	629.3	617.2	605.1	593.0	576.5	555.5	534.6	513.6	492.7	478.4
57.5°	582.4	569.2	556.0	542.8	529.7	512.6	491.5	470.4	449.4	428.4	414.8
60°	541.5	528.0	514.4	500.8	487.2	470.3	449.8	429.3	408.9	388.4	375.0
62.5°	500.7	487.1	473.5	460.0	446.5	429.4	409.0	388.5	368.0	347.6	335.0
65°	438.3	424.8	411.2	397.6	384.1	367.7	348.5	329.2	310.0	290.7	278.7
67.5°	375.9	362.2	348.5	334.8	321.1	305.0	286.6	268.2	249.7	231.2	222.3
70°	335.1	321.8	308.5	295.1	281.8	266.6	249.3	232.0	214.7	197.5	188.9
72.5°	294.2	281.2	268.1	254.9	241.8	227.4	211.7	196.1	180.3	164.7	157.6
75°	232.0	220.0	208.2	196.4	184.6	171.9	158.3	144.7	131.2	117.6	115.1
77.5°	175.1	164.4	153.7	143.0	132.3	122.5	113.8	105.1	96.4	87.6	86.3
80°	138.7	128.6	118.5	108.4	98.2	90.7	85.4	80.2	75.1	69.9	69.1
82.5°	104.1	95.4	86.7	77.9	69.1	63.6	61.1	58.8	56.3	53.9	53.2
85°	58.8	53.4	47.9	42.6	37.1	34.0	33.3	32.5	31.8	31.1	30.6
87.5°	21.4	19.6	17.7	15.7	13.9	13.1	13.5	13.9	14.3	14.6	14.5
90°	0.7	2.0	3.5	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9
92.5°	15.4	16.4	17.4	18.3	19.2	20.3	21.4	22.4	23.4	24.5	24.9
95°	37.6	38.6	39.6	40.6	41.6	42.6	43.8	44.9	46.1	47.2	47.8
97.5°	66.8	67.5	68.2	69.0	69.8	70.5	71.3	72.2	73.0	73.8	74.4
100°	86.7	87.6	88.4	89.3	90.1	90.9	91.6	92.3	93.0	93.7	94.2
102.5°	109.7	110.1	110.6	111.2	111.7	112.4	113.3	114.3	115.2	116.2	116.6
105°	143.4	143.7	144.0	144.3	144.6	145.4	146.6	147.9	149.2	150.4	150.4
107.5°	182.7	182.9	183.0	183.2	183.4	183.7	184.3	184.7	185.2	185.7	186.2
110°	207.2	207.4	207.7	208.0	208.3	208.6	208.9	209.1	209.5	209.7	210.3



TEST NUMBER: P332346-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	232.7	232.8	233.0	233.2	233.3	233.4	233.5	233.6	233.7	233.7	234.4
115°	270.9	271.3	271.7	272.1	272.6	272.7	272.4	272.1	271.8	271.6	271.7
117.5°	309.4	309.7	310.0	310.2	310.5	310.5	310.1	309.7	309.4	309.0	309.0
120°	333.4	334.2	335.1	335.9	336.8	336.9	336.1	335.4	334.8	334.0	333.9
122.5°	358.4	359.0	359.6	360.2	360.9	361.0	360.6	360.3	359.9	359.5	359.1
125°	396.5	396.9	397.3	397.8	398.2	398.3	397.9	397.7	397.4	397.1	396.6
127.5°	431.7	432.6	433.5	434.4	435.3	435.6	435.3	435.0	434.6	434.3	433.6
130°	455.1	456.2	457.4	458.5	459.7	460.0	459.6	459.2	458.8	458.3	457.7
132.5°	478.6	479.7	480.9	482.0	483.1	483.6	483.2	482.9	482.6	482.2	481.6
135°	514.4	515.3	516.1	517.0	517.8	518.2	518.0	517.9	517.7	517.6	517.1
137.5°	547.6	548.3	548.9	549.7	550.4	550.9	551.3	551.6	552.0	552.4	551.8
140°	570.5	571.2	571.9	572.7	573.3	573.7	573.9	574.1	574.2	574.3	574.2
142.5°	591.4	592.2	592.8	593.5	594.3	594.8	595.0	595.3	595.5	595.7	595.6
145°	624.0	624.4	624.6	624.9	625.2	625.5	626.0	626.4	626.8	627.2	627.1
147.5°	652.6	653.1	653.6	654.1	654.7	655.1	655.5	655.9	656.3	656.7	656.7
150°	672.5	672.8	673.0	673.4	673.6	673.9	674.2	674.5	674.7	675.1	675.1
152.5°	688.8	689.2	689.6	690.0	690.4	690.7	690.9	691.0	691.2	691.4	691.6
155°	714.5	714.5	714.5	714.5	714.5	714.6	714.8	714.9	715.1	715.2	715.8
157.5°	736.5	736.3	736.1	736.0	735.8	735.8	735.9	736.1	736.1	736.2	736.9
160°	750.2	750.0	749.7	749.4	749.1	749.0	749.0	749.0	749.0	749.0	749.7
162.5°	762.5	762.1	761.7	761.3	760.9	760.8	760.9	761.0	761.1	761.2	761.9
165°	778.3	777.9	777.5	777.1	776.6	776.4	776.4	776.4	776.4	776.4	777.2
167.5°	790.9	790.4	789.8	789.2	788.6	788.5	788.6	788.6	788.8	788.9	789.8
170°	798.1	797.5	797.0	796.4	795.8	795.5	795.5	795.5	795.5	795.5	796.5
172.5°	803.6	803.2	802.6	802.0	801.4	801.1	801.1	801.1	801.1	801.1	802.0
175°	809.5	808.9	808.5	807.9	807.3	807.0	807.0	807.0	807.0	807.0	807.9
177.5°	812.0	811.5	811.1	810.6	810.2	809.9	809.9	809.9	809.9	809.9	810.6
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5



TEST NUMBER: P332346-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1362.8	1365.0	1367.1	1368.0	1367.6	1367.3	1366.8	1366.4
5°	1353.8	1356.0	1358.2	1359.1	1358.6	1358.1	1357.6	1357.1
7.5°	1334.7	1335.9	1337.2	1337.4	1336.5	1335.7	1334.9	1334.0
10°	1317.7	1317.9	1318.2	1317.7	1316.4	1315.2	1313.9	1312.7
12.5°	1296.4	1296.3	1296.2	1295.3	1294.0	1292.5	1291.1	1289.6
15°	1259.2	1258.0	1256.8	1255.2	1253.5	1251.8	1250.1	1248.4
17.5°	1214.7	1212.1	1209.5	1206.9	1204.4	1201.8	1199.2	1196.6
20°	1184.2	1181.0	1177.9	1174.8	1171.8	1168.8	1165.9	1162.9
22.5°	1151.6	1147.6	1143.6	1140.2	1137.5	1134.7	1132.0	1129.2
25°	1098.2	1093.0	1087.9	1083.9	1081.2	1078.5	1075.8	1073.0
27.5°	1040.0	1032.8	1025.6	1019.9	1015.8	1011.6	1007.5	1003.4
30°	998.6	990.2	981.8	975.7	971.7	967.8	963.8	959.9
32.5°	957.9	948.8	939.6	932.9	928.8	924.6	920.5	916.3
35°	897.6	887.0	876.4	868.9	864.5	860.0	855.6	851.1
37.5°	832.8	820.8	808.8	800.0	794.5	789.0	783.6	778.1
40°	787.7	774.9	762.1	752.8	747.1	741.5	735.8	730.2
42.5°	744.5	730.5	716.5	706.9	701.9	696.8	691.7	686.6
45°	680.9	666.9	652.8	642.9	636.9	631.0	625.1	619.2
47.5°	615.2	600.0	584.7	574.4	569.1	563.9	558.6	553.3
50°	570.9	555.5	540.3	529.8	524.2	518.4	512.8	507.1
52.5°	528.0	512.1	496.2	485.7	480.6	475.6	470.5	465.4
55°	464.1	449.8	435.5	425.8	420.9	416.0	411.1	406.1
57.5°	401.3	387.8	374.3	365.4	361.3	357.0	352.9	348.6
60°	361.7	348.5	335.1	326.4	322.2	318.0	313.8	309.6
62.5°	322.5	310.0	297.4	288.9	284.6	280.2	275.8	271.4
65°	266.6	254.5	242.4	235.0	232.3	229.6	226.9	224.1
67.5°	213.2	204.2	195.2	189.1	186.3	183.4	180.4	177.6
70°	180.3	171.6	163.0	157.4	154.6	151.9	149.2	146.5
72.5°	150.6	143.5	136.5	132.4	131.3	130.1	129.0	127.8
75°	112.7	110.2	107.8	106.3	105.8	105.3	104.8	104.3
77.5°	85.0	83.6	82.3	81.4	81.0	80.5	80.0	79.5
80°	68.4	67.7	66.9	66.4	65.9	65.4	64.8	64.3
82.5°	52.4	51.7	51.0	50.5	50.5	50.4	50.2	50.1
85°	30.1	29.6	29.1	28.9	28.9	28.9	28.9	28.9
87.5°	14.4	14.3	14.3	14.2	14.0	13.9	13.7	13.6
90°	16.5	17.0	17.5	18.0	18.3	18.6	18.8	19.2
92.5°	25.4	25.8	26.3	26.4	26.3	26.1	25.9	25.8
95°	48.3	48.8	49.4	49.7	49.7	49.7	49.7	49.7
97.5°	75.1	75.7	76.4	76.7	76.6	76.6	76.6	76.5
100°	94.6	95.0	95.4	95.8	96.0	96.3	96.6	96.9
102.5°	117.0	117.4	117.8	118.1	118.0	117.9	117.9	117.8
105°	150.4	150.4	150.4	150.6	150.8	151.2	151.4	151.7
107.5°	186.6	187.1	187.6	187.7	187.5	187.4	187.2	187.0
110°	210.8	211.4	212.0	212.1	211.8	211.6	211.2	211.0





TEST NUMBER: P332346-930

CATALOG NUMBER: S123RDIP-S1000D805U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.1	235.7	236.4	236.7	236.7	236.6	236.5	236.5
115°	271.8	272.0	272.1	272.1	272.0	271.8	271.7	271.6
117.5°	309.0	308.9	308.9	308.7	308.3	307.9	307.5	307.1
120°	333.7	333.6	333.5	333.2	333.0	332.6	332.4	332.1
122.5°	358.8	358.4	358.1	357.7	357.3	356.9	356.4	356.0
125°	396.0	395.4	394.8	394.3	393.7	393.1	392.6	392.0
127.5°	432.8	431.9	431.2	430.5	429.8	429.2	428.5	427.9
130°	457.2	456.6	456.1	455.3	454.3	453.3	452.3	451.3
132.5°	480.9	480.2	479.6	478.8	478.1	477.3	476.5	475.8
135°	516.5	515.9	515.4	514.9	514.6	514.4	514.0	513.8
137.5°	551.2	550.7	550.0	549.4	548.9	548.4	547.9	547.3
140°	574.1	573.9	573.7	573.2	572.2	571.2	570.2	569.2
142.5°	595.5	595.3	595.2	594.8	593.9	593.2	592.4	591.7
145°	627.0	626.8	626.6	626.3	625.7	625.2	624.6	624.0
147.5°	656.7	656.7	656.7	656.2	655.4	654.5	653.7	652.9
150°	675.1	675.1	675.1	674.7	673.8	672.9	672.1	671.2
152.5°	691.8	692.0	692.3	692.0	691.3	690.6	689.8	689.1
155°	716.3	716.9	717.5	717.2	716.2	715.3	714.3	713.3
157.5°	737.4	738.0	738.6	738.5	737.8	736.9	736.1	735.3
160°	750.4	751.1	751.8	751.9	751.3	750.7	750.2	749.6
162.5°	762.6	763.4	764.1	763.9	763.0	762.1	761.2	760.3
165°	778.1	778.9	779.8	779.8	778.8	777.7	776.7	775.8
167.5°	790.7	791.5	792.4	792.4	791.5	790.7	789.8	788.9
170°	797.5	798.5	799.5	799.5	798.5	797.5	796.5	795.5
172.5°	802.9	803.8	804.6	804.6	803.6	802.6	801.6	800.6
175°	808.7	809.5	810.4	810.3	809.3	808.4	807.3	806.3
177.5°	811.3	812.0	812.6	812.6	811.8	811.0	810.2	809.4
180°	811.5	811.5	811.5	811.5	811.5	811.5	811.5	811.5

(END OF REPORT)