

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332379-930

Luminaire Tested: **S123RDIP-S1165D1025U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332379-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6600.6 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	92	84	79	74	85	79	74	69	68	65	61	59	56	54	50	48	46	42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36
4	77	67	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35	32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	30	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	28	25	22	20
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	26	23	20	18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	24	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16113	16113	16113	16113
5°	19207	16181	14249	16181
10°	23981	16088	12873	16088
15°	28149	15924	11739	15924
20°	31416	15678	10775	15678
25°	30914	15419	10183	15419
30°	22222	15181	9573	15181
35°	14837	14870	9179	14870
40°	10932	14497	8769	14497
45°	9168	13842	8369	13842
50°	8090	12983	7812	12983
55°	7096	12001	7047	12001
60°	6318	11063	6456	11063
65°	5547	10055	6006	10055
70°	4356	9155	5485	9155
75°	3839	7993	5011	7993
80°	3335	6794	4928	6794
85°	2692	5459	5224	5459



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.2	2.2
10°-20°	459.9	7.0
20°-30°	722.5	10.9
30°-40°	753.8	11.4
40°-50°	645.1	9.8
50°-60°	491.7	7.4
60°-70°	315.1	4.8
70°-80°	151.6	2.3
80°-90°	43.2	0.7
90°-100°	67.5	1.0
100°-110°	202.0	3.1
110°-120°	343.6	5.2
120°-130°	451.9	6.8
130°-140°	508.0	7.7
140°-150°	499.3	7.6
150°-160°	420.4	6.4
160°-170°	279.8	4.2
170°-180°	98.0	1.5
0°-30°	1329.6	20.1
0°-40°	2083.4	31.6
0°-60°	3220.2	48.8
0°-90°	3730.1	56.5
90°-120°	613.1	9.3
90°-150°	2072.3	31.4
90°-180°	2870.0	43.5
0°-180°	6600.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1497	1497	1497	1497	1497	
5°	1778	1498	1319	1498	1778	184
15°	2526	1429	1053	1429	2526	716
25°	2603	1298	857	1298	2603	1119
35°	1129	1132	698	1132	1129	740
45°	602	909	550	909	602	474
55°	378	640	376	640	378	342
65°	218	395	236	395	218	214
75°	92	192	120	192	92	99
85°	22	44	42	44	22	26
90°	24	1	24	1	24	13
95°	64	48	64	48	64	65
105°	194	183	194	183	194	206
115°	347	346	347	346	347	343
125°	500	506	500	506	500	448
135°	656	657	656	657	656	504
145°	797	797	797	797	797	497
155°	911	912	911	912	911	419
165°	990	994	990	994	990	279
175°	1030	1034	1030	1034	1030	98
180°	1036	1036	1036	1036	1036	



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1594.3	1596.4	1589.7	1588.7	1580.9	1578.9	1578.9	1568.1	1561.5	1552.8	1547.7
5°	1777.6	1787.9	1782.7	1771.2	1751.9	1747.4	1735.3	1716.0	1694.3	1667.4	1654.6
7.5°	2006.5	2020.5	2015.1	1997.2	1977.1	1960.9	1926.5	1894.6	1849.8	1810.6	1777.0
10°	2194.1	2179.4	2167.8	2150.5	2131.9	2101.8	2066.0	2016.6	1959.6	1914.7	1864.8
12.5°	2334.5	2332.2	2317.5	2299.7	2273.5	2244.8	2200.7	2140.6	2074.4	2009.5	1952.4
15°	2526.0	2529.9	2520.3	2501.7	2464.5	2413.9	2347.2	2322.3	2227.4	2157.0	2086.4
17.5°	2658.5	2657.8	2656.5	2630.7	2592.8	2556.8	2495.0	2429.3	2343.4	2244.1	2149.1
20°	2742.6	2736.2	2737.5	2708.7	2680.5	2638.8	2578.5	2483.1	2412.6	2297.9	2199.8
22.5°	2740.5	2739.3	2744.1	2734.3	2713.8	2681.8	2634.5	2553.8	2463.9	2348.1	2237.8
25°	2602.9	2597.8	2628.0	2636.3	2669.0	2674.7	2660.6	2616.4	2531.2	2412.0	2275.5
27.5°	2178.5	2175.6	2231.6	2301.5	2390.2	2459.1	2525.8	2557.9	2531.2	2445.8	2309.1
30°	1787.9	1848.0	1876.2	1977.5	2090.3	2224.9	2342.8	2454.9	2482.4	2445.3	2333.1
32.5°	1484.3	1536.9	1560.5	1647.4	1752.5	1910.1	2086.9	2245.7	2357.9	2386.3	2318.8
35°	1129.1	1129.8	1183.6	1222.0	1319.4	1481.6	1653.3	1866.0	2077.5	2237.7	2254.3
37.5°	901.0	904.2	936.7	975.0	1048.1	1133.8	1285.1	1461.9	1706.2	1952.2	2096.3
40°	778.0	783.7	808.0	845.9	898.4	963.1	1081.0	1247.7	1451.4	1725.0	1948.6
42.5°	699.0	708.3	720.9	750.0	782.5	843.2	938.5	1067.2	1252.5	1511.2	1769.3
45°	602.3	607.5	617.1	630.6	660.0	702.3	766.4	852.9	1006.7	1215.0	1473.2
47.5°	531.3	528.6	538.7	549.7	569.3	598.1	641.1	711.7	821.4	988.5	1207.5
50°	483.1	482.5	489.6	497.9	516.5	537.6	572.9	626.1	713.2	851.7	1052.2
52.5°	438.1	440.5	445.5	455.8	469.3	486.4	518.0	556.4	631.2	750.6	917.9
55°	378.1	380.0	387.0	392.8	402.4	419.7	439.6	471.7	522.9	606.2	744.0
57.5°	327.3	326.4	333.2	334.6	345.5	359.6	375.0	399.8	437.0	499.0	591.7
60°	293.5	291.6	297.3	301.8	307.6	319.1	331.9	356.3	385.8	431.3	510.7
62.5°	262.7	261.8	266.0	270.5	275.3	285.8	296.5	315.3	338.6	376.9	439.9
65°	217.8	219.8	221.7	223.6	226.2	232.6	242.9	255.7	271.7	298.6	344.1
67.5°	171.2	173.2	173.8	177.7	183.3	187.3	193.6	205.0	216.1	238.8	264.6
70°	138.4	137.8	138.4	140.3	147.4	154.4	162.7	171.1	178.1	194.1	216.0
72.5°	119.0	117.8	119.4	119.8	123.3	125.2	130.4	138.3	147.4	158.2	173.9
75°	92.3	92.3	92.3	92.3	94.8	96.1	98.1	100.0	103.1	108.3	119.8
77.5°	68.2	68.3	69.2	69.9	70.4	71.1	72.3	74.2	75.3	78.0	83.1
80°	53.8	54.5	53.8	54.5	54.5	55.8	56.4	58.3	58.9	62.1	64.1
82.5°	40.5	40.1	40.5	41.2	41.2	42.4	42.6	43.9	44.1	45.7	47.7
85°	21.8	20.5	21.8	21.1	22.4	21.1	21.8	23.1	23.1	23.7	26.3
87.5°	10.0	10.9	9.9	10.3	10.3	10.6	10.5	10.4	11.3	10.6	10.6
90°	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0	20.2	19.6	17.2
92.5°	32.9	33.1	33.3	33.5	33.8	33.6	33.0	32.4	31.8	31.2	29.9
95°	63.5	63.5	63.5	63.5	63.5	63.1	62.4	61.6	61.0	60.3	58.8
97.5°	97.7	97.8	97.8	97.9	97.9	97.6	96.8	95.9	95.1	94.2	93.2
100°	123.7	123.4	122.9	122.6	122.3	121.8	121.2	120.7	120.2	119.6	118.7
102.5°	150.4	150.5	150.5	150.6	150.7	150.4	149.9	149.4	148.8	148.3	147.1
105°	193.7	193.3	193.0	192.6	192.2	192.1	192.1	192.1	192.1	192.1	190.5
107.5°	238.8	239.0	239.2	239.5	239.6	239.5	238.9	238.3	237.7	237.2	236.5
110°	269.4	269.8	270.1	270.4	270.8	270.7	269.9	269.2	268.5	267.7	267.4



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	301.9	302.0	302.1	302.1	302.2	301.8	300.9	300.1	299.2	298.3	298.3
115°	346.7	346.9	347.1	347.2	347.4	347.4	347.2	347.1	346.9	346.7	347.1
117.5°	392.1	392.6	393.1	393.6	394.1	394.4	394.4	394.4	394.5	394.5	395.0
120°	424.0	424.4	424.8	425.1	425.4	425.7	425.9	426.1	426.2	426.5	427.4
122.5°	454.6	455.1	455.6	456.2	456.6	457.1	457.6	458.0	458.5	459.0	459.5
125°	500.5	501.2	502.0	502.7	503.4	504.1	504.8	505.6	506.3	507.0	507.4
127.5°	546.3	547.1	547.9	548.8	549.6	550.5	551.5	552.5	553.5	554.6	555.0
130°	576.2	577.5	578.7	580.0	581.2	582.3	582.9	583.7	584.4	585.1	585.7
132.5°	607.5	608.5	609.4	610.4	611.4	612.3	613.2	614.0	614.9	615.7	616.1
135°	656.0	656.3	656.6	657.0	657.4	657.9	658.7	659.4	660.1	660.8	661.0
137.5°	698.8	699.4	700.1	700.8	701.5	702.2	703.0	703.8	704.5	705.2	704.8
140°	726.8	728.1	729.3	730.6	731.8	732.5	732.7	732.9	733.1	733.3	733.1
142.5°	755.4	756.4	757.3	758.3	759.3	759.9	760.1	760.3	760.4	760.6	760.3
145°	796.7	797.4	798.2	798.9	799.6	800.1	800.3	800.5	800.6	800.8	800.3
147.5°	833.6	834.6	835.7	836.8	837.9	838.5	838.5	838.5	838.5	838.5	837.9
150°	857.0	858.0	859.2	860.2	861.3	861.9	861.9	861.9	861.9	861.9	861.5
152.5°	879.8	880.7	881.7	882.6	883.5	883.9	883.5	883.3	883.0	882.7	882.5
155°	910.7	911.9	913.2	914.5	915.7	916.0	915.3	914.6	913.9	913.1	913.0
157.5°	938.8	939.9	940.9	941.9	942.9	943.1	942.2	941.5	940.8	940.0	939.9
160°	957.1	957.8	958.5	959.3	959.9	959.9	959.0	958.1	957.2	956.3	956.3
162.5°	970.8	971.9	973.1	974.2	975.3	975.5	974.6	973.7	972.8	971.9	971.8
165°	990.4	991.7	993.0	994.3	995.5	995.6	994.5	993.4	992.3	991.2	991.2
167.5°	1007.2	1008.4	1009.4	1010.6	1011.7	1011.7	1010.6	1009.4	1008.4	1007.2	1007.1
170°	1015.7	1016.9	1018.2	1019.5	1020.8	1020.8	1019.5	1018.2	1016.9	1015.7	1015.7
172.5°	1022.1	1023.4	1024.7	1026.0	1027.3	1027.3	1026.2	1025.1	1023.9	1022.8	1022.8
175°	1029.5	1030.8	1032.0	1033.3	1034.5	1034.7	1033.6	1032.5	1031.4	1030.3	1030.3
177.5°	1033.4	1034.5	1035.4	1036.5	1037.5	1037.5	1036.7	1035.8	1034.9	1034.0	1034.0
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1545.6	1544.1	1536.9	1528.7	1517.9	1510.7	1505.1	1502.0	1492.8	1481.6	1473.8
5°	1641.1	1621.9	1601.3	1576.4	1553.3	1529.6	1514.8	1497.5	1476.4	1452.7	1436.1
7.5°	1743.4	1705.7	1665.1	1623.2	1581.8	1544.6	1511.8	1483.7	1450.0	1416.0	1392.2
10°	1821.8	1766.7	1709.7	1651.3	1598.1	1548.2	1509.7	1471.9	1431.6	1392.4	1363.0
12.5°	1893.0	1820.5	1754.8	1683.1	1615.1	1555.3	1500.0	1455.5	1407.0	1365.3	1331.7
15°	1983.3	1908.9	1829.5	1720.5	1630.2	1554.6	1487.3	1429.0	1370.0	1318.7	1286.1
17.5°	2067.6	1955.7	1848.9	1758.1	1640.7	1546.2	1464.1	1394.4	1329.7	1275.3	1235.1
20°	2102.5	1994.1	1878.2	1762.2	1646.8	1541.2	1445.6	1368.7	1301.5	1239.9	1202.8
22.5°	2123.4	2000.8	1878.7	1754.0	1631.5	1521.7	1427.2	1342.6	1269.7	1211.2	1165.4
25°	2148.0	2001.9	1867.3	1744.3	1619.3	1500.2	1388.0	1298.3	1219.4	1157.3	1108.6
27.5°	2164.1	1992.3	1833.2	1696.5	1569.7	1451.0	1348.3	1253.1	1173.2	1107.4	1055.2
30°	2167.1	1984.5	1807.0	1659.1	1530.2	1421.3	1312.4	1221.4	1136.8	1066.9	1018.2
32.5°	2171.3	1965.6	1771.6	1614.5	1482.5	1374.7	1275.9	1189.0	1102.4	1033.6	983.9
35°	2154.3	1955.1	1718.0	1537.2	1405.2	1300.8	1211.8	1131.6	1046.4	979.7	929.2
37.5°	2081.5	1913.4	1662.4	1450.4	1312.4	1215.6	1143.0	1073.2	995.1	923.2	875.5
40°	2008.2	1872.4	1619.3	1397.6	1253.4	1154.1	1088.8	1031.7	956.1	888.8	837.6
42.5°	1899.1	1816.6	1578.3	1342.2	1186.7	1091.0	1035.9	982.4	916.1	847.7	799.6
45°	1698.8	1709.7	1494.4	1254.0	1094.5	998.3	946.5	909.3	850.4	793.9	744.6
47.5°	1447.6	1549.5	1395.8	1160.1	997.2	907.0	861.6	829.2	789.5	734.1	689.1
50°	1283.5	1429.0	1316.9	1097.1	936.2	846.5	801.6	775.3	740.8	697.2	654.3
52.5°	1132.3	1288.5	1221.5	1026.8	870.1	788.1	744.2	722.6	695.1	654.1	615.3
55°	923.4	1081.7	1066.3	920.8	770.9	697.2	663.9	639.5	620.9	590.2	559.5
57.5°	746.9	897.0	904.9	802.9	683.5	610.7	582.0	563.6	551.5	528.3	499.9
60°	635.7	773.5	800.4	723.5	620.9	556.8	528.6	513.9	504.3	485.8	463.9
62.5°	543.4	660.6	691.1	635.8	560.9	501.0	478.9	464.7	458.2	442.1	422.9
65°	415.9	513.3	542.7	512.0	472.9	424.9	406.9	394.8	389.0	380.0	365.9
67.5°	312.7	383.7	416.0	394.4	380.3	349.8	338.4	331.9	326.8	320.7	308.8
70°	251.2	303.7	337.0	331.3	319.8	303.7	295.4	290.9	285.8	280.7	270.4
72.5°	201.9	238.1	269.4	272.3	262.9	259.7	252.3	250.5	247.4	241.2	235.5
75°	134.0	158.9	180.7	189.1	192.9	196.1	192.9	192.2	191.6	186.5	183.3
77.5°	87.8	101.3	115.0	129.2	135.2	139.6	140.6	142.9	141.2	138.5	137.0
80°	67.3	70.5	80.1	92.3	101.9	105.7	108.3	109.6	108.9	108.3	105.7
82.5°	48.8	51.5	56.0	64.6	72.6	79.1	80.6	80.4	81.8	82.2	80.1
85°	26.3	26.9	28.2	29.5	34.0	41.0	43.0	44.2	45.5	45.5	41.7
87.5°	11.2	10.2	10.8	10.4	11.5	11.7	14.3	16.6	17.4	15.7	16.1
90°	14.8	12.5	10.1	8.1	6.3	4.4	2.6	0.8	2.6	4.4	6.3
92.5°	28.5	27.2	25.9	24.6	23.4	22.2	21.0	19.7	21.0	22.2	23.4
95°	57.3	55.8	54.5	53.1	51.9	50.5	49.2	48.0	49.2	50.5	51.9
97.5°	92.1	91.1	90.0	89.0	88.1	87.2	86.3	85.3	86.3	87.2	88.1
100°	117.8	116.9	116.0	115.0	113.9	112.8	111.8	110.7	111.8	112.8	113.9
102.5°	145.9	144.7	143.5	142.6	141.9	141.3	140.6	140.0	140.6	141.3	141.9
105°	188.8	187.2	185.6	184.6	184.2	183.8	183.4	183.1	183.4	183.8	184.2
107.5°	235.9	235.2	234.6	234.2	233.9	233.7	233.5	233.3	233.5	233.7	233.9
110°	267.0	266.7	266.3	266.0	265.5	265.2	264.9	264.5	264.9	265.2	265.5



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	298.2	298.2	298.1	297.9	297.7	297.5	297.3	297.0	297.3	297.5	297.7
115°	347.4	347.8	348.1	348.1	347.5	347.0	346.4	345.8	346.4	347.0	347.5
117.5°	395.5	396.0	396.4	396.5	396.2	395.7	395.4	395.0	395.4	395.7	396.2
120°	428.3	429.2	430.1	430.0	428.9	427.8	426.7	425.7	426.7	427.8	428.9
122.5°	459.9	460.4	460.9	460.7	459.9	459.1	458.4	457.5	458.4	459.1	459.9
125°	507.8	508.1	508.5	508.3	507.8	507.3	506.8	506.2	506.8	507.3	507.8
127.5°	555.4	555.7	556.1	555.8	554.6	553.4	552.3	551.1	552.3	553.4	554.6
130°	586.2	586.8	587.3	586.9	585.4	584.0	582.5	581.1	582.5	584.0	585.4
132.5°	616.5	616.9	617.3	616.9	615.4	613.9	612.5	611.1	612.5	613.9	615.4
135°	661.2	661.4	661.5	661.1	660.0	658.9	657.9	656.8	657.9	658.9	660.0
137.5°	704.3	703.8	703.4	702.7	701.8	700.9	700.0	699.1	700.0	700.9	701.8
140°	732.9	732.7	732.5	732.0	731.1	730.2	729.3	728.4	729.3	730.2	731.1
142.5°	759.9	759.6	759.3	758.7	757.8	756.9	755.9	755.0	755.9	756.9	757.8
145°	799.7	799.2	798.7	798.2	797.9	797.4	797.1	796.7	797.1	797.4	797.9
147.5°	837.4	836.9	836.4	835.8	835.2	834.5	833.9	833.2	833.9	834.5	835.2
150°	861.1	860.8	860.4	860.1	859.7	859.3	859.0	858.6	859.0	859.3	859.7
152.5°	882.2	882.1	881.8	881.4	880.9	880.4	880.0	879.5	880.0	880.4	880.9
155°	912.7	912.6	912.4	912.3	912.3	912.3	912.3	912.3	912.3	912.3	912.3
157.5°	939.7	939.6	939.4	939.5	939.6	939.9	940.1	940.3	940.1	939.9	939.6
160°	956.3	956.3	956.3	956.4	956.8	957.2	957.5	957.9	957.5	957.2	956.8
162.5°	971.6	971.4	971.3	971.5	972.0	972.5	973.0	973.5	973.0	972.5	972.0
165°	991.2	991.2	991.2	991.6	992.1	992.6	993.1	993.7	993.1	992.6	992.1
167.5°	1006.9	1006.8	1006.7	1006.9	1007.6	1008.4	1009.1	1009.8	1009.1	1008.4	1007.6
170°	1015.7	1015.7	1015.7	1016.0	1016.8	1017.5	1018.2	1019.0	1018.2	1017.5	1016.8
172.5°	1022.8	1022.8	1022.8	1023.2	1023.9	1024.7	1025.4	1026.1	1025.4	1024.7	1023.9
175°	1030.3	1030.3	1030.3	1030.7	1031.4	1032.1	1032.8	1033.6	1032.8	1032.1	1031.4
177.5°	1034.0	1034.0	1034.0	1034.4	1034.9	1035.5	1036.1	1036.7	1036.1	1035.5	1034.9
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1471.3	1464.6	1460.0	1449.8	1443.1	1435.9	1428.7	1433.4	1432.8	1432.3	1432.3
5°	1422.0	1407.2	1393.8	1376.5	1365.5	1352.1	1341.8	1340.5	1343.1	1334.2	1329.0
7.5°	1373.0	1352.8	1333.7	1314.7	1294.5	1278.3	1268.1	1263.4	1256.9	1251.3	1245.6
10°	1338.6	1314.9	1296.3	1272.6	1250.8	1231.6	1219.4	1211.1	1206.6	1202.2	1193.8
12.5°	1303.3	1280.1	1256.4	1229.6	1208.8	1186.5	1177.4	1168.1	1159.4	1154.5	1143.0
15°	1251.5	1221.4	1196.4	1168.2	1145.1	1123.3	1110.5	1091.9	1089.3	1083.0	1071.4
17.5°	1199.5	1166.9	1132.5	1111.5	1085.5	1062.8	1043.3	1037.1	1018.7	1011.8	1001.8
20°	1158.5	1128.5	1102.2	1074.6	1036.8	1015.7	1000.3	992.0	977.2	968.2	961.8
22.5°	1123.2	1092.6	1062.2	1030.0	998.9	975.2	963.9	951.0	942.9	930.3	923.4
25°	1072.7	1039.3	1002.8	968.2	945.8	927.9	910.0	898.4	886.9	881.1	868.3
27.5°	1014.0	979.2	945.0	918.8	891.2	873.5	857.3	847.0	833.2	823.5	816.4
30°	981.7	940.7	911.2	887.5	852.2	835.6	823.5	810.7	800.4	790.1	783.1
32.5°	944.3	906.9	878.9	849.5	822.6	804.3	788.6	777.3	768.6	758.8	751.8
35°	885.6	854.2	825.3	795.9	776.0	757.4	738.8	729.2	720.9	711.9	705.6
37.5°	832.5	803.2	775.8	747.8	723.2	708.1	693.1	685.7	674.5	668.5	661.9
40°	799.7	770.9	741.4	714.5	688.8	677.4	663.9	653.0	642.7	638.2	631.2
42.5°	763.9	735.0	710.1	681.2	660.1	644.5	632.1	620.2	612.5	605.9	601.9
45°	710.6	685.0	660.6	631.9	612.0	598.5	584.4	573.5	566.5	562.0	554.9
47.5°	659.0	633.4	608.6	583.5	564.3	548.9	534.8	527.3	517.9	512.4	507.6
50°	621.6	598.5	572.3	549.2	529.9	514.5	503.0	493.4	485.1	478.0	474.8
52.5°	587.3	562.6	540.0	518.4	498.1	480.7	470.2	460.1	453.8	445.7	442.1
55°	530.6	506.9	487.6	466.5	446.6	431.9	419.1	410.1	403.7	394.8	389.6
57.5°	477.4	456.2	433.2	414.8	394.4	381.9	371.3	359.1	351.3	344.2	339.2
60°	441.5	417.2	397.3	380.0	362.1	346.0	336.4	326.8	318.5	311.4	307.0
62.5°	404.1	382.8	363.9	345.1	328.7	314.8	303.6	295.5	288.2	283.7	279.2
65°	346.7	330.0	310.8	295.4	280.1	269.8	260.8	253.7	248.7	245.4	241.6
67.5°	293.8	277.7	260.9	245.8	235.5	227.7	221.8	215.8	213.3	209.1	206.6
70°	259.5	242.9	228.1	216.6	206.4	200.6	196.7	192.2	189.6	184.6	182.0
72.5°	222.1	210.0	199.4	190.0	181.7	176.5	171.6	166.1	162.0	156.4	153.8
75°	175.0	164.0	155.7	149.3	144.1	137.1	130.1	124.3	122.4	120.5	119.8
77.5°	129.6	122.6	116.6	111.2	104.8	99.7	98.2	96.9	96.5	95.5	95.5
80°	101.9	95.5	91.0	84.5	80.7	80.7	80.7	79.5	80.1	80.1	80.1
82.5°	75.7	69.9	67.4	65.1	64.3	64.8	64.8	65.1	64.7	65.7	65.2
85°	39.1	39.7	41.0	40.4	41.0	41.0	42.3	41.7	42.3	41.0	42.3
87.5°	16.0	17.9	18.9	19.9	20.9	20.8	21.4	21.6	22.3	22.4	22.5
90°	8.1	10.1	12.5	14.8	17.2	19.6	20.2	21.0	21.7	22.4	23.0
92.5°	24.6	25.9	27.2	28.5	29.9	31.2	31.8	32.4	33.0	33.6	33.8
95°	53.1	54.5	55.8	57.3	58.8	60.3	61.0	61.6	62.4	63.1	63.5
97.5°	89.0	90.0	91.1	92.1	93.2	94.2	95.1	95.9	96.8	97.6	97.9
100°	115.0	116.0	116.9	117.8	118.7	119.6	120.2	120.7	121.2	121.8	122.3
102.5°	142.6	143.5	144.7	145.9	147.1	148.3	148.8	149.4	149.9	150.4	150.7
105°	184.6	185.6	187.2	188.8	190.5	192.1	192.1	192.1	192.1	192.1	192.2
107.5°	234.2	234.6	235.2	235.9	236.5	237.2	237.7	238.3	238.9	239.5	239.6
110°	266.0	266.3	266.7	267.0	267.4	267.7	268.5	269.2	269.9	270.7	270.8



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	297.9	298.1	298.2	298.2	298.3	298.3	299.2	300.1	300.9	301.8	302.2
115°	348.1	348.1	347.8	347.4	347.1	346.7	346.9	347.1	347.2	347.4	347.4
117.5°	396.5	396.4	396.0	395.5	395.0	394.5	394.5	394.4	394.4	394.4	394.1
120°	430.0	430.1	429.2	428.3	427.4	426.5	426.2	426.1	425.9	425.7	425.4
122.5°	460.7	460.9	460.4	459.9	459.5	459.0	458.5	458.0	457.6	457.1	456.6
125°	508.3	508.5	508.1	507.8	507.4	507.0	506.3	505.6	504.8	504.1	503.4
127.5°	555.8	556.1	555.7	555.4	555.0	554.6	553.5	552.5	551.5	550.5	549.6
130°	586.9	587.3	586.8	586.2	585.7	585.1	584.4	583.7	582.9	582.3	581.2
132.5°	616.9	617.3	616.9	616.5	616.1	615.7	614.9	614.0	613.2	612.3	611.4
135°	661.1	661.5	661.4	661.2	661.0	660.8	660.1	659.4	658.7	657.9	657.4
137.5°	702.7	703.4	703.8	704.3	704.8	705.2	704.5	703.8	703.0	702.2	701.5
140°	732.0	732.5	732.7	732.9	733.1	733.3	733.1	732.9	732.7	732.5	731.8
142.5°	758.7	759.3	759.6	759.9	760.3	760.6	760.4	760.3	760.1	759.9	759.3
145°	798.2	798.7	799.2	799.7	800.3	800.8	800.6	800.5	800.3	800.1	799.6
147.5°	835.8	836.4	836.9	837.4	837.9	838.5	838.5	838.5	838.5	838.5	837.9
150°	860.1	860.4	860.8	861.1	861.5	861.9	861.9	861.9	861.9	861.9	861.3
152.5°	881.4	881.8	882.1	882.2	882.5	882.7	883.0	883.3	883.5	883.9	883.5
155°	912.3	912.4	912.6	912.7	913.0	913.1	913.9	914.6	915.3	916.0	915.7
157.5°	939.5	939.4	939.6	939.7	939.9	940.0	940.8	941.5	942.2	943.1	942.9
160°	956.4	956.3	956.3	956.3	956.3	956.3	957.2	958.1	959.0	959.9	959.9
162.5°	971.5	971.3	971.4	971.6	971.8	971.9	972.8	973.7	974.6	975.5	975.3
165°	991.6	991.2	991.2	991.2	991.2	991.2	992.3	993.4	994.5	995.6	995.5
167.5°	1006.9	1006.7	1006.8	1006.9	1007.1	1007.2	1008.4	1009.4	1010.6	1011.7	1011.7
170°	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9	1018.2	1019.5	1020.8	1020.8
172.5°	1023.2	1022.8	1022.8	1022.8	1022.8	1022.8	1023.9	1025.1	1026.2	1027.3	1027.3
175°	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4	1032.5	1033.6	1034.7	1034.5
177.5°	1034.4	1034.0	1034.0	1034.0	1034.0	1034.0	1034.9	1035.8	1036.7	1037.5	1037.5
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1426.2	1425.6	1426.2	1424.1	1426.2	1425.6	1426.2	1432.3	1432.3	1432.8	1433.4
5°	1327.1	1326.5	1324.5	1318.7	1324.5	1326.5	1327.1	1329.0	1334.2	1343.1	1340.5
7.5°	1240.6	1239.7	1234.0	1234.2	1234.0	1239.7	1240.6	1245.6	1251.3	1256.9	1263.4
10°	1189.4	1189.9	1182.3	1177.8	1182.3	1189.9	1189.4	1193.8	1202.2	1206.6	1211.1
12.5°	1139.6	1136.7	1130.5	1125.5	1130.5	1136.7	1139.6	1143.0	1154.5	1159.4	1168.1
15°	1074.0	1067.6	1052.2	1053.4	1052.2	1067.6	1074.0	1071.4	1083.0	1089.3	1091.9
17.5°	996.7	992.0	991.7	982.8	991.7	992.0	996.7	1001.8	1011.8	1018.7	1037.1
20°	951.6	948.4	949.7	940.7	949.7	948.4	951.6	961.8	968.2	977.2	992.0
22.5°	916.2	913.0	907.6	904.8	907.6	913.0	916.2	923.4	930.3	942.9	951.0
25°	864.5	859.3	854.2	857.4	854.2	859.3	864.5	868.3	881.1	886.9	898.4
27.5°	812.7	808.9	803.7	803.1	803.7	808.9	812.7	816.4	823.5	833.2	847.0
30°	779.8	776.0	773.5	770.2	773.5	776.0	779.8	783.1	790.1	800.4	810.7
32.5°	746.6	745.8	741.2	740.5	741.2	745.8	746.6	751.8	758.8	768.6	777.3
35°	703.0	699.1	697.8	698.5	697.8	699.1	703.0	705.6	711.9	720.9	729.2
37.5°	661.5	656.4	654.1	651.8	654.1	656.4	661.5	661.9	668.5	674.5	685.7
40°	631.9	626.7	625.4	624.1	625.4	626.7	631.9	631.2	638.2	642.7	653.0
42.5°	598.5	596.5	595.7	593.4	595.7	596.5	598.5	601.9	605.9	612.5	620.2
45°	553.0	552.4	548.5	549.8	548.5	552.4	553.0	554.9	562.0	566.5	573.5
47.5°	505.1	502.2	499.5	501.3	499.5	502.2	505.1	507.6	512.4	517.9	527.3
50°	472.3	471.0	465.2	466.5	465.2	471.0	472.3	474.8	478.0	485.1	493.4
52.5°	439.4	434.6	432.4	431.6	432.4	434.6	439.4	442.1	445.7	453.8	460.1
55°	385.1	379.4	376.7	375.5	376.7	379.4	385.1	389.6	394.8	403.7	410.1
57.5°	331.8	330.3	328.2	329.6	328.2	330.3	331.8	339.2	344.2	351.3	359.1
60°	300.5	300.5	300.5	299.9	300.5	300.5	300.5	307.0	311.4	318.5	326.8
62.5°	276.5	274.9	274.4	275.3	274.4	274.9	276.5	279.2	283.7	288.2	295.5
65°	239.7	239.0	236.4	235.8	236.4	239.0	239.7	241.6	245.4	248.7	253.7
67.5°	205.0	202.6	201.9	201.0	201.9	202.6	205.0	206.6	209.1	213.3	215.8
70°	178.8	177.5	173.7	174.3	173.7	177.5	178.8	182.0	184.6	189.6	192.2
72.5°	150.6	149.3	148.5	147.7	148.5	149.3	150.6	153.8	156.4	162.0	166.1
75°	119.2	118.5	117.9	120.5	117.9	118.5	119.2	119.8	120.5	122.4	124.3
77.5°	95.5	95.5	95.9	94.8	95.9	95.5	95.5	95.5	95.5	96.5	96.9
80°	80.1	80.1	79.5	79.5	79.5	80.1	80.1	80.1	80.1	80.1	79.5
82.5°	64.2	64.7	65.1	64.1	65.1	64.7	64.2	65.2	65.7	64.7	65.1
85°	42.3	41.7	43.0	42.3	43.0	41.7	42.3	42.3	41.0	42.3	41.7
87.5°	23.6	22.7	22.7	23.3	22.7	22.7	23.6	22.5	22.4	22.3	21.6
90°	23.3	23.7	24.1	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0
92.5°	33.5	33.3	33.1	32.9	33.1	33.3	33.5	33.8	33.6	33.0	32.4
95°	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.5	63.1	62.4	61.6
97.5°	97.9	97.8	97.8	97.7	97.8	97.8	97.9	97.9	97.6	96.8	95.9
100°	122.6	122.9	123.4	123.7	123.4	122.9	122.6	122.3	121.8	121.2	120.7
102.5°	150.6	150.5	150.5	150.4	150.5	150.5	150.6	150.7	150.4	149.9	149.4
105°	192.6	193.0	193.3	193.7	193.3	193.0	192.6	192.2	192.1	192.1	192.1
107.5°	239.5	239.2	239.0	238.8	239.0	239.2	239.5	239.6	239.5	238.9	238.3
110°	270.4	270.1	269.8	269.4	269.8	270.1	270.4	270.8	270.7	269.9	269.2



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	302.1	302.1	302.0	301.9	302.0	302.1	302.1	302.2	301.8	300.9	300.1
115°	347.2	347.1	346.9	346.7	346.9	347.1	347.2	347.4	347.4	347.2	347.1
117.5°	393.6	393.1	392.6	392.1	392.6	393.1	393.6	394.1	394.4	394.4	394.4
120°	425.1	424.8	424.4	424.0	424.4	424.8	425.1	425.4	425.7	425.9	426.1
122.5°	456.2	455.6	455.1	454.6	455.1	455.6	456.2	456.6	457.1	457.6	458.0
125°	502.7	502.0	501.2	500.5	501.2	502.0	502.7	503.4	504.1	504.8	505.6
127.5°	548.8	547.9	547.1	546.3	547.1	547.9	548.8	549.6	550.5	551.5	552.5
130°	580.0	578.7	577.5	576.2	577.5	578.7	580.0	581.2	582.3	582.9	583.7
132.5°	610.4	609.4	608.5	607.5	608.5	609.4	610.4	611.4	612.3	613.2	614.0
135°	657.0	656.6	656.3	656.0	656.3	656.6	657.0	657.4	657.9	658.7	659.4
137.5°	700.8	700.1	699.4	698.8	699.4	700.1	700.8	701.5	702.2	703.0	703.8
140°	730.6	729.3	728.1	726.8	728.1	729.3	730.6	731.8	732.5	732.7	732.9
142.5°	758.3	757.3	756.4	755.4	756.4	757.3	758.3	759.3	759.9	760.1	760.3
145°	798.9	798.2	797.4	796.7	797.4	798.2	798.9	799.6	800.1	800.3	800.5
147.5°	836.8	835.7	834.6	833.6	834.6	835.7	836.8	837.9	838.5	838.5	838.5
150°	860.2	859.2	858.0	857.0	858.0	859.2	860.2	861.3	861.9	861.9	861.9
152.5°	882.6	881.7	880.7	879.8	880.7	881.7	882.6	883.5	883.9	883.5	883.3
155°	914.5	913.2	911.9	910.7	911.9	913.2	914.5	915.7	916.0	915.3	914.6
157.5°	941.9	940.9	939.9	938.8	939.9	940.9	941.9	942.9	943.1	942.2	941.5
160°	959.3	958.5	957.8	957.1	957.8	958.5	959.3	959.9	959.9	959.0	958.1
162.5°	974.2	973.1	971.9	970.8	971.9	973.1	974.2	975.3	975.5	974.6	973.7
165°	994.3	993.0	991.7	990.4	991.7	993.0	994.3	995.5	995.6	994.5	993.4
167.5°	1010.6	1009.4	1008.4	1007.2	1008.4	1009.4	1010.6	1011.7	1011.7	1010.6	1009.4
170°	1019.5	1018.2	1016.9	1015.7	1016.9	1018.2	1019.5	1020.8	1020.8	1019.5	1018.2
172.5°	1026.0	1024.7	1023.4	1022.1	1023.4	1024.7	1026.0	1027.3	1027.3	1026.2	1025.1
175°	1033.3	1032.0	1030.8	1029.5	1030.8	1032.0	1033.3	1034.5	1034.7	1033.6	1032.5
177.5°	1036.5	1035.4	1034.5	1033.4	1034.5	1035.4	1036.5	1037.5	1037.5	1036.7	1035.8
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1428.7	1435.9	1443.1	1449.8	1460.0	1464.6	1471.3	1473.8	1481.6	1492.8	1502.0
5°	1341.8	1352.1	1365.5	1376.5	1393.8	1407.2	1422.0	1436.1	1452.7	1476.4	1497.5
7.5°	1268.1	1278.3	1294.5	1314.7	1333.7	1352.8	1373.0	1392.2	1416.0	1450.0	1483.7
10°	1219.4	1231.6	1250.8	1272.6	1296.3	1314.9	1338.6	1363.0	1392.4	1431.6	1471.9
12.5°	1177.4	1186.5	1208.8	1229.6	1256.4	1280.1	1303.3	1331.7	1365.3	1407.0	1455.5
15°	1110.5	1123.3	1145.1	1168.2	1196.4	1221.4	1251.5	1286.1	1318.7	1370.0	1429.0
17.5°	1043.3	1062.8	1085.5	1111.5	1132.5	1166.9	1199.5	1235.1	1275.3	1329.7	1394.4
20°	1000.3	1015.7	1036.8	1074.6	1102.2	1128.5	1158.5	1202.8	1239.9	1301.5	1368.7
22.5°	963.9	975.2	998.9	1030.0	1062.2	1092.6	1123.2	1165.4	1211.2	1269.7	1342.6
25°	910.0	927.9	945.8	968.2	1002.8	1039.3	1072.7	1108.6	1157.3	1219.4	1298.3
27.5°	857.3	873.5	891.2	918.8	945.0	979.2	1014.0	1055.2	1107.4	1173.2	1253.1
30°	823.5	835.6	852.2	887.5	911.2	940.7	981.7	1018.2	1066.9	1136.8	1221.4
32.5°	788.6	804.3	822.6	849.5	878.9	906.9	944.3	983.9	1033.6	1102.4	1189.0
35°	738.8	757.4	776.0	795.9	825.3	854.2	885.6	929.2	979.7	1046.4	1131.6
37.5°	693.1	708.1	723.2	747.8	775.8	803.2	832.5	875.5	923.2	995.1	1073.2
40°	663.9	677.4	688.8	714.5	741.4	770.9	799.7	837.6	888.8	956.1	1031.7
42.5°	632.1	644.5	660.1	681.2	710.1	735.0	763.9	799.6	847.7	916.1	982.4
45°	584.4	598.5	612.0	631.9	660.6	685.0	710.6	744.6	793.9	850.4	909.3
47.5°	534.8	548.9	564.3	583.5	608.6	633.4	659.0	689.1	734.1	789.5	829.2
50°	503.0	514.5	529.9	549.2	572.3	598.5	621.6	654.3	697.2	740.8	775.3
52.5°	470.2	480.7	498.1	518.4	540.0	562.6	587.3	615.3	654.1	695.1	722.6
55°	419.1	431.9	446.6	466.5	487.6	506.9	530.6	559.5	590.2	620.9	639.5
57.5°	371.3	381.9	394.4	414.8	433.2	456.2	477.4	499.9	528.3	551.5	563.6
60°	336.4	346.0	362.1	380.0	397.3	417.2	441.5	463.9	485.8	504.3	513.9
62.5°	303.6	314.8	328.7	345.1	363.9	382.8	404.1	422.9	442.1	458.2	464.7
65°	260.8	269.8	280.1	295.4	310.8	330.0	346.7	365.9	380.0	389.0	394.8
67.5°	221.8	227.7	235.5	245.8	260.9	277.7	293.8	308.8	320.7	326.8	331.9
70°	196.7	200.6	206.4	216.6	228.1	242.9	259.5	270.4	280.7	285.8	290.9
72.5°	171.6	176.5	181.7	190.0	199.4	210.0	222.1	235.5	241.2	247.4	250.5
75°	130.1	137.1	144.1	149.3	155.7	164.0	175.0	183.3	186.5	191.6	192.2
77.5°	98.2	99.7	104.8	111.2	116.6	122.6	129.6	137.0	138.5	141.2	142.9
80°	80.7	80.7	80.7	84.5	91.0	95.5	101.9	105.7	108.3	108.9	109.6
82.5°	64.8	64.8	64.3	65.1	67.4	69.9	75.7	80.1	82.2	81.8	80.4
85°	42.3	41.0	41.0	40.4	41.0	39.7	39.1	41.7	45.5	45.5	44.2
87.5°	21.4	20.8	20.9	19.9	18.9	17.9	16.0	16.1	15.7	17.4	16.6
90°	20.2	19.6	17.2	14.8	12.5	10.1	8.1	6.3	4.4	2.6	0.8
92.5°	31.8	31.2	29.9	28.5	27.2	25.9	24.6	23.4	22.2	21.0	19.7
95°	61.0	60.3	58.8	57.3	55.8	54.5	53.1	51.9	50.5	49.2	48.0
97.5°	95.1	94.2	93.2	92.1	91.1	90.0	89.0	88.1	87.2	86.3	85.3
100°	120.2	119.6	118.7	117.8	116.9	116.0	115.0	113.9	112.8	111.8	110.7
102.5°	148.8	148.3	147.1	145.9	144.7	143.5	142.6	141.9	141.3	140.6	140.0
105°	192.1	192.1	190.5	188.8	187.2	185.6	184.6	184.2	183.8	183.4	183.1
107.5°	237.7	237.2	236.5	235.9	235.2	234.6	234.2	233.9	233.7	233.5	233.3
110°	268.5	267.7	267.4	267.0	266.7	266.3	266.0	265.5	265.2	264.9	264.5



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	299.2	298.3	298.3	298.2	298.2	298.1	297.9	297.7	297.5	297.3	297.0
115°	346.9	346.7	347.1	347.4	347.8	348.1	348.1	347.5	347.0	346.4	345.8
117.5°	394.5	394.5	395.0	395.5	396.0	396.4	396.5	396.2	395.7	395.4	395.0
120°	426.2	426.5	427.4	428.3	429.2	430.1	430.0	428.9	427.8	426.7	425.7
122.5°	458.5	459.0	459.5	459.9	460.4	460.9	460.7	459.9	459.1	458.4	457.5
125°	506.3	507.0	507.4	507.8	508.1	508.5	508.3	507.8	507.3	506.8	506.2
127.5°	553.5	554.6	555.0	555.4	555.7	556.1	555.8	554.6	553.4	552.3	551.1
130°	584.4	585.1	585.7	586.2	586.8	587.3	586.9	585.4	584.0	582.5	581.1
132.5°	614.9	615.7	616.1	616.5	616.9	617.3	616.9	615.4	613.9	612.5	611.1
135°	660.1	660.8	661.0	661.2	661.4	661.5	661.1	660.0	658.9	657.9	656.8
137.5°	704.5	705.2	704.8	704.3	703.8	703.4	702.7	701.8	700.9	700.0	699.1
140°	733.1	733.3	733.1	732.9	732.7	732.5	732.0	731.1	730.2	729.3	728.4
142.5°	760.4	760.6	760.3	759.9	759.6	759.3	758.7	757.8	756.9	755.9	755.0
145°	800.6	800.8	800.3	799.7	799.2	798.7	798.2	797.9	797.4	797.1	796.7
147.5°	838.5	838.5	837.9	837.4	836.9	836.4	835.8	835.2	834.5	833.9	833.2
150°	861.9	861.9	861.5	861.1	860.8	860.4	860.1	859.7	859.3	859.0	858.6
152.5°	883.0	882.7	882.5	882.2	882.1	881.8	881.4	880.9	880.4	880.0	879.5
155°	913.9	913.1	913.0	912.7	912.6	912.4	912.3	912.3	912.3	912.3	912.3
157.5°	940.8	940.0	939.9	939.7	939.6	939.4	939.5	939.6	939.9	940.1	940.3
160°	957.2	956.3	956.3	956.3	956.3	956.3	956.4	956.8	957.2	957.5	957.9
162.5°	972.8	971.9	971.8	971.6	971.4	971.3	971.5	972.0	972.5	973.0	973.5
165°	992.3	991.2	991.2	991.2	991.2	991.2	991.6	992.1	992.6	993.1	993.7
167.5°	1008.4	1007.2	1007.1	1006.9	1006.8	1006.7	1006.9	1007.6	1008.4	1009.1	1009.8
170°	1016.9	1015.7	1015.7	1015.7	1015.7	1015.7	1016.0	1016.8	1017.5	1018.2	1019.0
172.5°	1023.9	1022.8	1022.8	1022.8	1022.8	1022.8	1023.2	1023.9	1024.7	1025.4	1026.1
175°	1031.4	1030.3	1030.3	1030.3	1030.3	1030.3	1030.7	1031.4	1032.1	1032.8	1033.6
177.5°	1034.9	1034.0	1034.0	1034.0	1034.0	1034.0	1034.4	1034.9	1035.5	1036.1	1036.7
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1505.1	1510.7	1517.9	1528.7	1536.9	1544.1	1545.6	1547.7	1552.8	1561.5	1568.1
5°	1514.8	1529.6	1553.3	1576.4	1601.3	1621.9	1641.1	1654.6	1667.4	1694.3	1716.0
7.5°	1511.8	1544.6	1581.8	1623.2	1665.1	1705.7	1743.4	1777.0	1810.6	1849.8	1894.6
10°	1509.7	1548.2	1598.1	1651.3	1709.7	1766.7	1821.8	1864.8	1914.7	1959.6	2016.6
12.5°	1500.0	1555.3	1615.1	1683.1	1754.8	1820.5	1893.0	1952.4	2009.5	2074.4	2140.6
15°	1487.3	1554.6	1630.2	1720.5	1829.5	1908.9	1983.3	2086.4	2157.0	2227.4	2322.3
17.5°	1464.1	1546.2	1640.7	1758.1	1848.9	1955.7	2067.6	2149.1	2244.1	2343.4	2429.3
20°	1445.6	1541.2	1646.8	1762.2	1878.2	1994.1	2102.5	2199.8	2297.9	2412.6	2483.1
22.5°	1427.2	1521.7	1631.5	1754.0	1878.7	2000.8	2123.4	2237.8	2348.1	2463.9	2553.8
25°	1388.0	1500.2	1619.3	1744.3	1867.3	2001.9	2148.0	2275.5	2412.0	2531.2	2616.4
27.5°	1348.3	1451.0	1569.7	1696.5	1833.2	1992.3	2164.1	2309.1	2445.8	2531.2	2557.9
30°	1312.4	1421.3	1530.2	1659.1	1807.0	1984.5	2167.1	2333.1	2445.3	2482.4	2454.9
32.5°	1275.9	1374.7	1482.5	1614.5	1771.6	1965.6	2171.3	2318.8	2386.3	2357.9	2245.7
35°	1211.8	1300.8	1405.2	1537.2	1718.0	1955.1	2154.3	2254.3	2237.7	2077.5	1866.0
37.5°	1143.0	1215.6	1312.4	1450.4	1662.4	1913.4	2081.5	2096.3	1952.2	1706.2	1461.9
40°	1088.8	1154.1	1253.4	1397.6	1619.3	1872.4	2008.2	1948.6	1725.0	1451.4	1247.7
42.5°	1035.9	1091.0	1186.7	1342.2	1578.3	1816.6	1899.1	1769.3	1511.2	1252.5	1067.2
45°	946.5	998.3	1094.5	1254.0	1494.4	1709.7	1698.8	1473.2	1215.0	1006.7	852.9
47.5°	861.6	907.0	997.2	1160.1	1395.8	1549.5	1447.6	1207.5	988.5	821.4	711.7
50°	801.6	846.5	936.2	1097.1	1316.9	1429.0	1283.5	1052.2	851.7	713.2	626.1
52.5°	744.2	788.1	870.1	1026.8	1221.5	1288.5	1132.3	917.9	750.6	631.2	556.4
55°	663.9	697.2	770.9	920.8	1066.3	1081.7	923.4	744.0	606.2	522.9	471.7
57.5°	582.0	610.7	683.5	802.9	904.9	897.0	746.9	591.7	499.0	437.0	399.8
60°	528.6	556.8	620.9	723.5	800.4	773.5	635.7	510.7	431.3	385.8	356.3
62.5°	478.9	501.0	560.9	635.8	691.1	660.6	543.4	439.9	376.9	338.6	315.3
65°	406.9	424.9	472.9	512.0	542.7	513.3	415.9	344.1	298.6	271.7	255.7
67.5°	338.4	349.8	380.3	394.4	416.0	383.7	312.7	264.6	238.8	216.1	205.0
70°	295.4	303.7	319.8	331.3	337.0	303.7	251.2	216.0	194.1	178.1	171.1
72.5°	252.3	259.7	262.9	272.3	269.4	238.1	201.9	173.9	158.2	147.4	138.3
75°	192.9	196.1	192.9	189.1	180.7	158.9	134.0	119.8	108.3	103.1	100.0
77.5°	140.6	139.6	135.2	129.2	115.0	101.3	87.8	83.1	78.0	75.3	74.2
80°	108.3	105.7	101.9	92.3	80.1	70.5	67.3	64.1	62.1	58.9	58.3
82.5°	80.6	79.1	72.6	64.6	56.0	51.5	48.8	47.7	45.7	44.1	43.9
85°	43.0	41.0	34.0	29.5	28.2	26.9	26.3	26.3	23.7	23.1	23.1
87.5°	14.3	11.7	11.5	10.4	10.8	10.2	11.2	10.6	10.6	11.3	10.4
90°	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2	21.0
92.5°	21.0	22.2	23.4	24.6	25.9	27.2	28.5	29.9	31.2	31.8	32.4
95°	49.2	50.5	51.9	53.1	54.5	55.8	57.3	58.8	60.3	61.0	61.6
97.5°	86.3	87.2	88.1	89.0	90.0	91.1	92.1	93.2	94.2	95.1	95.9
100°	111.8	112.8	113.9	115.0	116.0	116.9	117.8	118.7	119.6	120.2	120.7
102.5°	140.6	141.3	141.9	142.6	143.5	144.7	145.9	147.1	148.3	148.8	149.4
105°	183.4	183.8	184.2	184.6	185.6	187.2	188.8	190.5	192.1	192.1	192.1
107.5°	233.5	233.7	233.9	234.2	234.6	235.2	235.9	236.5	237.2	237.7	238.3
110°	264.9	265.2	265.5	266.0	266.3	266.7	267.0	267.4	267.7	268.5	269.2



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	297.3	297.5	297.7	297.9	298.1	298.2	298.2	298.3	298.3	299.2	300.1
115°	346.4	347.0	347.5	348.1	348.1	347.8	347.4	347.1	346.7	346.9	347.1
117.5°	395.4	395.7	396.2	396.5	396.4	396.0	395.5	395.0	394.5	394.5	394.4
120°	426.7	427.8	428.9	430.0	430.1	429.2	428.3	427.4	426.5	426.2	426.1
122.5°	458.4	459.1	459.9	460.7	460.9	460.4	459.9	459.5	459.0	458.5	458.0
125°	506.8	507.3	507.8	508.3	508.5	508.1	507.8	507.4	507.0	506.3	505.6
127.5°	552.3	553.4	554.6	555.8	556.1	555.7	555.4	555.0	554.6	553.5	552.5
130°	582.5	584.0	585.4	586.9	587.3	586.8	586.2	585.7	585.1	584.4	583.7
132.5°	612.5	613.9	615.4	616.9	617.3	616.9	616.5	616.1	615.7	614.9	614.0
135°	657.9	658.9	660.0	661.1	661.5	661.4	661.2	661.0	660.8	660.1	659.4
137.5°	700.0	700.9	701.8	702.7	703.4	703.8	704.3	704.8	705.2	704.5	703.8
140°	729.3	730.2	731.1	732.0	732.5	732.7	732.9	733.1	733.3	733.1	732.9
142.5°	755.9	756.9	757.8	758.7	759.3	759.6	759.9	760.3	760.6	760.4	760.3
145°	797.1	797.4	797.9	798.2	798.7	799.2	799.7	800.3	800.8	800.6	800.5
147.5°	833.9	834.5	835.2	835.8	836.4	836.9	837.4	837.9	838.5	838.5	838.5
150°	859.0	859.3	859.7	860.1	860.4	860.8	861.1	861.5	861.9	861.9	861.9
152.5°	880.0	880.4	880.9	881.4	881.8	882.1	882.2	882.5	882.7	883.0	883.3
155°	912.3	912.3	912.3	912.3	912.4	912.6	912.7	913.0	913.1	913.9	914.6
157.5°	940.1	939.9	939.6	939.5	939.4	939.6	939.7	939.9	940.0	940.8	941.5
160°	957.5	957.2	956.8	956.4	956.3	956.3	956.3	956.3	956.3	957.2	958.1
162.5°	973.0	972.5	972.0	971.5	971.3	971.4	971.6	971.8	971.9	972.8	973.7
165°	993.1	992.6	992.1	991.6	991.2	991.2	991.2	991.2	991.2	992.3	993.4
167.5°	1009.1	1008.4	1007.6	1006.9	1006.7	1006.8	1006.9	1007.1	1007.2	1008.4	1009.4
170°	1018.2	1017.5	1016.8	1016.0	1015.7	1015.7	1015.7	1015.7	1015.7	1016.9	1018.2
172.5°	1025.4	1024.7	1023.9	1023.2	1022.8	1022.8	1022.8	1022.8	1022.8	1023.9	1025.1
175°	1032.8	1032.1	1031.4	1030.7	1030.3	1030.3	1030.3	1030.3	1030.3	1031.4	1032.5
177.5°	1036.1	1035.5	1034.9	1034.4	1034.0	1034.0	1034.0	1034.0	1034.0	1034.9	1035.8
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1578.9	1578.9	1580.9	1588.7	1589.7	1596.4	1594.3
5°	1735.3	1747.4	1751.9	1771.2	1782.7	1787.9	1777.6
7.5°	1926.5	1960.9	1977.1	1997.2	2015.1	2020.5	2006.5
10°	2066.0	2101.8	2131.9	2150.5	2167.8	2179.4	2194.1
12.5°	2200.7	2244.8	2273.5	2299.7	2317.5	2332.2	2334.5
15°	2347.2	2413.9	2464.5	2501.7	2520.3	2529.9	2526.0
17.5°	2495.0	2556.8	2592.8	2630.7	2656.5	2657.8	2658.5
20°	2578.5	2638.8	2680.5	2708.7	2737.5	2736.2	2742.6
22.5°	2634.5	2681.8	2713.8	2734.3	2744.1	2739.3	2740.5
25°	2660.6	2674.7	2669.0	2636.3	2628.0	2597.8	2602.9
27.5°	2525.8	2459.1	2390.2	2301.5	2231.6	2175.6	2178.5
30°	2342.8	2224.9	2090.3	1977.5	1876.2	1848.0	1787.9
32.5°	2086.9	1910.1	1752.5	1647.4	1560.5	1536.9	1484.3
35°	1653.3	1481.6	1319.4	1222.0	1183.6	1129.8	1129.1
37.5°	1285.1	1133.8	1048.1	975.0	936.7	904.2	901.0
40°	1081.0	963.1	898.4	845.9	808.0	783.7	778.0
42.5°	938.5	843.2	782.5	750.0	720.9	708.3	699.0
45°	766.4	702.3	660.0	630.6	617.1	607.5	602.3
47.5°	641.1	598.1	569.3	549.7	538.7	528.6	531.3
50°	572.9	537.6	516.5	497.9	489.6	482.5	483.1
52.5°	518.0	486.4	469.3	455.8	445.5	440.5	438.1
55°	439.6	419.7	402.4	392.8	387.0	380.0	378.1
57.5°	375.0	359.6	345.5	334.6	333.2	326.4	327.3
60°	331.9	319.1	307.6	301.8	297.3	291.6	293.5
62.5°	296.5	285.8	275.3	270.5	266.0	261.8	262.7
65°	242.9	232.6	226.2	223.6	221.7	219.8	217.8
67.5°	193.6	187.3	183.3	177.7	173.8	173.2	171.2
70°	162.7	154.4	147.4	140.3	138.4	137.8	138.4
72.5°	130.4	125.2	123.3	119.8	119.4	117.8	119.0
75°	98.1	96.1	94.8	92.3	92.3	92.3	92.3
77.5°	72.3	71.1	70.4	69.9	69.2	68.3	68.2
80°	56.4	55.8	54.5	54.5	53.8	54.5	53.8
82.5°	42.6	42.4	41.2	41.2	40.5	40.1	40.5
85°	21.8	21.1	22.4	21.1	21.8	20.5	21.8
87.5°	10.5	10.6	10.3	10.3	9.9	10.9	10.0
90°	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	33.0	33.6	33.8	33.5	33.3	33.1	32.9
95°	62.4	63.1	63.5	63.5	63.5	63.5	63.5
97.5°	96.8	97.6	97.9	97.9	97.8	97.8	97.7
100°	121.2	121.8	122.3	122.6	122.9	123.4	123.7
102.5°	149.9	150.4	150.7	150.6	150.5	150.5	150.4
105°	192.1	192.1	192.2	192.6	193.0	193.3	193.7
107.5°	238.9	239.5	239.6	239.5	239.2	239.0	238.8
110°	269.9	270.7	270.8	270.4	270.1	269.8	269.4



TEST NUMBER: P332379-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	300.9	301.8	302.2	302.1	302.1	302.0	301.9
115°	347.2	347.4	347.4	347.2	347.1	346.9	346.7
117.5°	394.4	394.4	394.1	393.6	393.1	392.6	392.1
120°	425.9	425.7	425.4	425.1	424.8	424.4	424.0
122.5°	457.6	457.1	456.6	456.2	455.6	455.1	454.6
125°	504.8	504.1	503.4	502.7	502.0	501.2	500.5
127.5°	551.5	550.5	549.6	548.8	547.9	547.1	546.3
130°	582.9	582.3	581.2	580.0	578.7	577.5	576.2
132.5°	613.2	612.3	611.4	610.4	609.4	608.5	607.5
135°	658.7	657.9	657.4	657.0	656.6	656.3	656.0
137.5°	703.0	702.2	701.5	700.8	700.1	699.4	698.8
140°	732.7	732.5	731.8	730.6	729.3	728.1	726.8
142.5°	760.1	759.9	759.3	758.3	757.3	756.4	755.4
145°	800.3	800.1	799.6	798.9	798.2	797.4	796.7
147.5°	838.5	838.5	837.9	836.8	835.7	834.6	833.6
150°	861.9	861.9	861.3	860.2	859.2	858.0	857.0
152.5°	883.5	883.9	883.5	882.6	881.7	880.7	879.8
155°	915.3	916.0	915.7	914.5	913.2	911.9	910.7
157.5°	942.2	943.1	942.9	941.9	940.9	939.9	938.8
160°	959.0	959.9	959.9	959.3	958.5	957.8	957.1
162.5°	974.6	975.5	975.3	974.2	973.1	971.9	970.8
165°	994.5	995.6	995.5	994.3	993.0	991.7	990.4
167.5°	1010.6	1011.7	1011.7	1010.6	1009.4	1008.4	1007.2
170°	1019.5	1020.8	1020.8	1019.5	1018.2	1016.9	1015.7
172.5°	1026.2	1027.3	1027.3	1026.0	1024.7	1023.4	1022.1
175°	1033.6	1034.7	1034.5	1033.3	1032.0	1030.8	1029.5
177.5°	1036.7	1037.5	1037.5	1036.5	1035.4	1034.5	1033.4
180°	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0	1036.0

(END OF REPORT)