

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332380-930

Luminaire Tested: **S123RDIP-S1165D1025U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332380-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4  
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6754.8 lumens  
Efficiency: N/A  
Efficacy: 101.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	100	95	92	88	92	89	86	83	77	74	72	65	64	62	55	54	53	48
2	91	84	78	73	85	78	73	69	68	64	61	58	55	53	49	47	45	41
3	84	75	67	62	78	70	63	58	60	56	52	52	48	46	44	42	39	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	34	31
5	71	59	52	46	66	56	49	44	49	43	39	42	38	35	36	33	30	27
6	65	54	46	40	61	50	43	38	44	39	34	38	34	31	33	30	27	24
7	61	49	41	35	56	46	39	34	40	35	31	35	31	27	30	27	24	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	24	22	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	22	20	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	16113	16113	16113	16113
5°	19207	16181	14249	16181
10°	23981	16088	12873	16088
15°	28149	15924	11739	15924
20°	31416	15678	10775	15678
25°	30914	15419	10183	15419
30°	22222	15181	9573	15181
35°	14837	14870	9179	14870
40°	10932	14497	8769	14497
45°	9168	13842	8369	13842
50°	8090	12983	7812	12983
55°	7096	12001	7047	12001
60°	6318	11063	6456	11063
65°	5547	10055	6006	10055
70°	4356	9155	5485	9155
75°	3839	7993	5011	7993
80°	3335	6794	4928	6794
85°	2692	5459	5224	5459



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.2	2.2
10°-20°	459.9	6.8
20°-30°	722.5	10.7
30°-40°	753.8	11.2
40°-50°	645.1	9.6
50°-60°	491.7	7.3
60°-70°	315.1	4.7
70°-80°	151.6	2.2
80°-90°	43.2	0.6
90°-100°	223.7	3.3
100°-110°	633.5	9.4
110°-120°	623.2	9.2
120°-130°	497.1	7.4
130°-140°	391.9	5.8
140°-150°	292.5	4.3
150°-160°	203.9	3.0
160°-170°	119.8	1.8
170°-180°	39.0	0.6
0°-30°	1329.6	19.7
0°-40°	2083.4	30.8
0°-60°	3220.2	47.7
0°-90°	3730.2	55.2
90°-120°	1480.5	21.9
90°-150°	2662.0	39.4
90°-180°	3025.0	44.8
0°-180°	6754.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1497	1497	1497	1497	1497	
5°	1778	1498	1319	1498	1778	184
15°	2526	1429	1053	1429	2526	716
25°	2603	1298	857	1298	2603	1119
35°	1129	1132	698	1132	1129	740
45°	602	909	550	909	602	474
55°	378	640	376	640	378	342
65°	218	395	236	395	218	214
75°	92	192	120	192	92	99
85°	22	44	42	44	22	26
90°	24	2	24	2	24	13
95°	94	28	94	28	94	170
105°	1035	94	1035	94	1035	1021
115°	1259	167	1259	167	1259	1223
125°	993	232	993	232	993	900
135°	805	272	805	272	805	624
145°	629	310	629	310	629	400
155°	522	352	522	352	522	243
165°	455	385	455	385	455	130
175°	409	401	409	401	409	40
180°	402	402	402	402	402	



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1594.3	1596.4	1589.7	1588.7	1580.9	1578.9	1578.9	1568.1	1561.5	1552.8	1547.7
5°	1777.6	1787.9	1782.7	1771.2	1751.9	1747.4	1735.3	1716.0	1694.3	1667.4	1654.6
7.5°	2006.5	2020.5	2015.1	1997.2	1977.1	1960.9	1926.5	1894.6	1849.8	1810.6	1777.0
10°	2194.1	2179.4	2167.8	2150.5	2131.9	2101.8	2066.0	2016.6	1959.6	1914.7	1864.8
12.5°	2334.5	2332.2	2317.5	2299.7	2273.5	2244.8	2200.7	2140.6	2074.4	2009.5	1952.4
15°	2526.0	2529.9	2520.3	2501.7	2464.5	2413.9	2347.2	2322.3	2227.4	2157.0	2086.4
17.5°	2658.5	2657.8	2656.5	2630.7	2592.8	2556.8	2495.0	2429.3	2343.4	2244.1	2149.1
20°	2742.6	2736.2	2737.5	2708.7	2680.5	2638.8	2578.5	2483.1	2412.6	2297.9	2199.8
22.5°	2740.5	2739.3	2744.1	2734.3	2713.8	2681.8	2634.5	2553.8	2463.9	2348.1	2237.8
25°	2602.9	2597.8	2628.0	2636.3	2669.0	2674.7	2660.6	2616.4	2531.2	2412.0	2275.5
27.5°	2178.5	2175.6	2231.6	2301.5	2390.2	2459.1	2525.8	2557.9	2531.2	2445.8	2309.1
30°	1787.9	1848.0	1876.2	1977.5	2090.3	2224.9	2342.8	2454.9	2482.4	2445.3	2333.1
32.5°	1484.3	1536.9	1560.5	1647.4	1752.5	1910.1	2086.9	2245.7	2357.9	2386.3	2318.8
35°	1129.1	1129.8	1183.6	1222.0	1319.4	1481.6	1653.3	1866.0	2077.5	2237.7	2254.3
37.5°	901.0	904.2	936.7	975.0	1048.1	1133.8	1285.1	1461.9	1706.2	1952.2	2096.3
40°	778.0	783.7	808.0	845.9	898.4	963.1	1081.0	1247.7	1451.4	1725.0	1948.6
42.5°	699.0	708.3	720.9	750.0	782.5	843.2	938.5	1067.2	1252.5	1511.2	1769.3
45°	602.3	607.5	617.1	630.6	660.0	702.3	766.4	852.9	1006.7	1215.0	1473.2
47.5°	531.3	528.6	538.7	549.7	569.3	598.1	641.1	711.7	821.4	988.5	1207.5
50°	483.1	482.5	489.6	497.9	516.5	537.6	572.9	626.1	713.2	851.7	1052.2
52.5°	438.1	440.5	445.5	455.8	469.3	486.4	518.0	556.4	631.2	750.6	917.9
55°	378.1	380.0	387.0	392.8	402.4	419.7	439.6	471.7	522.9	606.2	744.0
57.5°	327.3	326.4	333.2	334.6	345.5	359.6	375.0	399.8	437.0	499.0	591.7
60°	293.5	291.6	297.3	301.8	307.6	319.1	331.9	356.3	385.8	431.3	510.7
62.5°	262.7	261.8	266.0	270.5	275.3	285.8	296.5	315.3	338.6	376.9	439.9
65°	217.8	219.8	221.7	223.6	226.2	232.6	242.9	255.7	271.7	298.6	344.1
67.5°	171.2	173.2	173.8	177.7	183.3	187.3	193.6	205.0	216.1	238.8	264.6
70°	138.4	137.8	138.4	140.3	147.4	154.4	162.7	171.1	178.1	194.1	216.0
72.5°	119.0	117.8	119.4	119.8	123.3	125.2	130.4	138.3	147.4	158.2	173.9
75°	92.3	92.3	92.3	92.3	94.8	96.1	98.1	100.0	103.1	108.3	119.8
77.5°	68.2	68.3	69.2	69.9	70.4	71.1	72.3	74.2	75.3	78.0	83.1
80°	53.8	54.5	53.8	54.5	54.5	55.8	56.4	58.3	58.9	62.1	64.1
82.5°	40.5	40.1	40.5	41.2	41.2	42.4	42.6	43.9	44.1	45.7	47.7
85°	21.8	20.5	21.8	21.1	22.4	21.1	21.8	23.1	23.1	23.7	26.3
87.5°	9.9	11.0	9.9	10.2	10.4	10.5	10.4	10.2	11.1	10.8	10.8
90°	23.6	24.4	23.6	22.7	23.6	22.0	21.2	20.4	19.6	20.4	17.9
92.5°	39.2	40.7	39.9	42.3	43.8	48.0	54.4	68.5	94.4	125.1	137.7
95°	94.4	97.7	103.4	110.7	126.1	155.5	198.6	292.9	391.4	482.6	429.7
97.5°	257.0	264.0	286.0	322.6	382.6	480.0	585.0	730.3	800.1	747.9	547.6
100°	510.3	509.5	541.2	600.6	682.8	798.3	893.6	959.5	931.0	770.7	520.8
102.5°	748.5	767.3	793.8	840.8	904.8	978.0	1033.6	1035.7	937.5	728.4	481.8
105°	1035.2	1039.3	1065.3	1096.2	1133.7	1154.8	1139.4	1057.9	887.9	654.3	433.7
107.5°	1200.2	1207.7	1216.5	1226.9	1226.3	1197.3	1126.0	993.8	801.0	588.9	403.2
110°	1268.0	1269.6	1271.2	1264.7	1241.9	1184.9	1082.4	932.6	746.2	551.8	391.4



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1281.6	1281.2	1275.0	1254.9	1213.2	1140.0	1025.1	872.0	698.7	527.0	384.9
115°	1259.0	1254.9	1238.6	1202.8	1141.7	1053.0	933.4	791.8	641.3	500.5	382.5
117.5°	1187.0	1181.5	1158.1	1117.0	1053.4	963.4	856.0	733.8	606.6	484.9	383.9
120°	1127.2	1122.3	1102.7	1057.1	992.9	910.7	813.0	703.1	588.4	477.7	386.5
122.5°	1071.1	1064.9	1043.5	1002.5	945.3	869.0	778.5	679.1	573.4	473.1	391.1
125°	992.9	987.2	966.8	931.0	878.9	813.8	735.7	647.0	554.2	467.2	397.9
127.5°	928.4	923.2	904.8	874.2	827.8	768.6	698.1	619.0	537.3	464.2	405.8
130°	891.9	885.4	868.4	839.0	795.9	740.5	674.7	601.4	528.2	462.3	411.0
132.5°	856.1	851.6	836.4	807.1	766.6	713.9	652.5	585.1	519.7	461.6	414.9
135°	804.9	799.2	784.5	760.1	720.2	673.8	620.9	563.1	508.7	460.6	420.8
137.5°	750.6	746.9	734.6	709.8	676.3	636.1	590.5	543.2	499.0	458.9	424.6
140°	712.9	713.7	700.7	677.9	647.0	612.0	572.9	531.4	493.2	458.2	427.2
142.5°	677.8	678.6	666.8	646.7	620.3	589.9	556.0	520.3	488.0	456.9	429.2
145°	629.1	627.5	620.9	603.8	583.5	559.9	533.9	507.0	480.9	454.9	430.5
147.5°	589.1	588.4	582.2	570.6	555.2	538.4	517.4	496.1	474.1	451.8	430.5
150°	565.6	565.6	560.7	551.8	539.6	524.1	507.0	488.3	469.5	449.2	430.5
152.5°	546.1	546.1	543.2	534.8	525.2	512.4	497.3	481.1	464.4	446.0	428.5
155°	521.6	520.8	519.2	512.7	505.4	495.6	483.4	470.3	456.6	440.3	426.4
157.5°	499.4	499.5	498.2	493.3	487.0	479.3	469.9	459.0	447.8	435.2	423.7
160°	485.0	485.8	485.8	480.9	475.2	469.5	461.5	452.5	441.9	431.3	422.4
162.5°	472.0	472.8	472.8	468.6	464.9	459.8	452.3	444.7	436.0	427.4	419.8
165°	454.9	454.9	455.8	452.5	449.2	445.2	439.4	434.6	428.0	421.6	415.9
167.5°	438.6	438.6	439.4	437.2	435.7	432.8	429.5	425.7	420.4	415.7	412.0
170°	428.8	428.8	429.7	428.0	427.2	425.6	422.4	420.0	415.9	411.8	409.4
172.5°	419.8	420.4	421.9	420.3	420.1	419.1	416.5	414.7	411.3	408.5	407.4
175°	409.4	410.2	411.0	410.2	410.2	410.2	408.5	407.7	406.1	404.5	404.5
177.5°	403.3	403.3	404.6	404.0	404.6	404.6	404.0	403.3	402.7	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1545.6	1544.1	1536.9	1528.7	1517.9	1510.7	1505.1	1502.0	1492.8	1481.6	1473.8
5°	1641.1	1621.9	1601.3	1576.4	1553.3	1529.6	1514.8	1497.5	1476.4	1452.7	1436.1
7.5°	1743.4	1705.7	1665.1	1623.2	1581.8	1544.6	1511.8	1483.7	1450.0	1416.0	1392.2
10°	1821.8	1766.7	1709.7	1651.3	1598.1	1548.2	1509.7	1471.9	1431.6	1392.4	1363.0
12.5°	1893.0	1820.5	1754.8	1683.1	1615.1	1555.3	1500.0	1455.5	1407.0	1365.3	1331.7
15°	1983.3	1908.9	1829.5	1720.5	1630.2	1554.6	1487.3	1429.0	1370.0	1318.7	1286.1
17.5°	2067.6	1955.7	1848.9	1758.1	1640.7	1546.2	1464.1	1394.4	1329.7	1275.3	1235.1
20°	2102.5	1994.1	1878.2	1762.2	1646.8	1541.2	1445.6	1368.7	1301.5	1239.9	1202.8
22.5°	2123.4	2000.8	1878.7	1754.0	1631.5	1521.7	1427.2	1342.6	1269.7	1211.2	1165.4
25°	2148.0	2001.9	1867.3	1744.3	1619.3	1500.2	1388.0	1298.3	1219.4	1157.3	1108.6
27.5°	2164.1	1992.3	1833.2	1696.5	1569.7	1451.0	1348.3	1253.1	1173.2	1107.4	1055.2
30°	2167.1	1984.5	1807.0	1659.1	1530.2	1421.3	1312.4	1221.4	1136.8	1066.9	1018.2
32.5°	2171.3	1965.6	1771.6	1614.5	1482.5	1374.7	1275.9	1189.0	1102.4	1033.6	983.9
35°	2154.3	1955.1	1718.0	1537.2	1405.2	1300.8	1211.8	1131.6	1046.4	979.7	929.2
37.5°	2081.5	1913.4	1662.4	1450.4	1312.4	1215.6	1143.0	1073.2	995.1	923.2	875.5
40°	2008.2	1872.4	1619.3	1397.6	1253.4	1154.1	1088.8	1031.7	956.1	888.8	837.6
42.5°	1899.1	1816.6	1578.3	1342.2	1186.7	1091.0	1035.9	982.4	916.1	847.7	799.6
45°	1698.8	1709.7	1494.4	1254.0	1094.5	998.3	946.5	909.3	850.4	793.9	744.6
47.5°	1447.6	1549.5	1395.8	1160.1	997.2	907.0	861.6	829.2	789.5	734.1	689.1
50°	1283.5	1429.0	1316.9	1097.1	936.2	846.5	801.6	775.3	740.8	697.2	654.3
52.5°	1132.3	1288.5	1221.5	1026.8	870.1	788.1	744.2	722.6	695.1	654.1	615.3
55°	923.4	1081.7	1066.3	920.8	770.9	697.2	663.9	639.5	620.9	590.2	559.5
57.5°	746.9	897.0	904.9	802.9	683.5	610.7	582.0	563.6	551.5	528.3	499.9
60°	635.7	773.5	800.4	723.5	620.9	556.8	528.6	513.9	504.3	485.8	463.9
62.5°	543.4	660.6	691.1	635.8	560.9	501.0	478.9	464.7	458.2	442.1	422.9
65°	415.9	513.3	542.7	512.0	472.9	424.9	406.9	394.8	389.0	380.0	365.9
67.5°	312.7	383.7	416.0	394.4	380.3	349.8	338.4	331.9	326.8	320.7	308.8
70°	251.2	303.7	337.0	331.3	319.8	303.7	295.4	290.9	285.8	280.7	270.4
72.5°	201.9	238.1	269.4	272.3	262.9	259.7	252.3	250.5	247.4	241.2	235.5
75°	134.0	158.9	180.7	189.1	192.9	196.1	192.9	192.2	191.6	186.5	183.3
77.5°	87.8	101.3	115.0	129.2	135.2	139.6	140.6	142.9	141.2	138.5	137.0
80°	67.3	70.5	80.1	92.3	101.9	105.7	108.3	109.6	108.9	108.3	105.7
82.5°	48.8	51.5	56.0	64.6	72.6	79.1	80.6	80.4	81.8	82.2	80.1
85°	26.3	26.9	28.2	29.5	34.0	41.0	43.0	44.2	45.5	45.5	41.7
87.5°	11.3	10.3	10.8	10.5	11.7	11.7	14.5	16.7	17.5	15.8	16.3
90°	15.5	13.0	10.6	9.0	7.3	4.9	3.3	1.6	3.3	4.9	7.3
92.5°	103.4	68.3	47.0	35.0	28.1	21.9	15.0	10.1	15.0	21.9	28.1
95°	296.2	175.0	105.8	74.0	52.9	39.1	30.1	27.6	30.1	39.1	52.9
97.5°	325.1	188.3	122.2	87.9	67.0	55.0	48.0	47.2	48.0	55.0	67.0
100°	306.8	186.4	129.4	97.7	78.1	66.8	61.1	60.3	61.1	66.8	78.1
102.5°	291.1	189.0	137.9	108.8	91.2	80.4	75.3	73.9	75.3	80.4	91.2
105°	280.0	196.2	152.2	126.9	111.5	101.7	96.9	94.4	96.9	101.7	111.5
107.5°	279.2	209.5	170.9	147.5	133.0	123.4	118.6	116.2	118.6	123.4	133.0
110°	282.4	220.5	183.9	161.1	147.3	138.4	134.3	131.8	134.3	138.4	147.3





TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	288.9	231.6	197.6	175.5	161.6	152.7	148.6	146.2	148.6	152.7	161.6
115°	299.5	249.8	218.9	197.0	183.1	175.0	170.1	166.8	170.1	175.0	183.1
117.5°	313.5	269.2	238.6	218.3	202.8	195.3	191.3	187.5	191.3	195.3	202.8
120°	323.9	281.6	252.3	232.0	216.5	208.3	204.2	201.8	204.2	208.3	216.5
122.5°	333.7	294.6	266.0	244.3	229.5	220.7	216.6	214.2	216.6	220.7	229.5
125°	349.1	313.3	284.9	262.9	247.4	238.5	233.6	232.0	233.6	238.5	247.4
127.5°	361.8	329.6	302.1	280.1	263.0	253.9	247.9	245.5	247.9	253.9	263.0
130°	370.3	339.3	312.5	290.5	273.5	263.7	256.3	253.9	256.3	263.7	273.5
132.5°	378.1	347.8	321.6	300.3	283.2	271.5	263.5	260.4	263.5	271.5	283.2
135°	388.2	360.5	335.3	313.3	296.2	284.1	275.1	271.8	275.1	284.1	296.2
137.5°	395.7	369.3	345.0	324.7	307.8	294.7	286.0	282.6	286.0	294.7	307.8
140°	399.6	375.2	351.6	331.3	315.0	301.9	293.8	289.8	293.8	301.9	315.0
142.5°	403.5	379.8	356.8	337.7	321.5	309.7	300.9	297.5	300.9	309.7	321.5
145°	407.7	385.7	364.6	345.8	332.1	319.8	312.5	310.1	312.5	319.8	332.1
147.5°	410.3	390.6	371.3	355.3	341.9	331.4	324.2	322.8	324.2	331.4	341.9
150°	411.0	393.9	375.2	360.5	349.1	338.5	332.1	331.3	332.1	338.5	349.1
152.5°	412.3	395.8	379.8	365.7	355.6	346.3	339.8	339.7	339.8	346.3	355.6
155°	412.6	399.6	385.7	374.4	365.4	357.3	352.4	352.4	352.4	357.3	365.4
157.5°	413.4	401.7	390.6	381.8	374.2	367.0	363.1	362.5	363.1	367.0	374.2
160°	413.4	403.7	393.9	385.7	380.0	373.6	370.3	370.3	370.3	373.6	380.0
162.5°	412.8	404.3	395.8	389.0	383.9	378.8	376.2	376.2	376.2	378.8	383.9
165°	411.0	405.3	398.8	393.1	389.8	385.7	384.1	384.9	384.1	385.7	389.8
167.5°	409.7	405.1	400.4	396.8	394.5	391.4	390.6	391.6	390.6	391.4	394.5
170°	407.7	404.5	400.4	398.8	397.1	394.7	393.9	395.5	393.9	394.7	397.1
172.5°	407.1	404.5	401.0	400.1	399.1	397.3	397.1	398.1	397.1	397.3	399.1
175°	405.3	403.7	402.0	401.2	401.2	399.6	400.4	401.2	400.4	399.6	401.2
177.5°	404.0	402.7	402.0	402.0	402.0	401.4	402.0	402.7	402.0	401.4	402.0
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1471.3	1464.6	1460.0	1449.8	1443.1	1435.9	1428.7	1433.4	1432.8	1432.3	1432.3
5°	1422.0	1407.2	1393.8	1376.5	1365.5	1352.1	1341.8	1340.5	1343.1	1334.2	1329.0
7.5°	1373.0	1352.8	1333.7	1314.7	1294.5	1278.3	1268.1	1263.4	1256.9	1251.3	1245.6
10°	1338.6	1314.9	1296.3	1272.6	1250.8	1231.6	1219.4	1211.1	1206.6	1202.2	1193.8
12.5°	1303.3	1280.1	1256.4	1229.6	1208.8	1186.5	1177.4	1168.1	1159.4	1154.5	1143.0
15°	1251.5	1221.4	1196.4	1168.2	1145.1	1123.3	1110.5	1091.9	1089.3	1083.0	1071.4
17.5°	1199.5	1166.9	1132.5	1111.5	1085.5	1062.8	1043.3	1037.1	1018.7	1011.8	1001.8
20°	1158.5	1128.5	1102.2	1074.6	1036.8	1015.7	1000.3	992.0	977.2	968.2	961.8
22.5°	1123.2	1092.6	1062.2	1030.0	998.9	975.2	963.9	951.0	942.9	930.3	923.4
25°	1072.7	1039.3	1002.8	968.2	945.8	927.9	910.0	898.4	886.9	881.1	868.3
27.5°	1014.0	979.2	945.0	918.8	891.2	873.5	857.3	847.0	833.2	823.5	816.4
30°	981.7	940.7	911.2	887.5	852.2	835.6	823.5	810.7	800.4	790.1	783.1
32.5°	944.3	906.9	878.9	849.5	822.6	804.3	788.6	777.3	768.6	758.8	751.8
35°	885.6	854.2	825.3	795.9	776.0	757.4	738.8	729.2	720.9	711.9	705.6
37.5°	832.5	803.2	775.8	747.8	723.2	708.1	693.1	685.7	674.5	668.5	661.9
40°	799.7	770.9	741.4	714.5	688.8	677.4	663.9	653.0	642.7	638.2	631.2
42.5°	763.9	735.0	710.1	681.2	660.1	644.5	632.1	620.2	612.5	605.9	601.9
45°	710.6	685.0	660.6	631.9	612.0	598.5	584.4	573.5	566.5	562.0	554.9
47.5°	659.0	633.4	608.6	583.5	564.3	548.9	534.8	527.3	517.9	512.4	507.6
50°	621.6	598.5	572.3	549.2	529.9	514.5	503.0	493.4	485.1	478.0	474.8
52.5°	587.3	562.6	540.0	518.4	498.1	480.7	470.2	460.1	453.8	445.7	442.1
55°	530.6	506.9	487.6	466.5	446.6	431.9	419.1	410.1	403.7	394.8	389.6
57.5°	477.4	456.2	433.2	414.8	394.4	381.9	371.3	359.1	351.3	344.2	339.2
60°	441.5	417.2	397.3	380.0	362.1	346.0	336.4	326.8	318.5	311.4	307.0
62.5°	404.1	382.8	363.9	345.1	328.7	314.8	303.6	295.5	288.2	283.7	279.2
65°	346.7	330.0	310.8	295.4	280.1	269.8	260.8	253.7	248.7	245.4	241.6
67.5°	293.8	277.7	260.9	245.8	235.5	227.7	221.8	215.8	213.3	209.1	206.6
70°	259.5	242.9	228.1	216.6	206.4	200.6	196.7	192.2	189.6	184.6	182.0
72.5°	222.1	210.0	199.4	190.0	181.7	176.5	171.6	166.1	162.0	156.4	153.8
75°	175.0	164.0	155.7	149.3	144.1	137.1	130.1	124.3	122.4	120.5	119.8
77.5°	129.6	122.6	116.6	111.2	104.8	99.7	98.2	96.9	96.5	95.5	95.5
80°	101.9	95.5	91.0	84.5	80.7	80.7	80.7	79.5	80.1	80.1	80.1
82.5°	75.7	69.9	67.4	65.1	64.3	64.8	64.8	65.1	64.7	65.7	65.2
85°	39.1	39.7	41.0	40.4	41.0	41.0	42.3	41.7	42.3	41.0	42.3
87.5°	16.1	18.0	19.0	20.0	21.0	21.0	21.4	21.5	22.2	22.3	22.7
90°	9.0	10.6	13.0	15.5	17.9	20.4	19.6	20.4	21.2	22.0	23.6
92.5°	35.0	47.0	68.3	103.4	137.7	125.1	94.4	68.5	54.4	48.0	43.8
95°	74.0	105.8	175.0	296.2	429.7	482.6	391.4	292.9	198.6	155.5	126.1
97.5°	87.9	122.2	188.3	325.1	547.6	747.9	800.1	730.3	585.0	480.0	382.6
100°	97.7	129.4	186.4	306.8	520.8	770.7	931.0	959.5	893.6	798.3	682.8
102.5°	108.8	137.9	189.0	291.1	481.8	728.4	937.5	1035.7	1033.6	978.0	904.8
105°	126.9	152.2	196.2	280.0	433.7	654.3	887.9	1057.9	1139.4	1154.8	1133.7
107.5°	147.5	170.9	209.5	279.2	403.2	588.9	801.0	993.8	1126.0	1197.3	1226.3
110°	161.1	183.9	220.5	282.4	391.4	551.8	746.2	932.6	1082.4	1184.9	1241.9



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	175.5	197.6	231.6	288.9	384.9	527.0	698.7	872.0	1025.1	1140.0	1213.2
115°	197.0	218.9	249.8	299.5	382.5	500.5	641.3	791.8	933.4	1053.0	1141.7
117.5°	218.3	238.6	269.2	313.5	383.9	484.9	606.6	733.8	856.0	963.4	1053.4
120°	232.0	252.3	281.6	323.9	386.5	477.7	588.4	703.1	813.0	910.7	992.9
122.5°	244.3	266.0	294.6	333.7	391.1	473.1	573.4	679.1	778.5	869.0	945.3
125°	262.9	284.9	313.3	349.1	397.9	467.2	554.2	647.0	735.7	813.8	878.9
127.5°	280.1	302.1	329.6	361.8	405.8	464.2	537.3	619.0	698.1	768.6	827.8
130°	290.5	312.5	339.3	370.3	411.0	462.3	528.2	601.4	674.7	740.5	795.9
132.5°	300.3	321.6	347.8	378.1	414.9	461.6	519.7	585.1	652.5	713.9	766.6
135°	313.3	335.3	360.5	388.2	420.8	460.6	508.7	563.1	620.9	673.8	720.2
137.5°	324.7	345.0	369.3	395.7	424.6	458.9	499.0	543.2	590.5	636.1	676.3
140°	331.3	351.6	375.2	399.6	427.2	458.2	493.2	531.4	572.9	612.0	647.0
142.5°	337.7	356.8	379.8	403.5	429.2	456.9	488.0	520.3	556.0	589.9	620.3
145°	345.8	364.6	385.7	407.7	430.5	454.9	480.9	507.0	533.9	559.9	583.5
147.5°	355.3	371.3	390.6	410.3	430.5	451.8	474.1	496.1	517.4	538.4	555.2
150°	360.5	375.2	393.9	411.0	430.5	449.2	469.5	488.3	507.0	524.1	539.6
152.5°	365.7	379.8	395.8	412.3	428.5	446.0	464.4	481.1	497.3	512.4	525.2
155°	374.4	385.7	399.6	412.6	426.4	440.3	456.6	470.3	483.4	495.6	505.4
157.5°	381.8	390.6	401.7	413.4	423.7	435.2	447.8	459.0	469.9	479.3	487.0
160°	385.7	393.9	403.7	413.4	422.4	431.3	441.9	452.5	461.5	469.5	475.2
162.5°	389.0	395.8	404.3	412.8	419.8	427.4	436.0	444.7	452.3	459.8	464.9
165°	393.1	398.8	405.3	411.0	415.9	421.6	428.0	434.6	439.4	445.2	449.2
167.5°	396.8	400.4	405.1	409.7	412.0	415.7	420.4	425.7	429.5	432.8	435.7
170°	398.8	400.4	404.5	407.7	409.4	411.8	415.9	420.0	422.4	425.6	427.2
172.5°	400.1	401.0	404.5	407.1	407.4	408.5	411.3	414.7	416.5	419.1	420.1
175°	401.2	402.0	403.7	405.3	404.5	404.5	406.1	407.7	408.5	410.2	410.2
177.5°	402.0	402.0	402.7	404.0	402.7	402.0	402.7	403.3	404.0	404.6	404.6
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1426.2	1425.6	1426.2	1424.1	1426.2	1425.6	1426.2	1432.3	1432.3	1432.8	1433.4
5°	1327.1	1326.5	1324.5	1318.7	1324.5	1326.5	1327.1	1329.0	1334.2	1343.1	1340.5
7.5°	1240.6	1239.7	1234.0	1234.2	1234.0	1239.7	1240.6	1245.6	1251.3	1256.9	1263.4
10°	1189.4	1189.9	1182.3	1177.8	1182.3	1189.9	1189.4	1193.8	1202.2	1206.6	1211.1
12.5°	1139.6	1136.7	1130.5	1125.5	1130.5	1136.7	1139.6	1143.0	1154.5	1159.4	1168.1
15°	1074.0	1067.6	1052.2	1053.4	1052.2	1067.6	1074.0	1071.4	1083.0	1089.3	1091.9
17.5°	996.7	992.0	991.7	982.8	991.7	992.0	996.7	1001.8	1011.8	1018.7	1037.1
20°	951.6	948.4	949.7	940.7	949.7	948.4	951.6	961.8	968.2	977.2	992.0
22.5°	916.2	913.0	907.6	904.8	907.6	913.0	916.2	923.4	930.3	942.9	951.0
25°	864.5	859.3	854.2	857.4	854.2	859.3	864.5	868.3	881.1	886.9	898.4
27.5°	812.7	808.9	803.7	803.1	803.7	808.9	812.7	816.4	823.5	833.2	847.0
30°	779.8	776.0	773.5	770.2	773.5	776.0	779.8	783.1	790.1	800.4	810.7
32.5°	746.6	745.8	741.2	740.5	741.2	745.8	746.6	751.8	758.8	768.6	777.3
35°	703.0	699.1	697.8	698.5	697.8	699.1	703.0	705.6	711.9	720.9	729.2
37.5°	661.5	656.4	654.1	651.8	654.1	656.4	661.5	661.9	668.5	674.5	685.7
40°	631.9	626.7	625.4	624.1	625.4	626.7	631.9	631.2	638.2	642.7	653.0
42.5°	598.5	596.5	595.7	593.4	595.7	596.5	598.5	601.9	605.9	612.5	620.2
45°	553.0	552.4	548.5	549.8	548.5	552.4	553.0	554.9	562.0	566.5	573.5
47.5°	505.1	502.2	499.5	501.3	499.5	502.2	505.1	507.6	512.4	517.9	527.3
50°	472.3	471.0	465.2	466.5	465.2	471.0	472.3	474.8	478.0	485.1	493.4
52.5°	439.4	434.6	432.4	431.6	432.4	434.6	439.4	442.1	445.7	453.8	460.1
55°	385.1	379.4	376.7	375.5	376.7	379.4	385.1	389.6	394.8	403.7	410.1
57.5°	331.8	330.3	328.2	329.6	328.2	330.3	331.8	339.2	344.2	351.3	359.1
60°	300.5	300.5	300.5	299.9	300.5	300.5	300.5	307.0	311.4	318.5	326.8
62.5°	276.5	274.9	274.4	275.3	274.4	274.9	276.5	279.2	283.7	288.2	295.5
65°	239.7	239.0	236.4	235.8	236.4	239.0	239.7	241.6	245.4	248.7	253.7
67.5°	205.0	202.6	201.9	201.0	201.9	202.6	205.0	206.6	209.1	213.3	215.8
70°	178.8	177.5	173.7	174.3	173.7	177.5	178.8	182.0	184.6	189.6	192.2
72.5°	150.6	149.3	148.5	147.7	148.5	149.3	150.6	153.8	156.4	162.0	166.1
75°	119.2	118.5	117.9	120.5	117.9	118.5	119.2	119.8	120.5	122.4	124.3
77.5°	95.5	95.5	95.9	94.8	95.9	95.5	95.5	95.5	95.5	96.5	96.9
80°	80.1	80.1	79.5	79.5	79.5	80.1	80.1	80.1	80.1	80.1	79.5
82.5°	64.2	64.7	65.1	64.1	65.1	64.7	64.2	65.2	65.7	64.7	65.1
85°	42.3	41.7	43.0	42.3	43.0	41.7	42.3	42.3	41.0	42.3	41.7
87.5°	23.6	22.7	22.8	23.2	22.8	22.7	23.6	22.7	22.3	22.2	21.5
90°	22.7	23.6	24.4	23.6	24.4	23.6	22.7	23.6	22.0	21.2	20.4
92.5°	42.3	39.9	40.7	39.2	40.7	39.9	42.3	43.8	48.0	54.4	68.5
95°	110.7	103.4	97.7	94.4	97.7	103.4	110.7	126.1	155.5	198.6	292.9
97.5°	322.6	286.0	264.0	257.0	264.0	286.0	322.6	382.6	480.0	585.0	730.3
100°	600.6	541.2	509.5	510.3	509.5	541.2	600.6	682.8	798.3	893.6	959.5
102.5°	840.8	793.8	767.3	748.5	767.3	793.8	840.8	904.8	978.0	1033.6	1035.7
105°	1096.2	1065.3	1039.3	1035.2	1039.3	1065.3	1096.2	1133.7	1154.8	1139.4	1057.9
107.5°	1226.9	1216.5	1207.7	1200.2	1207.7	1216.5	1226.9	1226.3	1197.3	1126.0	993.8
110°	1264.7	1271.2	1269.6	1268.0	1269.6	1271.2	1264.7	1241.9	1184.9	1082.4	932.6



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1254.9	1275.0	1281.2	1281.6	1281.2	1275.0	1254.9	1213.2	1140.0	1025.1	872.0
115°	1202.8	1238.6	1254.9	1259.0	1254.9	1238.6	1202.8	1141.7	1053.0	933.4	791.8
117.5°	1117.0	1158.1	1181.5	1187.0	1181.5	1158.1	1117.0	1053.4	963.4	856.0	733.8
120°	1057.1	1102.7	1122.3	1127.2	1122.3	1102.7	1057.1	992.9	910.7	813.0	703.1
122.5°	1002.5	1043.5	1064.9	1071.1	1064.9	1043.5	1002.5	945.3	869.0	778.5	679.1
125°	931.0	966.8	987.2	992.9	987.2	966.8	931.0	878.9	813.8	735.7	647.0
127.5°	874.2	904.8	923.2	928.4	923.2	904.8	874.2	827.8	768.6	698.1	619.0
130°	839.0	868.4	885.4	891.9	885.4	868.4	839.0	795.9	740.5	674.7	601.4
132.5°	807.1	836.4	851.6	856.1	851.6	836.4	807.1	766.6	713.9	652.5	585.1
135°	760.1	784.5	799.2	804.9	799.2	784.5	760.1	720.2	673.8	620.9	563.1
137.5°	709.8	734.6	746.9	750.6	746.9	734.6	709.8	676.3	636.1	590.5	543.2
140°	677.9	700.7	713.7	712.9	713.7	700.7	677.9	647.0	612.0	572.9	531.4
142.5°	646.7	666.8	678.6	677.8	678.6	666.8	646.7	620.3	589.9	556.0	520.3
145°	603.8	620.9	627.5	629.1	627.5	620.9	603.8	583.5	559.9	533.9	507.0
147.5°	570.6	582.2	588.4	589.1	588.4	582.2	570.6	555.2	538.4	517.4	496.1
150°	551.8	560.7	565.6	565.6	565.6	560.7	551.8	539.6	524.1	507.0	488.3
152.5°	534.8	543.2	546.1	546.1	546.1	543.2	534.8	525.2	512.4	497.3	481.1
155°	512.7	519.2	520.8	521.6	520.8	519.2	512.7	505.4	495.6	483.4	470.3
157.5°	493.3	498.2	499.5	499.4	499.5	498.2	493.3	487.0	479.3	469.9	459.0
160°	480.9	485.8	485.8	485.0	485.8	485.8	480.9	475.2	469.5	461.5	452.5
162.5°	468.6	472.8	472.8	472.0	472.8	472.8	468.6	464.9	459.8	452.3	444.7
165°	452.5	455.8	454.9	454.9	454.9	455.8	452.5	449.2	445.2	439.4	434.6
167.5°	437.2	439.4	438.6	438.6	438.6	439.4	437.2	435.7	432.8	429.5	425.7
170°	428.0	429.7	428.8	428.8	428.8	429.7	428.0	427.2	425.6	422.4	420.0
172.5°	420.3	421.9	420.4	419.8	420.4	421.9	420.3	420.1	419.1	416.5	414.7
175°	410.2	411.0	410.2	409.4	410.2	411.0	410.2	410.2	410.2	408.5	407.7
177.5°	404.0	404.6	403.3	403.3	403.3	404.6	404.0	404.6	404.6	404.0	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1428.7	1435.9	1443.1	1449.8	1460.0	1464.6	1471.3	1473.8	1481.6	1492.8	1502.0
5°	1341.8	1352.1	1365.5	1376.5	1393.8	1407.2	1422.0	1436.1	1452.7	1476.4	1497.5
7.5°	1268.1	1278.3	1294.5	1314.7	1333.7	1352.8	1373.0	1392.2	1416.0	1450.0	1483.7
10°	1219.4	1231.6	1250.8	1272.6	1296.3	1314.9	1338.6	1363.0	1392.4	1431.6	1471.9
12.5°	1177.4	1186.5	1208.8	1229.6	1256.4	1280.1	1303.3	1331.7	1365.3	1407.0	1455.5
15°	1110.5	1123.3	1145.1	1168.2	1196.4	1221.4	1251.5	1286.1	1318.7	1370.0	1429.0
17.5°	1043.3	1062.8	1085.5	1111.5	1132.5	1166.9	1199.5	1235.1	1275.3	1329.7	1394.4
20°	1000.3	1015.7	1036.8	1074.6	1102.2	1128.5	1158.5	1202.8	1239.9	1301.5	1368.7
22.5°	963.9	975.2	998.9	1030.0	1062.2	1092.6	1123.2	1165.4	1211.2	1269.7	1342.6
25°	910.0	927.9	945.8	968.2	1002.8	1039.3	1072.7	1108.6	1157.3	1219.4	1298.3
27.5°	857.3	873.5	891.2	918.8	945.0	979.2	1014.0	1055.2	1107.4	1173.2	1253.1
30°	823.5	835.6	852.2	887.5	911.2	940.7	981.7	1018.2	1066.9	1136.8	1221.4
32.5°	788.6	804.3	822.6	849.5	878.9	906.9	944.3	983.9	1033.6	1102.4	1189.0
35°	738.8	757.4	776.0	795.9	825.3	854.2	885.6	929.2	979.7	1046.4	1131.6
37.5°	693.1	708.1	723.2	747.8	775.8	803.2	832.5	875.5	923.2	995.1	1073.2
40°	663.9	677.4	688.8	714.5	741.4	770.9	799.7	837.6	888.8	956.1	1031.7
42.5°	632.1	644.5	660.1	681.2	710.1	735.0	763.9	799.6	847.7	916.1	982.4
45°	584.4	598.5	612.0	631.9	660.6	685.0	710.6	744.6	793.9	850.4	909.3
47.5°	534.8	548.9	564.3	583.5	608.6	633.4	659.0	689.1	734.1	789.5	829.2
50°	503.0	514.5	529.9	549.2	572.3	598.5	621.6	654.3	697.2	740.8	775.3
52.5°	470.2	480.7	498.1	518.4	540.0	562.6	587.3	615.3	654.1	695.1	722.6
55°	419.1	431.9	446.6	466.5	487.6	506.9	530.6	559.5	590.2	620.9	639.5
57.5°	371.3	381.9	394.4	414.8	433.2	456.2	477.4	499.9	528.3	551.5	563.6
60°	336.4	346.0	362.1	380.0	397.3	417.2	441.5	463.9	485.8	504.3	513.9
62.5°	303.6	314.8	328.7	345.1	363.9	382.8	404.1	422.9	442.1	458.2	464.7
65°	260.8	269.8	280.1	295.4	310.8	330.0	346.7	365.9	380.0	389.0	394.8
67.5°	221.8	227.7	235.5	245.8	260.9	277.7	293.8	308.8	320.7	326.8	331.9
70°	196.7	200.6	206.4	216.6	228.1	242.9	259.5	270.4	280.7	285.8	290.9
72.5°	171.6	176.5	181.7	190.0	199.4	210.0	222.1	235.5	241.2	247.4	250.5
75°	130.1	137.1	144.1	149.3	155.7	164.0	175.0	183.3	186.5	191.6	192.2
77.5°	98.2	99.7	104.8	111.2	116.6	122.6	129.6	137.0	138.5	141.2	142.9
80°	80.7	80.7	80.7	84.5	91.0	95.5	101.9	105.7	108.3	108.9	109.6
82.5°	64.8	64.8	64.3	65.1	67.4	69.9	75.7	80.1	82.2	81.8	80.4
85°	42.3	41.0	41.0	40.4	41.0	39.7	39.1	41.7	45.5	45.5	44.2
87.5°	21.4	21.0	21.0	20.0	19.0	18.0	16.1	16.3	15.8	17.5	16.7
90°	19.6	20.4	17.9	15.5	13.0	10.6	9.0	7.3	4.9	3.3	1.6
92.5°	94.4	125.1	137.7	103.4	68.3	47.0	35.0	28.1	21.9	15.0	10.1
95°	391.4	482.6	429.7	296.2	175.0	105.8	74.0	52.9	39.1	30.1	27.6
97.5°	800.1	747.9	547.6	325.1	188.3	122.2	87.9	67.0	55.0	48.0	47.2
100°	931.0	770.7	520.8	306.8	186.4	129.4	97.7	78.1	66.8	61.1	60.3
102.5°	937.5	728.4	481.8	291.1	189.0	137.9	108.8	91.2	80.4	75.3	73.9
105°	887.9	654.3	433.7	280.0	196.2	152.2	126.9	111.5	101.7	96.9	94.4
107.5°	801.0	588.9	403.2	279.2	209.5	170.9	147.5	133.0	123.4	118.6	116.2
110°	746.2	551.8	391.4	282.4	220.5	183.9	161.1	147.3	138.4	134.3	131.8



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	698.7	527.0	384.9	288.9	231.6	197.6	175.5	161.6	152.7	148.6	146.2
115°	641.3	500.5	382.5	299.5	249.8	218.9	197.0	183.1	175.0	170.1	166.8
117.5°	606.6	484.9	383.9	313.5	269.2	238.6	218.3	202.8	195.3	191.3	187.5
120°	588.4	477.7	386.5	323.9	281.6	252.3	232.0	216.5	208.3	204.2	201.8
122.5°	573.4	473.1	391.1	333.7	294.6	266.0	244.3	229.5	220.7	216.6	214.2
125°	554.2	467.2	397.9	349.1	313.3	284.9	262.9	247.4	238.5	233.6	232.0
127.5°	537.3	464.2	405.8	361.8	329.6	302.1	280.1	263.0	253.9	247.9	245.5
130°	528.2	462.3	411.0	370.3	339.3	312.5	290.5	273.5	263.7	256.3	253.9
132.5°	519.7	461.6	414.9	378.1	347.8	321.6	300.3	283.2	271.5	263.5	260.4
135°	508.7	460.6	420.8	388.2	360.5	335.3	313.3	296.2	284.1	275.1	271.8
137.5°	499.0	458.9	424.6	395.7	369.3	345.0	324.7	307.8	294.7	286.0	282.6
140°	493.2	458.2	427.2	399.6	375.2	351.6	331.3	315.0	301.9	293.8	289.8
142.5°	488.0	456.9	429.2	403.5	379.8	356.8	337.7	321.5	309.7	300.9	297.5
145°	480.9	454.9	430.5	407.7	385.7	364.6	345.8	332.1	319.8	312.5	310.1
147.5°	474.1	451.8	430.5	410.3	390.6	371.3	355.3	341.9	331.4	324.2	322.8
150°	469.5	449.2	430.5	411.0	393.9	375.2	360.5	349.1	338.5	332.1	331.3
152.5°	464.4	446.0	428.5	412.3	395.8	379.8	365.7	355.6	346.3	339.8	339.7
155°	456.6	440.3	426.4	412.6	399.6	385.7	374.4	365.4	357.3	352.4	352.4
157.5°	447.8	435.2	423.7	413.4	401.7	390.6	381.8	374.2	367.0	363.1	362.5
160°	441.9	431.3	422.4	413.4	403.7	393.9	385.7	380.0	373.6	370.3	370.3
162.5°	436.0	427.4	419.8	412.8	404.3	395.8	389.0	383.9	378.8	376.2	376.2
165°	428.0	421.6	415.9	411.0	405.3	398.8	393.1	389.8	385.7	384.1	384.9
167.5°	420.4	415.7	412.0	409.7	405.1	400.4	396.8	394.5	391.4	390.6	391.6
170°	415.9	411.8	409.4	407.7	404.5	400.4	398.8	397.1	394.7	393.9	395.5
172.5°	411.3	408.5	407.4	407.1	404.5	401.0	400.1	399.1	397.3	397.1	398.1
175°	406.1	404.5	404.5	405.3	403.7	402.0	401.2	401.2	399.6	400.4	401.2
177.5°	402.7	402.0	402.7	404.0	402.7	402.0	402.0	402.0	401.4	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1505.1	1510.7	1517.9	1528.7	1536.9	1544.1	1545.6	1547.7	1552.8	1561.5	1568.1
5°	1514.8	1529.6	1553.3	1576.4	1601.3	1621.9	1641.1	1654.6	1667.4	1694.3	1716.0
7.5°	1511.8	1544.6	1581.8	1623.2	1665.1	1705.7	1743.4	1777.0	1810.6	1849.8	1894.6
10°	1509.7	1548.2	1598.1	1651.3	1709.7	1766.7	1821.8	1864.8	1914.7	1959.6	2016.6
12.5°	1500.0	1555.3	1615.1	1683.1	1754.8	1820.5	1893.0	1952.4	2009.5	2074.4	2140.6
15°	1487.3	1554.6	1630.2	1720.5	1829.5	1908.9	1983.3	2086.4	2157.0	2227.4	2322.3
17.5°	1464.1	1546.2	1640.7	1758.1	1848.9	1955.7	2067.6	2149.1	2244.1	2343.4	2429.3
20°	1445.6	1541.2	1646.8	1762.2	1878.2	1994.1	2102.5	2199.8	2297.9	2412.6	2483.1
22.5°	1427.2	1521.7	1631.5	1754.0	1878.7	2000.8	2123.4	2237.8	2348.1	2463.9	2553.8
25°	1388.0	1500.2	1619.3	1744.3	1867.3	2001.9	2148.0	2275.5	2412.0	2531.2	2616.4
27.5°	1348.3	1451.0	1569.7	1696.5	1833.2	1992.3	2164.1	2309.1	2445.8	2531.2	2557.9
30°	1312.4	1421.3	1530.2	1659.1	1807.0	1984.5	2167.1	2333.1	2445.3	2482.4	2454.9
32.5°	1275.9	1374.7	1482.5	1614.5	1771.6	1965.6	2171.3	2318.8	2386.3	2357.9	2245.7
35°	1211.8	1300.8	1405.2	1537.2	1718.0	1955.1	2154.3	2254.3	2237.7	2077.5	1866.0
37.5°	1143.0	1215.6	1312.4	1450.4	1662.4	1913.4	2081.5	2096.3	1952.2	1706.2	1461.9
40°	1088.8	1154.1	1253.4	1397.6	1619.3	1872.4	2008.2	1948.6	1725.0	1451.4	1247.7
42.5°	1035.9	1091.0	1186.7	1342.2	1578.3	1816.6	1899.1	1769.3	1511.2	1252.5	1067.2
45°	946.5	998.3	1094.5	1254.0	1494.4	1709.7	1698.8	1473.2	1215.0	1006.7	852.9
47.5°	861.6	907.0	997.2	1160.1	1395.8	1549.5	1447.6	1207.5	988.5	821.4	711.7
50°	801.6	846.5	936.2	1097.1	1316.9	1429.0	1283.5	1052.2	851.7	713.2	626.1
52.5°	744.2	788.1	870.1	1026.8	1221.5	1288.5	1132.3	917.9	750.6	631.2	556.4
55°	663.9	697.2	770.9	920.8	1066.3	1081.7	923.4	744.0	606.2	522.9	471.7
57.5°	582.0	610.7	683.5	802.9	904.9	897.0	746.9	591.7	499.0	437.0	399.8
60°	528.6	556.8	620.9	723.5	800.4	773.5	635.7	510.7	431.3	385.8	356.3
62.5°	478.9	501.0	560.9	635.8	691.1	660.6	543.4	439.9	376.9	338.6	315.3
65°	406.9	424.9	472.9	512.0	542.7	513.3	415.9	344.1	298.6	271.7	255.7
67.5°	338.4	349.8	380.3	394.4	416.0	383.7	312.7	264.6	238.8	216.1	205.0
70°	295.4	303.7	319.8	331.3	337.0	303.7	251.2	216.0	194.1	178.1	171.1
72.5°	252.3	259.7	262.9	272.3	269.4	238.1	201.9	173.9	158.2	147.4	138.3
75°	192.9	196.1	192.9	189.1	180.7	158.9	134.0	119.8	108.3	103.1	100.0
77.5°	140.6	139.6	135.2	129.2	115.0	101.3	87.8	83.1	78.0	75.3	74.2
80°	108.3	105.7	101.9	92.3	80.1	70.5	67.3	64.1	62.1	58.9	58.3
82.5°	80.6	79.1	72.6	64.6	56.0	51.5	48.8	47.7	45.7	44.1	43.9
85°	43.0	41.0	34.0	29.5	28.2	26.9	26.3	26.3	23.7	23.1	23.1
87.5°	14.5	11.7	11.7	10.5	10.8	10.3	11.3	10.8	10.8	11.1	10.2
90°	3.3	4.9	7.3	9.0	10.6	13.0	15.5	17.9	20.4	19.6	20.4
92.5°	15.0	21.9	28.1	35.0	47.0	68.3	103.4	137.7	125.1	94.4	68.5
95°	30.1	39.1	52.9	74.0	105.8	175.0	296.2	429.7	482.6	391.4	292.9
97.5°	48.0	55.0	67.0	87.9	122.2	188.3	325.1	547.6	747.9	800.1	730.3
100°	61.1	66.8	78.1	97.7	129.4	186.4	306.8	520.8	770.7	931.0	959.5
102.5°	75.3	80.4	91.2	108.8	137.9	189.0	291.1	481.8	728.4	937.5	1035.7
105°	96.9	101.7	111.5	126.9	152.2	196.2	280.0	433.7	654.3	887.9	1057.9
107.5°	118.6	123.4	133.0	147.5	170.9	209.5	279.2	403.2	588.9	801.0	993.8
110°	134.3	138.4	147.3	161.1	183.9	220.5	282.4	391.4	551.8	746.2	932.6





TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	148.6	152.7	161.6	175.5	197.6	231.6	288.9	384.9	527.0	698.7	872.0
115°	170.1	175.0	183.1	197.0	218.9	249.8	299.5	382.5	500.5	641.3	791.8
117.5°	191.3	195.3	202.8	218.3	238.6	269.2	313.5	383.9	484.9	606.6	733.8
120°	204.2	208.3	216.5	232.0	252.3	281.6	323.9	386.5	477.7	588.4	703.1
122.5°	216.6	220.7	229.5	244.3	266.0	294.6	333.7	391.1	473.1	573.4	679.1
125°	233.6	238.5	247.4	262.9	284.9	313.3	349.1	397.9	467.2	554.2	647.0
127.5°	247.9	253.9	263.0	280.1	302.1	329.6	361.8	405.8	464.2	537.3	619.0
130°	256.3	263.7	273.5	290.5	312.5	339.3	370.3	411.0	462.3	528.2	601.4
132.5°	263.5	271.5	283.2	300.3	321.6	347.8	378.1	414.9	461.6	519.7	585.1
135°	275.1	284.1	296.2	313.3	335.3	360.5	388.2	420.8	460.6	508.7	563.1
137.5°	286.0	294.7	307.8	324.7	345.0	369.3	395.7	424.6	458.9	499.0	543.2
140°	293.8	301.9	315.0	331.3	351.6	375.2	399.6	427.2	458.2	493.2	531.4
142.5°	300.9	309.7	321.5	337.7	356.8	379.8	403.5	429.2	456.9	488.0	520.3
145°	312.5	319.8	332.1	345.8	364.6	385.7	407.7	430.5	454.9	480.9	507.0
147.5°	324.2	331.4	341.9	355.3	371.3	390.6	410.3	430.5	451.8	474.1	496.1
150°	332.1	338.5	349.1	360.5	375.2	393.9	411.0	430.5	449.2	469.5	488.3
152.5°	339.8	346.3	355.6	365.7	379.8	395.8	412.3	428.5	446.0	464.4	481.1
155°	352.4	357.3	365.4	374.4	385.7	399.6	412.6	426.4	440.3	456.6	470.3
157.5°	363.1	367.0	374.2	381.8	390.6	401.7	413.4	423.7	435.2	447.8	459.0
160°	370.3	373.6	380.0	385.7	393.9	403.7	413.4	422.4	431.3	441.9	452.5
162.5°	376.2	378.8	383.9	389.0	395.8	404.3	412.8	419.8	427.4	436.0	444.7
165°	384.1	385.7	389.8	393.1	398.8	405.3	411.0	415.9	421.6	428.0	434.6
167.5°	390.6	391.4	394.5	396.8	400.4	405.1	409.7	412.0	415.7	420.4	425.7
170°	393.9	394.7	397.1	398.8	400.4	404.5	407.7	409.4	411.8	415.9	420.0
172.5°	397.1	397.3	399.1	400.1	401.0	404.5	407.1	407.4	408.5	411.3	414.7
175°	400.4	399.6	401.2	401.2	402.0	403.7	405.3	404.5	404.5	406.1	407.7
177.5°	402.0	401.4	402.0	402.0	402.0	402.7	404.0	402.7	402.0	402.7	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1578.9	1578.9	1580.9	1588.7	1589.7	1596.4	1594.3
5°	1735.3	1747.4	1751.9	1771.2	1782.7	1787.9	1777.6
7.5°	1926.5	1960.9	1977.1	1997.2	2015.1	2020.5	2006.5
10°	2066.0	2101.8	2131.9	2150.5	2167.8	2179.4	2194.1
12.5°	2200.7	2244.8	2273.5	2299.7	2317.5	2332.2	2334.5
15°	2347.2	2413.9	2464.5	2501.7	2520.3	2529.9	2526.0
17.5°	2495.0	2556.8	2592.8	2630.7	2656.5	2657.8	2658.5
20°	2578.5	2638.8	2680.5	2708.7	2737.5	2736.2	2742.6
22.5°	2634.5	2681.8	2713.8	2734.3	2744.1	2739.3	2740.5
25°	2660.6	2674.7	2669.0	2636.3	2628.0	2597.8	2602.9
27.5°	2525.8	2459.1	2390.2	2301.5	2231.6	2175.6	2178.5
30°	2342.8	2224.9	2090.3	1977.5	1876.2	1848.0	1787.9
32.5°	2086.9	1910.1	1752.5	1647.4	1560.5	1536.9	1484.3
35°	1653.3	1481.6	1319.4	1222.0	1183.6	1129.8	1129.1
37.5°	1285.1	1133.8	1048.1	975.0	936.7	904.2	901.0
40°	1081.0	963.1	898.4	845.9	808.0	783.7	778.0
42.5°	938.5	843.2	782.5	750.0	720.9	708.3	699.0
45°	766.4	702.3	660.0	630.6	617.1	607.5	602.3
47.5°	641.1	598.1	569.3	549.7	538.7	528.6	531.3
50°	572.9	537.6	516.5	497.9	489.6	482.5	483.1
52.5°	518.0	486.4	469.3	455.8	445.5	440.5	438.1
55°	439.6	419.7	402.4	392.8	387.0	380.0	378.1
57.5°	375.0	359.6	345.5	334.6	333.2	326.4	327.3
60°	331.9	319.1	307.6	301.8	297.3	291.6	293.5
62.5°	296.5	285.8	275.3	270.5	266.0	261.8	262.7
65°	242.9	232.6	226.2	223.6	221.7	219.8	217.8
67.5°	193.6	187.3	183.3	177.7	173.8	173.2	171.2
70°	162.7	154.4	147.4	140.3	138.4	137.8	138.4
72.5°	130.4	125.2	123.3	119.8	119.4	117.8	119.0
75°	98.1	96.1	94.8	92.3	92.3	92.3	92.3
77.5°	72.3	71.1	70.4	69.9	69.2	68.3	68.2
80°	56.4	55.8	54.5	54.5	53.8	54.5	53.8
82.5°	42.6	42.4	41.2	41.2	40.5	40.1	40.5
85°	21.8	21.1	22.4	21.1	21.8	20.5	21.8
87.5°	10.4	10.5	10.4	10.2	9.9	11.0	9.9
90°	21.2	22.0	23.6	22.7	23.6	24.4	23.6
92.5°	54.4	48.0	43.8	42.3	39.9	40.7	39.2
95°	198.6	155.5	126.1	110.7	103.4	97.7	94.4
97.5°	585.0	480.0	382.6	322.6	286.0	264.0	257.0
100°	893.6	798.3	682.8	600.6	541.2	509.5	510.3
102.5°	1033.6	978.0	904.8	840.8	793.8	767.3	748.5
105°	1139.4	1154.8	1133.7	1096.2	1065.3	1039.3	1035.2
107.5°	1126.0	1197.3	1226.3	1226.9	1216.5	1207.7	1200.2
110°	1082.4	1184.9	1241.9	1264.7	1271.2	1269.6	1268.0



TEST NUMBER: P332380-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1025.1	1140.0	1213.2	1254.9	1275.0	1281.2	1281.6
115°	933.4	1053.0	1141.7	1202.8	1238.6	1254.9	1259.0
117.5°	856.0	963.4	1053.4	1117.0	1158.1	1181.5	1187.0
120°	813.0	910.7	992.9	1057.1	1102.7	1122.3	1127.2
122.5°	778.5	869.0	945.3	1002.5	1043.5	1064.9	1071.1
125°	735.7	813.8	878.9	931.0	966.8	987.2	992.9
127.5°	698.1	768.6	827.8	874.2	904.8	923.2	928.4
130°	674.7	740.5	795.9	839.0	868.4	885.4	891.9
132.5°	652.5	713.9	766.6	807.1	836.4	851.6	856.1
135°	620.9	673.8	720.2	760.1	784.5	799.2	804.9
137.5°	590.5	636.1	676.3	709.8	734.6	746.9	750.6
140°	572.9	612.0	647.0	677.9	700.7	713.7	712.9
142.5°	556.0	589.9	620.3	646.7	666.8	678.6	677.8
145°	533.9	559.9	583.5	603.8	620.9	627.5	629.1
147.5°	517.4	538.4	555.2	570.6	582.2	588.4	589.1
150°	507.0	524.1	539.6	551.8	560.7	565.6	565.6
152.5°	497.3	512.4	525.2	534.8	543.2	546.1	546.1
155°	483.4	495.6	505.4	512.7	519.2	520.8	521.6
157.5°	469.9	479.3	487.0	493.3	498.2	499.5	499.4
160°	461.5	469.5	475.2	480.9	485.8	485.8	485.0
162.5°	452.3	459.8	464.9	468.6	472.8	472.8	472.0
165°	439.4	445.2	449.2	452.5	455.8	454.9	454.9
167.5°	429.5	432.8	435.7	437.2	439.4	438.6	438.6
170°	422.4	425.6	427.2	428.0	429.7	428.8	428.8
172.5°	416.5	419.1	420.1	420.3	421.9	420.4	419.8
175°	408.5	410.2	410.2	410.2	411.0	410.2	409.4
177.5°	404.0	404.6	404.6	404.0	404.6	403.3	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0

(END OF REPORT)