

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332381-930

Luminaire Tested: **S123RDIP-S1165D1025U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332381-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S1165D1025U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6913.2 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332381-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332381-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	58	55	52	50	46	44	42	38
3	82	73	66	60	76	68	62	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	42	47	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17009	17009	17009
5°	17074	16839	16935
10°	16978	16628	16571
15°	16796	16238	16067
20°	16544	15753	15385
25°	16286	15206	14719
30°	15945	14574	13779
35°	15594	13943	12917
40°	15271	13200	11849
45°	14846	12466	10886
50°	14380	11632	9808
55°	13902	10678	8801
60°	13464	9657	7698
65°	12893	8550	6594
70°	12180	7179	5325
75°	11137	5648	5011
80°	9930	5002	4612
85°	8386	4434	4113



TEST NUMBER: P332381-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.4	2.1
10°-20°	412.9	6.0
20°-30°	594.5	8.6
30°-40°	669.6	9.7
40°-50°	640.6	9.3
50°-60°	524.6	7.6
60°-70°	354.0	5.1
70°-80°	178.1	2.6
80°-90°	50.2	0.7
90°-100°	39.8	0.6
100°-110°	189.8	2.7
110°-120°	455.9	6.6
120°-130°	580.5	8.4
130°-140°	620.3	9.0
140°-150°	580.0	8.4
150°-160°	467.9	6.8
160°-170°	302.0	4.4
170°-180°	104.1	1.5
0°-30°	1155.7	16.7
0°-40°	1825.4	26.4
0°-60°	2990.6	43.3
0°-90°	3572.8	51.7
90°-120°	685.5	9.9
90°-150°	2466.4	35.7
90°-180°	3340.0	48.3
0°-180°	6913.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1580	1573	1558	1569	1567	150
15°	1507	1492	1457	1451	1442	424
25°	1371	1338	1280	1254	1239	630
35°	1187	1139	1061	1008	983	742
45°	975	915	819	748	715	752
55°	741	675	569	497	469	664
65°	506	434	336	276	259	501
75°	268	206	136	124	120	286
85°	68	41	36	33	33	76
90°	1	9	20	23	24	6
95°	50	19	25	31	31	61
105°	242	247	178	42	36	257
115°	455	460	467	475	478	449
125°	641	648	651	653	654	572
135°	798	803	806	809	806	614
145°	921	927	928	930	930	576
155°	1015	1013	1014	1018	1013	467
165°	1070	1068	1067	1073	1068	302
175°	1095	1092	1092	1097	1091	104
180°	1095	1095	1095	1095	1095	



TEST NUMBER: P332381-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2
2.5°	1585.3	1584.4	1583.5	1582.6	1581.7	1579.8	1577.1	1574.3	1571.7	1568.9	1571.4
5°	1580.2	1578.7	1577.4	1575.9	1574.5	1572.1	1568.6	1565.2	1561.8	1558.4	1561.0
7.5°	1565.5	1564.1	1562.5	1561.0	1559.4	1556.4	1552.0	1547.5	1543.1	1538.6	1540.1
10°	1553.3	1551.3	1549.3	1547.3	1545.3	1541.7	1536.6	1531.5	1526.3	1521.3	1521.5
12.5°	1535.9	1533.7	1531.4	1529.2	1527.0	1522.7	1516.5	1510.2	1503.9	1497.6	1497.5
15°	1507.2	1504.0	1500.9	1497.7	1494.6	1489.1	1481.1	1473.1	1465.1	1457.2	1455.7
17.5°	1471.0	1467.4	1463.7	1460.0	1456.5	1449.5	1439.4	1429.2	1419.1	1409.0	1406.0
20°	1444.3	1439.8	1435.3	1430.7	1426.1	1418.5	1407.6	1396.8	1385.9	1375.2	1371.4
22.5°	1414.6	1409.3	1404.1	1398.9	1393.7	1385.3	1373.8	1362.3	1350.8	1339.2	1334.6
25°	1371.3	1364.2	1357.1	1349.9	1342.8	1332.7	1319.6	1306.5	1293.4	1280.3	1274.3
27.5°	1318.7	1310.9	1303.0	1295.2	1287.3	1276.1	1261.5	1246.9	1232.3	1217.7	1209.4
30°	1282.9	1274.3	1265.8	1257.2	1248.7	1236.4	1220.5	1204.5	1188.6	1172.6	1162.9
32.5°	1247.0	1237.3	1227.6	1217.9	1208.3	1195.0	1178.1	1161.2	1144.4	1127.6	1117.0
35°	1186.7	1176.5	1166.2	1156.0	1145.7	1131.8	1114.1	1096.5	1078.8	1061.1	1048.9
37.5°	1125.8	1114.4	1102.9	1091.5	1080.2	1065.0	1046.2	1027.4	1008.5	989.6	975.8
40°	1086.8	1074.2	1061.7	1049.2	1036.7	1020.3	1000.0	979.8	959.6	939.4	924.5
42.5°	1042.7	1030.1	1017.7	1005.1	992.5	975.8	955.0	934.0	913.1	892.3	876.0
45°	975.3	962.5	949.7	936.9	924.0	906.6	884.7	862.7	840.8	818.9	802.7
47.5°	907.8	893.8	879.7	865.7	851.6	833.6	811.6	789.7	767.8	745.9	728.2
50°	858.7	845.3	831.8	818.5	805.1	786.9	763.9	740.8	717.7	694.6	676.9
52.5°	814.6	800.1	785.5	771.0	756.4	737.8	714.9	692.1	669.3	646.5	628.1
55°	740.8	726.8	712.8	698.9	684.9	665.9	641.6	617.4	593.2	569.0	552.5
57.5°	672.5	657.4	642.1	627.0	611.7	592.0	567.7	543.3	519.0	494.7	479.1
60°	625.4	609.8	594.1	578.5	562.7	543.1	519.4	495.9	472.2	448.6	433.2
62.5°	578.2	562.6	546.9	531.2	515.6	495.9	472.3	448.7	425.0	401.4	386.9
65°	506.2	490.6	474.9	459.3	443.6	424.6	402.4	380.2	358.0	335.7	321.8
67.5°	434.2	418.3	402.5	386.7	370.9	352.3	331.0	309.7	288.4	267.1	256.7
70°	387.0	371.7	356.3	340.9	325.5	307.9	288.0	268.0	248.1	228.1	218.2
72.5°	339.9	324.7	309.6	294.4	279.2	262.6	244.5	226.4	208.3	190.2	182.1
75°	267.8	254.2	240.5	226.8	213.2	198.5	182.9	167.1	151.5	135.8	133.0
77.5°	202.2	189.9	177.5	165.2	152.8	141.5	131.5	121.4	111.3	101.3	99.7
80°	160.2	148.5	136.8	125.1	113.5	104.7	98.7	92.7	86.7	80.7	79.9
82.5°	120.2	110.1	100.0	89.9	79.9	73.5	70.7	67.8	65.1	62.3	61.4
85°	67.9	61.6	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.8	22.6	20.5	18.3	16.2	15.3	15.8	16.3	16.8	17.2	17.1
90°	0.8	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2
92.5°	15.2	14.6	14.1	13.6	13.1	13.8	15.5	17.3	19.1	20.9	22.0
95°	49.7	42.2	34.8	27.4	20.0	17.3	19.2	21.3	23.2	25.2	26.5
97.5°	99.8	96.4	93.1	89.8	86.4	78.3	65.3	52.3	39.2	26.2	27.6
100°	137.5	141.1	144.8	148.4	152.0	139.7	111.5	83.2	55.0	26.8	28.3
102.5°	180.5	183.1	185.7	188.3	190.9	176.8	146.0	115.2	84.4	53.6	49.1
105°	242.5	244.5	246.5	248.5	250.5	243.3	227.1	210.8	194.5	178.2	146.2
107.5°	307.9	309.6	311.1	312.7	314.3	316.4	318.9	321.6	324.1	326.7	303.2
110°	351.6	353.0	354.4	355.9	357.3	359.1	361.0	363.1	365.0	367.0	361.0



TEST NUMBER: P332381-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.2	394.5	395.8	397.1	398.4	400.1	402.1	404.1	406.0	408.1	408.1
115°	454.9	456.0	457.1	458.2	459.3	460.6	462.2	463.8	465.5	467.1	469.0
117.5°	514.6	516.0	517.3	518.7	520.0	521.1	521.9	522.8	523.6	524.4	525.9
120°	551.7	553.3	555.0	556.6	558.2	559.4	559.9	560.4	561.0	561.5	563.0
122.5°	589.5	590.8	592.2	593.5	594.8	595.9	596.6	597.3	597.9	598.6	599.7
125°	641.2	642.7	644.2	645.6	647.0	648.2	648.9	649.5	650.3	651.0	651.4
127.5°	691.4	692.8	694.3	695.7	697.2	698.3	699.2	700.1	700.9	701.8	702.4
130°	722.7	724.1	725.5	727.0	728.5	729.5	730.3	731.0	731.6	732.4	733.1
132.5°	752.6	754.1	755.5	756.9	758.4	759.4	759.9	760.5	761.2	761.7	762.5
135°	798.3	799.4	800.5	801.6	802.7	803.6	804.3	805.0	805.8	806.5	807.0
137.5°	837.4	838.8	840.2	841.6	842.9	843.8	844.2	844.6	845.0	845.4	846.2
140°	863.4	864.5	865.6	866.7	867.8	868.6	869.1	869.7	870.3	870.7	871.5
142.5°	887.5	888.6	889.7	890.8	891.9	892.7	893.2	893.7	894.3	894.9	895.4
145°	921.2	922.5	923.7	925.0	926.3	927.1	927.5	927.8	928.1	928.5	928.9
147.5°	952.9	953.8	954.6	955.4	956.3	956.8	957.2	957.6	958.0	958.3	958.7
150°	972.5	973.1	973.5	974.1	974.6	975.1	975.4	975.8	976.2	976.6	976.9
152.5°	990.0	990.3	990.6	990.8	991.1	991.3	991.5	991.7	992.0	992.1	992.8
155°	1014.8	1014.4	1014.1	1013.7	1013.3	1013.3	1013.4	1013.6	1013.8	1014.0	1014.9
157.5°	1034.0	1034.0	1034.0	1033.9	1033.9	1033.7	1033.6	1033.4	1033.2	1033.0	1034.1
160°	1045.7	1045.5	1045.4	1045.2	1045.0	1044.8	1044.6	1044.5	1044.2	1044.1	1045.2
162.5°	1056.8	1056.3	1055.8	1055.4	1054.9	1054.6	1054.4	1054.2	1054.0	1053.9	1055.1
165°	1070.2	1069.6	1069.0	1068.5	1068.0	1067.6	1067.4	1067.2	1067.1	1066.9	1068.3
167.5°	1080.5	1079.9	1079.1	1078.4	1077.7	1077.3	1077.3	1077.3	1077.3	1077.3	1078.7
170°	1086.4	1085.7	1085.0	1084.3	1083.5	1083.1	1083.1	1083.1	1083.1	1083.1	1084.6
172.5°	1090.3	1089.5	1088.6	1087.7	1086.9	1086.5	1086.6	1086.8	1086.9	1087.0	1088.5
175°	1095.4	1094.5	1093.6	1092.7	1091.8	1091.4	1091.5	1091.8	1091.9	1092.1	1093.4
177.5°	1096.7	1095.9	1095.2	1094.5	1093.8	1093.5	1093.6	1093.8	1093.9	1094.1	1095.2
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332381-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2
2.5°	1573.9	1576.5	1578.9	1580.0	1579.5	1579.1	1578.6	1578.1
5°	1563.5	1566.1	1568.6	1569.6	1569.0	1568.5	1567.9	1567.3
7.5°	1541.5	1543.0	1544.3	1544.6	1543.6	1542.6	1541.6	1540.7
10°	1521.8	1522.1	1522.4	1521.8	1520.4	1519.0	1517.5	1516.1
12.5°	1497.3	1497.1	1497.0	1496.1	1494.4	1492.7	1491.1	1489.5
15°	1454.3	1452.9	1451.5	1449.8	1447.7	1445.8	1443.7	1441.8
17.5°	1403.0	1399.9	1396.9	1393.9	1390.9	1388.0	1385.0	1382.0
20°	1367.7	1364.0	1360.3	1356.7	1353.3	1349.9	1346.5	1343.1
22.5°	1330.0	1325.4	1320.8	1316.9	1313.7	1310.5	1307.3	1304.2
25°	1268.4	1262.3	1256.4	1251.8	1248.7	1245.5	1242.4	1239.3
27.5°	1201.1	1192.8	1184.5	1177.9	1173.1	1168.4	1163.6	1158.8
30°	1153.2	1143.6	1133.9	1126.8	1122.3	1117.7	1113.1	1108.6
32.5°	1106.4	1095.8	1085.2	1077.5	1072.7	1067.9	1063.2	1058.3
35°	1036.7	1024.4	1012.2	1003.5	998.3	993.2	988.1	983.0
37.5°	961.8	947.9	934.0	923.9	917.6	911.3	905.0	898.6
40°	909.8	895.0	880.2	869.5	862.9	856.4	849.9	843.3
42.5°	859.9	843.7	827.5	816.5	810.7	804.8	798.9	793.0
45°	786.4	770.2	754.0	742.5	735.6	728.8	721.9	715.1
47.5°	710.5	692.9	675.2	663.4	657.3	651.2	645.1	639.0
50°	659.3	641.6	623.9	611.9	605.4	598.8	592.2	585.7
52.5°	609.8	591.4	573.1	560.9	555.1	549.3	543.4	537.5
55°	536.0	519.4	503.0	491.9	486.2	480.5	474.7	469.0
57.5°	463.5	447.8	432.3	422.0	417.2	412.4	407.5	402.7
60°	417.8	402.4	387.0	376.9	372.1	367.2	362.4	357.6
62.5°	372.4	358.0	343.5	333.8	328.6	323.6	318.5	313.5
65°	307.9	293.9	280.0	271.4	268.3	265.1	262.0	258.9
67.5°	246.2	235.8	225.3	218.5	215.2	211.7	208.4	205.0
70°	208.1	198.2	188.3	181.7	178.6	175.5	172.3	169.2
72.5°	173.9	165.8	157.6	152.9	151.6	150.3	149.0	147.7
75°	130.1	127.3	124.4	122.8	122.2	121.6	121.1	120.5
77.5°	98.2	96.6	95.1	94.0	93.4	92.9	92.3	91.7
80°	79.0	78.2	77.3	76.6	76.1	75.5	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.1	58.0	58.0
85°	34.7	34.2	33.6	33.3	33.3	33.3	33.3	33.3
87.5°	17.0	17.0	16.9	16.8	16.6	16.5	16.3	16.1
90°	21.0	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	23.2	24.3	25.4	26.2	26.3	26.6	26.8	27.0
95°	27.7	29.0	30.3	30.9	30.9	30.9	30.9	30.9
97.5°	29.1	30.6	32.0	32.8	33.0	33.2	33.3	33.5
100°	29.8	31.2	32.6	33.4	33.7	33.8	34.0	34.2
102.5°	44.6	40.1	35.6	33.5	33.8	34.2	34.5	34.8
105°	114.2	82.2	50.2	34.3	34.7	35.1	35.5	35.8
107.5°	279.7	256.2	232.8	209.0	184.8	160.7	136.6	112.4
110°	355.1	349.1	343.2	327.3	301.3	275.5	249.6	223.8



TEST NUMBER: P332381-930

CATALOG NUMBER: S123RDIP-S1165D1025U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	408.2	408.4	408.5	405.8	400.3	394.8	389.4	383.9
115°	470.8	472.5	474.3	475.6	476.3	477.0	477.8	478.5
117.5°	527.3	528.7	530.2	531.0	531.2	531.2	531.4	531.6
120°	564.4	565.8	567.3	568.0	568.0	568.0	568.0	568.0
122.5°	600.6	601.7	602.7	603.2	603.4	603.6	603.6	603.8
125°	651.8	652.1	652.5	652.8	653.2	653.5	654.0	654.3
127.5°	703.0	703.5	704.1	704.3	703.8	703.5	703.1	702.8
130°	733.9	734.6	735.3	735.5	735.2	734.7	734.4	734.0
132.5°	763.1	763.9	764.6	764.7	764.2	763.7	763.2	762.7
135°	807.6	808.1	808.6	808.6	808.1	807.6	807.0	806.5
137.5°	847.1	848.0	848.8	849.1	848.7	848.4	848.0	847.7
140°	872.2	872.9	873.7	873.8	873.4	873.1	872.8	872.4
142.5°	896.0	896.6	897.2	897.2	896.7	896.2	895.7	895.2
145°	929.3	929.6	930.0	930.2	930.2	930.2	930.2	930.2
147.5°	959.0	959.4	959.8	959.5	958.7	957.9	957.0	956.2
150°	977.3	977.6	978.0	977.9	977.4	976.8	976.2	975.8
152.5°	993.4	994.1	994.7	994.7	993.8	993.0	992.2	991.3
155°	1015.8	1016.7	1017.6	1017.5	1016.4	1015.4	1014.2	1013.2
157.5°	1035.2	1036.2	1037.4	1037.2	1035.8	1034.4	1033.0	1031.6
160°	1046.3	1047.3	1048.4	1048.3	1047.1	1045.8	1044.6	1043.3
162.5°	1056.3	1057.5	1058.7	1058.8	1057.7	1056.5	1055.5	1054.3
165°	1069.8	1071.2	1072.7	1072.8	1071.5	1070.2	1068.9	1067.7
167.5°	1080.2	1081.7	1083.0	1083.0	1081.7	1080.2	1078.7	1077.3
170°	1086.1	1087.5	1088.9	1088.9	1087.5	1086.1	1084.6	1083.1
172.5°	1090.0	1091.4	1092.8	1092.7	1091.2	1089.6	1088.0	1086.4
175°	1094.6	1095.9	1097.1	1097.1	1095.6	1094.2	1092.7	1091.3
177.5°	1096.3	1097.6	1098.7	1098.5	1097.1	1095.7	1094.2	1092.7
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4

(END OF REPORT)