

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332258-930

Luminaire Tested: **S123RDIP-S340D1025U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332258-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1025U930-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4448.2 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25				
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	30	29	28	22				
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	26	25	24	18				
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21	16				
4	71	60	53	47	63	54	48	43	42	38	35	31	29	26	21	20	18	14				
5	65	54	46	41	57	48	42	37	38	33	30	28	25	23	19	17	16	12				
6	60	48	41	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11				
7	55	43	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	10				
8	51	39	32	27	45	35	29	25	28	24	20	21	18	16	15	13	11	9				
9	47	36	29	24	42	32	26	22	26	21	18	19	16	14	14	12	10	8				
10	44	33	26	21	39	30	24	20	24	19	16	18	15	13	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4776	4776	4776	4776
5°	5693	4796	4224	4796
10°	7109	4769	3816	4769
15°	8344	4719	3480	4719
20°	9313	4647	3194	4647
25°	9164	4570	3018	4570
30°	6586	4501	2838	4501
35°	4398	4407	2720	4407
40°	3240	4297	2599	4297
45°	2719	4102	2481	4102
50°	2398	3848	2316	3848
55°	2104	3558	2089	3558
60°	1873	3279	1914	3279
65°	1645	2980	1780	2980
70°	1290	2716	1627	2716
75°	1135	2371	1485	2371
80°	992	2008	1463	2008
85°	790	1618	1556	1618



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	1.0
10°-20°	136.3	3.1
20°-30°	214.2	4.8
30°-40°	223.4	5.0
40°-50°	191.2	4.3
50°-60°	145.7	3.3
60°-70°	93.4	2.1
70°-80°	44.9	1.0
80°-90°	15.0	0.3
90°-100°	39.8	0.9
100°-110°	189.8	4.3
110°-120°	455.9	10.2
120°-130°	580.5	13.1
130°-140°	620.3	13.9
140°-150°	580.0	13.0
150°-160°	467.9	10.5
160°-170°	302.0	6.8
170°-180°	104.1	2.3
0°-30°	394.1	8.9
0°-40°	617.6	13.9
0°-60°	954.5	21.5
0°-90°	1107.8	24.9
90°-120°	685.5	15.4
90°-150°	2466.4	55.4
90°-180°	3340.0	75.1
0°-180°	4448.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	527	444	391	444	527	54
15°	749	424	312	424	749	212
25°	772	385	254	385	772	332
35°	335	335	207	335	335	219
45°	179	270	163	270	179	140
55°	112	190	111	190	112	101
65°	65	117	70	117	65	64
75°	27	57	36	57	27	29
85°	6	13	13	13	6	8
90°	24	1	24	1	24	11
95°	31	50	31	50	31	26
105°	36	242	36	242	36	82
115°	478	455	478	455	478	442
125°	654	641	654	641	654	584
135°	806	798	806	798	806	622
145°	930	921	930	921	930	581
155°	1013	1015	1013	1015	1013	467
165°	1068	1070	1068	1070	1068	301
175°	1091	1095	1091	1095	1091	104
180°	1095	1095	1095	1095	1095	



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	472.6	473.2	471.2	470.9	468.6	468.1	468.1	464.8	462.8	460.3	458.8
5°	526.9	529.9	528.4	525.1	519.3	518.0	514.4	508.7	502.2	494.2	490.5
7.5°	594.8	598.9	597.3	592.1	586.0	581.2	571.0	561.6	548.4	536.7	526.8
10°	650.4	646.0	642.6	637.5	631.9	623.1	612.4	597.8	580.9	567.5	552.8
12.5°	692.0	691.3	687.0	681.7	673.9	665.4	652.3	634.5	614.9	595.7	578.7
15°	748.8	749.9	747.1	741.6	730.5	715.5	695.8	688.4	660.2	639.4	618.5
17.5°	788.1	787.8	787.4	779.8	768.6	757.9	739.6	720.1	694.6	665.2	637.1
20°	813.0	811.1	811.5	802.9	794.6	782.2	764.3	736.1	715.2	681.2	652.1
22.5°	812.4	812.0	813.4	810.5	804.5	795.0	780.9	757.0	730.3	696.0	663.3
25°	771.6	770.1	778.9	781.5	791.2	792.9	788.6	775.6	750.3	714.9	674.5
27.5°	645.7	644.9	661.5	682.2	708.5	729.0	748.7	758.2	750.3	725.0	684.4
30°	529.9	547.8	556.2	586.2	619.6	659.5	694.5	727.7	735.9	724.8	691.6
32.5°	440.0	455.6	462.6	488.3	519.5	566.2	618.6	665.7	699.0	707.4	687.4
35°	334.7	334.8	350.8	362.2	391.1	439.1	490.1	553.1	615.8	663.3	668.2
37.5°	267.1	268.0	277.7	289.0	310.7	336.1	380.9	433.3	505.7	578.6	621.4
40°	230.6	232.3	239.5	250.7	266.3	285.5	320.4	369.8	430.2	511.4	577.6
42.5°	207.2	209.9	213.7	222.3	232.0	250.0	278.2	316.3	371.3	448.0	524.5
45°	178.6	180.1	183.0	186.9	195.7	208.1	227.1	252.8	298.4	360.1	436.7
47.5°	157.5	156.7	159.7	162.9	168.8	177.3	190.0	210.9	243.4	293.0	357.9
50°	143.2	143.0	145.1	147.6	153.1	159.4	169.8	185.6	211.4	252.4	311.9
52.5°	129.9	130.5	132.1	135.1	139.1	144.1	153.5	164.9	187.1	222.5	272.1
55°	112.1	112.7	114.7	116.4	119.3	124.4	130.3	139.8	155.0	179.7	220.5
57.5°	97.0	96.8	98.7	99.2	102.4	106.6	111.1	118.5	129.6	147.9	175.4
60°	87.0	86.4	88.1	89.4	91.2	94.6	98.4	105.6	114.4	127.8	151.4
62.5°	77.9	77.6	78.8	80.2	81.6	84.7	87.9	93.4	100.4	111.7	130.4
65°	64.6	65.1	65.7	66.3	67.0	69.0	72.0	75.8	80.6	88.5	102.0
67.5°	50.8	51.4	51.5	52.7	54.3	55.5	57.4	60.7	64.1	70.8	78.4
70°	41.0	40.8	41.0	41.6	43.7	45.7	48.3	50.7	52.8	57.6	64.0
72.5°	35.2	34.9	35.4	35.5	36.5	37.1	38.6	41.0	43.7	46.9	51.5
75°	27.3	27.3	27.3	27.3	28.1	28.5	29.0	29.6	30.6	32.1	35.5
77.5°	20.2	20.2	20.5	20.7	20.9	21.1	21.4	22.0	22.3	23.2	24.6
80°	16.0	16.1	16.0	16.1	16.1	16.6	16.7	17.3	17.4	18.4	19.0
82.5°	12.0	11.9	12.0	12.2	12.2	12.6	12.6	13.0	13.0	13.5	14.1
85°	6.4	6.1	6.4	6.3	6.7	6.3	6.4	6.8	6.8	7.0	7.8
87.5°	6.4	6.6	6.3	6.4	6.3	6.3	6.2	6.0	6.2	5.9	5.5
90°	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0	20.2	19.6	17.2
92.5°	27.0	26.8	26.6	26.3	26.2	25.4	24.3	23.2	22.0	20.9	19.1
95°	30.9	30.9	30.9	30.9	30.9	30.3	29.0	27.7	26.5	25.2	23.2
97.5°	33.5	33.3	33.2	33.0	32.8	32.0	30.6	29.1	27.6	26.2	39.2
100°	34.2	34.0	33.8	33.7	33.4	32.6	31.2	29.8	28.3	26.8	55.0
102.5°	34.8	34.5	34.2	33.8	33.5	35.6	40.1	44.6	49.1	53.6	84.4
105°	35.8	35.5	35.1	34.7	34.3	50.2	82.2	114.2	146.2	178.2	194.5
107.5°	112.4	136.6	160.7	184.8	209.0	232.8	256.2	279.7	303.2	326.7	324.1
110°	223.8	249.6	275.5	301.3	327.3	343.2	349.1	355.1	361.0	367.0	365.0



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.9	389.4	394.8	400.3	405.8	408.5	408.4	408.2	408.1	408.1	406.0
115°	478.5	477.8	477.0	476.3	475.6	474.3	472.5	470.8	469.0	467.1	465.5
117.5°	531.6	531.4	531.2	531.2	531.0	530.2	528.7	527.3	525.9	524.4	523.6
120°	568.0	568.0	568.0	568.0	568.0	567.3	565.8	564.4	563.0	561.5	561.0
122.5°	603.8	603.6	603.6	603.4	603.2	602.7	601.7	600.6	599.7	598.6	597.9
125°	654.3	654.0	653.5	653.2	652.8	652.5	652.1	651.8	651.4	651.0	650.3
127.5°	702.8	703.1	703.5	703.8	704.3	704.1	703.5	703.0	702.4	701.8	700.9
130°	734.0	734.4	734.7	735.2	735.5	735.3	734.6	733.9	733.1	732.4	731.6
132.5°	762.7	763.2	763.7	764.2	764.7	764.6	763.9	763.1	762.5	761.7	761.2
135°	806.5	807.0	807.6	808.1	808.6	808.6	808.1	807.6	807.0	806.5	805.8
137.5°	847.7	848.0	848.4	848.7	849.1	848.8	848.0	847.1	846.2	845.4	845.0
140°	872.4	872.8	873.1	873.4	873.8	873.7	872.9	872.2	871.5	870.7	870.3
142.5°	895.2	895.7	896.2	896.7	897.2	897.2	896.6	896.0	895.4	894.9	894.3
145°	930.2	930.2	930.2	930.2	930.2	930.0	929.6	929.3	928.9	928.5	928.1
147.5°	956.2	957.0	957.9	958.7	959.5	959.8	959.4	959.0	958.7	958.3	958.0
150°	975.8	976.2	976.8	977.4	977.9	978.0	977.6	977.3	976.9	976.6	976.2
152.5°	991.3	992.2	993.0	993.8	994.7	994.7	994.1	993.4	992.8	992.1	992.0
155°	1013.2	1014.2	1015.4	1016.4	1017.5	1017.6	1016.7	1015.8	1014.9	1014.0	1013.8
157.5°	1031.6	1033.0	1034.4	1035.8	1037.2	1037.4	1036.2	1035.2	1034.1	1033.0	1033.2
160°	1043.3	1044.6	1045.8	1047.1	1048.3	1048.4	1047.3	1046.3	1045.2	1044.1	1044.2
162.5°	1054.3	1055.5	1056.5	1057.7	1058.8	1058.7	1057.5	1056.3	1055.1	1053.9	1054.0
165°	1067.7	1068.9	1070.2	1071.5	1072.8	1072.7	1071.2	1069.8	1068.3	1066.9	1067.1
167.5°	1077.3	1078.7	1080.2	1081.7	1083.0	1083.0	1081.7	1080.2	1078.7	1077.3	1077.3
170°	1083.1	1084.6	1086.1	1087.5	1088.9	1088.9	1087.5	1086.1	1084.6	1083.1	1083.1
172.5°	1086.4	1088.0	1089.6	1091.2	1092.7	1092.8	1091.4	1090.0	1088.5	1087.0	1086.9
175°	1091.3	1092.7	1094.2	1095.6	1097.1	1097.1	1095.9	1094.6	1093.4	1092.1	1091.9
177.5°	1092.7	1094.2	1095.7	1097.1	1098.5	1098.7	1097.6	1096.3	1095.2	1094.1	1093.9
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	458.1	457.7	455.6	453.1	450.0	447.8	446.1	445.2	442.5	439.1	436.9
5°	486.5	480.8	474.7	467.2	460.4	453.4	449.1	443.9	437.7	430.6	425.7
7.5°	516.7	505.6	493.6	481.1	468.9	457.9	448.1	439.8	429.8	419.7	412.7
10°	540.1	523.7	506.8	489.5	473.8	458.9	447.5	436.3	424.4	412.8	404.0
12.5°	561.2	539.6	520.2	498.9	478.7	461.1	444.7	431.5	417.0	404.7	394.8
15°	587.9	565.8	542.3	510.0	483.2	460.8	440.8	423.5	406.1	390.9	381.2
17.5°	612.9	579.8	548.0	521.1	486.3	458.4	434.0	413.4	394.1	378.1	366.1
20°	623.2	591.1	556.8	522.4	488.2	456.8	428.5	405.7	385.8	367.5	356.5
22.5°	629.4	593.1	556.8	519.9	483.6	451.0	423.1	397.9	376.3	359.1	345.4
25°	636.7	593.4	553.5	517.1	480.0	444.7	411.4	384.8	361.5	343.1	328.6
27.5°	641.5	590.5	543.4	502.9	465.3	430.2	399.7	371.5	347.7	328.2	312.7
30°	642.4	588.2	535.7	491.8	453.6	421.3	389.0	362.1	337.0	316.3	301.8
32.5°	643.6	582.6	525.1	478.6	439.4	407.5	378.2	352.5	326.8	306.4	291.6
35°	638.6	579.5	509.2	455.7	416.5	385.6	359.2	335.4	310.2	290.4	275.4
37.5°	617.0	567.2	492.8	429.9	389.0	360.4	338.8	318.1	295.0	273.6	259.5
40°	595.3	555.1	480.0	414.3	371.5	342.1	322.7	305.8	283.4	263.4	248.3
42.5°	563.0	538.4	467.8	397.9	351.8	323.4	307.0	291.2	271.6	251.3	237.0
45°	503.5	506.8	443.0	371.7	324.4	296.0	280.5	269.5	252.1	235.4	220.7
47.5°	429.1	459.3	413.8	343.9	295.6	268.9	255.4	245.8	234.0	217.6	204.2
50°	380.5	423.5	390.4	325.2	277.5	250.9	237.7	229.8	219.6	206.7	194.0
52.5°	335.7	382.0	362.1	304.4	257.9	233.6	220.6	214.2	206.0	193.9	182.4
55°	273.7	320.7	316.1	273.0	228.5	206.7	196.8	189.6	184.1	175.0	165.8
57.5°	221.4	265.9	268.2	238.0	202.6	181.0	172.5	167.1	163.5	156.6	148.1
60°	188.4	229.3	237.3	214.4	184.1	165.1	156.7	152.3	149.5	144.0	137.5
62.5°	161.1	195.8	204.9	188.5	166.3	148.5	141.9	137.8	135.8	131.1	125.4
65°	123.3	152.1	160.9	151.8	140.1	126.0	120.6	117.0	115.3	112.7	108.4
67.5°	92.7	113.7	123.4	116.9	112.7	103.7	100.4	98.4	96.9	95.1	91.6
70°	74.4	90.0	99.9	98.2	94.8	90.0	87.6	86.3	84.7	83.2	80.1
72.5°	59.8	70.6	79.8	80.7	77.9	77.0	74.8	74.2	73.3	71.5	69.8
75°	39.7	47.1	53.6	56.0	57.2	58.1	57.2	57.0	56.8	55.3	54.3
77.5°	26.0	30.0	34.1	38.3	40.1	41.3	41.7	42.4	41.8	41.1	40.6
80°	20.0	20.9	23.7	27.3	30.2	31.3	32.1	32.4	32.3	32.1	31.3
82.5°	14.5	15.2	16.6	19.2	21.5	23.4	23.9	23.8	24.2	24.4	23.7
85°	7.8	8.0	8.4	8.7	10.0	12.1	12.7	13.1	13.5	13.5	12.3
87.5°	5.4	4.8	4.6	4.2	4.3	4.1	4.6	5.1	5.5	5.3	5.6
90°	14.8	12.5	10.1	8.1	6.3	4.4	2.6	0.8	2.6	4.4	6.3
92.5°	17.3	15.5	13.8	13.1	13.6	14.1	14.6	15.2	14.6	14.1	13.6
95°	21.3	19.2	17.3	20.0	27.4	34.8	42.2	49.7	42.2	34.8	27.4
97.5°	52.3	65.3	78.3	86.4	89.8	93.1	96.4	99.8	96.4	93.1	89.8
100°	83.2	111.5	139.7	152.0	148.4	144.8	141.1	137.5	141.1	144.8	148.4
102.5°	115.2	146.0	176.8	190.9	188.3	185.7	183.1	180.5	183.1	185.7	188.3
105°	210.8	227.1	243.3	250.5	248.5	246.5	244.5	242.5	244.5	246.5	248.5
107.5°	321.6	318.9	316.4	314.3	312.7	311.1	309.6	307.9	309.6	311.1	312.7
110°	363.1	361.0	359.1	357.3	355.9	354.4	353.0	351.6	353.0	354.4	355.9



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	404.1	402.1	400.1	398.4	397.1	395.8	394.5	393.2	394.5	395.8	397.1
115°	463.8	462.2	460.6	459.3	458.2	457.1	456.0	454.9	456.0	457.1	458.2
117.5°	522.8	521.9	521.1	520.0	518.7	517.3	516.0	514.6	516.0	517.3	518.7
120°	560.4	559.9	559.4	558.2	556.6	555.0	553.3	551.7	553.3	555.0	556.6
122.5°	597.3	596.6	595.9	594.8	593.5	592.2	590.8	589.5	590.8	592.2	593.5
125°	649.5	648.9	648.2	647.0	645.6	644.2	642.7	641.2	642.7	644.2	645.6
127.5°	700.1	699.2	698.3	697.2	695.7	694.3	692.8	691.4	692.8	694.3	695.7
130°	731.0	730.3	729.5	728.5	727.0	725.5	724.1	722.7	724.1	725.5	727.0
132.5°	760.5	759.9	759.4	758.4	756.9	755.5	754.1	752.6	754.1	755.5	756.9
135°	805.0	804.3	803.6	802.7	801.6	800.5	799.4	798.3	799.4	800.5	801.6
137.5°	844.6	844.2	843.8	842.9	841.6	840.2	838.8	837.4	838.8	840.2	841.6
140°	869.7	869.1	868.6	867.8	866.7	865.6	864.5	863.4	864.5	865.6	866.7
142.5°	893.7	893.2	892.7	891.9	890.8	889.7	888.6	887.5	888.6	889.7	890.8
145°	927.8	927.5	927.1	926.3	925.0	923.7	922.5	921.2	922.5	923.7	925.0
147.5°	957.6	957.2	956.8	956.3	955.4	954.6	953.8	952.9	953.8	954.6	955.4
150°	975.8	975.4	975.1	974.6	974.1	973.5	973.1	972.5	973.1	973.5	974.1
152.5°	991.7	991.5	991.3	991.1	990.8	990.6	990.3	990.0	990.3	990.6	990.8
155°	1013.6	1013.4	1013.3	1013.3	1013.7	1014.1	1014.4	1014.8	1014.4	1014.1	1013.7
157.5°	1033.4	1033.6	1033.7	1033.9	1033.9	1034.0	1034.0	1034.0	1034.0	1034.0	1033.9
160°	1044.5	1044.6	1044.8	1045.0	1045.2	1045.4	1045.5	1045.7	1045.5	1045.4	1045.2
162.5°	1054.2	1054.4	1054.6	1054.9	1055.4	1055.8	1056.3	1056.8	1056.3	1055.8	1055.4
165°	1067.2	1067.4	1067.6	1068.0	1068.5	1069.0	1069.6	1070.2	1069.6	1069.0	1068.5
167.5°	1077.3	1077.3	1077.3	1077.7	1078.4	1079.1	1079.9	1080.5	1079.9	1079.1	1078.4
170°	1083.1	1083.1	1083.1	1083.5	1084.3	1085.0	1085.7	1086.4	1085.7	1085.0	1084.3
172.5°	1086.8	1086.6	1086.5	1086.9	1087.7	1088.6	1089.5	1090.3	1089.5	1088.6	1087.7
175°	1091.8	1091.5	1091.4	1091.8	1092.7	1093.6	1094.5	1095.4	1094.5	1093.6	1092.7
177.5°	1093.8	1093.6	1093.5	1093.8	1094.5	1095.2	1095.9	1096.7	1095.9	1095.2	1094.5
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	436.1	434.1	432.8	429.7	427.8	425.7	423.5	424.9	424.7	424.6	424.6
5°	421.5	417.1	413.1	408.0	404.8	400.8	397.8	397.4	398.1	395.5	394.0
7.5°	407.0	401.0	395.3	389.7	383.7	378.9	375.9	374.5	372.6	371.0	369.2
10°	396.8	389.8	384.3	377.2	370.8	365.1	361.5	359.0	357.7	356.4	353.8
12.5°	386.3	379.4	372.4	364.4	358.3	351.7	349.0	346.3	343.7	342.2	338.8
15°	371.0	362.1	354.7	346.3	339.4	333.0	329.2	323.7	322.9	321.0	317.6
17.5°	355.6	345.9	335.7	329.5	321.8	315.0	309.2	307.4	302.0	299.9	296.9
20°	343.4	334.5	326.7	318.5	307.4	301.1	296.5	294.1	289.7	287.0	285.1
22.5°	333.0	323.8	314.9	305.3	296.1	289.0	285.7	281.8	279.5	275.7	273.7
25°	318.0	308.1	297.3	287.0	280.4	275.1	269.7	266.3	262.9	261.1	257.4
27.5°	300.6	290.2	280.1	272.3	264.2	258.9	254.1	251.1	247.0	244.1	242.0
30°	291.0	278.8	270.1	263.1	252.7	247.7	244.1	240.3	237.3	234.2	232.1
32.5°	279.9	268.8	260.6	251.8	243.9	238.4	233.7	230.4	227.8	224.9	222.8
35°	262.5	253.2	244.7	235.9	230.0	224.5	219.0	216.1	213.7	211.0	209.1
37.5°	246.8	238.1	229.9	221.7	214.3	209.9	205.5	203.3	199.9	198.1	196.2
40°	237.1	228.5	219.8	211.8	204.2	200.8	196.8	193.6	190.5	189.1	187.1
42.5°	226.4	217.8	210.5	201.9	195.7	191.0	187.4	183.8	181.6	179.6	178.5
45°	210.7	203.1	195.8	187.3	181.4	177.4	173.3	170.0	168.0	166.6	164.5
47.5°	195.3	187.8	180.4	173.0	167.3	162.7	158.5	156.3	153.5	151.9	150.5
50°	184.3	177.4	169.7	162.8	157.1	152.5	149.1	146.3	143.8	141.7	140.7
52.5°	174.1	166.8	160.0	153.7	147.7	142.5	139.4	136.4	134.5	132.2	131.0
55°	157.3	150.3	144.6	138.3	132.4	128.0	124.3	121.6	119.7	117.0	115.5
57.5°	141.5	135.2	128.4	122.9	116.9	113.2	110.1	106.5	104.1	102.1	100.5
60°	130.9	123.7	117.7	112.7	107.3	102.6	99.7	96.9	94.4	92.3	91.0
62.5°	119.8	113.5	107.9	102.3	97.4	93.3	90.0	87.6	85.4	84.1	82.8
65°	102.7	97.8	92.1	87.6	83.0	80.0	77.3	75.3	73.7	72.7	71.6
67.5°	87.1	82.3	77.4	72.9	69.8	67.5	65.8	64.0	63.2	62.0	61.2
70°	77.0	72.0	67.6	64.2	61.1	59.4	58.3	57.0	56.3	54.7	54.0
72.5°	65.9	62.3	59.1	56.3	53.9	52.3	50.9	49.2	48.0	46.3	45.6
75°	51.9	48.6	46.1	44.3	42.7	40.7	38.6	36.9	36.3	35.7	35.5
77.5°	38.4	36.4	34.6	32.9	31.1	29.6	29.1	28.7	28.6	28.3	28.3
80°	30.2	28.3	27.0	25.1	24.0	24.0	24.0	23.6	23.7	23.7	23.7
82.5°	22.4	20.7	20.0	19.3	19.1	19.2	19.2	19.3	19.2	19.5	19.3
85°	11.6	11.7	12.1	12.0	12.1	12.1	12.6	12.3	12.6	12.1	12.6
87.5°	5.9	6.8	7.3	8.0	8.6	8.9	9.2	9.4	9.6	9.8	9.9
90°	8.1	10.1	12.5	14.8	17.2	19.6	20.2	21.0	21.7	22.4	23.0
92.5°	13.1	13.8	15.5	17.3	19.1	20.9	22.0	23.2	24.3	25.4	26.2
95°	20.0	17.3	19.2	21.3	23.2	25.2	26.5	27.7	29.0	30.3	30.9
97.5°	86.4	78.3	65.3	52.3	39.2	26.2	27.6	29.1	30.6	32.0	32.8
100°	152.0	139.7	111.5	83.2	55.0	26.8	28.3	29.8	31.2	32.6	33.4
102.5°	190.9	176.8	146.0	115.2	84.4	53.6	49.1	44.6	40.1	35.6	33.5
105°	250.5	243.3	227.1	210.8	194.5	178.2	146.2	114.2	82.2	50.2	34.3
107.5°	314.3	316.4	318.9	321.6	324.1	326.7	303.2	279.7	256.2	232.8	209.0
110°	357.3	359.1	361.0	363.1	365.0	367.0	361.0	355.1	349.1	343.2	327.3



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	398.4	400.1	402.1	404.1	406.0	408.1	408.1	408.2	408.4	408.5	405.8
115°	459.3	460.6	462.2	463.8	465.5	467.1	469.0	470.8	472.5	474.3	475.6
117.5°	520.0	521.1	521.9	522.8	523.6	524.4	525.9	527.3	528.7	530.2	531.0
120°	558.2	559.4	559.9	560.4	561.0	561.5	563.0	564.4	565.8	567.3	568.0
122.5°	594.8	595.9	596.6	597.3	597.9	598.6	599.7	600.6	601.7	602.7	603.2
125°	647.0	648.2	648.9	649.5	650.3	651.0	651.4	651.8	652.1	652.5	652.8
127.5°	697.2	698.3	699.2	700.1	700.9	701.8	702.4	703.0	703.5	704.1	704.3
130°	728.5	729.5	730.3	731.0	731.6	732.4	733.1	733.9	734.6	735.3	735.5
132.5°	758.4	759.4	759.9	760.5	761.2	761.7	762.5	763.1	763.9	764.6	764.7
135°	802.7	803.6	804.3	805.0	805.8	806.5	807.0	807.6	808.1	808.6	808.6
137.5°	842.9	843.8	844.2	844.6	845.0	845.4	846.2	847.1	848.0	848.8	849.1
140°	867.8	868.6	869.1	869.7	870.3	870.7	871.5	872.2	872.9	873.7	873.8
142.5°	891.9	892.7	893.2	893.7	894.3	894.9	895.4	896.0	896.6	897.2	897.2
145°	926.3	927.1	927.5	927.8	928.1	928.5	928.9	929.3	929.6	930.0	930.2
147.5°	956.3	956.8	957.2	957.6	958.0	958.3	958.7	959.0	959.4	959.8	959.5
150°	974.6	975.1	975.4	975.8	976.2	976.6	976.9	977.3	977.6	978.0	977.9
152.5°	991.1	991.3	991.5	991.7	992.0	992.1	992.8	993.4	994.1	994.7	994.7
155°	1013.3	1013.3	1013.4	1013.6	1013.8	1014.0	1014.9	1015.8	1016.7	1017.6	1017.5
157.5°	1033.9	1033.7	1033.6	1033.4	1033.2	1033.0	1034.1	1035.2	1036.2	1037.4	1037.2
160°	1045.0	1044.8	1044.6	1044.5	1044.2	1044.1	1045.2	1046.3	1047.3	1048.4	1048.3
162.5°	1054.9	1054.6	1054.4	1054.2	1054.0	1053.9	1055.1	1056.3	1057.5	1058.7	1058.8
165°	1068.0	1067.6	1067.4	1067.2	1067.1	1066.9	1068.3	1069.8	1071.2	1072.7	1072.8
167.5°	1077.7	1077.3	1077.3	1077.3	1077.3	1077.3	1078.7	1080.2	1081.7	1083.0	1083.0
170°	1083.5	1083.1	1083.1	1083.1	1083.1	1083.1	1084.6	1086.1	1087.5	1088.9	1088.9
172.5°	1086.9	1086.5	1086.6	1086.8	1086.9	1087.0	1088.5	1090.0	1091.4	1092.8	1092.7
175°	1091.8	1091.4	1091.5	1091.8	1091.9	1092.1	1093.4	1094.6	1095.9	1097.1	1097.1
177.5°	1093.8	1093.5	1093.6	1093.8	1093.9	1094.1	1095.2	1096.3	1097.6	1098.7	1098.5
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	422.7	422.6	422.7	422.2	422.7	422.6	422.7	424.6	424.6	424.7	424.9
5°	393.4	393.2	392.6	390.9	392.6	393.2	393.4	394.0	395.5	398.1	397.4
7.5°	367.7	367.5	365.8	365.8	365.8	367.5	367.7	369.2	371.0	372.6	374.5
10°	352.5	352.7	350.4	349.1	350.4	352.7	352.5	353.8	356.4	357.7	359.0
12.5°	337.8	337.0	335.1	333.6	335.1	337.0	337.8	338.8	342.2	343.7	346.3
15°	318.4	316.4	311.9	312.3	311.9	316.4	318.4	317.6	321.0	322.9	323.7
17.5°	295.5	294.1	294.0	291.3	294.0	294.1	295.5	296.9	299.9	302.0	307.4
20°	282.1	281.1	281.5	278.8	281.5	281.1	282.1	285.1	287.0	289.7	294.1
22.5°	271.6	270.6	269.0	268.2	269.0	270.6	271.6	273.7	275.7	279.5	281.8
25°	256.2	254.7	253.2	254.1	253.2	254.7	256.2	257.4	261.1	262.9	266.3
27.5°	240.9	239.8	238.2	238.1	238.2	239.8	240.9	242.0	244.1	247.0	251.1
30°	231.1	230.0	229.3	228.3	229.3	230.0	231.1	232.1	234.2	237.3	240.3
32.5°	221.3	221.0	219.7	219.5	219.7	221.0	221.3	222.8	224.9	227.8	230.4
35°	208.4	207.2	206.8	207.0	206.8	207.2	208.4	209.1	211.0	213.7	216.1
37.5°	196.1	194.6	193.9	193.2	193.9	194.6	196.1	196.2	198.1	199.9	203.3
40°	187.3	185.8	185.4	185.0	185.4	185.8	187.3	187.1	189.1	190.5	193.6
42.5°	177.4	176.8	176.6	175.9	176.6	176.8	177.4	178.5	179.6	181.6	183.8
45°	164.0	163.7	162.6	163.0	162.6	163.7	164.0	164.5	166.6	168.0	170.0
47.5°	149.7	148.9	148.1	148.6	148.1	148.9	149.7	150.5	151.9	153.5	156.3
50°	140.0	139.6	137.9	138.3	137.9	139.6	140.0	140.7	141.7	143.8	146.3
52.5°	130.3	128.8	128.2	127.9	128.2	128.8	130.3	131.0	132.2	134.5	136.4
55°	114.1	112.4	111.7	111.3	111.7	112.4	114.1	115.5	117.0	119.7	121.6
57.5°	98.3	97.9	97.3	97.7	97.3	97.9	98.3	100.5	102.1	104.1	106.5
60°	89.1	89.1	89.1	88.9	89.1	89.1	89.1	91.0	92.3	94.4	96.9
62.5°	81.9	81.4	81.4	81.6	81.4	81.4	81.9	82.8	84.1	85.4	87.6
65°	71.0	70.8	70.1	69.9	70.1	70.8	71.0	71.6	72.7	73.7	75.3
67.5°	60.7	60.1	59.8	59.6	59.8	60.1	60.7	61.2	62.0	63.2	64.0
70°	53.0	52.6	51.4	51.7	51.4	52.6	53.0	54.0	54.7	56.3	57.0
72.5°	44.7	44.3	44.0	43.8	44.0	44.3	44.7	45.6	46.3	48.0	49.2
75°	35.3	35.1	35.0	35.7	35.0	35.1	35.3	35.5	35.7	36.3	36.9
77.5°	28.3	28.3	28.5	28.1	28.5	28.3	28.3	28.3	28.3	28.6	28.7
80°	23.7	23.7	23.6	23.6	23.6	23.7	23.7	23.7	23.7	23.7	23.6
82.5°	19.0	19.2	19.3	19.0	19.3	19.2	19.0	19.3	19.5	19.2	19.3
85°	12.6	12.3	12.7	12.6	12.7	12.3	12.6	12.6	12.1	12.6	12.3
87.5°	10.3	10.0	10.1	10.4	10.1	10.0	10.3	9.9	9.8	9.6	9.4
90°	23.3	23.7	24.1	24.4	24.1	23.7	23.3	23.0	22.4	21.7	21.0
92.5°	26.3	26.6	26.8	27.0	26.8	26.6	26.3	26.2	25.4	24.3	23.2
95°	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.9	30.3	29.0	27.7
97.5°	33.0	33.2	33.3	33.5	33.3	33.2	33.0	32.8	32.0	30.6	29.1
100°	33.7	33.8	34.0	34.2	34.0	33.8	33.7	33.4	32.6	31.2	29.8
102.5°	33.8	34.2	34.5	34.8	34.5	34.2	33.8	33.5	35.6	40.1	44.6
105°	34.7	35.1	35.5	35.8	35.5	35.1	34.7	34.3	50.2	82.2	114.2
107.5°	184.8	160.7	136.6	112.4	136.6	160.7	184.8	209.0	232.8	256.2	279.7
110°	301.3	275.5	249.6	223.8	249.6	275.5	301.3	327.3	343.2	349.1	355.1



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	400.3	394.8	389.4	383.9	389.4	394.8	400.3	405.8	408.5	408.4	408.2
115°	476.3	477.0	477.8	478.5	477.8	477.0	476.3	475.6	474.3	472.5	470.8
117.5°	531.2	531.2	531.4	531.6	531.4	531.2	531.2	531.0	530.2	528.7	527.3
120°	568.0	568.0	568.0	568.0	568.0	568.0	568.0	568.0	567.3	565.8	564.4
122.5°	603.4	603.6	603.6	603.8	603.6	603.6	603.4	603.2	602.7	601.7	600.6
125°	653.2	653.5	654.0	654.3	654.0	653.5	653.2	652.8	652.5	652.1	651.8
127.5°	703.8	703.5	703.1	702.8	703.1	703.5	703.8	704.3	704.1	703.5	703.0
130°	735.2	734.7	734.4	734.0	734.4	734.7	735.2	735.5	735.3	734.6	733.9
132.5°	764.2	763.7	763.2	762.7	763.2	763.7	764.2	764.7	764.6	763.9	763.1
135°	808.1	807.6	807.0	806.5	807.0	807.6	808.1	808.6	808.6	808.1	807.6
137.5°	848.7	848.4	848.0	847.7	848.0	848.4	848.7	849.1	848.8	848.0	847.1
140°	873.4	873.1	872.8	872.4	872.8	873.1	873.4	873.8	873.7	872.9	872.2
142.5°	896.7	896.2	895.7	895.2	895.7	896.2	896.7	897.2	897.2	896.6	896.0
145°	930.2	930.2	930.2	930.2	930.2	930.2	930.2	930.2	930.0	929.6	929.3
147.5°	958.7	957.9	957.0	956.2	957.0	957.9	958.7	959.5	959.8	959.4	959.0
150°	977.4	976.8	976.2	975.8	976.2	976.8	977.4	977.9	978.0	977.6	977.3
152.5°	993.8	993.0	992.2	991.3	992.2	993.0	993.8	994.7	994.7	994.1	993.4
155°	1016.4	1015.4	1014.2	1013.2	1014.2	1015.4	1016.4	1017.5	1017.6	1016.7	1015.8
157.5°	1035.8	1034.4	1033.0	1031.6	1033.0	1034.4	1035.8	1037.2	1037.4	1036.2	1035.2
160°	1047.1	1045.8	1044.6	1043.3	1044.6	1045.8	1047.1	1048.3	1048.4	1047.3	1046.3
162.5°	1057.7	1056.5	1055.5	1054.3	1055.5	1056.5	1057.7	1058.8	1058.7	1057.5	1056.3
165°	1071.5	1070.2	1068.9	1067.7	1068.9	1070.2	1071.5	1072.8	1072.7	1071.2	1069.8
167.5°	1081.7	1080.2	1078.7	1077.3	1078.7	1080.2	1081.7	1083.0	1083.0	1081.7	1080.2
170°	1087.5	1086.1	1084.6	1083.1	1084.6	1086.1	1087.5	1088.9	1088.9	1087.5	1086.1
172.5°	1091.2	1089.6	1088.0	1086.4	1088.0	1089.6	1091.2	1092.7	1092.8	1091.4	1090.0
175°	1095.6	1094.2	1092.7	1091.3	1092.7	1094.2	1095.6	1097.1	1097.1	1095.9	1094.6
177.5°	1097.1	1095.7	1094.2	1092.7	1094.2	1095.7	1097.1	1098.5	1098.7	1097.6	1096.3
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	423.5	425.7	427.8	429.7	432.8	434.1	436.1	436.9	439.1	442.5	445.2
5°	397.8	400.8	404.8	408.0	413.1	417.1	421.5	425.7	430.6	437.7	443.9
7.5°	375.9	378.9	383.7	389.7	395.3	401.0	407.0	412.7	419.7	429.8	439.8
10°	361.5	365.1	370.8	377.2	384.3	389.8	396.8	404.0	412.8	424.4	436.3
12.5°	349.0	351.7	358.3	364.4	372.4	379.4	386.3	394.8	404.7	417.0	431.5
15°	329.2	333.0	339.4	346.3	354.7	362.1	371.0	381.2	390.9	406.1	423.5
17.5°	309.2	315.0	321.8	329.5	335.7	345.9	355.6	366.1	378.1	394.1	413.4
20°	296.5	301.1	307.4	318.5	326.7	334.5	343.4	356.5	367.5	385.8	405.7
22.5°	285.7	289.0	296.1	305.3	314.9	323.8	333.0	345.4	359.1	376.3	397.9
25°	269.7	275.1	280.4	287.0	297.3	308.1	318.0	328.6	343.1	361.5	384.8
27.5°	254.1	258.9	264.2	272.3	280.1	290.2	300.6	312.7	328.2	347.7	371.5
30°	244.1	247.7	252.7	263.1	270.1	278.8	291.0	301.8	316.3	337.0	362.1
32.5°	233.7	238.4	243.9	251.8	260.6	268.8	279.9	291.6	306.4	326.8	352.5
35°	219.0	224.5	230.0	235.9	244.7	253.2	262.5	275.4	290.4	310.2	335.4
37.5°	205.5	209.9	214.3	221.7	229.9	238.1	246.8	259.5	273.6	295.0	318.1
40°	196.8	200.8	204.2	211.8	219.8	228.5	237.1	248.3	263.4	283.4	305.8
42.5°	187.4	191.0	195.7	201.9	210.5	217.8	226.4	237.0	251.3	271.6	291.2
45°	173.3	177.4	181.4	187.3	195.8	203.1	210.7	220.7	235.4	252.1	269.5
47.5°	158.5	162.7	167.3	173.0	180.4	187.8	195.3	204.2	217.6	234.0	245.8
50°	149.1	152.5	157.1	162.8	169.7	177.4	184.3	194.0	206.7	219.6	229.8
52.5°	139.4	142.5	147.7	153.7	160.0	166.8	174.1	182.4	193.9	206.0	214.2
55°	124.3	128.0	132.4	138.3	144.6	150.3	157.3	165.8	175.0	184.1	189.6
57.5°	110.1	113.2	116.9	122.9	128.4	135.2	141.5	148.1	156.6	163.5	167.1
60°	99.7	102.6	107.3	112.7	117.7	123.7	130.9	137.5	144.0	149.5	152.3
62.5°	90.0	93.3	97.4	102.3	107.9	113.5	119.8	125.4	131.1	135.8	137.8
65°	77.3	80.0	83.0	87.6	92.1	97.8	102.7	108.4	112.7	115.3	117.0
67.5°	65.8	67.5	69.8	72.9	77.4	82.3	87.1	91.6	95.1	96.9	98.4
70°	58.3	59.4	61.1	64.2	67.6	72.0	77.0	80.1	83.2	84.7	86.3
72.5°	50.9	52.3	53.9	56.3	59.1	62.3	65.9	69.8	71.5	73.3	74.2
75°	38.6	40.7	42.7	44.3	46.1	48.6	51.9	54.3	55.3	56.8	57.0
77.5°	29.1	29.6	31.1	32.9	34.6	36.4	38.4	40.6	41.1	41.8	42.4
80°	24.0	24.0	24.0	25.1	27.0	28.3	30.2	31.3	32.1	32.3	32.4
82.5°	19.2	19.2	19.1	19.3	20.0	20.7	22.4	23.7	24.4	24.2	23.8
85°	12.6	12.1	12.1	12.0	12.1	11.7	11.6	12.3	13.5	13.5	13.1
87.5°	9.2	8.9	8.6	8.0	7.3	6.8	5.9	5.6	5.3	5.5	5.1
90°	20.2	19.6	17.2	14.8	12.5	10.1	8.1	6.3	4.4	2.6	0.8
92.5°	22.0	20.9	19.1	17.3	15.5	13.8	13.1	13.6	14.1	14.6	15.2
95°	26.5	25.2	23.2	21.3	19.2	17.3	20.0	27.4	34.8	42.2	49.7
97.5°	27.6	26.2	39.2	52.3	65.3	78.3	86.4	89.8	93.1	96.4	99.8
100°	28.3	26.8	55.0	83.2	111.5	139.7	152.0	148.4	144.8	141.1	137.5
102.5°	49.1	53.6	84.4	115.2	146.0	176.8	190.9	188.3	185.7	183.1	180.5
105°	146.2	178.2	194.5	210.8	227.1	243.3	250.5	248.5	246.5	244.5	242.5
107.5°	303.2	326.7	324.1	321.6	318.9	316.4	314.3	312.7	311.1	309.6	307.9
110°	361.0	367.0	365.0	363.1	361.0	359.1	357.3	355.9	354.4	353.0	351.6



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	408.1	408.1	406.0	404.1	402.1	400.1	398.4	397.1	395.8	394.5	393.2
115°	469.0	467.1	465.5	463.8	462.2	460.6	459.3	458.2	457.1	456.0	454.9
117.5°	525.9	524.4	523.6	522.8	521.9	521.1	520.0	518.7	517.3	516.0	514.6
120°	563.0	561.5	561.0	560.4	559.9	559.4	558.2	556.6	555.0	553.3	551.7
122.5°	599.7	598.6	597.9	597.3	596.6	595.9	594.8	593.5	592.2	590.8	589.5
125°	651.4	651.0	650.3	649.5	648.9	648.2	647.0	645.6	644.2	642.7	641.2
127.5°	702.4	701.8	700.9	700.1	699.2	698.3	697.2	695.7	694.3	692.8	691.4
130°	733.1	732.4	731.6	731.0	730.3	729.5	728.5	727.0	725.5	724.1	722.7
132.5°	762.5	761.7	761.2	760.5	759.9	759.4	758.4	756.9	755.5	754.1	752.6
135°	807.0	806.5	805.8	805.0	804.3	803.6	802.7	801.6	800.5	799.4	798.3
137.5°	846.2	845.4	845.0	844.6	844.2	843.8	842.9	841.6	840.2	838.8	837.4
140°	871.5	870.7	870.3	869.7	869.1	868.6	867.8	866.7	865.6	864.5	863.4
142.5°	895.4	894.9	894.3	893.7	893.2	892.7	891.9	890.8	889.7	888.6	887.5
145°	928.9	928.5	928.1	927.8	927.5	927.1	926.3	925.0	923.7	922.5	921.2
147.5°	958.7	958.3	958.0	957.6	957.2	956.8	956.3	955.4	954.6	953.8	952.9
150°	976.9	976.6	976.2	975.8	975.4	975.1	974.6	974.1	973.5	973.1	972.5
152.5°	992.8	992.1	992.0	991.7	991.5	991.3	991.1	990.8	990.6	990.3	990.0
155°	1014.9	1014.0	1013.8	1013.6	1013.4	1013.3	1013.3	1013.7	1014.1	1014.4	1014.8
157.5°	1034.1	1033.0	1033.2	1033.4	1033.6	1033.7	1033.9	1033.9	1034.0	1034.0	1034.0
160°	1045.2	1044.1	1044.2	1044.5	1044.6	1044.8	1045.0	1045.2	1045.4	1045.5	1045.7
162.5°	1055.1	1053.9	1054.0	1054.2	1054.4	1054.6	1054.9	1055.4	1055.8	1056.3	1056.8
165°	1068.3	1066.9	1067.1	1067.2	1067.4	1067.6	1068.0	1068.5	1069.0	1069.6	1070.2
167.5°	1078.7	1077.3	1077.3	1077.3	1077.3	1077.3	1077.7	1078.4	1079.1	1079.9	1080.5
170°	1084.6	1083.1	1083.1	1083.1	1083.1	1083.1	1083.5	1084.3	1085.0	1085.7	1086.4
172.5°	1088.5	1087.0	1086.9	1086.8	1086.6	1086.5	1086.9	1087.7	1088.6	1089.5	1090.3
175°	1093.4	1092.1	1091.9	1091.8	1091.5	1091.4	1091.8	1092.7	1093.6	1094.5	1095.4
177.5°	1095.2	1094.1	1093.9	1093.8	1093.6	1093.5	1093.8	1094.5	1095.2	1095.9	1096.7
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	446.1	447.8	450.0	453.1	455.6	457.7	458.1	458.8	460.3	462.8	464.8
5°	449.1	453.4	460.4	467.2	474.7	480.8	486.5	490.5	494.2	502.2	508.7
7.5°	448.1	457.9	468.9	481.1	493.6	505.6	516.7	526.8	536.7	548.4	561.6
10°	447.5	458.9	473.8	489.5	506.8	523.7	540.1	552.8	567.5	580.9	597.8
12.5°	444.7	461.1	478.7	498.9	520.2	539.6	561.2	578.7	595.7	614.9	634.5
15°	440.8	460.8	483.2	510.0	542.3	565.8	587.9	618.5	639.4	660.2	688.4
17.5°	434.0	458.4	486.3	521.1	548.0	579.8	612.9	637.1	665.2	694.6	720.1
20°	428.5	456.8	488.2	522.4	556.8	591.1	623.2	652.1	681.2	715.2	736.1
22.5°	423.1	451.0	483.6	519.9	556.8	593.1	629.4	663.3	696.0	730.3	757.0
25°	411.4	444.7	480.0	517.1	553.5	593.4	636.7	674.5	714.9	750.3	775.6
27.5°	399.7	430.2	465.3	502.9	543.4	590.5	641.5	684.4	725.0	750.3	758.2
30°	389.0	421.3	453.6	491.8	535.7	588.2	642.4	691.6	724.8	735.9	727.7
32.5°	378.2	407.5	439.4	478.6	525.1	582.6	643.6	687.4	707.4	699.0	665.7
35°	359.2	385.6	416.5	455.7	509.2	579.5	638.6	668.2	663.3	615.8	553.1
37.5°	338.8	360.4	389.0	429.9	492.8	567.2	617.0	621.4	578.6	505.7	433.3
40°	322.7	342.1	371.5	414.3	480.0	555.1	595.3	577.6	511.4	430.2	369.8
42.5°	307.0	323.4	351.8	397.9	467.8	538.4	563.0	524.5	448.0	371.3	316.3
45°	280.5	296.0	324.4	371.7	443.0	506.8	503.5	436.7	360.1	298.4	252.8
47.5°	255.4	268.9	295.6	343.9	413.8	459.3	429.1	357.9	293.0	243.4	210.9
50°	237.7	250.9	277.5	325.2	390.4	423.5	380.5	311.9	252.4	211.4	185.6
52.5°	220.6	233.6	257.9	304.4	362.1	382.0	335.7	272.1	222.5	187.1	164.9
55°	196.8	206.7	228.5	273.0	316.1	320.7	273.7	220.5	179.7	155.0	139.8
57.5°	172.5	181.0	202.6	238.0	268.2	265.9	221.4	175.4	147.9	129.6	118.5
60°	156.7	165.1	184.1	214.4	237.3	229.3	188.4	151.4	127.8	114.4	105.6
62.5°	141.9	148.5	166.3	188.5	204.9	195.8	161.1	130.4	111.7	100.4	93.4
65°	120.6	126.0	140.1	151.8	160.9	152.1	123.3	102.0	88.5	80.6	75.8
67.5°	100.4	103.7	112.7	116.9	123.4	113.7	92.7	78.4	70.8	64.1	60.7
70°	87.6	90.0	94.8	98.2	99.9	90.0	74.4	64.0	57.6	52.8	50.7
72.5°	74.8	77.0	77.9	80.7	79.8	70.6	59.8	51.5	46.9	43.7	41.0
75°	57.2	58.1	57.2	56.0	53.6	47.1	39.7	35.5	32.1	30.6	29.6
77.5°	41.7	41.3	40.1	38.3	34.1	30.0	26.0	24.6	23.2	22.3	22.0
80°	32.1	31.3	30.2	27.3	23.7	20.9	20.0	19.0	18.4	17.4	17.3
82.5°	23.9	23.4	21.5	19.2	16.6	15.2	14.5	14.1	13.5	13.0	13.0
85°	12.7	12.1	10.0	8.7	8.4	8.0	7.8	7.8	7.0	6.8	6.8
87.5°	4.6	4.1	4.3	4.2	4.6	4.8	5.4	5.5	5.9	6.2	6.0
90°	2.6	4.4	6.3	8.1	10.1	12.5	14.8	17.2	19.6	20.2	21.0
92.5°	14.6	14.1	13.6	13.1	13.8	15.5	17.3	19.1	20.9	22.0	23.2
95°	42.2	34.8	27.4	20.0	17.3	19.2	21.3	23.2	25.2	26.5	27.7
97.5°	96.4	93.1	89.8	86.4	78.3	65.3	52.3	39.2	26.2	27.6	29.1
100°	141.1	144.8	148.4	152.0	139.7	111.5	83.2	55.0	26.8	28.3	29.8
102.5°	183.1	185.7	188.3	190.9	176.8	146.0	115.2	84.4	53.6	49.1	44.6
105°	244.5	246.5	248.5	250.5	243.3	227.1	210.8	194.5	178.2	146.2	114.2
107.5°	309.6	311.1	312.7	314.3	316.4	318.9	321.6	324.1	326.7	303.2	279.7
110°	353.0	354.4	355.9	357.3	359.1	361.0	363.1	365.0	367.0	361.0	355.1



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	394.5	395.8	397.1	398.4	400.1	402.1	404.1	406.0	408.1	408.1	408.2
115°	456.0	457.1	458.2	459.3	460.6	462.2	463.8	465.5	467.1	469.0	470.8
117.5°	516.0	517.3	518.7	520.0	521.1	521.9	522.8	523.6	524.4	525.9	527.3
120°	553.3	555.0	556.6	558.2	559.4	559.9	560.4	561.0	561.5	563.0	564.4
122.5°	590.8	592.2	593.5	594.8	595.9	596.6	597.3	597.9	598.6	599.7	600.6
125°	642.7	644.2	645.6	647.0	648.2	648.9	649.5	650.3	651.0	651.4	651.8
127.5°	692.8	694.3	695.7	697.2	698.3	699.2	700.1	700.9	701.8	702.4	703.0
130°	724.1	725.5	727.0	728.5	729.5	730.3	731.0	731.6	732.4	733.1	733.9
132.5°	754.1	755.5	756.9	758.4	759.4	759.9	760.5	761.2	761.7	762.5	763.1
135°	799.4	800.5	801.6	802.7	803.6	804.3	805.0	805.8	806.5	807.0	807.6
137.5°	838.8	840.2	841.6	842.9	843.8	844.2	844.6	845.0	845.4	846.2	847.1
140°	864.5	865.6	866.7	867.8	868.6	869.1	869.7	870.3	870.7	871.5	872.2
142.5°	888.6	889.7	890.8	891.9	892.7	893.2	893.7	894.3	894.9	895.4	896.0
145°	922.5	923.7	925.0	926.3	927.1	927.5	927.8	928.1	928.5	928.9	929.3
147.5°	953.8	954.6	955.4	956.3	956.8	957.2	957.6	958.0	958.3	958.7	959.0
150°	973.1	973.5	974.1	974.6	975.1	975.4	975.8	976.2	976.6	976.9	977.3
152.5°	990.3	990.6	990.8	991.1	991.3	991.5	991.7	992.0	992.1	992.8	993.4
155°	1014.4	1014.1	1013.7	1013.3	1013.3	1013.4	1013.6	1013.8	1014.0	1014.9	1015.8
157.5°	1034.0	1034.0	1033.9	1033.9	1033.7	1033.6	1033.4	1033.2	1033.0	1034.1	1035.2
160°	1045.5	1045.4	1045.2	1045.0	1044.8	1044.6	1044.5	1044.2	1044.1	1045.2	1046.3
162.5°	1056.3	1055.8	1055.4	1054.9	1054.6	1054.4	1054.2	1054.0	1053.9	1055.1	1056.3
165°	1069.6	1069.0	1068.5	1068.0	1067.6	1067.4	1067.2	1067.1	1066.9	1068.3	1069.8
167.5°	1079.9	1079.1	1078.4	1077.7	1077.3	1077.3	1077.3	1077.3	1077.3	1078.7	1080.2
170°	1085.7	1085.0	1084.3	1083.5	1083.1	1083.1	1083.1	1083.1	1083.1	1084.6	1086.1
172.5°	1089.5	1088.6	1087.7	1086.9	1086.5	1086.6	1086.8	1086.9	1087.0	1088.5	1090.0
175°	1094.5	1093.6	1092.7	1091.8	1091.4	1091.5	1091.8	1091.9	1092.1	1093.4	1094.6
177.5°	1095.9	1095.2	1094.5	1093.8	1093.5	1093.6	1093.8	1093.9	1094.1	1095.2	1096.3
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	468.1	468.1	468.6	470.9	471.2	473.2	472.6
5°	514.4	518.0	519.3	525.1	528.4	529.9	526.9
7.5°	571.0	581.2	586.0	592.1	597.3	598.9	594.8
10°	612.4	623.1	631.9	637.5	642.6	646.0	650.4
12.5°	652.3	665.4	673.9	681.7	687.0	691.3	692.0
15°	695.8	715.5	730.5	741.6	747.1	749.9	748.8
17.5°	739.6	757.9	768.6	779.8	787.4	787.8	788.1
20°	764.3	782.2	794.6	802.9	811.5	811.1	813.0
22.5°	780.9	795.0	804.5	810.5	813.4	812.0	812.4
25°	788.6	792.9	791.2	781.5	778.9	770.1	771.6
27.5°	748.7	729.0	708.5	682.2	661.5	644.9	645.7
30°	694.5	659.5	619.6	586.2	556.2	547.8	529.9
32.5°	618.6	566.2	519.5	488.3	462.6	455.6	440.0
35°	490.1	439.1	391.1	362.2	350.8	334.8	334.7
37.5°	380.9	336.1	310.7	289.0	277.7	268.0	267.1
40°	320.4	285.5	266.3	250.7	239.5	232.3	230.6
42.5°	278.2	250.0	232.0	222.3	213.7	209.9	207.2
45°	227.1	208.1	195.7	186.9	183.0	180.1	178.6
47.5°	190.0	177.3	168.8	162.9	159.7	156.7	157.5
50°	169.8	159.4	153.1	147.6	145.1	143.0	143.2
52.5°	153.5	144.1	139.1	135.1	132.1	130.5	129.9
55°	130.3	124.4	119.3	116.4	114.7	112.7	112.1
57.5°	111.1	106.6	102.4	99.2	98.7	96.8	97.0
60°	98.4	94.6	91.2	89.4	88.1	86.4	87.0
62.5°	87.9	84.7	81.6	80.2	78.8	77.6	77.9
65°	72.0	69.0	67.0	66.3	65.7	65.1	64.6
67.5°	57.4	55.5	54.3	52.7	51.5	51.4	50.8
70°	48.3	45.7	43.7	41.6	41.0	40.8	41.0
72.5°	38.6	37.1	36.5	35.5	35.4	34.9	35.2
75°	29.0	28.5	28.1	27.3	27.3	27.3	27.3
77.5°	21.4	21.1	20.9	20.7	20.5	20.2	20.2
80°	16.7	16.6	16.1	16.1	16.0	16.1	16.0
82.5°	12.6	12.6	12.2	12.2	12.0	11.9	12.0
85°	6.4	6.3	6.7	6.3	6.4	6.1	6.4
87.5°	6.2	6.3	6.3	6.4	6.3	6.6	6.4
90°	21.7	22.4	23.0	23.3	23.7	24.1	24.4
92.5°	24.3	25.4	26.2	26.3	26.6	26.8	27.0
95°	29.0	30.3	30.9	30.9	30.9	30.9	30.9
97.5°	30.6	32.0	32.8	33.0	33.2	33.3	33.5
100°	31.2	32.6	33.4	33.7	33.8	34.0	34.2
102.5°	40.1	35.6	33.5	33.8	34.2	34.5	34.8
105°	82.2	50.2	34.3	34.7	35.1	35.5	35.8
107.5°	256.2	232.8	209.0	184.8	160.7	136.6	112.4
110°	349.1	343.2	327.3	301.3	275.5	249.6	223.8



TEST NUMBER: P332258-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	408.4	408.5	405.8	400.3	394.8	389.4	383.9
115°	472.5	474.3	475.6	476.3	477.0	477.8	478.5
117.5°	528.7	530.2	531.0	531.2	531.2	531.4	531.6
120°	565.8	567.3	568.0	568.0	568.0	568.0	568.0
122.5°	601.7	602.7	603.2	603.4	603.6	603.6	603.8
125°	652.1	652.5	652.8	653.2	653.5	654.0	654.3
127.5°	703.5	704.1	704.3	703.8	703.5	703.1	702.8
130°	734.6	735.3	735.5	735.2	734.7	734.4	734.0
132.5°	763.9	764.6	764.7	764.2	763.7	763.2	762.7
135°	808.1	808.6	808.6	808.1	807.6	807.0	806.5
137.5°	848.0	848.8	849.1	848.7	848.4	848.0	847.7
140°	872.9	873.7	873.8	873.4	873.1	872.8	872.4
142.5°	896.6	897.2	897.2	896.7	896.2	895.7	895.2
145°	929.6	930.0	930.2	930.2	930.2	930.2	930.2
147.5°	959.4	959.8	959.5	958.7	957.9	957.0	956.2
150°	977.6	978.0	977.9	977.4	976.8	976.2	975.8
152.5°	994.1	994.7	994.7	993.8	993.0	992.2	991.3
155°	1016.7	1017.6	1017.5	1016.4	1015.4	1014.2	1013.2
157.5°	1036.2	1037.4	1037.2	1035.8	1034.4	1033.0	1031.6
160°	1047.3	1048.4	1048.3	1047.1	1045.8	1044.6	1043.3
162.5°	1057.5	1058.7	1058.8	1057.7	1056.5	1055.5	1054.3
165°	1071.2	1072.7	1072.8	1071.5	1070.2	1068.9	1067.7
167.5°	1081.7	1083.0	1083.0	1081.7	1080.2	1078.7	1077.3
170°	1087.5	1088.9	1088.9	1087.5	1086.1	1084.6	1083.1
172.5°	1091.4	1092.8	1092.7	1091.2	1089.6	1088.0	1086.4
175°	1095.9	1097.1	1097.1	1095.6	1094.2	1092.7	1091.3
177.5°	1097.6	1098.7	1098.5	1097.1	1095.7	1094.2	1092.7
180°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4

(END OF REPORT)