

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332260-930

Luminaire Tested: **S123RDIP-S340D1025U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332260-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D1025U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4132.5 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30	23
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26	20
3	77	69	62	56	69	62	56	51	48	44	41	36	34	32	25	23	22	17
4	71	61	53	48	63	55	48	44	43	39	35	32	30	27	22	21	19	15
5	65	54	47	41	58	49	42	37	39	34	30	29	26	24	20	18	17	13
6	60	49	41	35	53	44	37	32	35	30	27	26	23	21	18	17	15	12
7	55	44	36	31	49	40	33	28	32	27	23	24	21	18	17	15	13	11
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10
9	48	36	29	24	43	33	27	22	26	22	18	20	17	15	14	12	11	9
10	44	33	26	22	40	30	24	20	24	20	17	19	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4776	4776	4776	4776
5°	5693	4796	4224	4796
10°	7109	4769	3816	4769
15°	8344	4719	3480	4719
20°	9313	4647	3194	4647
25°	9164	4570	3018	4570
30°	6586	4501	2838	4501
35°	4398	4407	2720	4407
40°	3240	4297	2599	4297
45°	2719	4102	2481	4102
50°	2398	3848	2316	3848
55°	2104	3558	2089	3558
60°	1873	3279	1914	3279
65°	1645	2980	1780	2980
70°	1290	2716	1627	2716
75°	1135	2371	1485	2371
80°	992	2008	1463	2008
85°	790	1618	1556	1618



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	1.1
10°-20°	136.3	3.3
20°-30°	214.2	5.2
30°-40°	223.4	5.4
40°-50°	191.2	4.6
50°-60°	145.7	3.5
60°-70°	93.4	2.3
70°-80°	44.9	1.1
80°-90°	15.0	0.4
90°-100°	223.7	5.4
100°-110°	633.5	15.3
110°-120°	623.2	15.1
120°-130°	497.1	12.0
130°-140°	391.9	9.5
140°-150°	292.5	7.1
150°-160°	203.9	4.9
160°-170°	119.8	2.9
170°-180°	39.0	0.9
0°-30°	394.1	9.5
0°-40°	617.6	14.9
0°-60°	954.5	23.1
0°-90°	1107.9	26.8
90°-120°	1480.5	35.8
90°-150°	2662.0	64.4
90°-180°	3025.0	73.2
0°-180°	4132.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	527	444	391	444	527	54
15°	749	424	312	424	749	212
25°	772	385	254	385	772	332
35°	335	335	207	335	335	219
45°	179	270	163	270	179	140
55°	112	190	111	190	112	101
65°	65	117	70	117	65	64
75°	27	57	36	57	27	29
85°	6	13	13	13	6	8
90°	24	2	24	2	24	13
95°	94	28	94	28	94	170
105°	1035	94	1035	94	1035	1021
115°	1259	167	1259	167	1259	1223
125°	993	232	993	232	993	900
135°	805	272	805	272	805	624
145°	629	310	629	310	629	400
155°	522	352	522	352	522	243
165°	455	385	455	385	455	130
175°	409	401	409	401	409	40
180°	402	402	402	402	402	



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	472.6	473.2	471.2	470.9	468.6	468.1	468.1	464.8	462.8	460.3	458.8
5°	526.9	529.9	528.4	525.1	519.3	518.0	514.4	508.7	502.2	494.2	490.5
7.5°	594.8	598.9	597.3	592.1	586.0	581.2	571.0	561.6	548.4	536.7	526.8
10°	650.4	646.0	642.6	637.5	631.9	623.1	612.4	597.8	580.9	567.5	552.8
12.5°	692.0	691.3	687.0	681.7	673.9	665.4	652.3	634.5	614.9	595.7	578.7
15°	748.8	749.9	747.1	741.6	730.5	715.5	695.8	688.4	660.2	639.4	618.5
17.5°	788.1	787.8	787.4	779.8	768.6	757.9	739.6	720.1	694.6	665.2	637.1
20°	813.0	811.1	811.5	802.9	794.6	782.2	764.3	736.1	715.2	681.2	652.1
22.5°	812.4	812.0	813.4	810.5	804.5	795.0	780.9	757.0	730.3	696.0	663.3
25°	771.6	770.1	778.9	781.5	791.2	792.9	788.6	775.6	750.3	714.9	674.5
27.5°	645.7	644.9	661.5	682.2	708.5	729.0	748.7	758.2	750.3	725.0	684.4
30°	529.9	547.8	556.2	586.2	619.6	659.5	694.5	727.7	735.9	724.8	691.6
32.5°	440.0	455.6	462.6	488.3	519.5	566.2	618.6	665.7	699.0	707.4	687.4
35°	334.7	334.8	350.8	362.2	391.1	439.1	490.1	553.1	615.8	663.3	668.2
37.5°	267.1	268.0	277.7	289.0	310.7	336.1	380.9	433.3	505.7	578.6	621.4
40°	230.6	232.3	239.5	250.7	266.3	285.5	320.4	369.8	430.2	511.4	577.6
42.5°	207.2	209.9	213.7	222.3	232.0	250.0	278.2	316.3	371.3	448.0	524.5
45°	178.6	180.1	183.0	186.9	195.7	208.1	227.1	252.8	298.4	360.1	436.7
47.5°	157.5	156.7	159.7	162.9	168.8	177.3	190.0	210.9	243.4	293.0	357.9
50°	143.2	143.0	145.1	147.6	153.1	159.4	169.8	185.6	211.4	252.4	311.9
52.5°	129.9	130.5	132.1	135.1	139.1	144.1	153.5	164.9	187.1	222.5	272.1
55°	112.1	112.7	114.7	116.4	119.3	124.4	130.3	139.8	155.0	179.7	220.5
57.5°	97.0	96.8	98.7	99.2	102.4	106.6	111.1	118.5	129.6	147.9	175.4
60°	87.0	86.4	88.1	89.4	91.2	94.6	98.4	105.6	114.4	127.8	151.4
62.5°	77.9	77.6	78.8	80.2	81.6	84.7	87.9	93.4	100.4	111.7	130.4
65°	64.6	65.1	65.7	66.3	67.0	69.0	72.0	75.8	80.6	88.5	102.0
67.5°	50.8	51.4	51.5	52.7	54.3	55.5	57.4	60.7	64.1	70.8	78.4
70°	41.0	40.8	41.0	41.6	43.7	45.7	48.3	50.7	52.8	57.6	64.0
72.5°	35.2	34.9	35.4	35.5	36.5	37.1	38.6	41.0	43.7	46.9	51.5
75°	27.3	27.3	27.3	27.3	28.1	28.5	29.0	29.6	30.6	32.1	35.5
77.5°	20.2	20.2	20.5	20.7	20.9	21.1	21.4	22.0	22.3	23.2	24.6
80°	16.0	16.1	16.0	16.1	16.1	16.6	16.7	17.3	17.4	18.4	19.0
82.5°	12.0	11.9	12.0	12.2	12.2	12.6	12.6	13.0	13.0	13.5	14.1
85°	6.4	6.1	6.4	6.3	6.7	6.3	6.4	6.8	6.8	7.0	7.8
87.5°	6.3	6.7	6.3	6.2	6.4	6.2	6.0	5.9	6.0	6.0	5.7
90°	23.6	24.4	23.6	22.7	23.6	22.0	21.2	20.4	19.6	20.4	17.9
92.5°	39.2	40.7	39.9	42.3	43.8	48.0	54.4	68.5	94.4	125.1	137.7
95°	94.4	97.7	103.4	110.7	126.1	155.5	198.6	292.9	391.4	482.6	429.7
97.5°	257.0	264.0	286.0	322.6	382.6	480.0	585.0	730.3	800.1	747.9	547.6
100°	510.3	509.5	541.2	600.6	682.8	798.3	893.6	959.5	931.0	770.7	520.8
102.5°	748.5	767.3	793.8	840.8	904.8	978.0	1033.6	1035.7	937.5	728.4	481.8
105°	1035.2	1039.3	1065.3	1096.2	1133.7	1154.8	1139.4	1057.9	887.9	654.3	433.7
107.5°	1200.2	1207.7	1216.5	1226.9	1226.3	1197.3	1126.0	993.8	801.0	588.9	403.2
110°	1268.0	1269.6	1271.2	1264.7	1241.9	1184.9	1082.4	932.6	746.2	551.8	391.4



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1281.6	1281.2	1275.0	1254.9	1213.2	1140.0	1025.1	872.0	698.7	527.0	384.9
115°	1259.0	1254.9	1238.6	1202.8	1141.7	1053.0	933.4	791.8	641.3	500.5	382.5
117.5°	1187.0	1181.5	1158.1	1117.0	1053.4	963.4	856.0	733.8	606.6	484.9	383.9
120°	1127.2	1122.3	1102.7	1057.1	992.9	910.7	813.0	703.1	588.4	477.7	386.5
122.5°	1071.1	1064.9	1043.5	1002.5	945.3	869.0	778.5	679.1	573.4	473.1	391.1
125°	992.9	987.2	966.8	931.0	878.9	813.8	735.7	647.0	554.2	467.2	397.9
127.5°	928.4	923.2	904.8	874.2	827.8	768.6	698.1	619.0	537.3	464.2	405.8
130°	891.9	885.4	868.4	839.0	795.9	740.5	674.7	601.4	528.2	462.3	411.0
132.5°	856.1	851.6	836.4	807.1	766.6	713.9	652.5	585.1	519.7	461.6	414.9
135°	804.9	799.2	784.5	760.1	720.2	673.8	620.9	563.1	508.7	460.6	420.8
137.5°	750.6	746.9	734.6	709.8	676.3	636.1	590.5	543.2	499.0	458.9	424.6
140°	712.9	713.7	700.7	677.9	647.0	612.0	572.9	531.4	493.2	458.2	427.2
142.5°	677.8	678.6	666.8	646.7	620.3	589.9	556.0	520.3	488.0	456.9	429.2
145°	629.1	627.5	620.9	603.8	583.5	559.9	533.9	507.0	480.9	454.9	430.5
147.5°	589.1	588.4	582.2	570.6	555.2	538.4	517.4	496.1	474.1	451.8	430.5
150°	565.6	565.6	560.7	551.8	539.6	524.1	507.0	488.3	469.5	449.2	430.5
152.5°	546.1	546.1	543.2	534.8	525.2	512.4	497.3	481.1	464.4	446.0	428.5
155°	521.6	520.8	519.2	512.7	505.4	495.6	483.4	470.3	456.6	440.3	426.4
157.5°	499.4	499.5	498.2	493.3	487.0	479.3	469.9	459.0	447.8	435.2	423.7
160°	485.0	485.8	485.8	480.9	475.2	469.5	461.5	452.5	441.9	431.3	422.4
162.5°	472.0	472.8	472.8	468.6	464.9	459.8	452.3	444.7	436.0	427.4	419.8
165°	454.9	454.9	455.8	452.5	449.2	445.2	439.4	434.6	428.0	421.6	415.9
167.5°	438.6	438.6	439.4	437.2	435.7	432.8	429.5	425.7	420.4	415.7	412.0
170°	428.8	428.8	429.7	428.0	427.2	425.6	422.4	420.0	415.9	411.8	409.4
172.5°	419.8	420.4	421.9	420.3	420.1	419.1	416.5	414.7	411.3	408.5	407.4
175°	409.4	410.2	411.0	410.2	410.2	410.2	408.5	407.7	406.1	404.5	404.5
177.5°	403.3	403.3	404.6	404.0	404.6	404.6	404.0	403.3	402.7	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	458.1	457.7	455.6	453.1	450.0	447.8	446.1	445.2	442.5	439.1	436.9
5°	486.5	480.8	474.7	467.2	460.4	453.4	449.1	443.9	437.7	430.6	425.7
7.5°	516.7	505.6	493.6	481.1	468.9	457.9	448.1	439.8	429.8	419.7	412.7
10°	540.1	523.7	506.8	489.5	473.8	458.9	447.5	436.3	424.4	412.8	404.0
12.5°	561.2	539.6	520.2	498.9	478.7	461.1	444.7	431.5	417.0	404.7	394.8
15°	587.9	565.8	542.3	510.0	483.2	460.8	440.8	423.5	406.1	390.9	381.2
17.5°	612.9	579.8	548.0	521.1	486.3	458.4	434.0	413.4	394.1	378.1	366.1
20°	623.2	591.1	556.8	522.4	488.2	456.8	428.5	405.7	385.8	367.5	356.5
22.5°	629.4	593.1	556.8	519.9	483.6	451.0	423.1	397.9	376.3	359.1	345.4
25°	636.7	593.4	553.5	517.1	480.0	444.7	411.4	384.8	361.5	343.1	328.6
27.5°	641.5	590.5	543.4	502.9	465.3	430.2	399.7	371.5	347.7	328.2	312.7
30°	642.4	588.2	535.7	491.8	453.6	421.3	389.0	362.1	337.0	316.3	301.8
32.5°	643.6	582.6	525.1	478.6	439.4	407.5	378.2	352.5	326.8	306.4	291.6
35°	638.6	579.5	509.2	455.7	416.5	385.6	359.2	335.4	310.2	290.4	275.4
37.5°	617.0	567.2	492.8	429.9	389.0	360.4	338.8	318.1	295.0	273.6	259.5
40°	595.3	555.1	480.0	414.3	371.5	342.1	322.7	305.8	283.4	263.4	248.3
42.5°	563.0	538.4	467.8	397.9	351.8	323.4	307.0	291.2	271.6	251.3	237.0
45°	503.5	506.8	443.0	371.7	324.4	296.0	280.5	269.5	252.1	235.4	220.7
47.5°	429.1	459.3	413.8	343.9	295.6	268.9	255.4	245.8	234.0	217.6	204.2
50°	380.5	423.5	390.4	325.2	277.5	250.9	237.7	229.8	219.6	206.7	194.0
52.5°	335.7	382.0	362.1	304.4	257.9	233.6	220.6	214.2	206.0	193.9	182.4
55°	273.7	320.7	316.1	273.0	228.5	206.7	196.8	189.6	184.1	175.0	165.8
57.5°	221.4	265.9	268.2	238.0	202.6	181.0	172.5	167.1	163.5	156.6	148.1
60°	188.4	229.3	237.3	214.4	184.1	165.1	156.7	152.3	149.5	144.0	137.5
62.5°	161.1	195.8	204.9	188.5	166.3	148.5	141.9	137.8	135.8	131.1	125.4
65°	123.3	152.1	160.9	151.8	140.1	126.0	120.6	117.0	115.3	112.7	108.4
67.5°	92.7	113.7	123.4	116.9	112.7	103.7	100.4	98.4	96.9	95.1	91.6
70°	74.4	90.0	99.9	98.2	94.8	90.0	87.6	86.3	84.7	83.2	80.1
72.5°	59.8	70.6	79.8	80.7	77.9	77.0	74.8	74.2	73.3	71.5	69.8
75°	39.7	47.1	53.6	56.0	57.2	58.1	57.2	57.0	56.8	55.3	54.3
77.5°	26.0	30.0	34.1	38.3	40.1	41.3	41.7	42.4	41.8	41.1	40.6
80°	20.0	20.9	23.7	27.3	30.2	31.3	32.1	32.4	32.3	32.1	31.3
82.5°	14.5	15.2	16.6	19.2	21.5	23.4	23.9	23.8	24.2	24.4	23.7
85°	7.8	8.0	8.4	8.7	10.0	12.1	12.7	13.1	13.5	13.5	12.3
87.5°	5.5	4.9	4.7	4.4	4.5	4.2	4.7	5.2	5.6	5.4	5.9
90°	15.5	13.0	10.6	9.0	7.3	4.9	3.3	1.6	3.3	4.9	7.3
92.5°	103.4	68.3	47.0	35.0	28.1	21.9	15.0	10.1	15.0	21.9	28.1
95°	296.2	175.0	105.8	74.0	52.9	39.1	30.1	27.6	30.1	39.1	52.9
97.5°	325.1	188.3	122.2	87.9	67.0	55.0	48.0	47.2	48.0	55.0	67.0
100°	306.8	186.4	129.4	97.7	78.1	66.8	61.1	60.3	61.1	66.8	78.1
102.5°	291.1	189.0	137.9	108.8	91.2	80.4	75.3	73.9	75.3	80.4	91.2
105°	280.0	196.2	152.2	126.9	111.5	101.7	96.9	94.4	96.9	101.7	111.5
107.5°	279.2	209.5	170.9	147.5	133.0	123.4	118.6	116.2	118.6	123.4	133.0
110°	282.4	220.5	183.9	161.1	147.3	138.4	134.3	131.8	134.3	138.4	147.3



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	288.9	231.6	197.6	175.5	161.6	152.7	148.6	146.2	148.6	152.7	161.6
115°	299.5	249.8	218.9	197.0	183.1	175.0	170.1	166.8	170.1	175.0	183.1
117.5°	313.5	269.2	238.6	218.3	202.8	195.3	191.3	187.5	191.3	195.3	202.8
120°	323.9	281.6	252.3	232.0	216.5	208.3	204.2	201.8	204.2	208.3	216.5
122.5°	333.7	294.6	266.0	244.3	229.5	220.7	216.6	214.2	216.6	220.7	229.5
125°	349.1	313.3	284.9	262.9	247.4	238.5	233.6	232.0	233.6	238.5	247.4
127.5°	361.8	329.6	302.1	280.1	263.0	253.9	247.9	245.5	247.9	253.9	263.0
130°	370.3	339.3	312.5	290.5	273.5	263.7	256.3	253.9	256.3	263.7	273.5
132.5°	378.1	347.8	321.6	300.3	283.2	271.5	263.5	260.4	263.5	271.5	283.2
135°	388.2	360.5	335.3	313.3	296.2	284.1	275.1	271.8	275.1	284.1	296.2
137.5°	395.7	369.3	345.0	324.7	307.8	294.7	286.0	282.6	286.0	294.7	307.8
140°	399.6	375.2	351.6	331.3	315.0	301.9	293.8	289.8	293.8	301.9	315.0
142.5°	403.5	379.8	356.8	337.7	321.5	309.7	300.9	297.5	300.9	309.7	321.5
145°	407.7	385.7	364.6	345.8	332.1	319.8	312.5	310.1	312.5	319.8	332.1
147.5°	410.3	390.6	371.3	355.3	341.9	331.4	324.2	322.8	324.2	331.4	341.9
150°	411.0	393.9	375.2	360.5	349.1	338.5	332.1	331.3	332.1	338.5	349.1
152.5°	412.3	395.8	379.8	365.7	355.6	346.3	339.8	339.7	339.8	346.3	355.6
155°	412.6	399.6	385.7	374.4	365.4	357.3	352.4	352.4	352.4	357.3	365.4
157.5°	413.4	401.7	390.6	381.8	374.2	367.0	363.1	362.5	363.1	367.0	374.2
160°	413.4	403.7	393.9	385.7	380.0	373.6	370.3	370.3	370.3	373.6	380.0
162.5°	412.8	404.3	395.8	389.0	383.9	378.8	376.2	376.2	376.2	378.8	383.9
165°	411.0	405.3	398.8	393.1	389.8	385.7	384.1	384.9	384.1	385.7	389.8
167.5°	409.7	405.1	400.4	396.8	394.5	391.4	390.6	391.6	390.6	391.4	394.5
170°	407.7	404.5	400.4	398.8	397.1	394.7	393.9	395.5	393.9	394.7	397.1
172.5°	407.1	404.5	401.0	400.1	399.1	397.3	397.1	398.1	397.1	397.3	399.1
175°	405.3	403.7	402.0	401.2	401.2	399.6	400.4	401.2	400.4	399.6	401.2
177.5°	404.0	402.7	402.0	402.0	402.0	401.4	402.0	402.7	402.0	401.4	402.0
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	436.1	434.1	432.8	429.7	427.8	425.7	423.5	424.9	424.7	424.6	424.6
5°	421.5	417.1	413.1	408.0	404.8	400.8	397.8	397.4	398.1	395.5	394.0
7.5°	407.0	401.0	395.3	389.7	383.7	378.9	375.9	374.5	372.6	371.0	369.2
10°	396.8	389.8	384.3	377.2	370.8	365.1	361.5	359.0	357.7	356.4	353.8
12.5°	386.3	379.4	372.4	364.4	358.3	351.7	349.0	346.3	343.7	342.2	338.8
15°	371.0	362.1	354.7	346.3	339.4	333.0	329.2	323.7	322.9	321.0	317.6
17.5°	355.6	345.9	335.7	329.5	321.8	315.0	309.2	307.4	302.0	299.9	296.9
20°	343.4	334.5	326.7	318.5	307.4	301.1	296.5	294.1	289.7	287.0	285.1
22.5°	333.0	323.8	314.9	305.3	296.1	289.0	285.7	281.8	279.5	275.7	273.7
25°	318.0	308.1	297.3	287.0	280.4	275.1	269.7	266.3	262.9	261.1	257.4
27.5°	300.6	290.2	280.1	272.3	264.2	258.9	254.1	251.1	247.0	244.1	242.0
30°	291.0	278.8	270.1	263.1	252.7	247.7	244.1	240.3	237.3	234.2	232.1
32.5°	279.9	268.8	260.6	251.8	243.9	238.4	233.7	230.4	227.8	224.9	222.8
35°	262.5	253.2	244.7	235.9	230.0	224.5	219.0	216.1	213.7	211.0	209.1
37.5°	246.8	238.1	229.9	221.7	214.3	209.9	205.5	203.3	199.9	198.1	196.2
40°	237.1	228.5	219.8	211.8	204.2	200.8	196.8	193.6	190.5	189.1	187.1
42.5°	226.4	217.8	210.5	201.9	195.7	191.0	187.4	183.8	181.6	179.6	178.5
45°	210.7	203.1	195.8	187.3	181.4	177.4	173.3	170.0	168.0	166.6	164.5
47.5°	195.3	187.8	180.4	173.0	167.3	162.7	158.5	156.3	153.5	151.9	150.5
50°	184.3	177.4	169.7	162.8	157.1	152.5	149.1	146.3	143.8	141.7	140.7
52.5°	174.1	166.8	160.0	153.7	147.7	142.5	139.4	136.4	134.5	132.2	131.0
55°	157.3	150.3	144.6	138.3	132.4	128.0	124.3	121.6	119.7	117.0	115.5
57.5°	141.5	135.2	128.4	122.9	116.9	113.2	110.1	106.5	104.1	102.1	100.5
60°	130.9	123.7	117.7	112.7	107.3	102.6	99.7	96.9	94.4	92.3	91.0
62.5°	119.8	113.5	107.9	102.3	97.4	93.3	90.0	87.6	85.4	84.1	82.8
65°	102.7	97.8	92.1	87.6	83.0	80.0	77.3	75.3	73.7	72.7	71.6
67.5°	87.1	82.3	77.4	72.9	69.8	67.5	65.8	64.0	63.2	62.0	61.2
70°	77.0	72.0	67.6	64.2	61.1	59.4	58.3	57.0	56.3	54.7	54.0
72.5°	65.9	62.3	59.1	56.3	53.9	52.3	50.9	49.2	48.0	46.3	45.6
75°	51.9	48.6	46.1	44.3	42.7	40.7	38.6	36.9	36.3	35.7	35.5
77.5°	38.4	36.4	34.6	32.9	31.1	29.6	29.1	28.7	28.6	28.3	28.3
80°	30.2	28.3	27.0	25.1	24.0	24.0	24.0	23.6	23.7	23.7	23.7
82.5°	22.4	20.7	20.0	19.3	19.1	19.2	19.2	19.3	19.2	19.5	19.3
85°	11.6	11.7	12.1	12.0	12.1	12.1	12.6	12.3	12.6	12.1	12.6
87.5°	6.0	6.8	7.5	8.1	8.7	9.0	9.0	9.2	9.5	9.7	10.0
90°	9.0	10.6	13.0	15.5	17.9	20.4	19.6	20.4	21.2	22.0	23.6
92.5°	35.0	47.0	68.3	103.4	137.7	125.1	94.4	68.5	54.4	48.0	43.8
95°	74.0	105.8	175.0	296.2	429.7	482.6	391.4	292.9	198.6	155.5	126.1
97.5°	87.9	122.2	188.3	325.1	547.6	747.9	800.1	730.3	585.0	480.0	382.6
100°	97.7	129.4	186.4	306.8	520.8	770.7	931.0	959.5	893.6	798.3	682.8
102.5°	108.8	137.9	189.0	291.1	481.8	728.4	937.5	1035.7	1033.6	978.0	904.8
105°	126.9	152.2	196.2	280.0	433.7	654.3	887.9	1057.9	1139.4	1154.8	1133.7
107.5°	147.5	170.9	209.5	279.2	403.2	588.9	801.0	993.8	1126.0	1197.3	1226.3
110°	161.1	183.9	220.5	282.4	391.4	551.8	746.2	932.6	1082.4	1184.9	1241.9



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	175.5	197.6	231.6	288.9	384.9	527.0	698.7	872.0	1025.1	1140.0	1213.2
115°	197.0	218.9	249.8	299.5	382.5	500.5	641.3	791.8	933.4	1053.0	1141.7
117.5°	218.3	238.6	269.2	313.5	383.9	484.9	606.6	733.8	856.0	963.4	1053.4
120°	232.0	252.3	281.6	323.9	386.5	477.7	588.4	703.1	813.0	910.7	992.9
122.5°	244.3	266.0	294.6	333.7	391.1	473.1	573.4	679.1	778.5	869.0	945.3
125°	262.9	284.9	313.3	349.1	397.9	467.2	554.2	647.0	735.7	813.8	878.9
127.5°	280.1	302.1	329.6	361.8	405.8	464.2	537.3	619.0	698.1	768.6	827.8
130°	290.5	312.5	339.3	370.3	411.0	462.3	528.2	601.4	674.7	740.5	795.9
132.5°	300.3	321.6	347.8	378.1	414.9	461.6	519.7	585.1	652.5	713.9	766.6
135°	313.3	335.3	360.5	388.2	420.8	460.6	508.7	563.1	620.9	673.8	720.2
137.5°	324.7	345.0	369.3	395.7	424.6	458.9	499.0	543.2	590.5	636.1	676.3
140°	331.3	351.6	375.2	399.6	427.2	458.2	493.2	531.4	572.9	612.0	647.0
142.5°	337.7	356.8	379.8	403.5	429.2	456.9	488.0	520.3	556.0	589.9	620.3
145°	345.8	364.6	385.7	407.7	430.5	454.9	480.9	507.0	533.9	559.9	583.5
147.5°	355.3	371.3	390.6	410.3	430.5	451.8	474.1	496.1	517.4	538.4	555.2
150°	360.5	375.2	393.9	411.0	430.5	449.2	469.5	488.3	507.0	524.1	539.6
152.5°	365.7	379.8	395.8	412.3	428.5	446.0	464.4	481.1	497.3	512.4	525.2
155°	374.4	385.7	399.6	412.6	426.4	440.3	456.6	470.3	483.4	495.6	505.4
157.5°	381.8	390.6	401.7	413.4	423.7	435.2	447.8	459.0	469.9	479.3	487.0
160°	385.7	393.9	403.7	413.4	422.4	431.3	441.9	452.5	461.5	469.5	475.2
162.5°	389.0	395.8	404.3	412.8	419.8	427.4	436.0	444.7	452.3	459.8	464.9
165°	393.1	398.8	405.3	411.0	415.9	421.6	428.0	434.6	439.4	445.2	449.2
167.5°	396.8	400.4	405.1	409.7	412.0	415.7	420.4	425.7	429.5	432.8	435.7
170°	398.8	400.4	404.5	407.7	409.4	411.8	415.9	420.0	422.4	425.6	427.2
172.5°	400.1	401.0	404.5	407.1	407.4	408.5	411.3	414.7	416.5	419.1	420.1
175°	401.2	402.0	403.7	405.3	404.5	404.5	406.1	407.7	408.5	410.2	410.2
177.5°	402.0	402.0	402.7	404.0	402.7	402.0	402.7	403.3	404.0	404.6	404.6
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	422.7	422.6	422.7	422.2	422.7	422.6	422.7	424.6	424.6	424.7	424.9
5°	393.4	393.2	392.6	390.9	392.6	393.2	393.4	394.0	395.5	398.1	397.4
7.5°	367.7	367.5	365.8	365.8	365.8	367.5	367.7	369.2	371.0	372.6	374.5
10°	352.5	352.7	350.4	349.1	350.4	352.7	352.5	353.8	356.4	357.7	359.0
12.5°	337.8	337.0	335.1	333.6	335.1	337.0	337.8	338.8	342.2	343.7	346.3
15°	318.4	316.4	311.9	312.3	311.9	316.4	318.4	317.6	321.0	322.9	323.7
17.5°	295.5	294.1	294.0	291.3	294.0	294.1	295.5	296.9	299.9	302.0	307.4
20°	282.1	281.1	281.5	278.8	281.5	281.1	282.1	285.1	287.0	289.7	294.1
22.5°	271.6	270.6	269.0	268.2	269.0	270.6	271.6	273.7	275.7	279.5	281.8
25°	256.2	254.7	253.2	254.1	253.2	254.7	256.2	257.4	261.1	262.9	266.3
27.5°	240.9	239.8	238.2	238.1	238.2	239.8	240.9	242.0	244.1	247.0	251.1
30°	231.1	230.0	229.3	228.3	229.3	230.0	231.1	232.1	234.2	237.3	240.3
32.5°	221.3	221.0	219.7	219.5	219.7	221.0	221.3	222.8	224.9	227.8	230.4
35°	208.4	207.2	206.8	207.0	206.8	207.2	208.4	209.1	211.0	213.7	216.1
37.5°	196.1	194.6	193.9	193.2	193.9	194.6	196.1	196.2	198.1	199.9	203.3
40°	187.3	185.8	185.4	185.0	185.4	185.8	187.3	187.1	189.1	190.5	193.6
42.5°	177.4	176.8	176.6	175.9	176.6	176.8	177.4	178.5	179.6	181.6	183.8
45°	164.0	163.7	162.6	163.0	162.6	163.7	164.0	164.5	166.6	168.0	170.0
47.5°	149.7	148.9	148.1	148.6	148.1	148.9	149.7	150.5	151.9	153.5	156.3
50°	140.0	139.6	137.9	138.3	137.9	139.6	140.0	140.7	141.7	143.8	146.3
52.5°	130.3	128.8	128.2	127.9	128.2	128.8	130.3	131.0	132.2	134.5	136.4
55°	114.1	112.4	111.7	111.3	111.7	112.4	114.1	115.5	117.0	119.7	121.6
57.5°	98.3	97.9	97.3	97.7	97.3	97.9	98.3	100.5	102.1	104.1	106.5
60°	89.1	89.1	89.1	88.9	89.1	89.1	89.1	91.0	92.3	94.4	96.9
62.5°	81.9	81.4	81.4	81.6	81.4	81.4	81.9	82.8	84.1	85.4	87.6
65°	71.0	70.8	70.1	69.9	70.1	70.8	71.0	71.6	72.7	73.7	75.3
67.5°	60.7	60.1	59.8	59.6	59.8	60.1	60.7	61.2	62.0	63.2	64.0
70°	53.0	52.6	51.4	51.7	51.4	52.6	53.0	54.0	54.7	56.3	57.0
72.5°	44.7	44.3	44.0	43.8	44.0	44.3	44.7	45.6	46.3	48.0	49.2
75°	35.3	35.1	35.0	35.7	35.0	35.1	35.3	35.5	35.7	36.3	36.9
77.5°	28.3	28.3	28.5	28.1	28.5	28.3	28.3	28.3	28.3	28.6	28.7
80°	23.7	23.7	23.6	23.6	23.6	23.7	23.7	23.7	23.7	23.7	23.6
82.5°	19.0	19.2	19.3	19.0	19.3	19.2	19.0	19.3	19.5	19.2	19.3
85°	12.6	12.3	12.7	12.6	12.7	12.3	12.6	12.6	12.1	12.6	12.3
87.5°	10.2	10.0	10.2	10.2	10.2	10.0	10.2	10.0	9.7	9.5	9.2
90°	22.7	23.6	24.4	23.6	24.4	23.6	22.7	23.6	22.0	21.2	20.4
92.5°	42.3	39.9	40.7	39.2	40.7	39.9	42.3	43.8	48.0	54.4	68.5
95°	110.7	103.4	97.7	94.4	97.7	103.4	110.7	126.1	155.5	198.6	292.9
97.5°	322.6	286.0	264.0	257.0	264.0	286.0	322.6	382.6	480.0	585.0	730.3
100°	600.6	541.2	509.5	510.3	509.5	541.2	600.6	682.8	798.3	893.6	959.5
102.5°	840.8	793.8	767.3	748.5	767.3	793.8	840.8	904.8	978.0	1033.6	1035.7
105°	1096.2	1065.3	1039.3	1035.2	1039.3	1065.3	1096.2	1133.7	1154.8	1139.4	1057.9
107.5°	1226.9	1216.5	1207.7	1200.2	1207.7	1216.5	1226.9	1226.3	1197.3	1126.0	993.8
110°	1264.7	1271.2	1269.6	1268.0	1269.6	1271.2	1264.7	1241.9	1184.9	1082.4	932.6



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1254.9	1275.0	1281.2	1281.6	1281.2	1275.0	1254.9	1213.2	1140.0	1025.1	872.0
115°	1202.8	1238.6	1254.9	1259.0	1254.9	1238.6	1202.8	1141.7	1053.0	933.4	791.8
117.5°	1117.0	1158.1	1181.5	1187.0	1181.5	1158.1	1117.0	1053.4	963.4	856.0	733.8
120°	1057.1	1102.7	1122.3	1127.2	1122.3	1102.7	1057.1	992.9	910.7	813.0	703.1
122.5°	1002.5	1043.5	1064.9	1071.1	1064.9	1043.5	1002.5	945.3	869.0	778.5	679.1
125°	931.0	966.8	987.2	992.9	987.2	966.8	931.0	878.9	813.8	735.7	647.0
127.5°	874.2	904.8	923.2	928.4	923.2	904.8	874.2	827.8	768.6	698.1	619.0
130°	839.0	868.4	885.4	891.9	885.4	868.4	839.0	795.9	740.5	674.7	601.4
132.5°	807.1	836.4	851.6	856.1	851.6	836.4	807.1	766.6	713.9	652.5	585.1
135°	760.1	784.5	799.2	804.9	799.2	784.5	760.1	720.2	673.8	620.9	563.1
137.5°	709.8	734.6	746.9	750.6	746.9	734.6	709.8	676.3	636.1	590.5	543.2
140°	677.9	700.7	713.7	712.9	713.7	700.7	677.9	647.0	612.0	572.9	531.4
142.5°	646.7	666.8	678.6	677.8	678.6	666.8	646.7	620.3	589.9	556.0	520.3
145°	603.8	620.9	627.5	629.1	627.5	620.9	603.8	583.5	559.9	533.9	507.0
147.5°	570.6	582.2	588.4	589.1	588.4	582.2	570.6	555.2	538.4	517.4	496.1
150°	551.8	560.7	565.6	565.6	565.6	560.7	551.8	539.6	524.1	507.0	488.3
152.5°	534.8	543.2	546.1	546.1	546.1	543.2	534.8	525.2	512.4	497.3	481.1
155°	512.7	519.2	520.8	521.6	520.8	519.2	512.7	505.4	495.6	483.4	470.3
157.5°	493.3	498.2	499.5	499.4	499.5	498.2	493.3	487.0	479.3	469.9	459.0
160°	480.9	485.8	485.8	485.0	485.8	485.8	480.9	475.2	469.5	461.5	452.5
162.5°	468.6	472.8	472.8	472.0	472.8	472.8	468.6	464.9	459.8	452.3	444.7
165°	452.5	455.8	454.9	454.9	454.9	455.8	452.5	449.2	445.2	439.4	434.6
167.5°	437.2	439.4	438.6	438.6	438.6	439.4	437.2	435.7	432.8	429.5	425.7
170°	428.0	429.7	428.8	428.8	428.8	429.7	428.0	427.2	425.6	422.4	420.0
172.5°	420.3	421.9	420.4	419.8	420.4	421.9	420.3	420.1	419.1	416.5	414.7
175°	410.2	411.0	410.2	409.4	410.2	411.0	410.2	410.2	410.2	408.5	407.7
177.5°	404.0	404.6	403.3	403.3	403.3	404.6	404.0	404.6	404.6	404.0	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	423.5	425.7	427.8	429.7	432.8	434.1	436.1	436.9	439.1	442.5	445.2
5°	397.8	400.8	404.8	408.0	413.1	417.1	421.5	425.7	430.6	437.7	443.9
7.5°	375.9	378.9	383.7	389.7	395.3	401.0	407.0	412.7	419.7	429.8	439.8
10°	361.5	365.1	370.8	377.2	384.3	389.8	396.8	404.0	412.8	424.4	436.3
12.5°	349.0	351.7	358.3	364.4	372.4	379.4	386.3	394.8	404.7	417.0	431.5
15°	329.2	333.0	339.4	346.3	354.7	362.1	371.0	381.2	390.9	406.1	423.5
17.5°	309.2	315.0	321.8	329.5	335.7	345.9	355.6	366.1	378.1	394.1	413.4
20°	296.5	301.1	307.4	318.5	326.7	334.5	343.4	356.5	367.5	385.8	405.7
22.5°	285.7	289.0	296.1	305.3	314.9	323.8	333.0	345.4	359.1	376.3	397.9
25°	269.7	275.1	280.4	287.0	297.3	308.1	318.0	328.6	343.1	361.5	384.8
27.5°	254.1	258.9	264.2	272.3	280.1	290.2	300.6	312.7	328.2	347.7	371.5
30°	244.1	247.7	252.7	263.1	270.1	278.8	291.0	301.8	316.3	337.0	362.1
32.5°	233.7	238.4	243.9	251.8	260.6	268.8	279.9	291.6	306.4	326.8	352.5
35°	219.0	224.5	230.0	235.9	244.7	253.2	262.5	275.4	290.4	310.2	335.4
37.5°	205.5	209.9	214.3	221.7	229.9	238.1	246.8	259.5	273.6	295.0	318.1
40°	196.8	200.8	204.2	211.8	219.8	228.5	237.1	248.3	263.4	283.4	305.8
42.5°	187.4	191.0	195.7	201.9	210.5	217.8	226.4	237.0	251.3	271.6	291.2
45°	173.3	177.4	181.4	187.3	195.8	203.1	210.7	220.7	235.4	252.1	269.5
47.5°	158.5	162.7	167.3	173.0	180.4	187.8	195.3	204.2	217.6	234.0	245.8
50°	149.1	152.5	157.1	162.8	169.7	177.4	184.3	194.0	206.7	219.6	229.8
52.5°	139.4	142.5	147.7	153.7	160.0	166.8	174.1	182.4	193.9	206.0	214.2
55°	124.3	128.0	132.4	138.3	144.6	150.3	157.3	165.8	175.0	184.1	189.6
57.5°	110.1	113.2	116.9	122.9	128.4	135.2	141.5	148.1	156.6	163.5	167.1
60°	99.7	102.6	107.3	112.7	117.7	123.7	130.9	137.5	144.0	149.5	152.3
62.5°	90.0	93.3	97.4	102.3	107.9	113.5	119.8	125.4	131.1	135.8	137.8
65°	77.3	80.0	83.0	87.6	92.1	97.8	102.7	108.4	112.7	115.3	117.0
67.5°	65.8	67.5	69.8	72.9	77.4	82.3	87.1	91.6	95.1	96.9	98.4
70°	58.3	59.4	61.1	64.2	67.6	72.0	77.0	80.1	83.2	84.7	86.3
72.5°	50.9	52.3	53.9	56.3	59.1	62.3	65.9	69.8	71.5	73.3	74.2
75°	38.6	40.7	42.7	44.3	46.1	48.6	51.9	54.3	55.3	56.8	57.0
77.5°	29.1	29.6	31.1	32.9	34.6	36.4	38.4	40.6	41.1	41.8	42.4
80°	24.0	24.0	24.0	25.1	27.0	28.3	30.2	31.3	32.1	32.3	32.4
82.5°	19.2	19.2	19.1	19.3	20.0	20.7	22.4	23.7	24.4	24.2	23.8
85°	12.6	12.1	12.1	12.0	12.1	11.7	11.6	12.3	13.5	13.5	13.1
87.5°	9.0	9.0	8.7	8.1	7.5	6.8	6.0	5.9	5.4	5.6	5.2
90°	19.6	20.4	17.9	15.5	13.0	10.6	9.0	7.3	4.9	3.3	1.6
92.5°	94.4	125.1	137.7	103.4	68.3	47.0	35.0	28.1	21.9	15.0	10.1
95°	391.4	482.6	429.7	296.2	175.0	105.8	74.0	52.9	39.1	30.1	27.6
97.5°	800.1	747.9	547.6	325.1	188.3	122.2	87.9	67.0	55.0	48.0	47.2
100°	931.0	770.7	520.8	306.8	186.4	129.4	97.7	78.1	66.8	61.1	60.3
102.5°	937.5	728.4	481.8	291.1	189.0	137.9	108.8	91.2	80.4	75.3	73.9
105°	887.9	654.3	433.7	280.0	196.2	152.2	126.9	111.5	101.7	96.9	94.4
107.5°	801.0	588.9	403.2	279.2	209.5	170.9	147.5	133.0	123.4	118.6	116.2
110°	746.2	551.8	391.4	282.4	220.5	183.9	161.1	147.3	138.4	134.3	131.8



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	698.7	527.0	384.9	288.9	231.6	197.6	175.5	161.6	152.7	148.6	146.2
115°	641.3	500.5	382.5	299.5	249.8	218.9	197.0	183.1	175.0	170.1	166.8
117.5°	606.6	484.9	383.9	313.5	269.2	238.6	218.3	202.8	195.3	191.3	187.5
120°	588.4	477.7	386.5	323.9	281.6	252.3	232.0	216.5	208.3	204.2	201.8
122.5°	573.4	473.1	391.1	333.7	294.6	266.0	244.3	229.5	220.7	216.6	214.2
125°	554.2	467.2	397.9	349.1	313.3	284.9	262.9	247.4	238.5	233.6	232.0
127.5°	537.3	464.2	405.8	361.8	329.6	302.1	280.1	263.0	253.9	247.9	245.5
130°	528.2	462.3	411.0	370.3	339.3	312.5	290.5	273.5	263.7	256.3	253.9
132.5°	519.7	461.6	414.9	378.1	347.8	321.6	300.3	283.2	271.5	263.5	260.4
135°	508.7	460.6	420.8	388.2	360.5	335.3	313.3	296.2	284.1	275.1	271.8
137.5°	499.0	458.9	424.6	395.7	369.3	345.0	324.7	307.8	294.7	286.0	282.6
140°	493.2	458.2	427.2	399.6	375.2	351.6	331.3	315.0	301.9	293.8	289.8
142.5°	488.0	456.9	429.2	403.5	379.8	356.8	337.7	321.5	309.7	300.9	297.5
145°	480.9	454.9	430.5	407.7	385.7	364.6	345.8	332.1	319.8	312.5	310.1
147.5°	474.1	451.8	430.5	410.3	390.6	371.3	355.3	341.9	331.4	324.2	322.8
150°	469.5	449.2	430.5	411.0	393.9	375.2	360.5	349.1	338.5	332.1	331.3
152.5°	464.4	446.0	428.5	412.3	395.8	379.8	365.7	355.6	346.3	339.8	339.7
155°	456.6	440.3	426.4	412.6	399.6	385.7	374.4	365.4	357.3	352.4	352.4
157.5°	447.8	435.2	423.7	413.4	401.7	390.6	381.8	374.2	367.0	363.1	362.5
160°	441.9	431.3	422.4	413.4	403.7	393.9	385.7	380.0	373.6	370.3	370.3
162.5°	436.0	427.4	419.8	412.8	404.3	395.8	389.0	383.9	378.8	376.2	376.2
165°	428.0	421.6	415.9	411.0	405.3	398.8	393.1	389.8	385.7	384.1	384.9
167.5°	420.4	415.7	412.0	409.7	405.1	400.4	396.8	394.5	391.4	390.6	391.6
170°	415.9	411.8	409.4	407.7	404.5	400.4	398.8	397.1	394.7	393.9	395.5
172.5°	411.3	408.5	407.4	407.1	404.5	401.0	400.1	399.1	397.3	397.1	398.1
175°	406.1	404.5	404.5	405.3	403.7	402.0	401.2	401.2	399.6	400.4	401.2
177.5°	402.7	402.0	402.7	404.0	402.7	402.0	402.0	402.0	401.4	402.0	402.7
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	446.1	447.8	450.0	453.1	455.6	457.7	458.1	458.8	460.3	462.8	464.8
5°	449.1	453.4	460.4	467.2	474.7	480.8	486.5	490.5	494.2	502.2	508.7
7.5°	448.1	457.9	468.9	481.1	493.6	505.6	516.7	526.8	536.7	548.4	561.6
10°	447.5	458.9	473.8	489.5	506.8	523.7	540.1	552.8	567.5	580.9	597.8
12.5°	444.7	461.1	478.7	498.9	520.2	539.6	561.2	578.7	595.7	614.9	634.5
15°	440.8	460.8	483.2	510.0	542.3	565.8	587.9	618.5	639.4	660.2	688.4
17.5°	434.0	458.4	486.3	521.1	548.0	579.8	612.9	637.1	665.2	694.6	720.1
20°	428.5	456.8	488.2	522.4	556.8	591.1	623.2	652.1	681.2	715.2	736.1
22.5°	423.1	451.0	483.6	519.9	556.8	593.1	629.4	663.3	696.0	730.3	757.0
25°	411.4	444.7	480.0	517.1	553.5	593.4	636.7	674.5	714.9	750.3	775.6
27.5°	399.7	430.2	465.3	502.9	543.4	590.5	641.5	684.4	725.0	750.3	758.2
30°	389.0	421.3	453.6	491.8	535.7	588.2	642.4	691.6	724.8	735.9	727.7
32.5°	378.2	407.5	439.4	478.6	525.1	582.6	643.6	687.4	707.4	699.0	665.7
35°	359.2	385.6	416.5	455.7	509.2	579.5	638.6	668.2	663.3	615.8	553.1
37.5°	338.8	360.4	389.0	429.9	492.8	567.2	617.0	621.4	578.6	505.7	433.3
40°	322.7	342.1	371.5	414.3	480.0	555.1	595.3	577.6	511.4	430.2	369.8
42.5°	307.0	323.4	351.8	397.9	467.8	538.4	563.0	524.5	448.0	371.3	316.3
45°	280.5	296.0	324.4	371.7	443.0	506.8	503.5	436.7	360.1	298.4	252.8
47.5°	255.4	268.9	295.6	343.9	413.8	459.3	429.1	357.9	293.0	243.4	210.9
50°	237.7	250.9	277.5	325.2	390.4	423.5	380.5	311.9	252.4	211.4	185.6
52.5°	220.6	233.6	257.9	304.4	362.1	382.0	335.7	272.1	222.5	187.1	164.9
55°	196.8	206.7	228.5	273.0	316.1	320.7	273.7	220.5	179.7	155.0	139.8
57.5°	172.5	181.0	202.6	238.0	268.2	265.9	221.4	175.4	147.9	129.6	118.5
60°	156.7	165.1	184.1	214.4	237.3	229.3	188.4	151.4	127.8	114.4	105.6
62.5°	141.9	148.5	166.3	188.5	204.9	195.8	161.1	130.4	111.7	100.4	93.4
65°	120.6	126.0	140.1	151.8	160.9	152.1	123.3	102.0	88.5	80.6	75.8
67.5°	100.4	103.7	112.7	116.9	123.4	113.7	92.7	78.4	70.8	64.1	60.7
70°	87.6	90.0	94.8	98.2	99.9	90.0	74.4	64.0	57.6	52.8	50.7
72.5°	74.8	77.0	77.9	80.7	79.8	70.6	59.8	51.5	46.9	43.7	41.0
75°	57.2	58.1	57.2	56.0	53.6	47.1	39.7	35.5	32.1	30.6	29.6
77.5°	41.7	41.3	40.1	38.3	34.1	30.0	26.0	24.6	23.2	22.3	22.0
80°	32.1	31.3	30.2	27.3	23.7	20.9	20.0	19.0	18.4	17.4	17.3
82.5°	23.9	23.4	21.5	19.2	16.6	15.2	14.5	14.1	13.5	13.0	13.0
85°	12.7	12.1	10.0	8.7	8.4	8.0	7.8	7.8	7.0	6.8	6.8
87.5°	4.7	4.2	4.5	4.4	4.7	4.9	5.5	5.7	6.0	6.0	5.9
90°	3.3	4.9	7.3	9.0	10.6	13.0	15.5	17.9	20.4	19.6	20.4
92.5°	15.0	21.9	28.1	35.0	47.0	68.3	103.4	137.7	125.1	94.4	68.5
95°	30.1	39.1	52.9	74.0	105.8	175.0	296.2	429.7	482.6	391.4	292.9
97.5°	48.0	55.0	67.0	87.9	122.2	188.3	325.1	547.6	747.9	800.1	730.3
100°	61.1	66.8	78.1	97.7	129.4	186.4	306.8	520.8	770.7	931.0	959.5
102.5°	75.3	80.4	91.2	108.8	137.9	189.0	291.1	481.8	728.4	937.5	1035.7
105°	96.9	101.7	111.5	126.9	152.2	196.2	280.0	433.7	654.3	887.9	1057.9
107.5°	118.6	123.4	133.0	147.5	170.9	209.5	279.2	403.2	588.9	801.0	993.8
110°	134.3	138.4	147.3	161.1	183.9	220.5	282.4	391.4	551.8	746.2	932.6



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	148.6	152.7	161.6	175.5	197.6	231.6	288.9	384.9	527.0	698.7	872.0
115°	170.1	175.0	183.1	197.0	218.9	249.8	299.5	382.5	500.5	641.3	791.8
117.5°	191.3	195.3	202.8	218.3	238.6	269.2	313.5	383.9	484.9	606.6	733.8
120°	204.2	208.3	216.5	232.0	252.3	281.6	323.9	386.5	477.7	588.4	703.1
122.5°	216.6	220.7	229.5	244.3	266.0	294.6	333.7	391.1	473.1	573.4	679.1
125°	233.6	238.5	247.4	262.9	284.9	313.3	349.1	397.9	467.2	554.2	647.0
127.5°	247.9	253.9	263.0	280.1	302.1	329.6	361.8	405.8	464.2	537.3	619.0
130°	256.3	263.7	273.5	290.5	312.5	339.3	370.3	411.0	462.3	528.2	601.4
132.5°	263.5	271.5	283.2	300.3	321.6	347.8	378.1	414.9	461.6	519.7	585.1
135°	275.1	284.1	296.2	313.3	335.3	360.5	388.2	420.8	460.6	508.7	563.1
137.5°	286.0	294.7	307.8	324.7	345.0	369.3	395.7	424.6	458.9	499.0	543.2
140°	293.8	301.9	315.0	331.3	351.6	375.2	399.6	427.2	458.2	493.2	531.4
142.5°	300.9	309.7	321.5	337.7	356.8	379.8	403.5	429.2	456.9	488.0	520.3
145°	312.5	319.8	332.1	345.8	364.6	385.7	407.7	430.5	454.9	480.9	507.0
147.5°	324.2	331.4	341.9	355.3	371.3	390.6	410.3	430.5	451.8	474.1	496.1
150°	332.1	338.5	349.1	360.5	375.2	393.9	411.0	430.5	449.2	469.5	488.3
152.5°	339.8	346.3	355.6	365.7	379.8	395.8	412.3	428.5	446.0	464.4	481.1
155°	352.4	357.3	365.4	374.4	385.7	399.6	412.6	426.4	440.3	456.6	470.3
157.5°	363.1	367.0	374.2	381.8	390.6	401.7	413.4	423.7	435.2	447.8	459.0
160°	370.3	373.6	380.0	385.7	393.9	403.7	413.4	422.4	431.3	441.9	452.5
162.5°	376.2	378.8	383.9	389.0	395.8	404.3	412.8	419.8	427.4	436.0	444.7
165°	384.1	385.7	389.8	393.1	398.8	405.3	411.0	415.9	421.6	428.0	434.6
167.5°	390.6	391.4	394.5	396.8	400.4	405.1	409.7	412.0	415.7	420.4	425.7
170°	393.9	394.7	397.1	398.8	400.4	404.5	407.7	409.4	411.8	415.9	420.0
172.5°	397.1	397.3	399.1	400.1	401.0	404.5	407.1	407.4	408.5	411.3	414.7
175°	400.4	399.6	401.2	401.2	402.0	403.7	405.3	404.5	404.5	406.1	407.7
177.5°	402.0	401.4	402.0	402.0	402.0	402.7	404.0	402.7	402.0	402.7	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0	402.0



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	468.1	468.1	468.6	470.9	471.2	473.2	472.6
5°	514.4	518.0	519.3	525.1	528.4	529.9	526.9
7.5°	571.0	581.2	586.0	592.1	597.3	598.9	594.8
10°	612.4	623.1	631.9	637.5	642.6	646.0	650.4
12.5°	652.3	665.4	673.9	681.7	687.0	691.3	692.0
15°	695.8	715.5	730.5	741.6	747.1	749.9	748.8
17.5°	739.6	757.9	768.6	779.8	787.4	787.8	788.1
20°	764.3	782.2	794.6	802.9	811.5	811.1	813.0
22.5°	780.9	795.0	804.5	810.5	813.4	812.0	812.4
25°	788.6	792.9	791.2	781.5	778.9	770.1	771.6
27.5°	748.7	729.0	708.5	682.2	661.5	644.9	645.7
30°	694.5	659.5	619.6	586.2	556.2	547.8	529.9
32.5°	618.6	566.2	519.5	488.3	462.6	455.6	440.0
35°	490.1	439.1	391.1	362.2	350.8	334.8	334.7
37.5°	380.9	336.1	310.7	289.0	277.7	268.0	267.1
40°	320.4	285.5	266.3	250.7	239.5	232.3	230.6
42.5°	278.2	250.0	232.0	222.3	213.7	209.9	207.2
45°	227.1	208.1	195.7	186.9	183.0	180.1	178.6
47.5°	190.0	177.3	168.8	162.9	159.7	156.7	157.5
50°	169.8	159.4	153.1	147.6	145.1	143.0	143.2
52.5°	153.5	144.1	139.1	135.1	132.1	130.5	129.9
55°	130.3	124.4	119.3	116.4	114.7	112.7	112.1
57.5°	111.1	106.6	102.4	99.2	98.7	96.8	97.0
60°	98.4	94.6	91.2	89.4	88.1	86.4	87.0
62.5°	87.9	84.7	81.6	80.2	78.8	77.6	77.9
65°	72.0	69.0	67.0	66.3	65.7	65.1	64.6
67.5°	57.4	55.5	54.3	52.7	51.5	51.4	50.8
70°	48.3	45.7	43.7	41.6	41.0	40.8	41.0
72.5°	38.6	37.1	36.5	35.5	35.4	34.9	35.2
75°	29.0	28.5	28.1	27.3	27.3	27.3	27.3
77.5°	21.4	21.1	20.9	20.7	20.5	20.2	20.2
80°	16.7	16.6	16.1	16.1	16.0	16.1	16.0
82.5°	12.6	12.6	12.2	12.2	12.0	11.9	12.0
85°	6.4	6.3	6.7	6.3	6.4	6.1	6.4
87.5°	6.0	6.2	6.4	6.2	6.3	6.7	6.3
90°	21.2	22.0	23.6	22.7	23.6	24.4	23.6
92.5°	54.4	48.0	43.8	42.3	39.9	40.7	39.2
95°	198.6	155.5	126.1	110.7	103.4	97.7	94.4
97.5°	585.0	480.0	382.6	322.6	286.0	264.0	257.0
100°	893.6	798.3	682.8	600.6	541.2	509.5	510.3
102.5°	1033.6	978.0	904.8	840.8	793.8	767.3	748.5
105°	1139.4	1154.8	1133.7	1096.2	1065.3	1039.3	1035.2
107.5°	1126.0	1197.3	1226.3	1226.9	1216.5	1207.7	1200.2
110°	1082.4	1184.9	1241.9	1264.7	1271.2	1269.6	1268.0



TEST NUMBER: P332260-930

CATALOG NUMBER: S123RDIP-S340D1025U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1025.1	1140.0	1213.2	1254.9	1275.0	1281.2	1281.6
115°	933.4	1053.0	1141.7	1202.8	1238.6	1254.9	1259.0
117.5°	856.0	963.4	1053.4	1117.0	1158.1	1181.5	1187.0
120°	813.0	910.7	992.9	1057.1	1102.7	1122.3	1127.2
122.5°	778.5	869.0	945.3	1002.5	1043.5	1064.9	1071.1
125°	735.7	813.8	878.9	931.0	966.8	987.2	992.9
127.5°	698.1	768.6	827.8	874.2	904.8	923.2	928.4
130°	674.7	740.5	795.9	839.0	868.4	885.4	891.9
132.5°	652.5	713.9	766.6	807.1	836.4	851.6	856.1
135°	620.9	673.8	720.2	760.1	784.5	799.2	804.9
137.5°	590.5	636.1	676.3	709.8	734.6	746.9	750.6
140°	572.9	612.0	647.0	677.9	700.7	713.7	712.9
142.5°	556.0	589.9	620.3	646.7	666.8	678.6	677.8
145°	533.9	559.9	583.5	603.8	620.9	627.5	629.1
147.5°	517.4	538.4	555.2	570.6	582.2	588.4	589.1
150°	507.0	524.1	539.6	551.8	560.7	565.6	565.6
152.5°	497.3	512.4	525.2	534.8	543.2	546.1	546.1
155°	483.4	495.6	505.4	512.7	519.2	520.8	521.6
157.5°	469.9	479.3	487.0	493.3	498.2	499.5	499.4
160°	461.5	469.5	475.2	480.9	485.8	485.8	485.0
162.5°	452.3	459.8	464.9	468.6	472.8	472.8	472.0
165°	439.4	445.2	449.2	452.5	455.8	454.9	454.9
167.5°	429.5	432.8	435.7	437.2	439.4	438.6	438.6
170°	422.4	425.6	427.2	428.0	429.7	428.8	428.8
172.5°	416.5	419.1	420.1	420.3	421.9	420.4	419.8
175°	408.5	410.2	410.2	410.2	411.0	410.2	409.4
177.5°	404.0	404.6	404.6	404.0	404.6	403.3	403.3
180°	402.0	402.0	402.0	402.0	402.0	402.0	402.0

(END OF REPORT)