

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332242-930

Luminaire Tested: **S123RDIP-S340D365U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332242-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-17,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S340D365U930-4F0-1E-UDD-A4
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2176.7 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	38
3	83	74	67	61	76	68	62	57	59	54	50	49	46	43	41	39	37	33
4	76	66	58	52	70	61	54	49	52	47	43	44	41	38	37	34	32	29
5	70	59	51	45	64	55	48	43	47	42	38	40	36	33	34	31	28	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23	20
8	56	44	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	18
9	52	40	33	28	48	37	31	26	33	27	24	28	24	21	24	21	18	16
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4776	4776	4776	4776
5°	5693	4796	4224	4796
10°	7109	4769	3816	4769
15°	8344	4719	3480	4719
20°	9313	4647	3194	4647
25°	9164	4570	3018	4570
30°	6586	4501	2838	4501
35°	4398	4407	2720	4407
40°	3240	4297	2599	4297
45°	2719	4102	2481	4102
50°	2398	3848	2316	3848
55°	2104	3558	2089	3558
60°	1873	3279	1914	3279
65°	1645	2980	1780	2980
70°	1290	2716	1627	2716
75°	1135	2371	1485	2371
80°	992	2008	1463	2008
85°	790	1618	1556	1618



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	2.0
10°-20°	136.3	6.3
20°-30°	214.2	9.8
30°-40°	223.4	10.3
40°-50°	191.2	8.8
50°-60°	145.7	6.7
60°-70°	93.4	4.3
70°-80°	44.9	2.1
80°-90°	13.0	0.6
90°-100°	79.2	3.6
100°-110°	224.3	10.3
110°-120°	220.6	10.1
120°-130°	176.0	8.1
130°-140°	138.8	6.4
140°-150°	103.6	4.8
150°-160°	72.2	3.3
160°-170°	42.4	1.9
170°-180°	13.8	0.6
0°-30°	394.1	18.1
0°-40°	617.6	28.4
0°-60°	954.5	43.9
0°-90°	1105.9	50.8
90°-120°	524.1	24.1
90°-150°	942.4	43.3
90°-180°	1071.0	49.2
0°-180°	2176.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	527	444	391	444	527	54
15°	749	424	312	424	749	212
25°	772	385	254	385	772	332
35°	335	335	207	335	335	219
45°	179	270	163	270	179	140
55°	112	190	111	190	112	101
65°	65	117	70	117	65	64
75°	27	57	36	57	27	29
85°	6	13	13	13	6	8
90°	8	1	8	1	8	5
95°	33	10	33	10	33	60
105°	366	33	366	33	366	362
115°	446	59	446	59	446	433
125°	352	82	352	82	352	319
135°	285	96	285	96	285	221
145°	223	110	223	110	223	142
155°	185	125	185	125	185	86
165°	161	136	161	136	161	46
175°	145	142	145	142	145	14
180°	142	142	142	142	142	



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	472.6	473.2	471.2	470.9	468.6	468.1	468.1	464.8	462.8	460.3	458.8
5°	526.9	529.9	528.4	525.1	519.3	518.0	514.4	508.7	502.2	494.2	490.5
7.5°	594.8	598.9	597.3	592.1	586.0	581.2	571.0	561.6	548.4	536.7	526.8
10°	650.4	646.0	642.6	637.5	631.9	623.1	612.4	597.8	580.9	567.5	552.8
12.5°	692.0	691.3	687.0	681.7	673.9	665.4	652.3	634.5	614.9	595.7	578.7
15°	748.8	749.9	747.1	741.6	730.5	715.5	695.8	688.4	660.2	639.4	618.5
17.5°	788.1	787.8	787.4	779.8	768.6	757.9	739.6	720.1	694.6	665.2	637.1
20°	813.0	811.1	811.5	802.9	794.6	782.2	764.3	736.1	715.2	681.2	652.1
22.5°	812.4	812.0	813.4	810.5	804.5	795.0	780.9	757.0	730.3	696.0	663.3
25°	771.6	770.1	778.9	781.5	791.2	792.9	788.6	775.6	750.3	714.9	674.5
27.5°	645.7	644.9	661.5	682.2	708.5	729.0	748.7	758.2	750.3	725.0	684.4
30°	529.9	547.8	556.2	586.2	619.6	659.5	694.5	727.7	735.9	724.8	691.6
32.5°	440.0	455.6	462.6	488.3	519.5	566.2	618.6	665.7	699.0	707.4	687.4
35°	334.7	334.8	350.8	362.2	391.1	439.1	490.1	553.1	615.8	663.3	668.2
37.5°	267.1	268.0	277.7	289.0	310.7	336.1	380.9	433.3	505.7	578.6	621.4
40°	230.6	232.3	239.5	250.7	266.3	285.5	320.4	369.8	430.2	511.4	577.6
42.5°	207.2	209.9	213.7	222.3	232.0	250.0	278.2	316.3	371.3	448.0	524.5
45°	178.6	180.1	183.0	186.9	195.7	208.1	227.1	252.8	298.4	360.1	436.7
47.5°	157.5	156.7	159.7	162.9	168.8	177.3	190.0	210.9	243.4	293.0	357.9
50°	143.2	143.0	145.1	147.6	153.1	159.4	169.8	185.6	211.4	252.4	311.9
52.5°	129.9	130.5	132.1	135.1	139.1	144.1	153.5	164.9	187.1	222.5	272.1
55°	112.1	112.7	114.7	116.4	119.3	124.4	130.3	139.8	155.0	179.7	220.5
57.5°	97.0	96.8	98.7	99.2	102.4	106.6	111.1	118.5	129.6	147.9	175.4
60°	87.0	86.4	88.1	89.4	91.2	94.6	98.4	105.6	114.4	127.8	151.4
62.5°	77.9	77.6	78.8	80.2	81.6	84.7	87.9	93.4	100.4	111.7	130.4
65°	64.6	65.1	65.7	66.3	67.0	69.0	72.0	75.8	80.6	88.5	102.0
67.5°	50.8	51.4	51.5	52.7	54.3	55.5	57.4	60.7	64.1	70.8	78.4
70°	41.0	40.8	41.0	41.6	43.7	45.7	48.3	50.7	52.8	57.6	64.0
72.5°	35.2	34.9	35.4	35.5	36.5	37.1	38.6	41.0	43.7	46.9	51.5
75°	27.3	27.3	27.3	27.3	28.1	28.5	29.0	29.6	30.6	32.1	35.5
77.5°	20.2	20.2	20.5	20.7	20.9	21.1	21.4	22.0	22.3	23.2	24.6
80°	16.0	16.1	16.0	16.1	16.1	16.6	16.7	17.3	17.4	18.4	19.0
82.5°	12.0	11.9	12.0	12.2	12.2	12.6	12.6	13.0	13.0	13.5	14.1
85°	6.4	6.1	6.4	6.3	6.7	6.3	6.4	6.8	6.8	7.0	7.8
87.5°	3.2	3.6	3.2	3.3	3.3	3.3	3.3	3.3	3.5	3.4	3.4
90°	8.3	8.6	8.3	8.1	8.3	7.7	7.5	7.2	6.9	7.2	6.4
92.5°	13.9	14.4	14.1	15.0	15.5	17.0	19.2	24.3	33.4	44.3	48.8
95°	33.4	34.6	36.6	39.2	44.7	55.0	70.3	103.7	138.6	170.9	152.1
97.5°	91.0	93.4	101.3	114.2	135.5	169.9	207.1	258.5	283.2	264.8	193.9
100°	180.7	180.3	191.6	212.6	241.7	282.7	316.3	339.7	329.6	272.9	184.4
102.5°	265.0	271.7	281.0	297.7	320.3	346.3	365.9	366.6	331.9	257.9	170.6
105°	366.5	367.9	377.2	388.1	401.4	408.8	403.3	374.5	314.3	231.6	153.6
107.5°	424.9	427.5	430.6	434.4	434.1	423.9	398.6	351.8	283.6	208.5	142.8
110°	448.9	449.5	450.0	447.8	439.7	419.5	383.2	330.2	264.2	195.3	138.6



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	453.7	453.6	451.4	444.3	429.5	403.6	362.9	308.8	247.4	186.5	136.2
115°	445.7	444.3	438.5	425.8	404.2	372.8	330.4	280.3	227.1	177.2	135.4
117.5°	420.2	418.2	410.0	395.5	372.9	341.0	303.0	259.8	214.7	171.6	135.9
120°	399.0	397.3	390.4	374.2	351.5	322.4	287.8	248.9	208.3	169.1	136.9
122.5°	379.2	377.0	369.4	354.9	334.7	307.6	275.6	240.4	203.0	167.5	138.4
125°	351.5	349.5	342.3	329.6	311.2	288.1	260.5	229.0	196.2	165.3	140.9
127.5°	328.6	326.9	320.3	309.5	293.1	272.1	247.1	219.2	190.2	164.4	143.7
130°	315.8	313.5	307.4	297.0	281.8	262.2	238.9	212.9	186.9	163.6	145.5
132.5°	303.1	301.5	296.1	285.8	271.4	252.7	231.0	207.2	184.0	163.4	146.9
135°	284.9	282.9	277.8	269.1	254.9	238.6	219.8	199.3	180.1	163.1	149.0
137.5°	265.8	264.4	260.1	251.3	239.5	225.2	209.0	192.2	176.7	162.4	150.3
140°	252.4	252.7	248.1	240.0	229.0	216.6	202.8	188.2	174.6	162.2	151.2
142.5°	239.9	240.2	236.1	228.9	219.6	208.8	196.8	184.3	172.8	161.8	152.0
145°	222.7	222.2	219.8	213.8	206.6	198.2	189.0	179.5	170.2	161.0	152.4
147.5°	208.6	208.3	206.1	202.0	196.6	190.6	183.2	175.6	167.9	160.0	152.4
150°	200.2	200.2	198.5	195.3	191.0	185.6	179.5	172.8	166.2	159.1	152.4
152.5°	193.3	193.3	192.2	189.3	186.0	181.4	176.0	170.3	164.4	157.9	151.7
155°	184.7	184.4	183.8	181.5	178.9	175.5	171.1	166.6	161.6	155.9	151.0
157.5°	176.8	176.8	176.3	174.6	172.4	169.7	166.3	162.5	158.5	154.1	150.0
160°	171.7	172.0	172.0	170.2	168.3	166.2	163.4	160.2	156.5	152.7	149.5
162.5°	167.1	167.4	167.4	165.9	164.6	162.8	160.1	157.4	154.3	151.3	148.6
165°	161.0	161.0	161.3	160.2	159.1	157.6	155.6	153.8	151.6	149.3	147.2
167.5°	155.3	155.3	155.6	154.7	154.3	153.2	152.1	150.7	148.9	147.2	145.9
170°	151.8	151.8	152.1	151.6	151.2	150.7	149.5	148.6	147.2	145.8	145.0
172.5°	148.6	148.9	149.4	148.8	148.7	148.4	147.5	146.8	145.6	144.6	144.2
175°	145.0	145.2	145.5	145.2	145.2	145.2	144.6	144.3	143.7	143.2	143.2
177.5°	142.8	142.8	143.2	143.0	143.2	143.2	143.0	142.8	142.6	142.4	142.6
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	458.1	457.7	455.6	453.1	450.0	447.8	446.1	445.2	442.5	439.1	436.9
5°	486.5	480.8	474.7	467.2	460.4	453.4	449.1	443.9	437.7	430.6	425.7
7.5°	516.7	505.6	493.6	481.1	468.9	457.9	448.1	439.8	429.8	419.7	412.7
10°	540.1	523.7	506.8	489.5	473.8	458.9	447.5	436.3	424.4	412.8	404.0
12.5°	561.2	539.6	520.2	498.9	478.7	461.1	444.7	431.5	417.0	404.7	394.8
15°	587.9	565.8	542.3	510.0	483.2	460.8	440.8	423.5	406.1	390.9	381.2
17.5°	612.9	579.8	548.0	521.1	486.3	458.4	434.0	413.4	394.1	378.1	366.1
20°	623.2	591.1	556.8	522.4	488.2	456.8	428.5	405.7	385.8	367.5	356.5
22.5°	629.4	593.1	556.8	519.9	483.6	451.0	423.1	397.9	376.3	359.1	345.4
25°	636.7	593.4	553.5	517.1	480.0	444.7	411.4	384.8	361.5	343.1	328.6
27.5°	641.5	590.5	543.4	502.9	465.3	430.2	399.7	371.5	347.7	328.2	312.7
30°	642.4	588.2	535.7	491.8	453.6	421.3	389.0	362.1	337.0	316.3	301.8
32.5°	643.6	582.6	525.1	478.6	439.4	407.5	378.2	352.5	326.8	306.4	291.6
35°	638.6	579.5	509.2	455.7	416.5	385.6	359.2	335.4	310.2	290.4	275.4
37.5°	617.0	567.2	492.8	429.9	389.0	360.4	338.8	318.1	295.0	273.6	259.5
40°	595.3	555.1	480.0	414.3	371.5	342.1	322.7	305.8	283.4	263.4	248.3
42.5°	563.0	538.4	467.8	397.9	351.8	323.4	307.0	291.2	271.6	251.3	237.0
45°	503.5	506.8	443.0	371.7	324.4	296.0	280.5	269.5	252.1	235.4	220.7
47.5°	429.1	459.3	413.8	343.9	295.6	268.9	255.4	245.8	234.0	217.6	204.2
50°	380.5	423.5	390.4	325.2	277.5	250.9	237.7	229.8	219.6	206.7	194.0
52.5°	335.7	382.0	362.1	304.4	257.9	233.6	220.6	214.2	206.0	193.9	182.4
55°	273.7	320.7	316.1	273.0	228.5	206.7	196.8	189.6	184.1	175.0	165.8
57.5°	221.4	265.9	268.2	238.0	202.6	181.0	172.5	167.1	163.5	156.6	148.1
60°	188.4	229.3	237.3	214.4	184.1	165.1	156.7	152.3	149.5	144.0	137.5
62.5°	161.1	195.8	204.9	188.5	166.3	148.5	141.9	137.8	135.8	131.1	125.4
65°	123.3	152.1	160.9	151.8	140.1	126.0	120.6	117.0	115.3	112.7	108.4
67.5°	92.7	113.7	123.4	116.9	112.7	103.7	100.4	98.4	96.9	95.1	91.6
70°	74.4	90.0	99.9	98.2	94.8	90.0	87.6	86.3	84.7	83.2	80.1
72.5°	59.8	70.6	79.8	80.7	77.9	77.0	74.8	74.2	73.3	71.5	69.8
75°	39.7	47.1	53.6	56.0	57.2	58.1	57.2	57.0	56.8	55.3	54.3
77.5°	26.0	30.0	34.1	38.3	40.1	41.3	41.7	42.4	41.8	41.1	40.6
80°	20.0	20.9	23.7	27.3	30.2	31.3	32.1	32.4	32.3	32.1	31.3
82.5°	14.5	15.2	16.6	19.2	21.5	23.4	23.9	23.8	24.2	24.4	23.7
85°	7.8	8.0	8.4	8.7	10.0	12.1	12.7	13.1	13.5	13.5	12.3
87.5°	3.5	3.2	3.3	3.2	3.6	3.5	4.3	5.0	5.2	4.7	4.9
90°	5.5	4.6	3.8	3.2	2.6	1.7	1.1	0.6	1.1	1.7	2.6
92.5°	36.6	24.2	16.6	12.4	9.9	7.7	5.3	3.6	5.3	7.7	9.9
95°	104.8	62.0	37.4	26.3	18.8	13.9	10.7	9.8	10.7	13.9	18.8
97.5°	115.0	66.7	43.3	31.1	23.7	19.5	17.0	16.7	17.0	19.5	23.7
100°	108.6	66.0	45.8	34.6	27.6	23.6	21.6	21.4	21.6	23.6	27.6
102.5°	103.1	66.9	48.8	38.5	32.3	28.5	26.7	26.2	26.7	28.5	32.3
105°	99.1	69.5	53.9	44.9	39.5	36.0	34.3	33.4	34.3	36.0	39.5
107.5°	98.8	74.2	60.5	52.2	47.0	43.7	42.0	41.2	42.0	43.7	47.0
110°	100.0	78.1	65.1	57.1	52.2	49.0	47.5	46.6	47.5	49.0	52.2



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	102.3	82.0	70.0	62.1	57.2	54.1	52.6	51.8	52.6	54.1	57.2
115°	106.0	88.5	77.5	69.7	64.8	62.0	60.3	59.0	60.3	62.0	64.8
117.5°	111.0	95.3	84.5	77.3	71.8	69.1	67.7	66.4	67.7	69.1	71.8
120°	114.6	99.7	89.3	82.1	76.6	73.8	72.3	71.4	72.3	73.8	76.6
122.5°	118.1	104.3	94.2	86.5	81.3	78.1	76.7	75.8	76.7	78.1	81.3
125°	123.6	111.0	100.9	93.0	87.6	84.4	82.7	82.1	82.7	84.4	87.6
127.5°	128.1	116.7	107.0	99.1	93.1	89.9	87.7	86.9	87.7	89.9	93.1
130°	131.1	120.2	110.6	102.9	96.8	93.4	90.7	89.9	90.7	93.4	96.8
132.5°	133.9	123.1	113.9	106.3	100.3	96.1	93.3	92.2	93.3	96.1	100.3
135°	137.5	127.6	118.7	111.0	104.8	100.5	97.3	96.2	97.3	100.5	104.8
137.5°	140.1	130.8	122.1	115.0	108.9	104.4	101.3	100.0	101.3	104.4	108.9
140°	141.5	132.8	124.5	117.2	111.5	106.9	104.0	102.6	104.0	106.9	111.5
142.5°	142.8	134.4	126.3	119.6	113.8	109.7	106.6	105.3	106.6	109.7	113.8
145°	144.3	136.6	129.1	122.5	117.6	113.2	110.6	109.7	110.6	113.2	117.6
147.5°	145.3	138.3	131.4	125.8	121.1	117.3	114.8	114.3	114.8	117.3	121.1
150°	145.5	139.4	132.8	127.6	123.6	119.8	117.6	117.2	117.6	119.8	123.6
152.5°	145.9	140.1	134.4	129.5	125.9	122.6	120.3	120.3	120.3	122.6	125.9
155°	146.1	141.5	136.6	132.6	129.4	126.5	124.7	124.7	124.7	126.5	129.4
157.5°	146.3	142.2	138.3	135.2	132.5	130.0	128.6	128.3	128.6	130.0	132.5
160°	146.3	142.9	139.4	136.6	134.5	132.2	131.1	131.1	131.1	132.2	134.5
162.5°	146.1	143.2	140.1	137.7	135.9	134.1	133.1	133.1	133.1	134.1	135.9
165°	145.5	143.5	141.2	139.2	138.0	136.6	136.0	136.2	136.0	136.6	138.0
167.5°	145.0	143.4	141.8	140.5	139.7	138.6	138.3	138.6	138.3	138.6	139.7
170°	144.3	143.2	141.8	141.2	140.6	139.7	139.4	140.0	139.4	139.7	140.6
172.5°	144.1	143.2	141.9	141.6	141.3	140.6	140.6	141.0	140.6	140.6	141.3
175°	143.5	142.9	142.4	142.0	142.0	141.5	141.8	142.0	141.8	141.5	142.0
177.5°	143.0	142.6	142.4	142.4	142.4	142.1	142.4	142.6	142.4	142.1	142.4
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	436.1	434.1	432.8	429.7	427.8	425.7	423.5	424.9	424.7	424.6	424.6
5°	421.5	417.1	413.1	408.0	404.8	400.8	397.8	397.4	398.1	395.5	394.0
7.5°	407.0	401.0	395.3	389.7	383.7	378.9	375.9	374.5	372.6	371.0	369.2
10°	396.8	389.8	384.3	377.2	370.8	365.1	361.5	359.0	357.7	356.4	353.8
12.5°	386.3	379.4	372.4	364.4	358.3	351.7	349.0	346.3	343.7	342.2	338.8
15°	371.0	362.1	354.7	346.3	339.4	333.0	329.2	323.7	322.9	321.0	317.6
17.5°	355.6	345.9	335.7	329.5	321.8	315.0	309.2	307.4	302.0	299.9	296.9
20°	343.4	334.5	326.7	318.5	307.4	301.1	296.5	294.1	289.7	287.0	285.1
22.5°	333.0	323.8	314.9	305.3	296.1	289.0	285.7	281.8	279.5	275.7	273.7
25°	318.0	308.1	297.3	287.0	280.4	275.1	269.7	266.3	262.9	261.1	257.4
27.5°	300.6	290.2	280.1	272.3	264.2	258.9	254.1	251.1	247.0	244.1	242.0
30°	291.0	278.8	270.1	263.1	252.7	247.7	244.1	240.3	237.3	234.2	232.1
32.5°	279.9	268.8	260.6	251.8	243.9	238.4	233.7	230.4	227.8	224.9	222.8
35°	262.5	253.2	244.7	235.9	230.0	224.5	219.0	216.1	213.7	211.0	209.1
37.5°	246.8	238.1	229.9	221.7	214.3	209.9	205.5	203.3	199.9	198.1	196.2
40°	237.1	228.5	219.8	211.8	204.2	200.8	196.8	193.6	190.5	189.1	187.1
42.5°	226.4	217.8	210.5	201.9	195.7	191.0	187.4	183.8	181.6	179.6	178.5
45°	210.7	203.1	195.8	187.3	181.4	177.4	173.3	170.0	168.0	166.6	164.5
47.5°	195.3	187.8	180.4	173.0	167.3	162.7	158.5	156.3	153.5	151.9	150.5
50°	184.3	177.4	169.7	162.8	157.1	152.5	149.1	146.3	143.8	141.7	140.7
52.5°	174.1	166.8	160.0	153.7	147.7	142.5	139.4	136.4	134.5	132.2	131.0
55°	157.3	150.3	144.6	138.3	132.4	128.0	124.3	121.6	119.7	117.0	115.5
57.5°	141.5	135.2	128.4	122.9	116.9	113.2	110.1	106.5	104.1	102.1	100.5
60°	130.9	123.7	117.7	112.7	107.3	102.6	99.7	96.9	94.4	92.3	91.0
62.5°	119.8	113.5	107.9	102.3	97.4	93.3	90.0	87.6	85.4	84.1	82.8
65°	102.7	97.8	92.1	87.6	83.0	80.0	77.3	75.3	73.7	72.7	71.6
67.5°	87.1	82.3	77.4	72.9	69.8	67.5	65.8	64.0	63.2	62.0	61.2
70°	77.0	72.0	67.6	64.2	61.1	59.4	58.3	57.0	56.3	54.7	54.0
72.5°	65.9	62.3	59.1	56.3	53.9	52.3	50.9	49.2	48.0	46.3	45.6
75°	51.9	48.6	46.1	44.3	42.7	40.7	38.6	36.9	36.3	35.7	35.5
77.5°	38.4	36.4	34.6	32.9	31.1	29.6	29.1	28.7	28.6	28.3	28.3
80°	30.2	28.3	27.0	25.1	24.0	24.0	24.0	23.6	23.7	23.7	23.7
82.5°	22.4	20.7	20.0	19.3	19.1	19.2	19.2	19.3	19.2	19.5	19.3
85°	11.6	11.7	12.1	12.0	12.1	12.1	12.6	12.3	12.6	12.1	12.6
87.5°	4.9	5.5	5.8	6.1	6.4	6.4	6.5	6.6	6.8	6.8	7.0
90°	3.2	3.8	4.6	5.5	6.4	7.2	6.9	7.2	7.5	7.7	8.3
92.5°	12.4	16.6	24.2	36.6	48.8	44.3	33.4	24.3	19.2	17.0	15.5
95°	26.3	37.4	62.0	104.8	152.1	170.9	138.6	103.7	70.3	55.0	44.7
97.5°	31.1	43.3	66.7	115.0	193.9	264.8	283.2	258.5	207.1	169.9	135.5
100°	34.6	45.8	66.0	108.6	184.4	272.9	329.6	339.7	316.3	282.7	241.7
102.5°	38.5	48.8	66.9	103.1	170.6	257.9	331.9	366.6	365.9	346.3	320.3
105°	44.9	53.9	69.5	99.1	153.6	231.6	314.3	374.5	403.3	408.8	401.4
107.5°	52.2	60.5	74.2	98.8	142.8	208.5	283.6	351.8	398.6	423.9	434.1
110°	57.1	65.1	78.1	100.0	138.6	195.3	264.2	330.2	383.2	419.5	439.7



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	62.1	70.0	82.0	102.3	136.2	186.5	247.4	308.8	362.9	403.6	429.5
115°	69.7	77.5	88.5	106.0	135.4	177.2	227.1	280.3	330.4	372.8	404.2
117.5°	77.3	84.5	95.3	111.0	135.9	171.6	214.7	259.8	303.0	341.0	372.9
120°	82.1	89.3	99.7	114.6	136.9	169.1	208.3	248.9	287.8	322.4	351.5
122.5°	86.5	94.2	104.3	118.1	138.4	167.5	203.0	240.4	275.6	307.6	334.7
125°	93.0	100.9	111.0	123.6	140.9	165.3	196.2	229.0	260.5	288.1	311.2
127.5°	99.1	107.0	116.7	128.1	143.7	164.4	190.2	219.2	247.1	272.1	293.1
130°	102.9	110.6	120.2	131.1	145.5	163.6	186.9	212.9	238.9	262.2	281.8
132.5°	106.3	113.9	123.1	133.9	146.9	163.4	184.0	207.2	231.0	252.7	271.4
135°	111.0	118.7	127.6	137.5	149.0	163.1	180.1	199.3	219.8	238.6	254.9
137.5°	115.0	122.1	130.8	140.1	150.3	162.4	176.7	192.2	209.0	225.2	239.5
140°	117.2	124.5	132.8	141.5	151.2	162.2	174.6	188.2	202.8	216.6	229.0
142.5°	119.6	126.3	134.4	142.8	152.0	161.8	172.8	184.3	196.8	208.8	219.6
145°	122.5	129.1	136.6	144.3	152.4	161.0	170.2	179.5	189.0	198.2	206.6
147.5°	125.8	131.4	138.3	145.3	152.4	160.0	167.9	175.6	183.2	190.6	196.6
150°	127.6	132.8	139.4	145.5	152.4	159.1	166.2	172.8	179.5	185.6	191.0
152.5°	129.5	134.4	140.1	145.9	151.7	157.9	164.4	170.3	176.0	181.4	186.0
155°	132.6	136.6	141.5	146.1	151.0	155.9	161.6	166.6	171.1	175.5	178.9
157.5°	135.2	138.3	142.2	146.3	150.0	154.1	158.5	162.5	166.3	169.7	172.4
160°	136.6	139.4	142.9	146.3	149.5	152.7	156.5	160.2	163.4	166.2	168.3
162.5°	137.7	140.1	143.2	146.1	148.6	151.3	154.3	157.4	160.1	162.8	164.6
165°	139.2	141.2	143.5	145.5	147.2	149.3	151.6	153.8	155.6	157.6	159.1
167.5°	140.5	141.8	143.4	145.0	145.9	147.2	148.9	150.7	152.1	153.2	154.3
170°	141.2	141.8	143.2	144.3	145.0	145.8	147.2	148.6	149.5	150.7	151.2
172.5°	141.6	141.9	143.2	144.1	144.2	144.6	145.6	146.8	147.5	148.4	148.7
175°	142.0	142.4	142.9	143.5	143.2	143.2	143.7	144.3	144.6	145.2	145.2
177.5°	142.4	142.4	142.6	143.0	142.6	142.4	142.6	142.8	143.0	143.2	143.2
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	422.7	422.6	422.7	422.2	422.7	422.6	422.7	424.6	424.6	424.7	424.9
5°	393.4	393.2	392.6	390.9	392.6	393.2	393.4	394.0	395.5	398.1	397.4
7.5°	367.7	367.5	365.8	365.8	365.8	367.5	367.7	369.2	371.0	372.6	374.5
10°	352.5	352.7	350.4	349.1	350.4	352.7	352.5	353.8	356.4	357.7	359.0
12.5°	337.8	337.0	335.1	333.6	335.1	337.0	337.8	338.8	342.2	343.7	346.3
15°	318.4	316.4	311.9	312.3	311.9	316.4	318.4	317.6	321.0	322.9	323.7
17.5°	295.5	294.1	294.0	291.3	294.0	294.1	295.5	296.9	299.9	302.0	307.4
20°	282.1	281.1	281.5	278.8	281.5	281.1	282.1	285.1	287.0	289.7	294.1
22.5°	271.6	270.6	269.0	268.2	269.0	270.6	271.6	273.7	275.7	279.5	281.8
25°	256.2	254.7	253.2	254.1	253.2	254.7	256.2	257.4	261.1	262.9	266.3
27.5°	240.9	239.8	238.2	238.1	238.2	239.8	240.9	242.0	244.1	247.0	251.1
30°	231.1	230.0	229.3	228.3	229.3	230.0	231.1	232.1	234.2	237.3	240.3
32.5°	221.3	221.0	219.7	219.5	219.7	221.0	221.3	222.8	224.9	227.8	230.4
35°	208.4	207.2	206.8	207.0	206.8	207.2	208.4	209.1	211.0	213.7	216.1
37.5°	196.1	194.6	193.9	193.2	193.9	194.6	196.1	196.2	198.1	199.9	203.3
40°	187.3	185.8	185.4	185.0	185.4	185.8	187.3	187.1	189.1	190.5	193.6
42.5°	177.4	176.8	176.6	175.9	176.6	176.8	177.4	178.5	179.6	181.6	183.8
45°	164.0	163.7	162.6	163.0	162.6	163.7	164.0	164.5	166.6	168.0	170.0
47.5°	149.7	148.9	148.1	148.6	148.1	148.9	149.7	150.5	151.9	153.5	156.3
50°	140.0	139.6	137.9	138.3	137.9	139.6	140.0	140.7	141.7	143.8	146.3
52.5°	130.3	128.8	128.2	127.9	128.2	128.8	130.3	131.0	132.2	134.5	136.4
55°	114.1	112.4	111.7	111.3	111.7	112.4	114.1	115.5	117.0	119.7	121.6
57.5°	98.3	97.9	97.3	97.7	97.3	97.9	98.3	100.5	102.1	104.1	106.5
60°	89.1	89.1	89.1	88.9	89.1	89.1	89.1	91.0	92.3	94.4	96.9
62.5°	81.9	81.4	81.4	81.6	81.4	81.4	81.9	82.8	84.1	85.4	87.6
65°	71.0	70.8	70.1	69.9	70.1	70.8	71.0	71.6	72.7	73.7	75.3
67.5°	60.7	60.1	59.8	59.6	59.8	60.1	60.7	61.2	62.0	63.2	64.0
70°	53.0	52.6	51.4	51.7	51.4	52.6	53.0	54.0	54.7	56.3	57.0
72.5°	44.7	44.3	44.0	43.8	44.0	44.3	44.7	45.6	46.3	48.0	49.2
75°	35.3	35.1	35.0	35.7	35.0	35.1	35.3	35.5	35.7	36.3	36.9
77.5°	28.3	28.3	28.5	28.1	28.5	28.3	28.3	28.3	28.3	28.6	28.7
80°	23.7	23.7	23.6	23.6	23.6	23.7	23.7	23.7	23.7	23.7	23.6
82.5°	19.0	19.2	19.3	19.0	19.3	19.2	19.0	19.3	19.5	19.2	19.3
85°	12.6	12.3	12.7	12.6	12.7	12.3	12.6	12.6	12.1	12.6	12.3
87.5°	7.3	7.0	7.0	7.2	7.0	7.0	7.3	7.0	6.8	6.8	6.6
90°	8.1	8.3	8.6	8.3	8.6	8.3	8.1	8.3	7.7	7.5	7.2
92.5°	15.0	14.1	14.4	13.9	14.4	14.1	15.0	15.5	17.0	19.2	24.3
95°	39.2	36.6	34.6	33.4	34.6	36.6	39.2	44.7	55.0	70.3	103.7
97.5°	114.2	101.3	93.4	91.0	93.4	101.3	114.2	135.5	169.9	207.1	258.5
100°	212.6	191.6	180.3	180.7	180.3	191.6	212.6	241.7	282.7	316.3	339.7
102.5°	297.7	281.0	271.7	265.0	271.7	281.0	297.7	320.3	346.3	365.9	366.6
105°	388.1	377.2	367.9	366.5	367.9	377.2	388.1	401.4	408.8	403.3	374.5
107.5°	434.4	430.6	427.5	424.9	427.5	430.6	434.4	434.1	423.9	398.6	351.8
110°	447.8	450.0	449.5	448.9	449.5	450.0	447.8	439.7	419.5	383.2	330.2



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	444.3	451.4	453.6	453.7	453.6	451.4	444.3	429.5	403.6	362.9	308.8
115°	425.8	438.5	444.3	445.7	444.3	438.5	425.8	404.2	372.8	330.4	280.3
117.5°	395.5	410.0	418.2	420.2	418.2	410.0	395.5	372.9	341.0	303.0	259.8
120°	374.2	390.4	397.3	399.0	397.3	390.4	374.2	351.5	322.4	287.8	248.9
122.5°	354.9	369.4	377.0	379.2	377.0	369.4	354.9	334.7	307.6	275.6	240.4
125°	329.6	342.3	349.5	351.5	349.5	342.3	329.6	311.2	288.1	260.5	229.0
127.5°	309.5	320.3	326.9	328.6	326.9	320.3	309.5	293.1	272.1	247.1	219.2
130°	297.0	307.4	313.5	315.8	313.5	307.4	297.0	281.8	262.2	238.9	212.9
132.5°	285.8	296.1	301.5	303.1	301.5	296.1	285.8	271.4	252.7	231.0	207.2
135°	269.1	277.8	282.9	284.9	282.9	277.8	269.1	254.9	238.6	219.8	199.3
137.5°	251.3	260.1	264.4	265.8	264.4	260.1	251.3	239.5	225.2	209.0	192.2
140°	240.0	248.1	252.7	252.4	252.7	248.1	240.0	229.0	216.6	202.8	188.2
142.5°	228.9	236.1	240.2	239.9	240.2	236.1	228.9	219.6	208.8	196.8	184.3
145°	213.8	219.8	222.2	222.7	222.2	219.8	213.8	206.6	198.2	189.0	179.5
147.5°	202.0	206.1	208.3	208.6	208.3	206.1	202.0	196.6	190.6	183.2	175.6
150°	195.3	198.5	200.2	200.2	200.2	198.5	195.3	191.0	185.6	179.5	172.8
152.5°	189.3	192.2	193.3	193.3	193.3	192.2	189.3	186.0	181.4	176.0	170.3
155°	181.5	183.8	184.4	184.7	184.4	183.8	181.5	178.9	175.5	171.1	166.6
157.5°	174.6	176.3	176.8	176.8	176.8	176.3	174.6	172.4	169.7	166.3	162.5
160°	170.2	172.0	172.0	171.7	172.0	172.0	170.2	168.3	166.2	163.4	160.2
162.5°	165.9	167.4	167.4	167.1	167.4	167.4	165.9	164.6	162.8	160.1	157.4
165°	160.2	161.3	161.0	161.0	161.0	161.3	160.2	159.1	157.6	155.6	153.8
167.5°	154.7	155.6	155.3	155.3	155.3	155.6	154.7	154.3	153.2	152.1	150.7
170°	151.6	152.1	151.8	151.8	151.8	152.1	151.6	151.2	150.7	149.5	148.6
172.5°	148.8	149.4	148.9	148.6	148.9	149.4	148.8	148.7	148.4	147.5	146.8
175°	145.2	145.5	145.2	145.0	145.2	145.5	145.2	145.2	145.2	144.6	144.3
177.5°	143.0	143.2	142.8	142.8	142.8	143.2	143.0	143.2	143.2	143.0	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	423.5	425.7	427.8	429.7	432.8	434.1	436.1	436.9	439.1	442.5	445.2
5°	397.8	400.8	404.8	408.0	413.1	417.1	421.5	425.7	430.6	437.7	443.9
7.5°	375.9	378.9	383.7	389.7	395.3	401.0	407.0	412.7	419.7	429.8	439.8
10°	361.5	365.1	370.8	377.2	384.3	389.8	396.8	404.0	412.8	424.4	436.3
12.5°	349.0	351.7	358.3	364.4	372.4	379.4	386.3	394.8	404.7	417.0	431.5
15°	329.2	333.0	339.4	346.3	354.7	362.1	371.0	381.2	390.9	406.1	423.5
17.5°	309.2	315.0	321.8	329.5	335.7	345.9	355.6	366.1	378.1	394.1	413.4
20°	296.5	301.1	307.4	318.5	326.7	334.5	343.4	356.5	367.5	385.8	405.7
22.5°	285.7	289.0	296.1	305.3	314.9	323.8	333.0	345.4	359.1	376.3	397.9
25°	269.7	275.1	280.4	287.0	297.3	308.1	318.0	328.6	343.1	361.5	384.8
27.5°	254.1	258.9	264.2	272.3	280.1	290.2	300.6	312.7	328.2	347.7	371.5
30°	244.1	247.7	252.7	263.1	270.1	278.8	291.0	301.8	316.3	337.0	362.1
32.5°	233.7	238.4	243.9	251.8	260.6	268.8	279.9	291.6	306.4	326.8	352.5
35°	219.0	224.5	230.0	235.9	244.7	253.2	262.5	275.4	290.4	310.2	335.4
37.5°	205.5	209.9	214.3	221.7	229.9	238.1	246.8	259.5	273.6	295.0	318.1
40°	196.8	200.8	204.2	211.8	219.8	228.5	237.1	248.3	263.4	283.4	305.8
42.5°	187.4	191.0	195.7	201.9	210.5	217.8	226.4	237.0	251.3	271.6	291.2
45°	173.3	177.4	181.4	187.3	195.8	203.1	210.7	220.7	235.4	252.1	269.5
47.5°	158.5	162.7	167.3	173.0	180.4	187.8	195.3	204.2	217.6	234.0	245.8
50°	149.1	152.5	157.1	162.8	169.7	177.4	184.3	194.0	206.7	219.6	229.8
52.5°	139.4	142.5	147.7	153.7	160.0	166.8	174.1	182.4	193.9	206.0	214.2
55°	124.3	128.0	132.4	138.3	144.6	150.3	157.3	165.8	175.0	184.1	189.6
57.5°	110.1	113.2	116.9	122.9	128.4	135.2	141.5	148.1	156.6	163.5	167.1
60°	99.7	102.6	107.3	112.7	117.7	123.7	130.9	137.5	144.0	149.5	152.3
62.5°	90.0	93.3	97.4	102.3	107.9	113.5	119.8	125.4	131.1	135.8	137.8
65°	77.3	80.0	83.0	87.6	92.1	97.8	102.7	108.4	112.7	115.3	117.0
67.5°	65.8	67.5	69.8	72.9	77.4	82.3	87.1	91.6	95.1	96.9	98.4
70°	58.3	59.4	61.1	64.2	67.6	72.0	77.0	80.1	83.2	84.7	86.3
72.5°	50.9	52.3	53.9	56.3	59.1	62.3	65.9	69.8	71.5	73.3	74.2
75°	38.6	40.7	42.7	44.3	46.1	48.6	51.9	54.3	55.3	56.8	57.0
77.5°	29.1	29.6	31.1	32.9	34.6	36.4	38.4	40.6	41.1	41.8	42.4
80°	24.0	24.0	24.0	25.1	27.0	28.3	30.2	31.3	32.1	32.3	32.4
82.5°	19.2	19.2	19.1	19.3	20.0	20.7	22.4	23.7	24.4	24.2	23.8
85°	12.6	12.1	12.1	12.0	12.1	11.7	11.6	12.3	13.5	13.5	13.1
87.5°	6.5	6.4	6.4	6.1	5.8	5.5	4.9	4.9	4.7	5.2	5.0
90°	6.9	7.2	6.4	5.5	4.6	3.8	3.2	2.6	1.7	1.1	0.6
92.5°	33.4	44.3	48.8	36.6	24.2	16.6	12.4	9.9	7.7	5.3	3.6
95°	138.6	170.9	152.1	104.8	62.0	37.4	26.3	18.8	13.9	10.7	9.8
97.5°	283.2	264.8	193.9	115.0	66.7	43.3	31.1	23.7	19.5	17.0	16.7
100°	329.6	272.9	184.4	108.6	66.0	45.8	34.6	27.6	23.6	21.6	21.4
102.5°	331.9	257.9	170.6	103.1	66.9	48.8	38.5	32.3	28.5	26.7	26.2
105°	314.3	231.6	153.6	99.1	69.5	53.9	44.9	39.5	36.0	34.3	33.4
107.5°	283.6	208.5	142.8	98.8	74.2	60.5	52.2	47.0	43.7	42.0	41.2
110°	264.2	195.3	138.6	100.0	78.1	65.1	57.1	52.2	49.0	47.5	46.6



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	247.4	186.5	136.2	102.3	82.0	70.0	62.1	57.2	54.1	52.6	51.8
115°	227.1	177.2	135.4	106.0	88.5	77.5	69.7	64.8	62.0	60.3	59.0
117.5°	214.7	171.6	135.9	111.0	95.3	84.5	77.3	71.8	69.1	67.7	66.4
120°	208.3	169.1	136.9	114.6	99.7	89.3	82.1	76.6	73.8	72.3	71.4
122.5°	203.0	167.5	138.4	118.1	104.3	94.2	86.5	81.3	78.1	76.7	75.8
125°	196.2	165.3	140.9	123.6	111.0	100.9	93.0	87.6	84.4	82.7	82.1
127.5°	190.2	164.4	143.7	128.1	116.7	107.0	99.1	93.1	89.9	87.7	86.9
130°	186.9	163.6	145.5	131.1	120.2	110.6	102.9	96.8	93.4	90.7	89.9
132.5°	184.0	163.4	146.9	133.9	123.1	113.9	106.3	100.3	96.1	93.3	92.2
135°	180.1	163.1	149.0	137.5	127.6	118.7	111.0	104.8	100.5	97.3	96.2
137.5°	176.7	162.4	150.3	140.1	130.8	122.1	115.0	108.9	104.4	101.3	100.0
140°	174.6	162.2	151.2	141.5	132.8	124.5	117.2	111.5	106.9	104.0	102.6
142.5°	172.8	161.8	152.0	142.8	134.4	126.3	119.6	113.8	109.7	106.6	105.3
145°	170.2	161.0	152.4	144.3	136.6	129.1	122.5	117.6	113.2	110.6	109.7
147.5°	167.9	160.0	152.4	145.3	138.3	131.4	125.8	121.1	117.3	114.8	114.3
150°	166.2	159.1	152.4	145.5	139.4	132.8	127.6	123.6	119.8	117.6	117.2
152.5°	164.4	157.9	151.7	145.9	140.1	134.4	129.5	125.9	122.6	120.3	120.3
155°	161.6	155.9	151.0	146.1	141.5	136.6	132.6	129.4	126.5	124.7	124.7
157.5°	158.5	154.1	150.0	146.3	142.2	138.3	135.2	132.5	130.0	128.6	128.3
160°	156.5	152.7	149.5	146.3	142.9	139.4	136.6	134.5	132.2	131.1	131.1
162.5°	154.3	151.3	148.6	146.1	143.2	140.1	137.7	135.9	134.1	133.1	133.1
165°	151.6	149.3	147.2	145.5	143.5	141.2	139.2	138.0	136.6	136.0	136.2
167.5°	148.9	147.2	145.9	145.0	143.4	141.8	140.5	139.7	138.6	138.3	138.6
170°	147.2	145.8	145.0	144.3	143.2	141.8	141.2	140.6	139.7	139.4	140.0
172.5°	145.6	144.6	144.2	144.1	143.2	141.9	141.6	141.3	140.6	140.6	141.0
175°	143.7	143.2	143.2	143.5	142.9	142.4	142.0	142.0	141.5	141.8	142.0
177.5°	142.6	142.4	142.6	143.0	142.6	142.4	142.4	142.4	142.1	142.4	142.6
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	446.1	447.8	450.0	453.1	455.6	457.7	458.1	458.8	460.3	462.8	464.8
5°	449.1	453.4	460.4	467.2	474.7	480.8	486.5	490.5	494.2	502.2	508.7
7.5°	448.1	457.9	468.9	481.1	493.6	505.6	516.7	526.8	536.7	548.4	561.6
10°	447.5	458.9	473.8	489.5	506.8	523.7	540.1	552.8	567.5	580.9	597.8
12.5°	444.7	461.1	478.7	498.9	520.2	539.6	561.2	578.7	595.7	614.9	634.5
15°	440.8	460.8	483.2	510.0	542.3	565.8	587.9	618.5	639.4	660.2	688.4
17.5°	434.0	458.4	486.3	521.1	548.0	579.8	612.9	637.1	665.2	694.6	720.1
20°	428.5	456.8	488.2	522.4	556.8	591.1	623.2	652.1	681.2	715.2	736.1
22.5°	423.1	451.0	483.6	519.9	556.8	593.1	629.4	663.3	696.0	730.3	757.0
25°	411.4	444.7	480.0	517.1	553.5	593.4	636.7	674.5	714.9	750.3	775.6
27.5°	399.7	430.2	465.3	502.9	543.4	590.5	641.5	684.4	725.0	750.3	758.2
30°	389.0	421.3	453.6	491.8	535.7	588.2	642.4	691.6	724.8	735.9	727.7
32.5°	378.2	407.5	439.4	478.6	525.1	582.6	643.6	687.4	707.4	699.0	665.7
35°	359.2	385.6	416.5	455.7	509.2	579.5	638.6	668.2	663.3	615.8	553.1
37.5°	338.8	360.4	389.0	429.9	492.8	567.2	617.0	621.4	578.6	505.7	433.3
40°	322.7	342.1	371.5	414.3	480.0	555.1	595.3	577.6	511.4	430.2	369.8
42.5°	307.0	323.4	351.8	397.9	467.8	538.4	563.0	524.5	448.0	371.3	316.3
45°	280.5	296.0	324.4	371.7	443.0	506.8	503.5	436.7	360.1	298.4	252.8
47.5°	255.4	268.9	295.6	343.9	413.8	459.3	429.1	357.9	293.0	243.4	210.9
50°	237.7	250.9	277.5	325.2	390.4	423.5	380.5	311.9	252.4	211.4	185.6
52.5°	220.6	233.6	257.9	304.4	362.1	382.0	335.7	272.1	222.5	187.1	164.9
55°	196.8	206.7	228.5	273.0	316.1	320.7	273.7	220.5	179.7	155.0	139.8
57.5°	172.5	181.0	202.6	238.0	268.2	265.9	221.4	175.4	147.9	129.6	118.5
60°	156.7	165.1	184.1	214.4	237.3	229.3	188.4	151.4	127.8	114.4	105.6
62.5°	141.9	148.5	166.3	188.5	204.9	195.8	161.1	130.4	111.7	100.4	93.4
65°	120.6	126.0	140.1	151.8	160.9	152.1	123.3	102.0	88.5	80.6	75.8
67.5°	100.4	103.7	112.7	116.9	123.4	113.7	92.7	78.4	70.8	64.1	60.7
70°	87.6	90.0	94.8	98.2	99.9	90.0	74.4	64.0	57.6	52.8	50.7
72.5°	74.8	77.0	77.9	80.7	79.8	70.6	59.8	51.5	46.9	43.7	41.0
75°	57.2	58.1	57.2	56.0	53.6	47.1	39.7	35.5	32.1	30.6	29.6
77.5°	41.7	41.3	40.1	38.3	34.1	30.0	26.0	24.6	23.2	22.3	22.0
80°	32.1	31.3	30.2	27.3	23.7	20.9	20.0	19.0	18.4	17.4	17.3
82.5°	23.9	23.4	21.5	19.2	16.6	15.2	14.5	14.1	13.5	13.0	13.0
85°	12.7	12.1	10.0	8.7	8.4	8.0	7.8	7.8	7.0	6.8	6.8
87.5°	4.3	3.5	3.6	3.2	3.3	3.2	3.5	3.4	3.4	3.5	3.3
90°	1.1	1.7	2.6	3.2	3.8	4.6	5.5	6.4	7.2	6.9	7.2
92.5°	5.3	7.7	9.9	12.4	16.6	24.2	36.6	48.8	44.3	33.4	24.3
95°	10.7	13.9	18.8	26.3	37.4	62.0	104.8	152.1	170.9	138.6	103.7
97.5°	17.0	19.5	23.7	31.1	43.3	66.7	115.0	193.9	264.8	283.2	258.5
100°	21.6	23.6	27.6	34.6	45.8	66.0	108.6	184.4	272.9	329.6	339.7
102.5°	26.7	28.5	32.3	38.5	48.8	66.9	103.1	170.6	257.9	331.9	366.6
105°	34.3	36.0	39.5	44.9	53.9	69.5	99.1	153.6	231.6	314.3	374.5
107.5°	42.0	43.7	47.0	52.2	60.5	74.2	98.8	142.8	208.5	283.6	351.8
110°	47.5	49.0	52.2	57.1	65.1	78.1	100.0	138.6	195.3	264.2	330.2



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	52.6	54.1	57.2	62.1	70.0	82.0	102.3	136.2	186.5	247.4	308.8
115°	60.3	62.0	64.8	69.7	77.5	88.5	106.0	135.4	177.2	227.1	280.3
117.5°	67.7	69.1	71.8	77.3	84.5	95.3	111.0	135.9	171.6	214.7	259.8
120°	72.3	73.8	76.6	82.1	89.3	99.7	114.6	136.9	169.1	208.3	248.9
122.5°	76.7	78.1	81.3	86.5	94.2	104.3	118.1	138.4	167.5	203.0	240.4
125°	82.7	84.4	87.6	93.0	100.9	111.0	123.6	140.9	165.3	196.2	229.0
127.5°	87.7	89.9	93.1	99.1	107.0	116.7	128.1	143.7	164.4	190.2	219.2
130°	90.7	93.4	96.8	102.9	110.6	120.2	131.1	145.5	163.6	186.9	212.9
132.5°	93.3	96.1	100.3	106.3	113.9	123.1	133.9	146.9	163.4	184.0	207.2
135°	97.3	100.5	104.8	111.0	118.7	127.6	137.5	149.0	163.1	180.1	199.3
137.5°	101.3	104.4	108.9	115.0	122.1	130.8	140.1	150.3	162.4	176.7	192.2
140°	104.0	106.9	111.5	117.2	124.5	132.8	141.5	151.2	162.2	174.6	188.2
142.5°	106.6	109.7	113.8	119.6	126.3	134.4	142.8	152.0	161.8	172.8	184.3
145°	110.6	113.2	117.6	122.5	129.1	136.6	144.3	152.4	161.0	170.2	179.5
147.5°	114.8	117.3	121.1	125.8	131.4	138.3	145.3	152.4	160.0	167.9	175.6
150°	117.6	119.8	123.6	127.6	132.8	139.4	145.5	152.4	159.1	166.2	172.8
152.5°	120.3	122.6	125.9	129.5	134.4	140.1	145.9	151.7	157.9	164.4	170.3
155°	124.7	126.5	129.4	132.6	136.6	141.5	146.1	151.0	155.9	161.6	166.6
157.5°	128.6	130.0	132.5	135.2	138.3	142.2	146.3	150.0	154.1	158.5	162.5
160°	131.1	132.2	134.5	136.6	139.4	142.9	146.3	149.5	152.7	156.5	160.2
162.5°	133.1	134.1	135.9	137.7	140.1	143.2	146.1	148.6	151.3	154.3	157.4
165°	136.0	136.6	138.0	139.2	141.2	143.5	145.5	147.2	149.3	151.6	153.8
167.5°	138.3	138.6	139.7	140.5	141.8	143.4	145.0	145.9	147.2	148.9	150.7
170°	139.4	139.7	140.6	141.2	141.8	143.2	144.3	145.0	145.8	147.2	148.6
172.5°	140.6	140.6	141.3	141.6	141.9	143.2	144.1	144.2	144.6	145.6	146.8
175°	141.8	141.5	142.0	142.0	142.4	142.9	143.5	143.2	143.2	143.7	144.3
177.5°	142.4	142.1	142.4	142.4	142.4	142.6	143.0	142.6	142.4	142.6	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4	142.4



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	443.7	443.7	443.7	443.7	443.7	443.7	443.7
2.5°	468.1	468.1	468.6	470.9	471.2	473.2	472.6
5°	514.4	518.0	519.3	525.1	528.4	529.9	526.9
7.5°	571.0	581.2	586.0	592.1	597.3	598.9	594.8
10°	612.4	623.1	631.9	637.5	642.6	646.0	650.4
12.5°	652.3	665.4	673.9	681.7	687.0	691.3	692.0
15°	695.8	715.5	730.5	741.6	747.1	749.9	748.8
17.5°	739.6	757.9	768.6	779.8	787.4	787.8	788.1
20°	764.3	782.2	794.6	802.9	811.5	811.1	813.0
22.5°	780.9	795.0	804.5	810.5	813.4	812.0	812.4
25°	788.6	792.9	791.2	781.5	778.9	770.1	771.6
27.5°	748.7	729.0	708.5	682.2	661.5	644.9	645.7
30°	694.5	659.5	619.6	586.2	556.2	547.8	529.9
32.5°	618.6	566.2	519.5	488.3	462.6	455.6	440.0
35°	490.1	439.1	391.1	362.2	350.8	334.8	334.7
37.5°	380.9	336.1	310.7	289.0	277.7	268.0	267.1
40°	320.4	285.5	266.3	250.7	239.5	232.3	230.6
42.5°	278.2	250.0	232.0	222.3	213.7	209.9	207.2
45°	227.1	208.1	195.7	186.9	183.0	180.1	178.6
47.5°	190.0	177.3	168.8	162.9	159.7	156.7	157.5
50°	169.8	159.4	153.1	147.6	145.1	143.0	143.2
52.5°	153.5	144.1	139.1	135.1	132.1	130.5	129.9
55°	130.3	124.4	119.3	116.4	114.7	112.7	112.1
57.5°	111.1	106.6	102.4	99.2	98.7	96.8	97.0
60°	98.4	94.6	91.2	89.4	88.1	86.4	87.0
62.5°	87.9	84.7	81.6	80.2	78.8	77.6	77.9
65°	72.0	69.0	67.0	66.3	65.7	65.1	64.6
67.5°	57.4	55.5	54.3	52.7	51.5	51.4	50.8
70°	48.3	45.7	43.7	41.6	41.0	40.8	41.0
72.5°	38.6	37.1	36.5	35.5	35.4	34.9	35.2
75°	29.0	28.5	28.1	27.3	27.3	27.3	27.3
77.5°	21.4	21.1	20.9	20.7	20.5	20.2	20.2
80°	16.7	16.6	16.1	16.1	16.0	16.1	16.0
82.5°	12.6	12.6	12.2	12.2	12.0	11.9	12.0
85°	6.4	6.3	6.7	6.3	6.4	6.1	6.4
87.5°	3.3	3.3	3.3	3.3	3.2	3.6	3.2
90°	7.5	7.7	8.3	8.1	8.3	8.6	8.3
92.5°	19.2	17.0	15.5	15.0	14.1	14.4	13.9
95°	70.3	55.0	44.7	39.2	36.6	34.6	33.4
97.5°	207.1	169.9	135.5	114.2	101.3	93.4	91.0
100°	316.3	282.7	241.7	212.6	191.6	180.3	180.7
102.5°	365.9	346.3	320.3	297.7	281.0	271.7	265.0
105°	403.3	408.8	401.4	388.1	377.2	367.9	366.5
107.5°	398.6	423.9	434.1	434.4	430.6	427.5	424.9
110°	383.2	419.5	439.7	447.8	450.0	449.5	448.9



TEST NUMBER: P332242-930

CATALOG NUMBER: S123RDIP-S340D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	362.9	403.6	429.5	444.3	451.4	453.6	453.7
115°	330.4	372.8	404.2	425.8	438.5	444.3	445.7
117.5°	303.0	341.0	372.9	395.5	410.0	418.2	420.2
120°	287.8	322.4	351.5	374.2	390.4	397.3	399.0
122.5°	275.6	307.6	334.7	354.9	369.4	377.0	379.2
125°	260.5	288.1	311.2	329.6	342.3	349.5	351.5
127.5°	247.1	272.1	293.1	309.5	320.3	326.9	328.6
130°	238.9	262.2	281.8	297.0	307.4	313.5	315.8
132.5°	231.0	252.7	271.4	285.8	296.1	301.5	303.1
135°	219.8	238.6	254.9	269.1	277.8	282.9	284.9
137.5°	209.0	225.2	239.5	251.3	260.1	264.4	265.8
140°	202.8	216.6	229.0	240.0	248.1	252.7	252.4
142.5°	196.8	208.8	219.6	228.9	236.1	240.2	239.9
145°	189.0	198.2	206.6	213.8	219.8	222.2	222.7
147.5°	183.2	190.6	196.6	202.0	206.1	208.3	208.6
150°	179.5	185.6	191.0	195.3	198.5	200.2	200.2
152.5°	176.0	181.4	186.0	189.3	192.2	193.3	193.3
155°	171.1	175.5	178.9	181.5	183.8	184.4	184.7
157.5°	166.3	169.7	172.4	174.6	176.3	176.8	176.8
160°	163.4	166.2	168.3	170.2	172.0	172.0	171.7
162.5°	160.1	162.8	164.6	165.9	167.4	167.4	167.1
165°	155.6	157.6	159.1	160.2	161.3	161.0	161.0
167.5°	152.1	153.2	154.3	154.7	155.6	155.3	155.3
170°	149.5	150.7	151.2	151.6	152.1	151.8	151.8
172.5°	147.5	148.4	148.7	148.8	149.4	148.9	148.6
175°	144.6	145.2	145.2	145.2	145.5	145.2	145.0
177.5°	143.0	143.2	143.2	143.0	143.2	142.8	142.8
180°	142.4	142.4	142.4	142.4	142.4	142.4	142.4

(END OF REPORT)